

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333017-940

Luminaire Tested: **S124RDIW-S350D470U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333017-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D470U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2946.5 lumens  
Efficiency: N/A  
Efficacy: 128.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333017-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333017-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4451	4451	4451
5°	4460	4406	4433
10°	4432	4353	4353
15°	4381	4262	4229
20°	4312	4141	4064
25°	4222	4000	3899
30°	4135	3852	3691
35°	4039	3698	3482
40°	3923	3523	3256
45°	3817	3350	3027
50°	3695	3149	2783
55°	3564	2940	2519
60°	3421	2713	2249
65°	3289	2428	1983
70°	3099	2110	1683
75°	2857	1753	1369
80°	2492	1334	1255
85°	2112	1213	1130



TEST NUMBER: P333017-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.8	1.8
10°-20°	144.4	4.9
20°-30°	208.5	7.1
30°-40°	236.4	8.0
40°-50°	228.2	7.7
50°-60°	189.8	6.4
60°-70°	131.1	4.4
70°-80°	66.4	2.3
80°-90°	18.6	0.6
90°-100°	18.5	0.6
100°-110°	117.8	4.0
110°-120°	225.4	7.6
120°-130°	286.1	9.7
130°-140°	306.1	10.4
140°-150°	286.3	9.7
150°-160°	230.9	7.8
160°-170°	148.9	5.1
170°-180°	51.3	1.7
0°-30°	404.7	13.7
0°-40°	641.0	21.8
0°-60°	1059.1	35.9
0°-90°	1275.1	43.3
90°-120°	361.7	12.3
90°-150°	1240.3	42.1
90°-180°	1671.0	56.7
0°-180°	2946.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	548	544	548	547	52
15°	524	520	510	509	506	148
25°	474	466	449	442	438	218
35°	410	396	375	361	353	256
45°	334	318	293	273	265	258
55°	253	236	209	188	179	226
65°	172	154	127	110	104	170
75°	92	76	56	47	44	97
85°	23	15	13	12	12	26
90°	1	6	9	11	12	2
95°	22	9	9	11	12	29
105°	122	124	126	129	115	127
115°	227	228	228	229	229	223
125°	319	321	320	321	322	285
135°	396	396	397	398	399	305
145°	457	458	458	458	459	285
155°	501	501	500	501	500	231
165°	528	526	526	529	526	149
175°	540	538	538	541	537	51
180°	540	540	540	540	540	



TEST NUMBER: P333017-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	552.6	552.2	552.0	551.7	551.3	550.8	550.0	549.2	548.3	547.5	548.3
5°	550.4	550.0	549.7	549.3	548.8	548.1	547.0	545.9	544.7	543.7	544.6
7.5°	545.4	545.0	544.7	544.2	543.9	542.9	541.4	539.9	538.5	537.1	537.6
10°	540.6	540.2	539.8	539.3	538.8	537.7	536.0	534.3	532.6	531.0	531.4
12.5°	534.6	534.0	533.5	533.0	532.4	531.2	529.1	527.2	525.2	523.2	523.4
15°	524.2	523.3	522.5	521.7	520.8	519.2	516.9	514.5	512.2	509.9	509.7
17.5°	511.7	510.4	509.2	508.0	506.8	504.7	501.9	499.1	496.3	493.5	492.9
20°	501.9	500.6	499.4	498.2	497.0	494.8	491.6	488.4	485.2	482.0	481.3
22.5°	491.1	489.6	488.3	487.0	485.5	483.1	479.7	476.4	473.0	469.5	468.4
25°	474.0	472.3	470.6	469.0	467.3	464.5	460.7	456.8	452.9	449.1	447.5
27.5°	456.1	454.0	451.8	449.8	447.6	444.5	440.4	436.3	432.2	428.1	426.1
30°	443.6	441.2	438.9	436.6	434.3	430.9	426.4	422.0	417.6	413.2	410.9
32.5°	430.4	427.8	425.2	422.5	419.8	416.3	411.7	407.2	402.6	398.1	395.3
35°	409.8	406.8	403.9	400.8	397.8	394.0	389.3	384.6	380.0	375.2	372.0
37.5°	387.8	384.7	381.7	378.5	375.4	371.3	366.0	360.9	355.7	350.5	347.0
40°	372.3	369.2	366.0	363.0	359.9	355.7	350.4	345.0	339.7	334.3	330.4
42.5°	357.4	354.2	350.9	347.7	344.5	340.0	334.5	328.9	323.3	317.7	313.7
45°	334.3	330.8	327.3	323.9	320.4	315.8	310.2	304.6	299.0	293.4	288.7
47.5°	310.4	306.8	303.3	299.6	296.0	291.3	285.5	279.6	273.8	268.0	263.1
50°	294.2	290.5	286.9	283.2	279.6	274.7	268.8	262.7	256.7	250.7	246.0
52.5°	277.7	274.0	270.5	266.9	263.3	258.4	252.3	246.1	240.0	233.8	229.1
55°	253.2	249.5	245.8	242.0	238.3	233.3	227.2	221.1	215.0	208.9	204.0
57.5°	229.1	225.2	221.3	217.4	213.5	208.6	202.5	196.5	190.6	184.5	179.6
60°	211.9	208.1	204.4	200.6	196.9	192.0	186.0	179.9	174.0	168.0	163.1
62.5°	196.4	192.4	188.5	184.7	180.7	175.8	169.6	163.5	157.3	151.1	146.6
65°	172.2	168.2	164.2	160.2	156.0	151.1	145.1	139.0	133.0	127.1	123.1
67.5°	147.1	143.3	139.4	135.5	131.7	127.0	121.4	115.8	110.2	104.7	101.2
70°	131.3	127.3	123.4	119.5	115.5	110.8	105.5	100.1	94.8	89.4	86.4
72.5°	114.4	110.8	107.3	103.7	100.1	95.9	90.8	85.7	80.7	75.6	73.0
75°	91.6	88.1	84.6	81.1	77.7	73.7	69.4	64.9	60.5	56.2	53.9
77.5°	68.5	65.5	62.6	59.7	56.7	53.4	49.8	46.3	42.7	39.1	37.9
80°	53.6	50.9	48.2	45.5	42.7	39.9	37.2	34.3	31.5	28.7	28.4
82.5°	40.8	38.3	35.8	33.3	30.8	28.7	27.1	25.5	23.9	22.3	22.1
85°	22.8	21.0	19.1	17.1	15.2	14.2	13.9	13.6	13.4	13.1	12.9
87.5°	8.0	7.6	7.2	6.8	6.4	6.2	6.3	6.3	6.4	6.5	6.5
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	5.1	5.2	5.2	5.3	5.4	5.7	6.4	7.1	7.8	8.6	9.1
95°	22.2	19.2	16.1	13.1	10.0	8.6	8.6	8.7	8.8	8.9	9.5
97.5°	47.2	49.1	51.0	52.9	54.8	50.7	40.8	30.7	20.7	10.7	10.7
100°	66.3	67.9	69.6	71.2	72.8	67.3	54.9	42.5	30.1	17.7	16.2
102.5°	87.7	88.8	90.0	91.1	92.4	92.1	90.5	88.9	87.3	85.7	69.2
105°	121.6	122.2	122.7	123.2	123.8	124.3	124.8	125.2	125.6	126.1	126.9
107.5°	153.3	153.6	153.8	154.1	154.4	154.8	155.3	156.0	156.6	157.2	157.6
110°	174.6	174.9	175.1	175.4	175.7	176.0	176.6	177.2	177.7	178.3	178.4



TEST NUMBER: P333017-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.3	195.7	196.3	196.7	197.2	197.6	197.9	198.0	198.3	198.6	198.6
115°	227.1	227.4	227.7	227.9	228.2	228.3	228.2	228.1	228.0	227.9	228.1
117.5°	255.8	256.2	256.5	256.9	257.3	257.5	257.7	257.9	258.2	258.3	258.2
120°	275.2	275.5	275.9	276.3	276.6	276.8	276.7	276.6	276.5	276.4	276.6
122.5°	293.3	293.6	293.7	294.0	294.2	294.4	294.4	294.6	294.7	294.9	295.0
125°	319.2	319.6	319.9	320.3	320.7	320.7	320.6	320.4	320.2	320.0	320.3
127.5°	343.8	343.9	344.0	344.1	344.2	344.5	344.8	345.3	345.7	346.1	346.1
130°	359.6	359.7	359.9	360.0	360.1	360.3	360.5	360.8	361.1	361.3	361.4
132.5°	374.3	374.3	374.5	374.7	374.9	375.1	375.5	375.8	376.1	376.5	376.6
135°	396.0	395.9	395.8	395.7	395.7	395.8	396.2	396.5	396.9	397.3	397.4
137.5°	415.4	415.4	415.4	415.4	415.5	415.7	416.1	416.5	416.9	417.3	417.5
140°	427.9	428.1	428.3	428.5	428.6	428.8	429.0	429.3	429.4	429.6	429.9
142.5°	439.3	439.6	440.0	440.2	440.6	440.8	440.9	441.0	441.1	441.2	441.4
145°	456.6	456.9	457.2	457.4	457.7	457.9	457.9	457.9	457.9	457.9	458.0
147.5°	470.5	471.0	471.4	472.0	472.5	472.7	472.6	472.5	472.4	472.3	472.4
150°	480.5	480.9	481.3	481.6	482.0	482.1	482.0	481.9	481.8	481.7	481.7
152.5°	488.9	489.2	489.5	489.7	490.1	490.1	490.0	489.8	489.6	489.5	489.6
155°	500.7	500.8	500.9	501.0	501.1	501.0	500.7	500.4	500.2	499.9	500.2
157.5°	510.7	510.6	510.5	510.5	510.4	510.2	510.0	509.6	509.3	509.1	509.5
160°	516.5	516.2	515.9	515.7	515.4	515.2	515.1	515.1	515.0	514.9	515.4
162.5°	521.7	521.3	520.9	520.6	520.3	520.0	520.0	519.9	519.8	519.7	520.2
165°	528.2	527.7	527.3	526.8	526.4	526.2	526.2	526.2	526.2	526.2	526.9
167.5°	533.3	532.9	532.4	532.0	531.5	531.2	531.2	531.1	531.1	531.0	531.8
170°	536.3	535.7	535.2	534.7	534.1	533.9	534.0	534.0	534.1	534.2	534.9
172.5°	538.2	537.7	537.2	536.6	536.1	535.8	535.9	536.0	536.1	536.2	536.9
175°	540.3	539.8	539.2	538.7	538.1	538.0	538.1	538.1	538.2	538.3	539.1
177.5°	541.3	540.8	540.3	539.8	539.3	539.1	539.2	539.4	539.5	539.7	540.2
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333017-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	549.2	550.0	550.8	551.2	551.1	551.1	551.0	550.9
5°	545.5	546.4	547.4	547.8	547.6	547.4	547.2	547.0
7.5°	538.2	538.9	539.5	539.6	539.3	539.0	538.7	538.4
10°	531.7	532.1	532.4	532.4	532.1	531.7	531.4	531.0
12.5°	523.6	523.9	524.1	524.0	523.4	522.9	522.4	521.8
15°	509.5	509.3	509.1	508.7	508.0	507.4	506.8	506.0
17.5°	492.4	492.0	491.4	490.6	489.6	488.7	487.7	486.7
20°	480.5	479.7	479.0	478.0	476.8	475.5	474.4	473.1
22.5°	467.3	466.1	465.0	464.0	463.0	462.0	461.0	459.9
25°	445.9	444.3	442.7	441.5	440.5	439.5	438.6	437.7
27.5°	424.1	422.1	420.2	418.6	417.1	415.8	414.5	413.1
30°	408.5	406.2	403.9	401.9	400.4	399.0	397.4	395.9
32.5°	392.6	389.9	387.2	385.0	383.6	382.2	380.8	379.3
35°	368.8	365.7	362.5	360.1	358.4	356.7	355.0	353.3
37.5°	343.4	339.8	336.3	333.6	331.9	330.2	328.5	326.8
40°	326.4	322.4	318.5	315.8	314.1	312.4	310.7	309.0
42.5°	309.7	305.7	301.7	298.8	297.0	295.2	293.5	291.8
45°	284.2	279.6	274.9	271.8	270.1	268.4	266.7	265.1
47.5°	258.4	253.6	248.9	245.6	243.7	241.8	240.0	238.2
50°	241.3	236.7	231.9	228.7	226.9	225.2	223.4	221.6
52.5°	224.3	219.5	214.8	211.4	209.6	207.8	205.9	204.0
55°	199.2	194.3	189.4	186.1	184.3	182.5	180.7	179.0
57.5°	174.6	169.7	164.7	161.6	160.2	158.9	157.5	156.1
60°	158.2	153.4	148.5	145.3	143.7	142.3	140.8	139.3
62.5°	142.1	137.6	133.1	130.3	129.0	127.9	126.6	125.5
65°	119.0	114.9	110.9	108.3	107.2	106.1	105.0	103.8
67.5°	97.7	94.3	90.8	88.5	87.2	86.0	84.7	83.5
70°	83.3	80.2	77.1	75.1	74.1	73.2	72.2	71.3
72.5°	70.4	67.7	65.1	63.3	62.4	61.6	60.7	59.8
75°	51.8	49.7	47.5	46.2	45.6	45.0	44.5	43.9
77.5°	36.6	35.4	34.2	33.4	33.3	33.1	32.9	32.7
80°	28.2	27.8	27.6	27.4	27.3	27.2	27.1	27.0
82.5°	21.8	21.7	21.5	21.3	21.2	21.1	21.0	21.0
85°	12.8	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	6.6	6.6	6.6	6.7	6.8	7.0	7.0	7.1
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	9.6	10.2	10.7	11.0	11.1	11.1	11.1	11.1
95°	10.0	10.5	11.1	11.3	11.4	11.5	11.6	11.7
97.5°	10.8	10.8	10.9	11.0	11.1	11.1	11.2	11.3
100°	14.7	13.2	11.7	11.0	11.1	11.1	11.2	11.3
102.5°	52.7	36.3	19.8	11.6	11.6	11.6	11.6	11.7
105°	127.7	128.5	129.3	128.1	124.8	121.6	118.4	115.2
107.5°	158.0	158.4	158.8	159.2	159.5	159.8	160.2	160.5
110°	178.6	178.8	179.0	179.1	179.4	179.7	179.9	180.2





TEST NUMBER: P333017-940

CATALOG NUMBER: S124RDIW-S350D470U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.5	198.5	198.4	198.6	198.9	199.3	199.7	199.9
115°	228.3	228.5	228.6	228.7	228.7	228.7	228.7	228.7
117.5°	258.2	258.2	258.2	258.2	258.1	258.1	258.1	258.0
120°	276.8	277.0	277.1	277.1	277.0	276.8	276.6	276.4
122.5°	295.1	295.2	295.2	295.2	295.1	294.9	294.7	294.5
125°	320.6	320.8	321.1	321.3	321.4	321.5	321.6	321.6
127.5°	346.0	345.9	345.9	345.8	345.7	345.6	345.6	345.5
130°	361.5	361.6	361.7	361.7	361.7	361.7	361.7	361.7
132.5°	376.7	376.7	376.8	376.8	376.7	376.7	376.7	376.6
135°	397.6	397.8	398.0	398.1	398.3	398.5	398.7	398.9
137.5°	417.7	417.9	418.1	418.1	418.1	418.0	418.0	417.9
140°	430.2	430.4	430.7	430.9	431.0	431.1	431.1	431.2
142.5°	441.6	441.8	442.0	442.1	442.1	442.2	442.2	442.2
145°	458.1	458.2	458.3	458.3	458.5	458.7	458.9	459.1
147.5°	472.5	472.5	472.6	472.7	472.8	472.9	473.0	473.1
150°	481.7	481.7	481.7	481.8	481.9	482.0	482.1	482.1
152.5°	489.7	489.9	490.1	490.1	490.1	490.0	489.9	489.9
155°	500.6	501.0	501.3	501.4	501.1	500.9	500.6	500.3
157.5°	510.0	510.4	510.9	510.9	510.4	510.0	509.5	509.1
160°	515.9	516.5	517.0	517.0	516.5	515.9	515.4	514.9
162.5°	520.8	521.3	521.8	521.8	521.2	520.6	520.0	519.4
165°	527.6	528.3	529.1	529.0	528.2	527.4	526.6	525.8
167.5°	532.6	533.4	534.2	534.1	533.2	532.4	531.5	530.6
170°	535.7	536.4	537.2	537.1	536.1	535.2	534.3	533.4
172.5°	537.6	538.3	539.0	539.0	538.0	537.0	536.0	535.0
175°	539.9	540.7	541.5	541.4	540.3	539.2	538.1	537.1
177.5°	540.8	541.4	542.0	541.8	541.0	540.1	539.2	538.4
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3

(END OF REPORT)