

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333035-940

Luminaire Tested: **S124RDIW-S575D470U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333035-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D470U940-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3849.7 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36
4	77	66	58	52	71	62	55	50	54	49	45	47	43	39	40	37	35	31
5	71	59	51	45	66	56	48	43	49	43	39	42	38	35	36	33	30	27
6	65	53	45	40	61	50	43	38	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	22
8	56	44	36	31	52	41	34	30	37	31	27	32	28	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6952	6952	6952	6952
5°	8064	6972	6163	6972
10°	9539	6942	5501	6942
15°	11019	6878	4726	6878
20°	12269	6790	4274	6790
25°	12665	6703	3968	6703
30°	11087	6598	3784	6598
35°	8630	6441	3672	6441
40°	6472	6263	3613	6263
45°	5109	5977	3580	5977
50°	4314	5647	3478	5647
55°	3761	5284	3291	5284
60°	3384	4907	2913	4907
65°	2982	4500	2506	4500
70°	2686	4079	2261	4079
75°	2249	3615	1928	3615
80°	1901	3082	1808	3082
85°	1612	2408	1612	2408



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	2.2
10°-20°	251.7	6.5
20°-30°	393.7	10.2
30°-40°	437.6	11.4
40°-50°	388.3	10.1
50°-60°	302.5	7.9
60°-70°	198.1	5.1
70°-80°	97.4	2.5
80°-90°	25.6	0.7
90°-100°	18.5	0.5
100°-110°	117.8	3.1
110°-120°	225.4	5.9
120°-130°	286.1	7.4
130°-140°	306.1	8.0
140°-150°	286.3	7.4
150°-160°	230.9	6.0
160°-170°	148.9	3.9
170°-180°	51.3	1.3
0°-30°	728.8	18.9
0°-40°	1166.4	30.3
0°-60°	1857.2	48.2
0°-90°	2178.3	56.6
90°-120°	361.7	9.4
90°-150°	1240.3	32.2
90°-180°	1671.0	43.4
0°-180°	3849.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	861	861	861	861	861	
5°	995	860	760	860	995	101
15°	1318	823	566	823	1318	375
25°	1422	752	446	752	1422	631
35°	876	654	373	654	876	549
45°	448	524	314	524	448	354
55°	267	375	234	375	267	243
65°	156	236	131	236	156	157
75°	72	116	62	116	72	79
85°	17	26	17	26	17	20
90°	12	1	12	1	12	6
95°	12	22	12	22	12	9
105°	115	122	115	122	115	100
115°	229	227	229	227	229	226
125°	322	319	322	319	322	286
135°	399	396	399	396	399	307
145°	459	457	459	457	459	287
155°	500	501	500	501	500	231
165°	526	528	526	528	526	149
175°	537	540	537	540	537	51
180°	540	540	540	540	540	



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	908.3	910.8	908.3	908.0	905.3	904.5	903.3	899.7	893.0	889.1	890.0
5°	995.1	1003.7	998.9	998.2	990.5	982.9	978.0	967.0	955.1	947.2	940.6
7.5°	1095.4	1100.4	1097.3	1092.4	1080.1	1073.1	1061.8	1047.2	1026.1	1009.9	995.1
10°	1163.7	1167.8	1166.4	1157.4	1148.4	1130.0	1119.6	1099.1	1072.4	1051.2	1031.4
12.5°	1230.8	1235.3	1223.1	1223.5	1206.4	1191.9	1175.4	1149.7	1118.7	1091.5	1066.8
15°	1318.4	1312.9	1312.9	1305.9	1286.8	1266.7	1249.7	1222.6	1183.7	1151.2	1116.9
17.5°	1387.0	1388.9	1386.1	1369.7	1354.7	1333.9	1302.7	1271.1	1235.0	1191.2	1156.2
20°	1428.1	1428.1	1425.0	1413.8	1394.4	1372.2	1338.5	1304.2	1258.4	1214.3	1174.7
22.5°	1444.7	1445.8	1442.2	1433.0	1415.5	1393.8	1365.2	1330.3	1283.1	1233.5	1184.5
25°	1421.8	1428.3	1429.1	1426.6	1421.5	1408.3	1383.7	1347.9	1305.6	1251.8	1199.1
27.5°	1305.4	1313.7	1321.0	1332.9	1348.9	1357.3	1358.3	1340.2	1303.2	1251.5	1198.5
30°	1189.4	1196.2	1218.8	1248.3	1271.2	1292.0	1310.1	1314.9	1294.1	1247.6	1191.8
32.5°	1060.5	1070.0	1092.5	1124.3	1162.4	1197.7	1238.2	1258.8	1258.3	1230.4	1178.8
35°	875.7	882.6	903.5	936.7	982.6	1034.9	1099.1	1149.1	1183.1	1180.6	1149.1
37.5°	706.2	714.1	735.1	762.8	807.2	872.0	934.2	1003.0	1065.9	1101.2	1090.6
40°	614.1	614.5	634.9	663.3	705.0	761.5	829.2	905.5	975.6	1032.9	1043.9
42.5°	541.4	541.4	555.0	585.7	615.6	668.9	733.4	809.2	891.3	957.3	986.8
45°	447.5	450.7	461.8	480.2	503.7	548.8	600.6	671.0	762.9	841.3	890.3
47.5°	379.0	383.6	390.7	405.6	424.5	454.5	497.2	560.5	635.3	721.6	791.2
50°	343.5	344.2	353.2	361.5	377.8	401.8	439.3	492.0	560.7	643.5	720.9
52.5°	313.0	312.8	318.3	328.8	342.1	360.7	390.9	439.0	499.9	574.2	654.1
55°	267.2	268.9	273.0	281.3	291.4	304.6	328.6	364.6	412.5	476.0	548.5
57.5°	232.3	233.2	236.5	240.0	249.2	258.9	276.8	301.8	342.2	394.2	461.8
60°	209.6	209.9	211.0	216.2	223.5	232.5	244.6	265.7	299.8	347.3	400.7
62.5°	187.3	188.0	189.6	193.4	199.0	205.3	217.9	235.0	263.1	303.7	351.9
65°	156.1	156.5	158.9	160.3	164.8	170.3	179.7	191.2	210.6	244.6	281.1
67.5°	130.5	130.5	130.5	132.5	135.6	139.3	144.9	154.1	168.7	189.6	221.7
70°	113.8	113.8	114.5	115.6	117.3	120.4	123.5	130.5	141.2	158.2	182.8
72.5°	98.3	98.5	99.2	99.4	100.3	102.9	105.2	109.6	117.6	130.5	150.3
75°	72.1	73.2	74.9	76.3	78.0	77.8	80.2	82.9	85.3	93.0	104.4
77.5°	53.7	53.1	53.3	54.6	54.8	55.1	56.8	58.9	60.8	64.4	68.5
80°	40.9	40.9	42.0	42.4	42.0	42.4	44.1	45.1	45.8	47.2	51.0
82.5°	30.9	31.5	31.1	31.5	31.7	32.1	33.5	33.7	34.4	35.0	36.6
85°	17.4	17.7	18.0	17.4	17.4	17.4	18.0	18.4	19.1	18.7	19.4
87.5°	8.6	8.2	8.5	8.4	8.6	8.3	8.5	8.9	8.3	8.5	8.3
90°	12.1	11.9	11.8	11.6	11.4	11.1	10.5	10.0	9.5	8.9	8.2
92.5°	11.1	11.1	11.1	11.1	11.0	10.7	10.2	9.6	9.1	8.6	7.8
95°	11.7	11.6	11.5	11.4	11.3	11.1	10.5	10.0	9.5	8.9	8.8
97.5°	11.3	11.2	11.1	11.1	11.0	10.9	10.8	10.8	10.7	10.7	20.7
100°	11.3	11.2	11.1	11.1	11.0	11.7	13.2	14.7	16.2	17.7	30.1
102.5°	11.7	11.6	11.6	11.6	11.6	19.8	36.3	52.7	69.2	85.7	87.3
105°	115.2	118.4	121.6	124.8	128.1	129.3	128.5	127.7	126.9	126.1	125.6
107.5°	160.5	160.2	159.8	159.5	159.2	158.8	158.4	158.0	157.6	157.2	156.6
110°	180.2	179.9	179.7	179.4	179.1	179.0	178.8	178.6	178.4	178.3	177.7



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.9	199.7	199.3	198.9	198.6	198.4	198.5	198.5	198.6	198.6	198.3
115°	228.7	228.7	228.7	228.7	228.7	228.6	228.5	228.3	228.1	227.9	228.0
117.5°	258.0	258.1	258.1	258.1	258.2	258.2	258.2	258.2	258.2	258.3	258.2
120°	276.4	276.6	276.8	277.0	277.1	277.1	277.0	276.8	276.6	276.4	276.5
122.5°	294.5	294.7	294.9	295.1	295.2	295.2	295.2	295.1	295.0	294.9	294.7
125°	321.6	321.6	321.5	321.4	321.3	321.1	320.8	320.6	320.3	320.0	320.2
127.5°	345.5	345.6	345.6	345.7	345.8	345.9	345.9	346.0	346.1	346.1	345.7
130°	361.7	361.7	361.7	361.7	361.7	361.7	361.6	361.5	361.4	361.3	361.1
132.5°	376.6	376.7	376.7	376.7	376.8	376.8	376.7	376.7	376.6	376.5	376.1
135°	398.9	398.7	398.5	398.3	398.1	398.0	397.8	397.6	397.4	397.3	396.9
137.5°	417.9	418.0	418.0	418.1	418.1	418.1	417.9	417.7	417.5	417.3	416.9
140°	431.2	431.1	431.1	431.0	430.9	430.7	430.4	430.2	429.9	429.6	429.4
142.5°	442.2	442.2	442.2	442.1	442.1	442.0	441.8	441.6	441.4	441.2	441.1
145°	459.1	458.9	458.7	458.5	458.3	458.3	458.2	458.1	458.0	457.9	457.9
147.5°	473.1	473.0	472.9	472.8	472.7	472.6	472.5	472.5	472.4	472.3	472.4
150°	482.1	482.1	482.0	481.9	481.8	481.7	481.7	481.7	481.7	481.7	481.8
152.5°	489.9	489.9	490.0	490.1	490.1	490.1	489.9	489.7	489.6	489.5	489.6
155°	500.3	500.6	500.9	501.1	501.4	501.3	501.0	500.6	500.2	499.9	500.2
157.5°	509.1	509.5	510.0	510.4	510.9	510.9	510.4	510.0	509.5	509.1	509.3
160°	514.9	515.4	515.9	516.5	517.0	517.0	516.5	515.9	515.4	514.9	515.0
162.5°	519.4	520.0	520.6	521.2	521.8	521.8	521.3	520.8	520.2	519.7	519.8
165°	525.8	526.6	527.4	528.2	529.0	529.1	528.3	527.6	526.9	526.2	526.2
167.5°	530.6	531.5	532.4	533.2	534.1	534.2	533.4	532.6	531.8	531.0	531.1
170°	533.4	534.3	535.2	536.1	537.1	537.2	536.4	535.7	534.9	534.2	534.1
172.5°	535.0	536.0	537.0	538.0	539.0	539.0	538.3	537.6	536.9	536.2	536.1
175°	537.1	538.1	539.2	540.3	541.4	541.5	540.7	539.9	539.1	538.3	538.2
177.5°	538.4	539.2	540.1	541.0	541.8	542.0	541.4	540.8	540.2	539.7	539.5
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	887.3	883.3	881.4	876.9	871.6	868.9	866.4	862.8	858.1	853.1	849.4
5°	932.3	923.9	913.5	901.0	889.9	879.1	869.8	860.4	849.7	838.6	827.5
7.5°	978.5	962.1	944.4	923.9	904.0	885.9	869.2	853.3	835.3	819.0	804.3
10°	1010.7	988.5	963.9	937.8	911.8	889.2	867.0	846.9	824.7	804.9	788.3
12.5°	1036.8	1010.7	981.1	948.6	917.3	890.0	864.5	838.3	813.1	791.6	769.4
15°	1080.0	1044.3	1004.4	965.5	925.0	887.9	853.5	823.0	794.2	764.0	742.8
17.5°	1109.8	1067.4	1019.0	972.2	924.3	880.5	840.9	804.5	771.2	740.5	715.2
20°	1127.6	1080.8	1027.0	973.8	920.1	873.3	830.6	790.3	756.0	722.7	696.7
22.5°	1137.6	1085.7	1027.0	971.3	915.7	865.0	818.1	776.2	738.8	705.5	676.7
25°	1140.8	1085.2	1025.2	961.4	900.4	846.6	798.0	752.5	710.9	677.6	647.0
27.5°	1136.3	1070.9	1009.5	944.0	881.0	824.3	773.3	725.5	683.9	648.1	616.8
30°	1129.6	1059.6	993.6	925.7	861.8	807.4	753.6	707.8	664.4	627.3	595.8
32.5°	1115.3	1045.7	974.8	905.1	840.4	784.3	733.3	687.2	644.7	606.7	573.2
35°	1086.6	1016.2	939.1	867.7	804.2	745.9	698.0	653.6	613.1	572.5	537.1
37.5°	1048.9	977.0	900.4	822.2	758.6	703.6	659.6	618.0	578.3	541.3	502.0
40°	1013.4	947.9	868.8	791.0	725.9	672.7	632.1	594.3	554.5	517.6	478.4
42.5°	970.4	914.5	834.6	756.6	692.2	641.1	603.2	566.3	530.0	494.4	453.4
45°	898.6	856.3	781.3	706.4	641.5	590.8	556.2	523.5	491.6	457.6	419.1
47.5°	816.3	787.6	723.0	646.2	586.2	540.6	507.1	480.5	453.4	419.5	385.7
50°	759.1	740.7	678.3	608.2	551.0	509.0	474.7	449.6	427.1	394.5	364.3
52.5°	698.0	688.3	635.5	568.5	513.2	472.1	442.7	420.3	397.4	370.3	342.1
55°	605.1	610.3	565.5	507.6	455.6	420.9	394.1	375.4	356.0	333.1	311.2
57.5°	510.0	529.1	499.0	448.1	399.3	367.3	347.1	331.4	315.1	296.0	277.4
60°	453.1	469.0	452.1	407.3	364.6	334.8	316.1	303.9	287.6	270.3	256.0
62.5°	397.6	414.6	404.6	368.5	328.9	303.2	286.7	275.4	263.2	248.1	233.3
65°	327.9	338.9	334.1	309.2	281.1	259.1	243.9	235.6	224.4	213.4	200.2
67.5°	251.1	272.6	269.7	256.5	232.2	215.1	205.1	197.8	187.6	179.4	170.4
70°	206.4	226.2	225.9	215.1	201.9	185.9	179.1	172.8	163.7	155.8	148.5
72.5°	169.0	187.1	189.8	181.6	172.5	160.4	153.7	149.5	140.7	135.3	129.3
75°	118.3	131.5	135.0	135.0	130.8	124.6	118.7	115.9	109.6	104.8	101.3
77.5°	77.6	85.9	91.3	92.6	93.2	91.1	86.2	84.3	79.5	77.8	74.5
80°	54.8	60.4	66.6	68.7	70.4	69.7	67.7	66.3	61.8	60.0	58.7
82.5°	37.9	40.9	46.1	50.6	50.2	52.0	50.2	49.0	45.7	45.0	43.6
85°	19.8	20.2	20.8	23.9	25.7	26.4	26.8	26.0	25.0	25.0	22.6
87.5°	8.1	7.8	8.1	7.9	8.0	9.0	9.6	9.7	9.0	8.4	7.8
90°	7.5	6.8	6.0	5.2	4.2	3.2	2.2	1.2	2.2	3.2	4.2
92.5°	7.1	6.4	5.7	5.4	5.3	5.2	5.2	5.1	5.2	5.2	5.3
95°	8.7	8.6	8.6	10.0	13.1	16.1	19.2	22.2	19.2	16.1	13.1
97.5°	30.7	40.8	50.7	54.8	52.9	51.0	49.1	47.2	49.1	51.0	52.9
100°	42.5	54.9	67.3	72.8	71.2	69.6	67.9	66.3	67.9	69.6	71.2
102.5°	88.9	90.5	92.1	92.4	91.1	90.0	88.8	87.7	88.8	90.0	91.1
105°	125.2	124.8	124.3	123.8	123.2	122.7	122.2	121.6	122.2	122.7	123.2
107.5°	156.0	155.3	154.8	154.4	154.1	153.8	153.6	153.3	153.6	153.8	154.1
110°	177.2	176.6	176.0	175.7	175.4	175.1	174.9	174.6	174.9	175.1	175.4



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	198.0	197.9	197.6	197.2	196.7	196.3	195.7	195.3	195.7	196.3	196.7
115°	228.1	228.2	228.3	228.2	227.9	227.7	227.4	227.1	227.4	227.7	227.9
117.5°	257.9	257.7	257.5	257.3	256.9	256.5	256.2	255.8	256.2	256.5	256.9
120°	276.6	276.7	276.8	276.6	276.3	275.9	275.5	275.2	275.5	275.9	276.3
122.5°	294.6	294.4	294.4	294.2	294.0	293.7	293.6	293.3	293.6	293.7	294.0
125°	320.4	320.6	320.7	320.7	320.3	319.9	319.6	319.2	319.6	319.9	320.3
127.5°	345.3	344.8	344.5	344.2	344.1	344.0	343.9	343.8	343.9	344.0	344.1
130°	360.8	360.5	360.3	360.1	360.0	359.9	359.7	359.6	359.7	359.9	360.0
132.5°	375.8	375.5	375.1	374.9	374.7	374.5	374.3	374.3	374.3	374.5	374.7
135°	396.5	396.2	395.8	395.7	395.7	395.8	395.9	396.0	395.9	395.8	395.7
137.5°	416.5	416.1	415.7	415.5	415.4	415.4	415.4	415.4	415.4	415.4	415.4
140°	429.3	429.0	428.8	428.6	428.5	428.3	428.1	427.9	428.1	428.3	428.5
142.5°	441.0	440.9	440.8	440.6	440.2	440.0	439.6	439.3	439.6	440.0	440.2
145°	457.9	457.9	457.9	457.7	457.4	457.2	456.9	456.6	456.9	457.2	457.4
147.5°	472.5	472.6	472.7	472.5	472.0	471.4	471.0	470.5	471.0	471.4	472.0
150°	481.9	482.0	482.1	482.0	481.6	481.3	480.9	480.5	480.9	481.3	481.6
152.5°	489.8	490.0	490.1	490.1	489.7	489.5	489.2	488.9	489.2	489.5	489.7
155°	500.4	500.7	501.0	501.1	501.0	500.9	500.8	500.7	500.8	500.9	501.0
157.5°	509.6	510.0	510.2	510.4	510.5	510.5	510.6	510.7	510.6	510.5	510.5
160°	515.1	515.1	515.2	515.4	515.7	515.9	516.2	516.5	516.2	515.9	515.7
162.5°	519.9	520.0	520.0	520.3	520.6	520.9	521.3	521.7	521.3	520.9	520.6
165°	526.2	526.2	526.2	526.4	526.8	527.3	527.7	528.2	527.7	527.3	526.8
167.5°	531.1	531.2	531.2	531.5	532.0	532.4	532.9	533.3	532.9	532.4	532.0
170°	534.0	534.0	533.9	534.1	534.7	535.2	535.7	536.3	535.7	535.2	534.7
172.5°	536.0	535.9	535.8	536.1	536.6	537.2	537.7	538.2	537.7	537.2	536.6
175°	538.1	538.1	538.0	538.1	538.7	539.2	539.8	540.3	539.8	539.2	538.7
177.5°	539.4	539.2	539.1	539.3	539.8	540.3	540.8	541.3	540.8	540.3	539.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	845.6	842.8	839.2	835.0	830.0	825.6	823.7	825.3	826.2	823.9	823.7
5°	819.8	811.2	804.2	793.8	785.5	778.6	773.6	771.6	772.3	766.8	765.4
7.5°	790.9	780.6	769.3	756.9	745.4	735.2	729.9	726.9	721.0	718.5	714.3
10°	772.3	758.4	747.3	732.7	719.6	707.4	701.5	696.7	690.8	688.0	682.1
12.5°	753.1	737.1	724.9	709.7	696.2	681.6	676.0	667.0	657.7	651.9	644.4
15°	726.1	706.8	691.8	673.8	657.8	641.1	626.2	609.6	603.3	590.1	582.6
17.5°	694.6	674.8	656.4	632.2	607.6	586.9	571.0	555.1	545.5	537.1	533.2
20°	673.8	655.8	630.1	602.0	574.5	551.6	538.8	528.4	518.0	512.1	507.9
22.5°	654.1	631.1	601.2	570.9	543.5	525.6	514.7	504.0	495.5	489.9	484.4
25°	621.1	590.8	559.3	524.6	505.9	490.3	478.4	469.8	464.6	457.3	454.5
27.5°	587.1	550.5	515.7	492.4	472.9	458.6	448.4	441.8	435.2	430.5	427.0
30°	561.0	523.9	492.7	470.5	450.7	438.9	430.5	422.9	417.8	413.9	411.2
32.5°	535.2	498.1	471.8	448.0	432.4	420.9	412.0	406.3	402.2	397.3	395.6
35°	497.8	464.9	442.0	420.5	404.6	394.1	387.2	381.3	377.8	376.5	375.4
37.5°	462.0	435.0	410.4	392.7	378.5	370.3	362.1	359.3	356.9	354.4	355.5
40°	439.3	413.9	392.1	373.4	361.9	352.8	347.9	344.6	342.4	342.4	342.4
42.5°	419.5	394.8	373.4	356.7	345.2	337.6	332.2	329.2	328.6	328.2	329.9
45°	389.0	366.0	344.6	330.6	320.9	313.3	310.1	307.7	307.7	309.2	309.5
47.5°	358.6	337.2	319.9	304.3	295.4	290.7	287.9	286.7	286.9	288.2	289.8
50°	340.0	318.9	301.8	287.9	279.6	275.1	272.7	272.0	272.7	272.7	275.1
52.5°	319.8	300.8	284.1	272.4	263.0	258.8	257.4	256.5	256.9	258.0	259.0
55°	290.1	273.0	257.1	246.0	239.1	236.3	233.2	233.5	232.8	233.5	233.5
57.5°	260.3	245.0	230.2	221.3	215.3	211.2	207.9	208.7	207.8	207.6	207.1
60°	241.1	224.4	212.7	204.7	197.8	194.3	191.2	191.9	190.8	190.1	188.8
62.5°	220.3	206.4	195.2	187.5	181.9	177.9	174.8	174.1	171.7	169.3	166.2
65°	190.1	178.7	168.6	161.3	156.1	153.0	150.6	148.5	143.3	137.8	135.0
67.5°	160.8	152.5	143.1	137.0	132.8	128.7	124.0	120.5	115.6	112.5	110.8
70°	141.9	133.9	125.9	120.0	115.6	111.7	106.5	104.1	100.6	99.2	97.5
72.5°	123.9	116.5	109.0	103.7	98.9	95.9	91.8	89.3	87.8	87.3	85.5
75°	96.5	90.6	85.0	80.2	76.3	74.3	72.5	70.8	70.1	67.0	65.2
77.5°	70.4	66.4	63.0	59.6	56.8	55.5	52.1	50.1	49.0	47.4	47.1
80°	54.8	52.1	48.6	46.5	42.7	41.3	39.9	39.6	39.2	38.9	38.5
82.5°	41.2	38.4	35.0	33.7	32.7	31.8	31.0	30.7	30.3	30.5	30.5
85°	20.8	19.4	19.4	19.1	18.7	18.4	18.0	18.0	17.7	18.0	17.7
87.5°	7.9	7.8	8.0	7.6	8.0	8.2	8.0	8.1	8.5	8.0	8.1
90°	5.2	6.0	6.8	7.5	8.2	8.9	9.5	10.0	10.5	11.1	11.4
92.5°	5.4	5.7	6.4	7.1	7.8	8.6	9.1	9.6	10.2	10.7	11.0
95°	10.0	8.6	8.6	8.7	8.8	8.9	9.5	10.0	10.5	11.1	11.3
97.5°	54.8	50.7	40.8	30.7	20.7	10.7	10.7	10.8	10.8	10.9	11.0
100°	72.8	67.3	54.9	42.5	30.1	17.7	16.2	14.7	13.2	11.7	11.0
102.5°	92.4	92.1	90.5	88.9	87.3	85.7	69.2	52.7	36.3	19.8	11.6
105°	123.8	124.3	124.8	125.2	125.6	126.1	126.9	127.7	128.5	129.3	128.1
107.5°	154.4	154.8	155.3	156.0	156.6	157.2	157.6	158.0	158.4	158.8	159.2
110°	175.7	176.0	176.6	177.2	177.7	178.3	178.4	178.6	178.8	179.0	179.1



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	197.2	197.6	197.9	198.0	198.3	198.6	198.6	198.5	198.5	198.4	198.6
115°	228.2	228.3	228.2	228.1	228.0	227.9	228.1	228.3	228.5	228.6	228.7
117.5°	257.3	257.5	257.7	257.9	258.2	258.3	258.2	258.2	258.2	258.2	258.2
120°	276.6	276.8	276.7	276.6	276.5	276.4	276.6	276.8	277.0	277.1	277.1
122.5°	294.2	294.4	294.4	294.6	294.7	294.9	295.0	295.1	295.2	295.2	295.2
125°	320.7	320.7	320.6	320.4	320.2	320.0	320.3	320.6	320.8	321.1	321.3
127.5°	344.2	344.5	344.8	345.3	345.7	346.1	346.1	346.0	345.9	345.9	345.8
130°	360.1	360.3	360.5	360.8	361.1	361.3	361.4	361.5	361.6	361.7	361.7
132.5°	374.9	375.1	375.5	375.8	376.1	376.5	376.6	376.7	376.7	376.8	376.8
135°	395.7	395.8	396.2	396.5	396.9	397.3	397.4	397.6	397.8	398.0	398.1
137.5°	415.5	415.7	416.1	416.5	416.9	417.3	417.5	417.7	417.9	418.1	418.1
140°	428.6	428.8	429.0	429.3	429.4	429.6	429.9	430.2	430.4	430.7	430.9
142.5°	440.6	440.8	440.9	441.0	441.1	441.2	441.4	441.6	441.8	442.0	442.1
145°	457.7	457.9	457.9	457.9	457.9	457.9	458.0	458.1	458.2	458.3	458.3
147.5°	472.5	472.7	472.6	472.5	472.4	472.3	472.4	472.5	472.5	472.6	472.7
150°	482.0	482.1	482.0	481.9	481.8	481.7	481.7	481.7	481.7	481.7	481.8
152.5°	490.1	490.1	490.0	489.8	489.6	489.5	489.6	489.7	489.9	490.1	490.1
155°	501.1	501.0	500.7	500.4	500.2	499.9	500.2	500.6	501.0	501.3	501.4
157.5°	510.4	510.2	510.0	509.6	509.3	509.1	509.5	510.0	510.4	510.9	510.9
160°	515.4	515.2	515.1	515.1	515.0	514.9	515.4	515.9	516.5	517.0	517.0
162.5°	520.3	520.0	520.0	519.9	519.8	519.7	520.2	520.8	521.3	521.8	521.8
165°	526.4	526.2	526.2	526.2	526.2	526.2	526.9	527.6	528.3	529.1	529.0
167.5°	531.5	531.2	531.2	531.1	531.1	531.0	531.8	532.6	533.4	534.2	534.1
170°	534.1	533.9	534.0	534.0	534.1	534.2	534.9	535.7	536.4	537.2	537.1
172.5°	536.1	535.8	535.9	536.0	536.1	536.2	536.9	537.6	538.3	539.0	539.0
175°	538.1	538.0	538.1	538.1	538.2	538.3	539.1	539.9	540.7	541.5	541.4
177.5°	539.3	539.1	539.2	539.4	539.5	539.7	540.2	540.8	541.4	542.0	541.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	822.0	822.5	820.6	820.0	820.6	822.5	822.0	823.7	823.9	826.2	825.3
5°	762.6	761.9	760.2	760.5	760.2	761.9	762.6	765.4	766.8	772.3	771.6
7.5°	711.8	709.1	709.9	707.0	709.9	709.1	711.8	714.3	718.5	721.0	726.9
10°	680.7	676.9	673.8	671.0	673.8	676.9	680.7	682.1	688.0	690.8	696.7
12.5°	638.3	635.0	630.7	631.6	630.7	635.0	638.3	644.4	651.9	657.7	667.0
15°	578.0	572.8	564.5	565.5	564.5	572.8	578.0	582.6	590.1	603.3	609.6
17.5°	527.0	527.1	523.3	524.1	523.3	527.1	527.0	533.2	537.1	545.5	555.1
20°	500.6	498.2	498.6	497.5	498.6	498.2	500.6	507.9	512.1	518.0	528.4
22.5°	482.3	479.4	476.9	474.7	476.9	479.4	482.3	484.4	489.9	495.5	504.0
25°	451.4	449.3	446.2	445.5	446.2	449.3	451.4	454.5	457.3	464.6	469.8
27.5°	424.2	423.7	422.5	420.9	422.5	423.7	424.2	427.0	430.5	435.2	441.8
30°	408.3	407.7	407.0	405.9	407.0	407.7	408.3	411.2	413.9	417.8	422.9
32.5°	394.2	393.8	393.1	393.2	393.1	393.8	394.2	395.6	397.3	402.2	406.3
35°	374.0	373.6	373.0	372.6	373.0	373.6	374.0	375.4	376.5	377.8	381.3
37.5°	355.2	356.1	355.6	355.5	355.6	356.1	355.2	355.5	354.4	356.9	359.3
40°	342.1	342.4	343.1	342.8	343.1	342.4	342.1	342.4	342.4	342.4	344.6
42.5°	331.3	331.4	332.3	331.1	332.3	331.4	331.3	329.9	328.2	328.6	329.2
45°	311.9	314.0	313.6	313.6	313.6	314.0	311.9	309.5	309.2	307.7	307.7
47.5°	290.7	292.6	293.0	292.9	293.0	292.6	290.7	289.8	288.2	286.9	286.7
50°	276.9	276.2	277.2	276.9	277.2	276.2	276.9	275.1	272.7	272.7	272.0
52.5°	259.9	260.1	260.0	259.7	260.0	260.1	259.9	259.0	258.0	256.9	256.5
55°	233.8	234.2	233.5	233.8	233.5	234.2	233.8	233.5	233.5	232.8	233.5
57.5°	205.5	203.8	204.6	203.8	204.6	203.8	205.5	207.1	207.6	207.8	208.7
60°	185.3	182.5	181.8	180.4	181.8	182.5	185.3	188.8	190.1	190.8	191.9
62.5°	162.5	160.6	158.2	159.3	158.2	160.6	162.5	166.2	169.3	171.7	174.1
65°	132.2	130.8	129.7	131.2	129.7	130.8	132.2	135.0	137.8	143.3	148.5
67.5°	109.4	108.7	108.7	108.0	108.7	108.7	109.4	110.8	112.5	115.6	120.5
70°	97.5	96.5	96.5	95.8	96.5	96.5	97.5	97.5	99.2	100.6	104.1
72.5°	85.2	84.3	84.5	84.1	84.5	84.3	85.2	85.5	87.3	87.8	89.3
75°	63.1	61.4	61.4	61.8	61.4	61.4	63.1	65.2	67.0	70.1	70.8
77.5°	47.1	46.7	47.3	46.6	47.3	46.7	47.1	47.1	47.4	49.0	50.1
80°	38.5	38.2	37.8	38.9	37.8	38.2	38.5	38.5	38.9	39.2	39.6
82.5°	29.9	29.9	29.8	31.1	29.8	29.9	29.9	30.5	30.5	30.3	30.7
85°	18.0	17.4	18.0	17.4	18.0	17.4	18.0	17.7	18.0	17.7	18.0
87.5°	8.7	8.5	8.2	8.6	8.2	8.5	8.7	8.1	8.0	8.5	8.1
90°	11.6	11.8	11.9	12.1	11.9	11.8	11.6	11.4	11.1	10.5	10.0
92.5°	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.0	10.7	10.2	9.6
95°	11.4	11.5	11.6	11.7	11.6	11.5	11.4	11.3	11.1	10.5	10.0
97.5°	11.1	11.1	11.2	11.3	11.2	11.1	11.1	11.0	10.9	10.8	10.8
100°	11.1	11.1	11.2	11.3	11.2	11.1	11.1	11.0	11.7	13.2	14.7
102.5°	11.6	11.6	11.6	11.7	11.6	11.6	11.6	11.6	19.8	36.3	52.7
105°	124.8	121.6	118.4	115.2	118.4	121.6	124.8	128.1	129.3	128.5	127.7
107.5°	159.5	159.8	160.2	160.5	160.2	159.8	159.5	159.2	158.8	158.4	158.0
110°	179.4	179.7	179.9	180.2	179.9	179.7	179.4	179.1	179.0	178.8	178.6



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	198.9	199.3	199.7	199.9	199.7	199.3	198.9	198.6	198.4	198.5	198.5
115°	228.7	228.7	228.7	228.7	228.7	228.7	228.7	228.7	228.6	228.5	228.3
117.5°	258.1	258.1	258.1	258.0	258.1	258.1	258.1	258.2	258.2	258.2	258.2
120°	277.0	276.8	276.6	276.4	276.6	276.8	277.0	277.1	277.1	277.0	276.8
122.5°	295.1	294.9	294.7	294.5	294.7	294.9	295.1	295.2	295.2	295.2	295.1
125°	321.4	321.5	321.6	321.6	321.6	321.5	321.4	321.3	321.1	320.8	320.6
127.5°	345.7	345.6	345.6	345.5	345.6	345.6	345.7	345.8	345.9	345.9	346.0
130°	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.7	361.6	361.5
132.5°	376.7	376.7	376.7	376.6	376.7	376.7	376.7	376.8	376.8	376.7	376.7
135°	398.3	398.5	398.7	398.9	398.7	398.5	398.3	398.1	398.0	397.8	397.6
137.5°	418.1	418.0	418.0	417.9	418.0	418.0	418.1	418.1	418.1	417.9	417.7
140°	431.0	431.1	431.1	431.2	431.1	431.1	431.0	430.9	430.7	430.4	430.2
142.5°	442.1	442.2	442.2	442.2	442.2	442.2	442.1	442.1	442.0	441.8	441.6
145°	458.5	458.7	458.9	459.1	458.9	458.7	458.5	458.3	458.3	458.2	458.1
147.5°	472.8	472.9	473.0	473.1	473.0	472.9	472.8	472.7	472.6	472.5	472.5
150°	481.9	482.0	482.1	482.1	482.1	482.0	481.9	481.8	481.7	481.7	481.7
152.5°	490.1	490.0	489.9	489.9	489.9	490.0	490.1	490.1	490.1	489.9	489.7
155°	501.1	500.9	500.6	500.3	500.6	500.9	501.1	501.4	501.3	501.0	500.6
157.5°	510.4	510.0	509.5	509.1	509.5	510.0	510.4	510.9	510.9	510.4	510.0
160°	516.5	515.9	515.4	514.9	515.4	515.9	516.5	517.0	517.0	516.5	515.9
162.5°	521.2	520.6	520.0	519.4	520.0	520.6	521.2	521.8	521.8	521.3	520.8
165°	528.2	527.4	526.6	525.8	526.6	527.4	528.2	529.0	529.1	528.3	527.6
167.5°	533.2	532.4	531.5	530.6	531.5	532.4	533.2	534.1	534.2	533.4	532.6
170°	536.1	535.2	534.3	533.4	534.3	535.2	536.1	537.1	537.2	536.4	535.7
172.5°	538.0	537.0	536.0	535.0	536.0	537.0	538.0	539.0	539.0	538.3	537.6
175°	540.3	539.2	538.1	537.1	538.1	539.2	540.3	541.4	541.5	540.7	539.9
177.5°	541.0	540.1	539.2	538.4	539.2	540.1	541.0	541.8	542.0	541.4	540.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	823.7	825.6	830.0	835.0	839.2	842.8	845.6	849.4	853.1	858.1	862.8
5°	773.6	778.6	785.5	793.8	804.2	811.2	819.8	827.5	838.6	849.7	860.4
7.5°	729.9	735.2	745.4	756.9	769.3	780.6	790.9	804.3	819.0	835.3	853.3
10°	701.5	707.4	719.6	732.7	747.3	758.4	772.3	788.3	804.9	824.7	846.9
12.5°	676.0	681.6	696.2	709.7	724.9	737.1	753.1	769.4	791.6	813.1	838.3
15°	626.2	641.1	657.8	673.8	691.8	706.8	726.1	742.8	764.0	794.2	823.0
17.5°	571.0	586.9	607.6	632.2	656.4	674.8	694.6	715.2	740.5	771.2	804.5
20°	538.8	551.6	574.5	602.0	630.1	655.8	673.8	696.7	722.7	756.0	790.3
22.5°	514.7	525.6	543.5	570.9	601.2	631.1	654.1	676.7	705.5	738.8	776.2
25°	478.4	490.3	505.9	524.6	559.3	590.8	621.1	647.0	677.6	710.9	752.5
27.5°	448.4	458.6	472.9	492.4	515.7	550.5	587.1	616.8	648.1	683.9	725.5
30°	430.5	438.9	450.7	470.5	492.7	523.9	561.0	595.8	627.3	664.4	707.8
32.5°	412.0	420.9	432.4	448.0	471.8	498.1	535.2	573.2	606.7	644.7	687.2
35°	387.2	394.1	404.6	420.5	442.0	464.9	497.8	537.1	572.5	613.1	653.6
37.5°	362.1	370.3	378.5	392.7	410.4	435.0	462.0	502.0	541.3	578.3	618.0
40°	347.9	352.8	361.9	373.4	392.1	413.9	439.3	478.4	517.6	554.5	594.3
42.5°	332.2	337.6	345.2	356.7	373.4	394.8	419.5	453.4	494.4	530.0	566.3
45°	310.1	313.3	320.9	330.6	344.6	366.0	389.0	419.1	457.6	491.6	523.5
47.5°	287.9	290.7	295.4	304.3	319.9	337.2	358.6	385.7	419.5	453.4	480.5
50°	272.7	275.1	279.6	287.9	301.8	318.9	340.0	364.3	394.5	427.1	449.6
52.5°	257.4	258.8	263.0	272.4	284.1	300.8	319.8	342.1	370.3	397.4	420.3
55°	233.2	236.3	239.1	246.0	257.1	273.0	290.1	311.2	333.1	356.0	375.4
57.5°	207.9	211.2	215.3	221.3	230.2	245.0	260.3	277.4	296.0	315.1	331.4
60°	191.2	194.3	197.8	204.7	212.7	224.4	241.1	256.0	270.3	287.6	303.9
62.5°	174.8	177.9	181.9	187.5	195.2	206.4	220.3	233.3	248.1	263.2	275.4
65°	150.6	153.0	156.1	161.3	168.6	178.7	190.1	200.2	213.4	224.4	235.6
67.5°	124.0	128.7	132.8	137.0	143.1	152.5	160.8	170.4	179.4	187.6	197.8
70°	106.5	111.7	115.6	120.0	125.9	133.9	141.9	148.5	155.8	163.7	172.8
72.5°	91.8	95.9	98.9	103.7	109.0	116.5	123.9	129.3	135.3	140.7	149.5
75°	72.5	74.3	76.3	80.2	85.0	90.6	96.5	101.3	104.8	109.6	115.9
77.5°	52.1	55.5	56.8	59.6	63.0	66.4	70.4	74.5	77.8	79.5	84.3
80°	39.9	41.3	42.7	46.5	48.6	52.1	54.8	58.7	60.0	61.8	66.3
82.5°	31.0	31.8	32.7	33.7	35.0	38.4	41.2	43.6	45.0	45.7	49.0
85°	18.0	18.4	18.7	19.1	19.4	19.4	20.8	22.6	25.0	25.0	26.0
87.5°	8.0	8.2	8.0	7.6	8.0	7.8	7.9	7.8	8.4	9.0	9.7
90°	9.5	8.9	8.2	7.5	6.8	6.0	5.2	4.2	3.2	2.2	1.2
92.5°	9.1	8.6	7.8	7.1	6.4	5.7	5.4	5.3	5.2	5.2	5.1
95°	9.5	8.9	8.8	8.7	8.6	8.6	10.0	13.1	16.1	19.2	22.2
97.5°	10.7	10.7	20.7	30.7	40.8	50.7	54.8	52.9	51.0	49.1	47.2
100°	16.2	17.7	30.1	42.5	54.9	67.3	72.8	71.2	69.6	67.9	66.3
102.5°	69.2	85.7	87.3	88.9	90.5	92.1	92.4	91.1	90.0	88.8	87.7
105°	126.9	126.1	125.6	125.2	124.8	124.3	123.8	123.2	122.7	122.2	121.6
107.5°	157.6	157.2	156.6	156.0	155.3	154.8	154.4	154.1	153.8	153.6	153.3
110°	178.4	178.3	177.7	177.2	176.6	176.0	175.7	175.4	175.1	174.9	174.6



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	198.6	198.6	198.3	198.0	197.9	197.6	197.2	196.7	196.3	195.7	195.3
115°	228.1	227.9	228.0	228.1	228.2	228.3	228.2	227.9	227.7	227.4	227.1
117.5°	258.2	258.3	258.2	257.9	257.7	257.5	257.3	256.9	256.5	256.2	255.8
120°	276.6	276.4	276.5	276.6	276.7	276.8	276.6	276.3	275.9	275.5	275.2
122.5°	295.0	294.9	294.7	294.6	294.4	294.4	294.2	294.0	293.7	293.6	293.3
125°	320.3	320.0	320.2	320.4	320.6	320.7	320.7	320.3	319.9	319.6	319.2
127.5°	346.1	346.1	345.7	345.3	344.8	344.5	344.2	344.1	344.0	343.9	343.8
130°	361.4	361.3	361.1	360.8	360.5	360.3	360.1	360.0	359.9	359.7	359.6
132.5°	376.6	376.5	376.1	375.8	375.5	375.1	374.9	374.7	374.5	374.3	374.3
135°	397.4	397.3	396.9	396.5	396.2	395.8	395.7	395.7	395.8	395.9	396.0
137.5°	417.5	417.3	416.9	416.5	416.1	415.7	415.5	415.4	415.4	415.4	415.4
140°	429.9	429.6	429.4	429.3	429.0	428.8	428.6	428.5	428.3	428.1	427.9
142.5°	441.4	441.2	441.1	441.0	440.9	440.8	440.6	440.2	440.0	439.6	439.3
145°	458.0	457.9	457.9	457.9	457.9	457.9	457.7	457.4	457.2	456.9	456.6
147.5°	472.4	472.3	472.4	472.5	472.6	472.7	472.5	472.0	471.4	471.0	470.5
150°	481.7	481.7	481.8	481.9	482.0	482.1	482.0	481.6	481.3	480.9	480.5
152.5°	489.6	489.5	489.6	489.8	490.0	490.1	490.1	489.7	489.5	489.2	488.9
155°	500.2	499.9	500.2	500.4	500.7	501.0	501.1	501.0	500.9	500.8	500.7
157.5°	509.5	509.1	509.3	509.6	510.0	510.2	510.4	510.5	510.5	510.6	510.7
160°	515.4	514.9	515.0	515.1	515.1	515.2	515.4	515.7	515.9	516.2	516.5
162.5°	520.2	519.7	519.8	519.9	520.0	520.0	520.3	520.6	520.9	521.3	521.7
165°	526.9	526.2	526.2	526.2	526.2	526.2	526.4	526.8	527.3	527.7	528.2
167.5°	531.8	531.0	531.1	531.1	531.2	531.2	531.5	532.0	532.4	532.9	533.3
170°	534.9	534.2	534.1	534.0	534.0	533.9	534.1	534.7	535.2	535.7	536.3
172.5°	536.9	536.2	536.1	536.0	535.9	535.8	536.1	536.6	537.2	537.7	538.2
175°	539.1	538.3	538.2	538.1	538.1	538.0	538.1	538.7	539.2	539.8	540.3
177.5°	540.2	539.7	539.5	539.4	539.2	539.1	539.3	539.8	540.3	540.8	541.3
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	866.4	868.9	871.6	876.9	881.4	883.3	887.3	890.0	889.1	893.0	899.7
5°	869.8	879.1	889.9	901.0	913.5	923.9	932.3	940.6	947.2	955.1	967.0
7.5°	869.2	885.9	904.0	923.9	944.4	962.1	978.5	995.1	1009.9	1026.1	1047.2
10°	867.0	889.2	911.8	937.8	963.9	988.5	1010.7	1031.4	1051.2	1072.4	1099.1
12.5°	864.5	890.0	917.3	948.6	981.1	1010.7	1036.8	1066.8	1091.5	1118.7	1149.7
15°	853.5	887.9	925.0	965.5	1004.4	1044.3	1080.0	1116.9	1151.2	1183.7	1222.6
17.5°	840.9	880.5	924.3	972.2	1019.0	1067.4	1109.8	1156.2	1191.2	1235.0	1271.1
20°	830.6	873.3	920.1	973.8	1027.0	1080.8	1127.6	1174.7	1214.3	1258.4	1304.2
22.5°	818.1	865.0	915.7	971.3	1027.0	1085.7	1137.6	1184.5	1233.5	1283.1	1330.3
25°	798.0	846.6	900.4	961.4	1025.2	1085.2	1140.8	1199.1	1251.8	1305.6	1347.9
27.5°	773.3	824.3	881.0	944.0	1009.5	1070.9	1136.3	1198.5	1251.5	1303.2	1340.2
30°	753.6	807.4	861.8	925.7	993.6	1059.6	1129.6	1191.8	1247.6	1294.1	1314.9
32.5°	733.3	784.3	840.4	905.1	974.8	1045.7	1115.3	1178.8	1230.4	1258.3	1258.8
35°	698.0	745.9	804.2	867.7	939.1	1016.2	1086.6	1149.1	1180.6	1183.1	1149.1
37.5°	659.6	703.6	758.6	822.2	900.4	977.0	1048.9	1090.6	1101.2	1065.9	1003.0
40°	632.1	672.7	725.9	791.0	868.8	947.9	1013.4	1043.9	1032.9	975.6	905.5
42.5°	603.2	641.1	692.2	756.6	834.6	914.5	970.4	986.8	957.3	891.3	809.2
45°	556.2	590.8	641.5	706.4	781.3	856.3	898.6	890.3	841.3	762.9	671.0
47.5°	507.1	540.6	586.2	646.2	723.0	787.6	816.3	791.2	721.6	635.3	560.5
50°	474.7	509.0	551.0	608.2	678.3	740.7	759.1	720.9	643.5	560.7	492.0
52.5°	442.7	472.1	513.2	568.5	635.5	688.3	698.0	654.1	574.2	499.9	439.0
55°	394.1	420.9	455.6	507.6	565.5	610.3	605.1	548.5	476.0	412.5	364.6
57.5°	347.1	367.3	399.3	448.1	499.0	529.1	510.0	461.8	394.2	342.2	301.8
60°	316.1	334.8	364.6	407.3	452.1	469.0	453.1	400.7	347.3	299.8	265.7
62.5°	286.7	303.2	328.9	368.5	404.6	414.6	397.6	351.9	303.7	263.1	235.0
65°	243.9	259.1	281.1	309.2	334.1	338.9	327.9	281.1	244.6	210.6	191.2
67.5°	205.1	215.1	232.2	256.5	269.7	272.6	251.1	221.7	189.6	168.7	154.1
70°	179.1	185.9	201.9	215.1	225.9	226.2	206.4	182.8	158.2	141.2	130.5
72.5°	153.7	160.4	172.5	181.6	189.8	187.1	169.0	150.3	130.5	117.6	109.6
75°	118.7	124.6	130.8	135.0	135.0	131.5	118.3	104.4	93.0	85.3	82.9
77.5°	86.2	91.1	93.2	92.6	91.3	85.9	77.6	68.5	64.4	60.8	58.9
80°	67.7	69.7	70.4	68.7	66.6	60.4	54.8	51.0	47.2	45.8	45.1
82.5°	50.2	52.0	50.2	50.6	46.1	40.9	37.9	36.6	35.0	34.4	33.7
85°	26.8	26.4	25.7	23.9	20.8	20.2	19.8	19.4	18.7	19.1	18.4
87.5°	9.6	9.0	8.0	7.9	8.1	7.8	8.1	8.3	8.5	8.3	8.9
90°	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5	10.0
92.5°	5.2	5.2	5.3	5.4	5.7	6.4	7.1	7.8	8.6	9.1	9.6
95°	19.2	16.1	13.1	10.0	8.6	8.6	8.7	8.8	8.9	9.5	10.0
97.5°	49.1	51.0	52.9	54.8	50.7	40.8	30.7	20.7	10.7	10.7	10.8
100°	67.9	69.6	71.2	72.8	67.3	54.9	42.5	30.1	17.7	16.2	14.7
102.5°	88.8	90.0	91.1	92.4	92.1	90.5	88.9	87.3	85.7	69.2	52.7
105°	122.2	122.7	123.2	123.8	124.3	124.8	125.2	125.6	126.1	126.9	127.7
107.5°	153.6	153.8	154.1	154.4	154.8	155.3	156.0	156.6	157.2	157.6	158.0
110°	174.9	175.1	175.4	175.7	176.0	176.6	177.2	177.7	178.3	178.4	178.6



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	195.7	196.3	196.7	197.2	197.6	197.9	198.0	198.3	198.6	198.6	198.5
115°	227.4	227.7	227.9	228.2	228.3	228.2	228.1	228.0	227.9	228.1	228.3
117.5°	256.2	256.5	256.9	257.3	257.5	257.7	257.9	258.2	258.3	258.2	258.2
120°	275.5	275.9	276.3	276.6	276.8	276.7	276.6	276.5	276.4	276.6	276.8
122.5°	293.6	293.7	294.0	294.2	294.4	294.4	294.6	294.7	294.9	295.0	295.1
125°	319.6	319.9	320.3	320.7	320.7	320.6	320.4	320.2	320.0	320.3	320.6
127.5°	343.9	344.0	344.1	344.2	344.5	344.8	345.3	345.7	346.1	346.1	346.0
130°	359.7	359.9	360.0	360.1	360.3	360.5	360.8	361.1	361.3	361.4	361.5
132.5°	374.3	374.5	374.7	374.9	375.1	375.5	375.8	376.1	376.5	376.6	376.7
135°	395.9	395.8	395.7	395.7	395.8	396.2	396.5	396.9	397.3	397.4	397.6
137.5°	415.4	415.4	415.4	415.5	415.7	416.1	416.5	416.9	417.3	417.5	417.7
140°	428.1	428.3	428.5	428.6	428.8	429.0	429.3	429.4	429.6	429.9	430.2
142.5°	439.6	440.0	440.2	440.6	440.8	440.9	441.0	441.1	441.2	441.4	441.6
145°	456.9	457.2	457.4	457.7	457.9	457.9	457.9	457.9	457.9	458.0	458.1
147.5°	471.0	471.4	472.0	472.5	472.7	472.6	472.5	472.4	472.3	472.4	472.5
150°	480.9	481.3	481.6	482.0	482.1	482.0	481.9	481.8	481.7	481.7	481.7
152.5°	489.2	489.5	489.7	490.1	490.1	490.0	489.8	489.6	489.5	489.6	489.7
155°	500.8	500.9	501.0	501.1	501.0	500.7	500.4	500.2	499.9	500.2	500.6
157.5°	510.6	510.5	510.5	510.4	510.2	510.0	509.6	509.3	509.1	509.5	510.0
160°	516.2	515.9	515.7	515.4	515.2	515.1	515.1	515.0	514.9	515.4	515.9
162.5°	521.3	520.9	520.6	520.3	520.0	520.0	519.9	519.8	519.7	520.2	520.8
165°	527.7	527.3	526.8	526.4	526.2	526.2	526.2	526.2	526.2	526.9	527.6
167.5°	532.9	532.4	532.0	531.5	531.2	531.2	531.1	531.1	531.0	531.8	532.6
170°	535.7	535.2	534.7	534.1	533.9	534.0	534.0	534.1	534.2	534.9	535.7
172.5°	537.7	537.2	536.6	536.1	535.8	535.9	536.0	536.1	536.2	536.9	537.6
175°	539.8	539.2	538.7	538.1	538.0	538.1	538.1	538.2	538.3	539.1	539.9
177.5°	540.8	540.3	539.8	539.3	539.1	539.2	539.4	539.5	539.7	540.2	540.8
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	861.1	861.1	861.1	861.1	861.1	861.1	861.1
2.5°	903.3	904.5	905.3	908.0	908.3	910.8	908.3
5°	978.0	982.9	990.5	998.2	998.9	1003.7	995.1
7.5°	1061.8	1073.1	1080.1	1092.4	1097.3	1100.4	1095.4
10°	1119.6	1130.0	1148.4	1157.4	1166.4	1167.8	1163.7
12.5°	1175.4	1191.9	1206.4	1223.5	1223.1	1235.3	1230.8
15°	1249.7	1266.7	1286.8	1305.9	1312.9	1312.9	1318.4
17.5°	1302.7	1333.9	1354.7	1369.7	1386.1	1388.9	1387.0
20°	1338.5	1372.2	1394.4	1413.8	1425.0	1428.1	1428.1
22.5°	1365.2	1393.8	1415.5	1433.0	1442.2	1445.8	1444.7
25°	1383.7	1408.3	1421.5	1426.6	1429.1	1428.3	1421.8
27.5°	1358.3	1357.3	1348.9	1332.9	1321.0	1313.7	1305.4
30°	1310.1	1292.0	1271.2	1248.3	1218.8	1196.2	1189.4
32.5°	1238.2	1197.7	1162.4	1124.3	1092.5	1070.0	1060.5
35°	1099.1	1034.9	982.6	936.7	903.5	882.6	875.7
37.5°	934.2	872.0	807.2	762.8	735.1	714.1	706.2
40°	829.2	761.5	705.0	663.3	634.9	614.5	614.1
42.5°	733.4	668.9	615.6	585.7	555.0	541.4	541.4
45°	600.6	548.8	503.7	480.2	461.8	450.7	447.5
47.5°	497.2	454.5	424.5	405.6	390.7	383.6	379.0
50°	439.3	401.8	377.8	361.5	353.2	344.2	343.5
52.5°	390.9	360.7	342.1	328.8	318.3	312.8	313.0
55°	328.6	304.6	291.4	281.3	273.0	268.9	267.2
57.5°	276.8	258.9	249.2	240.0	236.5	233.2	232.3
60°	244.6	232.5	223.5	216.2	211.0	209.9	209.6
62.5°	217.9	205.3	199.0	193.4	189.6	188.0	187.3
65°	179.7	170.3	164.8	160.3	158.9	156.5	156.1
67.5°	144.9	139.3	135.6	132.5	130.5	130.5	130.5
70°	123.5	120.4	117.3	115.6	114.5	113.8	113.8
72.5°	105.2	102.9	100.3	99.4	99.2	98.5	98.3
75°	80.2	77.8	78.0	76.3	74.9	73.2	72.1
77.5°	56.8	55.1	54.8	54.6	53.3	53.1	53.7
80°	44.1	42.4	42.0	42.4	42.0	40.9	40.9
82.5°	33.5	32.1	31.7	31.5	31.1	31.5	30.9
85°	18.0	17.4	17.4	17.4	18.0	17.7	17.4
87.5°	8.5	8.3	8.6	8.4	8.5	8.2	8.6
90°	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	10.2	10.7	11.0	11.1	11.1	11.1	11.1
95°	10.5	11.1	11.3	11.4	11.5	11.6	11.7
97.5°	10.8	10.9	11.0	11.1	11.1	11.2	11.3
100°	13.2	11.7	11.0	11.1	11.1	11.2	11.3
102.5°	36.3	19.8	11.6	11.6	11.6	11.6	11.7
105°	128.5	129.3	128.1	124.8	121.6	118.4	115.2
107.5°	158.4	158.8	159.2	159.5	159.8	160.2	160.5
110°	178.8	179.0	179.1	179.4	179.7	179.9	180.2



TEST NUMBER: P333035-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	198.5	198.4	198.6	198.9	199.3	199.7	199.9
115°	228.5	228.6	228.7	228.7	228.7	228.7	228.7
117.5°	258.2	258.2	258.2	258.1	258.1	258.1	258.0
120°	277.0	277.1	277.1	277.0	276.8	276.6	276.4
122.5°	295.2	295.2	295.2	295.1	294.9	294.7	294.5
125°	320.8	321.1	321.3	321.4	321.5	321.6	321.6
127.5°	345.9	345.9	345.8	345.7	345.6	345.6	345.5
130°	361.6	361.7	361.7	361.7	361.7	361.7	361.7
132.5°	376.7	376.8	376.8	376.7	376.7	376.7	376.6
135°	397.8	398.0	398.1	398.3	398.5	398.7	398.9
137.5°	417.9	418.1	418.1	418.1	418.0	418.0	417.9
140°	430.4	430.7	430.9	431.0	431.1	431.1	431.2
142.5°	441.8	442.0	442.1	442.1	442.2	442.2	442.2
145°	458.2	458.3	458.3	458.5	458.7	458.9	459.1
147.5°	472.5	472.6	472.7	472.8	472.9	473.0	473.1
150°	481.7	481.7	481.8	481.9	482.0	482.1	482.1
152.5°	489.9	490.1	490.1	490.1	490.0	489.9	489.9
155°	501.0	501.3	501.4	501.1	500.9	500.6	500.3
157.5°	510.4	510.9	510.9	510.4	510.0	509.5	509.1
160°	516.5	517.0	517.0	516.5	515.9	515.4	514.9
162.5°	521.3	521.8	521.8	521.2	520.6	520.0	519.4
165°	528.3	529.1	529.0	528.2	527.4	526.6	525.8
167.5°	533.4	534.2	534.1	533.2	532.4	531.5	530.6
170°	536.4	537.2	537.1	536.1	535.2	534.3	533.4
172.5°	538.3	539.0	539.0	538.0	537.0	536.0	535.0
175°	540.7	541.5	541.4	540.3	539.2	538.1	537.1
177.5°	541.4	542.0	541.8	541.0	540.1	539.2	538.4
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3

(END OF REPORT)