

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333352-927

Luminaire Tested: **S125DIW-S375D1050U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333352-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1050U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4538.1 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	22	20	19	14
5	65	53	46	40	57	48	41	36	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2785	2785	2785	2785
5°	3225	2795	2447	2795
10°	3752	2781	2144	2781
15°	4153	2760	1978	2760
20°	4649	2728	1844	2728
25°	5447	2691	1779	2691
30°	5883	2655	1723	2655
35°	4837	2588	1686	2588
40°	3438	2494	1645	2494
45°	2641	2367	1621	2367
50°	2255	2210	1619	2210
55°	2008	2057	1633	2057
60°	1811	1888	1674	1888
65°	1673	1721	1718	1721
70°	1522	1545	1743	1545
75°	1342	1362	1727	1362
80°	1131	1112	1581	1112
85°	897	800	1275	800



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	0.9
10°-20°	123.6	2.7
20°-30°	200.7	4.4
30°-40°	244.8	5.4
40°-50°	222.7	4.9
50°-60°	177.4	3.9
60°-70°	123.6	2.7
70°-80°	65.9	1.5
80°-90°	18.9	0.4
90°-100°	39.3	0.9
100°-110°	242.1	5.3
110°-120°	439.0	9.7
120°-130°	563.4	12.4
130°-140°	606.0	13.4
140°-150°	568.8	12.5
150°-160°	460.1	10.1
160°-170°	297.6	6.6
170°-180°	102.6	2.3
0°-30°	365.9	8.1
0°-40°	610.7	13.5
0°-60°	1010.8	22.3
0°-90°	1219.2	26.9
90°-120°	720.3	15.9
90°-150°	2458.6	54.2
90°-180°	3319.0	73.1
0°-180°	4538.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	498	431	378	431	498	50
15°	621	413	296	413	621	178
25°	764	378	250	378	764	349
35°	614	328	214	328	614	375
45°	289	259	178	259	289	231
55°	178	183	145	183	178	161
65°	110	113	112	113	110	109
75°	54	55	69	55	54	58
85°	12	11	17	11	12	14
90°	19	1	19	1	19	9
95°	17	46	17	46	17	14
105°	238	236	238	236	238	215
115°	439	442	439	442	439	436
125°	629	629	629	629	629	559
135°	781	784	781	784	781	603
145°	907	909	907	909	907	567
155°	994	1002	994	1002	994	458
165°	1051	1057	1051	1057	1051	297
175°	1076	1081	1076	1081	1076	102
180°	1081	1081	1081	1081	1081	



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	456.1	455.6	455.0	453.8	454.7	452.2	451.1	449.0	446.5	445.6	444.6
5°	497.5	498.4	499.4	495.5	495.9	493.3	487.4	482.7	478.9	473.9	470.4
7.5°	547.3	545.2	544.9	542.5	538.2	534.7	528.6	520.8	513.2	504.5	497.4
10°	572.2	572.4	570.8	567.8	563.2	559.9	551.9	544.2	534.9	523.9	516.0
12.5°	591.0	591.8	589.6	585.7	583.4	576.1	569.7	560.6	549.5	540.7	528.8
15°	621.2	619.2	617.8	612.8	609.0	601.3	591.3	581.7	569.7	558.5	547.3
17.5°	650.5	652.1	649.4	644.8	632.9	623.9	610.5	597.4	582.3	567.4	554.1
20°	676.5	678.0	673.8	665.9	651.6	642.7	625.0	608.1	590.7	571.5	556.8
22.5°	709.1	707.9	702.2	690.2	677.9	661.3	642.1	621.5	599.8	578.1	558.6
25°	764.4	756.7	753.2	738.4	722.2	697.8	671.5	641.4	614.3	585.6	560.7
27.5°	795.1	792.7	788.8	778.5	761.4	735.3	704.3	667.7	629.5	593.2	560.5
30°	788.9	789.3	789.6	786.4	775.4	755.8	724.8	685.6	640.1	599.3	561.6
32.5°	734.4	741.1	747.5	755.0	758.1	754.3	735.0	699.4	652.7	606.3	561.0
35°	613.5	615.6	636.3	656.8	684.6	706.2	720.6	704.9	665.6	612.3	560.3
37.5°	478.4	488.3	502.6	525.8	565.9	601.9	648.2	669.4	656.7	614.3	559.0
40°	407.8	417.0	426.4	450.0	483.8	527.4	579.9	624.7	635.2	608.1	554.6
42.5°	353.4	360.6	371.0	388.7	417.0	455.6	505.8	564.4	600.5	590.3	545.4
45°	289.2	293.8	301.8	315.9	336.4	366.6	410.9	475.0	530.8	549.3	523.6
47.5°	247.6	247.6	253.8	263.5	278.3	304.0	336.8	386.9	446.6	490.7	488.6
50°	224.4	223.5	228.5	236.9	248.6	265.6	296.9	337.0	394.3	444.3	458.2
52.5°	204.5	204.6	207.6	213.9	223.7	238.2	261.6	297.8	346.7	398.0	424.2
55°	178.3	177.5	181.0	185.2	192.4	201.9	218.7	246.4	286.1	336.6	370.7
57.5°	154.2	156.3	157.6	160.6	166.5	172.9	187.1	207.4	238.9	282.3	318.2
60°	140.2	142.2	143.3	146.2	151.0	156.5	167.5	183.9	210.5	247.9	283.5
62.5°	127.6	129.2	129.6	132.2	136.1	141.4	150.0	163.9	184.9	217.5	252.5
65°	109.5	109.5	110.2	113.0	114.8	119.5	126.1	136.2	153.0	178.5	208.3
67.5°	92.0	92.8	92.7	93.9	95.5	99.3	103.9	112.3	124.8	143.3	167.2
70°	80.6	81.3	81.1	82.0	83.8	86.2	90.1	97.9	106.9	122.8	143.3
72.5°	70.3	70.6	70.1	71.3	72.4	74.5	78.8	83.0	91.3	104.8	121.7
75°	53.8	54.2	54.6	55.3	56.4	57.5	59.7	63.8	69.4	79.5	90.2
77.5°	40.3	39.6	40.6	40.4	41.0	41.9	43.8	46.0	50.5	57.0	65.3
80°	30.4	30.6	30.6	30.7	31.7	32.2	33.8	35.5	39.0	43.7	49.6
82.5°	22.2	22.7	22.3	22.7	23.4	23.8	24.8	26.1	28.1	31.9	36.1
85°	12.1	11.2	11.6	11.9	11.9	12.1	12.8	13.4	14.5	15.9	17.6
87.5°	7.4	7.5	7.6	7.4	7.5	7.4	7.8	7.6	7.8	8.2	8.5
90°	19.3	18.7	18.1	17.7	17.1	16.4	15.5	14.6	13.7	12.8	11.6
92.5°	18.0	17.7	17.4	17.2	17.0	16.4	15.5	14.6	13.7	12.8	11.7
95°	16.8	16.8	16.8	16.8	16.8	16.4	15.5	14.6	13.7	12.8	19.6
97.5°	16.8	16.8	16.8	16.8	16.8	19.3	24.3	29.4	34.4	39.5	52.8
100°	16.8	17.5	18.2	18.9	19.6	33.3	59.8	86.3	112.9	139.4	138.7
102.5°	100.8	112.9	125.0	137.1	149.2	157.8	162.8	167.8	172.9	177.8	177.4
105°	238.0	238.1	238.3	238.5	238.7	238.8	238.8	238.8	238.8	238.8	238.8
107.5°	300.0	300.5	301.0	301.6	302.1	302.4	302.3	302.3	302.2	302.2	301.8
110°	342.9	342.7	342.5	342.4	342.2	342.4	342.9	343.4	344.0	344.5	344.1



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.4	381.6	381.8	382.1	382.4	382.9	383.5	384.2	384.8	385.6	385.3
115°	439.0	440.1	441.2	442.3	443.3	444.2	444.9	445.6	446.3	447.0	446.9
117.5°	500.6	501.1	501.5	502.0	502.4	503.1	504.1	505.0	505.9	506.8	506.1
120°	538.4	539.3	540.2	541.1	541.9	542.6	543.0	543.3	543.7	544.0	543.4
122.5°	574.3	575.4	576.4	577.4	578.5	579.1	579.5	579.8	580.2	580.5	580.3
125°	628.9	629.5	630.0	630.6	631.1	631.7	632.4	633.1	633.8	634.5	634.5
127.5°	674.9	676.2	677.6	678.9	680.2	681.0	681.4	681.8	682.2	682.6	682.7
130°	708.3	709.2	710.0	710.9	711.8	712.5	713.0	713.6	714.2	714.6	714.5
132.5°	739.0	739.9	740.8	741.7	742.6	743.1	743.1	743.3	743.4	743.5	743.9
135°	781.2	782.2	783.3	784.3	785.4	786.2	786.5	786.9	787.2	787.6	787.9
137.5°	823.5	824.4	825.3	826.2	827.2	827.6	827.5	827.4	827.4	827.3	827.6
140°	848.4	849.5	850.6	851.7	852.7	853.1	852.7	852.4	852.0	851.7	851.8
142.5°	872.2	873.2	874.3	875.4	876.5	876.9	876.9	876.8	876.7	876.6	876.4
145°	907.0	908.0	909.1	910.1	911.2	911.6	911.5	911.3	911.2	910.9	910.9
147.5°	935.6	936.9	938.2	939.4	940.8	941.3	941.1	940.9	940.6	940.4	940.2
150°	954.2	955.6	957.0	958.5	959.9	960.4	960.1	959.7	959.4	959.0	958.7
152.5°	971.5	972.8	974.1	975.3	976.7	977.1	976.8	976.4	976.0	975.7	975.3
155°	994.3	995.7	997.1	998.5	1000.0	1000.4	999.9	999.3	998.8	998.3	997.9
157.5°	1013.4	1014.8	1016.2	1017.6	1019.1	1019.5	1018.9	1018.4	1017.8	1017.2	1017.2
160°	1025.6	1027.0	1028.4	1029.8	1031.2	1031.6	1030.9	1030.2	1029.4	1028.7	1028.6
162.5°	1036.4	1038.0	1039.6	1041.1	1042.7	1043.0	1042.0	1041.0	1040.0	1038.9	1038.8
165°	1051.1	1052.6	1054.0	1055.4	1056.9	1057.0	1056.0	1054.9	1053.8	1052.7	1052.6
167.5°	1061.4	1063.0	1064.6	1066.2	1067.9	1068.0	1066.7	1065.4	1064.1	1062.9	1062.7
170°	1067.1	1068.8	1070.4	1072.0	1073.6	1073.7	1072.3	1070.9	1069.4	1068.0	1067.8
172.5°	1071.0	1072.6	1074.2	1075.9	1077.4	1077.6	1076.3	1075.1	1073.7	1072.5	1072.1
175°	1076.0	1077.6	1079.2	1080.8	1082.4	1082.5	1081.1	1079.7	1078.2	1076.8	1076.7
177.5°	1078.9	1080.1	1081.2	1082.3	1083.5	1083.5	1082.5	1081.5	1080.5	1079.5	1079.3
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	443.7	442.7	441.5	439.4	437.0	435.6	433.6	432.3	429.7	427.5	425.1
5°	466.2	461.4	457.1	451.4	445.2	441.2	436.4	431.1	425.6	419.9	413.7
7.5°	489.6	481.1	472.0	462.2	452.5	443.6	435.1	426.9	419.1	409.7	401.8
10°	505.2	494.6	483.2	469.9	456.9	445.5	434.0	424.0	413.7	402.7	393.0
12.5°	520.9	506.8	490.7	476.0	460.4	446.7	433.2	420.3	407.4	395.2	383.9
15°	532.0	519.5	504.7	483.8	466.2	447.3	429.4	412.8	397.2	383.7	369.4
17.5°	539.2	523.2	507.2	487.3	464.2	443.1	422.8	403.7	386.2	369.0	355.3
20°	540.5	524.0	507.4	487.8	464.2	440.1	419.7	396.9	378.0	360.2	343.4
22.5°	540.1	521.4	503.3	483.2	460.1	437.8	413.3	390.0	369.5	352.0	334.5
25°	536.0	516.0	493.3	473.0	450.3	426.7	401.8	377.6	356.8	336.8	319.4
27.5°	532.5	506.7	480.9	457.2	435.3	413.7	389.8	365.1	342.0	321.8	305.4
30°	528.3	499.9	471.0	446.2	423.7	402.7	380.2	356.0	331.8	312.1	294.5
32.5°	524.5	491.4	460.9	434.0	410.1	389.7	368.9	345.9	322.2	302.1	284.6
35°	517.1	478.9	443.9	413.5	388.1	367.0	349.6	328.2	306.4	287.0	270.2
37.5°	507.8	462.4	424.8	393.0	365.1	342.9	326.8	310.3	289.4	270.7	255.5
40°	500.4	450.7	410.9	378.3	349.4	326.4	311.3	295.8	278.5	261.0	244.9
42.5°	491.2	440.1	396.9	361.8	333.2	310.7	294.9	281.8	266.4	250.2	235.3
45°	474.3	421.0	374.1	336.4	307.5	285.3	269.1	259.2	247.6	232.3	219.7
47.5°	449.3	398.1	349.6	310.7	280.8	260.3	245.0	235.5	227.4	216.0	204.5
50°	427.2	381.0	331.8	293.3	263.4	242.7	228.6	220.0	213.1	204.3	194.6
52.5°	402.5	359.4	314.4	276.2	246.7	226.3	212.5	204.9	199.2	192.9	183.3
55°	363.1	326.5	284.8	248.6	221.3	201.4	189.3	182.7	177.9	173.2	167.3
57.5°	319.9	291.2	254.3	221.1	196.0	177.8	166.6	160.2	156.5	154.0	150.6
60°	289.4	264.9	233.1	202.8	178.3	162.2	151.2	146.2	143.1	141.2	138.6
62.5°	261.1	241.0	211.5	183.9	162.5	147.3	137.4	132.6	129.7	128.7	126.6
65°	219.5	203.9	179.6	156.7	138.4	125.4	117.2	112.6	110.7	109.6	109.8
67.5°	178.4	169.0	149.4	129.9	115.3	104.4	97.8	94.3	93.3	91.9	91.9
70°	153.4	146.2	129.8	112.7	99.7	91.3	85.5	81.8	80.9	80.2	80.0
72.5°	131.3	125.0	110.7	97.1	85.4	78.0	73.2	71.0	69.5	69.1	69.0
75°	98.6	95.2	83.8	73.0	65.0	59.9	56.6	54.6	53.5	53.2	53.5
77.5°	70.1	67.1	59.9	52.2	47.1	43.3	40.5	39.8	38.6	38.6	38.4
80°	52.7	50.7	46.1	40.1	35.9	32.6	31.1	29.9	29.5	28.9	29.5
82.5°	38.2	36.0	33.0	29.1	25.6	23.7	22.2	21.8	21.5	21.3	21.4
85°	18.9	19.0	17.2	14.3	12.8	11.7	10.8	10.8	10.6	10.5	10.6
87.5°	8.5	8.0	7.1	6.4	5.4	4.7	4.3	4.1	4.0	4.1	4.5
90°	10.3	9.1	7.8	6.5	5.1	3.6	2.2	0.8	2.2	3.6	5.1
92.5°	10.6	9.5	8.4	8.3	9.3	10.4	11.3	12.4	11.3	10.4	9.3
95°	26.4	33.1	39.8	43.6	44.0	44.6	45.2	45.6	45.2	44.6	44.0
97.5°	66.2	79.6	93.0	99.2	98.2	97.3	96.3	95.4	96.3	97.3	98.2
100°	138.0	137.3	136.6	135.9	135.4	134.8	134.4	133.8	134.4	134.8	135.4
102.5°	177.0	176.6	176.2	175.6	174.9	174.3	173.6	172.9	173.6	174.3	174.9
105°	238.8	238.8	238.8	238.4	237.7	236.9	236.2	235.5	236.2	236.9	237.7
107.5°	301.5	301.1	300.8	300.6	300.6	300.6	300.6	300.6	300.6	300.6	300.6
110°	343.8	343.4	343.1	342.9	342.9	342.9	342.9	342.9	342.9	342.9	342.9



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	385.1	384.9	384.7	384.4	383.9	383.5	383.1	382.6	383.1	383.5	383.9
115°	446.7	446.6	446.3	445.8	444.9	444.0	443.1	442.3	443.1	444.0	444.9
117.5°	505.5	504.8	504.1	503.8	503.8	503.9	503.9	504.0	503.9	503.9	503.8
120°	543.0	542.4	541.9	541.7	541.9	542.0	542.2	542.4	542.2	542.0	541.9
122.5°	580.0	579.8	579.6	579.1	578.4	577.7	577.0	576.4	577.0	577.7	578.4
125°	634.5	634.5	634.5	633.9	632.6	631.4	630.2	628.9	630.2	631.4	632.6
127.5°	682.9	682.9	683.0	682.6	681.8	680.9	680.0	679.1	680.0	680.9	681.8
130°	714.3	714.2	713.9	713.4	712.5	711.6	710.7	709.9	710.7	711.6	712.5
132.5°	744.3	744.7	745.0	744.7	743.7	742.7	741.6	740.6	741.6	742.7	743.7
135°	788.3	788.6	789.0	788.6	787.6	786.5	785.4	784.3	785.4	786.5	787.6
137.5°	828.0	828.3	828.6	828.3	827.4	826.4	825.5	824.6	825.5	826.4	827.4
140°	852.0	852.2	852.4	852.3	851.9	851.6	851.2	850.9	851.2	851.6	851.9
142.5°	876.2	875.9	875.7	875.4	875.2	875.0	874.8	874.6	874.8	875.0	875.2
145°	910.9	910.9	910.9	910.8	910.5	910.1	909.7	909.3	909.7	910.1	910.5
147.5°	940.0	939.8	939.6	939.5	939.6	939.7	939.8	939.8	939.8	939.7	939.6
150°	958.3	958.0	957.6	957.6	958.0	958.3	958.7	959.0	958.7	958.3	958.0
152.5°	975.0	974.6	974.3	974.5	975.3	976.0	976.8	977.6	976.8	976.0	975.3
155°	997.6	997.2	996.9	997.2	998.3	999.3	1000.4	1001.5	1000.4	999.3	998.3
157.5°	1017.1	1017.1	1017.1	1017.3	1018.0	1018.7	1019.3	1019.9	1019.3	1018.7	1018.0
160°	1028.4	1028.2	1028.0	1028.5	1029.5	1030.6	1031.7	1032.8	1031.7	1030.6	1029.5
162.5°	1038.6	1038.5	1038.2	1038.7	1039.8	1040.8	1042.0	1043.0	1042.0	1040.8	1039.8
165°	1052.4	1052.3	1052.0	1052.5	1053.6	1054.6	1055.7	1056.8	1055.7	1054.6	1053.6
167.5°	1062.5	1062.3	1062.2	1062.6	1063.7	1064.9	1066.0	1067.0	1066.0	1064.9	1063.7
170°	1067.6	1067.5	1067.3	1067.8	1069.1	1070.3	1071.6	1072.8	1071.6	1070.3	1069.1
172.5°	1071.8	1071.5	1071.2	1071.7	1072.9	1074.1	1075.4	1076.7	1075.4	1074.1	1072.9
175°	1076.4	1076.3	1076.1	1076.5	1077.6	1078.6	1079.7	1080.8	1079.7	1078.6	1077.6
177.5°	1079.3	1079.1	1079.0	1079.3	1080.1	1081.0	1081.9	1082.8	1081.9	1081.0	1080.1
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	423.8	422.2	420.9	418.0	416.3	414.2	412.4	414.3	412.3	413.1	411.8
5°	410.6	405.4	401.8	396.5	391.9	387.7	384.6	384.0	382.5	381.8	379.6
7.5°	394.7	388.2	382.0	375.0	369.2	363.2	359.4	356.2	354.2	351.4	349.5
10°	385.3	376.7	369.4	361.0	353.6	347.2	342.1	339.5	337.2	333.7	332.4
12.5°	373.8	364.9	355.9	346.9	339.8	332.7	328.4	324.5	322.8	318.9	318.5
15°	359.9	346.5	337.7	328.6	318.9	313.0	309.3	305.1	303.3	300.6	298.6
17.5°	343.3	331.4	320.4	310.9	302.6	297.7	293.1	290.3	287.1	285.3	282.0
20°	331.3	320.0	309.0	298.9	292.5	286.8	283.2	280.4	277.1	276.2	272.9
22.5°	321.2	308.7	298.2	289.7	282.7	276.3	272.4	270.5	268.2	265.4	264.7
25°	304.8	291.8	282.8	274.4	268.2	262.3	259.6	257.2	255.0	252.9	252.2
27.5°	290.6	278.9	268.3	260.7	255.2	249.9	247.6	244.6	243.0	241.4	239.4
30°	280.6	268.7	259.4	252.1	246.2	241.5	238.8	236.9	235.4	233.9	232.8
32.5°	270.4	259.4	250.3	243.1	237.3	233.7	231.4	230.0	228.4	226.6	225.2
35°	256.8	244.7	235.9	229.7	225.1	222.4	219.8	218.6	216.7	216.7	215.2
37.5°	241.5	231.1	223.3	217.7	213.6	211.1	208.3	207.5	206.3	205.5	205.0
40°	232.5	222.8	215.5	209.8	205.4	203.4	201.1	199.7	199.0	198.0	197.7
42.5°	223.1	213.8	206.8	201.6	197.7	196.1	194.0	193.0	191.5	190.3	190.0
45°	208.8	199.9	193.5	189.3	186.0	183.9	182.7	180.5	179.7	178.3	178.1
47.5°	195.4	186.7	180.5	177.0	174.1	172.5	170.5	168.3	167.4	166.7	166.6
50°	185.2	177.4	171.5	168.3	165.5	163.1	161.1	159.6	159.1	159.1	159.5
52.5°	175.0	168.3	163.3	159.3	156.7	154.2	152.3	151.4	150.6	151.5	152.1
55°	160.0	153.2	149.6	145.7	143.1	140.2	139.3	138.9	138.4	139.8	140.6
57.5°	144.1	139.3	135.1	131.3	129.0	127.2	126.0	125.8	126.8	127.5	129.9
60°	134.0	128.5	124.7	121.8	119.0	117.9	117.5	117.2	117.9	119.9	123.0
62.5°	122.9	118.4	114.2	112.1	110.0	108.2	108.1	108.4	109.8	112.2	115.3
65°	106.5	102.7	100.0	97.4	95.7	94.7	95.0	95.7	97.4	100.5	103.9
67.5°	89.9	87.3	84.8	82.8	81.2	81.2	81.6	82.7	84.6	88.2	91.3
70°	79.3	76.4	74.3	73.4	72.1	71.4	72.5	74.3	76.0	79.3	82.0
72.5°	68.6	66.1	64.5	63.8	63.3	62.7	63.1	65.1	67.3	70.6	73.8
75°	52.7	51.8	50.7	50.0	49.4	49.8	50.1	52.0	53.8	57.3	60.9
77.5°	38.5	37.5	36.8	36.7	36.4	36.6	37.6	39.0	40.7	43.3	46.0
80°	29.1	28.8	28.4	28.2	28.2	28.4	29.9	30.7	32.4	34.8	37.0
82.5°	21.2	21.0	20.9	20.8	21.0	21.1	21.9	23.1	24.5	26.3	28.2
85°	11.2	10.8	11.3	11.6	11.2	11.7	12.1	12.8	13.4	14.3	15.2
87.5°	5.0	5.5	5.6	6.0	6.3	6.8	6.8	7.6	8.1	8.6	8.6
90°	6.5	7.8	9.1	10.3	11.6	12.8	13.7	14.6	15.5	16.4	17.1
92.5°	8.3	8.4	9.5	10.6	11.7	12.8	13.7	14.6	15.5	16.4	17.0
95°	43.6	39.8	33.1	26.4	19.6	12.8	13.7	14.6	15.5	16.4	16.8
97.5°	99.2	93.0	79.6	66.2	52.8	39.5	34.4	29.4	24.3	19.3	16.8
100°	135.9	136.6	137.3	138.0	138.7	139.4	112.9	86.3	59.8	33.3	19.6
102.5°	175.6	176.2	176.6	177.0	177.4	177.8	172.9	167.8	162.8	157.8	149.2
105°	238.4	238.8	238.8	238.8	238.8	238.8	238.8	238.8	238.8	238.8	238.7
107.5°	300.6	300.8	301.1	301.5	301.8	302.2	302.2	302.3	302.3	302.4	302.1
110°	342.9	343.1	343.4	343.8	344.1	344.5	344.0	343.4	342.9	342.4	342.2



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	384.4	384.7	384.9	385.1	385.3	385.6	384.8	384.2	383.5	382.9	382.4
115°	445.8	446.3	446.6	446.7	446.9	447.0	446.3	445.6	444.9	444.2	443.3
117.5°	503.8	504.1	504.8	505.5	506.1	506.8	505.9	505.0	504.1	503.1	502.4
120°	541.7	541.9	542.4	543.0	543.4	544.0	543.7	543.3	543.0	542.6	541.9
122.5°	579.1	579.6	579.8	580.0	580.3	580.5	580.2	579.8	579.5	579.1	578.5
125°	633.9	634.5	634.5	634.5	634.5	634.5	633.8	633.1	632.4	631.7	631.1
127.5°	682.6	683.0	682.9	682.9	682.7	682.6	682.2	681.8	681.4	681.0	680.2
130°	713.4	713.9	714.2	714.3	714.5	714.6	714.2	713.6	713.0	712.5	711.8
132.5°	744.7	745.0	744.7	744.3	743.9	743.5	743.4	743.3	743.1	743.1	742.6
135°	788.6	789.0	788.6	788.3	787.9	787.6	787.2	786.9	786.5	786.2	785.4
137.5°	828.3	828.6	828.3	828.0	827.6	827.3	827.4	827.4	827.5	827.6	827.2
140°	852.3	852.4	852.2	852.0	851.8	851.7	852.0	852.4	852.7	853.1	852.7
142.5°	875.4	875.7	875.9	876.2	876.4	876.6	876.7	876.8	876.9	876.9	876.5
145°	910.8	910.9	910.9	910.9	910.9	910.9	911.2	911.3	911.5	911.6	911.2
147.5°	939.5	939.6	939.8	940.0	940.2	940.4	940.6	940.9	941.1	941.3	940.8
150°	957.6	957.6	958.0	958.3	958.7	959.0	959.4	959.7	960.1	960.4	959.9
152.5°	974.5	974.3	974.6	975.0	975.3	975.7	976.0	976.4	976.8	977.1	976.7
155°	997.2	996.9	997.2	997.6	997.9	998.3	998.8	999.3	999.9	1000.4	1000.0
157.5°	1017.3	1017.1	1017.1	1017.1	1017.2	1017.2	1017.8	1018.4	1018.9	1019.5	1019.1
160°	1028.5	1028.0	1028.2	1028.4	1028.6	1028.7	1029.4	1030.2	1030.9	1031.6	1031.2
162.5°	1038.7	1038.2	1038.5	1038.6	1038.8	1038.9	1040.0	1041.0	1042.0	1043.0	1042.7
165°	1052.5	1052.0	1052.3	1052.4	1052.6	1052.7	1053.8	1054.9	1056.0	1057.0	1056.9
167.5°	1062.6	1062.2	1062.3	1062.5	1062.7	1062.9	1064.1	1065.4	1066.7	1068.0	1067.9
170°	1067.8	1067.3	1067.5	1067.6	1067.8	1068.0	1069.4	1070.9	1072.3	1073.7	1073.6
172.5°	1071.7	1071.2	1071.5	1071.8	1072.1	1072.5	1073.7	1075.1	1076.3	1077.6	1077.4
175°	1076.5	1076.1	1076.3	1076.4	1076.7	1076.8	1078.2	1079.7	1081.1	1082.5	1082.4
177.5°	1079.3	1079.0	1079.1	1079.3	1079.3	1079.5	1080.5	1081.5	1082.5	1083.5	1083.5
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	410.9	411.9	411.1	412.3	411.1	411.9	410.9	411.8	413.1	412.3	414.3
5°	378.7	377.1	378.2	377.5	378.2	377.1	378.7	379.6	381.8	382.5	384.0
7.5°	349.0	347.5	345.6	344.8	345.6	347.5	349.0	349.5	351.4	354.2	356.2
10°	330.4	328.4	328.2	326.9	328.2	328.4	330.4	332.4	333.7	337.2	339.5
12.5°	316.8	314.9	312.8	312.3	312.8	314.9	316.8	318.5	318.9	322.8	324.5
15°	297.5	296.0	294.7	295.8	294.7	296.0	297.5	298.6	300.6	303.3	305.1
17.5°	281.4	280.2	280.0	278.6	280.0	280.2	281.4	282.0	285.3	287.1	290.3
20°	271.2	270.4	270.8	268.3	270.8	270.4	271.2	272.9	276.2	277.1	280.4
22.5°	263.2	261.4	261.2	260.7	261.2	261.4	263.2	264.7	265.4	268.2	270.5
25°	250.6	249.7	248.7	249.7	248.7	249.7	250.6	252.2	252.9	255.0	257.2
27.5°	239.6	238.4	238.2	238.4	238.2	238.4	239.6	239.4	241.4	243.0	244.6
30°	232.8	231.0	231.2	231.0	231.2	231.0	232.8	232.8	233.9	235.4	236.9
32.5°	225.5	224.3	224.0	223.7	224.0	224.3	225.5	225.2	226.6	228.4	230.0
35°	214.7	214.7	213.8	213.8	213.8	214.7	214.7	215.2	216.7	216.7	218.6
37.5°	204.5	204.4	203.8	203.9	203.8	204.4	204.5	205.0	205.5	206.3	207.5
40°	196.9	196.8	196.2	195.1	196.2	196.8	196.9	197.7	198.0	199.0	199.7
42.5°	189.6	189.0	188.8	188.4	188.8	189.0	189.6	190.0	190.3	191.5	193.0
45°	178.1	178.1	177.8	177.5	177.8	178.1	178.1	178.1	178.3	179.7	180.5
47.5°	166.9	167.2	167.9	167.8	167.9	167.2	166.9	166.6	166.7	167.4	168.3
50°	160.2	160.3	160.9	161.1	160.9	160.3	160.2	159.5	159.1	159.1	159.6
52.5°	152.7	153.8	154.5	154.3	154.5	153.8	152.7	152.1	151.5	150.6	151.4
55°	142.2	143.5	144.8	145.0	144.8	143.5	142.2	140.6	139.8	138.4	138.9
57.5°	131.9	133.6	135.0	135.5	135.0	133.6	131.9	129.9	127.5	126.8	125.8
60°	124.8	127.2	128.9	129.6	128.9	127.2	124.8	123.0	119.9	117.9	117.2
62.5°	118.1	120.8	122.4	122.6	122.4	120.8	118.1	115.3	112.2	109.8	108.4
65°	107.1	109.8	111.3	112.4	111.3	109.8	107.1	103.9	100.5	97.4	95.7
67.5°	95.2	98.0	99.6	100.4	99.6	98.0	95.2	91.3	88.2	84.6	82.7
70°	86.6	89.4	91.5	92.3	91.5	89.4	86.6	82.0	79.3	76.0	74.3
72.5°	78.1	80.6	82.3	83.2	82.3	80.6	78.1	73.8	70.6	67.3	65.1
75°	63.3	66.6	68.3	69.2	68.3	66.6	63.3	60.9	57.3	53.8	52.0
77.5°	48.8	51.8	52.8	53.3	52.8	51.8	48.8	46.0	43.3	40.7	39.0
80°	39.1	41.0	42.3	42.5	42.3	41.0	39.1	37.0	34.8	32.4	30.7
82.5°	30.1	31.6	32.0	32.5	32.0	31.6	30.1	28.2	26.3	24.5	23.1
85°	16.5	17.2	17.4	17.2	17.4	17.2	16.5	15.2	14.3	13.4	12.8
87.5°	9.0	8.9	9.0	9.4	9.0	8.9	9.0	8.6	8.6	8.1	7.6
90°	17.7	18.1	18.7	19.3	18.7	18.1	17.7	17.1	16.4	15.5	14.6
92.5°	17.2	17.4	17.7	18.0	17.7	17.4	17.2	17.0	16.4	15.5	14.6
95°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.4	15.5	14.6
97.5°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	19.3	24.3	29.4
100°	18.9	18.2	17.5	16.8	17.5	18.2	18.9	19.6	33.3	59.8	86.3
102.5°	137.1	125.0	112.9	100.8	112.9	125.0	137.1	149.2	157.8	162.8	167.8
105°	238.5	238.3	238.1	238.0	238.1	238.3	238.5	238.7	238.8	238.8	238.8
107.5°	301.6	301.0	300.5	300.0	300.5	301.0	301.6	302.1	302.4	302.3	302.3
110°	342.4	342.5	342.7	342.9	342.7	342.5	342.4	342.2	342.4	342.9	343.4



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	382.1	381.8	381.6	381.4	381.6	381.8	382.1	382.4	382.9	383.5	384.2
115°	442.3	441.2	440.1	439.0	440.1	441.2	442.3	443.3	444.2	444.9	445.6
117.5°	502.0	501.5	501.1	500.6	501.1	501.5	502.0	502.4	503.1	504.1	505.0
120°	541.1	540.2	539.3	538.4	539.3	540.2	541.1	541.9	542.6	543.0	543.3
122.5°	577.4	576.4	575.4	574.3	575.4	576.4	577.4	578.5	579.1	579.5	579.8
125°	630.6	630.0	629.5	628.9	629.5	630.0	630.6	631.1	631.7	632.4	633.1
127.5°	678.9	677.6	676.2	674.9	676.2	677.6	678.9	680.2	681.0	681.4	681.8
130°	710.9	710.0	709.2	708.3	709.2	710.0	710.9	711.8	712.5	713.0	713.6
132.5°	741.7	740.8	739.9	739.0	739.9	740.8	741.7	742.6	743.1	743.1	743.3
135°	784.3	783.3	782.2	781.2	782.2	783.3	784.3	785.4	786.2	786.5	786.9
137.5°	826.2	825.3	824.4	823.5	824.4	825.3	826.2	827.2	827.6	827.5	827.4
140°	851.7	850.6	849.5	848.4	849.5	850.6	851.7	852.7	853.1	852.7	852.4
142.5°	875.4	874.3	873.2	872.2	873.2	874.3	875.4	876.5	876.9	876.9	876.8
145°	910.1	909.1	908.0	907.0	908.0	909.1	910.1	911.2	911.6	911.5	911.3
147.5°	939.4	938.2	936.9	935.6	936.9	938.2	939.4	940.8	941.3	941.1	940.9
150°	958.5	957.0	955.6	954.2	955.6	957.0	958.5	959.9	960.4	960.1	959.7
152.5°	975.3	974.1	972.8	971.5	972.8	974.1	975.3	976.7	977.1	976.8	976.4
155°	998.5	997.1	995.7	994.3	995.7	997.1	998.5	1000.0	1000.4	999.9	999.3
157.5°	1017.6	1016.2	1014.8	1013.4	1014.8	1016.2	1017.6	1019.1	1019.5	1018.9	1018.4
160°	1029.8	1028.4	1027.0	1025.6	1027.0	1028.4	1029.8	1031.2	1031.6	1030.9	1030.2
162.5°	1041.1	1039.6	1038.0	1036.4	1038.0	1039.6	1041.1	1042.7	1043.0	1042.0	1041.0
165°	1055.4	1054.0	1052.6	1051.1	1052.6	1054.0	1055.4	1056.9	1057.0	1056.0	1054.9
167.5°	1066.2	1064.6	1063.0	1061.4	1063.0	1064.6	1066.2	1067.9	1068.0	1066.7	1065.4
170°	1072.0	1070.4	1068.8	1067.1	1068.8	1070.4	1072.0	1073.6	1073.7	1072.3	1070.9
172.5°	1075.9	1074.2	1072.6	1071.0	1072.6	1074.2	1075.9	1077.4	1077.6	1076.3	1075.1
175°	1080.8	1079.2	1077.6	1076.0	1077.6	1079.2	1080.8	1082.4	1082.5	1081.1	1079.7
177.5°	1082.3	1081.2	1080.1	1078.9	1080.1	1081.2	1082.3	1083.5	1083.5	1082.5	1081.5
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	412.4	414.2	416.3	418.0	420.9	422.2	423.8	425.1	427.5	429.7	432.3
5°	384.6	387.7	391.9	396.5	401.8	405.4	410.6	413.7	419.9	425.6	431.1
7.5°	359.4	363.2	369.2	375.0	382.0	388.2	394.7	401.8	409.7	419.1	426.9
10°	342.1	347.2	353.6	361.0	369.4	376.7	385.3	393.0	402.7	413.7	424.0
12.5°	328.4	332.7	339.8	346.9	355.9	364.9	373.8	383.9	395.2	407.4	420.3
15°	309.3	313.0	318.9	328.6	337.7	346.5	359.9	369.4	383.7	397.2	412.8
17.5°	293.1	297.7	302.6	310.9	320.4	331.4	343.3	355.3	369.0	386.2	403.7
20°	283.2	286.8	292.5	298.9	309.0	320.0	331.3	343.4	360.2	378.0	396.9
22.5°	272.4	276.3	282.7	289.7	298.2	308.7	321.2	334.5	352.0	369.5	390.0
25°	259.6	262.3	268.2	274.4	282.8	291.8	304.8	319.4	336.8	356.8	377.6
27.5°	247.6	249.9	255.2	260.7	268.3	278.9	290.6	305.4	321.8	342.0	365.1
30°	238.8	241.5	246.2	252.1	259.4	268.7	280.6	294.5	312.1	331.8	356.0
32.5°	231.4	233.7	237.3	243.1	250.3	259.4	270.4	284.6	302.1	322.2	345.9
35°	219.8	222.4	225.1	229.7	235.9	244.7	256.8	270.2	287.0	306.4	328.2
37.5°	208.3	211.1	213.6	217.7	223.3	231.1	241.5	255.5	270.7	289.4	310.3
40°	201.1	203.4	205.4	209.8	215.5	222.8	232.5	244.9	261.0	278.5	295.8
42.5°	194.0	196.1	197.7	201.6	206.8	213.8	223.1	235.3	250.2	266.4	281.8
45°	182.7	183.9	186.0	189.3	193.5	199.9	208.8	219.7	232.3	247.6	259.2
47.5°	170.5	172.5	174.1	177.0	180.5	186.7	195.4	204.5	216.0	227.4	235.5
50°	161.1	163.1	165.5	168.3	171.5	177.4	185.2	194.6	204.3	213.1	220.0
52.5°	152.3	154.2	156.7	159.3	163.3	168.3	175.0	183.3	192.9	199.2	204.9
55°	139.3	140.2	143.1	145.7	149.6	153.2	160.0	167.3	173.2	177.9	182.7
57.5°	126.0	127.2	129.0	131.3	135.1	139.3	144.1	150.6	154.0	156.5	160.2
60°	117.5	117.9	119.0	121.8	124.7	128.5	134.0	138.6	141.2	143.1	146.2
62.5°	108.1	108.2	110.0	112.1	114.2	118.4	122.9	126.6	128.7	129.7	132.6
65°	95.0	94.7	95.7	97.4	100.0	102.7	106.5	109.8	109.6	110.7	112.6
67.5°	81.6	81.2	81.2	82.8	84.8	87.3	89.9	91.9	91.9	93.3	94.3
70°	72.5	71.4	72.1	73.4	74.3	76.4	79.3	80.0	80.2	80.9	81.8
72.5°	63.1	62.7	63.3	63.8	64.5	66.1	68.6	69.0	69.1	69.5	71.0
75°	50.1	49.8	49.4	50.0	50.7	51.8	52.7	53.5	53.2	53.5	54.6
77.5°	37.6	36.6	36.4	36.7	36.8	37.5	38.5	38.4	38.6	38.6	39.8
80°	29.9	28.4	28.2	28.2	28.4	28.8	29.1	29.5	28.9	29.5	29.9
82.5°	21.9	21.1	21.0	20.8	20.9	21.0	21.2	21.4	21.3	21.5	21.8
85°	12.1	11.7	11.2	11.6	11.3	10.8	11.2	10.6	10.5	10.6	10.8
87.5°	6.8	6.8	6.3	6.0	5.6	5.5	5.0	4.5	4.1	4.0	4.1
90°	13.7	12.8	11.6	10.3	9.1	7.8	6.5	5.1	3.6	2.2	0.8
92.5°	13.7	12.8	11.7	10.6	9.5	8.4	8.3	9.3	10.4	11.3	12.4
95°	13.7	12.8	19.6	26.4	33.1	39.8	43.6	44.0	44.6	45.2	45.6
97.5°	34.4	39.5	52.8	66.2	79.6	93.0	99.2	98.2	97.3	96.3	95.4
100°	112.9	139.4	138.7	138.0	137.3	136.6	135.9	135.4	134.8	134.4	133.8
102.5°	172.9	177.8	177.4	177.0	176.6	176.2	175.6	174.9	174.3	173.6	172.9
105°	238.8	238.8	238.8	238.8	238.8	238.8	238.4	237.7	236.9	236.2	235.5
107.5°	302.2	302.2	301.8	301.5	301.1	300.8	300.6	300.6	300.6	300.6	300.6
110°	344.0	344.5	344.1	343.8	343.4	343.1	342.9	342.9	342.9	342.9	342.9



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	384.8	385.6	385.3	385.1	384.9	384.7	384.4	383.9	383.5	383.1	382.6
115°	446.3	447.0	446.9	446.7	446.6	446.3	445.8	444.9	444.0	443.1	442.3
117.5°	505.9	506.8	506.1	505.5	504.8	504.1	503.8	503.8	503.9	503.9	504.0
120°	543.7	544.0	543.4	543.0	542.4	541.9	541.7	541.9	542.0	542.2	542.4
122.5°	580.2	580.5	580.3	580.0	579.8	579.6	579.1	578.4	577.7	577.0	576.4
125°	633.8	634.5	634.5	634.5	634.5	634.5	633.9	632.6	631.4	630.2	628.9
127.5°	682.2	682.6	682.7	682.9	682.9	683.0	682.6	681.8	680.9	680.0	679.1
130°	714.2	714.6	714.5	714.3	714.2	713.9	713.4	712.5	711.6	710.7	709.9
132.5°	743.4	743.5	743.9	744.3	744.7	745.0	744.7	743.7	742.7	741.6	740.6
135°	787.2	787.6	787.9	788.3	788.6	789.0	788.6	787.6	786.5	785.4	784.3
137.5°	827.4	827.3	827.6	828.0	828.3	828.6	828.3	827.4	826.4	825.5	824.6
140°	852.0	851.7	851.8	852.0	852.2	852.4	852.3	851.9	851.6	851.2	850.9
142.5°	876.7	876.6	876.4	876.2	875.9	875.7	875.4	875.2	875.0	874.8	874.6
145°	911.2	910.9	910.9	910.9	910.9	910.9	910.8	910.5	910.1	909.7	909.3
147.5°	940.6	940.4	940.2	940.0	939.8	939.6	939.5	939.6	939.7	939.8	939.8
150°	959.4	959.0	958.7	958.3	958.0	957.6	957.6	958.0	958.3	958.7	959.0
152.5°	976.0	975.7	975.3	975.0	974.6	974.3	974.5	975.3	976.0	976.8	977.6
155°	998.8	998.3	997.9	997.6	997.2	996.9	997.2	998.3	999.3	1000.4	1001.5
157.5°	1017.8	1017.2	1017.2	1017.1	1017.1	1017.1	1017.3	1018.0	1018.7	1019.3	1019.9
160°	1029.4	1028.7	1028.6	1028.4	1028.2	1028.0	1028.5	1029.5	1030.6	1031.7	1032.8
162.5°	1040.0	1038.9	1038.8	1038.6	1038.5	1038.2	1038.7	1039.8	1040.8	1042.0	1043.0
165°	1053.8	1052.7	1052.6	1052.4	1052.3	1052.0	1052.5	1053.6	1054.6	1055.7	1056.8
167.5°	1064.1	1062.9	1062.7	1062.5	1062.3	1062.2	1062.6	1063.7	1064.9	1066.0	1067.0
170°	1069.4	1068.0	1067.8	1067.6	1067.5	1067.3	1067.8	1069.1	1070.3	1071.6	1072.8
172.5°	1073.7	1072.5	1072.1	1071.8	1071.5	1071.2	1071.7	1072.9	1074.1	1075.4	1076.7
175°	1078.2	1076.8	1076.7	1076.4	1076.3	1076.1	1076.5	1077.6	1078.6	1079.7	1080.8
177.5°	1080.5	1079.5	1079.3	1079.3	1079.1	1079.0	1079.3	1080.1	1081.0	1081.9	1082.8
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	433.6	435.6	437.0	439.4	441.5	442.7	443.7	444.6	445.6	446.5	449.0
5°	436.4	441.2	445.2	451.4	457.1	461.4	466.2	470.4	473.9	478.9	482.7
7.5°	435.1	443.6	452.5	462.2	472.0	481.1	489.6	497.4	504.5	513.2	520.8
10°	434.0	445.5	456.9	469.9	483.2	494.6	505.2	516.0	523.9	534.9	544.2
12.5°	433.2	446.7	460.4	476.0	490.7	506.8	520.9	528.8	540.7	549.5	560.6
15°	429.4	447.3	466.2	483.8	504.7	519.5	532.0	547.3	558.5	569.7	581.7
17.5°	422.8	443.1	464.2	487.3	507.2	523.2	539.2	554.1	567.4	582.3	597.4
20°	419.7	440.1	464.2	487.8	507.4	524.0	540.5	556.8	571.5	590.7	608.1
22.5°	413.3	437.8	460.1	483.2	503.3	521.4	540.1	558.6	578.1	599.8	621.5
25°	401.8	426.7	450.3	473.0	493.3	516.0	536.0	560.7	585.6	614.3	641.4
27.5°	389.8	413.7	435.3	457.2	480.9	506.7	532.5	560.5	593.2	629.5	667.7
30°	380.2	402.7	423.7	446.2	471.0	499.9	528.3	561.6	599.3	640.1	685.6
32.5°	368.9	389.7	410.1	434.0	460.9	491.4	524.5	561.0	606.3	652.7	699.4
35°	349.6	367.0	388.1	413.5	443.9	478.9	517.1	560.3	612.3	665.6	704.9
37.5°	326.8	342.9	365.1	393.0	424.8	462.4	507.8	559.0	614.3	656.7	669.4
40°	311.3	326.4	349.4	378.3	410.9	450.7	500.4	554.6	608.1	635.2	624.7
42.5°	294.9	310.7	333.2	361.8	396.9	440.1	491.2	545.4	590.3	600.5	564.4
45°	269.1	285.3	307.5	336.4	374.1	421.0	474.3	523.6	549.3	530.8	475.0
47.5°	245.0	260.3	280.8	310.7	349.6	398.1	449.3	488.6	490.7	446.6	386.9
50°	228.6	242.7	263.4	293.3	331.8	381.0	427.2	458.2	444.3	394.3	337.0
52.5°	212.5	226.3	246.7	276.2	314.4	359.4	402.5	424.2	398.0	346.7	297.8
55°	189.3	201.4	221.3	248.6	284.8	326.5	363.1	370.7	336.6	286.1	246.4
57.5°	166.6	177.8	196.0	221.1	254.3	291.2	319.9	318.2	282.3	238.9	207.4
60°	151.2	162.2	178.3	202.8	233.1	264.9	289.4	283.5	247.9	210.5	183.9
62.5°	137.4	147.3	162.5	183.9	211.5	241.0	261.1	252.5	217.5	184.9	163.9
65°	117.2	125.4	138.4	156.7	179.6	203.9	219.5	208.3	178.5	153.0	136.2
67.5°	97.8	104.4	115.3	129.9	149.4	169.0	178.4	167.2	143.3	124.8	112.3
70°	85.5	91.3	99.7	112.7	129.8	146.2	153.4	143.3	122.8	106.9	97.9
72.5°	73.2	78.0	85.4	97.1	110.7	125.0	131.3	121.7	104.8	91.3	83.0
75°	56.6	59.9	65.0	73.0	83.8	95.2	98.6	90.2	79.5	69.4	63.8
77.5°	40.5	43.3	47.1	52.2	59.9	67.1	70.1	65.3	57.0	50.5	46.0
80°	31.1	32.6	35.9	40.1	46.1	50.7	52.7	49.6	43.7	39.0	35.5
82.5°	22.2	23.7	25.6	29.1	33.0	36.0	38.2	36.1	31.9	28.1	26.1
85°	10.8	11.7	12.8	14.3	17.2	19.0	18.9	17.6	15.9	14.5	13.4
87.5°	4.3	4.7	5.4	6.4	7.1	8.0	8.5	8.5	8.2	7.8	7.6
90°	2.2	3.6	5.1	6.5	7.8	9.1	10.3	11.6	12.8	13.7	14.6
92.5°	11.3	10.4	9.3	8.3	8.4	9.5	10.6	11.7	12.8	13.7	14.6
95°	45.2	44.6	44.0	43.6	39.8	33.1	26.4	19.6	12.8	13.7	14.6
97.5°	96.3	97.3	98.2	99.2	93.0	79.6	66.2	52.8	39.5	34.4	29.4
100°	134.4	134.8	135.4	135.9	136.6	137.3	138.0	138.7	139.4	112.9	86.3
102.5°	173.6	174.3	174.9	175.6	176.2	176.6	177.0	177.4	177.8	172.9	167.8
105°	236.2	236.9	237.7	238.4	238.8	238.8	238.8	238.8	238.8	238.8	238.8
107.5°	300.6	300.6	300.6	300.6	300.8	301.1	301.5	301.8	302.2	302.2	302.3
110°	342.9	342.9	342.9	342.9	343.1	343.4	343.8	344.1	344.5	344.0	343.4



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.1	383.5	383.9	384.4	384.7	384.9	385.1	385.3	385.6	384.8	384.2
115°	443.1	444.0	444.9	445.8	446.3	446.6	446.7	446.9	447.0	446.3	445.6
117.5°	503.9	503.9	503.8	503.8	504.1	504.8	505.5	506.1	506.8	505.9	505.0
120°	542.2	542.0	541.9	541.7	541.9	542.4	543.0	543.4	544.0	543.7	543.3
122.5°	577.0	577.7	578.4	579.1	579.6	579.8	580.0	580.3	580.5	580.2	579.8
125°	630.2	631.4	632.6	633.9	634.5	634.5	634.5	634.5	634.5	633.8	633.1
127.5°	680.0	680.9	681.8	682.6	683.0	682.9	682.9	682.7	682.6	682.2	681.8
130°	710.7	711.6	712.5	713.4	713.9	714.2	714.3	714.5	714.6	714.2	713.6
132.5°	741.6	742.7	743.7	744.7	745.0	744.7	744.3	743.9	743.5	743.4	743.3
135°	785.4	786.5	787.6	788.6	789.0	788.6	788.3	787.9	787.6	787.2	786.9
137.5°	825.5	826.4	827.4	828.3	828.6	828.3	828.0	827.6	827.3	827.4	827.4
140°	851.2	851.6	851.9	852.3	852.4	852.2	852.0	851.8	851.7	852.0	852.4
142.5°	874.8	875.0	875.2	875.4	875.7	875.9	876.2	876.4	876.6	876.7	876.8
145°	909.7	910.1	910.5	910.8	910.9	910.9	910.9	910.9	910.9	911.2	911.3
147.5°	939.8	939.7	939.6	939.5	939.6	939.8	940.0	940.2	940.4	940.6	940.9
150°	958.7	958.3	958.0	957.6	957.6	958.0	958.3	958.7	959.0	959.4	959.7
152.5°	976.8	976.0	975.3	974.5	974.3	974.6	975.0	975.3	975.7	976.0	976.4
155°	1000.4	999.3	998.3	997.2	996.9	997.2	997.6	997.9	998.3	998.8	999.3
157.5°	1019.3	1018.7	1018.0	1017.3	1017.1	1017.1	1017.1	1017.2	1017.2	1017.8	1018.4
160°	1031.7	1030.6	1029.5	1028.5	1028.0	1028.2	1028.4	1028.6	1028.7	1029.4	1030.2
162.5°	1042.0	1040.8	1039.8	1038.7	1038.2	1038.5	1038.6	1038.8	1038.9	1040.0	1041.0
165°	1055.7	1054.6	1053.6	1052.5	1052.0	1052.3	1052.4	1052.6	1052.7	1053.8	1054.9
167.5°	1066.0	1064.9	1063.7	1062.6	1062.2	1062.3	1062.5	1062.7	1062.9	1064.1	1065.4
170°	1071.6	1070.3	1069.1	1067.8	1067.3	1067.5	1067.6	1067.8	1068.0	1069.4	1070.9
172.5°	1075.4	1074.1	1072.9	1071.7	1071.2	1071.5	1071.8	1072.1	1072.5	1073.7	1075.1
175°	1079.7	1078.6	1077.6	1076.5	1076.1	1076.3	1076.4	1076.7	1076.8	1078.2	1079.7
177.5°	1081.9	1081.0	1080.1	1079.3	1079.0	1079.1	1079.3	1079.3	1079.5	1080.5	1081.5
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	451.1	452.2	454.7	453.8	455.0	455.6	456.1
5°	487.4	493.3	495.9	495.5	499.4	498.4	497.5
7.5°	528.6	534.7	538.2	542.5	544.9	545.2	547.3
10°	551.9	559.9	563.2	567.8	570.8	572.4	572.2
12.5°	569.7	576.1	583.4	585.7	589.6	591.8	591.0
15°	591.3	601.3	609.0	612.8	617.8	619.2	621.2
17.5°	610.5	623.9	632.9	644.8	649.4	652.1	650.5
20°	625.0	642.7	651.6	665.9	673.8	678.0	676.5
22.5°	642.1	661.3	677.9	690.2	702.2	707.9	709.1
25°	671.5	697.8	722.2	738.4	753.2	756.7	764.4
27.5°	704.3	735.3	761.4	778.5	788.8	792.7	795.1
30°	724.8	755.8	775.4	786.4	789.6	789.3	788.9
32.5°	735.0	754.3	758.1	755.0	747.5	741.1	734.4
35°	720.6	706.2	684.6	656.8	636.3	615.6	613.5
37.5°	648.2	601.9	565.9	525.8	502.6	488.3	478.4
40°	579.9	527.4	483.8	450.0	426.4	417.0	407.8
42.5°	505.8	455.6	417.0	388.7	371.0	360.6	353.4
45°	410.9	366.6	336.4	315.9	301.8	293.8	289.2
47.5°	336.8	304.0	278.3	263.5	253.8	247.6	247.6
50°	296.9	265.6	248.6	236.9	228.5	223.5	224.4
52.5°	261.6	238.2	223.7	213.9	207.6	204.6	204.5
55°	218.7	201.9	192.4	185.2	181.0	177.5	178.3
57.5°	187.1	172.9	166.5	160.6	157.6	156.3	154.2
60°	167.5	156.5	151.0	146.2	143.3	142.2	140.2
62.5°	150.0	141.4	136.1	132.2	129.6	129.2	127.6
65°	126.1	119.5	114.8	113.0	110.2	109.5	109.5
67.5°	103.9	99.3	95.5	93.9	92.7	92.8	92.0
70°	90.1	86.2	83.8	82.0	81.1	81.3	80.6
72.5°	78.8	74.5	72.4	71.3	70.1	70.6	70.3
75°	59.7	57.5	56.4	55.3	54.6	54.2	53.8
77.5°	43.8	41.9	41.0	40.4	40.6	39.6	40.3
80°	33.8	32.2	31.7	30.7	30.6	30.6	30.4
82.5°	24.8	23.8	23.4	22.7	22.3	22.7	22.2
85°	12.8	12.1	11.9	11.9	11.6	11.2	12.1
87.5°	7.8	7.4	7.5	7.4	7.6	7.5	7.4
90°	15.5	16.4	17.1	17.7	18.1	18.7	19.3
92.5°	15.5	16.4	17.0	17.2	17.4	17.7	18.0
95°	15.5	16.4	16.8	16.8	16.8	16.8	16.8
97.5°	24.3	19.3	16.8	16.8	16.8	16.8	16.8
100°	59.8	33.3	19.6	18.9	18.2	17.5	16.8
102.5°	162.8	157.8	149.2	137.1	125.0	112.9	100.8
105°	238.8	238.8	238.7	238.5	238.3	238.1	238.0
107.5°	302.3	302.4	302.1	301.6	301.0	300.5	300.0
110°	342.9	342.4	342.2	342.4	342.5	342.7	342.9



TEST NUMBER: P333352-927

CATALOG NUMBER: S125DIW-S375D1050U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	383.5	382.9	382.4	382.1	381.8	381.6	381.4
115°	444.9	444.2	443.3	442.3	441.2	440.1	439.0
117.5°	504.1	503.1	502.4	502.0	501.5	501.1	500.6
120°	543.0	542.6	541.9	541.1	540.2	539.3	538.4
122.5°	579.5	579.1	578.5	577.4	576.4	575.4	574.3
125°	632.4	631.7	631.1	630.6	630.0	629.5	628.9
127.5°	681.4	681.0	680.2	678.9	677.6	676.2	674.9
130°	713.0	712.5	711.8	710.9	710.0	709.2	708.3
132.5°	743.1	743.1	742.6	741.7	740.8	739.9	739.0
135°	786.5	786.2	785.4	784.3	783.3	782.2	781.2
137.5°	827.5	827.6	827.2	826.2	825.3	824.4	823.5
140°	852.7	853.1	852.7	851.7	850.6	849.5	848.4
142.5°	876.9	876.9	876.5	875.4	874.3	873.2	872.2
145°	911.5	911.6	911.2	910.1	909.1	908.0	907.0
147.5°	941.1	941.3	940.8	939.4	938.2	936.9	935.6
150°	960.1	960.4	959.9	958.5	957.0	955.6	954.2
152.5°	976.8	977.1	976.7	975.3	974.1	972.8	971.5
155°	999.9	1000.4	1000.0	998.5	997.1	995.7	994.3
157.5°	1018.9	1019.5	1019.1	1017.6	1016.2	1014.8	1013.4
160°	1030.9	1031.6	1031.2	1029.8	1028.4	1027.0	1025.6
162.5°	1042.0	1043.0	1042.7	1041.1	1039.6	1038.0	1036.4
165°	1056.0	1057.0	1056.9	1055.4	1054.0	1052.6	1051.1
167.5°	1066.7	1068.0	1067.9	1066.2	1064.6	1063.0	1061.4
170°	1072.3	1073.7	1073.6	1072.0	1070.4	1068.8	1067.1
172.5°	1076.3	1077.6	1077.4	1075.9	1074.2	1072.6	1071.0
175°	1081.1	1082.5	1082.4	1080.8	1079.2	1077.6	1076.0
177.5°	1082.5	1083.5	1083.5	1082.3	1081.2	1080.1	1078.9
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8

(END OF REPORT)