

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333371-927

Luminaire Tested: **S125DIW-S610D470U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333371-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D470U927-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3289.1 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	61	56	52	54	50	47	46	43	41	37
4	77	66	58	52	72	62	55	49	55	49	45	48	44	40	42	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	24	46	35	28	23	31	25	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4579	4579	4579	4579
5°	5302	4595	4023	4595
10°	6169	4571	3525	4571
15°	6829	4537	3251	4537
20°	7644	4484	3032	4484
25°	8955	4424	2925	4424
30°	9672	4365	2832	4365
35°	7953	4254	2771	4254
40°	5653	4100	2705	4100
45°	4343	3892	2666	3892
50°	3706	3634	2661	3634
55°	3300	3381	2684	3381
60°	2977	3105	2753	3105
65°	2751	2829	2823	2829
70°	2500	2540	2865	2540
75°	2208	2238	2840	2238
80°	1860	1822	2596	1822
85°	1475	1312	2097	1312



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.3	2.1
10°-20°	203.2	6.2
20°-30°	330.0	10.0
30°-40°	402.5	12.2
40°-50°	366.2	11.1
50°-60°	291.7	8.9
60°-70°	203.2	6.2
70°-80°	108.3	3.3
80°-90°	28.4	0.9
90°-100°	30.9	0.9
100°-110°	91.2	2.8
110°-120°	154.6	4.7
120°-130°	203.4	6.2
130°-140°	227.9	6.9
140°-150°	223.4	6.8
150°-160°	187.6	5.7
160°-170°	124.7	3.8
170°-180°	43.6	1.3
0°-30°	601.5	18.3
0°-40°	1004.0	30.5
0°-60°	1661.8	50.5
0°-90°	2001.7	60.9
90°-120°	276.7	8.4
90°-150°	931.5	28.3
90°-180°	1287.0	39.1
0°-180°	3289.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	818	709	620	709	818	82
15°	1021	679	486	679	1021	292
25°	1257	621	410	621	1257	574
35°	1009	540	352	540	1009	617
45°	476	426	292	426	476	381
55°	293	300	238	300	293	264
65°	180	185	185	185	180	179
75°	88	90	114	90	88	95
85°	20	18	28	18	20	23
90°	9	0	9	0	9	6
95°	31	23	31	23	31	31
105°	89	82	89	82	89	94
115°	156	155	156	155	156	154
125°	227	226	227	226	227	203
135°	295	294	295	294	295	227
145°	357	356	357	356	357	223
155°	407	407	407	407	407	187
165°	442	443	442	443	442	124
175°	458	460	458	460	458	44
180°	461	461	461	461	461	



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	750.0	748.9	748.0	746.1	747.5	743.4	741.5	738.2	734.0	732.6	730.9
5°	817.9	819.4	820.9	814.6	815.2	811.0	801.4	793.5	787.3	779.1	773.4
7.5°	899.8	896.2	896.0	891.8	884.8	879.2	869.0	856.1	843.7	829.5	817.8
10°	940.7	941.0	938.3	933.5	926.0	920.5	907.3	894.7	879.3	861.3	848.3
12.5°	971.5	972.8	969.4	962.9	959.2	947.1	936.7	921.6	903.4	889.0	869.3
15°	1021.4	1018.0	1015.7	1007.5	1001.2	988.6	972.0	956.3	936.5	918.1	899.8
17.5°	1069.4	1072.1	1067.5	1060.1	1040.5	1025.7	1003.5	982.1	957.4	932.8	910.9
20°	1112.2	1114.7	1107.7	1094.8	1071.3	1056.5	1027.4	999.7	971.1	939.5	915.4
22.5°	1165.7	1163.8	1154.4	1134.7	1114.4	1087.1	1055.6	1021.8	986.0	950.3	918.3
25°	1256.7	1244.0	1238.3	1213.9	1187.2	1147.2	1103.8	1054.5	1010.0	962.7	921.8
27.5°	1307.1	1303.1	1296.8	1279.8	1251.6	1208.9	1157.8	1097.6	1034.7	975.2	921.5
30°	1297.0	1297.6	1298.2	1292.8	1274.8	1242.5	1191.7	1127.0	1052.3	985.2	923.3
32.5°	1207.4	1218.4	1228.9	1241.3	1246.3	1240.2	1208.3	1149.9	1073.1	996.8	922.3
35°	1008.7	1012.0	1046.1	1079.7	1125.5	1161.0	1184.8	1158.9	1094.2	1006.6	921.1
37.5°	786.5	802.8	826.3	864.4	930.4	989.5	1065.6	1100.5	1079.6	1009.8	919.0
40°	670.5	685.6	700.8	739.7	795.4	867.0	953.3	1027.1	1044.3	999.7	911.8
42.5°	580.9	592.9	609.9	639.1	685.6	749.0	831.6	927.9	987.1	970.3	896.7
45°	475.5	483.0	496.2	519.4	553.1	602.8	675.6	780.9	872.7	903.1	860.6
47.5°	406.9	406.9	417.2	433.2	457.6	499.7	553.6	636.1	734.1	806.7	803.3
50°	368.9	367.4	375.6	389.4	408.7	436.7	488.1	554.1	648.2	730.4	753.2
52.5°	336.2	336.4	341.4	351.6	367.7	391.7	430.1	489.5	570.0	654.3	697.4
55°	293.1	291.9	297.6	304.5	316.3	331.9	359.7	405.0	470.3	553.4	609.3
57.5°	253.7	256.9	259.2	264.0	273.8	284.2	307.6	341.0	392.8	464.1	523.2
60°	230.5	233.9	235.6	240.4	248.3	257.3	275.4	302.5	346.1	407.5	466.1
62.5°	209.8	212.4	213.0	217.3	223.7	232.5	246.7	269.4	304.0	357.6	415.1
65°	180.0	180.0	181.2	185.7	188.7	196.5	207.3	223.9	251.6	293.4	342.5
67.5°	151.1	152.7	152.3	154.3	157.1	163.2	171.0	184.6	205.1	235.6	274.9
70°	132.4	133.6	133.3	134.8	137.8	141.7	148.1	161.0	175.7	201.9	235.6
72.5°	115.6	116.1	115.3	117.2	119.1	122.5	129.5	136.4	150.2	172.3	200.0
75°	88.5	89.0	89.7	90.9	92.7	94.5	98.1	105.0	114.1	130.6	148.4
77.5°	66.3	65.2	66.6	66.5	67.5	68.8	72.0	75.7	83.1	93.6	107.3
80°	50.0	50.2	50.2	50.5	52.0	53.0	55.7	58.4	64.1	71.9	81.5
82.5°	36.4	37.2	36.8	37.3	38.6	39.2	40.7	42.9	46.3	52.4	59.4
85°	19.9	18.4	18.9	19.6	19.6	19.9	21.1	21.9	23.8	26.1	28.9
87.5°	7.5	7.9	8.2	8.1	8.2	8.2	9.1	9.0	9.7	10.3	11.2
90°	8.6	8.4	8.2	7.9	7.7	7.4	7.0	6.6	6.2	5.8	5.1
92.5°	17.0	16.8	16.6	16.4	16.2	15.9	15.4	14.8	14.3	13.8	13.1
95°	30.9	30.7	30.6	30.4	30.3	29.9	29.3	28.8	28.2	27.6	26.9
97.5°	46.8	46.7	46.7	46.5	46.4	46.1	45.6	45.1	44.5	44.0	42.9
100°	58.9	58.7	58.5	58.4	58.2	57.8	57.1	56.4	55.7	54.9	53.9
102.5°	71.0	70.7	70.5	70.3	70.0	69.6	68.8	68.0	67.2	66.4	65.9
105°	89.0	88.8	88.6	88.3	88.1	87.7	87.2	86.7	86.3	85.8	85.3
107.5°	107.6	107.6	107.6	107.7	107.7	107.5	107.3	107.0	106.8	106.5	106.2
110°	121.4	121.4	121.5	121.6	121.7	121.6	121.4	121.1	120.9	120.6	120.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.8	135.0	135.1	135.3	135.5	135.5	135.3	135.2	135.1	135.0	134.7
115°	156.2	156.3	156.4	156.5	156.5	156.6	156.7	156.8	156.9	156.9	156.8
117.5°	177.0	177.3	177.7	178.0	178.3	178.4	178.3	178.3	178.2	178.2	178.0
120°	191.4	191.7	192.0	192.3	192.7	192.8	192.8	192.8	192.8	192.8	192.7
122.5°	205.7	206.0	206.3	206.5	206.8	206.9	207.0	207.1	207.1	207.2	207.0
125°	227.3	227.4	227.4	227.5	227.6	227.8	227.9	228.1	228.2	228.4	228.3
127.5°	248.0	248.1	248.3	248.4	248.6	248.7	248.8	248.9	249.0	249.1	248.9
130°	261.7	261.9	262.1	262.2	262.4	262.5	262.6	262.7	262.8	262.8	262.7
132.5°	274.6	274.9	275.1	275.4	275.6	275.7	275.8	275.8	275.9	276.0	276.1
135°	294.8	295.1	295.4	295.7	296.0	296.2	296.2	296.2	296.2	296.2	296.1
137.5°	314.4	314.8	315.3	315.7	316.1	316.2	316.1	316.0	315.9	315.8	315.6
140°	327.1	327.5	327.9	328.3	328.7	328.8	328.7	328.5	328.4	328.2	328.0
142.5°	339.1	339.5	339.9	340.3	340.7	340.9	340.8	340.7	340.6	340.6	340.2
145°	357.3	357.5	357.7	358.0	358.2	358.3	358.3	358.3	358.3	358.3	358.1
147.5°	372.7	373.2	373.8	374.3	374.9	375.0	374.9	374.6	374.5	374.3	374.1
150°	384.2	384.4	384.5	384.7	384.8	384.9	384.9	384.9	384.9	384.9	384.6
152.5°	393.6	394.0	394.3	394.5	394.8	394.8	394.7	394.5	394.3	394.1	394.0
155°	407.2	407.6	408.0	408.4	408.8	408.8	408.4	408.1	407.8	407.5	407.4
157.5°	418.4	419.0	419.5	420.0	420.6	420.6	420.3	420.0	419.7	419.4	419.3
160°	426.2	426.6	427.0	427.4	427.8	427.9	427.5	427.2	426.9	426.5	426.4
162.5°	432.8	433.2	433.7	434.2	434.7	434.7	434.3	434.0	433.6	433.2	433.2
165°	441.6	442.1	442.6	443.1	443.5	443.6	443.3	443.0	442.7	442.4	442.3
167.5°	448.7	449.2	449.6	450.1	450.7	450.7	450.2	449.7	449.2	448.8	448.8
170°	452.4	453.0	453.5	454.1	454.6	454.7	454.2	453.7	453.2	452.7	452.7
172.5°	455.6	456.1	456.5	457.0	457.6	457.6	457.1	456.6	456.1	455.7	455.7
175°	458.5	459.1	459.6	460.2	460.7	460.8	460.3	459.8	459.3	458.8	458.8
177.5°	460.3	460.7	461.1	461.6	462.0	462.1	461.7	461.3	460.9	460.5	460.6
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	729.4	727.8	725.9	722.5	718.4	716.2	712.9	710.7	706.3	702.7	698.9
5°	766.4	758.7	751.5	742.1	731.9	725.2	717.4	708.7	699.7	690.3	680.1
7.5°	804.8	791.0	775.9	759.7	743.9	729.4	715.4	701.8	689.0	673.6	660.5
10°	830.6	813.1	794.5	772.5	751.1	732.5	713.5	697.0	680.1	662.0	646.1
12.5°	856.3	833.1	806.8	782.6	756.9	734.4	712.1	690.9	669.8	649.7	631.2
15°	874.5	854.1	829.7	795.4	766.4	735.5	706.0	678.6	653.0	630.7	607.3
17.5°	886.5	860.2	833.9	801.1	763.2	728.5	695.1	663.8	634.9	606.7	584.1
20°	888.7	861.6	834.2	802.0	763.2	723.4	690.1	652.4	621.4	592.2	564.5
22.5°	888.0	857.2	827.4	794.2	756.5	719.9	679.5	641.1	607.4	578.8	549.9
25°	881.1	848.3	811.0	777.6	740.3	701.5	660.5	620.8	586.5	553.7	525.1
27.5°	875.4	832.9	790.7	751.7	715.7	680.1	641.0	600.2	562.2	528.9	502.0
30°	868.5	821.8	774.3	733.6	696.6	662.0	625.0	585.3	545.6	513.1	484.2
32.5°	862.2	807.9	757.7	713.4	674.3	640.6	606.5	568.7	529.7	496.7	467.9
35°	850.2	787.3	729.8	679.8	637.9	603.4	574.8	539.6	503.7	471.8	444.2
37.5°	834.8	760.2	698.5	646.1	600.2	563.8	537.2	510.2	475.8	445.0	420.0
40°	822.8	740.9	675.6	622.0	574.5	536.5	511.9	486.3	457.7	429.1	402.7
42.5°	807.6	723.6	652.4	594.8	547.8	510.8	484.9	463.2	438.0	411.3	386.7
45°	779.7	692.1	615.1	553.1	505.6	469.1	442.4	426.1	407.2	381.9	361.2
47.5°	738.7	654.4	574.7	510.7	461.7	427.9	402.8	387.2	373.9	355.1	336.3
50°	702.3	626.2	545.6	482.1	433.0	399.0	375.9	361.7	350.3	335.8	319.9
52.5°	661.7	590.8	517.0	454.2	405.6	372.1	349.4	336.9	327.4	317.0	301.3
55°	597.1	536.9	468.3	408.7	363.8	331.1	311.2	300.3	292.5	284.7	275.0
57.5°	525.9	478.8	418.0	363.5	322.3	292.4	273.9	263.3	257.2	253.2	247.6
60°	475.8	435.5	383.1	333.4	293.1	266.6	248.6	240.4	235.4	232.0	227.8
62.5°	429.3	396.2	347.7	302.4	267.1	242.1	225.9	218.1	213.2	211.6	208.0
65°	360.8	335.3	295.2	257.6	227.5	206.1	192.6	185.1	182.0	180.2	180.5
67.5°	293.3	277.7	245.7	213.6	189.5	171.6	160.7	155.0	153.4	151.1	151.0
70°	252.2	240.4	213.3	185.4	164.0	150.2	140.5	134.5	133.0	131.8	131.5
72.5°	215.8	205.6	182.0	159.6	140.5	128.3	120.3	116.7	114.2	113.5	113.4
75°	162.2	156.5	137.8	120.1	106.9	98.4	93.0	89.7	87.9	87.5	87.9
77.5°	115.3	110.4	98.5	85.9	77.6	71.1	66.5	65.4	63.4	63.5	63.1
80°	86.7	83.3	75.8	65.9	59.0	53.6	51.2	49.0	48.5	47.5	48.5
82.5°	62.8	59.3	54.2	47.8	42.1	38.9	36.4	35.8	35.4	35.0	35.2
85°	31.0	31.3	28.3	23.4	21.1	19.3	17.7	17.7	17.4	17.2	17.4
87.5°	11.5	10.9	9.8	9.0	7.7	6.8	6.5	6.6	5.9	5.9	6.3
90°	4.6	4.0	3.5	2.9	2.3	1.7	1.0	0.4	1.0	1.7	2.3
92.5°	12.4	11.7	11.0	10.5	10.1	9.6	9.1	8.7	9.1	9.6	10.1
95°	26.1	25.3	24.5	24.0	23.8	23.7	23.5	23.4	23.5	23.7	23.8
97.5°	41.8	40.7	39.6	39.1	39.0	38.9	38.8	38.7	38.8	38.9	39.0
100°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3
102.5°	65.4	64.9	64.3	63.9	63.6	63.3	62.9	62.6	62.9	63.3	63.6
105°	84.8	84.4	83.9	83.5	83.0	82.6	82.2	81.8	82.2	82.6	83.0
107.5°	105.8	105.4	105.1	104.7	104.3	103.9	103.5	103.1	103.5	103.9	104.3
110°	120.2	119.9	119.7	119.4	119.0	118.6	118.2	117.8	118.2	118.6	119.0





TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	134.4	134.1	133.8	133.6	133.3	133.1	132.9	132.7	132.9	133.1	133.3
115°	156.6	156.5	156.3	156.1	155.7	155.4	155.0	154.7	155.0	155.4	155.7
117.5°	177.8	177.8	177.6	177.4	177.3	177.1	177.0	176.9	177.0	177.1	177.3
120°	192.7	192.6	192.5	192.3	191.9	191.5	191.1	190.7	191.1	191.5	191.9
122.5°	206.8	206.5	206.4	206.1	206.0	205.9	205.7	205.6	205.7	205.9	206.0
125°	228.2	228.1	228.1	227.8	227.3	226.8	226.3	225.9	226.3	226.8	227.3
127.5°	248.8	248.7	248.7	248.5	248.2	248.0	247.6	247.4	247.6	248.0	248.2
130°	262.5	262.4	262.2	261.9	261.5	261.1	260.7	260.3	260.7	261.1	261.5
132.5°	276.1	276.2	276.2	275.8	275.2	274.6	273.9	273.2	273.9	274.6	275.2
135°	296.0	296.0	295.9	295.6	295.2	294.7	294.2	293.7	294.2	294.7	295.2
137.5°	315.4	315.3	315.1	314.8	314.3	313.9	313.4	312.9	313.4	313.9	314.3
140°	327.7	327.5	327.3	326.9	326.5	326.1	325.7	325.3	325.7	326.1	326.5
142.5°	339.9	339.6	339.3	339.0	338.7	338.3	337.9	337.6	337.9	338.3	338.7
145°	357.8	357.6	357.4	357.1	356.8	356.5	356.2	355.8	356.2	356.5	356.8
147.5°	373.9	373.7	373.5	373.4	373.1	373.0	372.8	372.6	372.8	373.0	373.1
150°	384.3	384.0	383.7	383.5	383.6	383.7	383.7	383.8	383.7	383.7	383.6
152.5°	393.9	393.7	393.6	393.5	393.3	393.2	393.2	393.0	393.2	393.2	393.3
155°	407.3	407.3	407.2	407.2	407.2	407.2	407.2	407.2	407.2	407.2	407.2
157.5°	419.2	419.1	419.1	419.1	419.3	419.5	419.6	419.8	419.6	419.5	419.3
160°	426.4	426.3	426.2	426.3	426.5	426.7	427.1	427.3	427.1	426.7	426.5
162.5°	433.1	433.1	433.1	433.2	433.3	433.6	433.7	433.9	433.7	433.6	433.3
165°	442.2	442.1	442.0	442.0	442.2	442.4	442.5	442.7	442.5	442.4	442.2
167.5°	448.8	448.8	448.8	448.9	449.2	449.6	449.9	450.2	449.9	449.6	449.2
170°	452.7	452.7	452.7	452.9	453.2	453.5	453.8	454.2	453.8	453.5	453.2
172.5°	455.7	455.7	455.7	455.8	456.1	456.5	456.8	457.1	456.8	456.5	456.1
175°	458.8	458.8	458.8	459.0	459.3	459.6	459.9	460.3	459.9	459.6	459.3
177.5°	460.7	460.7	460.7	460.9	461.2	461.4	461.7	461.9	461.7	461.4	461.2
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	696.7	694.0	691.9	687.1	684.4	680.8	677.9	681.0	677.7	679.1	677.0
5°	675.0	666.5	660.5	651.8	644.3	637.4	632.2	631.4	628.9	627.7	624.2
7.5°	648.9	638.3	628.0	616.6	606.9	597.1	590.8	585.7	582.3	577.7	574.6
10°	633.4	619.3	607.3	593.4	581.4	570.8	562.4	558.3	554.3	548.6	546.5
12.5°	614.4	599.8	585.1	570.3	558.8	547.0	539.8	533.5	530.8	524.3	523.6
15°	591.6	569.7	555.2	540.2	524.2	514.6	508.6	501.7	498.7	494.2	490.8
17.5°	564.4	544.8	526.7	511.2	497.5	489.4	481.9	477.1	472.0	469.1	463.6
20°	544.7	526.0	507.9	491.4	480.9	471.6	465.6	461.1	455.6	454.1	448.7
22.5°	528.1	507.5	490.1	476.3	464.8	454.2	447.7	444.7	440.9	436.3	435.2
25°	501.1	479.7	464.9	451.1	440.8	431.3	426.7	422.8	419.2	415.9	414.7
27.5°	477.7	458.6	441.1	428.6	419.7	410.9	406.9	402.2	399.5	396.9	393.6
30°	461.4	441.8	426.4	414.4	404.7	397.0	392.7	389.4	387.0	384.6	382.8
32.5°	444.5	426.4	411.5	399.7	390.1	384.2	380.4	378.1	375.4	372.6	370.3
35°	422.2	402.3	387.9	377.6	370.1	365.6	361.4	359.3	356.3	356.3	353.9
37.5°	397.1	379.9	367.2	357.8	351.1	347.1	342.5	341.1	339.1	337.9	337.1
40°	382.1	366.2	354.2	344.8	337.6	334.3	330.7	328.3	327.1	325.6	325.0
42.5°	366.8	351.6	340.0	331.4	325.1	322.3	318.9	317.3	314.8	312.8	312.5
45°	343.3	328.6	318.1	311.2	305.8	302.5	300.3	296.8	295.5	293.1	292.8
47.5°	321.2	307.0	296.7	291.0	286.2	283.5	280.2	276.6	275.2	274.0	273.9
50°	304.5	291.6	281.9	276.6	272.0	268.2	264.8	262.4	261.5	261.5	262.1
52.5°	287.7	276.7	268.5	261.9	257.6	253.4	250.4	248.9	247.6	249.0	250.1
55°	263.0	251.9	245.9	239.6	235.4	230.5	229.0	228.4	227.5	229.9	231.1
57.5°	236.9	229.1	222.0	215.8	212.0	209.2	207.2	206.8	208.5	209.6	213.6
60°	220.3	211.3	204.9	200.1	195.6	193.8	193.2	192.6	193.8	197.1	202.2
62.5°	202.0	194.6	187.8	184.3	180.9	177.9	177.8	178.2	180.5	184.3	189.5
65°	175.2	168.8	164.3	160.1	157.4	155.6	156.2	157.4	160.1	165.2	171.0
67.5°	147.9	143.5	139.5	136.1	133.5	133.5	134.1	135.9	139.1	145.0	150.2
70°	130.3	125.5	122.2	120.6	118.6	117.4	119.1	122.2	124.8	130.3	134.8
72.5°	112.7	108.6	106.1	105.0	104.1	103.1	103.8	107.0	110.7	116.1	121.4
75°	86.7	85.2	83.3	82.1	81.3	81.8	82.5	85.5	88.5	94.2	100.2
77.5°	63.3	61.7	60.6	60.3	59.8	60.1	61.8	64.0	67.0	71.1	75.7
80°	47.8	47.2	46.7	46.3	46.3	46.7	49.0	50.5	53.2	57.2	60.8
82.5°	34.9	34.5	34.4	34.3	34.5	34.6	36.0	38.0	40.2	43.3	46.3
85°	18.4	17.7	18.7	18.9	18.4	19.3	19.9	21.1	21.9	23.4	25.0
87.5°	6.6	7.2	7.1	7.4	7.5	8.2	8.0	9.0	9.6	10.1	10.0
90°	2.9	3.5	4.0	4.6	5.1	5.8	6.2	6.6	7.0	7.4	7.7
92.5°	10.5	11.0	11.7	12.4	13.1	13.8	14.3	14.8	15.4	15.9	16.2
95°	24.0	24.5	25.3	26.1	26.9	27.6	28.2	28.8	29.3	29.9	30.3
97.5°	39.1	39.6	40.7	41.8	42.9	44.0	44.5	45.1	45.6	46.1	46.4
100°	50.3	50.8	51.8	52.8	53.9	54.9	55.7	56.4	57.1	57.8	58.2
102.5°	63.9	64.3	64.9	65.4	65.9	66.4	67.2	68.0	68.8	69.6	70.0
105°	83.5	83.9	84.4	84.8	85.3	85.8	86.3	86.7	87.2	87.7	88.1
107.5°	104.7	105.1	105.4	105.8	106.2	106.5	106.8	107.0	107.3	107.5	107.7
110°	119.4	119.7	119.9	120.2	120.4	120.6	120.9	121.1	121.4	121.6	121.7



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	133.6	133.8	134.1	134.4	134.7	135.0	135.1	135.2	135.3	135.5	135.5
115°	156.1	156.3	156.5	156.6	156.8	156.9	156.9	156.8	156.7	156.6	156.5
117.5°	177.4	177.6	177.8	177.8	178.0	178.2	178.2	178.3	178.3	178.4	178.3
120°	192.3	192.5	192.6	192.7	192.7	192.8	192.8	192.8	192.8	192.8	192.7
122.5°	206.1	206.4	206.5	206.8	207.0	207.2	207.1	207.1	207.0	206.9	206.8
125°	227.8	228.1	228.1	228.2	228.3	228.4	228.2	228.1	227.9	227.8	227.6
127.5°	248.5	248.7	248.7	248.8	248.9	249.1	249.0	248.9	248.8	248.7	248.6
130°	261.9	262.2	262.4	262.5	262.7	262.8	262.8	262.7	262.6	262.5	262.4
132.5°	275.8	276.2	276.2	276.1	276.1	276.0	275.9	275.8	275.8	275.7	275.6
135°	295.6	295.9	296.0	296.0	296.1	296.2	296.2	296.2	296.2	296.2	296.0
137.5°	314.8	315.1	315.3	315.4	315.6	315.8	315.9	316.0	316.1	316.2	316.1
140°	326.9	327.3	327.5	327.7	328.0	328.2	328.4	328.5	328.7	328.8	328.7
142.5°	339.0	339.3	339.6	339.9	340.2	340.6	340.6	340.7	340.8	340.9	340.7
145°	357.1	357.4	357.6	357.8	358.1	358.3	358.3	358.3	358.3	358.3	358.2
147.5°	373.4	373.5	373.7	373.9	374.1	374.3	374.5	374.6	374.9	375.0	374.9
150°	383.5	383.7	384.0	384.3	384.6	384.9	384.9	384.9	384.9	384.9	384.8
152.5°	393.5	393.6	393.7	393.9	394.0	394.1	394.3	394.5	394.7	394.8	394.8
155°	407.2	407.2	407.3	407.3	407.4	407.5	407.8	408.1	408.4	408.8	408.8
157.5°	419.1	419.1	419.1	419.2	419.3	419.4	419.7	420.0	420.3	420.6	420.6
160°	426.3	426.2	426.3	426.4	426.4	426.5	426.9	427.2	427.5	427.9	427.8
162.5°	433.2	433.1	433.1	433.1	433.2	433.2	433.6	434.0	434.3	434.7	434.7
165°	442.0	442.0	442.1	442.2	442.3	442.4	442.7	443.0	443.3	443.6	443.5
167.5°	448.9	448.8	448.8	448.8	448.8	448.8	449.2	449.7	450.2	450.7	450.7
170°	452.9	452.7	452.7	452.7	452.7	452.7	453.2	453.7	454.2	454.7	454.6
172.5°	455.8	455.7	455.7	455.7	455.7	455.7	456.1	456.6	457.1	457.6	457.6
175°	459.0	458.8	458.8	458.8	458.8	458.8	459.3	459.8	460.3	460.8	460.7
177.5°	460.9	460.7	460.7	460.7	460.6	460.5	460.9	461.3	461.7	462.1	462.0
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	675.5	677.2	675.8	677.7	675.8	677.2	675.5	677.0	679.1	677.7	681.0
5°	622.7	619.9	621.7	620.5	621.7	619.9	622.7	624.2	627.7	628.9	631.4
7.5°	573.8	571.2	568.2	566.8	568.2	571.2	573.8	574.6	577.7	582.3	585.7
10°	543.2	539.9	539.6	537.5	539.6	539.9	543.2	546.5	548.6	554.3	558.3
12.5°	520.8	517.7	514.3	513.4	514.3	517.7	520.8	523.6	524.3	530.8	533.5
15°	489.0	486.6	484.5	486.3	484.5	486.6	489.0	490.8	494.2	498.7	501.7
17.5°	462.6	460.6	460.3	458.0	460.3	460.6	462.6	463.6	469.1	472.0	477.1
20°	446.0	444.5	445.0	441.2	445.0	444.5	446.0	448.7	454.1	455.6	461.1
22.5°	432.8	429.8	429.4	428.6	429.4	429.8	432.8	435.2	436.3	440.9	444.7
25°	412.0	410.5	409.0	410.5	409.0	410.5	412.0	414.7	415.9	419.2	422.8
27.5°	393.9	392.1	391.7	391.8	391.7	392.1	393.9	393.6	396.9	399.5	402.2
30°	382.8	379.8	380.1	379.8	380.1	379.8	382.8	382.8	384.6	387.0	389.4
32.5°	370.7	368.7	368.3	367.7	368.3	368.7	370.7	370.3	372.6	375.4	378.1
35°	353.0	353.0	351.5	351.5	351.5	353.0	353.0	353.9	356.3	356.3	359.3
37.5°	336.3	336.0	335.1	335.3	335.1	336.0	336.3	337.1	337.9	339.1	341.1
40°	323.8	323.5	322.6	320.8	322.6	323.5	323.8	325.0	325.6	327.1	328.3
42.5°	311.8	310.8	310.3	309.7	310.3	310.8	311.8	312.5	312.8	314.8	317.3
45°	292.8	292.8	292.2	291.9	292.2	292.8	292.8	292.8	293.1	295.5	296.8
47.5°	274.4	275.0	276.1	275.9	276.1	275.0	274.4	273.9	274.0	275.2	276.6
50°	263.3	263.6	264.5	264.8	264.5	263.6	263.3	262.1	261.5	261.5	262.4
52.5°	251.0	252.8	253.9	253.7	253.9	252.8	251.0	250.1	249.0	247.6	248.9
55°	233.9	235.9	238.1	238.4	238.1	235.9	233.9	231.1	229.9	227.5	228.4
57.5°	216.8	219.8	222.0	222.7	222.0	219.8	216.8	213.6	209.6	208.5	206.8
60°	205.3	209.1	211.8	213.1	211.8	209.1	205.3	202.2	197.1	193.8	192.6
62.5°	194.2	198.5	201.3	201.5	201.3	198.5	194.2	189.5	184.3	180.5	178.2
65°	176.0	180.5	183.0	184.7	183.0	180.5	176.0	171.0	165.2	160.1	157.4
67.5°	156.5	161.1	163.7	165.2	163.7	161.1	156.5	150.2	145.0	139.1	135.9
70°	142.4	146.9	150.4	151.7	150.4	146.9	142.4	134.8	130.3	124.8	122.2
72.5°	128.4	132.4	135.3	136.7	135.3	132.4	128.4	121.4	116.1	110.7	107.0
75°	104.1	109.6	112.3	113.8	112.3	109.6	104.1	100.2	94.2	88.5	85.5
77.5°	80.3	85.2	86.8	87.6	86.8	85.2	80.3	75.7	71.1	67.0	64.0
80°	64.4	67.4	69.6	69.8	69.6	67.4	64.4	60.8	57.2	53.2	50.5
82.5°	49.5	52.0	52.7	53.5	52.7	52.0	49.5	46.3	43.3	40.2	38.0
85°	27.1	28.3	28.6	28.3	28.6	28.3	27.1	25.0	23.4	21.9	21.1
87.5°	10.5	10.3	10.4	10.9	10.4	10.3	10.5	10.0	10.1	9.6	9.0
90°	7.9	8.2	8.4	8.6	8.4	8.2	7.9	7.7	7.4	7.0	6.6
92.5°	16.4	16.6	16.8	17.0	16.8	16.6	16.4	16.2	15.9	15.4	14.8
95°	30.4	30.6	30.7	30.9	30.7	30.6	30.4	30.3	29.9	29.3	28.8
97.5°	46.5	46.7	46.7	46.8	46.7	46.7	46.5	46.4	46.1	45.6	45.1
100°	58.4	58.5	58.7	58.9	58.7	58.5	58.4	58.2	57.8	57.1	56.4
102.5°	70.3	70.5	70.7	71.0	70.7	70.5	70.3	70.0	69.6	68.8	68.0
105°	88.3	88.6	88.8	89.0	88.8	88.6	88.3	88.1	87.7	87.2	86.7
107.5°	107.7	107.6	107.6	107.6	107.6	107.6	107.7	107.7	107.5	107.3	107.0
110°	121.6	121.5	121.4	121.4	121.4	121.5	121.6	121.7	121.6	121.4	121.1



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	135.3	135.1	135.0	134.8	135.0	135.1	135.3	135.5	135.5	135.3	135.2
115°	156.5	156.4	156.3	156.2	156.3	156.4	156.5	156.5	156.6	156.7	156.8
117.5°	178.0	177.7	177.3	177.0	177.3	177.7	178.0	178.3	178.4	178.3	178.3
120°	192.3	192.0	191.7	191.4	191.7	192.0	192.3	192.7	192.8	192.8	192.8
122.5°	206.5	206.3	206.0	205.7	206.0	206.3	206.5	206.8	206.9	207.0	207.1
125°	227.5	227.4	227.4	227.3	227.4	227.4	227.5	227.6	227.8	227.9	228.1
127.5°	248.4	248.3	248.1	248.0	248.1	248.3	248.4	248.6	248.7	248.8	248.9
130°	262.2	262.1	261.9	261.7	261.9	262.1	262.2	262.4	262.5	262.6	262.7
132.5°	275.4	275.1	274.9	274.6	274.9	275.1	275.4	275.6	275.7	275.8	275.8
135°	295.7	295.4	295.1	294.8	295.1	295.4	295.7	296.0	296.2	296.2	296.2
137.5°	315.7	315.3	314.8	314.4	314.8	315.3	315.7	316.1	316.2	316.1	316.0
140°	328.3	327.9	327.5	327.1	327.5	327.9	328.3	328.7	328.8	328.7	328.5
142.5°	340.3	339.9	339.5	339.1	339.5	339.9	340.3	340.7	340.9	340.8	340.7
145°	358.0	357.7	357.5	357.3	357.5	357.7	358.0	358.2	358.3	358.3	358.3
147.5°	374.3	373.8	373.2	372.7	373.2	373.8	374.3	374.9	375.0	374.9	374.6
150°	384.7	384.5	384.4	384.2	384.4	384.5	384.7	384.8	384.9	384.9	384.9
152.5°	394.5	394.3	394.0	393.6	394.0	394.3	394.5	394.8	394.8	394.7	394.5
155°	408.4	408.0	407.6	407.2	407.6	408.0	408.4	408.8	408.8	408.4	408.1
157.5°	420.0	419.5	419.0	418.4	419.0	419.5	420.0	420.6	420.6	420.3	420.0
160°	427.4	427.0	426.6	426.2	426.6	427.0	427.4	427.8	427.9	427.5	427.2
162.5°	434.2	433.7	433.2	432.8	433.2	433.7	434.2	434.7	434.7	434.3	434.0
165°	443.1	442.6	442.1	441.6	442.1	442.6	443.1	443.5	443.6	443.3	443.0
167.5°	450.1	449.6	449.2	448.7	449.2	449.6	450.1	450.7	450.7	450.2	449.7
170°	454.1	453.5	453.0	452.4	453.0	453.5	454.1	454.6	454.7	454.2	453.7
172.5°	457.0	456.5	456.1	455.6	456.1	456.5	457.0	457.6	457.6	457.1	456.6
175°	460.2	459.6	459.1	458.5	459.1	459.6	460.2	460.7	460.8	460.3	459.8
177.5°	461.6	461.1	460.7	460.3	460.7	461.1	461.6	462.0	462.1	461.7	461.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	677.9	680.8	684.4	687.1	691.9	694.0	696.7	698.9	702.7	706.3	710.7
5°	632.2	637.4	644.3	651.8	660.5	666.5	675.0	680.1	690.3	699.7	708.7
7.5°	590.8	597.1	606.9	616.6	628.0	638.3	648.9	660.5	673.6	689.0	701.8
10°	562.4	570.8	581.4	593.4	607.3	619.3	633.4	646.1	662.0	680.1	697.0
12.5°	539.8	547.0	558.8	570.3	585.1	599.8	614.4	631.2	649.7	669.8	690.9
15°	508.6	514.6	524.2	540.2	555.2	569.7	591.6	607.3	630.7	653.0	678.6
17.5°	481.9	489.4	497.5	511.2	526.7	544.8	564.4	584.1	606.7	634.9	663.8
20°	465.6	471.6	480.9	491.4	507.9	526.0	544.7	564.5	592.2	621.4	652.4
22.5°	447.7	454.2	464.8	476.3	490.1	507.5	528.1	549.9	578.8	607.4	641.1
25°	426.7	431.3	440.8	451.1	464.9	479.7	501.1	525.1	553.7	586.5	620.8
27.5°	406.9	410.9	419.7	428.6	441.1	458.6	477.7	502.0	528.9	562.2	600.2
30°	392.7	397.0	404.7	414.4	426.4	441.8	461.4	484.2	513.1	545.6	585.3
32.5°	380.4	384.2	390.1	399.7	411.5	426.4	444.5	467.9	496.7	529.7	568.7
35°	361.4	365.6	370.1	377.6	387.9	402.3	422.2	444.2	471.8	503.7	539.6
37.5°	342.5	347.1	351.1	357.8	367.2	379.9	397.1	420.0	445.0	475.8	510.2
40°	330.7	334.3	337.6	344.8	354.2	366.2	382.1	402.7	429.1	457.7	486.3
42.5°	318.9	322.3	325.1	331.4	340.0	351.6	366.8	386.7	411.3	438.0	463.2
45°	300.3	302.5	305.8	311.2	318.1	328.6	343.3	361.2	381.9	407.2	426.1
47.5°	280.2	283.5	286.2	291.0	296.7	307.0	321.2	336.3	355.1	373.9	387.2
50°	264.8	268.2	272.0	276.6	281.9	291.6	304.5	319.9	335.8	350.3	361.7
52.5°	250.4	253.4	257.6	261.9	268.5	276.7	287.7	301.3	317.0	327.4	336.9
55°	229.0	230.5	235.4	239.6	245.9	251.9	263.0	275.0	284.7	292.5	300.3
57.5°	207.2	209.2	212.0	215.8	222.0	229.1	236.9	247.6	253.2	257.2	263.3
60°	193.2	193.8	195.6	200.1	204.9	211.3	220.3	227.8	232.0	235.4	240.4
62.5°	177.8	177.9	180.9	184.3	187.8	194.6	202.0	208.0	211.6	213.2	218.1
65°	156.2	155.6	157.4	160.1	164.3	168.8	175.2	180.5	180.2	182.0	185.1
67.5°	134.1	133.5	133.5	136.1	139.5	143.5	147.9	151.0	151.1	153.4	155.0
70°	119.1	117.4	118.6	120.6	122.2	125.5	130.3	131.5	131.8	133.0	134.5
72.5°	103.8	103.1	104.1	105.0	106.1	108.6	112.7	113.4	113.5	114.2	116.7
75°	82.5	81.8	81.3	82.1	83.3	85.2	86.7	87.9	87.5	87.9	89.7
77.5°	61.8	60.1	59.8	60.3	60.6	61.7	63.3	63.1	63.5	63.4	65.4
80°	49.0	46.7	46.3	46.3	46.7	47.2	47.8	48.5	47.5	48.5	49.0
82.5°	36.0	34.6	34.5	34.3	34.4	34.5	34.9	35.2	35.0	35.4	35.8
85°	19.9	19.3	18.4	18.9	18.7	17.7	18.4	17.4	17.2	17.4	17.7
87.5°	8.0	8.2	7.5	7.4	7.1	7.2	6.6	6.3	5.9	5.9	6.6
90°	6.2	5.8	5.1	4.6	4.0	3.5	2.9	2.3	1.7	1.0	0.4
92.5°	14.3	13.8	13.1	12.4	11.7	11.0	10.5	10.1	9.6	9.1	8.7
95°	28.2	27.6	26.9	26.1	25.3	24.5	24.0	23.8	23.7	23.5	23.4
97.5°	44.5	44.0	42.9	41.8	40.7	39.6	39.1	39.0	38.9	38.8	38.7
100°	55.7	54.9	53.9	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
102.5°	67.2	66.4	65.9	65.4	64.9	64.3	63.9	63.6	63.3	62.9	62.6
105°	86.3	85.8	85.3	84.8	84.4	83.9	83.5	83.0	82.6	82.2	81.8
107.5°	106.8	106.5	106.2	105.8	105.4	105.1	104.7	104.3	103.9	103.5	103.1
110°	120.9	120.6	120.4	120.2	119.9	119.7	119.4	119.0	118.6	118.2	117.8



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	135.1	135.0	134.7	134.4	134.1	133.8	133.6	133.3	133.1	132.9	132.7
115°	156.9	156.9	156.8	156.6	156.5	156.3	156.1	155.7	155.4	155.0	154.7
117.5°	178.2	178.2	178.0	177.8	177.8	177.6	177.4	177.3	177.1	177.0	176.9
120°	192.8	192.8	192.7	192.7	192.6	192.5	192.3	191.9	191.5	191.1	190.7
122.5°	207.1	207.2	207.0	206.8	206.5	206.4	206.1	206.0	205.9	205.7	205.6
125°	228.2	228.4	228.3	228.2	228.1	228.1	227.8	227.3	226.8	226.3	225.9
127.5°	249.0	249.1	248.9	248.8	248.7	248.7	248.5	248.2	248.0	247.6	247.4
130°	262.8	262.8	262.7	262.5	262.4	262.2	261.9	261.5	261.1	260.7	260.3
132.5°	275.9	276.0	276.1	276.1	276.2	276.2	275.8	275.2	274.6	273.9	273.2
135°	296.2	296.2	296.1	296.0	296.0	295.9	295.6	295.2	294.7	294.2	293.7
137.5°	315.9	315.8	315.6	315.4	315.3	315.1	314.8	314.3	313.9	313.4	312.9
140°	328.4	328.2	328.0	327.7	327.5	327.3	326.9	326.5	326.1	325.7	325.3
142.5°	340.6	340.6	340.2	339.9	339.6	339.3	339.0	338.7	338.3	337.9	337.6
145°	358.3	358.3	358.1	357.8	357.6	357.4	357.1	356.8	356.5	356.2	355.8
147.5°	374.5	374.3	374.1	373.9	373.7	373.5	373.4	373.1	373.0	372.8	372.6
150°	384.9	384.9	384.6	384.3	384.0	383.7	383.5	383.6	383.7	383.7	383.8
152.5°	394.3	394.1	394.0	393.9	393.7	393.6	393.5	393.3	393.2	393.2	393.0
155°	407.8	407.5	407.4	407.3	407.3	407.2	407.2	407.2	407.2	407.2	407.2
157.5°	419.7	419.4	419.3	419.2	419.1	419.1	419.1	419.3	419.5	419.6	419.8
160°	426.9	426.5	426.4	426.4	426.3	426.2	426.3	426.5	426.7	427.1	427.3
162.5°	433.6	433.2	433.2	433.1	433.1	433.1	433.2	433.3	433.6	433.7	433.9
165°	442.7	442.4	442.3	442.2	442.1	442.0	442.0	442.2	442.4	442.5	442.7
167.5°	449.2	448.8	448.8	448.8	448.8	448.8	448.9	449.2	449.6	449.9	450.2
170°	453.2	452.7	452.7	452.7	452.7	452.7	452.9	453.2	453.5	453.8	454.2
172.5°	456.1	455.7	455.7	455.7	455.7	455.7	455.8	456.1	456.5	456.8	457.1
175°	459.3	458.8	458.8	458.8	458.8	458.8	459.0	459.3	459.6	459.9	460.3
177.5°	460.9	460.5	460.6	460.7	460.7	460.7	460.9	461.2	461.4	461.7	461.9
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	712.9	716.2	718.4	722.5	725.9	727.8	729.4	730.9	732.6	734.0	738.2
5°	717.4	725.2	731.9	742.1	751.5	758.7	766.4	773.4	779.1	787.3	793.5
7.5°	715.4	729.4	743.9	759.7	775.9	791.0	804.8	817.8	829.5	843.7	856.1
10°	713.5	732.5	751.1	772.5	794.5	813.1	830.6	848.3	861.3	879.3	894.7
12.5°	712.1	734.4	756.9	782.6	806.8	833.1	856.3	869.3	889.0	903.4	921.6
15°	706.0	735.5	766.4	795.4	829.7	854.1	874.5	899.8	918.1	936.5	956.3
17.5°	695.1	728.5	763.2	801.1	833.9	860.2	886.5	910.9	932.8	957.4	982.1
20°	690.1	723.4	763.2	802.0	834.2	861.6	888.7	915.4	939.5	971.1	999.7
22.5°	679.5	719.9	756.5	794.2	827.4	857.2	888.0	918.3	950.3	986.0	1021.8
25°	660.5	701.5	740.3	777.6	811.0	848.3	881.1	921.8	962.7	1010.0	1054.5
27.5°	641.0	680.1	715.7	751.7	790.7	832.9	875.4	921.5	975.2	1034.7	1097.6
30°	625.0	662.0	696.6	733.6	774.3	821.8	868.5	923.3	985.2	1052.3	1127.0
32.5°	606.5	640.6	674.3	713.4	757.7	807.9	862.2	922.3	996.8	1073.1	1149.9
35°	574.8	603.4	637.9	679.8	729.8	787.3	850.2	921.1	1006.6	1094.2	1158.9
37.5°	537.2	563.8	600.2	646.1	698.5	760.2	834.8	919.0	1009.8	1079.6	1100.5
40°	511.9	536.5	574.5	622.0	675.6	740.9	822.8	911.8	999.7	1044.3	1027.1
42.5°	484.9	510.8	547.8	594.8	652.4	723.6	807.6	896.7	970.3	987.1	927.9
45°	442.4	469.1	505.6	553.1	615.1	692.1	779.7	860.6	903.1	872.7	780.9
47.5°	402.8	427.9	461.7	510.7	574.7	654.4	738.7	803.3	806.7	734.1	636.1
50°	375.9	399.0	433.0	482.1	545.6	626.2	702.3	753.2	730.4	648.2	554.1
52.5°	349.4	372.1	405.6	454.2	517.0	590.8	661.7	697.4	654.3	570.0	489.5
55°	311.2	331.1	363.8	408.7	468.3	536.9	597.1	609.3	553.4	470.3	405.0
57.5°	273.9	292.4	322.3	363.5	418.0	478.8	525.9	523.2	464.1	392.8	341.0
60°	248.6	266.6	293.1	333.4	383.1	435.5	475.8	466.1	407.5	346.1	302.5
62.5°	225.9	242.1	267.1	302.4	347.7	396.2	429.3	415.1	357.6	304.0	269.4
65°	192.6	206.1	227.5	257.6	295.2	335.3	360.8	342.5	293.4	251.6	223.9
67.5°	160.7	171.6	189.5	213.6	245.7	277.7	293.3	274.9	235.6	205.1	184.6
70°	140.5	150.2	164.0	185.4	213.3	240.4	252.2	235.6	201.9	175.7	161.0
72.5°	120.3	128.3	140.5	159.6	182.0	205.6	215.8	200.0	172.3	150.2	136.4
75°	93.0	98.4	106.9	120.1	137.8	156.5	162.2	148.4	130.6	114.1	105.0
77.5°	66.5	71.1	77.6	85.9	98.5	110.4	115.3	107.3	93.6	83.1	75.7
80°	51.2	53.6	59.0	65.9	75.8	83.3	86.7	81.5	71.9	64.1	58.4
82.5°	36.4	38.9	42.1	47.8	54.2	59.3	62.8	59.4	52.4	46.3	42.9
85°	17.7	19.3	21.1	23.4	28.3	31.3	31.0	28.9	26.1	23.8	21.9
87.5°	6.5	6.8	7.7	9.0	9.8	10.9	11.5	11.2	10.3	9.7	9.0
90°	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.8	6.2	6.6
92.5°	9.1	9.6	10.1	10.5	11.0	11.7	12.4	13.1	13.8	14.3	14.8
95°	23.5	23.7	23.8	24.0	24.5	25.3	26.1	26.9	27.6	28.2	28.8
97.5°	38.8	38.9	39.0	39.1	39.6	40.7	41.8	42.9	44.0	44.5	45.1
100°	50.3	50.3	50.3	50.3	50.8	51.8	52.8	53.9	54.9	55.7	56.4
102.5°	62.9	63.3	63.6	63.9	64.3	64.9	65.4	65.9	66.4	67.2	68.0
105°	82.2	82.6	83.0	83.5	83.9	84.4	84.8	85.3	85.8	86.3	86.7
107.5°	103.5	103.9	104.3	104.7	105.1	105.4	105.8	106.2	106.5	106.8	107.0
110°	118.2	118.6	119.0	119.4	119.7	119.9	120.2	120.4	120.6	120.9	121.1





TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	132.9	133.1	133.3	133.6	133.8	134.1	134.4	134.7	135.0	135.1	135.2
115°	155.0	155.4	155.7	156.1	156.3	156.5	156.6	156.8	156.9	156.9	156.8
117.5°	177.0	177.1	177.3	177.4	177.6	177.8	177.8	178.0	178.2	178.2	178.3
120°	191.1	191.5	191.9	192.3	192.5	192.6	192.7	192.7	192.8	192.8	192.8
122.5°	205.7	205.9	206.0	206.1	206.4	206.5	206.8	207.0	207.2	207.1	207.1
125°	226.3	226.8	227.3	227.8	228.1	228.1	228.2	228.3	228.4	228.2	228.1
127.5°	247.6	248.0	248.2	248.5	248.7	248.7	248.8	248.9	249.1	249.0	248.9
130°	260.7	261.1	261.5	261.9	262.2	262.4	262.5	262.7	262.8	262.8	262.7
132.5°	273.9	274.6	275.2	275.8	276.2	276.2	276.1	276.1	276.0	275.9	275.8
135°	294.2	294.7	295.2	295.6	295.9	296.0	296.0	296.1	296.2	296.2	296.2
137.5°	313.4	313.9	314.3	314.8	315.1	315.3	315.4	315.6	315.8	315.9	316.0
140°	325.7	326.1	326.5	326.9	327.3	327.5	327.7	328.0	328.2	328.4	328.5
142.5°	337.9	338.3	338.7	339.0	339.3	339.6	339.9	340.2	340.6	340.6	340.7
145°	356.2	356.5	356.8	357.1	357.4	357.6	357.8	358.1	358.3	358.3	358.3
147.5°	372.8	373.0	373.1	373.4	373.5	373.7	373.9	374.1	374.3	374.5	374.6
150°	383.7	383.7	383.6	383.5	383.7	384.0	384.3	384.6	384.9	384.9	384.9
152.5°	393.2	393.2	393.3	393.5	393.6	393.7	393.9	394.0	394.1	394.3	394.5
155°	407.2	407.2	407.2	407.2	407.2	407.3	407.3	407.4	407.5	407.8	408.1
157.5°	419.6	419.5	419.3	419.1	419.1	419.1	419.2	419.3	419.4	419.7	420.0
160°	427.1	426.7	426.5	426.3	426.2	426.3	426.4	426.4	426.5	426.9	427.2
162.5°	433.7	433.6	433.3	433.2	433.1	433.1	433.1	433.2	433.2	433.6	434.0
165°	442.5	442.4	442.2	442.0	442.0	442.1	442.2	442.3	442.4	442.7	443.0
167.5°	449.9	449.6	449.2	448.9	448.8	448.8	448.8	448.8	448.8	449.2	449.7
170°	453.8	453.5	453.2	452.9	452.7	452.7	452.7	452.7	452.7	453.2	453.7
172.5°	456.8	456.5	456.1	455.8	455.7	455.7	455.7	455.7	455.7	456.1	456.6
175°	459.9	459.6	459.3	459.0	458.8	458.8	458.8	458.8	458.8	459.3	459.8
177.5°	461.7	461.4	461.2	460.9	460.7	460.7	460.7	460.6	460.5	460.9	461.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	741.5	743.4	747.5	746.1	748.0	748.9	750.0
5°	801.4	811.0	815.2	814.6	820.9	819.4	817.9
7.5°	869.0	879.2	884.8	891.8	896.0	896.2	899.8
10°	907.3	920.5	926.0	933.5	938.3	941.0	940.7
12.5°	936.7	947.1	959.2	962.9	969.4	972.8	971.5
15°	972.0	988.6	1001.2	1007.5	1015.7	1018.0	1021.4
17.5°	1003.5	1025.7	1040.5	1060.1	1067.5	1072.1	1069.4
20°	1027.4	1056.5	1071.3	1094.8	1107.7	1114.7	1112.2
22.5°	1055.6	1087.1	1114.4	1134.7	1154.4	1163.8	1165.7
25°	1103.8	1147.2	1187.2	1213.9	1238.3	1244.0	1256.7
27.5°	1157.8	1208.9	1251.6	1279.8	1296.8	1303.1	1307.1
30°	1191.7	1242.5	1274.8	1292.8	1298.2	1297.6	1297.0
32.5°	1208.3	1240.2	1246.3	1241.3	1228.9	1218.4	1207.4
35°	1184.8	1161.0	1125.5	1079.7	1046.1	1012.0	1008.7
37.5°	1065.6	989.5	930.4	864.4	826.3	802.8	786.5
40°	953.3	867.0	795.4	739.7	700.8	685.6	670.5
42.5°	831.6	749.0	685.6	639.1	609.9	592.9	580.9
45°	675.6	602.8	553.1	519.4	496.2	483.0	475.5
47.5°	553.6	499.7	457.6	433.2	417.2	406.9	406.9
50°	488.1	436.7	408.7	389.4	375.6	367.4	368.9
52.5°	430.1	391.7	367.7	351.6	341.4	336.4	336.2
55°	359.7	331.9	316.3	304.5	297.6	291.9	293.1
57.5°	307.6	284.2	273.8	264.0	259.2	256.9	253.7
60°	275.4	257.3	248.3	240.4	235.6	233.9	230.5
62.5°	246.7	232.5	223.7	217.3	213.0	212.4	209.8
65°	207.3	196.5	188.7	185.7	181.2	180.0	180.0
67.5°	171.0	163.2	157.1	154.3	152.3	152.7	151.1
70°	148.1	141.7	137.8	134.8	133.3	133.6	132.4
72.5°	129.5	122.5	119.1	117.2	115.3	116.1	115.6
75°	98.1	94.5	92.7	90.9	89.7	89.0	88.5
77.5°	72.0	68.8	67.5	66.5	66.6	65.2	66.3
80°	55.7	53.0	52.0	50.5	50.2	50.2	50.0
82.5°	40.7	39.2	38.6	37.3	36.8	37.2	36.4
85°	21.1	19.9	19.6	19.6	18.9	18.4	19.9
87.5°	9.1	8.2	8.2	8.1	8.2	7.9	7.5
90°	7.0	7.4	7.7	7.9	8.2	8.4	8.6
92.5°	15.4	15.9	16.2	16.4	16.6	16.8	17.0
95°	29.3	29.9	30.3	30.4	30.6	30.7	30.9
97.5°	45.6	46.1	46.4	46.5	46.7	46.7	46.8
100°	57.1	57.8	58.2	58.4	58.5	58.7	58.9
102.5°	68.8	69.6	70.0	70.3	70.5	70.7	71.0
105°	87.2	87.7	88.1	88.3	88.6	88.8	89.0
107.5°	107.3	107.5	107.7	107.7	107.6	107.6	107.6
110°	121.4	121.6	121.7	121.6	121.5	121.4	121.4



TEST NUMBER: P333371-927

CATALOG NUMBER: S125DIW-S610D470U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	135.3	135.5	135.5	135.3	135.1	135.0	134.8
115°	156.7	156.6	156.5	156.5	156.4	156.3	156.2
117.5°	178.3	178.4	178.3	178.0	177.7	177.3	177.0
120°	192.8	192.8	192.7	192.3	192.0	191.7	191.4
122.5°	207.0	206.9	206.8	206.5	206.3	206.0	205.7
125°	227.9	227.8	227.6	227.5	227.4	227.4	227.3
127.5°	248.8	248.7	248.6	248.4	248.3	248.1	248.0
130°	262.6	262.5	262.4	262.2	262.1	261.9	261.7
132.5°	275.8	275.7	275.6	275.4	275.1	274.9	274.6
135°	296.2	296.2	296.0	295.7	295.4	295.1	294.8
137.5°	316.1	316.2	316.1	315.7	315.3	314.8	314.4
140°	328.7	328.8	328.7	328.3	327.9	327.5	327.1
142.5°	340.8	340.9	340.7	340.3	339.9	339.5	339.1
145°	358.3	358.3	358.2	358.0	357.7	357.5	357.3
147.5°	374.9	375.0	374.9	374.3	373.8	373.2	372.7
150°	384.9	384.9	384.8	384.7	384.5	384.4	384.2
152.5°	394.7	394.8	394.8	394.5	394.3	394.0	393.6
155°	408.4	408.8	408.8	408.4	408.0	407.6	407.2
157.5°	420.3	420.6	420.6	420.0	419.5	419.0	418.4
160°	427.5	427.9	427.8	427.4	427.0	426.6	426.2
162.5°	434.3	434.7	434.7	434.2	433.7	433.2	432.8
165°	443.3	443.6	443.5	443.1	442.6	442.1	441.6
167.5°	450.2	450.7	450.7	450.1	449.6	449.2	448.7
170°	454.2	454.7	454.6	454.1	453.5	453.0	452.4
172.5°	457.1	457.6	457.6	457.0	456.5	456.1	455.6
175°	460.3	460.8	460.7	460.2	459.6	459.1	458.5
177.5°	461.7	462.1	462.0	461.6	461.1	460.7	460.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)