

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333717-927

Luminaire Tested: **S125RDIW-S1090D1560U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333717-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7661.9 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		65	65	65		51	51	51	44
1	97	93	89	86	89	85	82	79	71	68	66		58	56	55		45	44	44	38
2	88	81	75	71	81	75	70	65	62	59	56		51	48	46		40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47		45	42	39		36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40		40	37	34		32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35		36	33	30		29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30		33	29	26		27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27		30	26	23		24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24		27	23	21		22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21		25	21	18		21	18	16	13
10	47	35	28	23	43	32	26	22	28	23	19		23	19	17		19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8412	8412	8412	8412
5°	9678	8423	7439	8423
10°	11101	8380	6564	8380
15°	11990	8294	5834	8294
20°	13221	8194	5388	8194
25°	15302	8062	4999	8062
30°	16651	7923	4745	7923
35°	14046	7761	4511	7761
40°	9809	7470	4309	7470
45°	7277	7077	4112	7077
50°	5801	6666	3943	6666
55°	4925	6159	3792	6159
60°	4255	5704	3550	5704
65°	3791	5213	3055	5213
70°	3331	4775	2787	4775
75°	2882	4135	2615	4135
80°	2187	3481	2187	3481
85°	1823	2734	2060	2734



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.9	1.6
10°-20°	366.0	4.8
20°-30°	580.4	7.6
30°-40°	699.9	9.1
40°-50°	625.0	8.2
50°-60°	479.3	6.3
60°-70°	311.5	4.1
70°-80°	151.4	2.0
80°-90°	39.5	0.5
90°-100°	102.8	1.3
100°-110°	303.6	4.0
110°-120°	514.3	6.7
120°-130°	676.9	8.8
130°-140°	758.4	9.9
140°-150°	743.3	9.7
150°-160°	624.3	8.1
160°-170°	415.0	5.4
170°-180°	145.2	1.9
0°-30°	1071.3	14.0
0°-40°	1771.2	23.1
0°-60°	2875.5	37.5
0°-90°	3377.9	44.1
90°-120°	920.8	12.0
90°-150°	3099.4	40.5
90°-180°	4284.0	55.9
0°-180°	7661.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1302	1302	1302	1302	1302	
5°	1493	1299	1147	1299	1493	149
15°	1793	1240	873	1240	1793	514
25°	2147	1131	702	1131	2147	986
35°	1782	984	572	984	1782	1076
45°	797	775	450	775	797	636
55°	437	547	337	547	437	397
65°	248	341	200	341	248	247
75°	116	166	105	166	116	123
85°	25	37	28	37	25	29
90°	29	1	29	1	29	18
95°	103	78	103	78	103	105
105°	296	272	296	272	296	314
115°	520	515	520	515	520	514
125°	756	752	756	752	756	675
135°	981	977	981	977	981	757
145°	1189	1184	1189	1184	1189	742
155°	1355	1355	1355	1355	1355	623
165°	1470	1473	1470	1473	1470	414
175°	1526	1532	1526	1532	1526	145
180°	1535	1535	1535	1535	1535	



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1370.1	1369.2	1371.0	1366.2	1366.7	1359.4	1359.4	1353.8	1346.6	1341.0	1338.4
5°	1492.8	1493.9	1491.8	1483.8	1478.4	1470.4	1461.3	1445.3	1431.9	1419.0	1408.9
7.5°	1619.2	1619.9	1612.9	1610.4	1597.0	1587.1	1566.9	1545.1	1525.7	1501.2	1482.3
10°	1692.8	1692.3	1684.7	1678.9	1667.1	1652.2	1632.4	1606.7	1582.6	1555.9	1530.3
12.5°	1735.6	1734.2	1731.8	1724.7	1713.7	1700.5	1683.7	1658.4	1628.8	1599.6	1569.6
15°	1793.3	1789.5	1782.6	1773.5	1758.0	1742.5	1723.8	1701.4	1673.0	1639.8	1612.1
17.5°	1864.7	1864.9	1854.2	1841.5	1820.4	1793.1	1764.2	1728.0	1689.5	1653.0	1623.4
20°	1923.7	1922.2	1911.5	1886.9	1862.8	1828.6	1795.5	1751.0	1704.0	1656.5	1619.5
22.5°	2008.5	2004.3	1993.1	1960.9	1923.6	1879.5	1828.8	1774.6	1717.7	1663.7	1615.3
25°	2147.3	2144.0	2122.1	2084.7	2032.3	1964.4	1898.1	1823.8	1742.0	1670.9	1612.1
27.5°	2242.2	2238.7	2222.5	2191.3	2143.0	2071.6	1981.8	1882.5	1780.4	1682.5	1597.8
30°	2232.8	2240.8	2238.7	2224.3	2187.9	2123.8	2040.9	1929.1	1807.8	1692.8	1591.7
32.5°	2098.5	2105.7	2124.5	2152.8	2155.0	2129.3	2067.4	1964.2	1838.6	1707.8	1587.1
35°	1781.5	1791.2	1827.6	1884.8	1959.6	2022.1	2035.0	1979.3	1866.5	1725.9	1580.0
37.5°	1369.6	1422.2	1452.9	1513.1	1626.2	1741.2	1851.9	1892.7	1844.6	1718.5	1568.5
40°	1163.5	1176.3	1230.8	1298.7	1393.9	1513.7	1671.4	1785.3	1789.1	1701.4	1550.5
42.5°	995.8	1012.0	1049.5	1103.7	1185.2	1305.0	1467.8	1618.0	1687.7	1654.3	1527.0
45°	796.7	809.0	836.2	878.0	940.5	1039.4	1179.5	1353.3	1491.2	1545.2	1464.0
47.5°	654.4	661.1	684.8	716.6	762.9	835.0	943.4	1094.2	1259.7	1375.7	1364.3
50°	577.4	584.9	603.1	627.2	666.2	727.1	813.8	939.4	1110.0	1251.6	1280.0
52.5°	517.5	523.8	535.1	557.9	590.1	636.9	706.9	820.5	974.0	1124.7	1190.2
55°	437.4	441.6	450.8	463.6	489.3	522.9	583.4	661.9	786.0	937.8	1034.0
57.5°	371.3	373.4	379.2	391.1	408.8	433.4	477.1	543.7	632.6	769.4	875.6
60°	329.4	331.5	339.0	347.0	360.9	383.3	417.6	464.1	549.6	662.5	769.9
62.5°	296.0	297.3	300.5	308.5	320.7	338.0	365.0	402.9	471.0	570.1	671.5
65°	248.1	248.6	249.7	256.1	263.6	276.4	294.1	320.8	372.2	447.0	536.8
67.5°	202.1	202.9	206.6	208.8	216.7	223.4	233.8	254.2	290.3	340.8	410.7
70°	176.4	175.9	179.7	182.4	185.0	193.1	199.9	216.6	239.0	277.5	335.8
72.5°	152.5	151.1	152.7	153.7	157.2	162.6	169.6	179.7	197.1	223.6	268.2
75°	115.5	116.1	116.1	117.1	119.8	121.9	124.1	129.4	139.0	156.7	180.7
77.5°	81.0	80.2	82.5	82.8	84.4	86.7	88.6	90.7	94.7	101.9	114.3
80°	58.8	58.8	59.3	60.9	60.4	61.5	64.2	66.3	71.1	75.4	79.7
82.5°	45.2	44.7	45.2	45.6	45.5	46.5	47.5	47.9	49.7	51.9	54.8
85°	24.6	24.6	25.1	25.1	25.7	25.7	26.2	26.2	26.2	26.7	27.3
87.5°	15.1	14.6	13.9	13.8	14.1	14.7	14.0	13.3	13.1	12.8	12.8
90°	28.7	27.9	27.1	26.3	25.5	24.4	23.1	21.8	20.4	19.1	17.3
92.5°	56.4	55.8	55.2	54.7	54.0	52.9	51.1	49.4	47.6	45.9	43.6
95°	102.7	102.2	101.7	101.2	100.6	99.4	97.6	95.7	93.9	92.0	89.4
97.5°	155.8	155.5	155.2	154.9	154.6	153.4	151.7	150.0	148.2	146.5	142.8
100°	195.9	195.4	194.9	194.3	193.8	192.3	190.0	187.6	185.2	182.8	179.4
102.5°	236.1	235.4	234.6	233.9	233.1	231.4	228.9	226.2	223.6	221.0	219.3
105°	296.3	295.5	294.7	293.9	293.1	291.9	290.3	288.8	287.2	285.6	283.9
107.5°	357.9	358.0	358.1	358.1	358.1	357.7	357.0	356.2	355.4	354.6	353.4
110°	403.9	404.1	404.3	404.6	404.9	404.6	403.9	403.1	402.2	401.4	400.6



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	448.8	449.2	449.7	450.2	450.7	450.7	450.4	450.0	449.6	449.2	448.2
115°	519.8	520.0	520.2	520.5	520.8	521.0	521.3	521.6	521.8	522.1	521.6
117.5°	589.0	590.1	591.1	592.2	593.3	593.7	593.5	593.3	593.0	592.9	592.3
120°	636.8	637.9	638.9	640.0	641.0	641.6	641.6	641.6	641.6	641.6	641.3
122.5°	684.6	685.4	686.3	687.1	688.0	688.5	688.7	689.0	689.1	689.4	688.6
125°	756.3	756.5	756.8	757.1	757.3	757.7	758.3	758.8	759.3	759.9	759.6
127.5°	825.1	825.6	826.2	826.6	827.2	827.6	827.9	828.1	828.4	828.7	828.4
130°	871.0	871.5	872.0	872.6	873.1	873.5	873.8	874.0	874.3	874.6	874.0
132.5°	913.9	914.7	915.4	916.2	917.0	917.4	917.7	918.0	918.2	918.5	918.6
135°	980.9	981.9	983.0	984.0	985.2	985.6	985.6	985.6	985.6	985.6	985.4
137.5°	1046.3	1047.7	1049.0	1050.4	1051.7	1052.2	1051.9	1051.5	1051.2	1050.9	1050.3
140°	1088.4	1089.7	1091.1	1092.4	1093.7	1094.1	1093.6	1093.1	1092.5	1092.0	1091.2
142.5°	1128.5	1129.9	1131.2	1132.5	1133.9	1134.4	1134.0	1133.7	1133.4	1133.1	1132.1
145°	1188.7	1189.5	1190.3	1191.1	1191.9	1192.3	1192.3	1192.3	1192.3	1192.3	1191.5
147.5°	1240.2	1242.0	1243.7	1245.5	1247.4	1247.9	1247.3	1246.7	1246.0	1245.4	1244.8
150°	1278.3	1278.9	1279.5	1279.9	1280.5	1280.8	1280.8	1280.8	1280.8	1280.8	1279.7
152.5°	1310.0	1310.9	1311.9	1312.8	1313.8	1313.9	1313.3	1312.6	1312.0	1311.4	1310.9
155°	1354.9	1356.1	1357.5	1358.8	1360.2	1360.3	1359.2	1358.1	1357.1	1356.1	1355.7
157.5°	1392.3	1394.1	1395.8	1397.6	1399.4	1399.7	1398.7	1397.6	1396.5	1395.4	1395.2
160°	1418.2	1419.5	1420.8	1422.1	1423.5	1423.6	1422.5	1421.5	1420.4	1419.4	1419.1
162.5°	1440.1	1441.7	1443.2	1444.8	1446.3	1446.4	1445.2	1443.9	1442.6	1441.3	1441.3
165°	1469.5	1471.2	1472.7	1474.3	1475.9	1476.2	1475.1	1474.0	1473.0	1472.0	1471.6
167.5°	1492.9	1494.6	1496.3	1497.9	1499.5	1499.5	1497.9	1496.4	1494.8	1493.2	1493.2
170°	1505.4	1507.2	1509.1	1510.9	1512.8	1512.9	1511.3	1509.7	1508.2	1506.6	1506.6
172.5°	1515.9	1517.5	1519.2	1520.8	1522.5	1522.5	1520.9	1519.3	1517.7	1516.2	1516.2
175°	1525.7	1527.6	1529.4	1531.3	1533.1	1533.3	1531.7	1530.1	1528.4	1526.9	1526.9
177.5°	1531.4	1532.9	1534.4	1535.9	1537.4	1537.5	1536.2	1534.9	1533.7	1532.4	1532.6
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1338.4	1335.4	1329.8	1324.7	1318.3	1312.7	1308.9	1304.2	1298.2	1290.9	1284.9
5°	1397.6	1385.8	1370.4	1357.0	1339.9	1326.5	1312.6	1299.3	1285.9	1268.8	1253.8
7.5°	1463.3	1439.0	1415.4	1385.7	1358.8	1334.7	1311.5	1288.2	1265.3	1241.0	1217.6
10°	1503.5	1474.1	1441.5	1404.1	1369.8	1337.2	1307.3	1277.9	1246.9	1219.6	1190.2
12.5°	1541.2	1503.2	1465.9	1418.6	1377.5	1337.7	1299.6	1262.9	1229.8	1194.4	1162.8
15°	1575.2	1537.7	1496.0	1438.3	1381.1	1332.9	1288.0	1240.5	1199.3	1159.7	1124.4
17.5°	1588.3	1549.0	1500.6	1445.1	1382.6	1322.1	1264.2	1212.0	1163.6	1117.5	1077.8
20°	1583.2	1545.2	1495.5	1442.6	1375.7	1312.6	1250.1	1192.3	1138.4	1089.6	1047.4
22.5°	1570.7	1531.5	1483.5	1427.6	1364.1	1297.2	1230.4	1168.8	1112.2	1061.8	1015.8
25°	1552.2	1498.7	1449.5	1395.0	1334.6	1268.3	1199.3	1131.4	1071.0	1019.6	969.4
27.5°	1532.8	1466.1	1403.5	1349.3	1285.5	1226.3	1159.8	1090.2	1026.7	974.4	922.8
30°	1515.3	1440.4	1371.4	1310.0	1249.5	1193.4	1130.3	1062.4	997.2	943.2	890.8
32.5°	1493.4	1413.9	1338.1	1267.2	1208.9	1153.2	1096.1	1031.2	967.7	912.0	858.7
35°	1466.1	1364.5	1282.1	1206.7	1142.1	1088.1	1036.7	984.4	920.8	863.0	811.1
37.5°	1430.1	1314.9	1219.6	1137.5	1069.2	1015.0	974.5	926.6	868.5	813.3	765.1
40°	1408.3	1279.0	1174.6	1093.4	1021.8	964.6	926.6	886.0	833.1	781.2	733.0
42.5°	1379.3	1246.0	1129.3	1044.7	972.6	917.5	879.1	843.6	799.2	750.4	698.8
45°	1322.2	1182.2	1059.7	968.8	896.1	842.1	806.3	774.8	741.1	696.2	651.3
47.5°	1248.0	1115.6	987.5	888.2	817.0	766.8	732.1	707.2	683.1	644.9	601.3
50°	1188.6	1060.8	935.6	839.5	763.5	715.9	683.3	663.5	641.6	606.9	570.5
52.5°	1118.4	1004.3	881.8	783.4	711.8	667.2	635.8	616.1	598.0	569.7	535.0
55°	1007.9	907.9	795.6	706.3	640.6	595.6	565.7	547.0	536.3	512.2	485.0
57.5°	880.3	808.7	709.6	623.5	565.4	521.0	499.1	483.2	471.0	454.1	434.8
60°	791.3	741.1	652.3	570.5	517.1	474.8	455.0	441.6	430.4	416.0	401.0
62.5°	701.1	664.5	587.3	517.1	467.9	432.5	413.9	401.9	389.0	379.2	364.6
65°	580.1	547.5	494.0	438.9	393.6	365.2	351.8	341.1	333.1	322.4	312.3
67.5°	451.3	438.0	401.1	363.1	330.5	305.3	293.7	286.3	276.6	270.2	263.2
70°	372.2	365.8	339.5	314.4	283.9	266.8	256.1	252.9	241.1	234.7	229.9
72.5°	302.0	299.0	283.9	266.5	245.0	230.0	220.1	216.6	209.1	203.9	200.8
75°	206.9	208.0	205.3	194.1	186.1	176.4	167.9	165.7	160.4	156.1	153.4
77.5°	130.9	136.3	136.6	136.0	132.8	126.9	123.4	121.8	116.5	114.9	114.3
80°	89.8	95.7	101.1	100.5	99.4	97.8	95.1	93.6	90.9	89.3	88.2
82.5°	59.9	65.4	69.8	72.7	72.5	70.9	69.1	68.4	67.8	66.6	66.4
85°	28.4	29.4	31.0	34.8	37.4	37.9	37.4	36.9	35.3	35.8	36.4
87.5°	12.9	12.5	12.6	12.2	11.3	13.1	13.9	13.9	13.5	13.1	12.6
90°	15.4	13.5	11.6	9.7	7.6	5.5	3.3	1.2	3.3	5.5	7.6
92.5°	41.3	39.1	36.8	34.9	33.4	31.9	30.4	28.9	30.4	31.9	33.4
95°	86.7	84.1	81.4	79.8	79.2	78.7	78.2	77.6	78.2	78.7	79.2
97.5°	139.2	135.5	131.8	129.9	129.7	129.4	129.2	129.0	129.2	129.4	129.7
100°	175.9	172.5	169.0	167.2	167.2	167.2	167.2	167.2	167.2	167.2	167.2
102.5°	217.5	215.8	214.0	212.6	211.5	210.5	209.5	208.3	209.5	210.5	211.5
105°	282.3	280.7	279.2	277.7	276.4	275.0	273.7	272.4	273.7	275.0	276.4
107.5°	352.1	350.9	349.7	348.4	347.1	345.8	344.4	343.1	344.4	345.8	347.1
110°	399.8	399.0	398.2	397.2	395.9	394.5	393.2	391.9	393.2	394.5	395.9



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	447.2	446.2	445.2	444.3	443.6	443.0	442.3	441.6	442.3	443.0	443.6
115°	521.0	520.5	520.0	519.2	518.1	517.1	516.0	514.9	516.0	517.1	518.1
117.5°	591.8	591.4	590.9	590.4	589.9	589.5	589.0	588.5	589.0	589.5	589.9
120°	641.0	640.8	640.5	639.7	638.4	637.1	635.7	634.4	635.7	637.1	638.4
122.5°	688.0	687.3	686.6	686.0	685.6	685.1	684.6	684.1	684.6	685.1	685.6
125°	759.3	759.1	758.8	757.9	756.3	754.7	753.0	751.5	753.0	754.7	756.3
127.5°	828.1	827.8	827.4	826.8	825.9	825.0	824.1	823.2	824.1	825.0	825.9
130°	873.5	873.0	872.4	871.5	870.1	868.9	867.5	866.2	867.5	868.9	870.1
132.5°	918.7	918.9	918.9	917.9	915.8	913.5	911.4	909.2	911.4	913.5	915.8
135°	985.2	984.8	984.6	983.7	982.1	980.5	978.9	977.3	978.9	980.5	982.1
137.5°	1049.7	1049.2	1048.5	1047.5	1045.9	1044.4	1042.9	1041.3	1042.9	1044.4	1045.9
140°	1090.4	1089.6	1088.8	1087.7	1086.4	1085.1	1083.8	1082.4	1083.8	1085.1	1086.4
142.5°	1131.1	1130.0	1129.0	1128.0	1126.9	1125.8	1124.7	1123.6	1124.7	1125.8	1126.9
145°	1190.7	1189.9	1189.1	1188.3	1187.2	1186.1	1185.0	1184.0	1185.0	1186.1	1187.2
147.5°	1244.1	1243.5	1242.9	1242.2	1241.7	1241.0	1240.5	1239.9	1240.5	1241.0	1241.7
150°	1278.7	1277.6	1276.5	1276.1	1276.4	1276.7	1276.9	1277.2	1276.9	1276.7	1276.4
152.5°	1310.5	1310.1	1309.6	1309.2	1308.8	1308.5	1308.1	1307.7	1308.1	1308.5	1308.8
155°	1355.5	1355.3	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9
157.5°	1395.0	1394.6	1394.4	1394.6	1395.1	1395.7	1396.3	1396.9	1396.3	1395.7	1395.1
160°	1418.8	1418.6	1418.3	1418.6	1419.4	1420.1	1420.9	1421.7	1420.9	1420.1	1419.4
162.5°	1441.2	1441.1	1441.1	1441.4	1442.0	1442.6	1443.1	1443.8	1443.1	1442.6	1442.0
165°	1471.4	1471.2	1470.8	1471.0	1471.6	1472.0	1472.6	1473.1	1472.6	1472.0	1471.6
167.5°	1493.2	1493.2	1493.2	1493.7	1494.8	1495.9	1496.9	1497.9	1496.9	1495.9	1494.8
170°	1506.6	1506.6	1506.6	1507.1	1508.2	1509.2	1510.3	1511.3	1510.3	1509.2	1508.2
172.5°	1516.2	1516.2	1516.2	1516.6	1517.7	1518.8	1519.9	1520.9	1519.9	1518.8	1517.7
175°	1526.9	1526.9	1526.9	1527.4	1528.4	1529.5	1530.6	1531.7	1530.6	1529.5	1528.4
177.5°	1532.8	1533.0	1533.2	1533.7	1534.6	1535.5	1536.3	1537.2	1536.3	1535.5	1534.6
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1280.6	1274.7	1270.4	1261.9	1255.8	1253.3	1248.6	1247.3	1252.0	1248.6	1248.2
5°	1242.6	1227.1	1214.8	1202.5	1189.1	1180.6	1167.8	1165.6	1162.4	1157.5	1156.5
7.5°	1196.9	1176.7	1160.9	1140.6	1122.9	1108.7	1092.7	1085.1	1080.9	1074.7	1066.4
10°	1166.1	1142.1	1120.7	1100.3	1078.5	1060.8	1044.7	1032.5	1024.5	1016.9	1013.8
12.5°	1135.8	1111.3	1083.9	1059.3	1034.8	1015.0	997.3	989.3	980.4	971.6	964.2
15°	1088.6	1056.0	1026.0	997.7	976.8	955.5	938.3	926.6	913.2	909.5	895.1
17.5°	1038.6	1006.5	971.5	941.7	917.5	894.0	875.1	861.8	851.8	838.0	831.3
20°	1007.3	969.4	935.2	907.9	881.1	853.3	834.1	822.8	813.3	802.0	796.7
22.5°	974.0	936.8	901.8	869.8	842.6	815.3	801.6	790.0	779.0	768.7	761.6
25°	925.0	887.6	850.6	817.5	789.2	769.4	753.4	740.0	734.1	724.0	716.4
27.5°	876.5	836.8	798.5	765.4	743.2	723.7	710.5	699.9	689.3	680.4	673.9
30°	845.3	804.7	763.0	736.8	713.3	694.5	680.1	669.9	661.9	653.9	649.1
32.5°	814.1	772.2	735.1	706.9	684.6	668.4	653.6	643.9	635.4	626.5	620.8
35°	764.1	721.3	691.3	663.5	641.6	626.6	616.5	602.6	595.6	589.2	583.4
37.5°	717.6	677.8	645.4	621.0	601.9	587.1	573.9	566.4	557.9	552.1	547.2
40°	683.3	647.0	617.6	591.9	578.0	561.4	549.1	539.5	533.1	525.6	520.2
42.5°	652.5	618.7	590.2	567.0	549.8	535.8	523.9	514.3	506.1	500.8	496.3
45°	609.0	575.3	547.5	526.1	510.1	496.7	484.4	479.6	468.9	462.5	460.3
47.5°	564.0	533.9	507.0	487.3	470.9	458.2	446.6	436.8	430.9	424.6	421.2
50°	533.6	504.7	479.6	460.3	444.3	430.4	419.7	413.3	405.3	399.4	395.1
52.5°	503.3	476.5	451.4	433.0	419.1	405.2	393.2	386.8	379.2	375.4	372.5
55°	459.9	431.5	410.1	391.9	377.5	364.6	353.4	347.0	342.2	338.4	337.4
57.5°	410.7	388.2	368.3	351.9	336.9	324.9	315.1	309.0	304.7	304.1	301.0
60°	378.6	358.2	340.1	322.4	309.6	298.3	289.8	282.8	278.5	278.1	276.9
62.5°	346.5	327.0	310.1	294.6	283.0	272.3	264.1	256.4	253.7	251.1	248.7
65°	298.9	281.2	267.4	255.0	242.7	233.6	225.6	220.9	214.9	211.8	205.9
67.5°	252.2	238.4	225.1	214.8	205.1	196.5	189.8	182.7	178.7	176.1	171.8
70°	221.3	210.6	197.3	186.1	178.6	171.7	166.3	158.3	155.6	153.4	151.3
72.5°	192.3	182.8	171.7	162.6	155.0	148.5	142.4	138.6	135.9	133.8	132.5
75°	151.3	142.2	132.6	126.2	120.8	115.5	112.3	109.6	108.5	108.0	105.8
77.5°	111.1	106.3	98.6	93.5	89.9	87.8	84.9	83.5	83.4	81.0	80.3
80°	85.0	82.3	75.9	73.8	71.1	69.0	67.3	64.7	62.0	60.9	59.3
82.5°	63.2	60.5	58.0	54.5	52.3	51.0	49.4	48.4	48.8	47.3	46.5
85°	33.7	31.0	29.9	29.4	28.4	29.4	28.8	28.4	27.8	27.3	27.8
87.5°	12.6	13.0	13.0	14.2	13.3	14.1	14.3	14.2	14.5	14.7	14.5
90°	9.7	11.6	13.5	15.4	17.3	19.1	20.4	21.8	23.1	24.4	25.5
92.5°	34.9	36.8	39.1	41.3	43.6	45.9	47.6	49.4	51.1	52.9	54.0
95°	79.8	81.4	84.1	86.7	89.4	92.0	93.9	95.7	97.6	99.4	100.6
97.5°	129.9	131.8	135.5	139.2	142.8	146.5	148.2	150.0	151.7	153.4	154.6
100°	167.2	169.0	172.5	175.9	179.4	182.8	185.2	187.6	190.0	192.3	193.8
102.5°	212.6	214.0	215.8	217.5	219.3	221.0	223.6	226.2	228.9	231.4	233.1
105°	277.7	279.2	280.7	282.3	283.9	285.6	287.2	288.8	290.3	291.9	293.1
107.5°	348.4	349.7	350.9	352.1	353.4	354.6	355.4	356.2	357.0	357.7	358.1
110°	397.2	398.2	399.0	399.8	400.6	401.4	402.2	403.1	403.9	404.6	404.9



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	444.3	445.2	446.2	447.2	448.2	449.2	449.6	450.0	450.4	450.7	450.7
115°	519.2	520.0	520.5	521.0	521.6	522.1	521.8	521.6	521.3	521.0	520.8
117.5°	590.4	590.9	591.4	591.8	592.3	592.9	593.0	593.3	593.5	593.7	593.3
120°	639.7	640.5	640.8	641.0	641.3	641.6	641.6	641.6	641.6	641.6	641.0
122.5°	686.0	686.6	687.3	688.0	688.6	689.4	689.1	689.0	688.7	688.5	688.0
125°	757.9	758.8	759.1	759.3	759.6	759.9	759.3	758.8	758.3	757.7	757.3
127.5°	826.8	827.4	827.8	828.1	828.4	828.7	828.4	828.1	827.9	827.6	827.2
130°	871.5	872.4	873.0	873.5	874.0	874.6	874.3	874.0	873.8	873.5	873.1
132.5°	917.9	918.9	918.9	918.7	918.6	918.5	918.2	918.0	917.7	917.4	917.0
135°	983.7	984.6	984.8	985.2	985.4	985.6	985.6	985.6	985.6	985.6	985.2
137.5°	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2	1051.5	1051.9	1052.2	1051.7
140°	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5	1093.1	1093.6	1094.1	1093.7
142.5°	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4	1133.7	1134.0	1134.4	1133.9
145°	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3	1192.3	1192.3	1192.3	1191.9
147.5°	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0	1246.7	1247.3	1247.9	1247.4
150°	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8	1280.8	1280.8	1280.8	1280.5
152.5°	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0	1312.6	1313.3	1313.9	1313.8
155°	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1	1358.1	1359.2	1360.3	1360.2
157.5°	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5	1397.6	1398.7	1399.7	1399.4
160°	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4	1421.5	1422.5	1423.6	1423.5
162.5°	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6	1443.9	1445.2	1446.4	1446.3
165°	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0	1474.0	1475.1	1476.2	1475.9
167.5°	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8	1496.4	1497.9	1499.5	1499.5
170°	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2	1509.7	1511.3	1512.9	1512.8
172.5°	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7	1519.3	1520.9	1522.5	1522.5
175°	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4	1530.1	1531.7	1533.3	1533.1
177.5°	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7	1534.9	1536.2	1537.5	1537.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1247.7	1243.0	1241.7	1243.4	1241.7	1243.0	1247.7	1248.2	1248.6	1252.0	1247.3
5°	1151.2	1145.8	1148.5	1147.4	1148.5	1145.8	1151.2	1156.5	1157.5	1162.4	1165.6
7.5°	1066.3	1059.6	1052.6	1054.8	1052.6	1059.6	1066.3	1066.4	1074.7	1080.9	1085.1
10°	1006.8	1001.5	998.2	1000.9	998.2	1001.5	1006.8	1013.8	1016.9	1024.5	1032.5
12.5°	956.7	953.5	950.8	949.6	950.8	953.5	956.7	964.2	971.6	980.4	989.3
15°	888.7	882.3	879.6	872.6	879.6	882.3	888.7	895.1	909.5	913.2	926.6
17.5°	825.9	823.7	816.7	813.8	816.7	823.7	825.9	831.3	838.0	851.8	861.8
20°	788.6	786.5	779.6	783.9	779.6	786.5	788.6	796.7	802.0	813.3	822.8
22.5°	757.9	753.1	750.9	749.6	750.9	753.1	757.9	761.6	768.7	779.0	790.0
25°	714.3	707.3	704.7	701.5	704.7	707.3	714.3	716.4	724.0	734.1	740.0
27.5°	670.9	667.2	663.6	662.8	663.6	667.2	670.9	673.9	680.4	689.3	699.9
30°	642.7	639.0	636.3	636.3	636.3	639.0	642.7	649.1	653.9	661.9	669.9
32.5°	617.4	614.6	611.9	611.5	611.9	614.6	617.4	620.8	626.5	635.4	643.9
35°	580.7	576.4	575.3	572.1	575.3	576.4	580.7	583.4	589.2	595.6	602.6
37.5°	542.5	538.9	538.8	538.5	538.8	538.9	542.5	547.2	552.1	557.9	566.4
40°	518.1	515.4	514.9	511.1	514.9	515.4	518.1	520.2	525.6	533.1	539.5
42.5°	492.0	490.6	488.8	487.2	488.8	490.6	492.0	496.3	500.8	506.1	514.3
45°	456.6	452.9	452.9	450.2	452.9	452.9	456.6	460.3	462.5	468.9	479.6
47.5°	420.0	417.2	417.5	414.7	417.5	417.2	420.0	421.2	424.6	430.9	436.8
50°	395.7	394.0	393.6	392.4	393.6	394.0	395.7	395.1	399.4	405.3	413.3
52.5°	371.3	370.5	372.6	370.2	372.6	370.5	371.3	372.5	375.4	379.2	386.8
55°	338.4	336.8	340.1	336.8	340.1	336.8	338.4	337.4	338.4	342.2	347.0
57.5°	300.7	299.2	302.1	300.5	302.1	299.2	300.7	301.0	304.1	304.7	309.0
60°	275.9	272.7	274.3	274.8	274.3	272.7	275.9	276.9	278.1	278.5	282.8
62.5°	246.4	244.5	245.7	243.2	245.7	244.5	246.4	248.7	251.1	253.7	256.4
65°	204.8	203.2	201.1	199.9	201.1	203.2	204.8	205.9	211.8	214.9	220.9
67.5°	172.1	168.2	168.1	169.0	168.1	168.2	172.1	171.8	176.1	178.7	182.7
70°	148.1	148.1	147.6	147.6	147.6	148.1	148.1	151.3	153.4	155.6	158.3
72.5°	131.4	131.0	130.0	129.6	130.0	131.0	131.4	132.5	133.8	135.9	138.6
75°	105.8	106.4	105.4	104.8	105.4	106.4	105.8	105.8	108.0	108.5	109.6
77.5°	78.2	75.9	77.1	75.9	77.1	75.9	78.2	80.3	81.0	83.4	83.5
80°	59.3	58.8	60.4	58.8	60.4	58.8	59.3	59.3	60.9	62.0	64.7
82.5°	47.0	46.4	47.1	45.9	47.1	46.4	47.0	46.5	47.3	48.8	48.4
85°	28.4	27.8	27.3	27.8	27.3	27.8	28.4	27.8	27.3	27.8	28.4
87.5°	15.1	14.8	15.0	15.1	15.0	14.8	15.1	14.5	14.7	14.5	14.2
90°	26.3	27.1	27.9	28.7	27.9	27.1	26.3	25.5	24.4	23.1	21.8
92.5°	54.7	55.2	55.8	56.4	55.8	55.2	54.7	54.0	52.9	51.1	49.4
95°	101.2	101.7	102.2	102.7	102.2	101.7	101.2	100.6	99.4	97.6	95.7
97.5°	154.9	155.2	155.5	155.8	155.5	155.2	154.9	154.6	153.4	151.7	150.0
100°	194.3	194.9	195.4	195.9	195.4	194.9	194.3	193.8	192.3	190.0	187.6
102.5°	233.9	234.6	235.4	236.1	235.4	234.6	233.9	233.1	231.4	228.9	226.2
105°	293.9	294.7	295.5	296.3	295.5	294.7	293.9	293.1	291.9	290.3	288.8
107.5°	358.1	358.1	358.0	357.9	358.0	358.1	358.1	358.1	357.7	357.0	356.2
110°	404.6	404.3	404.1	403.9	404.1	404.3	404.6	404.9	404.6	403.9	403.1



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	450.2	449.7	449.2	448.8	449.2	449.7	450.2	450.7	450.7	450.4	450.0
115°	520.5	520.2	520.0	519.8	520.0	520.2	520.5	520.8	521.0	521.3	521.6
117.5°	592.2	591.1	590.1	589.0	590.1	591.1	592.2	593.3	593.7	593.5	593.3
120°	640.0	638.9	637.9	636.8	637.9	638.9	640.0	641.0	641.6	641.6	641.6
122.5°	687.1	686.3	685.4	684.6	685.4	686.3	687.1	688.0	688.5	688.7	689.0
125°	757.1	756.8	756.5	756.3	756.5	756.8	757.1	757.3	757.7	758.3	758.8
127.5°	826.6	826.2	825.6	825.1	825.6	826.2	826.6	827.2	827.6	827.9	828.1
130°	872.6	872.0	871.5	871.0	871.5	872.0	872.6	873.1	873.5	873.8	874.0
132.5°	916.2	915.4	914.7	913.9	914.7	915.4	916.2	917.0	917.4	917.7	918.0
135°	984.0	983.0	981.9	980.9	981.9	983.0	984.0	985.2	985.6	985.6	985.6
137.5°	1050.4	1049.0	1047.7	1046.3	1047.7	1049.0	1050.4	1051.7	1052.2	1051.9	1051.5
140°	1092.4	1091.1	1089.7	1088.4	1089.7	1091.1	1092.4	1093.7	1094.1	1093.6	1093.1
142.5°	1132.5	1131.2	1129.9	1128.5	1129.9	1131.2	1132.5	1133.9	1134.4	1134.0	1133.7
145°	1191.1	1190.3	1189.5	1188.7	1189.5	1190.3	1191.1	1191.9	1192.3	1192.3	1192.3
147.5°	1245.5	1243.7	1242.0	1240.2	1242.0	1243.7	1245.5	1247.4	1247.9	1247.3	1246.7
150°	1279.9	1279.5	1278.9	1278.3	1278.9	1279.5	1279.9	1280.5	1280.8	1280.8	1280.8
152.5°	1312.8	1311.9	1310.9	1310.0	1310.9	1311.9	1312.8	1313.8	1313.9	1313.3	1312.6
155°	1358.8	1357.5	1356.1	1354.9	1356.1	1357.5	1358.8	1360.2	1360.3	1359.2	1358.1
157.5°	1397.6	1395.8	1394.1	1392.3	1394.1	1395.8	1397.6	1399.4	1399.7	1398.7	1397.6
160°	1422.1	1420.8	1419.5	1418.2	1419.5	1420.8	1422.1	1423.5	1423.6	1422.5	1421.5
162.5°	1444.8	1443.2	1441.7	1440.1	1441.7	1443.2	1444.8	1446.3	1446.4	1445.2	1443.9
165°	1474.3	1472.7	1471.2	1469.5	1471.2	1472.7	1474.3	1475.9	1476.2	1475.1	1474.0
167.5°	1497.9	1496.3	1494.6	1492.9	1494.6	1496.3	1497.9	1499.5	1499.5	1497.9	1496.4
170°	1510.9	1509.1	1507.2	1505.4	1507.2	1509.1	1510.9	1512.8	1512.9	1511.3	1509.7
172.5°	1520.8	1519.2	1517.5	1515.9	1517.5	1519.2	1520.8	1522.5	1522.5	1520.9	1519.3
175°	1531.3	1529.4	1527.6	1525.7	1527.6	1529.4	1531.3	1533.1	1533.3	1531.7	1530.1
177.5°	1535.9	1534.4	1532.9	1531.4	1532.9	1534.4	1535.9	1537.4	1537.5	1536.2	1534.9
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1248.6	1253.3	1255.8	1261.9	1270.4	1274.7	1280.6	1284.9	1290.9	1298.2	1304.2
5°	1167.8	1180.6	1189.1	1202.5	1214.8	1227.1	1242.6	1253.8	1268.8	1285.9	1299.3
7.5°	1092.7	1108.7	1122.9	1140.6	1160.9	1176.7	1196.9	1217.6	1241.0	1265.3	1288.2
10°	1044.7	1060.8	1078.5	1100.3	1120.7	1142.1	1166.1	1190.2	1219.6	1246.9	1277.9
12.5°	997.3	1015.0	1034.8	1059.3	1083.9	1111.3	1135.8	1162.8	1194.4	1229.8	1262.9
15°	938.3	955.5	976.8	997.7	1026.0	1056.0	1088.6	1124.4	1159.7	1199.3	1240.5
17.5°	875.1	894.0	917.5	941.7	971.5	1006.5	1038.6	1077.8	1117.5	1163.6	1212.0
20°	834.1	853.3	881.1	907.9	935.2	969.4	1007.3	1047.4	1089.6	1138.4	1192.3
22.5°	801.6	815.3	842.6	869.8	901.8	936.8	974.0	1015.8	1061.8	1112.2	1168.8
25°	753.4	769.4	789.2	817.5	850.6	887.6	925.0	969.4	1019.6	1071.0	1131.4
27.5°	710.5	723.7	743.2	765.4	798.5	836.8	876.5	922.8	974.4	1026.7	1090.2
30°	680.1	694.5	713.3	736.8	763.0	804.7	845.3	890.8	943.2	997.2	1062.4
32.5°	653.6	668.4	684.6	706.9	735.1	772.2	814.1	858.7	912.0	967.7	1031.2
35°	616.5	626.6	641.6	663.5	691.3	721.3	764.1	811.1	863.0	920.8	984.4
37.5°	573.9	587.1	601.9	621.0	645.4	677.8	717.6	765.1	813.3	868.5	926.6
40°	549.1	561.4	578.0	591.9	617.6	647.0	683.3	733.0	781.2	833.1	886.0
42.5°	523.9	535.8	549.8	567.0	590.2	618.7	652.5	698.8	750.4	799.2	843.6
45°	484.4	496.7	510.1	526.1	547.5	575.3	609.0	651.3	696.2	741.1	774.8
47.5°	446.6	458.2	470.9	487.3	507.0	533.9	564.0	601.3	644.9	683.1	707.2
50°	419.7	430.4	444.3	460.3	479.6	504.7	533.6	570.5	606.9	641.6	663.5
52.5°	393.2	405.2	419.1	433.0	451.4	476.5	503.3	535.0	569.7	598.0	616.1
55°	353.4	364.6	377.5	391.9	410.1	431.5	459.9	485.0	512.2	536.3	547.0
57.5°	315.1	324.9	336.9	351.9	368.3	388.2	410.7	434.8	454.1	471.0	483.2
60°	289.8	298.3	309.6	322.4	340.1	358.2	378.6	401.0	416.0	430.4	441.6
62.5°	264.1	272.3	283.0	294.6	310.1	327.0	346.5	364.6	379.2	389.0	401.9
65°	225.6	233.6	242.7	255.0	267.4	281.2	298.9	312.3	322.4	333.1	341.1
67.5°	189.8	196.5	205.1	214.8	225.1	238.4	252.2	263.2	270.2	276.6	286.3
70°	166.3	171.7	178.6	186.1	197.3	210.6	221.3	229.9	234.7	241.1	252.9
72.5°	142.4	148.5	155.0	162.6	171.7	182.8	192.3	200.8	203.9	209.1	216.6
75°	112.3	115.5	120.8	126.2	132.6	142.2	151.3	153.4	156.1	160.4	165.7
77.5°	84.9	87.8	89.9	93.5	98.6	106.3	111.1	114.3	114.9	116.5	121.8
80°	67.3	69.0	71.1	73.8	75.9	82.3	85.0	88.2	89.3	90.9	93.6
82.5°	49.4	51.0	52.3	54.5	58.0	60.5	63.2	66.4	66.6	67.8	68.4
85°	28.8	29.4	28.4	29.4	29.9	31.0	33.7	36.4	35.8	35.3	36.9
87.5°	14.3	14.1	13.3	14.2	13.0	13.0	12.6	12.6	13.1	13.5	13.9
90°	20.4	19.1	17.3	15.4	13.5	11.6	9.7	7.6	5.5	3.3	1.2
92.5°	47.6	45.9	43.6	41.3	39.1	36.8	34.9	33.4	31.9	30.4	28.9
95°	93.9	92.0	89.4	86.7	84.1	81.4	79.8	79.2	78.7	78.2	77.6
97.5°	148.2	146.5	142.8	139.2	135.5	131.8	129.9	129.7	129.4	129.2	129.0
100°	185.2	182.8	179.4	175.9	172.5	169.0	167.2	167.2	167.2	167.2	167.2
102.5°	223.6	221.0	219.3	217.5	215.8	214.0	212.6	211.5	210.5	209.5	208.3
105°	287.2	285.6	283.9	282.3	280.7	279.2	277.7	276.4	275.0	273.7	272.4
107.5°	355.4	354.6	353.4	352.1	350.9	349.7	348.4	347.1	345.8	344.4	343.1
110°	402.2	401.4	400.6	399.8	399.0	398.2	397.2	395.9	394.5	393.2	391.9



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	449.6	449.2	448.2	447.2	446.2	445.2	444.3	443.6	443.0	442.3	441.6
115°	521.8	522.1	521.6	521.0	520.5	520.0	519.2	518.1	517.1	516.0	514.9
117.5°	593.0	592.9	592.3	591.8	591.4	590.9	590.4	589.9	589.5	589.0	588.5
120°	641.6	641.6	641.3	641.0	640.8	640.5	639.7	638.4	637.1	635.7	634.4
122.5°	689.1	689.4	688.6	688.0	687.3	686.6	686.0	685.6	685.1	684.6	684.1
125°	759.3	759.9	759.6	759.3	759.1	758.8	757.9	756.3	754.7	753.0	751.5
127.5°	828.4	828.7	828.4	828.1	827.8	827.4	826.8	825.9	825.0	824.1	823.2
130°	874.3	874.6	874.0	873.5	873.0	872.4	871.5	870.1	868.9	867.5	866.2
132.5°	918.2	918.5	918.6	918.7	918.9	918.9	917.9	915.8	913.5	911.4	909.2
135°	985.6	985.6	985.4	985.2	984.8	984.6	983.7	982.1	980.5	978.9	977.3
137.5°	1051.2	1050.9	1050.3	1049.7	1049.2	1048.5	1047.5	1045.9	1044.4	1042.9	1041.3
140°	1092.5	1092.0	1091.2	1090.4	1089.6	1088.8	1087.7	1086.4	1085.1	1083.8	1082.4
142.5°	1133.4	1133.1	1132.1	1131.1	1130.0	1129.0	1128.0	1126.9	1125.8	1124.7	1123.6
145°	1192.3	1192.3	1191.5	1190.7	1189.9	1189.1	1188.3	1187.2	1186.1	1185.0	1184.0
147.5°	1246.0	1245.4	1244.8	1244.1	1243.5	1242.9	1242.2	1241.7	1241.0	1240.5	1239.9
150°	1280.8	1280.8	1279.7	1278.7	1277.6	1276.5	1276.1	1276.4	1276.7	1276.9	1277.2
152.5°	1312.0	1311.4	1310.9	1310.5	1310.1	1309.6	1309.2	1308.8	1308.5	1308.1	1307.7
155°	1357.1	1356.1	1355.7	1355.5	1355.3	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9
157.5°	1396.5	1395.4	1395.2	1395.0	1394.6	1394.4	1394.6	1395.1	1395.7	1396.3	1396.9
160°	1420.4	1419.4	1419.1	1418.8	1418.6	1418.3	1418.6	1419.4	1420.1	1420.9	1421.7
162.5°	1442.6	1441.3	1441.3	1441.2	1441.1	1441.1	1441.4	1442.0	1442.6	1443.1	1443.8
165°	1473.0	1472.0	1471.6	1471.4	1471.2	1470.8	1471.0	1471.6	1472.0	1472.6	1473.1
167.5°	1494.8	1493.2	1493.2	1493.2	1493.2	1493.2	1493.7	1494.8	1495.9	1496.9	1497.9
170°	1508.2	1506.6	1506.6	1506.6	1506.6	1506.6	1507.1	1508.2	1509.2	1510.3	1511.3
172.5°	1517.7	1516.2	1516.2	1516.2	1516.2	1516.2	1516.6	1517.7	1518.8	1519.9	1520.9
175°	1528.4	1526.9	1526.9	1526.9	1526.9	1526.9	1527.4	1528.4	1529.5	1530.6	1531.7
177.5°	1533.7	1532.4	1532.6	1532.8	1533.0	1533.2	1533.7	1534.6	1535.5	1536.3	1537.2
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1308.9	1312.7	1318.3	1324.7	1329.8	1335.4	1338.4	1338.4	1341.0	1346.6	1353.8
5°	1312.6	1326.5	1339.9	1357.0	1370.4	1385.8	1397.6	1408.9	1419.0	1431.9	1445.3
7.5°	1311.5	1334.7	1358.8	1385.7	1415.4	1439.0	1463.3	1482.3	1501.2	1525.7	1545.1
10°	1307.3	1337.2	1369.8	1404.1	1441.5	1474.1	1503.5	1530.3	1555.9	1582.6	1606.7
12.5°	1299.6	1337.7	1377.5	1418.6	1465.9	1503.2	1541.2	1569.6	1599.6	1628.8	1658.4
15°	1288.0	1332.9	1381.1	1438.3	1496.0	1537.7	1575.2	1612.1	1639.8	1673.0	1701.4
17.5°	1264.2	1322.1	1382.6	1445.1	1500.6	1549.0	1588.3	1623.4	1653.0	1689.5	1728.0
20°	1250.1	1312.6	1375.7	1442.6	1495.5	1545.2	1583.2	1619.5	1656.5	1704.0	1751.0
22.5°	1230.4	1297.2	1364.1	1427.6	1483.5	1531.5	1570.7	1615.3	1663.7	1717.7	1774.6
25°	1199.3	1268.3	1334.6	1395.0	1449.5	1498.7	1552.2	1612.1	1670.9	1742.0	1823.8
27.5°	1159.8	1226.3	1285.5	1349.3	1403.5	1466.1	1532.8	1597.8	1682.5	1780.4	1882.5
30°	1130.3	1193.4	1249.5	1310.0	1371.4	1440.4	1515.3	1591.7	1692.8	1807.8	1929.1
32.5°	1096.1	1153.2	1208.9	1267.2	1338.1	1413.9	1493.4	1587.1	1707.8	1838.6	1964.2
35°	1036.7	1088.1	1142.1	1206.7	1282.1	1364.5	1466.1	1580.0	1725.9	1866.5	1979.3
37.5°	974.5	1015.0	1069.2	1137.5	1219.6	1314.9	1430.1	1568.5	1718.5	1844.6	1892.7
40°	926.6	964.6	1021.8	1093.4	1174.6	1279.0	1408.3	1550.5	1701.4	1789.1	1785.3
42.5°	879.1	917.5	972.6	1044.7	1129.3	1246.0	1379.3	1527.0	1654.3	1687.7	1618.0
45°	806.3	842.1	896.1	968.8	1059.7	1182.2	1322.2	1464.0	1545.2	1491.2	1353.3
47.5°	732.1	766.8	817.0	888.2	987.5	1115.6	1248.0	1364.3	1375.7	1259.7	1094.2
50°	683.3	715.9	763.5	839.5	935.6	1060.8	1188.6	1280.0	1251.6	1110.0	939.4
52.5°	635.8	667.2	711.8	783.4	881.8	1004.3	1118.4	1190.2	1124.7	974.0	820.5
55°	565.7	595.6	640.6	706.3	795.6	907.9	1007.9	1034.0	937.8	786.0	661.9
57.5°	499.1	521.0	565.4	623.5	709.6	808.7	880.3	875.6	769.4	632.6	543.7
60°	455.0	474.8	517.1	570.5	652.3	741.1	791.3	769.9	662.5	549.6	464.1
62.5°	413.9	432.5	467.9	517.1	587.3	664.5	701.1	671.5	570.1	471.0	402.9
65°	351.8	365.2	393.6	438.9	494.0	547.5	580.1	536.8	447.0	372.2	320.8
67.5°	293.7	305.3	330.5	363.1	401.1	438.0	451.3	410.7	340.8	290.3	254.2
70°	256.1	266.8	283.9	314.4	339.5	365.8	372.2	335.8	277.5	239.0	216.6
72.5°	220.1	230.0	245.0	266.5	283.9	299.0	302.0	268.2	223.6	197.1	179.7
75°	167.9	176.4	186.1	194.1	205.3	208.0	206.9	180.7	156.7	139.0	129.4
77.5°	123.4	126.9	132.8	136.0	136.6	136.3	130.9	114.3	101.9	94.7	90.7
80°	95.1	97.8	99.4	100.5	101.1	95.7	89.8	79.7	75.4	71.1	66.3
82.5°	69.1	70.9	72.5	72.7	69.8	65.4	59.9	54.8	51.9	49.7	47.9
85°	37.4	37.9	37.4	34.8	31.0	29.4	28.4	27.3	26.7	26.2	26.2
87.5°	13.9	13.1	11.3	12.2	12.6	12.5	12.9	12.8	12.8	13.1	13.3
90°	3.3	5.5	7.6	9.7	11.6	13.5	15.4	17.3	19.1	20.4	21.8
92.5°	30.4	31.9	33.4	34.9	36.8	39.1	41.3	43.6	45.9	47.6	49.4
95°	78.2	78.7	79.2	79.8	81.4	84.1	86.7	89.4	92.0	93.9	95.7
97.5°	129.2	129.4	129.7	129.9	131.8	135.5	139.2	142.8	146.5	148.2	150.0
100°	167.2	167.2	167.2	167.2	169.0	172.5	175.9	179.4	182.8	185.2	187.6
102.5°	209.5	210.5	211.5	212.6	214.0	215.8	217.5	219.3	221.0	223.6	226.2
105°	273.7	275.0	276.4	277.7	279.2	280.7	282.3	283.9	285.6	287.2	288.8
107.5°	344.4	345.8	347.1	348.4	349.7	350.9	352.1	353.4	354.6	355.4	356.2
110°	393.2	394.5	395.9	397.2	398.2	399.0	399.8	400.6	401.4	402.2	403.1



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	442.3	443.0	443.6	444.3	445.2	446.2	447.2	448.2	449.2	449.6	450.0
115°	516.0	517.1	518.1	519.2	520.0	520.5	521.0	521.6	522.1	521.8	521.6
117.5°	589.0	589.5	589.9	590.4	590.9	591.4	591.8	592.3	592.9	593.0	593.3
120°	635.7	637.1	638.4	639.7	640.5	640.8	641.0	641.3	641.6	641.6	641.6
122.5°	684.6	685.1	685.6	686.0	686.6	687.3	688.0	688.6	689.4	689.1	689.0
125°	753.0	754.7	756.3	757.9	758.8	759.1	759.3	759.6	759.9	759.3	758.8
127.5°	824.1	825.0	825.9	826.8	827.4	827.8	828.1	828.4	828.7	828.4	828.1
130°	867.5	868.9	870.1	871.5	872.4	873.0	873.5	874.0	874.6	874.3	874.0
132.5°	911.4	913.5	915.8	917.9	918.9	918.9	918.7	918.6	918.5	918.2	918.0
135°	978.9	980.5	982.1	983.7	984.6	984.8	985.2	985.4	985.6	985.6	985.6
137.5°	1042.9	1044.4	1045.9	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2	1051.5
140°	1083.8	1085.1	1086.4	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5	1093.1
142.5°	1124.7	1125.8	1126.9	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4	1133.7
145°	1185.0	1186.1	1187.2	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3	1192.3
147.5°	1240.5	1241.0	1241.7	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0	1246.7
150°	1276.9	1276.7	1276.4	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8	1280.8
152.5°	1308.1	1308.5	1308.8	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0	1312.6
155°	1354.9	1354.9	1354.9	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1	1358.1
157.5°	1396.3	1395.7	1395.1	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5	1397.6
160°	1420.9	1420.1	1419.4	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4	1421.5
162.5°	1443.1	1442.6	1442.0	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6	1443.9
165°	1472.6	1472.0	1471.6	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0	1474.0
167.5°	1496.9	1495.9	1494.8	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8	1496.4
170°	1510.3	1509.2	1508.2	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2	1509.7
172.5°	1519.9	1518.8	1517.7	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7	1519.3
175°	1530.6	1529.5	1528.4	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4	1530.1
177.5°	1536.3	1535.5	1534.6	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7	1534.9
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
2.5°	1359.4	1359.4	1366.7	1366.2	1371.0	1369.2	1370.1
5°	1461.3	1470.4	1478.4	1483.8	1491.8	1493.9	1492.8
7.5°	1566.9	1587.1	1597.0	1610.4	1612.9	1619.9	1619.2
10°	1632.4	1652.2	1667.1	1678.9	1684.7	1692.3	1692.8
12.5°	1683.7	1700.5	1713.7	1724.7	1731.8	1734.2	1735.6
15°	1723.8	1742.5	1758.0	1773.5	1782.6	1789.5	1793.3
17.5°	1764.2	1793.1	1820.4	1841.5	1854.2	1864.9	1864.7
20°	1795.5	1828.6	1862.8	1886.9	1911.5	1922.2	1923.7
22.5°	1828.8	1879.5	1923.6	1960.9	1993.1	2004.3	2008.5
25°	1898.1	1964.4	2032.3	2084.7	2122.1	2144.0	2147.3
27.5°	1981.8	2071.6	2143.0	2191.3	2222.5	2238.7	2242.2
30°	2040.9	2123.8	2187.9	2224.3	2238.7	2240.8	2232.8
32.5°	2067.4	2129.3	2155.0	2152.8	2124.5	2105.7	2098.5
35°	2035.0	2022.1	1959.6	1884.8	1827.6	1791.2	1781.5
37.5°	1851.9	1741.2	1626.2	1513.1	1452.9	1422.2	1369.6
40°	1671.4	1513.7	1393.9	1298.7	1230.8	1176.3	1163.5
42.5°	1467.8	1305.0	1185.2	1103.7	1049.5	1012.0	995.8
45°	1179.5	1039.4	940.5	878.0	836.2	809.0	796.7
47.5°	943.4	835.0	762.9	716.6	684.8	661.1	654.4
50°	813.8	727.1	666.2	627.2	603.1	584.9	577.4
52.5°	706.9	636.9	590.1	557.9	535.1	523.8	517.5
55°	583.4	522.9	489.3	463.6	450.8	441.6	437.4
57.5°	477.1	433.4	408.8	391.1	379.2	373.4	371.3
60°	417.6	383.3	360.9	347.0	339.0	331.5	329.4
62.5°	365.0	338.0	320.7	308.5	300.5	297.3	296.0
65°	294.1	276.4	263.6	256.1	249.7	248.6	248.1
67.5°	233.8	223.4	216.7	208.8	206.6	202.9	202.1
70°	199.9	193.1	185.0	182.4	179.7	175.9	176.4
72.5°	169.6	162.6	157.2	153.7	152.7	151.1	152.5
75°	124.1	121.9	119.8	117.1	116.1	116.1	115.5
77.5°	88.6	86.7	84.4	82.8	82.5	80.2	81.0
80°	64.2	61.5	60.4	60.9	59.3	58.8	58.8
82.5°	47.5	46.5	45.5	45.6	45.2	44.7	45.2
85°	26.2	25.7	25.7	25.1	25.1	24.6	24.6
87.5°	14.0	14.7	14.1	13.8	13.9	14.6	15.1
90°	23.1	24.4	25.5	26.3	27.1	27.9	28.7
92.5°	51.1	52.9	54.0	54.7	55.2	55.8	56.4
95°	97.6	99.4	100.6	101.2	101.7	102.2	102.7
97.5°	151.7	153.4	154.6	154.9	155.2	155.5	155.8
100°	190.0	192.3	193.8	194.3	194.9	195.4	195.9
102.5°	228.9	231.4	233.1	233.9	234.6	235.4	236.1
105°	290.3	291.9	293.1	293.9	294.7	295.5	296.3
107.5°	357.0	357.7	358.1	358.1	358.1	358.0	357.9
110°	403.9	404.6	404.9	404.6	404.3	404.1	403.9



TEST NUMBER: P333717-927

CATALOG NUMBER: S125RDIW-S1090D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	450.7	450.7	450.2	449.7	449.2	448.8
115°	521.3	521.0	520.8	520.5	520.2	520.0	519.8
117.5°	593.5	593.7	593.3	592.2	591.1	590.1	589.0
120°	641.6	641.6	641.0	640.0	638.9	637.9	636.8
122.5°	688.7	688.5	688.0	687.1	686.3	685.4	684.6
125°	758.3	757.7	757.3	757.1	756.8	756.5	756.3
127.5°	827.9	827.6	827.2	826.6	826.2	825.6	825.1
130°	873.8	873.5	873.1	872.6	872.0	871.5	871.0
132.5°	917.7	917.4	917.0	916.2	915.4	914.7	913.9
135°	985.6	985.6	985.2	984.0	983.0	981.9	980.9
137.5°	1051.9	1052.2	1051.7	1050.4	1049.0	1047.7	1046.3
140°	1093.6	1094.1	1093.7	1092.4	1091.1	1089.7	1088.4
142.5°	1134.0	1134.4	1133.9	1132.5	1131.2	1129.9	1128.5
145°	1192.3	1192.3	1191.9	1191.1	1190.3	1189.5	1188.7
147.5°	1247.3	1247.9	1247.4	1245.5	1243.7	1242.0	1240.2
150°	1280.8	1280.8	1280.5	1279.9	1279.5	1278.9	1278.3
152.5°	1313.3	1313.9	1313.8	1312.8	1311.9	1310.9	1310.0
155°	1359.2	1360.3	1360.2	1358.8	1357.5	1356.1	1354.9
157.5°	1398.7	1399.7	1399.4	1397.6	1395.8	1394.1	1392.3
160°	1422.5	1423.6	1423.5	1422.1	1420.8	1419.5	1418.2
162.5°	1445.2	1446.4	1446.3	1444.8	1443.2	1441.7	1440.1
165°	1475.1	1476.2	1475.9	1474.3	1472.7	1471.2	1469.5
167.5°	1497.9	1499.5	1499.5	1497.9	1496.3	1494.6	1492.9
170°	1511.3	1512.9	1512.8	1510.9	1509.1	1507.2	1505.4
172.5°	1520.9	1522.5	1522.5	1520.8	1519.2	1517.5	1515.9
175°	1531.7	1533.3	1533.1	1531.3	1529.4	1527.6	1525.7
177.5°	1536.2	1537.5	1537.4	1535.9	1534.4	1532.9	1531.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2

(END OF REPORT)