

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333731-927

Luminaire Tested: **S125RDIW-S1270D1050U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333731-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6743.7 lumens  
Efficiency: N/A  
Efficacy: 100.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333731-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333731-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	54	49
2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	50	47	46	41
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	71	61	54	49	53	48	44	46	42	39	40	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10561	10561	10561
5°	10585	10466	10529
10°	10506	10368	10368
15°	10380	10158	10075
20°	10221	9864	9745
25°	10033	9576	9365
30°	9801	9238	8944
35°	9563	8891	8472
40°	9340	8528	8008
45°	9070	8122	7501
50°	8799	7681	6974
55°	8483	7260	6411
60°	8169	6748	5807
65°	7795	6154	5115
70°	7370	5410	4409
75°	6780	4561	3666
80°	5973	3582	3080
85°	5039	2927	2749



TEST NUMBER: P333731-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.8	2.3
10°-20°	429.7	6.4
20°-30°	623.1	9.2
30°-40°	710.2	10.5
40°-50°	692.3	10.3
50°-60°	582.7	8.6
60°-70°	408.5	6.1
70°-80°	210.0	3.1
80°-90°	55.3	0.8
90°-100°	69.1	1.0
100°-110°	204.0	3.0
110°-120°	345.5	5.1
120°-130°	454.7	6.7
130°-140°	509.6	7.6
140°-150°	499.4	7.4
150°-160°	419.5	6.2
160°-170°	278.8	4.1
170°-180°	97.6	1.4
0°-30°	1206.6	17.9
0°-40°	1916.8	28.4
0°-60°	3191.8	47.3
0°-90°	3865.5	57.3
90°-120°	618.6	9.2
90°-150°	2082.3	30.9
90°-180°	2878.0	42.7
0°-180°	6743.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1635	1635	1635	1635	1635	
5°	1633	1627	1614	1626	1624	155
15°	1552	1544	1519	1517	1507	437
25°	1408	1388	1344	1328	1314	648
35°	1213	1182	1128	1093	1074	759
45°	993	955	889	842	821	766
55°	753	712	645	591	569	674
65°	510	467	403	355	335	505
75°	272	234	183	157	147	288
85°	68	47	40	38	37	76
90°	1	7	13	17	19	6
95°	52	54	62	67	69	56
105°	183	187	192	196	199	195
115°	346	349	351	350	349	342
125°	505	509	510	509	508	452
135°	657	661	662	662	659	506
145°	795	799	801	801	799	497
155°	910	910	911	914	910	419
165°	990	988	989	992	987	279
175°	1029	1026	1026	1030	1025	98
180°	1031	1031	1031	1031	1031	



TEST NUMBER: P333731-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1638.2	1637.6	1636.9	1636.3	1635.6	1634.2	1632.0	1629.8	1627.6	1625.4	1627.6
5°	1632.8	1631.7	1630.6	1629.5	1628.4	1626.4	1623.3	1620.3	1617.3	1614.3	1617.0
7.5°	1616.8	1615.7	1614.7	1613.6	1612.6	1610.3	1606.6	1603.0	1599.4	1595.8	1597.7
10°	1602.0	1601.1	1600.3	1599.5	1598.6	1596.3	1592.4	1588.6	1584.8	1581.0	1581.8
12.5°	1585.2	1584.1	1583.0	1582.0	1581.0	1577.9	1572.7	1567.6	1562.3	1557.2	1557.8
15°	1552.5	1550.9	1549.3	1547.6	1545.9	1542.2	1536.4	1530.7	1525.0	1519.2	1518.9
17.5°	1515.7	1513.2	1510.7	1508.2	1505.6	1500.7	1493.5	1486.2	1479.0	1471.7	1470.4
20°	1487.1	1484.3	1481.5	1478.8	1476.1	1470.3	1461.6	1452.8	1444.0	1435.2	1433.8
22.5°	1455.5	1452.7	1449.9	1447.2	1444.5	1438.5	1429.3	1420.1	1410.8	1401.6	1398.9
25°	1408.0	1403.9	1399.8	1395.7	1391.5	1384.4	1374.3	1364.1	1353.9	1343.8	1340.2
27.5°	1353.7	1348.7	1343.7	1338.7	1333.7	1325.8	1314.9	1304.0	1293.2	1282.3	1277.3
30°	1314.2	1308.9	1303.7	1298.5	1293.3	1284.9	1273.4	1261.9	1250.3	1238.8	1232.5
32.5°	1275.7	1269.6	1263.5	1257.4	1251.3	1242.3	1230.6	1218.9	1207.0	1195.3	1188.4
35°	1212.9	1206.3	1199.7	1193.1	1186.5	1177.0	1164.7	1152.4	1140.0	1127.7	1119.7
37.5°	1151.4	1143.4	1135.4	1127.4	1119.3	1108.9	1096.2	1083.5	1070.7	1058.0	1048.5
40°	1107.9	1099.6	1091.4	1083.2	1075.0	1064.2	1051.1	1037.9	1024.7	1011.5	1001.2
42.5°	1062.5	1054.0	1045.5	1037.0	1028.6	1017.6	1004.0	990.4	976.8	963.1	953.2
45°	993.0	985.1	977.1	969.2	961.2	949.7	934.5	919.5	904.4	889.3	878.3
47.5°	921.1	912.8	904.4	896.0	887.6	875.8	860.5	845.3	830.1	814.9	803.6
50°	875.7	866.6	857.5	848.5	839.5	827.1	811.4	795.8	780.1	764.5	753.0
52.5°	826.2	817.0	807.7	798.4	789.2	777.1	762.4	747.7	732.8	718.1	705.7
55°	753.4	744.7	735.9	727.1	718.3	706.2	690.9	675.5	660.1	644.8	632.4
57.5°	679.8	670.4	661.0	651.6	642.2	630.2	615.4	600.5	585.7	570.8	558.8
60°	632.4	622.7	613.1	603.6	594.0	581.7	566.9	552.1	537.3	522.4	510.4
62.5°	582.0	572.8	563.6	554.4	545.3	533.2	518.2	503.1	488.1	473.0	461.8
65°	510.1	500.7	491.5	482.1	472.8	460.8	446.3	431.7	417.2	402.7	391.7
67.5°	438.7	429.4	420.0	410.7	401.4	389.8	375.8	361.9	347.9	334.0	323.9
70°	390.3	381.0	371.6	362.3	353.0	341.4	327.7	314.0	300.2	286.5	278.1
72.5°	342.9	333.7	324.6	315.5	306.4	295.4	282.6	269.7	256.9	244.1	236.2
75°	271.7	263.5	255.2	247.0	238.8	228.9	217.4	205.9	194.3	182.8	176.7
77.5°	201.1	194.5	187.9	181.3	174.8	166.8	157.6	148.4	139.2	129.9	125.7
80°	160.6	154.0	147.4	140.8	134.2	127.1	119.4	111.7	104.0	96.3	93.9
82.5°	121.0	115.1	109.2	103.2	97.4	91.7	86.4	81.2	75.9	70.7	69.5
85°	68.0	63.0	58.1	53.1	48.2	45.0	43.6	42.3	40.9	39.5	39.2
87.5°	22.9	21.6	20.4	19.2	17.9	17.3	17.3	17.3	17.3	17.4	17.6
90°	0.8	2.2	3.6	5.1	6.5	7.8	9.1	10.4	11.6	12.8	13.7
92.5°	19.4	20.4	21.4	22.4	23.4	24.7	26.2	27.7	29.3	30.8	32.0
95°	52.2	52.5	52.9	53.2	53.6	54.7	56.5	58.2	60.0	61.8	63.1
97.5°	86.7	86.8	87.0	87.1	87.3	88.6	91.0	93.5	95.9	98.4	99.6
100°	112.4	112.4	112.4	112.4	112.4	113.5	115.8	118.2	120.5	122.8	124.5
102.5°	140.0	140.7	141.4	142.1	142.8	143.8	145.0	146.2	147.3	148.5	150.3
105°	183.0	183.9	184.8	185.7	186.6	187.6	188.6	189.7	190.8	191.9	192.9
107.5°	230.5	231.4	232.3	233.2	234.1	235.0	235.8	236.6	237.4	238.2	238.8
110°	263.2	264.2	265.1	265.9	266.9	267.6	268.1	268.6	269.2	269.7	270.2



TEST NUMBER: P333731-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	296.7	297.1	297.6	298.1	298.5	299.1	299.8	300.5	301.1	301.8	302.1
115°	345.9	346.7	347.4	348.1	348.8	349.4	349.7	350.1	350.4	350.8	350.6
117.5°	395.4	395.7	396.0	396.3	396.7	397.0	397.4	397.7	398.0	398.3	398.5
120°	426.2	427.1	428.0	428.9	429.8	430.3	430.5	430.7	430.9	431.0	431.0
122.5°	459.6	459.9	460.3	460.6	460.9	461.3	461.8	462.2	462.7	463.2	463.0
125°	504.9	506.0	507.0	508.1	509.1	509.8	510.0	510.2	510.3	510.5	510.2
127.5°	553.0	553.7	554.3	554.8	555.5	555.9	556.1	556.3	556.5	556.7	556.6
130°	581.9	582.8	583.8	584.6	585.5	586.1	586.5	586.8	587.2	587.6	587.4
132.5°	610.9	612.3	613.8	615.2	616.7	617.4	617.3	617.3	617.2	617.1	617.0
135°	656.6	657.7	658.7	659.8	660.9	661.5	661.7	661.9	662.0	662.2	662.2
137.5°	699.7	700.7	701.7	702.7	703.8	704.5	704.9	705.3	705.7	706.1	706.2
140°	727.2	728.1	729.0	729.9	730.8	731.5	732.1	732.6	733.1	733.6	734.0
142.5°	754.9	755.6	756.4	757.1	757.9	758.6	759.2	759.9	760.6	761.3	761.4
145°	795.4	796.1	796.9	797.6	798.3	798.9	799.5	800.0	800.6	801.1	801.1
147.5°	833.1	833.5	833.9	834.2	834.6	835.0	835.4	835.8	836.3	836.7	837.2
150°	858.1	857.9	857.7	857.5	857.4	857.6	858.3	859.0	859.8	860.5	860.5
152.5°	878.6	878.8	879.1	879.4	879.6	879.9	880.2	880.4	880.7	881.1	881.5
155°	910.2	910.2	910.2	910.2	910.2	910.3	910.5	910.7	910.9	911.1	911.8
157.5°	938.5	938.1	937.7	937.3	936.9	936.8	937.0	937.2	937.4	937.5	938.3
160°	955.2	954.7	954.1	953.6	953.1	952.9	953.1	953.2	953.4	953.6	954.3
162.5°	969.9	969.6	969.2	968.8	968.4	968.2	968.3	968.3	968.4	968.4	969.2
165°	989.8	989.4	989.0	988.6	988.2	988.2	988.4	988.6	988.7	988.9	989.6
167.5°	1006.4	1005.7	1005.0	1004.2	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.2
170°	1015.4	1014.7	1014.0	1013.3	1012.6	1012.2	1012.2	1012.2	1012.2	1012.2	1013.3
172.5°	1021.8	1021.1	1020.4	1019.7	1019.0	1018.6	1018.6	1018.6	1018.6	1018.6	1019.7
175°	1029.0	1028.3	1027.6	1026.9	1026.2	1025.8	1025.8	1025.8	1025.8	1025.8	1026.9
177.5°	1032.8	1032.1	1031.6	1031.0	1030.5	1030.1	1029.9	1029.8	1029.7	1029.5	1030.4
180°	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4



TEST NUMBER: P333731-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1629.8	1632.0	1634.2	1635.1	1635.0	1634.7	1634.5	1634.3
5°	1619.8	1622.5	1625.2	1626.4	1625.8	1625.2	1624.7	1624.1
7.5°	1599.6	1601.6	1603.5	1604.1	1603.5	1602.9	1602.3	1601.7
10°	1582.5	1583.4	1584.2	1584.2	1583.4	1582.5	1581.8	1581.0
12.5°	1558.5	1559.0	1559.6	1559.3	1558.1	1556.8	1555.5	1554.3
15°	1518.6	1518.4	1518.1	1516.7	1514.3	1511.8	1509.3	1506.8
17.5°	1469.0	1467.6	1466.3	1464.6	1462.5	1460.5	1458.5	1456.4
20°	1432.4	1431.1	1429.7	1427.8	1425.3	1422.8	1420.4	1417.9
22.5°	1396.2	1393.5	1390.8	1388.5	1386.5	1384.4	1382.4	1380.4
25°	1336.6	1333.1	1329.5	1326.2	1323.2	1320.2	1317.2	1314.2
27.5°	1272.3	1267.3	1262.3	1258.4	1255.5	1252.5	1249.6	1246.7
30°	1226.2	1219.9	1213.5	1209.2	1206.7	1204.2	1201.7	1199.3
32.5°	1181.4	1174.4	1167.4	1162.4	1159.3	1156.1	1153.0	1149.9
35°	1111.7	1103.7	1095.8	1089.9	1086.1	1082.2	1078.4	1074.5
37.5°	1038.9	1029.4	1019.8	1013.1	1009.4	1005.7	1002.0	998.2
40°	990.7	980.2	969.9	963.0	959.6	956.4	953.1	949.8
42.5°	943.2	933.2	923.2	915.8	910.9	906.1	901.3	896.4
45°	867.3	856.3	845.3	837.8	833.7	829.6	825.5	821.3
47.5°	792.3	781.0	769.7	761.8	757.2	752.7	748.1	743.5
50°	741.5	729.9	718.4	710.6	706.5	702.3	698.2	694.1
52.5°	693.2	680.9	668.4	660.2	656.1	652.0	647.8	643.7
55°	620.0	607.7	595.3	586.9	582.6	578.1	573.8	569.4
57.5°	546.7	534.6	522.5	514.6	510.6	506.8	502.9	499.0
60°	498.3	486.2	474.1	466.0	461.9	457.8	453.7	449.6
62.5°	450.7	439.4	428.3	420.6	416.5	412.3	408.2	404.1
65°	380.7	369.7	358.7	351.2	347.1	342.9	338.8	334.7
67.5°	313.9	303.8	293.8	287.1	283.8	280.5	277.3	273.9
70°	269.5	261.0	252.5	246.6	243.3	240.0	236.7	233.5
72.5°	228.4	220.5	212.6	207.6	205.4	203.3	201.1	198.8
75°	170.7	164.7	158.7	154.6	152.7	150.8	148.9	146.9
77.5°	121.4	117.2	113.0	110.2	108.8	107.3	105.9	104.5
80°	91.4	89.0	86.4	84.9	84.4	83.8	83.3	82.8
82.5°	68.4	67.2	66.1	65.3	65.0	64.6	64.3	64.0
85°	39.0	38.7	38.4	38.2	37.9	37.6	37.3	37.1
87.5°	17.7	17.9	18.1	18.1	18.1	17.9	17.8	17.7
90°	14.7	15.5	16.4	17.1	17.7	18.2	18.7	19.3
92.5°	33.2	34.4	35.6	36.3	36.7	37.1	37.5	37.9
95°	64.3	65.5	66.8	67.6	68.0	68.3	68.7	69.0
97.5°	100.8	102.0	103.1	103.8	104.0	104.3	104.5	104.6
100°	126.0	127.6	129.2	130.2	130.6	130.9	131.3	131.7
102.5°	152.0	153.8	155.5	156.6	157.1	157.6	158.1	158.6
105°	194.0	195.0	196.1	196.9	197.5	198.0	198.5	199.1
107.5°	239.3	239.9	240.3	240.7	240.6	240.6	240.5	240.5
110°	270.8	271.3	271.9	272.0	271.9	271.6	271.5	271.3





TEST NUMBER: P333731-927

CATALOG NUMBER: S125RDIW-S1270D1050U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	302.3	302.5	302.8	302.8	302.5	302.1	301.8	301.5
115°	350.4	350.2	350.1	349.9	349.7	349.5	349.4	349.2
117.5°	398.5	398.7	398.9	398.5	397.8	397.1	396.4	395.7
120°	431.0	431.0	431.0	430.7	430.0	429.3	428.6	427.9
122.5°	462.9	462.7	462.6	462.2	461.7	461.1	460.5	459.9
125°	509.8	509.5	509.1	508.8	508.7	508.4	508.3	508.1
127.5°	556.3	556.2	556.0	555.8	555.4	555.1	554.7	554.4
130°	587.2	587.0	586.8	586.6	586.2	585.9	585.5	585.2
132.5°	616.7	616.6	616.4	616.1	615.5	615.1	614.6	614.0
135°	662.2	662.2	662.2	661.9	661.2	660.4	659.7	659.0
137.5°	706.5	706.7	706.9	706.5	705.7	704.8	703.9	703.0
140°	734.4	734.7	735.1	734.8	734.0	733.0	732.1	731.3
142.5°	761.7	761.9	762.2	761.8	760.9	760.0	759.1	758.2
145°	801.1	801.1	801.1	800.8	800.3	799.7	799.2	798.7
147.5°	837.6	838.0	838.4	838.0	836.9	835.6	834.4	833.2
150°	860.5	860.5	860.5	860.3	859.9	859.6	859.2	858.9
152.5°	881.9	882.3	882.7	882.6	882.0	881.4	880.7	880.0
155°	912.5	913.2	913.9	913.8	912.9	912.0	911.2	910.2
157.5°	939.0	939.7	940.4	940.2	939.0	937.8	936.6	935.5
160°	955.1	955.8	956.5	956.3	955.5	954.6	953.7	952.8
162.5°	970.1	970.9	971.8	971.7	970.7	969.6	968.6	967.6
165°	990.3	991.0	991.7	991.6	990.5	989.4	988.4	987.3
167.5°	1005.4	1006.4	1007.5	1007.5	1006.4	1005.3	1004.2	1003.1
170°	1014.3	1015.4	1016.4	1016.4	1015.1	1013.9	1012.6	1011.4
172.5°	1020.7	1021.8	1022.9	1022.9	1021.8	1020.6	1019.5	1018.4
175°	1027.9	1029.0	1030.2	1030.0	1028.8	1027.5	1026.3	1025.0
177.5°	1031.3	1032.1	1032.9	1032.8	1031.9	1030.9	1029.9	1028.9
180°	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4

(END OF REPORT)