

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333723-927

Luminaire Tested: **S125RDIW-S1270D470U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333723-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D470U927-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5151.7 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333723-927

CATALOG NUMBER: S125RDIW-S1270D470U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333723-927

CATALOG NUMBER: S125RDIW-S1270D470U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	99	95	92	99	95	91	88	86	83	81	78	76	74	70	69	68	64
2	95	87	81	76	90	83	78	73	76	71	67	69	65	62	62	60	57	54
3	87	77	69	63	82	74	67	61	67	62	57	61	57	53	56	52	49	46
4	80	68	60	54	75	65	58	52	60	54	49	55	50	46	50	46	43	40
5	73	61	53	47	69	59	51	45	54	47	43	49	44	40	45	41	37	35
6	68	55	47	41	64	53	45	40	49	42	37	45	39	35	41	37	33	31
7	63	50	42	36	60	48	41	35	44	38	33	41	35	31	38	33	30	27
8	58	46	38	32	55	44	37	31	41	34	30	38	32	28	35	30	27	24
9	55	42	34	29	52	40	33	28	37	31	27	35	29	25	32	27	24	22
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10561	10561	10561
5°	10585	10466	10529
10°	10506	10368	10368
15°	10380	10158	10075
20°	10221	9864	9745
25°	10033	9576	9365
30°	9801	9238	8944
35°	9563	8891	8472
40°	9340	8528	8008
45°	9070	8122	7501
50°	8799	7681	6974
55°	8483	7260	6411
60°	8169	6748	5807
65°	7795	6154	5115
70°	7370	5410	4409
75°	6780	4561	3666
80°	5973	3582	3080
85°	5039	2927	2749



TEST NUMBER: P333723-927

CATALOG NUMBER: S125RDIW-S1270D470U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.8	3.0
10°-20°	429.7	8.3
20°-30°	623.1	12.1
30°-40°	710.2	13.8
40°-50°	692.3	13.4
50°-60°	582.7	11.3
60°-70°	408.5	7.9
70°-80°	210.0	4.1
80°-90°	54.0	1.0
90°-100°	30.9	0.6
100°-110°	91.2	1.8
110°-120°	154.6	3.0
120°-130°	203.4	3.9
130°-140°	227.9	4.4
140°-150°	223.4	4.3
150°-160°	187.6	3.6
160°-170°	124.7	2.4
170°-180°	43.6	0.8
0°-30°	1206.6	23.4
0°-40°	1916.8	37.2
0°-60°	3191.8	62.0
0°-90°	3864.3	75.0
90°-120°	276.7	5.4
90°-150°	931.5	18.1
90°-180°	1287.0	25.0
0°-180°	5151.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1635	1635	1635	1635	1635	
5°	1633	1627	1614	1626	1624	155
15°	1552	1544	1519	1517	1507	437
25°	1408	1388	1344	1328	1314	648
35°	1213	1182	1128	1093	1074	759
45°	993	955	889	842	821	766
55°	753	712	645	591	569	674
65°	510	467	403	355	335	505
75°	272	234	183	157	147	288
85°	68	47	40	38	37	76
90°	0	3	6	8	9	4
95°	23	24	28	30	31	25
105°	82	84	86	88	89	87
115°	155	156	157	157	156	153
125°	226	228	228	228	227	202
135°	294	296	296	296	295	226
145°	356	357	358	358	357	222
155°	407	407	408	409	407	187
165°	443	442	442	444	442	125
175°	460	459	459	461	458	44
180°	461	461	461	461	461	



TEST NUMBER: P333723-927

CATALOG NUMBER: S125RDIW-S1270D470U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1638.2	1637.6	1636.9	1636.3	1635.6	1634.2	1632.0	1629.8	1627.6	1625.4	1627.6
5°	1632.8	1631.7	1630.6	1629.5	1628.4	1626.4	1623.3	1620.3	1617.3	1614.3	1617.0
7.5°	1616.8	1615.7	1614.7	1613.6	1612.6	1610.3	1606.6	1603.0	1599.4	1595.8	1597.7
10°	1602.0	1601.1	1600.3	1599.5	1598.6	1596.3	1592.4	1588.6	1584.8	1581.0	1581.8
12.5°	1585.2	1584.1	1583.0	1582.0	1581.0	1577.9	1572.7	1567.6	1562.3	1557.2	1557.8
15°	1552.5	1550.9	1549.3	1547.6	1545.9	1542.2	1536.4	1530.7	1525.0	1519.2	1518.9
17.5°	1515.7	1513.2	1510.7	1508.2	1505.6	1500.7	1493.5	1486.2	1479.0	1471.7	1470.4
20°	1487.1	1484.3	1481.5	1478.8	1476.1	1470.3	1461.6	1452.8	1444.0	1435.2	1433.8
22.5°	1455.5	1452.7	1449.9	1447.2	1444.5	1438.5	1429.3	1420.1	1410.8	1401.6	1398.9
25°	1408.0	1403.9	1399.8	1395.7	1391.5	1384.4	1374.3	1364.1	1353.9	1343.8	1340.2
27.5°	1353.7	1348.7	1343.7	1338.7	1333.7	1325.8	1314.9	1304.0	1293.2	1282.3	1277.3
30°	1314.2	1308.9	1303.7	1298.5	1293.3	1284.9	1273.4	1261.9	1250.3	1238.8	1232.5
32.5°	1275.7	1269.6	1263.5	1257.4	1251.3	1242.3	1230.6	1218.9	1207.0	1195.3	1188.4
35°	1212.9	1206.3	1199.7	1193.1	1186.5	1177.0	1164.7	1152.4	1140.0	1127.7	1119.7
37.5°	1151.4	1143.4	1135.4	1127.4	1119.3	1108.9	1096.2	1083.5	1070.7	1058.0	1048.5
40°	1107.9	1099.6	1091.4	1083.2	1075.0	1064.2	1051.1	1037.9	1024.7	1011.5	1001.2
42.5°	1062.5	1054.0	1045.5	1037.0	1028.6	1017.6	1004.0	990.4	976.8	963.1	953.2
45°	993.0	985.1	977.1	969.2	961.2	949.7	934.5	919.5	904.4	889.3	878.3
47.5°	921.1	912.8	904.4	896.0	887.6	875.8	860.5	845.3	830.1	814.9	803.6
50°	875.7	866.6	857.5	848.5	839.5	827.1	811.4	795.8	780.1	764.5	753.0
52.5°	826.2	817.0	807.7	798.4	789.2	777.1	762.4	747.7	732.8	718.1	705.7
55°	753.4	744.7	735.9	727.1	718.3	706.2	690.9	675.5	660.1	644.8	632.4
57.5°	679.8	670.4	661.0	651.6	642.2	630.2	615.4	600.5	585.7	570.8	558.8
60°	632.4	622.7	613.1	603.6	594.0	581.7	566.9	552.1	537.3	522.4	510.4
62.5°	582.0	572.8	563.6	554.4	545.3	533.2	518.2	503.1	488.1	473.0	461.8
65°	510.1	500.7	491.5	482.1	472.8	460.8	446.3	431.7	417.2	402.7	391.7
67.5°	438.7	429.4	420.0	410.7	401.4	389.8	375.8	361.9	347.9	334.0	323.9
70°	390.3	381.0	371.6	362.3	353.0	341.4	327.7	314.0	300.2	286.5	278.1
72.5°	342.9	333.7	324.6	315.5	306.4	295.4	282.6	269.7	256.9	244.1	236.2
75°	271.7	263.5	255.2	247.0	238.8	228.9	217.4	205.9	194.3	182.8	176.7
77.5°	201.1	194.5	187.9	181.3	174.8	166.8	157.6	148.4	139.2	129.9	125.7
80°	160.6	154.0	147.4	140.8	134.2	127.1	119.4	111.7	104.0	96.3	93.9
82.5°	121.0	115.1	109.2	103.2	97.4	91.7	86.4	81.2	75.9	70.7	69.5
85°	68.0	63.0	58.1	53.1	48.2	45.0	43.6	42.3	40.9	39.5	39.2
87.5°	22.8	21.4	20.0	18.5	17.2	16.4	16.3	16.2	16.1	16.0	16.1
90°	0.4	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.8	6.2
92.5°	8.7	9.1	9.6	10.1	10.5	11.0	11.7	12.4	13.1	13.8	14.3
95°	23.4	23.5	23.7	23.8	24.0	24.5	25.3	26.1	26.9	27.6	28.2
97.5°	38.7	38.8	38.9	39.0	39.1	39.6	40.7	41.8	42.9	44.0	44.5
100°	50.3	50.3	50.3	50.3	50.3	50.8	51.8	52.8	53.9	54.9	55.7
102.5°	62.6	62.9	63.3	63.6	63.9	64.3	64.9	65.4	65.9	66.4	67.2
105°	81.8	82.2	82.6	83.0	83.5	83.9	84.4	84.8	85.3	85.8	86.3
107.5°	103.1	103.5	103.9	104.3	104.7	105.1	105.4	105.8	106.2	106.5	106.8
110°	117.8	118.2	118.6	119.0	119.4	119.7	119.9	120.2	120.4	120.6	120.9



TEST NUMBER: P333723-927

CATALOG NUMBER: S125RDIW-S1270D470U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.7	132.9	133.1	133.3	133.6	133.8	134.1	134.4	134.7	135.0	135.1
115°	154.7	155.0	155.4	155.7	156.1	156.3	156.5	156.6	156.8	156.9	156.9
117.5°	176.9	177.0	177.1	177.3	177.4	177.6	177.8	177.8	178.0	178.2	178.2
120°	190.7	191.1	191.5	191.9	192.3	192.5	192.6	192.7	192.7	192.8	192.8
122.5°	205.6	205.7	205.9	206.0	206.1	206.4	206.5	206.8	207.0	207.2	207.1
125°	225.9	226.3	226.8	227.3	227.8	228.1	228.1	228.2	228.3	228.4	228.2
127.5°	247.4	247.6	248.0	248.2	248.5	248.7	248.7	248.8	248.9	249.1	249.0
130°	260.3	260.7	261.1	261.5	261.9	262.2	262.4	262.5	262.7	262.8	262.8
132.5°	273.2	273.9	274.6	275.2	275.8	276.2	276.2	276.1	276.1	276.0	275.9
135°	293.7	294.2	294.7	295.2	295.6	295.9	296.0	296.0	296.1	296.2	296.2
137.5°	312.9	313.4	313.9	314.3	314.8	315.1	315.3	315.4	315.6	315.8	315.9
140°	325.3	325.7	326.1	326.5	326.9	327.3	327.5	327.7	328.0	328.2	328.4
142.5°	337.6	337.9	338.3	338.7	339.0	339.3	339.6	339.9	340.2	340.6	340.6
145°	355.8	356.2	356.5	356.8	357.1	357.4	357.6	357.8	358.1	358.3	358.3
147.5°	372.6	372.8	373.0	373.1	373.4	373.5	373.7	373.9	374.1	374.3	374.5
150°	383.8	383.7	383.7	383.6	383.5	383.7	384.0	384.3	384.6	384.9	384.9
152.5°	393.0	393.2	393.2	393.3	393.5	393.6	393.7	393.9	394.0	394.1	394.3
155°	407.2	407.2	407.2	407.2	407.2	407.2	407.3	407.3	407.4	407.5	407.8
157.5°	419.8	419.6	419.5	419.3	419.1	419.1	419.1	419.2	419.3	419.4	419.7
160°	427.3	427.1	426.7	426.5	426.3	426.2	426.3	426.4	426.4	426.5	426.9
162.5°	433.9	433.7	433.6	433.3	433.2	433.1	433.1	433.1	433.2	433.2	433.6
165°	442.7	442.5	442.4	442.2	442.0	442.0	442.1	442.2	442.3	442.4	442.7
167.5°	450.2	449.9	449.6	449.2	448.9	448.8	448.8	448.8	448.8	448.8	449.2
170°	454.2	453.8	453.5	453.2	452.9	452.7	452.7	452.7	452.7	452.7	453.2
172.5°	457.1	456.8	456.5	456.1	455.8	455.7	455.7	455.7	455.7	455.7	456.1
175°	460.3	459.9	459.6	459.3	459.0	458.8	458.8	458.8	458.8	458.8	459.3
177.5°	461.9	461.7	461.4	461.2	460.9	460.7	460.7	460.7	460.6	460.5	460.9
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P333723-927

CATALOG NUMBER: S125RDIW-S1270D470U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1629.8	1632.0	1634.2	1635.1	1635.0	1634.7	1634.5	1634.3
5°	1619.8	1622.5	1625.2	1626.4	1625.8	1625.2	1624.7	1624.1
7.5°	1599.6	1601.6	1603.5	1604.1	1603.5	1602.9	1602.3	1601.7
10°	1582.5	1583.4	1584.2	1584.2	1583.4	1582.5	1581.8	1581.0
12.5°	1558.5	1559.0	1559.6	1559.3	1558.1	1556.8	1555.5	1554.3
15°	1518.6	1518.4	1518.1	1516.7	1514.3	1511.8	1509.3	1506.8
17.5°	1469.0	1467.6	1466.3	1464.6	1462.5	1460.5	1458.5	1456.4
20°	1432.4	1431.1	1429.7	1427.8	1425.3	1422.8	1420.4	1417.9
22.5°	1396.2	1393.5	1390.8	1388.5	1386.5	1384.4	1382.4	1380.4
25°	1336.6	1333.1	1329.5	1326.2	1323.2	1320.2	1317.2	1314.2
27.5°	1272.3	1267.3	1262.3	1258.4	1255.5	1252.5	1249.6	1246.7
30°	1226.2	1219.9	1213.5	1209.2	1206.7	1204.2	1201.7	1199.3
32.5°	1181.4	1174.4	1167.4	1162.4	1159.3	1156.1	1153.0	1149.9
35°	1111.7	1103.7	1095.8	1089.9	1086.1	1082.2	1078.4	1074.5
37.5°	1038.9	1029.4	1019.8	1013.1	1009.4	1005.7	1002.0	998.2
40°	990.7	980.2	969.9	963.0	959.6	956.4	953.1	949.8
42.5°	943.2	933.2	923.2	915.8	910.9	906.1	901.3	896.4
45°	867.3	856.3	845.3	837.8	833.7	829.6	825.5	821.3
47.5°	792.3	781.0	769.7	761.8	757.2	752.7	748.1	743.5
50°	741.5	729.9	718.4	710.6	706.5	702.3	698.2	694.1
52.5°	693.2	680.9	668.4	660.2	656.1	652.0	647.8	643.7
55°	620.0	607.7	595.3	586.9	582.6	578.1	573.8	569.4
57.5°	546.7	534.6	522.5	514.6	510.6	506.8	502.9	499.0
60°	498.3	486.2	474.1	466.0	461.9	457.8	453.7	449.6
62.5°	450.7	439.4	428.3	420.6	416.5	412.3	408.2	404.1
65°	380.7	369.7	358.7	351.2	347.1	342.9	338.8	334.7
67.5°	313.9	303.8	293.8	287.1	283.8	280.5	277.3	273.9
70°	269.5	261.0	252.5	246.6	243.3	240.0	236.7	233.5
72.5°	228.4	220.5	212.6	207.6	205.4	203.3	201.1	198.8
75°	170.7	164.7	158.7	154.6	152.7	150.8	148.9	146.9
77.5°	121.4	117.2	113.0	110.2	108.8	107.3	105.9	104.5
80°	91.4	89.0	86.4	84.9	84.4	83.8	83.3	82.8
82.5°	68.4	67.2	66.1	65.3	65.0	64.6	64.3	64.0
85°	39.0	38.7	38.4	38.2	37.9	37.6	37.3	37.1
87.5°	16.2	16.2	16.3	16.2	16.1	15.9	15.8	15.5
90°	6.6	7.0	7.4	7.7	7.9	8.2	8.4	8.6
92.5°	14.8	15.4	15.9	16.2	16.4	16.6	16.8	17.0
95°	28.8	29.3	29.9	30.3	30.4	30.6	30.7	30.9
97.5°	45.1	45.6	46.1	46.4	46.5	46.7	46.7	46.8
100°	56.4	57.1	57.8	58.2	58.4	58.5	58.7	58.9
102.5°	68.0	68.8	69.6	70.0	70.3	70.5	70.7	71.0
105°	86.7	87.2	87.7	88.1	88.3	88.6	88.8	89.0
107.5°	107.0	107.3	107.5	107.7	107.7	107.6	107.6	107.6
110°	121.1	121.4	121.6	121.7	121.6	121.5	121.4	121.4





TEST NUMBER: P333723-927

CATALOG NUMBER: S125RDIW-S1270D470U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.2	135.3	135.5	135.5	135.3	135.1	135.0	134.8
115°	156.8	156.7	156.6	156.5	156.5	156.4	156.3	156.2
117.5°	178.3	178.3	178.4	178.3	178.0	177.7	177.3	177.0
120°	192.8	192.8	192.8	192.7	192.3	192.0	191.7	191.4
122.5°	207.1	207.0	206.9	206.8	206.5	206.3	206.0	205.7
125°	228.1	227.9	227.8	227.6	227.5	227.4	227.4	227.3
127.5°	248.9	248.8	248.7	248.6	248.4	248.3	248.1	248.0
130°	262.7	262.6	262.5	262.4	262.2	262.1	261.9	261.7
132.5°	275.8	275.8	275.7	275.6	275.4	275.1	274.9	274.6
135°	296.2	296.2	296.2	296.0	295.7	295.4	295.1	294.8
137.5°	316.0	316.1	316.2	316.1	315.7	315.3	314.8	314.4
140°	328.5	328.7	328.8	328.7	328.3	327.9	327.5	327.1
142.5°	340.7	340.8	340.9	340.7	340.3	339.9	339.5	339.1
145°	358.3	358.3	358.3	358.2	358.0	357.7	357.5	357.3
147.5°	374.6	374.9	375.0	374.9	374.3	373.8	373.2	372.7
150°	384.9	384.9	384.9	384.8	384.7	384.5	384.4	384.2
152.5°	394.5	394.7	394.8	394.8	394.5	394.3	394.0	393.6
155°	408.1	408.4	408.8	408.8	408.4	408.0	407.6	407.2
157.5°	420.0	420.3	420.6	420.6	420.0	419.5	419.0	418.4
160°	427.2	427.5	427.9	427.8	427.4	427.0	426.6	426.2
162.5°	434.0	434.3	434.7	434.7	434.2	433.7	433.2	432.8
165°	443.0	443.3	443.6	443.5	443.1	442.6	442.1	441.6
167.5°	449.7	450.2	450.7	450.7	450.1	449.6	449.2	448.7
170°	453.7	454.2	454.7	454.6	454.1	453.5	453.0	452.4
172.5°	456.6	457.1	457.6	457.6	457.0	456.5	456.1	455.6
175°	459.8	460.3	460.8	460.7	460.2	459.6	459.1	458.5
177.5°	461.3	461.7	462.1	462.0	461.6	461.1	460.7	460.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)