

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333656-927

Luminaire Tested: **S125RDIW-S375D1560U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333656-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1560U927-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6098.7 lumens  
Efficiency: N/A  
Efficacy: 114.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	25	24	24	16
2	83	76	70	65	73	67	63	59	51	48	45	36	34	32	22	21	20	14
3	76	67	60	55	67	59	54	49	45	41	38	32	29	27	19	18	17	12
4	69	59	52	46	61	52	46	41	40	36	32	28	26	23	17	16	15	10
5	63	52	45	39	56	47	40	35	36	31	28	25	22	20	16	14	13	9
6	58	47	39	34	51	42	35	31	32	27	24	23	20	18	14	13	11	8
7	54	42	35	29	47	38	31	27	29	24	21	21	18	16	13	11	10	7
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	10	9	6
9	46	35	28	23	41	31	25	21	24	19	16	17	14	12	11	9	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.8	0.7
10°-20°	125.3	2.1
20°-30°	198.7	3.3
30°-40°	239.6	3.9
40°-50°	214.0	3.5
50°-60°	164.1	2.7
60°-70°	106.6	1.7
70°-80°	51.8	0.9
80°-90°	15.7	0.3
90°-100°	58.5	1.0
100°-110°	360.3	5.9
110°-120°	653.4	10.7
120°-130°	838.6	13.8
130°-140°	902.0	14.8
140°-150°	846.7	13.9
150°-160°	684.9	11.2
160°-170°	442.9	7.3
170°-180°	152.8	2.5
0°-30°	366.8	6.0
0°-40°	606.3	9.9
0°-60°	984.4	16.1
0°-90°	1158.6	19.0
90°-120°	1072.2	17.6
90°-150°	3659.5	60.0
90°-180°	4940.0	81.0
0°-180°	6098.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	29	1	29	1	29	13
95°	25	68	25	68	25	21
105°	354	351	354	351	354	320
115°	654	658	654	658	654	649
125°	936	936	936	936	936	833
135°	1163	1167	1163	1167	1163	897
145°	1350	1354	1350	1354	1350	843
155°	1480	1491	1480	1491	1480	682
165°	1565	1573	1565	1573	1565	442
175°	1602	1609	1602	1609	1602	152
180°	1609	1609	1609	1609	1609	



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	9.0	8.6	8.3	8.2	8.2	8.2	7.8	7.4	7.1	6.9	6.7
90°	28.6	27.8	27.0	26.2	25.4	24.4	23.1	21.7	20.4	19.1	17.2
92.5°	26.7	26.4	26.0	25.6	25.2	24.4	23.1	21.7	20.4	19.1	17.4
95°	25.0	25.0	25.0	25.0	25.0	24.4	23.1	21.7	20.4	19.1	29.2
97.5°	25.0	25.0	25.0	25.0	25.0	28.8	36.3	43.7	51.2	58.7	78.6
100°	25.0	26.1	27.2	28.2	29.3	49.6	89.0	128.5	168.0	207.5	206.4
102.5°	150.0	168.0	186.1	204.1	222.1	234.9	242.3	249.8	257.3	264.7	264.1
105°	354.2	354.4	354.7	355.0	355.2	355.4	355.4	355.4	355.4	355.4	355.4
107.5°	446.5	447.3	448.1	448.9	449.6	450.0	450.0	450.0	449.9	449.8	449.3
110°	510.4	510.2	509.8	509.6	509.4	509.6	510.4	511.2	512.0	512.8	512.2



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	567.6	568.0	568.4	568.8	569.1	569.8	570.8	571.8	572.8	573.9	573.5
115°	653.5	655.1	656.6	658.3	659.9	661.2	662.3	663.3	664.3	665.4	665.2
117.5°	745.0	745.8	746.5	747.2	747.8	748.8	750.3	751.6	753.0	754.4	753.4
120°	801.4	802.7	804.0	805.3	806.7	807.6	808.1	808.7	809.2	809.7	808.9
122.5°	854.8	856.3	857.9	859.4	860.9	862.0	862.5	863.0	863.6	864.1	863.7
125°	936.1	936.9	937.7	938.5	939.3	940.2	941.3	942.4	943.4	944.4	944.4
127.5°	1004.6	1006.5	1008.5	1010.4	1012.4	1013.7	1014.3	1014.9	1015.4	1016.1	1016.2
130°	1054.2	1055.5	1056.9	1058.2	1059.5	1060.6	1061.4	1062.2	1063.0	1063.7	1063.4
132.5°	1099.9	1101.3	1102.6	1104.0	1105.3	1106.0	1106.2	1106.4	1106.5	1106.7	1107.2
135°	1162.7	1164.3	1165.9	1167.4	1169.0	1170.1	1170.7	1171.2	1171.7	1172.3	1172.7
137.5°	1225.7	1227.0	1228.4	1229.8	1231.2	1231.8	1231.7	1231.6	1231.5	1231.4	1231.8
140°	1262.9	1264.5	1266.1	1267.7	1269.2	1269.8	1269.2	1268.7	1268.2	1267.7	1267.9
142.5°	1298.1	1299.7	1301.3	1302.9	1304.6	1305.3	1305.2	1305.0	1305.0	1304.9	1304.5
145°	1350.0	1351.5	1353.1	1354.7	1356.3	1356.9	1356.7	1356.5	1356.1	1355.9	1355.9
147.5°	1392.7	1394.6	1396.5	1398.4	1400.3	1401.1	1400.7	1400.4	1400.1	1399.8	1399.5
150°	1420.3	1422.4	1424.5	1426.6	1428.8	1429.6	1429.0	1428.5	1428.0	1427.4	1426.9
152.5°	1446.0	1448.0	1449.9	1451.8	1453.7	1454.4	1453.8	1453.3	1452.8	1452.2	1451.8
155°	1479.9	1482.0	1484.2	1486.3	1488.4	1489.1	1488.3	1487.5	1486.7	1485.9	1485.3
157.5°	1508.3	1510.4	1512.5	1514.7	1516.8	1517.4	1516.6	1515.7	1514.9	1514.0	1513.9
160°	1526.5	1528.5	1530.7	1532.8	1534.9	1535.4	1534.4	1533.3	1532.2	1531.2	1530.9
162.5°	1542.6	1545.0	1547.3	1549.7	1552.0	1552.4	1550.9	1549.4	1547.9	1546.4	1546.2
165°	1564.6	1566.7	1568.8	1571.0	1573.0	1573.4	1571.8	1570.1	1568.5	1566.9	1566.7
167.5°	1579.8	1582.2	1584.6	1587.0	1589.4	1589.6	1587.7	1585.8	1583.9	1582.0	1581.8
170°	1588.4	1590.8	1593.2	1595.6	1598.0	1598.1	1596.0	1593.9	1591.7	1589.6	1589.4
172.5°	1594.2	1596.6	1598.9	1601.3	1603.7	1603.9	1602.0	1600.1	1598.2	1596.3	1595.9
175°	1601.6	1603.9	1606.3	1608.7	1611.1	1611.2	1609.1	1606.9	1604.9	1602.7	1602.5
177.5°	1605.8	1607.5	1609.2	1610.9	1612.6	1612.7	1611.2	1609.8	1608.3	1606.8	1606.5
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	6.4	6.1	5.9	5.5	4.9	5.1	5.2	4.9	5.1	5.1	5.3
90°	15.4	13.5	11.6	9.7	7.5	5.5	3.3	1.2	3.3	5.5	7.5
92.5°	15.8	14.2	12.5	12.4	13.9	15.4	16.9	18.4	16.9	15.4	13.9
95°	39.2	49.3	59.3	64.8	65.6	66.4	67.2	68.0	67.2	66.4	65.6
97.5°	98.5	118.4	138.4	147.7	146.2	144.7	143.3	141.9	143.3	144.7	146.2
100°	205.4	204.3	203.3	202.3	201.5	200.7	199.9	199.2	199.9	200.7	201.5
102.5°	263.5	262.8	262.2	261.3	260.4	259.4	258.3	257.4	258.3	259.4	260.4
105°	355.4	355.4	355.4	354.8	353.8	352.8	351.6	350.6	351.6	352.8	353.8
107.5°	448.8	448.2	447.7	447.4	447.4	447.4	447.4	447.4	447.4	447.4	447.4
110°	511.7	511.2	510.6	510.4	510.4	510.4	510.4	510.4	510.4	510.4	510.4





TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	573.2	572.9	572.6	572.1	571.5	570.8	570.2	569.6	570.2	570.8	571.5
115°	664.9	664.6	664.3	663.5	662.3	660.9	659.6	658.3	659.6	660.9	662.3
117.5°	752.3	751.4	750.4	749.9	750.0	750.0	750.0	750.1	750.0	750.0	750.0
120°	808.1	807.3	806.5	806.3	806.5	806.8	807.1	807.3	807.1	806.8	806.5
122.5°	863.3	863.0	862.6	861.9	860.9	859.9	858.9	857.9	858.9	859.9	860.9
125°	944.4	944.4	944.4	943.6	941.7	939.8	937.9	936.1	937.9	939.8	941.7
127.5°	1016.4	1016.5	1016.7	1016.1	1014.8	1013.4	1012.1	1010.7	1012.1	1013.4	1014.8
130°	1063.2	1063.0	1062.6	1061.8	1060.6	1059.2	1057.9	1056.5	1057.9	1059.2	1060.6
132.5°	1107.8	1108.4	1109.0	1108.5	1107.0	1105.4	1103.9	1102.3	1103.9	1105.4	1107.0
135°	1173.3	1173.9	1174.3	1173.9	1172.3	1170.7	1169.0	1167.4	1169.0	1170.7	1172.3
137.5°	1232.3	1232.8	1233.3	1232.9	1231.4	1230.1	1228.7	1227.3	1228.7	1230.1	1231.4
140°	1268.2	1268.4	1268.7	1268.6	1268.0	1267.5	1267.0	1266.5	1267.0	1267.5	1268.0
142.5°	1304.1	1303.8	1303.4	1303.0	1302.7	1302.3	1302.0	1301.7	1302.0	1302.3	1302.7
145°	1355.9	1355.9	1355.9	1355.7	1355.1	1354.6	1354.0	1353.5	1354.0	1354.6	1355.1
147.5°	1399.2	1398.8	1398.5	1398.4	1398.5	1398.6	1398.7	1398.8	1398.7	1398.6	1398.5
150°	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1426.9	1426.4	1425.8
152.5°	1451.2	1450.6	1450.1	1450.4	1451.6	1452.8	1454.0	1455.1	1454.0	1452.8	1451.6
155°	1484.8	1484.3	1483.8	1484.3	1485.9	1487.5	1489.1	1490.6	1489.1	1487.5	1485.9
157.5°	1513.9	1513.9	1513.8	1514.3	1515.2	1516.2	1517.1	1518.1	1517.1	1516.2	1515.2
160°	1530.7	1530.4	1530.1	1530.8	1532.4	1534.0	1535.6	1537.2	1535.6	1534.0	1532.4
162.5°	1545.9	1545.6	1545.4	1546.0	1547.6	1549.3	1550.9	1552.4	1550.9	1549.3	1547.6
165°	1566.5	1566.1	1565.9	1566.5	1568.1	1569.7	1571.4	1573.0	1571.4	1569.7	1568.1
167.5°	1581.4	1581.2	1581.0	1581.6	1583.3	1584.9	1586.6	1588.2	1586.6	1584.9	1583.3
170°	1589.1	1588.8	1588.6	1589.4	1591.2	1593.1	1594.9	1596.8	1594.9	1593.1	1591.2
172.5°	1595.4	1594.9	1594.4	1595.1	1597.0	1598.8	1600.7	1602.5	1600.7	1598.8	1597.0
175°	1602.2	1602.0	1601.7	1602.3	1603.9	1605.5	1607.1	1608.7	1607.1	1605.5	1603.9
177.5°	1606.4	1606.1	1605.9	1606.5	1607.7	1609.0	1610.3	1611.5	1610.3	1609.0	1607.7
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	5.6	6.0	6.2	6.9	6.8	7.4	7.6	7.7	8.0	8.2	8.3
90°	9.7	11.6	13.5	15.4	17.2	19.1	20.4	21.7	23.1	24.4	25.4
92.5°	12.4	12.5	14.2	15.8	17.4	19.1	20.4	21.7	23.1	24.4	25.2
95°	64.8	59.3	49.3	39.2	29.2	19.1	20.4	21.7	23.1	24.4	25.0
97.5°	147.7	138.4	118.4	98.5	78.6	58.7	51.2	43.7	36.3	28.8	25.0
100°	202.3	203.3	204.3	205.4	206.4	207.5	168.0	128.5	89.0	49.6	29.3
102.5°	261.3	262.2	262.8	263.5	264.1	264.7	257.3	249.8	242.3	234.9	222.1
105°	354.8	355.4	355.4	355.4	355.4	355.4	355.4	355.4	355.4	355.4	355.2
107.5°	447.4	447.7	448.2	448.8	449.3	449.8	449.9	450.0	450.0	450.0	449.6
110°	510.4	510.6	511.2	511.7	512.2	512.8	512.0	511.2	510.4	509.6	509.4



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	572.1	572.6	572.9	573.2	573.5	573.9	572.8	571.8	570.8	569.8	569.1
115°	663.5	664.3	664.6	664.9	665.2	665.4	664.3	663.3	662.3	661.2	659.9
117.5°	749.9	750.4	751.4	752.3	753.4	754.4	753.0	751.6	750.3	748.8	747.8
120°	806.3	806.5	807.3	808.1	808.9	809.7	809.2	808.7	808.1	807.6	806.7
122.5°	861.9	862.6	863.0	863.3	863.7	864.1	863.6	863.0	862.5	862.0	860.9
125°	943.6	944.4	944.4	944.4	944.4	944.4	943.4	942.4	941.3	940.2	939.3
127.5°	1016.1	1016.7	1016.5	1016.4	1016.2	1016.1	1015.4	1014.9	1014.3	1013.7	1012.4
130°	1061.8	1062.6	1063.0	1063.2	1063.4	1063.7	1063.0	1062.2	1061.4	1060.6	1059.5
132.5°	1108.5	1109.0	1108.4	1107.8	1107.2	1106.7	1106.5	1106.4	1106.2	1106.0	1105.3
135°	1173.9	1174.3	1173.9	1173.3	1172.7	1172.3	1171.7	1171.2	1170.7	1170.1	1169.0
137.5°	1232.9	1233.3	1232.8	1232.3	1231.8	1231.4	1231.5	1231.6	1231.7	1231.8	1231.2
140°	1268.6	1268.7	1268.4	1268.2	1267.9	1267.7	1268.2	1268.7	1269.2	1269.8	1269.2
142.5°	1303.0	1303.4	1303.8	1304.1	1304.5	1304.9	1305.0	1305.0	1305.2	1305.3	1304.6
145°	1355.7	1355.9	1355.9	1355.9	1355.9	1355.9	1356.1	1356.5	1356.7	1356.9	1356.3
147.5°	1398.4	1398.5	1398.8	1399.2	1399.5	1399.8	1400.1	1400.4	1400.7	1401.1	1400.3
150°	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1428.0	1428.5	1429.0	1429.6	1428.8
152.5°	1450.4	1450.1	1450.6	1451.2	1451.8	1452.2	1452.8	1453.3	1453.8	1454.4	1453.7
155°	1484.3	1483.8	1484.3	1484.8	1485.3	1485.9	1486.7	1487.5	1488.3	1489.1	1488.4
157.5°	1514.3	1513.8	1513.9	1513.9	1513.9	1514.0	1514.9	1515.7	1516.6	1517.4	1516.8
160°	1530.8	1530.1	1530.4	1530.7	1530.9	1531.2	1532.2	1533.3	1534.4	1535.4	1534.9
162.5°	1546.0	1545.4	1545.6	1545.9	1546.2	1546.4	1547.9	1549.4	1550.9	1552.4	1552.0
165°	1566.5	1565.9	1566.1	1566.5	1566.7	1566.9	1568.5	1570.1	1571.8	1573.4	1573.0
167.5°	1581.6	1581.0	1581.2	1581.4	1581.8	1582.0	1583.9	1585.8	1587.7	1589.6	1589.4
170°	1589.4	1588.6	1588.8	1589.1	1589.4	1589.6	1591.7	1593.9	1596.0	1598.1	1598.0
172.5°	1595.1	1594.4	1594.9	1595.4	1595.9	1596.3	1598.2	1600.1	1602.0	1603.9	1603.7
175°	1602.3	1601.7	1602.0	1602.2	1602.5	1602.7	1604.9	1606.9	1609.1	1611.2	1611.1
177.5°	1606.5	1605.9	1606.1	1606.4	1606.5	1606.8	1608.3	1609.8	1611.2	1612.7	1612.6
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	8.6	8.6	8.8	9.0	8.8	8.6	8.6	8.3	8.2	8.0	7.7
90°	26.2	27.0	27.8	28.6	27.8	27.0	26.2	25.4	24.4	23.1	21.7
92.5°	25.6	26.0	26.4	26.7	26.4	26.0	25.6	25.2	24.4	23.1	21.7
95°	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	24.4	23.1	21.7
97.5°	25.0	25.0	25.0	25.0	25.0	25.0	25.0	25.0	28.8	36.3	43.7
100°	28.2	27.2	26.1	25.0	26.1	27.2	28.2	29.3	49.6	89.0	128.5
102.5°	204.1	186.1	168.0	150.0	168.0	186.1	204.1	222.1	234.9	242.3	249.8
105°	355.0	354.7	354.4	354.2	354.4	354.7	355.0	355.2	355.4	355.4	355.4
107.5°	448.9	448.1	447.3	446.5	447.3	448.1	448.9	449.6	450.0	450.0	450.0
110°	509.6	509.8	510.2	510.4	510.2	509.8	509.6	509.4	509.6	510.4	511.2



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	568.8	568.4	568.0	567.6	568.0	568.4	568.8	569.1	569.8	570.8	571.8
115°	658.3	656.6	655.1	653.5	655.1	656.6	658.3	659.9	661.2	662.3	663.3
117.5°	747.2	746.5	745.8	745.0	745.8	746.5	747.2	747.8	748.8	750.3	751.6
120°	805.3	804.0	802.7	801.4	802.7	804.0	805.3	806.7	807.6	808.1	808.7
122.5°	859.4	857.9	856.3	854.8	856.3	857.9	859.4	860.9	862.0	862.5	863.0
125°	938.5	937.7	936.9	936.1	936.9	937.7	938.5	939.3	940.2	941.3	942.4
127.5°	1010.4	1008.5	1006.5	1004.6	1006.5	1008.5	1010.4	1012.4	1013.7	1014.3	1014.9
130°	1058.2	1056.9	1055.5	1054.2	1055.5	1056.9	1058.2	1059.5	1060.6	1061.4	1062.2
132.5°	1104.0	1102.6	1101.3	1099.9	1101.3	1102.6	1104.0	1105.3	1106.0	1106.2	1106.4
135°	1167.4	1165.9	1164.3	1162.7	1164.3	1165.9	1167.4	1169.0	1170.1	1170.7	1171.2
137.5°	1229.8	1228.4	1227.0	1225.7	1227.0	1228.4	1229.8	1231.2	1231.8	1231.7	1231.6
140°	1267.7	1266.1	1264.5	1262.9	1264.5	1266.1	1267.7	1269.2	1269.8	1269.2	1268.7
142.5°	1302.9	1301.3	1299.7	1298.1	1299.7	1301.3	1302.9	1304.6	1305.3	1305.2	1305.0
145°	1354.7	1353.1	1351.5	1350.0	1351.5	1353.1	1354.7	1356.3	1356.9	1356.7	1356.5
147.5°	1398.4	1396.5	1394.6	1392.7	1394.6	1396.5	1398.4	1400.3	1401.1	1400.7	1400.4
150°	1426.6	1424.5	1422.4	1420.3	1422.4	1424.5	1426.6	1428.8	1429.6	1429.0	1428.5
152.5°	1451.8	1449.9	1448.0	1446.0	1448.0	1449.9	1451.8	1453.7	1454.4	1453.8	1453.3
155°	1486.3	1484.2	1482.0	1479.9	1482.0	1484.2	1486.3	1488.4	1489.1	1488.3	1487.5
157.5°	1514.7	1512.5	1510.4	1508.3	1510.4	1512.5	1514.7	1516.8	1517.4	1516.6	1515.7
160°	1532.8	1530.7	1528.5	1526.5	1528.5	1530.7	1532.8	1534.9	1535.4	1534.4	1533.3
162.5°	1549.7	1547.3	1545.0	1542.6	1545.0	1547.3	1549.7	1552.0	1552.4	1550.9	1549.4
165°	1571.0	1568.8	1566.7	1564.6	1566.7	1568.8	1571.0	1573.0	1573.4	1571.8	1570.1
167.5°	1587.0	1584.6	1582.2	1579.8	1582.2	1584.6	1587.0	1589.4	1589.6	1587.7	1585.8
170°	1595.6	1593.2	1590.8	1588.4	1590.8	1593.2	1595.6	1598.0	1598.1	1596.0	1593.9
172.5°	1601.3	1598.9	1596.6	1594.2	1596.6	1598.9	1601.3	1603.7	1603.9	1602.0	1600.1
175°	1608.7	1606.3	1603.9	1601.6	1603.9	1606.3	1608.7	1611.1	1611.2	1609.1	1606.9
177.5°	1610.9	1609.2	1607.5	1605.8	1607.5	1609.2	1610.9	1612.6	1612.7	1611.2	1609.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	7.6	7.4	6.8	6.9	6.2	6.0	5.6	5.3	5.1	5.1	4.9
90°	20.4	19.1	17.2	15.4	13.5	11.6	9.7	7.5	5.5	3.3	1.2
92.5°	20.4	19.1	17.4	15.8	14.2	12.5	12.4	13.9	15.4	16.9	18.4
95°	20.4	19.1	29.2	39.2	49.3	59.3	64.8	65.6	66.4	67.2	68.0
97.5°	51.2	58.7	78.6	98.5	118.4	138.4	147.7	146.2	144.7	143.3	141.9
100°	168.0	207.5	206.4	205.4	204.3	203.3	202.3	201.5	200.7	199.9	199.2
102.5°	257.3	264.7	264.1	263.5	262.8	262.2	261.3	260.4	259.4	258.3	257.4
105°	355.4	355.4	355.4	355.4	355.4	355.4	354.8	353.8	352.8	351.6	350.6
107.5°	449.9	449.8	449.3	448.8	448.2	447.7	447.4	447.4	447.4	447.4	447.4
110°	512.0	512.8	512.2	511.7	511.2	510.6	510.4	510.4	510.4	510.4	510.4



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	572.8	573.9	573.5	573.2	572.9	572.6	572.1	571.5	570.8	570.2	569.6
115°	664.3	665.4	665.2	664.9	664.6	664.3	663.5	662.3	660.9	659.6	658.3
117.5°	753.0	754.4	753.4	752.3	751.4	750.4	749.9	750.0	750.0	750.0	750.1
120°	809.2	809.7	808.9	808.1	807.3	806.5	806.3	806.5	806.8	807.1	807.3
122.5°	863.6	864.1	863.7	863.3	863.0	862.6	861.9	860.9	859.9	858.9	857.9
125°	943.4	944.4	944.4	944.4	944.4	944.4	943.6	941.7	939.8	937.9	936.1
127.5°	1015.4	1016.1	1016.2	1016.4	1016.5	1016.7	1016.1	1014.8	1013.4	1012.1	1010.7
130°	1063.0	1063.7	1063.4	1063.2	1063.0	1062.6	1061.8	1060.6	1059.2	1057.9	1056.5
132.5°	1106.5	1106.7	1107.2	1107.8	1108.4	1109.0	1108.5	1107.0	1105.4	1103.9	1102.3
135°	1171.7	1172.3	1172.7	1173.3	1173.9	1174.3	1173.9	1172.3	1170.7	1169.0	1167.4
137.5°	1231.5	1231.4	1231.8	1232.3	1232.8	1233.3	1232.9	1231.4	1230.1	1228.7	1227.3
140°	1268.2	1267.7	1267.9	1268.2	1268.4	1268.7	1268.6	1268.0	1267.5	1267.0	1266.5
142.5°	1305.0	1304.9	1304.5	1304.1	1303.8	1303.4	1303.0	1302.7	1302.3	1302.0	1301.7
145°	1356.1	1355.9	1355.9	1355.9	1355.9	1355.9	1355.7	1355.1	1354.6	1354.0	1353.5
147.5°	1400.1	1399.8	1399.5	1399.2	1398.8	1398.5	1398.4	1398.5	1398.6	1398.7	1398.8
150°	1428.0	1427.4	1426.9	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4
152.5°	1452.8	1452.2	1451.8	1451.2	1450.6	1450.1	1450.4	1451.6	1452.8	1454.0	1455.1
155°	1486.7	1485.9	1485.3	1484.8	1484.3	1483.8	1484.3	1485.9	1487.5	1489.1	1490.6
157.5°	1514.9	1514.0	1513.9	1513.9	1513.9	1513.8	1514.3	1515.2	1516.2	1517.1	1518.1
160°	1532.2	1531.2	1530.9	1530.7	1530.4	1530.1	1530.8	1532.4	1534.0	1535.6	1537.2
162.5°	1547.9	1546.4	1546.2	1545.9	1545.6	1545.4	1546.0	1547.6	1549.3	1550.9	1552.4
165°	1568.5	1566.9	1566.7	1566.5	1566.1	1565.9	1566.5	1568.1	1569.7	1571.4	1573.0
167.5°	1583.9	1582.0	1581.8	1581.4	1581.2	1581.0	1581.6	1583.3	1584.9	1586.6	1588.2
170°	1591.7	1589.6	1589.4	1589.1	1588.8	1588.6	1589.4	1591.2	1593.1	1594.9	1596.8
172.5°	1598.2	1596.3	1595.9	1595.4	1594.9	1594.4	1595.1	1597.0	1598.8	1600.7	1602.5
175°	1604.9	1602.7	1602.5	1602.2	1602.0	1601.7	1602.3	1603.9	1605.5	1607.1	1608.7
177.5°	1608.3	1606.8	1606.5	1606.4	1606.1	1605.9	1606.5	1607.7	1609.0	1610.3	1611.5
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	5.2	5.1	4.9	5.5	5.9	6.1	6.4	6.7	6.9	7.1	7.4
90°	3.3	5.5	7.5	9.7	11.6	13.5	15.4	17.2	19.1	20.4	21.7
92.5°	16.9	15.4	13.9	12.4	12.5	14.2	15.8	17.4	19.1	20.4	21.7
95°	67.2	66.4	65.6	64.8	59.3	49.3	39.2	29.2	19.1	20.4	21.7
97.5°	143.3	144.7	146.2	147.7	138.4	118.4	98.5	78.6	58.7	51.2	43.7
100°	199.9	200.7	201.5	202.3	203.3	204.3	205.4	206.4	207.5	168.0	128.5
102.5°	258.3	259.4	260.4	261.3	262.2	262.8	263.5	264.1	264.7	257.3	249.8
105°	351.6	352.8	353.8	354.8	355.4	355.4	355.4	355.4	355.4	355.4	355.4
107.5°	447.4	447.4	447.4	447.4	447.7	448.2	448.8	449.3	449.8	449.9	450.0
110°	510.4	510.4	510.4	510.4	510.6	511.2	511.7	512.2	512.8	512.0	511.2





TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	570.2	570.8	571.5	572.1	572.6	572.9	573.2	573.5	573.9	572.8	571.8
115°	659.6	660.9	662.3	663.5	664.3	664.6	664.9	665.2	665.4	664.3	663.3
117.5°	750.0	750.0	750.0	749.9	750.4	751.4	752.3	753.4	754.4	753.0	751.6
120°	807.1	806.8	806.5	806.3	806.5	807.3	808.1	808.9	809.7	809.2	808.7
122.5°	858.9	859.9	860.9	861.9	862.6	863.0	863.3	863.7	864.1	863.6	863.0
125°	937.9	939.8	941.7	943.6	944.4	944.4	944.4	944.4	944.4	943.4	942.4
127.5°	1012.1	1013.4	1014.8	1016.1	1016.7	1016.5	1016.4	1016.2	1016.1	1015.4	1014.9
130°	1057.9	1059.2	1060.6	1061.8	1062.6	1063.0	1063.2	1063.4	1063.7	1063.0	1062.2
132.5°	1103.9	1105.4	1107.0	1108.5	1109.0	1108.4	1107.8	1107.2	1106.7	1106.5	1106.4
135°	1169.0	1170.7	1172.3	1173.9	1174.3	1173.9	1173.3	1172.7	1172.3	1171.7	1171.2
137.5°	1228.7	1230.1	1231.4	1232.9	1233.3	1232.8	1232.3	1231.8	1231.4	1231.5	1231.6
140°	1267.0	1267.5	1268.0	1268.6	1268.7	1268.4	1268.2	1267.9	1267.7	1268.2	1268.7
142.5°	1302.0	1302.3	1302.7	1303.0	1303.4	1303.8	1304.1	1304.5	1304.9	1305.0	1305.0
145°	1354.0	1354.6	1355.1	1355.7	1355.9	1355.9	1355.9	1355.9	1355.9	1356.1	1356.5
147.5°	1398.7	1398.6	1398.5	1398.4	1398.5	1398.8	1399.2	1399.5	1399.8	1400.1	1400.4
150°	1426.9	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1428.0	1428.5
152.5°	1454.0	1452.8	1451.6	1450.4	1450.1	1450.6	1451.2	1451.8	1452.2	1452.8	1453.3
155°	1489.1	1487.5	1485.9	1484.3	1483.8	1484.3	1484.8	1485.3	1485.9	1486.7	1487.5
157.5°	1517.1	1516.2	1515.2	1514.3	1513.8	1513.9	1513.9	1513.9	1514.0	1514.9	1515.7
160°	1535.6	1534.0	1532.4	1530.8	1530.1	1530.4	1530.7	1530.9	1531.2	1532.2	1533.3
162.5°	1550.9	1549.3	1547.6	1546.0	1545.4	1545.6	1545.9	1546.2	1546.4	1547.9	1549.4
165°	1571.4	1569.7	1568.1	1566.5	1565.9	1566.1	1566.5	1566.7	1566.9	1568.5	1570.1
167.5°	1586.6	1584.9	1583.3	1581.6	1581.0	1581.2	1581.4	1581.8	1582.0	1583.9	1585.8
170°	1594.9	1593.1	1591.2	1589.4	1588.6	1588.8	1589.1	1589.4	1589.6	1591.7	1593.9
172.5°	1600.7	1598.8	1597.0	1595.1	1594.4	1594.9	1595.4	1595.9	1596.3	1598.2	1600.1
175°	1607.1	1605.5	1603.9	1602.3	1601.7	1602.0	1602.2	1602.5	1602.7	1604.9	1606.9
177.5°	1610.3	1609.0	1607.7	1606.5	1605.9	1606.1	1606.4	1606.5	1606.8	1608.3	1609.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	7.8	8.2	8.2	8.2	8.3	8.6	9.0
90°	23.1	24.4	25.4	26.2	27.0	27.8	28.6
92.5°	23.1	24.4	25.2	25.6	26.0	26.4	26.7
95°	23.1	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	36.3	28.8	25.0	25.0	25.0	25.0	25.0
100°	89.0	49.6	29.3	28.2	27.2	26.1	25.0
102.5°	242.3	234.9	222.1	204.1	186.1	168.0	150.0
105°	355.4	355.4	355.2	355.0	354.7	354.4	354.2
107.5°	450.0	450.0	449.6	448.9	448.1	447.3	446.5
110°	510.4	509.6	509.4	509.6	509.8	510.2	510.4



TEST NUMBER: P333656-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	570.8	569.8	569.1	568.8	568.4	568.0	567.6
115°	662.3	661.2	659.9	658.3	656.6	655.1	653.5
117.5°	750.3	748.8	747.8	747.2	746.5	745.8	745.0
120°	808.1	807.6	806.7	805.3	804.0	802.7	801.4
122.5°	862.5	862.0	860.9	859.4	857.9	856.3	854.8
125°	941.3	940.2	939.3	938.5	937.7	936.9	936.1
127.5°	1014.3	1013.7	1012.4	1010.4	1008.5	1006.5	1004.6
130°	1061.4	1060.6	1059.5	1058.2	1056.9	1055.5	1054.2
132.5°	1106.2	1106.0	1105.3	1104.0	1102.6	1101.3	1099.9
135°	1170.7	1170.1	1169.0	1167.4	1165.9	1164.3	1162.7
137.5°	1231.7	1231.8	1231.2	1229.8	1228.4	1227.0	1225.7
140°	1269.2	1269.8	1269.2	1267.7	1266.1	1264.5	1262.9
142.5°	1305.2	1305.3	1304.6	1302.9	1301.3	1299.7	1298.1
145°	1356.7	1356.9	1356.3	1354.7	1353.1	1351.5	1350.0
147.5°	1400.7	1401.1	1400.3	1398.4	1396.5	1394.6	1392.7
150°	1429.0	1429.6	1428.8	1426.6	1424.5	1422.4	1420.3
152.5°	1453.8	1454.4	1453.7	1451.8	1449.9	1448.0	1446.0
155°	1488.3	1489.1	1488.4	1486.3	1484.2	1482.0	1479.9
157.5°	1516.6	1517.4	1516.8	1514.7	1512.5	1510.4	1508.3
160°	1534.4	1535.4	1534.9	1532.8	1530.7	1528.5	1526.5
162.5°	1550.9	1552.4	1552.0	1549.7	1547.3	1545.0	1542.6
165°	1571.8	1573.4	1573.0	1571.0	1568.8	1566.7	1564.6
167.5°	1587.7	1589.6	1589.4	1587.0	1584.6	1582.2	1579.8
170°	1596.0	1598.1	1598.0	1595.6	1593.2	1590.8	1588.4
172.5°	1602.0	1603.9	1603.7	1601.3	1598.9	1596.6	1594.2
175°	1609.1	1611.2	1611.1	1608.7	1606.3	1603.9	1601.6
177.5°	1611.2	1612.7	1612.6	1610.9	1609.2	1607.5	1605.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7

(END OF REPORT)