

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333657-927

Luminaire Tested: **S125RDIW-S375D1560U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333657-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1560U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5442.6 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	28	21	20	19	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	42	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	29	23	19	22	18	15	16	14	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	0.8
10°-20°	125.3	2.3
20°-30°	198.7	3.7
30°-40°	239.6	4.4
40°-50°	214.0	3.9
50°-60°	164.1	3.0
60°-70°	106.6	2.0
70°-80°	51.8	1.0
80°-90°	15.7	0.3
90°-100°	102.8	1.9
100°-110°	303.6	5.6
110°-120°	514.3	9.4
120°-130°	676.9	12.4
130°-140°	758.4	13.9
140°-150°	743.3	13.7
150°-160°	624.3	11.5
160°-170°	415.0	7.6
170°-180°	145.2	2.7
0°-30°	366.8	6.7
0°-40°	606.3	11.1
0°-60°	984.4	18.1
0°-90°	1158.6	21.3
90°-120°	920.8	16.9
90°-150°	3099.4	56.9
90°-180°	4284.0	78.7
0°-180°	5442.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	29	1	29	1	29	17
95°	103	78	103	78	103	105
105°	296	272	296	272	296	314
115°	520	515	520	515	520	514
125°	756	752	756	752	756	675
135°	981	977	981	977	981	757
145°	1189	1184	1189	1184	1189	742
155°	1355	1355	1355	1355	1355	623
165°	1470	1473	1470	1473	1470	414
175°	1526	1532	1526	1532	1526	145
180°	1535	1535	1535	1535	1535	



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	9.0	8.6	8.3	8.2	8.2	8.2	7.8	7.4	7.1	6.9	6.7
90°	28.7	27.9	27.1	26.3	25.5	24.4	23.1	21.8	20.4	19.1	17.3
92.5°	56.4	55.8	55.2	54.7	54.0	52.9	51.1	49.4	47.6	45.9	43.6
95°	102.7	102.2	101.7	101.2	100.6	99.4	97.6	95.7	93.9	92.0	89.4
97.5°	155.8	155.5	155.2	154.9	154.6	153.4	151.7	150.0	148.2	146.5	142.8
100°	195.9	195.4	194.9	194.3	193.8	192.3	190.0	187.6	185.2	182.8	179.4
102.5°	236.1	235.4	234.6	233.9	233.1	231.4	228.9	226.2	223.6	221.0	219.3
105°	296.3	295.5	294.7	293.9	293.1	291.9	290.3	288.8	287.2	285.6	283.9
107.5°	357.9	358.0	358.1	358.1	358.1	357.7	357.0	356.2	355.4	354.6	353.4
110°	403.9	404.1	404.3	404.6	404.9	404.6	403.9	403.1	402.2	401.4	400.6



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	448.8	449.2	449.7	450.2	450.7	450.7	450.4	450.0	449.6	449.2	448.2
115°	519.8	520.0	520.2	520.5	520.8	521.0	521.3	521.6	521.8	522.1	521.6
117.5°	589.0	590.1	591.1	592.2	593.3	593.7	593.5	593.3	593.0	592.9	592.3
120°	636.8	637.9	638.9	640.0	641.0	641.6	641.6	641.6	641.6	641.6	641.3
122.5°	684.6	685.4	686.3	687.1	688.0	688.5	688.7	689.0	689.1	689.4	688.6
125°	756.3	756.5	756.8	757.1	757.3	757.7	758.3	758.8	759.3	759.9	759.6
127.5°	825.1	825.6	826.2	826.6	827.2	827.6	827.9	828.1	828.4	828.7	828.4
130°	871.0	871.5	872.0	872.6	873.1	873.5	873.8	874.0	874.3	874.6	874.0
132.5°	913.9	914.7	915.4	916.2	917.0	917.4	917.7	918.0	918.2	918.5	918.6
135°	980.9	981.9	983.0	984.0	985.2	985.6	985.6	985.6	985.6	985.6	985.4
137.5°	1046.3	1047.7	1049.0	1050.4	1051.7	1052.2	1051.9	1051.5	1051.2	1050.9	1050.3
140°	1088.4	1089.7	1091.1	1092.4	1093.7	1094.1	1093.6	1093.1	1092.5	1092.0	1091.2
142.5°	1128.5	1129.9	1131.2	1132.5	1133.9	1134.4	1134.0	1133.7	1133.4	1133.1	1132.1
145°	1188.7	1189.5	1190.3	1191.1	1191.9	1192.3	1192.3	1192.3	1192.3	1192.3	1191.5
147.5°	1240.2	1242.0	1243.7	1245.5	1247.4	1247.9	1247.3	1246.7	1246.0	1245.4	1244.8
150°	1278.3	1278.9	1279.5	1279.9	1280.5	1280.8	1280.8	1280.8	1280.8	1280.8	1279.7
152.5°	1310.0	1310.9	1311.9	1312.8	1313.8	1313.9	1313.3	1312.6	1312.0	1311.4	1310.9
155°	1354.9	1356.1	1357.5	1358.8	1360.2	1360.3	1359.2	1358.1	1357.1	1356.1	1355.7
157.5°	1392.3	1394.1	1395.8	1397.6	1399.4	1399.7	1398.7	1397.6	1396.5	1395.4	1395.2
160°	1418.2	1419.5	1420.8	1422.1	1423.5	1423.6	1422.5	1421.5	1420.4	1419.4	1419.1
162.5°	1440.1	1441.7	1443.2	1444.8	1446.3	1446.4	1445.2	1443.9	1442.6	1441.3	1441.3
165°	1469.5	1471.2	1472.7	1474.3	1475.9	1476.2	1475.1	1474.0	1473.0	1472.0	1471.6
167.5°	1492.9	1494.6	1496.3	1497.9	1499.5	1499.5	1497.9	1496.4	1494.8	1493.2	1493.2
170°	1505.4	1507.2	1509.1	1510.9	1512.8	1512.9	1511.3	1509.7	1508.2	1506.6	1506.6
172.5°	1515.9	1517.5	1519.2	1520.8	1522.5	1522.5	1520.9	1519.3	1517.7	1516.2	1516.2
175°	1525.7	1527.6	1529.4	1531.3	1533.1	1533.3	1531.7	1530.1	1528.4	1526.9	1526.9
177.5°	1531.4	1532.9	1534.4	1535.9	1537.4	1537.5	1536.2	1534.9	1533.7	1532.4	1532.6
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	6.4	6.1	5.9	5.5	4.9	5.1	5.2	4.9	5.1	5.1	5.3
90°	15.4	13.5	11.6	9.7	7.6	5.5	3.3	1.2	3.3	5.5	7.6
92.5°	41.3	39.1	36.8	34.9	33.4	31.9	30.4	28.9	30.4	31.9	33.4
95°	86.7	84.1	81.4	79.8	79.2	78.7	78.2	77.6	78.2	78.7	79.2
97.5°	139.2	135.5	131.8	129.9	129.7	129.4	129.2	129.0	129.2	129.4	129.7
100°	175.9	172.5	169.0	167.2	167.2	167.2	167.2	167.2	167.2	167.2	167.2
102.5°	217.5	215.8	214.0	212.6	211.5	210.5	209.5	208.3	209.5	210.5	211.5
105°	282.3	280.7	279.2	277.7	276.4	275.0	273.7	272.4	273.7	275.0	276.4
107.5°	352.1	350.9	349.7	348.4	347.1	345.8	344.4	343.1	344.4	345.8	347.1
110°	399.8	399.0	398.2	397.2	395.9	394.5	393.2	391.9	393.2	394.5	395.9



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	447.2	446.2	445.2	444.3	443.6	443.0	442.3	441.6	442.3	443.0	443.6
115°	521.0	520.5	520.0	519.2	518.1	517.1	516.0	514.9	516.0	517.1	518.1
117.5°	591.8	591.4	590.9	590.4	589.9	589.5	589.0	588.5	589.0	589.5	589.9
120°	641.0	640.8	640.5	639.7	638.4	637.1	635.7	634.4	635.7	637.1	638.4
122.5°	688.0	687.3	686.6	686.0	685.6	685.1	684.6	684.1	684.6	685.1	685.6
125°	759.3	759.1	758.8	757.9	756.3	754.7	753.0	751.5	753.0	754.7	756.3
127.5°	828.1	827.8	827.4	826.8	825.9	825.0	824.1	823.2	824.1	825.0	825.9
130°	873.5	873.0	872.4	871.5	870.1	868.9	867.5	866.2	867.5	868.9	870.1
132.5°	918.7	918.9	918.9	917.9	915.8	913.5	911.4	909.2	911.4	913.5	915.8
135°	985.2	984.8	984.6	983.7	982.1	980.5	978.9	977.3	978.9	980.5	982.1
137.5°	1049.7	1049.2	1048.5	1047.5	1045.9	1044.4	1042.9	1041.3	1042.9	1044.4	1045.9
140°	1090.4	1089.6	1088.8	1087.7	1086.4	1085.1	1083.8	1082.4	1083.8	1085.1	1086.4
142.5°	1131.1	1130.0	1129.0	1128.0	1126.9	1125.8	1124.7	1123.6	1124.7	1125.8	1126.9
145°	1190.7	1189.9	1189.1	1188.3	1187.2	1186.1	1185.0	1184.0	1185.0	1186.1	1187.2
147.5°	1244.1	1243.5	1242.9	1242.2	1241.7	1241.0	1240.5	1239.9	1240.5	1241.0	1241.7
150°	1278.7	1277.6	1276.5	1276.1	1276.4	1276.7	1276.9	1277.2	1276.9	1276.7	1276.4
152.5°	1310.5	1310.1	1309.6	1309.2	1308.8	1308.5	1308.1	1307.7	1308.1	1308.5	1308.8
155°	1355.5	1355.3	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9
157.5°	1395.0	1394.6	1394.4	1394.6	1395.1	1395.7	1396.3	1396.9	1396.3	1395.7	1395.1
160°	1418.8	1418.6	1418.3	1418.6	1419.4	1420.1	1420.9	1421.7	1420.9	1420.1	1419.4
162.5°	1441.2	1441.1	1441.1	1441.4	1442.0	1442.6	1443.1	1443.8	1443.1	1442.6	1442.0
165°	1471.4	1471.2	1470.8	1471.0	1471.6	1472.0	1472.6	1473.1	1472.6	1472.0	1471.6
167.5°	1493.2	1493.2	1493.2	1493.7	1494.8	1495.9	1496.9	1497.9	1496.9	1495.9	1494.8
170°	1506.6	1506.6	1506.6	1507.1	1508.2	1509.2	1510.3	1511.3	1510.3	1509.2	1508.2
172.5°	1516.2	1516.2	1516.2	1516.6	1517.7	1518.8	1519.9	1520.9	1519.9	1518.8	1517.7
175°	1526.9	1526.9	1526.9	1527.4	1528.4	1529.5	1530.6	1531.7	1530.6	1529.5	1528.4
177.5°	1532.8	1533.0	1533.2	1533.7	1534.6	1535.5	1536.3	1537.2	1536.3	1535.5	1534.6
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	5.6	6.0	6.3	6.9	6.8	7.4	7.6	7.7	8.0	8.2	8.3
90°	9.7	11.6	13.5	15.4	17.3	19.1	20.4	21.8	23.1	24.4	25.5
92.5°	34.9	36.8	39.1	41.3	43.6	45.9	47.6	49.4	51.1	52.9	54.0
95°	79.8	81.4	84.1	86.7	89.4	92.0	93.9	95.7	97.6	99.4	100.6
97.5°	129.9	131.8	135.5	139.2	142.8	146.5	148.2	150.0	151.7	153.4	154.6
100°	167.2	169.0	172.5	175.9	179.4	182.8	185.2	187.6	190.0	192.3	193.8
102.5°	212.6	214.0	215.8	217.5	219.3	221.0	223.6	226.2	228.9	231.4	233.1
105°	277.7	279.2	280.7	282.3	283.9	285.6	287.2	288.8	290.3	291.9	293.1
107.5°	348.4	349.7	350.9	352.1	353.4	354.6	355.4	356.2	357.0	357.7	358.1
110°	397.2	398.2	399.0	399.8	400.6	401.4	402.2	403.1	403.9	404.6	404.9



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	444.3	445.2	446.2	447.2	448.2	449.2	449.6	450.0	450.4	450.7	450.7
115°	519.2	520.0	520.5	521.0	521.6	522.1	521.8	521.6	521.3	521.0	520.8
117.5°	590.4	590.9	591.4	591.8	592.3	592.9	593.0	593.3	593.5	593.7	593.3
120°	639.7	640.5	640.8	641.0	641.3	641.6	641.6	641.6	641.6	641.6	641.0
122.5°	686.0	686.6	687.3	688.0	688.6	689.4	689.1	689.0	688.7	688.5	688.0
125°	757.9	758.8	759.1	759.3	759.6	759.9	759.3	758.8	758.3	757.7	757.3
127.5°	826.8	827.4	827.8	828.1	828.4	828.7	828.4	828.1	827.9	827.6	827.2
130°	871.5	872.4	873.0	873.5	874.0	874.6	874.3	874.0	873.8	873.5	873.1
132.5°	917.9	918.9	918.9	918.7	918.6	918.5	918.2	918.0	917.7	917.4	917.0
135°	983.7	984.6	984.8	985.2	985.4	985.6	985.6	985.6	985.6	985.6	985.2
137.5°	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2	1051.5	1051.9	1052.2	1051.7
140°	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5	1093.1	1093.6	1094.1	1093.7
142.5°	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4	1133.7	1134.0	1134.4	1133.9
145°	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3	1192.3	1192.3	1192.3	1191.9
147.5°	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0	1246.7	1247.3	1247.9	1247.4
150°	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8	1280.8	1280.8	1280.8	1280.5
152.5°	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0	1312.6	1313.3	1313.9	1313.8
155°	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1	1358.1	1359.2	1360.3	1360.2
157.5°	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5	1397.6	1398.7	1399.7	1399.4
160°	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4	1421.5	1422.5	1423.6	1423.5
162.5°	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6	1443.9	1445.2	1446.4	1446.3
165°	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0	1474.0	1475.1	1476.2	1475.9
167.5°	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8	1496.4	1497.9	1499.5	1499.5
170°	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2	1509.7	1511.3	1512.9	1512.8
172.5°	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7	1519.3	1520.9	1522.5	1522.5
175°	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4	1530.1	1531.7	1533.3	1533.1
177.5°	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7	1534.9	1536.2	1537.5	1537.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	8.6	8.6	8.8	9.0	8.8	8.6	8.6	8.3	8.2	8.0	7.7
90°	26.3	27.1	27.9	28.7	27.9	27.1	26.3	25.5	24.4	23.1	21.8
92.5°	54.7	55.2	55.8	56.4	55.8	55.2	54.7	54.0	52.9	51.1	49.4
95°	101.2	101.7	102.2	102.7	102.2	101.7	101.2	100.6	99.4	97.6	95.7
97.5°	154.9	155.2	155.5	155.8	155.5	155.2	154.9	154.6	153.4	151.7	150.0
100°	194.3	194.9	195.4	195.9	195.4	194.9	194.3	193.8	192.3	190.0	187.6
102.5°	233.9	234.6	235.4	236.1	235.4	234.6	233.9	233.1	231.4	228.9	226.2
105°	293.9	294.7	295.5	296.3	295.5	294.7	293.9	293.1	291.9	290.3	288.8
107.5°	358.1	358.1	358.0	357.9	358.0	358.1	358.1	358.1	357.7	357.0	356.2
110°	404.6	404.3	404.1	403.9	404.1	404.3	404.6	404.9	404.6	403.9	403.1



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	450.2	449.7	449.2	448.8	449.2	449.7	450.2	450.7	450.7	450.4	450.0
115°	520.5	520.2	520.0	519.8	520.0	520.2	520.5	520.8	521.0	521.3	521.6
117.5°	592.2	591.1	590.1	589.0	590.1	591.1	592.2	593.3	593.7	593.5	593.3
120°	640.0	638.9	637.9	636.8	637.9	638.9	640.0	641.0	641.6	641.6	641.6
122.5°	687.1	686.3	685.4	684.6	685.4	686.3	687.1	688.0	688.5	688.7	689.0
125°	757.1	756.8	756.5	756.3	756.5	756.8	757.1	757.3	757.7	758.3	758.8
127.5°	826.6	826.2	825.6	825.1	825.6	826.2	826.6	827.2	827.6	827.9	828.1
130°	872.6	872.0	871.5	871.0	871.5	872.0	872.6	873.1	873.5	873.8	874.0
132.5°	916.2	915.4	914.7	913.9	914.7	915.4	916.2	917.0	917.4	917.7	918.0
135°	984.0	983.0	981.9	980.9	981.9	983.0	984.0	985.2	985.6	985.6	985.6
137.5°	1050.4	1049.0	1047.7	1046.3	1047.7	1049.0	1050.4	1051.7	1052.2	1051.9	1051.5
140°	1092.4	1091.1	1089.7	1088.4	1089.7	1091.1	1092.4	1093.7	1094.1	1093.6	1093.1
142.5°	1132.5	1131.2	1129.9	1128.5	1129.9	1131.2	1132.5	1133.9	1134.4	1134.0	1133.7
145°	1191.1	1190.3	1189.5	1188.7	1189.5	1190.3	1191.1	1191.9	1192.3	1192.3	1192.3
147.5°	1245.5	1243.7	1242.0	1240.2	1242.0	1243.7	1245.5	1247.4	1247.9	1247.3	1246.7
150°	1279.9	1279.5	1278.9	1278.3	1278.9	1279.5	1279.9	1280.5	1280.8	1280.8	1280.8
152.5°	1312.8	1311.9	1310.9	1310.0	1310.9	1311.9	1312.8	1313.8	1313.9	1313.3	1312.6
155°	1358.8	1357.5	1356.1	1354.9	1356.1	1357.5	1358.8	1360.2	1360.3	1359.2	1358.1
157.5°	1397.6	1395.8	1394.1	1392.3	1394.1	1395.8	1397.6	1399.4	1399.7	1398.7	1397.6
160°	1422.1	1420.8	1419.5	1418.2	1419.5	1420.8	1422.1	1423.5	1423.6	1422.5	1421.5
162.5°	1444.8	1443.2	1441.7	1440.1	1441.7	1443.2	1444.8	1446.3	1446.4	1445.2	1443.9
165°	1474.3	1472.7	1471.2	1469.5	1471.2	1472.7	1474.3	1475.9	1476.2	1475.1	1474.0
167.5°	1497.9	1496.3	1494.6	1492.9	1494.6	1496.3	1497.9	1499.5	1499.5	1497.9	1496.4
170°	1510.9	1509.1	1507.2	1505.4	1507.2	1509.1	1510.9	1512.8	1512.9	1511.3	1509.7
172.5°	1520.8	1519.2	1517.5	1515.9	1517.5	1519.2	1520.8	1522.5	1522.5	1520.9	1519.3
175°	1531.3	1529.4	1527.6	1525.7	1527.6	1529.4	1531.3	1533.1	1533.3	1531.7	1530.1
177.5°	1535.9	1534.4	1532.9	1531.4	1532.9	1534.4	1535.9	1537.4	1537.5	1536.2	1534.9
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	7.6	7.4	6.8	6.9	6.3	6.0	5.6	5.3	5.1	5.1	4.9
90°	20.4	19.1	17.3	15.4	13.5	11.6	9.7	7.6	5.5	3.3	1.2
92.5°	47.6	45.9	43.6	41.3	39.1	36.8	34.9	33.4	31.9	30.4	28.9
95°	93.9	92.0	89.4	86.7	84.1	81.4	79.8	79.2	78.7	78.2	77.6
97.5°	148.2	146.5	142.8	139.2	135.5	131.8	129.9	129.7	129.4	129.2	129.0
100°	185.2	182.8	179.4	175.9	172.5	169.0	167.2	167.2	167.2	167.2	167.2
102.5°	223.6	221.0	219.3	217.5	215.8	214.0	212.6	211.5	210.5	209.5	208.3
105°	287.2	285.6	283.9	282.3	280.7	279.2	277.7	276.4	275.0	273.7	272.4
107.5°	355.4	354.6	353.4	352.1	350.9	349.7	348.4	347.1	345.8	344.4	343.1
110°	402.2	401.4	400.6	399.8	399.0	398.2	397.2	395.9	394.5	393.2	391.9



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	449.6	449.2	448.2	447.2	446.2	445.2	444.3	443.6	443.0	442.3	441.6
115°	521.8	522.1	521.6	521.0	520.5	520.0	519.2	518.1	517.1	516.0	514.9
117.5°	593.0	592.9	592.3	591.8	591.4	590.9	590.4	589.9	589.5	589.0	588.5
120°	641.6	641.6	641.3	641.0	640.8	640.5	639.7	638.4	637.1	635.7	634.4
122.5°	689.1	689.4	688.6	688.0	687.3	686.6	686.0	685.6	685.1	684.6	684.1
125°	759.3	759.9	759.6	759.3	759.1	758.8	757.9	756.3	754.7	753.0	751.5
127.5°	828.4	828.7	828.4	828.1	827.8	827.4	826.8	825.9	825.0	824.1	823.2
130°	874.3	874.6	874.0	873.5	873.0	872.4	871.5	870.1	868.9	867.5	866.2
132.5°	918.2	918.5	918.6	918.7	918.9	918.9	917.9	915.8	913.5	911.4	909.2
135°	985.6	985.6	985.4	985.2	984.8	984.6	983.7	982.1	980.5	978.9	977.3
137.5°	1051.2	1050.9	1050.3	1049.7	1049.2	1048.5	1047.5	1045.9	1044.4	1042.9	1041.3
140°	1092.5	1092.0	1091.2	1090.4	1089.6	1088.8	1087.7	1086.4	1085.1	1083.8	1082.4
142.5°	1133.4	1133.1	1132.1	1131.1	1130.0	1129.0	1128.0	1126.9	1125.8	1124.7	1123.6
145°	1192.3	1192.3	1191.5	1190.7	1189.9	1189.1	1188.3	1187.2	1186.1	1185.0	1184.0
147.5°	1246.0	1245.4	1244.8	1244.1	1243.5	1242.9	1242.2	1241.7	1241.0	1240.5	1239.9
150°	1280.8	1280.8	1279.7	1278.7	1277.6	1276.5	1276.1	1276.4	1276.7	1276.9	1277.2
152.5°	1312.0	1311.4	1310.9	1310.5	1310.1	1309.6	1309.2	1308.8	1308.5	1308.1	1307.7
155°	1357.1	1356.1	1355.7	1355.5	1355.3	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9
157.5°	1396.5	1395.4	1395.2	1395.0	1394.6	1394.4	1394.6	1395.1	1395.7	1396.3	1396.9
160°	1420.4	1419.4	1419.1	1418.8	1418.6	1418.3	1418.6	1419.4	1420.1	1420.9	1421.7
162.5°	1442.6	1441.3	1441.3	1441.2	1441.1	1441.1	1441.4	1442.0	1442.6	1443.1	1443.8
165°	1473.0	1472.0	1471.6	1471.4	1471.2	1470.8	1471.0	1471.6	1472.0	1472.6	1473.1
167.5°	1494.8	1493.2	1493.2	1493.2	1493.2	1493.2	1493.7	1494.8	1495.9	1496.9	1497.9
170°	1508.2	1506.6	1506.6	1506.6	1506.6	1506.6	1507.1	1508.2	1509.2	1510.3	1511.3
172.5°	1517.7	1516.2	1516.2	1516.2	1516.2	1516.2	1516.6	1517.7	1518.8	1519.9	1520.9
175°	1528.4	1526.9	1526.9	1526.9	1526.9	1526.9	1527.4	1528.4	1529.5	1530.6	1531.7
177.5°	1533.7	1532.4	1532.6	1532.8	1533.0	1533.2	1533.7	1534.6	1535.5	1536.3	1537.2
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	5.2	5.1	4.9	5.5	5.9	6.1	6.4	6.7	6.9	7.1	7.4
90°	3.3	5.5	7.6	9.7	11.6	13.5	15.4	17.3	19.1	20.4	21.8
92.5°	30.4	31.9	33.4	34.9	36.8	39.1	41.3	43.6	45.9	47.6	49.4
95°	78.2	78.7	79.2	79.8	81.4	84.1	86.7	89.4	92.0	93.9	95.7
97.5°	129.2	129.4	129.7	129.9	131.8	135.5	139.2	142.8	146.5	148.2	150.0
100°	167.2	167.2	167.2	167.2	169.0	172.5	175.9	179.4	182.8	185.2	187.6
102.5°	209.5	210.5	211.5	212.6	214.0	215.8	217.5	219.3	221.0	223.6	226.2
105°	273.7	275.0	276.4	277.7	279.2	280.7	282.3	283.9	285.6	287.2	288.8
107.5°	344.4	345.8	347.1	348.4	349.7	350.9	352.1	353.4	354.6	355.4	356.2
110°	393.2	394.5	395.9	397.2	398.2	399.0	399.8	400.6	401.4	402.2	403.1



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	442.3	443.0	443.6	444.3	445.2	446.2	447.2	448.2	449.2	449.6	450.0
115°	516.0	517.1	518.1	519.2	520.0	520.5	521.0	521.6	522.1	521.8	521.6
117.5°	589.0	589.5	589.9	590.4	590.9	591.4	591.8	592.3	592.9	593.0	593.3
120°	635.7	637.1	638.4	639.7	640.5	640.8	641.0	641.3	641.6	641.6	641.6
122.5°	684.6	685.1	685.6	686.0	686.6	687.3	688.0	688.6	689.4	689.1	689.0
125°	753.0	754.7	756.3	757.9	758.8	759.1	759.3	759.6	759.9	759.3	758.8
127.5°	824.1	825.0	825.9	826.8	827.4	827.8	828.1	828.4	828.7	828.4	828.1
130°	867.5	868.9	870.1	871.5	872.4	873.0	873.5	874.0	874.6	874.3	874.0
132.5°	911.4	913.5	915.8	917.9	918.9	918.9	918.7	918.6	918.5	918.2	918.0
135°	978.9	980.5	982.1	983.7	984.6	984.8	985.2	985.4	985.6	985.6	985.6
137.5°	1042.9	1044.4	1045.9	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2	1051.5
140°	1083.8	1085.1	1086.4	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5	1093.1
142.5°	1124.7	1125.8	1126.9	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4	1133.7
145°	1185.0	1186.1	1187.2	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3	1192.3
147.5°	1240.5	1241.0	1241.7	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0	1246.7
150°	1276.9	1276.7	1276.4	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8	1280.8
152.5°	1308.1	1308.5	1308.8	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0	1312.6
155°	1354.9	1354.9	1354.9	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1	1358.1
157.5°	1396.3	1395.7	1395.1	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5	1397.6
160°	1420.9	1420.1	1419.4	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4	1421.5
162.5°	1443.1	1442.6	1442.0	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6	1443.9
165°	1472.6	1472.0	1471.6	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0	1474.0
167.5°	1496.9	1495.9	1494.8	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8	1496.4
170°	1510.3	1509.2	1508.2	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2	1509.7
172.5°	1519.9	1518.8	1517.7	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7	1519.3
175°	1530.6	1529.5	1528.4	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4	1530.1
177.5°	1536.3	1535.5	1534.6	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7	1534.9
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	7.8	8.2	8.2	8.2	8.3	8.6	9.0
90°	23.1	24.4	25.5	26.3	27.1	27.9	28.7
92.5°	51.1	52.9	54.0	54.7	55.2	55.8	56.4
95°	97.6	99.4	100.6	101.2	101.7	102.2	102.7
97.5°	151.7	153.4	154.6	154.9	155.2	155.5	155.8
100°	190.0	192.3	193.8	194.3	194.9	195.4	195.9
102.5°	228.9	231.4	233.1	233.9	234.6	235.4	236.1
105°	290.3	291.9	293.1	293.9	294.7	295.5	296.3
107.5°	357.0	357.7	358.1	358.1	358.1	358.0	357.9
110°	403.9	404.6	404.9	404.6	404.3	404.1	403.9



TEST NUMBER: P333657-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	450.7	450.7	450.2	449.7	449.2	448.8
115°	521.3	521.0	520.8	520.5	520.2	520.0	519.8
117.5°	593.5	593.7	593.3	592.2	591.1	590.1	589.0
120°	641.6	641.6	641.0	640.0	638.9	637.9	636.8
122.5°	688.7	688.5	688.0	687.1	686.3	685.4	684.6
125°	758.3	757.7	757.3	757.1	756.8	756.5	756.3
127.5°	827.9	827.6	827.2	826.6	826.2	825.6	825.1
130°	873.8	873.5	873.1	872.6	872.0	871.5	871.0
132.5°	917.7	917.4	917.0	916.2	915.4	914.7	913.9
135°	985.6	985.6	985.2	984.0	983.0	981.9	980.9
137.5°	1051.9	1052.2	1051.7	1050.4	1049.0	1047.7	1046.3
140°	1093.6	1094.1	1093.7	1092.4	1091.1	1089.7	1088.4
142.5°	1134.0	1134.4	1133.9	1132.5	1131.2	1129.9	1128.5
145°	1192.3	1192.3	1191.9	1191.1	1190.3	1189.5	1188.7
147.5°	1247.3	1247.9	1247.4	1245.5	1243.7	1242.0	1240.2
150°	1280.8	1280.8	1280.5	1279.9	1279.5	1278.9	1278.3
152.5°	1313.3	1313.9	1313.8	1312.8	1311.9	1310.9	1310.0
155°	1359.2	1360.3	1360.2	1358.8	1357.5	1356.1	1354.9
157.5°	1398.7	1399.7	1399.4	1397.6	1395.8	1394.1	1392.3
160°	1422.5	1423.6	1423.5	1422.1	1420.8	1419.5	1418.2
162.5°	1445.2	1446.4	1446.3	1444.8	1443.2	1441.7	1440.1
165°	1475.1	1476.2	1475.9	1474.3	1472.7	1471.2	1469.5
167.5°	1497.9	1499.5	1499.5	1497.9	1496.3	1494.6	1492.9
170°	1511.3	1512.9	1512.8	1510.9	1509.1	1507.2	1505.4
172.5°	1520.9	1522.5	1522.5	1520.8	1519.2	1517.5	1515.9
175°	1531.7	1533.3	1533.1	1531.3	1529.4	1527.6	1525.7
177.5°	1536.2	1537.5	1537.4	1535.9	1534.4	1532.9	1531.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2

(END OF REPORT)