

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333660-927

Luminaire Tested: **S125RDIW-S610D470U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333660-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D470U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3384.8 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	100	95	92	88	93	89	86	83	77	74	72	66	64	62	55	54	53	48
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	76	66	58	52	71	62	55	49	54	48	44	46	42	39	40	37	34	31
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	36	32	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	21	25	22	19	17
10	49	37	29	25	45	34	28	23	31	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4735	4735	4735	4735
5°	5447	4741	4187	4741
10°	6248	4716	3694	4716
15°	6748	4668	3284	4668
20°	7442	4612	3032	4612
25°	8612	4538	2813	4538
30°	9371	4459	2671	4459
35°	7905	4368	2539	4368
40°	5520	4204	2426	4204
45°	4095	3982	2314	3982
50°	3265	3752	2219	3752
55°	2771	3466	2135	3466
60°	2395	3211	1998	3211
65°	2135	2934	1721	2934
70°	1875	2689	1567	2689
75°	1622	2328	1472	2328
80°	1231	1960	1231	1960
85°	1030	1541	1163	1541



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	2.1
10°-20°	206.0	6.1
20°-30°	326.6	9.7
30°-40°	393.9	11.6
40°-50°	351.8	10.4
50°-60°	269.8	8.0
60°-70°	175.3	5.2
70°-80°	85.2	2.5
80°-90°	21.4	0.6
90°-100°	17.6	0.5
100°-110°	108.3	3.2
110°-120°	196.4	5.8
120°-130°	252.0	7.4
130°-140°	271.1	8.0
140°-150°	254.4	7.5
150°-160°	205.8	6.1
160°-170°	133.1	3.9
170°-180°	45.9	1.4
0°-30°	602.9	17.8
0°-40°	996.8	29.5
0°-60°	1618.4	47.8
0°-90°	1900.3	56.1
90°-120°	322.2	9.5
90°-150°	1099.7	32.5
90°-180°	1485.0	43.9
0°-180°	3384.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	733	733	733	733	733	
5°	840	731	646	731	840	84
15°	1009	698	491	698	1009	289
25°	1209	637	395	637	1209	555
35°	1003	554	322	554	1003	606
45°	448	436	253	436	448	358
55°	246	308	190	308	246	223
65°	140	192	113	192	140	139
75°	65	93	59	93	65	69
85°	14	21	16	21	14	16
90°	9	0	9	0	9	4
95°	8	20	8	20	8	6
105°	106	105	106	105	106	96
115°	196	198	196	198	196	195
125°	281	281	281	281	281	250
135°	349	351	349	351	349	270
145°	406	407	406	407	406	253
155°	445	448	445	448	445	205
165°	470	473	470	473	470	133
175°	481	484	481	484	481	46
180°	484	484	484	484	484	



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	771.1	770.6	771.6	768.9	769.2	765.1	765.1	761.9	757.9	754.7	753.3
5°	840.2	840.8	839.6	835.0	832.0	827.5	822.4	813.4	805.9	798.7	793.0
7.5°	911.3	911.7	907.8	906.4	898.8	893.3	881.9	869.7	858.7	844.9	834.3
10°	952.8	952.4	948.2	944.9	938.3	929.9	918.7	904.3	890.7	875.7	861.3
12.5°	976.8	976.0	974.7	970.7	964.6	957.0	947.6	933.4	916.7	900.2	883.4
15°	1009.3	1007.2	1003.3	998.1	989.4	980.7	970.2	957.6	941.6	923.0	907.3
17.5°	1049.5	1049.6	1043.5	1036.5	1024.6	1009.2	992.9	972.6	950.9	930.3	913.7
20°	1082.8	1081.8	1075.8	1062.0	1048.5	1029.2	1010.5	985.6	959.1	932.2	911.5
22.5°	1130.4	1128.1	1121.8	1103.6	1082.6	1057.8	1029.3	998.8	966.8	936.4	909.1
25°	1208.6	1206.7	1194.4	1173.3	1143.8	1105.6	1068.3	1026.4	980.4	940.4	907.3
27.5°	1261.9	1260.0	1250.9	1233.3	1206.1	1165.9	1115.4	1059.5	1002.0	947.0	899.2
30°	1256.6	1261.2	1260.0	1251.9	1231.4	1195.2	1148.7	1085.8	1017.4	952.8	895.9
32.5°	1181.1	1185.1	1195.7	1211.6	1212.8	1198.4	1163.6	1105.5	1034.7	961.2	893.2
35°	1002.7	1008.1	1028.6	1060.7	1102.9	1138.1	1145.3	1114.0	1050.5	971.4	889.2
37.5°	770.9	800.5	817.7	851.6	915.2	980.0	1042.3	1065.2	1038.2	967.2	882.8
40°	654.8	662.0	692.8	730.9	784.5	851.9	940.7	1004.8	1006.9	957.6	872.7
42.5°	560.5	569.6	590.7	621.2	667.0	734.4	826.1	910.7	949.8	931.1	859.4
45°	448.4	455.3	470.6	494.1	529.3	585.0	663.8	761.7	839.3	869.7	823.9
47.5°	368.4	372.1	385.4	403.3	429.4	469.9	530.9	615.8	709.0	774.3	767.9
50°	325.0	329.2	339.5	353.0	374.9	409.2	458.0	528.7	624.7	704.5	720.4
52.5°	291.3	294.8	301.2	314.0	332.1	358.5	397.8	461.8	548.2	633.0	669.9
55°	246.1	248.6	253.7	260.9	275.4	294.3	328.3	372.6	442.4	527.8	582.0
57.5°	209.0	210.2	213.4	220.1	230.0	243.9	268.5	306.0	356.1	433.0	492.8
60°	185.4	186.6	190.8	195.3	203.1	215.8	235.0	261.2	309.3	372.9	433.3
62.5°	166.6	167.3	169.1	173.6	180.5	190.3	205.4	226.8	265.1	320.8	378.0
65°	139.7	139.9	140.5	144.2	148.4	155.6	165.5	180.5	209.5	251.6	302.1
67.5°	113.8	114.2	116.3	117.6	121.9	125.7	131.6	143.1	163.4	191.8	231.1
70°	99.3	99.0	101.1	102.6	104.1	108.6	112.6	121.8	134.5	156.2	189.0
72.5°	85.8	85.1	86.0	86.5	88.5	91.6	95.5	101.2	110.9	125.9	150.9
75°	65.0	65.3	65.3	65.9	67.4	68.6	69.8	72.8	78.3	88.2	101.7
77.5°	45.6	45.2	46.4	46.6	47.5	48.8	49.8	51.0	53.2	57.4	64.3
80°	33.1	33.1	33.4	34.3	34.0	34.6	36.1	37.3	40.0	42.5	44.8
82.5°	25.4	25.2	25.4	25.7	25.6	26.1	26.7	26.9	28.0	29.2	30.9
85°	13.9	13.9	14.2	14.2	14.4	14.4	14.7	14.7	14.7	15.1	15.4
87.5°	7.1	6.7	6.4	6.4	6.6	7.0	6.7	6.3	6.3	6.2	6.3
90°	8.6	8.4	8.2	7.9	7.7	7.3	6.9	6.5	6.1	5.7	5.1
92.5°	8.0	7.9	7.8	7.7	7.6	7.3	6.9	6.5	6.1	5.7	5.2
95°	7.5	7.5	7.5	7.5	7.5	7.3	6.9	6.5	6.1	5.7	8.8
97.5°	7.5	7.5	7.5	7.5	7.5	8.6	10.9	13.2	15.4	17.7	23.6
100°	7.5	7.8	8.2	8.5	8.8	14.9	26.8	38.7	50.5	62.3	62.0
102.5°	45.1	50.5	55.9	61.3	66.8	70.6	72.8	75.1	77.3	79.5	79.4
105°	106.5	106.5	106.6	106.7	106.8	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.2	134.4	134.7	134.9	135.1	135.2	135.2	135.2	135.2	135.1	135.0
110°	153.4	153.3	153.2	153.1	153.0	153.1	153.4	153.6	153.8	154.1	153.9



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.6	170.7	170.8	171.0	171.0	171.3	171.5	171.8	172.1	172.5	172.4
115°	196.4	196.9	197.3	197.8	198.3	198.7	199.0	199.3	199.6	199.9	199.9
117.5°	223.9	224.1	224.3	224.5	224.7	225.1	225.5	225.9	226.3	226.7	226.4
120°	240.8	241.2	241.6	242.0	242.4	242.7	242.9	243.0	243.2	243.4	243.1
122.5°	256.9	257.4	257.8	258.3	258.7	259.0	259.2	259.4	259.5	259.7	259.6
125°	281.3	281.5	281.8	282.0	282.3	282.6	282.9	283.2	283.5	283.8	283.8
127.5°	301.9	302.5	303.1	303.6	304.3	304.7	304.8	305.0	305.1	305.3	305.4
130°	316.8	317.2	317.6	318.0	318.4	318.7	318.9	319.2	319.4	319.6	319.6
132.5°	330.6	331.0	331.4	331.8	332.2	332.4	332.4	332.5	332.6	332.6	332.7
135°	349.4	349.9	350.4	350.9	351.3	351.6	351.8	352.0	352.1	352.3	352.4
137.5°	368.4	368.8	369.2	369.6	370.0	370.2	370.2	370.1	370.1	370.0	370.2
140°	379.5	380.0	380.5	381.0	381.4	381.6	381.4	381.3	381.1	381.0	381.0
142.5°	390.1	390.6	391.1	391.6	392.1	392.3	392.2	392.2	392.1	392.1	392.1
145°	405.7	406.2	406.6	407.1	407.6	407.8	407.7	407.7	407.6	407.5	407.5
147.5°	418.5	419.1	419.7	420.3	420.8	421.0	421.0	420.9	420.7	420.6	420.6
150°	426.8	427.5	428.1	428.7	429.4	429.6	429.4	429.3	429.1	429.0	428.8
152.5°	434.6	435.1	435.7	436.3	436.9	437.0	436.9	436.7	436.6	436.4	436.3
155°	444.7	445.4	446.0	446.6	447.3	447.5	447.3	447.0	446.8	446.6	446.4
157.5°	453.3	453.9	454.6	455.2	455.8	456.0	455.7	455.5	455.3	455.0	455.0
160°	458.8	459.4	460.0	460.7	461.3	461.4	461.1	460.8	460.5	460.2	460.1
162.5°	463.6	464.3	465.0	465.7	466.4	466.5	466.1	465.6	465.2	464.8	464.7
165°	470.2	470.8	471.4	472.1	472.8	472.9	472.4	471.9	471.3	470.9	470.8
167.5°	474.8	475.5	476.2	476.9	477.7	477.7	477.1	476.6	476.0	475.4	475.3
170°	477.4	478.1	478.8	479.5	480.2	480.3	479.7	479.0	478.3	477.7	477.6
172.5°	479.1	479.8	480.5	481.3	482.0	482.0	481.4	480.9	480.3	479.7	479.6
175°	481.3	482.0	482.8	483.5	484.2	484.2	483.5	482.9	482.3	481.6	481.6
177.5°	482.6	483.1	483.6	484.1	484.7	484.7	484.2	483.8	483.3	482.9	482.8
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	753.3	751.6	748.5	745.6	742.0	738.9	736.7	734.0	730.6	726.6	723.2
5°	786.6	780.0	771.3	763.7	754.2	746.6	738.8	731.3	723.7	714.1	705.7
7.5°	823.6	809.9	796.6	779.9	764.7	751.1	738.2	725.0	712.1	698.5	685.2
10°	846.2	829.7	811.3	790.2	771.0	752.7	735.8	719.2	701.8	686.4	669.9
12.5°	867.4	846.1	825.1	798.4	775.3	752.9	731.4	710.8	692.1	672.2	654.4
15°	886.5	865.5	842.0	809.5	777.3	750.2	724.9	698.2	675.0	652.7	632.9
17.5°	893.9	871.9	844.5	813.3	778.2	744.1	711.5	682.1	654.9	628.9	606.6
20°	891.0	869.7	841.7	811.9	774.3	738.8	703.5	671.1	640.6	613.3	589.5
22.5°	884.1	862.0	835.0	803.5	767.8	730.1	692.5	657.8	626.0	597.6	571.7
25°	873.6	843.5	815.8	785.1	751.1	713.8	675.0	636.8	602.8	573.9	545.6
27.5°	862.7	825.1	790.0	759.4	723.5	690.2	652.8	613.6	577.8	548.4	519.4
30°	852.9	810.7	771.9	737.3	703.3	671.7	636.1	597.9	561.3	530.8	501.4
32.5°	840.6	795.7	753.1	713.2	680.4	649.0	616.9	580.4	544.6	513.3	483.3
35°	825.1	767.9	721.6	679.2	642.8	612.4	583.5	554.0	518.2	485.7	456.5
37.5°	804.9	740.1	686.4	640.2	601.8	571.2	548.5	521.5	488.9	457.7	430.6
40°	792.7	719.9	661.2	615.4	575.0	542.9	521.5	498.6	468.8	439.7	412.6
42.5°	776.3	701.3	635.6	588.0	547.4	516.4	494.8	474.8	449.8	422.3	393.3
45°	744.2	665.4	596.4	545.3	504.4	474.0	453.8	436.0	417.1	391.8	366.5
47.5°	702.4	627.9	555.7	499.9	459.8	431.6	412.0	398.0	384.4	363.0	338.4
50°	669.0	597.1	526.6	472.5	429.8	402.9	384.6	373.4	361.1	341.6	321.1
52.5°	629.5	565.3	496.3	440.9	400.6	375.5	357.8	346.7	336.5	320.6	301.1
55°	567.3	511.0	447.7	397.5	360.5	335.3	318.4	307.8	301.8	288.3	272.9
57.5°	495.4	455.1	399.4	350.9	318.2	293.2	280.9	272.0	265.1	255.6	244.7
60°	445.4	417.1	367.1	321.1	291.0	267.2	256.1	248.6	242.2	234.1	225.7
62.5°	394.6	374.0	330.6	291.0	263.3	243.4	233.0	226.2	218.9	213.4	205.3
65°	326.5	308.2	278.1	247.1	221.5	205.6	198.0	192.0	187.5	181.5	175.7
67.5°	254.0	246.5	225.8	204.4	186.0	171.8	165.3	161.1	155.7	152.1	148.1
70°	209.5	205.8	191.1	177.0	159.8	150.2	144.2	142.4	135.7	132.1	129.4
72.5°	170.0	168.3	159.8	150.0	137.9	129.4	123.9	121.8	117.6	114.8	113.0
75°	116.5	117.1	115.6	109.2	104.7	99.3	94.5	93.3	90.3	87.9	86.3
77.5°	73.7	76.8	76.8	76.5	74.8	71.5	69.5	68.5	65.6	64.7	64.3
80°	50.5	53.9	56.9	56.6	56.0	55.1	53.6	52.7	51.2	50.2	49.7
82.5°	33.7	36.8	39.3	41.0	40.8	39.9	38.9	38.4	38.2	37.5	37.4
85°	15.9	16.6	17.4	19.6	21.1	21.4	21.1	20.8	19.9	20.2	20.4
87.5°	6.5	6.3	6.5	6.3	6.0	7.1	7.7	7.8	7.4	7.1	6.7
90°	4.6	4.0	3.5	2.9	2.3	1.7	1.0	0.4	1.0	1.7	2.3
92.5°	4.8	4.3	3.7	3.7	4.2	4.6	5.1	5.5	5.1	4.6	4.2
95°	11.8	14.8	17.8	19.5	19.7	20.0	20.2	20.4	20.2	20.0	19.7
97.5°	29.6	35.6	41.6	44.4	44.0	43.5	43.1	42.6	43.1	43.5	44.0
100°	61.7	61.4	61.1	60.8	60.6	60.4	60.1	59.8	60.1	60.4	60.6
102.5°	79.1	79.0	78.8	78.6	78.3	78.0	77.6	77.3	77.6	78.0	78.3
105°	106.8	106.8	106.8	106.6	106.3	106.0	105.7	105.4	105.7	106.0	106.3
107.5°	134.8	134.7	134.5	134.4	134.4	134.4	134.4	134.4	134.4	134.4	134.4
110°	153.8	153.6	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	172.3	172.1	172.1	171.9	171.7	171.5	171.3	171.2	171.3	171.5	171.7
115°	199.8	199.7	199.6	199.4	199.0	198.6	198.2	197.8	198.2	198.6	199.0
117.5°	226.1	225.8	225.5	225.4	225.4	225.4	225.4	225.5	225.4	225.4	225.4
120°	242.9	242.6	242.4	242.3	242.4	242.5	242.6	242.6	242.6	242.5	242.4
122.5°	259.4	259.4	259.2	259.0	258.7	258.4	258.1	257.9	258.1	258.4	258.7
125°	283.8	283.8	283.8	283.5	283.0	282.4	281.9	281.3	281.9	282.4	283.0
127.5°	305.5	305.5	305.5	305.4	305.0	304.6	304.2	303.7	304.2	304.6	305.0
130°	319.5	319.4	319.3	319.1	318.7	318.3	317.9	317.5	317.9	318.3	318.7
132.5°	333.0	333.1	333.3	333.1	332.6	332.2	331.8	331.3	331.8	332.2	332.6
135°	352.6	352.8	352.9	352.8	352.3	351.8	351.3	350.9	351.3	351.8	352.3
137.5°	370.3	370.5	370.7	370.5	370.1	369.6	369.2	368.8	369.2	369.6	370.1
140°	381.1	381.2	381.3	381.2	381.0	380.9	380.7	380.6	380.7	380.9	381.0
142.5°	391.9	391.8	391.7	391.6	391.5	391.4	391.3	391.2	391.3	391.4	391.5
145°	407.5	407.5	407.5	407.4	407.3	407.1	406.9	406.8	406.9	407.1	407.3
147.5°	420.5	420.4	420.3	420.3	420.3	420.3	420.3	420.4	420.3	420.3	420.3
150°	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0	428.8	428.6	428.5
152.5°	436.1	435.9	435.8	435.9	436.3	436.6	437.0	437.3	437.0	436.6	436.3
155°	446.2	446.1	445.9	446.1	446.6	447.0	447.5	448.0	447.5	447.0	446.6
157.5°	455.0	455.0	455.0	455.0	455.3	455.7	455.9	456.2	455.9	455.7	455.3
160°	460.0	459.9	459.9	460.0	460.5	461.0	461.4	461.9	461.4	461.0	460.5
162.5°	464.6	464.5	464.5	464.6	465.1	465.6	466.0	466.5	466.0	465.6	465.1
165°	470.7	470.6	470.6	470.8	471.3	471.7	472.2	472.7	472.2	471.7	471.3
167.5°	475.2	475.2	475.1	475.3	475.8	476.3	476.8	477.3	476.8	476.3	475.8
170°	477.5	477.4	477.4	477.6	478.2	478.7	479.3	479.9	479.3	478.7	478.2
172.5°	479.4	479.3	479.2	479.3	479.9	480.5	481.0	481.6	481.0	480.5	479.9
175°	481.5	481.4	481.3	481.6	482.0	482.5	483.0	483.5	483.0	482.5	482.0
177.5°	482.8	482.7	482.6	482.8	483.2	483.5	483.9	484.3	483.9	483.5	483.2
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	720.8	717.4	715.0	710.2	706.8	705.4	702.7	702.0	704.6	702.7	702.5
5°	699.3	690.6	683.7	676.8	669.2	664.5	657.2	656.0	654.2	651.5	650.9
7.5°	673.7	662.3	653.4	641.9	632.0	624.0	615.0	610.7	608.3	604.8	600.2
10°	656.3	642.8	630.7	619.3	607.0	597.1	588.0	581.1	576.6	572.4	570.5
12.5°	639.2	625.4	610.1	596.2	582.4	571.2	561.3	556.7	551.8	546.8	542.6
15°	612.7	594.3	577.5	561.5	549.8	537.7	528.1	521.5	514.0	511.9	503.7
17.5°	584.6	566.5	546.8	530.0	516.4	503.1	492.6	485.1	479.3	471.6	467.9
20°	567.0	545.6	526.3	511.0	495.9	480.3	469.4	463.1	457.7	451.4	448.4
22.5°	548.2	527.3	507.6	489.6	474.3	458.8	451.1	444.6	438.5	432.6	428.6
25°	520.6	499.6	478.8	460.1	444.2	433.0	424.0	416.5	413.2	407.4	403.2
27.5°	493.4	471.0	449.4	430.8	418.3	407.3	399.9	394.0	387.9	382.9	379.3
30°	475.8	452.9	429.4	414.7	401.4	390.9	382.8	377.1	372.6	368.0	365.4
32.5°	458.2	434.6	413.8	397.8	385.3	376.2	367.9	362.3	357.6	352.6	349.4
35°	430.0	405.9	389.1	373.4	361.1	352.7	347.0	339.1	335.3	331.6	328.3
37.5°	403.9	381.4	363.2	349.5	338.8	330.4	323.1	318.8	314.0	310.8	308.0
40°	384.6	364.1	347.6	333.1	325.3	316.0	309.0	303.6	300.0	295.8	292.8
42.5°	367.3	348.2	332.2	319.2	309.4	301.5	294.9	289.5	284.9	281.9	279.3
45°	342.8	323.8	308.2	296.1	287.1	279.6	272.7	269.9	263.9	260.3	259.1
47.5°	317.4	300.5	285.3	274.3	265.0	257.9	251.4	245.9	242.6	239.0	237.1
50°	300.3	284.1	269.9	259.1	250.1	242.2	236.2	232.6	228.1	224.8	222.4
52.5°	283.2	268.2	254.1	243.7	235.8	228.1	221.3	217.7	213.4	211.3	209.6
55°	258.8	242.9	230.8	220.5	212.5	205.3	198.9	195.3	192.6	190.5	189.9
57.5°	231.1	218.5	207.3	198.0	189.6	182.8	177.3	173.9	171.5	171.2	169.4
60°	213.0	201.6	191.4	181.5	174.2	167.9	163.1	159.2	156.8	156.5	155.9
62.5°	195.0	184.0	174.5	165.8	159.3	153.2	148.7	144.3	142.8	141.3	140.0
65°	168.2	158.3	150.4	143.5	136.7	131.5	127.0	124.3	121.0	119.1	115.9
67.5°	141.9	134.2	126.7	120.9	115.4	110.6	106.9	102.8	100.6	99.1	96.7
70°	124.6	118.6	111.1	104.7	100.5	96.6	93.6	89.0	87.5	86.3	85.2
72.5°	108.2	102.9	96.6	91.5	87.3	83.6	80.1	78.0	76.5	75.3	74.5
75°	85.2	80.0	74.6	71.0	68.0	65.0	63.2	61.7	61.1	60.8	59.6
77.5°	62.5	59.8	55.5	52.6	50.6	49.4	47.8	47.0	47.0	45.6	45.2
80°	47.8	46.3	42.7	41.5	40.0	38.8	37.9	36.4	34.9	34.3	33.4
82.5°	35.6	34.1	32.6	30.7	29.5	28.7	27.8	27.3	27.4	26.6	26.1
85°	18.9	17.4	16.9	16.6	15.9	16.6	16.2	15.9	15.7	15.4	15.7
87.5°	6.6	6.7	6.6	7.2	6.6	6.9	7.0	6.8	6.9	7.0	6.8
90°	2.9	3.5	4.0	4.6	5.1	5.7	6.1	6.5	6.9	7.3	7.7
92.5°	3.7	3.7	4.3	4.8	5.2	5.7	6.1	6.5	6.9	7.3	7.6
95°	19.5	17.8	14.8	11.8	8.8	5.7	6.1	6.5	6.9	7.3	7.5
97.5°	44.4	41.6	35.6	29.6	23.6	17.7	15.4	13.2	10.9	8.6	7.5
100°	60.8	61.1	61.4	61.7	62.0	62.3	50.5	38.7	26.8	14.9	8.8
102.5°	78.6	78.8	79.0	79.1	79.4	79.5	77.3	75.1	72.8	70.6	66.8
105°	106.6	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.4	134.5	134.7	134.8	135.0	135.1	135.2	135.2	135.2	135.2	135.1
110°	153.4	153.4	153.6	153.8	153.9	154.1	153.8	153.6	153.4	153.1	153.0



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	171.9	172.1	172.1	172.3	172.4	172.5	172.1	171.8	171.5	171.3	171.0
115°	199.4	199.6	199.7	199.8	199.9	199.9	199.6	199.3	199.0	198.7	198.3
117.5°	225.4	225.5	225.8	226.1	226.4	226.7	226.3	225.9	225.5	225.1	224.7
120°	242.3	242.4	242.6	242.9	243.1	243.4	243.2	243.0	242.9	242.7	242.4
122.5°	259.0	259.2	259.4	259.4	259.6	259.7	259.5	259.4	259.2	259.0	258.7
125°	283.5	283.8	283.8	283.8	283.8	283.8	283.5	283.2	282.9	282.6	282.3
127.5°	305.4	305.5	305.5	305.5	305.4	305.3	305.1	305.0	304.8	304.7	304.3
130°	319.1	319.3	319.4	319.5	319.6	319.6	319.4	319.2	318.9	318.7	318.4
132.5°	333.1	333.3	333.1	333.0	332.7	332.6	332.6	332.5	332.4	332.4	332.2
135°	352.8	352.9	352.8	352.6	352.4	352.3	352.1	352.0	351.8	351.6	351.3
137.5°	370.5	370.7	370.5	370.3	370.2	370.0	370.1	370.1	370.2	370.2	370.0
140°	381.2	381.3	381.2	381.1	381.0	381.0	381.1	381.3	381.4	381.6	381.4
142.5°	391.6	391.7	391.8	391.9	392.1	392.1	392.1	392.2	392.2	392.3	392.1
145°	407.4	407.5	407.5	407.5	407.5	407.5	407.6	407.7	407.7	407.8	407.6
147.5°	420.3	420.3	420.4	420.5	420.6	420.6	420.7	420.9	421.0	421.0	420.8
150°	428.3	428.3	428.5	428.6	428.8	429.0	429.1	429.3	429.4	429.6	429.4
152.5°	435.9	435.8	435.9	436.1	436.3	436.4	436.6	436.7	436.9	437.0	436.9
155°	446.1	445.9	446.1	446.2	446.4	446.6	446.8	447.0	447.3	447.5	447.3
157.5°	455.0	455.0	455.0	455.0	455.0	455.0	455.3	455.5	455.7	456.0	455.8
160°	460.0	459.9	459.9	460.0	460.1	460.2	460.5	460.8	461.1	461.4	461.3
162.5°	464.6	464.5	464.5	464.6	464.7	464.8	465.2	465.6	466.1	466.5	466.4
165°	470.8	470.6	470.6	470.7	470.8	470.9	471.3	471.9	472.4	472.9	472.8
167.5°	475.3	475.1	475.2	475.2	475.3	475.4	476.0	476.6	477.1	477.7	477.7
170°	477.6	477.4	477.4	477.5	477.6	477.7	478.3	479.0	479.7	480.3	480.2
172.5°	479.3	479.2	479.3	479.4	479.6	479.7	480.3	480.9	481.4	482.0	482.0
175°	481.6	481.3	481.4	481.5	481.6	481.6	482.3	482.9	483.5	484.2	484.2
177.5°	482.8	482.6	482.7	482.8	482.8	482.9	483.3	483.8	484.2	484.7	484.7
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.3	699.6	698.9	699.8	698.9	699.6	702.3	702.5	702.7	704.6	702.0
5°	647.9	644.9	646.4	645.8	646.4	644.9	647.9	650.9	651.5	654.2	656.0
7.5°	600.1	596.4	592.4	593.7	592.4	596.4	600.1	600.2	604.8	608.3	610.7
10°	566.6	563.6	561.8	563.3	561.8	563.6	566.6	570.5	572.4	576.6	581.1
12.5°	538.4	536.7	535.1	534.5	535.1	536.7	538.4	542.6	546.8	551.8	556.7
15°	500.1	496.5	495.0	491.2	495.0	496.5	500.1	503.7	511.9	514.0	521.5
17.5°	464.8	463.6	459.7	458.0	459.7	463.6	464.8	467.9	471.6	479.3	485.1
20°	443.9	442.7	438.8	441.2	438.8	442.7	443.9	448.4	451.4	457.7	463.1
22.5°	426.5	423.9	422.6	421.9	422.6	423.9	426.5	428.6	432.6	438.5	444.6
25°	402.0	398.2	396.6	394.8	396.6	398.2	402.0	403.2	407.4	413.2	416.5
27.5°	377.6	375.5	373.5	373.0	373.5	375.5	377.6	379.3	382.9	387.9	394.0
30°	361.7	359.6	358.1	358.1	358.1	359.6	361.7	365.4	368.0	372.6	377.1
32.5°	347.5	345.9	344.4	344.1	344.4	345.9	347.5	349.4	352.6	357.6	362.3
35°	326.8	324.4	323.8	322.0	323.8	324.4	326.8	328.3	331.6	335.3	339.1
37.5°	305.3	303.3	303.2	303.1	303.2	303.3	305.3	308.0	310.8	314.0	318.8
40°	291.6	290.1	289.8	287.7	289.8	290.1	291.6	292.8	295.8	300.0	303.6
42.5°	276.9	276.2	275.1	274.2	275.1	276.2	276.9	279.3	281.9	284.9	289.5
45°	257.0	254.9	254.9	253.4	254.9	254.9	257.0	259.1	260.3	263.9	269.9
47.5°	236.4	234.8	235.0	233.4	235.0	234.8	236.4	237.1	239.0	242.6	245.9
50°	222.7	221.8	221.5	220.9	221.5	221.8	222.7	222.4	224.8	228.1	232.6
52.5°	209.0	208.6	209.7	208.3	209.7	208.6	209.0	209.6	211.3	213.4	217.7
55°	190.5	189.6	191.4	189.6	191.4	189.6	190.5	189.9	190.5	192.6	195.3
57.5°	169.2	168.4	170.0	169.1	170.0	168.4	169.2	169.4	171.2	171.5	173.9
60°	155.3	153.4	154.4	154.7	154.4	153.4	155.3	155.9	156.5	156.8	159.2
62.5°	138.6	137.6	138.2	136.9	138.2	137.6	138.6	140.0	141.3	142.8	144.3
65°	115.3	114.4	113.1	112.6	113.1	114.4	115.3	115.9	119.1	121.0	124.3
67.5°	96.8	94.7	94.6	95.1	94.6	94.7	96.8	96.7	99.1	100.6	102.8
70°	83.3	83.3	83.0	83.0	83.0	83.3	83.3	85.2	86.3	87.5	89.0
72.5°	74.0	73.8	73.2	73.0	73.2	73.8	74.0	74.5	75.3	76.5	78.0
75°	59.6	59.9	59.3	59.0	59.3	59.9	59.6	59.6	60.8	61.1	61.7
77.5°	44.0	42.7	43.4	42.7	43.4	42.7	44.0	45.2	45.6	47.0	47.0
80°	33.4	33.1	34.0	33.1	34.0	33.1	33.4	33.4	34.3	34.9	36.4
82.5°	26.5	26.1	26.5	25.9	26.5	26.1	26.5	26.1	26.6	27.4	27.3
85°	15.9	15.7	15.4	15.7	15.4	15.7	15.9	15.7	15.4	15.7	15.9
87.5°	7.1	6.9	7.0	7.1	7.0	6.9	7.1	6.8	7.0	6.9	6.8
90°	7.9	8.2	8.4	8.6	8.4	8.2	7.9	7.7	7.3	6.9	6.5
92.5°	7.7	7.8	7.9	8.0	7.9	7.8	7.7	7.6	7.3	6.9	6.5
95°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.3	6.9	6.5
97.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.6	10.9	13.2
100°	8.5	8.2	7.8	7.5	7.8	8.2	8.5	8.8	14.9	26.8	38.7
102.5°	61.3	55.9	50.5	45.1	50.5	55.9	61.3	66.8	70.6	72.8	75.1
105°	106.7	106.6	106.5	106.5	106.5	106.6	106.7	106.8	106.8	106.8	106.8
107.5°	134.9	134.7	134.4	134.2	134.4	134.7	134.9	135.1	135.2	135.2	135.2
110°	153.1	153.2	153.3	153.4	153.3	153.2	153.1	153.0	153.1	153.4	153.6



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	171.0	170.8	170.7	170.6	170.7	170.8	171.0	171.0	171.3	171.5	171.8
115°	197.8	197.3	196.9	196.4	196.9	197.3	197.8	198.3	198.7	199.0	199.3
117.5°	224.5	224.3	224.1	223.9	224.1	224.3	224.5	224.7	225.1	225.5	225.9
120°	242.0	241.6	241.2	240.8	241.2	241.6	242.0	242.4	242.7	242.9	243.0
122.5°	258.3	257.8	257.4	256.9	257.4	257.8	258.3	258.7	259.0	259.2	259.4
125°	282.0	281.8	281.5	281.3	281.5	281.8	282.0	282.3	282.6	282.9	283.2
127.5°	303.6	303.1	302.5	301.9	302.5	303.1	303.6	304.3	304.7	304.8	305.0
130°	318.0	317.6	317.2	316.8	317.2	317.6	318.0	318.4	318.7	318.9	319.2
132.5°	331.8	331.4	331.0	330.6	331.0	331.4	331.8	332.2	332.4	332.4	332.5
135°	350.9	350.4	349.9	349.4	349.9	350.4	350.9	351.3	351.6	351.8	352.0
137.5°	369.6	369.2	368.8	368.4	368.8	369.2	369.6	370.0	370.2	370.2	370.1
140°	381.0	380.5	380.0	379.5	380.0	380.5	381.0	381.4	381.6	381.4	381.3
142.5°	391.6	391.1	390.6	390.1	390.6	391.1	391.6	392.1	392.3	392.2	392.2
145°	407.1	406.6	406.2	405.7	406.2	406.6	407.1	407.6	407.8	407.7	407.7
147.5°	420.3	419.7	419.1	418.5	419.1	419.7	420.3	420.8	421.0	421.0	420.9
150°	428.7	428.1	427.5	426.8	427.5	428.1	428.7	429.4	429.6	429.4	429.3
152.5°	436.3	435.7	435.1	434.6	435.1	435.7	436.3	436.9	437.0	436.9	436.7
155°	446.6	446.0	445.4	444.7	445.4	446.0	446.6	447.3	447.5	447.3	447.0
157.5°	455.2	454.6	453.9	453.3	453.9	454.6	455.2	455.8	456.0	455.7	455.5
160°	460.7	460.0	459.4	458.8	459.4	460.0	460.7	461.3	461.4	461.1	460.8
162.5°	465.7	465.0	464.3	463.6	464.3	465.0	465.7	466.4	466.5	466.1	465.6
165°	472.1	471.4	470.8	470.2	470.8	471.4	472.1	472.8	472.9	472.4	471.9
167.5°	476.9	476.2	475.5	474.8	475.5	476.2	476.9	477.7	477.7	477.1	476.6
170°	479.5	478.8	478.1	477.4	478.1	478.8	479.5	480.2	480.3	479.7	479.0
172.5°	481.3	480.5	479.8	479.1	479.8	480.5	481.3	482.0	482.0	481.4	480.9
175°	483.5	482.8	482.0	481.3	482.0	482.8	483.5	484.2	484.2	483.5	482.9
177.5°	484.1	483.6	483.1	482.6	483.1	483.6	484.1	484.7	484.7	484.2	483.8
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	702.7	705.4	706.8	710.2	715.0	717.4	720.8	723.2	726.6	730.6	734.0
5°	657.2	664.5	669.2	676.8	683.7	690.6	699.3	705.7	714.1	723.7	731.3
7.5°	615.0	624.0	632.0	641.9	653.4	662.3	673.7	685.2	698.5	712.1	725.0
10°	588.0	597.1	607.0	619.3	630.7	642.8	656.3	669.9	686.4	701.8	719.2
12.5°	561.3	571.2	582.4	596.2	610.1	625.4	639.2	654.4	672.2	692.1	710.8
15°	528.1	537.7	549.8	561.5	577.5	594.3	612.7	632.9	652.7	675.0	698.2
17.5°	492.6	503.1	516.4	530.0	546.8	566.5	584.6	606.6	628.9	654.9	682.1
20°	469.4	480.3	495.9	511.0	526.3	545.6	567.0	589.5	613.3	640.6	671.1
22.5°	451.1	458.8	474.3	489.6	507.6	527.3	548.2	571.7	597.6	626.0	657.8
25°	424.0	433.0	444.2	460.1	478.8	499.6	520.6	545.6	573.9	602.8	636.8
27.5°	399.9	407.3	418.3	430.8	449.4	471.0	493.4	519.4	548.4	577.8	613.6
30°	382.8	390.9	401.4	414.7	429.4	452.9	475.8	501.4	530.8	561.3	597.9
32.5°	367.9	376.2	385.3	397.8	413.8	434.6	458.2	483.3	513.3	544.6	580.4
35°	347.0	352.7	361.1	373.4	389.1	405.9	430.0	456.5	485.7	518.2	554.0
37.5°	323.1	330.4	338.8	349.5	363.2	381.4	403.9	430.6	457.7	488.9	521.5
40°	309.0	316.0	325.3	333.1	347.6	364.1	384.6	412.6	439.7	468.8	498.6
42.5°	294.9	301.5	309.4	319.2	332.2	348.2	367.3	393.3	422.3	449.8	474.8
45°	272.7	279.6	287.1	296.1	308.2	323.8	342.8	366.5	391.8	417.1	436.0
47.5°	251.4	257.9	265.0	274.3	285.3	300.5	317.4	338.4	363.0	384.4	398.0
50°	236.2	242.2	250.1	259.1	269.9	284.1	300.3	321.1	341.6	361.1	373.4
52.5°	221.3	228.1	235.8	243.7	254.1	268.2	283.2	301.1	320.6	336.5	346.7
55°	198.9	205.3	212.5	220.5	230.8	242.9	258.8	272.9	288.3	301.8	307.8
57.5°	177.3	182.8	189.6	198.0	207.3	218.5	231.1	244.7	255.6	265.1	272.0
60°	163.1	167.9	174.2	181.5	191.4	201.6	213.0	225.7	234.1	242.2	248.6
62.5°	148.7	153.2	159.3	165.8	174.5	184.0	195.0	205.3	213.4	218.9	226.2
65°	127.0	131.5	136.7	143.5	150.4	158.3	168.2	175.7	181.5	187.5	192.0
67.5°	106.9	110.6	115.4	120.9	126.7	134.2	141.9	148.1	152.1	155.7	161.1
70°	93.6	96.6	100.5	104.7	111.1	118.6	124.6	129.4	132.1	135.7	142.4
72.5°	80.1	83.6	87.3	91.5	96.6	102.9	108.2	113.0	114.8	117.6	121.8
75°	63.2	65.0	68.0	71.0	74.6	80.0	85.2	86.3	87.9	90.3	93.3
77.5°	47.8	49.4	50.6	52.6	55.5	59.8	62.5	64.3	64.7	65.6	68.5
80°	37.9	38.8	40.0	41.5	42.7	46.3	47.8	49.7	50.2	51.2	52.7
82.5°	27.8	28.7	29.5	30.7	32.6	34.1	35.6	37.4	37.5	38.2	38.4
85°	16.2	16.6	15.9	16.6	16.9	17.4	18.9	20.4	20.2	19.9	20.8
87.5°	7.0	6.9	6.6	7.2	6.6	6.7	6.6	6.7	7.1	7.4	7.8
90°	6.1	5.7	5.1	4.6	4.0	3.5	2.9	2.3	1.7	1.0	0.4
92.5°	6.1	5.7	5.2	4.8	4.3	3.7	3.7	4.2	4.6	5.1	5.5
95°	6.1	5.7	8.8	11.8	14.8	17.8	19.5	19.7	20.0	20.2	20.4
97.5°	15.4	17.7	23.6	29.6	35.6	41.6	44.4	44.0	43.5	43.1	42.6
100°	50.5	62.3	62.0	61.7	61.4	61.1	60.8	60.6	60.4	60.1	59.8
102.5°	77.3	79.5	79.4	79.1	79.0	78.8	78.6	78.3	78.0	77.6	77.3
105°	106.8	106.8	106.8	106.8	106.8	106.8	106.6	106.3	106.0	105.7	105.4
107.5°	135.2	135.1	135.0	134.8	134.7	134.5	134.4	134.4	134.4	134.4	134.4
110°	153.8	154.1	153.9	153.8	153.6	153.4	153.4	153.4	153.4	153.4	153.4



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	172.1	172.5	172.4	172.3	172.1	172.1	171.9	171.7	171.5	171.3	171.2
115°	199.6	199.9	199.9	199.8	199.7	199.6	199.4	199.0	198.6	198.2	197.8
117.5°	226.3	226.7	226.4	226.1	225.8	225.5	225.4	225.4	225.4	225.4	225.5
120°	243.2	243.4	243.1	242.9	242.6	242.4	242.3	242.4	242.5	242.6	242.6
122.5°	259.5	259.7	259.6	259.4	259.4	259.2	259.0	258.7	258.4	258.1	257.9
125°	283.5	283.8	283.8	283.8	283.8	283.8	283.5	283.0	282.4	281.9	281.3
127.5°	305.1	305.3	305.4	305.5	305.5	305.5	305.4	305.0	304.6	304.2	303.7
130°	319.4	319.6	319.6	319.5	319.4	319.3	319.1	318.7	318.3	317.9	317.5
132.5°	332.6	332.6	332.7	333.0	333.1	333.3	333.1	332.6	332.2	331.8	331.3
135°	352.1	352.3	352.4	352.6	352.8	352.9	352.8	352.3	351.8	351.3	350.9
137.5°	370.1	370.0	370.2	370.3	370.5	370.7	370.5	370.1	369.6	369.2	368.8
140°	381.1	381.0	381.0	381.1	381.2	381.3	381.2	381.0	380.9	380.7	380.6
142.5°	392.1	392.1	392.1	391.9	391.8	391.7	391.6	391.5	391.4	391.3	391.2
145°	407.6	407.5	407.5	407.5	407.5	407.5	407.4	407.3	407.1	406.9	406.8
147.5°	420.7	420.6	420.6	420.5	420.4	420.3	420.3	420.3	420.3	420.3	420.4
150°	429.1	429.0	428.8	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0
152.5°	436.6	436.4	436.3	436.1	435.9	435.8	435.9	436.3	436.6	437.0	437.3
155°	446.8	446.6	446.4	446.2	446.1	445.9	446.1	446.6	447.0	447.5	448.0
157.5°	455.3	455.0	455.0	455.0	455.0	455.0	455.0	455.3	455.7	455.9	456.2
160°	460.5	460.2	460.1	460.0	459.9	459.9	460.0	460.5	461.0	461.4	461.9
162.5°	465.2	464.8	464.7	464.6	464.5	464.5	464.6	465.1	465.6	466.0	466.5
165°	471.3	470.9	470.8	470.7	470.6	470.6	470.8	471.3	471.7	472.2	472.7
167.5°	476.0	475.4	475.3	475.2	475.2	475.1	475.3	475.8	476.3	476.8	477.3
170°	478.3	477.7	477.6	477.5	477.4	477.4	477.6	478.2	478.7	479.3	479.9
172.5°	480.3	479.7	479.6	479.4	479.3	479.2	479.3	479.9	480.5	481.0	481.6
175°	482.3	481.6	481.6	481.5	481.4	481.3	481.6	482.0	482.5	483.0	483.5
177.5°	483.3	482.9	482.8	482.8	482.7	482.6	482.8	483.2	483.5	483.9	484.3
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	736.7	738.9	742.0	745.6	748.5	751.6	753.3	753.3	754.7	757.9	761.9
5°	738.8	746.6	754.2	763.7	771.3	780.0	786.6	793.0	798.7	805.9	813.4
7.5°	738.2	751.1	764.7	779.9	796.6	809.9	823.6	834.3	844.9	858.7	869.7
10°	735.8	752.7	771.0	790.2	811.3	829.7	846.2	861.3	875.7	890.7	904.3
12.5°	731.4	752.9	775.3	798.4	825.1	846.1	867.4	883.4	900.2	916.7	933.4
15°	724.9	750.2	777.3	809.5	842.0	865.5	886.5	907.3	923.0	941.6	957.6
17.5°	711.5	744.1	778.2	813.3	844.5	871.9	893.9	913.7	930.3	950.9	972.6
20°	703.5	738.8	774.3	811.9	841.7	869.7	891.0	911.5	932.2	959.1	985.6
22.5°	692.5	730.1	767.8	803.5	835.0	862.0	884.1	909.1	936.4	966.8	998.8
25°	675.0	713.8	751.1	785.1	815.8	843.5	873.6	907.3	940.4	980.4	1026.4
27.5°	652.8	690.2	723.5	759.4	790.0	825.1	862.7	899.2	947.0	1002.0	1059.5
30°	636.1	671.7	703.3	737.3	771.9	810.7	852.9	895.9	952.8	1017.4	1085.8
32.5°	616.9	649.0	680.4	713.2	753.1	795.7	840.6	893.2	961.2	1034.7	1105.5
35°	583.5	612.4	642.8	679.2	721.6	767.9	825.1	889.2	971.4	1050.5	1114.0
37.5°	548.5	571.2	601.8	640.2	686.4	740.1	804.9	882.8	967.2	1038.2	1065.2
40°	521.5	542.9	575.0	615.4	661.2	719.9	792.7	872.7	957.6	1006.9	1004.8
42.5°	494.8	516.4	547.4	588.0	635.6	701.3	776.3	859.4	931.1	949.8	910.7
45°	453.8	474.0	504.4	545.3	596.4	665.4	744.2	823.9	869.7	839.3	761.7
47.5°	412.0	431.6	459.8	499.9	555.7	627.9	702.4	767.9	774.3	709.0	615.8
50°	384.6	402.9	429.8	472.5	526.6	597.1	669.0	720.4	704.5	624.7	528.7
52.5°	357.8	375.5	400.6	440.9	496.3	565.3	629.5	669.9	633.0	548.2	461.8
55°	318.4	335.3	360.5	397.5	447.7	511.0	567.3	582.0	527.8	442.4	372.6
57.5°	280.9	293.2	318.2	350.9	399.4	455.1	495.4	492.8	433.0	356.1	306.0
60°	256.1	267.2	291.0	321.1	367.1	417.1	445.4	433.3	372.9	309.3	261.2
62.5°	233.0	243.4	263.3	291.0	330.6	374.0	394.6	378.0	320.8	265.1	226.8
65°	198.0	205.6	221.5	247.1	278.1	308.2	326.5	302.1	251.6	209.5	180.5
67.5°	165.3	171.8	186.0	204.4	225.8	246.5	254.0	231.1	191.8	163.4	143.1
70°	144.2	150.2	159.8	177.0	191.1	205.8	209.5	189.0	156.2	134.5	121.8
72.5°	123.9	129.4	137.9	150.0	159.8	168.3	170.0	150.9	125.9	110.9	101.2
75°	94.5	99.3	104.7	109.2	115.6	117.1	116.5	101.7	88.2	78.3	72.8
77.5°	69.5	71.5	74.8	76.5	76.8	76.8	73.7	64.3	57.4	53.2	51.0
80°	53.6	55.1	56.0	56.6	56.9	53.9	50.5	44.8	42.5	40.0	37.3
82.5°	38.9	39.9	40.8	41.0	39.3	36.8	33.7	30.9	29.2	28.0	26.9
85°	21.1	21.4	21.1	19.6	17.4	16.6	15.9	15.4	15.1	14.7	14.7
87.5°	7.7	7.1	6.0	6.3	6.5	6.3	6.5	6.3	6.2	6.3	6.3
90°	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.7	6.1	6.5
92.5°	5.1	4.6	4.2	3.7	3.7	4.3	4.8	5.2	5.7	6.1	6.5
95°	20.2	20.0	19.7	19.5	17.8	14.8	11.8	8.8	5.7	6.1	6.5
97.5°	43.1	43.5	44.0	44.4	41.6	35.6	29.6	23.6	17.7	15.4	13.2
100°	60.1	60.4	60.6	60.8	61.1	61.4	61.7	62.0	62.3	50.5	38.7
102.5°	77.6	78.0	78.3	78.6	78.8	79.0	79.1	79.4	79.5	77.3	75.1
105°	105.7	106.0	106.3	106.6	106.8	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.4	134.4	134.4	134.4	134.5	134.7	134.8	135.0	135.1	135.2	135.2
110°	153.4	153.4	153.4	153.4	153.4	153.6	153.8	153.9	154.1	153.8	153.6



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.3	171.5	171.7	171.9	172.1	172.1	172.3	172.4	172.5	172.1	171.8
115°	198.2	198.6	199.0	199.4	199.6	199.7	199.8	199.9	199.9	199.6	199.3
117.5°	225.4	225.4	225.4	225.4	225.5	225.8	226.1	226.4	226.7	226.3	225.9
120°	242.6	242.5	242.4	242.3	242.4	242.6	242.9	243.1	243.4	243.2	243.0
122.5°	258.1	258.4	258.7	259.0	259.2	259.4	259.4	259.6	259.7	259.5	259.4
125°	281.9	282.4	283.0	283.5	283.8	283.8	283.8	283.8	283.8	283.5	283.2
127.5°	304.2	304.6	305.0	305.4	305.5	305.5	305.5	305.4	305.3	305.1	305.0
130°	317.9	318.3	318.7	319.1	319.3	319.4	319.5	319.6	319.6	319.4	319.2
132.5°	331.8	332.2	332.6	333.1	333.3	333.1	333.0	332.7	332.6	332.6	332.5
135°	351.3	351.8	352.3	352.8	352.9	352.8	352.6	352.4	352.3	352.1	352.0
137.5°	369.2	369.6	370.1	370.5	370.7	370.5	370.3	370.2	370.0	370.1	370.1
140°	380.7	380.9	381.0	381.2	381.3	381.2	381.1	381.0	381.0	381.1	381.3
142.5°	391.3	391.4	391.5	391.6	391.7	391.8	391.9	392.1	392.1	392.1	392.2
145°	406.9	407.1	407.3	407.4	407.5	407.5	407.5	407.5	407.5	407.6	407.7
147.5°	420.3	420.3	420.3	420.3	420.3	420.4	420.5	420.6	420.6	420.7	420.9
150°	428.8	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0	429.1	429.3
152.5°	437.0	436.6	436.3	435.9	435.8	435.9	436.1	436.3	436.4	436.6	436.7
155°	447.5	447.0	446.6	446.1	445.9	446.1	446.2	446.4	446.6	446.8	447.0
157.5°	455.9	455.7	455.3	455.0	455.0	455.0	455.0	455.0	455.0	455.3	455.5
160°	461.4	461.0	460.5	460.0	459.9	459.9	460.0	460.1	460.2	460.5	460.8
162.5°	466.0	465.6	465.1	464.6	464.5	464.5	464.6	464.7	464.8	465.2	465.6
165°	472.2	471.7	471.3	470.8	470.6	470.6	470.7	470.8	470.9	471.3	471.9
167.5°	476.8	476.3	475.8	475.3	475.1	475.2	475.2	475.3	475.4	476.0	476.6
170°	479.3	478.7	478.2	477.6	477.4	477.4	477.5	477.6	477.7	478.3	479.0
172.5°	481.0	480.5	479.9	479.3	479.2	479.3	479.4	479.6	479.7	480.3	480.9
175°	483.0	482.5	482.0	481.6	481.3	481.4	481.5	481.6	481.6	482.3	482.9
177.5°	483.9	483.5	483.2	482.8	482.6	482.7	482.8	482.8	482.9	483.3	483.8
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	733.1	733.1	733.1	733.1	733.1	733.1	733.1
2.5°	765.1	765.1	769.2	768.9	771.6	770.6	771.1
5°	822.4	827.5	832.0	835.0	839.6	840.8	840.2
7.5°	881.9	893.3	898.8	906.4	907.8	911.7	911.3
10°	918.7	929.9	938.3	944.9	948.2	952.4	952.8
12.5°	947.6	957.0	964.6	970.7	974.7	976.0	976.8
15°	970.2	980.7	989.4	998.1	1003.3	1007.2	1009.3
17.5°	992.9	1009.2	1024.6	1036.5	1043.5	1049.6	1049.5
20°	1010.5	1029.2	1048.5	1062.0	1075.8	1081.8	1082.8
22.5°	1029.3	1057.8	1082.6	1103.6	1121.8	1128.1	1130.4
25°	1068.3	1105.6	1143.8	1173.3	1194.4	1206.7	1208.6
27.5°	1115.4	1165.9	1206.1	1233.3	1250.9	1260.0	1261.9
30°	1148.7	1195.2	1231.4	1251.9	1260.0	1261.2	1256.6
32.5°	1163.6	1198.4	1212.8	1211.6	1195.7	1185.1	1181.1
35°	1145.3	1138.1	1102.9	1060.7	1028.6	1008.1	1002.7
37.5°	1042.3	980.0	915.2	851.6	817.7	800.5	770.9
40°	940.7	851.9	784.5	730.9	692.8	662.0	654.8
42.5°	826.1	734.4	667.0	621.2	590.7	569.6	560.5
45°	663.8	585.0	529.3	494.1	470.6	455.3	448.4
47.5°	530.9	469.9	429.4	403.3	385.4	372.1	368.4
50°	458.0	409.2	374.9	353.0	339.5	329.2	325.0
52.5°	397.8	358.5	332.1	314.0	301.2	294.8	291.3
55°	328.3	294.3	275.4	260.9	253.7	248.6	246.1
57.5°	268.5	243.9	230.0	220.1	213.4	210.2	209.0
60°	235.0	215.8	203.1	195.3	190.8	186.6	185.4
62.5°	205.4	190.3	180.5	173.6	169.1	167.3	166.6
65°	165.5	155.6	148.4	144.2	140.5	139.9	139.7
67.5°	131.6	125.7	121.9	117.6	116.3	114.2	113.8
70°	112.6	108.6	104.1	102.6	101.1	99.0	99.3
72.5°	95.5	91.6	88.5	86.5	86.0	85.1	85.8
75°	69.8	68.6	67.4	65.9	65.3	65.3	65.0
77.5°	49.8	48.8	47.5	46.6	46.4	45.2	45.6
80°	36.1	34.6	34.0	34.3	33.4	33.1	33.1
82.5°	26.7	26.1	25.6	25.7	25.4	25.2	25.4
85°	14.7	14.4	14.4	14.2	14.2	13.9	13.9
87.5°	6.7	7.0	6.6	6.4	6.4	6.7	7.1
90°	6.9	7.3	7.7	7.9	8.2	8.4	8.6
92.5°	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	10.9	8.6	7.5	7.5	7.5	7.5	7.5
100°	26.8	14.9	8.8	8.5	8.2	7.8	7.5
102.5°	72.8	70.6	66.8	61.3	55.9	50.5	45.1
105°	106.8	106.8	106.8	106.7	106.6	106.5	106.5
107.5°	135.2	135.2	135.1	134.9	134.7	134.4	134.2
110°	153.4	153.1	153.0	153.1	153.2	153.3	153.4



TEST NUMBER: P333660-927

CATALOG NUMBER: S125RDIW-S610D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	171.5	171.3	171.0	171.0	170.8	170.7	170.6
115°	199.0	198.7	198.3	197.8	197.3	196.9	196.4
117.5°	225.5	225.1	224.7	224.5	224.3	224.1	223.9
120°	242.9	242.7	242.4	242.0	241.6	241.2	240.8
122.5°	259.2	259.0	258.7	258.3	257.8	257.4	256.9
125°	282.9	282.6	282.3	282.0	281.8	281.5	281.3
127.5°	304.8	304.7	304.3	303.6	303.1	302.5	301.9
130°	318.9	318.7	318.4	318.0	317.6	317.2	316.8
132.5°	332.4	332.4	332.2	331.8	331.4	331.0	330.6
135°	351.8	351.6	351.3	350.9	350.4	349.9	349.4
137.5°	370.2	370.2	370.0	369.6	369.2	368.8	368.4
140°	381.4	381.6	381.4	381.0	380.5	380.0	379.5
142.5°	392.2	392.3	392.1	391.6	391.1	390.6	390.1
145°	407.7	407.8	407.6	407.1	406.6	406.2	405.7
147.5°	421.0	421.0	420.8	420.3	419.7	419.1	418.5
150°	429.4	429.6	429.4	428.7	428.1	427.5	426.8
152.5°	436.9	437.0	436.9	436.3	435.7	435.1	434.6
155°	447.3	447.5	447.3	446.6	446.0	445.4	444.7
157.5°	455.7	456.0	455.8	455.2	454.6	453.9	453.3
160°	461.1	461.4	461.3	460.7	460.0	459.4	458.8
162.5°	466.1	466.5	466.4	465.7	465.0	464.3	463.6
165°	472.4	472.9	472.8	472.1	471.4	470.8	470.2
167.5°	477.1	477.7	477.7	476.9	476.2	475.5	474.8
170°	479.7	480.3	480.2	479.5	478.8	478.1	477.4
172.5°	481.4	482.0	482.0	481.3	480.5	479.8	479.1
175°	483.5	484.2	484.2	483.5	482.8	482.0	481.3
177.5°	484.2	484.7	484.7	484.1	483.6	483.1	482.6
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5

(END OF REPORT)