

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333449-830

Luminaire Tested: **S125DIW-S1090D1340U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333449-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D1340U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8616.8 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49																												
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42																												
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	44	42	40	35																												
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30																												
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26																												
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23																												
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20																												
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18																												
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16																												
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14																												
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.3	1.7
10°-20°	429.6	5.0
20°-30°	697.6	8.1
30°-40°	850.9	9.9
40°-50°	774.1	9.0
50°-60°	616.6	7.2
60°-70°	429.5	5.0
70°-80°	229.0	2.7
80°-90°	61.2	0.7
90°-100°	105.2	1.2
100°-110°	310.7	3.6
110°-120°	526.3	6.1
120°-130°	692.7	8.0
130°-140°	776.1	9.0
140°-150°	760.7	8.8
150°-160°	638.9	7.4
160°-170°	424.7	4.9
170°-180°	148.6	1.7
0°-30°	1271.5	14.8
0°-40°	2122.4	24.6
0°-60°	3513.1	40.8
0°-90°	4232.8	49.1
90°-120°	942.3	10.9
90°-150°	3171.8	36.8
90°-180°	4384.0	50.9
0°-180°	8616.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	29	1	29	1	29	18
95°	105	80	105	80	105	107
105°	303	279	303	279	303	321
115°	532	527	532	527	532	526
125°	774	769	774	769	774	691
135°	1004	1000	1004	1000	1004	774
145°	1216	1212	1216	1212	1216	759
155°	1386	1386	1386	1386	1386	638
165°	1504	1508	1504	1508	1504	424
175°	1561	1567	1561	1567	1561	148
180°	1571	1571	1571	1571	1571	



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	18.1	18.9	19.3	19.1	19.5	19.2	21.0	20.7	22.0	23.3	24.9
90°	29.3	28.6	27.7	26.9	26.1	25.0	23.7	22.2	20.9	19.6	17.6
92.5°	57.7	57.1	56.6	55.9	55.3	54.1	52.3	50.5	48.7	46.9	44.6
95°	105.2	104.6	104.1	103.5	102.9	101.8	99.8	97.9	96.0	94.2	91.4
97.5°	159.5	159.1	158.8	158.4	158.2	157.0	155.2	153.4	151.7	149.9	146.2
100°	200.5	200.0	199.4	198.9	198.3	196.8	194.4	192.0	189.5	187.1	183.5
102.5°	241.6	240.8	240.1	239.3	238.6	236.9	234.1	231.5	228.8	226.2	224.4
105°	303.2	302.4	301.6	300.8	299.9	298.7	297.1	295.5	293.9	292.2	290.6
107.5°	366.3	366.4	366.4	366.5	366.6	366.2	365.3	364.5	363.7	362.9	361.7
110°	413.2	413.5	413.8	414.1	414.3	414.1	413.2	412.5	411.6	410.8	410.0



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.2	459.7	460.2	460.7	461.2	461.2	460.8	460.4	460.1	459.7	458.6
115°	531.9	532.2	532.3	532.6	532.9	533.2	533.5	533.8	534.0	534.3	533.8
117.5°	602.8	603.9	604.9	606.1	607.1	607.6	607.3	607.1	606.9	606.7	606.1
120°	651.7	652.7	653.8	654.9	656.0	656.6	656.6	656.6	656.6	656.6	656.3
122.5°	700.6	701.4	702.3	703.1	704.1	704.6	704.8	705.0	705.2	705.5	704.7
125°	773.9	774.2	774.5	774.8	775.1	775.4	776.0	776.5	777.0	777.6	777.3
127.5°	844.3	844.9	845.5	846.0	846.5	847.0	847.2	847.4	847.7	848.0	847.7
130°	891.3	891.8	892.4	893.0	893.4	893.9	894.2	894.4	894.7	894.9	894.4
132.5°	935.3	936.0	936.8	937.6	938.4	938.9	939.1	939.4	939.7	940.0	940.1
135°	1003.8	1004.8	1006.0	1007.0	1008.1	1008.7	1008.7	1008.7	1008.7	1008.7	1008.4
137.5°	1070.8	1072.1	1073.5	1074.9	1076.2	1076.8	1076.4	1076.1	1075.7	1075.4	1074.9
140°	1113.8	1115.2	1116.5	1117.9	1119.3	1119.6	1119.1	1118.6	1118.0	1117.5	1116.6
142.5°	1154.9	1156.2	1157.6	1159.0	1160.4	1160.8	1160.6	1160.2	1159.9	1159.5	1158.5
145°	1216.5	1217.3	1218.1	1219.0	1219.7	1220.2	1220.2	1220.2	1220.2	1220.2	1219.4
147.5°	1269.1	1270.9	1272.8	1274.6	1276.5	1277.1	1276.4	1275.7	1275.2	1274.5	1273.8
150°	1308.2	1308.7	1309.3	1309.9	1310.4	1310.7	1310.7	1310.7	1310.7	1310.7	1309.6
152.5°	1340.5	1341.4	1342.5	1343.4	1344.4	1344.5	1343.9	1343.2	1342.7	1342.0	1341.5
155°	1386.5	1387.8	1389.2	1390.5	1391.9	1392.0	1390.9	1389.9	1388.7	1387.7	1387.4
157.5°	1424.8	1426.6	1428.4	1430.2	1432.0	1432.4	1431.3	1430.2	1429.1	1428.0	1427.8
160°	1451.2	1452.6	1454.0	1455.4	1456.7	1456.8	1455.8	1454.6	1453.6	1452.5	1452.2
162.5°	1473.8	1475.4	1476.9	1478.5	1480.1	1480.2	1478.8	1477.6	1476.3	1475.0	1474.9
165°	1503.8	1505.4	1507.1	1508.7	1510.3	1510.6	1509.6	1508.4	1507.4	1506.3	1506.0
167.5°	1527.8	1529.5	1531.2	1532.9	1534.6	1534.6	1533.0	1531.3	1529.7	1528.0	1528.0
170°	1540.5	1542.4	1544.4	1546.2	1548.1	1548.2	1546.6	1545.0	1543.4	1541.7	1541.7
172.5°	1551.2	1552.9	1554.6	1556.3	1558.0	1558.0	1556.4	1554.8	1553.1	1551.5	1551.5
175°	1561.3	1563.2	1565.1	1567.0	1568.9	1569.1	1567.4	1565.8	1564.1	1562.5	1562.5
177.5°	1567.2	1568.7	1570.2	1571.7	1573.3	1573.4	1572.1	1570.7	1569.4	1568.1	1568.4
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	25.5	24.1	21.8	19.8	16.8	14.9	13.9	13.9	12.9	12.8	13.8
90°	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	42.3	40.0	37.6	35.6	34.1	32.6	31.1	29.6	31.1	32.6	34.1
95°	88.7	86.0	83.3	81.6	81.1	80.6	80.0	79.5	80.0	80.6	81.1
97.5°	142.4	138.6	134.9	132.9	132.7	132.5	132.2	132.1	132.2	132.5	132.7
100°	180.0	176.4	173.0	171.2	171.2	171.2	171.2	171.2	171.2	171.2	171.2
102.5°	222.6	220.8	219.0	217.5	216.5	215.4	214.3	213.2	214.3	215.4	216.5
105°	289.0	287.3	285.7	284.2	282.9	281.4	280.1	278.8	280.1	281.4	282.9
107.5°	360.3	359.1	357.9	356.6	355.2	353.8	352.5	351.1	352.5	353.8	355.2
110°	409.2	408.4	407.6	406.4	405.1	403.8	402.4	401.1	402.4	403.8	405.1





TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.6	456.6	455.6	454.7	454.0	453.3	452.6	451.9	452.6	453.3	454.0
115°	533.2	532.6	532.2	531.3	530.2	529.1	528.0	527.0	528.0	529.1	530.2
117.5°	605.7	605.2	604.7	604.3	603.7	603.2	602.8	602.3	602.8	603.2	603.7
120°	656.0	655.7	655.4	654.7	653.3	652.0	650.5	649.2	650.5	652.0	653.3
122.5°	704.1	703.3	702.7	702.0	701.5	701.1	700.6	700.1	700.6	701.1	701.5
125°	777.0	776.7	776.5	775.5	773.9	772.3	770.6	769.0	770.6	772.3	773.9
127.5°	847.3	847.1	846.7	846.1	845.2	844.2	843.3	842.4	843.3	844.2	845.2
130°	893.9	893.3	892.8	891.8	890.5	889.1	887.8	886.4	887.8	889.1	890.5
132.5°	940.2	940.3	940.4	939.3	937.1	934.9	932.6	930.4	932.6	934.9	937.1
135°	1008.1	1007.9	1007.6	1006.6	1005.0	1003.3	1001.7	1000.1	1001.7	1003.3	1005.0
137.5°	1074.2	1073.7	1073.0	1072.0	1070.4	1068.8	1067.2	1065.6	1067.2	1068.8	1070.4
140°	1115.9	1115.0	1114.2	1113.1	1111.8	1110.4	1109.1	1107.7	1109.1	1110.4	1111.8
142.5°	1157.4	1156.4	1155.4	1154.3	1153.2	1152.1	1150.9	1149.8	1150.9	1152.1	1153.2
145°	1218.5	1217.8	1216.9	1216.0	1214.8	1213.8	1212.7	1211.6	1212.7	1213.8	1214.8
147.5°	1273.2	1272.5	1271.9	1271.2	1270.6	1270.1	1269.4	1268.9	1269.4	1270.1	1270.6
150°	1308.5	1307.4	1306.3	1305.9	1306.2	1306.5	1306.7	1307.0	1306.7	1306.5	1306.2
152.5°	1341.0	1340.7	1340.2	1339.8	1339.4	1339.1	1338.7	1338.3	1338.7	1339.1	1339.4
155°	1387.1	1386.9	1386.6	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5
157.5°	1427.5	1427.2	1426.9	1427.1	1427.7	1428.3	1428.9	1429.5	1428.9	1428.3	1427.7
160°	1452.0	1451.7	1451.4	1451.7	1452.5	1453.3	1454.2	1454.9	1454.2	1453.3	1452.5
162.5°	1474.9	1474.8	1474.8	1475.1	1475.6	1476.2	1476.9	1477.4	1476.9	1476.2	1475.6
165°	1505.7	1505.4	1505.2	1505.3	1505.9	1506.4	1506.9	1507.5	1506.9	1506.4	1505.9
167.5°	1528.0	1528.0	1528.0	1528.6	1529.7	1530.8	1531.8	1533.0	1531.8	1530.8	1529.7
170°	1541.7	1541.7	1541.7	1542.3	1543.4	1544.5	1545.6	1546.6	1545.6	1544.5	1543.4
172.5°	1551.5	1551.5	1551.5	1552.1	1553.1	1554.3	1555.3	1556.4	1555.3	1554.3	1553.1
175°	1562.5	1562.5	1562.5	1563.1	1564.1	1565.3	1566.3	1567.4	1566.3	1565.3	1564.1
177.5°	1568.6	1568.8	1569.1	1569.5	1570.5	1571.3	1572.2	1573.0	1572.2	1571.3	1570.5
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	14.7	16.1	16.0	16.9	17.2	18.7	18.5	20.7	22.1	23.3	23.0
90°	9.9	12.0	13.9	15.7	17.6	19.6	20.9	22.2	23.7	25.0	26.1
92.5°	35.6	37.6	40.0	42.3	44.6	46.9	48.7	50.5	52.3	54.1	55.3
95°	81.6	83.3	86.0	88.7	91.4	94.2	96.0	97.9	99.8	101.8	102.9
97.5°	132.9	134.9	138.6	142.4	146.2	149.9	151.7	153.4	155.2	157.0	158.2
100°	171.2	173.0	176.4	180.0	183.5	187.1	189.5	192.0	194.4	196.8	198.3
102.5°	217.5	219.0	220.8	222.6	224.4	226.2	228.8	231.5	234.1	236.9	238.6
105°	284.2	285.7	287.3	289.0	290.6	292.2	293.9	295.5	297.1	298.7	299.9
107.5°	356.6	357.9	359.1	360.3	361.7	362.9	363.7	364.5	365.3	366.2	366.6
110°	406.4	407.6	408.4	409.2	410.0	410.8	411.6	412.5	413.2	414.1	414.3



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	454.7	455.6	456.6	457.6	458.6	459.7	460.1	460.4	460.8	461.2	461.2
115°	531.3	532.2	532.6	533.2	533.8	534.3	534.0	533.8	533.5	533.2	532.9
117.5°	604.3	604.7	605.2	605.7	606.1	606.7	606.9	607.1	607.3	607.6	607.1
120°	654.7	655.4	655.7	656.0	656.3	656.6	656.6	656.6	656.6	656.6	656.0
122.5°	702.0	702.7	703.3	704.1	704.7	705.5	705.2	705.0	704.8	704.6	704.1
125°	775.5	776.5	776.7	777.0	777.3	777.6	777.0	776.5	776.0	775.4	775.1
127.5°	846.1	846.7	847.1	847.3	847.7	848.0	847.7	847.4	847.2	847.0	846.5
130°	891.8	892.8	893.3	893.9	894.4	894.9	894.7	894.4	894.2	893.9	893.4
132.5°	939.3	940.4	940.3	940.2	940.1	940.0	939.7	939.4	939.1	938.9	938.4
135°	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7	1008.7	1008.7	1008.7	1008.1
137.5°	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7	1076.1	1076.4	1076.8	1076.2
140°	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0	1118.6	1119.1	1119.6	1119.3
142.5°	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9	1160.2	1160.6	1160.8	1160.4
145°	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2	1220.2	1220.2	1220.2	1219.7
147.5°	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2	1275.7	1276.4	1277.1	1276.5
150°	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7	1310.7	1310.7	1310.7	1310.4
152.5°	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7	1343.2	1343.9	1344.5	1344.4
155°	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7	1389.9	1390.9	1392.0	1391.9
157.5°	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1	1430.2	1431.3	1432.4	1432.0
160°	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6	1454.6	1455.8	1456.8	1456.7
162.5°	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3	1477.6	1478.8	1480.2	1480.1
165°	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4	1508.4	1509.6	1510.6	1510.3
167.5°	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7	1531.3	1533.0	1534.6	1534.6
170°	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4	1545.0	1546.6	1548.2	1548.1
172.5°	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1	1554.8	1556.4	1558.0	1558.0
175°	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1	1565.8	1567.4	1569.1	1568.9
177.5°	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4	1570.7	1572.1	1573.4	1573.3
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	24.2	23.8	24.0	25.2	24.0	23.8	24.2	23.0	23.3	22.1	20.7
90°	26.9	27.7	28.6	29.3	28.6	27.7	26.9	26.1	25.0	23.7	22.2
92.5°	55.9	56.6	57.1	57.7	57.1	56.6	55.9	55.3	54.1	52.3	50.5
95°	103.5	104.1	104.6	105.2	104.6	104.1	103.5	102.9	101.8	99.8	97.9
97.5°	158.4	158.8	159.1	159.5	159.1	158.8	158.4	158.2	157.0	155.2	153.4
100°	198.9	199.4	200.0	200.5	200.0	199.4	198.9	198.3	196.8	194.4	192.0
102.5°	239.3	240.1	240.8	241.6	240.8	240.1	239.3	238.6	236.9	234.1	231.5
105°	300.8	301.6	302.4	303.2	302.4	301.6	300.8	299.9	298.7	297.1	295.5
107.5°	366.5	366.4	366.4	366.3	366.4	366.4	366.5	366.6	366.2	365.3	364.5
110°	414.1	413.8	413.5	413.2	413.5	413.8	414.1	414.3	414.1	413.2	412.5



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	460.7	460.2	459.7	459.2	459.7	460.2	460.7	461.2	461.2	460.8	460.4
115°	532.6	532.3	532.2	531.9	532.2	532.3	532.6	532.9	533.2	533.5	533.8
117.5°	606.1	604.9	603.9	602.8	603.9	604.9	606.1	607.1	607.6	607.3	607.1
120°	654.9	653.8	652.7	651.7	652.7	653.8	654.9	656.0	656.6	656.6	656.6
122.5°	703.1	702.3	701.4	700.6	701.4	702.3	703.1	704.1	704.6	704.8	705.0
125°	774.8	774.5	774.2	773.9	774.2	774.5	774.8	775.1	775.4	776.0	776.5
127.5°	846.0	845.5	844.9	844.3	844.9	845.5	846.0	846.5	847.0	847.2	847.4
130°	893.0	892.4	891.8	891.3	891.8	892.4	893.0	893.4	893.9	894.2	894.4
132.5°	937.6	936.8	936.0	935.3	936.0	936.8	937.6	938.4	938.9	939.1	939.4
135°	1007.0	1006.0	1004.8	1003.8	1004.8	1006.0	1007.0	1008.1	1008.7	1008.7	1008.7
137.5°	1074.9	1073.5	1072.1	1070.8	1072.1	1073.5	1074.9	1076.2	1076.8	1076.4	1076.1
140°	1117.9	1116.5	1115.2	1113.8	1115.2	1116.5	1117.9	1119.3	1119.6	1119.1	1118.6
142.5°	1159.0	1157.6	1156.2	1154.9	1156.2	1157.6	1159.0	1160.4	1160.8	1160.6	1160.2
145°	1219.0	1218.1	1217.3	1216.5	1217.3	1218.1	1219.0	1219.7	1220.2	1220.2	1220.2
147.5°	1274.6	1272.8	1270.9	1269.1	1270.9	1272.8	1274.6	1276.5	1277.1	1276.4	1275.7
150°	1309.9	1309.3	1308.7	1308.2	1308.7	1309.3	1309.9	1310.4	1310.7	1310.7	1310.7
152.5°	1343.4	1342.5	1341.4	1340.5	1341.4	1342.5	1343.4	1344.4	1344.5	1343.9	1343.2
155°	1390.5	1389.2	1387.8	1386.5	1387.8	1389.2	1390.5	1391.9	1392.0	1390.9	1389.9
157.5°	1430.2	1428.4	1426.6	1424.8	1426.6	1428.4	1430.2	1432.0	1432.4	1431.3	1430.2
160°	1455.4	1454.0	1452.6	1451.2	1452.6	1454.0	1455.4	1456.7	1456.8	1455.8	1454.6
162.5°	1478.5	1476.9	1475.4	1473.8	1475.4	1476.9	1478.5	1480.1	1480.2	1478.8	1477.6
165°	1508.7	1507.1	1505.4	1503.8	1505.4	1507.1	1508.7	1510.3	1510.6	1509.6	1508.4
167.5°	1532.9	1531.2	1529.5	1527.8	1529.5	1531.2	1532.9	1534.6	1534.6	1533.0	1531.3
170°	1546.2	1544.4	1542.4	1540.5	1542.4	1544.4	1546.2	1548.1	1548.2	1546.6	1545.0
172.5°	1556.3	1554.6	1552.9	1551.2	1552.9	1554.6	1556.3	1558.0	1558.0	1556.4	1554.8
175°	1567.0	1565.1	1563.2	1561.3	1563.2	1565.1	1567.0	1568.9	1569.1	1567.4	1565.8
177.5°	1571.7	1570.2	1568.7	1567.2	1568.7	1570.2	1571.7	1573.3	1573.4	1572.1	1570.7
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	18.5	18.7	17.2	16.9	16.0	16.1	14.7	13.8	12.8	12.9	13.9
90°	20.9	19.6	17.6	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	48.7	46.9	44.6	42.3	40.0	37.6	35.6	34.1	32.6	31.1	29.6
95°	96.0	94.2	91.4	88.7	86.0	83.3	81.6	81.1	80.6	80.0	79.5
97.5°	151.7	149.9	146.2	142.4	138.6	134.9	132.9	132.7	132.5	132.2	132.1
100°	189.5	187.1	183.5	180.0	176.4	173.0	171.2	171.2	171.2	171.2	171.2
102.5°	228.8	226.2	224.4	222.6	220.8	219.0	217.5	216.5	215.4	214.3	213.2
105°	293.9	292.2	290.6	289.0	287.3	285.7	284.2	282.9	281.4	280.1	278.8
107.5°	363.7	362.9	361.7	360.3	359.1	357.9	356.6	355.2	353.8	352.5	351.1
110°	411.6	410.8	410.0	409.2	408.4	407.6	406.4	405.1	403.8	402.4	401.1



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	460.1	459.7	458.6	457.6	456.6	455.6	454.7	454.0	453.3	452.6	451.9
115°	534.0	534.3	533.8	533.2	532.6	532.2	531.3	530.2	529.1	528.0	527.0
117.5°	606.9	606.7	606.1	605.7	605.2	604.7	604.3	603.7	603.2	602.8	602.3
120°	656.6	656.6	656.3	656.0	655.7	655.4	654.7	653.3	652.0	650.5	649.2
122.5°	705.2	705.5	704.7	704.1	703.3	702.7	702.0	701.5	701.1	700.6	700.1
125°	777.0	777.6	777.3	777.0	776.7	776.5	775.5	773.9	772.3	770.6	769.0
127.5°	847.7	848.0	847.7	847.3	847.1	846.7	846.1	845.2	844.2	843.3	842.4
130°	894.7	894.9	894.4	893.9	893.3	892.8	891.8	890.5	889.1	887.8	886.4
132.5°	939.7	940.0	940.1	940.2	940.3	940.4	939.3	937.1	934.9	932.6	930.4
135°	1008.7	1008.7	1008.4	1008.1	1007.9	1007.6	1006.6	1005.0	1003.3	1001.7	1000.1
137.5°	1075.7	1075.4	1074.9	1074.2	1073.7	1073.0	1072.0	1070.4	1068.8	1067.2	1065.6
140°	1118.0	1117.5	1116.6	1115.9	1115.0	1114.2	1113.1	1111.8	1110.4	1109.1	1107.7
142.5°	1159.9	1159.5	1158.5	1157.4	1156.4	1155.4	1154.3	1153.2	1152.1	1150.9	1149.8
145°	1220.2	1220.2	1219.4	1218.5	1217.8	1216.9	1216.0	1214.8	1213.8	1212.7	1211.6
147.5°	1275.2	1274.5	1273.8	1273.2	1272.5	1271.9	1271.2	1270.6	1270.1	1269.4	1268.9
150°	1310.7	1310.7	1309.6	1308.5	1307.4	1306.3	1305.9	1306.2	1306.5	1306.7	1307.0
152.5°	1342.7	1342.0	1341.5	1341.0	1340.7	1340.2	1339.8	1339.4	1339.1	1338.7	1338.3
155°	1388.7	1387.7	1387.4	1387.1	1386.9	1386.6	1386.5	1386.5	1386.5	1386.5	1386.5
157.5°	1429.1	1428.0	1427.8	1427.5	1427.2	1426.9	1427.1	1427.7	1428.3	1428.9	1429.5
160°	1453.6	1452.5	1452.2	1452.0	1451.7	1451.4	1451.7	1452.5	1453.3	1454.2	1454.9
162.5°	1476.3	1475.0	1474.9	1474.9	1474.8	1474.8	1475.1	1475.6	1476.2	1476.9	1477.4
165°	1507.4	1506.3	1506.0	1505.7	1505.4	1505.2	1505.3	1505.9	1506.4	1506.9	1507.5
167.5°	1529.7	1528.0	1528.0	1528.0	1528.0	1528.0	1528.6	1529.7	1530.8	1531.8	1533.0
170°	1543.4	1541.7	1541.7	1541.7	1541.7	1541.7	1542.3	1543.4	1544.5	1545.6	1546.6
172.5°	1553.1	1551.5	1551.5	1551.5	1551.5	1551.5	1552.1	1553.1	1554.3	1555.3	1556.4
175°	1564.1	1562.5	1562.5	1562.5	1562.5	1562.5	1563.1	1564.1	1565.3	1566.3	1567.4
177.5°	1569.4	1568.1	1568.4	1568.6	1568.8	1569.1	1569.5	1570.5	1571.3	1572.2	1573.0
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.9	14.9	16.8	19.8	21.8	24.1	25.5	24.9	23.3	22.0	20.7
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.6	20.9	22.2
92.5°	31.1	32.6	34.1	35.6	37.6	40.0	42.3	44.6	46.9	48.7	50.5
95°	80.0	80.6	81.1	81.6	83.3	86.0	88.7	91.4	94.2	96.0	97.9
97.5°	132.2	132.5	132.7	132.9	134.9	138.6	142.4	146.2	149.9	151.7	153.4
100°	171.2	171.2	171.2	171.2	173.0	176.4	180.0	183.5	187.1	189.5	192.0
102.5°	214.3	215.4	216.5	217.5	219.0	220.8	222.6	224.4	226.2	228.8	231.5
105°	280.1	281.4	282.9	284.2	285.7	287.3	289.0	290.6	292.2	293.9	295.5
107.5°	352.5	353.8	355.2	356.6	357.9	359.1	360.3	361.7	362.9	363.7	364.5
110°	402.4	403.8	405.1	406.4	407.6	408.4	409.2	410.0	410.8	411.6	412.5





TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	452.6	453.3	454.0	454.7	455.6	456.6	457.6	458.6	459.7	460.1	460.4
115°	528.0	529.1	530.2	531.3	532.2	532.6	533.2	533.8	534.3	534.0	533.8
117.5°	602.8	603.2	603.7	604.3	604.7	605.2	605.7	606.1	606.7	606.9	607.1
120°	650.5	652.0	653.3	654.7	655.4	655.7	656.0	656.3	656.6	656.6	656.6
122.5°	700.6	701.1	701.5	702.0	702.7	703.3	704.1	704.7	705.5	705.2	705.0
125°	770.6	772.3	773.9	775.5	776.5	776.7	777.0	777.3	777.6	777.0	776.5
127.5°	843.3	844.2	845.2	846.1	846.7	847.1	847.3	847.7	848.0	847.7	847.4
130°	887.8	889.1	890.5	891.8	892.8	893.3	893.9	894.4	894.9	894.7	894.4
132.5°	932.6	934.9	937.1	939.3	940.4	940.3	940.2	940.1	940.0	939.7	939.4
135°	1001.7	1003.3	1005.0	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7	1008.7
137.5°	1067.2	1068.8	1070.4	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7	1076.1
140°	1109.1	1110.4	1111.8	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0	1118.6
142.5°	1150.9	1152.1	1153.2	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9	1160.2
145°	1212.7	1213.8	1214.8	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2	1220.2
147.5°	1269.4	1270.1	1270.6	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2	1275.7
150°	1306.7	1306.5	1306.2	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7	1310.7
152.5°	1338.7	1339.1	1339.4	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7	1343.2
155°	1386.5	1386.5	1386.5	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7	1389.9
157.5°	1428.9	1428.3	1427.7	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1	1430.2
160°	1454.2	1453.3	1452.5	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6	1454.6
162.5°	1476.9	1476.2	1475.6	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3	1477.6
165°	1506.9	1506.4	1505.9	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4	1508.4
167.5°	1531.8	1530.8	1529.7	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7	1531.3
170°	1545.6	1544.5	1543.4	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4	1545.0
172.5°	1555.3	1554.3	1553.1	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1	1554.8
175°	1566.3	1565.3	1564.1	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1	1565.8
177.5°	1572.2	1571.3	1570.5	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4	1570.7
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	21.0	19.2	19.5	19.1	19.3	18.9	18.1
90°	23.7	25.0	26.1	26.9	27.7	28.6	29.3
92.5°	52.3	54.1	55.3	55.9	56.6	57.1	57.7
95°	99.8	101.8	102.9	103.5	104.1	104.6	105.2
97.5°	155.2	157.0	158.2	158.4	158.8	159.1	159.5
100°	194.4	196.8	198.3	198.9	199.4	200.0	200.5
102.5°	234.1	236.9	238.6	239.3	240.1	240.8	241.6
105°	297.1	298.7	299.9	300.8	301.6	302.4	303.2
107.5°	365.3	366.2	366.6	366.5	366.4	366.4	366.3
110°	413.2	414.1	414.3	414.1	413.8	413.5	413.2



TEST NUMBER: P333449-830

CATALOG NUMBER: S125DIW-S1090D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	460.8	461.2	461.2	460.7	460.2	459.7	459.2
115°	533.5	533.2	532.9	532.6	532.3	532.2	531.9
117.5°	607.3	607.6	607.1	606.1	604.9	603.9	602.8
120°	656.6	656.6	656.0	654.9	653.8	652.7	651.7
122.5°	704.8	704.6	704.1	703.1	702.3	701.4	700.6
125°	776.0	775.4	775.1	774.8	774.5	774.2	773.9
127.5°	847.2	847.0	846.5	846.0	845.5	844.9	844.3
130°	894.2	893.9	893.4	893.0	892.4	891.8	891.3
132.5°	939.1	938.9	938.4	937.6	936.8	936.0	935.3
135°	1008.7	1008.7	1008.1	1007.0	1006.0	1004.8	1003.8
137.5°	1076.4	1076.8	1076.2	1074.9	1073.5	1072.1	1070.8
140°	1119.1	1119.6	1119.3	1117.9	1116.5	1115.2	1113.8
142.5°	1160.6	1160.8	1160.4	1159.0	1157.6	1156.2	1154.9
145°	1220.2	1220.2	1219.7	1219.0	1218.1	1217.3	1216.5
147.5°	1276.4	1277.1	1276.5	1274.6	1272.8	1270.9	1269.1
150°	1310.7	1310.7	1310.4	1309.9	1309.3	1308.7	1308.2
152.5°	1343.9	1344.5	1344.4	1343.4	1342.5	1341.4	1340.5
155°	1390.9	1392.0	1391.9	1390.5	1389.2	1387.8	1386.5
157.5°	1431.3	1432.4	1432.0	1430.2	1428.4	1426.6	1424.8
160°	1455.8	1456.8	1456.7	1455.4	1454.0	1452.6	1451.2
162.5°	1478.8	1480.2	1480.1	1478.5	1476.9	1475.4	1473.8
165°	1509.6	1510.6	1510.3	1508.7	1507.1	1505.4	1503.8
167.5°	1533.0	1534.6	1534.6	1532.9	1531.2	1529.5	1527.8
170°	1546.6	1548.2	1548.1	1546.2	1544.4	1542.4	1540.5
172.5°	1556.4	1558.0	1558.0	1556.3	1554.6	1552.9	1551.2
175°	1567.4	1569.1	1568.9	1567.0	1565.1	1563.2	1561.3
177.5°	1572.1	1573.4	1573.3	1571.7	1570.2	1568.7	1567.2
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1

(END OF REPORT)