

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333464-830

Luminaire Tested: **S125DIW-S1270D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333464-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D470U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6601.1 lumens  
Efficiency: N/A  
Efficacy: 126.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333464-830

CATALOG NUMBER: S125DIW-S1270D470U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333464-830

CATALOG NUMBER: S125DIW-S1270D470U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	62	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333464-830

CATALOG NUMBER: S125DIW-S1270D470U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.1	2.7
10°-20°	494.7	7.5
20°-30°	730.5	11.1
30°-40°	852.4	12.9
40°-50°	856.1	13.0
50°-60°	751.5	11.4
60°-70°	559.9	8.5
70°-80°	320.2	4.9
80°-90°	94.3	1.4
90°-100°	20.9	0.3
100°-110°	128.8	2.0
110°-120°	233.6	3.5
120°-130°	299.9	4.5
130°-140°	322.5	4.9
140°-150°	302.7	4.6
150°-160°	244.9	3.7
160°-170°	158.4	2.4
170°-180°	54.6	0.8
0°-30°	1400.3	21.2
0°-40°	2252.7	34.1
0°-60°	3860.3	58.5
0°-90°	4834.7	73.2
90°-120°	383.4	5.8
90°-150°	1308.5	19.8
90°-180°	1766.0	26.8
0°-180°	6601.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	0	4	7	9	10	5
95°	24	22	7	9	9	31
105°	125	127	127	127	127	133
115°	235	237	238	236	234	233
125°	335	338	338	336	335	299
135°	418	420	419	418	416	322
145°	484	485	485	485	483	303
155°	533	531	531	532	529	245
165°	562	560	560	563	559	159
175°	575	573	573	576	573	55
180°	575	575	575	575	575	



TEST NUMBER: P333464-830

CATALOG NUMBER: S125DIW-S1270D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	31.9	32.0	32.1	32.2	32.4	32.4	32.3	32.2	32.0	32.0	32.0
90°	0.5	1.2	2.0	2.7	3.5	4.1	4.8	5.5	6.1	6.8	7.3
92.5°	6.6	6.0	5.5	5.0	4.4	4.4	5.1	5.7	6.2	6.8	7.3
95°	24.3	24.0	23.8	23.5	23.2	21.2	17.6	14.0	10.5	6.8	7.3
97.5°	50.7	51.3	51.7	52.3	52.8	49.5	42.3	35.3	28.1	21.0	18.3
100°	71.2	71.5	71.8	72.1	72.4	72.7	73.0	73.4	73.8	74.2	60.0
102.5°	92.0	92.4	92.7	93.1	93.5	93.8	94.0	94.2	94.4	94.6	92.0
105°	125.4	125.7	126.1	126.5	126.9	127.1	127.1	127.1	127.1	127.1	127.1
107.5°	159.9	159.9	159.9	159.9	159.9	160.0	160.2	160.4	160.6	160.8	160.9
110°	182.5	182.5	182.5	182.5	182.5	182.6	182.8	182.9	183.1	183.3	183.0



TEST NUMBER: P333464-830

CATALOG NUMBER: S125DIW-S1270D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	203.7	203.9	204.1	204.3	204.5	204.7	204.8	205.0	205.1	205.2	204.8
115°	235.4	235.8	236.3	236.8	237.2	237.5	237.6	237.7	237.8	237.9	237.5
117.5°	268.2	268.2	268.2	268.2	268.2	268.3	268.6	269.0	269.4	269.8	269.3
120°	288.7	288.6	288.5	288.4	288.3	288.4	288.7	289.0	289.3	289.5	289.4
122.5°	306.8	307.1	307.5	307.8	308.2	308.4	308.6	308.7	308.9	309.0	308.8
125°	334.7	335.4	336.0	336.7	337.3	337.7	337.7	337.7	337.7	337.7	337.3
127.5°	361.4	361.9	362.4	362.9	363.4	363.5	363.4	363.4	363.4	363.3	363.1
130°	377.8	378.2	378.7	379.2	379.7	379.9	380.0	380.1	380.2	380.3	380.0
132.5°	394.2	394.7	395.3	395.8	396.3	396.5	396.3	396.2	395.9	395.7	395.7
135°	417.5	418.0	418.6	419.1	419.7	419.9	419.7	419.5	419.3	419.1	419.0
137.5°	438.8	439.3	439.8	440.4	440.8	441.0	440.8	440.6	440.5	440.3	440.4
140°	452.8	453.0	453.2	453.4	453.6	453.6	453.6	453.5	453.4	453.3	453.5
142.5°	465.4	465.6	465.7	465.8	465.9	466.0	466.2	466.3	466.5	466.6	466.6
145°	484.0	484.2	484.4	484.6	484.7	484.8	484.8	484.8	484.8	484.8	484.9
147.5°	500.2	500.1	500.1	500.0	500.0	500.0	500.2	500.3	500.4	500.5	500.6
150°	510.4	510.2	510.0	509.8	509.6	509.6	509.8	510.0	510.2	510.4	510.6
152.5°	520.3	519.9	519.4	519.1	518.6	518.5	518.7	518.9	519.1	519.2	519.4
155°	533.0	532.4	531.9	531.3	530.7	530.6	530.7	530.9	531.1	531.3	531.6
157.5°	542.8	542.4	542.2	541.8	541.4	541.3	541.3	541.3	541.3	541.4	541.7
160°	549.6	549.0	548.5	547.9	547.3	547.1	547.2	547.3	547.4	547.5	547.9
162.5°	555.1	554.5	553.9	553.4	552.8	552.6	552.7	552.8	552.9	553.0	553.5
165°	562.4	561.8	561.3	560.7	560.2	559.9	560.0	560.1	560.2	560.2	560.8
167.5°	567.9	567.3	566.8	566.1	565.5	565.2	565.3	565.4	565.5	565.6	566.4
170°	571.0	570.3	569.6	568.9	568.3	568.0	568.1	568.2	568.3	568.4	569.1
172.5°	573.0	572.3	571.7	571.0	570.3	570.1	570.2	570.4	570.6	570.8	571.5
175°	575.2	574.7	574.1	573.5	573.0	572.7	572.8	572.9	573.0	573.1	573.8
177.5°	576.3	575.8	575.3	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.0
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P333464-830

CATALOG NUMBER: S125DIW-S1270D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	32.1	32.2	32.3	32.1	31.7	31.2	30.7	30.3
90°	7.7	8.2	8.7	9.1	9.4	9.7	10.0	10.3
92.5°	7.7	8.2	8.7	9.0	9.1	9.3	9.4	9.5
95°	7.7	8.2	8.7	9.0	9.0	9.0	9.0	9.0
97.5°	15.6	13.0	10.3	9.0	9.0	9.0	9.0	9.0
100°	46.0	31.9	17.7	10.5	10.1	9.7	9.3	9.0
102.5°	89.4	86.6	84.0	79.5	73.0	66.5	60.0	53.6
105°	127.1	127.1	127.1	127.1	127.0	126.9	126.8	126.7
107.5°	160.9	160.9	160.9	160.8	160.5	160.2	159.9	159.7
110°	182.8	182.5	182.2	182.1	182.2	182.3	182.4	182.5





TEST NUMBER: P333464-830

CATALOG NUMBER: S125DIW-S1270D470U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	204.4	204.1	203.8	203.5	203.4	203.2	203.1	202.9
115°	237.1	236.8	236.4	235.9	235.4	234.8	234.2	233.7
117.5°	268.7	268.2	267.8	267.4	267.1	266.9	266.6	266.5
120°	289.2	289.0	288.8	288.4	287.9	287.5	287.0	286.5
122.5°	308.6	308.4	308.2	307.8	307.3	306.7	306.2	305.7
125°	337.0	336.6	336.2	335.8	335.5	335.3	335.0	334.7
127.5°	362.9	362.7	362.5	362.0	361.3	360.6	359.9	359.2
130°	379.8	379.5	379.2	378.8	378.3	377.9	377.4	376.9
132.5°	395.6	395.5	395.5	395.2	394.7	394.3	393.8	393.3
135°	418.8	418.6	418.4	418.0	417.5	416.9	416.3	415.8
137.5°	440.4	440.5	440.5	440.3	439.7	439.2	438.8	438.3
140°	453.6	453.8	454.0	453.8	453.3	452.7	452.1	451.6
142.5°	466.7	466.7	466.7	466.5	465.9	465.3	464.8	464.2
145°	485.0	485.1	485.2	484.9	484.4	483.8	483.2	482.7
147.5°	500.8	500.9	501.0	500.7	500.0	499.4	498.6	497.9
150°	510.8	511.0	511.1	510.9	510.1	509.3	508.6	507.8
152.5°	519.6	519.8	520.0	519.8	519.1	518.4	517.7	517.1
155°	531.9	532.2	532.4	532.2	531.4	530.7	529.9	529.1
157.5°	542.0	542.2	542.5	542.3	541.6	540.8	540.1	539.3
160°	548.3	548.7	549.0	548.8	548.1	547.3	546.6	545.8
162.5°	554.0	554.6	555.1	555.0	554.1	553.3	552.4	551.6
165°	561.5	562.0	562.6	562.5	561.8	560.9	560.2	559.4
167.5°	567.0	567.7	568.4	568.4	567.4	566.6	565.7	564.9
170°	569.9	570.7	571.5	571.4	570.5	569.7	568.8	568.0
172.5°	572.1	572.8	573.5	573.4	572.6	571.7	570.9	570.0
175°	574.6	575.3	576.1	576.1	575.2	574.4	573.5	572.7
177.5°	575.6	576.1	576.6	576.6	576.0	575.4	574.8	574.2
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2

(END OF REPORT)