

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333345-830

Luminaire Tested: **S125DIW-S375D470U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333345-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D470U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2965.8 lumens  
Efficiency: N/A  
Efficacy: 128.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333345-830

CATALOG NUMBER: S125DIW-S375D470U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333345-830

CATALOG NUMBER: S125DIW-S375D470U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48					48			
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46					41				
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39					34				
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33					29				
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28					25				
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	25					21				
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22					19				
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19					17				
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17					15				
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16					13				
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14					12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333345-830

CATALOG NUMBER: S125DIW-S375D470U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.9	1.8
10°-20°	146.6	4.9
20°-30°	216.5	7.3
30°-40°	252.7	8.5
40°-50°	253.8	8.6
50°-60°	222.8	7.5
60°-70°	166.0	5.6
70°-80°	94.9	3.2
80°-90°	28.8	1.0
90°-100°	36.8	1.2
100°-110°	108.6	3.7
110°-120°	183.9	6.2
120°-130°	242.0	8.2
130°-140°	271.2	9.1
140°-150°	265.8	9.0
150°-160°	223.2	7.5
160°-170°	148.4	5.0
170°-180°	51.9	1.8
0°-30°	415.1	14.0
0°-40°	667.8	22.5
0°-60°	1144.3	38.6
0°-90°	1434.0	48.4
90°-120°	329.3	11.1
90°-150°	1108.3	37.4
90°-180°	1532.0	51.7
0°-180°	2965.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	0	4	7	9	10	3
95°	28	29	33	36	37	30
105°	97	100	102	105	106	104
115°	184	186	187	186	186	182
125°	269	271	272	271	270	241
135°	349	352	352	352	351	269
145°	423	425	426	426	425	265
155°	484	484	485	486	484	223
165°	527	526	526	528	526	149
175°	548	546	546	548	546	52
180°	549	549	549	549	549	



TEST NUMBER: P333345-830

CATALOG NUMBER: S125DIW-S375D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.5	9.6	9.8	10.0	10.1	10.2	10.3	10.3	10.4	10.5	10.6
90°	0.5	1.2	2.0	2.7	3.5	4.1	4.8	5.5	6.1	6.9	7.4
92.5°	10.4	10.8	11.4	12.0	12.4	13.1	13.9	14.8	15.6	16.4	17.1
95°	27.8	28.0	28.2	28.4	28.6	29.1	30.1	31.0	32.0	32.9	33.6
97.5°	46.1	46.2	46.3	46.4	46.5	47.1	48.4	49.8	51.1	52.4	53.0
100°	59.9	59.9	59.9	59.9	59.9	60.4	61.6	62.9	64.1	65.3	66.3
102.5°	74.5	74.8	75.3	75.7	76.1	76.5	77.2	77.8	78.4	79.0	79.9
105°	97.4	97.8	98.3	98.8	99.3	99.8	100.4	100.9	101.5	102.1	102.6
107.5°	122.7	123.2	123.7	124.1	124.6	125.1	125.5	125.9	126.4	126.8	127.1
110°	140.2	140.6	141.1	141.6	142.0	142.4	142.7	143.0	143.3	143.5	143.8



TEST NUMBER: P333345-830

CATALOG NUMBER: S125DIW-S375D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.9	158.2	158.3	158.6	158.9	159.2	159.6	159.9	160.2	160.6	160.8
115°	184.1	184.5	184.9	185.3	185.7	186.0	186.2	186.3	186.5	186.7	186.6
117.5°	210.5	210.6	210.8	210.9	211.1	211.3	211.5	211.6	211.8	212.0	212.1
120°	226.9	227.3	227.8	228.3	228.8	229.0	229.1	229.2	229.3	229.4	229.4
122.5°	244.6	244.8	245.0	245.2	245.2	245.5	245.7	246.0	246.3	246.5	246.4
125°	268.7	269.3	269.8	270.4	271.0	271.4	271.5	271.5	271.6	271.7	271.5
127.5°	294.4	294.6	295.0	295.3	295.7	295.9	296.0	296.1	296.1	296.3	296.2
130°	309.7	310.2	310.7	311.1	311.6	312.0	312.2	312.4	312.5	312.7	312.6
132.5°	325.1	325.8	326.7	327.4	328.2	328.6	328.6	328.5	328.5	328.4	328.3
135°	349.4	350.1	350.6	351.2	351.8	352.0	352.1	352.2	352.3	352.4	352.4
137.5°	372.3	372.9	373.4	374.0	374.6	374.9	375.1	375.3	375.5	375.8	375.9
140°	387.0	387.5	388.0	388.4	388.9	389.4	389.6	389.9	390.2	390.5	390.7
142.5°	401.7	402.1	402.6	402.9	403.3	403.7	404.1	404.4	404.8	405.2	405.3
145°	423.4	423.8	424.1	424.5	424.9	425.2	425.5	425.7	426.0	426.3	426.3
147.5°	443.4	443.6	443.7	443.9	444.2	444.4	444.6	444.9	445.1	445.4	445.5
150°	456.7	456.6	456.5	456.4	456.3	456.5	456.9	457.2	457.6	458.0	458.0
152.5°	467.6	467.8	467.9	468.0	468.2	468.3	468.4	468.6	468.7	468.9	469.1
155°	484.5	484.5	484.5	484.5	484.5	484.5	484.6	484.7	484.7	484.8	485.2
157.5°	499.5	499.3	499.1	498.9	498.6	498.6	498.7	498.8	498.9	499.0	499.4
160°	508.4	508.1	507.7	507.5	507.2	507.1	507.2	507.3	507.4	507.5	507.9
162.5°	516.2	516.0	515.9	515.6	515.4	515.3	515.3	515.3	515.4	515.4	515.9
165°	526.7	526.5	526.3	526.1	525.9	525.9	526.0	526.1	526.2	526.3	526.7
167.5°	535.6	535.3	534.9	534.5	534.1	534.0	534.0	534.0	534.0	534.0	534.5
170°	540.4	540.0	539.6	539.2	538.9	538.7	538.7	538.7	538.7	538.7	539.2
172.5°	543.8	543.5	543.1	542.7	542.3	542.2	542.2	542.2	542.2	542.2	542.7
175°	547.7	547.2	546.9	546.5	546.1	545.9	545.9	545.9	545.9	545.9	546.5
177.5°	549.6	549.3	549.0	548.7	548.4	548.2	548.2	548.1	548.0	547.9	548.4
180°	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9



TEST NUMBER: P333345-830

CATALOG NUMBER: S125DIW-S375D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	10.7	10.7	10.8	10.8	10.7	10.7	10.6	10.4
90°	7.8	8.3	8.8	9.1	9.4	9.7	10.0	10.3
92.5°	17.6	18.3	18.9	19.3	19.5	19.7	20.0	20.2
95°	34.2	34.9	35.5	36.0	36.2	36.4	36.6	36.8
97.5°	53.6	54.3	54.9	55.2	55.3	55.5	55.6	55.7
100°	67.1	68.0	68.8	69.3	69.5	69.7	69.8	70.0
102.5°	80.9	81.8	82.8	83.3	83.6	83.9	84.2	84.5
105°	103.2	103.8	104.3	104.8	105.1	105.4	105.7	105.9
107.5°	127.3	127.6	127.9	128.1	128.1	128.0	128.0	128.0
110°	144.1	144.4	144.7	144.8	144.7	144.6	144.5	144.4





TEST NUMBER: P333345-830

CATALOG NUMBER: S125DIW-S375D470U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	160.9	161.0	161.2	161.2	161.0	160.8	160.6	160.4
115°	186.5	186.4	186.3	186.2	186.2	186.1	186.0	185.9
117.5°	212.2	212.2	212.3	212.2	211.8	211.4	210.9	210.6
120°	229.4	229.4	229.4	229.2	228.8	228.5	228.1	227.7
122.5°	246.4	246.3	246.2	246.0	245.7	245.4	245.1	244.8
125°	271.4	271.2	271.0	270.8	270.7	270.6	270.5	270.4
127.5°	296.1	296.1	296.0	295.8	295.6	295.4	295.2	295.0
130°	312.5	312.5	312.4	312.2	312.0	311.8	311.6	311.4
132.5°	328.2	328.1	328.0	327.9	327.6	327.3	327.1	326.8
135°	352.4	352.4	352.4	352.2	351.9	351.5	351.1	350.7
137.5°	376.0	376.1	376.3	376.1	375.6	375.1	374.6	374.1
140°	390.9	391.1	391.2	391.1	390.6	390.1	389.6	389.2
142.5°	405.4	405.5	405.6	405.4	404.9	404.4	404.0	403.5
145°	426.3	426.3	426.3	426.2	425.9	425.7	425.4	425.1
147.5°	445.7	446.0	446.2	446.0	445.4	444.7	444.0	443.5
150°	458.0	458.0	458.0	457.9	457.7	457.5	457.3	457.1
152.5°	469.4	469.6	469.8	469.8	469.4	469.1	468.7	468.3
155°	485.6	486.0	486.4	486.4	485.9	485.4	484.9	484.5
157.5°	499.7	500.1	500.5	500.4	499.7	499.1	498.5	497.9
160°	508.3	508.7	509.1	509.0	508.5	508.0	507.6	507.1
162.5°	516.3	516.7	517.2	517.2	516.6	516.0	515.5	514.9
165°	527.1	527.4	527.8	527.7	527.2	526.6	526.0	525.5
167.5°	535.1	535.6	536.2	536.2	535.6	535.0	534.4	533.9
170°	539.8	540.4	541.0	540.9	540.3	539.6	538.9	538.3
172.5°	543.3	543.8	544.4	544.4	543.8	543.2	542.6	542.1
175°	547.1	547.7	548.3	548.2	547.5	546.9	546.2	545.5
177.5°	548.8	549.3	549.8	549.7	549.2	548.7	548.1	547.6
180°	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9

(END OF REPORT)