

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333395-830

Luminaire Tested: **S125DIW-S610D1560U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333395-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D1560U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7481.5 lumens  
Efficiency: N/A  
Efficacy: 123.5 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	34	27
2	86	78	73	68	77	71	66	62	56	53	50	43	41	39	31	30	28	23
3	78	69	62	56	70	62	56	52	50	46	42	38	35	33	28	26	24	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	16	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5448	5448	5448	5448
5°	6309	5466	4786	5466
10°	7340	5438	4194	5438
15°	8125	5398	3869	5398
20°	9095	5335	3608	5335
25°	10655	5264	3480	5264
30°	11508	5193	3370	5193
35°	9462	5062	3297	5062
40°	6726	4878	3217	4878
45°	5167	4631	3172	4631
50°	4410	4324	3166	4324
55°	3926	4023	3193	4023
60°	3543	3695	3274	3695
65°	3272	3365	3359	3365
70°	2974	3021	3408	3021
75°	2628	2662	3376	2662
80°	2213	2168	3087	2168
85°	1756	1564	2490	1564



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.2	1.1
10°-20°	241.8	3.2
20°-30°	392.6	5.2
30°-40°	478.9	6.4
40°-50°	435.7	5.8
50°-60°	347.0	4.6
60°-70°	241.7	3.2
70°-80°	128.9	1.7
80°-90°	36.5	0.5
90°-100°	122.3	1.6
100°-110°	361.3	4.8
110°-120°	611.9	8.2
120°-130°	805.3	10.8
130°-140°	902.4	12.1
140°-150°	884.4	11.8
150°-160°	742.8	9.9
160°-170°	493.8	6.6
170°-180°	172.8	2.3
0°-30°	715.6	9.6
0°-40°	1194.5	16.0
0°-60°	1977.3	26.4
0°-90°	2384.4	31.9
90°-120°	1095.5	14.6
90°-150°	3687.7	49.3
90°-180°	5097.0	68.1
0°-180°	7481.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	844	844	844	844	844	
5°	973	843	738	843	973	98
15°	1215	807	579	807	1215	348
25°	1495	739	488	739	1495	683
35°	1200	642	418	642	1200	735
45°	566	507	347	507	566	453
55°	349	357	284	357	349	314
65°	214	220	220	220	214	212
75°	105	107	135	107	105	113
85°	24	21	34	21	24	28
90°	34	1	34	1	34	20
95°	122	92	122	92	122	124
105°	352	324	352	324	352	373
115°	618	613	618	613	618	612
125°	900	894	900	894	900	803
135°	1167	1163	1167	1163	1167	900
145°	1414	1409	1414	1409	1414	883
155°	1612	1612	1612	1612	1612	742
165°	1748	1753	1748	1753	1748	493
175°	1815	1822	1815	1822	1815	172
180°	1827	1827	1827	1827	1827	



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	892.3	891.1	889.9	887.7	889.4	884.5	882.2	878.3	873.4	871.7	869.6
5°	973.2	975.0	976.8	969.2	970.0	965.0	953.5	944.1	936.7	927.0	920.2
7.5°	1070.5	1066.3	1066.0	1061.1	1052.7	1046.0	1034.0	1018.6	1003.8	986.9	973.0
10°	1119.3	1119.6	1116.4	1110.7	1101.7	1095.2	1079.5	1064.5	1046.2	1024.7	1009.4
12.5°	1155.9	1157.4	1153.4	1145.7	1141.2	1126.8	1114.5	1096.6	1074.9	1057.7	1034.3
15°	1215.2	1211.3	1208.4	1198.7	1191.2	1176.2	1156.5	1137.8	1114.3	1092.4	1070.5
17.5°	1272.3	1275.5	1270.2	1261.3	1238.0	1220.4	1194.0	1168.6	1139.1	1109.8	1083.7
20°	1323.3	1326.3	1318.0	1302.6	1274.7	1257.1	1222.4	1189.4	1155.5	1117.9	1089.2
22.5°	1387.0	1384.7	1373.6	1350.1	1326.0	1293.5	1255.9	1215.8	1173.2	1130.7	1092.6
25°	1495.2	1480.2	1473.4	1444.4	1412.5	1364.9	1313.3	1254.6	1201.6	1145.4	1096.7
27.5°	1555.2	1550.5	1542.9	1522.7	1489.2	1438.3	1377.5	1306.0	1231.1	1160.3	1096.5
30°	1543.2	1543.9	1544.6	1538.1	1516.7	1478.4	1417.9	1340.9	1252.1	1172.2	1098.5
32.5°	1436.6	1449.6	1462.2	1476.9	1482.9	1475.6	1437.7	1368.1	1276.8	1186.0	1097.3
35°	1200.1	1204.1	1244.6	1284.7	1339.1	1381.4	1409.7	1378.8	1301.8	1197.7	1096.0
37.5°	935.8	955.2	983.2	1028.5	1107.0	1177.3	1267.8	1309.4	1284.5	1201.5	1093.4
40°	797.8	815.7	833.9	880.1	946.3	1031.5	1134.3	1222.0	1242.5	1189.4	1084.9
42.5°	691.2	705.4	725.7	760.3	815.7	891.2	989.4	1104.0	1174.5	1154.5	1066.9
45°	565.7	574.7	590.4	618.0	658.1	717.2	803.8	929.2	1038.3	1074.5	1024.0
47.5°	484.2	484.2	496.4	515.5	544.4	594.6	658.6	756.9	873.5	959.8	955.7
50°	438.9	437.2	446.9	463.4	486.3	519.5	580.8	659.2	771.3	869.0	896.2
52.5°	400.0	400.2	406.1	418.3	437.5	466.0	511.7	582.4	678.2	778.4	829.7
55°	348.7	347.3	354.1	362.3	376.4	394.9	427.9	481.9	559.6	658.5	725.0
57.5°	301.8	305.7	308.4	314.1	325.7	338.2	366.0	405.7	467.3	552.1	622.5
60°	274.3	278.2	280.3	286.1	295.4	306.1	327.6	359.9	411.8	484.8	554.6
62.5°	249.6	252.7	253.4	258.5	266.2	276.6	293.5	320.6	361.7	425.5	493.9
65°	214.1	214.1	215.6	220.9	224.5	233.8	246.7	266.4	299.4	349.1	407.5
67.5°	179.8	181.6	181.3	183.6	186.9	194.2	203.4	219.6	244.0	280.3	327.1
70°	157.5	159.0	158.6	160.4	164.0	168.6	176.2	191.5	209.1	240.3	280.3
72.5°	137.5	138.1	137.1	139.5	141.7	145.7	154.1	162.3	178.7	205.0	238.0
75°	105.3	105.9	106.7	108.1	110.3	112.4	116.7	125.0	135.7	155.4	176.5
77.5°	78.9	77.6	79.3	79.1	80.3	81.9	85.7	90.1	98.9	111.3	127.7
80°	59.5	59.8	59.8	60.1	61.9	63.1	66.3	69.5	76.3	85.6	97.0
82.5°	43.4	44.3	43.7	44.4	45.9	46.7	48.4	51.1	55.0	62.4	70.7
85°	23.7	21.9	22.5	23.3	23.3	23.7	25.1	26.1	28.3	31.1	34.4
87.5°	13.7	14.0	14.1	13.9	14.0	13.9	14.7	14.3	14.9	15.5	16.1
90°	34.1	33.2	32.2	31.3	30.3	29.0	27.5	25.9	24.3	22.7	20.5
92.5°	67.1	66.4	65.7	65.0	64.3	63.0	60.8	58.7	56.6	54.6	51.8
95°	122.2	121.6	121.0	120.4	119.7	118.3	116.1	113.9	111.7	109.4	106.3
97.5°	185.4	185.0	184.6	184.3	183.9	182.6	180.5	178.4	176.3	174.3	169.9
100°	233.1	232.5	231.9	231.2	230.6	228.8	226.0	223.2	220.4	217.4	213.4
102.5°	280.9	280.0	279.1	278.2	277.4	275.3	272.3	269.2	266.1	263.0	260.9
105°	352.5	351.6	350.6	349.7	348.7	347.3	345.4	343.6	341.7	339.8	337.8
107.5°	425.8	425.9	426.0	426.0	426.1	425.7	424.7	423.8	422.8	421.9	420.5
110°	480.5	480.8	481.1	481.5	481.7	481.5	480.5	479.6	478.5	477.6	476.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	534.0	534.5	535.1	535.6	536.2	536.2	535.8	535.4	534.9	534.5	533.3
115°	618.4	618.7	619.0	619.3	619.6	619.9	620.3	620.6	620.9	621.2	620.6
117.5°	700.8	702.1	703.3	704.6	705.9	706.3	706.2	705.9	705.6	705.4	704.7
120°	757.7	758.9	760.2	761.5	762.7	763.4	763.4	763.4	763.4	763.4	763.0
122.5°	814.5	815.5	816.5	817.6	818.6	819.2	819.4	819.7	819.9	820.2	819.4
125°	899.8	900.1	900.4	900.8	901.1	901.5	902.2	902.9	903.4	904.1	903.8
127.5°	981.7	982.3	983.0	983.5	984.2	984.7	985.1	985.3	985.6	986.0	985.6
130°	1036.3	1036.9	1037.6	1038.2	1038.8	1039.2	1039.6	1039.9	1040.2	1040.6	1039.9
132.5°	1087.4	1088.4	1089.2	1090.1	1091.0	1091.6	1091.9	1092.2	1092.5	1092.9	1093.0
135°	1167.1	1168.3	1169.6	1170.8	1172.1	1172.7	1172.7	1172.7	1172.7	1172.7	1172.4
137.5°	1244.9	1246.5	1248.1	1249.7	1251.3	1251.9	1251.5	1251.1	1250.8	1250.4	1249.6
140°	1295.0	1296.6	1298.2	1299.8	1301.3	1301.7	1301.2	1300.5	1299.9	1299.3	1298.4
142.5°	1342.7	1344.3	1346.0	1347.5	1349.1	1349.7	1349.2	1348.9	1348.5	1348.1	1347.0
145°	1414.4	1415.3	1416.3	1417.2	1418.1	1418.6	1418.6	1418.6	1418.6	1418.6	1417.7
147.5°	1475.6	1477.7	1479.8	1482.0	1484.1	1484.8	1484.0	1483.3	1482.5	1481.8	1481.0
150°	1521.0	1521.6	1522.3	1522.9	1523.5	1523.9	1523.9	1523.9	1523.9	1523.9	1522.6
152.5°	1558.6	1559.7	1560.9	1562.0	1563.1	1563.3	1562.5	1561.8	1561.0	1560.3	1559.7
155°	1612.0	1613.5	1615.1	1616.7	1618.3	1618.4	1617.2	1615.9	1614.7	1613.4	1613.1
157.5°	1656.6	1658.7	1660.8	1662.8	1665.0	1665.4	1664.2	1662.8	1661.6	1660.3	1660.0
160°	1687.3	1688.9	1690.5	1692.1	1693.7	1693.8	1692.5	1691.3	1690.0	1688.8	1688.5
162.5°	1713.4	1715.3	1717.1	1719.0	1720.8	1721.0	1719.5	1718.0	1716.5	1714.9	1714.9
165°	1748.4	1750.4	1752.3	1754.2	1756.1	1756.3	1755.1	1753.8	1752.6	1751.3	1751.0
167.5°	1776.3	1778.3	1780.3	1782.2	1784.1	1784.1	1782.3	1780.4	1778.5	1776.6	1776.6
170°	1791.1	1793.3	1795.5	1797.7	1800.0	1800.1	1798.2	1796.3	1794.4	1792.5	1792.5
172.5°	1803.6	1805.5	1807.5	1809.5	1811.5	1811.5	1809.6	1807.7	1805.8	1803.9	1803.9
175°	1815.2	1817.5	1819.7	1821.9	1824.1	1824.3	1822.4	1820.5	1818.5	1816.7	1816.7
177.5°	1822.1	1823.8	1825.6	1827.4	1829.2	1829.3	1827.8	1826.3	1824.8	1823.3	1823.4
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	867.9	865.9	863.7	859.6	854.7	852.2	848.2	845.6	840.4	836.1	831.5
5°	911.9	902.7	894.1	883.0	870.8	862.9	853.6	843.2	832.5	821.3	809.2
7.5°	957.5	941.1	923.2	903.9	885.1	867.8	851.2	835.0	819.8	801.4	785.9
10°	988.3	967.4	945.3	919.1	893.7	871.5	848.9	829.2	809.2	787.7	768.7
12.5°	1018.9	991.2	959.9	931.1	900.6	873.8	847.3	822.1	796.9	773.1	751.0
15°	1040.5	1016.2	987.1	946.3	911.9	875.1	840.0	807.4	776.9	750.5	722.6
17.5°	1054.7	1023.4	992.2	953.1	908.0	866.8	827.0	789.8	755.4	721.8	694.9
20°	1057.3	1025.1	992.5	954.2	908.0	860.7	821.0	776.3	739.3	704.6	671.7
22.5°	1056.5	1019.9	984.5	945.0	900.0	856.5	808.4	762.8	722.7	688.6	654.2
25°	1048.4	1009.4	965.0	925.2	880.8	834.6	785.9	738.7	697.9	658.8	624.8
27.5°	1041.6	991.0	940.8	894.4	851.5	809.2	762.6	714.2	668.9	629.3	597.3
30°	1033.3	977.8	921.2	872.9	828.9	787.7	743.7	696.4	649.1	610.5	576.1
32.5°	1025.9	961.2	901.5	848.9	802.3	762.2	721.6	676.7	630.3	591.0	556.7
35°	1011.5	936.7	868.3	808.8	759.0	717.9	683.9	642.0	599.4	561.4	528.5
37.5°	993.3	904.5	831.0	768.7	714.2	670.8	639.1	607.0	566.1	529.5	499.7
40°	978.9	881.6	803.8	740.1	683.5	638.4	609.1	578.6	544.6	510.6	479.1
42.5°	960.8	860.9	776.3	707.8	651.8	607.8	576.9	551.1	521.1	489.4	460.1
45°	927.7	823.5	731.9	658.1	601.5	558.2	526.3	507.0	484.5	454.4	429.7
47.5°	878.9	778.6	683.8	607.7	549.3	509.2	479.3	460.7	444.9	422.5	400.1
50°	835.7	745.1	649.1	573.6	515.2	474.8	447.2	430.4	416.8	399.5	380.6
52.5°	787.3	702.9	615.1	540.4	482.6	442.7	415.7	400.9	389.6	377.2	358.5
55°	710.4	638.8	557.1	486.3	432.9	393.9	370.2	357.3	348.0	338.7	327.3
57.5°	625.7	569.7	497.3	432.5	383.4	347.9	325.8	313.3	306.0	301.2	294.5
60°	566.1	518.1	455.8	396.7	348.7	317.3	295.8	286.1	280.0	276.1	271.1
62.5°	510.8	471.4	413.7	359.8	317.8	288.0	268.8	259.5	253.6	251.8	247.5
65°	429.3	398.9	351.3	306.5	270.7	245.2	229.1	220.2	216.6	214.4	214.8
67.5°	349.0	330.5	292.3	254.1	225.5	204.2	191.2	184.4	182.6	179.7	179.6
70°	300.0	286.1	253.8	220.6	195.1	178.7	167.2	160.0	158.3	156.8	156.5
72.5°	256.7	244.6	216.6	189.9	167.1	152.6	143.2	138.8	135.9	135.1	135.0
75°	193.0	186.2	164.0	142.9	127.1	117.1	110.7	106.7	104.5	104.2	104.5
77.5°	137.2	131.3	117.2	102.2	92.3	84.6	79.2	77.9	75.4	75.5	75.1
80°	103.1	99.2	90.2	78.4	70.2	63.7	60.9	58.3	57.7	56.6	57.7
82.5°	74.7	70.5	64.5	56.9	50.1	46.3	43.4	42.6	42.1	41.7	41.8
85°	36.9	37.2	33.6	27.9	25.1	22.9	21.1	21.1	20.7	20.5	20.7
87.5°	16.3	15.3	13.7	12.3	10.4	9.0	8.2	8.0	7.6	7.9	8.7
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	49.1	46.5	43.7	41.5	39.7	38.0	36.2	34.4	36.2	38.0	39.7
95°	103.1	100.0	96.8	94.9	94.3	93.7	93.0	92.4	93.0	93.7	94.3
97.5°	165.6	161.2	156.8	154.6	154.3	154.0	153.7	153.5	153.7	154.0	154.3
100°	209.2	205.2	201.0	199.0	199.0	199.0	199.0	199.0	199.0	199.0	199.0
102.5°	258.8	256.7	254.7	253.0	251.7	250.4	249.2	247.9	249.2	250.4	251.7
105°	335.9	334.0	332.2	330.5	328.9	327.3	325.6	324.1	325.6	327.3	328.9
107.5°	419.0	417.5	416.1	414.5	413.0	411.4	409.8	408.2	409.8	411.4	413.0
110°	475.7	474.8	473.8	472.6	471.0	469.4	467.9	466.3	467.9	469.4	471.0





TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	532.1	530.8	529.7	528.7	527.8	527.1	526.2	525.4	526.2	527.1	527.8
115°	619.9	619.3	618.7	617.7	616.4	615.2	614.0	612.7	614.0	615.2	616.4
117.5°	704.2	703.6	703.0	702.5	701.9	701.3	700.8	700.2	700.8	701.3	701.9
120°	762.7	762.4	762.0	761.1	759.6	758.0	756.4	754.8	756.4	758.0	759.6
122.5°	818.6	817.7	816.9	816.2	815.7	815.1	814.5	814.0	814.5	815.1	815.7
125°	903.4	903.1	902.9	901.7	899.8	898.0	896.0	894.1	896.0	898.0	899.8
127.5°	985.2	984.9	984.5	983.7	982.6	981.6	980.5	979.4	980.5	981.6	982.6
130°	1039.2	1038.7	1038.0	1036.9	1035.3	1033.8	1032.2	1030.6	1032.2	1033.8	1035.3
132.5°	1093.1	1093.3	1093.3	1092.1	1089.6	1086.9	1084.4	1081.8	1084.4	1086.9	1089.6
135°	1172.1	1171.8	1171.5	1170.4	1168.5	1166.6	1164.7	1162.8	1164.7	1166.6	1168.5
137.5°	1249.0	1248.3	1247.5	1246.3	1244.4	1242.6	1240.9	1239.0	1240.9	1242.6	1244.4
140°	1297.4	1296.4	1295.4	1294.2	1292.6	1291.0	1289.5	1287.9	1289.5	1291.0	1292.6
142.5°	1345.8	1344.5	1343.3	1342.1	1340.8	1339.4	1338.1	1336.8	1338.1	1339.4	1340.8
145°	1416.7	1415.8	1414.9	1413.8	1412.5	1411.3	1409.9	1408.7	1409.9	1411.3	1412.5
147.5°	1480.3	1479.5	1478.8	1478.0	1477.3	1476.6	1475.9	1475.3	1475.9	1476.6	1477.3
150°	1521.4	1520.0	1518.8	1518.3	1518.6	1519.0	1519.3	1519.6	1519.3	1519.0	1518.6
152.5°	1559.2	1558.8	1558.2	1557.7	1557.3	1556.9	1556.4	1555.9	1556.4	1556.9	1557.3
155°	1612.8	1612.5	1612.1	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0
157.5°	1659.7	1659.3	1659.1	1659.3	1659.9	1660.7	1661.3	1662.0	1661.3	1660.7	1659.9
160°	1688.1	1687.8	1687.5	1687.8	1688.8	1689.7	1690.6	1691.6	1690.6	1689.7	1688.8
162.5°	1714.8	1714.7	1714.7	1715.0	1715.7	1716.4	1717.0	1717.8	1717.0	1716.4	1715.7
165°	1750.7	1750.4	1750.0	1750.2	1750.9	1751.4	1752.1	1752.8	1752.1	1751.4	1750.9
167.5°	1776.6	1776.6	1776.6	1777.3	1778.5	1779.8	1781.0	1782.3	1781.0	1779.8	1778.5
170°	1792.5	1792.5	1792.5	1793.2	1794.4	1795.6	1797.0	1798.2	1797.0	1795.6	1794.4
172.5°	1803.9	1803.9	1803.9	1804.5	1805.8	1807.0	1808.4	1809.6	1808.4	1807.0	1805.8
175°	1816.7	1816.7	1816.7	1817.3	1818.5	1819.9	1821.1	1822.4	1821.1	1819.9	1818.5
177.5°	1823.7	1824.0	1824.2	1824.9	1825.9	1826.9	1827.9	1828.9	1827.9	1826.9	1825.9
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	829.0	825.8	823.2	817.5	814.4	810.0	806.6	810.3	806.3	808.0	805.5
5°	803.1	793.1	785.9	775.5	766.6	758.4	752.2	751.2	748.3	746.9	742.6
7.5°	772.0	759.5	747.2	733.6	722.1	710.5	702.9	696.8	692.8	687.4	683.7
10°	753.7	736.9	722.6	706.1	691.7	679.2	669.2	664.2	659.5	652.7	650.3
12.5°	731.0	713.7	696.2	678.5	664.9	650.8	642.2	634.7	631.5	623.8	623.0
15°	703.9	677.8	660.6	642.7	623.7	612.3	605.1	596.9	593.3	588.0	584.0
17.5°	671.6	648.2	626.7	608.2	591.9	582.3	573.3	567.7	561.6	558.1	551.6
20°	648.1	625.8	604.4	584.7	572.1	561.1	553.9	548.6	542.1	540.3	533.9
22.5°	628.3	603.8	583.2	566.7	553.0	540.5	532.7	529.0	524.6	519.1	517.8
25°	596.2	570.7	553.2	536.7	524.5	513.1	507.7	503.0	498.8	494.8	493.4
27.5°	568.4	545.6	524.8	509.9	499.4	488.9	484.2	478.5	475.3	472.2	468.3
30°	548.9	525.7	507.4	493.0	481.5	472.3	467.2	463.4	460.4	457.6	455.4
32.5°	528.9	507.3	489.6	475.6	464.1	457.1	452.6	449.9	446.7	443.3	440.5
35°	502.4	478.7	461.6	449.3	440.4	435.0	430.0	427.5	424.0	424.0	421.0
37.5°	472.5	452.0	436.9	425.7	417.7	412.9	407.6	405.9	403.5	402.0	401.1
40°	454.7	435.7	421.4	410.3	401.7	397.8	393.5	390.6	389.2	387.4	386.7
42.5°	436.4	418.3	404.5	394.3	386.8	383.4	379.5	377.5	374.6	372.2	371.8
45°	408.5	391.0	378.4	370.2	363.8	359.9	357.3	353.1	351.6	348.7	348.4
47.5°	382.1	365.2	353.0	346.2	340.5	337.3	333.4	329.1	327.4	326.0	325.9
50°	362.3	346.9	335.5	329.0	323.7	319.1	315.1	312.3	311.1	311.1	311.9
52.5°	342.3	329.2	319.4	311.6	306.5	301.5	297.9	296.1	294.5	296.2	297.6
55°	312.9	299.7	292.6	285.0	280.0	274.3	272.5	271.7	270.7	273.5	274.9
57.5°	281.8	272.6	264.2	256.7	252.2	248.9	246.5	246.1	248.1	249.4	254.1
60°	262.1	251.4	243.8	238.1	232.7	230.5	229.9	229.1	230.5	234.5	240.6
62.5°	240.3	231.6	223.5	219.2	215.3	211.7	211.5	212.0	214.8	219.3	225.5
65°	208.4	200.9	195.5	190.5	187.3	185.1	185.9	187.3	190.5	196.6	203.4
67.5°	176.0	170.8	166.0	161.9	158.8	158.8	159.6	161.7	165.5	172.5	178.7
70°	155.0	149.3	145.3	143.5	141.1	139.7	141.8	145.3	148.5	155.0	160.4
72.5°	134.1	129.2	126.2	125.0	123.9	122.7	123.5	127.3	131.7	138.2	144.4
75°	103.1	101.3	99.2	97.7	96.7	97.4	98.1	101.7	105.3	112.1	119.2
77.5°	75.3	73.4	72.1	71.7	71.2	71.5	73.5	76.2	79.7	84.6	90.1
80°	56.9	56.2	55.5	55.1	55.1	55.5	58.3	60.1	63.3	68.1	72.3
82.5°	41.5	41.0	40.9	40.8	41.1	41.2	42.9	45.2	47.9	51.5	55.1
85°	21.9	21.1	22.2	22.5	21.9	22.9	23.7	25.1	26.1	27.9	29.7
87.5°	9.4	10.6	10.7	11.4	11.9	12.8	12.9	14.3	15.3	16.1	16.1
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.9	27.5	29.0	30.3
92.5°	41.5	43.7	46.5	49.1	51.8	54.6	56.6	58.7	60.8	63.0	64.3
95°	94.9	96.8	100.0	103.1	106.3	109.4	111.7	113.9	116.1	118.3	119.7
97.5°	154.6	156.8	161.2	165.6	169.9	174.3	176.3	178.4	180.5	182.6	183.9
100°	199.0	201.0	205.2	209.2	213.4	217.4	220.4	223.2	226.0	228.8	230.6
102.5°	253.0	254.7	256.7	258.8	260.9	263.0	266.1	269.2	272.3	275.3	277.4
105°	330.5	332.2	334.0	335.9	337.8	339.8	341.7	343.6	345.4	347.3	348.7
107.5°	414.5	416.1	417.5	419.0	420.5	421.9	422.8	423.8	424.7	425.7	426.1
110°	472.6	473.8	474.8	475.7	476.6	477.6	478.5	479.6	480.5	481.5	481.7



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	528.7	529.7	530.8	532.1	533.3	534.5	534.9	535.4	535.8	536.2	536.2
115°	617.7	618.7	619.3	619.9	620.6	621.2	620.9	620.6	620.3	619.9	619.6
117.5°	702.5	703.0	703.6	704.2	704.7	705.4	705.6	705.9	706.2	706.3	705.9
120°	761.1	762.0	762.4	762.7	763.0	763.4	763.4	763.4	763.4	763.4	762.7
122.5°	816.2	816.9	817.7	818.6	819.4	820.2	819.9	819.7	819.4	819.2	818.6
125°	901.7	902.9	903.1	903.4	903.8	904.1	903.4	902.9	902.2	901.5	901.1
127.5°	983.7	984.5	984.9	985.2	985.6	986.0	985.6	985.3	985.1	984.7	984.2
130°	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2	1039.9	1039.6	1039.2	1038.8
132.5°	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5	1092.2	1091.9	1091.6	1091.0
135°	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7	1172.7	1172.7	1172.7	1172.1
137.5°	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8	1251.1	1251.5	1251.9	1251.3
140°	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9	1300.5	1301.2	1301.7	1301.3
142.5°	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5	1348.9	1349.2	1349.7	1349.1
145°	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6	1418.6	1418.6	1418.6	1418.1
147.5°	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5	1483.3	1484.0	1484.8	1484.1
150°	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9	1523.9	1523.9	1523.9	1523.5
152.5°	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0	1561.8	1562.5	1563.3	1563.1
155°	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7	1615.9	1617.2	1618.4	1618.3
157.5°	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6	1662.8	1664.2	1665.4	1665.0
160°	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0	1691.3	1692.5	1693.8	1693.7
162.5°	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5	1718.0	1719.5	1721.0	1720.8
165°	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6	1753.8	1755.1	1756.3	1756.1
167.5°	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5	1780.4	1782.3	1784.1	1784.1
170°	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4	1796.3	1798.2	1800.1	1800.0
172.5°	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8	1807.7	1809.6	1811.5	1811.5
175°	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5	1820.5	1822.4	1824.3	1824.1
177.5°	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8	1826.3	1827.8	1829.3	1829.2
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	803.7	805.8	804.1	806.3	804.1	805.8	803.7	805.5	808.0	806.3	810.3
5°	740.8	737.5	739.7	738.3	739.7	737.5	740.8	742.6	746.9	748.3	751.2
7.5°	682.7	679.6	676.1	674.4	676.1	679.6	682.7	683.7	687.4	692.8	696.8
10°	646.3	642.3	642.0	639.5	642.0	642.3	646.3	650.3	652.7	659.5	664.2
12.5°	619.6	616.0	611.9	610.9	611.9	616.0	619.6	623.0	623.8	631.5	634.7
15°	581.8	579.0	576.5	578.6	576.5	579.0	581.8	584.0	588.0	593.3	596.9
17.5°	550.4	548.0	547.6	545.0	547.6	548.0	550.4	551.6	558.1	561.6	567.7
20°	530.7	528.9	529.5	524.9	529.5	528.9	530.7	533.9	540.3	542.1	548.6
22.5°	514.9	511.3	511.0	510.0	511.0	511.3	514.9	517.8	519.1	524.6	529.0
25°	490.2	488.4	486.6	488.4	486.6	488.4	490.2	493.4	494.8	498.8	503.0
27.5°	468.6	466.5	466.0	466.2	466.0	466.5	468.6	468.3	472.2	475.3	478.5
30°	455.4	451.9	452.2	451.9	452.2	451.9	455.4	455.4	457.6	460.4	463.4
32.5°	441.1	438.7	438.2	437.5	438.2	438.7	441.1	440.5	443.3	446.7	449.9
35°	420.0	420.0	418.2	418.2	418.2	420.0	420.0	421.0	424.0	424.0	427.5
37.5°	400.1	399.8	398.7	398.9	398.7	399.8	400.1	401.1	402.0	403.5	405.9
40°	385.2	384.9	383.8	381.6	383.8	384.9	385.2	386.7	387.4	389.2	390.6
42.5°	371.0	369.8	369.2	368.5	369.2	369.8	371.0	371.8	372.2	374.6	377.5
45°	348.4	348.4	347.7	347.3	347.7	348.4	348.4	348.4	348.7	351.6	353.1
47.5°	326.5	327.2	328.5	328.3	328.5	327.2	326.5	325.9	326.0	327.4	329.1
50°	313.3	313.7	314.7	315.1	314.7	313.7	313.3	311.9	311.1	311.1	312.3
52.5°	298.7	300.8	302.1	301.9	302.1	300.8	298.7	297.6	296.2	294.5	296.1
55°	278.2	280.7	283.2	283.6	283.2	280.7	278.2	274.9	273.5	270.7	271.7
57.5°	258.0	261.5	264.1	264.9	264.1	261.5	258.0	254.1	249.4	248.1	246.1
60°	244.2	248.8	252.0	253.5	252.0	248.8	244.2	240.6	234.5	230.5	229.1
62.5°	231.0	236.2	239.5	239.8	239.5	236.2	231.0	225.5	219.3	214.8	212.0
65°	209.4	214.8	217.7	219.8	217.7	214.8	209.4	203.4	196.6	190.5	187.3
67.5°	186.2	191.6	194.8	196.5	194.8	191.6	186.2	178.7	172.5	165.5	161.7
70°	169.4	174.7	179.0	180.5	179.0	174.7	169.4	160.4	155.0	148.5	145.3
72.5°	152.8	157.5	161.0	162.7	161.0	157.5	152.8	144.4	138.2	131.7	127.3
75°	123.9	130.4	133.6	135.3	133.6	130.4	123.9	119.2	112.1	105.3	101.7
77.5°	95.6	101.4	103.3	104.2	103.3	101.4	95.6	90.1	84.6	79.7	76.2
80°	76.6	80.2	82.8	83.0	82.8	80.2	76.6	72.3	68.1	63.3	60.1
82.5°	58.9	61.8	62.7	63.6	62.7	61.8	58.9	55.1	51.5	47.9	45.2
85°	32.2	33.6	34.0	33.6	34.0	33.6	32.2	29.7	27.9	26.1	25.1
87.5°	16.9	16.8	17.0	17.7	17.0	16.8	16.9	16.1	16.1	15.3	14.3
90°	31.3	32.2	33.2	34.1	33.2	32.2	31.3	30.3	29.0	27.5	25.9
92.5°	65.0	65.7	66.4	67.1	66.4	65.7	65.0	64.3	63.0	60.8	58.7
95°	120.4	121.0	121.6	122.2	121.6	121.0	120.4	119.7	118.3	116.1	113.9
97.5°	184.3	184.6	185.0	185.4	185.0	184.6	184.3	183.9	182.6	180.5	178.4
100°	231.2	231.9	232.5	233.1	232.5	231.9	231.2	230.6	228.8	226.0	223.2
102.5°	278.2	279.1	280.0	280.9	280.0	279.1	278.2	277.4	275.3	272.3	269.2
105°	349.7	350.6	351.6	352.5	351.6	350.6	349.7	348.7	347.3	345.4	343.6
107.5°	426.0	426.0	425.9	425.8	425.9	426.0	426.0	426.1	425.7	424.7	423.8
110°	481.5	481.1	480.8	480.5	480.8	481.1	481.5	481.7	481.5	480.5	479.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	535.6	535.1	534.5	534.0	534.5	535.1	535.6	536.2	536.2	535.8	535.4
115°	619.3	619.0	618.7	618.4	618.7	619.0	619.3	619.6	619.9	620.3	620.6
117.5°	704.6	703.3	702.1	700.8	702.1	703.3	704.6	705.9	706.3	706.2	705.9
120°	761.5	760.2	758.9	757.7	758.9	760.2	761.5	762.7	763.4	763.4	763.4
122.5°	817.6	816.5	815.5	814.5	815.5	816.5	817.6	818.6	819.2	819.4	819.7
125°	900.8	900.4	900.1	899.8	900.1	900.4	900.8	901.1	901.5	902.2	902.9
127.5°	983.5	983.0	982.3	981.7	982.3	983.0	983.5	984.2	984.7	985.1	985.3
130°	1038.2	1037.6	1036.9	1036.3	1036.9	1037.6	1038.2	1038.8	1039.2	1039.6	1039.9
132.5°	1090.1	1089.2	1088.4	1087.4	1088.4	1089.2	1090.1	1091.0	1091.6	1091.9	1092.2
135°	1170.8	1169.6	1168.3	1167.1	1168.3	1169.6	1170.8	1172.1	1172.7	1172.7	1172.7
137.5°	1249.7	1248.1	1246.5	1244.9	1246.5	1248.1	1249.7	1251.3	1251.9	1251.5	1251.1
140°	1299.8	1298.2	1296.6	1295.0	1296.6	1298.2	1299.8	1301.3	1301.7	1301.2	1300.5
142.5°	1347.5	1346.0	1344.3	1342.7	1344.3	1346.0	1347.5	1349.1	1349.7	1349.2	1348.9
145°	1417.2	1416.3	1415.3	1414.4	1415.3	1416.3	1417.2	1418.1	1418.6	1418.6	1418.6
147.5°	1482.0	1479.8	1477.7	1475.6	1477.7	1479.8	1482.0	1484.1	1484.8	1484.0	1483.3
150°	1522.9	1522.3	1521.6	1521.0	1521.6	1522.3	1522.9	1523.5	1523.9	1523.9	1523.9
152.5°	1562.0	1560.9	1559.7	1558.6	1559.7	1560.9	1562.0	1563.1	1563.3	1562.5	1561.8
155°	1616.7	1615.1	1613.5	1612.0	1613.5	1615.1	1616.7	1618.3	1618.4	1617.2	1615.9
157.5°	1662.8	1660.8	1658.7	1656.6	1658.7	1660.8	1662.8	1665.0	1665.4	1664.2	1662.8
160°	1692.1	1690.5	1688.9	1687.3	1688.9	1690.5	1692.1	1693.7	1693.8	1692.5	1691.3
162.5°	1719.0	1717.1	1715.3	1713.4	1715.3	1717.1	1719.0	1720.8	1721.0	1719.5	1718.0
165°	1754.2	1752.3	1750.4	1748.4	1750.4	1752.3	1754.2	1756.1	1756.3	1755.1	1753.8
167.5°	1782.2	1780.3	1778.3	1776.3	1778.3	1780.3	1782.2	1784.1	1784.1	1782.3	1780.4
170°	1797.7	1795.5	1793.3	1791.1	1793.3	1795.5	1797.7	1800.0	1800.1	1798.2	1796.3
172.5°	1809.5	1807.5	1805.5	1803.6	1805.5	1807.5	1809.5	1811.5	1811.5	1809.6	1807.7
175°	1821.9	1819.7	1817.5	1815.2	1817.5	1819.7	1821.9	1824.1	1824.3	1822.4	1820.5
177.5°	1827.4	1825.6	1823.8	1822.1	1823.8	1825.6	1827.4	1829.2	1829.3	1827.8	1826.3
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	806.6	810.0	814.4	817.5	823.2	825.8	829.0	831.5	836.1	840.4	845.6
5°	752.2	758.4	766.6	775.5	785.9	793.1	803.1	809.2	821.3	832.5	843.2
7.5°	702.9	710.5	722.1	733.6	747.2	759.5	772.0	785.9	801.4	819.8	835.0
10°	669.2	679.2	691.7	706.1	722.6	736.9	753.7	768.7	787.7	809.2	829.2
12.5°	642.2	650.8	664.9	678.5	696.2	713.7	731.0	751.0	773.1	796.9	822.1
15°	605.1	612.3	623.7	642.7	660.6	677.8	703.9	722.6	750.5	776.9	807.4
17.5°	573.3	582.3	591.9	608.2	626.7	648.2	671.6	694.9	721.8	755.4	789.8
20°	553.9	561.1	572.1	584.7	604.4	625.8	648.1	671.7	704.6	739.3	776.3
22.5°	532.7	540.5	553.0	566.7	583.2	603.8	628.3	654.2	688.6	722.7	762.8
25°	507.7	513.1	524.5	536.7	553.2	570.7	596.2	624.8	658.8	697.9	738.7
27.5°	484.2	488.9	499.4	509.9	524.8	545.6	568.4	597.3	629.3	668.9	714.2
30°	467.2	472.3	481.5	493.0	507.4	525.7	548.9	576.1	610.5	649.1	696.4
32.5°	452.6	457.1	464.1	475.6	489.6	507.3	528.9	556.7	591.0	630.3	676.7
35°	430.0	435.0	440.4	449.3	461.6	478.7	502.4	528.5	561.4	599.4	642.0
37.5°	407.6	412.9	417.7	425.7	436.9	452.0	472.5	499.7	529.5	566.1	607.0
40°	393.5	397.8	401.7	410.3	421.4	435.7	454.7	479.1	510.6	544.6	578.6
42.5°	379.5	383.4	386.8	394.3	404.5	418.3	436.4	460.1	489.4	521.1	551.1
45°	357.3	359.9	363.8	370.2	378.4	391.0	408.5	429.7	454.4	484.5	507.0
47.5°	333.4	337.3	340.5	346.2	353.0	365.2	382.1	400.1	422.5	444.9	460.7
50°	315.1	319.1	323.7	329.0	335.5	346.9	362.3	380.6	399.5	416.8	430.4
52.5°	297.9	301.5	306.5	311.6	319.4	329.2	342.3	358.5	377.2	389.6	400.9
55°	272.5	274.3	280.0	285.0	292.6	299.7	312.9	327.3	338.7	348.0	357.3
57.5°	246.5	248.9	252.2	256.7	264.2	272.6	281.8	294.5	301.2	306.0	313.3
60°	229.9	230.5	232.7	238.1	243.8	251.4	262.1	271.1	276.1	280.0	286.1
62.5°	211.5	211.7	215.3	219.2	223.5	231.6	240.3	247.5	251.8	253.6	259.5
65°	185.9	185.1	187.3	190.5	195.5	200.9	208.4	214.8	214.4	216.6	220.2
67.5°	159.6	158.8	158.8	161.9	166.0	170.8	176.0	179.6	179.7	182.6	184.4
70°	141.8	139.7	141.1	143.5	145.3	149.3	155.0	156.5	156.8	158.3	160.0
72.5°	123.5	122.7	123.9	125.0	126.2	129.2	134.1	135.0	135.1	135.9	138.8
75°	98.1	97.4	96.7	97.7	99.2	101.3	103.1	104.5	104.2	104.5	106.7
77.5°	73.5	71.5	71.2	71.7	72.1	73.4	75.3	75.1	75.5	75.4	77.9
80°	58.3	55.5	55.1	55.1	55.5	56.2	56.9	57.7	56.6	57.7	58.3
82.5°	42.9	41.2	41.1	40.8	40.9	41.0	41.5	41.8	41.7	42.1	42.6
85°	23.7	22.9	21.9	22.5	22.2	21.1	21.9	20.7	20.5	20.7	21.1
87.5°	12.9	12.8	11.9	11.4	10.7	10.6	9.4	8.7	7.9	7.6	8.0
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	56.6	54.6	51.8	49.1	46.5	43.7	41.5	39.7	38.0	36.2	34.4
95°	111.7	109.4	106.3	103.1	100.0	96.8	94.9	94.3	93.7	93.0	92.4
97.5°	176.3	174.3	169.9	165.6	161.2	156.8	154.6	154.3	154.0	153.7	153.5
100°	220.4	217.4	213.4	209.2	205.2	201.0	199.0	199.0	199.0	199.0	199.0
102.5°	266.1	263.0	260.9	258.8	256.7	254.7	253.0	251.7	250.4	249.2	247.9
105°	341.7	339.8	337.8	335.9	334.0	332.2	330.5	328.9	327.3	325.6	324.1
107.5°	422.8	421.9	420.5	419.0	417.5	416.1	414.5	413.0	411.4	409.8	408.2
110°	478.5	477.6	476.6	475.7	474.8	473.8	472.6	471.0	469.4	467.9	466.3



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	534.9	534.5	533.3	532.1	530.8	529.7	528.7	527.8	527.1	526.2	525.4
115°	620.9	621.2	620.6	619.9	619.3	618.7	617.7	616.4	615.2	614.0	612.7
117.5°	705.6	705.4	704.7	704.2	703.6	703.0	702.5	701.9	701.3	700.8	700.2
120°	763.4	763.4	763.0	762.7	762.4	762.0	761.1	759.6	758.0	756.4	754.8
122.5°	819.9	820.2	819.4	818.6	817.7	816.9	816.2	815.7	815.1	814.5	814.0
125°	903.4	904.1	903.8	903.4	903.1	902.9	901.7	899.8	898.0	896.0	894.1
127.5°	985.6	986.0	985.6	985.2	984.9	984.5	983.7	982.6	981.6	980.5	979.4
130°	1040.2	1040.6	1039.9	1039.2	1038.7	1038.0	1036.9	1035.3	1033.8	1032.2	1030.6
132.5°	1092.5	1092.9	1093.0	1093.1	1093.3	1093.3	1092.1	1089.6	1086.9	1084.4	1081.8
135°	1172.7	1172.7	1172.4	1172.1	1171.8	1171.5	1170.4	1168.5	1166.6	1164.7	1162.8
137.5°	1250.8	1250.4	1249.6	1249.0	1248.3	1247.5	1246.3	1244.4	1242.6	1240.9	1239.0
140°	1299.9	1299.3	1298.4	1297.4	1296.4	1295.4	1294.2	1292.6	1291.0	1289.5	1287.9
142.5°	1348.5	1348.1	1347.0	1345.8	1344.5	1343.3	1342.1	1340.8	1339.4	1338.1	1336.8
145°	1418.6	1418.6	1417.7	1416.7	1415.8	1414.9	1413.8	1412.5	1411.3	1409.9	1408.7
147.5°	1482.5	1481.8	1481.0	1480.3	1479.5	1478.8	1478.0	1477.3	1476.6	1475.9	1475.3
150°	1523.9	1523.9	1522.6	1521.4	1520.0	1518.8	1518.3	1518.6	1519.0	1519.3	1519.6
152.5°	1561.0	1560.3	1559.7	1559.2	1558.8	1558.2	1557.7	1557.3	1556.9	1556.4	1555.9
155°	1614.7	1613.4	1613.1	1612.8	1612.5	1612.1	1612.0	1612.0	1612.0	1612.0	1612.0
157.5°	1661.6	1660.3	1660.0	1659.7	1659.3	1659.1	1659.3	1659.9	1660.7	1661.3	1662.0
160°	1690.0	1688.8	1688.5	1688.1	1687.8	1687.5	1687.8	1688.8	1689.7	1690.6	1691.6
162.5°	1716.5	1714.9	1714.9	1714.8	1714.7	1714.7	1715.0	1715.7	1716.4	1717.0	1717.8
165°	1752.6	1751.3	1751.0	1750.7	1750.4	1750.0	1750.2	1750.9	1751.4	1752.1	1752.8
167.5°	1778.5	1776.6	1776.6	1776.6	1776.6	1776.6	1777.3	1778.5	1779.8	1781.0	1782.3
170°	1794.4	1792.5	1792.5	1792.5	1792.5	1792.5	1793.2	1794.4	1795.6	1797.0	1798.2
172.5°	1805.8	1803.9	1803.9	1803.9	1803.9	1803.9	1804.5	1805.8	1807.0	1808.4	1809.6
175°	1818.5	1816.7	1816.7	1816.7	1816.7	1816.7	1817.3	1818.5	1819.9	1821.1	1822.4
177.5°	1824.8	1823.3	1823.4	1823.7	1824.0	1824.2	1824.9	1825.9	1826.9	1827.9	1828.9
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	848.2	852.2	854.7	859.6	863.7	865.9	867.9	869.6	871.7	873.4	878.3
5°	853.6	862.9	870.8	883.0	894.1	902.7	911.9	920.2	927.0	936.7	944.1
7.5°	851.2	867.8	885.1	903.9	923.2	941.1	957.5	973.0	986.9	1003.8	1018.6
10°	848.9	871.5	893.7	919.1	945.3	967.4	988.3	1009.4	1024.7	1046.2	1064.5
12.5°	847.3	873.8	900.6	931.1	959.9	991.2	1018.9	1034.3	1057.7	1074.9	1096.6
15°	840.0	875.1	911.9	946.3	987.1	1016.2	1040.5	1070.5	1092.4	1114.3	1137.8
17.5°	827.0	866.8	908.0	953.1	992.2	1023.4	1054.7	1083.7	1109.8	1139.1	1168.6
20°	821.0	860.7	908.0	954.2	992.5	1025.1	1057.3	1089.2	1117.9	1155.5	1189.4
22.5°	808.4	856.5	900.0	945.0	984.5	1019.9	1056.5	1092.6	1130.7	1173.2	1215.8
25°	785.9	834.6	880.8	925.2	965.0	1009.4	1048.4	1096.7	1145.4	1201.6	1254.6
27.5°	762.6	809.2	851.5	894.4	940.8	991.0	1041.6	1096.5	1160.3	1231.1	1306.0
30°	743.7	787.7	828.9	872.9	921.2	977.8	1033.3	1098.5	1172.2	1252.1	1340.9
32.5°	721.6	762.2	802.3	848.9	901.5	961.2	1025.9	1097.3	1186.0	1276.8	1368.1
35°	683.9	717.9	759.0	808.8	868.3	936.7	1011.5	1096.0	1197.7	1301.8	1378.8
37.5°	639.1	670.8	714.2	768.7	831.0	904.5	993.3	1093.4	1201.5	1284.5	1309.4
40°	609.1	638.4	683.5	740.1	803.8	881.6	978.9	1084.9	1189.4	1242.5	1222.0
42.5°	576.9	607.8	651.8	707.8	776.3	860.9	960.8	1066.9	1154.5	1174.5	1104.0
45°	526.3	558.2	601.5	658.1	731.9	823.5	927.7	1024.0	1074.5	1038.3	929.2
47.5°	479.3	509.2	549.3	607.7	683.8	778.6	878.9	955.7	959.8	873.5	756.9
50°	447.2	474.8	515.2	573.6	649.1	745.1	835.7	896.2	869.0	771.3	659.2
52.5°	415.7	442.7	482.6	540.4	615.1	702.9	787.3	829.7	778.4	678.2	582.4
55°	370.2	393.9	432.9	486.3	557.1	638.8	710.4	725.0	658.5	559.6	481.9
57.5°	325.8	347.9	383.4	432.5	497.3	569.7	625.7	622.5	552.1	467.3	405.7
60°	295.8	317.3	348.7	396.7	455.8	518.1	566.1	554.6	484.8	411.8	359.9
62.5°	268.8	288.0	317.8	359.8	413.7	471.4	510.8	493.9	425.5	361.7	320.6
65°	229.1	245.2	270.7	306.5	351.3	398.9	429.3	407.5	349.1	299.4	266.4
67.5°	191.2	204.2	225.5	254.1	292.3	330.5	349.0	327.1	280.3	244.0	219.6
70°	167.2	178.7	195.1	220.6	253.8	286.1	300.0	280.3	240.3	209.1	191.5
72.5°	143.2	152.6	167.1	189.9	216.6	244.6	256.7	238.0	205.0	178.7	162.3
75°	110.7	117.1	127.1	142.9	164.0	186.2	193.0	176.5	155.4	135.7	125.0
77.5°	79.2	84.6	92.3	102.2	117.2	131.3	137.2	127.7	111.3	98.9	90.1
80°	60.9	63.7	70.2	78.4	90.2	99.2	103.1	97.0	85.6	76.3	69.5
82.5°	43.4	46.3	50.1	56.9	64.5	70.5	74.7	70.7	62.4	55.0	51.1
85°	21.1	22.9	25.1	27.9	33.6	37.2	36.9	34.4	31.1	28.3	26.1
87.5°	8.2	9.0	10.4	12.3	13.7	15.3	16.3	16.1	15.5	14.9	14.3
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.9
92.5°	36.2	38.0	39.7	41.5	43.7	46.5	49.1	51.8	54.6	56.6	58.7
95°	93.0	93.7	94.3	94.9	96.8	100.0	103.1	106.3	109.4	111.7	113.9
97.5°	153.7	154.0	154.3	154.6	156.8	161.2	165.6	169.9	174.3	176.3	178.4
100°	199.0	199.0	199.0	199.0	201.0	205.2	209.2	213.4	217.4	220.4	223.2
102.5°	249.2	250.4	251.7	253.0	254.7	256.7	258.8	260.9	263.0	266.1	269.2
105°	325.6	327.3	328.9	330.5	332.2	334.0	335.9	337.8	339.8	341.7	343.6
107.5°	409.8	411.4	413.0	414.5	416.1	417.5	419.0	420.5	421.9	422.8	423.8
110°	467.9	469.4	471.0	472.6	473.8	474.8	475.7	476.6	477.6	478.5	479.6





TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	526.2	527.1	527.8	528.7	529.7	530.8	532.1	533.3	534.5	534.9	535.4
115°	614.0	615.2	616.4	617.7	618.7	619.3	619.9	620.6	621.2	620.9	620.6
117.5°	700.8	701.3	701.9	702.5	703.0	703.6	704.2	704.7	705.4	705.6	705.9
120°	756.4	758.0	759.6	761.1	762.0	762.4	762.7	763.0	763.4	763.4	763.4
122.5°	814.5	815.1	815.7	816.2	816.9	817.7	818.6	819.4	820.2	819.9	819.7
125°	896.0	898.0	899.8	901.7	902.9	903.1	903.4	903.8	904.1	903.4	902.9
127.5°	980.5	981.6	982.6	983.7	984.5	984.9	985.2	985.6	986.0	985.6	985.3
130°	1032.2	1033.8	1035.3	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2	1039.9
132.5°	1084.4	1086.9	1089.6	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5	1092.2
135°	1164.7	1166.6	1168.5	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7	1172.7
137.5°	1240.9	1242.6	1244.4	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8	1251.1
140°	1289.5	1291.0	1292.6	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9	1300.5
142.5°	1338.1	1339.4	1340.8	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5	1348.9
145°	1409.9	1411.3	1412.5	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6	1418.6
147.5°	1475.9	1476.6	1477.3	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5	1483.3
150°	1519.3	1519.0	1518.6	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9	1523.9
152.5°	1556.4	1556.9	1557.3	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0	1561.8
155°	1612.0	1612.0	1612.0	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7	1615.9
157.5°	1661.3	1660.7	1659.9	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6	1662.8
160°	1690.6	1689.7	1688.8	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0	1691.3
162.5°	1717.0	1716.4	1715.7	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5	1718.0
165°	1752.1	1751.4	1750.9	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6	1753.8
167.5°	1781.0	1779.8	1778.5	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5	1780.4
170°	1797.0	1795.6	1794.4	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4	1796.3
172.5°	1808.4	1807.0	1805.8	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8	1807.7
175°	1821.1	1819.9	1818.5	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5	1820.5
177.5°	1827.9	1826.9	1825.9	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8	1826.3
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	882.2	884.5	889.4	887.7	889.9	891.1	892.3
5°	953.5	965.0	970.0	969.2	976.8	975.0	973.2
7.5°	1034.0	1046.0	1052.7	1061.1	1066.0	1066.3	1070.5
10°	1079.5	1095.2	1101.7	1110.7	1116.4	1119.6	1119.3
12.5°	1114.5	1126.8	1141.2	1145.7	1153.4	1157.4	1155.9
15°	1156.5	1176.2	1191.2	1198.7	1208.4	1211.3	1215.2
17.5°	1194.0	1220.4	1238.0	1261.3	1270.2	1275.5	1272.3
20°	1222.4	1257.1	1274.7	1302.6	1318.0	1326.3	1323.3
22.5°	1255.9	1293.5	1326.0	1350.1	1373.6	1384.7	1387.0
25°	1313.3	1364.9	1412.5	1444.4	1473.4	1480.2	1495.2
27.5°	1377.5	1438.3	1489.2	1522.7	1542.9	1550.5	1555.2
30°	1417.9	1478.4	1516.7	1538.1	1544.6	1543.9	1543.2
32.5°	1437.7	1475.6	1482.9	1476.9	1462.2	1449.6	1436.6
35°	1409.7	1381.4	1339.1	1284.7	1244.6	1204.1	1200.1
37.5°	1267.8	1177.3	1107.0	1028.5	983.2	955.2	935.8
40°	1134.3	1031.5	946.3	880.1	833.9	815.7	797.8
42.5°	989.4	891.2	815.7	760.3	725.7	705.4	691.2
45°	803.8	717.2	658.1	618.0	590.4	574.7	565.7
47.5°	658.6	594.6	544.4	515.5	496.4	484.2	484.2
50°	580.8	519.5	486.3	463.4	446.9	437.2	438.9
52.5°	511.7	466.0	437.5	418.3	406.1	400.2	400.0
55°	427.9	394.9	376.4	362.3	354.1	347.3	348.7
57.5°	366.0	338.2	325.7	314.1	308.4	305.7	301.8
60°	327.6	306.1	295.4	286.1	280.3	278.2	274.3
62.5°	293.5	276.6	266.2	258.5	253.4	252.7	249.6
65°	246.7	233.8	224.5	220.9	215.6	214.1	214.1
67.5°	203.4	194.2	186.9	183.6	181.3	181.6	179.8
70°	176.2	168.6	164.0	160.4	158.6	159.0	157.5
72.5°	154.1	145.7	141.7	139.5	137.1	138.1	137.5
75°	116.7	112.4	110.3	108.1	106.7	105.9	105.3
77.5°	85.7	81.9	80.3	79.1	79.3	77.6	78.9
80°	66.3	63.1	61.9	60.1	59.8	59.8	59.5
82.5°	48.4	46.7	45.9	44.4	43.7	44.3	43.4
85°	25.1	23.7	23.3	23.3	22.5	21.9	23.7
87.5°	14.7	13.9	14.0	13.9	14.1	14.0	13.7
90°	27.5	29.0	30.3	31.3	32.2	33.2	34.1
92.5°	60.8	63.0	64.3	65.0	65.7	66.4	67.1
95°	116.1	118.3	119.7	120.4	121.0	121.6	122.2
97.5°	180.5	182.6	183.9	184.3	184.6	185.0	185.4
100°	226.0	228.8	230.6	231.2	231.9	232.5	233.1
102.5°	272.3	275.3	277.4	278.2	279.1	280.0	280.9
105°	345.4	347.3	348.7	349.7	350.6	351.6	352.5
107.5°	424.7	425.7	426.1	426.0	426.0	425.9	425.8
110°	480.5	481.5	481.7	481.5	481.1	480.8	480.5



TEST NUMBER: P333395-830

CATALOG NUMBER: S125DIW-S610D1560U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	535.8	536.2	536.2	535.6	535.1	534.5	534.0
115°	620.3	619.9	619.6	619.3	619.0	618.7	618.4
117.5°	706.2	706.3	705.9	704.6	703.3	702.1	700.8
120°	763.4	763.4	762.7	761.5	760.2	758.9	757.7
122.5°	819.4	819.2	818.6	817.6	816.5	815.5	814.5
125°	902.2	901.5	901.1	900.8	900.4	900.1	899.8
127.5°	985.1	984.7	984.2	983.5	983.0	982.3	981.7
130°	1039.6	1039.2	1038.8	1038.2	1037.6	1036.9	1036.3
132.5°	1091.9	1091.6	1091.0	1090.1	1089.2	1088.4	1087.4
135°	1172.7	1172.7	1172.1	1170.8	1169.6	1168.3	1167.1
137.5°	1251.5	1251.9	1251.3	1249.7	1248.1	1246.5	1244.9
140°	1301.2	1301.7	1301.3	1299.8	1298.2	1296.6	1295.0
142.5°	1349.2	1349.7	1349.1	1347.5	1346.0	1344.3	1342.7
145°	1418.6	1418.6	1418.1	1417.2	1416.3	1415.3	1414.4
147.5°	1484.0	1484.8	1484.1	1482.0	1479.8	1477.7	1475.6
150°	1523.9	1523.9	1523.5	1522.9	1522.3	1521.6	1521.0
152.5°	1562.5	1563.3	1563.1	1562.0	1560.9	1559.7	1558.6
155°	1617.2	1618.4	1618.3	1616.7	1615.1	1613.5	1612.0
157.5°	1664.2	1665.4	1665.0	1662.8	1660.8	1658.7	1656.6
160°	1692.5	1693.8	1693.7	1692.1	1690.5	1688.9	1687.3
162.5°	1719.5	1721.0	1720.8	1719.0	1717.1	1715.3	1713.4
165°	1755.1	1756.3	1756.1	1754.2	1752.3	1750.4	1748.4
167.5°	1782.3	1784.1	1784.1	1782.2	1780.3	1778.3	1776.3
170°	1798.2	1800.1	1800.0	1797.7	1795.5	1793.3	1791.1
172.5°	1809.6	1811.5	1811.5	1809.5	1807.5	1805.5	1803.6
175°	1822.4	1824.3	1824.1	1821.9	1819.7	1817.5	1815.2
177.5°	1827.8	1829.3	1829.2	1827.4	1825.6	1823.8	1822.1
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6

(END OF REPORT)