

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333709-830

Luminaire Tested: **S125RDIW-S1090D1050U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333709-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7442.2 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	52	51	46
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	29
5	70	58	50	45	65	55	48	42	48	42	38	41	37	33	35	31	29	26
6	64	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	23
7	60	48	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	2.0
10°-20°	435.5	5.9
20°-30°	690.5	9.3
30°-40°	832.7	11.2
40°-50°	743.6	10.0
50°-60°	570.3	7.7
60°-70°	370.6	5.0
70°-80°	180.2	2.4
80°-90°	45.7	0.6
90°-100°	82.2	1.1
100°-110°	242.7	3.3
110°-120°	411.1	5.5
120°-130°	541.1	7.3
130°-140°	606.3	8.1
140°-150°	594.2	8.0
150°-160°	499.1	6.7
160°-170°	331.7	4.5
170°-180°	116.1	1.6
0°-30°	1274.6	17.1
0°-40°	2107.3	28.3
0°-60°	3421.2	46.0
0°-90°	4017.7	54.0
90°-120°	736.0	9.9
90°-150°	2477.6	33.3
90°-180°	3424.0	46.0
0°-180°	7442.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	23	1	23	1	23	15
95°	82	62	82	62	82	84
105°	237	218	237	218	237	251
115°	416	412	416	412	416	411
125°	604	601	604	601	604	540
135°	784	781	784	781	784	605
145°	950	946	950	946	950	593
155°	1083	1083	1083	1083	1083	498
165°	1175	1178	1175	1178	1175	331
175°	1220	1224	1220	1224	1220	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	15.7	15.2	14.5	14.4	14.8	15.6	14.9	14.1	13.9	13.8	13.9
90°	22.9	22.2	21.7	21.0	20.4	19.5	18.5	17.4	16.3	15.3	13.8
92.5°	45.1	44.6	44.1	43.6	43.2	42.3	40.9	39.5	38.1	36.7	34.9
95°	82.1	81.7	81.2	80.9	80.4	79.5	77.9	76.5	75.0	73.5	71.4
97.5°	124.5	124.3	124.0	123.8	123.5	122.7	121.3	119.9	118.5	117.1	114.1
100°	156.7	156.2	155.8	155.3	155.0	153.7	151.8	150.0	148.1	146.1	143.4
102.5°	188.7	188.1	187.6	186.9	186.3	185.0	182.9	180.9	178.8	176.7	175.3
105°	236.9	236.2	235.5	235.0	234.3	233.4	232.1	230.8	229.5	228.3	227.0
107.5°	286.2	286.2	286.3	286.3	286.3	286.0	285.4	284.7	284.1	283.4	282.5
110°	322.8	323.0	323.2	323.5	323.7	323.5	322.8	322.2	321.5	320.9	320.3



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	358.7	359.1	359.5	359.9	360.2	360.2	360.0	359.7	359.4	359.1	358.3
115°	415.5	415.7	415.8	416.0	416.3	416.5	416.7	416.9	417.2	417.4	416.9
117.5°	470.8	471.6	472.5	473.3	474.2	474.6	474.4	474.2	474.1	473.9	473.5
120°	509.1	509.9	510.8	511.6	512.5	512.8	512.8	512.8	512.8	512.8	512.6
122.5°	547.2	547.9	548.6	549.3	550.0	550.4	550.5	550.7	550.9	551.1	550.5
125°	604.5	604.7	604.9	605.2	605.4	605.7	606.1	606.5	607.0	607.4	607.2
127.5°	659.6	660.0	660.4	660.8	661.3	661.6	661.8	661.9	662.2	662.4	662.1
130°	696.3	696.6	697.1	697.5	698.0	698.2	698.4	698.7	698.9	699.1	698.7
132.5°	730.6	731.2	731.8	732.4	733.0	733.4	733.6	733.8	734.1	734.2	734.3
135°	784.1	784.9	785.8	786.6	787.5	787.9	787.9	787.9	787.9	787.9	787.7
137.5°	836.4	837.4	838.6	839.6	840.7	841.0	840.8	840.6	840.3	840.1	839.6
140°	870.1	871.1	872.1	873.3	874.3	874.6	874.2	873.7	873.4	872.9	872.2
142.5°	902.1	903.2	904.3	905.3	906.3	906.8	906.5	906.3	906.0	905.8	904.9
145°	950.3	950.9	951.5	952.2	952.8	953.1	953.1	953.1	953.1	953.1	952.5
147.5°	991.4	992.8	994.2	995.7	997.1	997.6	997.0	996.6	996.1	995.5	995.0
150°	1021.9	1022.3	1022.8	1023.1	1023.6	1023.8	1023.8	1023.8	1023.8	1023.8	1022.9
152.5°	1047.1	1047.8	1048.7	1049.4	1050.2	1050.3	1049.8	1049.2	1048.8	1048.3	1047.9
155°	1083.0	1084.1	1085.1	1086.2	1087.2	1087.4	1086.6	1085.7	1084.9	1084.0	1083.7
157.5°	1113.0	1114.4	1115.8	1117.2	1118.6	1118.9	1118.0	1117.2	1116.3	1115.5	1115.3
160°	1133.6	1134.7	1135.8	1136.8	1137.8	1138.0	1137.2	1136.3	1135.5	1134.6	1134.3
162.5°	1151.2	1152.4	1153.7	1154.9	1156.1	1156.2	1155.2	1154.2	1153.2	1152.2	1152.2
165°	1174.7	1176.0	1177.2	1178.6	1179.8	1180.0	1179.1	1178.3	1177.4	1176.6	1176.4
167.5°	1193.4	1194.8	1196.1	1197.4	1198.7	1198.7	1197.4	1196.2	1194.9	1193.6	1193.6
170°	1203.3	1204.9	1206.4	1207.8	1209.3	1209.4	1208.2	1206.8	1205.6	1204.3	1204.3
172.5°	1211.7	1213.1	1214.4	1215.7	1217.0	1217.0	1215.8	1214.5	1213.2	1211.9	1211.9
175°	1219.6	1221.1	1222.6	1224.1	1225.5	1225.7	1224.4	1223.0	1221.8	1220.5	1220.5
177.5°	1224.2	1225.4	1226.5	1227.8	1228.9	1229.0	1228.0	1227.0	1226.0	1224.9	1225.1
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	14.1	13.9	14.0	13.8	12.9	15.1	16.3	16.5	15.8	15.1	14.4
90°	12.3	10.8	9.3	7.7	6.0	4.3	2.6	0.9	2.6	4.3	6.0
92.5°	33.0	31.2	29.4	27.9	26.7	25.4	24.3	23.1	24.3	25.4	26.7
95°	69.3	67.2	65.0	63.8	63.3	63.0	62.5	62.1	62.5	63.0	63.3
97.5°	111.2	108.3	105.4	103.9	103.7	103.5	103.3	103.1	103.3	103.5	103.7
100°	140.6	137.8	135.1	133.7	133.7	133.7	133.7	133.7	133.7	133.7	133.7
102.5°	173.9	172.5	171.1	169.9	169.1	168.2	167.4	166.5	167.4	168.2	169.1
105°	225.7	224.4	223.2	222.0	220.9	219.9	218.8	217.7	218.8	219.9	220.9
107.5°	281.5	280.5	279.6	278.5	277.5	276.4	275.3	274.3	275.3	276.4	277.5
110°	319.6	319.0	318.4	317.5	316.4	315.4	314.3	313.2	314.3	315.4	316.4



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	357.5	356.7	355.9	355.2	354.7	354.1	353.5	353.0	353.5	354.1	354.7
115°	416.5	416.0	415.7	415.0	414.2	413.3	412.5	411.6	412.5	413.3	414.2
117.5°	473.2	472.8	472.4	472.0	471.6	471.2	470.8	470.4	470.8	471.2	471.6
120°	512.5	512.2	512.0	511.3	510.3	509.3	508.2	507.1	508.2	509.3	510.3
122.5°	550.0	549.4	548.8	548.4	548.0	547.6	547.2	546.9	547.2	547.6	548.0
125°	607.0	606.8	606.5	605.8	604.5	603.2	602.0	600.7	602.0	603.2	604.5
127.5°	661.9	661.7	661.4	660.9	660.2	659.5	658.7	658.0	658.7	659.5	660.2
130°	698.2	697.9	697.4	696.6	695.6	694.6	693.4	692.4	693.4	694.6	695.6
132.5°	734.4	734.5	734.6	733.8	732.0	730.3	728.5	726.8	728.5	730.3	732.0
135°	787.5	787.3	787.0	786.4	785.0	783.7	782.5	781.2	782.5	783.7	785.0
137.5°	839.1	838.7	838.2	837.4	836.1	834.9	833.7	832.5	833.7	834.9	836.1
140°	871.7	871.0	870.3	869.5	868.5	867.4	866.3	865.3	866.3	867.4	868.5
142.5°	904.2	903.3	902.6	901.7	900.8	899.9	899.0	898.1	899.0	899.9	900.8
145°	951.9	951.2	950.6	949.8	949.0	948.1	947.3	946.4	947.3	948.1	949.0
147.5°	994.5	994.0	993.5	993.0	992.5	992.1	991.6	991.2	991.6	992.1	992.5
150°	1022.1	1021.2	1020.4	1020.1	1020.3	1020.5	1020.8	1021.0	1020.8	1020.5	1020.3
152.5°	1047.5	1047.3	1046.9	1046.6	1046.3	1045.9	1045.7	1045.4	1045.7	1045.9	1046.3
155°	1083.5	1083.4	1083.1	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
157.5°	1115.0	1114.8	1114.7	1114.7	1115.2	1115.7	1116.2	1116.6	1116.2	1115.7	1115.2
160°	1134.2	1134.0	1133.8	1134.0	1134.6	1135.2	1135.9	1136.5	1135.9	1135.2	1134.6
162.5°	1152.1	1152.1	1152.0	1152.2	1152.6	1153.1	1153.6	1154.0	1153.6	1153.1	1152.6
165°	1176.2	1176.0	1175.7	1175.8	1176.3	1176.7	1177.1	1177.6	1177.1	1176.7	1176.3
167.5°	1193.6	1193.6	1193.6	1194.0	1194.9	1195.7	1196.6	1197.4	1196.6	1195.7	1194.9
170°	1204.3	1204.3	1204.3	1204.8	1205.6	1206.5	1207.3	1208.2	1207.3	1206.5	1205.6
172.5°	1211.9	1211.9	1211.9	1212.4	1213.2	1214.1	1214.9	1215.8	1214.9	1214.1	1213.2
175°	1220.5	1220.5	1220.5	1221.0	1221.8	1222.7	1223.5	1224.4	1223.5	1222.7	1221.8
177.5°	1225.3	1225.4	1225.6	1226.1	1226.7	1227.4	1228.0	1228.8	1228.0	1227.4	1226.7
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	14.2	14.6	14.4	15.7	14.4	15.3	15.5	15.2	15.4	15.6	15.3
90°	7.7	9.3	10.8	12.3	13.8	15.3	16.3	17.4	18.5	19.5	20.4
92.5°	27.9	29.4	31.2	33.0	34.9	36.7	38.1	39.5	40.9	42.3	43.2
95°	63.8	65.0	67.2	69.3	71.4	73.5	75.0	76.5	77.9	79.5	80.4
97.5°	103.9	105.4	108.3	111.2	114.1	117.1	118.5	119.9	121.3	122.7	123.5
100°	133.7	135.1	137.8	140.6	143.4	146.1	148.1	150.0	151.8	153.7	155.0
102.5°	169.9	171.1	172.5	173.9	175.3	176.7	178.8	180.9	182.9	185.0	186.3
105°	222.0	223.2	224.4	225.7	227.0	228.3	229.5	230.8	232.1	233.4	234.3
107.5°	278.5	279.6	280.5	281.5	282.5	283.4	284.1	284.7	285.4	286.0	286.3
110°	317.5	318.4	319.0	319.6	320.3	320.9	321.5	322.2	322.8	323.5	323.7



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	355.2	355.9	356.7	357.5	358.3	359.1	359.4	359.7	360.0	360.2	360.2
115°	415.0	415.7	416.0	416.5	416.9	417.4	417.2	416.9	416.7	416.5	416.3
117.5°	472.0	472.4	472.8	473.2	473.5	473.9	474.1	474.2	474.4	474.6	474.2
120°	511.3	512.0	512.2	512.5	512.6	512.8	512.8	512.8	512.8	512.8	512.5
122.5°	548.4	548.8	549.4	550.0	550.5	551.1	550.9	550.7	550.5	550.4	550.0
125°	605.8	606.5	606.8	607.0	607.2	607.4	607.0	606.5	606.1	605.7	605.4
127.5°	660.9	661.4	661.7	661.9	662.1	662.4	662.2	661.9	661.8	661.6	661.3
130°	696.6	697.4	697.9	698.2	698.7	699.1	698.9	698.7	698.4	698.2	698.0
132.5°	733.8	734.6	734.5	734.4	734.3	734.2	734.1	733.8	733.6	733.4	733.0
135°	786.4	787.0	787.3	787.5	787.7	787.9	787.9	787.9	787.9	787.9	787.5
137.5°	837.4	838.2	838.7	839.1	839.6	840.1	840.3	840.6	840.8	841.0	840.7
140°	869.5	870.3	871.0	871.7	872.2	872.9	873.4	873.7	874.2	874.6	874.3
142.5°	901.7	902.6	903.3	904.2	904.9	905.8	906.0	906.3	906.5	906.8	906.3
145°	949.8	950.6	951.2	951.9	952.5	953.1	953.1	953.1	953.1	953.1	952.8
147.5°	993.0	993.5	994.0	994.5	995.0	995.5	996.1	996.6	997.0	997.6	997.1
150°	1020.1	1020.4	1021.2	1022.1	1022.9	1023.8	1023.8	1023.8	1023.8	1023.8	1023.6
152.5°	1046.6	1046.9	1047.3	1047.5	1047.9	1048.3	1048.8	1049.2	1049.8	1050.3	1050.2
155°	1083.0	1083.1	1083.4	1083.5	1083.7	1084.0	1084.9	1085.7	1086.6	1087.4	1087.2
157.5°	1114.7	1114.7	1114.8	1115.0	1115.3	1115.5	1116.3	1117.2	1118.0	1118.9	1118.6
160°	1134.0	1133.8	1134.0	1134.2	1134.3	1134.6	1135.5	1136.3	1137.2	1138.0	1137.8
162.5°	1152.2	1152.0	1152.1	1152.1	1152.2	1152.2	1153.2	1154.2	1155.2	1156.2	1156.1
165°	1175.8	1175.7	1176.0	1176.2	1176.4	1176.6	1177.4	1178.3	1179.1	1180.0	1179.8
167.5°	1194.0	1193.6	1193.6	1193.6	1193.6	1193.6	1194.9	1196.2	1197.4	1198.7	1198.7
170°	1204.8	1204.3	1204.3	1204.3	1204.3	1204.3	1205.6	1206.8	1208.2	1209.4	1209.3
172.5°	1212.4	1211.9	1211.9	1211.9	1211.9	1211.9	1213.2	1214.5	1215.8	1217.0	1217.0
175°	1221.0	1220.5	1220.5	1220.5	1220.5	1220.5	1221.8	1223.0	1224.4	1225.7	1225.5
177.5°	1226.1	1225.6	1225.4	1225.3	1225.1	1224.9	1226.0	1227.0	1228.0	1229.0	1228.9
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	15.9	15.6	15.6	15.7	15.6	15.6	15.9	15.3	15.6	15.4	15.2
90°	21.0	21.7	22.2	22.9	22.2	21.7	21.0	20.4	19.5	18.5	17.4
92.5°	43.6	44.1	44.6	45.1	44.6	44.1	43.6	43.2	42.3	40.9	39.5
95°	80.9	81.2	81.7	82.1	81.7	81.2	80.9	80.4	79.5	77.9	76.5
97.5°	123.8	124.0	124.3	124.5	124.3	124.0	123.8	123.5	122.7	121.3	119.9
100°	155.3	155.8	156.2	156.7	156.2	155.8	155.3	155.0	153.7	151.8	150.0
102.5°	186.9	187.6	188.1	188.7	188.1	187.6	186.9	186.3	185.0	182.9	180.9
105°	235.0	235.5	236.2	236.9	236.2	235.5	235.0	234.3	233.4	232.1	230.8
107.5°	286.3	286.3	286.2	286.2	286.2	286.3	286.3	286.3	286.0	285.4	284.7
110°	323.5	323.2	323.0	322.8	323.0	323.2	323.5	323.7	323.5	322.8	322.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	359.9	359.5	359.1	358.7	359.1	359.5	359.9	360.2	360.2	360.0	359.7
115°	416.0	415.8	415.7	415.5	415.7	415.8	416.0	416.3	416.5	416.7	416.9
117.5°	473.3	472.5	471.6	470.8	471.6	472.5	473.3	474.2	474.6	474.4	474.2
120°	511.6	510.8	509.9	509.1	509.9	510.8	511.6	512.5	512.8	512.8	512.8
122.5°	549.3	548.6	547.9	547.2	547.9	548.6	549.3	550.0	550.4	550.5	550.7
125°	605.2	604.9	604.7	604.5	604.7	604.9	605.2	605.4	605.7	606.1	606.5
127.5°	660.8	660.4	660.0	659.6	660.0	660.4	660.8	661.3	661.6	661.8	661.9
130°	697.5	697.1	696.6	696.3	696.6	697.1	697.5	698.0	698.2	698.4	698.7
132.5°	732.4	731.8	731.2	730.6	731.2	731.8	732.4	733.0	733.4	733.6	733.8
135°	786.6	785.8	784.9	784.1	784.9	785.8	786.6	787.5	787.9	787.9	787.9
137.5°	839.6	838.6	837.4	836.4	837.4	838.6	839.6	840.7	841.0	840.8	840.6
140°	873.3	872.1	871.1	870.1	871.1	872.1	873.3	874.3	874.6	874.2	873.7
142.5°	905.3	904.3	903.2	902.1	903.2	904.3	905.3	906.3	906.8	906.5	906.3
145°	952.2	951.5	950.9	950.3	950.9	951.5	952.2	952.8	953.1	953.1	953.1
147.5°	995.7	994.2	992.8	991.4	992.8	994.2	995.7	997.1	997.6	997.0	996.6
150°	1023.1	1022.8	1022.3	1021.9	1022.3	1022.8	1023.1	1023.6	1023.8	1023.8	1023.8
152.5°	1049.4	1048.7	1047.8	1047.1	1047.8	1048.7	1049.4	1050.2	1050.3	1049.8	1049.2
155°	1086.2	1085.1	1084.1	1083.0	1084.1	1085.1	1086.2	1087.2	1087.4	1086.6	1085.7
157.5°	1117.2	1115.8	1114.4	1113.0	1114.4	1115.8	1117.2	1118.6	1118.9	1118.0	1117.2
160°	1136.8	1135.8	1134.7	1133.6	1134.7	1135.8	1136.8	1137.8	1138.0	1137.2	1136.3
162.5°	1154.9	1153.7	1152.4	1151.2	1152.4	1153.7	1154.9	1156.1	1156.2	1155.2	1154.2
165°	1178.6	1177.2	1176.0	1174.7	1176.0	1177.2	1178.6	1179.8	1180.0	1179.1	1178.3
167.5°	1197.4	1196.1	1194.8	1193.4	1194.8	1196.1	1197.4	1198.7	1198.7	1197.4	1196.2
170°	1207.8	1206.4	1204.9	1203.3	1204.9	1206.4	1207.8	1209.3	1209.4	1208.2	1206.8
172.5°	1215.7	1214.4	1213.1	1211.7	1213.1	1214.4	1215.7	1217.0	1217.0	1215.8	1214.5
175°	1224.1	1222.6	1221.1	1219.6	1221.1	1222.6	1224.1	1225.5	1225.7	1224.4	1223.0
177.5°	1227.8	1226.5	1225.4	1224.2	1225.4	1226.5	1227.8	1228.9	1229.0	1228.0	1227.0
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	15.5	15.3	14.4	15.7	14.4	14.6	14.2	14.4	15.1	15.8	16.5
90°	16.3	15.3	13.8	12.3	10.8	9.3	7.7	6.0	4.3	2.6	0.9
92.5°	38.1	36.7	34.9	33.0	31.2	29.4	27.9	26.7	25.4	24.3	23.1
95°	75.0	73.5	71.4	69.3	67.2	65.0	63.8	63.3	63.0	62.5	62.1
97.5°	118.5	117.1	114.1	111.2	108.3	105.4	103.9	103.7	103.5	103.3	103.1
100°	148.1	146.1	143.4	140.6	137.8	135.1	133.7	133.7	133.7	133.7	133.7
102.5°	178.8	176.7	175.3	173.9	172.5	171.1	169.9	169.1	168.2	167.4	166.5
105°	229.5	228.3	227.0	225.7	224.4	223.2	222.0	220.9	219.9	218.8	217.7
107.5°	284.1	283.4	282.5	281.5	280.5	279.6	278.5	277.5	276.4	275.3	274.3
110°	321.5	320.9	320.3	319.6	319.0	318.4	317.5	316.4	315.4	314.3	313.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	359.4	359.1	358.3	357.5	356.7	355.9	355.2	354.7	354.1	353.5	353.0
115°	417.2	417.4	416.9	416.5	416.0	415.7	415.0	414.2	413.3	412.5	411.6
117.5°	474.1	473.9	473.5	473.2	472.8	472.4	472.0	471.6	471.2	470.8	470.4
120°	512.8	512.8	512.6	512.5	512.2	512.0	511.3	510.3	509.3	508.2	507.1
122.5°	550.9	551.1	550.5	550.0	549.4	548.8	548.4	548.0	547.6	547.2	546.9
125°	607.0	607.4	607.2	607.0	606.8	606.5	605.8	604.5	603.2	602.0	600.7
127.5°	662.2	662.4	662.1	661.9	661.7	661.4	660.9	660.2	659.5	658.7	658.0
130°	698.9	699.1	698.7	698.2	697.9	697.4	696.6	695.6	694.6	693.4	692.4
132.5°	734.1	734.2	734.3	734.4	734.5	734.6	733.8	732.0	730.3	728.5	726.8
135°	787.9	787.9	787.7	787.5	787.3	787.0	786.4	785.0	783.7	782.5	781.2
137.5°	840.3	840.1	839.6	839.1	838.7	838.2	837.4	836.1	834.9	833.7	832.5
140°	873.4	872.9	872.2	871.7	871.0	870.3	869.5	868.5	867.4	866.3	865.3
142.5°	906.0	905.8	904.9	904.2	903.3	902.6	901.7	900.8	899.9	899.0	898.1
145°	953.1	953.1	952.5	951.9	951.2	950.6	949.8	949.0	948.1	947.3	946.4
147.5°	996.1	995.5	995.0	994.5	994.0	993.5	993.0	992.5	992.1	991.6	991.2
150°	1023.8	1023.8	1022.9	1022.1	1021.2	1020.4	1020.1	1020.3	1020.5	1020.8	1021.0
152.5°	1048.8	1048.3	1047.9	1047.5	1047.3	1046.9	1046.6	1046.3	1045.9	1045.7	1045.4
155°	1084.9	1084.0	1083.7	1083.5	1083.4	1083.1	1083.0	1083.0	1083.0	1083.0	1083.0
157.5°	1116.3	1115.5	1115.3	1115.0	1114.8	1114.7	1114.7	1115.2	1115.7	1116.2	1116.6
160°	1135.5	1134.6	1134.3	1134.2	1134.0	1133.8	1134.0	1134.6	1135.2	1135.9	1136.5
162.5°	1153.2	1152.2	1152.2	1152.1	1152.1	1152.0	1152.2	1152.6	1153.1	1153.6	1154.0
165°	1177.4	1176.6	1176.4	1176.2	1176.0	1175.7	1175.8	1176.3	1176.7	1177.1	1177.6
167.5°	1194.9	1193.6	1193.6	1193.6	1193.6	1193.6	1194.0	1194.9	1195.7	1196.6	1197.4
170°	1205.6	1204.3	1204.3	1204.3	1204.3	1204.3	1204.8	1205.6	1206.5	1207.3	1208.2
172.5°	1213.2	1211.9	1211.9	1211.9	1211.9	1211.9	1212.4	1213.2	1214.1	1214.9	1215.8
175°	1221.8	1220.5	1220.5	1220.5	1220.5	1220.5	1221.0	1221.8	1222.7	1223.5	1224.4
177.5°	1226.0	1224.9	1225.1	1225.3	1225.4	1225.6	1226.1	1226.7	1227.4	1228.0	1228.8
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.3	15.1	12.9	13.8	14.0	13.9	14.1	13.9	13.8	13.9	14.1
90°	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3	17.4
92.5°	24.3	25.4	26.7	27.9	29.4	31.2	33.0	34.9	36.7	38.1	39.5
95°	62.5	63.0	63.3	63.8	65.0	67.2	69.3	71.4	73.5	75.0	76.5
97.5°	103.3	103.5	103.7	103.9	105.4	108.3	111.2	114.1	117.1	118.5	119.9
100°	133.7	133.7	133.7	133.7	135.1	137.8	140.6	143.4	146.1	148.1	150.0
102.5°	167.4	168.2	169.1	169.9	171.1	172.5	173.9	175.3	176.7	178.8	180.9
105°	218.8	219.9	220.9	222.0	223.2	224.4	225.7	227.0	228.3	229.5	230.8
107.5°	275.3	276.4	277.5	278.5	279.6	280.5	281.5	282.5	283.4	284.1	284.7
110°	314.3	315.4	316.4	317.5	318.4	319.0	319.6	320.3	320.9	321.5	322.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	353.5	354.1	354.7	355.2	355.9	356.7	357.5	358.3	359.1	359.4	359.7
115°	412.5	413.3	414.2	415.0	415.7	416.0	416.5	416.9	417.4	417.2	416.9
117.5°	470.8	471.2	471.6	472.0	472.4	472.8	473.2	473.5	473.9	474.1	474.2
120°	508.2	509.3	510.3	511.3	512.0	512.2	512.5	512.6	512.8	512.8	512.8
122.5°	547.2	547.6	548.0	548.4	548.8	549.4	550.0	550.5	551.1	550.9	550.7
125°	602.0	603.2	604.5	605.8	606.5	606.8	607.0	607.2	607.4	607.0	606.5
127.5°	658.7	659.5	660.2	660.9	661.4	661.7	661.9	662.1	662.4	662.2	661.9
130°	693.4	694.6	695.6	696.6	697.4	697.9	698.2	698.7	699.1	698.9	698.7
132.5°	728.5	730.3	732.0	733.8	734.6	734.5	734.4	734.3	734.2	734.1	733.8
135°	782.5	783.7	785.0	786.4	787.0	787.3	787.5	787.7	787.9	787.9	787.9
137.5°	833.7	834.9	836.1	837.4	838.2	838.7	839.1	839.6	840.1	840.3	840.6
140°	866.3	867.4	868.5	869.5	870.3	871.0	871.7	872.2	872.9	873.4	873.7
142.5°	899.0	899.9	900.8	901.7	902.6	903.3	904.2	904.9	905.8	906.0	906.3
145°	947.3	948.1	949.0	949.8	950.6	951.2	951.9	952.5	953.1	953.1	953.1
147.5°	991.6	992.1	992.5	993.0	993.5	994.0	994.5	995.0	995.5	996.1	996.6
150°	1020.8	1020.5	1020.3	1020.1	1020.4	1021.2	1022.1	1022.9	1023.8	1023.8	1023.8
152.5°	1045.7	1045.9	1046.3	1046.6	1046.9	1047.3	1047.5	1047.9	1048.3	1048.8	1049.2
155°	1083.0	1083.0	1083.0	1083.0	1083.1	1083.4	1083.5	1083.7	1084.0	1084.9	1085.7
157.5°	1116.2	1115.7	1115.2	1114.7	1114.7	1114.8	1115.0	1115.3	1115.5	1116.3	1117.2
160°	1135.9	1135.2	1134.6	1134.0	1133.8	1134.0	1134.2	1134.3	1134.6	1135.5	1136.3
162.5°	1153.6	1153.1	1152.6	1152.2	1152.0	1152.1	1152.1	1152.2	1152.2	1153.2	1154.2
165°	1177.1	1176.7	1176.3	1175.8	1175.7	1176.0	1176.2	1176.4	1176.6	1177.4	1178.3
167.5°	1196.6	1195.7	1194.9	1194.0	1193.6	1193.6	1193.6	1193.6	1193.6	1194.9	1196.2
170°	1207.3	1206.5	1205.6	1204.8	1204.3	1204.3	1204.3	1204.3	1204.3	1205.6	1206.8
172.5°	1214.9	1214.1	1213.2	1212.4	1211.9	1211.9	1211.9	1211.9	1211.9	1213.2	1214.5
175°	1223.5	1222.7	1221.8	1221.0	1220.5	1220.5	1220.5	1220.5	1220.5	1221.8	1223.0
177.5°	1228.0	1227.4	1226.7	1226.1	1225.6	1225.4	1225.3	1225.1	1224.9	1226.0	1227.0
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	14.9	15.6	14.8	14.4	14.5	15.2	15.7
90°	18.5	19.5	20.4	21.0	21.7	22.2	22.9
92.5°	40.9	42.3	43.2	43.6	44.1	44.6	45.1
95°	77.9	79.5	80.4	80.9	81.2	81.7	82.1
97.5°	121.3	122.7	123.5	123.8	124.0	124.3	124.5
100°	151.8	153.7	155.0	155.3	155.8	156.2	156.7
102.5°	182.9	185.0	186.3	186.9	187.6	188.1	188.7
105°	232.1	233.4	234.3	235.0	235.5	236.2	236.9
107.5°	285.4	286.0	286.3	286.3	286.3	286.2	286.2
110°	322.8	323.5	323.7	323.5	323.2	323.0	322.8



TEST NUMBER: P333709-830

CATALOG NUMBER: S125RDIW-S1090D1050U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	360.0	360.2	360.2	359.9	359.5	359.1	358.7
115°	416.7	416.5	416.3	416.0	415.8	415.7	415.5
117.5°	474.4	474.6	474.2	473.3	472.5	471.6	470.8
120°	512.8	512.8	512.5	511.6	510.8	509.9	509.1
122.5°	550.5	550.4	550.0	549.3	548.6	547.9	547.2
125°	606.1	605.7	605.4	605.2	604.9	604.7	604.5
127.5°	661.8	661.6	661.3	660.8	660.4	660.0	659.6
130°	698.4	698.2	698.0	697.5	697.1	696.6	696.3
132.5°	733.6	733.4	733.0	732.4	731.8	731.2	730.6
135°	787.9	787.9	787.5	786.6	785.8	784.9	784.1
137.5°	840.8	841.0	840.7	839.6	838.6	837.4	836.4
140°	874.2	874.6	874.3	873.3	872.1	871.1	870.1
142.5°	906.5	906.8	906.3	905.3	904.3	903.2	902.1
145°	953.1	953.1	952.8	952.2	951.5	950.9	950.3
147.5°	997.0	997.6	997.1	995.7	994.2	992.8	991.4
150°	1023.8	1023.8	1023.6	1023.1	1022.8	1022.3	1021.9
152.5°	1049.8	1050.3	1050.2	1049.4	1048.7	1047.8	1047.1
155°	1086.6	1087.4	1087.2	1086.2	1085.1	1084.1	1083.0
157.5°	1118.0	1118.9	1118.6	1117.2	1115.8	1114.4	1113.0
160°	1137.2	1138.0	1137.8	1136.8	1135.8	1134.7	1133.6
162.5°	1155.2	1156.2	1156.1	1154.9	1153.7	1152.4	1151.2
165°	1179.1	1180.0	1179.8	1178.6	1177.2	1176.0	1174.7
167.5°	1197.4	1198.7	1198.7	1197.4	1196.1	1194.8	1193.4
170°	1208.2	1209.4	1209.3	1207.8	1206.4	1204.9	1203.3
172.5°	1215.8	1217.0	1217.0	1215.7	1214.4	1213.1	1211.7
175°	1224.4	1225.7	1225.5	1224.1	1222.6	1221.1	1219.6
177.5°	1228.0	1229.0	1228.9	1227.8	1226.5	1225.4	1224.2
180°	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2	1227.2

(END OF REPORT)