

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333706-830

Luminaire Tested: **S125RDIW-S1090D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333706-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D770U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6875.0 lumens  
Efficiency: N/A  
Efficacy: 128.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333706-830

CATALOG NUMBER: S125RDIW-S1090D770U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333706-830

CATALOG NUMBER: S125RDIW-S1090D770U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	72	85	78	73	68	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	42	39	36
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34	31
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30	27
6	65	53	44	39	60	49	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	32	40	34	29	35	30	26	30	26	24	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333706-830

CATALOG NUMBER: S125RDIW-S1090D770U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.4	2.3
10°-20°	442.7	6.4
20°-30°	642.0	9.3
30°-40°	731.6	10.6
40°-50°	713.2	10.4
50°-60°	600.3	8.7
60°-70°	420.8	6.1
70°-80°	216.3	3.1
80°-90°	56.6	0.8
90°-100°	34.2	0.5
100°-110°	211.0	3.1
110°-120°	382.7	5.6
120°-130°	491.1	7.1
130°-140°	528.2	7.7
140°-150°	495.8	7.2
150°-160°	401.1	5.8
160°-170°	259.4	3.8
170°-180°	89.5	1.3
0°-30°	1243.1	18.1
0°-40°	1974.7	28.7
0°-60°	3288.2	47.8
0°-90°	3981.9	57.9
90°-120°	627.9	9.1
90°-150°	2143.1	31.2
90°-180°	2893.0	42.1
0°-180°	6875.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	6	11	15	17	5
95°	40	36	11	14	15	51
105°	205	208	208	208	208	218
115°	386	389	390	387	383	382
125°	548	553	553	550	548	489
135°	684	688	686	685	681	527
145°	793	794	794	794	791	496
155°	873	869	870	872	867	402
165°	921	917	918	921	916	260
175°	942	938	939	944	938	90
180°	942	942	942	942	942	



TEST NUMBER: P333706-830

CATALOG NUMBER: S125RDIW-S1090D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.6	22.2	20.9	19.5	18.2	17.5	17.5	17.5	17.5	17.5	17.6
90°	0.7	2.0	3.2	4.4	5.7	6.8	7.9	9.0	10.1	11.2	12.0
92.5°	10.7	9.9	9.0	8.1	7.3	7.4	8.3	9.2	10.2	11.2	12.0
95°	39.8	39.3	38.8	38.5	38.0	34.8	28.8	23.0	17.1	11.2	12.0
97.5°	83.1	84.0	84.8	85.6	86.4	81.1	69.4	57.7	46.0	34.4	30.0
100°	116.6	117.1	117.5	118.0	118.5	119.0	119.7	120.3	120.9	121.5	98.4
102.5°	150.7	151.3	151.9	152.5	153.1	153.5	153.9	154.3	154.7	155.0	150.7
105°	205.3	205.9	206.6	207.2	207.8	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	262.0	262.0	262.0	262.0	262.0	262.2	262.5	262.8	263.2	263.4	263.4
110°	298.9	298.9	298.9	298.9	298.9	299.1	299.4	299.7	300.0	300.3	299.8



TEST NUMBER: P333706-830

CATALOG NUMBER: S125RDIW-S1090D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.6	333.9	334.3	334.7	335.1	335.4	335.5	335.7	335.9	336.1	335.5
115°	385.5	386.3	387.1	387.9	388.6	389.1	389.3	389.4	389.6	389.7	389.1
117.5°	439.3	439.2	439.2	439.2	439.1	439.4	440.1	440.6	441.2	441.8	441.0
120°	472.8	472.7	472.5	472.3	472.2	472.3	472.8	473.3	473.7	474.2	473.9
122.5°	502.4	503.0	503.6	504.2	504.8	505.2	505.4	505.6	505.9	506.1	505.8
125°	548.3	549.3	550.4	551.5	552.6	553.1	553.1	553.1	553.1	553.1	552.5
127.5°	591.9	592.8	593.5	594.3	595.0	595.4	595.3	595.2	595.1	595.0	594.7
130°	618.8	619.5	620.3	621.1	621.9	622.4	622.5	622.6	622.8	622.9	622.5
132.5°	645.5	646.5	647.4	648.3	649.2	649.5	649.1	648.8	648.5	648.1	648.0
135°	683.7	684.7	685.6	686.5	687.5	687.8	687.5	687.1	686.8	686.5	686.2
137.5°	718.8	719.6	720.4	721.2	722.0	722.3	722.0	721.7	721.4	721.1	721.2
140°	741.7	742.0	742.3	742.6	742.9	743.0	742.8	742.7	742.5	742.3	742.7
142.5°	762.3	762.5	762.7	762.9	763.1	763.3	763.6	763.7	763.9	764.2	764.2
145°	792.7	793.0	793.3	793.6	793.9	794.1	794.1	794.1	794.1	794.1	794.2
147.5°	819.3	819.2	819.1	819.1	819.0	819.1	819.3	819.4	819.5	819.7	819.9
150°	835.9	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	836.3
152.5°	852.2	851.5	850.8	850.2	849.4	849.2	849.6	849.9	850.2	850.5	850.8
155°	873.0	872.0	871.1	870.2	869.3	868.9	869.3	869.6	869.9	870.2	870.6
157.5°	889.0	888.5	888.0	887.4	886.8	886.6	886.6	886.6	886.6	886.6	887.2
160°	900.2	899.3	898.3	897.4	896.5	896.1	896.3	896.5	896.5	896.7	897.4
162.5°	909.2	908.2	907.3	906.3	905.4	905.0	905.2	905.4	905.5	905.7	906.5
165°	921.1	920.2	919.4	918.4	917.5	917.1	917.2	917.4	917.6	917.7	918.6
167.5°	930.1	929.2	928.2	927.3	926.2	925.9	926.0	926.1	926.3	926.5	927.6
170°	935.2	934.1	932.9	931.9	930.8	930.3	930.5	930.7	930.8	930.9	932.2
172.5°	938.5	937.5	936.3	935.2	934.2	933.8	934.1	934.3	934.6	934.9	935.9
175°	942.2	941.2	940.3	939.3	938.4	938.0	938.2	938.3	938.5	938.7	939.9
177.5°	943.8	943.0	942.4	941.6	940.8	940.5	940.7	940.8	940.8	941.0	941.9
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333706-830

CATALOG NUMBER: S125RDIW-S1090D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	17.8	18.0	18.1	18.1	18.0	17.9	17.7	17.6
90°	12.7	13.5	14.2	14.9	15.4	15.8	16.3	16.8
92.5°	12.7	13.5	14.2	14.8	15.0	15.2	15.5	15.6
95°	12.7	13.5	14.2	14.7	14.7	14.7	14.7	14.7
97.5°	25.6	21.2	16.9	14.7	14.7	14.7	14.7	14.7
100°	75.3	52.1	29.0	17.2	16.5	15.9	15.3	14.7
102.5°	146.3	141.9	137.5	130.1	119.5	109.0	98.4	87.8
105°	208.1	208.1	208.1	208.0	207.9	207.7	207.5	207.5
107.5°	263.5	263.5	263.5	263.3	262.9	262.4	261.9	261.5
110°	299.4	298.9	298.4	298.3	298.4	298.6	298.8	298.9





TEST NUMBER: P333706-830

CATALOG NUMBER: S125RDIW-S1090D770U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.9	334.3	333.7	333.3	333.1	332.9	332.6	332.4
115°	388.4	387.9	387.2	386.4	385.5	384.6	383.6	382.7
117.5°	440.2	439.4	438.6	438.0	437.5	437.2	436.8	436.4
120°	473.6	473.3	473.0	472.4	471.6	470.9	470.1	469.3
122.5°	505.4	505.1	504.8	504.2	503.3	502.4	501.5	500.6
125°	551.9	551.3	550.6	550.1	549.6	549.1	548.7	548.3
127.5°	594.4	594.0	593.7	593.0	591.7	590.6	589.5	588.3
130°	622.1	621.6	621.1	620.5	619.7	619.0	618.1	617.4
132.5°	647.9	647.8	647.7	647.3	646.5	645.7	645.0	644.2
135°	685.9	685.6	685.3	684.7	683.7	682.8	681.8	680.9
137.5°	721.3	721.3	721.4	721.0	720.2	719.4	718.6	717.8
140°	743.0	743.3	743.7	743.3	742.3	741.5	740.6	739.6
142.5°	764.3	764.4	764.4	764.0	763.1	762.1	761.2	760.3
145°	794.4	794.6	794.7	794.3	793.3	792.4	791.5	790.6
147.5°	820.1	820.3	820.5	820.0	819.0	817.8	816.7	815.6
150°	836.6	836.9	837.3	836.8	835.5	834.2	833.0	831.8
152.5°	851.1	851.4	851.8	851.3	850.2	849.1	848.0	846.9
155°	871.1	871.6	872.0	871.7	870.4	869.2	868.0	866.7
157.5°	887.7	888.2	888.6	888.3	887.0	885.8	884.6	883.4
160°	898.0	898.6	899.2	898.9	897.7	896.5	895.2	893.9
162.5°	907.4	908.2	909.2	908.9	907.6	906.2	904.8	903.4
165°	919.5	920.5	921.4	921.2	920.0	918.8	917.6	916.2
167.5°	928.7	929.8	930.9	930.9	929.4	928.0	926.6	925.2
170°	933.4	934.7	935.9	935.9	934.4	933.0	931.6	930.3
172.5°	937.1	938.2	939.3	939.1	937.8	936.4	935.0	933.6
175°	941.1	942.4	943.6	943.5	942.2	940.8	939.3	937.9
177.5°	942.7	943.6	944.5	944.4	943.4	942.4	941.4	940.5
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2

(END OF REPORT)