

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333652-830

Luminaire Tested: **S125RDIW-S375D1340U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333652-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1340U830-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6433.3 lumens  
Efficiency: N/A  
Efficacy: 138.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	27	26	25	18
2	83	77	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19	13
4	70	60	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	29	23	19	22	18	15	17	14	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	0.8
10°-20°	149.1	2.3
20°-30°	236.4	3.7
30°-40°	285.1	4.4
40°-50°	254.6	4.0
50°-60°	195.2	3.0
60°-70°	126.9	2.0
70°-80°	61.7	1.0
80°-90°	18.1	0.3
90°-100°	59.8	0.9
100°-110°	368.7	5.7
110°-120°	668.7	10.4
120°-130°	858.2	13.3
130°-140°	923.1	14.3
140°-150°	866.4	13.5
150°-160°	700.9	10.9
160°-170°	453.3	7.0
170°-180°	156.3	2.4
0°-30°	436.4	6.8
0°-40°	721.4	11.2
0°-60°	1171.3	18.2
0°-90°	1377.9	21.4
90°-120°	1097.2	17.1
90°-150°	3744.9	58.2
90°-180°	5055.0	78.6
0°-180°	6433.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	29	1	29	1	29	13
95°	26	70	26	70	26	21
105°	362	359	362	359	362	328
115°	669	674	669	674	669	664
125°	958	958	958	958	958	852
135°	1190	1195	1190	1195	1190	918
145°	1382	1385	1382	1385	1382	863
155°	1514	1525	1514	1525	1514	698
165°	1601	1610	1601	1610	1601	452
175°	1639	1646	1639	1646	1639	156
180°	1646	1646	1646	1646	1646	



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	9.7	9.3	9.0	8.9	8.9	9.0	8.6	8.1	7.8	7.5	7.4
90°	29.3	28.5	27.6	26.9	26.0	25.0	23.6	22.2	20.9	19.5	17.6
92.5°	27.3	27.0	26.6	26.2	25.8	25.0	23.6	22.2	20.9	19.5	17.8
95°	25.6	25.6	25.6	25.6	25.6	25.0	23.6	22.2	20.9	19.5	29.8
97.5°	25.6	25.6	25.6	25.6	25.6	29.4	37.1	44.8	52.4	60.0	80.4
100°	25.6	26.7	27.8	28.8	30.0	50.7	91.1	131.5	171.9	212.4	211.2
102.5°	153.5	171.9	190.4	208.9	227.2	240.3	248.0	255.6	263.3	270.9	270.2
105°	362.4	362.7	363.0	363.3	363.5	363.6	363.6	363.6	363.6	363.6	363.6
107.5°	456.9	457.7	458.5	459.3	460.1	460.5	460.5	460.4	460.3	460.3	459.8
110°	522.4	522.1	521.8	521.5	521.2	521.5	522.4	523.1	524.0	524.7	524.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	580.9	581.3	581.6	582.0	582.4	583.2	584.2	585.1	586.2	587.2	586.9
115°	668.7	670.3	672.0	673.6	675.2	676.7	677.7	678.8	679.9	681.0	680.7
117.5°	762.5	763.2	763.9	764.6	765.3	766.4	767.8	769.2	770.6	772.0	771.0
120°	820.1	821.4	822.7	824.2	825.5	826.4	827.0	827.6	828.1	828.6	827.8
122.5°	874.8	876.3	877.9	879.5	881.0	882.1	882.6	883.2	883.7	884.3	883.9
125°	958.0	958.8	959.6	960.5	961.2	962.1	963.3	964.3	965.4	966.5	966.5
127.5°	1028.0	1030.0	1032.1	1034.1	1036.0	1037.4	1037.9	1038.6	1039.2	1039.7	1039.9
130°	1078.8	1080.2	1081.5	1082.9	1084.2	1085.3	1086.1	1086.9	1087.8	1088.5	1088.3
132.5°	1125.7	1127.0	1128.4	1129.7	1131.1	1131.8	1132.0	1132.2	1132.4	1132.5	1133.1
135°	1189.9	1191.5	1193.1	1194.8	1196.4	1197.4	1198.0	1198.5	1199.1	1199.6	1200.1
137.5°	1254.2	1255.7	1257.1	1258.5	1259.9	1260.6	1260.5	1260.4	1260.3	1260.2	1260.7
140°	1292.3	1294.0	1295.6	1297.2	1298.8	1299.4	1298.8	1298.4	1297.8	1297.2	1297.5
142.5°	1328.5	1330.1	1331.7	1333.3	1335.0	1335.8	1335.7	1335.5	1335.4	1335.3	1334.9
145°	1381.5	1383.1	1384.7	1386.3	1388.0	1388.6	1388.4	1388.1	1387.8	1387.5	1387.5
147.5°	1425.1	1427.1	1429.0	1431.0	1432.9	1433.8	1433.4	1433.1	1432.8	1432.5	1432.1
150°	1453.4	1455.6	1457.7	1459.9	1462.1	1462.9	1462.4	1461.9	1461.3	1460.8	1460.2
152.5°	1479.8	1481.8	1483.8	1485.6	1487.6	1488.3	1487.8	1487.2	1486.7	1486.1	1485.6
155°	1514.5	1516.6	1518.8	1521.0	1523.1	1523.8	1523.0	1522.2	1521.4	1520.6	1520.0
157.5°	1543.5	1545.7	1547.8	1550.0	1552.2	1552.8	1552.0	1551.1	1550.2	1549.4	1549.4
160°	1562.1	1564.2	1566.4	1568.6	1570.7	1571.3	1570.2	1569.1	1568.0	1567.0	1566.7
162.5°	1578.7	1581.0	1583.4	1585.8	1588.2	1588.7	1587.1	1585.5	1584.0	1582.5	1582.2
165°	1601.1	1603.3	1605.4	1607.6	1609.8	1610.1	1608.4	1606.8	1605.1	1603.5	1603.3
167.5°	1616.7	1619.2	1621.6	1624.0	1626.5	1626.7	1624.8	1622.9	1620.9	1618.9	1618.6
170°	1625.5	1628.0	1630.4	1632.9	1635.3	1635.4	1633.2	1631.1	1628.9	1626.7	1626.5
172.5°	1631.4	1633.8	1636.3	1638.7	1641.2	1641.3	1639.5	1637.5	1635.5	1633.5	1633.0
175°	1638.9	1641.3	1643.8	1646.2	1648.7	1648.8	1646.6	1644.5	1642.3	1640.1	1639.9
177.5°	1643.3	1645.0	1646.8	1648.5	1650.3	1650.4	1648.9	1647.4	1645.9	1644.3	1644.1
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	7.2	6.8	6.6	6.1	5.6	6.0	6.0	5.8	5.9	6.0	6.0
90°	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	16.1	14.5	12.8	12.7	14.2	15.7	17.2	18.8	17.2	15.7	14.2
95°	40.2	50.4	60.7	66.3	67.1	68.0	68.7	69.6	68.7	68.0	67.1
97.5°	100.9	121.2	141.6	151.1	149.6	148.2	146.7	145.2	146.7	148.2	149.6
100°	210.2	209.1	208.0	207.1	206.2	205.4	204.6	203.8	204.6	205.4	206.2
102.5°	269.7	269.0	268.3	267.5	266.5	265.4	264.4	263.3	264.4	265.4	266.5
105°	363.6	363.6	363.6	363.2	362.0	361.0	359.9	358.8	359.9	361.0	362.0
107.5°	459.2	458.7	458.2	457.9	457.9	457.9	457.9	457.9	457.9	457.9	457.9
110°	523.7	523.1	522.5	522.4	522.4	522.4	522.4	522.4	522.4	522.4	522.4





TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	586.5	586.3	586.0	585.4	584.8	584.2	583.5	582.9	583.5	584.2	584.8
115°	680.4	680.1	679.9	679.1	677.7	676.4	675.0	673.6	675.0	676.4	677.7
117.5°	770.0	768.9	767.9	767.4	767.4	767.5	767.5	767.6	767.5	767.5	767.4
120°	827.0	826.1	825.4	825.1	825.4	825.7	826.0	826.1	826.0	825.7	825.4
122.5°	883.5	883.2	882.8	882.0	881.0	880.0	878.9	877.9	878.9	880.0	881.0
125°	966.5	966.5	966.5	965.5	963.7	961.8	959.9	958.0	959.9	961.8	963.7
127.5°	1040.1	1040.2	1040.4	1039.8	1038.4	1037.1	1035.8	1034.3	1035.8	1037.1	1038.4
130°	1088.0	1087.8	1087.5	1086.7	1085.3	1083.9	1082.6	1081.2	1082.6	1083.9	1085.3
132.5°	1133.7	1134.3	1134.9	1134.3	1132.8	1131.2	1129.6	1128.1	1129.6	1131.2	1132.8
135°	1200.7	1201.3	1201.7	1201.3	1199.6	1198.0	1196.4	1194.8	1196.4	1198.0	1199.6
137.5°	1261.1	1261.6	1262.1	1261.6	1260.2	1258.8	1257.4	1256.0	1257.4	1258.8	1260.2
140°	1297.8	1298.1	1298.4	1298.2	1297.6	1297.1	1296.6	1296.0	1296.6	1297.1	1297.6
142.5°	1334.5	1334.2	1333.8	1333.4	1333.1	1332.8	1332.5	1332.1	1332.5	1332.8	1333.1
145°	1387.5	1387.5	1387.5	1387.2	1386.8	1386.2	1385.6	1385.1	1385.6	1386.2	1386.8
147.5°	1431.8	1431.4	1431.2	1431.1	1431.2	1431.3	1431.3	1431.4	1431.3	1431.3	1431.2
150°	1459.7	1459.2	1458.6	1458.6	1459.2	1459.7	1460.2	1460.8	1460.2	1459.7	1459.2
152.5°	1485.1	1484.5	1483.9	1484.3	1485.5	1486.7	1487.9	1489.0	1487.9	1486.7	1485.5
155°	1519.5	1518.9	1518.4	1518.9	1520.6	1522.2	1523.8	1525.4	1523.8	1522.2	1520.6
157.5°	1549.3	1549.2	1549.2	1549.6	1550.6	1551.5	1552.6	1553.5	1552.6	1551.5	1550.6
160°	1566.4	1566.1	1565.8	1566.5	1568.1	1569.8	1571.4	1573.0	1571.4	1569.8	1568.1
162.5°	1582.1	1581.8	1581.5	1582.2	1583.8	1585.4	1587.1	1588.7	1587.1	1585.4	1583.8
165°	1603.0	1602.7	1602.4	1603.2	1604.8	1606.4	1608.0	1609.7	1608.0	1606.4	1604.8
167.5°	1618.3	1618.1	1617.9	1618.5	1620.2	1621.9	1623.6	1625.2	1623.6	1621.9	1620.2
170°	1626.2	1625.9	1625.6	1626.5	1628.3	1630.2	1632.2	1634.1	1632.2	1630.2	1628.3
172.5°	1632.6	1632.1	1631.6	1632.3	1634.2	1636.2	1638.0	1639.9	1638.0	1636.2	1634.2
175°	1639.6	1639.4	1639.1	1639.7	1641.3	1643.0	1644.6	1646.2	1644.6	1643.0	1641.3
177.5°	1643.9	1643.7	1643.4	1644.0	1645.3	1646.6	1647.8	1649.2	1647.8	1646.6	1645.3
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	6.3	6.8	7.0	7.6	7.5	8.1	8.4	8.5	8.8	9.0	9.0
90°	9.9	12.0	13.9	15.7	17.6	19.5	20.9	22.2	23.6	25.0	26.0
92.5°	12.7	12.8	14.5	16.1	17.8	19.5	20.9	22.2	23.6	25.0	25.8
95°	66.3	60.7	50.4	40.2	29.8	19.5	20.9	22.2	23.6	25.0	25.6
97.5°	151.1	141.6	121.2	100.9	80.4	60.0	52.4	44.8	37.1	29.4	25.6
100°	207.1	208.0	209.1	210.2	211.2	212.4	171.9	131.5	91.1	50.7	30.0
102.5°	267.5	268.3	269.0	269.7	270.2	270.9	263.3	255.6	248.0	240.3	227.2
105°	363.2	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.6	363.5
107.5°	457.9	458.2	458.7	459.2	459.8	460.3	460.3	460.4	460.5	460.5	460.1
110°	522.4	522.5	523.1	523.7	524.2	524.7	524.0	523.1	522.4	521.5	521.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	585.4	586.0	586.3	586.5	586.9	587.2	586.2	585.1	584.2	583.2	582.4
115°	679.1	679.9	680.1	680.4	680.7	681.0	679.9	678.8	677.7	676.7	675.2
117.5°	767.4	767.9	768.9	770.0	771.0	772.0	770.6	769.2	767.8	766.4	765.3
120°	825.1	825.4	826.1	827.0	827.8	828.6	828.1	827.6	827.0	826.4	825.5
122.5°	882.0	882.8	883.2	883.5	883.9	884.3	883.7	883.2	882.6	882.1	881.0
125°	965.5	966.5	966.5	966.5	966.5	966.5	965.4	964.3	963.3	962.1	961.2
127.5°	1039.8	1040.4	1040.2	1040.1	1039.9	1039.7	1039.2	1038.6	1037.9	1037.4	1036.0
130°	1086.7	1087.5	1087.8	1088.0	1088.3	1088.5	1087.8	1086.9	1086.1	1085.3	1084.2
132.5°	1134.3	1134.9	1134.3	1133.7	1133.1	1132.5	1132.4	1132.2	1132.0	1131.8	1131.1
135°	1201.3	1201.7	1201.3	1200.7	1200.1	1199.6	1199.1	1198.5	1198.0	1197.4	1196.4
137.5°	1261.6	1262.1	1261.6	1261.1	1260.7	1260.2	1260.3	1260.4	1260.5	1260.6	1259.9
140°	1298.2	1298.4	1298.1	1297.8	1297.5	1297.2	1297.8	1298.4	1298.8	1299.4	1298.8
142.5°	1333.4	1333.8	1334.2	1334.5	1334.9	1335.3	1335.4	1335.5	1335.7	1335.8	1335.0
145°	1387.2	1387.5	1387.5	1387.5	1387.5	1387.5	1387.8	1388.1	1388.4	1388.6	1388.0
147.5°	1431.1	1431.2	1431.4	1431.8	1432.1	1432.5	1432.8	1433.1	1433.4	1433.8	1432.9
150°	1458.6	1458.6	1459.2	1459.7	1460.2	1460.8	1461.3	1461.9	1462.4	1462.9	1462.1
152.5°	1484.3	1483.9	1484.5	1485.1	1485.6	1486.1	1486.7	1487.2	1487.8	1488.3	1487.6
155°	1518.9	1518.4	1518.9	1519.5	1520.0	1520.6	1521.4	1522.2	1523.0	1523.8	1523.1
157.5°	1549.6	1549.2	1549.2	1549.3	1549.4	1549.4	1550.2	1551.1	1552.0	1552.8	1552.2
160°	1566.5	1565.8	1566.1	1566.4	1566.7	1567.0	1568.0	1569.1	1570.2	1571.3	1570.7
162.5°	1582.2	1581.5	1581.8	1582.1	1582.2	1582.5	1584.0	1585.5	1587.1	1588.7	1588.2
165°	1603.2	1602.4	1602.7	1603.0	1603.3	1603.5	1605.1	1606.8	1608.4	1610.1	1609.8
167.5°	1618.5	1617.9	1618.1	1618.3	1618.6	1618.9	1620.9	1622.9	1624.8	1626.7	1626.5
170°	1626.5	1625.6	1625.9	1626.2	1626.5	1626.7	1628.9	1631.1	1633.2	1635.4	1635.3
172.5°	1632.3	1631.6	1632.1	1632.6	1633.0	1633.5	1635.5	1637.5	1639.5	1641.3	1641.2
175°	1639.7	1639.1	1639.4	1639.6	1639.9	1640.1	1642.3	1644.5	1646.6	1648.8	1648.7
177.5°	1644.0	1643.4	1643.7	1643.9	1644.1	1644.3	1645.9	1647.4	1648.9	1650.4	1650.3
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	9.3	9.3	9.5	9.7	9.5	9.3	9.3	9.0	9.0	8.8	8.5
90°	26.9	27.6	28.5	29.3	28.5	27.6	26.9	26.0	25.0	23.6	22.2
92.5°	26.2	26.6	27.0	27.3	27.0	26.6	26.2	25.8	25.0	23.6	22.2
95°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.0	23.6	22.2
97.5°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	29.4	37.1	44.8
100°	28.8	27.8	26.7	25.6	26.7	27.8	28.8	30.0	50.7	91.1	131.5
102.5°	208.9	190.4	171.9	153.5	171.9	190.4	208.9	227.2	240.3	248.0	255.6
105°	363.3	363.0	362.7	362.4	362.7	363.0	363.3	363.5	363.6	363.6	363.6
107.5°	459.3	458.5	457.7	456.9	457.7	458.5	459.3	460.1	460.5	460.5	460.4
110°	521.5	521.8	522.1	522.4	522.1	521.8	521.5	521.2	521.5	522.4	523.1



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	582.0	581.6	581.3	580.9	581.3	581.6	582.0	582.4	583.2	584.2	585.1
115°	673.6	672.0	670.3	668.7	670.3	672.0	673.6	675.2	676.7	677.7	678.8
117.5°	764.6	763.9	763.2	762.5	763.2	763.9	764.6	765.3	766.4	767.8	769.2
120°	824.2	822.7	821.4	820.1	821.4	822.7	824.2	825.5	826.4	827.0	827.6
122.5°	879.5	877.9	876.3	874.8	876.3	877.9	879.5	881.0	882.1	882.6	883.2
125°	960.5	959.6	958.8	958.0	958.8	959.6	960.5	961.2	962.1	963.3	964.3
127.5°	1034.1	1032.1	1030.0	1028.0	1030.0	1032.1	1034.1	1036.0	1037.4	1037.9	1038.6
130°	1082.9	1081.5	1080.2	1078.8	1080.2	1081.5	1082.9	1084.2	1085.3	1086.1	1086.9
132.5°	1129.7	1128.4	1127.0	1125.7	1127.0	1128.4	1129.7	1131.1	1131.8	1132.0	1132.2
135°	1194.8	1193.1	1191.5	1189.9	1191.5	1193.1	1194.8	1196.4	1197.4	1198.0	1198.5
137.5°	1258.5	1257.1	1255.7	1254.2	1255.7	1257.1	1258.5	1259.9	1260.6	1260.5	1260.4
140°	1297.2	1295.6	1294.0	1292.3	1294.0	1295.6	1297.2	1298.8	1299.4	1298.8	1298.4
142.5°	1333.3	1331.7	1330.1	1328.5	1330.1	1331.7	1333.3	1335.0	1335.8	1335.7	1335.5
145°	1386.3	1384.7	1383.1	1381.5	1383.1	1384.7	1386.3	1388.0	1388.6	1388.4	1388.1
147.5°	1431.0	1429.0	1427.1	1425.1	1427.1	1429.0	1431.0	1432.9	1433.8	1433.4	1433.1
150°	1459.9	1457.7	1455.6	1453.4	1455.6	1457.7	1459.9	1462.1	1462.9	1462.4	1461.9
152.5°	1485.6	1483.8	1481.8	1479.8	1481.8	1483.8	1485.6	1487.6	1488.3	1487.8	1487.2
155°	1521.0	1518.8	1516.6	1514.5	1516.6	1518.8	1521.0	1523.1	1523.8	1523.0	1522.2
157.5°	1550.0	1547.8	1545.7	1543.5	1545.7	1547.8	1550.0	1552.2	1552.8	1552.0	1551.1
160°	1568.6	1566.4	1564.2	1562.1	1564.2	1566.4	1568.6	1570.7	1571.3	1570.2	1569.1
162.5°	1585.8	1583.4	1581.0	1578.7	1581.0	1583.4	1585.8	1588.2	1588.7	1587.1	1585.5
165°	1607.6	1605.4	1603.3	1601.1	1603.3	1605.4	1607.6	1609.8	1610.1	1608.4	1606.8
167.5°	1624.0	1621.6	1619.2	1616.7	1619.2	1621.6	1624.0	1626.5	1626.7	1624.8	1622.9
170°	1632.9	1630.4	1628.0	1625.5	1628.0	1630.4	1632.9	1635.3	1635.4	1633.2	1631.1
172.5°	1638.7	1636.3	1633.8	1631.4	1633.8	1636.3	1638.7	1641.2	1641.3	1639.5	1637.5
175°	1646.2	1643.8	1641.3	1638.9	1641.3	1643.8	1646.2	1648.7	1648.8	1646.6	1644.5
177.5°	1648.5	1646.8	1645.0	1643.3	1645.0	1646.8	1648.5	1650.3	1650.4	1648.9	1647.4
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	8.4	8.1	7.5	7.6	7.0	6.8	6.3	6.0	6.0	5.9	5.8
90°	20.9	19.5	17.6	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	20.9	19.5	17.8	16.1	14.5	12.8	12.7	14.2	15.7	17.2	18.8
95°	20.9	19.5	29.8	40.2	50.4	60.7	66.3	67.1	68.0	68.7	69.6
97.5°	52.4	60.0	80.4	100.9	121.2	141.6	151.1	149.6	148.2	146.7	145.2
100°	171.9	212.4	211.2	210.2	209.1	208.0	207.1	206.2	205.4	204.6	203.8
102.5°	263.3	270.9	270.2	269.7	269.0	268.3	267.5	266.5	265.4	264.4	263.3
105°	363.6	363.6	363.6	363.6	363.6	363.6	363.2	362.0	361.0	359.9	358.8
107.5°	460.3	460.3	459.8	459.2	458.7	458.2	457.9	457.9	457.9	457.9	457.9
110°	524.0	524.7	524.2	523.7	523.1	522.5	522.4	522.4	522.4	522.4	522.4



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	586.2	587.2	586.9	586.5	586.3	586.0	585.4	584.8	584.2	583.5	582.9
115°	679.9	681.0	680.7	680.4	680.1	679.9	679.1	677.7	676.4	675.0	673.6
117.5°	770.6	772.0	771.0	770.0	768.9	767.9	767.4	767.4	767.5	767.5	767.6
120°	828.1	828.6	827.8	827.0	826.1	825.4	825.1	825.4	825.7	826.0	826.1
122.5°	883.7	884.3	883.9	883.5	883.2	882.8	882.0	881.0	880.0	878.9	877.9
125°	965.4	966.5	966.5	966.5	966.5	966.5	965.5	963.7	961.8	959.9	958.0
127.5°	1039.2	1039.7	1039.9	1040.1	1040.2	1040.4	1039.8	1038.4	1037.1	1035.8	1034.3
130°	1087.8	1088.5	1088.3	1088.0	1087.8	1087.5	1086.7	1085.3	1083.9	1082.6	1081.2
132.5°	1132.4	1132.5	1133.1	1133.7	1134.3	1134.9	1134.3	1132.8	1131.2	1129.6	1128.1
135°	1199.1	1199.6	1200.1	1200.7	1201.3	1201.7	1201.3	1199.6	1198.0	1196.4	1194.8
137.5°	1260.3	1260.2	1260.7	1261.1	1261.6	1262.1	1261.6	1260.2	1258.8	1257.4	1256.0
140°	1297.8	1297.2	1297.5	1297.8	1298.1	1298.4	1298.2	1297.6	1297.1	1296.6	1296.0
142.5°	1335.4	1335.3	1334.9	1334.5	1334.2	1333.8	1333.4	1333.1	1332.8	1332.5	1332.1
145°	1387.8	1387.5	1387.5	1387.5	1387.5	1387.5	1387.2	1386.8	1386.2	1385.6	1385.1
147.5°	1432.8	1432.5	1432.1	1431.8	1431.4	1431.2	1431.1	1431.2	1431.3	1431.3	1431.4
150°	1461.3	1460.8	1460.2	1459.7	1459.2	1458.6	1458.6	1459.2	1459.7	1460.2	1460.8
152.5°	1486.7	1486.1	1485.6	1485.1	1484.5	1483.9	1484.3	1485.5	1486.7	1487.9	1489.0
155°	1521.4	1520.6	1520.0	1519.5	1518.9	1518.4	1518.9	1520.6	1522.2	1523.8	1525.4
157.5°	1550.2	1549.4	1549.4	1549.3	1549.2	1549.2	1549.6	1550.6	1551.5	1552.6	1553.5
160°	1568.0	1567.0	1566.7	1566.4	1566.1	1565.8	1566.5	1568.1	1569.8	1571.4	1573.0
162.5°	1584.0	1582.5	1582.2	1582.1	1581.8	1581.5	1582.2	1583.8	1585.4	1587.1	1588.7
165°	1605.1	1603.5	1603.3	1603.0	1602.7	1602.4	1603.2	1604.8	1606.4	1608.0	1609.7
167.5°	1620.9	1618.9	1618.6	1618.3	1618.1	1617.9	1618.5	1620.2	1621.9	1623.6	1625.2
170°	1628.9	1626.7	1626.5	1626.2	1625.9	1625.6	1626.5	1628.3	1630.2	1632.2	1634.1
172.5°	1635.5	1633.5	1633.0	1632.6	1632.1	1631.6	1632.3	1634.2	1636.2	1638.0	1639.9
175°	1642.3	1640.1	1639.9	1639.6	1639.4	1639.1	1639.7	1641.3	1643.0	1644.6	1646.2
177.5°	1645.9	1644.3	1644.1	1643.9	1643.7	1643.4	1644.0	1645.3	1646.6	1647.8	1649.2
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	6.0	6.0	5.6	6.1	6.6	6.8	7.2	7.4	7.5	7.8	8.1
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.5	20.9	22.2
92.5°	17.2	15.7	14.2	12.7	12.8	14.5	16.1	17.8	19.5	20.9	22.2
95°	68.7	68.0	67.1	66.3	60.7	50.4	40.2	29.8	19.5	20.9	22.2
97.5°	146.7	148.2	149.6	151.1	141.6	121.2	100.9	80.4	60.0	52.4	44.8
100°	204.6	205.4	206.2	207.1	208.0	209.1	210.2	211.2	212.4	171.9	131.5
102.5°	264.4	265.4	266.5	267.5	268.3	269.0	269.7	270.2	270.9	263.3	255.6
105°	359.9	361.0	362.0	363.2	363.6	363.6	363.6	363.6	363.6	363.6	363.6
107.5°	457.9	457.9	457.9	457.9	458.2	458.7	459.2	459.8	460.3	460.3	460.4
110°	522.4	522.4	522.4	522.4	522.5	523.1	523.7	524.2	524.7	524.0	523.1





TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	583.5	584.2	584.8	585.4	586.0	586.3	586.5	586.9	587.2	586.2	585.1
115°	675.0	676.4	677.7	679.1	679.9	680.1	680.4	680.7	681.0	679.9	678.8
117.5°	767.5	767.5	767.4	767.4	767.9	768.9	770.0	771.0	772.0	770.6	769.2
120°	826.0	825.7	825.4	825.1	825.4	826.1	827.0	827.8	828.6	828.1	827.6
122.5°	878.9	880.0	881.0	882.0	882.8	883.2	883.5	883.9	884.3	883.7	883.2
125°	959.9	961.8	963.7	965.5	966.5	966.5	966.5	966.5	966.5	965.4	964.3
127.5°	1035.8	1037.1	1038.4	1039.8	1040.4	1040.2	1040.1	1039.9	1039.7	1039.2	1038.6
130°	1082.6	1083.9	1085.3	1086.7	1087.5	1087.8	1088.0	1088.3	1088.5	1087.8	1086.9
132.5°	1129.6	1131.2	1132.8	1134.3	1134.9	1134.3	1133.7	1133.1	1132.5	1132.4	1132.2
135°	1196.4	1198.0	1199.6	1201.3	1201.7	1201.3	1200.7	1200.1	1199.6	1199.1	1198.5
137.5°	1257.4	1258.8	1260.2	1261.6	1262.1	1261.6	1261.1	1260.7	1260.2	1260.3	1260.4
140°	1296.6	1297.1	1297.6	1298.2	1298.4	1298.1	1297.8	1297.5	1297.2	1297.8	1298.4
142.5°	1332.5	1332.8	1333.1	1333.4	1333.8	1334.2	1334.5	1334.9	1335.3	1335.4	1335.5
145°	1385.6	1386.2	1386.8	1387.2	1387.5	1387.5	1387.5	1387.5	1387.5	1387.8	1388.1
147.5°	1431.3	1431.3	1431.2	1431.1	1431.2	1431.4	1431.8	1432.1	1432.5	1432.8	1433.1
150°	1460.2	1459.7	1459.2	1458.6	1458.6	1459.2	1459.7	1460.2	1460.8	1461.3	1461.9
152.5°	1487.9	1486.7	1485.5	1484.3	1483.9	1484.5	1485.1	1485.6	1486.1	1486.7	1487.2
155°	1523.8	1522.2	1520.6	1518.9	1518.4	1518.9	1519.5	1520.0	1520.6	1521.4	1522.2
157.5°	1552.6	1551.5	1550.6	1549.6	1549.2	1549.2	1549.3	1549.4	1549.4	1550.2	1551.1
160°	1571.4	1569.8	1568.1	1566.5	1565.8	1566.1	1566.4	1566.7	1567.0	1568.0	1569.1
162.5°	1587.1	1585.4	1583.8	1582.2	1581.5	1581.8	1582.1	1582.2	1582.5	1584.0	1585.5
165°	1608.0	1606.4	1604.8	1603.2	1602.4	1602.7	1603.0	1603.3	1603.5	1605.1	1606.8
167.5°	1623.6	1621.9	1620.2	1618.5	1617.9	1618.1	1618.3	1618.6	1618.9	1620.9	1622.9
170°	1632.2	1630.2	1628.3	1626.5	1625.6	1625.9	1626.2	1626.5	1626.7	1628.9	1631.1
172.5°	1638.0	1636.2	1634.2	1632.3	1631.6	1632.1	1632.6	1633.0	1633.5	1635.5	1637.5
175°	1644.6	1643.0	1641.3	1639.7	1639.1	1639.4	1639.6	1639.9	1640.1	1642.3	1644.5
177.5°	1647.8	1646.6	1645.3	1644.0	1643.4	1643.7	1643.9	1644.1	1644.3	1645.9	1647.4
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	8.6	9.0	8.9	8.9	9.0	9.3	9.7
90°	23.6	25.0	26.0	26.9	27.6	28.5	29.3
92.5°	23.6	25.0	25.8	26.2	26.6	27.0	27.3
95°	23.6	25.0	25.6	25.6	25.6	25.6	25.6
97.5°	37.1	29.4	25.6	25.6	25.6	25.6	25.6
100°	91.1	50.7	30.0	28.8	27.8	26.7	25.6
102.5°	248.0	240.3	227.2	208.9	190.4	171.9	153.5
105°	363.6	363.6	363.5	363.3	363.0	362.7	362.4
107.5°	460.5	460.5	460.1	459.3	458.5	457.7	456.9
110°	522.4	521.5	521.2	521.5	521.8	522.1	522.4



TEST NUMBER: P333652-830

CATALOG NUMBER: S125RDIW-S375D1340U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	584.2	583.2	582.4	582.0	581.6	581.3	580.9
115°	677.7	676.7	675.2	673.6	672.0	670.3	668.7
117.5°	767.8	766.4	765.3	764.6	763.9	763.2	762.5
120°	827.0	826.4	825.5	824.2	822.7	821.4	820.1
122.5°	882.6	882.1	881.0	879.5	877.9	876.3	874.8
125°	963.3	962.1	961.2	960.5	959.6	958.8	958.0
127.5°	1037.9	1037.4	1036.0	1034.1	1032.1	1030.0	1028.0
130°	1086.1	1085.3	1084.2	1082.9	1081.5	1080.2	1078.8
132.5°	1132.0	1131.8	1131.1	1129.7	1128.4	1127.0	1125.7
135°	1198.0	1197.4	1196.4	1194.8	1193.1	1191.5	1189.9
137.5°	1260.5	1260.6	1259.9	1258.5	1257.1	1255.7	1254.2
140°	1298.8	1299.4	1298.8	1297.2	1295.6	1294.0	1292.3
142.5°	1335.7	1335.8	1335.0	1333.3	1331.7	1330.1	1328.5
145°	1388.4	1388.6	1388.0	1386.3	1384.7	1383.1	1381.5
147.5°	1433.4	1433.8	1432.9	1431.0	1429.0	1427.1	1425.1
150°	1462.4	1462.9	1462.1	1459.9	1457.7	1455.6	1453.4
152.5°	1487.8	1488.3	1487.6	1485.6	1483.8	1481.8	1479.8
155°	1523.0	1523.8	1523.1	1521.0	1518.8	1516.6	1514.5
157.5°	1552.0	1552.8	1552.2	1550.0	1547.8	1545.7	1543.5
160°	1570.2	1571.3	1570.7	1568.6	1566.4	1564.2	1562.1
162.5°	1587.1	1588.7	1588.2	1585.8	1583.4	1581.0	1578.7
165°	1608.4	1610.1	1609.8	1607.6	1605.4	1603.3	1601.1
167.5°	1624.8	1626.7	1626.5	1624.0	1621.6	1619.2	1616.7
170°	1633.2	1635.4	1635.3	1632.9	1630.4	1628.0	1625.5
172.5°	1639.5	1641.3	1641.2	1638.7	1636.3	1633.8	1631.4
175°	1646.6	1648.8	1648.7	1646.2	1643.8	1641.3	1638.9
177.5°	1648.9	1650.4	1650.3	1648.5	1646.8	1645.0	1643.3
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2

(END OF REPORT)