

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333657-830

Luminaire Tested: **S125RDIW-S375D1560U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333657-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1560U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6475.6 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333657-830
CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	28	21	20	19	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	42	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	29	23	19	22	18	15	16	14	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	0.8
10°-20°	149.1	2.3
20°-30°	236.4	3.7
30°-40°	285.1	4.4
40°-50°	254.6	3.9
50°-60°	195.2	3.0
60°-70°	126.9	2.0
70°-80°	61.7	1.0
80°-90°	18.7	0.3
90°-100°	122.3	1.9
100°-110°	361.3	5.6
110°-120°	611.9	9.4
120°-130°	805.3	12.4
130°-140°	902.4	13.9
140°-150°	884.4	13.7
150°-160°	742.8	11.5
160°-170°	493.8	7.6
170°-180°	172.8	2.7
0°-30°	436.4	6.7
0°-40°	721.4	11.1
0°-60°	1171.3	18.1
0°-90°	1378.5	21.3
90°-120°	1095.5	16.9
90°-150°	3687.7	56.9
90°-180°	5097.0	78.7
0°-180°	6475.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	34	1	34	1	34	20
95°	122	92	122	92	122	124
105°	352	324	352	324	352	373
115°	618	613	618	613	618	612
125°	900	894	900	894	900	803
135°	1167	1163	1167	1163	1167	900
145°	1414	1409	1414	1409	1414	883
155°	1612	1612	1612	1612	1612	742
165°	1748	1753	1748	1753	1748	493
175°	1815	1822	1815	1822	1815	172
180°	1827	1827	1827	1827	1827	



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	10.7	10.3	9.9	9.7	9.7	9.8	9.3	8.9	8.5	8.2	7.9
90°	34.1	33.2	32.2	31.3	30.3	29.0	27.5	25.9	24.3	22.7	20.5
92.5°	67.1	66.4	65.7	65.0	64.3	63.0	60.8	58.7	56.6	54.6	51.8
95°	122.2	121.6	121.0	120.4	119.7	118.3	116.1	113.9	111.7	109.4	106.3
97.5°	185.4	185.0	184.6	184.3	183.9	182.6	180.5	178.4	176.3	174.3	169.9
100°	233.1	232.5	231.9	231.2	230.6	228.8	226.0	223.2	220.4	217.4	213.4
102.5°	280.9	280.0	279.1	278.2	277.4	275.3	272.3	269.2	266.1	263.0	260.9
105°	352.5	351.6	350.6	349.7	348.7	347.3	345.4	343.6	341.7	339.8	337.8
107.5°	425.8	425.9	426.0	426.0	426.1	425.7	424.7	423.8	422.8	421.9	420.5
110°	480.5	480.8	481.1	481.5	481.7	481.5	480.5	479.6	478.5	477.6	476.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	534.0	534.5	535.1	535.6	536.2	536.2	535.8	535.4	534.9	534.5	533.3
115°	618.4	618.7	619.0	619.3	619.6	619.9	620.3	620.6	620.9	621.2	620.6
117.5°	700.8	702.1	703.3	704.6	705.9	706.3	706.2	705.9	705.6	705.4	704.7
120°	757.7	758.9	760.2	761.5	762.7	763.4	763.4	763.4	763.4	763.4	763.0
122.5°	814.5	815.5	816.5	817.6	818.6	819.2	819.4	819.7	819.9	820.2	819.4
125°	899.8	900.1	900.4	900.8	901.1	901.5	902.2	902.9	903.4	904.1	903.8
127.5°	981.7	982.3	983.0	983.5	984.2	984.7	985.1	985.3	985.6	986.0	985.6
130°	1036.3	1036.9	1037.6	1038.2	1038.8	1039.2	1039.6	1039.9	1040.2	1040.6	1039.9
132.5°	1087.4	1088.4	1089.2	1090.1	1091.0	1091.6	1091.9	1092.2	1092.5	1092.9	1093.0
135°	1167.1	1168.3	1169.6	1170.8	1172.1	1172.7	1172.7	1172.7	1172.7	1172.7	1172.4
137.5°	1244.9	1246.5	1248.1	1249.7	1251.3	1251.9	1251.5	1251.1	1250.8	1250.4	1249.6
140°	1295.0	1296.6	1298.2	1299.8	1301.3	1301.7	1301.2	1300.5	1299.9	1299.3	1298.4
142.5°	1342.7	1344.3	1346.0	1347.5	1349.1	1349.7	1349.2	1348.9	1348.5	1348.1	1347.0
145°	1414.4	1415.3	1416.3	1417.2	1418.1	1418.6	1418.6	1418.6	1418.6	1418.6	1417.7
147.5°	1475.6	1477.7	1479.8	1482.0	1484.1	1484.8	1484.0	1483.3	1482.5	1481.8	1481.0
150°	1521.0	1521.6	1522.3	1522.9	1523.5	1523.9	1523.9	1523.9	1523.9	1523.9	1522.6
152.5°	1558.6	1559.7	1560.9	1562.0	1563.1	1563.3	1562.5	1561.8	1561.0	1560.3	1559.7
155°	1612.0	1613.5	1615.1	1616.7	1618.3	1618.4	1617.2	1615.9	1614.7	1613.4	1613.1
157.5°	1656.6	1658.7	1660.8	1662.8	1665.0	1665.4	1664.2	1662.8	1661.6	1660.3	1660.0
160°	1687.3	1688.9	1690.5	1692.1	1693.7	1693.8	1692.5	1691.3	1690.0	1688.8	1688.5
162.5°	1713.4	1715.3	1717.1	1719.0	1720.8	1721.0	1719.5	1718.0	1716.5	1714.9	1714.9
165°	1748.4	1750.4	1752.3	1754.2	1756.1	1756.3	1755.1	1753.8	1752.6	1751.3	1751.0
167.5°	1776.3	1778.3	1780.3	1782.2	1784.1	1784.1	1782.3	1780.4	1778.5	1776.6	1776.6
170°	1791.1	1793.3	1795.5	1797.7	1800.0	1800.1	1798.2	1796.3	1794.4	1792.5	1792.5
172.5°	1803.6	1805.5	1807.5	1809.5	1811.5	1811.5	1809.6	1807.7	1805.8	1803.9	1803.9
175°	1815.2	1817.5	1819.7	1821.9	1824.1	1824.3	1822.4	1820.5	1818.5	1816.7	1816.7
177.5°	1822.1	1823.8	1825.6	1827.4	1829.2	1829.3	1827.8	1826.3	1824.8	1823.3	1823.4
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	7.6	7.3	7.0	6.5	5.8	6.1	6.2	5.8	6.0	6.1	6.3
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	49.1	46.5	43.7	41.5	39.7	38.0	36.2	34.4	36.2	38.0	39.7
95°	103.1	100.0	96.8	94.9	94.3	93.7	93.0	92.4	93.0	93.7	94.3
97.5°	165.6	161.2	156.8	154.6	154.3	154.0	153.7	153.5	153.7	154.0	154.3
100°	209.2	205.2	201.0	199.0	199.0	199.0	199.0	199.0	199.0	199.0	199.0
102.5°	258.8	256.7	254.7	253.0	251.7	250.4	249.2	247.9	249.2	250.4	251.7
105°	335.9	334.0	332.2	330.5	328.9	327.3	325.6	324.1	325.6	327.3	328.9
107.5°	419.0	417.5	416.1	414.5	413.0	411.4	409.8	408.2	409.8	411.4	413.0
110°	475.7	474.8	473.8	472.6	471.0	469.4	467.9	466.3	467.9	469.4	471.0



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	532.1	530.8	529.7	528.7	527.8	527.1	526.2	525.4	526.2	527.1	527.8
115°	619.9	619.3	618.7	617.7	616.4	615.2	614.0	612.7	614.0	615.2	616.4
117.5°	704.2	703.6	703.0	702.5	701.9	701.3	700.8	700.2	700.8	701.3	701.9
120°	762.7	762.4	762.0	761.1	759.6	758.0	756.4	754.8	756.4	758.0	759.6
122.5°	818.6	817.7	816.9	816.2	815.7	815.1	814.5	814.0	814.5	815.1	815.7
125°	903.4	903.1	902.9	901.7	899.8	898.0	896.0	894.1	896.0	898.0	899.8
127.5°	985.2	984.9	984.5	983.7	982.6	981.6	980.5	979.4	980.5	981.6	982.6
130°	1039.2	1038.7	1038.0	1036.9	1035.3	1033.8	1032.2	1030.6	1032.2	1033.8	1035.3
132.5°	1093.1	1093.3	1093.3	1092.1	1089.6	1086.9	1084.4	1081.8	1084.4	1086.9	1089.6
135°	1172.1	1171.8	1171.5	1170.4	1168.5	1166.6	1164.7	1162.8	1164.7	1166.6	1168.5
137.5°	1249.0	1248.3	1247.5	1246.3	1244.4	1242.6	1240.9	1239.0	1240.9	1242.6	1244.4
140°	1297.4	1296.4	1295.4	1294.2	1292.6	1291.0	1289.5	1287.9	1289.5	1291.0	1292.6
142.5°	1345.8	1344.5	1343.3	1342.1	1340.8	1339.4	1338.1	1336.8	1338.1	1339.4	1340.8
145°	1416.7	1415.8	1414.9	1413.8	1412.5	1411.3	1409.9	1408.7	1409.9	1411.3	1412.5
147.5°	1480.3	1479.5	1478.8	1478.0	1477.3	1476.6	1475.9	1475.3	1475.9	1476.6	1477.3
150°	1521.4	1520.0	1518.8	1518.3	1518.6	1519.0	1519.3	1519.6	1519.3	1519.0	1518.6
152.5°	1559.2	1558.8	1558.2	1557.7	1557.3	1556.9	1556.4	1555.9	1556.4	1556.9	1557.3
155°	1612.8	1612.5	1612.1	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0	1612.0
157.5°	1659.7	1659.3	1659.1	1659.3	1659.9	1660.7	1661.3	1662.0	1661.3	1660.7	1659.9
160°	1688.1	1687.8	1687.5	1687.8	1688.8	1689.7	1690.6	1691.6	1690.6	1689.7	1688.8
162.5°	1714.8	1714.7	1714.7	1715.0	1715.7	1716.4	1717.0	1717.8	1717.0	1716.4	1715.7
165°	1750.7	1750.4	1750.0	1750.2	1750.9	1751.4	1752.1	1752.8	1752.1	1751.4	1750.9
167.5°	1776.6	1776.6	1776.6	1777.3	1778.5	1779.8	1781.0	1782.3	1781.0	1779.8	1778.5
170°	1792.5	1792.5	1792.5	1793.2	1794.4	1795.6	1797.0	1798.2	1797.0	1795.6	1794.4
172.5°	1803.9	1803.9	1803.9	1804.5	1805.8	1807.0	1808.4	1809.6	1808.4	1807.0	1805.8
175°	1816.7	1816.7	1816.7	1817.3	1818.5	1819.9	1821.1	1822.4	1821.1	1819.9	1818.5
177.5°	1823.7	1824.0	1824.2	1824.9	1825.9	1826.9	1827.9	1828.9	1827.9	1826.9	1825.9
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	6.7	7.2	7.4	8.2	8.1	8.8	9.0	9.1	9.5	9.8	9.9
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.9	27.5	29.0	30.3
92.5°	41.5	43.7	46.5	49.1	51.8	54.6	56.6	58.7	60.8	63.0	64.3
95°	94.9	96.8	100.0	103.1	106.3	109.4	111.7	113.9	116.1	118.3	119.7
97.5°	154.6	156.8	161.2	165.6	169.9	174.3	176.3	178.4	180.5	182.6	183.9
100°	199.0	201.0	205.2	209.2	213.4	217.4	220.4	223.2	226.0	228.8	230.6
102.5°	253.0	254.7	256.7	258.8	260.9	263.0	266.1	269.2	272.3	275.3	277.4
105°	330.5	332.2	334.0	335.9	337.8	339.8	341.7	343.6	345.4	347.3	348.7
107.5°	414.5	416.1	417.5	419.0	420.5	421.9	422.8	423.8	424.7	425.7	426.1
110°	472.6	473.8	474.8	475.7	476.6	477.6	478.5	479.6	480.5	481.5	481.7



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	528.7	529.7	530.8	532.1	533.3	534.5	534.9	535.4	535.8	536.2	536.2
115°	617.7	618.7	619.3	619.9	620.6	621.2	620.9	620.6	620.3	619.9	619.6
117.5°	702.5	703.0	703.6	704.2	704.7	705.4	705.6	705.9	706.2	706.3	705.9
120°	761.1	762.0	762.4	762.7	763.0	763.4	763.4	763.4	763.4	763.4	762.7
122.5°	816.2	816.9	817.7	818.6	819.4	820.2	819.9	819.7	819.4	819.2	818.6
125°	901.7	902.9	903.1	903.4	903.8	904.1	903.4	902.9	902.2	901.5	901.1
127.5°	983.7	984.5	984.9	985.2	985.6	986.0	985.6	985.3	985.1	984.7	984.2
130°	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2	1039.9	1039.6	1039.2	1038.8
132.5°	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5	1092.2	1091.9	1091.6	1091.0
135°	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7	1172.7	1172.7	1172.7	1172.1
137.5°	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8	1251.1	1251.5	1251.9	1251.3
140°	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9	1300.5	1301.2	1301.7	1301.3
142.5°	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5	1348.9	1349.2	1349.7	1349.1
145°	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6	1418.6	1418.6	1418.6	1418.1
147.5°	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5	1483.3	1484.0	1484.8	1484.1
150°	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9	1523.9	1523.9	1523.9	1523.5
152.5°	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0	1561.8	1562.5	1563.3	1563.1
155°	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7	1615.9	1617.2	1618.4	1618.3
157.5°	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6	1662.8	1664.2	1665.4	1665.0
160°	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0	1691.3	1692.5	1693.8	1693.7
162.5°	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5	1718.0	1719.5	1721.0	1720.8
165°	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6	1753.8	1755.1	1756.3	1756.1
167.5°	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5	1780.4	1782.3	1784.1	1784.1
170°	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4	1796.3	1798.2	1800.1	1800.0
172.5°	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8	1807.7	1809.6	1811.5	1811.5
175°	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5	1820.5	1822.4	1824.3	1824.1
177.5°	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8	1826.3	1827.8	1829.3	1829.2
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	10.3	10.3	10.5	10.7	10.5	10.3	10.3	9.9	9.8	9.5	9.1
90°	31.3	32.2	33.2	34.1	33.2	32.2	31.3	30.3	29.0	27.5	25.9
92.5°	65.0	65.7	66.4	67.1	66.4	65.7	65.0	64.3	63.0	60.8	58.7
95°	120.4	121.0	121.6	122.2	121.6	121.0	120.4	119.7	118.3	116.1	113.9
97.5°	184.3	184.6	185.0	185.4	185.0	184.6	184.3	183.9	182.6	180.5	178.4
100°	231.2	231.9	232.5	233.1	232.5	231.9	231.2	230.6	228.8	226.0	223.2
102.5°	278.2	279.1	280.0	280.9	280.0	279.1	278.2	277.4	275.3	272.3	269.2
105°	349.7	350.6	351.6	352.5	351.6	350.6	349.7	348.7	347.3	345.4	343.6
107.5°	426.0	426.0	425.9	425.8	425.9	426.0	426.0	426.1	425.7	424.7	423.8
110°	481.5	481.1	480.8	480.5	480.8	481.1	481.5	481.7	481.5	480.5	479.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	535.6	535.1	534.5	534.0	534.5	535.1	535.6	536.2	536.2	535.8	535.4
115°	619.3	619.0	618.7	618.4	618.7	619.0	619.3	619.6	619.9	620.3	620.6
117.5°	704.6	703.3	702.1	700.8	702.1	703.3	704.6	705.9	706.3	706.2	705.9
120°	761.5	760.2	758.9	757.7	758.9	760.2	761.5	762.7	763.4	763.4	763.4
122.5°	817.6	816.5	815.5	814.5	815.5	816.5	817.6	818.6	819.2	819.4	819.7
125°	900.8	900.4	900.1	899.8	900.1	900.4	900.8	901.1	901.5	902.2	902.9
127.5°	983.5	983.0	982.3	981.7	982.3	983.0	983.5	984.2	984.7	985.1	985.3
130°	1038.2	1037.6	1036.9	1036.3	1036.9	1037.6	1038.2	1038.8	1039.2	1039.6	1039.9
132.5°	1090.1	1089.2	1088.4	1087.4	1088.4	1089.2	1090.1	1091.0	1091.6	1091.9	1092.2
135°	1170.8	1169.6	1168.3	1167.1	1168.3	1169.6	1170.8	1172.1	1172.7	1172.7	1172.7
137.5°	1249.7	1248.1	1246.5	1244.9	1246.5	1248.1	1249.7	1251.3	1251.9	1251.5	1251.1
140°	1299.8	1298.2	1296.6	1295.0	1296.6	1298.2	1299.8	1301.3	1301.7	1301.2	1300.5
142.5°	1347.5	1346.0	1344.3	1342.7	1344.3	1346.0	1347.5	1349.1	1349.7	1349.2	1348.9
145°	1417.2	1416.3	1415.3	1414.4	1415.3	1416.3	1417.2	1418.1	1418.6	1418.6	1418.6
147.5°	1482.0	1479.8	1477.7	1475.6	1477.7	1479.8	1482.0	1484.1	1484.8	1484.0	1483.3
150°	1522.9	1522.3	1521.6	1521.0	1521.6	1522.3	1522.9	1523.5	1523.9	1523.9	1523.9
152.5°	1562.0	1560.9	1559.7	1558.6	1559.7	1560.9	1562.0	1563.1	1563.3	1562.5	1561.8
155°	1616.7	1615.1	1613.5	1612.0	1613.5	1615.1	1616.7	1618.3	1618.4	1617.2	1615.9
157.5°	1662.8	1660.8	1658.7	1656.6	1658.7	1660.8	1662.8	1665.0	1665.4	1664.2	1662.8
160°	1692.1	1690.5	1688.9	1687.3	1688.9	1690.5	1692.1	1693.7	1693.8	1692.5	1691.3
162.5°	1719.0	1717.1	1715.3	1713.4	1715.3	1717.1	1719.0	1720.8	1721.0	1719.5	1718.0
165°	1754.2	1752.3	1750.4	1748.4	1750.4	1752.3	1754.2	1756.1	1756.3	1755.1	1753.8
167.5°	1782.2	1780.3	1778.3	1776.3	1778.3	1780.3	1782.2	1784.1	1784.1	1782.3	1780.4
170°	1797.7	1795.5	1793.3	1791.1	1793.3	1795.5	1797.7	1800.0	1800.1	1798.2	1796.3
172.5°	1809.5	1807.5	1805.5	1803.6	1805.5	1807.5	1809.5	1811.5	1811.5	1809.6	1807.7
175°	1821.9	1819.7	1817.5	1815.2	1817.5	1819.7	1821.9	1824.1	1824.3	1822.4	1820.5
177.5°	1827.4	1825.6	1823.8	1822.1	1823.8	1825.6	1827.4	1829.2	1829.3	1827.8	1826.3
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	9.0	8.8	8.1	8.2	7.4	7.2	6.7	6.3	6.1	6.0	5.8
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	56.6	54.6	51.8	49.1	46.5	43.7	41.5	39.7	38.0	36.2	34.4
95°	111.7	109.4	106.3	103.1	100.0	96.8	94.9	94.3	93.7	93.0	92.4
97.5°	176.3	174.3	169.9	165.6	161.2	156.8	154.6	154.3	154.0	153.7	153.5
100°	220.4	217.4	213.4	209.2	205.2	201.0	199.0	199.0	199.0	199.0	199.0
102.5°	266.1	263.0	260.9	258.8	256.7	254.7	253.0	251.7	250.4	249.2	247.9
105°	341.7	339.8	337.8	335.9	334.0	332.2	330.5	328.9	327.3	325.6	324.1
107.5°	422.8	421.9	420.5	419.0	417.5	416.1	414.5	413.0	411.4	409.8	408.2
110°	478.5	477.6	476.6	475.7	474.8	473.8	472.6	471.0	469.4	467.9	466.3



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	534.9	534.5	533.3	532.1	530.8	529.7	528.7	527.8	527.1	526.2	525.4
115°	620.9	621.2	620.6	619.9	619.3	618.7	617.7	616.4	615.2	614.0	612.7
117.5°	705.6	705.4	704.7	704.2	703.6	703.0	702.5	701.9	701.3	700.8	700.2
120°	763.4	763.4	763.0	762.7	762.4	762.0	761.1	759.6	758.0	756.4	754.8
122.5°	819.9	820.2	819.4	818.6	817.7	816.9	816.2	815.7	815.1	814.5	814.0
125°	903.4	904.1	903.8	903.4	903.1	902.9	901.7	899.8	898.0	896.0	894.1
127.5°	985.6	986.0	985.6	985.2	984.9	984.5	983.7	982.6	981.6	980.5	979.4
130°	1040.2	1040.6	1039.9	1039.2	1038.7	1038.0	1036.9	1035.3	1033.8	1032.2	1030.6
132.5°	1092.5	1092.9	1093.0	1093.1	1093.3	1093.3	1092.1	1089.6	1086.9	1084.4	1081.8
135°	1172.7	1172.7	1172.4	1172.1	1171.8	1171.5	1170.4	1168.5	1166.6	1164.7	1162.8
137.5°	1250.8	1250.4	1249.6	1249.0	1248.3	1247.5	1246.3	1244.4	1242.6	1240.9	1239.0
140°	1299.9	1299.3	1298.4	1297.4	1296.4	1295.4	1294.2	1292.6	1291.0	1289.5	1287.9
142.5°	1348.5	1348.1	1347.0	1345.8	1344.5	1343.3	1342.1	1340.8	1339.4	1338.1	1336.8
145°	1418.6	1418.6	1417.7	1416.7	1415.8	1414.9	1413.8	1412.5	1411.3	1409.9	1408.7
147.5°	1482.5	1481.8	1481.0	1480.3	1479.5	1478.8	1478.0	1477.3	1476.6	1475.9	1475.3
150°	1523.9	1523.9	1522.6	1521.4	1520.0	1518.8	1518.3	1518.6	1519.0	1519.3	1519.6
152.5°	1561.0	1560.3	1559.7	1559.2	1558.8	1558.2	1557.7	1557.3	1556.9	1556.4	1555.9
155°	1614.7	1613.4	1613.1	1612.8	1612.5	1612.1	1612.0	1612.0	1612.0	1612.0	1612.0
157.5°	1661.6	1660.3	1660.0	1659.7	1659.3	1659.1	1659.3	1659.9	1660.7	1661.3	1662.0
160°	1690.0	1688.8	1688.5	1688.1	1687.8	1687.5	1687.8	1688.8	1689.7	1690.6	1691.6
162.5°	1716.5	1714.9	1714.9	1714.8	1714.7	1714.7	1715.0	1715.7	1716.4	1717.0	1717.8
165°	1752.6	1751.3	1751.0	1750.7	1750.4	1750.0	1750.2	1750.9	1751.4	1752.1	1752.8
167.5°	1778.5	1776.6	1776.6	1776.6	1776.6	1776.6	1777.3	1778.5	1779.8	1781.0	1782.3
170°	1794.4	1792.5	1792.5	1792.5	1792.5	1792.5	1793.2	1794.4	1795.6	1797.0	1798.2
172.5°	1805.8	1803.9	1803.9	1803.9	1803.9	1803.9	1804.5	1805.8	1807.0	1808.4	1809.6
175°	1818.5	1816.7	1816.7	1816.7	1816.7	1816.7	1817.3	1818.5	1819.9	1821.1	1822.4
177.5°	1824.8	1823.3	1823.4	1823.7	1824.0	1824.2	1824.9	1825.9	1826.9	1827.9	1828.9
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	6.2	6.1	5.8	6.5	7.0	7.3	7.6	7.9	8.2	8.5	8.9
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.9
92.5°	36.2	38.0	39.7	41.5	43.7	46.5	49.1	51.8	54.6	56.6	58.7
95°	93.0	93.7	94.3	94.9	96.8	100.0	103.1	106.3	109.4	111.7	113.9
97.5°	153.7	154.0	154.3	154.6	156.8	161.2	165.6	169.9	174.3	176.3	178.4
100°	199.0	199.0	199.0	199.0	201.0	205.2	209.2	213.4	217.4	220.4	223.2
102.5°	249.2	250.4	251.7	253.0	254.7	256.7	258.8	260.9	263.0	266.1	269.2
105°	325.6	327.3	328.9	330.5	332.2	334.0	335.9	337.8	339.8	341.7	343.6
107.5°	409.8	411.4	413.0	414.5	416.1	417.5	419.0	420.5	421.9	422.8	423.8
110°	467.9	469.4	471.0	472.6	473.8	474.8	475.7	476.6	477.6	478.5	479.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	526.2	527.1	527.8	528.7	529.7	530.8	532.1	533.3	534.5	534.9	535.4
115°	614.0	615.2	616.4	617.7	618.7	619.3	619.9	620.6	621.2	620.9	620.6
117.5°	700.8	701.3	701.9	702.5	703.0	703.6	704.2	704.7	705.4	705.6	705.9
120°	756.4	758.0	759.6	761.1	762.0	762.4	762.7	763.0	763.4	763.4	763.4
122.5°	814.5	815.1	815.7	816.2	816.9	817.7	818.6	819.4	820.2	819.9	819.7
125°	896.0	898.0	899.8	901.7	902.9	903.1	903.4	903.8	904.1	903.4	902.9
127.5°	980.5	981.6	982.6	983.7	984.5	984.9	985.2	985.6	986.0	985.6	985.3
130°	1032.2	1033.8	1035.3	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2	1039.9
132.5°	1084.4	1086.9	1089.6	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5	1092.2
135°	1164.7	1166.6	1168.5	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7	1172.7
137.5°	1240.9	1242.6	1244.4	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8	1251.1
140°	1289.5	1291.0	1292.6	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9	1300.5
142.5°	1338.1	1339.4	1340.8	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5	1348.9
145°	1409.9	1411.3	1412.5	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6	1418.6
147.5°	1475.9	1476.6	1477.3	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5	1483.3
150°	1519.3	1519.0	1518.6	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9	1523.9
152.5°	1556.4	1556.9	1557.3	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0	1561.8
155°	1612.0	1612.0	1612.0	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7	1615.9
157.5°	1661.3	1660.7	1659.9	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6	1662.8
160°	1690.6	1689.7	1688.8	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0	1691.3
162.5°	1717.0	1716.4	1715.7	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5	1718.0
165°	1752.1	1751.4	1750.9	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6	1753.8
167.5°	1781.0	1779.8	1778.5	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5	1780.4
170°	1797.0	1795.6	1794.4	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4	1796.3
172.5°	1808.4	1807.0	1805.8	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8	1807.7
175°	1821.1	1819.9	1818.5	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5	1820.5
177.5°	1827.9	1826.9	1825.9	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8	1826.3
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	9.3	9.8	9.7	9.7	9.9	10.3	10.7
90°	27.5	29.0	30.3	31.3	32.2	33.2	34.1
92.5°	60.8	63.0	64.3	65.0	65.7	66.4	67.1
95°	116.1	118.3	119.7	120.4	121.0	121.6	122.2
97.5°	180.5	182.6	183.9	184.3	184.6	185.0	185.4
100°	226.0	228.8	230.6	231.2	231.9	232.5	233.1
102.5°	272.3	275.3	277.4	278.2	279.1	280.0	280.9
105°	345.4	347.3	348.7	349.7	350.6	351.6	352.5
107.5°	424.7	425.7	426.1	426.0	426.0	425.9	425.8
110°	480.5	481.5	481.7	481.5	481.1	480.8	480.5



TEST NUMBER: P333657-830

CATALOG NUMBER: S125RDIW-S375D1560U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	535.8	536.2	536.2	535.6	535.1	534.5	534.0
115°	620.3	619.9	619.6	619.3	619.0	618.7	618.4
117.5°	706.2	706.3	705.9	704.6	703.3	702.1	700.8
120°	763.4	763.4	762.7	761.5	760.2	758.9	757.7
122.5°	819.4	819.2	818.6	817.6	816.5	815.5	814.5
125°	902.2	901.5	901.1	900.8	900.4	900.1	899.8
127.5°	985.1	984.7	984.2	983.5	983.0	982.3	981.7
130°	1039.6	1039.2	1038.8	1038.2	1037.6	1036.9	1036.3
132.5°	1091.9	1091.6	1091.0	1090.1	1089.2	1088.4	1087.4
135°	1172.7	1172.7	1172.1	1170.8	1169.6	1168.3	1167.1
137.5°	1251.5	1251.9	1251.3	1249.7	1248.1	1246.5	1244.9
140°	1301.2	1301.7	1301.3	1299.8	1298.2	1296.6	1295.0
142.5°	1349.2	1349.7	1349.1	1347.5	1346.0	1344.3	1342.7
145°	1418.6	1418.6	1418.1	1417.2	1416.3	1415.3	1414.4
147.5°	1484.0	1484.8	1484.1	1482.0	1479.8	1477.7	1475.6
150°	1523.9	1523.9	1523.5	1522.9	1522.3	1521.6	1521.0
152.5°	1562.5	1563.3	1563.1	1562.0	1560.9	1559.7	1558.6
155°	1617.2	1618.4	1618.3	1616.7	1615.1	1613.5	1612.0
157.5°	1664.2	1665.4	1665.0	1662.8	1660.8	1658.7	1656.6
160°	1692.5	1693.8	1693.7	1692.1	1690.5	1688.9	1687.3
162.5°	1719.5	1721.0	1720.8	1719.0	1717.1	1715.3	1713.4
165°	1755.1	1756.3	1756.1	1754.2	1752.3	1750.4	1748.4
167.5°	1782.3	1784.1	1784.1	1782.2	1780.3	1778.3	1776.3
170°	1798.2	1800.1	1800.0	1797.7	1795.5	1793.3	1791.1
172.5°	1809.6	1811.5	1811.5	1809.5	1807.5	1805.5	1803.6
175°	1822.4	1824.3	1824.1	1821.9	1819.7	1817.5	1815.2
177.5°	1827.8	1829.3	1829.2	1827.4	1825.6	1823.8	1822.1
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6

(END OF REPORT)