

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333449-930

Luminaire Tested: **S125DIW-S1090D1340U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333449-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1340U930-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7453.5 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	44	42	40	35
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8373	8373	8373	8373
5°	9697	8401	7356	8401
10°	11281	8358	6445	8358
15°	12488	8297	5945	8297
20°	13978	8199	5544	8199
25°	16376	8089	5349	8089
30°	17687	7982	5179	7982
35°	14542	7779	5067	7779
40°	10336	7497	4945	7497
45°	7941	7117	4875	7117
50°	6779	6646	4866	6646
55°	6035	6184	4908	6184
60°	5444	5679	5032	5679
65°	5029	5171	5164	5171
70°	4572	4645	5238	4645
75°	4037	4092	5190	4092
80°	3396	3336	4749	3336
85°	2690	2401	3831	2401



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	1.7
10°-20°	371.6	5.0
20°-30°	603.4	8.1
30°-40°	736.0	9.9
40°-50°	669.6	9.0
50°-60°	533.4	7.2
60°-70°	371.5	5.0
70°-80°	198.1	2.7
80°-90°	53.0	0.7
90°-100°	91.0	1.2
100°-110°	268.8	3.6
110°-120°	455.3	6.1
120°-130°	599.1	8.0
130°-140°	671.4	9.0
140°-150°	658.0	8.8
150°-160°	552.7	7.4
160°-170°	367.4	4.9
170°-180°	128.6	1.7
0°-30°	1099.8	14.8
0°-40°	1835.9	24.6
0°-60°	3038.8	40.8
0°-90°	3661.4	49.1
90°-120°	815.1	10.9
90°-150°	2743.6	36.8
90°-180°	3792.0	50.9
0°-180°	7453.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1496	1296	1135	1296	1496	151
15°	1868	1241	889	1241	1868	535
25°	2298	1135	751	1135	2298	1050
35°	1844	987	643	987	1844	1129
45°	869	779	534	779	869	696
55°	536	549	436	549	536	483
65°	329	338	338	338	329	327
75°	162	164	208	164	162	174
85°	36	32	52	32	36	43
90°	25	1	25	1	25	16
95°	91	69	91	69	91	93
105°	262	241	262	241	262	278
115°	460	456	460	456	460	455
125°	669	665	669	665	669	598
135°	868	865	868	865	868	670
145°	1052	1048	1052	1048	1052	657
155°	1199	1199	1199	1199	1199	552
165°	1301	1304	1301	1304	1301	367
175°	1350	1356	1350	1356	1350	128
180°	1359	1359	1359	1359	1359	



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1371.3	1369.5	1367.8	1364.2	1366.9	1359.4	1355.9	1349.7	1342.2	1339.6	1336.5
5°	1495.7	1498.4	1501.2	1489.6	1490.7	1483.0	1465.4	1451.1	1439.6	1424.7	1414.2
7.5°	1645.4	1638.8	1638.3	1630.8	1618.0	1607.6	1589.1	1565.5	1542.8	1516.8	1495.3
10°	1720.2	1720.8	1715.8	1707.0	1693.2	1683.3	1659.1	1636.0	1607.9	1574.9	1551.3
12.5°	1776.5	1778.8	1772.6	1760.7	1754.0	1731.8	1712.9	1685.3	1652.0	1625.5	1589.6
15°	1867.7	1861.7	1857.3	1842.3	1830.8	1807.7	1777.4	1748.8	1712.5	1678.9	1645.4
17.5°	1955.5	1960.3	1952.1	1938.5	1902.7	1875.7	1835.1	1795.9	1750.7	1705.7	1665.6
20°	2033.8	2038.2	2025.6	2002.0	1959.0	1932.1	1878.7	1828.1	1775.8	1718.0	1674.0
22.5°	2131.6	2128.1	2111.0	2075.0	2037.8	1987.9	1930.2	1868.6	1803.0	1737.8	1679.3
25°	2298.0	2274.8	2264.4	2219.9	2170.9	2097.7	2018.4	1928.2	1846.7	1760.4	1685.5
27.5°	2390.2	2383.0	2371.3	2340.2	2288.8	2210.5	2117.1	2007.1	1892.2	1783.1	1685.2
30°	2371.7	2372.8	2373.9	2364.0	2331.0	2272.2	2179.1	2060.8	1924.4	1801.6	1688.2
32.5°	2208.0	2228.0	2247.1	2269.8	2279.1	2267.8	2209.5	2102.7	1962.2	1822.8	1686.5
35°	1844.5	1850.6	1912.8	1974.4	2058.1	2123.0	2166.5	2119.1	2000.8	1840.7	1684.4
37.5°	1438.3	1467.9	1511.0	1580.6	1701.4	1809.5	1948.5	2012.4	1974.2	1846.6	1680.6
40°	1226.0	1253.5	1281.7	1352.6	1454.4	1585.3	1743.3	1878.1	1909.5	1828.1	1667.4
42.5°	1062.3	1084.1	1115.2	1168.6	1253.7	1369.7	1520.5	1696.7	1805.2	1774.3	1639.6
45°	869.4	883.2	907.4	949.8	1011.5	1102.2	1235.4	1428.0	1595.9	1651.4	1573.9
47.5°	744.2	744.1	763.0	792.2	836.7	913.8	1012.3	1163.2	1342.5	1475.1	1468.9
50°	674.7	671.9	686.7	712.1	747.3	798.5	892.6	1013.1	1185.3	1335.5	1377.4
52.5°	614.8	615.1	624.3	642.9	672.5	716.2	786.4	895.1	1042.3	1196.5	1275.2
55°	536.0	533.8	544.2	556.9	578.4	607.0	657.6	740.7	860.1	1011.9	1114.4
57.5°	463.7	469.9	474.0	482.8	500.7	519.8	562.5	623.5	718.2	848.6	956.8
60°	421.5	427.5	430.9	439.7	454.0	470.5	503.5	553.0	632.8	745.1	852.4
62.5°	383.7	388.4	389.5	397.4	409.1	425.2	451.1	492.8	555.8	654.0	759.0
65°	329.1	329.1	331.3	339.5	345.0	359.3	379.1	409.4	460.1	536.5	626.2
67.5°	276.5	279.1	278.6	282.2	287.2	298.4	312.6	337.5	375.0	430.9	502.6
70°	242.1	244.3	243.8	246.5	252.0	259.2	270.8	294.4	321.4	369.2	430.9
72.5°	211.3	212.2	210.8	214.4	217.7	224.0	236.8	249.5	274.7	315.1	365.7
75°	161.8	162.9	164.0	166.2	169.5	172.8	179.4	192.1	208.6	238.8	271.3
77.5°	121.3	119.2	121.8	121.5	123.4	125.9	131.8	138.4	152.0	171.1	196.2
80°	91.3	91.9	91.9	92.5	95.2	96.9	101.8	106.7	117.2	131.5	149.1
82.5°	66.7	68.2	67.3	68.2	70.5	71.7	74.5	78.6	84.6	95.9	108.6
85°	36.3	33.6	34.7	35.8	35.8	36.3	38.5	40.2	43.5	47.9	52.8
87.5°	15.7	16.4	16.7	16.6	16.9	16.6	18.2	17.9	19.0	20.1	21.5
90°	25.4	24.7	24.0	23.2	22.6	21.6	20.5	19.2	18.1	17.0	15.2
92.5°	49.9	49.4	48.9	48.3	47.9	46.8	45.2	43.7	42.2	40.6	38.6
95°	91.0	90.5	90.0	89.5	89.0	88.1	86.3	84.7	83.1	81.4	79.1
97.5°	137.9	137.6	137.4	137.1	136.8	135.8	134.3	132.7	131.2	129.6	126.5
100°	173.4	173.0	172.5	172.0	171.5	170.2	168.1	166.1	164.0	161.8	158.7
102.5°	209.0	208.3	207.7	207.0	206.4	204.9	202.5	200.2	198.0	195.7	194.1
105°	262.3	261.5	260.9	260.2	259.4	258.4	257.0	255.6	254.2	252.7	251.4
107.5°	316.8	316.9	316.9	317.0	317.1	316.7	316.0	315.3	314.6	313.9	312.8
110°	357.4	357.7	357.9	358.2	358.4	358.2	357.4	356.8	356.0	355.3	354.7



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.2	397.6	398.1	398.5	398.9	398.9	398.6	398.3	397.9	397.6	396.7
115°	460.1	460.3	460.5	460.7	461.0	461.2	461.5	461.7	461.9	462.2	461.7
117.5°	521.4	522.4	523.3	524.2	525.1	525.5	525.3	525.1	525.0	524.8	524.3
120°	563.7	564.6	565.6	566.5	567.4	567.9	567.9	567.9	567.9	567.9	567.7
122.5°	606.0	606.7	607.5	608.2	609.0	609.4	609.7	609.8	610.0	610.3	609.6
125°	669.4	669.7	669.9	670.2	670.4	670.7	671.2	671.6	672.1	672.6	672.4
127.5°	730.3	730.8	731.3	731.8	732.2	732.6	732.8	733.0	733.3	733.5	733.3
130°	770.9	771.4	771.9	772.4	772.8	773.2	773.5	773.6	773.9	774.1	773.6
132.5°	809.0	809.7	810.3	811.1	811.7	812.1	812.4	812.6	812.9	813.1	813.2
135°	868.3	869.2	870.2	871.1	872.0	872.5	872.5	872.5	872.5	872.5	872.3
137.5°	926.3	927.4	928.5	929.8	930.9	931.4	931.1	930.8	930.5	930.3	929.8
140°	963.4	964.7	965.8	966.9	968.2	968.5	968.0	967.6	967.1	966.6	965.9
142.5°	999.0	1000.1	1001.4	1002.5	1003.7	1004.1	1003.9	1003.6	1003.3	1003.0	1002.1
145°	1052.3	1053.0	1053.7	1054.4	1055.1	1055.5	1055.5	1055.5	1055.5	1055.5	1054.8
147.5°	1097.8	1099.3	1101.0	1102.5	1104.2	1104.6	1104.1	1103.5	1103.0	1102.4	1101.9
150°	1131.6	1132.0	1132.5	1133.0	1133.5	1133.8	1133.8	1133.8	1133.8	1133.8	1132.8
152.5°	1159.5	1160.3	1161.2	1162.0	1162.9	1163.0	1162.5	1161.9	1161.4	1160.8	1160.4
155°	1199.3	1200.4	1201.7	1202.8	1204.0	1204.1	1203.1	1202.2	1201.3	1200.4	1200.1
157.5°	1232.5	1234.0	1235.6	1237.1	1238.7	1239.0	1238.0	1237.1	1236.2	1235.3	1235.0
160°	1255.3	1256.5	1257.7	1258.9	1260.0	1260.1	1259.2	1258.3	1257.4	1256.4	1256.1
162.5°	1274.8	1276.2	1277.5	1278.9	1280.3	1280.3	1279.2	1278.1	1277.0	1275.9	1275.8
165°	1300.8	1302.2	1303.7	1305.0	1306.4	1306.7	1305.8	1304.8	1303.9	1302.9	1302.7
167.5°	1321.5	1323.0	1324.5	1325.9	1327.4	1327.4	1326.0	1324.6	1323.1	1321.8	1321.8
170°	1332.5	1334.2	1335.9	1337.5	1339.1	1339.2	1337.8	1336.4	1335.1	1333.6	1333.6
172.5°	1341.8	1343.3	1344.8	1346.2	1347.7	1347.7	1346.3	1344.9	1343.5	1342.1	1342.1
175°	1350.5	1352.2	1353.8	1355.4	1357.1	1357.2	1355.8	1354.4	1353.0	1351.6	1351.6
177.5°	1355.6	1356.9	1358.2	1359.5	1360.9	1361.0	1359.8	1358.7	1357.6	1356.4	1356.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1333.9	1330.8	1327.3	1321.1	1313.6	1309.7	1303.5	1299.6	1291.6	1285.0	1278.0
5°	1401.6	1387.3	1374.1	1357.0	1338.3	1326.2	1311.9	1295.9	1279.4	1262.3	1243.7
7.5°	1471.7	1446.3	1418.9	1389.3	1360.3	1333.7	1308.2	1283.3	1260.0	1231.8	1207.9
10°	1518.8	1486.9	1452.8	1412.6	1373.5	1339.4	1304.7	1274.5	1243.7	1210.6	1181.5
12.5°	1565.9	1523.4	1475.2	1431.1	1384.1	1342.9	1302.1	1263.5	1224.7	1188.2	1154.1
15°	1599.1	1561.7	1517.1	1454.4	1401.6	1344.9	1290.9	1240.9	1194.1	1153.4	1110.5
17.5°	1621.1	1572.8	1524.9	1464.8	1395.5	1332.1	1271.1	1213.7	1161.0	1109.4	1068.0
20°	1625.0	1575.5	1525.4	1466.5	1395.5	1322.9	1261.8	1193.0	1136.4	1083.0	1032.3
22.5°	1623.7	1567.6	1513.0	1452.5	1383.2	1316.3	1242.4	1172.3	1110.8	1058.3	1005.5
25°	1611.3	1551.3	1483.0	1422.0	1353.7	1282.7	1207.9	1135.2	1072.5	1012.5	960.3
27.5°	1600.9	1523.1	1445.9	1374.6	1308.7	1243.7	1172.0	1097.6	1028.0	967.3	918.0
30°	1588.1	1502.8	1415.8	1341.6	1273.9	1210.6	1143.0	1070.3	997.7	938.2	885.4
32.5°	1576.7	1477.3	1385.5	1304.6	1233.0	1171.4	1109.1	1039.9	968.6	908.3	855.5
35°	1554.5	1439.6	1334.5	1243.1	1166.6	1103.3	1051.1	986.7	921.2	862.8	812.2
37.5°	1526.5	1390.0	1277.2	1181.5	1097.6	1030.9	982.3	932.9	870.0	813.8	768.0
40°	1504.5	1354.8	1235.4	1137.4	1050.5	981.1	936.0	889.2	837.0	784.7	736.3
42.5°	1476.8	1323.1	1193.1	1087.7	1001.6	934.1	886.7	847.0	800.9	752.1	707.2
45°	1425.8	1265.7	1124.8	1011.5	924.5	857.9	808.9	779.2	744.5	698.3	660.3
47.5°	1350.9	1196.6	1050.9	933.9	844.2	782.5	736.6	708.1	683.7	649.3	614.9
50°	1284.3	1145.2	997.7	881.6	791.9	729.7	687.3	661.5	640.5	614.1	585.0
52.5°	1210.0	1080.4	945.3	830.5	741.7	680.4	638.9	616.1	598.7	579.8	551.1
55°	1091.8	981.7	856.2	747.3	665.3	605.3	569.0	549.2	534.9	520.6	503.0
57.5°	961.6	875.5	764.3	664.7	589.2	534.7	500.8	481.5	470.3	463.0	452.7
60°	870.0	796.3	700.5	609.7	536.0	487.5	454.5	439.7	430.3	424.3	416.5
62.5°	785.1	724.5	635.8	552.9	488.4	442.6	413.2	398.8	389.8	386.9	380.5
65°	659.8	613.0	539.8	471.1	416.0	376.9	352.2	338.4	332.9	329.6	330.2
67.5°	536.4	507.9	449.1	390.4	346.6	313.8	294.0	283.4	280.6	276.2	276.1
70°	461.1	439.7	390.1	339.0	299.9	274.6	257.0	246.0	243.2	241.0	240.5
72.5°	394.7	375.9	332.9	291.9	256.7	234.6	220.0	213.4	208.9	207.6	207.5
75°	296.6	286.2	252.0	219.6	195.3	179.9	170.1	164.0	160.7	160.1	160.7
77.5°	210.8	201.7	180.0	157.0	141.8	130.1	121.7	119.6	115.9	116.0	115.4
80°	158.5	152.5	138.7	120.5	107.9	97.9	93.5	89.7	88.6	86.9	88.6
82.5°	114.9	108.4	99.1	87.5	77.0	71.1	66.7	65.5	64.8	64.1	64.4
85°	56.7	57.2	51.7	42.9	38.5	35.2	32.4	32.4	31.9	31.4	31.9
87.5°	22.1	20.9	18.8	17.1	14.5	12.9	12.1	12.1	11.2	11.1	11.9
90°	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1	2.9	4.8	6.7
92.5°	36.6	34.6	32.5	30.8	29.5	28.2	26.9	25.6	26.9	28.2	29.5
95°	76.7	74.4	72.1	70.6	70.1	69.7	69.2	68.7	69.2	69.7	70.1
97.5°	123.2	119.9	116.7	115.0	114.8	114.6	114.4	114.2	114.4	114.6	114.8
100°	155.7	152.6	149.6	148.1	148.1	148.1	148.1	148.1	148.1	148.1	148.1
102.5°	192.6	191.0	189.5	188.2	187.3	186.3	185.4	184.4	185.4	186.3	187.3
105°	250.0	248.5	247.1	245.8	244.7	243.4	242.3	241.2	242.3	243.4	244.7
107.5°	311.7	310.6	309.6	308.4	307.3	306.1	304.9	303.7	304.9	306.1	307.3
110°	353.9	353.3	352.5	351.6	350.4	349.3	348.1	346.9	348.1	349.3	350.4



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	395.8	394.9	394.1	393.3	392.7	392.1	391.5	390.9	391.5	392.1	392.7
115°	461.2	460.7	460.3	459.6	458.6	457.7	456.7	455.8	456.7	457.7	458.6
117.5°	523.9	523.5	523.1	522.7	522.2	521.8	521.4	521.0	521.4	521.8	522.2
120°	567.4	567.2	567.0	566.3	565.1	563.9	562.7	561.6	562.7	563.9	565.1
122.5°	609.0	608.4	607.8	607.2	606.8	606.4	606.0	605.6	606.0	606.4	606.8
125°	672.1	671.9	671.6	670.8	669.4	668.1	666.6	665.2	666.6	668.1	669.4
127.5°	733.0	732.7	732.4	731.9	731.1	730.3	729.4	728.6	729.4	730.3	731.1
130°	773.2	772.7	772.3	771.4	770.3	769.1	767.9	766.7	767.9	769.1	770.3
132.5°	813.3	813.3	813.4	812.5	810.6	808.7	806.7	804.8	806.7	808.7	810.6
135°	872.0	871.8	871.6	870.7	869.4	867.9	866.5	865.1	866.5	867.9	869.4
137.5°	929.2	928.7	928.1	927.2	925.9	924.5	923.2	921.8	923.2	924.5	925.9
140°	965.2	964.5	963.8	962.9	961.7	960.5	959.4	958.1	959.4	960.5	961.7
142.5°	1001.2	1000.3	999.4	998.5	997.5	996.5	995.6	994.6	995.6	996.5	997.5
145°	1054.0	1053.4	1052.6	1051.8	1050.8	1049.9	1049.0	1048.1	1049.0	1049.9	1050.8
147.5°	1101.3	1100.7	1100.2	1099.6	1099.1	1098.6	1098.0	1097.6	1098.0	1098.6	1099.1
150°	1131.9	1130.9	1129.9	1129.6	1129.8	1130.1	1130.3	1130.6	1130.3	1130.1	1129.8
152.5°	1160.0	1159.7	1159.3	1158.9	1158.6	1158.3	1158.0	1157.6	1158.0	1158.3	1158.6
155°	1199.9	1199.6	1199.4	1199.3	1199.3	1199.3	1199.3	1199.3	1199.3	1199.3	1199.3
157.5°	1234.8	1234.5	1234.3	1234.4	1234.9	1235.5	1236.0	1236.5	1236.0	1235.5	1234.9
160°	1256.0	1255.7	1255.5	1255.7	1256.4	1257.1	1257.8	1258.5	1257.8	1257.1	1256.4
162.5°	1275.8	1275.7	1275.7	1275.9	1276.4	1276.9	1277.5	1278.0	1277.5	1276.9	1276.4
165°	1302.4	1302.2	1302.0	1302.1	1302.6	1303.0	1303.5	1304.0	1303.5	1303.0	1302.6
167.5°	1321.8	1321.8	1321.8	1322.3	1323.1	1324.1	1325.0	1326.0	1325.0	1324.1	1323.1
170°	1333.6	1333.6	1333.6	1334.1	1335.1	1335.9	1336.9	1337.8	1336.9	1335.9	1335.1
172.5°	1342.1	1342.1	1342.1	1342.6	1343.5	1344.4	1345.3	1346.3	1345.3	1344.4	1343.5
175°	1351.6	1351.6	1351.6	1352.1	1353.0	1354.0	1354.9	1355.8	1354.9	1354.0	1353.0
177.5°	1356.8	1357.0	1357.2	1357.6	1358.5	1359.2	1359.9	1360.7	1359.9	1359.2	1358.5
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1274.0	1269.2	1265.2	1256.4	1251.6	1245.0	1239.7	1245.4	1239.3	1241.9	1238.0
5°	1234.3	1218.9	1207.9	1191.9	1178.2	1165.5	1156.2	1154.5	1150.1	1147.9	1141.3
7.5°	1186.5	1167.3	1148.3	1127.4	1109.8	1091.8	1080.4	1071.0	1064.7	1056.5	1050.8
10°	1158.4	1132.5	1110.5	1085.2	1063.2	1043.9	1028.5	1020.8	1013.7	1003.1	999.3
12.5°	1123.6	1096.8	1070.0	1042.9	1021.7	1000.3	987.1	975.4	970.5	958.7	957.5
15°	1081.9	1041.7	1015.3	987.7	958.6	941.0	930.0	917.3	911.8	903.6	897.5
17.5°	1032.1	996.2	963.2	934.7	909.7	894.9	881.3	872.5	863.1	857.7	847.7
20°	996.1	961.9	928.9	898.6	879.4	862.3	851.3	843.0	833.2	830.4	820.5
22.5°	965.6	928.0	896.3	870.9	849.9	830.6	818.7	813.1	806.2	797.8	795.8
25°	916.2	877.2	850.2	824.9	806.2	788.6	780.3	773.1	766.5	760.5	758.3
27.5°	873.5	838.6	806.6	783.7	767.4	751.4	744.1	735.4	730.6	725.7	719.7
30°	843.6	807.8	779.8	757.7	740.1	725.9	718.1	712.1	707.7	703.3	699.9
32.5°	812.8	779.7	752.4	730.9	713.3	702.5	695.7	691.4	686.6	681.3	677.1
35°	772.1	735.7	709.3	690.6	676.9	668.6	660.9	657.0	651.5	651.5	647.1
37.5°	726.2	694.8	671.5	654.4	642.0	634.7	626.3	623.7	620.2	617.8	616.3
40°	698.9	669.7	647.7	630.6	617.4	611.4	604.8	600.4	598.2	595.4	594.3
42.5°	670.7	642.9	621.7	606.0	594.5	589.4	583.2	580.1	575.7	572.1	571.4
45°	627.9	600.9	581.6	569.0	559.1	553.0	549.2	542.6	540.4	536.0	535.4
47.5°	587.3	561.4	542.5	532.1	523.4	518.4	512.4	505.8	503.3	501.1	500.8
50°	556.9	533.2	515.6	505.7	497.5	490.3	484.3	479.9	478.2	478.2	479.3
52.5°	526.1	505.9	491.0	478.8	471.1	463.4	457.9	455.2	452.7	455.3	457.3
55°	480.9	460.6	449.6	438.1	430.3	421.5	418.7	417.7	416.0	420.4	422.7
57.5°	433.2	418.9	406.0	394.5	387.6	382.5	378.8	378.1	381.2	383.4	390.4
60°	402.8	386.3	374.7	365.9	357.7	354.4	353.3	352.2	354.4	360.4	369.8
62.5°	369.3	356.0	343.5	336.9	330.8	325.3	325.1	325.8	330.2	337.1	346.4
65°	320.2	308.7	300.4	292.8	287.8	284.5	285.6	287.8	292.8	302.1	312.6
67.5°	270.4	262.5	255.1	248.8	244.1	244.1	245.2	248.5	254.4	265.1	274.7
70°	238.3	229.5	223.4	220.7	216.8	214.6	217.9	223.4	228.4	238.3	246.5
72.5°	206.1	198.7	194.0	192.1	190.4	188.7	189.7	195.7	202.4	212.3	221.8
75°	158.5	155.7	152.5	150.3	148.5	149.7	150.7	156.3	161.8	172.3	183.3
77.5°	115.7	112.8	110.8	110.3	109.4	110.0	113.0	117.1	122.5	130.1	138.4
80°	87.5	86.4	85.3	84.7	84.7	85.3	89.7	92.5	97.4	104.5	111.1
82.5°	63.8	63.0	62.9	62.7	63.2	63.3	66.0	69.5	73.6	79.0	84.7
85°	33.6	32.4	34.1	34.7	33.6	35.2	36.3	38.5	40.2	42.9	45.7
87.5°	12.7	13.9	13.9	14.6	14.9	16.1	16.0	17.9	19.1	20.1	19.9
90°	8.6	10.4	12.0	13.6	15.2	17.0	18.1	19.2	20.5	21.6	22.6
92.5°	30.8	32.5	34.6	36.6	38.6	40.6	42.2	43.7	45.2	46.8	47.9
95°	70.6	72.1	74.4	76.7	79.1	81.4	83.1	84.7	86.3	88.1	89.0
97.5°	115.0	116.7	119.9	123.2	126.5	129.6	131.2	132.7	134.3	135.8	136.8
100°	148.1	149.6	152.6	155.7	158.7	161.8	164.0	166.1	168.1	170.2	171.5
102.5°	188.2	189.5	191.0	192.6	194.1	195.7	198.0	200.2	202.5	204.9	206.4
105°	245.8	247.1	248.5	250.0	251.4	252.7	254.2	255.6	257.0	258.4	259.4
107.5°	308.4	309.6	310.6	311.7	312.8	313.9	314.6	315.3	316.0	316.7	317.1
110°	351.6	352.5	353.3	353.9	354.7	355.3	356.0	356.8	357.4	358.2	358.4



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	393.3	394.1	394.9	395.8	396.7	397.6	397.9	398.3	398.6	398.9	398.9
115°	459.6	460.3	460.7	461.2	461.7	462.2	461.9	461.7	461.5	461.2	461.0
117.5°	522.7	523.1	523.5	523.9	524.3	524.8	525.0	525.1	525.3	525.5	525.1
120°	566.3	567.0	567.2	567.4	567.7	567.9	567.9	567.9	567.9	567.9	567.4
122.5°	607.2	607.8	608.4	609.0	609.6	610.3	610.0	609.8	609.7	609.4	609.0
125°	670.8	671.6	671.9	672.1	672.4	672.6	672.1	671.6	671.2	670.7	670.4
127.5°	731.9	732.4	732.7	733.0	733.3	733.5	733.3	733.0	732.8	732.6	732.2
130°	771.4	772.3	772.7	773.2	773.6	774.1	773.9	773.6	773.5	773.2	772.8
132.5°	812.5	813.4	813.3	813.3	813.2	813.1	812.9	812.6	812.4	812.1	811.7
135°	870.7	871.6	871.8	872.0	872.3	872.5	872.5	872.5	872.5	872.5	872.0
137.5°	927.2	928.1	928.7	929.2	929.8	930.3	930.5	930.8	931.1	931.4	930.9
140°	962.9	963.8	964.5	965.2	965.9	966.6	967.1	967.6	968.0	968.5	968.2
142.5°	998.5	999.4	1000.3	1001.2	1002.1	1003.0	1003.3	1003.6	1003.9	1004.1	1003.7
145°	1051.8	1052.6	1053.4	1054.0	1054.8	1055.5	1055.5	1055.5	1055.5	1055.5	1055.1
147.5°	1099.6	1100.2	1100.7	1101.3	1101.9	1102.4	1103.0	1103.5	1104.1	1104.6	1104.2
150°	1129.6	1129.9	1130.9	1131.9	1132.8	1133.8	1133.8	1133.8	1133.8	1133.8	1133.5
152.5°	1158.9	1159.3	1159.7	1160.0	1160.4	1160.8	1161.4	1161.9	1162.5	1163.0	1162.9
155°	1199.3	1199.4	1199.6	1199.9	1200.1	1200.4	1201.3	1202.2	1203.1	1204.1	1204.0
157.5°	1234.4	1234.3	1234.5	1234.8	1235.0	1235.3	1236.2	1237.1	1238.0	1239.0	1238.7
160°	1255.7	1255.5	1255.7	1256.0	1256.1	1256.4	1257.4	1258.3	1259.2	1260.1	1260.0
162.5°	1275.9	1275.7	1275.7	1275.8	1275.8	1275.9	1277.0	1278.1	1279.2	1280.3	1280.3
165°	1302.1	1302.0	1302.2	1302.4	1302.7	1302.9	1303.9	1304.8	1305.8	1306.7	1306.4
167.5°	1322.3	1321.8	1321.8	1321.8	1321.8	1321.8	1323.1	1324.6	1326.0	1327.4	1327.4
170°	1334.1	1333.6	1333.6	1333.6	1333.6	1333.6	1335.1	1336.4	1337.8	1339.2	1339.1
172.5°	1342.6	1342.1	1342.1	1342.1	1342.1	1342.1	1343.5	1344.9	1346.3	1347.7	1347.7
175°	1352.1	1351.6	1351.6	1351.6	1351.6	1351.6	1353.0	1354.4	1355.8	1357.2	1357.1
177.5°	1357.6	1357.2	1357.0	1356.8	1356.7	1356.4	1357.6	1358.7	1359.8	1361.0	1360.9
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1235.3	1238.4	1235.7	1239.3	1235.7	1238.4	1235.3	1238.0	1241.9	1239.3	1245.4
5°	1138.6	1133.6	1136.9	1134.7	1136.9	1133.6	1138.6	1141.3	1147.9	1150.1	1154.5
7.5°	1049.2	1044.5	1039.0	1036.5	1039.0	1044.5	1049.2	1050.8	1056.5	1064.7	1071.0
10°	993.3	987.2	986.7	982.8	986.7	987.2	993.3	999.3	1003.1	1013.7	1020.8
12.5°	952.4	946.7	940.4	938.8	940.4	946.7	952.4	957.5	958.7	970.5	975.4
15°	894.2	889.8	886.0	889.2	886.0	889.8	894.2	897.5	903.6	911.8	917.3
17.5°	845.9	842.3	841.6	837.6	841.6	842.3	845.9	847.7	857.7	863.1	872.5
20°	815.5	812.8	813.9	806.7	813.9	812.8	815.5	820.5	830.4	833.2	843.0
22.5°	791.3	785.9	785.3	783.8	785.3	785.9	791.3	795.8	797.8	806.2	813.1
25°	753.3	750.6	747.9	750.6	747.9	750.6	753.3	758.3	760.5	766.5	773.1
27.5°	720.2	716.9	716.2	716.5	716.2	716.9	720.2	719.7	725.7	730.6	735.4
30°	699.9	694.5	695.0	694.5	695.0	694.5	699.9	699.9	703.3	707.7	712.1
32.5°	677.9	674.2	673.4	672.5	673.4	674.2	677.9	677.1	681.3	686.6	691.4
35°	645.5	645.5	642.7	642.7	642.7	645.5	645.5	647.1	651.5	651.5	657.0
37.5°	615.0	614.4	612.8	613.0	612.8	614.4	615.0	616.3	617.8	620.2	623.7
40°	592.1	591.6	589.9	586.6	589.9	591.6	592.1	594.3	595.4	598.2	600.4
42.5°	570.1	568.3	567.4	566.4	567.4	568.3	570.1	571.4	572.1	575.7	580.1
45°	535.4	535.4	534.3	533.8	534.3	535.4	535.4	535.4	536.0	540.4	542.6
47.5°	501.7	502.7	504.8	504.5	504.8	502.7	501.7	500.8	501.1	503.3	505.8
50°	481.5	482.1	483.7	484.3	483.7	482.1	481.5	479.3	478.2	478.2	479.9
52.5°	459.0	462.3	464.3	464.0	464.3	462.3	459.0	457.3	455.3	452.7	455.2
55°	427.5	431.5	435.3	435.9	435.3	431.5	427.5	422.7	420.4	416.0	417.7
57.5°	396.4	401.8	405.9	407.2	405.9	401.8	396.4	390.4	383.4	381.2	378.1
60°	375.3	382.5	387.4	389.6	387.4	382.5	375.3	369.8	360.4	354.4	352.2
62.5°	355.1	363.1	368.0	368.4	368.0	363.1	355.1	346.4	337.1	330.2	325.8
65°	321.9	330.2	334.6	337.9	334.6	330.2	321.9	312.6	302.1	292.8	287.8
67.5°	286.3	294.5	299.4	302.0	299.4	294.5	286.3	274.7	265.1	254.4	248.5
70°	260.3	268.6	275.2	277.4	275.2	268.6	260.3	246.5	238.3	228.4	223.4
72.5°	234.7	242.1	247.4	250.1	247.4	242.1	234.7	221.8	212.3	202.4	195.7
75°	190.4	200.3	205.3	208.0	205.3	200.3	190.4	183.3	172.3	161.8	156.3
77.5°	146.8	155.8	158.8	160.2	158.8	155.8	146.8	138.4	130.1	122.5	117.1
80°	117.7	123.3	127.1	127.7	127.1	123.3	117.7	111.1	104.5	97.4	92.5
82.5°	90.5	95.1	96.3	97.8	96.3	95.1	90.5	84.7	79.0	73.6	69.5
85°	49.5	51.7	52.3	51.7	52.3	51.7	49.5	45.7	42.9	40.2	38.5
87.5°	21.0	20.6	20.8	21.8	20.8	20.6	21.0	19.9	20.1	19.1	17.9
90°	23.2	24.0	24.7	25.4	24.7	24.0	23.2	22.6	21.6	20.5	19.2
92.5°	48.3	48.9	49.4	49.9	49.4	48.9	48.3	47.9	46.8	45.2	43.7
95°	89.5	90.0	90.5	91.0	90.5	90.0	89.5	89.0	88.1	86.3	84.7
97.5°	137.1	137.4	137.6	137.9	137.6	137.4	137.1	136.8	135.8	134.3	132.7
100°	172.0	172.5	173.0	173.4	173.0	172.5	172.0	171.5	170.2	168.1	166.1
102.5°	207.0	207.7	208.3	209.0	208.3	207.7	207.0	206.4	204.9	202.5	200.2
105°	260.2	260.9	261.5	262.3	261.5	260.9	260.2	259.4	258.4	257.0	255.6
107.5°	317.0	316.9	316.9	316.8	316.9	316.9	317.0	317.1	316.7	316.0	315.3
110°	358.2	357.9	357.7	357.4	357.7	357.9	358.2	358.4	358.2	357.4	356.8



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	398.5	398.1	397.6	397.2	397.6	398.1	398.5	398.9	398.9	398.6	398.3
115°	460.7	460.5	460.3	460.1	460.3	460.5	460.7	461.0	461.2	461.5	461.7
117.5°	524.2	523.3	522.4	521.4	522.4	523.3	524.2	525.1	525.5	525.3	525.1
120°	566.5	565.6	564.6	563.7	564.6	565.6	566.5	567.4	567.9	567.9	567.9
122.5°	608.2	607.5	606.7	606.0	606.7	607.5	608.2	609.0	609.4	609.7	609.8
125°	670.2	669.9	669.7	669.4	669.7	669.9	670.2	670.4	670.7	671.2	671.6
127.5°	731.8	731.3	730.8	730.3	730.8	731.3	731.8	732.2	732.6	732.8	733.0
130°	772.4	771.9	771.4	770.9	771.4	771.9	772.4	772.8	773.2	773.5	773.6
132.5°	811.1	810.3	809.7	809.0	809.7	810.3	811.1	811.7	812.1	812.4	812.6
135°	871.1	870.2	869.2	868.3	869.2	870.2	871.1	872.0	872.5	872.5	872.5
137.5°	929.8	928.5	927.4	926.3	927.4	928.5	929.8	930.9	931.4	931.1	930.8
140°	966.9	965.8	964.7	963.4	964.7	965.8	966.9	968.2	968.5	968.0	967.6
142.5°	1002.5	1001.4	1000.1	999.0	1000.1	1001.4	1002.5	1003.7	1004.1	1003.9	1003.6
145°	1054.4	1053.7	1053.0	1052.3	1053.0	1053.7	1054.4	1055.1	1055.5	1055.5	1055.5
147.5°	1102.5	1101.0	1099.3	1097.8	1099.3	1101.0	1102.5	1104.2	1104.6	1104.1	1103.5
150°	1133.0	1132.5	1132.0	1131.6	1132.0	1132.5	1133.0	1133.5	1133.8	1133.8	1133.8
152.5°	1162.0	1161.2	1160.3	1159.5	1160.3	1161.2	1162.0	1162.9	1163.0	1162.5	1161.9
155°	1202.8	1201.7	1200.4	1199.3	1200.4	1201.7	1202.8	1204.0	1204.1	1203.1	1202.2
157.5°	1237.1	1235.6	1234.0	1232.5	1234.0	1235.6	1237.1	1238.7	1239.0	1238.0	1237.1
160°	1258.9	1257.7	1256.5	1255.3	1256.5	1257.7	1258.9	1260.0	1260.1	1259.2	1258.3
162.5°	1278.9	1277.5	1276.2	1274.8	1276.2	1277.5	1278.9	1280.3	1280.3	1279.2	1278.1
165°	1305.0	1303.7	1302.2	1300.8	1302.2	1303.7	1305.0	1306.4	1306.7	1305.8	1304.8
167.5°	1325.9	1324.5	1323.0	1321.5	1323.0	1324.5	1325.9	1327.4	1327.4	1326.0	1324.6
170°	1337.5	1335.9	1334.2	1332.5	1334.2	1335.9	1337.5	1339.1	1339.2	1337.8	1336.4
172.5°	1346.2	1344.8	1343.3	1341.8	1343.3	1344.8	1346.2	1347.7	1347.7	1346.3	1344.9
175°	1355.4	1353.8	1352.2	1350.5	1352.2	1353.8	1355.4	1357.1	1357.2	1355.8	1354.4
177.5°	1359.5	1358.2	1356.9	1355.6	1356.9	1358.2	1359.5	1360.9	1361.0	1359.8	1358.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1239.7	1245.0	1251.6	1256.4	1265.2	1269.2	1274.0	1278.0	1285.0	1291.6	1299.6
5°	1156.2	1165.5	1178.2	1191.9	1207.9	1218.9	1234.3	1243.7	1262.3	1279.4	1295.9
7.5°	1080.4	1091.8	1109.8	1127.4	1148.3	1167.3	1186.5	1207.9	1231.8	1260.0	1283.3
10°	1028.5	1043.9	1063.2	1085.2	1110.5	1132.5	1158.4	1181.5	1210.6	1243.7	1274.5
12.5°	987.1	1000.3	1021.7	1042.9	1070.0	1096.8	1123.6	1154.1	1188.2	1224.7	1263.5
15°	930.0	941.0	958.6	987.7	1015.3	1041.7	1081.9	1110.5	1153.4	1194.1	1240.9
17.5°	881.3	894.9	909.7	934.7	963.2	996.2	1032.1	1068.0	1109.4	1161.0	1213.7
20°	851.3	862.3	879.4	898.6	928.9	961.9	996.1	1032.3	1083.0	1136.4	1193.0
22.5°	818.7	830.6	849.9	870.9	896.3	928.0	965.6	1005.5	1058.3	1110.8	1172.3
25°	780.3	788.6	806.2	824.9	850.2	877.2	916.2	960.3	1012.5	1072.5	1135.2
27.5°	744.1	751.4	767.4	783.7	806.6	838.6	873.5	918.0	967.3	1028.0	1097.6
30°	718.1	725.9	740.1	757.7	779.8	807.8	843.6	885.4	938.2	997.7	1070.3
32.5°	695.7	702.5	713.3	730.9	752.4	779.7	812.8	855.5	908.3	968.6	1039.9
35°	660.9	668.6	676.9	690.6	709.3	735.7	772.1	812.2	862.8	921.2	986.7
37.5°	626.3	634.7	642.0	654.4	671.5	694.8	726.2	768.0	813.8	870.0	932.9
40°	604.8	611.4	617.4	630.6	647.7	669.7	698.9	736.3	784.7	837.0	889.2
42.5°	583.2	589.4	594.5	606.0	621.7	642.9	670.7	707.2	752.1	800.9	847.0
45°	549.2	553.0	559.1	569.0	581.6	600.9	627.9	660.3	698.3	744.5	779.2
47.5°	512.4	518.4	523.4	532.1	542.5	561.4	587.3	614.9	649.3	683.7	708.1
50°	484.3	490.3	497.5	505.7	515.6	533.2	556.9	585.0	614.1	640.5	661.5
52.5°	457.9	463.4	471.1	478.8	491.0	505.9	526.1	551.1	579.8	598.7	616.1
55°	418.7	421.5	430.3	438.1	449.6	460.6	480.9	503.0	520.6	534.9	549.2
57.5°	378.8	382.5	387.6	394.5	406.0	418.9	433.2	452.7	463.0	470.3	481.5
60°	353.3	354.4	357.7	365.9	374.7	386.3	402.8	416.5	424.3	430.3	439.7
62.5°	325.1	325.3	330.8	336.9	343.5	356.0	369.3	380.5	386.9	389.8	398.8
65°	285.6	284.5	287.8	292.8	300.4	308.7	320.2	330.2	329.6	332.9	338.4
67.5°	245.2	244.1	244.1	248.8	255.1	262.5	270.4	276.1	276.2	280.6	283.4
70°	217.9	214.6	216.8	220.7	223.4	229.5	238.3	240.5	241.0	243.2	246.0
72.5°	189.7	188.7	190.4	192.1	194.0	198.7	206.1	207.5	207.6	208.9	213.4
75°	150.7	149.7	148.5	150.3	152.5	155.7	158.5	160.7	160.1	160.7	164.0
77.5°	113.0	110.0	109.4	110.3	110.8	112.8	115.7	115.4	116.0	115.9	119.6
80°	89.7	85.3	84.7	84.7	85.3	86.4	87.5	88.6	86.9	88.6	89.7
82.5°	66.0	63.3	63.2	62.7	62.9	63.0	63.8	64.4	64.1	64.8	65.5
85°	36.3	35.2	33.6	34.7	34.1	32.4	33.6	31.9	31.4	31.9	32.4
87.5°	16.0	16.1	14.9	14.6	13.9	13.9	12.7	11.9	11.1	11.2	12.1
90°	18.1	17.0	15.2	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1
92.5°	42.2	40.6	38.6	36.6	34.6	32.5	30.8	29.5	28.2	26.9	25.6
95°	83.1	81.4	79.1	76.7	74.4	72.1	70.6	70.1	69.7	69.2	68.7
97.5°	131.2	129.6	126.5	123.2	119.9	116.7	115.0	114.8	114.6	114.4	114.2
100°	164.0	161.8	158.7	155.7	152.6	149.6	148.1	148.1	148.1	148.1	148.1
102.5°	198.0	195.7	194.1	192.6	191.0	189.5	188.2	187.3	186.3	185.4	184.4
105°	254.2	252.7	251.4	250.0	248.5	247.1	245.8	244.7	243.4	242.3	241.2
107.5°	314.6	313.9	312.8	311.7	310.6	309.6	308.4	307.3	306.1	304.9	303.7
110°	356.0	355.3	354.7	353.9	353.3	352.5	351.6	350.4	349.3	348.1	346.9



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	397.9	397.6	396.7	395.8	394.9	394.1	393.3	392.7	392.1	391.5	390.9
115°	461.9	462.2	461.7	461.2	460.7	460.3	459.6	458.6	457.7	456.7	455.8
117.5°	525.0	524.8	524.3	523.9	523.5	523.1	522.7	522.2	521.8	521.4	521.0
120°	567.9	567.9	567.7	567.4	567.2	567.0	566.3	565.1	563.9	562.7	561.6
122.5°	610.0	610.3	609.6	609.0	608.4	607.8	607.2	606.8	606.4	606.0	605.6
125°	672.1	672.6	672.4	672.1	671.9	671.6	670.8	669.4	668.1	666.6	665.2
127.5°	733.3	733.5	733.3	733.0	732.7	732.4	731.9	731.1	730.3	729.4	728.6
130°	773.9	774.1	773.6	773.2	772.7	772.3	771.4	770.3	769.1	767.9	766.7
132.5°	812.9	813.1	813.2	813.3	813.3	813.4	812.5	810.6	808.7	806.7	804.8
135°	872.5	872.5	872.3	872.0	871.8	871.6	870.7	869.4	867.9	866.5	865.1
137.5°	930.5	930.3	929.8	929.2	928.7	928.1	927.2	925.9	924.5	923.2	921.8
140°	967.1	966.6	965.9	965.2	964.5	963.8	962.9	961.7	960.5	959.4	958.1
142.5°	1003.3	1003.0	1002.1	1001.2	1000.3	999.4	998.5	997.5	996.5	995.6	994.6
145°	1055.5	1055.5	1054.8	1054.0	1053.4	1052.6	1051.8	1050.8	1049.9	1049.0	1048.1
147.5°	1103.0	1102.4	1101.9	1101.3	1100.7	1100.2	1099.6	1099.1	1098.6	1098.0	1097.6
150°	1133.8	1133.8	1132.8	1131.9	1130.9	1129.9	1129.6	1129.8	1130.1	1130.3	1130.6
152.5°	1161.4	1160.8	1160.4	1160.0	1159.7	1159.3	1158.9	1158.6	1158.3	1158.0	1157.6
155°	1201.3	1200.4	1200.1	1199.9	1199.6	1199.4	1199.3	1199.3	1199.3	1199.3	1199.3
157.5°	1236.2	1235.3	1235.0	1234.8	1234.5	1234.3	1234.4	1234.9	1235.5	1236.0	1236.5
160°	1257.4	1256.4	1256.1	1256.0	1255.7	1255.5	1255.7	1256.4	1257.1	1257.8	1258.5
162.5°	1277.0	1275.9	1275.8	1275.8	1275.7	1275.7	1275.9	1276.4	1276.9	1277.5	1278.0
165°	1303.9	1302.9	1302.7	1302.4	1302.2	1302.0	1302.1	1302.6	1303.0	1303.5	1304.0
167.5°	1323.1	1321.8	1321.8	1321.8	1321.8	1321.8	1322.3	1323.1	1324.1	1325.0	1326.0
170°	1335.1	1333.6	1333.6	1333.6	1333.6	1333.6	1334.1	1335.1	1335.9	1336.9	1337.8
172.5°	1343.5	1342.1	1342.1	1342.1	1342.1	1342.1	1342.6	1343.5	1344.4	1345.3	1346.3
175°	1353.0	1351.6	1351.6	1351.6	1351.6	1351.6	1352.1	1353.0	1354.0	1354.9	1355.8
177.5°	1357.6	1356.4	1356.7	1356.8	1357.0	1357.2	1357.6	1358.5	1359.2	1359.9	1360.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1303.5	1309.7	1313.6	1321.1	1327.3	1330.8	1333.9	1336.5	1339.6	1342.2	1349.7
5°	1311.9	1326.2	1338.3	1357.0	1374.1	1387.3	1401.6	1414.2	1424.7	1439.6	1451.1
7.5°	1308.2	1333.7	1360.3	1389.3	1418.9	1446.3	1471.7	1495.3	1516.8	1542.8	1565.5
10°	1304.7	1339.4	1373.5	1412.6	1452.8	1486.9	1518.8	1551.3	1574.9	1607.9	1636.0
12.5°	1302.1	1342.9	1384.1	1431.1	1475.2	1523.4	1565.9	1589.6	1625.5	1652.0	1685.3
15°	1290.9	1344.9	1401.6	1454.4	1517.1	1561.7	1599.1	1645.4	1678.9	1712.5	1748.8
17.5°	1271.1	1332.1	1395.5	1464.8	1524.9	1572.8	1621.1	1665.6	1705.7	1750.7	1795.9
20°	1261.8	1322.9	1395.5	1466.5	1525.4	1575.5	1625.0	1674.0	1718.0	1775.8	1828.1
22.5°	1242.4	1316.3	1383.2	1452.5	1513.0	1567.6	1623.7	1679.3	1737.8	1803.0	1868.6
25°	1207.9	1282.7	1353.7	1422.0	1483.0	1551.3	1611.3	1685.5	1760.4	1846.7	1928.2
27.5°	1172.0	1243.7	1308.7	1374.6	1445.9	1523.1	1600.9	1685.2	1783.1	1892.2	2007.1
30°	1143.0	1210.6	1273.9	1341.6	1415.8	1502.8	1588.1	1688.2	1801.6	1924.4	2060.8
32.5°	1109.1	1171.4	1233.0	1304.6	1385.5	1477.3	1576.7	1686.5	1822.8	1962.2	2102.7
35°	1051.1	1103.3	1166.6	1243.1	1334.5	1439.6	1554.5	1684.4	1840.7	2000.8	2119.1
37.5°	982.3	1030.9	1097.6	1181.5	1277.2	1390.0	1526.5	1680.6	1846.6	1974.2	2012.4
40°	936.0	981.1	1050.5	1137.4	1235.4	1354.8	1504.5	1667.4	1828.1	1909.5	1878.1
42.5°	886.7	934.1	1001.6	1087.7	1193.1	1323.1	1476.8	1639.6	1774.3	1805.2	1696.7
45°	808.9	857.9	924.5	1011.5	1124.8	1265.7	1425.8	1573.9	1651.4	1595.9	1428.0
47.5°	736.6	782.5	844.2	933.9	1050.9	1196.6	1350.9	1468.9	1475.1	1342.5	1163.2
50°	687.3	729.7	791.9	881.6	997.7	1145.2	1284.3	1377.4	1335.5	1185.3	1013.1
52.5°	638.9	680.4	741.7	830.5	945.3	1080.4	1210.0	1275.2	1196.5	1042.3	895.1
55°	569.0	605.3	665.3	747.3	856.2	981.7	1091.8	1114.4	1011.9	860.1	740.7
57.5°	500.8	534.7	589.2	664.7	764.3	875.5	961.6	956.8	848.6	718.2	623.5
60°	454.5	487.5	536.0	609.7	700.5	796.3	870.0	852.4	745.1	632.8	553.0
62.5°	413.2	442.6	488.4	552.9	635.8	724.5	785.1	759.0	654.0	555.8	492.8
65°	352.2	376.9	416.0	471.1	539.8	613.0	659.8	626.2	536.5	460.1	409.4
67.5°	294.0	313.8	346.6	390.4	449.1	507.9	536.4	502.6	430.9	375.0	337.5
70°	257.0	274.6	299.9	339.0	390.1	439.7	461.1	430.9	369.2	321.4	294.4
72.5°	220.0	234.6	256.7	291.9	332.9	375.9	394.7	365.7	315.1	274.7	249.5
75°	170.1	179.9	195.3	219.6	252.0	286.2	296.6	271.3	238.8	208.6	192.1
77.5°	121.7	130.1	141.8	157.0	180.0	201.7	210.8	196.2	171.1	152.0	138.4
80°	93.5	97.9	107.9	120.5	138.7	152.5	158.5	149.1	131.5	117.2	106.7
82.5°	66.7	71.1	77.0	87.5	99.1	108.4	114.9	108.6	95.9	84.6	78.6
85°	32.4	35.2	38.5	42.9	51.7	57.2	56.7	52.8	47.9	43.5	40.2
87.5°	12.1	12.9	14.5	17.1	18.8	20.9	22.1	21.5	20.1	19.0	17.9
90°	2.9	4.8	6.7	8.6	10.4	12.0	13.6	15.2	17.0	18.1	19.2
92.5°	26.9	28.2	29.5	30.8	32.5	34.6	36.6	38.6	40.6	42.2	43.7
95°	69.2	69.7	70.1	70.6	72.1	74.4	76.7	79.1	81.4	83.1	84.7
97.5°	114.4	114.6	114.8	115.0	116.7	119.9	123.2	126.5	129.6	131.2	132.7
100°	148.1	148.1	148.1	148.1	149.6	152.6	155.7	158.7	161.8	164.0	166.1
102.5°	185.4	186.3	187.3	188.2	189.5	191.0	192.6	194.1	195.7	198.0	200.2
105°	242.3	243.4	244.7	245.8	247.1	248.5	250.0	251.4	252.7	254.2	255.6
107.5°	304.9	306.1	307.3	308.4	309.6	310.6	311.7	312.8	313.9	314.6	315.3
110°	348.1	349.3	350.4	351.6	352.5	353.3	353.9	354.7	355.3	356.0	356.8



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	391.5	392.1	392.7	393.3	394.1	394.9	395.8	396.7	397.6	397.9	398.3
115°	456.7	457.7	458.6	459.6	460.3	460.7	461.2	461.7	462.2	461.9	461.7
117.5°	521.4	521.8	522.2	522.7	523.1	523.5	523.9	524.3	524.8	525.0	525.1
120°	562.7	563.9	565.1	566.3	567.0	567.2	567.4	567.7	567.9	567.9	567.9
122.5°	606.0	606.4	606.8	607.2	607.8	608.4	609.0	609.6	610.3	610.0	609.8
125°	666.6	668.1	669.4	670.8	671.6	671.9	672.1	672.4	672.6	672.1	671.6
127.5°	729.4	730.3	731.1	731.9	732.4	732.7	733.0	733.3	733.5	733.3	733.0
130°	767.9	769.1	770.3	771.4	772.3	772.7	773.2	773.6	774.1	773.9	773.6
132.5°	806.7	808.7	810.6	812.5	813.4	813.3	813.3	813.2	813.1	812.9	812.6
135°	866.5	867.9	869.4	870.7	871.6	871.8	872.0	872.3	872.5	872.5	872.5
137.5°	923.2	924.5	925.9	927.2	928.1	928.7	929.2	929.8	930.3	930.5	930.8
140°	959.4	960.5	961.7	962.9	963.8	964.5	965.2	965.9	966.6	967.1	967.6
142.5°	995.6	996.5	997.5	998.5	999.4	1000.3	1001.2	1002.1	1003.0	1003.3	1003.6
145°	1049.0	1049.9	1050.8	1051.8	1052.6	1053.4	1054.0	1054.8	1055.5	1055.5	1055.5
147.5°	1098.0	1098.6	1099.1	1099.6	1100.2	1100.7	1101.3	1101.9	1102.4	1103.0	1103.5
150°	1130.3	1130.1	1129.8	1129.6	1129.9	1130.9	1131.9	1132.8	1133.8	1133.8	1133.8
152.5°	1158.0	1158.3	1158.6	1158.9	1159.3	1159.7	1160.0	1160.4	1160.8	1161.4	1161.9
155°	1199.3	1199.3	1199.3	1199.3	1199.4	1199.6	1199.9	1200.1	1200.4	1201.3	1202.2
157.5°	1236.0	1235.5	1234.9	1234.4	1234.3	1234.5	1234.8	1235.0	1235.3	1236.2	1237.1
160°	1257.8	1257.1	1256.4	1255.7	1255.5	1255.7	1256.0	1256.1	1256.4	1257.4	1258.3
162.5°	1277.5	1276.9	1276.4	1275.9	1275.7	1275.7	1275.8	1275.8	1275.9	1277.0	1278.1
165°	1303.5	1303.0	1302.6	1302.1	1302.0	1302.2	1302.4	1302.7	1302.9	1303.9	1304.8
167.5°	1325.0	1324.1	1323.1	1322.3	1321.8	1321.8	1321.8	1321.8	1321.8	1323.1	1324.6
170°	1336.9	1335.9	1335.1	1334.1	1333.6	1333.6	1333.6	1333.6	1333.6	1335.1	1336.4
172.5°	1345.3	1344.4	1343.5	1342.6	1342.1	1342.1	1342.1	1342.1	1342.1	1343.5	1344.9
175°	1354.9	1354.0	1353.0	1352.1	1351.6	1351.6	1351.6	1351.6	1351.6	1353.0	1354.4
177.5°	1359.9	1359.2	1358.5	1357.6	1357.2	1357.0	1356.8	1356.7	1356.4	1357.6	1358.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1355.9	1359.4	1366.9	1364.2	1367.8	1369.5	1371.3
5°	1465.4	1483.0	1490.7	1489.6	1501.2	1498.4	1495.7
7.5°	1589.1	1607.6	1618.0	1630.8	1638.3	1638.8	1645.4
10°	1659.1	1683.3	1693.2	1707.0	1715.8	1720.8	1720.2
12.5°	1712.9	1731.8	1754.0	1760.7	1772.6	1778.8	1776.5
15°	1777.4	1807.7	1830.8	1842.3	1857.3	1861.7	1867.7
17.5°	1835.1	1875.7	1902.7	1938.5	1952.1	1960.3	1955.5
20°	1878.7	1932.1	1959.0	2002.0	2025.6	2038.2	2033.8
22.5°	1930.2	1987.9	2037.8	2075.0	2111.0	2128.1	2131.6
25°	2018.4	2097.7	2170.9	2219.9	2264.4	2274.8	2298.0
27.5°	2117.1	2210.5	2288.8	2340.2	2371.3	2383.0	2390.2
30°	2179.1	2272.2	2331.0	2364.0	2373.9	2372.8	2371.7
32.5°	2209.5	2267.8	2279.1	2269.8	2247.1	2228.0	2208.0
35°	2166.5	2123.0	2058.1	1974.4	1912.8	1850.6	1844.5
37.5°	1948.5	1809.5	1701.4	1580.6	1511.0	1467.9	1438.3
40°	1743.3	1585.3	1454.4	1352.6	1281.7	1253.5	1226.0
42.5°	1520.5	1369.7	1253.7	1168.6	1115.2	1084.1	1062.3
45°	1235.4	1102.2	1011.5	949.8	907.4	883.2	869.4
47.5°	1012.3	913.8	836.7	792.2	763.0	744.1	744.2
50°	892.6	798.5	747.3	712.1	686.7	671.9	674.7
52.5°	786.4	716.2	672.5	642.9	624.3	615.1	614.8
55°	657.6	607.0	578.4	556.9	544.2	533.8	536.0
57.5°	562.5	519.8	500.7	482.8	474.0	469.9	463.7
60°	503.5	470.5	454.0	439.7	430.9	427.5	421.5
62.5°	451.1	425.2	409.1	397.4	389.5	388.4	383.7
65°	379.1	359.3	345.0	339.5	331.3	329.1	329.1
67.5°	312.6	298.4	287.2	282.2	278.6	279.1	276.5
70°	270.8	259.2	252.0	246.5	243.8	244.3	242.1
72.5°	236.8	224.0	217.7	214.4	210.8	212.2	211.3
75°	179.4	172.8	169.5	166.2	164.0	162.9	161.8
77.5°	131.8	125.9	123.4	121.5	121.8	119.2	121.3
80°	101.8	96.9	95.2	92.5	91.9	91.9	91.3
82.5°	74.5	71.7	70.5	68.2	67.3	68.2	66.7
85°	38.5	36.3	35.8	35.8	34.7	33.6	36.3
87.5°	18.2	16.6	16.9	16.6	16.7	16.4	15.7
90°	20.5	21.6	22.6	23.2	24.0	24.7	25.4
92.5°	45.2	46.8	47.9	48.3	48.9	49.4	49.9
95°	86.3	88.1	89.0	89.5	90.0	90.5	91.0
97.5°	134.3	135.8	136.8	137.1	137.4	137.6	137.9
100°	168.1	170.2	171.5	172.0	172.5	173.0	173.4
102.5°	202.5	204.9	206.4	207.0	207.7	208.3	209.0
105°	257.0	258.4	259.4	260.2	260.9	261.5	262.3
107.5°	316.0	316.7	317.1	317.0	316.9	316.9	316.8
110°	357.4	358.2	358.4	358.2	357.9	357.7	357.4



TEST NUMBER: P333449-930

CATALOG NUMBER: S125DIW-S1090D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	398.6	398.9	398.9	398.5	398.1	397.6	397.2
115°	461.5	461.2	461.0	460.7	460.5	460.3	460.1
117.5°	525.3	525.5	525.1	524.2	523.3	522.4	521.4
120°	567.9	567.9	567.4	566.5	565.6	564.6	563.7
122.5°	609.7	609.4	609.0	608.2	607.5	606.7	606.0
125°	671.2	670.7	670.4	670.2	669.9	669.7	669.4
127.5°	732.8	732.6	732.2	731.8	731.3	730.8	730.3
130°	773.5	773.2	772.8	772.4	771.9	771.4	770.9
132.5°	812.4	812.1	811.7	811.1	810.3	809.7	809.0
135°	872.5	872.5	872.0	871.1	870.2	869.2	868.3
137.5°	931.1	931.4	930.9	929.8	928.5	927.4	926.3
140°	968.0	968.5	968.2	966.9	965.8	964.7	963.4
142.5°	1003.9	1004.1	1003.7	1002.5	1001.4	1000.1	999.0
145°	1055.5	1055.5	1055.1	1054.4	1053.7	1053.0	1052.3
147.5°	1104.1	1104.6	1104.2	1102.5	1101.0	1099.3	1097.8
150°	1133.8	1133.8	1133.5	1133.0	1132.5	1132.0	1131.6
152.5°	1162.5	1163.0	1162.9	1162.0	1161.2	1160.3	1159.5
155°	1203.1	1204.1	1204.0	1202.8	1201.7	1200.4	1199.3
157.5°	1238.0	1239.0	1238.7	1237.1	1235.6	1234.0	1232.5
160°	1259.2	1260.1	1260.0	1258.9	1257.7	1256.5	1255.3
162.5°	1279.2	1280.3	1280.3	1278.9	1277.5	1276.2	1274.8
165°	1305.8	1306.7	1306.4	1305.0	1303.7	1302.2	1300.8
167.5°	1326.0	1327.4	1327.4	1325.9	1324.5	1323.0	1321.5
170°	1337.8	1339.2	1339.1	1337.5	1335.9	1334.2	1332.5
172.5°	1346.3	1347.7	1347.7	1346.2	1344.8	1343.3	1341.8
175°	1355.8	1357.2	1357.1	1355.4	1353.8	1352.2	1350.5
177.5°	1359.8	1361.0	1360.9	1359.5	1358.2	1356.9	1355.6
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0

(END OF REPORT)