

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333489-930

Luminaire Tested: **S125DIW-S1270D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333489-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1560U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8593.4 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333489-930

CATALOG NUMBER: S125DIW-S1270D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333489-930

CATALOG NUMBER: S125DIW-S1270D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	82	79	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10377	10377	10377
5°	10400	10301	10367
10°	10337	10228	10287
15°	10224	10105	10148
20°	10065	9933	9950
25°	9892	9728	9719
30°	9679	9508	9461
35°	9451	9270	9140
40°	9217	9012	8884
45°	8963	8777	8603
50°	8685	8493	8238
55°	8417	8173	7944
60°	8094	7848	7569
65°	7713	7459	7207
70°	7345	7009	6770
75°	6692	6470	6248
80°	5954	5861	5720
85°	5187	5276	4987



TEST NUMBER: P333489-930

CATALOG NUMBER: S125DIW-S1270D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	1.8
10°-20°	427.9	5.0
20°-30°	631.9	7.4
30°-40°	737.3	8.6
40°-50°	740.5	8.6
50°-60°	650.0	7.6
60°-70°	484.3	5.6
70°-80°	276.9	3.2
80°-90°	84.0	1.0
90°-100°	105.8	1.2
100°-110°	312.5	3.6
110°-120°	529.3	6.2
120°-130°	696.6	8.1
130°-140°	780.6	9.1
140°-150°	765.0	8.9
150°-160°	642.6	7.5
160°-170°	427.1	5.0
170°-180°	149.5	1.7
0°-30°	1211.3	14.1
0°-40°	1948.6	22.7
0°-60°	3339.1	38.9
0°-90°	4184.4	48.7
90°-120°	947.6	11.0
90°-150°	3189.8	37.1
90°-180°	4409.0	51.3
0°-180°	8593.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1607	1607	1607	1607	1607	
5°	1604	1601	1589	1600	1599	152
15°	1529	1525	1511	1517	1518	431
25°	1388	1381	1365	1367	1364	638
35°	1199	1193	1176	1169	1159	749
45°	981	976	961	946	942	756
55°	748	743	726	715	706	667
65°	505	501	488	477	472	501
75°	268	266	259	255	250	286
85°	70	71	71	70	67	78
90°	1	11	20	26	30	8
95°	80	83	95	103	106	85
105°	280	287	294	301	305	299
115°	530	535	537	536	535	524
125°	773	780	782	780	778	692
135°	1006	1013	1014	1014	1010	775
145°	1218	1223	1227	1227	1223	761
155°	1394	1394	1396	1400	1394	642
165°	1516	1514	1515	1519	1512	428
175°	1576	1572	1571	1578	1570	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333489-930

CATALOG NUMBER: S125DIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1610.8	1610.1	1609.5	1608.7	1608.1	1606.6	1604.3	1602.1	1599.9	1597.6	1599.9
5°	1604.2	1603.6	1603.0	1602.5	1601.9	1600.3	1597.4	1594.6	1591.8	1588.9	1591.5
7.5°	1589.4	1588.9	1588.3	1587.7	1587.1	1585.3	1582.3	1579.2	1576.1	1573.0	1575.4
10°	1576.2	1575.6	1575.1	1574.5	1573.9	1572.1	1569.0	1565.9	1562.8	1559.7	1562.0
12.5°	1559.9	1558.9	1558.0	1556.9	1555.9	1554.0	1551.0	1548.2	1545.3	1542.4	1544.3
15°	1529.2	1528.4	1527.5	1526.6	1525.8	1523.8	1520.7	1517.6	1514.5	1511.4	1512.8
17.5°	1493.9	1492.6	1491.3	1490.1	1488.9	1486.6	1483.4	1480.2	1477.0	1473.7	1475.5
20°	1464.4	1463.8	1463.2	1462.6	1462.1	1460.0	1456.3	1452.6	1448.9	1445.3	1447.2
22.5°	1434.8	1433.9	1432.8	1431.8	1430.8	1428.6	1425.1	1421.7	1418.2	1414.8	1416.1
25°	1388.1	1386.7	1385.3	1383.9	1382.4	1379.9	1376.2	1372.6	1368.9	1365.2	1365.8
27.5°	1333.4	1332.6	1331.7	1330.9	1330.1	1327.7	1324.0	1320.1	1316.4	1312.6	1312.7
30°	1297.9	1297.0	1296.2	1295.3	1294.5	1291.9	1287.7	1283.4	1279.2	1275.0	1274.4
32.5°	1259.2	1257.9	1256.6	1255.3	1254.0	1251.5	1247.7	1243.9	1240.1	1236.3	1235.3
35°	1198.7	1197.6	1196.5	1195.3	1194.2	1191.6	1187.6	1183.7	1179.7	1175.8	1174.4
37.5°	1135.9	1134.5	1133.1	1131.6	1130.2	1127.6	1124.0	1120.2	1116.5	1112.8	1110.7
40°	1093.2	1091.8	1090.4	1088.9	1087.5	1084.8	1080.9	1076.9	1073.0	1069.0	1066.5
42.5°	1047.4	1046.3	1045.1	1043.8	1042.7	1040.1	1036.2	1032.2	1028.3	1024.3	1022.0
45°	981.3	980.2	979.1	978.0	976.8	974.5	971.2	967.8	964.4	961.0	957.6
47.5°	910.1	910.2	910.3	910.3	910.4	908.3	904.3	900.3	896.2	892.1	888.7
50°	864.4	863.6	862.7	861.9	861.0	858.8	855.5	852.1	848.7	845.3	841.6
52.5°	817.6	817.0	816.4	815.7	815.1	813.0	809.3	805.8	802.2	798.5	795.3
55°	747.5	746.6	745.8	744.9	744.0	741.7	737.7	733.8	729.8	725.9	723.3
57.5°	673.4	673.0	672.5	672.1	671.6	669.8	666.4	663.1	659.7	656.4	653.1
60°	626.6	625.6	624.4	623.3	622.2	620.0	616.9	613.8	610.7	607.6	604.8
62.5°	577.9	577.0	576.1	575.1	574.2	572.5	569.8	567.1	564.5	561.8	558.8
65°	504.7	504.1	503.5	503.0	502.4	500.5	497.4	494.3	491.2	488.1	485.6
67.5°	433.7	432.5	431.4	430.2	429.0	427.2	424.9	422.6	420.3	417.9	415.8
70°	389.0	387.6	386.1	384.7	383.4	381.3	378.8	376.3	373.7	371.2	369.5
72.5°	340.1	339.2	338.3	337.3	336.3	335.0	333.4	331.7	330.1	328.5	326.5
75°	268.2	267.7	267.1	266.5	266.0	265.0	263.6	262.1	260.7	259.3	258.4
77.5°	201.9	201.6	201.4	201.2	201.0	200.5	199.7	198.9	198.0	197.3	196.8
80°	160.1	160.1	160.1	160.1	160.1	159.9	159.3	158.7	158.2	157.6	157.4
82.5°	123.5	123.1	122.6	122.2	121.7	121.5	121.3	121.2	121.2	121.0	120.5
85°	70.0	70.2	70.4	70.8	71.0	71.2	71.2	71.2	71.2	71.2	70.9
87.5°	27.7	28.1	28.6	29.0	29.4	29.8	29.9	30.1	30.2	30.4	30.7
90°	1.2	3.4	5.6	7.8	9.9	12.0	13.9	15.8	17.8	19.6	21.0
92.5°	29.8	31.3	32.9	34.3	35.9	37.8	40.2	42.5	44.8	47.2	49.0
95°	79.9	80.5	81.0	81.5	82.1	83.7	86.5	89.2	92.0	94.7	96.6
97.5°	132.8	133.0	133.2	133.5	133.7	135.7	139.4	143.2	147.0	150.7	152.5
100°	172.1	172.1	172.1	172.1	172.1	173.9	177.5	181.0	184.6	188.1	190.6
102.5°	214.4	215.6	216.6	217.7	218.8	220.3	222.1	223.9	225.7	227.5	230.2
105°	280.4	281.7	283.1	284.5	285.8	287.3	288.9	290.6	292.2	293.9	295.5
107.5°	353.1	354.5	355.9	357.3	358.6	360.0	361.2	362.4	363.7	364.9	365.7
110°	403.3	404.7	406.0	407.4	408.8	409.9	410.7	411.5	412.3	413.1	413.9



TEST NUMBER: P333489-930

CATALOG NUMBER: S125DIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.4	455.2	455.9	456.6	457.3	458.2	459.2	460.2	461.3	462.4	462.7
115°	529.9	531.1	532.1	533.2	534.3	535.2	535.7	536.2	536.8	537.4	537.0
117.5°	605.7	606.2	606.7	607.2	607.6	608.1	608.6	609.1	609.6	610.2	610.3
120°	652.9	654.3	655.7	657.0	658.4	659.2	659.5	659.7	660.0	660.3	660.3
122.5°	704.1	704.6	705.1	705.6	706.0	706.6	707.4	708.1	708.7	709.5	709.2
125°	773.4	775.0	776.7	778.4	780.0	781.0	781.2	781.5	781.8	782.0	781.5
127.5°	847.2	848.2	849.1	849.9	850.9	851.6	851.9	852.2	852.6	852.9	852.6
130°	891.4	892.8	894.2	895.5	896.9	897.9	898.5	898.9	899.5	900.1	899.8
132.5°	935.7	938.0	940.2	942.5	944.7	945.7	945.7	945.5	945.4	945.3	945.0
135°	1005.8	1007.5	1009.1	1010.7	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4
137.5°	1071.7	1073.3	1074.9	1076.4	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9
140°	1114.0	1115.4	1116.7	1118.1	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4
142.5°	1156.3	1157.5	1158.6	1159.8	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4
145°	1218.5	1219.6	1220.7	1221.8	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1
147.5°	1276.1	1276.7	1277.2	1277.9	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4
150°	1314.4	1314.2	1313.9	1313.6	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2
152.5°	1345.9	1346.3	1346.7	1347.0	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3
155°	1394.4	1394.4	1394.4	1394.4	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7
157.5°	1437.6	1437.0	1436.5	1435.8	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3
160°	1463.2	1462.4	1461.6	1460.8	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8
162.5°	1485.9	1485.2	1484.7	1484.1	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7
165°	1516.1	1515.6	1515.0	1514.5	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0
167.5°	1541.6	1540.6	1539.5	1538.4	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4
170°	1555.4	1554.4	1553.2	1552.2	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2
172.5°	1565.3	1564.2	1563.1	1562.0	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0
175°	1576.4	1575.2	1574.2	1573.0	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0
177.5°	1582.0	1581.1	1580.3	1579.4	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333489-930

CATALOG NUMBER: S125DIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1602.1	1604.3	1606.6	1607.6	1607.4	1607.2	1607.0	1606.7
5°	1594.0	1596.6	1599.1	1600.3	1599.9	1599.7	1599.4	1599.1
7.5°	1577.8	1580.4	1582.8	1584.0	1583.7	1583.4	1583.1	1582.8
10°	1564.2	1566.5	1568.7	1569.7	1569.5	1569.1	1568.9	1568.6
12.5°	1546.1	1547.8	1549.6	1550.5	1550.5	1550.4	1550.4	1550.3
15°	1514.3	1515.6	1517.0	1517.8	1517.8	1517.8	1517.8	1517.8
17.5°	1477.2	1479.0	1480.7	1480.9	1479.5	1478.1	1476.7	1475.3
20°	1449.3	1451.2	1453.2	1453.5	1452.0	1450.7	1449.3	1447.8
22.5°	1417.4	1418.7	1420.0	1420.2	1419.2	1418.2	1417.2	1416.3
25°	1366.4	1366.9	1367.5	1367.3	1366.5	1365.6	1364.8	1363.9
27.5°	1312.8	1313.0	1313.0	1312.6	1311.8	1311.0	1310.1	1309.3
30°	1273.8	1273.3	1272.7	1272.0	1271.1	1270.3	1269.4	1268.6
32.5°	1234.3	1233.3	1232.2	1230.9	1229.5	1227.9	1226.4	1224.9
35°	1173.0	1171.6	1170.2	1168.3	1166.0	1163.8	1161.6	1159.3
37.5°	1108.6	1106.5	1104.4	1102.7	1101.4	1100.1	1098.8	1097.5
40°	1064.0	1061.4	1058.8	1057.2	1056.3	1055.5	1054.6	1053.8
42.5°	1019.7	1017.3	1015.0	1013.3	1011.9	1010.6	1009.3	1008.0
45°	954.2	950.8	947.5	945.3	944.4	943.6	942.7	941.9
47.5°	885.2	881.7	878.3	875.6	873.6	871.6	869.7	867.7
50°	838.0	834.3	830.6	827.8	825.8	823.9	821.9	819.9
52.5°	792.1	788.9	785.6	782.9	780.7	778.5	776.3	774.1
55°	720.7	718.2	715.7	713.4	711.4	709.5	707.4	705.5
57.5°	649.9	646.6	643.4	641.2	640.1	639.0	637.9	636.8
60°	601.9	599.2	596.3	593.9	591.9	590.0	588.0	586.0
62.5°	555.7	552.7	549.7	547.4	545.8	544.3	542.7	541.3
65°	483.1	480.5	477.9	476.1	475.0	473.9	472.7	471.6
67.5°	413.7	411.5	409.4	408.0	407.2	406.6	405.9	405.2
70°	367.8	366.1	364.4	363.0	361.8	360.7	359.6	358.5
72.5°	324.7	322.7	320.8	319.3	318.1	317.0	315.8	314.7
75°	257.6	256.7	255.9	254.9	253.8	252.7	251.5	250.4
77.5°	196.2	195.8	195.3	194.6	193.8	193.0	192.2	191.4
80°	157.0	156.8	156.5	156.0	155.5	154.9	154.3	153.8
82.5°	120.0	119.5	119.0	118.7	118.5	118.5	118.3	118.2
85°	70.6	70.4	70.0	69.6	69.1	68.5	67.9	67.3
87.5°	30.9	31.2	31.5	31.5	31.1	30.9	30.6	30.3
90°	22.4	23.8	25.1	26.3	27.1	27.9	28.7	29.5
92.5°	50.8	52.6	54.5	55.6	56.3	56.8	57.4	58.0
95°	98.5	100.4	102.3	103.5	104.1	104.7	105.2	105.7
97.5°	154.3	156.1	157.9	159.1	159.4	159.7	160.0	160.4
100°	193.1	195.5	198.0	199.5	200.0	200.6	201.1	201.6
102.5°	232.8	235.5	238.1	239.9	240.7	241.4	242.2	243.0
105°	297.2	298.8	300.4	301.7	302.5	303.3	304.1	304.9
107.5°	366.6	367.4	368.2	368.6	368.5	368.5	368.4	368.4
110°	414.8	415.6	416.5	416.7	416.5	416.1	415.9	415.6



TEST NUMBER: P333489-930

CATALOG NUMBER: S125DIW-S1270D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	463.1	463.5	463.8	463.8	463.3	462.8	462.4	461.9
115°	536.8	536.5	536.2	536.0	535.7	535.4	535.2	534.9
117.5°	610.6	610.8	611.0	610.6	609.4	608.4	607.3	606.2
120°	660.3	660.3	660.3	659.7	658.7	657.5	656.5	655.4
122.5°	709.1	708.8	708.6	708.1	707.2	706.3	705.4	704.6
125°	781.0	780.4	779.8	779.4	779.2	778.9	778.6	778.4
127.5°	852.3	852.1	851.7	851.3	850.8	850.3	849.7	849.1
130°	899.5	899.3	898.9	898.5	898.1	897.5	896.9	896.4
132.5°	944.8	944.5	944.2	943.7	943.0	942.2	941.4	940.6
135°	1014.4	1014.4	1014.4	1013.9	1012.8	1011.7	1010.6	1009.5
137.5°	1082.2	1082.6	1082.9	1082.4	1081.0	1079.6	1078.2	1076.8
140°	1124.9	1125.5	1126.0	1125.6	1124.3	1122.9	1121.5	1120.1
142.5°	1166.8	1167.1	1167.5	1166.9	1165.6	1164.2	1162.9	1161.5
145°	1227.1	1227.1	1227.1	1226.7	1225.9	1225.1	1224.3	1223.4
147.5°	1283.0	1283.7	1284.3	1283.8	1281.9	1280.0	1278.2	1276.4
150°	1318.2	1318.2	1318.2	1317.8	1317.3	1316.8	1316.2	1315.6
152.5°	1351.0	1351.6	1352.3	1352.1	1351.1	1350.1	1349.2	1348.2
155°	1397.7	1398.9	1400.0	1399.9	1398.5	1397.1	1395.7	1394.4
157.5°	1438.4	1439.5	1440.6	1440.2	1438.4	1436.6	1434.8	1433.0
160°	1463.0	1464.0	1465.2	1465.0	1463.6	1462.2	1460.9	1459.5
162.5°	1486.0	1487.4	1488.7	1488.5	1486.9	1485.3	1483.8	1482.1
165°	1517.0	1518.2	1519.2	1519.0	1517.4	1515.7	1514.1	1512.4
167.5°	1540.0	1541.6	1543.3	1543.3	1541.6	1539.9	1538.2	1536.5
170°	1553.8	1555.4	1557.1	1557.0	1555.0	1553.1	1551.2	1549.3
172.5°	1563.7	1565.3	1566.9	1566.9	1565.2	1563.5	1561.8	1560.2
175°	1574.8	1576.4	1578.0	1577.8	1576.0	1574.0	1572.1	1570.2
177.5°	1579.7	1581.0	1582.3	1582.3	1580.7	1579.2	1577.6	1576.1
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1

(END OF REPORT)