

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333364-930

Luminaire Tested: **S125DIW-S375D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333364-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6340.1 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24	17
2	83	76	70	65	73	67	63	58	51	48	45	36	34	32	22	21	20	14
3	76	67	60	54	67	59	53	49	45	41	38	32	30	27	20	18	17	12
4	69	59	52	46	61	52	46	41	40	36	32	28	26	23	18	16	15	10
5	63	52	45	39	56	47	40	35	36	31	28	25	23	20	16	14	13	9
6	58	47	39	34	51	42	35	30	32	27	24	23	20	18	14	13	11	8
7	54	42	35	29	47	37	31	26	29	24	21	21	18	15	13	11	10	7
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	10	9	6
9	46	34	27	23	41	31	25	20	24	19	16	17	14	12	11	9	8	6
10	43	31	25	20	38	28	22	18	22	17	15	16	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2866	2866	2866	2866
5°	3319	2877	2519	2877
10°	3862	2861	2207	2861
15°	4275	2841	2035	2841
20°	4786	2808	1898	2808
25°	5606	2770	1831	2770
30°	6055	2732	1773	2732
35°	4978	2663	1735	2663
40°	3538	2566	1693	2566
45°	2719	2437	1669	2437
50°	2321	2275	1666	2275
55°	2066	2117	1680	2117
60°	1864	1944	1723	1944
65°	1722	1771	1768	1771
70°	1565	1590	1794	1590
75°	1382	1402	1777	1402
80°	1164	1142	1625	1142
85°	926	823	1312	823



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	0.7
10°-20°	127.2	2.0
20°-30°	206.6	3.3
30°-40°	252.0	4.0
40°-50°	229.2	3.6
50°-60°	182.6	2.9
60°-70°	127.2	2.0
70°-80°	67.8	1.1
80°-90°	20.6	0.3
90°-100°	60.2	0.9
100°-110°	370.8	5.8
110°-120°	672.5	10.6
120°-130°	863.1	13.6
130°-140°	928.3	14.6
140°-150°	871.4	13.7
150°-160°	704.9	11.1
160°-170°	455.9	7.2
170°-180°	157.2	2.5
0°-30°	376.5	5.9
0°-40°	628.5	9.9
0°-60°	1040.3	16.4
0°-90°	1255.9	19.8
90°-120°	1103.5	17.4
90°-150°	3766.2	59.4
90°-180°	5084.0	80.2
0°-180°	6340.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	512	444	388	444	512	52
15°	639	425	304	425	639	183
25°	787	389	257	389	787	359
35°	631	338	220	338	631	386
45°	298	267	183	267	298	238
55°	184	188	149	188	184	165
65°	113	116	116	116	113	112
75°	55	56	71	56	55	60
85°	12	11	18	11	12	15
90°	29	1	29	1	29	13
95°	26	70	26	70	26	21
105°	364	361	364	361	364	330
115°	672	678	672	678	672	668
125°	963	963	963	963	963	857
135°	1197	1202	1197	1202	1197	923
145°	1389	1393	1389	1393	1389	868
155°	1523	1534	1523	1534	1523	702
165°	1610	1619	1610	1619	1610	454
175°	1648	1656	1648	1656	1648	157
180°	1656	1656	1656	1656	1656	



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	469.4	468.9	468.2	467.1	468.0	465.4	464.2	462.1	459.5	458.6	457.5
5°	512.0	513.0	514.0	510.0	510.4	507.7	501.7	496.8	492.8	487.7	484.1
7.5°	563.3	561.1	560.8	558.3	553.9	550.3	544.0	536.0	528.2	519.3	511.9
10°	588.9	589.1	587.4	584.4	579.7	576.3	568.0	560.1	550.5	539.2	531.1
12.5°	608.2	609.0	606.8	602.8	600.5	592.9	586.4	577.0	565.6	556.5	544.2
15°	639.4	637.3	635.9	630.7	626.8	618.9	608.5	598.7	586.3	574.8	563.3
17.5°	669.4	671.2	668.3	663.7	651.3	642.1	628.3	614.8	599.3	583.9	570.2
20°	696.3	697.8	693.5	685.3	670.7	661.5	643.2	625.8	608.0	588.2	573.1
22.5°	729.8	728.6	722.7	710.4	697.7	680.6	660.8	639.7	617.3	594.9	574.9
25°	786.7	778.8	775.2	759.9	743.2	718.1	691.0	660.1	632.3	602.7	577.1
27.5°	818.3	815.8	811.8	801.2	783.6	756.8	724.8	687.1	647.8	610.5	576.9
30°	812.0	812.4	812.7	809.3	798.0	777.9	746.0	705.6	658.8	616.8	578.0
32.5°	755.9	762.7	769.3	777.1	780.2	776.3	756.4	719.8	671.7	624.0	577.4
35°	631.4	633.6	654.8	676.0	704.6	726.8	741.7	725.5	685.0	630.1	576.7
37.5°	492.4	502.6	517.3	541.1	582.4	619.5	667.1	688.9	675.9	632.2	575.4
40°	419.7	429.2	438.8	463.1	497.9	542.7	596.8	642.9	653.7	625.8	570.8
42.5°	363.7	371.1	381.8	400.1	429.2	468.9	520.6	580.9	618.0	607.5	561.3
45°	297.7	302.4	310.6	325.1	346.3	377.3	422.9	488.9	546.3	565.3	538.8
47.5°	254.8	254.8	261.2	271.2	286.4	312.8	346.6	398.2	459.6	505.0	502.9
50°	231.0	230.0	235.1	243.8	255.8	273.4	305.6	346.8	405.8	457.2	471.6
52.5°	210.4	210.6	213.7	220.1	230.2	245.2	269.2	306.5	356.8	409.6	436.6
55°	183.5	182.7	186.3	190.6	198.0	207.8	225.1	253.6	294.5	346.4	381.5
57.5°	158.7	160.9	162.2	165.3	171.4	178.0	192.6	213.4	245.9	290.5	327.5
60°	144.3	146.3	147.5	150.5	155.4	161.1	172.4	189.3	216.6	255.1	291.8
62.5°	131.3	133.0	133.4	136.1	140.1	145.5	154.4	168.7	190.3	223.9	259.8
65°	112.7	112.7	113.4	116.3	118.1	123.0	129.8	140.1	157.5	183.7	214.4
67.5°	94.7	95.6	95.4	96.6	98.3	102.2	107.0	115.5	128.4	147.5	172.1
70°	82.9	83.6	83.5	84.4	86.3	88.7	92.7	100.8	110.0	126.4	147.5
72.5°	72.3	72.6	72.2	73.4	74.5	76.6	81.1	85.4	94.0	107.9	125.2
75°	55.4	55.8	56.2	56.9	58.0	59.2	61.4	65.7	71.4	81.8	92.9
77.5°	41.5	40.8	41.7	41.6	42.2	43.1	45.1	47.4	52.0	58.6	67.2
80°	31.3	31.5	31.5	31.6	32.6	33.2	34.8	36.5	40.1	45.0	51.0
82.5°	22.8	23.3	23.0	23.4	24.1	24.5	25.5	26.9	28.9	32.9	37.2
85°	12.5	11.5	11.9	12.2	12.2	12.5	13.2	13.8	14.9	16.4	18.1
87.5°	9.5	9.6	9.6	9.5	9.5	9.2	9.5	9.3	9.5	9.6	9.9
90°	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3	21.0	19.6	17.7
92.5°	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3	21.0	19.6	17.9
95°	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3	21.0	19.6	30.0
97.5°	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0	52.7	60.4	80.9
100°	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2	172.9	213.5	212.5
102.5°	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1	264.8	272.5	271.8
105°	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1	463.0	462.9	462.4
110°	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1	526.9	527.7	527.2



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5	589.5	590.6	590.3
115°	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7	683.7	684.9	684.6
117.5°	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6	774.9	776.4	775.3
120°	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3	832.8	833.3	832.5
122.5°	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2	888.8	889.3	888.9
125°	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9	970.9	972.0	972.0
127.5°	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5	1045.1	1045.7	1045.9
130°	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2	1094.0	1094.8	1094.5
132.5°	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6	1138.8	1139.0	1139.5
135°	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3	1205.9	1206.5	1207.0
137.5°	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5	1267.5	1267.3	1267.8
140°	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7	1305.2	1304.6	1304.9
142.5°	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1	1343.0	1343.0	1342.6
145°	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0	1395.7	1395.5	1395.5
147.5°	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3	1441.0	1440.6	1440.3
150°	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1	1469.7	1469.1	1468.5
152.5°	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7	1495.2	1494.6	1494.1
155°	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9	1530.1	1529.3	1528.7
157.5°	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9	1559.1	1558.2	1558.1
160°	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0	1577.0	1575.9	1575.6
162.5°	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6	1593.1	1591.5	1591.3
165°	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9	1614.3	1612.7	1612.4
167.5°	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1	1630.1	1628.2	1627.9
170°	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4	1638.2	1636.0	1635.7
172.5°	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8	1644.9	1642.9	1642.4
175°	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8	1651.7	1649.5	1649.3
177.5°	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8	1655.2	1653.7	1653.4
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	456.6	455.6	454.4	452.2	449.7	448.3	446.3	444.9	442.2	439.9	437.5
5°	479.8	474.9	470.4	464.6	458.2	454.0	449.1	443.7	438.0	432.2	425.7
7.5°	503.9	495.1	485.8	475.6	465.7	456.6	447.8	439.4	431.4	421.7	413.5
10°	519.9	509.0	497.3	483.6	470.2	458.5	446.7	436.3	425.7	414.5	404.5
12.5°	536.1	521.5	505.0	489.9	473.9	459.7	445.8	432.5	419.3	406.8	395.1
15°	547.5	534.7	519.4	497.9	479.8	460.4	442.0	424.9	408.8	394.8	380.2
17.5°	555.0	538.4	522.0	501.5	477.8	456.1	435.1	415.5	397.5	379.8	365.7
20°	556.3	539.3	522.2	502.1	477.8	452.9	431.9	408.5	389.1	370.7	353.4
22.5°	555.9	536.6	518.0	497.3	473.5	450.6	425.3	401.4	380.3	362.3	344.2
25°	551.6	531.1	507.7	486.8	463.4	439.1	413.5	388.7	367.2	346.7	328.7
27.5°	548.0	521.5	495.0	470.6	448.0	425.7	401.2	375.8	352.0	331.2	314.3
30°	543.7	514.5	484.7	459.3	436.1	414.5	391.3	366.4	341.5	321.2	303.1
32.5°	539.8	505.7	474.3	446.6	422.1	401.0	379.7	356.0	331.6	311.0	292.9
35°	532.2	492.8	456.8	425.6	399.4	377.7	359.8	337.8	315.4	295.4	278.1
37.5°	522.6	475.9	437.2	404.5	375.8	352.9	336.3	319.4	297.8	278.6	262.9
40°	515.0	463.8	422.9	389.4	359.6	335.9	320.4	304.4	286.6	268.6	252.1
42.5°	505.6	453.0	408.5	372.3	342.9	319.8	303.5	290.0	274.2	257.5	242.1
45°	488.1	433.3	385.1	346.3	316.5	293.7	277.0	266.8	254.9	239.0	226.1
47.5°	462.4	409.7	359.8	319.8	289.0	267.9	252.2	242.4	234.1	222.3	210.5
50°	439.7	392.1	341.5	301.8	271.1	249.8	235.3	226.4	219.3	210.3	200.2
52.5°	414.3	369.9	323.6	284.3	253.9	232.9	218.7	210.9	205.0	198.5	188.7
55°	373.7	336.1	293.1	255.8	227.8	207.2	194.8	188.0	183.1	178.2	172.2
57.5°	329.2	299.7	261.7	227.6	201.7	183.0	171.5	164.9	161.0	158.5	155.0
60°	297.8	272.6	239.9	208.7	183.5	166.9	155.6	150.5	147.3	145.3	142.6
62.5°	268.7	248.0	217.7	189.3	167.2	151.6	141.5	136.5	133.5	132.4	130.3
65°	225.9	209.9	184.8	161.3	142.4	129.1	120.6	115.9	114.0	112.8	113.0
67.5°	183.6	173.9	153.8	133.7	118.6	107.5	100.6	97.0	96.0	94.6	94.6
70°	157.8	150.5	133.5	116.0	102.6	94.0	88.0	84.2	83.2	82.5	82.3
72.5°	135.1	128.7	114.0	100.0	87.9	80.3	75.3	73.1	71.5	71.1	71.0
75°	101.5	98.0	86.3	75.2	66.9	61.6	58.2	56.2	55.0	54.8	55.0
77.5°	72.2	69.1	61.6	53.7	48.5	44.5	41.7	40.9	39.7	39.7	39.5
80°	54.2	52.2	47.5	41.3	36.9	33.5	32.0	30.7	30.3	29.8	30.3
82.5°	39.3	37.1	33.9	29.9	26.3	24.4	22.8	22.4	22.2	21.9	22.0
85°	19.4	19.6	17.7	14.7	13.2	12.1	11.1	11.1	10.9	10.8	10.9
87.5°	9.8	9.1	8.2	7.3	6.1	5.2	4.6	4.3	4.3	4.6	5.1
90°	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9	17.4	15.8	14.3
95°	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0	69.1	68.3	67.5
97.5°	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0	147.5	149.0	150.5
100°	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0	205.8	206.6	207.4
102.5°	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9	265.9	266.9	268.0
105°	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9	361.9	363.1	364.1
107.5°	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5	460.5	460.5	460.5
110°	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2	586.9	587.5	588.2
115°	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5	678.8	680.2	681.6
117.5°	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0	771.9	771.8	771.8
120°	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9	830.6	830.4	830.1
122.5°	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0	883.9	885.0	886.1
125°	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4	965.3	967.3	969.1
127.5°	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2	1041.6	1043.0	1044.4
130°	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4	1088.8	1090.1	1091.5
132.5°	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5	1136.1	1137.7	1139.3
135°	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5	1203.1	1204.8	1206.5
137.5°	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1	1264.5	1266.0	1267.4
140°	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4	1304.0	1304.5	1305.0
142.5°	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7	1340.0	1340.4	1340.7
145°	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0	1393.5	1394.1	1394.7
147.5°	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7	1439.5	1439.4	1439.3
150°	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1468.5	1468.0	1467.5
152.5°	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5	1496.4	1495.2	1494.0
155°	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1	1532.5	1530.9	1529.3
157.5°	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4	1561.4	1560.4	1559.4
160°	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0	1580.4	1578.7	1577.1
162.5°	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7	1596.1	1594.5	1592.8
165°	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9	1617.2	1615.5	1613.9
167.5°	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5	1632.9	1631.2	1629.5
170°	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4	1641.4	1639.6	1637.6
172.5°	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3	1647.4	1645.4	1643.6
175°	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6	1654.0	1652.4	1650.7
177.5°	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6	1657.3	1656.0	1654.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	436.2	434.5	433.2	430.2	428.4	426.2	424.4	426.4	424.3	425.2	423.8
5°	422.6	417.3	413.5	408.1	403.3	399.0	395.8	395.3	393.7	393.0	390.7
7.5°	406.2	399.6	393.1	386.0	379.9	373.8	369.9	366.6	364.5	361.7	359.7
10°	396.6	387.7	380.2	371.5	363.9	357.3	352.1	349.4	347.0	343.4	342.1
12.5°	384.7	375.5	366.3	357.0	349.8	342.4	337.9	333.9	332.2	328.2	327.8
15°	370.4	356.6	347.6	338.2	328.2	322.1	318.4	314.1	312.2	309.3	307.3
17.5°	353.4	341.0	329.8	320.0	311.4	306.4	301.7	298.7	295.5	293.6	290.2
20°	341.0	329.3	318.0	307.6	301.0	295.2	291.5	288.6	285.2	284.3	280.9
22.5°	330.6	317.7	306.9	298.2	291.0	284.4	280.3	278.3	276.1	273.1	272.5
25°	313.6	300.3	291.1	282.4	276.0	269.9	267.2	264.7	262.4	260.3	259.6
27.5°	299.1	287.1	276.1	268.3	262.7	257.2	254.8	251.8	250.1	248.4	246.4
30°	288.8	276.5	266.9	259.4	253.4	248.5	245.8	243.8	242.3	240.8	239.6
32.5°	278.3	266.9	257.6	250.2	244.2	240.5	238.1	236.7	235.1	233.3	231.8
35°	264.3	251.8	242.8	236.4	231.7	228.9	226.2	224.9	223.1	223.1	221.5
37.5°	248.6	237.8	229.8	224.0	219.8	217.3	214.4	213.5	212.3	211.5	211.0
40°	239.3	229.3	221.8	215.9	211.4	209.3	207.0	205.5	204.8	203.8	203.5
42.5°	229.6	220.0	212.9	207.5	203.5	201.8	199.7	198.6	197.1	195.8	195.6
45°	214.9	205.7	199.1	194.8	191.4	189.3	188.0	185.7	185.0	183.5	183.3
47.5°	201.1	192.2	185.7	182.1	179.2	177.5	175.5	173.2	172.3	171.5	171.5
50°	190.6	182.5	176.5	173.2	170.3	167.9	165.8	164.3	163.7	163.7	164.1
52.5°	180.1	173.2	168.1	164.0	161.3	158.7	156.7	155.8	155.0	155.9	156.5
55°	164.7	157.7	153.9	149.9	147.3	144.3	143.3	143.0	142.4	143.9	144.7
57.5°	148.3	143.4	139.0	135.1	132.7	130.9	129.7	129.5	130.5	131.3	133.7
60°	137.9	132.2	128.3	125.3	122.5	121.3	120.9	120.6	121.3	123.4	126.6
62.5°	126.5	121.9	117.6	115.4	113.2	111.4	111.3	111.5	113.0	115.4	118.6
65°	109.7	105.7	102.9	100.2	98.5	97.4	97.8	98.5	100.2	103.5	107.0
67.5°	92.5	89.8	87.3	85.2	83.6	83.6	84.0	85.1	87.1	90.7	94.0
70°	81.6	78.6	76.5	75.6	74.2	73.5	74.6	76.5	78.2	81.6	84.4
72.5°	70.6	68.0	66.4	65.7	65.1	64.6	65.0	67.0	69.3	72.6	76.0
75°	54.2	53.3	52.2	51.4	50.9	51.3	51.6	53.5	55.4	58.9	62.7
77.5°	39.6	38.6	37.9	37.7	37.4	37.7	38.7	40.1	41.9	44.5	47.4
80°	29.9	29.6	29.2	29.0	29.0	29.2	30.7	31.6	33.3	35.8	38.1
82.5°	21.9	21.6	21.5	21.4	21.6	21.7	22.6	23.8	25.2	27.1	29.0
85°	11.5	11.1	11.7	11.9	11.5	12.1	12.5	13.2	13.8	14.7	15.7
87.5°	5.8	6.4	6.7	7.3	7.6	8.3	8.4	9.3	9.9	10.4	10.5
90°	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3	23.7	25.1	26.2
92.5°	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3	23.7	25.1	25.9
95°	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3	23.7	25.1	25.8
97.5°	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0	37.3	29.6	25.8
100°	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2	91.6	51.0	30.2
102.5°	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1	249.4	241.7	228.6
105°	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.6
107.5°	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1	463.1	463.2	462.8
110°	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1	525.3	524.5	524.2



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5	587.5	586.4	585.7
115°	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7	681.6	680.4	679.1
117.5°	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6	772.2	770.7	769.6
120°	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3	831.7	831.2	830.2
122.5°	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2	887.7	887.1	886.1
125°	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9	968.7	967.7	966.7
127.5°	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5	1043.9	1043.3	1042.0
130°	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2	1092.3	1091.5	1090.4
132.5°	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6	1138.5	1138.3	1137.5
135°	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3	1204.8	1204.3	1203.1
137.5°	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5	1267.6	1267.8	1267.1
140°	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7	1306.3	1306.8	1306.3
142.5°	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1	1343.3	1343.4	1342.6
145°	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0	1396.3	1396.5	1395.9
147.5°	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3	1441.6	1441.9	1441.1
150°	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1	1470.7	1471.3	1470.5
152.5°	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7	1496.2	1496.8	1496.1
155°	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9	1531.7	1532.5	1531.8
157.5°	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9	1560.8	1561.7	1561.1
160°	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0	1579.2	1580.2	1579.7
162.5°	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6	1596.2	1597.7	1597.3
165°	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9	1617.6	1619.3	1618.9
167.5°	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1	1634.0	1636.0	1635.7
170°	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4	1642.6	1644.7	1644.6
172.5°	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8	1648.8	1650.7	1650.5
175°	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8	1656.0	1658.2	1658.1
177.5°	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8	1658.2	1659.8	1659.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	422.9	424.0	423.1	424.3	423.1	424.0	422.9	423.8	425.2	424.3	426.4
5°	389.8	388.1	389.2	388.5	389.2	388.1	389.8	390.7	393.0	393.7	395.3
7.5°	359.2	357.6	355.7	354.8	355.7	357.6	359.2	359.7	361.7	364.5	366.6
10°	340.1	337.9	337.8	336.5	337.8	337.9	340.1	342.1	343.4	347.0	349.4
12.5°	326.0	324.1	322.0	321.4	322.0	324.1	326.0	327.8	328.2	332.2	333.9
15°	306.1	304.6	303.3	304.4	303.3	304.6	306.1	307.3	309.3	312.2	314.1
17.5°	289.6	288.4	288.1	286.7	288.1	288.4	289.6	290.2	293.6	295.5	298.7
20°	279.2	278.3	278.7	276.1	278.7	278.3	279.2	280.9	284.3	285.2	288.6
22.5°	270.9	269.0	268.8	268.3	268.8	269.0	270.9	272.5	273.1	276.1	278.3
25°	257.9	257.0	256.0	257.0	256.0	257.0	257.9	259.6	260.3	262.4	264.7
27.5°	246.5	245.4	245.2	245.3	245.2	245.4	246.5	246.4	248.4	250.1	251.8
30°	239.6	237.7	237.9	237.7	237.9	237.7	239.6	239.6	240.8	242.3	243.8
32.5°	232.1	230.8	230.6	230.2	230.6	230.8	232.1	231.8	233.3	235.1	236.7
35°	220.9	220.9	220.0	220.0	220.0	220.9	220.9	221.5	223.1	223.1	224.9
37.5°	210.5	210.3	209.8	209.9	209.8	210.3	210.5	211.0	211.5	212.3	213.5
40°	202.7	202.5	201.9	200.8	201.9	202.5	202.7	203.5	203.8	204.8	205.5
42.5°	195.2	194.5	194.3	193.9	194.3	194.5	195.2	195.6	195.8	197.1	198.6
45°	183.3	183.3	183.0	182.7	183.0	183.3	183.3	183.3	183.5	185.0	185.7
47.5°	171.8	172.1	172.8	172.7	172.8	172.1	171.8	171.5	171.5	172.3	173.2
50°	164.9	165.0	165.6	165.8	165.6	165.0	164.9	164.1	163.7	163.7	164.3
52.5°	157.2	158.2	159.0	158.8	159.0	158.2	157.2	156.5	155.9	155.0	155.8
55°	146.3	147.7	149.0	149.2	149.0	147.7	146.3	144.7	143.9	142.4	143.0
57.5°	135.7	137.5	138.9	139.4	138.9	137.5	135.7	133.7	131.3	130.5	129.5
60°	128.5	130.9	132.6	133.4	132.6	130.9	128.5	126.6	123.4	121.3	120.6
62.5°	121.6	124.3	126.0	126.1	126.0	124.3	121.6	118.6	115.4	113.0	111.5
65°	110.2	113.0	114.5	115.7	114.5	113.0	110.2	107.0	103.5	100.2	98.5
67.5°	98.0	100.9	102.5	103.4	102.5	100.9	98.0	94.0	90.7	87.1	85.1
70°	89.1	92.0	94.2	95.0	94.2	92.0	89.1	84.4	81.6	78.2	76.5
72.5°	80.4	82.9	84.7	85.6	84.7	82.9	80.4	76.0	72.6	69.3	67.0
75°	65.1	68.6	70.3	71.2	70.3	68.6	65.1	62.7	58.9	55.4	53.5
77.5°	50.2	53.3	54.4	54.9	54.4	53.3	50.2	47.4	44.5	41.9	40.1
80°	40.3	42.2	43.5	43.7	43.5	42.2	40.3	38.1	35.8	33.3	31.6
82.5°	31.0	32.5	32.9	33.4	32.9	32.5	31.0	29.0	27.1	25.2	23.8
85°	17.0	17.7	17.9	17.7	17.9	17.7	17.0	15.7	14.7	13.8	13.2
87.5°	11.0	11.0	11.2	11.7	11.2	11.0	11.0	10.5	10.4	9.9	9.3
90°	27.0	27.8	28.6	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3
92.5°	26.3	26.7	27.1	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3
95°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3
97.5°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0
100°	29.0	28.0	26.9	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2
102.5°	210.0	191.5	172.9	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1
105°	365.3	365.1	364.8	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7
107.5°	461.9	461.1	460.3	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1
110°	524.5	524.7	525.1	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	585.4	585.0	584.6	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5
115°	677.5	675.8	674.2	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7
117.5°	769.0	768.3	767.5	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6
120°	828.8	827.4	826.1	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3
122.5°	884.5	882.9	881.3	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2
125°	965.9	965.1	964.3	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9
127.5°	1039.9	1038.0	1035.9	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5
130°	1089.1	1087.7	1086.3	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2
132.5°	1136.2	1134.8	1133.4	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6
135°	1201.5	1199.9	1198.2	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3
137.5°	1265.7	1264.3	1262.8	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5
140°	1304.6	1303.0	1301.4	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7
142.5°	1340.9	1339.3	1337.7	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1
145°	1394.2	1392.6	1391.0	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0
147.5°	1439.2	1437.2	1435.3	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3
150°	1468.3	1466.1	1464.0	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1
152.5°	1494.1	1492.2	1490.2	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7
155°	1529.7	1527.5	1525.3	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9
157.5°	1558.9	1556.7	1554.4	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9
160°	1577.5	1575.3	1573.1	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0
162.5°	1594.9	1592.4	1590.1	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6
165°	1616.8	1614.6	1612.4	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9
167.5°	1633.3	1630.8	1628.4	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1
170°	1642.2	1639.7	1637.2	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4
172.5°	1648.0	1645.6	1643.2	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8
175°	1655.6	1653.2	1650.7	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8
177.5°	1657.9	1656.2	1654.4	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	424.4	426.2	428.4	430.2	433.2	434.5	436.2	437.5	439.9	442.2	444.9
5°	395.8	399.0	403.3	408.1	413.5	417.3	422.6	425.7	432.2	438.0	443.7
7.5°	369.9	373.8	379.9	386.0	393.1	399.6	406.2	413.5	421.7	431.4	439.4
10°	352.1	357.3	363.9	371.5	380.2	387.7	396.6	404.5	414.5	425.7	436.3
12.5°	337.9	342.4	349.8	357.0	366.3	375.5	384.7	395.1	406.8	419.3	432.5
15°	318.4	322.1	328.2	338.2	347.6	356.6	370.4	380.2	394.8	408.8	424.9
17.5°	301.7	306.4	311.4	320.0	329.8	341.0	353.4	365.7	379.8	397.5	415.5
20°	291.5	295.2	301.0	307.6	318.0	329.3	341.0	353.4	370.7	389.1	408.5
22.5°	280.3	284.4	291.0	298.2	306.9	317.7	330.6	344.2	362.3	380.3	401.4
25°	267.2	269.9	276.0	282.4	291.1	300.3	313.6	328.7	346.7	367.2	388.7
27.5°	254.8	257.2	262.7	268.3	276.1	287.1	299.1	314.3	331.2	352.0	375.8
30°	245.8	248.5	253.4	259.4	266.9	276.5	288.8	303.1	321.2	341.5	366.4
32.5°	238.1	240.5	244.2	250.2	257.6	266.9	278.3	292.9	311.0	331.6	356.0
35°	226.2	228.9	231.7	236.4	242.8	251.8	264.3	278.1	295.4	315.4	337.8
37.5°	214.4	217.3	219.8	224.0	229.8	237.8	248.6	262.9	278.6	297.8	319.4
40°	207.0	209.3	211.4	215.9	221.8	229.3	239.3	252.1	268.6	286.6	304.4
42.5°	199.7	201.8	203.5	207.5	212.9	220.0	229.6	242.1	257.5	274.2	290.0
45°	188.0	189.3	191.4	194.8	199.1	205.7	214.9	226.1	239.0	254.9	266.8
47.5°	175.5	177.5	179.2	182.1	185.7	192.2	201.1	210.5	222.3	234.1	242.4
50°	165.8	167.9	170.3	173.2	176.5	182.5	190.6	200.2	210.3	219.3	226.4
52.5°	156.7	158.7	161.3	164.0	168.1	173.2	180.1	188.7	198.5	205.0	210.9
55°	143.3	144.3	147.3	149.9	153.9	157.7	164.7	172.2	178.2	183.1	188.0
57.5°	129.7	130.9	132.7	135.1	139.0	143.4	148.3	155.0	158.5	161.0	164.9
60°	120.9	121.3	122.5	125.3	128.3	132.2	137.9	142.6	145.3	147.3	150.5
62.5°	111.3	111.4	113.2	115.4	117.6	121.9	126.5	130.3	132.4	133.5	136.5
65°	97.8	97.4	98.5	100.2	102.9	105.7	109.7	113.0	112.8	114.0	115.9
67.5°	84.0	83.6	83.6	85.2	87.3	89.8	92.5	94.6	94.6	96.0	97.0
70°	74.6	73.5	74.2	75.6	76.5	78.6	81.6	82.3	82.5	83.2	84.2
72.5°	65.0	64.6	65.1	65.7	66.4	68.0	70.6	71.0	71.1	71.5	73.1
75°	51.6	51.3	50.9	51.4	52.2	53.3	54.2	55.0	54.8	55.0	56.2
77.5°	38.7	37.7	37.4	37.7	37.9	38.6	39.6	39.5	39.7	39.7	40.9
80°	30.7	29.2	29.0	29.0	29.2	29.6	29.9	30.3	29.8	30.3	30.7
82.5°	22.6	21.7	21.6	21.4	21.5	21.6	21.9	22.0	21.9	22.2	22.4
85°	12.5	12.1	11.5	11.9	11.7	11.1	11.5	10.9	10.8	10.9	11.1
87.5°	8.4	8.3	7.6	7.3	6.7	6.4	5.8	5.1	4.6	4.3	4.3
90°	21.0	19.6	17.7	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	21.0	19.6	17.9	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9
95°	21.0	19.6	30.0	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0
97.5°	52.7	60.4	80.9	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0
100°	172.9	213.5	212.5	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0
102.5°	264.8	272.5	271.8	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9
105°	365.7	365.7	365.7	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9
107.5°	463.0	462.9	462.4	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5
110°	526.9	527.7	527.2	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	589.5	590.6	590.3	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2
115°	683.7	684.9	684.6	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5
117.5°	774.9	776.4	775.3	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0
120°	832.8	833.3	832.5	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9
122.5°	888.8	889.3	888.9	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0
125°	970.9	972.0	972.0	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4
127.5°	1045.1	1045.7	1045.9	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2
130°	1094.0	1094.8	1094.5	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4
132.5°	1138.8	1139.0	1139.5	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5
135°	1205.9	1206.5	1207.0	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5
137.5°	1267.5	1267.3	1267.8	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1
140°	1305.2	1304.6	1304.9	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4
142.5°	1343.0	1343.0	1342.6	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7
145°	1395.7	1395.5	1395.5	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0
147.5°	1441.0	1440.6	1440.3	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7
150°	1469.7	1469.1	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1
152.5°	1495.2	1494.6	1494.1	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5
155°	1530.1	1529.3	1528.7	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1
157.5°	1559.1	1558.2	1558.1	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4
160°	1577.0	1575.9	1575.6	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0
162.5°	1593.1	1591.5	1591.3	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7
165°	1614.3	1612.7	1612.4	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9
167.5°	1630.1	1628.2	1627.9	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5
170°	1638.2	1636.0	1635.7	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4
172.5°	1644.9	1642.9	1642.4	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3
175°	1651.7	1649.5	1649.3	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6
177.5°	1655.2	1653.7	1653.4	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	446.3	448.3	449.7	452.2	454.4	455.6	456.6	457.5	458.6	459.5	462.1
5°	449.1	454.0	458.2	464.6	470.4	474.9	479.8	484.1	487.7	492.8	496.8
7.5°	447.8	456.6	465.7	475.6	485.8	495.1	503.9	511.9	519.3	528.2	536.0
10°	446.7	458.5	470.2	483.6	497.3	509.0	519.9	531.1	539.2	550.5	560.1
12.5°	445.8	459.7	473.9	489.9	505.0	521.5	536.1	544.2	556.5	565.6	577.0
15°	442.0	460.4	479.8	497.9	519.4	534.7	547.5	563.3	574.8	586.3	598.7
17.5°	435.1	456.1	477.8	501.5	522.0	538.4	555.0	570.2	583.9	599.3	614.8
20°	431.9	452.9	477.8	502.1	522.2	539.3	556.3	573.1	588.2	608.0	625.8
22.5°	425.3	450.6	473.5	497.3	518.0	536.6	555.9	574.9	594.9	617.3	639.7
25°	413.5	439.1	463.4	486.8	507.7	531.1	551.6	577.1	602.7	632.3	660.1
27.5°	401.2	425.7	448.0	470.6	495.0	521.5	548.0	576.9	610.5	647.8	687.1
30°	391.3	414.5	436.1	459.3	484.7	514.5	543.7	578.0	616.8	658.8	705.6
32.5°	379.7	401.0	422.1	446.6	474.3	505.7	539.8	577.4	624.0	671.7	719.8
35°	359.8	377.7	399.4	425.6	456.8	492.8	532.2	576.7	630.1	685.0	725.5
37.5°	336.3	352.9	375.8	404.5	437.2	475.9	522.6	575.4	632.2	675.9	688.9
40°	320.4	335.9	359.6	389.4	422.9	463.8	515.0	570.8	625.8	653.7	642.9
42.5°	303.5	319.8	342.9	372.3	408.5	453.0	505.6	561.3	607.5	618.0	580.9
45°	277.0	293.7	316.5	346.3	385.1	433.3	488.1	538.8	565.3	546.3	488.9
47.5°	252.2	267.9	289.0	319.8	359.8	409.7	462.4	502.9	505.0	459.6	398.2
50°	235.3	249.8	271.1	301.8	341.5	392.1	439.7	471.6	457.2	405.8	346.8
52.5°	218.7	232.9	253.9	284.3	323.6	369.9	414.3	436.6	409.6	356.8	306.5
55°	194.8	207.2	227.8	255.8	293.1	336.1	373.7	381.5	346.4	294.5	253.6
57.5°	171.5	183.0	201.7	227.6	261.7	299.7	329.2	327.5	290.5	245.9	213.4
60°	155.6	166.9	183.5	208.7	239.9	272.6	297.8	291.8	255.1	216.6	189.3
62.5°	141.5	151.6	167.2	189.3	217.7	248.0	268.7	259.8	223.9	190.3	168.7
65°	120.6	129.1	142.4	161.3	184.8	209.9	225.9	214.4	183.7	157.5	140.1
67.5°	100.6	107.5	118.6	133.7	153.8	173.9	183.6	172.1	147.5	128.4	115.5
70°	88.0	94.0	102.6	116.0	133.5	150.5	157.8	147.5	126.4	110.0	100.8
72.5°	75.3	80.3	87.9	100.0	114.0	128.7	135.1	125.2	107.9	94.0	85.4
75°	58.2	61.6	66.9	75.2	86.3	98.0	101.5	92.9	81.8	71.4	65.7
77.5°	41.7	44.5	48.5	53.7	61.6	69.1	72.2	67.2	58.6	52.0	47.4
80°	32.0	33.5	36.9	41.3	47.5	52.2	54.2	51.0	45.0	40.1	36.5
82.5°	22.8	24.4	26.3	29.9	33.9	37.1	39.3	37.2	32.9	28.9	26.9
85°	11.1	12.1	13.2	14.7	17.7	19.6	19.4	18.1	16.4	14.9	13.8
87.5°	4.6	5.2	6.1	7.3	8.2	9.1	9.8	9.9	9.6	9.5	9.3
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3
92.5°	17.4	15.8	14.3	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3
95°	69.1	68.3	67.5	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3
97.5°	147.5	149.0	150.5	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0
100°	205.8	206.6	207.4	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2
102.5°	265.9	266.9	268.0	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1
105°	361.9	363.1	364.1	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	460.5	460.5	460.5	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1
110°	525.3	525.3	525.3	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	586.9	587.5	588.2	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5
115°	678.8	680.2	681.6	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7
117.5°	771.9	771.8	771.8	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6
120°	830.6	830.4	830.1	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3
122.5°	883.9	885.0	886.1	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2
125°	965.3	967.3	969.1	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9
127.5°	1041.6	1043.0	1044.4	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5
130°	1088.8	1090.1	1091.5	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2
132.5°	1136.1	1137.7	1139.3	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6
135°	1203.1	1204.8	1206.5	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3
137.5°	1264.5	1266.0	1267.4	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5
140°	1304.0	1304.5	1305.0	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7
142.5°	1340.0	1340.4	1340.7	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1
145°	1393.5	1394.1	1394.7	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0
147.5°	1439.5	1439.4	1439.3	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3
150°	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1
152.5°	1496.4	1495.2	1494.0	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7
155°	1532.5	1530.9	1529.3	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9
157.5°	1561.4	1560.4	1559.4	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9
160°	1580.4	1578.7	1577.1	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0
162.5°	1596.1	1594.5	1592.8	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6
165°	1617.2	1615.5	1613.9	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9
167.5°	1632.9	1631.2	1629.5	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1
170°	1641.4	1639.6	1637.6	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4
172.5°	1647.4	1645.4	1643.6	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8
175°	1654.0	1652.4	1650.7	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8
177.5°	1657.3	1656.0	1654.6	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	464.2	465.4	468.0	467.1	468.2	468.9	469.4
5°	501.7	507.7	510.4	510.0	514.0	513.0	512.0
7.5°	544.0	550.3	553.9	558.3	560.8	561.1	563.3
10°	568.0	576.3	579.7	584.4	587.4	589.1	588.9
12.5°	586.4	592.9	600.5	602.8	606.8	609.0	608.2
15°	608.5	618.9	626.8	630.7	635.9	637.3	639.4
17.5°	628.3	642.1	651.3	663.7	668.3	671.2	669.4
20°	643.2	661.5	670.7	685.3	693.5	697.8	696.3
22.5°	660.8	680.6	697.7	710.4	722.7	728.6	729.8
25°	691.0	718.1	743.2	759.9	775.2	778.8	786.7
27.5°	724.8	756.8	783.6	801.2	811.8	815.8	818.3
30°	746.0	777.9	798.0	809.3	812.7	812.4	812.0
32.5°	756.4	776.3	780.2	777.1	769.3	762.7	755.9
35°	741.7	726.8	704.6	676.0	654.8	633.6	631.4
37.5°	667.1	619.5	582.4	541.1	517.3	502.6	492.4
40°	596.8	542.7	497.9	463.1	438.8	429.2	419.7
42.5°	520.6	468.9	429.2	400.1	381.8	371.1	363.7
45°	422.9	377.3	346.3	325.1	310.6	302.4	297.7
47.5°	346.6	312.8	286.4	271.2	261.2	254.8	254.8
50°	305.6	273.4	255.8	243.8	235.1	230.0	231.0
52.5°	269.2	245.2	230.2	220.1	213.7	210.6	210.4
55°	225.1	207.8	198.0	190.6	186.3	182.7	183.5
57.5°	192.6	178.0	171.4	165.3	162.2	160.9	158.7
60°	172.4	161.1	155.4	150.5	147.5	146.3	144.3
62.5°	154.4	145.5	140.1	136.1	133.4	133.0	131.3
65°	129.8	123.0	118.1	116.3	113.4	112.7	112.7
67.5°	107.0	102.2	98.3	96.6	95.4	95.6	94.7
70°	92.7	88.7	86.3	84.4	83.5	83.6	82.9
72.5°	81.1	76.6	74.5	73.4	72.2	72.6	72.3
75°	61.4	59.2	58.0	56.9	56.2	55.8	55.4
77.5°	45.1	43.1	42.2	41.6	41.7	40.8	41.5
80°	34.8	33.2	32.6	31.6	31.5	31.5	31.3
82.5°	25.5	24.5	24.1	23.4	23.0	23.3	22.8
85°	13.2	12.5	12.2	12.2	11.9	11.5	12.5
87.5°	9.5	9.2	9.5	9.5	9.6	9.6	9.5
90°	23.7	25.1	26.2	27.0	27.8	28.6	29.4
92.5°	23.7	25.1	25.9	26.3	26.7	27.1	27.5
95°	23.7	25.1	25.8	25.8	25.8	25.8	25.8
97.5°	37.3	29.6	25.8	25.8	25.8	25.8	25.8
100°	91.6	51.0	30.2	29.0	28.0	26.9	25.8
102.5°	249.4	241.7	228.6	210.0	191.5	172.9	154.4
105°	365.7	365.7	365.6	365.3	365.1	364.8	364.5
107.5°	463.1	463.2	462.8	461.9	461.1	460.3	459.5
110°	525.3	524.5	524.2	524.5	524.7	525.1	525.3



TEST NUMBER: P333364-930

CATALOG NUMBER: S125DIW-S375D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	587.5	586.4	585.7	585.4	585.0	584.6	584.2
115°	681.6	680.4	679.1	677.5	675.8	674.2	672.5
117.5°	772.2	770.7	769.6	769.0	768.3	767.5	766.8
120°	831.7	831.2	830.2	828.8	827.4	826.1	824.8
122.5°	887.7	887.1	886.1	884.5	882.9	881.3	879.7
125°	968.7	967.7	966.7	965.9	965.1	964.3	963.4
127.5°	1043.9	1043.3	1042.0	1039.9	1038.0	1035.9	1033.9
130°	1092.3	1091.5	1090.4	1089.1	1087.7	1086.3	1084.9
132.5°	1138.5	1138.3	1137.5	1136.2	1134.8	1133.4	1132.0
135°	1204.8	1204.3	1203.1	1201.5	1199.9	1198.2	1196.6
137.5°	1267.6	1267.8	1267.1	1265.7	1264.3	1262.8	1261.4
140°	1306.3	1306.8	1306.3	1304.6	1303.0	1301.4	1299.8
142.5°	1343.3	1343.4	1342.6	1340.9	1339.3	1337.7	1336.0
145°	1396.3	1396.5	1395.9	1394.2	1392.6	1391.0	1389.4
147.5°	1441.6	1441.9	1441.1	1439.2	1437.2	1435.3	1433.3
150°	1470.7	1471.3	1470.5	1468.3	1466.1	1464.0	1461.8
152.5°	1496.2	1496.8	1496.1	1494.1	1492.2	1490.2	1488.2
155°	1531.7	1532.5	1531.8	1529.7	1527.5	1525.3	1523.1
157.5°	1560.8	1561.7	1561.1	1558.9	1556.7	1554.4	1552.3
160°	1579.2	1580.2	1579.7	1577.5	1575.3	1573.1	1571.0
162.5°	1596.2	1597.7	1597.3	1594.9	1592.4	1590.1	1587.6
165°	1617.6	1619.3	1618.9	1616.8	1614.6	1612.4	1610.2
167.5°	1634.0	1636.0	1635.7	1633.3	1630.8	1628.4	1626.0
170°	1642.6	1644.7	1644.6	1642.2	1639.7	1637.2	1634.8
172.5°	1648.8	1650.7	1650.5	1648.0	1645.6	1643.2	1640.7
175°	1656.0	1658.2	1658.1	1655.6	1653.2	1650.7	1648.3
177.5°	1658.2	1659.8	1659.7	1657.9	1656.2	1654.4	1652.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6

(END OF REPORT)