

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333340-930

Luminaire Tested: **S125DIW-S375D470U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333340-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D470U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2781.4 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	93	89	85	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	41	39	37	32
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	28	24
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	26	24	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	28	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2866	2866	2866	2866
5°	3319	2877	2519	2877
10°	3862	2861	2207	2861
15°	4275	2841	2035	2841
20°	4786	2808	1898	2808
25°	5606	2770	1831	2770
30°	6055	2732	1773	2732
35°	4978	2663	1735	2663
40°	3538	2566	1693	2566
45°	2719	2437	1669	2437
50°	2321	2275	1666	2275
55°	2066	2117	1680	2117
60°	1864	1944	1723	1944
65°	1722	1771	1768	1771
70°	1565	1590	1794	1590
75°	1382	1402	1777	1402
80°	1164	1142	1625	1142
85°	926	823	1312	823



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.5
10°-20°	127.2	4.6
20°-30°	206.6	7.4
30°-40°	252.0	9.1
40°-50°	229.2	8.2
50°-60°	182.6	6.6
60°-70°	127.2	4.6
70°-80°	67.8	2.4
80°-90°	18.2	0.7
90°-100°	18.1	0.6
100°-110°	111.4	4.0
110°-120°	202.1	7.3
120°-130°	259.4	9.3
130°-140°	279.0	10.0
140°-150°	261.9	9.4
150°-160°	211.8	7.6
160°-170°	137.0	4.9
170°-180°	47.3	1.7
0°-30°	376.5	13.5
0°-40°	628.5	22.6
0°-60°	1040.3	37.4
0°-90°	1253.5	45.1
90°-120°	331.6	11.9
90°-150°	1131.8	40.7
90°-180°	1528.0	54.9
0°-180°	2781.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	512	444	388	444	512	52
15°	639	425	304	425	639	183
25°	787	389	257	389	787	359
35°	631	338	220	338	631	386
45°	298	267	183	267	298	238
55°	184	188	149	188	184	165
65°	113	116	116	116	113	112
75°	55	56	71	56	55	60
85°	12	11	18	11	12	15
90°	9	0	9	0	9	4
95°	8	21	8	21	8	6
105°	110	108	110	108	110	99
115°	202	204	202	204	202	201
125°	290	290	290	290	290	258
135°	360	361	360	361	360	278
145°	418	419	418	419	418	261
155°	458	461	458	461	458	211
165°	484	486	484	486	484	137
175°	495	498	495	498	495	47
180°	498	498	498	498	498	



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	469.4	468.9	468.2	467.1	468.0	465.4	464.2	462.1	459.5	458.6	457.5
5°	512.0	513.0	514.0	510.0	510.4	507.7	501.7	496.8	492.8	487.7	484.1
7.5°	563.3	561.1	560.8	558.3	553.9	550.3	544.0	536.0	528.2	519.3	511.9
10°	588.9	589.1	587.4	584.4	579.7	576.3	568.0	560.1	550.5	539.2	531.1
12.5°	608.2	609.0	606.8	602.8	600.5	592.9	586.4	577.0	565.6	556.5	544.2
15°	639.4	637.3	635.9	630.7	626.8	618.9	608.5	598.7	586.3	574.8	563.3
17.5°	669.4	671.2	668.3	663.7	651.3	642.1	628.3	614.8	599.3	583.9	570.2
20°	696.3	697.8	693.5	685.3	670.7	661.5	643.2	625.8	608.0	588.2	573.1
22.5°	729.8	728.6	722.7	710.4	697.7	680.6	660.8	639.7	617.3	594.9	574.9
25°	786.7	778.8	775.2	759.9	743.2	718.1	691.0	660.1	632.3	602.7	577.1
27.5°	818.3	815.8	811.8	801.2	783.6	756.8	724.8	687.1	647.8	610.5	576.9
30°	812.0	812.4	812.7	809.3	798.0	777.9	746.0	705.6	658.8	616.8	578.0
32.5°	755.9	762.7	769.3	777.1	780.2	776.3	756.4	719.8	671.7	624.0	577.4
35°	631.4	633.6	654.8	676.0	704.6	726.8	741.7	725.5	685.0	630.1	576.7
37.5°	492.4	502.6	517.3	541.1	582.4	619.5	667.1	688.9	675.9	632.2	575.4
40°	419.7	429.2	438.8	463.1	497.9	542.7	596.8	642.9	653.7	625.8	570.8
42.5°	363.7	371.1	381.8	400.1	429.2	468.9	520.6	580.9	618.0	607.5	561.3
45°	297.7	302.4	310.6	325.1	346.3	377.3	422.9	488.9	546.3	565.3	538.8
47.5°	254.8	254.8	261.2	271.2	286.4	312.8	346.6	398.2	459.6	505.0	502.9
50°	231.0	230.0	235.1	243.8	255.8	273.4	305.6	346.8	405.8	457.2	471.6
52.5°	210.4	210.6	213.7	220.1	230.2	245.2	269.2	306.5	356.8	409.6	436.6
55°	183.5	182.7	186.3	190.6	198.0	207.8	225.1	253.6	294.5	346.4	381.5
57.5°	158.7	160.9	162.2	165.3	171.4	178.0	192.6	213.4	245.9	290.5	327.5
60°	144.3	146.3	147.5	150.5	155.4	161.1	172.4	189.3	216.6	255.1	291.8
62.5°	131.3	133.0	133.4	136.1	140.1	145.5	154.4	168.7	190.3	223.9	259.8
65°	112.7	112.7	113.4	116.3	118.1	123.0	129.8	140.1	157.5	183.7	214.4
67.5°	94.7	95.6	95.4	96.6	98.3	102.2	107.0	115.5	128.4	147.5	172.1
70°	82.9	83.6	83.5	84.4	86.3	88.7	92.7	100.8	110.0	126.4	147.5
72.5°	72.3	72.6	72.2	73.4	74.5	76.6	81.1	85.4	94.0	107.9	125.2
75°	55.4	55.8	56.2	56.9	58.0	59.2	61.4	65.7	71.4	81.8	92.9
77.5°	41.5	40.8	41.7	41.6	42.2	43.1	45.1	47.4	52.0	58.6	67.2
80°	31.3	31.5	31.5	31.6	32.6	33.2	34.8	36.5	40.1	45.0	51.0
82.5°	22.8	23.3	23.0	23.4	24.1	24.5	25.5	26.9	28.9	32.9	37.2
85°	12.5	11.5	11.9	12.2	12.2	12.5	13.2	13.8	14.9	16.4	18.1
87.5°	5.4	5.6	5.7	5.7	5.8	5.7	6.3	6.2	6.5	6.9	7.4
90°	8.9	8.6	8.4	8.2	7.9	7.5	7.1	6.7	6.3	5.9	5.3
92.5°	8.2	8.2	8.1	7.9	7.8	7.5	7.1	6.7	6.3	5.9	5.4
95°	7.7	7.7	7.7	7.7	7.7	7.5	7.1	6.7	6.3	5.9	9.0
97.5°	7.7	7.7	7.7	7.7	7.7	8.9	11.3	13.5	15.8	18.2	24.3
100°	7.7	8.1	8.4	8.7	9.0	15.3	27.6	39.8	51.9	64.2	63.8
102.5°	46.4	51.9	57.6	63.1	68.7	72.6	74.9	77.3	79.6	81.9	81.7
105°	109.6	109.7	109.7	109.8	109.9	109.9	109.9	109.9	109.9	109.9	109.9
107.5°	138.1	138.4	138.6	138.8	139.1	139.2	139.2	139.2	139.2	139.1	138.9
110°	157.8	157.8	157.7	157.6	157.5	157.6	157.8	158.1	158.3	158.6	158.4



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	175.5	175.7	175.8	175.9	176.0	176.3	176.5	176.8	177.2	177.5	177.4
115°	202.1	202.6	203.1	203.6	204.1	204.5	204.8	205.1	205.5	205.8	205.7
117.5°	230.5	230.6	230.9	231.1	231.3	231.6	232.0	232.4	232.9	233.3	233.0
120°	247.9	248.3	248.7	249.1	249.5	249.8	250.0	250.1	250.3	250.5	250.2
122.5°	264.4	264.9	265.3	265.8	266.3	266.6	266.8	266.9	267.1	267.3	267.2
125°	289.5	289.8	290.0	290.2	290.5	290.8	291.1	291.5	291.8	292.1	292.1
127.5°	310.7	311.3	311.9	312.5	313.2	313.6	313.7	313.9	314.1	314.2	314.3
130°	326.0	326.4	326.9	327.3	327.7	328.0	328.2	328.5	328.7	329.0	328.9
132.5°	340.2	340.6	341.0	341.4	341.9	342.1	342.1	342.2	342.3	342.3	342.4
135°	359.6	360.1	360.6	361.1	361.6	361.9	362.1	362.2	362.4	362.6	362.7
137.5°	379.1	379.5	379.9	380.3	380.8	381.0	381.0	380.9	380.9	380.8	381.0
140°	390.6	391.1	391.6	392.1	392.6	392.7	392.6	392.4	392.2	392.1	392.2
142.5°	401.5	402.0	402.5	403.0	403.5	403.7	403.7	403.7	403.6	403.6	403.5
145°	417.5	418.0	418.5	419.0	419.5	419.7	419.6	419.6	419.5	419.4	419.4
147.5°	430.7	431.3	431.9	432.5	433.1	433.3	433.3	433.2	433.0	432.9	432.8
150°	439.3	439.9	440.6	441.2	441.9	442.1	442.0	441.8	441.6	441.5	441.3
152.5°	447.3	447.8	448.4	449.0	449.6	449.8	449.6	449.5	449.3	449.1	449.0
155°	457.7	458.4	459.0	459.7	460.3	460.6	460.3	460.1	459.8	459.6	459.4
157.5°	466.5	467.2	467.8	468.5	469.1	469.3	469.0	468.8	468.6	468.3	468.2
160°	472.1	472.8	473.4	474.1	474.7	474.9	474.6	474.3	473.9	473.6	473.5
162.5°	477.1	477.8	478.6	479.3	480.0	480.1	479.7	479.2	478.7	478.3	478.3
165°	483.9	484.5	485.2	485.9	486.6	486.7	486.2	485.7	485.1	484.6	484.5
167.5°	488.6	489.3	490.1	490.8	491.6	491.6	491.1	490.5	489.9	489.3	489.2
170°	491.3	492.0	492.8	493.5	494.2	494.3	493.7	492.9	492.3	491.6	491.5
172.5°	493.1	493.8	494.6	495.3	496.0	496.1	495.5	494.9	494.3	493.7	493.6
175°	495.4	496.1	496.8	497.6	498.3	498.3	497.7	497.0	496.4	495.7	495.6
177.5°	496.7	497.2	497.7	498.2	498.8	498.8	498.3	497.9	497.4	497.0	496.9
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	456.6	455.6	454.4	452.2	449.7	448.3	446.3	444.9	442.2	439.9	437.5
5°	479.8	474.9	470.4	464.6	458.2	454.0	449.1	443.7	438.0	432.2	425.7
7.5°	503.9	495.1	485.8	475.6	465.7	456.6	447.8	439.4	431.4	421.7	413.5
10°	519.9	509.0	497.3	483.6	470.2	458.5	446.7	436.3	425.7	414.5	404.5
12.5°	536.1	521.5	505.0	489.9	473.9	459.7	445.8	432.5	419.3	406.8	395.1
15°	547.5	534.7	519.4	497.9	479.8	460.4	442.0	424.9	408.8	394.8	380.2
17.5°	555.0	538.4	522.0	501.5	477.8	456.1	435.1	415.5	397.5	379.8	365.7
20°	556.3	539.3	522.2	502.1	477.8	452.9	431.9	408.5	389.1	370.7	353.4
22.5°	555.9	536.6	518.0	497.3	473.5	450.6	425.3	401.4	380.3	362.3	344.2
25°	551.6	531.1	507.7	486.8	463.4	439.1	413.5	388.7	367.2	346.7	328.7
27.5°	548.0	521.5	495.0	470.6	448.0	425.7	401.2	375.8	352.0	331.2	314.3
30°	543.7	514.5	484.7	459.3	436.1	414.5	391.3	366.4	341.5	321.2	303.1
32.5°	539.8	505.7	474.3	446.6	422.1	401.0	379.7	356.0	331.6	311.0	292.9
35°	532.2	492.8	456.8	425.6	399.4	377.7	359.8	337.8	315.4	295.4	278.1
37.5°	522.6	475.9	437.2	404.5	375.8	352.9	336.3	319.4	297.8	278.6	262.9
40°	515.0	463.8	422.9	389.4	359.6	335.9	320.4	304.4	286.6	268.6	252.1
42.5°	505.6	453.0	408.5	372.3	342.9	319.8	303.5	290.0	274.2	257.5	242.1
45°	488.1	433.3	385.1	346.3	316.5	293.7	277.0	266.8	254.9	239.0	226.1
47.5°	462.4	409.7	359.8	319.8	289.0	267.9	252.2	242.4	234.1	222.3	210.5
50°	439.7	392.1	341.5	301.8	271.1	249.8	235.3	226.4	219.3	210.3	200.2
52.5°	414.3	369.9	323.6	284.3	253.9	232.9	218.7	210.9	205.0	198.5	188.7
55°	373.7	336.1	293.1	255.8	227.8	207.2	194.8	188.0	183.1	178.2	172.2
57.5°	329.2	299.7	261.7	227.6	201.7	183.0	171.5	164.9	161.0	158.5	155.0
60°	297.8	272.6	239.9	208.7	183.5	166.9	155.6	150.5	147.3	145.3	142.6
62.5°	268.7	248.0	217.7	189.3	167.2	151.6	141.5	136.5	133.5	132.4	130.3
65°	225.9	209.9	184.8	161.3	142.4	129.1	120.6	115.9	114.0	112.8	113.0
67.5°	183.6	173.9	153.8	133.7	118.6	107.5	100.6	97.0	96.0	94.6	94.6
70°	157.8	150.5	133.5	116.0	102.6	94.0	88.0	84.2	83.2	82.5	82.3
72.5°	135.1	128.7	114.0	100.0	87.9	80.3	75.3	73.1	71.5	71.1	71.0
75°	101.5	98.0	86.3	75.2	66.9	61.6	58.2	56.2	55.0	54.8	55.0
77.5°	72.2	69.1	61.6	53.7	48.5	44.5	41.7	40.9	39.7	39.7	39.5
80°	54.2	52.2	47.5	41.3	36.9	33.5	32.0	30.7	30.3	29.8	30.3
82.5°	39.3	37.1	33.9	29.9	26.3	24.4	22.8	22.4	22.2	21.9	22.0
85°	19.4	19.6	17.7	14.7	13.2	12.1	11.1	11.1	10.9	10.8	10.9
87.5°	7.6	7.2	6.4	5.9	5.0	4.4	4.2	4.2	3.8	3.8	4.1
90°	4.7	4.2	3.6	3.0	2.4	1.7	1.1	0.4	1.1	1.7	2.4
92.5°	4.9	4.4	3.8	3.8	4.3	4.7	5.2	5.7	5.2	4.7	4.3
95°	12.1	15.2	18.3	20.1	20.3	20.5	20.8	21.0	20.8	20.5	20.3
97.5°	30.5	36.6	42.8	45.7	45.2	44.8	44.4	43.9	44.4	44.8	45.2
100°	63.5	63.2	62.9	62.6	62.4	62.1	61.9	61.6	61.9	62.1	62.4
102.5°	81.4	81.3	81.1	80.9	80.6	80.2	79.9	79.6	79.9	80.2	80.6
105°	109.9	109.9	109.9	109.7	109.4	109.1	108.8	108.4	108.8	109.1	109.4
107.5°	138.8	138.6	138.4	138.4	138.4	138.4	138.4	138.4	138.4	138.4	138.4
110°	158.2	158.1	157.9	157.8	157.8	157.8	157.8	157.8	157.8	157.8	157.8



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	177.3	177.2	177.1	176.9	176.8	176.5	176.3	176.2	176.3	176.5	176.8
115°	205.6	205.5	205.5	205.2	204.8	204.4	204.0	203.6	204.0	204.4	204.8
117.5°	232.7	232.4	232.1	232.0	232.0	232.0	232.0	232.0	232.0	232.0	232.0
120°	250.0	249.7	249.5	249.4	249.5	249.6	249.6	249.7	249.6	249.6	249.5
122.5°	267.0	266.9	266.8	266.6	266.3	266.0	265.6	265.4	265.6	266.0	266.3
125°	292.1	292.1	292.1	291.8	291.2	290.7	290.1	289.5	290.1	290.7	291.2
127.5°	314.4	314.4	314.5	314.3	313.9	313.5	313.1	312.6	313.1	313.5	313.9
130°	328.8	328.7	328.6	328.4	328.0	327.6	327.2	326.8	327.2	327.6	328.0
132.5°	342.7	342.8	343.0	342.8	342.3	341.9	341.4	341.0	341.4	341.9	342.3
135°	362.9	363.1	363.2	363.1	362.6	362.1	361.6	361.1	361.6	362.1	362.6
137.5°	381.2	381.3	381.5	381.3	380.9	380.4	380.0	379.6	380.0	380.4	380.9
140°	392.2	392.3	392.4	392.3	392.2	392.0	391.8	391.7	391.8	392.0	392.2
142.5°	403.3	403.2	403.1	403.0	402.9	402.8	402.8	402.6	402.8	402.8	402.9
145°	419.4	419.4	419.4	419.3	419.1	419.0	418.8	418.7	418.8	419.0	419.1
147.5°	432.8	432.7	432.5	432.5	432.5	432.6	432.6	432.7	432.6	432.6	432.5
150°	441.2	441.0	440.8	440.8	441.0	441.2	441.3	441.5	441.3	441.2	441.0
152.5°	448.8	448.7	448.5	448.6	449.0	449.3	449.7	450.0	449.7	449.3	449.0
155°	459.3	459.1	458.9	459.1	459.6	460.1	460.6	461.1	460.6	460.1	459.6
157.5°	468.2	468.2	468.2	468.3	468.6	469.0	469.2	469.5	469.2	469.0	468.6
160°	473.4	473.4	473.3	473.4	473.9	474.4	474.9	475.4	474.9	474.4	473.9
162.5°	478.2	478.1	478.0	478.2	478.7	479.2	479.6	480.1	479.6	479.2	478.7
165°	484.5	484.4	484.3	484.5	485.0	485.5	486.0	486.5	486.0	485.5	485.0
167.5°	489.1	489.0	488.9	489.2	489.7	490.2	490.7	491.2	490.7	490.2	489.7
170°	491.5	491.4	491.3	491.5	492.1	492.7	493.3	493.9	493.3	492.7	492.1
172.5°	493.4	493.3	493.2	493.3	493.9	494.5	495.0	495.6	495.0	494.5	493.9
175°	495.5	495.5	495.4	495.6	496.1	496.6	497.1	497.6	497.1	496.6	496.1
177.5°	496.8	496.8	496.7	496.8	497.3	497.7	498.1	498.5	498.1	497.7	497.3
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	436.2	434.5	433.2	430.2	428.4	426.2	424.4	426.4	424.3	425.2	423.8
5°	422.6	417.3	413.5	408.1	403.3	399.0	395.8	395.3	393.7	393.0	390.7
7.5°	406.2	399.6	393.1	386.0	379.9	373.8	369.9	366.6	364.5	361.7	359.7
10°	396.6	387.7	380.2	371.5	363.9	357.3	352.1	349.4	347.0	343.4	342.1
12.5°	384.7	375.5	366.3	357.0	349.8	342.4	337.9	333.9	332.2	328.2	327.8
15°	370.4	356.6	347.6	338.2	328.2	322.1	318.4	314.1	312.2	309.3	307.3
17.5°	353.4	341.0	329.8	320.0	311.4	306.4	301.7	298.7	295.5	293.6	290.2
20°	341.0	329.3	318.0	307.6	301.0	295.2	291.5	288.6	285.2	284.3	280.9
22.5°	330.6	317.7	306.9	298.2	291.0	284.4	280.3	278.3	276.1	273.1	272.5
25°	313.6	300.3	291.1	282.4	276.0	269.9	267.2	264.7	262.4	260.3	259.6
27.5°	299.1	287.1	276.1	268.3	262.7	257.2	254.8	251.8	250.1	248.4	246.4
30°	288.8	276.5	266.9	259.4	253.4	248.5	245.8	243.8	242.3	240.8	239.6
32.5°	278.3	266.9	257.6	250.2	244.2	240.5	238.1	236.7	235.1	233.3	231.8
35°	264.3	251.8	242.8	236.4	231.7	228.9	226.2	224.9	223.1	223.1	221.5
37.5°	248.6	237.8	229.8	224.0	219.8	217.3	214.4	213.5	212.3	211.5	211.0
40°	239.3	229.3	221.8	215.9	211.4	209.3	207.0	205.5	204.8	203.8	203.5
42.5°	229.6	220.0	212.9	207.5	203.5	201.8	199.7	198.6	197.1	195.8	195.6
45°	214.9	205.7	199.1	194.8	191.4	189.3	188.0	185.7	185.0	183.5	183.3
47.5°	201.1	192.2	185.7	182.1	179.2	177.5	175.5	173.2	172.3	171.5	171.5
50°	190.6	182.5	176.5	173.2	170.3	167.9	165.8	164.3	163.7	163.7	164.1
52.5°	180.1	173.2	168.1	164.0	161.3	158.7	156.7	155.8	155.0	155.9	156.5
55°	164.7	157.7	153.9	149.9	147.3	144.3	143.3	143.0	142.4	143.9	144.7
57.5°	148.3	143.4	139.0	135.1	132.7	130.9	129.7	129.5	130.5	131.3	133.7
60°	137.9	132.2	128.3	125.3	122.5	121.3	120.9	120.6	121.3	123.4	126.6
62.5°	126.5	121.9	117.6	115.4	113.2	111.4	111.3	111.5	113.0	115.4	118.6
65°	109.7	105.7	102.9	100.2	98.5	97.4	97.8	98.5	100.2	103.5	107.0
67.5°	92.5	89.8	87.3	85.2	83.6	83.6	84.0	85.1	87.1	90.7	94.0
70°	81.6	78.6	76.5	75.6	74.2	73.5	74.6	76.5	78.2	81.6	84.4
72.5°	70.6	68.0	66.4	65.7	65.1	64.6	65.0	67.0	69.3	72.6	76.0
75°	54.2	53.3	52.2	51.4	50.9	51.3	51.6	53.5	55.4	58.9	62.7
77.5°	39.6	38.6	37.9	37.7	37.4	37.7	38.7	40.1	41.9	44.5	47.4
80°	29.9	29.6	29.2	29.0	29.0	29.2	30.7	31.6	33.3	35.8	38.1
82.5°	21.9	21.6	21.5	21.4	21.6	21.7	22.6	23.8	25.2	27.1	29.0
85°	11.5	11.1	11.7	11.9	11.5	12.1	12.5	13.2	13.8	14.7	15.7
87.5°	4.4	4.8	4.7	5.1	5.1	5.5	5.5	6.2	6.5	6.9	6.8
90°	3.0	3.6	4.2	4.7	5.3	5.9	6.3	6.7	7.1	7.5	7.9
92.5°	3.8	3.8	4.4	4.9	5.4	5.9	6.3	6.7	7.1	7.5	7.8
95°	20.1	18.3	15.2	12.1	9.0	5.9	6.3	6.7	7.1	7.5	7.7
97.5°	45.7	42.8	36.6	30.5	24.3	18.2	15.8	13.5	11.3	8.9	7.7
100°	62.6	62.9	63.2	63.5	63.8	64.2	51.9	39.8	27.6	15.3	9.0
102.5°	80.9	81.1	81.3	81.4	81.7	81.9	79.6	77.3	74.9	72.6	68.7
105°	109.7	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9	109.9
107.5°	138.4	138.4	138.6	138.8	138.9	139.1	139.2	139.2	139.2	139.2	139.1
110°	157.8	157.9	158.1	158.2	158.4	158.6	158.3	158.1	157.8	157.6	157.5



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	176.9	177.1	177.2	177.3	177.4	177.5	177.2	176.8	176.5	176.3	176.0
115°	205.2	205.5	205.5	205.6	205.7	205.8	205.5	205.1	204.8	204.5	204.1
117.5°	232.0	232.1	232.4	232.7	233.0	233.3	232.9	232.4	232.0	231.6	231.3
120°	249.4	249.5	249.7	250.0	250.2	250.5	250.3	250.1	250.0	249.8	249.5
122.5°	266.6	266.8	266.9	267.0	267.2	267.3	267.1	266.9	266.8	266.6	266.3
125°	291.8	292.1	292.1	292.1	292.1	292.1	291.8	291.5	291.1	290.8	290.5
127.5°	314.3	314.5	314.4	314.4	314.3	314.2	314.1	313.9	313.7	313.6	313.2
130°	328.4	328.6	328.7	328.8	328.9	329.0	328.7	328.5	328.2	328.0	327.7
132.5°	342.8	343.0	342.8	342.7	342.4	342.3	342.3	342.2	342.1	342.1	341.9
135°	363.1	363.2	363.1	362.9	362.7	362.6	362.4	362.2	362.1	361.9	361.6
137.5°	381.3	381.5	381.3	381.2	381.0	380.8	380.9	380.9	381.0	381.0	380.8
140°	392.3	392.4	392.3	392.2	392.2	392.1	392.2	392.4	392.6	392.7	392.6
142.5°	403.0	403.1	403.2	403.3	403.5	403.6	403.6	403.7	403.7	403.7	403.5
145°	419.3	419.4	419.4	419.4	419.4	419.4	419.5	419.6	419.6	419.7	419.5
147.5°	432.5	432.5	432.7	432.8	432.8	432.9	433.0	433.2	433.3	433.3	433.1
150°	440.8	440.8	441.0	441.2	441.3	441.5	441.6	441.8	442.0	442.1	441.9
152.5°	448.6	448.5	448.7	448.8	449.0	449.1	449.3	449.5	449.6	449.8	449.6
155°	459.1	458.9	459.1	459.3	459.4	459.6	459.8	460.1	460.3	460.6	460.3
157.5°	468.3	468.2	468.2	468.2	468.2	468.3	468.6	468.8	469.0	469.3	469.1
160°	473.4	473.3	473.4	473.4	473.5	473.6	473.9	474.3	474.6	474.9	474.7
162.5°	478.2	478.0	478.1	478.2	478.3	478.3	478.7	479.2	479.7	480.1	480.0
165°	484.5	484.3	484.4	484.5	484.5	484.6	485.1	485.7	486.2	486.7	486.6
167.5°	489.2	488.9	489.0	489.1	489.2	489.3	489.9	490.5	491.1	491.6	491.6
170°	491.5	491.3	491.4	491.5	491.5	491.6	492.3	492.9	493.7	494.3	494.2
172.5°	493.3	493.2	493.3	493.4	493.6	493.7	494.3	494.9	495.5	496.1	496.0
175°	495.6	495.4	495.5	495.5	495.6	495.7	496.4	497.0	497.7	498.3	498.3
177.5°	496.8	496.7	496.8	496.8	496.9	497.0	497.4	497.9	498.3	498.8	498.8
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	422.9	424.0	423.1	424.3	423.1	424.0	422.9	423.8	425.2	424.3	426.4
5°	389.8	388.1	389.2	388.5	389.2	388.1	389.8	390.7	393.0	393.7	395.3
7.5°	359.2	357.6	355.7	354.8	355.7	357.6	359.2	359.7	361.7	364.5	366.6
10°	340.1	337.9	337.8	336.5	337.8	337.9	340.1	342.1	343.4	347.0	349.4
12.5°	326.0	324.1	322.0	321.4	322.0	324.1	326.0	327.8	328.2	332.2	333.9
15°	306.1	304.6	303.3	304.4	303.3	304.6	306.1	307.3	309.3	312.2	314.1
17.5°	289.6	288.4	288.1	286.7	288.1	288.4	289.6	290.2	293.6	295.5	298.7
20°	279.2	278.3	278.7	276.1	278.7	278.3	279.2	280.9	284.3	285.2	288.6
22.5°	270.9	269.0	268.8	268.3	268.8	269.0	270.9	272.5	273.1	276.1	278.3
25°	257.9	257.0	256.0	257.0	256.0	257.0	257.9	259.6	260.3	262.4	264.7
27.5°	246.5	245.4	245.2	245.3	245.2	245.4	246.5	246.4	248.4	250.1	251.8
30°	239.6	237.7	237.9	237.7	237.9	237.7	239.6	239.6	240.8	242.3	243.8
32.5°	232.1	230.8	230.6	230.2	230.6	230.8	232.1	231.8	233.3	235.1	236.7
35°	220.9	220.9	220.0	220.0	220.0	220.9	220.9	221.5	223.1	223.1	224.9
37.5°	210.5	210.3	209.8	209.9	209.8	210.3	210.5	211.0	211.5	212.3	213.5
40°	202.7	202.5	201.9	200.8	201.9	202.5	202.7	203.5	203.8	204.8	205.5
42.5°	195.2	194.5	194.3	193.9	194.3	194.5	195.2	195.6	195.8	197.1	198.6
45°	183.3	183.3	183.0	182.7	183.0	183.3	183.3	183.3	183.5	185.0	185.7
47.5°	171.8	172.1	172.8	172.7	172.8	172.1	171.8	171.5	171.5	172.3	173.2
50°	164.9	165.0	165.6	165.8	165.6	165.0	164.9	164.1	163.7	163.7	164.3
52.5°	157.2	158.2	159.0	158.8	159.0	158.2	157.2	156.5	155.9	155.0	155.8
55°	146.3	147.7	149.0	149.2	149.0	147.7	146.3	144.7	143.9	142.4	143.0
57.5°	135.7	137.5	138.9	139.4	138.9	137.5	135.7	133.7	131.3	130.5	129.5
60°	128.5	130.9	132.6	133.4	132.6	130.9	128.5	126.6	123.4	121.3	120.6
62.5°	121.6	124.3	126.0	126.1	126.0	124.3	121.6	118.6	115.4	113.0	111.5
65°	110.2	113.0	114.5	115.7	114.5	113.0	110.2	107.0	103.5	100.2	98.5
67.5°	98.0	100.9	102.5	103.4	102.5	100.9	98.0	94.0	90.7	87.1	85.1
70°	89.1	92.0	94.2	95.0	94.2	92.0	89.1	84.4	81.6	78.2	76.5
72.5°	80.4	82.9	84.7	85.6	84.7	82.9	80.4	76.0	72.6	69.3	67.0
75°	65.1	68.6	70.3	71.2	70.3	68.6	65.1	62.7	58.9	55.4	53.5
77.5°	50.2	53.3	54.4	54.9	54.4	53.3	50.2	47.4	44.5	41.9	40.1
80°	40.3	42.2	43.5	43.7	43.5	42.2	40.3	38.1	35.8	33.3	31.6
82.5°	31.0	32.5	32.9	33.4	32.9	32.5	31.0	29.0	27.1	25.2	23.8
85°	17.0	17.7	17.9	17.7	17.9	17.7	17.0	15.7	14.7	13.8	13.2
87.5°	7.2	7.1	7.2	7.5	7.2	7.1	7.2	6.8	6.9	6.5	6.2
90°	8.2	8.4	8.6	8.9	8.6	8.4	8.2	7.9	7.5	7.1	6.7
92.5°	7.9	8.1	8.2	8.2	8.2	8.1	7.9	7.8	7.5	7.1	6.7
95°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.5	7.1	6.7
97.5°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	8.9	11.3	13.5
100°	8.7	8.4	8.1	7.7	8.1	8.4	8.7	9.0	15.3	27.6	39.8
102.5°	63.1	57.6	51.9	46.4	51.9	57.6	63.1	68.7	72.6	74.9	77.3
105°	109.8	109.7	109.7	109.6	109.7	109.7	109.8	109.9	109.9	109.9	109.9
107.5°	138.8	138.6	138.4	138.1	138.4	138.6	138.8	139.1	139.2	139.2	139.2
110°	157.6	157.7	157.8	157.8	157.8	157.7	157.6	157.5	157.6	157.8	158.1



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.9	175.8	175.7	175.5	175.7	175.8	175.9	176.0	176.3	176.5	176.8
115°	203.6	203.1	202.6	202.1	202.6	203.1	203.6	204.1	204.5	204.8	205.1
117.5°	231.1	230.9	230.6	230.5	230.6	230.9	231.1	231.3	231.6	232.0	232.4
120°	249.1	248.7	248.3	247.9	248.3	248.7	249.1	249.5	249.8	250.0	250.1
122.5°	265.8	265.3	264.9	264.4	264.9	265.3	265.8	266.3	266.6	266.8	266.9
125°	290.2	290.0	289.8	289.5	289.8	290.0	290.2	290.5	290.8	291.1	291.5
127.5°	312.5	311.9	311.3	310.7	311.3	311.9	312.5	313.2	313.6	313.7	313.9
130°	327.3	326.9	326.4	326.0	326.4	326.9	327.3	327.7	328.0	328.2	328.5
132.5°	341.4	341.0	340.6	340.2	340.6	341.0	341.4	341.9	342.1	342.1	342.2
135°	361.1	360.6	360.1	359.6	360.1	360.6	361.1	361.6	361.9	362.1	362.2
137.5°	380.3	379.9	379.5	379.1	379.5	379.9	380.3	380.8	381.0	381.0	380.9
140°	392.1	391.6	391.1	390.6	391.1	391.6	392.1	392.6	392.7	392.6	392.4
142.5°	403.0	402.5	402.0	401.5	402.0	402.5	403.0	403.5	403.7	403.7	403.7
145°	419.0	418.5	418.0	417.5	418.0	418.5	419.0	419.5	419.7	419.6	419.6
147.5°	432.5	431.9	431.3	430.7	431.3	431.9	432.5	433.1	433.3	433.3	433.2
150°	441.2	440.6	439.9	439.3	439.9	440.6	441.2	441.9	442.1	442.0	441.8
152.5°	449.0	448.4	447.8	447.3	447.8	448.4	449.0	449.6	449.8	449.6	449.5
155°	459.7	459.0	458.4	457.7	458.4	459.0	459.7	460.3	460.6	460.3	460.1
157.5°	468.5	467.8	467.2	466.5	467.2	467.8	468.5	469.1	469.3	469.0	468.8
160°	474.1	473.4	472.8	472.1	472.8	473.4	474.1	474.7	474.9	474.6	474.3
162.5°	479.3	478.6	477.8	477.1	477.8	478.6	479.3	480.0	480.1	479.7	479.2
165°	485.9	485.2	484.5	483.9	484.5	485.2	485.9	486.6	486.7	486.2	485.7
167.5°	490.8	490.1	489.3	488.6	489.3	490.1	490.8	491.6	491.6	491.1	490.5
170°	493.5	492.8	492.0	491.3	492.0	492.8	493.5	494.2	494.3	493.7	492.9
172.5°	495.3	494.6	493.8	493.1	493.8	494.6	495.3	496.0	496.1	495.5	494.9
175°	497.6	496.8	496.1	495.4	496.1	496.8	497.6	498.3	498.3	497.7	497.0
177.5°	498.2	497.7	497.2	496.7	497.2	497.7	498.2	498.8	498.8	498.3	497.9
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	424.4	426.2	428.4	430.2	433.2	434.5	436.2	437.5	439.9	442.2	444.9
5°	395.8	399.0	403.3	408.1	413.5	417.3	422.6	425.7	432.2	438.0	443.7
7.5°	369.9	373.8	379.9	386.0	393.1	399.6	406.2	413.5	421.7	431.4	439.4
10°	352.1	357.3	363.9	371.5	380.2	387.7	396.6	404.5	414.5	425.7	436.3
12.5°	337.9	342.4	349.8	357.0	366.3	375.5	384.7	395.1	406.8	419.3	432.5
15°	318.4	322.1	328.2	338.2	347.6	356.6	370.4	380.2	394.8	408.8	424.9
17.5°	301.7	306.4	311.4	320.0	329.8	341.0	353.4	365.7	379.8	397.5	415.5
20°	291.5	295.2	301.0	307.6	318.0	329.3	341.0	353.4	370.7	389.1	408.5
22.5°	280.3	284.4	291.0	298.2	306.9	317.7	330.6	344.2	362.3	380.3	401.4
25°	267.2	269.9	276.0	282.4	291.1	300.3	313.6	328.7	346.7	367.2	388.7
27.5°	254.8	257.2	262.7	268.3	276.1	287.1	299.1	314.3	331.2	352.0	375.8
30°	245.8	248.5	253.4	259.4	266.9	276.5	288.8	303.1	321.2	341.5	366.4
32.5°	238.1	240.5	244.2	250.2	257.6	266.9	278.3	292.9	311.0	331.6	356.0
35°	226.2	228.9	231.7	236.4	242.8	251.8	264.3	278.1	295.4	315.4	337.8
37.5°	214.4	217.3	219.8	224.0	229.8	237.8	248.6	262.9	278.6	297.8	319.4
40°	207.0	209.3	211.4	215.9	221.8	229.3	239.3	252.1	268.6	286.6	304.4
42.5°	199.7	201.8	203.5	207.5	212.9	220.0	229.6	242.1	257.5	274.2	290.0
45°	188.0	189.3	191.4	194.8	199.1	205.7	214.9	226.1	239.0	254.9	266.8
47.5°	175.5	177.5	179.2	182.1	185.7	192.2	201.1	210.5	222.3	234.1	242.4
50°	165.8	167.9	170.3	173.2	176.5	182.5	190.6	200.2	210.3	219.3	226.4
52.5°	156.7	158.7	161.3	164.0	168.1	173.2	180.1	188.7	198.5	205.0	210.9
55°	143.3	144.3	147.3	149.9	153.9	157.7	164.7	172.2	178.2	183.1	188.0
57.5°	129.7	130.9	132.7	135.1	139.0	143.4	148.3	155.0	158.5	161.0	164.9
60°	120.9	121.3	122.5	125.3	128.3	132.2	137.9	142.6	145.3	147.3	150.5
62.5°	111.3	111.4	113.2	115.4	117.6	121.9	126.5	130.3	132.4	133.5	136.5
65°	97.8	97.4	98.5	100.2	102.9	105.7	109.7	113.0	112.8	114.0	115.9
67.5°	84.0	83.6	83.6	85.2	87.3	89.8	92.5	94.6	94.6	96.0	97.0
70°	74.6	73.5	74.2	75.6	76.5	78.6	81.6	82.3	82.5	83.2	84.2
72.5°	65.0	64.6	65.1	65.7	66.4	68.0	70.6	71.0	71.1	71.5	73.1
75°	51.6	51.3	50.9	51.4	52.2	53.3	54.2	55.0	54.8	55.0	56.2
77.5°	38.7	37.7	37.4	37.7	37.9	38.6	39.6	39.5	39.7	39.7	40.9
80°	30.7	29.2	29.0	29.0	29.2	29.6	29.9	30.3	29.8	30.3	30.7
82.5°	22.6	21.7	21.6	21.4	21.5	21.6	21.9	22.0	21.9	22.2	22.4
85°	12.5	12.1	11.5	11.9	11.7	11.1	11.5	10.9	10.8	10.9	11.1
87.5°	5.5	5.5	5.1	5.1	4.7	4.8	4.4	4.1	3.8	3.8	4.2
90°	6.3	5.9	5.3	4.7	4.2	3.6	3.0	2.4	1.7	1.1	0.4
92.5°	6.3	5.9	5.4	4.9	4.4	3.8	3.8	4.3	4.7	5.2	5.7
95°	6.3	5.9	9.0	12.1	15.2	18.3	20.1	20.3	20.5	20.8	21.0
97.5°	15.8	18.2	24.3	30.5	36.6	42.8	45.7	45.2	44.8	44.4	43.9
100°	51.9	64.2	63.8	63.5	63.2	62.9	62.6	62.4	62.1	61.9	61.6
102.5°	79.6	81.9	81.7	81.4	81.3	81.1	80.9	80.6	80.2	79.9	79.6
105°	109.9	109.9	109.9	109.9	109.9	109.9	109.7	109.4	109.1	108.8	108.4
107.5°	139.2	139.1	138.9	138.8	138.6	138.4	138.4	138.4	138.4	138.4	138.4
110°	158.3	158.6	158.4	158.2	158.1	157.9	157.8	157.8	157.8	157.8	157.8



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	177.5	177.4	177.3	177.2	177.1	176.9	176.8	176.5	176.3	176.2
115°	205.5	205.8	205.7	205.6	205.5	205.5	205.2	204.8	204.4	204.0	203.6
117.5°	232.9	233.3	233.0	232.7	232.4	232.1	232.0	232.0	232.0	232.0	232.0
120°	250.3	250.5	250.2	250.0	249.7	249.5	249.4	249.5	249.6	249.6	249.7
122.5°	267.1	267.3	267.2	267.0	266.9	266.8	266.6	266.3	266.0	265.6	265.4
125°	291.8	292.1	292.1	292.1	292.1	292.1	291.8	291.2	290.7	290.1	289.5
127.5°	314.1	314.2	314.3	314.4	314.4	314.5	314.3	313.9	313.5	313.1	312.6
130°	328.7	329.0	328.9	328.8	328.7	328.6	328.4	328.0	327.6	327.2	326.8
132.5°	342.3	342.3	342.4	342.7	342.8	343.0	342.8	342.3	341.9	341.4	341.0
135°	362.4	362.6	362.7	362.9	363.1	363.2	363.1	362.6	362.1	361.6	361.1
137.5°	380.9	380.8	381.0	381.2	381.3	381.5	381.3	380.9	380.4	380.0	379.6
140°	392.2	392.1	392.2	392.2	392.3	392.4	392.3	392.2	392.0	391.8	391.7
142.5°	403.6	403.6	403.5	403.3	403.2	403.1	403.0	402.9	402.8	402.8	402.6
145°	419.5	419.4	419.4	419.4	419.4	419.4	419.3	419.1	419.0	418.8	418.7
147.5°	433.0	432.9	432.8	432.8	432.7	432.5	432.5	432.5	432.6	432.6	432.7
150°	441.6	441.5	441.3	441.2	441.0	440.8	440.8	441.0	441.2	441.3	441.5
152.5°	449.3	449.1	449.0	448.8	448.7	448.5	448.6	449.0	449.3	449.7	450.0
155°	459.8	459.6	459.4	459.3	459.1	458.9	459.1	459.6	460.1	460.6	461.1
157.5°	468.6	468.3	468.2	468.2	468.2	468.2	468.3	468.6	469.0	469.2	469.5
160°	473.9	473.6	473.5	473.4	473.4	473.3	473.4	473.9	474.4	474.9	475.4
162.5°	478.7	478.3	478.3	478.2	478.1	478.0	478.2	478.7	479.2	479.6	480.1
165°	485.1	484.6	484.5	484.5	484.4	484.3	484.5	485.0	485.5	486.0	486.5
167.5°	489.9	489.3	489.2	489.1	489.0	488.9	489.2	489.7	490.2	490.7	491.2
170°	492.3	491.6	491.5	491.5	491.4	491.3	491.5	492.1	492.7	493.3	493.9
172.5°	494.3	493.7	493.6	493.4	493.3	493.2	493.3	493.9	494.5	495.0	495.6
175°	496.4	495.7	495.6	495.5	495.5	495.4	495.6	496.1	496.6	497.1	497.6
177.5°	497.4	497.0	496.9	496.8	496.8	496.7	496.8	497.3	497.7	498.1	498.5
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	446.3	448.3	449.7	452.2	454.4	455.6	456.6	457.5	458.6	459.5	462.1
5°	449.1	454.0	458.2	464.6	470.4	474.9	479.8	484.1	487.7	492.8	496.8
7.5°	447.8	456.6	465.7	475.6	485.8	495.1	503.9	511.9	519.3	528.2	536.0
10°	446.7	458.5	470.2	483.6	497.3	509.0	519.9	531.1	539.2	550.5	560.1
12.5°	445.8	459.7	473.9	489.9	505.0	521.5	536.1	544.2	556.5	565.6	577.0
15°	442.0	460.4	479.8	497.9	519.4	534.7	547.5	563.3	574.8	586.3	598.7
17.5°	435.1	456.1	477.8	501.5	522.0	538.4	555.0	570.2	583.9	599.3	614.8
20°	431.9	452.9	477.8	502.1	522.2	539.3	556.3	573.1	588.2	608.0	625.8
22.5°	425.3	450.6	473.5	497.3	518.0	536.6	555.9	574.9	594.9	617.3	639.7
25°	413.5	439.1	463.4	486.8	507.7	531.1	551.6	577.1	602.7	632.3	660.1
27.5°	401.2	425.7	448.0	470.6	495.0	521.5	548.0	576.9	610.5	647.8	687.1
30°	391.3	414.5	436.1	459.3	484.7	514.5	543.7	578.0	616.8	658.8	705.6
32.5°	379.7	401.0	422.1	446.6	474.3	505.7	539.8	577.4	624.0	671.7	719.8
35°	359.8	377.7	399.4	425.6	456.8	492.8	532.2	576.7	630.1	685.0	725.5
37.5°	336.3	352.9	375.8	404.5	437.2	475.9	522.6	575.4	632.2	675.9	688.9
40°	320.4	335.9	359.6	389.4	422.9	463.8	515.0	570.8	625.8	653.7	642.9
42.5°	303.5	319.8	342.9	372.3	408.5	453.0	505.6	561.3	607.5	618.0	580.9
45°	277.0	293.7	316.5	346.3	385.1	433.3	488.1	538.8	565.3	546.3	488.9
47.5°	252.2	267.9	289.0	319.8	359.8	409.7	462.4	502.9	505.0	459.6	398.2
50°	235.3	249.8	271.1	301.8	341.5	392.1	439.7	471.6	457.2	405.8	346.8
52.5°	218.7	232.9	253.9	284.3	323.6	369.9	414.3	436.6	409.6	356.8	306.5
55°	194.8	207.2	227.8	255.8	293.1	336.1	373.7	381.5	346.4	294.5	253.6
57.5°	171.5	183.0	201.7	227.6	261.7	299.7	329.2	327.5	290.5	245.9	213.4
60°	155.6	166.9	183.5	208.7	239.9	272.6	297.8	291.8	255.1	216.6	189.3
62.5°	141.5	151.6	167.2	189.3	217.7	248.0	268.7	259.8	223.9	190.3	168.7
65°	120.6	129.1	142.4	161.3	184.8	209.9	225.9	214.4	183.7	157.5	140.1
67.5°	100.6	107.5	118.6	133.7	153.8	173.9	183.6	172.1	147.5	128.4	115.5
70°	88.0	94.0	102.6	116.0	133.5	150.5	157.8	147.5	126.4	110.0	100.8
72.5°	75.3	80.3	87.9	100.0	114.0	128.7	135.1	125.2	107.9	94.0	85.4
75°	58.2	61.6	66.9	75.2	86.3	98.0	101.5	92.9	81.8	71.4	65.7
77.5°	41.7	44.5	48.5	53.7	61.6	69.1	72.2	67.2	58.6	52.0	47.4
80°	32.0	33.5	36.9	41.3	47.5	52.2	54.2	51.0	45.0	40.1	36.5
82.5°	22.8	24.4	26.3	29.9	33.9	37.1	39.3	37.2	32.9	28.9	26.9
85°	11.1	12.1	13.2	14.7	17.7	19.6	19.4	18.1	16.4	14.9	13.8
87.5°	4.2	4.4	5.0	5.9	6.4	7.2	7.6	7.4	6.9	6.5	6.2
90°	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	5.9	6.3	6.7
92.5°	5.2	4.7	4.3	3.8	3.8	4.4	4.9	5.4	5.9	6.3	6.7
95°	20.8	20.5	20.3	20.1	18.3	15.2	12.1	9.0	5.9	6.3	6.7
97.5°	44.4	44.8	45.2	45.7	42.8	36.6	30.5	24.3	18.2	15.8	13.5
100°	61.9	62.1	62.4	62.6	62.9	63.2	63.5	63.8	64.2	51.9	39.8
102.5°	79.9	80.2	80.6	80.9	81.1	81.3	81.4	81.7	81.9	79.6	77.3
105°	108.8	109.1	109.4	109.7	109.9	109.9	109.9	109.9	109.9	109.9	109.9
107.5°	138.4	138.4	138.4	138.4	138.4	138.6	138.8	138.9	139.1	139.2	139.2
110°	157.8	157.8	157.8	157.8	157.9	158.1	158.2	158.4	158.6	158.3	158.1



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	176.3	176.5	176.8	176.9	177.1	177.2	177.3	177.4	177.5	177.2	176.8
115°	204.0	204.4	204.8	205.2	205.5	205.5	205.6	205.7	205.8	205.5	205.1
117.5°	232.0	232.0	232.0	232.0	232.1	232.4	232.7	233.0	233.3	232.9	232.4
120°	249.6	249.6	249.5	249.4	249.5	249.7	250.0	250.2	250.5	250.3	250.1
122.5°	265.6	266.0	266.3	266.6	266.8	266.9	267.0	267.2	267.3	267.1	266.9
125°	290.1	290.7	291.2	291.8	292.1	292.1	292.1	292.1	292.1	291.8	291.5
127.5°	313.1	313.5	313.9	314.3	314.5	314.4	314.4	314.3	314.2	314.1	313.9
130°	327.2	327.6	328.0	328.4	328.6	328.7	328.8	328.9	329.0	328.7	328.5
132.5°	341.4	341.9	342.3	342.8	343.0	342.8	342.7	342.4	342.3	342.3	342.2
135°	361.6	362.1	362.6	363.1	363.2	363.1	362.9	362.7	362.6	362.4	362.2
137.5°	380.0	380.4	380.9	381.3	381.5	381.3	381.2	381.0	380.8	380.9	380.9
140°	391.8	392.0	392.2	392.3	392.4	392.3	392.2	392.2	392.1	392.2	392.4
142.5°	402.8	402.8	402.9	403.0	403.1	403.2	403.3	403.5	403.6	403.6	403.7
145°	418.8	419.0	419.1	419.3	419.4	419.4	419.4	419.4	419.4	419.5	419.6
147.5°	432.6	432.6	432.5	432.5	432.5	432.7	432.8	432.8	432.9	433.0	433.2
150°	441.3	441.2	441.0	440.8	440.8	441.0	441.2	441.3	441.5	441.6	441.8
152.5°	449.7	449.3	449.0	448.6	448.5	448.7	448.8	449.0	449.1	449.3	449.5
155°	460.6	460.1	459.6	459.1	458.9	459.1	459.3	459.4	459.6	459.8	460.1
157.5°	469.2	469.0	468.6	468.3	468.2	468.2	468.2	468.2	468.3	468.6	468.8
160°	474.9	474.4	473.9	473.4	473.3	473.4	473.4	473.5	473.6	473.9	474.3
162.5°	479.6	479.2	478.7	478.2	478.0	478.1	478.2	478.3	478.3	478.7	479.2
165°	486.0	485.5	485.0	484.5	484.3	484.4	484.5	484.5	484.6	485.1	485.7
167.5°	490.7	490.2	489.7	489.2	488.9	489.0	489.1	489.2	489.3	489.9	490.5
170°	493.3	492.7	492.1	491.5	491.3	491.4	491.5	491.5	491.6	492.3	492.9
172.5°	495.0	494.5	493.9	493.3	493.2	493.3	493.4	493.6	493.7	494.3	494.9
175°	497.1	496.6	496.1	495.6	495.4	495.5	495.5	495.6	495.7	496.4	497.0
177.5°	498.1	497.7	497.3	496.8	496.7	496.8	496.8	496.9	497.0	497.4	497.9
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	464.2	465.4	468.0	467.1	468.2	468.9	469.4
5°	501.7	507.7	510.4	510.0	514.0	513.0	512.0
7.5°	544.0	550.3	553.9	558.3	560.8	561.1	563.3
10°	568.0	576.3	579.7	584.4	587.4	589.1	588.9
12.5°	586.4	592.9	600.5	602.8	606.8	609.0	608.2
15°	608.5	618.9	626.8	630.7	635.9	637.3	639.4
17.5°	628.3	642.1	651.3	663.7	668.3	671.2	669.4
20°	643.2	661.5	670.7	685.3	693.5	697.8	696.3
22.5°	660.8	680.6	697.7	710.4	722.7	728.6	729.8
25°	691.0	718.1	743.2	759.9	775.2	778.8	786.7
27.5°	724.8	756.8	783.6	801.2	811.8	815.8	818.3
30°	746.0	777.9	798.0	809.3	812.7	812.4	812.0
32.5°	756.4	776.3	780.2	777.1	769.3	762.7	755.9
35°	741.7	726.8	704.6	676.0	654.8	633.6	631.4
37.5°	667.1	619.5	582.4	541.1	517.3	502.6	492.4
40°	596.8	542.7	497.9	463.1	438.8	429.2	419.7
42.5°	520.6	468.9	429.2	400.1	381.8	371.1	363.7
45°	422.9	377.3	346.3	325.1	310.6	302.4	297.7
47.5°	346.6	312.8	286.4	271.2	261.2	254.8	254.8
50°	305.6	273.4	255.8	243.8	235.1	230.0	231.0
52.5°	269.2	245.2	230.2	220.1	213.7	210.6	210.4
55°	225.1	207.8	198.0	190.6	186.3	182.7	183.5
57.5°	192.6	178.0	171.4	165.3	162.2	160.9	158.7
60°	172.4	161.1	155.4	150.5	147.5	146.3	144.3
62.5°	154.4	145.5	140.1	136.1	133.4	133.0	131.3
65°	129.8	123.0	118.1	116.3	113.4	112.7	112.7
67.5°	107.0	102.2	98.3	96.6	95.4	95.6	94.7
70°	92.7	88.7	86.3	84.4	83.5	83.6	82.9
72.5°	81.1	76.6	74.5	73.4	72.2	72.6	72.3
75°	61.4	59.2	58.0	56.9	56.2	55.8	55.4
77.5°	45.1	43.1	42.2	41.6	41.7	40.8	41.5
80°	34.8	33.2	32.6	31.6	31.5	31.5	31.3
82.5°	25.5	24.5	24.1	23.4	23.0	23.3	22.8
85°	13.2	12.5	12.2	12.2	11.9	11.5	12.5
87.5°	6.3	5.7	5.8	5.7	5.7	5.6	5.4
90°	7.1	7.5	7.9	8.2	8.4	8.6	8.9
92.5°	7.1	7.5	7.8	7.9	8.1	8.2	8.2
95°	7.1	7.5	7.7	7.7	7.7	7.7	7.7
97.5°	11.3	8.9	7.7	7.7	7.7	7.7	7.7
100°	27.6	15.3	9.0	8.7	8.4	8.1	7.7
102.5°	74.9	72.6	68.7	63.1	57.6	51.9	46.4
105°	109.9	109.9	109.9	109.8	109.7	109.7	109.6
107.5°	139.2	139.2	139.1	138.8	138.6	138.4	138.1
110°	157.8	157.6	157.5	157.6	157.7	157.8	157.8



TEST NUMBER: P333340-930

CATALOG NUMBER: S125DIW-S375D470U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	176.5	176.3	176.0	175.9	175.8	175.7	175.5
115°	204.8	204.5	204.1	203.6	203.1	202.6	202.1
117.5°	232.0	231.6	231.3	231.1	230.9	230.6	230.5
120°	250.0	249.8	249.5	249.1	248.7	248.3	247.9
122.5°	266.8	266.6	266.3	265.8	265.3	264.9	264.4
125°	291.1	290.8	290.5	290.2	290.0	289.8	289.5
127.5°	313.7	313.6	313.2	312.5	311.9	311.3	310.7
130°	328.2	328.0	327.7	327.3	326.9	326.4	326.0
132.5°	342.1	342.1	341.9	341.4	341.0	340.6	340.2
135°	362.1	361.9	361.6	361.1	360.6	360.1	359.6
137.5°	381.0	381.0	380.8	380.3	379.9	379.5	379.1
140°	392.6	392.7	392.6	392.1	391.6	391.1	390.6
142.5°	403.7	403.7	403.5	403.0	402.5	402.0	401.5
145°	419.6	419.7	419.5	419.0	418.5	418.0	417.5
147.5°	433.3	433.3	433.1	432.5	431.9	431.3	430.7
150°	442.0	442.1	441.9	441.2	440.6	439.9	439.3
152.5°	449.6	449.8	449.6	449.0	448.4	447.8	447.3
155°	460.3	460.6	460.3	459.7	459.0	458.4	457.7
157.5°	469.0	469.3	469.1	468.5	467.8	467.2	466.5
160°	474.6	474.9	474.7	474.1	473.4	472.8	472.1
162.5°	479.7	480.1	480.0	479.3	478.6	477.8	477.1
165°	486.2	486.7	486.6	485.9	485.2	484.5	483.9
167.5°	491.1	491.6	491.6	490.8	490.1	489.3	488.6
170°	493.7	494.3	494.2	493.5	492.8	492.0	491.3
172.5°	495.5	496.1	496.0	495.3	494.6	493.8	493.1
175°	497.7	498.3	498.3	497.6	496.8	496.1	495.4
177.5°	498.3	498.8	498.8	498.2	497.7	497.2	496.7
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6

(END OF REPORT)