

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333347-930

Luminaire Tested: **S125DIW-S375D770U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333347-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D770U930-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3424.3 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	37	31
2	87	79	73	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2866	2866	2866	2866
5°	3319	2877	2519	2877
10°	3862	2861	2207	2861
15°	4275	2841	2035	2841
20°	4786	2808	1898	2808
25°	5606	2770	1831	2770
30°	6055	2732	1773	2732
35°	4978	2663	1735	2663
40°	3538	2566	1693	2566
45°	2719	2437	1669	2437
50°	2321	2275	1666	2275
55°	2066	2117	1680	2117
60°	1864	1944	1723	1944
65°	1722	1771	1768	1771
70°	1565	1590	1794	1590
75°	1382	1402	1777	1402
80°	1164	1142	1625	1142
85°	926	823	1312	823



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.2
10°-20°	127.2	3.7
20°-30°	206.6	6.0
30°-40°	252.0	7.4
40°-50°	229.2	6.7
50°-60°	182.6	5.3
60°-70°	127.2	3.7
70°-80°	67.8	2.0
80°-90°	18.8	0.5
90°-100°	52.1	1.5
100°-110°	153.8	4.5
110°-120°	260.5	7.6
120°-130°	342.9	10.0
130°-140°	384.2	11.2
140°-150°	376.6	11.0
150°-160°	316.3	9.2
160°-170°	210.2	6.1
170°-180°	73.6	2.1
0°-30°	376.5	11.0
0°-40°	628.5	18.4
0°-60°	1040.3	30.4
0°-90°	1254.1	36.6
90°-120°	466.4	13.6
90°-150°	1570.1	45.9
90°-180°	2170.0	63.4
0°-180°	3424.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	512	444	388	444	512	52
15°	639	425	304	425	639	183
25°	787	389	257	389	787	359
35°	631	338	220	338	631	386
45°	298	267	183	267	298	238
55°	184	188	149	188	184	165
65°	113	116	116	116	113	112
75°	55	56	71	56	55	60
85°	12	11	18	11	12	15
90°	14	1	14	1	14	9
95°	52	39	52	39	52	53
105°	150	138	150	138	150	159
115°	263	261	263	261	263	260
125°	383	381	383	381	383	342
135°	497	495	497	495	497	383
145°	602	600	602	600	602	376
155°	686	686	686	686	686	316
165°	744	746	744	746	744	210
175°	773	776	773	776	773	73
180°	778	778	778	778	778	



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	469.4	468.9	468.2	467.1	468.0	465.4	464.2	462.1	459.5	458.6	457.5
5°	512.0	513.0	514.0	510.0	510.4	507.7	501.7	496.8	492.8	487.7	484.1
7.5°	563.3	561.1	560.8	558.3	553.9	550.3	544.0	536.0	528.2	519.3	511.9
10°	588.9	589.1	587.4	584.4	579.7	576.3	568.0	560.1	550.5	539.2	531.1
12.5°	608.2	609.0	606.8	602.8	600.5	592.9	586.4	577.0	565.6	556.5	544.2
15°	639.4	637.3	635.9	630.7	626.8	618.9	608.5	598.7	586.3	574.8	563.3
17.5°	669.4	671.2	668.3	663.7	651.3	642.1	628.3	614.8	599.3	583.9	570.2
20°	696.3	697.8	693.5	685.3	670.7	661.5	643.2	625.8	608.0	588.2	573.1
22.5°	729.8	728.6	722.7	710.4	697.7	680.6	660.8	639.7	617.3	594.9	574.9
25°	786.7	778.8	775.2	759.9	743.2	718.1	691.0	660.1	632.3	602.7	577.1
27.5°	818.3	815.8	811.8	801.2	783.6	756.8	724.8	687.1	647.8	610.5	576.9
30°	812.0	812.4	812.7	809.3	798.0	777.9	746.0	705.6	658.8	616.8	578.0
32.5°	755.9	762.7	769.3	777.1	780.2	776.3	756.4	719.8	671.7	624.0	577.4
35°	631.4	633.6	654.8	676.0	704.6	726.8	741.7	725.5	685.0	630.1	576.7
37.5°	492.4	502.6	517.3	541.1	582.4	619.5	667.1	688.9	675.9	632.2	575.4
40°	419.7	429.2	438.8	463.1	497.9	542.7	596.8	642.9	653.7	625.8	570.8
42.5°	363.7	371.1	381.8	400.1	429.2	468.9	520.6	580.9	618.0	607.5	561.3
45°	297.7	302.4	310.6	325.1	346.3	377.3	422.9	488.9	546.3	565.3	538.8
47.5°	254.8	254.8	261.2	271.2	286.4	312.8	346.6	398.2	459.6	505.0	502.9
50°	231.0	230.0	235.1	243.8	255.8	273.4	305.6	346.8	405.8	457.2	471.6
52.5°	210.4	210.6	213.7	220.1	230.2	245.2	269.2	306.5	356.8	409.6	436.6
55°	183.5	182.7	186.3	190.6	198.0	207.8	225.1	253.6	294.5	346.4	381.5
57.5°	158.7	160.9	162.2	165.3	171.4	178.0	192.6	213.4	245.9	290.5	327.5
60°	144.3	146.3	147.5	150.5	155.4	161.1	172.4	189.3	216.6	255.1	291.8
62.5°	131.3	133.0	133.4	136.1	140.1	145.5	154.4	168.7	190.3	223.9	259.8
65°	112.7	112.7	113.4	116.3	118.1	123.0	129.8	140.1	157.5	183.7	214.4
67.5°	94.7	95.6	95.4	96.6	98.3	102.2	107.0	115.5	128.4	147.5	172.1
70°	82.9	83.6	83.5	84.4	86.3	88.7	92.7	100.8	110.0	126.4	147.5
72.5°	72.3	72.6	72.2	73.4	74.5	76.6	81.1	85.4	94.0	107.9	125.2
75°	55.4	55.8	56.2	56.9	58.0	59.2	61.4	65.7	71.4	81.8	92.9
77.5°	41.5	40.8	41.7	41.6	42.2	43.1	45.1	47.4	52.0	58.6	67.2
80°	31.3	31.5	31.5	31.6	32.6	33.2	34.8	36.5	40.1	45.0	51.0
82.5°	22.8	23.3	23.0	23.4	24.1	24.5	25.5	26.9	28.9	32.9	37.2
85°	12.5	11.5	11.9	12.2	12.2	12.5	13.2	13.8	14.9	16.4	18.1
87.5°	6.5	6.8	6.8	6.8	6.8	6.7	7.2	7.0	7.3	7.7	8.1
90°	14.5	14.1	13.7	13.3	12.9	12.4	11.7	11.0	10.4	9.7	8.7
92.5°	28.5	28.3	28.0	27.7	27.4	26.8	25.9	25.0	24.1	23.2	22.1
95°	52.0	51.8	51.5	51.3	51.0	50.4	49.4	48.5	47.5	46.6	45.2
97.5°	78.9	78.8	78.6	78.4	78.3	77.8	76.9	76.0	75.1	74.2	72.3
100°	99.2	99.0	98.7	98.5	98.2	97.4	96.2	95.0	93.8	92.6	90.8
102.5°	119.6	119.2	118.9	118.5	118.1	117.2	115.9	114.6	113.3	111.9	111.0
105°	150.1	149.7	149.3	148.9	148.5	147.9	147.1	146.3	145.4	144.6	143.8
107.5°	181.3	181.3	181.4	181.4	181.4	181.2	180.8	180.4	180.0	179.6	179.0
110°	204.6	204.7	204.8	205.0	205.1	205.0	204.6	204.2	203.7	203.3	202.9



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	227.3	227.6	227.8	228.0	228.3	228.3	228.1	228.0	227.8	227.6	227.1
115°	263.3	263.4	263.6	263.7	263.8	263.9	264.1	264.2	264.3	264.5	264.2
117.5°	298.4	298.9	299.5	300.0	300.5	300.8	300.6	300.5	300.4	300.4	300.1
120°	322.6	323.1	323.7	324.2	324.7	325.0	325.0	325.0	325.0	325.0	324.9
122.5°	346.8	347.2	347.6	348.1	348.5	348.8	348.9	349.0	349.1	349.2	348.9
125°	383.1	383.3	383.4	383.5	383.7	383.8	384.1	384.4	384.7	384.9	384.8
127.5°	418.0	418.2	418.5	418.8	419.1	419.2	419.4	419.6	419.6	419.8	419.6
130°	441.2	441.5	441.7	442.1	442.3	442.5	442.6	442.8	442.9	443.0	442.8
132.5°	463.0	463.4	463.7	464.1	464.5	464.8	464.9	465.0	465.2	465.3	465.4
135°	496.9	497.4	498.0	498.5	499.0	499.3	499.3	499.3	499.3	499.3	499.2
137.5°	530.0	530.8	531.4	532.1	532.7	533.0	532.9	532.7	532.6	532.4	532.1
140°	551.4	552.0	552.7	553.4	554.1	554.2	554.0	553.8	553.4	553.2	552.8
142.5°	571.7	572.3	573.1	573.7	574.4	574.6	574.5	574.3	574.1	574.0	573.5
145°	602.2	602.6	603.0	603.4	603.8	604.1	604.1	604.1	604.1	604.1	603.6
147.5°	628.3	629.2	630.1	631.0	631.9	632.2	631.9	631.5	631.2	630.9	630.6
150°	647.6	647.8	648.2	648.4	648.7	648.8	648.8	648.8	648.8	648.8	648.2
152.5°	663.6	664.1	664.6	665.0	665.5	665.6	665.3	665.0	664.6	664.3	664.1
155°	686.3	687.0	687.7	688.4	689.0	689.1	688.5	688.0	687.5	687.0	686.8
157.5°	705.3	706.2	707.1	708.0	708.9	709.1	708.5	708.0	707.4	706.9	706.8
160°	718.4	719.1	719.7	720.4	721.1	721.1	720.6	720.1	719.6	719.0	718.8
162.5°	729.5	730.3	731.1	731.9	732.7	732.7	732.1	731.5	730.8	730.2	730.1
165°	744.4	745.3	746.1	746.9	747.6	747.8	747.3	746.7	746.2	745.7	745.5
167.5°	756.3	757.2	758.0	758.8	759.6	759.6	758.9	758.1	757.2	756.4	756.4
170°	762.6	763.5	764.5	765.4	766.4	766.5	765.6	764.8	764.0	763.2	763.2
172.5°	767.9	768.7	769.6	770.5	771.3	771.3	770.5	769.6	768.8	768.0	768.0
175°	772.9	773.8	774.8	775.7	776.7	776.7	775.9	775.1	774.3	773.5	773.5
177.5°	775.8	776.6	777.3	778.0	778.8	778.9	778.2	777.6	776.9	776.2	776.4
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	456.6	455.6	454.4	452.2	449.7	448.3	446.3	444.9	442.2	439.9	437.5
5°	479.8	474.9	470.4	464.6	458.2	454.0	449.1	443.7	438.0	432.2	425.7
7.5°	503.9	495.1	485.8	475.6	465.7	456.6	447.8	439.4	431.4	421.7	413.5
10°	519.9	509.0	497.3	483.6	470.2	458.5	446.7	436.3	425.7	414.5	404.5
12.5°	536.1	521.5	505.0	489.9	473.9	459.7	445.8	432.5	419.3	406.8	395.1
15°	547.5	534.7	519.4	497.9	479.8	460.4	442.0	424.9	408.8	394.8	380.2
17.5°	555.0	538.4	522.0	501.5	477.8	456.1	435.1	415.5	397.5	379.8	365.7
20°	556.3	539.3	522.2	502.1	477.8	452.9	431.9	408.5	389.1	370.7	353.4
22.5°	555.9	536.6	518.0	497.3	473.5	450.6	425.3	401.4	380.3	362.3	344.2
25°	551.6	531.1	507.7	486.8	463.4	439.1	413.5	388.7	367.2	346.7	328.7
27.5°	548.0	521.5	495.0	470.6	448.0	425.7	401.2	375.8	352.0	331.2	314.3
30°	543.7	514.5	484.7	459.3	436.1	414.5	391.3	366.4	341.5	321.2	303.1
32.5°	539.8	505.7	474.3	446.6	422.1	401.0	379.7	356.0	331.6	311.0	292.9
35°	532.2	492.8	456.8	425.6	399.4	377.7	359.8	337.8	315.4	295.4	278.1
37.5°	522.6	475.9	437.2	404.5	375.8	352.9	336.3	319.4	297.8	278.6	262.9
40°	515.0	463.8	422.9	389.4	359.6	335.9	320.4	304.4	286.6	268.6	252.1
42.5°	505.6	453.0	408.5	372.3	342.9	319.8	303.5	290.0	274.2	257.5	242.1
45°	488.1	433.3	385.1	346.3	316.5	293.7	277.0	266.8	254.9	239.0	226.1
47.5°	462.4	409.7	359.8	319.8	289.0	267.9	252.2	242.4	234.1	222.3	210.5
50°	439.7	392.1	341.5	301.8	271.1	249.8	235.3	226.4	219.3	210.3	200.2
52.5°	414.3	369.9	323.6	284.3	253.9	232.9	218.7	210.9	205.0	198.5	188.7
55°	373.7	336.1	293.1	255.8	227.8	207.2	194.8	188.0	183.1	178.2	172.2
57.5°	329.2	299.7	261.7	227.6	201.7	183.0	171.5	164.9	161.0	158.5	155.0
60°	297.8	272.6	239.9	208.7	183.5	166.9	155.6	150.5	147.3	145.3	142.6
62.5°	268.7	248.0	217.7	189.3	167.2	151.6	141.5	136.5	133.5	132.4	130.3
65°	225.9	209.9	184.8	161.3	142.4	129.1	120.6	115.9	114.0	112.8	113.0
67.5°	183.6	173.9	153.8	133.7	118.6	107.5	100.6	97.0	96.0	94.6	94.6
70°	157.8	150.5	133.5	116.0	102.6	94.0	88.0	84.2	83.2	82.5	82.3
72.5°	135.1	128.7	114.0	100.0	87.9	80.3	75.3	73.1	71.5	71.1	71.0
75°	101.5	98.0	86.3	75.2	66.9	61.6	58.2	56.2	55.0	54.8	55.0
77.5°	72.2	69.1	61.6	53.7	48.5	44.5	41.7	40.9	39.7	39.7	39.5
80°	54.2	52.2	47.5	41.3	36.9	33.5	32.0	30.7	30.3	29.8	30.3
82.5°	39.3	37.1	33.9	29.9	26.3	24.4	22.8	22.4	22.2	21.9	22.0
85°	19.4	19.6	17.7	14.7	13.2	12.1	11.1	11.1	10.9	10.8	10.9
87.5°	8.2	7.7	6.9	6.3	5.3	4.6	4.2	4.2	3.9	4.0	4.4
90°	7.8	6.8	6.0	4.9	3.8	2.8	1.7	0.6	1.7	2.8	3.8
92.5°	21.0	19.8	18.6	17.7	16.9	16.1	15.4	14.7	15.4	16.1	16.9
95°	43.9	42.6	41.3	40.4	40.1	39.9	39.6	39.4	39.6	39.9	40.1
97.5°	70.5	68.6	66.8	65.8	65.7	65.6	65.5	65.4	65.5	65.6	65.7
100°	89.1	87.3	85.6	84.7	84.7	84.7	84.7	84.7	84.7	84.7	84.7
102.5°	110.2	109.3	108.4	107.7	107.1	106.6	106.1	105.6	106.1	106.6	107.1
105°	143.0	142.3	141.5	140.7	140.0	139.3	138.7	138.0	138.7	139.3	140.0
107.5°	178.4	177.8	177.2	176.5	175.9	175.2	174.5	173.8	174.5	175.2	175.9
110°	202.5	202.1	201.7	201.2	200.6	199.8	199.2	198.5	199.2	199.8	200.6



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	226.6	226.0	225.5	225.1	224.8	224.4	224.0	223.7	224.0	224.4	224.8
115°	263.9	263.7	263.4	263.0	262.4	262.0	261.4	260.9	261.4	262.0	262.4
117.5°	299.9	299.6	299.4	299.1	298.9	298.6	298.4	298.2	298.4	298.6	298.9
120°	324.7	324.6	324.5	324.1	323.4	322.7	322.0	321.4	322.0	322.7	323.4
122.5°	348.5	348.1	347.8	347.6	347.3	347.1	346.8	346.6	346.8	347.1	347.3
125°	384.7	384.5	384.4	383.9	383.1	382.3	381.5	380.7	381.5	382.3	383.1
127.5°	419.5	419.3	419.1	418.8	418.4	417.9	417.4	417.0	417.4	417.9	418.4
130°	442.5	442.2	442.0	441.5	440.8	440.2	439.4	438.8	439.4	440.2	440.8
132.5°	465.4	465.5	465.5	465.0	463.9	462.8	461.7	460.6	461.7	462.8	463.9
135°	499.0	498.9	498.8	498.3	497.5	496.7	495.9	495.0	495.9	496.7	497.5
137.5°	531.7	531.5	531.2	530.7	529.9	529.0	528.3	527.5	528.3	529.0	529.9
140°	552.4	552.0	551.5	551.1	550.3	549.7	549.0	548.4	549.0	549.7	550.3
142.5°	573.0	572.5	571.9	571.4	570.9	570.3	569.7	569.2	569.7	570.3	570.9
145°	603.2	602.8	602.4	601.9	601.4	600.9	600.3	599.8	600.3	600.9	601.4
147.5°	630.2	629.9	629.6	629.3	629.0	628.7	628.4	628.1	628.4	628.7	629.0
150°	647.8	647.2	646.7	646.5	646.6	646.7	646.9	647.0	646.9	646.7	646.6
152.5°	663.9	663.7	663.4	663.2	663.1	662.8	662.7	662.5	662.7	662.8	663.1
155°	686.6	686.6	686.4	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3
157.5°	706.6	706.5	706.4	706.5	706.8	707.0	707.4	707.7	707.4	707.0	706.8
160°	718.8	718.6	718.4	718.6	719.0	719.4	719.8	720.2	719.8	719.4	719.0
162.5°	730.1	730.1	730.0	730.2	730.5	730.8	731.1	731.4	731.1	730.8	730.5
165°	745.3	745.3	745.1	745.2	745.4	745.8	746.0	746.2	746.0	745.8	745.4
167.5°	756.4	756.4	756.4	756.7	757.2	757.7	758.3	758.9	758.3	757.7	757.2
170°	763.2	763.2	763.2	763.4	764.0	764.5	765.1	765.6	765.1	764.5	764.0
172.5°	768.0	768.0	768.0	768.3	768.8	769.4	769.9	770.5	769.9	769.4	768.8
175°	773.5	773.5	773.5	773.7	774.3	774.9	775.3	775.9	775.3	774.9	774.3
177.5°	776.5	776.6	776.7	777.0	777.4	777.8	778.3	778.7	778.3	777.8	777.4
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	436.2	434.5	433.2	430.2	428.4	426.2	424.4	426.4	424.3	425.2	423.8
5°	422.6	417.3	413.5	408.1	403.3	399.0	395.8	395.3	393.7	393.0	390.7
7.5°	406.2	399.6	393.1	386.0	379.9	373.8	369.9	366.6	364.5	361.7	359.7
10°	396.6	387.7	380.2	371.5	363.9	357.3	352.1	349.4	347.0	343.4	342.1
12.5°	384.7	375.5	366.3	357.0	349.8	342.4	337.9	333.9	332.2	328.2	327.8
15°	370.4	356.6	347.6	338.2	328.2	322.1	318.4	314.1	312.2	309.3	307.3
17.5°	353.4	341.0	329.8	320.0	311.4	306.4	301.7	298.7	295.5	293.6	290.2
20°	341.0	329.3	318.0	307.6	301.0	295.2	291.5	288.6	285.2	284.3	280.9
22.5°	330.6	317.7	306.9	298.2	291.0	284.4	280.3	278.3	276.1	273.1	272.5
25°	313.6	300.3	291.1	282.4	276.0	269.9	267.2	264.7	262.4	260.3	259.6
27.5°	299.1	287.1	276.1	268.3	262.7	257.2	254.8	251.8	250.1	248.4	246.4
30°	288.8	276.5	266.9	259.4	253.4	248.5	245.8	243.8	242.3	240.8	239.6
32.5°	278.3	266.9	257.6	250.2	244.2	240.5	238.1	236.7	235.1	233.3	231.8
35°	264.3	251.8	242.8	236.4	231.7	228.9	226.2	224.9	223.1	223.1	221.5
37.5°	248.6	237.8	229.8	224.0	219.8	217.3	214.4	213.5	212.3	211.5	211.0
40°	239.3	229.3	221.8	215.9	211.4	209.3	207.0	205.5	204.8	203.8	203.5
42.5°	229.6	220.0	212.9	207.5	203.5	201.8	199.7	198.6	197.1	195.8	195.6
45°	214.9	205.7	199.1	194.8	191.4	189.3	188.0	185.7	185.0	183.5	183.3
47.5°	201.1	192.2	185.7	182.1	179.2	177.5	175.5	173.2	172.3	171.5	171.5
50°	190.6	182.5	176.5	173.2	170.3	167.9	165.8	164.3	163.7	163.7	164.1
52.5°	180.1	173.2	168.1	164.0	161.3	158.7	156.7	155.8	155.0	155.9	156.5
55°	164.7	157.7	153.9	149.9	147.3	144.3	143.3	143.0	142.4	143.9	144.7
57.5°	148.3	143.4	139.0	135.1	132.7	130.9	129.7	129.5	130.5	131.3	133.7
60°	137.9	132.2	128.3	125.3	122.5	121.3	120.9	120.6	121.3	123.4	126.6
62.5°	126.5	121.9	117.6	115.4	113.2	111.4	111.3	111.5	113.0	115.4	118.6
65°	109.7	105.7	102.9	100.2	98.5	97.4	97.8	98.5	100.2	103.5	107.0
67.5°	92.5	89.8	87.3	85.2	83.6	83.6	84.0	85.1	87.1	90.7	94.0
70°	81.6	78.6	76.5	75.6	74.2	73.5	74.6	76.5	78.2	81.6	84.4
72.5°	70.6	68.0	66.4	65.7	65.1	64.6	65.0	67.0	69.3	72.6	76.0
75°	54.2	53.3	52.2	51.4	50.9	51.3	51.6	53.5	55.4	58.9	62.7
77.5°	39.6	38.6	37.9	37.7	37.4	37.7	38.7	40.1	41.9	44.5	47.4
80°	29.9	29.6	29.2	29.0	29.0	29.2	30.7	31.6	33.3	35.8	38.1
82.5°	21.9	21.6	21.5	21.4	21.6	21.7	22.6	23.8	25.2	27.1	29.0
85°	11.5	11.1	11.7	11.9	11.5	12.1	12.5	13.2	13.8	14.7	15.7
87.5°	4.7	5.2	5.3	5.6	5.8	6.3	6.3	7.0	7.5	7.9	7.8
90°	4.9	6.0	6.8	7.8	8.7	9.7	10.4	11.0	11.7	12.4	12.9
92.5°	17.7	18.6	19.8	21.0	22.1	23.2	24.1	25.0	25.9	26.8	27.4
95°	40.4	41.3	42.6	43.9	45.2	46.6	47.5	48.5	49.4	50.4	51.0
97.5°	65.8	66.8	68.6	70.5	72.3	74.2	75.1	76.0	76.9	77.8	78.3
100°	84.7	85.6	87.3	89.1	90.8	92.6	93.8	95.0	96.2	97.4	98.2
102.5°	107.7	108.4	109.3	110.2	111.0	111.9	113.3	114.6	115.9	117.2	118.1
105°	140.7	141.5	142.3	143.0	143.8	144.6	145.4	146.3	147.1	147.9	148.5
107.5°	176.5	177.2	177.8	178.4	179.0	179.6	180.0	180.4	180.8	181.2	181.4
110°	201.2	201.7	202.1	202.5	202.9	203.3	203.7	204.2	204.6	205.0	205.1



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	225.1	225.5	226.0	226.6	227.1	227.6	227.8	228.0	228.1	228.3	228.3
115°	263.0	263.4	263.7	263.9	264.2	264.5	264.3	264.2	264.1	263.9	263.8
117.5°	299.1	299.4	299.6	299.9	300.1	300.4	300.4	300.5	300.6	300.8	300.5
120°	324.1	324.5	324.6	324.7	324.9	325.0	325.0	325.0	325.0	325.0	324.7
122.5°	347.6	347.8	348.1	348.5	348.9	349.2	349.1	349.0	348.9	348.8	348.5
125°	383.9	384.4	384.5	384.7	384.8	384.9	384.7	384.4	384.1	383.8	383.7
127.5°	418.8	419.1	419.3	419.5	419.6	419.8	419.6	419.6	419.4	419.2	419.1
130°	441.5	442.0	442.2	442.5	442.8	443.0	442.9	442.8	442.6	442.5	442.3
132.5°	465.0	465.5	465.5	465.4	465.4	465.3	465.2	465.0	464.9	464.8	464.5
135°	498.3	498.8	498.9	499.0	499.2	499.3	499.3	499.3	499.3	499.3	499.0
137.5°	530.7	531.2	531.5	531.7	532.1	532.4	532.6	532.7	532.9	533.0	532.7
140°	551.1	551.5	552.0	552.4	552.8	553.2	553.4	553.8	554.0	554.2	554.1
142.5°	571.4	571.9	572.5	573.0	573.5	574.0	574.1	574.3	574.5	574.6	574.4
145°	601.9	602.4	602.8	603.2	603.6	604.1	604.1	604.1	604.1	604.1	603.8
147.5°	629.3	629.6	629.9	630.2	630.6	630.9	631.2	631.5	631.9	632.2	631.9
150°	646.5	646.7	647.2	647.8	648.2	648.8	648.8	648.8	648.8	648.8	648.7
152.5°	663.2	663.4	663.7	663.9	664.1	664.3	664.6	665.0	665.3	665.6	665.5
155°	686.3	686.4	686.6	686.6	686.8	687.0	687.5	688.0	688.5	689.1	689.0
157.5°	706.5	706.4	706.5	706.6	706.8	706.9	707.4	708.0	708.5	709.1	708.9
160°	718.6	718.4	718.6	718.8	718.8	719.0	719.6	720.1	720.6	721.1	721.1
162.5°	730.2	730.0	730.1	730.1	730.1	730.2	730.8	731.5	732.1	732.7	732.7
165°	745.2	745.1	745.3	745.3	745.5	745.7	746.2	746.7	747.3	747.8	747.6
167.5°	756.7	756.4	756.4	756.4	756.4	756.4	757.2	758.1	758.9	759.6	759.6
170°	763.4	763.2	763.2	763.2	763.2	763.2	764.0	764.8	765.6	766.5	766.4
172.5°	768.3	768.0	768.0	768.0	768.0	768.0	768.8	769.6	770.5	771.3	771.3
175°	773.7	773.5	773.5	773.5	773.5	773.5	774.3	775.1	775.9	776.7	776.7
177.5°	777.0	776.7	776.6	776.5	776.4	776.2	776.9	777.6	778.2	778.9	778.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	422.9	424.0	423.1	424.3	423.1	424.0	422.9	423.8	425.2	424.3	426.4
5°	389.8	388.1	389.2	388.5	389.2	388.1	389.8	390.7	393.0	393.7	395.3
7.5°	359.2	357.6	355.7	354.8	355.7	357.6	359.2	359.7	361.7	364.5	366.6
10°	340.1	337.9	337.8	336.5	337.8	337.9	340.1	342.1	343.4	347.0	349.4
12.5°	326.0	324.1	322.0	321.4	322.0	324.1	326.0	327.8	328.2	332.2	333.9
15°	306.1	304.6	303.3	304.4	303.3	304.6	306.1	307.3	309.3	312.2	314.1
17.5°	289.6	288.4	288.1	286.7	288.1	288.4	289.6	290.2	293.6	295.5	298.7
20°	279.2	278.3	278.7	276.1	278.7	278.3	279.2	280.9	284.3	285.2	288.6
22.5°	270.9	269.0	268.8	268.3	268.8	269.0	270.9	272.5	273.1	276.1	278.3
25°	257.9	257.0	256.0	257.0	256.0	257.0	257.9	259.6	260.3	262.4	264.7
27.5°	246.5	245.4	245.2	245.3	245.2	245.4	246.5	246.4	248.4	250.1	251.8
30°	239.6	237.7	237.9	237.7	237.9	237.7	239.6	239.6	240.8	242.3	243.8
32.5°	232.1	230.8	230.6	230.2	230.6	230.8	232.1	231.8	233.3	235.1	236.7
35°	220.9	220.9	220.0	220.0	220.0	220.9	220.9	221.5	223.1	223.1	224.9
37.5°	210.5	210.3	209.8	209.9	209.8	210.3	210.5	211.0	211.5	212.3	213.5
40°	202.7	202.5	201.9	200.8	201.9	202.5	202.7	203.5	203.8	204.8	205.5
42.5°	195.2	194.5	194.3	193.9	194.3	194.5	195.2	195.6	195.8	197.1	198.6
45°	183.3	183.3	183.0	182.7	183.0	183.3	183.3	183.3	183.5	185.0	185.7
47.5°	171.8	172.1	172.8	172.7	172.8	172.1	171.8	171.5	171.5	172.3	173.2
50°	164.9	165.0	165.6	165.8	165.6	165.0	164.9	164.1	163.7	163.7	164.3
52.5°	157.2	158.2	159.0	158.8	159.0	158.2	157.2	156.5	155.9	155.0	155.8
55°	146.3	147.7	149.0	149.2	149.0	147.7	146.3	144.7	143.9	142.4	143.0
57.5°	135.7	137.5	138.9	139.4	138.9	137.5	135.7	133.7	131.3	130.5	129.5
60°	128.5	130.9	132.6	133.4	132.6	130.9	128.5	126.6	123.4	121.3	120.6
62.5°	121.6	124.3	126.0	126.1	126.0	124.3	121.6	118.6	115.4	113.0	111.5
65°	110.2	113.0	114.5	115.7	114.5	113.0	110.2	107.0	103.5	100.2	98.5
67.5°	98.0	100.9	102.5	103.4	102.5	100.9	98.0	94.0	90.7	87.1	85.1
70°	89.1	92.0	94.2	95.0	94.2	92.0	89.1	84.4	81.6	78.2	76.5
72.5°	80.4	82.9	84.7	85.6	84.7	82.9	80.4	76.0	72.6	69.3	67.0
75°	65.1	68.6	70.3	71.2	70.3	68.6	65.1	62.7	58.9	55.4	53.5
77.5°	50.2	53.3	54.4	54.9	54.4	53.3	50.2	47.4	44.5	41.9	40.1
80°	40.3	42.2	43.5	43.7	43.5	42.2	40.3	38.1	35.8	33.3	31.6
82.5°	31.0	32.5	32.9	33.4	32.9	32.5	31.0	29.0	27.1	25.2	23.8
85°	17.0	17.7	17.9	17.7	17.9	17.7	17.0	15.7	14.7	13.8	13.2
87.5°	8.2	8.2	8.2	8.6	8.2	8.2	8.2	7.8	7.9	7.5	7.0
90°	13.3	13.7	14.1	14.5	14.1	13.7	13.3	12.9	12.4	11.7	11.0
92.5°	27.7	28.0	28.3	28.5	28.3	28.0	27.7	27.4	26.8	25.9	25.0
95°	51.3	51.5	51.8	52.0	51.8	51.5	51.3	51.0	50.4	49.4	48.5
97.5°	78.4	78.6	78.8	78.9	78.8	78.6	78.4	78.3	77.8	76.9	76.0
100°	98.5	98.7	99.0	99.2	99.0	98.7	98.5	98.2	97.4	96.2	95.0
102.5°	118.5	118.9	119.2	119.6	119.2	118.9	118.5	118.1	117.2	115.9	114.6
105°	148.9	149.3	149.7	150.1	149.7	149.3	148.9	148.5	147.9	147.1	146.3
107.5°	181.4	181.4	181.3	181.3	181.3	181.4	181.4	181.4	181.2	180.8	180.4
110°	205.0	204.8	204.7	204.6	204.7	204.8	205.0	205.1	205.0	204.6	204.2



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	228.0	227.8	227.6	227.3	227.6	227.8	228.0	228.3	228.3	228.1	228.0
115°	263.7	263.6	263.4	263.3	263.4	263.6	263.7	263.8	263.9	264.1	264.2
117.5°	300.0	299.5	298.9	298.4	298.9	299.5	300.0	300.5	300.8	300.6	300.5
120°	324.2	323.7	323.1	322.6	323.1	323.7	324.2	324.7	325.0	325.0	325.0
122.5°	348.1	347.6	347.2	346.8	347.2	347.6	348.1	348.5	348.8	348.9	349.0
125°	383.5	383.4	383.3	383.1	383.3	383.4	383.5	383.7	383.8	384.1	384.4
127.5°	418.8	418.5	418.2	418.0	418.2	418.5	418.8	419.1	419.2	419.4	419.6
130°	442.1	441.7	441.5	441.2	441.5	441.7	442.1	442.3	442.5	442.6	442.8
132.5°	464.1	463.7	463.4	463.0	463.4	463.7	464.1	464.5	464.8	464.9	465.0
135°	498.5	498.0	497.4	496.9	497.4	498.0	498.5	499.0	499.3	499.3	499.3
137.5°	532.1	531.4	530.8	530.0	530.8	531.4	532.1	532.7	533.0	532.9	532.7
140°	553.4	552.7	552.0	551.4	552.0	552.7	553.4	554.1	554.2	554.0	553.8
142.5°	573.7	573.1	572.3	571.7	572.3	573.1	573.7	574.4	574.6	574.5	574.3
145°	603.4	603.0	602.6	602.2	602.6	603.0	603.4	603.8	604.1	604.1	604.1
147.5°	631.0	630.1	629.2	628.3	629.2	630.1	631.0	631.9	632.2	631.9	631.5
150°	648.4	648.2	647.8	647.6	647.8	648.2	648.4	648.7	648.8	648.8	648.8
152.5°	665.0	664.6	664.1	663.6	664.1	664.6	665.0	665.5	665.6	665.3	665.0
155°	688.4	687.7	687.0	686.3	687.0	687.7	688.4	689.0	689.1	688.5	688.0
157.5°	708.0	707.1	706.2	705.3	706.2	707.1	708.0	708.9	709.1	708.5	708.0
160°	720.4	719.7	719.1	718.4	719.1	719.7	720.4	721.1	721.1	720.6	720.1
162.5°	731.9	731.1	730.3	729.5	730.3	731.1	731.9	732.7	732.7	732.1	731.5
165°	746.9	746.1	745.3	744.4	745.3	746.1	746.9	747.6	747.8	747.3	746.7
167.5°	758.8	758.0	757.2	756.3	757.2	758.0	758.8	759.6	759.6	758.9	758.1
170°	765.4	764.5	763.5	762.6	763.5	764.5	765.4	766.4	766.5	765.6	764.8
172.5°	770.5	769.6	768.7	767.9	768.7	769.6	770.5	771.3	771.3	770.5	769.6
175°	775.7	774.8	773.8	772.9	773.8	774.8	775.7	776.7	776.7	775.9	775.1
177.5°	778.0	777.3	776.6	775.8	776.6	777.3	778.0	778.8	778.9	778.2	777.6
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	424.4	426.2	428.4	430.2	433.2	434.5	436.2	437.5	439.9	442.2	444.9
5°	395.8	399.0	403.3	408.1	413.5	417.3	422.6	425.7	432.2	438.0	443.7
7.5°	369.9	373.8	379.9	386.0	393.1	399.6	406.2	413.5	421.7	431.4	439.4
10°	352.1	357.3	363.9	371.5	380.2	387.7	396.6	404.5	414.5	425.7	436.3
12.5°	337.9	342.4	349.8	357.0	366.3	375.5	384.7	395.1	406.8	419.3	432.5
15°	318.4	322.1	328.2	338.2	347.6	356.6	370.4	380.2	394.8	408.8	424.9
17.5°	301.7	306.4	311.4	320.0	329.8	341.0	353.4	365.7	379.8	397.5	415.5
20°	291.5	295.2	301.0	307.6	318.0	329.3	341.0	353.4	370.7	389.1	408.5
22.5°	280.3	284.4	291.0	298.2	306.9	317.7	330.6	344.2	362.3	380.3	401.4
25°	267.2	269.9	276.0	282.4	291.1	300.3	313.6	328.7	346.7	367.2	388.7
27.5°	254.8	257.2	262.7	268.3	276.1	287.1	299.1	314.3	331.2	352.0	375.8
30°	245.8	248.5	253.4	259.4	266.9	276.5	288.8	303.1	321.2	341.5	366.4
32.5°	238.1	240.5	244.2	250.2	257.6	266.9	278.3	292.9	311.0	331.6	356.0
35°	226.2	228.9	231.7	236.4	242.8	251.8	264.3	278.1	295.4	315.4	337.8
37.5°	214.4	217.3	219.8	224.0	229.8	237.8	248.6	262.9	278.6	297.8	319.4
40°	207.0	209.3	211.4	215.9	221.8	229.3	239.3	252.1	268.6	286.6	304.4
42.5°	199.7	201.8	203.5	207.5	212.9	220.0	229.6	242.1	257.5	274.2	290.0
45°	188.0	189.3	191.4	194.8	199.1	205.7	214.9	226.1	239.0	254.9	266.8
47.5°	175.5	177.5	179.2	182.1	185.7	192.2	201.1	210.5	222.3	234.1	242.4
50°	165.8	167.9	170.3	173.2	176.5	182.5	190.6	200.2	210.3	219.3	226.4
52.5°	156.7	158.7	161.3	164.0	168.1	173.2	180.1	188.7	198.5	205.0	210.9
55°	143.3	144.3	147.3	149.9	153.9	157.7	164.7	172.2	178.2	183.1	188.0
57.5°	129.7	130.9	132.7	135.1	139.0	143.4	148.3	155.0	158.5	161.0	164.9
60°	120.9	121.3	122.5	125.3	128.3	132.2	137.9	142.6	145.3	147.3	150.5
62.5°	111.3	111.4	113.2	115.4	117.6	121.9	126.5	130.3	132.4	133.5	136.5
65°	97.8	97.4	98.5	100.2	102.9	105.7	109.7	113.0	112.8	114.0	115.9
67.5°	84.0	83.6	83.6	85.2	87.3	89.8	92.5	94.6	94.6	96.0	97.0
70°	74.6	73.5	74.2	75.6	76.5	78.6	81.6	82.3	82.5	83.2	84.2
72.5°	65.0	64.6	65.1	65.7	66.4	68.0	70.6	71.0	71.1	71.5	73.1
75°	51.6	51.3	50.9	51.4	52.2	53.3	54.2	55.0	54.8	55.0	56.2
77.5°	38.7	37.7	37.4	37.7	37.9	38.6	39.6	39.5	39.7	39.7	40.9
80°	30.7	29.2	29.0	29.0	29.2	29.6	29.9	30.3	29.8	30.3	30.7
82.5°	22.6	21.7	21.6	21.4	21.5	21.6	21.9	22.0	21.9	22.2	22.4
85°	12.5	12.1	11.5	11.9	11.7	11.1	11.5	10.9	10.8	10.9	11.1
87.5°	6.3	6.3	5.8	5.6	5.3	5.2	4.7	4.4	4.0	3.9	4.2
90°	10.4	9.7	8.7	7.8	6.8	6.0	4.9	3.8	2.8	1.7	0.6
92.5°	24.1	23.2	22.1	21.0	19.8	18.6	17.7	16.9	16.1	15.4	14.7
95°	47.5	46.6	45.2	43.9	42.6	41.3	40.4	40.1	39.9	39.6	39.4
97.5°	75.1	74.2	72.3	70.5	68.6	66.8	65.8	65.7	65.6	65.5	65.4
100°	93.8	92.6	90.8	89.1	87.3	85.6	84.7	84.7	84.7	84.7	84.7
102.5°	113.3	111.9	111.0	110.2	109.3	108.4	107.7	107.1	106.6	106.1	105.6
105°	145.4	144.6	143.8	143.0	142.3	141.5	140.7	140.0	139.3	138.7	138.0
107.5°	180.0	179.6	179.0	178.4	177.8	177.2	176.5	175.9	175.2	174.5	173.8
110°	203.7	203.3	202.9	202.5	202.1	201.7	201.2	200.6	199.8	199.2	198.5



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	227.8	227.6	227.1	226.6	226.0	225.5	225.1	224.8	224.4	224.0	223.7
115°	264.3	264.5	264.2	263.9	263.7	263.4	263.0	262.4	262.0	261.4	260.9
117.5°	300.4	300.4	300.1	299.9	299.6	299.4	299.1	298.9	298.6	298.4	298.2
120°	325.0	325.0	324.9	324.7	324.6	324.5	324.1	323.4	322.7	322.0	321.4
122.5°	349.1	349.2	348.9	348.5	348.1	347.8	347.6	347.3	347.1	346.8	346.6
125°	384.7	384.9	384.8	384.7	384.5	384.4	383.9	383.1	382.3	381.5	380.7
127.5°	419.6	419.8	419.6	419.5	419.3	419.1	418.8	418.4	417.9	417.4	417.0
130°	442.9	443.0	442.8	442.5	442.2	442.0	441.5	440.8	440.2	439.4	438.8
132.5°	465.2	465.3	465.4	465.4	465.5	465.5	465.0	463.9	462.8	461.7	460.6
135°	499.3	499.3	499.2	499.0	498.9	498.8	498.3	497.5	496.7	495.9	495.0
137.5°	532.6	532.4	532.1	531.7	531.5	531.2	530.7	529.9	529.0	528.3	527.5
140°	553.4	553.2	552.8	552.4	552.0	551.5	551.1	550.3	549.7	549.0	548.4
142.5°	574.1	574.0	573.5	573.0	572.5	571.9	571.4	570.9	570.3	569.7	569.2
145°	604.1	604.1	603.6	603.2	602.8	602.4	601.9	601.4	600.9	600.3	599.8
147.5°	631.2	630.9	630.6	630.2	629.9	629.6	629.3	629.0	628.7	628.4	628.1
150°	648.8	648.8	648.2	647.8	647.2	646.7	646.5	646.6	646.7	646.9	647.0
152.5°	664.6	664.3	664.1	663.9	663.7	663.4	663.2	663.1	662.8	662.7	662.5
155°	687.5	687.0	686.8	686.6	686.6	686.4	686.3	686.3	686.3	686.3	686.3
157.5°	707.4	706.9	706.8	706.6	706.5	706.4	706.5	706.8	707.0	707.4	707.7
160°	719.6	719.0	718.8	718.8	718.6	718.4	718.6	719.0	719.4	719.8	720.2
162.5°	730.8	730.2	730.1	730.1	730.1	730.0	730.2	730.5	730.8	731.1	731.4
165°	746.2	745.7	745.5	745.3	745.3	745.1	745.2	745.4	745.8	746.0	746.2
167.5°	757.2	756.4	756.4	756.4	756.4	756.4	756.7	757.2	757.7	758.3	758.9
170°	764.0	763.2	763.2	763.2	763.2	763.2	763.4	764.0	764.5	765.1	765.6
172.5°	768.8	768.0	768.0	768.0	768.0	768.0	768.3	768.8	769.4	769.9	770.5
175°	774.3	773.5	773.5	773.5	773.5	773.5	773.7	774.3	774.9	775.3	775.9
177.5°	776.9	776.2	776.4	776.5	776.6	776.7	777.0	777.4	777.8	778.3	778.7
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	446.3	448.3	449.7	452.2	454.4	455.6	456.6	457.5	458.6	459.5	462.1
5°	449.1	454.0	458.2	464.6	470.4	474.9	479.8	484.1	487.7	492.8	496.8
7.5°	447.8	456.6	465.7	475.6	485.8	495.1	503.9	511.9	519.3	528.2	536.0
10°	446.7	458.5	470.2	483.6	497.3	509.0	519.9	531.1	539.2	550.5	560.1
12.5°	445.8	459.7	473.9	489.9	505.0	521.5	536.1	544.2	556.5	565.6	577.0
15°	442.0	460.4	479.8	497.9	519.4	534.7	547.5	563.3	574.8	586.3	598.7
17.5°	435.1	456.1	477.8	501.5	522.0	538.4	555.0	570.2	583.9	599.3	614.8
20°	431.9	452.9	477.8	502.1	522.2	539.3	556.3	573.1	588.2	608.0	625.8
22.5°	425.3	450.6	473.5	497.3	518.0	536.6	555.9	574.9	594.9	617.3	639.7
25°	413.5	439.1	463.4	486.8	507.7	531.1	551.6	577.1	602.7	632.3	660.1
27.5°	401.2	425.7	448.0	470.6	495.0	521.5	548.0	576.9	610.5	647.8	687.1
30°	391.3	414.5	436.1	459.3	484.7	514.5	543.7	578.0	616.8	658.8	705.6
32.5°	379.7	401.0	422.1	446.6	474.3	505.7	539.8	577.4	624.0	671.7	719.8
35°	359.8	377.7	399.4	425.6	456.8	492.8	532.2	576.7	630.1	685.0	725.5
37.5°	336.3	352.9	375.8	404.5	437.2	475.9	522.6	575.4	632.2	675.9	688.9
40°	320.4	335.9	359.6	389.4	422.9	463.8	515.0	570.8	625.8	653.7	642.9
42.5°	303.5	319.8	342.9	372.3	408.5	453.0	505.6	561.3	607.5	618.0	580.9
45°	277.0	293.7	316.5	346.3	385.1	433.3	488.1	538.8	565.3	546.3	488.9
47.5°	252.2	267.9	289.0	319.8	359.8	409.7	462.4	502.9	505.0	459.6	398.2
50°	235.3	249.8	271.1	301.8	341.5	392.1	439.7	471.6	457.2	405.8	346.8
52.5°	218.7	232.9	253.9	284.3	323.6	369.9	414.3	436.6	409.6	356.8	306.5
55°	194.8	207.2	227.8	255.8	293.1	336.1	373.7	381.5	346.4	294.5	253.6
57.5°	171.5	183.0	201.7	227.6	261.7	299.7	329.2	327.5	290.5	245.9	213.4
60°	155.6	166.9	183.5	208.7	239.9	272.6	297.8	291.8	255.1	216.6	189.3
62.5°	141.5	151.6	167.2	189.3	217.7	248.0	268.7	259.8	223.9	190.3	168.7
65°	120.6	129.1	142.4	161.3	184.8	209.9	225.9	214.4	183.7	157.5	140.1
67.5°	100.6	107.5	118.6	133.7	153.8	173.9	183.6	172.1	147.5	128.4	115.5
70°	88.0	94.0	102.6	116.0	133.5	150.5	157.8	147.5	126.4	110.0	100.8
72.5°	75.3	80.3	87.9	100.0	114.0	128.7	135.1	125.2	107.9	94.0	85.4
75°	58.2	61.6	66.9	75.2	86.3	98.0	101.5	92.9	81.8	71.4	65.7
77.5°	41.7	44.5	48.5	53.7	61.6	69.1	72.2	67.2	58.6	52.0	47.4
80°	32.0	33.5	36.9	41.3	47.5	52.2	54.2	51.0	45.0	40.1	36.5
82.5°	22.8	24.4	26.3	29.9	33.9	37.1	39.3	37.2	32.9	28.9	26.9
85°	11.1	12.1	13.2	14.7	17.7	19.6	19.4	18.1	16.4	14.9	13.8
87.5°	4.2	4.6	5.3	6.3	6.9	7.7	8.2	8.1	7.7	7.3	7.0
90°	1.7	2.8	3.8	4.9	6.0	6.8	7.8	8.7	9.7	10.4	11.0
92.5°	15.4	16.1	16.9	17.7	18.6	19.8	21.0	22.1	23.2	24.1	25.0
95°	39.6	39.9	40.1	40.4	41.3	42.6	43.9	45.2	46.6	47.5	48.5
97.5°	65.5	65.6	65.7	65.8	66.8	68.6	70.5	72.3	74.2	75.1	76.0
100°	84.7	84.7	84.7	84.7	85.6	87.3	89.1	90.8	92.6	93.8	95.0
102.5°	106.1	106.6	107.1	107.7	108.4	109.3	110.2	111.0	111.9	113.3	114.6
105°	138.7	139.3	140.0	140.7	141.5	142.3	143.0	143.8	144.6	145.4	146.3
107.5°	174.5	175.2	175.9	176.5	177.2	177.8	178.4	179.0	179.6	180.0	180.4
110°	199.2	199.8	200.6	201.2	201.7	202.1	202.5	202.9	203.3	203.7	204.2



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	224.0	224.4	224.8	225.1	225.5	226.0	226.6	227.1	227.6	227.8	228.0
115°	261.4	262.0	262.4	263.0	263.4	263.7	263.9	264.2	264.5	264.3	264.2
117.5°	298.4	298.6	298.9	299.1	299.4	299.6	299.9	300.1	300.4	300.4	300.5
120°	322.0	322.7	323.4	324.1	324.5	324.6	324.7	324.9	325.0	325.0	325.0
122.5°	346.8	347.1	347.3	347.6	347.8	348.1	348.5	348.9	349.2	349.1	349.0
125°	381.5	382.3	383.1	383.9	384.4	384.5	384.7	384.8	384.9	384.7	384.4
127.5°	417.4	417.9	418.4	418.8	419.1	419.3	419.5	419.6	419.8	419.6	419.6
130°	439.4	440.2	440.8	441.5	442.0	442.2	442.5	442.8	443.0	442.9	442.8
132.5°	461.7	462.8	463.9	465.0	465.5	465.5	465.4	465.4	465.3	465.2	465.0
135°	495.9	496.7	497.5	498.3	498.8	498.9	499.0	499.2	499.3	499.3	499.3
137.5°	528.3	529.0	529.9	530.7	531.2	531.5	531.7	532.1	532.4	532.6	532.7
140°	549.0	549.7	550.3	551.1	551.5	552.0	552.4	552.8	553.2	553.4	553.8
142.5°	569.7	570.3	570.9	571.4	571.9	572.5	573.0	573.5	574.0	574.1	574.3
145°	600.3	600.9	601.4	601.9	602.4	602.8	603.2	603.6	604.1	604.1	604.1
147.5°	628.4	628.7	629.0	629.3	629.6	629.9	630.2	630.6	630.9	631.2	631.5
150°	646.9	646.7	646.6	646.5	646.7	647.2	647.8	648.2	648.8	648.8	648.8
152.5°	662.7	662.8	663.1	663.2	663.4	663.7	663.9	664.1	664.3	664.6	665.0
155°	686.3	686.3	686.3	686.3	686.4	686.6	686.6	686.8	687.0	687.5	688.0
157.5°	707.4	707.0	706.8	706.5	706.4	706.5	706.6	706.8	706.9	707.4	708.0
160°	719.8	719.4	719.0	718.6	718.4	718.6	718.8	718.8	719.0	719.6	720.1
162.5°	731.1	730.8	730.5	730.2	730.0	730.1	730.1	730.1	730.2	730.8	731.5
165°	746.0	745.8	745.4	745.2	745.1	745.3	745.3	745.5	745.7	746.2	746.7
167.5°	758.3	757.7	757.2	756.7	756.4	756.4	756.4	756.4	756.4	757.2	758.1
170°	765.1	764.5	764.0	763.4	763.2	763.2	763.2	763.2	763.2	764.0	764.8
172.5°	769.9	769.4	768.8	768.3	768.0	768.0	768.0	768.0	768.0	768.8	769.6
175°	775.3	774.9	774.3	773.7	773.5	773.5	773.5	773.5	773.5	774.3	775.1
177.5°	778.3	777.8	777.4	777.0	776.7	776.6	776.5	776.4	776.2	776.9	777.6
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	464.2	465.4	468.0	467.1	468.2	468.9	469.4
5°	501.7	507.7	510.4	510.0	514.0	513.0	512.0
7.5°	544.0	550.3	553.9	558.3	560.8	561.1	563.3
10°	568.0	576.3	579.7	584.4	587.4	589.1	588.9
12.5°	586.4	592.9	600.5	602.8	606.8	609.0	608.2
15°	608.5	618.9	626.8	630.7	635.9	637.3	639.4
17.5°	628.3	642.1	651.3	663.7	668.3	671.2	669.4
20°	643.2	661.5	670.7	685.3	693.5	697.8	696.3
22.5°	660.8	680.6	697.7	710.4	722.7	728.6	729.8
25°	691.0	718.1	743.2	759.9	775.2	778.8	786.7
27.5°	724.8	756.8	783.6	801.2	811.8	815.8	818.3
30°	746.0	777.9	798.0	809.3	812.7	812.4	812.0
32.5°	756.4	776.3	780.2	777.1	769.3	762.7	755.9
35°	741.7	726.8	704.6	676.0	654.8	633.6	631.4
37.5°	667.1	619.5	582.4	541.1	517.3	502.6	492.4
40°	596.8	542.7	497.9	463.1	438.8	429.2	419.7
42.5°	520.6	468.9	429.2	400.1	381.8	371.1	363.7
45°	422.9	377.3	346.3	325.1	310.6	302.4	297.7
47.5°	346.6	312.8	286.4	271.2	261.2	254.8	254.8
50°	305.6	273.4	255.8	243.8	235.1	230.0	231.0
52.5°	269.2	245.2	230.2	220.1	213.7	210.6	210.4
55°	225.1	207.8	198.0	190.6	186.3	182.7	183.5
57.5°	192.6	178.0	171.4	165.3	162.2	160.9	158.7
60°	172.4	161.1	155.4	150.5	147.5	146.3	144.3
62.5°	154.4	145.5	140.1	136.1	133.4	133.0	131.3
65°	129.8	123.0	118.1	116.3	113.4	112.7	112.7
67.5°	107.0	102.2	98.3	96.6	95.4	95.6	94.7
70°	92.7	88.7	86.3	84.4	83.5	83.6	82.9
72.5°	81.1	76.6	74.5	73.4	72.2	72.6	72.3
75°	61.4	59.2	58.0	56.9	56.2	55.8	55.4
77.5°	45.1	43.1	42.2	41.6	41.7	40.8	41.5
80°	34.8	33.2	32.6	31.6	31.5	31.5	31.3
82.5°	25.5	24.5	24.1	23.4	23.0	23.3	22.8
85°	13.2	12.5	12.2	12.2	11.9	11.5	12.5
87.5°	7.2	6.7	6.8	6.8	6.8	6.8	6.5
90°	11.7	12.4	12.9	13.3	13.7	14.1	14.5
92.5°	25.9	26.8	27.4	27.7	28.0	28.3	28.5
95°	49.4	50.4	51.0	51.3	51.5	51.8	52.0
97.5°	76.9	77.8	78.3	78.4	78.6	78.8	78.9
100°	96.2	97.4	98.2	98.5	98.7	99.0	99.2
102.5°	115.9	117.2	118.1	118.5	118.9	119.2	119.6
105°	147.1	147.9	148.5	148.9	149.3	149.7	150.1
107.5°	180.8	181.2	181.4	181.4	181.4	181.3	181.3
110°	204.6	205.0	205.1	205.0	204.8	204.7	204.6



TEST NUMBER: P333347-930

CATALOG NUMBER: S125DIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	228.1	228.3	228.3	228.0	227.8	227.6	227.3
115°	264.1	263.9	263.8	263.7	263.6	263.4	263.3
117.5°	300.6	300.8	300.5	300.0	299.5	298.9	298.4
120°	325.0	325.0	324.7	324.2	323.7	323.1	322.6
122.5°	348.9	348.8	348.5	348.1	347.6	347.2	346.8
125°	384.1	383.8	383.7	383.5	383.4	383.3	383.1
127.5°	419.4	419.2	419.1	418.8	418.5	418.2	418.0
130°	442.6	442.5	442.3	442.1	441.7	441.5	441.2
132.5°	464.9	464.8	464.5	464.1	463.7	463.4	463.0
135°	499.3	499.3	499.0	498.5	498.0	497.4	496.9
137.5°	532.9	533.0	532.7	532.1	531.4	530.8	530.0
140°	554.0	554.2	554.1	553.4	552.7	552.0	551.4
142.5°	574.5	574.6	574.4	573.7	573.1	572.3	571.7
145°	604.1	604.1	603.8	603.4	603.0	602.6	602.2
147.5°	631.9	632.2	631.9	631.0	630.1	629.2	628.3
150°	648.8	648.8	648.7	648.4	648.2	647.8	647.6
152.5°	665.3	665.6	665.5	665.0	664.6	664.1	663.6
155°	688.5	689.1	689.0	688.4	687.7	687.0	686.3
157.5°	708.5	709.1	708.9	708.0	707.1	706.2	705.3
160°	720.6	721.1	721.1	720.4	719.7	719.1	718.4
162.5°	732.1	732.7	732.7	731.9	731.1	730.3	729.5
165°	747.3	747.8	747.6	746.9	746.1	745.3	744.4
167.5°	758.9	759.6	759.6	758.8	758.0	757.2	756.3
170°	765.6	766.5	766.4	765.4	764.5	763.5	762.6
172.5°	770.5	771.3	771.3	770.5	769.6	768.7	767.9
175°	775.9	776.7	776.7	775.7	774.8	773.8	772.9
177.5°	778.2	778.9	778.8	778.0	777.3	776.6	775.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7

(END OF REPORT)