

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333424-930

Luminaire Tested: **S125DIW-S850D1560U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333424-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1560U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7902.1 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	67	63	58	55	52	45	43	41	34	32	31	26
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	18	16	13
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	33	27	23	28	23	19	22	18	16	17	14	13	10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6442	6442	6442	6442
5°	7459	6463	5659	6463
10°	8679	6430	4958	6430
15°	9607	6383	4574	6383
20°	10754	6308	4265	6308
25°	12598	6223	4115	6223
30°	13607	6141	3985	6141
35°	11188	5984	3899	5984
40°	7952	5767	3805	5767
45°	6109	5476	3751	5476
50°	5215	5112	3743	5112
55°	4644	4757	3775	4757
60°	4188	4370	3871	4370
65°	3869	3978	3972	3978
70°	3518	3573	4030	3573
75°	3107	3147	3992	3147
80°	2615	2566	3652	2566
85°	2075	1845	2949	1845



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	1.2
10°-20°	285.9	3.6
20°-30°	464.2	5.9
30°-40°	566.3	7.2
40°-50°	515.1	6.5
50°-60°	410.3	5.2
60°-70°	285.8	3.6
70°-80°	152.4	1.9
80°-90°	41.9	0.5
90°-100°	60.2	0.8
100°-110°	370.8	4.7
110°-120°	672.5	8.5
120°-130°	863.1	10.9
130°-140°	928.3	11.7
140°-150°	871.4	11.0
150°-160°	704.9	8.9
160°-170°	455.9	5.8
170°-180°	157.2	2.0
0°-30°	846.1	10.7
0°-40°	1412.4	17.9
0°-60°	2337.8	29.6
0°-90°	2817.9	35.7
90°-120°	1103.5	14.0
90°-150°	3766.2	47.7
90°-180°	5084.0	64.3
0°-180°	7902.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1151	997	873	997	1151	116
15°	1437	955	684	955	1437	411
25°	1768	873	578	873	1768	807
35°	1419	759	494	759	1419	868
45°	669	600	411	600	669	535
55°	412	422	335	422	412	371
65°	253	260	260	260	253	251
75°	124	126	160	126	124	134
85°	28	25	40	25	28	33
90°	29	1	29	1	29	14
95°	26	70	26	70	26	21
105°	364	361	364	361	364	330
115°	672	678	672	678	672	668
125°	963	963	963	963	963	857
135°	1197	1202	1197	1202	1197	923
145°	1389	1393	1389	1393	1389	868
155°	1523	1534	1523	1534	1523	702
165°	1610	1619	1610	1619	1610	454
175°	1648	1656	1648	1656	1648	157
180°	1656	1656	1656	1656	1656	



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1055.0	1053.6	1052.3	1049.5	1051.6	1045.9	1043.1	1038.4	1032.7	1030.6	1028.3
5°	1150.6	1152.8	1154.9	1146.0	1146.9	1140.9	1127.4	1116.4	1107.5	1096.1	1088.0
7.5°	1265.8	1260.8	1260.4	1254.7	1244.7	1236.8	1222.5	1204.4	1186.9	1166.9	1150.4
10°	1323.4	1323.8	1320.0	1313.2	1302.7	1295.0	1276.4	1258.6	1237.1	1211.6	1193.4
12.5°	1366.8	1368.5	1363.7	1354.5	1349.4	1332.3	1317.7	1296.6	1270.9	1250.6	1222.9
15°	1436.9	1432.2	1428.8	1417.4	1408.5	1390.7	1367.4	1345.4	1317.4	1291.6	1265.8
17.5°	1504.4	1508.1	1501.8	1491.3	1463.8	1443.0	1411.8	1381.6	1346.9	1312.2	1281.4
20°	1564.7	1568.1	1558.4	1540.2	1507.2	1486.4	1445.3	1406.4	1366.1	1321.7	1287.8
22.5°	1639.9	1637.2	1624.1	1596.4	1567.7	1529.4	1484.9	1437.5	1387.2	1336.9	1291.9
25°	1767.9	1750.1	1742.1	1707.8	1670.1	1613.8	1552.8	1483.4	1420.7	1354.3	1296.7
27.5°	1838.8	1833.3	1824.3	1800.4	1760.8	1700.6	1628.7	1544.1	1455.7	1371.8	1296.5
30°	1824.6	1825.5	1826.4	1818.7	1793.3	1748.0	1676.5	1585.4	1480.4	1386.0	1298.9
32.5°	1698.7	1714.1	1728.8	1746.2	1753.3	1744.7	1699.8	1617.6	1509.6	1402.3	1297.5
35°	1419.0	1423.8	1471.5	1519.0	1583.3	1633.3	1666.7	1630.4	1539.3	1416.1	1295.8
37.5°	1106.4	1129.4	1162.5	1216.0	1308.9	1392.0	1499.0	1548.2	1518.8	1420.6	1292.9
40°	943.2	964.4	985.9	1040.6	1118.9	1219.7	1341.2	1444.9	1469.0	1406.4	1282.7
42.5°	817.3	834.0	857.9	899.0	964.5	1053.7	1169.8	1305.4	1388.8	1365.1	1261.4
45°	668.9	679.5	698.1	730.7	778.1	848.0	950.4	1098.6	1227.7	1270.5	1210.8
47.5°	572.5	572.4	586.9	609.4	643.7	703.0	778.8	894.9	1032.8	1134.8	1130.1
50°	519.0	516.9	528.3	547.8	574.9	614.2	686.6	779.3	911.9	1027.4	1059.6
52.5°	473.0	473.2	480.2	494.6	517.3	551.0	605.0	688.6	801.8	920.5	981.0
55°	412.4	410.7	418.7	428.4	444.9	466.9	505.9	569.8	661.7	778.5	857.3
57.5°	356.8	361.4	364.7	371.5	385.1	399.9	432.8	479.6	552.5	652.8	736.1
60°	324.2	329.0	331.5	338.3	349.3	362.0	387.3	425.5	486.8	573.2	655.7
62.5°	295.1	298.8	299.6	305.7	314.7	327.1	347.1	379.0	427.5	503.1	584.0
65°	253.2	253.2	254.9	261.2	265.5	276.5	291.7	315.0	353.9	412.8	481.8
67.5°	212.7	214.7	214.3	217.1	221.0	229.5	240.4	259.7	288.5	331.5	386.7
70°	186.3	187.9	187.5	189.6	193.9	199.4	208.3	226.5	247.2	284.1	331.5
72.5°	162.6	163.2	162.2	164.9	167.5	172.3	182.2	191.9	211.3	242.4	281.4
75°	124.5	125.3	126.1	127.8	130.4	132.9	138.0	147.7	160.5	183.8	208.7
77.5°	93.3	91.7	93.8	93.5	94.9	96.9	101.3	106.5	116.9	131.7	151.0
80°	70.3	70.7	70.7	71.1	73.2	74.5	78.4	82.1	90.2	101.2	114.7
82.5°	51.3	52.4	51.8	52.5	54.3	55.2	57.3	60.4	65.1	73.8	83.6
85°	28.0	25.8	26.7	27.6	27.6	28.0	29.6	30.9	33.4	36.9	40.6
87.5°	14.0	14.5	14.7	14.5	14.8	14.5	15.6	15.3	16.1	16.8	17.8
90°	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3	21.0	19.6	17.7
92.5°	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3	21.0	19.6	17.9
95°	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3	21.0	19.6	30.0
97.5°	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0	52.7	60.4	80.9
100°	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2	172.9	213.5	212.5
102.5°	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1	264.8	272.5	271.8
105°	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1	463.0	462.9	462.4
110°	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1	526.9	527.7	527.2



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5	589.5	590.6	590.3
115°	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7	683.7	684.9	684.6
117.5°	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6	774.9	776.4	775.3
120°	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3	832.8	833.3	832.5
122.5°	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2	888.8	889.3	888.9
125°	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9	970.9	972.0	972.0
127.5°	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5	1045.1	1045.7	1045.9
130°	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2	1094.0	1094.8	1094.5
132.5°	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6	1138.8	1139.0	1139.5
135°	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3	1205.9	1206.5	1207.0
137.5°	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5	1267.5	1267.3	1267.8
140°	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7	1305.2	1304.6	1304.9
142.5°	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1	1343.0	1343.0	1342.6
145°	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0	1395.7	1395.5	1395.5
147.5°	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3	1441.0	1440.6	1440.3
150°	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1	1469.7	1469.1	1468.5
152.5°	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7	1495.2	1494.6	1494.1
155°	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9	1530.1	1529.3	1528.7
157.5°	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9	1559.1	1558.2	1558.1
160°	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0	1577.0	1575.9	1575.6
162.5°	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6	1593.1	1591.5	1591.3
165°	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9	1614.3	1612.7	1612.4
167.5°	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1	1630.1	1628.2	1627.9
170°	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4	1638.2	1636.0	1635.7
172.5°	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8	1644.9	1642.9	1642.4
175°	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8	1651.7	1649.5	1649.3
177.5°	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8	1655.2	1653.7	1653.4
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1026.2	1023.9	1021.1	1016.4	1010.6	1007.5	1002.8	999.8	993.7	988.6	983.2
5°	1078.2	1067.2	1057.1	1044.0	1029.6	1020.3	1009.3	996.9	984.3	971.2	956.8
7.5°	1132.2	1112.7	1091.5	1068.8	1046.5	1026.1	1006.5	987.2	969.3	947.6	929.3
10°	1168.4	1143.9	1117.6	1086.7	1056.7	1030.5	1003.8	980.5	956.8	931.4	908.9
12.5°	1204.7	1172.0	1134.9	1101.0	1064.8	1033.1	1001.8	972.0	942.2	914.1	887.9
15°	1230.3	1201.4	1167.2	1118.9	1078.2	1034.7	993.2	954.6	918.7	887.4	854.4
17.5°	1247.1	1210.0	1173.2	1126.9	1073.6	1024.8	977.9	933.8	893.2	853.5	821.7
20°	1250.2	1212.0	1173.5	1128.2	1073.6	1017.7	970.8	917.8	874.2	833.2	794.2
22.5°	1249.1	1206.0	1164.0	1117.4	1064.1	1012.7	955.9	901.9	854.6	814.2	773.6
25°	1239.6	1193.4	1140.9	1094.0	1041.5	986.8	929.3	873.3	825.1	778.9	738.7
27.5°	1231.6	1171.7	1112.3	1057.5	1006.8	956.8	901.6	844.4	790.9	744.1	706.2
30°	1221.8	1156.2	1089.2	1032.1	980.1	931.4	879.3	823.5	767.5	721.8	681.2
32.5°	1213.0	1136.5	1065.9	1003.7	948.5	901.2	853.2	800.1	745.2	698.8	658.1
35°	1196.0	1107.5	1026.6	956.3	897.5	848.8	808.6	759.0	708.7	663.8	624.8
37.5°	1174.4	1069.3	982.6	908.9	844.4	793.1	755.7	717.6	669.3	626.1	590.8
40°	1157.4	1042.3	950.4	875.1	808.2	754.8	720.2	684.1	643.9	603.7	566.5
42.5°	1136.1	1017.9	917.9	836.8	770.5	718.6	682.2	651.6	616.1	578.6	544.0
45°	1096.9	973.7	865.4	778.1	711.2	660.0	622.3	599.5	572.8	537.2	508.0
47.5°	1039.3	920.6	808.5	718.5	649.5	602.0	566.7	544.8	525.9	499.5	473.0
50°	988.1	881.0	767.5	678.2	609.2	561.3	528.8	508.8	492.8	472.5	450.0
52.5°	930.8	831.2	727.2	639.0	570.6	523.4	491.5	474.0	460.6	446.1	424.0
55°	839.9	755.3	658.8	574.9	511.8	465.7	437.7	422.5	411.5	400.5	386.9
57.5°	739.7	673.5	588.0	511.4	453.3	411.3	385.2	370.4	361.9	356.2	348.2
60°	669.3	612.6	538.9	469.0	412.4	375.1	349.7	338.3	331.1	326.4	320.5
62.5°	604.0	557.4	489.1	425.3	375.8	340.6	317.9	306.8	299.9	297.6	292.7
65°	507.6	471.7	415.3	362.4	320.1	290.0	270.9	260.3	256.1	253.6	254.0
67.5°	412.7	390.8	345.5	300.4	266.6	241.4	226.2	218.0	215.9	212.5	212.5
70°	354.7	338.3	300.2	260.8	230.7	211.2	197.7	189.2	187.1	185.4	185.0
72.5°	303.6	289.2	256.1	224.5	197.5	180.4	169.3	164.2	160.7	159.7	159.6
75°	228.2	220.1	193.9	168.9	150.3	138.4	130.9	126.1	123.6	123.2	123.6
77.5°	162.2	155.2	138.5	120.8	109.1	100.1	93.7	92.0	89.2	89.3	88.8
80°	121.9	117.2	106.7	92.7	83.0	75.3	72.0	69.0	68.2	66.9	68.2
82.5°	88.4	83.4	76.2	67.3	59.3	54.7	51.3	50.4	49.9	49.2	49.6
85°	43.6	44.0	39.8	33.0	29.6	27.1	24.9	24.9	24.5	24.1	24.5
87.5°	18.1	17.0	15.2	13.9	11.7	10.3	9.5	9.4	8.8	8.9	9.7
90°	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9	17.4	15.8	14.3
95°	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0	69.1	68.3	67.5
97.5°	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0	147.5	149.0	150.5
100°	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0	205.8	206.6	207.4
102.5°	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9	265.9	266.9	268.0
105°	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9	361.9	363.1	364.1
107.5°	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5	460.5	460.5	460.5
110°	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2	586.9	587.5	588.2
115°	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5	678.8	680.2	681.6
117.5°	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0	771.9	771.8	771.8
120°	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9	830.6	830.4	830.1
122.5°	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0	883.9	885.0	886.1
125°	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4	965.3	967.3	969.1
127.5°	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2	1041.6	1043.0	1044.4
130°	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4	1088.8	1090.1	1091.5
132.5°	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5	1136.1	1137.7	1139.3
135°	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5	1203.1	1204.8	1206.5
137.5°	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1	1264.5	1266.0	1267.4
140°	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4	1304.0	1304.5	1305.0
142.5°	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7	1340.0	1340.4	1340.7
145°	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0	1393.5	1394.1	1394.7
147.5°	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7	1439.5	1439.4	1439.3
150°	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1468.5	1468.0	1467.5
152.5°	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5	1496.4	1495.2	1494.0
155°	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1	1532.5	1530.9	1529.3
157.5°	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4	1561.4	1560.4	1559.4
160°	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0	1580.4	1578.7	1577.1
162.5°	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7	1596.1	1594.5	1592.8
165°	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9	1617.2	1615.5	1613.9
167.5°	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5	1632.9	1631.2	1629.5
170°	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4	1641.4	1639.6	1637.6
172.5°	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3	1647.4	1645.4	1643.6
175°	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6	1654.0	1652.4	1650.7
177.5°	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6	1657.3	1656.0	1654.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	980.2	976.4	973.4	966.6	962.9	957.8	953.7	958.1	953.4	955.4	952.4
5°	949.6	937.8	929.3	917.0	906.4	896.7	889.5	888.2	884.8	883.1	878.0
7.5°	912.8	898.0	883.5	867.4	853.8	840.0	831.2	823.9	819.1	812.8	808.5
10°	891.1	871.2	854.4	834.9	817.9	803.1	791.2	785.3	779.8	771.8	768.8
12.5°	864.4	843.8	823.1	802.3	786.1	769.6	759.4	750.4	746.7	737.5	736.6
15°	832.3	801.4	781.1	759.9	737.4	723.9	715.4	705.7	701.5	695.1	690.5
17.5°	794.0	766.5	741.0	719.1	699.9	688.4	677.9	671.2	664.0	659.8	652.2
20°	766.3	740.0	714.6	691.3	676.5	663.4	654.9	648.6	641.0	638.9	631.2
22.5°	742.9	714.0	689.6	670.0	653.8	639.0	629.8	625.6	620.3	613.8	612.2
25°	704.9	674.8	654.1	634.6	620.2	606.7	600.3	594.8	589.7	585.1	583.3
27.5°	672.1	645.1	620.5	602.9	590.4	578.0	572.4	565.7	562.1	558.3	553.8
30°	649.0	621.5	599.9	582.9	569.4	558.4	552.4	547.8	544.5	541.0	538.5
32.5°	625.3	599.8	578.9	562.3	548.8	540.5	535.2	531.9	528.2	524.1	520.9
35°	593.9	566.0	545.7	531.3	520.7	514.4	508.4	505.5	501.2	501.2	497.8
37.5°	558.6	534.5	516.6	503.4	494.0	488.3	481.8	479.8	477.1	475.3	474.2
40°	537.7	515.2	498.3	485.2	475.0	470.3	465.3	461.9	460.2	458.0	457.2
42.5°	516.0	494.6	478.3	466.2	457.4	453.4	448.7	446.3	442.9	440.1	439.6
45°	483.1	462.3	447.5	437.7	430.2	425.5	422.5	417.4	415.7	412.4	411.9
47.5°	451.8	431.9	417.4	409.4	402.7	398.8	394.2	389.1	387.2	385.5	385.3
50°	428.4	410.3	396.6	389.1	382.7	377.2	372.5	369.2	367.9	367.9	368.8
52.5°	404.7	389.2	377.7	368.4	362.4	356.5	352.2	350.2	348.2	350.3	351.8
55°	370.0	354.3	345.8	337.0	331.1	324.2	322.2	321.3	320.1	323.4	325.1
57.5°	333.3	322.3	312.3	303.5	298.2	294.3	291.5	290.9	293.3	294.9	300.4
60°	309.9	297.2	288.3	281.5	275.2	272.6	271.8	270.9	272.6	277.3	284.5
62.5°	284.1	273.9	264.2	259.2	254.5	250.3	250.1	250.6	254.0	259.3	266.5
65°	246.4	237.5	231.1	225.2	221.4	218.9	219.7	221.4	225.2	232.4	240.4
67.5°	208.1	201.9	196.2	191.4	187.8	187.8	188.7	191.2	195.7	204.0	211.3
70°	183.3	176.5	171.9	169.7	166.8	165.1	167.6	171.9	175.7	183.3	189.6
72.5°	158.6	152.9	149.2	147.7	146.5	145.1	145.9	150.5	155.7	163.3	170.7
75°	121.9	119.8	117.2	115.6	114.3	115.1	116.0	120.3	124.5	132.5	141.0
77.5°	88.9	86.7	85.3	84.9	84.1	84.5	87.0	90.1	94.2	100.1	106.5
80°	67.3	66.4	65.6	65.2	65.2	65.6	69.0	71.1	74.9	80.5	85.5
82.5°	49.0	48.5	48.3	48.3	48.6	48.7	50.7	53.5	56.7	60.8	65.2
85°	25.8	24.9	26.3	26.7	25.8	27.1	28.0	29.6	30.9	33.0	35.1
87.5°	10.4	11.6	11.6	12.3	12.7	13.8	13.7	15.3	16.2	17.2	17.1
90°	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3	23.7	25.1	26.2
92.5°	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3	23.7	25.1	25.9
95°	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3	23.7	25.1	25.8
97.5°	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0	37.3	29.6	25.8
100°	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2	91.6	51.0	30.2
102.5°	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1	249.4	241.7	228.6
105°	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.7	365.6
107.5°	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1	463.1	463.2	462.8
110°	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1	525.3	524.5	524.2



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5	587.5	586.4	585.7
115°	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7	681.6	680.4	679.1
117.5°	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6	772.2	770.7	769.6
120°	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3	831.7	831.2	830.2
122.5°	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2	887.7	887.1	886.1
125°	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9	968.7	967.7	966.7
127.5°	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5	1043.9	1043.3	1042.0
130°	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2	1092.3	1091.5	1090.4
132.5°	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6	1138.5	1138.3	1137.5
135°	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3	1204.8	1204.3	1203.1
137.5°	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5	1267.6	1267.8	1267.1
140°	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7	1306.3	1306.8	1306.3
142.5°	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1	1343.3	1343.4	1342.6
145°	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0	1396.3	1396.5	1395.9
147.5°	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3	1441.6	1441.9	1441.1
150°	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1	1470.7	1471.3	1470.5
152.5°	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7	1496.2	1496.8	1496.1
155°	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9	1531.7	1532.5	1531.8
157.5°	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9	1560.8	1561.7	1561.1
160°	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0	1579.2	1580.2	1579.7
162.5°	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6	1596.2	1597.7	1597.3
165°	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9	1617.6	1619.3	1618.9
167.5°	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1	1634.0	1636.0	1635.7
170°	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4	1642.6	1644.7	1644.6
172.5°	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8	1648.8	1650.7	1650.5
175°	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8	1656.0	1658.2	1658.1
177.5°	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8	1658.2	1659.8	1659.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	950.3	952.7	950.6	953.4	950.6	952.7	950.3	952.4	955.4	953.4	958.1
5°	875.9	872.1	874.7	872.9	874.7	872.1	875.9	878.0	883.1	884.8	888.2
7.5°	807.1	803.5	799.4	797.4	799.4	803.5	807.1	808.5	812.8	819.1	823.9
10°	764.2	759.5	759.0	756.1	759.0	759.5	764.2	768.8	771.8	779.8	785.3
12.5°	732.6	728.3	723.5	722.3	723.5	728.3	732.6	736.6	737.5	746.7	750.4
15°	687.9	684.5	681.6	684.1	681.6	684.5	687.9	690.5	695.1	701.5	705.7
17.5°	650.8	648.0	647.4	644.3	647.4	648.0	650.8	652.2	659.8	664.0	671.2
20°	627.4	625.3	626.1	620.6	626.1	625.3	627.4	631.2	638.9	641.0	648.6
22.5°	608.8	604.6	604.1	603.0	604.1	604.6	608.8	612.2	613.8	620.3	625.6
25°	579.6	577.5	575.4	577.5	575.4	577.5	579.6	583.3	585.1	589.7	594.8
27.5°	554.1	551.5	551.0	551.2	551.0	551.5	554.1	553.8	558.3	562.1	565.7
30°	538.5	534.3	534.7	534.3	534.7	534.3	538.5	538.5	541.0	544.5	547.8
32.5°	521.5	518.7	518.1	517.3	518.1	518.7	521.5	520.9	524.1	528.2	531.9
35°	496.6	496.6	494.5	494.5	494.5	496.6	496.6	497.8	501.2	501.2	505.5
37.5°	473.1	472.7	471.4	471.7	471.4	472.7	473.1	474.2	475.3	477.1	479.8
40°	455.5	455.1	453.8	451.3	453.8	455.1	455.5	457.2	458.0	460.2	461.9
42.5°	438.5	437.2	436.6	435.7	436.6	437.2	438.5	439.6	440.1	442.9	446.3
45°	411.9	411.9	411.1	410.7	411.1	411.9	411.9	411.9	412.4	415.7	417.4
47.5°	386.0	386.8	388.4	388.2	388.4	386.8	386.0	385.3	385.5	387.2	389.1
50°	370.4	370.9	372.1	372.5	372.1	370.9	370.4	368.8	367.9	367.9	369.2
52.5°	353.2	355.6	357.2	356.9	357.2	355.6	353.2	351.8	350.3	348.2	350.2
55°	329.0	331.9	334.8	335.3	334.8	331.9	329.0	325.1	323.4	320.1	321.3
57.5°	305.0	309.2	312.3	313.2	312.3	309.2	305.0	300.4	294.9	293.3	290.9
60°	288.7	294.2	298.1	299.7	298.1	294.2	288.7	284.5	277.3	272.6	270.9
62.5°	273.1	279.3	283.2	283.5	283.2	279.3	273.1	266.5	259.3	254.0	250.6
65°	247.7	254.0	257.4	259.9	257.4	254.0	247.7	240.4	232.4	225.2	221.4
67.5°	220.2	226.6	230.3	232.4	230.3	226.6	220.2	211.3	204.0	195.7	191.2
70°	200.2	206.6	211.7	213.4	211.7	206.6	200.2	189.6	183.3	175.7	171.9
72.5°	180.6	186.3	190.4	192.3	190.4	186.3	180.6	170.7	163.3	155.7	150.5
75°	146.5	154.1	157.9	160.0	157.9	154.1	146.5	141.0	132.5	124.5	120.3
77.5°	112.9	119.9	122.2	123.3	122.2	119.9	112.9	106.5	100.1	94.2	90.1
80°	90.6	94.8	97.8	98.2	97.8	94.8	90.6	85.5	80.5	74.9	71.1
82.5°	69.6	73.1	74.1	75.2	74.1	73.1	69.6	65.2	60.8	56.7	53.5
85°	38.1	39.8	40.2	39.8	40.2	39.8	38.1	35.1	33.0	30.9	29.6
87.5°	17.9	17.8	17.9	18.8	17.9	17.8	17.9	17.1	17.2	16.2	15.3
90°	27.0	27.8	28.6	29.4	28.6	27.8	27.0	26.2	25.1	23.7	22.3
92.5°	26.3	26.7	27.1	27.5	27.1	26.7	26.3	25.9	25.1	23.7	22.3
95°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.1	23.7	22.3
97.5°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	29.6	37.3	45.0
100°	29.0	28.0	26.9	25.8	26.9	28.0	29.0	30.2	51.0	91.6	132.2
102.5°	210.0	191.5	172.9	154.4	172.9	191.5	210.0	228.6	241.7	249.4	257.1
105°	365.3	365.1	364.8	364.5	364.8	365.1	365.3	365.6	365.7	365.7	365.7
107.5°	461.9	461.1	460.3	459.5	460.3	461.1	461.9	462.8	463.2	463.1	463.1
110°	524.5	524.7	525.1	525.3	525.1	524.7	524.5	524.2	524.5	525.3	526.1



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	585.4	585.0	584.6	584.2	584.6	585.0	585.4	585.7	586.4	587.5	588.5
115°	677.5	675.8	674.2	672.5	674.2	675.8	677.5	679.1	680.4	681.6	682.7
117.5°	769.0	768.3	767.5	766.8	767.5	768.3	769.0	769.6	770.7	772.2	773.6
120°	828.8	827.4	826.1	824.8	826.1	827.4	828.8	830.2	831.2	831.7	832.3
122.5°	884.5	882.9	881.3	879.7	881.3	882.9	884.5	886.1	887.1	887.7	888.2
125°	965.9	965.1	964.3	963.4	964.3	965.1	965.9	966.7	967.7	968.7	969.9
127.5°	1039.9	1038.0	1035.9	1033.9	1035.9	1038.0	1039.9	1042.0	1043.3	1043.9	1044.5
130°	1089.1	1087.7	1086.3	1084.9	1086.3	1087.7	1089.1	1090.4	1091.5	1092.3	1093.2
132.5°	1136.2	1134.8	1133.4	1132.0	1133.4	1134.8	1136.2	1137.5	1138.3	1138.5	1138.6
135°	1201.5	1199.9	1198.2	1196.6	1198.2	1199.9	1201.5	1203.1	1204.3	1204.8	1205.3
137.5°	1265.7	1264.3	1262.8	1261.4	1262.8	1264.3	1265.7	1267.1	1267.8	1267.6	1267.5
140°	1304.6	1303.0	1301.4	1299.8	1301.4	1303.0	1304.6	1306.3	1306.8	1306.3	1305.7
142.5°	1340.9	1339.3	1337.7	1336.0	1337.7	1339.3	1340.9	1342.6	1343.4	1343.3	1343.1
145°	1394.2	1392.6	1391.0	1389.4	1391.0	1392.6	1394.2	1395.9	1396.5	1396.3	1396.0
147.5°	1439.2	1437.2	1435.3	1433.3	1435.3	1437.2	1439.2	1441.1	1441.9	1441.6	1441.3
150°	1468.3	1466.1	1464.0	1461.8	1464.0	1466.1	1468.3	1470.5	1471.3	1470.7	1470.1
152.5°	1494.1	1492.2	1490.2	1488.2	1490.2	1492.2	1494.1	1496.1	1496.8	1496.2	1495.7
155°	1529.7	1527.5	1525.3	1523.1	1525.3	1527.5	1529.7	1531.8	1532.5	1531.7	1530.9
157.5°	1558.9	1556.7	1554.4	1552.3	1554.4	1556.7	1558.9	1561.1	1561.7	1560.8	1559.9
160°	1577.5	1575.3	1573.1	1571.0	1573.1	1575.3	1577.5	1579.7	1580.2	1579.2	1578.0
162.5°	1594.9	1592.4	1590.1	1587.6	1590.1	1592.4	1594.9	1597.3	1597.7	1596.2	1594.6
165°	1616.8	1614.6	1612.4	1610.2	1612.4	1614.6	1616.8	1618.9	1619.3	1617.6	1615.9
167.5°	1633.3	1630.8	1628.4	1626.0	1628.4	1630.8	1633.3	1635.7	1636.0	1634.0	1632.1
170°	1642.2	1639.7	1637.2	1634.8	1637.2	1639.7	1642.2	1644.6	1644.7	1642.6	1640.4
172.5°	1648.0	1645.6	1643.2	1640.7	1643.2	1645.6	1648.0	1650.5	1650.7	1648.8	1646.8
175°	1655.6	1653.2	1650.7	1648.3	1650.7	1653.2	1655.6	1658.1	1658.2	1656.0	1653.8
177.5°	1657.9	1656.2	1654.4	1652.7	1654.4	1656.2	1657.9	1659.7	1659.8	1658.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	953.7	957.8	962.9	966.6	973.4	976.4	980.2	983.2	988.6	993.7	999.8
5°	889.5	896.7	906.4	917.0	929.3	937.8	949.6	956.8	971.2	984.3	996.9
7.5°	831.2	840.0	853.8	867.4	883.5	898.0	912.8	929.3	947.6	969.3	987.2
10°	791.2	803.1	817.9	834.9	854.4	871.2	891.1	908.9	931.4	956.8	980.5
12.5°	759.4	769.6	786.1	802.3	823.1	843.8	864.4	887.9	914.1	942.2	972.0
15°	715.4	723.9	737.4	759.9	781.1	801.4	832.3	854.4	887.4	918.7	954.6
17.5°	677.9	688.4	699.9	719.1	741.0	766.5	794.0	821.7	853.5	893.2	933.8
20°	654.9	663.4	676.5	691.3	714.6	740.0	766.3	794.2	833.2	874.2	917.8
22.5°	629.8	639.0	653.8	670.0	689.6	714.0	742.9	773.6	814.2	854.6	901.9
25°	600.3	606.7	620.2	634.6	654.1	674.8	704.9	738.7	778.9	825.1	873.3
27.5°	572.4	578.0	590.4	602.9	620.5	645.1	672.1	706.2	744.1	790.9	844.4
30°	552.4	558.4	569.4	582.9	599.9	621.5	649.0	681.2	721.8	767.5	823.5
32.5°	535.2	540.5	548.8	562.3	578.9	599.8	625.3	658.1	698.8	745.2	800.1
35°	508.4	514.4	520.7	531.3	545.7	566.0	593.9	624.8	663.8	708.7	759.0
37.5°	481.8	488.3	494.0	503.4	516.6	534.5	558.6	590.8	626.1	669.3	717.6
40°	465.3	470.3	475.0	485.2	498.3	515.2	537.7	566.5	603.7	643.9	684.1
42.5°	448.7	453.4	457.4	466.2	478.3	494.6	516.0	544.0	578.6	616.1	651.6
45°	422.5	425.5	430.2	437.7	447.5	462.3	483.1	508.0	537.2	572.8	599.5
47.5°	394.2	398.8	402.7	409.4	417.4	431.9	451.8	473.0	499.5	525.9	544.8
50°	372.5	377.2	382.7	389.1	396.6	410.3	428.4	450.0	472.5	492.8	508.8
52.5°	352.2	356.5	362.4	368.4	377.7	389.2	404.7	424.0	446.1	460.6	474.0
55°	322.2	324.2	331.1	337.0	345.8	354.3	370.0	386.9	400.5	411.5	422.5
57.5°	291.5	294.3	298.2	303.5	312.3	322.3	333.3	348.2	356.2	361.9	370.4
60°	271.8	272.6	275.2	281.5	288.3	297.2	309.9	320.5	326.4	331.1	338.3
62.5°	250.1	250.3	254.5	259.2	264.2	273.9	284.1	292.7	297.6	299.9	306.8
65°	219.7	218.9	221.4	225.2	231.1	237.5	246.4	254.0	253.6	256.1	260.3
67.5°	188.7	187.8	187.8	191.4	196.2	201.9	208.1	212.5	212.5	215.9	218.0
70°	167.6	165.1	166.8	169.7	171.9	176.5	183.3	185.0	185.4	187.1	189.2
72.5°	145.9	145.1	146.5	147.7	149.2	152.9	158.6	159.6	159.7	160.7	164.2
75°	116.0	115.1	114.3	115.6	117.2	119.8	121.9	123.6	123.2	123.6	126.1
77.5°	87.0	84.5	84.1	84.9	85.3	86.7	88.9	88.8	89.3	89.2	92.0
80°	69.0	65.6	65.2	65.2	65.6	66.4	67.3	68.2	66.9	68.2	69.0
82.5°	50.7	48.7	48.6	48.3	48.3	48.5	49.0	49.6	49.2	49.9	50.4
85°	28.0	27.1	25.8	26.7	26.3	24.9	25.8	24.5	24.1	24.5	24.9
87.5°	13.7	13.8	12.7	12.3	11.6	11.6	10.4	9.7	8.9	8.8	9.4
90°	21.0	19.6	17.7	15.8	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	21.0	19.6	17.9	16.2	14.6	12.9	12.8	14.3	15.8	17.4	18.9
95°	21.0	19.6	30.0	40.4	50.7	61.1	66.7	67.5	68.3	69.1	70.0
97.5°	52.7	60.4	80.9	101.4	121.9	142.4	152.0	150.5	149.0	147.5	146.0
100°	172.9	213.5	212.5	211.4	210.3	209.2	208.2	207.4	206.6	205.8	205.0
102.5°	264.8	272.5	271.8	271.2	270.5	269.9	269.0	268.0	266.9	265.9	264.9
105°	365.7	365.7	365.7	365.7	365.7	365.7	365.2	364.1	363.1	361.9	360.9
107.5°	463.0	462.9	462.4	461.9	461.3	460.7	460.5	460.5	460.5	460.5	460.5
110°	526.9	527.7	527.2	526.7	526.1	525.5	525.3	525.3	525.3	525.3	525.3



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	589.5	590.6	590.3	590.0	589.6	589.3	588.8	588.2	587.5	586.9	586.2
115°	683.7	684.9	684.6	684.3	684.0	683.7	682.9	681.6	680.2	678.8	677.5
117.5°	774.9	776.4	775.3	774.3	773.3	772.3	771.8	771.8	771.8	771.9	772.0
120°	832.8	833.3	832.5	831.7	830.9	830.1	829.8	830.1	830.4	830.6	830.9
122.5°	888.8	889.3	888.9	888.5	888.2	887.8	887.0	886.1	885.0	883.9	883.0
125°	970.9	972.0	972.0	972.0	972.0	972.0	971.1	969.1	967.3	965.3	963.4
127.5°	1045.1	1045.7	1045.9	1046.0	1046.2	1046.4	1045.7	1044.4	1043.0	1041.6	1040.2
130°	1094.0	1094.8	1094.5	1094.2	1094.0	1093.6	1092.8	1091.5	1090.1	1088.8	1087.4
132.5°	1138.8	1139.0	1139.5	1140.1	1140.8	1141.3	1140.8	1139.3	1137.7	1136.1	1134.5
135°	1205.9	1206.5	1207.0	1207.5	1208.1	1208.6	1208.1	1206.5	1204.8	1203.1	1201.5
137.5°	1267.5	1267.3	1267.8	1268.3	1268.8	1269.3	1268.9	1267.4	1266.0	1264.5	1263.1
140°	1305.2	1304.6	1304.9	1305.2	1305.5	1305.7	1305.6	1305.0	1304.5	1304.0	1303.4
142.5°	1343.0	1343.0	1342.6	1342.1	1341.8	1341.4	1341.0	1340.7	1340.4	1340.0	1339.7
145°	1395.7	1395.5	1395.5	1395.5	1395.5	1395.5	1395.2	1394.7	1394.1	1393.5	1393.0
147.5°	1441.0	1440.6	1440.3	1440.0	1439.7	1439.3	1439.2	1439.3	1439.4	1439.5	1439.7
150°	1469.7	1469.1	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1
152.5°	1495.2	1494.6	1494.1	1493.5	1493.0	1492.4	1492.7	1494.0	1495.2	1496.4	1497.5
155°	1530.1	1529.3	1528.7	1528.1	1527.6	1527.1	1527.6	1529.3	1530.9	1532.5	1534.1
157.5°	1559.1	1558.2	1558.1	1558.1	1558.0	1558.0	1558.4	1559.4	1560.4	1561.4	1562.4
160°	1577.0	1575.9	1575.6	1575.3	1575.1	1574.8	1575.5	1577.1	1578.7	1580.4	1582.0
162.5°	1593.1	1591.5	1591.3	1591.1	1590.7	1590.5	1591.1	1592.8	1594.5	1596.1	1597.7
165°	1614.3	1612.7	1612.4	1612.2	1611.8	1611.6	1612.3	1613.9	1615.5	1617.2	1618.9
167.5°	1630.1	1628.2	1627.9	1627.6	1627.3	1627.1	1627.7	1629.5	1631.2	1632.9	1634.5
170°	1638.2	1636.0	1635.7	1635.5	1635.2	1634.9	1635.7	1637.6	1639.6	1641.4	1643.4
172.5°	1644.9	1642.9	1642.4	1641.9	1641.4	1641.0	1641.6	1643.6	1645.4	1647.4	1649.3
175°	1651.7	1649.5	1649.3	1648.9	1648.7	1648.5	1649.1	1650.7	1652.4	1654.0	1655.6
177.5°	1655.2	1653.7	1653.4	1653.3	1653.0	1652.8	1653.3	1654.6	1656.0	1657.3	1658.6
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1002.8	1007.5	1010.6	1016.4	1021.1	1023.9	1026.2	1028.3	1030.6	1032.7	1038.4
5°	1009.3	1020.3	1029.6	1044.0	1057.1	1067.2	1078.2	1088.0	1096.1	1107.5	1116.4
7.5°	1006.5	1026.1	1046.5	1068.8	1091.5	1112.7	1132.2	1150.4	1166.9	1186.9	1204.4
10°	1003.8	1030.5	1056.7	1086.7	1117.6	1143.9	1168.4	1193.4	1211.6	1237.1	1258.6
12.5°	1001.8	1033.1	1064.8	1101.0	1134.9	1172.0	1204.7	1222.9	1250.6	1270.9	1296.6
15°	993.2	1034.7	1078.2	1118.9	1167.2	1201.4	1230.3	1265.8	1291.6	1317.4	1345.4
17.5°	977.9	1024.8	1073.6	1126.9	1173.2	1210.0	1247.1	1281.4	1312.2	1346.9	1381.6
20°	970.8	1017.7	1073.6	1128.2	1173.5	1212.0	1250.2	1287.8	1321.7	1366.1	1406.4
22.5°	955.9	1012.7	1064.1	1117.4	1164.0	1206.0	1249.1	1291.9	1336.9	1387.2	1437.5
25°	929.3	986.8	1041.5	1094.0	1140.9	1193.4	1239.6	1296.7	1354.3	1420.7	1483.4
27.5°	901.6	956.8	1006.8	1057.5	1112.3	1171.7	1231.6	1296.5	1371.8	1455.7	1544.1
30°	879.3	931.4	980.1	1032.1	1089.2	1156.2	1221.8	1298.9	1386.0	1480.4	1585.4
32.5°	853.2	901.2	948.5	1003.7	1065.9	1136.5	1213.0	1297.5	1402.3	1509.6	1617.6
35°	808.6	848.8	897.5	956.3	1026.6	1107.5	1196.0	1295.8	1416.1	1539.3	1630.4
37.5°	755.7	793.1	844.4	908.9	982.6	1069.3	1174.4	1292.9	1420.6	1518.8	1548.2
40°	720.2	754.8	808.2	875.1	950.4	1042.3	1157.4	1282.7	1406.4	1469.0	1444.9
42.5°	682.2	718.6	770.5	836.8	917.9	1017.9	1136.1	1261.4	1365.1	1388.8	1305.4
45°	622.3	660.0	711.2	778.1	865.4	973.7	1096.9	1210.8	1270.5	1227.7	1098.6
47.5°	566.7	602.0	649.5	718.5	808.5	920.6	1039.3	1130.1	1134.8	1032.8	894.9
50°	528.8	561.3	609.2	678.2	767.5	881.0	988.1	1059.6	1027.4	911.9	779.3
52.5°	491.5	523.4	570.6	639.0	727.2	831.2	930.8	981.0	920.5	801.8	688.6
55°	437.7	465.7	511.8	574.9	658.8	755.3	839.9	857.3	778.5	661.7	569.8
57.5°	385.2	411.3	453.3	511.4	588.0	673.5	739.7	736.1	652.8	552.5	479.6
60°	349.7	375.1	412.4	469.0	538.9	612.6	669.3	655.7	573.2	486.8	425.5
62.5°	317.9	340.6	375.8	425.3	489.1	557.4	604.0	584.0	503.1	427.5	379.0
65°	270.9	290.0	320.1	362.4	415.3	471.7	507.6	481.8	412.8	353.9	315.0
67.5°	226.2	241.4	266.6	300.4	345.5	390.8	412.7	386.7	331.5	288.5	259.7
70°	197.7	211.2	230.7	260.8	300.2	338.3	354.7	331.5	284.1	247.2	226.5
72.5°	169.3	180.4	197.5	224.5	256.1	289.2	303.6	281.4	242.4	211.3	191.9
75°	130.9	138.4	150.3	168.9	193.9	220.1	228.2	208.7	183.8	160.5	147.7
77.5°	93.7	100.1	109.1	120.8	138.5	155.2	162.2	151.0	131.7	116.9	106.5
80°	72.0	75.3	83.0	92.7	106.7	117.2	121.9	114.7	101.2	90.2	82.1
82.5°	51.3	54.7	59.3	67.3	76.2	83.4	88.4	83.6	73.8	65.1	60.4
85°	24.9	27.1	29.6	33.0	39.8	44.0	43.6	40.6	36.9	33.4	30.9
87.5°	9.5	10.3	11.7	13.9	15.2	17.0	18.1	17.8	16.8	16.1	15.3
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.8	17.7	19.6	21.0	22.3
92.5°	17.4	15.8	14.3	12.8	12.9	14.6	16.2	17.9	19.6	21.0	22.3
95°	69.1	68.3	67.5	66.7	61.1	50.7	40.4	30.0	19.6	21.0	22.3
97.5°	147.5	149.0	150.5	152.0	142.4	121.9	101.4	80.9	60.4	52.7	45.0
100°	205.8	206.6	207.4	208.2	209.2	210.3	211.4	212.5	213.5	172.9	132.2
102.5°	265.9	266.9	268.0	269.0	269.9	270.5	271.2	271.8	272.5	264.8	257.1
105°	361.9	363.1	364.1	365.2	365.7	365.7	365.7	365.7	365.7	365.7	365.7
107.5°	460.5	460.5	460.5	460.5	460.7	461.3	461.9	462.4	462.9	463.0	463.1
110°	525.3	525.3	525.3	525.3	525.5	526.1	526.7	527.2	527.7	526.9	526.1



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	586.9	587.5	588.2	588.8	589.3	589.6	590.0	590.3	590.6	589.5	588.5
115°	678.8	680.2	681.6	682.9	683.7	684.0	684.3	684.6	684.9	683.7	682.7
117.5°	771.9	771.8	771.8	771.8	772.3	773.3	774.3	775.3	776.4	774.9	773.6
120°	830.6	830.4	830.1	829.8	830.1	830.9	831.7	832.5	833.3	832.8	832.3
122.5°	883.9	885.0	886.1	887.0	887.8	888.2	888.5	888.9	889.3	888.8	888.2
125°	965.3	967.3	969.1	971.1	972.0	972.0	972.0	972.0	972.0	970.9	969.9
127.5°	1041.6	1043.0	1044.4	1045.7	1046.4	1046.2	1046.0	1045.9	1045.7	1045.1	1044.5
130°	1088.8	1090.1	1091.5	1092.8	1093.6	1094.0	1094.2	1094.5	1094.8	1094.0	1093.2
132.5°	1136.1	1137.7	1139.3	1140.8	1141.3	1140.8	1140.1	1139.5	1139.0	1138.8	1138.6
135°	1203.1	1204.8	1206.5	1208.1	1208.6	1208.1	1207.5	1207.0	1206.5	1205.9	1205.3
137.5°	1264.5	1266.0	1267.4	1268.9	1269.3	1268.8	1268.3	1267.8	1267.3	1267.5	1267.5
140°	1304.0	1304.5	1305.0	1305.6	1305.7	1305.5	1305.2	1304.9	1304.6	1305.2	1305.7
142.5°	1340.0	1340.4	1340.7	1341.0	1341.4	1341.8	1342.1	1342.6	1343.0	1343.0	1343.1
145°	1393.5	1394.1	1394.7	1395.2	1395.5	1395.5	1395.5	1395.5	1395.5	1395.7	1396.0
147.5°	1439.5	1439.4	1439.3	1439.2	1439.3	1439.7	1440.0	1440.3	1440.6	1441.0	1441.3
150°	1468.5	1468.0	1467.5	1466.9	1466.9	1467.5	1468.0	1468.5	1469.1	1469.7	1470.1
152.5°	1496.4	1495.2	1494.0	1492.7	1492.4	1493.0	1493.5	1494.1	1494.6	1495.2	1495.7
155°	1532.5	1530.9	1529.3	1527.6	1527.1	1527.6	1528.1	1528.7	1529.3	1530.1	1530.9
157.5°	1561.4	1560.4	1559.4	1558.4	1558.0	1558.0	1558.1	1558.1	1558.2	1559.1	1559.9
160°	1580.4	1578.7	1577.1	1575.5	1574.8	1575.1	1575.3	1575.6	1575.9	1577.0	1578.0
162.5°	1596.1	1594.5	1592.8	1591.1	1590.5	1590.7	1591.1	1591.3	1591.5	1593.1	1594.6
165°	1617.2	1615.5	1613.9	1612.3	1611.6	1611.8	1612.2	1612.4	1612.7	1614.3	1615.9
167.5°	1632.9	1631.2	1629.5	1627.7	1627.1	1627.3	1627.6	1627.9	1628.2	1630.1	1632.1
170°	1641.4	1639.6	1637.6	1635.7	1634.9	1635.2	1635.5	1635.7	1636.0	1638.2	1640.4
172.5°	1647.4	1645.4	1643.6	1641.6	1641.0	1641.4	1641.9	1642.4	1642.9	1644.9	1646.8
175°	1654.0	1652.4	1650.7	1649.1	1648.5	1648.7	1648.9	1649.3	1649.5	1651.7	1653.8
177.5°	1657.3	1656.0	1654.6	1653.3	1652.8	1653.0	1653.3	1653.4	1653.7	1655.2	1656.8
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1043.1	1045.9	1051.6	1049.5	1052.3	1053.6	1055.0
5°	1127.4	1140.9	1146.9	1146.0	1154.9	1152.8	1150.6
7.5°	1222.5	1236.8	1244.7	1254.7	1260.4	1260.8	1265.8
10°	1276.4	1295.0	1302.7	1313.2	1320.0	1323.8	1323.4
12.5°	1317.7	1332.3	1349.4	1354.5	1363.7	1368.5	1366.8
15°	1367.4	1390.7	1408.5	1417.4	1428.8	1432.2	1436.9
17.5°	1411.8	1443.0	1463.8	1491.3	1501.8	1508.1	1504.4
20°	1445.3	1486.4	1507.2	1540.2	1558.4	1568.1	1564.7
22.5°	1484.9	1529.4	1567.7	1596.4	1624.1	1637.2	1639.9
25°	1552.8	1613.8	1670.1	1707.8	1742.1	1750.1	1767.9
27.5°	1628.7	1700.6	1760.8	1800.4	1824.3	1833.3	1838.8
30°	1676.5	1748.0	1793.3	1818.7	1826.4	1825.5	1824.6
32.5°	1699.8	1744.7	1753.3	1746.2	1728.8	1714.1	1698.7
35°	1666.7	1633.3	1583.3	1519.0	1471.5	1423.8	1419.0
37.5°	1499.0	1392.0	1308.9	1216.0	1162.5	1129.4	1106.4
40°	1341.2	1219.7	1118.9	1040.6	985.9	964.4	943.2
42.5°	1169.8	1053.7	964.5	899.0	857.9	834.0	817.3
45°	950.4	848.0	778.1	730.7	698.1	679.5	668.9
47.5°	778.8	703.0	643.7	609.4	586.9	572.4	572.5
50°	686.6	614.2	574.9	547.8	528.3	516.9	519.0
52.5°	605.0	551.0	517.3	494.6	480.2	473.2	473.0
55°	505.9	466.9	444.9	428.4	418.7	410.7	412.4
57.5°	432.8	399.9	385.1	371.5	364.7	361.4	356.8
60°	387.3	362.0	349.3	338.3	331.5	329.0	324.2
62.5°	347.1	327.1	314.7	305.7	299.6	298.8	295.1
65°	291.7	276.5	265.5	261.2	254.9	253.2	253.2
67.5°	240.4	229.5	221.0	217.1	214.3	214.7	212.7
70°	208.3	199.4	193.9	189.6	187.5	187.9	186.3
72.5°	182.2	172.3	167.5	164.9	162.2	163.2	162.6
75°	138.0	132.9	130.4	127.8	126.1	125.3	124.5
77.5°	101.3	96.9	94.9	93.5	93.8	91.7	93.3
80°	78.4	74.5	73.2	71.1	70.7	70.7	70.3
82.5°	57.3	55.2	54.3	52.5	51.8	52.4	51.3
85°	29.6	28.0	27.6	27.6	26.7	25.8	28.0
87.5°	15.6	14.5	14.8	14.5	14.7	14.5	14.0
90°	23.7	25.1	26.2	27.0	27.8	28.6	29.4
92.5°	23.7	25.1	25.9	26.3	26.7	27.1	27.5
95°	23.7	25.1	25.8	25.8	25.8	25.8	25.8
97.5°	37.3	29.6	25.8	25.8	25.8	25.8	25.8
100°	91.6	51.0	30.2	29.0	28.0	26.9	25.8
102.5°	249.4	241.7	228.6	210.0	191.5	172.9	154.4
105°	365.7	365.7	365.6	365.3	365.1	364.8	364.5
107.5°	463.1	463.2	462.8	461.9	461.1	460.3	459.5
110°	525.3	524.5	524.2	524.5	524.7	525.1	525.3



TEST NUMBER: P333424-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	587.5	586.4	585.7	585.4	585.0	584.6	584.2
115°	681.6	680.4	679.1	677.5	675.8	674.2	672.5
117.5°	772.2	770.7	769.6	769.0	768.3	767.5	766.8
120°	831.7	831.2	830.2	828.8	827.4	826.1	824.8
122.5°	887.7	887.1	886.1	884.5	882.9	881.3	879.7
125°	968.7	967.7	966.7	965.9	965.1	964.3	963.4
127.5°	1043.9	1043.3	1042.0	1039.9	1038.0	1035.9	1033.9
130°	1092.3	1091.5	1090.4	1089.1	1087.7	1086.3	1084.9
132.5°	1138.5	1138.3	1137.5	1136.2	1134.8	1133.4	1132.0
135°	1204.8	1204.3	1203.1	1201.5	1199.9	1198.2	1196.6
137.5°	1267.6	1267.8	1267.1	1265.7	1264.3	1262.8	1261.4
140°	1306.3	1306.8	1306.3	1304.6	1303.0	1301.4	1299.8
142.5°	1343.3	1343.4	1342.6	1340.9	1339.3	1337.7	1336.0
145°	1396.3	1396.5	1395.9	1394.2	1392.6	1391.0	1389.4
147.5°	1441.6	1441.9	1441.1	1439.2	1437.2	1435.3	1433.3
150°	1470.7	1471.3	1470.5	1468.3	1466.1	1464.0	1461.8
152.5°	1496.2	1496.8	1496.1	1494.1	1492.2	1490.2	1488.2
155°	1531.7	1532.5	1531.8	1529.7	1527.5	1525.3	1523.1
157.5°	1560.8	1561.7	1561.1	1558.9	1556.7	1554.4	1552.3
160°	1579.2	1580.2	1579.7	1577.5	1575.3	1573.1	1571.0
162.5°	1596.2	1597.7	1597.3	1594.9	1592.4	1590.1	1587.6
165°	1617.6	1619.3	1618.9	1616.8	1614.6	1612.4	1610.2
167.5°	1634.0	1636.0	1635.7	1633.3	1630.8	1628.4	1626.0
170°	1642.6	1644.7	1644.6	1642.2	1639.7	1637.2	1634.8
172.5°	1648.8	1650.7	1650.5	1648.0	1645.6	1643.2	1640.7
175°	1656.0	1658.2	1658.1	1655.6	1653.2	1650.7	1648.3
177.5°	1658.2	1659.8	1659.7	1657.9	1656.2	1654.4	1652.7
180°	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6	1655.6

(END OF REPORT)