

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333425-930

Luminaire Tested: **S125DIW-S850D1560U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333425-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1560U930-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7226.9 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	35	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	26	25	21
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6442	6442	6442	6442
5°	7459	6463	5659	6463
10°	8679	6430	4958	6430
15°	9607	6383	4574	6383
20°	10754	6308	4265	6308
25°	12598	6223	4115	6223
30°	13607	6141	3985	6141
35°	11188	5984	3899	5984
40°	7952	5767	3805	5767
45°	6109	5476	3751	5476
50°	5215	5112	3743	5112
55°	4644	4757	3775	4757
60°	4188	4370	3871	4370
65°	3869	3978	3972	3978
70°	3518	3573	4030	3573
75°	3107	3147	3992	3147
80°	2615	2566	3652	2566
85°	2075	1845	2949	1845



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	1.3
10°-20°	285.9	4.0
20°-30°	464.2	6.4
30°-40°	566.3	7.8
40°-50°	515.1	7.1
50°-60°	410.3	5.7
60°-70°	285.8	4.0
70°-80°	152.4	2.1
80°-90°	41.9	0.6
90°-100°	105.8	1.5
100°-110°	312.5	4.3
110°-120°	529.3	7.3
120°-130°	696.6	9.6
130°-140°	780.6	10.8
140°-150°	765.0	10.6
150°-160°	642.6	8.9
160°-170°	427.1	5.9
170°-180°	149.5	2.1
0°-30°	846.1	11.7
0°-40°	1412.4	19.5
0°-60°	2337.8	32.3
0°-90°	2817.9	39.0
90°-120°	947.6	13.1
90°-150°	3189.8	44.1
90°-180°	4409.0	61.0
0°-180°	7226.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1151	997	873	997	1151	116
15°	1437	955	684	955	1437	411
25°	1768	873	578	873	1768	807
35°	1419	759	494	759	1419	868
45°	669	600	411	600	669	535
55°	412	422	335	422	412	371
65°	253	260	260	260	253	251
75°	124	126	160	126	124	134
85°	28	25	40	25	28	33
90°	30	1	30	1	30	18
95°	106	80	106	80	106	108
105°	305	280	305	280	305	323
115°	535	530	535	530	535	529
125°	778	773	778	773	778	695
135°	1010	1006	1010	1006	1010	779
145°	1223	1218	1223	1218	1223	764
155°	1394	1394	1394	1394	1394	642
165°	1512	1516	1512	1516	1512	426
175°	1570	1576	1570	1576	1570	149
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1055.0	1053.6	1052.3	1049.5	1051.6	1045.9	1043.1	1038.4	1032.7	1030.6	1028.3
5°	1150.6	1152.8	1154.9	1146.0	1146.9	1140.9	1127.4	1116.4	1107.5	1096.1	1088.0
7.5°	1265.8	1260.8	1260.4	1254.7	1244.7	1236.8	1222.5	1204.4	1186.9	1166.9	1150.4
10°	1323.4	1323.8	1320.0	1313.2	1302.7	1295.0	1276.4	1258.6	1237.1	1211.6	1193.4
12.5°	1366.8	1368.5	1363.7	1354.5	1349.4	1332.3	1317.7	1296.6	1270.9	1250.6	1222.9
15°	1436.9	1432.2	1428.8	1417.4	1408.5	1390.7	1367.4	1345.4	1317.4	1291.6	1265.8
17.5°	1504.4	1508.1	1501.8	1491.3	1463.8	1443.0	1411.8	1381.6	1346.9	1312.2	1281.4
20°	1564.7	1568.1	1558.4	1540.2	1507.2	1486.4	1445.3	1406.4	1366.1	1321.7	1287.8
22.5°	1639.9	1637.2	1624.1	1596.4	1567.7	1529.4	1484.9	1437.5	1387.2	1336.9	1291.9
25°	1767.9	1750.1	1742.1	1707.8	1670.1	1613.8	1552.8	1483.4	1420.7	1354.3	1296.7
27.5°	1838.8	1833.3	1824.3	1800.4	1760.8	1700.6	1628.7	1544.1	1455.7	1371.8	1296.5
30°	1824.6	1825.5	1826.4	1818.7	1793.3	1748.0	1676.5	1585.4	1480.4	1386.0	1298.9
32.5°	1698.7	1714.1	1728.8	1746.2	1753.3	1744.7	1699.8	1617.6	1509.6	1402.3	1297.5
35°	1419.0	1423.8	1471.5	1519.0	1583.3	1633.3	1666.7	1630.4	1539.3	1416.1	1295.8
37.5°	1106.4	1129.4	1162.5	1216.0	1308.9	1392.0	1499.0	1548.2	1518.8	1420.6	1292.9
40°	943.2	964.4	985.9	1040.6	1118.9	1219.7	1341.2	1444.9	1469.0	1406.4	1282.7
42.5°	817.3	834.0	857.9	899.0	964.5	1053.7	1169.8	1305.4	1388.8	1365.1	1261.4
45°	668.9	679.5	698.1	730.7	778.1	848.0	950.4	1098.6	1227.7	1270.5	1210.8
47.5°	572.5	572.4	586.9	609.4	643.7	703.0	778.8	894.9	1032.8	1134.8	1130.1
50°	519.0	516.9	528.3	547.8	574.9	614.2	686.6	779.3	911.9	1027.4	1059.6
52.5°	473.0	473.2	480.2	494.6	517.3	551.0	605.0	688.6	801.8	920.5	981.0
55°	412.4	410.7	418.7	428.4	444.9	466.9	505.9	569.8	661.7	778.5	857.3
57.5°	356.8	361.4	364.7	371.5	385.1	399.9	432.8	479.6	552.5	652.8	736.1
60°	324.2	329.0	331.5	338.3	349.3	362.0	387.3	425.5	486.8	573.2	655.7
62.5°	295.1	298.8	299.6	305.7	314.7	327.1	347.1	379.0	427.5	503.1	584.0
65°	253.2	253.2	254.9	261.2	265.5	276.5	291.7	315.0	353.9	412.8	481.8
67.5°	212.7	214.7	214.3	217.1	221.0	229.5	240.4	259.7	288.5	331.5	386.7
70°	186.3	187.9	187.5	189.6	193.9	199.4	208.3	226.5	247.2	284.1	331.5
72.5°	162.6	163.2	162.2	164.9	167.5	172.3	182.2	191.9	211.3	242.4	281.4
75°	124.5	125.3	126.1	127.8	130.4	132.9	138.0	147.7	160.5	183.8	208.7
77.5°	93.3	91.7	93.8	93.5	94.9	96.9	101.3	106.5	116.9	131.7	151.0
80°	70.3	70.7	70.7	71.1	73.2	74.5	78.4	82.1	90.2	101.2	114.7
82.5°	51.3	52.4	51.8	52.5	54.3	55.2	57.3	60.4	65.1	73.8	83.6
85°	28.0	25.8	26.7	27.6	27.6	28.0	29.6	30.9	33.4	36.9	40.6
87.5°	14.0	14.5	14.8	14.6	14.8	14.5	15.6	15.3	16.1	16.8	17.8
90°	29.5	28.7	27.9	27.1	26.3	25.1	23.8	22.4	21.0	19.6	17.8
92.5°	58.0	57.4	56.8	56.3	55.6	54.5	52.6	50.8	49.0	47.2	44.8
95°	105.7	105.2	104.7	104.1	103.5	102.3	100.4	98.5	96.6	94.7	92.0
97.5°	160.4	160.0	159.7	159.4	159.1	157.9	156.1	154.3	152.5	150.7	147.0
100°	201.6	201.1	200.6	200.0	199.5	198.0	195.5	193.1	190.6	188.1	184.6
102.5°	243.0	242.2	241.4	240.7	239.9	238.1	235.5	232.8	230.2	227.5	225.7
105°	304.9	304.1	303.3	302.5	301.7	300.4	298.8	297.2	295.5	293.9	292.2
107.5°	368.4	368.4	368.5	368.5	368.6	368.2	367.4	366.6	365.7	364.9	363.7
110°	415.6	415.9	416.1	416.5	416.7	416.5	415.6	414.8	413.9	413.1	412.3



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.9	462.4	462.8	463.3	463.8	463.8	463.5	463.1	462.7	462.4	461.3
115°	534.9	535.2	535.4	535.7	536.0	536.2	536.5	536.8	537.0	537.4	536.8
117.5°	606.2	607.3	608.4	609.4	610.6	611.0	610.8	610.6	610.3	610.2	609.6
120°	655.4	656.5	657.5	658.7	659.7	660.3	660.3	660.3	660.3	660.3	660.0
122.5°	704.6	705.4	706.3	707.2	708.1	708.6	708.8	709.1	709.2	709.5	708.7
125°	778.4	778.6	778.9	779.2	779.4	779.8	780.4	781.0	781.5	782.0	781.8
127.5°	849.1	849.7	850.3	850.8	851.3	851.7	852.1	852.3	852.6	852.9	852.6
130°	896.4	896.9	897.5	898.1	898.5	898.9	899.3	899.5	899.8	900.1	899.5
132.5°	940.6	941.4	942.2	943.0	943.7	944.2	944.5	944.8	945.0	945.3	945.4
135°	1009.5	1010.6	1011.7	1012.8	1013.9	1014.4	1014.4	1014.4	1014.4	1014.4	1014.2
137.5°	1076.8	1078.2	1079.6	1081.0	1082.4	1082.9	1082.6	1082.2	1081.9	1081.6	1080.9
140°	1120.1	1121.5	1122.9	1124.3	1125.6	1126.0	1125.5	1124.9	1124.4	1123.9	1123.1
142.5°	1161.5	1162.9	1164.2	1165.6	1166.9	1167.5	1167.1	1166.8	1166.4	1166.1	1165.1
145°	1223.4	1224.3	1225.1	1225.9	1226.7	1227.1	1227.1	1227.1	1227.1	1227.1	1226.3
147.5°	1276.4	1278.2	1280.0	1281.9	1283.8	1284.3	1283.7	1283.0	1282.4	1281.7	1281.1
150°	1315.6	1316.2	1316.8	1317.3	1317.8	1318.2	1318.2	1318.2	1318.2	1318.2	1317.0
152.5°	1348.2	1349.2	1350.1	1351.1	1352.1	1352.3	1351.6	1351.0	1350.3	1349.6	1349.2
155°	1394.4	1395.7	1397.1	1398.5	1399.9	1400.0	1398.9	1397.7	1396.7	1395.6	1395.3
157.5°	1433.0	1434.8	1436.6	1438.4	1440.2	1440.6	1439.5	1438.4	1437.3	1436.1	1435.9
160°	1459.5	1460.9	1462.2	1463.6	1465.0	1465.2	1464.0	1463.0	1461.8	1460.8	1460.5
162.5°	1482.1	1483.8	1485.3	1486.9	1488.5	1488.7	1487.4	1486.0	1484.7	1483.4	1483.4
165°	1512.4	1514.1	1515.7	1517.4	1519.0	1519.2	1518.2	1517.0	1516.0	1514.9	1514.6
167.5°	1536.5	1538.2	1539.9	1541.6	1543.3	1543.3	1541.6	1540.0	1538.4	1536.8	1536.8
170°	1549.3	1551.2	1553.1	1555.0	1557.0	1557.1	1555.4	1553.8	1552.2	1550.5	1550.5
172.5°	1560.2	1561.8	1563.5	1565.2	1566.9	1566.9	1565.3	1563.7	1562.0	1560.4	1560.4
175°	1570.2	1572.1	1574.0	1576.0	1577.8	1578.0	1576.4	1574.8	1573.0	1571.4	1571.4
177.5°	1576.1	1577.6	1579.2	1580.7	1582.3	1582.3	1581.0	1579.7	1578.4	1577.1	1577.3
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1026.2	1023.9	1021.1	1016.4	1010.6	1007.5	1002.8	999.8	993.7	988.6	983.2
5°	1078.2	1067.2	1057.1	1044.0	1029.6	1020.3	1009.3	996.9	984.3	971.2	956.8
7.5°	1132.2	1112.7	1091.5	1068.8	1046.5	1026.1	1006.5	987.2	969.3	947.6	929.3
10°	1168.4	1143.9	1117.6	1086.7	1056.7	1030.5	1003.8	980.5	956.8	931.4	908.9
12.5°	1204.7	1172.0	1134.9	1101.0	1064.8	1033.1	1001.8	972.0	942.2	914.1	887.9
15°	1230.3	1201.4	1167.2	1118.9	1078.2	1034.7	993.2	954.6	918.7	887.4	854.4
17.5°	1247.1	1210.0	1173.2	1126.9	1073.6	1024.8	977.9	933.8	893.2	853.5	821.7
20°	1250.2	1212.0	1173.5	1128.2	1073.6	1017.7	970.8	917.8	874.2	833.2	794.2
22.5°	1249.1	1206.0	1164.0	1117.4	1064.1	1012.7	955.9	901.9	854.6	814.2	773.6
25°	1239.6	1193.4	1140.9	1094.0	1041.5	986.8	929.3	873.3	825.1	778.9	738.7
27.5°	1231.6	1171.7	1112.3	1057.5	1006.8	956.8	901.6	844.4	790.9	744.1	706.2
30°	1221.8	1156.2	1089.2	1032.1	980.1	931.4	879.3	823.5	767.5	721.8	681.2
32.5°	1213.0	1136.5	1065.9	1003.7	948.5	901.2	853.2	800.1	745.2	698.8	658.1
35°	1196.0	1107.5	1026.6	956.3	897.5	848.8	808.6	759.0	708.7	663.8	624.8
37.5°	1174.4	1069.3	982.6	908.9	844.4	793.1	755.7	717.6	669.3	626.1	590.8
40°	1157.4	1042.3	950.4	875.1	808.2	754.8	720.2	684.1	643.9	603.7	566.5
42.5°	1136.1	1017.9	917.9	836.8	770.5	718.6	682.2	651.6	616.1	578.6	544.0
45°	1096.9	973.7	865.4	778.1	711.2	660.0	622.3	599.5	572.8	537.2	508.0
47.5°	1039.3	920.6	808.5	718.5	649.5	602.0	566.7	544.8	525.9	499.5	473.0
50°	988.1	881.0	767.5	678.2	609.2	561.3	528.8	508.8	492.8	472.5	450.0
52.5°	930.8	831.2	727.2	639.0	570.6	523.4	491.5	474.0	460.6	446.1	424.0
55°	839.9	755.3	658.8	574.9	511.8	465.7	437.7	422.5	411.5	400.5	386.9
57.5°	739.7	673.5	588.0	511.4	453.3	411.3	385.2	370.4	361.9	356.2	348.2
60°	669.3	612.6	538.9	469.0	412.4	375.1	349.7	338.3	331.1	326.4	320.5
62.5°	604.0	557.4	489.1	425.3	375.8	340.6	317.9	306.8	299.9	297.6	292.7
65°	507.6	471.7	415.3	362.4	320.1	290.0	270.9	260.3	256.1	253.6	254.0
67.5°	412.7	390.8	345.5	300.4	266.6	241.4	226.2	218.0	215.9	212.5	212.5
70°	354.7	338.3	300.2	260.8	230.7	211.2	197.7	189.2	187.1	185.4	185.0
72.5°	303.6	289.2	256.1	224.5	197.5	180.4	169.3	164.2	160.7	159.7	159.6
75°	228.2	220.1	193.9	168.9	150.3	138.4	130.9	126.1	123.6	123.2	123.6
77.5°	162.2	155.2	138.5	120.8	109.1	100.1	93.7	92.0	89.2	89.3	88.8
80°	121.9	117.2	106.7	92.7	83.0	75.3	72.0	69.0	68.2	66.9	68.2
82.5°	88.4	83.4	76.2	67.3	59.3	54.7	51.3	50.4	49.9	49.2	49.6
85°	43.6	44.0	39.8	33.0	29.6	27.1	24.9	24.9	24.5	24.1	24.5
87.5°	18.1	17.0	15.2	13.9	11.7	10.3	9.5	9.4	8.8	8.9	9.7
90°	15.8	13.9	12.0	9.9	7.8	5.6	3.4	1.2	3.4	5.6	7.8
92.5°	42.5	40.2	37.8	35.9	34.3	32.9	31.3	29.8	31.3	32.9	34.3
95°	89.2	86.5	83.7	82.1	81.5	81.0	80.5	79.9	80.5	81.0	81.5
97.5°	143.2	139.4	135.7	133.7	133.5	133.2	133.0	132.8	133.0	133.2	133.5
100°	181.0	177.5	173.9	172.1	172.1	172.1	172.1	172.1	172.1	172.1	172.1
102.5°	223.9	222.1	220.3	218.8	217.7	216.6	215.6	214.4	215.6	216.6	217.7
105°	290.6	288.9	287.3	285.8	284.5	283.1	281.7	280.4	281.7	283.1	284.5
107.5°	362.4	361.2	360.0	358.6	357.3	355.9	354.5	353.1	354.5	355.9	357.3
110°	411.5	410.7	409.9	408.8	407.4	406.0	404.7	403.3	404.7	406.0	407.4





TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	460.2	459.2	458.2	457.3	456.6	455.9	455.2	454.4	455.2	455.9	456.6
115°	536.2	535.7	535.2	534.3	533.2	532.1	531.1	529.9	531.1	532.1	533.2
117.5°	609.1	608.6	608.1	607.6	607.2	606.7	606.2	605.7	606.2	606.7	607.2
120°	659.7	659.5	659.2	658.4	657.0	655.7	654.3	652.9	654.3	655.7	657.0
122.5°	708.1	707.4	706.6	706.0	705.6	705.1	704.6	704.1	704.6	705.1	705.6
125°	781.5	781.2	781.0	780.0	778.4	776.7	775.0	773.4	775.0	776.7	778.4
127.5°	852.2	851.9	851.6	850.9	849.9	849.1	848.2	847.2	848.2	849.1	849.9
130°	898.9	898.5	897.9	896.9	895.5	894.2	892.8	891.4	892.8	894.2	895.5
132.5°	945.5	945.7	945.7	944.7	942.5	940.2	938.0	935.7	938.0	940.2	942.5
135°	1013.9	1013.6	1013.3	1012.4	1010.7	1009.1	1007.5	1005.8	1007.5	1009.1	1010.7
137.5°	1080.4	1079.8	1079.1	1078.1	1076.4	1074.9	1073.3	1071.7	1073.3	1074.9	1076.4
140°	1122.3	1121.4	1120.5	1119.5	1118.1	1116.7	1115.4	1114.0	1115.4	1116.7	1118.1
142.5°	1164.1	1163.0	1162.0	1160.9	1159.8	1158.6	1157.5	1156.3	1157.5	1158.6	1159.8
145°	1225.5	1224.7	1223.8	1222.9	1221.8	1220.7	1219.6	1218.5	1219.6	1220.7	1221.8
147.5°	1280.4	1279.8	1279.1	1278.5	1277.9	1277.2	1276.7	1276.1	1276.7	1277.2	1277.9
150°	1316.0	1314.8	1313.8	1313.4	1313.6	1313.9	1314.2	1314.4	1314.2	1313.9	1313.6
152.5°	1348.7	1348.3	1347.9	1347.4	1347.0	1346.7	1346.3	1345.9	1346.3	1346.7	1347.0
155°	1395.1	1394.8	1394.5	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4
157.5°	1435.7	1435.3	1435.1	1435.3	1435.8	1436.5	1437.0	1437.6	1437.0	1436.5	1435.8
160°	1460.2	1460.0	1459.7	1460.0	1460.8	1461.6	1462.4	1463.2	1462.4	1461.6	1460.8
162.5°	1483.3	1483.2	1483.2	1483.4	1484.1	1484.7	1485.2	1485.9	1485.2	1484.7	1484.1
165°	1514.3	1514.1	1513.8	1513.9	1514.5	1515.0	1515.6	1516.1	1515.6	1515.0	1514.5
167.5°	1536.8	1536.8	1536.8	1537.3	1538.4	1539.5	1540.6	1541.6	1540.6	1539.5	1538.4
170°	1550.5	1550.5	1550.5	1551.1	1552.2	1553.2	1554.4	1555.4	1554.4	1553.2	1552.2
172.5°	1560.4	1560.4	1560.4	1560.9	1562.0	1563.1	1564.2	1565.3	1564.2	1563.1	1562.0
175°	1571.4	1571.4	1571.4	1572.0	1573.0	1574.2	1575.2	1576.4	1575.2	1574.2	1573.0
177.5°	1577.5	1577.8	1577.9	1578.5	1579.4	1580.3	1581.1	1582.0	1581.1	1580.3	1579.4
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	980.2	976.4	973.4	966.6	962.9	957.8	953.7	958.1	953.4	955.4	952.4
5°	949.6	937.8	929.3	917.0	906.4	896.7	889.5	888.2	884.8	883.1	878.0
7.5°	912.8	898.0	883.5	867.4	853.8	840.0	831.2	823.9	819.1	812.8	808.5
10°	891.1	871.2	854.4	834.9	817.9	803.1	791.2	785.3	779.8	771.8	768.8
12.5°	864.4	843.8	823.1	802.3	786.1	769.6	759.4	750.4	746.7	737.5	736.6
15°	832.3	801.4	781.1	759.9	737.4	723.9	715.4	705.7	701.5	695.1	690.5
17.5°	794.0	766.5	741.0	719.1	699.9	688.4	677.9	671.2	664.0	659.8	652.2
20°	766.3	740.0	714.6	691.3	676.5	663.4	654.9	648.6	641.0	638.9	631.2
22.5°	742.9	714.0	689.6	670.0	653.8	639.0	629.8	625.6	620.3	613.8	612.2
25°	704.9	674.8	654.1	634.6	620.2	606.7	600.3	594.8	589.7	585.1	583.3
27.5°	672.1	645.1	620.5	602.9	590.4	578.0	572.4	565.7	562.1	558.3	553.8
30°	649.0	621.5	599.9	582.9	569.4	558.4	552.4	547.8	544.5	541.0	538.5
32.5°	625.3	599.8	578.9	562.3	548.8	540.5	535.2	531.9	528.2	524.1	520.9
35°	593.9	566.0	545.7	531.3	520.7	514.4	508.4	505.5	501.2	501.2	497.8
37.5°	558.6	534.5	516.6	503.4	494.0	488.3	481.8	479.8	477.1	475.3	474.2
40°	537.7	515.2	498.3	485.2	475.0	470.3	465.3	461.9	460.2	458.0	457.2
42.5°	516.0	494.6	478.3	466.2	457.4	453.4	448.7	446.3	442.9	440.1	439.6
45°	483.1	462.3	447.5	437.7	430.2	425.5	422.5	417.4	415.7	412.4	411.9
47.5°	451.8	431.9	417.4	409.4	402.7	398.8	394.2	389.1	387.2	385.5	385.3
50°	428.4	410.3	396.6	389.1	382.7	377.2	372.5	369.2	367.9	367.9	368.8
52.5°	404.7	389.2	377.7	368.4	362.4	356.5	352.2	350.2	348.2	350.3	351.8
55°	370.0	354.3	345.8	337.0	331.1	324.2	322.2	321.3	320.1	323.4	325.1
57.5°	333.3	322.3	312.3	303.5	298.2	294.3	291.5	290.9	293.3	294.9	300.4
60°	309.9	297.2	288.3	281.5	275.2	272.6	271.8	270.9	272.6	277.3	284.5
62.5°	284.1	273.9	264.2	259.2	254.5	250.3	250.1	250.6	254.0	259.3	266.5
65°	246.4	237.5	231.1	225.2	221.4	218.9	219.7	221.4	225.2	232.4	240.4
67.5°	208.1	201.9	196.2	191.4	187.8	187.8	188.7	191.2	195.7	204.0	211.3
70°	183.3	176.5	171.9	169.7	166.8	165.1	167.6	171.9	175.7	183.3	189.6
72.5°	158.6	152.9	149.2	147.7	146.5	145.1	145.9	150.5	155.7	163.3	170.7
75°	121.9	119.8	117.2	115.6	114.3	115.1	116.0	120.3	124.5	132.5	141.0
77.5°	88.9	86.7	85.3	84.9	84.1	84.5	87.0	90.1	94.2	100.1	106.5
80°	67.3	66.4	65.6	65.2	65.2	65.6	69.0	71.1	74.9	80.5	85.5
82.5°	49.0	48.5	48.3	48.3	48.6	48.7	50.7	53.5	56.7	60.8	65.2
85°	25.8	24.9	26.3	26.7	25.8	27.1	28.0	29.6	30.9	33.0	35.1
87.5°	10.4	11.6	11.6	12.3	12.7	13.8	13.7	15.3	16.3	17.2	17.1
90°	9.9	12.0	13.9	15.8	17.8	19.6	21.0	22.4	23.8	25.1	26.3
92.5°	35.9	37.8	40.2	42.5	44.8	47.2	49.0	50.8	52.6	54.5	55.6
95°	82.1	83.7	86.5	89.2	92.0	94.7	96.6	98.5	100.4	102.3	103.5
97.5°	133.7	135.7	139.4	143.2	147.0	150.7	152.5	154.3	156.1	157.9	159.1
100°	172.1	173.9	177.5	181.0	184.6	188.1	190.6	193.1	195.5	198.0	199.5
102.5°	218.8	220.3	222.1	223.9	225.7	227.5	230.2	232.8	235.5	238.1	239.9
105°	285.8	287.3	288.9	290.6	292.2	293.9	295.5	297.2	298.8	300.4	301.7
107.5°	358.6	360.0	361.2	362.4	363.7	364.9	365.7	366.6	367.4	368.2	368.6
110°	408.8	409.9	410.7	411.5	412.3	413.1	413.9	414.8	415.6	416.5	416.7



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	457.3	458.2	459.2	460.2	461.3	462.4	462.7	463.1	463.5	463.8	463.8
115°	534.3	535.2	535.7	536.2	536.8	537.4	537.0	536.8	536.5	536.2	536.0
117.5°	607.6	608.1	608.6	609.1	609.6	610.2	610.3	610.6	610.8	611.0	610.6
120°	658.4	659.2	659.5	659.7	660.0	660.3	660.3	660.3	660.3	660.3	659.7
122.5°	706.0	706.6	707.4	708.1	708.7	709.5	709.2	709.1	708.8	708.6	708.1
125°	780.0	781.0	781.2	781.5	781.8	782.0	781.5	781.0	780.4	779.8	779.4
127.5°	850.9	851.6	851.9	852.2	852.6	852.9	852.6	852.3	852.1	851.7	851.3
130°	896.9	897.9	898.5	898.9	899.5	900.1	899.8	899.5	899.3	898.9	898.5
132.5°	944.7	945.7	945.7	945.5	945.4	945.3	945.0	944.8	944.5	944.2	943.7
135°	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4	1014.4	1014.4	1014.4	1013.9
137.5°	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9	1082.2	1082.6	1082.9	1082.4
140°	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4	1124.9	1125.5	1126.0	1125.6
142.5°	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4	1166.8	1167.1	1167.5	1166.9
145°	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1	1227.1	1227.1	1227.1	1226.7
147.5°	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4	1283.0	1283.7	1284.3	1283.8
150°	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2	1318.2	1318.2	1318.2	1317.8
152.5°	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3	1351.0	1351.6	1352.3	1352.1
155°	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7	1397.7	1398.9	1400.0	1399.9
157.5°	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3	1438.4	1439.5	1440.6	1440.2
160°	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8	1463.0	1464.0	1465.2	1465.0
162.5°	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7	1486.0	1487.4	1488.7	1488.5
165°	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0	1517.0	1518.2	1519.2	1519.0
167.5°	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4	1540.0	1541.6	1543.3	1543.3
170°	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2	1553.8	1555.4	1557.1	1557.0
172.5°	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0	1563.7	1565.3	1566.9	1566.9
175°	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0	1574.8	1576.4	1578.0	1577.8
177.5°	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4	1579.7	1581.0	1582.3	1582.3
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	950.3	952.7	950.6	953.4	950.6	952.7	950.3	952.4	955.4	953.4	958.1
5°	875.9	872.1	874.7	872.9	874.7	872.1	875.9	878.0	883.1	884.8	888.2
7.5°	807.1	803.5	799.4	797.4	799.4	803.5	807.1	808.5	812.8	819.1	823.9
10°	764.2	759.5	759.0	756.1	759.0	759.5	764.2	768.8	771.8	779.8	785.3
12.5°	732.6	728.3	723.5	722.3	723.5	728.3	732.6	736.6	737.5	746.7	750.4
15°	687.9	684.5	681.6	684.1	681.6	684.5	687.9	690.5	695.1	701.5	705.7
17.5°	650.8	648.0	647.4	644.3	647.4	648.0	650.8	652.2	659.8	664.0	671.2
20°	627.4	625.3	626.1	620.6	626.1	625.3	627.4	631.2	638.9	641.0	648.6
22.5°	608.8	604.6	604.1	603.0	604.1	604.6	608.8	612.2	613.8	620.3	625.6
25°	579.6	577.5	575.4	577.5	575.4	577.5	579.6	583.3	585.1	589.7	594.8
27.5°	554.1	551.5	551.0	551.2	551.0	551.5	554.1	553.8	558.3	562.1	565.7
30°	538.5	534.3	534.7	534.3	534.7	534.3	538.5	538.5	541.0	544.5	547.8
32.5°	521.5	518.7	518.1	517.3	518.1	518.7	521.5	520.9	524.1	528.2	531.9
35°	496.6	496.6	494.5	494.5	494.5	496.6	496.6	497.8	501.2	501.2	505.5
37.5°	473.1	472.7	471.4	471.7	471.4	472.7	473.1	474.2	475.3	477.1	479.8
40°	455.5	455.1	453.8	451.3	453.8	455.1	455.5	457.2	458.0	460.2	461.9
42.5°	438.5	437.2	436.6	435.7	436.6	437.2	438.5	439.6	440.1	442.9	446.3
45°	411.9	411.9	411.1	410.7	411.1	411.9	411.9	411.9	412.4	415.7	417.4
47.5°	386.0	386.8	388.4	388.2	388.4	386.8	386.0	385.3	385.5	387.2	389.1
50°	370.4	370.9	372.1	372.5	372.1	370.9	370.4	368.8	367.9	367.9	369.2
52.5°	353.2	355.6	357.2	356.9	357.2	355.6	353.2	351.8	350.3	348.2	350.2
55°	329.0	331.9	334.8	335.3	334.8	331.9	329.0	325.1	323.4	320.1	321.3
57.5°	305.0	309.2	312.3	313.2	312.3	309.2	305.0	300.4	294.9	293.3	290.9
60°	288.7	294.2	298.1	299.7	298.1	294.2	288.7	284.5	277.3	272.6	270.9
62.5°	273.1	279.3	283.2	283.5	283.2	279.3	273.1	266.5	259.3	254.0	250.6
65°	247.7	254.0	257.4	259.9	257.4	254.0	247.7	240.4	232.4	225.2	221.4
67.5°	220.2	226.6	230.3	232.4	230.3	226.6	220.2	211.3	204.0	195.7	191.2
70°	200.2	206.6	211.7	213.4	211.7	206.6	200.2	189.6	183.3	175.7	171.9
72.5°	180.6	186.3	190.4	192.3	190.4	186.3	180.6	170.7	163.3	155.7	150.5
75°	146.5	154.1	157.9	160.0	157.9	154.1	146.5	141.0	132.5	124.5	120.3
77.5°	112.9	119.9	122.2	123.3	122.2	119.9	112.9	106.5	100.1	94.2	90.1
80°	90.6	94.8	97.8	98.2	97.8	94.8	90.6	85.5	80.5	74.9	71.1
82.5°	69.6	73.1	74.1	75.2	74.1	73.1	69.6	65.2	60.8	56.7	53.5
85°	38.1	39.8	40.2	39.8	40.2	39.8	38.1	35.1	33.0	30.9	29.6
87.5°	17.9	17.8	17.9	18.8	17.9	17.8	17.9	17.1	17.2	16.3	15.3
90°	27.1	27.9	28.7	29.5	28.7	27.9	27.1	26.3	25.1	23.8	22.4
92.5°	56.3	56.8	57.4	58.0	57.4	56.8	56.3	55.6	54.5	52.6	50.8
95°	104.1	104.7	105.2	105.7	105.2	104.7	104.1	103.5	102.3	100.4	98.5
97.5°	159.4	159.7	160.0	160.4	160.0	159.7	159.4	159.1	157.9	156.1	154.3
100°	200.0	200.6	201.1	201.6	201.1	200.6	200.0	199.5	198.0	195.5	193.1
102.5°	240.7	241.4	242.2	243.0	242.2	241.4	240.7	239.9	238.1	235.5	232.8
105°	302.5	303.3	304.1	304.9	304.1	303.3	302.5	301.7	300.4	298.8	297.2
107.5°	368.5	368.5	368.4	368.4	368.4	368.5	368.5	368.6	368.2	367.4	366.6
110°	416.5	416.1	415.9	415.6	415.9	416.1	416.5	416.7	416.5	415.6	414.8



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	463.3	462.8	462.4	461.9	462.4	462.8	463.3	463.8	463.8	463.5	463.1
115°	535.7	535.4	535.2	534.9	535.2	535.4	535.7	536.0	536.2	536.5	536.8
117.5°	609.4	608.4	607.3	606.2	607.3	608.4	609.4	610.6	611.0	610.8	610.6
120°	658.7	657.5	656.5	655.4	656.5	657.5	658.7	659.7	660.3	660.3	660.3
122.5°	707.2	706.3	705.4	704.6	705.4	706.3	707.2	708.1	708.6	708.8	709.1
125°	779.2	778.9	778.6	778.4	778.6	778.9	779.2	779.4	779.8	780.4	781.0
127.5°	850.8	850.3	849.7	849.1	849.7	850.3	850.8	851.3	851.7	852.1	852.3
130°	898.1	897.5	896.9	896.4	896.9	897.5	898.1	898.5	898.9	899.3	899.5
132.5°	943.0	942.2	941.4	940.6	941.4	942.2	943.0	943.7	944.2	944.5	944.8
135°	1012.8	1011.7	1010.6	1009.5	1010.6	1011.7	1012.8	1013.9	1014.4	1014.4	1014.4
137.5°	1081.0	1079.6	1078.2	1076.8	1078.2	1079.6	1081.0	1082.4	1082.9	1082.6	1082.2
140°	1124.3	1122.9	1121.5	1120.1	1121.5	1122.9	1124.3	1125.6	1126.0	1125.5	1124.9
142.5°	1165.6	1164.2	1162.9	1161.5	1162.9	1164.2	1165.6	1166.9	1167.5	1167.1	1166.8
145°	1225.9	1225.1	1224.3	1223.4	1224.3	1225.1	1225.9	1226.7	1227.1	1227.1	1227.1
147.5°	1281.9	1280.0	1278.2	1276.4	1278.2	1280.0	1281.9	1283.8	1284.3	1283.7	1283.0
150°	1317.3	1316.8	1316.2	1315.6	1316.2	1316.8	1317.3	1317.8	1318.2	1318.2	1318.2
152.5°	1351.1	1350.1	1349.2	1348.2	1349.2	1350.1	1351.1	1352.1	1352.3	1351.6	1351.0
155°	1398.5	1397.1	1395.7	1394.4	1395.7	1397.1	1398.5	1399.9	1400.0	1398.9	1397.7
157.5°	1438.4	1436.6	1434.8	1433.0	1434.8	1436.6	1438.4	1440.2	1440.6	1439.5	1438.4
160°	1463.6	1462.2	1460.9	1459.5	1460.9	1462.2	1463.6	1465.0	1465.2	1464.0	1463.0
162.5°	1486.9	1485.3	1483.8	1482.1	1483.8	1485.3	1486.9	1488.5	1488.7	1487.4	1486.0
165°	1517.4	1515.7	1514.1	1512.4	1514.1	1515.7	1517.4	1519.0	1519.2	1518.2	1517.0
167.5°	1541.6	1539.9	1538.2	1536.5	1538.2	1539.9	1541.6	1543.3	1543.3	1541.6	1540.0
170°	1555.0	1553.1	1551.2	1549.3	1551.2	1553.1	1555.0	1557.0	1557.1	1555.4	1553.8
172.5°	1565.2	1563.5	1561.8	1560.2	1561.8	1563.5	1565.2	1566.9	1566.9	1565.3	1563.7
175°	1576.0	1574.0	1572.1	1570.2	1572.1	1574.0	1576.0	1577.8	1578.0	1576.4	1574.8
177.5°	1580.7	1579.2	1577.6	1576.1	1577.6	1579.2	1580.7	1582.3	1582.3	1581.0	1579.7
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	953.7	957.8	962.9	966.6	973.4	976.4	980.2	983.2	988.6	993.7	999.8
5°	889.5	896.7	906.4	917.0	929.3	937.8	949.6	956.8	971.2	984.3	996.9
7.5°	831.2	840.0	853.8	867.4	883.5	898.0	912.8	929.3	947.6	969.3	987.2
10°	791.2	803.1	817.9	834.9	854.4	871.2	891.1	908.9	931.4	956.8	980.5
12.5°	759.4	769.6	786.1	802.3	823.1	843.8	864.4	887.9	914.1	942.2	972.0
15°	715.4	723.9	737.4	759.9	781.1	801.4	832.3	854.4	887.4	918.7	954.6
17.5°	677.9	688.4	699.9	719.1	741.0	766.5	794.0	821.7	853.5	893.2	933.8
20°	654.9	663.4	676.5	691.3	714.6	740.0	766.3	794.2	833.2	874.2	917.8
22.5°	629.8	639.0	653.8	670.0	689.6	714.0	742.9	773.6	814.2	854.6	901.9
25°	600.3	606.7	620.2	634.6	654.1	674.8	704.9	738.7	778.9	825.1	873.3
27.5°	572.4	578.0	590.4	602.9	620.5	645.1	672.1	706.2	744.1	790.9	844.4
30°	552.4	558.4	569.4	582.9	599.9	621.5	649.0	681.2	721.8	767.5	823.5
32.5°	535.2	540.5	548.8	562.3	578.9	599.8	625.3	658.1	698.8	745.2	800.1
35°	508.4	514.4	520.7	531.3	545.7	566.0	593.9	624.8	663.8	708.7	759.0
37.5°	481.8	488.3	494.0	503.4	516.6	534.5	558.6	590.8	626.1	669.3	717.6
40°	465.3	470.3	475.0	485.2	498.3	515.2	537.7	566.5	603.7	643.9	684.1
42.5°	448.7	453.4	457.4	466.2	478.3	494.6	516.0	544.0	578.6	616.1	651.6
45°	422.5	425.5	430.2	437.7	447.5	462.3	483.1	508.0	537.2	572.8	599.5
47.5°	394.2	398.8	402.7	409.4	417.4	431.9	451.8	473.0	499.5	525.9	544.8
50°	372.5	377.2	382.7	389.1	396.6	410.3	428.4	450.0	472.5	492.8	508.8
52.5°	352.2	356.5	362.4	368.4	377.7	389.2	404.7	424.0	446.1	460.6	474.0
55°	322.2	324.2	331.1	337.0	345.8	354.3	370.0	386.9	400.5	411.5	422.5
57.5°	291.5	294.3	298.2	303.5	312.3	322.3	333.3	348.2	356.2	361.9	370.4
60°	271.8	272.6	275.2	281.5	288.3	297.2	309.9	320.5	326.4	331.1	338.3
62.5°	250.1	250.3	254.5	259.2	264.2	273.9	284.1	292.7	297.6	299.9	306.8
65°	219.7	218.9	221.4	225.2	231.1	237.5	246.4	254.0	253.6	256.1	260.3
67.5°	188.7	187.8	187.8	191.4	196.2	201.9	208.1	212.5	212.5	215.9	218.0
70°	167.6	165.1	166.8	169.7	171.9	176.5	183.3	185.0	185.4	187.1	189.2
72.5°	145.9	145.1	146.5	147.7	149.2	152.9	158.6	159.6	159.7	160.7	164.2
75°	116.0	115.1	114.3	115.6	117.2	119.8	121.9	123.6	123.2	123.6	126.1
77.5°	87.0	84.5	84.1	84.9	85.3	86.7	88.9	88.8	89.3	89.2	92.0
80°	69.0	65.6	65.2	65.2	65.6	66.4	67.3	68.2	66.9	68.2	69.0
82.5°	50.7	48.7	48.6	48.3	48.3	48.5	49.0	49.6	49.2	49.9	50.4
85°	28.0	27.1	25.8	26.7	26.3	24.9	25.8	24.5	24.1	24.5	24.9
87.5°	13.7	13.8	12.7	12.3	11.6	11.6	10.4	9.7	8.9	8.8	9.4
90°	21.0	19.6	17.8	15.8	13.9	12.0	9.9	7.8	5.6	3.4	1.2
92.5°	49.0	47.2	44.8	42.5	40.2	37.8	35.9	34.3	32.9	31.3	29.8
95°	96.6	94.7	92.0	89.2	86.5	83.7	82.1	81.5	81.0	80.5	79.9
97.5°	152.5	150.7	147.0	143.2	139.4	135.7	133.7	133.5	133.2	133.0	132.8
100°	190.6	188.1	184.6	181.0	177.5	173.9	172.1	172.1	172.1	172.1	172.1
102.5°	230.2	227.5	225.7	223.9	222.1	220.3	218.8	217.7	216.6	215.6	214.4
105°	295.5	293.9	292.2	290.6	288.9	287.3	285.8	284.5	283.1	281.7	280.4
107.5°	365.7	364.9	363.7	362.4	361.2	360.0	358.6	357.3	355.9	354.5	353.1
110°	413.9	413.1	412.3	411.5	410.7	409.9	408.8	407.4	406.0	404.7	403.3



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	462.7	462.4	461.3	460.2	459.2	458.2	457.3	456.6	455.9	455.2	454.4
115°	537.0	537.4	536.8	536.2	535.7	535.2	534.3	533.2	532.1	531.1	529.9
117.5°	610.3	610.2	609.6	609.1	608.6	608.1	607.6	607.2	606.7	606.2	605.7
120°	660.3	660.3	660.0	659.7	659.5	659.2	658.4	657.0	655.7	654.3	652.9
122.5°	709.2	709.5	708.7	708.1	707.4	706.6	706.0	705.6	705.1	704.6	704.1
125°	781.5	782.0	781.8	781.5	781.2	781.0	780.0	778.4	776.7	775.0	773.4
127.5°	852.6	852.9	852.6	852.2	851.9	851.6	850.9	849.9	849.1	848.2	847.2
130°	899.8	900.1	899.5	898.9	898.5	897.9	896.9	895.5	894.2	892.8	891.4
132.5°	945.0	945.3	945.4	945.5	945.7	945.7	944.7	942.5	940.2	938.0	935.7
135°	1014.4	1014.4	1014.2	1013.9	1013.6	1013.3	1012.4	1010.7	1009.1	1007.5	1005.8
137.5°	1081.9	1081.6	1080.9	1080.4	1079.8	1079.1	1078.1	1076.4	1074.9	1073.3	1071.7
140°	1124.4	1123.9	1123.1	1122.3	1121.4	1120.5	1119.5	1118.1	1116.7	1115.4	1114.0
142.5°	1166.4	1166.1	1165.1	1164.1	1163.0	1162.0	1160.9	1159.8	1158.6	1157.5	1156.3
145°	1227.1	1227.1	1226.3	1225.5	1224.7	1223.8	1222.9	1221.8	1220.7	1219.6	1218.5
147.5°	1282.4	1281.7	1281.1	1280.4	1279.8	1279.1	1278.5	1277.9	1277.2	1276.7	1276.1
150°	1318.2	1318.2	1317.0	1316.0	1314.8	1313.8	1313.4	1313.6	1313.9	1314.2	1314.4
152.5°	1350.3	1349.6	1349.2	1348.7	1348.3	1347.9	1347.4	1347.0	1346.7	1346.3	1345.9
155°	1396.7	1395.6	1395.3	1395.1	1394.8	1394.5	1394.4	1394.4	1394.4	1394.4	1394.4
157.5°	1437.3	1436.1	1435.9	1435.7	1435.3	1435.1	1435.3	1435.8	1436.5	1437.0	1437.6
160°	1461.8	1460.8	1460.5	1460.2	1460.0	1459.7	1460.0	1460.8	1461.6	1462.4	1463.2
162.5°	1484.7	1483.4	1483.4	1483.3	1483.2	1483.2	1483.4	1484.1	1484.7	1485.2	1485.9
165°	1516.0	1514.9	1514.6	1514.3	1514.1	1513.8	1513.9	1514.5	1515.0	1515.6	1516.1
167.5°	1538.4	1536.8	1536.8	1536.8	1536.8	1536.8	1537.3	1538.4	1539.5	1540.6	1541.6
170°	1552.2	1550.5	1550.5	1550.5	1550.5	1550.5	1551.1	1552.2	1553.2	1554.4	1555.4
172.5°	1562.0	1560.4	1560.4	1560.4	1560.4	1560.4	1560.9	1562.0	1563.1	1564.2	1565.3
175°	1573.0	1571.4	1571.4	1571.4	1571.4	1571.4	1572.0	1573.0	1574.2	1575.2	1576.4
177.5°	1578.4	1577.1	1577.3	1577.5	1577.8	1577.9	1578.5	1579.4	1580.3	1581.1	1582.0
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1002.8	1007.5	1010.6	1016.4	1021.1	1023.9	1026.2	1028.3	1030.6	1032.7	1038.4
5°	1009.3	1020.3	1029.6	1044.0	1057.1	1067.2	1078.2	1088.0	1096.1	1107.5	1116.4
7.5°	1006.5	1026.1	1046.5	1068.8	1091.5	1112.7	1132.2	1150.4	1166.9	1186.9	1204.4
10°	1003.8	1030.5	1056.7	1086.7	1117.6	1143.9	1168.4	1193.4	1211.6	1237.1	1258.6
12.5°	1001.8	1033.1	1064.8	1101.0	1134.9	1172.0	1204.7	1222.9	1250.6	1270.9	1296.6
15°	993.2	1034.7	1078.2	1118.9	1167.2	1201.4	1230.3	1265.8	1291.6	1317.4	1345.4
17.5°	977.9	1024.8	1073.6	1126.9	1173.2	1210.0	1247.1	1281.4	1312.2	1346.9	1381.6
20°	970.8	1017.7	1073.6	1128.2	1173.5	1212.0	1250.2	1287.8	1321.7	1366.1	1406.4
22.5°	955.9	1012.7	1064.1	1117.4	1164.0	1206.0	1249.1	1291.9	1336.9	1387.2	1437.5
25°	929.3	986.8	1041.5	1094.0	1140.9	1193.4	1239.6	1296.7	1354.3	1420.7	1483.4
27.5°	901.6	956.8	1006.8	1057.5	1112.3	1171.7	1231.6	1296.5	1371.8	1455.7	1544.1
30°	879.3	931.4	980.1	1032.1	1089.2	1156.2	1221.8	1298.9	1386.0	1480.4	1585.4
32.5°	853.2	901.2	948.5	1003.7	1065.9	1136.5	1213.0	1297.5	1402.3	1509.6	1617.6
35°	808.6	848.8	897.5	956.3	1026.6	1107.5	1196.0	1295.8	1416.1	1539.3	1630.4
37.5°	755.7	793.1	844.4	908.9	982.6	1069.3	1174.4	1292.9	1420.6	1518.8	1548.2
40°	720.2	754.8	808.2	875.1	950.4	1042.3	1157.4	1282.7	1406.4	1469.0	1444.9
42.5°	682.2	718.6	770.5	836.8	917.9	1017.9	1136.1	1261.4	1365.1	1388.8	1305.4
45°	622.3	660.0	711.2	778.1	865.4	973.7	1096.9	1210.8	1270.5	1227.7	1098.6
47.5°	566.7	602.0	649.5	718.5	808.5	920.6	1039.3	1130.1	1134.8	1032.8	894.9
50°	528.8	561.3	609.2	678.2	767.5	881.0	988.1	1059.6	1027.4	911.9	779.3
52.5°	491.5	523.4	570.6	639.0	727.2	831.2	930.8	981.0	920.5	801.8	688.6
55°	437.7	465.7	511.8	574.9	658.8	755.3	839.9	857.3	778.5	661.7	569.8
57.5°	385.2	411.3	453.3	511.4	588.0	673.5	739.7	736.1	652.8	552.5	479.6
60°	349.7	375.1	412.4	469.0	538.9	612.6	669.3	655.7	573.2	486.8	425.5
62.5°	317.9	340.6	375.8	425.3	489.1	557.4	604.0	584.0	503.1	427.5	379.0
65°	270.9	290.0	320.1	362.4	415.3	471.7	507.6	481.8	412.8	353.9	315.0
67.5°	226.2	241.4	266.6	300.4	345.5	390.8	412.7	386.7	331.5	288.5	259.7
70°	197.7	211.2	230.7	260.8	300.2	338.3	354.7	331.5	284.1	247.2	226.5
72.5°	169.3	180.4	197.5	224.5	256.1	289.2	303.6	281.4	242.4	211.3	191.9
75°	130.9	138.4	150.3	168.9	193.9	220.1	228.2	208.7	183.8	160.5	147.7
77.5°	93.7	100.1	109.1	120.8	138.5	155.2	162.2	151.0	131.7	116.9	106.5
80°	72.0	75.3	83.0	92.7	106.7	117.2	121.9	114.7	101.2	90.2	82.1
82.5°	51.3	54.7	59.3	67.3	76.2	83.4	88.4	83.6	73.8	65.1	60.4
85°	24.9	27.1	29.6	33.0	39.8	44.0	43.6	40.6	36.9	33.4	30.9
87.5°	9.5	10.3	11.7	13.9	15.2	17.0	18.1	17.8	16.8	16.1	15.3
90°	3.4	5.6	7.8	9.9	12.0	13.9	15.8	17.8	19.6	21.0	22.4
92.5°	31.3	32.9	34.3	35.9	37.8	40.2	42.5	44.8	47.2	49.0	50.8
95°	80.5	81.0	81.5	82.1	83.7	86.5	89.2	92.0	94.7	96.6	98.5
97.5°	133.0	133.2	133.5	133.7	135.7	139.4	143.2	147.0	150.7	152.5	154.3
100°	172.1	172.1	172.1	172.1	173.9	177.5	181.0	184.6	188.1	190.6	193.1
102.5°	215.6	216.6	217.7	218.8	220.3	222.1	223.9	225.7	227.5	230.2	232.8
105°	281.7	283.1	284.5	285.8	287.3	288.9	290.6	292.2	293.9	295.5	297.2
107.5°	354.5	355.9	357.3	358.6	360.0	361.2	362.4	363.7	364.9	365.7	366.6
110°	404.7	406.0	407.4	408.8	409.9	410.7	411.5	412.3	413.1	413.9	414.8





TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.2	455.9	456.6	457.3	458.2	459.2	460.2	461.3	462.4	462.7	463.1
115°	531.1	532.1	533.2	534.3	535.2	535.7	536.2	536.8	537.4	537.0	536.8
117.5°	606.2	606.7	607.2	607.6	608.1	608.6	609.1	609.6	610.2	610.3	610.6
120°	654.3	655.7	657.0	658.4	659.2	659.5	659.7	660.0	660.3	660.3	660.3
122.5°	704.6	705.1	705.6	706.0	706.6	707.4	708.1	708.7	709.5	709.2	709.1
125°	775.0	776.7	778.4	780.0	781.0	781.2	781.5	781.8	782.0	781.5	781.0
127.5°	848.2	849.1	849.9	850.9	851.6	851.9	852.2	852.6	852.9	852.6	852.3
130°	892.8	894.2	895.5	896.9	897.9	898.5	898.9	899.5	900.1	899.8	899.5
132.5°	938.0	940.2	942.5	944.7	945.7	945.7	945.5	945.4	945.3	945.0	944.8
135°	1007.5	1009.1	1010.7	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4	1014.4
137.5°	1073.3	1074.9	1076.4	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9	1082.2
140°	1115.4	1116.7	1118.1	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4	1124.9
142.5°	1157.5	1158.6	1159.8	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4	1166.8
145°	1219.6	1220.7	1221.8	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1	1227.1
147.5°	1276.7	1277.2	1277.9	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4	1283.0
150°	1314.2	1313.9	1313.6	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2	1318.2
152.5°	1346.3	1346.7	1347.0	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3	1351.0
155°	1394.4	1394.4	1394.4	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7	1397.7
157.5°	1437.0	1436.5	1435.8	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3	1438.4
160°	1462.4	1461.6	1460.8	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8	1463.0
162.5°	1485.2	1484.7	1484.1	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7	1486.0
165°	1515.6	1515.0	1514.5	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0	1517.0
167.5°	1540.6	1539.5	1538.4	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4	1540.0
170°	1554.4	1553.2	1552.2	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2	1553.8
172.5°	1564.2	1563.1	1562.0	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0	1563.7
175°	1575.2	1574.2	1573.0	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0	1574.8
177.5°	1581.1	1580.3	1579.4	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4	1579.7
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1043.1	1045.9	1051.6	1049.5	1052.3	1053.6	1055.0
5°	1127.4	1140.9	1146.9	1146.0	1154.9	1152.8	1150.6
7.5°	1222.5	1236.8	1244.7	1254.7	1260.4	1260.8	1265.8
10°	1276.4	1295.0	1302.7	1313.2	1320.0	1323.8	1323.4
12.5°	1317.7	1332.3	1349.4	1354.5	1363.7	1368.5	1366.8
15°	1367.4	1390.7	1408.5	1417.4	1428.8	1432.2	1436.9
17.5°	1411.8	1443.0	1463.8	1491.3	1501.8	1508.1	1504.4
20°	1445.3	1486.4	1507.2	1540.2	1558.4	1568.1	1564.7
22.5°	1484.9	1529.4	1567.7	1596.4	1624.1	1637.2	1639.9
25°	1552.8	1613.8	1670.1	1707.8	1742.1	1750.1	1767.9
27.5°	1628.7	1700.6	1760.8	1800.4	1824.3	1833.3	1838.8
30°	1676.5	1748.0	1793.3	1818.7	1826.4	1825.5	1824.6
32.5°	1699.8	1744.7	1753.3	1746.2	1728.8	1714.1	1698.7
35°	1666.7	1633.3	1583.3	1519.0	1471.5	1423.8	1419.0
37.5°	1499.0	1392.0	1308.9	1216.0	1162.5	1129.4	1106.4
40°	1341.2	1219.7	1118.9	1040.6	985.9	964.4	943.2
42.5°	1169.8	1053.7	964.5	899.0	857.9	834.0	817.3
45°	950.4	848.0	778.1	730.7	698.1	679.5	668.9
47.5°	778.8	703.0	643.7	609.4	586.9	572.4	572.5
50°	686.6	614.2	574.9	547.8	528.3	516.9	519.0
52.5°	605.0	551.0	517.3	494.6	480.2	473.2	473.0
55°	505.9	466.9	444.9	428.4	418.7	410.7	412.4
57.5°	432.8	399.9	385.1	371.5	364.7	361.4	356.8
60°	387.3	362.0	349.3	338.3	331.5	329.0	324.2
62.5°	347.1	327.1	314.7	305.7	299.6	298.8	295.1
65°	291.7	276.5	265.5	261.2	254.9	253.2	253.2
67.5°	240.4	229.5	221.0	217.1	214.3	214.7	212.7
70°	208.3	199.4	193.9	189.6	187.5	187.9	186.3
72.5°	182.2	172.3	167.5	164.9	162.2	163.2	162.6
75°	138.0	132.9	130.4	127.8	126.1	125.3	124.5
77.5°	101.3	96.9	94.9	93.5	93.8	91.7	93.3
80°	78.4	74.5	73.2	71.1	70.7	70.7	70.3
82.5°	57.3	55.2	54.3	52.5	51.8	52.4	51.3
85°	29.6	28.0	27.6	27.6	26.7	25.8	28.0
87.5°	15.6	14.5	14.8	14.6	14.8	14.5	14.0
90°	23.8	25.1	26.3	27.1	27.9	28.7	29.5
92.5°	52.6	54.5	55.6	56.3	56.8	57.4	58.0
95°	100.4	102.3	103.5	104.1	104.7	105.2	105.7
97.5°	156.1	157.9	159.1	159.4	159.7	160.0	160.4
100°	195.5	198.0	199.5	200.0	200.6	201.1	201.6
102.5°	235.5	238.1	239.9	240.7	241.4	242.2	243.0
105°	298.8	300.4	301.7	302.5	303.3	304.1	304.9
107.5°	367.4	368.2	368.6	368.5	368.5	368.4	368.4
110°	415.6	416.5	416.7	416.5	416.1	415.9	415.6



TEST NUMBER: P333425-930

CATALOG NUMBER: S125DIW-S850D1560U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	463.5	463.8	463.8	463.3	462.8	462.4	461.9
115°	536.5	536.2	536.0	535.7	535.4	535.2	534.9
117.5°	610.8	611.0	610.6	609.4	608.4	607.3	606.2
120°	660.3	660.3	659.7	658.7	657.5	656.5	655.4
122.5°	708.8	708.6	708.1	707.2	706.3	705.4	704.6
125°	780.4	779.8	779.4	779.2	778.9	778.6	778.4
127.5°	852.1	851.7	851.3	850.8	850.3	849.7	849.1
130°	899.3	898.9	898.5	898.1	897.5	896.9	896.4
132.5°	944.5	944.2	943.7	943.0	942.2	941.4	940.6
135°	1014.4	1014.4	1013.9	1012.8	1011.7	1010.6	1009.5
137.5°	1082.6	1082.9	1082.4	1081.0	1079.6	1078.2	1076.8
140°	1125.5	1126.0	1125.6	1124.3	1122.9	1121.5	1120.1
142.5°	1167.1	1167.5	1166.9	1165.6	1164.2	1162.9	1161.5
145°	1227.1	1227.1	1226.7	1225.9	1225.1	1224.3	1223.4
147.5°	1283.7	1284.3	1283.8	1281.9	1280.0	1278.2	1276.4
150°	1318.2	1318.2	1317.8	1317.3	1316.8	1316.2	1315.6
152.5°	1351.6	1352.3	1352.1	1351.1	1350.1	1349.2	1348.2
155°	1398.9	1400.0	1399.9	1398.5	1397.1	1395.7	1394.4
157.5°	1439.5	1440.6	1440.2	1438.4	1436.6	1434.8	1433.0
160°	1464.0	1465.2	1465.0	1463.6	1462.2	1460.9	1459.5
162.5°	1487.4	1488.7	1488.5	1486.9	1485.3	1483.8	1482.1
165°	1518.2	1519.2	1519.0	1517.4	1515.7	1514.1	1512.4
167.5°	1541.6	1543.3	1543.3	1541.6	1539.9	1538.2	1536.5
170°	1555.4	1557.1	1557.0	1555.0	1553.1	1551.2	1549.3
172.5°	1565.3	1566.9	1566.9	1565.2	1563.5	1561.8	1560.2
175°	1576.4	1578.0	1577.8	1576.0	1574.0	1572.1	1570.2
177.5°	1581.0	1582.3	1582.3	1580.7	1579.2	1577.6	1576.1
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1

(END OF REPORT)