

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333706-930

Luminaire Tested: **S125RDIW-S1090D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333706-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D770U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5946.9 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333706-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333706-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88		75	75	75		63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73		66	65	63		56	55	54	49
2	91	84	78	72	85	78	73	68	68	64	61		59	56	53		50	48	46	42
3	83	74	67	61	77	69	63	57	60	55	51		52	48	45		44	42	39	36
4	76	66	58	52	71	61	54	49	54	48	44		47	42	39		40	37	34	31
5	70	59	50	44	65	55	48	42	48	42	38		42	37	34		36	33	30	27
6	65	53	44	39	60	49	42	37	44	38	33		38	33	30		33	29	26	24
7	60	48	40	34	56	45	38	32	40	34	29		35	30	26		30	26	24	21
8	56	43	36	30	52	41	34	29	36	30	26		32	27	24		28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24		29	25	21		26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21		27	23	19		24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9412	9412	9412
5°	9433	9326	9383
10°	9362	9239	9239
15°	9250	9052	8978
20°	9108	8790	8685
25°	8941	8533	8345
30°	8733	8232	7970
35°	8521	7923	7550
40°	8323	7599	7136
45°	8082	7238	6685
50°	7840	6845	6215
55°	7560	6469	5713
60°	7279	6013	5174
65°	6946	5483	4557
70°	6567	4823	3928
75°	6041	4065	3266
80°	5322	3195	2741
85°	4483	2608	2445



TEST NUMBER: P333706-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.0	2.3
10°-20°	382.9	6.4
20°-30°	555.3	9.3
30°-40°	632.9	10.6
40°-50°	616.9	10.4
50°-60°	519.3	8.7
60°-70°	364.0	6.1
70°-80°	187.1	3.1
80°-90°	49.0	0.8
90°-100°	29.6	0.5
100°-110°	182.5	3.1
110°-120°	331.0	5.6
120°-130°	424.8	7.1
130°-140°	456.9	7.7
140°-150°	428.9	7.2
150°-160°	346.9	5.8
160°-170°	224.4	3.8
170°-180°	77.4	1.3
0°-30°	1075.3	18.1
0°-40°	1708.1	28.7
0°-60°	2844.3	47.8
0°-90°	3444.3	57.9
90°-120°	543.2	9.1
90°-150°	1853.8	31.2
90°-180°	2503.0	42.1
0°-180°	5946.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1455	1450	1438	1449	1447	138
15°	1384	1376	1354	1352	1343	390
25°	1255	1237	1198	1183	1171	577
35°	1081	1053	1005	974	958	676
45°	885	851	792	750	732	682
55°	671	635	574	527	507	600
65°	454	416	359	316	298	450
75°	242	208	163	140	131	256
85°	60	42	35	34	33	68
90°	1	5	10	13	14	4
95°	34	32	10	12	13	44
105°	178	180	180	180	179	188
115°	334	336	337	335	331	330
125°	474	478	478	476	474	423
135°	591	595	594	592	589	456
145°	686	687	687	687	684	429
155°	755	752	753	754	750	348
165°	797	793	794	797	793	225
175°	815	812	812	816	811	78
180°	815	815	815	815	815	



TEST NUMBER: P333706-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1459.9	1459.3	1458.7	1458.1	1457.5	1456.3	1454.3	1452.4	1450.4	1448.5	1450.4
5°	1455.1	1454.1	1453.1	1452.1	1451.2	1449.3	1446.6	1443.9	1441.2	1438.5	1441.0
7.5°	1440.7	1439.8	1438.8	1437.9	1437.0	1434.9	1431.7	1428.5	1425.2	1422.0	1423.8
10°	1427.5	1426.8	1426.0	1425.3	1424.6	1422.5	1419.1	1415.7	1412.3	1408.8	1409.6
12.5°	1412.5	1411.6	1410.7	1409.7	1408.8	1406.1	1401.5	1396.9	1392.3	1387.6	1388.2
15°	1383.5	1382.0	1380.5	1379.1	1377.6	1374.4	1369.2	1364.1	1358.9	1353.8	1353.6
17.5°	1350.7	1348.4	1346.2	1343.9	1341.7	1337.3	1330.9	1324.5	1317.9	1311.5	1310.3
20°	1325.2	1322.7	1320.3	1317.8	1315.4	1310.3	1302.4	1294.6	1286.8	1279.0	1277.7
22.5°	1297.0	1294.5	1292.1	1289.6	1287.2	1281.9	1273.7	1265.4	1257.2	1249.0	1246.6
25°	1254.7	1251.1	1247.4	1243.7	1240.1	1233.7	1224.7	1215.6	1206.6	1197.5	1194.3
27.5°	1206.3	1201.8	1197.3	1192.9	1188.5	1181.5	1171.7	1162.0	1152.3	1142.6	1138.2
30°	1171.1	1166.4	1161.8	1157.2	1152.5	1145.0	1134.7	1124.5	1114.2	1103.9	1098.3
32.5°	1136.7	1131.3	1125.8	1120.5	1115.0	1107.1	1096.6	1086.1	1075.6	1065.2	1059.0
35°	1080.8	1075.0	1069.1	1063.2	1057.4	1048.9	1037.9	1026.9	1015.9	1004.9	997.8
37.5°	1026.0	1018.9	1011.7	1004.6	997.4	988.2	976.8	965.5	954.1	942.8	934.3
40°	987.2	979.9	972.6	965.2	957.9	948.4	936.6	924.9	913.1	901.4	892.1
42.5°	946.7	939.2	931.7	924.1	916.6	906.8	894.6	882.6	870.4	858.3	849.4
45°	884.9	877.8	870.7	863.6	856.6	846.3	832.8	819.4	805.9	792.5	782.7
47.5°	820.8	813.3	805.8	798.4	790.9	780.4	766.9	753.3	739.7	726.2	716.1
50°	780.3	772.3	764.2	756.1	748.0	737.0	723.1	709.1	695.2	681.3	671.0
52.5°	736.3	728.1	719.7	711.5	703.3	692.5	679.4	666.2	653.1	639.9	628.8
55°	671.4	663.6	655.7	647.9	640.1	629.3	615.6	601.9	588.2	574.5	563.5
57.5°	605.8	597.5	589.1	580.7	572.3	561.6	548.4	535.2	522.0	508.7	498.0
60°	563.5	555.0	546.4	537.9	529.3	518.4	505.2	492.0	478.7	465.5	454.8
62.5°	518.6	510.5	502.3	494.1	485.9	475.2	461.8	448.3	435.0	421.5	411.6
65°	454.5	446.2	437.9	429.6	421.3	410.7	397.7	384.7	371.8	358.8	349.0
67.5°	390.9	382.6	374.3	366.0	357.7	347.3	334.8	322.5	310.1	297.6	288.7
70°	347.8	339.5	331.2	322.9	314.5	304.3	292.0	279.8	267.6	255.4	247.8
72.5°	305.6	297.4	289.3	281.2	273.0	263.3	251.8	240.4	228.9	217.5	210.5
75°	242.1	234.8	227.5	220.1	212.8	204.0	193.7	183.4	173.2	162.9	157.5
77.5°	179.2	173.3	167.5	161.6	155.7	148.6	140.5	132.2	124.0	115.8	112.0
80°	143.1	137.2	131.3	125.5	119.6	113.2	106.4	99.5	92.7	85.9	83.6
82.5°	107.9	102.6	97.3	92.0	86.7	81.8	77.0	72.3	67.7	62.9	62.0
85°	60.5	56.1	51.7	47.3	42.9	40.1	38.9	37.7	36.4	35.2	35.0
87.5°	20.4	19.2	18.1	16.9	15.7	15.2	15.2	15.2	15.2	15.2	15.2
90°	0.6	1.7	2.8	3.8	4.9	5.9	6.8	7.8	8.7	9.7	10.4
92.5°	9.3	8.6	7.8	7.0	6.3	6.4	7.2	8.0	8.8	9.7	10.4
95°	34.4	34.0	33.6	33.3	32.9	30.1	24.9	19.9	14.8	9.7	10.4
97.5°	71.9	72.6	73.4	74.0	74.8	70.1	60.0	49.9	39.8	29.8	25.9
100°	100.9	101.3	101.7	102.1	102.5	103.0	103.5	104.0	104.6	105.1	85.1
102.5°	130.4	130.9	131.4	131.9	132.4	132.8	133.1	133.5	133.8	134.1	130.4
105°	177.6	178.1	178.7	179.2	179.8	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.7	226.7	226.7	226.7	226.7	226.8	227.1	227.3	227.6	227.9	227.9
110°	258.5	258.5	258.5	258.5	258.5	258.7	258.9	259.3	259.5	259.8	259.3



TEST NUMBER: P333706-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.5	288.9	289.2	289.5	289.8	290.1	290.2	290.4	290.6	290.7	290.2
115°	333.5	334.1	334.8	335.5	336.1	336.6	336.7	336.8	337.0	337.1	336.6
117.5°	380.0	379.9	379.9	379.9	379.8	380.1	380.7	381.2	381.6	382.1	381.5
120°	409.0	408.9	408.7	408.5	408.5	408.5	409.0	409.4	409.8	410.2	409.9
122.5°	434.6	435.1	435.6	436.1	436.7	437.0	437.2	437.3	437.6	437.7	437.5
125°	474.3	475.2	476.1	477.0	478.0	478.4	478.4	478.4	478.4	478.4	477.9
127.5°	512.0	512.7	513.4	514.0	514.7	515.0	514.9	514.9	514.8	514.7	514.4
130°	535.2	535.9	536.5	537.3	537.9	538.3	538.4	538.6	538.7	538.8	538.4
132.5°	558.4	559.2	560.0	560.8	561.6	561.8	561.5	561.2	560.9	560.6	560.5
135°	591.4	592.2	593.0	593.9	594.7	594.9	594.7	594.4	594.1	593.9	593.5
137.5°	621.7	622.5	623.1	623.9	624.5	624.8	624.5	624.3	624.0	623.8	623.9
140°	641.6	641.8	642.1	642.4	642.6	642.7	642.5	642.5	642.3	642.1	642.5
142.5°	659.4	659.6	659.7	659.9	660.1	660.2	660.5	660.6	660.8	661.0	661.0
145°	685.7	685.9	686.2	686.5	686.7	686.9	686.9	686.9	686.9	686.9	687.0
147.5°	708.7	708.6	708.5	708.5	708.4	708.5	708.7	708.7	708.9	709.1	709.2
150°	723.1	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	723.4
152.5°	737.1	736.5	736.0	735.4	734.7	734.6	734.9	735.2	735.4	735.6	736.0
155°	755.1	754.3	753.5	752.7	752.0	751.6	752.0	752.2	752.4	752.7	753.1
157.5°	769.0	768.6	768.1	767.6	767.1	766.9	766.9	767.0	767.0	767.0	767.4
160°	778.7	777.9	777.1	776.2	775.5	775.1	775.3	775.4	775.5	775.7	776.2
162.5°	786.4	785.6	784.8	784.0	783.2	782.9	783.0	783.2	783.3	783.4	784.2
165°	796.8	796.0	795.2	794.4	793.6	793.3	793.4	793.5	793.7	793.8	794.6
167.5°	804.5	803.7	802.9	802.1	801.2	800.9	801.0	801.1	801.3	801.4	802.3
170°	808.9	808.0	807.0	806.1	805.1	804.7	804.9	805.0	805.1	805.3	806.3
172.5°	811.8	810.9	809.9	808.9	808.0	807.7	808.0	808.2	808.5	808.7	809.6
175°	815.0	814.2	813.3	812.5	811.7	811.4	811.5	811.6	811.8	812.0	813.0
177.5°	816.4	815.7	815.1	814.5	813.8	813.5	813.7	813.8	813.8	814.0	814.7
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333706-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1452.4	1454.3	1456.3	1457.1	1456.9	1456.8	1456.5	1456.4
5°	1443.4	1445.9	1448.3	1449.3	1448.8	1448.3	1447.8	1447.3
7.5°	1425.5	1427.2	1428.9	1429.5	1428.9	1428.4	1427.8	1427.3
10°	1410.3	1411.0	1411.8	1411.8	1411.0	1410.3	1409.6	1408.8
12.5°	1388.8	1389.3	1389.8	1389.5	1388.4	1387.3	1386.2	1385.0
15°	1353.3	1353.1	1352.8	1351.6	1349.4	1347.2	1345.0	1342.8
17.5°	1309.0	1307.8	1306.6	1305.1	1303.3	1301.5	1299.7	1297.9
20°	1276.5	1275.3	1274.1	1272.4	1270.2	1268.0	1265.8	1263.6
22.5°	1244.2	1241.8	1239.4	1237.3	1235.5	1233.7	1231.8	1230.0
25°	1191.2	1188.0	1184.8	1181.9	1179.2	1176.5	1173.8	1171.1
27.5°	1133.8	1129.4	1124.9	1121.4	1118.8	1116.1	1113.5	1111.0
30°	1092.7	1087.0	1081.4	1077.5	1075.3	1073.1	1070.9	1068.7
32.5°	1052.8	1046.5	1040.3	1035.8	1033.1	1030.3	1027.4	1024.7
35°	990.7	983.6	976.5	971.3	967.8	964.4	961.0	957.6
37.5°	925.8	917.3	908.7	902.9	899.5	896.2	892.8	889.5
40°	882.8	873.5	864.2	858.1	855.2	852.2	849.3	846.4
42.5°	840.5	831.5	822.6	816.0	811.7	807.5	803.2	798.8
45°	772.9	763.1	753.3	746.6	742.9	739.2	735.6	731.9
47.5°	706.0	695.9	685.9	678.8	674.7	670.7	666.7	662.6
50°	660.7	650.4	640.2	633.2	629.6	625.9	622.2	618.6
52.5°	617.8	606.7	595.7	588.3	584.7	581.0	577.3	573.6
55°	552.5	541.5	530.5	523.0	519.1	515.2	511.3	507.4
57.5°	487.2	476.5	465.7	458.5	455.1	451.6	448.1	444.7
60°	444.0	433.3	422.5	415.3	411.6	408.0	404.3	400.6
62.5°	401.6	391.6	381.6	374.8	371.1	367.5	363.8	360.1
65°	339.2	329.5	319.7	312.9	309.2	305.6	301.9	298.2
67.5°	279.7	270.8	261.8	255.8	252.9	250.0	247.0	244.1
70°	240.2	232.6	225.0	219.7	216.8	213.9	210.9	208.0
72.5°	203.5	196.5	189.5	185.0	183.0	181.1	179.1	177.2
75°	152.1	146.8	141.4	137.8	136.1	134.4	132.6	130.9
77.5°	108.3	104.5	100.7	98.2	96.9	95.6	94.4	93.1
80°	81.4	79.2	77.0	75.7	75.2	74.7	74.2	73.7
82.5°	60.9	59.8	58.9	58.2	57.9	57.6	57.3	57.0
85°	34.7	34.5	34.2	34.0	33.8	33.5	33.3	33.0
87.5°	15.4	15.6	15.7	15.7	15.6	15.5	15.3	15.2
90°	11.0	11.7	12.3	12.9	13.3	13.7	14.1	14.5
92.5°	11.0	11.7	12.3	12.8	13.0	13.1	13.4	13.5
95°	11.0	11.7	12.3	12.7	12.7	12.7	12.7	12.7
97.5°	22.2	18.3	14.6	12.7	12.7	12.7	12.7	12.7
100°	65.1	45.1	25.1	14.8	14.3	13.8	13.2	12.7
102.5°	126.5	122.8	119.0	112.5	103.4	94.2	85.1	76.0
105°	180.0	180.0	180.0	179.9	179.9	179.7	179.5	179.4
107.5°	228.0	228.0	228.0	227.8	227.4	227.0	226.6	226.2
110°	258.9	258.5	258.1	258.0	258.1	258.3	258.4	258.5



TEST NUMBER: P333706-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	289.7	289.2	288.6	288.3	288.1	288.0	287.7	287.6
115°	336.0	335.5	334.9	334.3	333.5	332.6	331.8	331.0
117.5°	380.7	380.1	379.4	378.9	378.5	378.1	377.8	377.5
120°	409.7	409.4	409.1	408.6	408.0	407.3	406.7	405.9
122.5°	437.2	436.9	436.7	436.1	435.4	434.6	433.8	433.0
125°	477.4	476.9	476.3	475.8	475.4	475.0	474.7	474.3
127.5°	514.1	513.8	513.6	512.9	511.8	510.9	509.9	508.9
130°	538.1	537.7	537.3	536.7	536.1	535.4	534.7	534.0
132.5°	560.4	560.4	560.3	559.9	559.2	558.6	557.9	557.3
135°	593.3	593.0	592.8	592.2	591.4	590.6	589.8	589.0
137.5°	623.9	623.9	624.0	623.7	623.0	622.3	621.6	620.9
140°	642.7	642.9	643.3	642.9	642.1	641.4	640.6	639.8
142.5°	661.1	661.2	661.2	660.9	660.1	659.3	658.4	657.6
145°	687.1	687.3	687.4	687.1	686.2	685.4	684.7	683.9
147.5°	709.4	709.6	709.7	709.3	708.4	707.4	706.5	705.5
150°	723.7	723.9	724.2	723.8	722.7	721.6	720.6	719.5
152.5°	736.2	736.5	736.8	736.4	735.4	734.5	733.5	732.5
155°	753.5	753.9	754.3	754.0	752.9	751.9	750.8	749.7
157.5°	767.8	768.3	768.7	768.3	767.3	766.2	765.2	764.1
160°	776.7	777.3	777.8	777.6	776.5	775.4	774.4	773.2
162.5°	784.9	785.6	786.4	786.2	785.1	783.8	782.7	781.5
165°	795.4	796.2	797.0	796.9	795.8	794.8	793.7	792.6
167.5°	803.3	804.3	805.3	805.2	804.0	802.7	801.5	800.3
170°	807.4	808.5	809.6	809.5	808.3	807.1	805.8	804.7
172.5°	810.6	811.5	812.5	812.4	811.2	810.0	808.8	807.6
175°	814.1	815.1	816.2	816.1	815.0	813.8	812.5	811.3
177.5°	815.5	816.2	817.0	816.9	816.0	815.2	814.3	813.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0

(END OF REPORT)