

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333707-930

Luminaire Tested: **S125RDIW-S1090D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333707-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D770U930-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5614.5 lumens  
Efficiency: N/A  
Efficacy: 104.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333707-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333707-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	52	50	48	44
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	34	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9412	9412	9412
5°	9433	9326	9383
10°	9362	9239	9239
15°	9250	9052	8978
20°	9108	8790	8685
25°	8941	8533	8345
30°	8733	8232	7970
35°	8521	7923	7550
40°	8323	7599	7136
45°	8082	7238	6685
50°	7840	6845	6215
55°	7560	6469	5713
60°	7279	6013	5174
65°	6946	5483	4557
70°	6567	4823	3928
75°	6041	4065	3266
80°	5322	3195	2741
85°	4483	2608	2445



TEST NUMBER: P333707-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.0	2.4
10°-20°	382.9	6.8
20°-30°	555.3	9.9
30°-40°	632.9	11.3
40°-50°	616.9	11.0
50°-60°	519.3	9.2
60°-70°	364.0	6.5
70°-80°	187.1	3.3
80°-90°	49.0	0.9
90°-100°	52.1	0.9
100°-110°	153.8	2.7
110°-120°	260.5	4.6
120°-130°	342.9	6.1
130°-140°	384.2	6.8
140°-150°	376.6	6.7
150°-160°	316.3	5.6
160°-170°	210.2	3.7
170°-180°	73.6	1.3
0°-30°	1075.3	19.2
0°-40°	1708.1	30.4
0°-60°	2844.3	50.7
0°-90°	3444.3	61.3
90°-120°	466.4	8.3
90°-150°	1570.1	28.0
90°-180°	2170.0	38.6
0°-180°	5614.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1455	1450	1438	1449	1447	138
15°	1384	1376	1354	1352	1343	390
25°	1255	1237	1198	1183	1171	577
35°	1081	1053	1005	974	958	676
45°	885	851	792	750	732	682
55°	671	635	574	527	507	600
65°	454	416	359	316	298	450
75°	242	208	163	140	131	256
85°	60	42	35	34	33	68
90°	1	5	10	13	14	5
95°	39	41	47	51	52	42
105°	138	141	145	148	150	147
115°	261	263	264	264	263	258
125°	381	384	385	384	383	341
135°	495	499	499	499	497	381
145°	600	602	604	604	602	375
155°	686	686	687	689	686	316
165°	746	745	746	748	744	210
175°	776	774	774	777	773	74
180°	778	778	778	778	778	



TEST NUMBER: P333707-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1459.9	1459.3	1458.7	1458.1	1457.5	1456.3	1454.3	1452.4	1450.4	1448.5	1450.4
5°	1455.1	1454.1	1453.1	1452.1	1451.2	1449.3	1446.6	1443.9	1441.2	1438.5	1441.0
7.5°	1440.7	1439.8	1438.8	1437.9	1437.0	1434.9	1431.7	1428.5	1425.2	1422.0	1423.8
10°	1427.5	1426.8	1426.0	1425.3	1424.6	1422.5	1419.1	1415.7	1412.3	1408.8	1409.6
12.5°	1412.5	1411.6	1410.7	1409.7	1408.8	1406.1	1401.5	1396.9	1392.3	1387.6	1388.2
15°	1383.5	1382.0	1380.5	1379.1	1377.6	1374.4	1369.2	1364.1	1358.9	1353.8	1353.6
17.5°	1350.7	1348.4	1346.2	1343.9	1341.7	1337.3	1330.9	1324.5	1317.9	1311.5	1310.3
20°	1325.2	1322.7	1320.3	1317.8	1315.4	1310.3	1302.4	1294.6	1286.8	1279.0	1277.7
22.5°	1297.0	1294.5	1292.1	1289.6	1287.2	1281.9	1273.7	1265.4	1257.2	1249.0	1246.6
25°	1254.7	1251.1	1247.4	1243.7	1240.1	1233.7	1224.7	1215.6	1206.6	1197.5	1194.3
27.5°	1206.3	1201.8	1197.3	1192.9	1188.5	1181.5	1171.7	1162.0	1152.3	1142.6	1138.2
30°	1171.1	1166.4	1161.8	1157.2	1152.5	1145.0	1134.7	1124.5	1114.2	1103.9	1098.3
32.5°	1136.7	1131.3	1125.8	1120.5	1115.0	1107.1	1096.6	1086.1	1075.6	1065.2	1059.0
35°	1080.8	1075.0	1069.1	1063.2	1057.4	1048.9	1037.9	1026.9	1015.9	1004.9	997.8
37.5°	1026.0	1018.9	1011.7	1004.6	997.4	988.2	976.8	965.5	954.1	942.8	934.3
40°	987.2	979.9	972.6	965.2	957.9	948.4	936.6	924.9	913.1	901.4	892.1
42.5°	946.7	939.2	931.7	924.1	916.6	906.8	894.6	882.6	870.4	858.3	849.4
45°	884.9	877.8	870.7	863.6	856.6	846.3	832.8	819.4	805.9	792.5	782.7
47.5°	820.8	813.3	805.8	798.4	790.9	780.4	766.9	753.3	739.7	726.2	716.1
50°	780.3	772.3	764.2	756.1	748.0	737.0	723.1	709.1	695.2	681.3	671.0
52.5°	736.3	728.1	719.7	711.5	703.3	692.5	679.4	666.2	653.1	639.9	628.8
55°	671.4	663.6	655.7	647.9	640.1	629.3	615.6	601.9	588.2	574.5	563.5
57.5°	605.8	597.5	589.1	580.7	572.3	561.6	548.4	535.2	522.0	508.7	498.0
60°	563.5	555.0	546.4	537.9	529.3	518.4	505.2	492.0	478.7	465.5	454.8
62.5°	518.6	510.5	502.3	494.1	485.9	475.2	461.8	448.3	435.0	421.5	411.6
65°	454.5	446.2	437.9	429.6	421.3	410.7	397.7	384.7	371.8	358.8	349.0
67.5°	390.9	382.6	374.3	366.0	357.7	347.3	334.8	322.5	310.1	297.6	288.7
70°	347.8	339.5	331.2	322.9	314.5	304.3	292.0	279.8	267.6	255.4	247.8
72.5°	305.6	297.4	289.3	281.2	273.0	263.3	251.8	240.4	228.9	217.5	210.5
75°	242.1	234.8	227.5	220.1	212.8	204.0	193.7	183.4	173.2	162.9	157.5
77.5°	179.2	173.3	167.5	161.6	155.7	148.6	140.5	132.2	124.0	115.8	112.0
80°	143.1	137.2	131.3	125.5	119.6	113.2	106.4	99.5	92.7	85.9	83.6
82.5°	107.9	102.6	97.3	92.0	86.7	81.8	77.0	72.3	67.7	62.9	62.0
85°	60.5	56.1	51.7	47.3	42.9	40.1	38.9	37.7	36.4	35.2	35.0
87.5°	20.4	19.2	18.1	16.9	15.7	15.2	15.2	15.2	15.2	15.2	15.2
90°	0.6	1.7	2.8	3.8	4.9	6.0	6.8	7.8	8.7	9.7	10.4
92.5°	14.7	15.4	16.1	16.9	17.7	18.6	19.8	21.0	22.1	23.2	24.1
95°	39.4	39.6	39.9	40.1	40.4	41.3	42.6	43.9	45.2	46.6	47.5
97.5°	65.4	65.5	65.6	65.7	65.8	66.8	68.6	70.5	72.3	74.2	75.1
100°	84.7	84.7	84.7	84.7	84.7	85.6	87.3	89.1	90.8	92.6	93.8
102.5°	105.6	106.1	106.6	107.1	107.7	108.4	109.3	110.2	111.0	111.9	113.3
105°	138.0	138.7	139.3	140.0	140.7	141.5	142.3	143.0	143.8	144.6	145.4
107.5°	173.8	174.5	175.2	175.9	176.5	177.2	177.8	178.4	179.0	179.6	180.0
110°	198.5	199.2	199.8	200.6	201.2	201.7	202.1	202.5	202.9	203.3	203.7



TEST NUMBER: P333707-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	223.7	224.0	224.4	224.8	225.1	225.5	226.0	226.6	227.1	227.6	227.8
115°	260.9	261.4	262.0	262.4	263.0	263.4	263.7	263.9	264.2	264.5	264.3
117.5°	298.2	298.4	298.6	298.9	299.1	299.4	299.6	299.9	300.1	300.4	300.4
120°	321.4	322.0	322.7	323.4	324.1	324.5	324.6	324.7	324.9	325.0	325.0
122.5°	346.6	346.8	347.1	347.3	347.6	347.8	348.1	348.5	348.9	349.2	349.1
125°	380.7	381.5	382.3	383.1	383.9	384.4	384.5	384.7	384.8	384.9	384.7
127.5°	417.0	417.4	417.9	418.4	418.8	419.1	419.3	419.5	419.6	419.8	419.6
130°	438.8	439.4	440.2	440.8	441.5	442.0	442.2	442.5	442.8	443.0	442.9
132.5°	460.6	461.7	462.8	463.9	465.0	465.5	465.5	465.4	465.4	465.3	465.2
135°	495.0	495.9	496.7	497.5	498.3	498.8	498.9	499.0	499.2	499.3	499.3
137.5°	527.5	528.3	529.0	529.9	530.7	531.2	531.5	531.7	532.1	532.4	532.6
140°	548.4	549.0	549.7	550.3	551.1	551.5	552.0	552.4	552.8	553.2	553.4
142.5°	569.2	569.7	570.3	570.9	571.4	571.9	572.5	573.0	573.5	574.0	574.1
145°	599.8	600.3	600.9	601.4	601.9	602.4	602.8	603.2	603.6	604.1	604.1
147.5°	628.1	628.4	628.7	629.0	629.3	629.6	629.9	630.2	630.6	630.9	631.2
150°	647.0	646.9	646.7	646.6	646.5	646.7	647.2	647.8	648.2	648.8	648.8
152.5°	662.5	662.7	662.8	663.1	663.2	663.4	663.7	663.9	664.1	664.3	664.6
155°	686.3	686.3	686.3	686.3	686.3	686.4	686.6	686.6	686.8	687.0	687.5
157.5°	707.7	707.4	707.0	706.8	706.5	706.4	706.5	706.6	706.8	706.9	707.4
160°	720.2	719.8	719.4	719.0	718.6	718.4	718.6	718.8	718.8	719.0	719.6
162.5°	731.4	731.1	730.8	730.5	730.2	730.0	730.1	730.1	730.1	730.2	730.8
165°	746.2	746.0	745.8	745.4	745.2	745.1	745.3	745.3	745.5	745.7	746.2
167.5°	758.9	758.3	757.7	757.2	756.7	756.4	756.4	756.4	756.4	756.4	757.2
170°	765.6	765.1	764.5	764.0	763.4	763.2	763.2	763.2	763.2	763.2	764.0
172.5°	770.5	769.9	769.4	768.8	768.3	768.0	768.0	768.0	768.0	768.0	768.8
175°	775.9	775.3	774.9	774.3	773.7	773.5	773.5	773.5	773.5	773.5	774.3
177.5°	778.7	778.3	777.8	777.4	777.0	776.7	776.6	776.5	776.4	776.2	776.9
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333707-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1452.4	1454.3	1456.3	1457.1	1456.9	1456.8	1456.5	1456.4
5°	1443.4	1445.9	1448.3	1449.3	1448.8	1448.3	1447.8	1447.3
7.5°	1425.5	1427.2	1428.9	1429.5	1428.9	1428.4	1427.8	1427.3
10°	1410.3	1411.0	1411.8	1411.8	1411.0	1410.3	1409.6	1408.8
12.5°	1388.8	1389.3	1389.8	1389.5	1388.4	1387.3	1386.2	1385.0
15°	1353.3	1353.1	1352.8	1351.6	1349.4	1347.2	1345.0	1342.8
17.5°	1309.0	1307.8	1306.6	1305.1	1303.3	1301.5	1299.7	1297.9
20°	1276.5	1275.3	1274.1	1272.4	1270.2	1268.0	1265.8	1263.6
22.5°	1244.2	1241.8	1239.4	1237.3	1235.5	1233.7	1231.8	1230.0
25°	1191.2	1188.0	1184.8	1181.9	1179.2	1176.5	1173.8	1171.1
27.5°	1133.8	1129.4	1124.9	1121.4	1118.8	1116.1	1113.5	1111.0
30°	1092.7	1087.0	1081.4	1077.5	1075.3	1073.1	1070.9	1068.7
32.5°	1052.8	1046.5	1040.3	1035.8	1033.1	1030.3	1027.4	1024.7
35°	990.7	983.6	976.5	971.3	967.8	964.4	961.0	957.6
37.5°	925.8	917.3	908.7	902.9	899.5	896.2	892.8	889.5
40°	882.8	873.5	864.2	858.1	855.2	852.2	849.3	846.4
42.5°	840.5	831.5	822.6	816.0	811.7	807.5	803.2	798.8
45°	772.9	763.1	753.3	746.6	742.9	739.2	735.6	731.9
47.5°	706.0	695.9	685.9	678.8	674.7	670.7	666.7	662.6
50°	660.7	650.4	640.2	633.2	629.6	625.9	622.2	618.6
52.5°	617.8	606.7	595.7	588.3	584.7	581.0	577.3	573.6
55°	552.5	541.5	530.5	523.0	519.1	515.2	511.3	507.4
57.5°	487.2	476.5	465.7	458.5	455.1	451.6	448.1	444.7
60°	444.0	433.3	422.5	415.3	411.6	408.0	404.3	400.6
62.5°	401.6	391.6	381.6	374.8	371.1	367.5	363.8	360.1
65°	339.2	329.5	319.7	312.9	309.2	305.6	301.9	298.2
67.5°	279.7	270.8	261.8	255.8	252.9	250.0	247.0	244.1
70°	240.2	232.6	225.0	219.7	216.8	213.9	210.9	208.0
72.5°	203.5	196.5	189.5	185.0	183.0	181.1	179.1	177.2
75°	152.1	146.8	141.4	137.8	136.1	134.4	132.6	130.9
77.5°	108.3	104.5	100.7	98.2	96.9	95.6	94.4	93.1
80°	81.4	79.2	77.0	75.7	75.2	74.7	74.2	73.7
82.5°	60.9	59.8	58.9	58.2	57.9	57.6	57.3	57.0
85°	34.7	34.5	34.2	34.0	33.8	33.5	33.3	33.0
87.5°	15.4	15.6	15.7	15.7	15.6	15.5	15.3	15.2
90°	11.0	11.7	12.4	12.9	13.3	13.7	14.1	14.5
92.5°	25.0	25.9	26.8	27.4	27.7	28.0	28.3	28.5
95°	48.5	49.4	50.4	51.0	51.3	51.5	51.8	52.0
97.5°	76.0	76.9	77.8	78.3	78.4	78.6	78.8	78.9
100°	95.0	96.2	97.4	98.2	98.5	98.7	99.0	99.2
102.5°	114.6	115.9	117.2	118.1	118.5	118.9	119.2	119.6
105°	146.3	147.1	147.9	148.5	148.9	149.3	149.7	150.1
107.5°	180.4	180.8	181.2	181.4	181.4	181.4	181.3	181.3
110°	204.2	204.6	205.0	205.1	205.0	204.8	204.7	204.6





TEST NUMBER: P333707-930

CATALOG NUMBER: S125RDIW-S1090D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.0	228.1	228.3	228.3	228.0	227.8	227.6	227.3
115°	264.2	264.1	263.9	263.8	263.7	263.6	263.4	263.3
117.5°	300.5	300.6	300.8	300.5	300.0	299.5	298.9	298.4
120°	325.0	325.0	325.0	324.7	324.2	323.7	323.1	322.6
122.5°	349.0	348.9	348.8	348.5	348.1	347.6	347.2	346.8
125°	384.4	384.1	383.8	383.7	383.5	383.4	383.3	383.1
127.5°	419.6	419.4	419.2	419.1	418.8	418.5	418.2	418.0
130°	442.8	442.6	442.5	442.3	442.1	441.7	441.5	441.2
132.5°	465.0	464.9	464.8	464.5	464.1	463.7	463.4	463.0
135°	499.3	499.3	499.3	499.0	498.5	498.0	497.4	496.9
137.5°	532.7	532.9	533.0	532.7	532.1	531.4	530.8	530.0
140°	553.8	554.0	554.2	554.1	553.4	552.7	552.0	551.4
142.5°	574.3	574.5	574.6	574.4	573.7	573.1	572.3	571.7
145°	604.1	604.1	604.1	603.8	603.4	603.0	602.6	602.2
147.5°	631.5	631.9	632.2	631.9	631.0	630.1	629.2	628.3
150°	648.8	648.8	648.8	648.7	648.4	648.2	647.8	647.6
152.5°	665.0	665.3	665.6	665.5	665.0	664.6	664.1	663.6
155°	688.0	688.5	689.1	689.0	688.4	687.7	687.0	686.3
157.5°	708.0	708.5	709.1	708.9	708.0	707.1	706.2	705.3
160°	720.1	720.6	721.1	721.1	720.4	719.7	719.1	718.4
162.5°	731.5	732.1	732.7	732.7	731.9	731.1	730.3	729.5
165°	746.7	747.3	747.8	747.6	746.9	746.1	745.3	744.4
167.5°	758.1	758.9	759.6	759.6	758.8	758.0	757.2	756.3
170°	764.8	765.6	766.5	766.4	765.4	764.5	763.5	762.6
172.5°	769.6	770.5	771.3	771.3	770.5	769.6	768.7	767.9
175°	775.1	775.9	776.7	776.7	775.7	774.8	773.8	772.9
177.5°	777.6	778.2	778.9	778.8	778.0	777.3	776.6	775.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7

(END OF REPORT)