

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333649-930

Luminaire Tested: **S125RDIW-S375D1050U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333649-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1050U930-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4153.5 lumens  
Efficiency: N/A  
Efficacy: 109.3 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°    - · - · 135°-315°



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	43	43	39	35	33	30	28	23	21	20	16
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	1.1
10°-20°	129.0	3.1
20°-30°	204.5	4.9
30°-40°	246.6	5.9
40°-50°	220.2	5.3
50°-60°	168.9	4.1
60°-70°	109.7	2.6
70°-80°	53.3	1.3
80°-90°	15.0	0.4
90°-100°	71.1	1.7
100°-110°	210.0	5.1
110°-120°	355.6	8.6
120°-130°	468.0	11.3
130°-140°	524.4	12.6
140°-150°	514.0	12.4
150°-160°	431.7	10.4
160°-170°	287.0	6.9
170°-180°	100.4	2.4
0°-30°	377.5	9.1
0°-40°	624.0	15.0
0°-60°	1013.1	24.4
0°-90°	1191.3	28.7
90°-120°	636.7	15.3
90°-150°	2143.1	51.6
90°-180°	2962.0	71.3
0°-180°	4153.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	10
90°	20	1	20	1	20	12
95°	71	54	71	54	71	72
105°	205	188	205	188	205	217
115°	359	356	359	356	359	355
125°	523	520	523	520	523	467
135°	678	676	678	676	678	523
145°	822	819	822	819	822	513
155°	937	937	937	937	937	431
165°	1016	1019	1016	1019	1016	286
175°	1055	1059	1055	1059	1055	100
180°	1062	1062	1062	1062	1062	



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	7.3	7.0	6.8	6.7	6.7	6.8	6.5	6.2	6.0	5.8	5.7
90°	19.8	19.2	18.8	18.2	17.6	16.9	16.0	15.1	14.1	13.2	11.9
92.5°	39.0	38.6	38.2	37.7	37.3	36.6	35.4	34.2	32.9	31.7	30.2
95°	71.0	70.7	70.3	70.0	69.5	68.7	67.4	66.2	64.9	63.6	61.8
97.5°	107.7	107.5	107.3	107.0	106.8	106.2	104.9	103.7	102.5	101.3	98.7
100°	135.5	135.1	134.8	134.4	134.0	133.0	131.3	129.7	128.1	126.4	124.0
102.5°	163.2	162.7	162.2	161.7	161.2	160.0	158.2	156.5	154.7	152.9	151.6
105°	204.9	204.3	203.7	203.3	202.7	201.9	200.7	199.7	198.5	197.5	196.3
107.5°	247.5	247.5	247.6	247.6	247.7	247.4	246.9	246.3	245.7	245.2	244.3
110°	279.2	279.4	279.6	279.8	280.0	279.8	279.2	278.7	278.1	277.6	277.0



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.3	310.6	311.0	311.3	311.6	311.6	311.4	311.1	310.9	310.6	309.9
115°	359.4	359.5	359.7	359.9	360.1	360.3	360.4	360.6	360.9	361.0	360.6
117.5°	407.2	408.0	408.7	409.4	410.2	410.5	410.3	410.2	410.1	409.9	409.6
120°	440.3	441.1	441.8	442.5	443.3	443.6	443.6	443.6	443.6	443.6	443.4
122.5°	473.4	473.9	474.5	475.2	475.7	476.1	476.2	476.4	476.5	476.7	476.2
125°	522.9	523.1	523.3	523.5	523.7	523.9	524.3	524.6	525.1	525.4	525.2
127.5°	570.5	570.9	571.3	571.6	572.0	572.3	572.4	572.6	572.8	573.0	572.7
130°	602.3	602.6	603.0	603.3	603.7	604.0	604.1	604.4	604.5	604.7	604.4
132.5°	631.9	632.5	633.0	633.5	634.1	634.4	634.5	634.7	635.0	635.1	635.2
135°	678.2	679.0	679.7	680.4	681.2	681.5	681.5	681.5	681.5	681.5	681.3
137.5°	723.5	724.4	725.4	726.3	727.2	727.5	727.3	727.1	726.8	726.7	726.3
140°	752.6	753.5	754.4	755.4	756.3	756.5	756.2	755.8	755.5	755.0	754.5
142.5°	780.3	781.3	782.2	783.1	784.0	784.4	784.2	783.9	783.7	783.5	782.8
145°	822.0	822.6	823.0	823.6	824.2	824.4	824.4	824.4	824.4	824.4	823.9
147.5°	857.5	858.8	860.0	861.3	862.5	862.9	862.4	862.0	861.6	861.1	860.7
150°	883.9	884.3	884.7	885.0	885.4	885.6	885.6	885.6	885.6	885.6	884.8
152.5°	905.7	906.4	907.1	907.8	908.4	908.5	908.1	907.6	907.2	906.8	906.4
155°	936.8	937.8	938.7	939.6	940.4	940.6	939.9	939.1	938.4	937.7	937.4
157.5°	962.8	963.9	965.2	966.4	967.6	967.8	967.1	966.4	965.6	964.9	964.7
160°	980.6	981.5	982.4	983.3	984.2	984.4	983.7	982.9	982.2	981.5	981.2
162.5°	995.8	996.9	997.9	999.0	1000.0	1000.1	999.2	998.4	997.5	996.6	996.6
165°	1016.1	1017.2	1018.3	1019.5	1020.5	1020.7	1019.9	1019.2	1018.5	1017.7	1017.6
167.5°	1032.3	1033.5	1034.6	1035.8	1036.9	1036.9	1035.8	1034.7	1033.6	1032.5	1032.5
170°	1040.9	1042.2	1043.5	1044.7	1046.0	1046.1	1045.1	1043.9	1042.8	1041.7	1041.7
172.5°	1048.1	1049.3	1050.4	1051.6	1052.7	1052.7	1051.7	1050.5	1049.5	1048.3	1048.3
175°	1054.9	1056.2	1057.5	1058.8	1060.1	1060.2	1059.1	1057.9	1056.9	1055.7	1055.7
177.5°	1058.9	1060.0	1060.9	1062.0	1063.0	1063.1	1062.3	1061.4	1060.5	1059.6	1059.7
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	5.6	5.3	5.2	5.0	4.5	5.0	5.1	5.0	5.0	5.0	5.0
90°	10.7	9.4	8.1	6.7	5.2	3.8	2.3	0.8	2.3	3.8	5.2
92.5°	28.5	27.0	25.4	24.1	23.1	22.0	21.0	20.0	21.0	22.0	23.1
95°	59.9	58.1	56.3	55.2	54.8	54.5	54.1	53.7	54.1	54.5	54.8
97.5°	96.2	93.7	91.2	89.8	89.7	89.5	89.4	89.2	89.4	89.5	89.7
100°	121.6	119.2	116.8	115.7	115.7	115.7	115.7	115.7	115.7	115.7	115.7
102.5°	150.4	149.2	148.0	147.0	146.3	145.5	144.8	144.1	144.8	145.5	146.3
105°	195.3	194.1	193.1	192.0	191.1	190.2	189.2	188.3	189.2	190.2	191.1
107.5°	243.5	242.6	241.8	240.9	240.0	239.1	238.1	237.3	238.1	239.1	240.0
110°	276.5	275.9	275.4	274.7	273.7	272.8	271.9	270.9	271.9	272.8	273.7





TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	309.2	308.5	307.9	307.2	306.8	306.3	305.8	305.3	305.8	306.3	306.8
115°	360.3	359.9	359.5	359.0	358.2	357.5	356.8	356.0	356.8	357.5	358.2
117.5°	409.3	409.0	408.6	408.3	407.9	407.6	407.2	406.9	407.2	407.6	407.9
120°	443.3	443.0	442.9	442.3	441.4	440.5	439.6	438.6	439.6	440.5	441.4
122.5°	475.7	475.2	474.7	474.3	474.0	473.7	473.4	473.0	473.4	473.7	474.0
125°	525.1	524.9	524.6	524.0	522.9	521.8	520.7	519.6	520.7	521.8	522.9
127.5°	572.6	572.3	572.1	571.7	571.0	570.5	569.8	569.2	569.8	570.5	571.0
130°	604.0	603.6	603.2	602.6	601.7	600.8	599.8	598.9	599.8	600.8	601.7
132.5°	635.3	635.4	635.4	634.7	633.2	631.7	630.1	628.7	630.1	631.7	633.2
135°	681.2	681.0	680.8	680.2	679.1	677.9	676.9	675.7	676.9	677.9	679.1
137.5°	725.9	725.5	725.0	724.3	723.3	722.2	721.1	720.1	721.1	722.2	723.3
140°	754.0	753.4	752.8	752.1	751.2	750.3	749.3	748.4	749.3	750.3	751.2
142.5°	782.1	781.4	780.7	780.0	779.2	778.4	777.6	776.9	777.6	778.4	779.2
145°	823.4	822.8	822.2	821.6	820.8	820.1	819.4	818.6	819.4	820.1	820.8
147.5°	860.2	859.8	859.4	858.9	858.5	858.2	857.8	857.4	857.8	858.2	858.5
150°	884.1	883.4	882.6	882.4	882.6	882.7	883.0	883.1	883.0	882.7	882.6
152.5°	906.1	905.9	905.6	905.3	905.1	904.7	904.5	904.2	904.5	904.7	905.1
155°	937.3	937.1	936.9	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8
157.5°	964.5	964.3	964.2	964.3	964.7	965.1	965.5	965.9	965.5	965.1	964.7
160°	981.0	980.9	980.7	980.9	981.5	981.9	982.5	983.1	982.5	981.9	981.5
162.5°	996.5	996.5	996.5	996.6	997.0	997.4	997.8	998.3	997.8	997.4	997.0
165°	1017.4	1017.2	1017.0	1017.1	1017.5	1017.8	1018.2	1018.6	1018.2	1017.8	1017.5
167.5°	1032.5	1032.5	1032.5	1032.8	1033.6	1034.3	1035.0	1035.8	1035.0	1034.3	1033.6
170°	1041.7	1041.7	1041.7	1042.1	1042.8	1043.6	1044.3	1045.1	1044.3	1043.6	1042.8
172.5°	1048.3	1048.3	1048.3	1048.7	1049.5	1050.2	1050.9	1051.7	1050.9	1050.2	1049.5
175°	1055.7	1055.7	1055.7	1056.1	1056.9	1057.6	1058.3	1059.1	1058.3	1057.6	1056.9
177.5°	1059.9	1060.0	1060.1	1060.5	1061.1	1061.7	1062.3	1062.9	1062.3	1061.7	1061.1
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	5.1	5.4	5.5	6.0	5.9	6.3	6.4	6.4	6.7	6.8	6.8
90°	6.7	8.1	9.4	10.7	11.9	13.2	14.1	15.1	16.0	16.9	17.6
92.5°	24.1	25.4	27.0	28.5	30.2	31.7	32.9	34.2	35.4	36.6	37.3
95°	55.2	56.3	58.1	59.9	61.8	63.6	64.9	66.2	67.4	68.7	69.5
97.5°	89.8	91.2	93.7	96.2	98.7	101.3	102.5	103.7	104.9	106.2	106.8
100°	115.7	116.8	119.2	121.6	124.0	126.4	128.1	129.7	131.3	133.0	134.0
102.5°	147.0	148.0	149.2	150.4	151.6	152.9	154.7	156.5	158.2	160.0	161.2
105°	192.0	193.1	194.1	195.3	196.3	197.5	198.5	199.7	200.7	201.9	202.7
107.5°	240.9	241.8	242.6	243.5	244.3	245.2	245.7	246.3	246.9	247.4	247.7
110°	274.7	275.4	275.9	276.5	277.0	277.6	278.1	278.7	279.2	279.8	280.0



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	307.2	307.9	308.5	309.2	309.9	310.6	310.9	311.1	311.4	311.6	311.6
115°	359.0	359.5	359.9	360.3	360.6	361.0	360.9	360.6	360.4	360.3	360.1
117.5°	408.3	408.6	409.0	409.3	409.6	409.9	410.1	410.2	410.3	410.5	410.2
120°	442.3	442.9	443.0	443.3	443.4	443.6	443.6	443.6	443.6	443.6	443.3
122.5°	474.3	474.7	475.2	475.7	476.2	476.7	476.5	476.4	476.2	476.1	475.7
125°	524.0	524.6	524.9	525.1	525.2	525.4	525.1	524.6	524.3	523.9	523.7
127.5°	571.7	572.1	572.3	572.6	572.7	573.0	572.8	572.6	572.4	572.3	572.0
130°	602.6	603.2	603.6	604.0	604.4	604.7	604.5	604.4	604.1	604.0	603.7
132.5°	634.7	635.4	635.4	635.3	635.2	635.1	635.0	634.7	634.5	634.4	634.1
135°	680.2	680.8	681.0	681.2	681.3	681.5	681.5	681.5	681.5	681.5	681.2
137.5°	724.3	725.0	725.5	725.9	726.3	726.7	726.8	727.1	727.3	727.5	727.2
140°	752.1	752.8	753.4	754.0	754.5	755.0	755.5	755.8	756.2	756.5	756.3
142.5°	780.0	780.7	781.4	782.1	782.8	783.5	783.7	783.9	784.2	784.4	784.0
145°	821.6	822.2	822.8	823.4	823.9	824.4	824.4	824.4	824.4	824.4	824.2
147.5°	858.9	859.4	859.8	860.2	860.7	861.1	861.6	862.0	862.4	862.9	862.5
150°	882.4	882.6	883.4	884.1	884.8	885.6	885.6	885.6	885.6	885.6	885.4
152.5°	905.3	905.6	905.9	906.1	906.4	906.8	907.2	907.6	908.1	908.5	908.4
155°	936.8	936.9	937.1	937.3	937.4	937.7	938.4	939.1	939.9	940.6	940.4
157.5°	964.3	964.2	964.3	964.5	964.7	964.9	965.6	966.4	967.1	967.8	967.6
160°	980.9	980.7	980.9	981.0	981.2	981.5	982.2	982.9	983.7	984.4	984.2
162.5°	996.6	996.5	996.5	996.5	996.6	996.6	997.5	998.4	999.2	1000.1	1000.0
165°	1017.1	1017.0	1017.2	1017.4	1017.6	1017.7	1018.5	1019.2	1019.9	1020.7	1020.5
167.5°	1032.8	1032.5	1032.5	1032.5	1032.5	1032.5	1033.6	1034.7	1035.8	1036.9	1036.9
170°	1042.1	1041.7	1041.7	1041.7	1041.7	1041.7	1042.8	1043.9	1045.1	1046.1	1046.0
172.5°	1048.7	1048.3	1048.3	1048.3	1048.3	1048.3	1049.5	1050.5	1051.7	1052.7	1052.7
175°	1056.1	1055.7	1055.7	1055.7	1055.7	1055.7	1056.9	1057.9	1059.1	1060.2	1060.1
177.5°	1060.5	1060.1	1060.0	1059.9	1059.7	1059.6	1060.5	1061.4	1062.3	1063.1	1063.0
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	7.1	7.1	7.2	7.3	7.2	7.1	7.1	6.8	6.8	6.7	6.4
90°	18.2	18.8	19.2	19.8	19.2	18.8	18.2	17.6	16.9	16.0	15.1
92.5°	37.7	38.2	38.6	39.0	38.6	38.2	37.7	37.3	36.6	35.4	34.2
95°	70.0	70.3	70.7	71.0	70.7	70.3	70.0	69.5	68.7	67.4	66.2
97.5°	107.0	107.3	107.5	107.7	107.5	107.3	107.0	106.8	106.2	104.9	103.7
100°	134.4	134.8	135.1	135.5	135.1	134.8	134.4	134.0	133.0	131.3	129.7
102.5°	161.7	162.2	162.7	163.2	162.7	162.2	161.7	161.2	160.0	158.2	156.5
105°	203.3	203.7	204.3	204.9	204.3	203.7	203.3	202.7	201.9	200.7	199.7
107.5°	247.6	247.6	247.5	247.5	247.5	247.6	247.6	247.7	247.4	246.9	246.3
110°	279.8	279.6	279.4	279.2	279.4	279.6	279.8	280.0	279.8	279.2	278.7



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	311.3	311.0	310.6	310.3	310.6	311.0	311.3	311.6	311.6	311.4	311.1
115°	359.9	359.7	359.5	359.4	359.5	359.7	359.9	360.1	360.3	360.4	360.6
117.5°	409.4	408.7	408.0	407.2	408.0	408.7	409.4	410.2	410.5	410.3	410.2
120°	442.5	441.8	441.1	440.3	441.1	441.8	442.5	443.3	443.6	443.6	443.6
122.5°	475.2	474.5	473.9	473.4	473.9	474.5	475.2	475.7	476.1	476.2	476.4
125°	523.5	523.3	523.1	522.9	523.1	523.3	523.5	523.7	523.9	524.3	524.6
127.5°	571.6	571.3	570.9	570.5	570.9	571.3	571.6	572.0	572.3	572.4	572.6
130°	603.3	603.0	602.6	602.3	602.6	603.0	603.3	603.7	604.0	604.1	604.4
132.5°	633.5	633.0	632.5	631.9	632.5	633.0	633.5	634.1	634.4	634.5	634.7
135°	680.4	679.7	679.0	678.2	679.0	679.7	680.4	681.2	681.5	681.5	681.5
137.5°	726.3	725.4	724.4	723.5	724.4	725.4	726.3	727.2	727.5	727.3	727.1
140°	755.4	754.4	753.5	752.6	753.5	754.4	755.4	756.3	756.5	756.2	755.8
142.5°	783.1	782.2	781.3	780.3	781.3	782.2	783.1	784.0	784.4	784.2	783.9
145°	823.6	823.0	822.6	822.0	822.6	823.0	823.6	824.2	824.4	824.4	824.4
147.5°	861.3	860.0	858.8	857.5	858.8	860.0	861.3	862.5	862.9	862.4	862.0
150°	885.0	884.7	884.3	883.9	884.3	884.7	885.0	885.4	885.6	885.6	885.6
152.5°	907.8	907.1	906.4	905.7	906.4	907.1	907.8	908.4	908.5	908.1	907.6
155°	939.6	938.7	937.8	936.8	937.8	938.7	939.6	940.4	940.6	939.9	939.1
157.5°	966.4	965.2	963.9	962.8	963.9	965.2	966.4	967.6	967.8	967.1	966.4
160°	983.3	982.4	981.5	980.6	981.5	982.4	983.3	984.2	984.4	983.7	982.9
162.5°	999.0	997.9	996.9	995.8	996.9	997.9	999.0	1000.0	1000.1	999.2	998.4
165°	1019.5	1018.3	1017.2	1016.1	1017.2	1018.3	1019.5	1020.5	1020.7	1019.9	1019.2
167.5°	1035.8	1034.6	1033.5	1032.3	1033.5	1034.6	1035.8	1036.9	1036.9	1035.8	1034.7
170°	1044.7	1043.5	1042.2	1040.9	1042.2	1043.5	1044.7	1046.0	1046.1	1045.1	1043.9
172.5°	1051.6	1050.4	1049.3	1048.1	1049.3	1050.4	1051.6	1052.7	1052.7	1051.7	1050.5
175°	1058.8	1057.5	1056.2	1054.9	1056.2	1057.5	1058.8	1060.1	1060.2	1059.1	1057.9
177.5°	1062.0	1060.9	1060.0	1058.9	1060.0	1060.9	1062.0	1063.0	1063.1	1062.3	1061.4
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	6.4	6.3	5.9	6.0	5.5	5.4	5.1	5.0	5.0	5.0	5.0
90°	14.1	13.2	11.9	10.7	9.4	8.1	6.7	5.2	3.8	2.3	0.8
92.5°	32.9	31.7	30.2	28.5	27.0	25.4	24.1	23.1	22.0	21.0	20.0
95°	64.9	63.6	61.8	59.9	58.1	56.3	55.2	54.8	54.5	54.1	53.7
97.5°	102.5	101.3	98.7	96.2	93.7	91.2	89.8	89.7	89.5	89.4	89.2
100°	128.1	126.4	124.0	121.6	119.2	116.8	115.7	115.7	115.7	115.7	115.7
102.5°	154.7	152.9	151.6	150.4	149.2	148.0	147.0	146.3	145.5	144.8	144.1
105°	198.5	197.5	196.3	195.3	194.1	193.1	192.0	191.1	190.2	189.2	188.3
107.5°	245.7	245.2	244.3	243.5	242.6	241.8	240.9	240.0	239.1	238.1	237.3
110°	278.1	277.6	277.0	276.5	275.9	275.4	274.7	273.7	272.8	271.9	270.9



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	310.9	310.6	309.9	309.2	308.5	307.9	307.2	306.8	306.3	305.8	305.3
115°	360.9	361.0	360.6	360.3	359.9	359.5	359.0	358.2	357.5	356.8	356.0
117.5°	410.1	409.9	409.6	409.3	409.0	408.6	408.3	407.9	407.6	407.2	406.9
120°	443.6	443.6	443.4	443.3	443.0	442.9	442.3	441.4	440.5	439.6	438.6
122.5°	476.5	476.7	476.2	475.7	475.2	474.7	474.3	474.0	473.7	473.4	473.0
125°	525.1	525.4	525.2	525.1	524.9	524.6	524.0	522.9	521.8	520.7	519.6
127.5°	572.8	573.0	572.7	572.6	572.3	572.1	571.7	571.0	570.5	569.8	569.2
130°	604.5	604.7	604.4	604.0	603.6	603.2	602.6	601.7	600.8	599.8	598.9
132.5°	635.0	635.1	635.2	635.3	635.4	635.4	634.7	633.2	631.7	630.1	628.7
135°	681.5	681.5	681.3	681.2	681.0	680.8	680.2	679.1	677.9	676.9	675.7
137.5°	726.8	726.7	726.3	725.9	725.5	725.0	724.3	723.3	722.2	721.1	720.1
140°	755.5	755.0	754.5	754.0	753.4	752.8	752.1	751.2	750.3	749.3	748.4
142.5°	783.7	783.5	782.8	782.1	781.4	780.7	780.0	779.2	778.4	777.6	776.9
145°	824.4	824.4	823.9	823.4	822.8	822.2	821.6	820.8	820.1	819.4	818.6
147.5°	861.6	861.1	860.7	860.2	859.8	859.4	858.9	858.5	858.2	857.8	857.4
150°	885.6	885.6	884.8	884.1	883.4	882.6	882.4	882.6	882.7	883.0	883.1
152.5°	907.2	906.8	906.4	906.1	905.9	905.6	905.3	905.1	904.7	904.5	904.2
155°	938.4	937.7	937.4	937.3	937.1	936.9	936.8	936.8	936.8	936.8	936.8
157.5°	965.6	964.9	964.7	964.5	964.3	964.2	964.3	964.7	965.1	965.5	965.9
160°	982.2	981.5	981.2	981.0	980.9	980.7	980.9	981.5	981.9	982.5	983.1
162.5°	997.5	996.6	996.6	996.5	996.5	996.5	996.6	997.0	997.4	997.8	998.3
165°	1018.5	1017.7	1017.6	1017.4	1017.2	1017.0	1017.1	1017.5	1017.8	1018.2	1018.6
167.5°	1033.6	1032.5	1032.5	1032.5	1032.5	1032.5	1032.8	1033.6	1034.3	1035.0	1035.8
170°	1042.8	1041.7	1041.7	1041.7	1041.7	1041.7	1042.1	1042.8	1043.6	1044.3	1045.1
172.5°	1049.5	1048.3	1048.3	1048.3	1048.3	1048.3	1048.7	1049.5	1050.2	1050.9	1051.7
175°	1056.9	1055.7	1055.7	1055.7	1055.7	1055.7	1056.1	1056.9	1057.6	1058.3	1059.1
177.5°	1060.5	1059.6	1059.7	1059.9	1060.0	1060.1	1060.5	1061.1	1061.7	1062.3	1062.9
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	5.1	5.0	4.5	5.0	5.2	5.3	5.6	5.7	5.8	6.0	6.2
90°	2.3	3.8	5.2	6.7	8.1	9.4	10.7	11.9	13.2	14.1	15.1
92.5°	21.0	22.0	23.1	24.1	25.4	27.0	28.5	30.2	31.7	32.9	34.2
95°	54.1	54.5	54.8	55.2	56.3	58.1	59.9	61.8	63.6	64.9	66.2
97.5°	89.4	89.5	89.7	89.8	91.2	93.7	96.2	98.7	101.3	102.5	103.7
100°	115.7	115.7	115.7	115.7	116.8	119.2	121.6	124.0	126.4	128.1	129.7
102.5°	144.8	145.5	146.3	147.0	148.0	149.2	150.4	151.6	152.9	154.7	156.5
105°	189.2	190.2	191.1	192.0	193.1	194.1	195.3	196.3	197.5	198.5	199.7
107.5°	238.1	239.1	240.0	240.9	241.8	242.6	243.5	244.3	245.2	245.7	246.3
110°	271.9	272.8	273.7	274.7	275.4	275.9	276.5	277.0	277.6	278.1	278.7





TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	305.8	306.3	306.8	307.2	307.9	308.5	309.2	309.9	310.6	310.9	311.1
115°	356.8	357.5	358.2	359.0	359.5	359.9	360.3	360.6	361.0	360.9	360.6
117.5°	407.2	407.6	407.9	408.3	408.6	409.0	409.3	409.6	409.9	410.1	410.2
120°	439.6	440.5	441.4	442.3	442.9	443.0	443.3	443.4	443.6	443.6	443.6
122.5°	473.4	473.7	474.0	474.3	474.7	475.2	475.7	476.2	476.7	476.5	476.4
125°	520.7	521.8	522.9	524.0	524.6	524.9	525.1	525.2	525.4	525.1	524.6
127.5°	569.8	570.5	571.0	571.7	572.1	572.3	572.6	572.7	573.0	572.8	572.6
130°	599.8	600.8	601.7	602.6	603.2	603.6	604.0	604.4	604.7	604.5	604.4
132.5°	630.1	631.7	633.2	634.7	635.4	635.4	635.3	635.2	635.1	635.0	634.7
135°	676.9	677.9	679.1	680.2	680.8	681.0	681.2	681.3	681.5	681.5	681.5
137.5°	721.1	722.2	723.3	724.3	725.0	725.5	725.9	726.3	726.7	726.8	727.1
140°	749.3	750.3	751.2	752.1	752.8	753.4	754.0	754.5	755.0	755.5	755.8
142.5°	777.6	778.4	779.2	780.0	780.7	781.4	782.1	782.8	783.5	783.7	783.9
145°	819.4	820.1	820.8	821.6	822.2	822.8	823.4	823.9	824.4	824.4	824.4
147.5°	857.8	858.2	858.5	858.9	859.4	859.8	860.2	860.7	861.1	861.6	862.0
150°	883.0	882.7	882.6	882.4	882.6	883.4	884.1	884.8	885.6	885.6	885.6
152.5°	904.5	904.7	905.1	905.3	905.6	905.9	906.1	906.4	906.8	907.2	907.6
155°	936.8	936.8	936.8	936.8	936.9	937.1	937.3	937.4	937.7	938.4	939.1
157.5°	965.5	965.1	964.7	964.3	964.2	964.3	964.5	964.7	964.9	965.6	966.4
160°	982.5	981.9	981.5	980.9	980.7	980.9	981.0	981.2	981.5	982.2	982.9
162.5°	997.8	997.4	997.0	996.6	996.5	996.5	996.5	996.6	996.6	997.5	998.4
165°	1018.2	1017.8	1017.5	1017.1	1017.0	1017.2	1017.4	1017.6	1017.7	1018.5	1019.2
167.5°	1035.0	1034.3	1033.6	1032.8	1032.5	1032.5	1032.5	1032.5	1032.5	1033.6	1034.7
170°	1044.3	1043.6	1042.8	1042.1	1041.7	1041.7	1041.7	1041.7	1041.7	1042.8	1043.9
172.5°	1050.9	1050.2	1049.5	1048.7	1048.3	1048.3	1048.3	1048.3	1048.3	1049.5	1050.5
175°	1058.3	1057.6	1056.9	1056.1	1055.7	1055.7	1055.7	1055.7	1055.7	1056.9	1057.9
177.5°	1062.3	1061.7	1061.1	1060.5	1060.1	1060.0	1059.9	1059.7	1059.6	1060.5	1061.4
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	6.5	6.8	6.7	6.7	6.8	7.0	7.3
90°	16.0	16.9	17.6	18.2	18.8	19.2	19.8
92.5°	35.4	36.6	37.3	37.7	38.2	38.6	39.0
95°	67.4	68.7	69.5	70.0	70.3	70.7	71.0
97.5°	104.9	106.2	106.8	107.0	107.3	107.5	107.7
100°	131.3	133.0	134.0	134.4	134.8	135.1	135.5
102.5°	158.2	160.0	161.2	161.7	162.2	162.7	163.2
105°	200.7	201.9	202.7	203.3	203.7	204.3	204.9
107.5°	246.9	247.4	247.7	247.6	247.6	247.5	247.5
110°	279.2	279.8	280.0	279.8	279.6	279.4	279.2



TEST NUMBER: P333649-930

CATALOG NUMBER: S125RDIW-S375D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	311.4	311.6	311.6	311.3	311.0	310.6	310.3
115°	360.4	360.3	360.1	359.9	359.7	359.5	359.4
117.5°	410.3	410.5	410.2	409.4	408.7	408.0	407.2
120°	443.6	443.6	443.3	442.5	441.8	441.1	440.3
122.5°	476.2	476.1	475.7	475.2	474.5	473.9	473.4
125°	524.3	523.9	523.7	523.5	523.3	523.1	522.9
127.5°	572.4	572.3	572.0	571.6	571.3	570.9	570.5
130°	604.1	604.0	603.7	603.3	603.0	602.6	602.3
132.5°	634.5	634.4	634.1	633.5	633.0	632.5	631.9
135°	681.5	681.5	681.2	680.4	679.7	679.0	678.2
137.5°	727.3	727.5	727.2	726.3	725.4	724.4	723.5
140°	756.2	756.5	756.3	755.4	754.4	753.5	752.6
142.5°	784.2	784.4	784.0	783.1	782.2	781.3	780.3
145°	824.4	824.4	824.2	823.6	823.0	822.6	822.0
147.5°	862.4	862.9	862.5	861.3	860.0	858.8	857.5
150°	885.6	885.6	885.4	885.0	884.7	884.3	883.9
152.5°	908.1	908.5	908.4	907.8	907.1	906.4	905.7
155°	939.9	940.6	940.4	939.6	938.7	937.8	936.8
157.5°	967.1	967.8	967.6	966.4	965.2	963.9	962.8
160°	983.7	984.4	984.2	983.3	982.4	981.5	980.6
162.5°	999.2	1000.1	1000.0	999.0	997.9	996.9	995.8
165°	1019.9	1020.7	1020.5	1019.5	1018.3	1017.2	1016.1
167.5°	1035.8	1036.9	1036.9	1035.8	1034.6	1033.5	1032.3
170°	1045.1	1046.1	1046.0	1044.7	1043.5	1042.2	1040.9
172.5°	1051.7	1052.7	1052.7	1051.6	1050.4	1049.3	1048.1
175°	1059.1	1060.2	1060.1	1058.8	1057.5	1056.2	1054.9
177.5°	1062.3	1063.1	1063.0	1062.0	1060.9	1060.0	1058.9
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5

(END OF REPORT)