

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333653-930

Luminaire Tested: **S125RDIW-S375D1340U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333653-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1340U930-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4984.1 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	53	47	62	54	47	42	42	37	34	31	28	26	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	20	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	0.9
10°-20°	129.0	2.6
20°-30°	204.5	4.1
30°-40°	246.6	4.9
40°-50°	220.2	4.4
50°-60°	168.9	3.4
60°-70°	109.7	2.2
70°-80°	53.3	1.1
80°-90°	15.7	0.3
90°-100°	91.0	1.8
100°-110°	268.8	5.4
110°-120°	455.3	9.1
120°-130°	599.1	12.0
130°-140°	671.4	13.5
140°-150°	658.0	13.2
150°-160°	552.7	11.1
160°-170°	367.4	7.4
170°-180°	128.6	2.6
0°-30°	377.5	7.6
0°-40°	624.0	12.5
0°-60°	1013.1	20.3
0°-90°	1191.9	23.9
90°-120°	815.1	16.4
90°-150°	2743.6	55.0
90°-180°	3792.0	76.1
0°-180°	4984.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	11
90°	25	1	25	1	25	15
95°	91	69	91	69	91	93
105°	262	241	262	241	262	278
115°	460	456	460	456	460	455
125°	669	665	669	665	669	598
135°	868	865	868	865	868	670
145°	1052	1048	1052	1048	1052	657
155°	1199	1199	1199	1199	1199	552
165°	1301	1304	1301	1304	1301	367
175°	1350	1356	1350	1356	1350	128
180°	1359	1359	1359	1359	1359	



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	8.4	8.1	7.8	7.7	7.7	7.8	7.4	7.0	6.8	6.5	6.4
90°	25.4	24.7	24.0	23.2	22.6	21.6	20.5	19.2	18.1	17.0	15.2
92.5°	49.9	49.4	48.9	48.3	47.9	46.8	45.2	43.7	42.2	40.6	38.6
95°	91.0	90.5	90.0	89.5	89.0	88.1	86.3	84.7	83.1	81.4	79.1
97.5°	137.9	137.6	137.4	137.1	136.8	135.8	134.3	132.7	131.2	129.6	126.5
100°	173.4	173.0	172.5	172.0	171.5	170.2	168.1	166.1	164.0	161.8	158.7
102.5°	209.0	208.3	207.7	207.0	206.4	204.9	202.5	200.2	198.0	195.7	194.1
105°	262.3	261.5	260.9	260.2	259.4	258.4	257.0	255.6	254.2	252.7	251.4
107.5°	316.8	316.9	316.9	317.0	317.1	316.7	316.0	315.3	314.6	313.9	312.8
110°	357.4	357.7	357.9	358.2	358.4	358.2	357.4	356.8	356.0	355.3	354.7



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.2	397.6	398.1	398.5	398.9	398.9	398.6	398.3	397.9	397.6	396.7
115°	460.1	460.3	460.5	460.7	461.0	461.2	461.5	461.7	461.9	462.2	461.7
117.5°	521.4	522.4	523.3	524.2	525.1	525.5	525.3	525.1	525.0	524.8	524.3
120°	563.7	564.6	565.6	566.5	567.4	567.9	567.9	567.9	567.9	567.9	567.7
122.5°	606.0	606.7	607.5	608.2	609.0	609.4	609.7	609.8	610.0	610.3	609.6
125°	669.4	669.7	669.9	670.2	670.4	670.7	671.2	671.6	672.1	672.6	672.4
127.5°	730.3	730.8	731.3	731.8	732.2	732.6	732.8	733.0	733.3	733.5	733.3
130°	770.9	771.4	771.9	772.4	772.8	773.2	773.5	773.6	773.9	774.1	773.6
132.5°	809.0	809.7	810.3	811.1	811.7	812.1	812.4	812.6	812.9	813.1	813.2
135°	868.3	869.2	870.2	871.1	872.0	872.5	872.5	872.5	872.5	872.5	872.3
137.5°	926.3	927.4	928.5	929.8	930.9	931.4	931.1	930.8	930.5	930.3	929.8
140°	963.4	964.7	965.8	966.9	968.2	968.5	968.0	967.6	967.1	966.6	965.9
142.5°	999.0	1000.1	1001.4	1002.5	1003.7	1004.1	1003.9	1003.6	1003.3	1003.0	1002.1
145°	1052.3	1053.0	1053.7	1054.4	1055.1	1055.5	1055.5	1055.5	1055.5	1055.5	1054.8
147.5°	1097.8	1099.3	1101.0	1102.5	1104.2	1104.6	1104.1	1103.5	1103.0	1102.4	1101.9
150°	1131.6	1132.0	1132.5	1133.0	1133.5	1133.8	1133.8	1133.8	1133.8	1133.8	1132.8
152.5°	1159.5	1160.3	1161.2	1162.0	1162.9	1163.0	1162.5	1161.9	1161.4	1160.8	1160.4
155°	1199.3	1200.4	1201.7	1202.8	1204.0	1204.1	1203.1	1202.2	1201.3	1200.4	1200.1
157.5°	1232.5	1234.0	1235.6	1237.1	1238.7	1239.0	1238.0	1237.1	1236.2	1235.3	1235.0
160°	1255.3	1256.5	1257.7	1258.9	1260.0	1260.1	1259.2	1258.3	1257.4	1256.4	1256.1
162.5°	1274.8	1276.2	1277.5	1278.9	1280.3	1280.3	1279.2	1278.1	1277.0	1275.9	1275.8
165°	1300.8	1302.2	1303.7	1305.0	1306.4	1306.7	1305.8	1304.8	1303.9	1302.9	1302.7
167.5°	1321.5	1323.0	1324.5	1325.9	1327.4	1327.4	1326.0	1324.6	1323.1	1321.8	1321.8
170°	1332.5	1334.2	1335.9	1337.5	1339.1	1339.2	1337.8	1336.4	1335.1	1333.6	1333.6
172.5°	1341.8	1343.3	1344.8	1346.2	1347.7	1347.7	1346.3	1344.9	1343.5	1342.1	1342.1
175°	1350.5	1352.2	1353.8	1355.4	1357.1	1357.2	1355.8	1354.4	1353.0	1351.6	1351.6
177.5°	1355.6	1356.9	1358.2	1359.5	1360.9	1361.0	1359.8	1358.7	1357.6	1356.4	1356.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	6.2	5.9	5.7	5.3	4.8	5.2	5.3	5.1	5.1	5.2	5.2
90°	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1	2.9	4.8	6.7
92.5°	36.6	34.6	32.5	30.8	29.5	28.2	26.9	25.6	26.9	28.2	29.5
95°	76.7	74.4	72.1	70.6	70.1	69.7	69.2	68.7	69.2	69.7	70.1
97.5°	123.2	119.9	116.7	115.0	114.8	114.6	114.4	114.2	114.4	114.6	114.8
100°	155.7	152.6	149.6	148.1	148.1	148.1	148.1	148.1	148.1	148.1	148.1
102.5°	192.6	191.0	189.5	188.2	187.3	186.3	185.4	184.4	185.4	186.3	187.3
105°	250.0	248.5	247.1	245.8	244.7	243.4	242.3	241.2	242.3	243.4	244.7
107.5°	311.7	310.6	309.6	308.4	307.3	306.1	304.9	303.7	304.9	306.1	307.3
110°	353.9	353.3	352.5	351.6	350.4	349.3	348.1	346.9	348.1	349.3	350.4



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	395.8	394.9	394.1	393.3	392.7	392.1	391.5	390.9	391.5	392.1	392.7
115°	461.2	460.7	460.3	459.6	458.6	457.7	456.7	455.8	456.7	457.7	458.6
117.5°	523.9	523.5	523.1	522.7	522.2	521.8	521.4	521.0	521.4	521.8	522.2
120°	567.4	567.2	567.0	566.3	565.1	563.9	562.7	561.6	562.7	563.9	565.1
122.5°	609.0	608.4	607.8	607.2	606.8	606.4	606.0	605.6	606.0	606.4	606.8
125°	672.1	671.9	671.6	670.8	669.4	668.1	666.6	665.2	666.6	668.1	669.4
127.5°	733.0	732.7	732.4	731.9	731.1	730.3	729.4	728.6	729.4	730.3	731.1
130°	773.2	772.7	772.3	771.4	770.3	769.1	767.9	766.7	767.9	769.1	770.3
132.5°	813.3	813.3	813.4	812.5	810.6	808.7	806.7	804.8	806.7	808.7	810.6
135°	872.0	871.8	871.6	870.7	869.4	867.9	866.5	865.1	866.5	867.9	869.4
137.5°	929.2	928.7	928.1	927.2	925.9	924.5	923.2	921.8	923.2	924.5	925.9
140°	965.2	964.5	963.8	962.9	961.7	960.5	959.4	958.1	959.4	960.5	961.7
142.5°	1001.2	1000.3	999.4	998.5	997.5	996.5	995.6	994.6	995.6	996.5	997.5
145°	1054.0	1053.4	1052.6	1051.8	1050.8	1049.9	1049.0	1048.1	1049.0	1049.9	1050.8
147.5°	1101.3	1100.7	1100.2	1099.6	1099.1	1098.6	1098.0	1097.6	1098.0	1098.6	1099.1
150°	1131.9	1130.9	1129.9	1129.6	1129.8	1130.1	1130.3	1130.6	1130.3	1130.1	1129.8
152.5°	1160.0	1159.7	1159.3	1158.9	1158.6	1158.3	1158.0	1157.6	1158.0	1158.3	1158.6
155°	1199.9	1199.6	1199.4	1199.3	1199.3	1199.3	1199.3	1199.3	1199.3	1199.3	1199.3
157.5°	1234.8	1234.5	1234.3	1234.4	1234.9	1235.5	1236.0	1236.5	1236.0	1235.5	1234.9
160°	1256.0	1255.7	1255.5	1255.7	1256.4	1257.1	1257.8	1258.5	1257.8	1257.1	1256.4
162.5°	1275.8	1275.7	1275.7	1275.9	1276.4	1276.9	1277.5	1278.0	1277.5	1276.9	1276.4
165°	1302.4	1302.2	1302.0	1302.1	1302.6	1303.0	1303.5	1304.0	1303.5	1303.0	1302.6
167.5°	1321.8	1321.8	1321.8	1322.3	1323.1	1324.1	1325.0	1326.0	1325.0	1324.1	1323.1
170°	1333.6	1333.6	1333.6	1334.1	1335.1	1335.9	1336.9	1337.8	1336.9	1335.9	1335.1
172.5°	1342.1	1342.1	1342.1	1342.6	1343.5	1344.4	1345.3	1346.3	1345.3	1344.4	1343.5
175°	1351.6	1351.6	1351.6	1352.1	1353.0	1354.0	1354.9	1355.8	1354.9	1354.0	1353.0
177.5°	1356.8	1357.0	1357.2	1357.6	1358.5	1359.2	1359.9	1360.7	1359.9	1359.2	1358.5
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	5.5	5.9	6.0	6.6	6.5	7.0	7.3	7.3	7.6	7.8	7.8
90°	8.6	10.4	12.0	13.6	15.2	17.0	18.1	19.2	20.5	21.6	22.6
92.5°	30.8	32.5	34.6	36.6	38.6	40.6	42.2	43.7	45.2	46.8	47.9
95°	70.6	72.1	74.4	76.7	79.1	81.4	83.1	84.7	86.3	88.1	89.0
97.5°	115.0	116.7	119.9	123.2	126.5	129.6	131.2	132.7	134.3	135.8	136.8
100°	148.1	149.6	152.6	155.7	158.7	161.8	164.0	166.1	168.1	170.2	171.5
102.5°	188.2	189.5	191.0	192.6	194.1	195.7	198.0	200.2	202.5	204.9	206.4
105°	245.8	247.1	248.5	250.0	251.4	252.7	254.2	255.6	257.0	258.4	259.4
107.5°	308.4	309.6	310.6	311.7	312.8	313.9	314.6	315.3	316.0	316.7	317.1
110°	351.6	352.5	353.3	353.9	354.7	355.3	356.0	356.8	357.4	358.2	358.4



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	393.3	394.1	394.9	395.8	396.7	397.6	397.9	398.3	398.6	398.9	398.9
115°	459.6	460.3	460.7	461.2	461.7	462.2	461.9	461.7	461.5	461.2	461.0
117.5°	522.7	523.1	523.5	523.9	524.3	524.8	525.0	525.1	525.3	525.5	525.1
120°	566.3	567.0	567.2	567.4	567.7	567.9	567.9	567.9	567.9	567.9	567.4
122.5°	607.2	607.8	608.4	609.0	609.6	610.3	610.0	609.8	609.7	609.4	609.0
125°	670.8	671.6	671.9	672.1	672.4	672.6	672.1	671.6	671.2	670.7	670.4
127.5°	731.9	732.4	732.7	733.0	733.3	733.5	733.3	733.0	732.8	732.6	732.2
130°	771.4	772.3	772.7	773.2	773.6	774.1	773.9	773.6	773.5	773.2	772.8
132.5°	812.5	813.4	813.3	813.3	813.2	813.1	812.9	812.6	812.4	812.1	811.7
135°	870.7	871.6	871.8	872.0	872.3	872.5	872.5	872.5	872.5	872.5	872.0
137.5°	927.2	928.1	928.7	929.2	929.8	930.3	930.5	930.8	931.1	931.4	930.9
140°	962.9	963.8	964.5	965.2	965.9	966.6	967.1	967.6	968.0	968.5	968.2
142.5°	998.5	999.4	1000.3	1001.2	1002.1	1003.0	1003.3	1003.6	1003.9	1004.1	1003.7
145°	1051.8	1052.6	1053.4	1054.0	1054.8	1055.5	1055.5	1055.5	1055.5	1055.5	1055.1
147.5°	1099.6	1100.2	1100.7	1101.3	1101.9	1102.4	1103.0	1103.5	1104.1	1104.6	1104.2
150°	1129.6	1129.9	1130.9	1131.9	1132.8	1133.8	1133.8	1133.8	1133.8	1133.8	1133.5
152.5°	1158.9	1159.3	1159.7	1160.0	1160.4	1160.8	1161.4	1161.9	1162.5	1163.0	1162.9
155°	1199.3	1199.4	1199.6	1199.9	1200.1	1200.4	1201.3	1202.2	1203.1	1204.1	1204.0
157.5°	1234.4	1234.3	1234.5	1234.8	1235.0	1235.3	1236.2	1237.1	1238.0	1239.0	1238.7
160°	1255.7	1255.5	1255.7	1256.0	1256.1	1256.4	1257.4	1258.3	1259.2	1260.1	1260.0
162.5°	1275.9	1275.7	1275.7	1275.8	1275.8	1275.9	1277.0	1278.1	1279.2	1280.3	1280.3
165°	1302.1	1302.0	1302.2	1302.4	1302.7	1302.9	1303.9	1304.8	1305.8	1306.7	1306.4
167.5°	1322.3	1321.8	1321.8	1321.8	1321.8	1321.8	1323.1	1324.6	1326.0	1327.4	1327.4
170°	1334.1	1333.6	1333.6	1333.6	1333.6	1333.6	1335.1	1336.4	1337.8	1339.2	1339.1
172.5°	1342.6	1342.1	1342.1	1342.1	1342.1	1342.1	1343.5	1344.9	1346.3	1347.7	1347.7
175°	1352.1	1351.6	1351.6	1351.6	1351.6	1351.6	1353.0	1354.4	1355.8	1357.2	1357.1
177.5°	1357.6	1357.2	1357.0	1356.8	1356.7	1356.4	1357.6	1358.7	1359.8	1361.0	1360.9
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	8.2	8.1	8.2	8.4	8.2	8.1	8.2	7.8	7.8	7.6	7.3
90°	23.2	24.0	24.7	25.4	24.7	24.0	23.2	22.6	21.6	20.5	19.2
92.5°	48.3	48.9	49.4	49.9	49.4	48.9	48.3	47.9	46.8	45.2	43.7
95°	89.5	90.0	90.5	91.0	90.5	90.0	89.5	89.0	88.1	86.3	84.7
97.5°	137.1	137.4	137.6	137.9	137.6	137.4	137.1	136.8	135.8	134.3	132.7
100°	172.0	172.5	173.0	173.4	173.0	172.5	172.0	171.5	170.2	168.1	166.1
102.5°	207.0	207.7	208.3	209.0	208.3	207.7	207.0	206.4	204.9	202.5	200.2
105°	260.2	260.9	261.5	262.3	261.5	260.9	260.2	259.4	258.4	257.0	255.6
107.5°	317.0	316.9	316.9	316.8	316.9	316.9	317.0	317.1	316.7	316.0	315.3
110°	358.2	357.9	357.7	357.4	357.7	357.9	358.2	358.4	358.2	357.4	356.8



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	398.5	398.1	397.6	397.2	397.6	398.1	398.5	398.9	398.9	398.6	398.3
115°	460.7	460.5	460.3	460.1	460.3	460.5	460.7	461.0	461.2	461.5	461.7
117.5°	524.2	523.3	522.4	521.4	522.4	523.3	524.2	525.1	525.5	525.3	525.1
120°	566.5	565.6	564.6	563.7	564.6	565.6	566.5	567.4	567.9	567.9	567.9
122.5°	608.2	607.5	606.7	606.0	606.7	607.5	608.2	609.0	609.4	609.7	609.8
125°	670.2	669.9	669.7	669.4	669.7	669.9	670.2	670.4	670.7	671.2	671.6
127.5°	731.8	731.3	730.8	730.3	730.8	731.3	731.8	732.2	732.6	732.8	733.0
130°	772.4	771.9	771.4	770.9	771.4	771.9	772.4	772.8	773.2	773.5	773.6
132.5°	811.1	810.3	809.7	809.0	809.7	810.3	811.1	811.7	812.1	812.4	812.6
135°	871.1	870.2	869.2	868.3	869.2	870.2	871.1	872.0	872.5	872.5	872.5
137.5°	929.8	928.5	927.4	926.3	927.4	928.5	929.8	930.9	931.4	931.1	930.8
140°	966.9	965.8	964.7	963.4	964.7	965.8	966.9	968.2	968.5	968.0	967.6
142.5°	1002.5	1001.4	1000.1	999.0	1000.1	1001.4	1002.5	1003.7	1004.1	1003.9	1003.6
145°	1054.4	1053.7	1053.0	1052.3	1053.0	1053.7	1054.4	1055.1	1055.5	1055.5	1055.5
147.5°	1102.5	1101.0	1099.3	1097.8	1099.3	1101.0	1102.5	1104.2	1104.6	1104.1	1103.5
150°	1133.0	1132.5	1132.0	1131.6	1132.0	1132.5	1133.0	1133.5	1133.8	1133.8	1133.8
152.5°	1162.0	1161.2	1160.3	1159.5	1160.3	1161.2	1162.0	1162.9	1163.0	1162.5	1161.9
155°	1202.8	1201.7	1200.4	1199.3	1200.4	1201.7	1202.8	1204.0	1204.1	1203.1	1202.2
157.5°	1237.1	1235.6	1234.0	1232.5	1234.0	1235.6	1237.1	1238.7	1239.0	1238.0	1237.1
160°	1258.9	1257.7	1256.5	1255.3	1256.5	1257.7	1258.9	1260.0	1260.1	1259.2	1258.3
162.5°	1278.9	1277.5	1276.2	1274.8	1276.2	1277.5	1278.9	1280.3	1280.3	1279.2	1278.1
165°	1305.0	1303.7	1302.2	1300.8	1302.2	1303.7	1305.0	1306.4	1306.7	1305.8	1304.8
167.5°	1325.9	1324.5	1323.0	1321.5	1323.0	1324.5	1325.9	1327.4	1327.4	1326.0	1324.6
170°	1337.5	1335.9	1334.2	1332.5	1334.2	1335.9	1337.5	1339.1	1339.2	1337.8	1336.4
172.5°	1346.2	1344.8	1343.3	1341.8	1343.3	1344.8	1346.2	1347.7	1347.7	1346.3	1344.9
175°	1355.4	1353.8	1352.2	1350.5	1352.2	1353.8	1355.4	1357.1	1357.2	1355.8	1354.4
177.5°	1359.5	1358.2	1356.9	1355.6	1356.9	1358.2	1359.5	1360.9	1361.0	1359.8	1358.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	7.3	7.0	6.5	6.6	6.0	5.9	5.5	5.2	5.2	5.1	5.1
90°	18.1	17.0	15.2	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1
92.5°	42.2	40.6	38.6	36.6	34.6	32.5	30.8	29.5	28.2	26.9	25.6
95°	83.1	81.4	79.1	76.7	74.4	72.1	70.6	70.1	69.7	69.2	68.7
97.5°	131.2	129.6	126.5	123.2	119.9	116.7	115.0	114.8	114.6	114.4	114.2
100°	164.0	161.8	158.7	155.7	152.6	149.6	148.1	148.1	148.1	148.1	148.1
102.5°	198.0	195.7	194.1	192.6	191.0	189.5	188.2	187.3	186.3	185.4	184.4
105°	254.2	252.7	251.4	250.0	248.5	247.1	245.8	244.7	243.4	242.3	241.2
107.5°	314.6	313.9	312.8	311.7	310.6	309.6	308.4	307.3	306.1	304.9	303.7
110°	356.0	355.3	354.7	353.9	353.3	352.5	351.6	350.4	349.3	348.1	346.9



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	397.9	397.6	396.7	395.8	394.9	394.1	393.3	392.7	392.1	391.5	390.9
115°	461.9	462.2	461.7	461.2	460.7	460.3	459.6	458.6	457.7	456.7	455.8
117.5°	525.0	524.8	524.3	523.9	523.5	523.1	522.7	522.2	521.8	521.4	521.0
120°	567.9	567.9	567.7	567.4	567.2	567.0	566.3	565.1	563.9	562.7	561.6
122.5°	610.0	610.3	609.6	609.0	608.4	607.8	607.2	606.8	606.4	606.0	605.6
125°	672.1	672.6	672.4	672.1	671.9	671.6	670.8	669.4	668.1	666.6	665.2
127.5°	733.3	733.5	733.3	733.0	732.7	732.4	731.9	731.1	730.3	729.4	728.6
130°	773.9	774.1	773.6	773.2	772.7	772.3	771.4	770.3	769.1	767.9	766.7
132.5°	812.9	813.1	813.2	813.3	813.3	813.4	812.5	810.6	808.7	806.7	804.8
135°	872.5	872.5	872.3	872.0	871.8	871.6	870.7	869.4	867.9	866.5	865.1
137.5°	930.5	930.3	929.8	929.2	928.7	928.1	927.2	925.9	924.5	923.2	921.8
140°	967.1	966.6	965.9	965.2	964.5	963.8	962.9	961.7	960.5	959.4	958.1
142.5°	1003.3	1003.0	1002.1	1001.2	1000.3	999.4	998.5	997.5	996.5	995.6	994.6
145°	1055.5	1055.5	1054.8	1054.0	1053.4	1052.6	1051.8	1050.8	1049.9	1049.0	1048.1
147.5°	1103.0	1102.4	1101.9	1101.3	1100.7	1100.2	1099.6	1099.1	1098.6	1098.0	1097.6
150°	1133.8	1133.8	1132.8	1131.9	1130.9	1129.9	1129.6	1129.8	1130.1	1130.3	1130.6
152.5°	1161.4	1160.8	1160.4	1160.0	1159.7	1159.3	1158.9	1158.6	1158.3	1158.0	1157.6
155°	1201.3	1200.4	1200.1	1199.9	1199.6	1199.4	1199.3	1199.3	1199.3	1199.3	1199.3
157.5°	1236.2	1235.3	1235.0	1234.8	1234.5	1234.3	1234.4	1234.9	1235.5	1236.0	1236.5
160°	1257.4	1256.4	1256.1	1256.0	1255.7	1255.5	1255.7	1256.4	1257.1	1257.8	1258.5
162.5°	1277.0	1275.9	1275.8	1275.8	1275.7	1275.7	1275.9	1276.4	1276.9	1277.5	1278.0
165°	1303.9	1302.9	1302.7	1302.4	1302.2	1302.0	1302.1	1302.6	1303.0	1303.5	1304.0
167.5°	1323.1	1321.8	1321.8	1321.8	1321.8	1321.8	1322.3	1323.1	1324.1	1325.0	1326.0
170°	1335.1	1333.6	1333.6	1333.6	1333.6	1333.6	1334.1	1335.1	1335.9	1336.9	1337.8
172.5°	1343.5	1342.1	1342.1	1342.1	1342.1	1342.1	1342.6	1343.5	1344.4	1345.3	1346.3
175°	1353.0	1351.6	1351.6	1351.6	1351.6	1351.6	1352.1	1353.0	1354.0	1354.9	1355.8
177.5°	1357.6	1356.4	1356.7	1356.8	1357.0	1357.2	1357.6	1358.5	1359.2	1359.9	1360.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	5.3	5.2	4.8	5.3	5.7	5.9	6.2	6.4	6.5	6.8	7.0
90°	2.9	4.8	6.7	8.6	10.4	12.0	13.6	15.2	17.0	18.1	19.2
92.5°	26.9	28.2	29.5	30.8	32.5	34.6	36.6	38.6	40.6	42.2	43.7
95°	69.2	69.7	70.1	70.6	72.1	74.4	76.7	79.1	81.4	83.1	84.7
97.5°	114.4	114.6	114.8	115.0	116.7	119.9	123.2	126.5	129.6	131.2	132.7
100°	148.1	148.1	148.1	148.1	149.6	152.6	155.7	158.7	161.8	164.0	166.1
102.5°	185.4	186.3	187.3	188.2	189.5	191.0	192.6	194.1	195.7	198.0	200.2
105°	242.3	243.4	244.7	245.8	247.1	248.5	250.0	251.4	252.7	254.2	255.6
107.5°	304.9	306.1	307.3	308.4	309.6	310.6	311.7	312.8	313.9	314.6	315.3
110°	348.1	349.3	350.4	351.6	352.5	353.3	353.9	354.7	355.3	356.0	356.8



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	391.5	392.1	392.7	393.3	394.1	394.9	395.8	396.7	397.6	397.9	398.3
115°	456.7	457.7	458.6	459.6	460.3	460.7	461.2	461.7	462.2	461.9	461.7
117.5°	521.4	521.8	522.2	522.7	523.1	523.5	523.9	524.3	524.8	525.0	525.1
120°	562.7	563.9	565.1	566.3	567.0	567.2	567.4	567.7	567.9	567.9	567.9
122.5°	606.0	606.4	606.8	607.2	607.8	608.4	609.0	609.6	610.3	610.0	609.8
125°	666.6	668.1	669.4	670.8	671.6	671.9	672.1	672.4	672.6	672.1	671.6
127.5°	729.4	730.3	731.1	731.9	732.4	732.7	733.0	733.3	733.5	733.3	733.0
130°	767.9	769.1	770.3	771.4	772.3	772.7	773.2	773.6	774.1	773.9	773.6
132.5°	806.7	808.7	810.6	812.5	813.4	813.3	813.3	813.2	813.1	812.9	812.6
135°	866.5	867.9	869.4	870.7	871.6	871.8	872.0	872.3	872.5	872.5	872.5
137.5°	923.2	924.5	925.9	927.2	928.1	928.7	929.2	929.8	930.3	930.5	930.8
140°	959.4	960.5	961.7	962.9	963.8	964.5	965.2	965.9	966.6	967.1	967.6
142.5°	995.6	996.5	997.5	998.5	999.4	1000.3	1001.2	1002.1	1003.0	1003.3	1003.6
145°	1049.0	1049.9	1050.8	1051.8	1052.6	1053.4	1054.0	1054.8	1055.5	1055.5	1055.5
147.5°	1098.0	1098.6	1099.1	1099.6	1100.2	1100.7	1101.3	1101.9	1102.4	1103.0	1103.5
150°	1130.3	1130.1	1129.8	1129.6	1129.9	1130.9	1131.9	1132.8	1133.8	1133.8	1133.8
152.5°	1158.0	1158.3	1158.6	1158.9	1159.3	1159.7	1160.0	1160.4	1160.8	1161.4	1161.9
155°	1199.3	1199.3	1199.3	1199.3	1199.4	1199.6	1199.9	1200.1	1200.4	1201.3	1202.2
157.5°	1236.0	1235.5	1234.9	1234.4	1234.3	1234.5	1234.8	1235.0	1235.3	1236.2	1237.1
160°	1257.8	1257.1	1256.4	1255.7	1255.5	1255.7	1256.0	1256.1	1256.4	1257.4	1258.3
162.5°	1277.5	1276.9	1276.4	1275.9	1275.7	1275.7	1275.8	1275.8	1275.9	1277.0	1278.1
165°	1303.5	1303.0	1302.6	1302.1	1302.0	1302.2	1302.4	1302.7	1302.9	1303.9	1304.8
167.5°	1325.0	1324.1	1323.1	1322.3	1321.8	1321.8	1321.8	1321.8	1321.8	1323.1	1324.6
170°	1336.9	1335.9	1335.1	1334.1	1333.6	1333.6	1333.6	1333.6	1333.6	1335.1	1336.4
172.5°	1345.3	1344.4	1343.5	1342.6	1342.1	1342.1	1342.1	1342.1	1342.1	1343.5	1344.9
175°	1354.9	1354.0	1353.0	1352.1	1351.6	1351.6	1351.6	1351.6	1351.6	1353.0	1354.4
177.5°	1359.9	1359.2	1358.5	1357.6	1357.2	1357.0	1356.8	1356.7	1356.4	1357.6	1358.7
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	7.4	7.8	7.7	7.7	7.8	8.1	8.4
90°	20.5	21.6	22.6	23.2	24.0	24.7	25.4
92.5°	45.2	46.8	47.9	48.3	48.9	49.4	49.9
95°	86.3	88.1	89.0	89.5	90.0	90.5	91.0
97.5°	134.3	135.8	136.8	137.1	137.4	137.6	137.9
100°	168.1	170.2	171.5	172.0	172.5	173.0	173.4
102.5°	202.5	204.9	206.4	207.0	207.7	208.3	209.0
105°	257.0	258.4	259.4	260.2	260.9	261.5	262.3
107.5°	316.0	316.7	317.1	317.0	316.9	316.9	316.8
110°	357.4	358.2	358.4	358.2	357.9	357.7	357.4



TEST NUMBER: P333653-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	398.6	398.9	398.9	398.5	398.1	397.6	397.2
115°	461.5	461.2	461.0	460.7	460.5	460.3	460.1
117.5°	525.3	525.5	525.1	524.2	523.3	522.4	521.4
120°	567.9	567.9	567.4	566.5	565.6	564.6	563.7
122.5°	609.7	609.4	609.0	608.2	607.5	606.7	606.0
125°	671.2	670.7	670.4	670.2	669.9	669.7	669.4
127.5°	732.8	732.6	732.2	731.8	731.3	730.8	730.3
130°	773.5	773.2	772.8	772.4	771.9	771.4	770.9
132.5°	812.4	812.1	811.7	811.1	810.3	809.7	809.0
135°	872.5	872.5	872.0	871.1	870.2	869.2	868.3
137.5°	931.1	931.4	930.9	929.8	928.5	927.4	926.3
140°	968.0	968.5	968.2	966.9	965.8	964.7	963.4
142.5°	1003.9	1004.1	1003.7	1002.5	1001.4	1000.1	999.0
145°	1055.5	1055.5	1055.1	1054.4	1053.7	1053.0	1052.3
147.5°	1104.1	1104.6	1104.2	1102.5	1101.0	1099.3	1097.8
150°	1133.8	1133.8	1133.5	1133.0	1132.5	1132.0	1131.6
152.5°	1162.5	1163.0	1162.9	1162.0	1161.2	1160.3	1159.5
155°	1203.1	1204.1	1204.0	1202.8	1201.7	1200.4	1199.3
157.5°	1238.0	1239.0	1238.7	1237.1	1235.6	1234.0	1232.5
160°	1259.2	1260.1	1260.0	1258.9	1257.7	1256.5	1255.3
162.5°	1279.2	1280.3	1280.3	1278.9	1277.5	1276.2	1274.8
165°	1305.8	1306.7	1306.4	1305.0	1303.7	1302.2	1300.8
167.5°	1326.0	1327.4	1327.4	1325.9	1324.5	1323.0	1321.5
170°	1337.8	1339.2	1339.1	1337.5	1335.9	1334.2	1332.5
172.5°	1346.3	1347.7	1347.7	1346.2	1344.8	1343.3	1341.8
175°	1355.8	1357.2	1357.1	1355.4	1353.8	1352.2	1350.5
177.5°	1359.8	1361.0	1360.9	1359.5	1358.2	1356.9	1355.6
180°	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0	1359.0

(END OF REPORT)