

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333645-930

Luminaire Tested: **S125RDIW-S375D770U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333645-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D770U930-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3360.8 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	79	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	55	49	65	56	50	45	46	41	38	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	39	41	36	32	33	29	26	25	22	20	17
6	61	50	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	29	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.3
10°-20°	129.0	3.8
20°-30°	204.5	6.1
30°-40°	246.6	7.3
40°-50°	220.2	6.6
50°-60°	168.9	5.0
60°-70°	109.7	3.3
70°-80°	53.3	1.6
80°-90°	14.4	0.4
90°-100°	52.1	1.5
100°-110°	153.8	4.6
110°-120°	260.5	7.8
120°-130°	342.9	10.2
130°-140°	384.2	11.4
140°-150°	376.6	11.2
150°-160°	316.3	9.4
160°-170°	210.2	6.3
170°-180°	73.6	2.2
0°-30°	377.5	11.2
0°-40°	624.0	18.6
0°-60°	1013.1	30.1
0°-90°	1190.7	35.4
90°-120°	466.4	13.9
90°-150°	1570.1	46.7
90°-180°	2170.0	64.6
0°-180°	3360.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	10
90°	14	1	14	1	14	9
95°	52	39	52	39	52	53
105°	150	138	150	138	150	159
115°	263	261	263	261	263	260
125°	383	381	383	381	383	342
135°	497	495	497	495	497	383
145°	602	600	602	600	602	376
155°	686	686	686	686	686	316
165°	744	746	744	746	744	210
175°	773	776	773	776	773	73
180°	778	778	778	778	778	



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	6.2	6.0	5.8	5.7	5.7	6.0	5.6	5.4	5.2	5.1	5.1
90°	14.5	14.1	13.7	13.3	12.9	12.4	11.7	11.0	10.4	9.7	8.7
92.5°	28.5	28.3	28.0	27.7	27.4	26.8	25.9	25.0	24.1	23.2	22.1
95°	52.0	51.8	51.5	51.3	51.0	50.4	49.4	48.5	47.5	46.6	45.2
97.5°	78.9	78.8	78.6	78.4	78.3	77.8	76.9	76.0	75.1	74.2	72.3
100°	99.2	99.0	98.7	98.5	98.2	97.4	96.2	95.0	93.8	92.6	90.8
102.5°	119.6	119.2	118.9	118.5	118.1	117.2	115.9	114.6	113.3	111.9	111.0
105°	150.1	149.7	149.3	148.9	148.5	147.9	147.1	146.3	145.4	144.6	143.8
107.5°	181.3	181.3	181.4	181.4	181.4	181.2	180.8	180.4	180.0	179.6	179.0
110°	204.6	204.7	204.8	205.0	205.1	205.0	204.6	204.2	203.7	203.3	202.9



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	227.3	227.6	227.8	228.0	228.3	228.3	228.1	228.0	227.8	227.6	227.1
115°	263.3	263.4	263.6	263.7	263.8	263.9	264.1	264.2	264.3	264.5	264.2
117.5°	298.4	298.9	299.5	300.0	300.5	300.8	300.6	300.5	300.4	300.4	300.1
120°	322.6	323.1	323.7	324.2	324.7	325.0	325.0	325.0	325.0	325.0	324.9
122.5°	346.8	347.2	347.6	348.1	348.5	348.8	348.9	349.0	349.1	349.2	348.9
125°	383.1	383.3	383.4	383.5	383.7	383.8	384.1	384.4	384.7	384.9	384.8
127.5°	418.0	418.2	418.5	418.8	419.1	419.2	419.4	419.6	419.6	419.8	419.6
130°	441.2	441.5	441.7	442.1	442.3	442.5	442.6	442.8	442.9	443.0	442.8
132.5°	463.0	463.4	463.7	464.1	464.5	464.8	464.9	465.0	465.2	465.3	465.4
135°	496.9	497.4	498.0	498.5	499.0	499.3	499.3	499.3	499.3	499.3	499.2
137.5°	530.0	530.8	531.4	532.1	532.7	533.0	532.9	532.7	532.6	532.4	532.1
140°	551.4	552.0	552.7	553.4	554.1	554.2	554.0	553.8	553.4	553.2	552.8
142.5°	571.7	572.3	573.1	573.7	574.4	574.6	574.5	574.3	574.1	574.0	573.5
145°	602.2	602.6	603.0	603.4	603.8	604.1	604.1	604.1	604.1	604.1	603.6
147.5°	628.3	629.2	630.1	631.0	631.9	632.2	631.9	631.5	631.2	630.9	630.6
150°	647.6	647.8	648.2	648.4	648.7	648.8	648.8	648.8	648.8	648.8	648.2
152.5°	663.6	664.1	664.6	665.0	665.5	665.6	665.3	665.0	664.6	664.3	664.1
155°	686.3	687.0	687.7	688.4	689.0	689.1	688.5	688.0	687.5	687.0	686.8
157.5°	705.3	706.2	707.1	708.0	708.9	709.1	708.5	708.0	707.4	706.9	706.8
160°	718.4	719.1	719.7	720.4	721.1	721.1	720.6	720.1	719.6	719.0	718.8
162.5°	729.5	730.3	731.1	731.9	732.7	732.7	732.1	731.5	730.8	730.2	730.1
165°	744.4	745.3	746.1	746.9	747.6	747.8	747.3	746.7	746.2	745.7	745.5
167.5°	756.3	757.2	758.0	758.8	759.6	759.6	758.9	758.1	757.2	756.4	756.4
170°	762.6	763.5	764.5	765.4	766.4	766.5	765.6	764.8	764.0	763.2	763.2
172.5°	767.9	768.7	769.6	770.5	771.3	771.3	770.5	769.6	768.8	768.0	768.0
175°	772.9	773.8	774.8	775.7	776.7	776.7	775.9	775.1	774.3	773.5	773.5
177.5°	775.8	776.6	777.3	778.0	778.8	778.9	778.2	777.6	776.9	776.2	776.4
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	5.1	4.8	4.8	4.6	4.2	4.8	5.0	5.0	4.9	4.8	4.6
90°	7.8	6.8	6.0	4.9	3.8	2.8	1.7	0.6	1.7	2.8	3.8
92.5°	21.0	19.8	18.6	17.7	16.9	16.1	15.4	14.7	15.4	16.1	16.9
95°	43.9	42.6	41.3	40.4	40.1	39.9	39.6	39.4	39.6	39.9	40.1
97.5°	70.5	68.6	66.8	65.8	65.7	65.6	65.5	65.4	65.5	65.6	65.7
100°	89.1	87.3	85.6	84.7	84.7	84.7	84.7	84.7	84.7	84.7	84.7
102.5°	110.2	109.3	108.4	107.7	107.1	106.6	106.1	105.6	106.1	106.6	107.1
105°	143.0	142.3	141.5	140.7	140.0	139.3	138.7	138.0	138.7	139.3	140.0
107.5°	178.4	177.8	177.2	176.5	175.9	175.2	174.5	173.8	174.5	175.2	175.9
110°	202.5	202.1	201.7	201.2	200.6	199.8	199.2	198.5	199.2	199.8	200.6



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	226.6	226.0	225.5	225.1	224.8	224.4	224.0	223.7	224.0	224.4	224.8
115°	263.9	263.7	263.4	263.0	262.4	262.0	261.4	260.9	261.4	262.0	262.4
117.5°	299.9	299.6	299.4	299.1	298.9	298.6	298.4	298.2	298.4	298.6	298.9
120°	324.7	324.6	324.5	324.1	323.4	322.7	322.0	321.4	322.0	322.7	323.4
122.5°	348.5	348.1	347.8	347.6	347.3	347.1	346.8	346.6	346.8	347.1	347.3
125°	384.7	384.5	384.4	383.9	383.1	382.3	381.5	380.7	381.5	382.3	383.1
127.5°	419.5	419.3	419.1	418.8	418.4	417.9	417.4	417.0	417.4	417.9	418.4
130°	442.5	442.2	442.0	441.5	440.8	440.2	439.4	438.8	439.4	440.2	440.8
132.5°	465.4	465.5	465.5	465.0	463.9	462.8	461.7	460.6	461.7	462.8	463.9
135°	499.0	498.9	498.8	498.3	497.5	496.7	495.9	495.0	495.9	496.7	497.5
137.5°	531.7	531.5	531.2	530.7	529.9	529.0	528.3	527.5	528.3	529.0	529.9
140°	552.4	552.0	551.5	551.1	550.3	549.7	549.0	548.4	549.0	549.7	550.3
142.5°	573.0	572.5	571.9	571.4	570.9	570.3	569.7	569.2	569.7	570.3	570.9
145°	603.2	602.8	602.4	601.9	601.4	600.9	600.3	599.8	600.3	600.9	601.4
147.5°	630.2	629.9	629.6	629.3	629.0	628.7	628.4	628.1	628.4	628.7	629.0
150°	647.8	647.2	646.7	646.5	646.6	646.7	646.9	647.0	646.9	646.7	646.6
152.5°	663.9	663.7	663.4	663.2	663.1	662.8	662.7	662.5	662.7	662.8	663.1
155°	686.6	686.6	686.4	686.3	686.3	686.3	686.3	686.3	686.3	686.3	686.3
157.5°	706.6	706.5	706.4	706.5	706.8	707.0	707.4	707.7	707.4	707.0	706.8
160°	718.8	718.6	718.4	718.6	719.0	719.4	719.8	720.2	719.8	719.4	719.0
162.5°	730.1	730.1	730.0	730.2	730.5	730.8	731.1	731.4	731.1	730.8	730.5
165°	745.3	745.3	745.1	745.2	745.4	745.8	746.0	746.2	746.0	745.8	745.4
167.5°	756.4	756.4	756.4	756.7	757.2	757.7	758.3	758.9	758.3	757.7	757.2
170°	763.2	763.2	763.2	763.4	764.0	764.5	765.1	765.6	765.1	764.5	764.0
172.5°	768.0	768.0	768.0	768.3	768.8	769.4	769.9	770.5	769.9	769.4	768.8
175°	773.5	773.5	773.5	773.7	774.3	774.9	775.3	775.9	775.3	774.9	774.3
177.5°	776.5	776.6	776.7	777.0	777.4	777.8	778.3	778.7	778.3	777.8	777.4
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	4.7	5.0	5.0	5.5	5.2	5.5	5.7	5.7	5.8	6.0	5.9
90°	4.9	6.0	6.8	7.8	8.7	9.7	10.4	11.0	11.7	12.4	12.9
92.5°	17.7	18.6	19.8	21.0	22.1	23.2	24.1	25.0	25.9	26.8	27.4
95°	40.4	41.3	42.6	43.9	45.2	46.6	47.5	48.5	49.4	50.4	51.0
97.5°	65.8	66.8	68.6	70.5	72.3	74.2	75.1	76.0	76.9	77.8	78.3
100°	84.7	85.6	87.3	89.1	90.8	92.6	93.8	95.0	96.2	97.4	98.2
102.5°	107.7	108.4	109.3	110.2	111.0	111.9	113.3	114.6	115.9	117.2	118.1
105°	140.7	141.5	142.3	143.0	143.8	144.6	145.4	146.3	147.1	147.9	148.5
107.5°	176.5	177.2	177.8	178.4	179.0	179.6	180.0	180.4	180.8	181.2	181.4
110°	201.2	201.7	202.1	202.5	202.9	203.3	203.7	204.2	204.6	205.0	205.1



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	225.1	225.5	226.0	226.6	227.1	227.6	227.8	228.0	228.1	228.3	228.3
115°	263.0	263.4	263.7	263.9	264.2	264.5	264.3	264.2	264.1	263.9	263.8
117.5°	299.1	299.4	299.6	299.9	300.1	300.4	300.4	300.5	300.6	300.8	300.5
120°	324.1	324.5	324.6	324.7	324.9	325.0	325.0	325.0	325.0	325.0	324.7
122.5°	347.6	347.8	348.1	348.5	348.9	349.2	349.1	349.0	348.9	348.8	348.5
125°	383.9	384.4	384.5	384.7	384.8	384.9	384.7	384.4	384.1	383.8	383.7
127.5°	418.8	419.1	419.3	419.5	419.6	419.8	419.6	419.6	419.4	419.2	419.1
130°	441.5	442.0	442.2	442.5	442.8	443.0	442.9	442.8	442.6	442.5	442.3
132.5°	465.0	465.5	465.5	465.4	465.4	465.3	465.2	465.0	464.9	464.8	464.5
135°	498.3	498.8	498.9	499.0	499.2	499.3	499.3	499.3	499.3	499.3	499.0
137.5°	530.7	531.2	531.5	531.7	532.1	532.4	532.6	532.7	532.9	533.0	532.7
140°	551.1	551.5	552.0	552.4	552.8	553.2	553.4	553.8	554.0	554.2	554.1
142.5°	571.4	571.9	572.5	573.0	573.5	574.0	574.1	574.3	574.5	574.6	574.4
145°	601.9	602.4	602.8	603.2	603.6	604.1	604.1	604.1	604.1	604.1	603.8
147.5°	629.3	629.6	629.9	630.2	630.6	630.9	631.2	631.5	631.9	632.2	631.9
150°	646.5	646.7	647.2	647.8	648.2	648.8	648.8	648.8	648.8	648.8	648.7
152.5°	663.2	663.4	663.7	663.9	664.1	664.3	664.6	665.0	665.3	665.6	665.5
155°	686.3	686.4	686.6	686.6	686.8	687.0	687.5	688.0	688.5	689.1	689.0
157.5°	706.5	706.4	706.5	706.6	706.8	706.9	707.4	708.0	708.5	709.1	708.9
160°	718.6	718.4	718.6	718.8	718.8	719.0	719.6	720.1	720.6	721.1	721.1
162.5°	730.2	730.0	730.1	730.1	730.1	730.2	730.8	731.5	732.1	732.7	732.7
165°	745.2	745.1	745.3	745.3	745.5	745.7	746.2	746.7	747.3	747.8	747.6
167.5°	756.7	756.4	756.4	756.4	756.4	756.4	757.2	758.1	758.9	759.6	759.6
170°	763.4	763.2	763.2	763.2	763.2	763.2	764.0	764.8	765.6	766.5	766.4
172.5°	768.3	768.0	768.0	768.0	768.0	768.0	768.8	769.6	770.5	771.3	771.3
175°	773.7	773.5	773.5	773.5	773.5	773.5	774.3	775.1	775.9	776.7	776.7
177.5°	777.0	776.7	776.6	776.5	776.4	776.2	776.9	777.6	778.2	778.9	778.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	6.1	6.0	6.1	6.2	6.1	6.0	6.1	5.9	6.0	5.8	5.7
90°	13.3	13.7	14.1	14.5	14.1	13.7	13.3	12.9	12.4	11.7	11.0
92.5°	27.7	28.0	28.3	28.5	28.3	28.0	27.7	27.4	26.8	25.9	25.0
95°	51.3	51.5	51.8	52.0	51.8	51.5	51.3	51.0	50.4	49.4	48.5
97.5°	78.4	78.6	78.8	78.9	78.8	78.6	78.4	78.3	77.8	76.9	76.0
100°	98.5	98.7	99.0	99.2	99.0	98.7	98.5	98.2	97.4	96.2	95.0
102.5°	118.5	118.9	119.2	119.6	119.2	118.9	118.5	118.1	117.2	115.9	114.6
105°	148.9	149.3	149.7	150.1	149.7	149.3	148.9	148.5	147.9	147.1	146.3
107.5°	181.4	181.4	181.3	181.3	181.3	181.4	181.4	181.4	181.2	180.8	180.4
110°	205.0	204.8	204.7	204.6	204.7	204.8	205.0	205.1	205.0	204.6	204.2



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	228.0	227.8	227.6	227.3	227.6	227.8	228.0	228.3	228.3	228.1	228.0
115°	263.7	263.6	263.4	263.3	263.4	263.6	263.7	263.8	263.9	264.1	264.2
117.5°	300.0	299.5	298.9	298.4	298.9	299.5	300.0	300.5	300.8	300.6	300.5
120°	324.2	323.7	323.1	322.6	323.1	323.7	324.2	324.7	325.0	325.0	325.0
122.5°	348.1	347.6	347.2	346.8	347.2	347.6	348.1	348.5	348.8	348.9	349.0
125°	383.5	383.4	383.3	383.1	383.3	383.4	383.5	383.7	383.8	384.1	384.4
127.5°	418.8	418.5	418.2	418.0	418.2	418.5	418.8	419.1	419.2	419.4	419.6
130°	442.1	441.7	441.5	441.2	441.5	441.7	442.1	442.3	442.5	442.6	442.8
132.5°	464.1	463.7	463.4	463.0	463.4	463.7	464.1	464.5	464.8	464.9	465.0
135°	498.5	498.0	497.4	496.9	497.4	498.0	498.5	499.0	499.3	499.3	499.3
137.5°	532.1	531.4	530.8	530.0	530.8	531.4	532.1	532.7	533.0	532.9	532.7
140°	553.4	552.7	552.0	551.4	552.0	552.7	553.4	554.1	554.2	554.0	553.8
142.5°	573.7	573.1	572.3	571.7	572.3	573.1	573.7	574.4	574.6	574.5	574.3
145°	603.4	603.0	602.6	602.2	602.6	603.0	603.4	603.8	604.1	604.1	604.1
147.5°	631.0	630.1	629.2	628.3	629.2	630.1	631.0	631.9	632.2	631.9	631.5
150°	648.4	648.2	647.8	647.6	647.8	648.2	648.4	648.7	648.8	648.8	648.8
152.5°	665.0	664.6	664.1	663.6	664.1	664.6	665.0	665.5	665.6	665.3	665.0
155°	688.4	687.7	687.0	686.3	687.0	687.7	688.4	689.0	689.1	688.5	688.0
157.5°	708.0	707.1	706.2	705.3	706.2	707.1	708.0	708.9	709.1	708.5	708.0
160°	720.4	719.7	719.1	718.4	719.1	719.7	720.4	721.1	721.1	720.6	720.1
162.5°	731.9	731.1	730.3	729.5	730.3	731.1	731.9	732.7	732.7	732.1	731.5
165°	746.9	746.1	745.3	744.4	745.3	746.1	746.9	747.6	747.8	747.3	746.7
167.5°	758.8	758.0	757.2	756.3	757.2	758.0	758.8	759.6	759.6	758.9	758.1
170°	765.4	764.5	763.5	762.6	763.5	764.5	765.4	766.4	766.5	765.6	764.8
172.5°	770.5	769.6	768.7	767.9	768.7	769.6	770.5	771.3	771.3	770.5	769.6
175°	775.7	774.8	773.8	772.9	773.8	774.8	775.7	776.7	776.7	775.9	775.1
177.5°	778.0	777.3	776.6	775.8	776.6	777.3	778.0	778.8	778.9	778.2	777.6
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	5.7	5.5	5.2	5.5	5.0	5.0	4.7	4.6	4.8	4.9	5.0
90°	10.4	9.7	8.7	7.8	6.8	6.0	4.9	3.8	2.8	1.7	0.6
92.5°	24.1	23.2	22.1	21.0	19.8	18.6	17.7	16.9	16.1	15.4	14.7
95°	47.5	46.6	45.2	43.9	42.6	41.3	40.4	40.1	39.9	39.6	39.4
97.5°	75.1	74.2	72.3	70.5	68.6	66.8	65.8	65.7	65.6	65.5	65.4
100°	93.8	92.6	90.8	89.1	87.3	85.6	84.7	84.7	84.7	84.7	84.7
102.5°	113.3	111.9	111.0	110.2	109.3	108.4	107.7	107.1	106.6	106.1	105.6
105°	145.4	144.6	143.8	143.0	142.3	141.5	140.7	140.0	139.3	138.7	138.0
107.5°	180.0	179.6	179.0	178.4	177.8	177.2	176.5	175.9	175.2	174.5	173.8
110°	203.7	203.3	202.9	202.5	202.1	201.7	201.2	200.6	199.8	199.2	198.5



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	227.8	227.6	227.1	226.6	226.0	225.5	225.1	224.8	224.4	224.0	223.7
115°	264.3	264.5	264.2	263.9	263.7	263.4	263.0	262.4	262.0	261.4	260.9
117.5°	300.4	300.4	300.1	299.9	299.6	299.4	299.1	298.9	298.6	298.4	298.2
120°	325.0	325.0	324.9	324.7	324.6	324.5	324.1	323.4	322.7	322.0	321.4
122.5°	349.1	349.2	348.9	348.5	348.1	347.8	347.6	347.3	347.1	346.8	346.6
125°	384.7	384.9	384.8	384.7	384.5	384.4	383.9	383.1	382.3	381.5	380.7
127.5°	419.6	419.8	419.6	419.5	419.3	419.1	418.8	418.4	417.9	417.4	417.0
130°	442.9	443.0	442.8	442.5	442.2	442.0	441.5	440.8	440.2	439.4	438.8
132.5°	465.2	465.3	465.4	465.4	465.5	465.5	465.0	463.9	462.8	461.7	460.6
135°	499.3	499.3	499.2	499.0	498.9	498.8	498.3	497.5	496.7	495.9	495.0
137.5°	532.6	532.4	532.1	531.7	531.5	531.2	530.7	529.9	529.0	528.3	527.5
140°	553.4	553.2	552.8	552.4	552.0	551.5	551.1	550.3	549.7	549.0	548.4
142.5°	574.1	574.0	573.5	573.0	572.5	571.9	571.4	570.9	570.3	569.7	569.2
145°	604.1	604.1	603.6	603.2	602.8	602.4	601.9	601.4	600.9	600.3	599.8
147.5°	631.2	630.9	630.6	630.2	629.9	629.6	629.3	629.0	628.7	628.4	628.1
150°	648.8	648.8	648.2	647.8	647.2	646.7	646.5	646.6	646.7	646.9	647.0
152.5°	664.6	664.3	664.1	663.9	663.7	663.4	663.2	663.1	662.8	662.7	662.5
155°	687.5	687.0	686.8	686.6	686.6	686.4	686.3	686.3	686.3	686.3	686.3
157.5°	707.4	706.9	706.8	706.6	706.5	706.4	706.5	706.8	707.0	707.4	707.7
160°	719.6	719.0	718.8	718.8	718.6	718.4	718.6	719.0	719.4	719.8	720.2
162.5°	730.8	730.2	730.1	730.1	730.1	730.0	730.2	730.5	730.8	731.1	731.4
165°	746.2	745.7	745.5	745.3	745.3	745.1	745.2	745.4	745.8	746.0	746.2
167.5°	757.2	756.4	756.4	756.4	756.4	756.4	756.7	757.2	757.7	758.3	758.9
170°	764.0	763.2	763.2	763.2	763.2	763.2	763.4	764.0	764.5	765.1	765.6
172.5°	768.8	768.0	768.0	768.0	768.0	768.0	768.3	768.8	769.4	769.9	770.5
175°	774.3	773.5	773.5	773.5	773.5	773.5	773.7	774.3	774.9	775.3	775.9
177.5°	776.9	776.2	776.4	776.5	776.6	776.7	777.0	777.4	777.8	778.3	778.7
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	5.0	4.8	4.2	4.6	4.8	4.8	5.1	5.1	5.1	5.2	5.4
90°	1.7	2.8	3.8	4.9	6.0	6.8	7.8	8.7	9.7	10.4	11.0
92.5°	15.4	16.1	16.9	17.7	18.6	19.8	21.0	22.1	23.2	24.1	25.0
95°	39.6	39.9	40.1	40.4	41.3	42.6	43.9	45.2	46.6	47.5	48.5
97.5°	65.5	65.6	65.7	65.8	66.8	68.6	70.5	72.3	74.2	75.1	76.0
100°	84.7	84.7	84.7	84.7	85.6	87.3	89.1	90.8	92.6	93.8	95.0
102.5°	106.1	106.6	107.1	107.7	108.4	109.3	110.2	111.0	111.9	113.3	114.6
105°	138.7	139.3	140.0	140.7	141.5	142.3	143.0	143.8	144.6	145.4	146.3
107.5°	174.5	175.2	175.9	176.5	177.2	177.8	178.4	179.0	179.6	180.0	180.4
110°	199.2	199.8	200.6	201.2	201.7	202.1	202.5	202.9	203.3	203.7	204.2



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	224.0	224.4	224.8	225.1	225.5	226.0	226.6	227.1	227.6	227.8	228.0
115°	261.4	262.0	262.4	263.0	263.4	263.7	263.9	264.2	264.5	264.3	264.2
117.5°	298.4	298.6	298.9	299.1	299.4	299.6	299.9	300.1	300.4	300.4	300.5
120°	322.0	322.7	323.4	324.1	324.5	324.6	324.7	324.9	325.0	325.0	325.0
122.5°	346.8	347.1	347.3	347.6	347.8	348.1	348.5	348.9	349.2	349.1	349.0
125°	381.5	382.3	383.1	383.9	384.4	384.5	384.7	384.8	384.9	384.7	384.4
127.5°	417.4	417.9	418.4	418.8	419.1	419.3	419.5	419.6	419.8	419.6	419.6
130°	439.4	440.2	440.8	441.5	442.0	442.2	442.5	442.8	443.0	442.9	442.8
132.5°	461.7	462.8	463.9	465.0	465.5	465.5	465.4	465.4	465.3	465.2	465.0
135°	495.9	496.7	497.5	498.3	498.8	498.9	499.0	499.2	499.3	499.3	499.3
137.5°	528.3	529.0	529.9	530.7	531.2	531.5	531.7	532.1	532.4	532.6	532.7
140°	549.0	549.7	550.3	551.1	551.5	552.0	552.4	552.8	553.2	553.4	553.8
142.5°	569.7	570.3	570.9	571.4	571.9	572.5	573.0	573.5	574.0	574.1	574.3
145°	600.3	600.9	601.4	601.9	602.4	602.8	603.2	603.6	604.1	604.1	604.1
147.5°	628.4	628.7	629.0	629.3	629.6	629.9	630.2	630.6	630.9	631.2	631.5
150°	646.9	646.7	646.6	646.5	646.7	647.2	647.8	648.2	648.8	648.8	648.8
152.5°	662.7	662.8	663.1	663.2	663.4	663.7	663.9	664.1	664.3	664.6	665.0
155°	686.3	686.3	686.3	686.3	686.4	686.6	686.6	686.8	687.0	687.5	688.0
157.5°	707.4	707.0	706.8	706.5	706.4	706.5	706.6	706.8	706.9	707.4	708.0
160°	719.8	719.4	719.0	718.6	718.4	718.6	718.8	718.8	719.0	719.6	720.1
162.5°	731.1	730.8	730.5	730.2	730.0	730.1	730.1	730.1	730.2	730.8	731.5
165°	746.0	745.8	745.4	745.2	745.1	745.3	745.3	745.5	745.7	746.2	746.7
167.5°	758.3	757.7	757.2	756.7	756.4	756.4	756.4	756.4	756.4	757.2	758.1
170°	765.1	764.5	764.0	763.4	763.2	763.2	763.2	763.2	763.2	764.0	764.8
172.5°	769.9	769.4	768.8	768.3	768.0	768.0	768.0	768.0	768.0	768.8	769.6
175°	775.3	774.9	774.3	773.7	773.5	773.5	773.5	773.5	773.5	774.3	775.1
177.5°	778.3	777.8	777.4	777.0	776.7	776.6	776.5	776.4	776.2	776.9	777.6
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	5.6	6.0	5.7	5.7	5.8	6.0	6.2
90°	11.7	12.4	12.9	13.3	13.7	14.1	14.5
92.5°	25.9	26.8	27.4	27.7	28.0	28.3	28.5
95°	49.4	50.4	51.0	51.3	51.5	51.8	52.0
97.5°	76.9	77.8	78.3	78.4	78.6	78.8	78.9
100°	96.2	97.4	98.2	98.5	98.7	99.0	99.2
102.5°	115.9	117.2	118.1	118.5	118.9	119.2	119.6
105°	147.1	147.9	148.5	148.9	149.3	149.7	150.1
107.5°	180.8	181.2	181.4	181.4	181.4	181.3	181.3
110°	204.6	205.0	205.1	205.0	204.8	204.7	204.6



TEST NUMBER: P333645-930

CATALOG NUMBER: S125RDIW-S375D770U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	228.1	228.3	228.3	228.0	227.8	227.6	227.3
115°	264.1	263.9	263.8	263.7	263.6	263.4	263.3
117.5°	300.6	300.8	300.5	300.0	299.5	298.9	298.4
120°	325.0	325.0	324.7	324.2	323.7	323.1	322.6
122.5°	348.9	348.8	348.5	348.1	347.6	347.2	346.8
125°	384.1	383.8	383.7	383.5	383.4	383.3	383.1
127.5°	419.4	419.2	419.1	418.8	418.5	418.2	418.0
130°	442.6	442.5	442.3	442.1	441.7	441.5	441.2
132.5°	464.9	464.8	464.5	464.1	463.7	463.4	463.0
135°	499.3	499.3	499.0	498.5	498.0	497.4	496.9
137.5°	532.9	533.0	532.7	532.1	531.4	530.8	530.0
140°	554.0	554.2	554.1	553.4	552.7	552.0	551.4
142.5°	574.5	574.6	574.4	573.7	573.1	572.3	571.7
145°	604.1	604.1	603.8	603.4	603.0	602.6	602.2
147.5°	631.9	632.2	631.9	631.0	630.1	629.2	628.3
150°	648.8	648.8	648.7	648.4	648.2	647.8	647.6
152.5°	665.3	665.6	665.5	665.0	664.6	664.1	663.6
155°	688.5	689.1	689.0	688.4	687.7	687.0	686.3
157.5°	708.5	709.1	708.9	708.0	707.1	706.2	705.3
160°	720.6	721.1	721.1	720.4	719.7	719.1	718.4
162.5°	732.1	732.7	732.7	731.9	731.1	730.3	729.5
165°	747.3	747.8	747.6	746.9	746.1	745.3	744.4
167.5°	758.9	759.6	759.6	758.8	758.0	757.2	756.3
170°	765.6	766.5	766.4	765.4	764.5	763.5	762.6
172.5°	770.5	771.3	771.3	770.5	769.6	768.7	767.9
175°	775.9	776.7	776.7	775.7	774.8	773.8	772.9
177.5°	778.2	778.9	778.8	778.0	777.3	776.6	775.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7

(END OF REPORT)