

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333669-930

Luminaire Tested: **S125RDIW-S610D1050U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333669-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D1050U930-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4919.2 lumens  
Efficiency: N/A  
Efficacy: 108.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	58	51	46	48	43	39	38	35	32	30	27	26	22
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	25	24	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4873	4873	4873	4873
5°	5606	4879	4309	4879
10°	6431	4854	3802	4854
15°	6946	4804	3380	4804
20°	7659	4746	3120	4746
25°	8863	4670	2895	4670
30°	9645	4589	2748	4589
35°	8136	4495	2613	4495
40°	5681	4326	2496	4326
45°	4215	4098	2382	4098
50°	3361	3861	2284	3861
55°	2852	3567	2197	3567
60°	2465	3304	2056	3304
65°	2196	3020	1771	3020
70°	1930	2766	1613	2766
75°	1669	2395	1515	2395
80°	1268	2016	1268	2016
85°	1060	1586	1193	1586



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	1.5
10°-20°	212.0	4.3
20°-30°	336.2	6.8
30°-40°	405.4	8.2
40°-50°	362.0	7.4
50°-60°	277.6	5.6
60°-70°	180.4	3.7
70°-80°	87.7	1.8
80°-90°	23.3	0.5
90°-100°	71.1	1.4
100°-110°	210.0	4.3
110°-120°	355.6	7.2
120°-130°	468.0	9.5
130°-140°	524.4	10.7
140°-150°	514.0	10.4
150°-160°	431.7	8.8
160°-170°	287.0	5.8
170°-180°	100.4	2.0
0°-30°	620.5	12.6
0°-40°	1025.9	20.9
0°-60°	1665.6	33.9
0°-90°	1957.0	39.8
90°-120°	636.7	12.9
90°-150°	2143.1	43.6
90°-180°	2962.0	60.2
0°-180°	4919.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	754	754	754	754	754	
5°	865	753	665	753	865	86
15°	1039	718	506	718	1039	298
25°	1244	655	406	655	1244	571
35°	1032	570	331	570	1032	623
45°	462	449	261	449	462	368
55°	253	317	195	317	253	230
65°	144	198	116	198	144	143
75°	67	96	61	96	67	71
85°	14	21	16	21	14	17
90°	20	1	20	1	20	12
95°	71	54	71	54	71	72
105°	205	188	205	188	205	217
115°	359	356	359	356	359	355
125°	523	520	523	520	523	467
135°	678	676	678	676	678	523
145°	822	819	822	819	822	513
155°	937	937	937	937	937	431
165°	1016	1019	1016	1019	1016	286
175°	1055	1059	1055	1059	1055	100
180°	1062	1062	1062	1062	1062	



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	793.6	793.1	794.1	791.3	791.7	787.4	787.4	784.2	780.0	776.7	775.3
5°	864.7	865.4	864.1	859.4	856.3	851.7	846.4	837.1	829.4	822.0	816.1
7.5°	937.9	938.3	934.3	932.9	925.0	919.3	907.7	895.0	883.8	869.5	858.7
10°	980.6	980.2	975.9	972.5	965.6	957.0	945.5	930.7	916.7	901.2	886.4
12.5°	1005.3	1004.5	1003.1	999.0	992.7	985.0	975.3	960.7	943.5	926.5	909.2
15°	1038.8	1036.6	1032.6	1027.3	1018.3	1009.3	998.5	985.5	969.1	949.9	933.8
17.5°	1080.1	1080.2	1074.0	1066.7	1054.5	1038.6	1021.9	1000.9	978.6	957.5	940.4
20°	1114.4	1113.4	1107.2	1093.0	1079.0	1059.2	1040.0	1014.3	987.1	959.4	938.1
22.5°	1163.4	1161.0	1154.5	1135.8	1114.2	1088.7	1059.3	1027.9	995.0	963.7	935.6
25°	1243.8	1241.9	1229.2	1207.5	1177.2	1137.8	1099.4	1056.4	1009.0	967.8	933.8
27.5°	1298.8	1296.7	1287.4	1269.3	1241.3	1200.0	1147.9	1090.5	1031.3	974.6	925.4
30°	1293.3	1298.0	1296.7	1288.4	1267.3	1230.1	1182.2	1117.4	1047.1	980.6	922.0
32.5°	1215.5	1219.7	1230.6	1247.0	1248.2	1233.4	1197.5	1137.8	1064.9	989.2	919.2
35°	1031.9	1037.5	1058.6	1091.7	1135.1	1171.3	1178.8	1146.6	1081.2	999.7	915.2
37.5°	793.4	823.9	841.6	876.4	941.9	1008.6	1072.7	1096.3	1068.5	995.4	908.6
40°	673.9	681.3	713.0	752.3	807.4	876.8	968.2	1034.1	1036.2	985.5	898.1
42.5°	576.8	586.2	607.9	639.3	686.5	755.9	850.2	937.3	977.5	958.2	884.5
45°	461.5	468.6	484.4	508.5	544.8	602.1	683.2	783.9	863.8	895.0	848.0
47.5°	379.1	382.9	396.6	415.1	441.9	483.6	546.4	633.8	729.7	796.9	790.3
50°	334.5	338.8	349.4	363.3	385.9	421.2	471.4	544.1	642.9	725.0	741.4
52.5°	299.8	303.4	310.0	323.2	341.8	368.9	409.4	475.3	564.2	651.4	689.4
55°	253.3	255.8	261.1	268.5	283.4	302.9	337.9	383.4	455.3	543.2	599.0
57.5°	215.1	216.3	219.6	226.5	236.8	251.0	276.3	315.0	366.5	445.6	507.2
60°	190.8	192.0	196.3	201.0	209.0	222.1	241.9	268.8	318.4	383.8	446.0
62.5°	171.5	172.2	174.1	178.7	185.7	195.8	211.4	233.4	272.8	330.2	389.0
65°	143.7	144.0	144.6	148.4	152.7	160.1	170.3	185.8	215.6	258.9	311.0
67.5°	117.1	117.5	119.7	121.0	125.5	129.4	135.4	147.2	168.2	197.4	237.8
70°	102.2	101.9	104.0	105.6	107.1	111.8	115.9	125.4	138.4	160.8	194.5
72.5°	88.3	87.6	88.5	89.0	91.1	94.2	98.2	104.1	114.1	129.6	155.3
75°	66.9	67.2	67.2	67.8	69.4	70.6	71.8	74.9	80.6	90.7	104.7
77.5°	47.0	46.5	47.8	47.9	48.8	50.2	51.3	52.5	54.8	59.0	66.2
80°	34.1	34.1	34.4	35.3	35.0	35.6	37.2	38.4	41.2	43.7	46.1
82.5°	26.2	25.9	26.2	26.4	26.3	26.9	27.5	27.7	28.8	30.0	31.8
85°	14.3	14.3	14.6	14.6	14.8	14.8	15.2	15.2	15.2	15.5	15.8
87.5°	9.4	9.0	8.7	8.6	8.7	9.0	8.6	8.2	8.0	7.8	7.8
90°	19.8	19.2	18.8	18.2	17.6	16.9	16.0	15.1	14.1	13.2	11.9
92.5°	39.0	38.6	38.2	37.7	37.3	36.6	35.4	34.2	32.9	31.7	30.2
95°	71.0	70.7	70.3	70.0	69.5	68.7	67.4	66.2	64.9	63.6	61.8
97.5°	107.7	107.5	107.3	107.0	106.8	106.2	104.9	103.7	102.5	101.3	98.7
100°	135.5	135.1	134.8	134.4	134.0	133.0	131.3	129.7	128.1	126.4	124.0
102.5°	163.2	162.7	162.2	161.7	161.2	160.0	158.2	156.5	154.7	152.9	151.6
105°	204.9	204.3	203.7	203.3	202.7	201.9	200.7	199.7	198.5	197.5	196.3
107.5°	247.5	247.5	247.6	247.6	247.7	247.4	246.9	246.3	245.7	245.2	244.3
110°	279.2	279.4	279.6	279.8	280.0	279.8	279.2	278.7	278.1	277.6	277.0



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.3	310.6	311.0	311.3	311.6	311.6	311.4	311.1	310.9	310.6	309.9
115°	359.4	359.5	359.7	359.9	360.1	360.3	360.4	360.6	360.9	361.0	360.6
117.5°	407.2	408.0	408.7	409.4	410.2	410.5	410.3	410.2	410.1	409.9	409.6
120°	440.3	441.1	441.8	442.5	443.3	443.6	443.6	443.6	443.6	443.6	443.4
122.5°	473.4	473.9	474.5	475.2	475.7	476.1	476.2	476.4	476.5	476.7	476.2
125°	522.9	523.1	523.3	523.5	523.7	523.9	524.3	524.6	525.1	525.4	525.2
127.5°	570.5	570.9	571.3	571.6	572.0	572.3	572.4	572.6	572.8	573.0	572.7
130°	602.3	602.6	603.0	603.3	603.7	604.0	604.1	604.4	604.5	604.7	604.4
132.5°	631.9	632.5	633.0	633.5	634.1	634.4	634.5	634.7	635.0	635.1	635.2
135°	678.2	679.0	679.7	680.4	681.2	681.5	681.5	681.5	681.5	681.5	681.3
137.5°	723.5	724.4	725.4	726.3	727.2	727.5	727.3	727.1	726.8	726.7	726.3
140°	752.6	753.5	754.4	755.4	756.3	756.5	756.2	755.8	755.5	755.0	754.5
142.5°	780.3	781.3	782.2	783.1	784.0	784.4	784.2	783.9	783.7	783.5	782.8
145°	822.0	822.6	823.0	823.6	824.2	824.4	824.4	824.4	824.4	824.4	823.9
147.5°	857.5	858.8	860.0	861.3	862.5	862.9	862.4	862.0	861.6	861.1	860.7
150°	883.9	884.3	884.7	885.0	885.4	885.6	885.6	885.6	885.6	885.6	884.8
152.5°	905.7	906.4	907.1	907.8	908.4	908.5	908.1	907.6	907.2	906.8	906.4
155°	936.8	937.8	938.7	939.6	940.4	940.6	939.9	939.1	938.4	937.7	937.4
157.5°	962.8	963.9	965.2	966.4	967.6	967.8	967.1	966.4	965.6	964.9	964.7
160°	980.6	981.5	982.4	983.3	984.2	984.4	983.7	982.9	982.2	981.5	981.2
162.5°	995.8	996.9	997.9	999.0	1000.0	1000.1	999.2	998.4	997.5	996.6	996.6
165°	1016.1	1017.2	1018.3	1019.5	1020.5	1020.7	1019.9	1019.2	1018.5	1017.7	1017.6
167.5°	1032.3	1033.5	1034.6	1035.8	1036.9	1036.9	1035.8	1034.7	1033.6	1032.5	1032.5
170°	1040.9	1042.2	1043.5	1044.7	1046.0	1046.1	1045.1	1043.9	1042.8	1041.7	1041.7
172.5°	1048.1	1049.3	1050.4	1051.6	1052.7	1052.7	1051.7	1050.5	1049.5	1048.3	1048.3
175°	1054.9	1056.2	1057.5	1058.8	1060.1	1060.2	1059.1	1057.9	1056.9	1055.7	1055.7
177.5°	1058.9	1060.0	1060.9	1062.0	1063.0	1063.1	1062.3	1061.4	1060.5	1059.6	1059.7
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	775.3	773.6	770.3	767.4	763.6	760.4	758.1	755.5	752.0	747.8	744.3
5°	809.6	802.7	793.8	786.0	776.2	768.4	760.3	752.6	744.9	734.9	726.3
7.5°	847.6	833.6	819.9	802.7	787.0	773.1	759.7	746.2	732.9	718.8	705.2
10°	870.9	853.9	834.9	813.3	793.4	774.6	757.2	740.2	722.3	706.5	689.4
12.5°	892.7	870.7	849.1	821.7	797.9	774.9	752.8	731.6	712.3	691.9	673.5
15°	912.4	890.7	866.6	833.2	800.0	772.1	746.1	718.5	694.7	671.7	651.3
17.5°	920.0	897.3	869.2	837.1	800.9	765.8	732.3	702.1	674.0	647.3	624.3
20°	917.0	895.0	866.3	835.6	796.9	760.3	724.1	690.6	659.3	631.2	606.7
22.5°	909.9	887.1	859.3	827.0	790.2	751.4	712.7	677.0	644.2	615.1	588.4
25°	899.1	868.1	839.6	808.0	773.1	734.7	694.7	655.3	620.4	590.6	561.5
27.5°	887.9	849.2	813.0	781.5	744.6	710.4	671.8	631.5	594.7	564.4	534.6
30°	877.8	834.4	794.4	758.8	723.8	691.3	654.7	615.4	577.6	546.3	516.0
32.5°	865.1	819.0	775.1	734.0	700.3	668.0	634.9	597.3	560.5	528.2	497.4
35°	849.2	790.4	742.7	699.0	661.5	630.2	600.5	570.1	533.3	499.9	469.9
37.5°	828.4	761.7	706.5	658.8	619.4	587.9	564.5	536.7	503.1	471.1	443.2
40°	815.8	740.9	680.4	633.3	591.8	558.7	536.7	513.1	482.5	452.5	424.6
42.5°	798.9	721.8	654.2	605.1	563.4	531.5	509.2	488.7	462.9	434.6	404.8
45°	765.9	684.8	613.8	561.2	519.1	487.8	467.0	448.7	429.3	403.2	377.2
47.5°	722.9	646.2	571.9	514.5	473.2	444.2	424.0	409.6	395.7	373.6	348.3
50°	688.5	614.5	542.0	486.2	442.3	414.7	395.8	384.3	371.6	351.6	330.4
52.5°	647.8	581.8	510.8	453.8	412.3	386.5	368.3	356.9	346.3	330.0	309.9
55°	583.8	525.9	460.8	409.1	371.0	345.0	327.7	316.8	310.6	296.7	280.9
57.5°	509.9	468.4	411.1	361.2	327.5	301.7	289.1	279.9	272.9	263.0	251.8
60°	458.4	429.3	377.8	330.4	299.5	275.0	263.6	255.8	249.3	240.9	232.3
62.5°	406.1	384.9	340.2	299.5	271.0	250.5	239.8	232.8	225.3	219.6	211.2
65°	336.1	317.2	286.2	254.3	228.0	211.6	203.8	197.6	193.0	186.8	180.8
67.5°	261.4	253.7	232.4	210.3	191.4	176.8	170.2	165.8	160.2	156.5	152.5
70°	215.6	211.8	196.7	182.1	164.4	154.6	148.4	146.5	139.7	136.0	133.1
72.5°	175.0	173.2	164.4	154.3	141.9	133.2	127.5	125.4	121.1	118.1	116.3
75°	119.8	120.5	119.0	112.4	107.8	102.2	97.3	96.0	92.9	90.4	88.9
77.5°	75.8	79.0	79.1	78.8	77.0	73.5	71.5	70.5	67.5	66.6	66.2
80°	52.0	55.4	58.5	58.2	57.6	56.7	55.1	54.2	52.7	51.7	51.1
82.5°	34.7	37.8	40.4	42.2	42.0	41.1	40.0	39.5	39.3	38.6	38.5
85°	16.4	17.0	17.9	20.1	21.7	22.0	21.7	21.4	20.5	20.8	21.0
87.5°	7.8	7.6	7.6	7.3	6.8	7.7	8.2	8.1	7.9	7.7	7.5
90°	10.7	9.4	8.1	6.7	5.2	3.8	2.3	0.8	2.3	3.8	5.2
92.5°	28.5	27.0	25.4	24.1	23.1	22.0	21.0	20.0	21.0	22.0	23.1
95°	59.9	58.1	56.3	55.2	54.8	54.5	54.1	53.7	54.1	54.5	54.8
97.5°	96.2	93.7	91.2	89.8	89.7	89.5	89.4	89.2	89.4	89.5	89.7
100°	121.6	119.2	116.8	115.7	115.7	115.7	115.7	115.7	115.7	115.7	115.7
102.5°	150.4	149.2	148.0	147.0	146.3	145.5	144.8	144.1	144.8	145.5	146.3
105°	195.3	194.1	193.1	192.0	191.1	190.2	189.2	188.3	189.2	190.2	191.1
107.5°	243.5	242.6	241.8	240.9	240.0	239.1	238.1	237.3	238.1	239.1	240.0
110°	276.5	275.9	275.4	274.7	273.7	272.8	271.9	270.9	271.9	272.8	273.7





TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	309.2	308.5	307.9	307.2	306.8	306.3	305.8	305.3	305.8	306.3	306.8
115°	360.3	359.9	359.5	359.0	358.2	357.5	356.8	356.0	356.8	357.5	358.2
117.5°	409.3	409.0	408.6	408.3	407.9	407.6	407.2	406.9	407.2	407.6	407.9
120°	443.3	443.0	442.9	442.3	441.4	440.5	439.6	438.6	439.6	440.5	441.4
122.5°	475.7	475.2	474.7	474.3	474.0	473.7	473.4	473.0	473.4	473.7	474.0
125°	525.1	524.9	524.6	524.0	522.9	521.8	520.7	519.6	520.7	521.8	522.9
127.5°	572.6	572.3	572.1	571.7	571.0	570.5	569.8	569.2	569.8	570.5	571.0
130°	604.0	603.6	603.2	602.6	601.7	600.8	599.8	598.9	599.8	600.8	601.7
132.5°	635.3	635.4	635.4	634.7	633.2	631.7	630.1	628.7	630.1	631.7	633.2
135°	681.2	681.0	680.8	680.2	679.1	677.9	676.9	675.7	676.9	677.9	679.1
137.5°	725.9	725.5	725.0	724.3	723.3	722.2	721.1	720.1	721.1	722.2	723.3
140°	754.0	753.4	752.8	752.1	751.2	750.3	749.3	748.4	749.3	750.3	751.2
142.5°	782.1	781.4	780.7	780.0	779.2	778.4	777.6	776.9	777.6	778.4	779.2
145°	823.4	822.8	822.2	821.6	820.8	820.1	819.4	818.6	819.4	820.1	820.8
147.5°	860.2	859.8	859.4	858.9	858.5	858.2	857.8	857.4	857.8	858.2	858.5
150°	884.1	883.4	882.6	882.4	882.6	882.7	883.0	883.1	883.0	882.7	882.6
152.5°	906.1	905.9	905.6	905.3	905.1	904.7	904.5	904.2	904.5	904.7	905.1
155°	937.3	937.1	936.9	936.8	936.8	936.8	936.8	936.8	936.8	936.8	936.8
157.5°	964.5	964.3	964.2	964.3	964.7	965.1	965.5	965.9	965.5	965.1	964.7
160°	981.0	980.9	980.7	980.9	981.5	981.9	982.5	983.1	982.5	981.9	981.5
162.5°	996.5	996.5	996.5	996.6	997.0	997.4	997.8	998.3	997.8	997.4	997.0
165°	1017.4	1017.2	1017.0	1017.1	1017.5	1017.8	1018.2	1018.6	1018.2	1017.8	1017.5
167.5°	1032.5	1032.5	1032.5	1032.8	1033.6	1034.3	1035.0	1035.8	1035.0	1034.3	1033.6
170°	1041.7	1041.7	1041.7	1042.1	1042.8	1043.6	1044.3	1045.1	1044.3	1043.6	1042.8
172.5°	1048.3	1048.3	1048.3	1048.7	1049.5	1050.2	1050.9	1051.7	1050.9	1050.2	1049.5
175°	1055.7	1055.7	1055.7	1056.1	1056.9	1057.6	1058.3	1059.1	1058.3	1057.6	1056.9
177.5°	1059.9	1060.0	1060.1	1060.5	1061.1	1061.7	1062.3	1062.9	1062.3	1061.7	1061.1
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	741.8	738.3	735.9	730.9	727.4	725.9	723.3	722.5	725.2	723.3	723.0
5°	719.7	710.8	703.7	696.5	688.8	683.9	676.4	675.1	673.3	670.5	669.9
7.5°	693.3	681.6	672.5	660.6	650.4	642.2	632.9	628.5	626.1	622.5	617.7
10°	675.5	661.5	649.1	637.4	624.7	614.5	605.2	598.0	593.4	589.1	587.2
12.5°	657.9	643.7	627.9	613.6	599.4	587.9	577.6	573.0	567.9	562.8	558.5
15°	630.6	611.6	594.4	577.9	565.8	553.4	543.6	536.7	529.0	526.8	518.4
17.5°	601.6	583.0	562.7	545.4	531.5	517.8	507.0	499.2	493.3	485.3	481.5
20°	583.5	561.5	541.7	525.9	510.4	494.3	483.1	476.6	471.1	464.6	461.5
22.5°	564.2	542.7	522.4	503.9	488.1	472.2	464.3	457.5	451.3	445.2	441.2
25°	535.8	514.1	492.8	473.5	457.1	445.6	436.3	428.6	425.3	419.3	415.0
27.5°	507.8	484.7	462.5	443.4	430.5	419.1	411.6	405.4	399.3	394.1	390.4
30°	489.7	466.1	442.0	426.8	413.1	402.4	394.0	388.1	383.4	378.8	376.0
32.5°	471.6	447.3	425.8	409.4	396.6	387.2	378.6	372.9	368.0	362.9	359.6
35°	442.5	417.8	400.5	384.3	371.6	363.0	357.1	349.0	345.0	341.3	337.9
37.5°	415.6	392.6	373.8	359.7	348.7	340.1	332.5	328.1	323.2	319.8	317.0
40°	395.8	374.7	357.8	342.8	334.8	325.2	318.0	312.5	308.8	304.4	301.3
42.5°	378.0	358.4	341.9	328.5	318.5	310.3	303.5	297.9	293.2	290.1	287.5
45°	352.8	333.2	317.2	304.8	295.5	287.7	280.6	277.8	271.6	267.9	266.7
47.5°	326.7	309.2	293.7	282.3	272.7	265.4	258.7	253.1	249.6	246.0	244.0
50°	309.1	292.4	277.8	266.7	257.4	249.3	243.1	239.4	234.7	231.4	228.9
52.5°	291.5	276.0	261.5	250.8	242.7	234.7	227.8	224.0	219.6	217.4	215.7
55°	266.4	250.0	237.6	227.0	218.7	211.2	204.7	201.0	198.2	196.1	195.4
57.5°	237.8	224.9	213.4	203.8	195.2	188.2	182.5	179.0	176.5	176.2	174.3
60°	219.2	207.5	197.0	186.8	179.3	172.8	167.9	163.9	161.3	161.0	160.5
62.5°	200.7	189.4	179.6	170.6	164.0	157.7	153.0	148.5	147.0	145.4	144.1
65°	173.1	162.9	154.8	147.7	140.6	135.3	130.7	127.9	124.5	122.6	119.3
67.5°	146.0	138.1	130.4	124.4	118.8	113.8	110.0	105.8	103.5	102.0	99.5
70°	128.2	122.1	114.3	107.8	103.5	99.4	96.3	91.6	90.1	88.9	87.6
72.5°	111.4	105.9	99.4	94.2	89.8	86.0	82.4	80.3	78.8	77.5	76.7
75°	87.6	82.3	76.8	73.1	70.0	66.9	65.1	63.5	62.9	62.5	61.3
77.5°	64.3	61.6	57.1	54.1	52.1	50.9	49.2	48.3	48.3	47.0	46.6
80°	49.2	47.7	43.9	42.7	41.2	39.9	39.1	37.5	36.0	35.3	34.4
82.5°	36.6	35.1	33.6	31.6	30.3	29.5	28.6	28.0	28.2	27.4	26.9
85°	19.5	17.9	17.4	17.0	16.4	17.0	16.7	16.4	16.1	15.8	16.1
87.5°	7.5	7.8	7.8	8.6	8.1	8.6	8.8	8.7	8.9	9.0	9.0
90°	6.7	8.1	9.4	10.7	11.9	13.2	14.1	15.1	16.0	16.9	17.6
92.5°	24.1	25.4	27.0	28.5	30.2	31.7	32.9	34.2	35.4	36.6	37.3
95°	55.2	56.3	58.1	59.9	61.8	63.6	64.9	66.2	67.4	68.7	69.5
97.5°	89.8	91.2	93.7	96.2	98.7	101.3	102.5	103.7	104.9	106.2	106.8
100°	115.7	116.8	119.2	121.6	124.0	126.4	128.1	129.7	131.3	133.0	134.0
102.5°	147.0	148.0	149.2	150.4	151.6	152.9	154.7	156.5	158.2	160.0	161.2
105°	192.0	193.1	194.1	195.3	196.3	197.5	198.5	199.7	200.7	201.9	202.7
107.5°	240.9	241.8	242.6	243.5	244.3	245.2	245.7	246.3	246.9	247.4	247.7
110°	274.7	275.4	275.9	276.5	277.0	277.6	278.1	278.7	279.2	279.8	280.0



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	307.2	307.9	308.5	309.2	309.9	310.6	310.9	311.1	311.4	311.6	311.6
115°	359.0	359.5	359.9	360.3	360.6	361.0	360.9	360.6	360.4	360.3	360.1
117.5°	408.3	408.6	409.0	409.3	409.6	409.9	410.1	410.2	410.3	410.5	410.2
120°	442.3	442.9	443.0	443.3	443.4	443.6	443.6	443.6	443.6	443.6	443.3
122.5°	474.3	474.7	475.2	475.7	476.2	476.7	476.5	476.4	476.2	476.1	475.7
125°	524.0	524.6	524.9	525.1	525.2	525.4	525.1	524.6	524.3	523.9	523.7
127.5°	571.7	572.1	572.3	572.6	572.7	573.0	572.8	572.6	572.4	572.3	572.0
130°	602.6	603.2	603.6	604.0	604.4	604.7	604.5	604.4	604.1	604.0	603.7
132.5°	634.7	635.4	635.4	635.3	635.2	635.1	635.0	634.7	634.5	634.4	634.1
135°	680.2	680.8	681.0	681.2	681.3	681.5	681.5	681.5	681.5	681.5	681.2
137.5°	724.3	725.0	725.5	725.9	726.3	726.7	726.8	727.1	727.3	727.5	727.2
140°	752.1	752.8	753.4	754.0	754.5	755.0	755.5	755.8	756.2	756.5	756.3
142.5°	780.0	780.7	781.4	782.1	782.8	783.5	783.7	783.9	784.2	784.4	784.0
145°	821.6	822.2	822.8	823.4	823.9	824.4	824.4	824.4	824.4	824.4	824.2
147.5°	858.9	859.4	859.8	860.2	860.7	861.1	861.6	862.0	862.4	862.9	862.5
150°	882.4	882.6	883.4	884.1	884.8	885.6	885.6	885.6	885.6	885.6	885.4
152.5°	905.3	905.6	905.9	906.1	906.4	906.8	907.2	907.6	908.1	908.5	908.4
155°	936.8	936.9	937.1	937.3	937.4	937.7	938.4	939.1	939.9	940.6	940.4
157.5°	964.3	964.2	964.3	964.5	964.7	964.9	965.6	966.4	967.1	967.8	967.6
160°	980.9	980.7	980.9	981.0	981.2	981.5	982.2	982.9	983.7	984.4	984.2
162.5°	996.6	996.5	996.5	996.5	996.6	996.6	997.5	998.4	999.2	1000.1	1000.0
165°	1017.1	1017.0	1017.2	1017.4	1017.6	1017.7	1018.5	1019.2	1019.9	1020.7	1020.5
167.5°	1032.8	1032.5	1032.5	1032.5	1032.5	1032.5	1033.6	1034.7	1035.8	1036.9	1036.9
170°	1042.1	1041.7	1041.7	1041.7	1041.7	1041.7	1042.8	1043.9	1045.1	1046.1	1046.0
172.5°	1048.7	1048.3	1048.3	1048.3	1048.3	1048.3	1049.5	1050.5	1051.7	1052.7	1052.7
175°	1056.1	1055.7	1055.7	1055.7	1055.7	1055.7	1056.9	1057.9	1059.1	1060.2	1060.1
177.5°	1060.5	1060.1	1060.0	1059.9	1059.7	1059.6	1060.5	1061.4	1062.3	1063.1	1063.0
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	722.8	720.0	719.3	720.2	719.3	720.0	722.8	723.0	723.3	725.2	722.5
5°	666.8	663.7	665.3	664.6	665.3	663.7	666.8	669.9	670.5	673.3	675.1
7.5°	617.6	613.8	609.7	611.0	609.7	613.8	617.6	617.7	622.5	626.1	628.5
10°	583.2	580.1	578.2	579.8	578.2	580.1	583.2	587.2	589.1	593.4	598.0
12.5°	554.2	552.4	550.7	550.1	550.7	552.4	554.2	558.5	562.8	567.9	573.0
15°	514.7	511.0	509.5	505.5	509.5	511.0	514.7	518.4	526.8	529.0	536.7
17.5°	478.3	477.1	473.1	471.4	473.1	477.1	478.3	481.5	485.3	493.3	499.2
20°	456.8	455.6	451.6	454.0	451.6	455.6	456.8	461.5	464.6	471.1	476.6
22.5°	439.0	436.3	435.0	434.2	435.0	436.3	439.0	441.2	445.2	451.3	457.5
25°	413.8	409.8	408.2	406.3	408.2	409.8	413.8	415.0	419.3	425.3	428.6
27.5°	388.7	386.5	384.4	383.9	384.4	386.5	388.7	390.4	394.1	399.3	405.4
30°	372.3	370.1	368.5	368.5	368.5	370.1	372.3	376.0	378.8	383.4	388.1
32.5°	357.7	356.0	354.4	354.2	354.4	356.0	357.7	359.6	362.9	368.0	372.9
35°	336.3	333.9	333.2	331.4	333.2	333.9	336.3	337.9	341.3	345.0	349.0
37.5°	314.2	312.2	312.1	311.9	312.1	312.2	314.2	317.0	319.8	323.2	328.1
40°	300.1	298.6	298.2	296.1	298.2	298.6	300.1	301.3	304.4	308.8	312.5
42.5°	285.0	284.2	283.2	282.2	283.2	284.2	285.0	287.5	290.1	293.2	297.9
45°	264.5	262.4	262.4	260.8	262.4	262.4	264.5	266.7	267.9	271.6	277.8
47.5°	243.3	241.7	241.8	240.2	241.8	241.7	243.3	244.0	246.0	249.6	253.1
50°	229.2	228.3	228.0	227.3	228.0	228.3	229.2	228.9	231.4	234.7	239.4
52.5°	215.1	214.7	215.8	214.4	215.8	214.7	215.1	215.7	217.4	219.6	224.0
55°	196.1	195.1	197.0	195.1	197.0	195.1	196.1	195.4	196.1	198.2	201.0
57.5°	174.1	173.3	175.0	174.1	175.0	173.3	174.1	174.3	176.2	176.5	179.0
60°	159.8	157.9	158.9	159.2	158.9	157.9	159.8	160.5	161.0	161.3	163.9
62.5°	142.7	141.6	142.3	140.9	142.3	141.6	142.7	144.1	145.4	147.0	148.5
65°	118.6	117.7	116.4	115.9	116.4	117.7	118.6	119.3	122.6	124.5	127.9
67.5°	99.6	97.4	97.3	97.8	97.3	97.4	99.6	99.5	102.0	103.5	105.8
70°	85.8	85.8	85.4	85.4	85.4	85.8	85.8	87.6	88.9	90.1	91.6
72.5°	76.1	75.9	75.3	75.1	75.3	75.9	76.1	76.7	77.5	78.8	80.3
75°	61.3	61.6	61.0	60.7	61.0	61.6	61.3	61.3	62.5	62.9	63.5
77.5°	45.2	43.9	44.7	43.9	44.7	43.9	45.2	46.6	47.0	48.3	48.3
80°	34.4	34.1	35.0	34.1	35.0	34.1	34.4	34.4	35.3	36.0	37.5
82.5°	27.2	26.9	27.3	26.7	27.3	26.9	27.2	26.9	27.4	28.2	28.0
85°	16.4	16.1	15.8	16.1	15.8	16.1	16.4	16.1	15.8	16.1	16.4
87.5°	9.3	9.2	9.3	9.4	9.3	9.2	9.3	9.0	9.0	8.9	8.7
90°	18.2	18.8	19.2	19.8	19.2	18.8	18.2	17.6	16.9	16.0	15.1
92.5°	37.7	38.2	38.6	39.0	38.6	38.2	37.7	37.3	36.6	35.4	34.2
95°	70.0	70.3	70.7	71.0	70.7	70.3	70.0	69.5	68.7	67.4	66.2
97.5°	107.0	107.3	107.5	107.7	107.5	107.3	107.0	106.8	106.2	104.9	103.7
100°	134.4	134.8	135.1	135.5	135.1	134.8	134.4	134.0	133.0	131.3	129.7
102.5°	161.7	162.2	162.7	163.2	162.7	162.2	161.7	161.2	160.0	158.2	156.5
105°	203.3	203.7	204.3	204.9	204.3	203.7	203.3	202.7	201.9	200.7	199.7
107.5°	247.6	247.6	247.5	247.5	247.5	247.6	247.6	247.7	247.4	246.9	246.3
110°	279.8	279.6	279.4	279.2	279.4	279.6	279.8	280.0	279.8	279.2	278.7



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	311.3	311.0	310.6	310.3	310.6	311.0	311.3	311.6	311.6	311.4	311.1
115°	359.9	359.7	359.5	359.4	359.5	359.7	359.9	360.1	360.3	360.4	360.6
117.5°	409.4	408.7	408.0	407.2	408.0	408.7	409.4	410.2	410.5	410.3	410.2
120°	442.5	441.8	441.1	440.3	441.1	441.8	442.5	443.3	443.6	443.6	443.6
122.5°	475.2	474.5	473.9	473.4	473.9	474.5	475.2	475.7	476.1	476.2	476.4
125°	523.5	523.3	523.1	522.9	523.1	523.3	523.5	523.7	523.9	524.3	524.6
127.5°	571.6	571.3	570.9	570.5	570.9	571.3	571.6	572.0	572.3	572.4	572.6
130°	603.3	603.0	602.6	602.3	602.6	603.0	603.3	603.7	604.0	604.1	604.4
132.5°	633.5	633.0	632.5	631.9	632.5	633.0	633.5	634.1	634.4	634.5	634.7
135°	680.4	679.7	679.0	678.2	679.0	679.7	680.4	681.2	681.5	681.5	681.5
137.5°	726.3	725.4	724.4	723.5	724.4	725.4	726.3	727.2	727.5	727.3	727.1
140°	755.4	754.4	753.5	752.6	753.5	754.4	755.4	756.3	756.5	756.2	755.8
142.5°	783.1	782.2	781.3	780.3	781.3	782.2	783.1	784.0	784.4	784.2	783.9
145°	823.6	823.0	822.6	822.0	822.6	823.0	823.6	824.2	824.4	824.4	824.4
147.5°	861.3	860.0	858.8	857.5	858.8	860.0	861.3	862.5	862.9	862.4	862.0
150°	885.0	884.7	884.3	883.9	884.3	884.7	885.0	885.4	885.6	885.6	885.6
152.5°	907.8	907.1	906.4	905.7	906.4	907.1	907.8	908.4	908.5	908.1	907.6
155°	939.6	938.7	937.8	936.8	937.8	938.7	939.6	940.4	940.6	939.9	939.1
157.5°	966.4	965.2	963.9	962.8	963.9	965.2	966.4	967.6	967.8	967.1	966.4
160°	983.3	982.4	981.5	980.6	981.5	982.4	983.3	984.2	984.4	983.7	982.9
162.5°	999.0	997.9	996.9	995.8	996.9	997.9	999.0	1000.0	1000.1	999.2	998.4
165°	1019.5	1018.3	1017.2	1016.1	1017.2	1018.3	1019.5	1020.5	1020.7	1019.9	1019.2
167.5°	1035.8	1034.6	1033.5	1032.3	1033.5	1034.6	1035.8	1036.9	1036.9	1035.8	1034.7
170°	1044.7	1043.5	1042.2	1040.9	1042.2	1043.5	1044.7	1046.0	1046.1	1045.1	1043.9
172.5°	1051.6	1050.4	1049.3	1048.1	1049.3	1050.4	1051.6	1052.7	1052.7	1051.7	1050.5
175°	1058.8	1057.5	1056.2	1054.9	1056.2	1057.5	1058.8	1060.1	1060.2	1059.1	1057.9
177.5°	1062.0	1060.9	1060.0	1058.9	1060.0	1060.9	1062.0	1063.0	1063.1	1062.3	1061.4
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	723.3	725.9	727.4	730.9	735.9	738.3	741.8	744.3	747.8	752.0	755.5
5°	676.4	683.9	688.8	696.5	703.7	710.8	719.7	726.3	734.9	744.9	752.6
7.5°	632.9	642.2	650.4	660.6	672.5	681.6	693.3	705.2	718.8	732.9	746.2
10°	605.2	614.5	624.7	637.4	649.1	661.5	675.5	689.4	706.5	722.3	740.2
12.5°	577.6	587.9	599.4	613.6	627.9	643.7	657.9	673.5	691.9	712.3	731.6
15°	543.6	553.4	565.8	577.9	594.4	611.6	630.6	651.3	671.7	694.7	718.5
17.5°	507.0	517.8	531.5	545.4	562.7	583.0	601.6	624.3	647.3	674.0	702.1
20°	483.1	494.3	510.4	525.9	541.7	561.5	583.5	606.7	631.2	659.3	690.6
22.5°	464.3	472.2	488.1	503.9	522.4	542.7	564.2	588.4	615.1	644.2	677.0
25°	436.3	445.6	457.1	473.5	492.8	514.1	535.8	561.5	590.6	620.4	655.3
27.5°	411.6	419.1	430.5	443.4	462.5	484.7	507.8	534.6	564.4	594.7	631.5
30°	394.0	402.4	413.1	426.8	442.0	466.1	489.7	516.0	546.3	577.6	615.4
32.5°	378.6	387.2	396.6	409.4	425.8	447.3	471.6	497.4	528.2	560.5	597.3
35°	357.1	363.0	371.6	384.3	400.5	417.8	442.5	469.9	499.9	533.3	570.1
37.5°	332.5	340.1	348.7	359.7	373.8	392.6	415.6	443.2	471.1	503.1	536.7
40°	318.0	325.2	334.8	342.8	357.8	374.7	395.8	424.6	452.5	482.5	513.1
42.5°	303.5	310.3	318.5	328.5	341.9	358.4	378.0	404.8	434.6	462.9	488.7
45°	280.6	287.7	295.5	304.8	317.2	333.2	352.8	377.2	403.2	429.3	448.7
47.5°	258.7	265.4	272.7	282.3	293.7	309.2	326.7	348.3	373.6	395.7	409.6
50°	243.1	249.3	257.4	266.7	277.8	292.4	309.1	330.4	351.6	371.6	384.3
52.5°	227.8	234.7	242.7	250.8	261.5	276.0	291.5	309.9	330.0	346.3	356.9
55°	204.7	211.2	218.7	227.0	237.6	250.0	266.4	280.9	296.7	310.6	316.8
57.5°	182.5	188.2	195.2	203.8	213.4	224.9	237.8	251.8	263.0	272.9	279.9
60°	167.9	172.8	179.3	186.8	197.0	207.5	219.2	232.3	240.9	249.3	255.8
62.5°	153.0	157.7	164.0	170.6	179.6	189.4	200.7	211.2	219.6	225.3	232.8
65°	130.7	135.3	140.6	147.7	154.8	162.9	173.1	180.8	186.8	193.0	197.6
67.5°	110.0	113.8	118.8	124.4	130.4	138.1	146.0	152.5	156.5	160.2	165.8
70°	96.3	99.4	103.5	107.8	114.3	122.1	128.2	133.1	136.0	139.7	146.5
72.5°	82.4	86.0	89.8	94.2	99.4	105.9	111.4	116.3	118.1	121.1	125.4
75°	65.1	66.9	70.0	73.1	76.8	82.3	87.6	88.9	90.4	92.9	96.0
77.5°	49.2	50.9	52.1	54.1	57.1	61.6	64.3	66.2	66.6	67.5	70.5
80°	39.1	39.9	41.2	42.7	43.9	47.7	49.2	51.1	51.7	52.7	54.2
82.5°	28.6	29.5	30.3	31.6	33.6	35.1	36.6	38.5	38.6	39.3	39.5
85°	16.7	17.0	16.4	17.0	17.4	17.9	19.5	21.0	20.8	20.5	21.4
87.5°	8.8	8.6	8.1	8.6	7.8	7.8	7.5	7.5	7.7	7.9	8.1
90°	14.1	13.2	11.9	10.7	9.4	8.1	6.7	5.2	3.8	2.3	0.8
92.5°	32.9	31.7	30.2	28.5	27.0	25.4	24.1	23.1	22.0	21.0	20.0
95°	64.9	63.6	61.8	59.9	58.1	56.3	55.2	54.8	54.5	54.1	53.7
97.5°	102.5	101.3	98.7	96.2	93.7	91.2	89.8	89.7	89.5	89.4	89.2
100°	128.1	126.4	124.0	121.6	119.2	116.8	115.7	115.7	115.7	115.7	115.7
102.5°	154.7	152.9	151.6	150.4	149.2	148.0	147.0	146.3	145.5	144.8	144.1
105°	198.5	197.5	196.3	195.3	194.1	193.1	192.0	191.1	190.2	189.2	188.3
107.5°	245.7	245.2	244.3	243.5	242.6	241.8	240.9	240.0	239.1	238.1	237.3
110°	278.1	277.6	277.0	276.5	275.9	275.4	274.7	273.7	272.8	271.9	270.9



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	310.9	310.6	309.9	309.2	308.5	307.9	307.2	306.8	306.3	305.8	305.3
115°	360.9	361.0	360.6	360.3	359.9	359.5	359.0	358.2	357.5	356.8	356.0
117.5°	410.1	409.9	409.6	409.3	409.0	408.6	408.3	407.9	407.6	407.2	406.9
120°	443.6	443.6	443.4	443.3	443.0	442.9	442.3	441.4	440.5	439.6	438.6
122.5°	476.5	476.7	476.2	475.7	475.2	474.7	474.3	474.0	473.7	473.4	473.0
125°	525.1	525.4	525.2	525.1	524.9	524.6	524.0	522.9	521.8	520.7	519.6
127.5°	572.8	573.0	572.7	572.6	572.3	572.1	571.7	571.0	570.5	569.8	569.2
130°	604.5	604.7	604.4	604.0	603.6	603.2	602.6	601.7	600.8	599.8	598.9
132.5°	635.0	635.1	635.2	635.3	635.4	635.4	634.7	633.2	631.7	630.1	628.7
135°	681.5	681.5	681.3	681.2	681.0	680.8	680.2	679.1	677.9	676.9	675.7
137.5°	726.8	726.7	726.3	725.9	725.5	725.0	724.3	723.3	722.2	721.1	720.1
140°	755.5	755.0	754.5	754.0	753.4	752.8	752.1	751.2	750.3	749.3	748.4
142.5°	783.7	783.5	782.8	782.1	781.4	780.7	780.0	779.2	778.4	777.6	776.9
145°	824.4	824.4	823.9	823.4	822.8	822.2	821.6	820.8	820.1	819.4	818.6
147.5°	861.6	861.1	860.7	860.2	859.8	859.4	858.9	858.5	858.2	857.8	857.4
150°	885.6	885.6	884.8	884.1	883.4	882.6	882.4	882.6	882.7	883.0	883.1
152.5°	907.2	906.8	906.4	906.1	905.9	905.6	905.3	905.1	904.7	904.5	904.2
155°	938.4	937.7	937.4	937.3	937.1	936.9	936.8	936.8	936.8	936.8	936.8
157.5°	965.6	964.9	964.7	964.5	964.3	964.2	964.3	964.7	965.1	965.5	965.9
160°	982.2	981.5	981.2	981.0	980.9	980.7	980.9	981.5	981.9	982.5	983.1
162.5°	997.5	996.6	996.6	996.5	996.5	996.5	996.6	997.0	997.4	997.8	998.3
165°	1018.5	1017.7	1017.6	1017.4	1017.2	1017.0	1017.1	1017.5	1017.8	1018.2	1018.6
167.5°	1033.6	1032.5	1032.5	1032.5	1032.5	1032.5	1032.8	1033.6	1034.3	1035.0	1035.8
170°	1042.8	1041.7	1041.7	1041.7	1041.7	1041.7	1042.1	1042.8	1043.6	1044.3	1045.1
172.5°	1049.5	1048.3	1048.3	1048.3	1048.3	1048.3	1048.7	1049.5	1050.2	1050.9	1051.7
175°	1056.9	1055.7	1055.7	1055.7	1055.7	1055.7	1056.1	1056.9	1057.6	1058.3	1059.1
177.5°	1060.5	1059.6	1059.7	1059.9	1060.0	1060.1	1060.5	1061.1	1061.7	1062.3	1062.9
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	758.1	760.4	763.6	767.4	770.3	773.6	775.3	775.3	776.7	780.0	784.2
5°	760.3	768.4	776.2	786.0	793.8	802.7	809.6	816.1	822.0	829.4	837.1
7.5°	759.7	773.1	787.0	802.7	819.9	833.6	847.6	858.7	869.5	883.8	895.0
10°	757.2	774.6	793.4	813.3	834.9	853.9	870.9	886.4	901.2	916.7	930.7
12.5°	752.8	774.9	797.9	821.7	849.1	870.7	892.7	909.2	926.5	943.5	960.7
15°	746.1	772.1	800.0	833.2	866.6	890.7	912.4	933.8	949.9	969.1	985.5
17.5°	732.3	765.8	800.9	837.1	869.2	897.3	920.0	940.4	957.5	978.6	1000.9
20°	724.1	760.3	796.9	835.6	866.3	895.0	917.0	938.1	959.4	987.1	1014.3
22.5°	712.7	751.4	790.2	827.0	859.3	887.1	909.9	935.6	963.7	995.0	1027.9
25°	694.7	734.7	773.1	808.0	839.6	868.1	899.1	933.8	967.8	1009.0	1056.4
27.5°	671.8	710.4	744.6	781.5	813.0	849.2	887.9	925.4	974.6	1031.3	1090.5
30°	654.7	691.3	723.8	758.8	794.4	834.4	877.8	922.0	980.6	1047.1	1117.4
32.5°	634.9	668.0	700.3	734.0	775.1	819.0	865.1	919.2	989.2	1064.9	1137.8
35°	600.5	630.2	661.5	699.0	742.7	790.4	849.2	915.2	999.7	1081.2	1146.6
37.5°	564.5	587.9	619.4	658.8	706.5	761.7	828.4	908.6	995.4	1068.5	1096.3
40°	536.7	558.7	591.8	633.3	680.4	740.9	815.8	898.1	985.5	1036.2	1034.1
42.5°	509.2	531.5	563.4	605.1	654.2	721.8	798.9	884.5	958.2	977.5	937.3
45°	467.0	487.8	519.1	561.2	613.8	684.8	765.9	848.0	895.0	863.8	783.9
47.5°	424.0	444.2	473.2	514.5	571.9	646.2	722.9	790.3	796.9	729.7	633.8
50°	395.8	414.7	442.3	486.2	542.0	614.5	688.5	741.4	725.0	642.9	544.1
52.5°	368.3	386.5	412.3	453.8	510.8	581.8	647.8	689.4	651.4	564.2	475.3
55°	327.7	345.0	371.0	409.1	460.8	525.9	583.8	599.0	543.2	455.3	383.4
57.5°	289.1	301.7	327.5	361.2	411.1	468.4	509.9	507.2	445.6	366.5	315.0
60°	263.6	275.0	299.5	330.4	377.8	429.3	458.4	446.0	383.8	318.4	268.8
62.5°	239.8	250.5	271.0	299.5	340.2	384.9	406.1	389.0	330.2	272.8	233.4
65°	203.8	211.6	228.0	254.3	286.2	317.2	336.1	311.0	258.9	215.6	185.8
67.5°	170.2	176.8	191.4	210.3	232.4	253.7	261.4	237.8	197.4	168.2	147.2
70°	148.4	154.6	164.4	182.1	196.7	211.8	215.6	194.5	160.8	138.4	125.4
72.5°	127.5	133.2	141.9	154.3	164.4	173.2	175.0	155.3	129.6	114.1	104.1
75°	97.3	102.2	107.8	112.4	119.0	120.5	119.8	104.7	90.7	80.6	74.9
77.5°	71.5	73.5	77.0	78.8	79.1	79.0	75.8	66.2	59.0	54.8	52.5
80°	55.1	56.7	57.6	58.2	58.5	55.4	52.0	46.1	43.7	41.2	38.4
82.5°	40.0	41.1	42.0	42.2	40.4	37.8	34.7	31.8	30.0	28.8	27.7
85°	21.7	22.0	21.7	20.1	17.9	17.0	16.4	15.8	15.5	15.2	15.2
87.5°	8.2	7.7	6.8	7.3	7.6	7.6	7.8	7.8	7.8	8.0	8.2
90°	2.3	3.8	5.2	6.7	8.1	9.4	10.7	11.9	13.2	14.1	15.1
92.5°	21.0	22.0	23.1	24.1	25.4	27.0	28.5	30.2	31.7	32.9	34.2
95°	54.1	54.5	54.8	55.2	56.3	58.1	59.9	61.8	63.6	64.9	66.2
97.5°	89.4	89.5	89.7	89.8	91.2	93.7	96.2	98.7	101.3	102.5	103.7
100°	115.7	115.7	115.7	115.7	116.8	119.2	121.6	124.0	126.4	128.1	129.7
102.5°	144.8	145.5	146.3	147.0	148.0	149.2	150.4	151.6	152.9	154.7	156.5
105°	189.2	190.2	191.1	192.0	193.1	194.1	195.3	196.3	197.5	198.5	199.7
107.5°	238.1	239.1	240.0	240.9	241.8	242.6	243.5	244.3	245.2	245.7	246.3
110°	271.9	272.8	273.7	274.7	275.4	275.9	276.5	277.0	277.6	278.1	278.7





TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	305.8	306.3	306.8	307.2	307.9	308.5	309.2	309.9	310.6	310.9	311.1
115°	356.8	357.5	358.2	359.0	359.5	359.9	360.3	360.6	361.0	360.9	360.6
117.5°	407.2	407.6	407.9	408.3	408.6	409.0	409.3	409.6	409.9	410.1	410.2
120°	439.6	440.5	441.4	442.3	442.9	443.0	443.3	443.4	443.6	443.6	443.6
122.5°	473.4	473.7	474.0	474.3	474.7	475.2	475.7	476.2	476.7	476.5	476.4
125°	520.7	521.8	522.9	524.0	524.6	524.9	525.1	525.2	525.4	525.1	524.6
127.5°	569.8	570.5	571.0	571.7	572.1	572.3	572.6	572.7	573.0	572.8	572.6
130°	599.8	600.8	601.7	602.6	603.2	603.6	604.0	604.4	604.7	604.5	604.4
132.5°	630.1	631.7	633.2	634.7	635.4	635.4	635.3	635.2	635.1	635.0	634.7
135°	676.9	677.9	679.1	680.2	680.8	681.0	681.2	681.3	681.5	681.5	681.5
137.5°	721.1	722.2	723.3	724.3	725.0	725.5	725.9	726.3	726.7	726.8	727.1
140°	749.3	750.3	751.2	752.1	752.8	753.4	754.0	754.5	755.0	755.5	755.8
142.5°	777.6	778.4	779.2	780.0	780.7	781.4	782.1	782.8	783.5	783.7	783.9
145°	819.4	820.1	820.8	821.6	822.2	822.8	823.4	823.9	824.4	824.4	824.4
147.5°	857.8	858.2	858.5	858.9	859.4	859.8	860.2	860.7	861.1	861.6	862.0
150°	883.0	882.7	882.6	882.4	882.6	883.4	884.1	884.8	885.6	885.6	885.6
152.5°	904.5	904.7	905.1	905.3	905.6	905.9	906.1	906.4	906.8	907.2	907.6
155°	936.8	936.8	936.8	936.8	936.9	937.1	937.3	937.4	937.7	938.4	939.1
157.5°	965.5	965.1	964.7	964.3	964.2	964.3	964.5	964.7	964.9	965.6	966.4
160°	982.5	981.9	981.5	980.9	980.7	980.9	981.0	981.2	981.5	982.2	982.9
162.5°	997.8	997.4	997.0	996.6	996.5	996.5	996.5	996.6	996.6	997.5	998.4
165°	1018.2	1017.8	1017.5	1017.1	1017.0	1017.2	1017.4	1017.6	1017.7	1018.5	1019.2
167.5°	1035.0	1034.3	1033.6	1032.8	1032.5	1032.5	1032.5	1032.5	1032.5	1033.6	1034.7
170°	1044.3	1043.6	1042.8	1042.1	1041.7	1041.7	1041.7	1041.7	1041.7	1042.8	1043.9
172.5°	1050.9	1050.2	1049.5	1048.7	1048.3	1048.3	1048.3	1048.3	1048.3	1049.5	1050.5
175°	1058.3	1057.6	1056.9	1056.1	1055.7	1055.7	1055.7	1055.7	1055.7	1056.9	1057.9
177.5°	1062.3	1061.7	1061.1	1060.5	1060.1	1060.0	1059.9	1059.7	1059.6	1060.5	1061.4
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	754.5	754.5	754.5	754.5	754.5	754.5	754.5
2.5°	787.4	787.4	791.7	791.3	794.1	793.1	793.6
5°	846.4	851.7	856.3	859.4	864.1	865.4	864.7
7.5°	907.7	919.3	925.0	932.9	934.3	938.3	937.9
10°	945.5	957.0	965.6	972.5	975.9	980.2	980.6
12.5°	975.3	985.0	992.7	999.0	1003.1	1004.5	1005.3
15°	998.5	1009.3	1018.3	1027.3	1032.6	1036.6	1038.8
17.5°	1021.9	1038.6	1054.5	1066.7	1074.0	1080.2	1080.1
20°	1040.0	1059.2	1079.0	1093.0	1107.2	1113.4	1114.4
22.5°	1059.3	1088.7	1114.2	1135.8	1154.5	1161.0	1163.4
25°	1099.4	1137.8	1177.2	1207.5	1229.2	1241.9	1243.8
27.5°	1147.9	1200.0	1241.3	1269.3	1287.4	1296.7	1298.8
30°	1182.2	1230.1	1267.3	1288.4	1296.7	1298.0	1293.3
32.5°	1197.5	1233.4	1248.2	1247.0	1230.6	1219.7	1215.5
35°	1178.8	1171.3	1135.1	1091.7	1058.6	1037.5	1031.9
37.5°	1072.7	1008.6	941.9	876.4	841.6	823.9	793.4
40°	968.2	876.8	807.4	752.3	713.0	681.3	673.9
42.5°	850.2	755.9	686.5	639.3	607.9	586.2	576.8
45°	683.2	602.1	544.8	508.5	484.4	468.6	461.5
47.5°	546.4	483.6	441.9	415.1	396.6	382.9	379.1
50°	471.4	421.2	385.9	363.3	349.4	338.8	334.5
52.5°	409.4	368.9	341.8	323.2	310.0	303.4	299.8
55°	337.9	302.9	283.4	268.5	261.1	255.8	253.3
57.5°	276.3	251.0	236.8	226.5	219.6	216.3	215.1
60°	241.9	222.1	209.0	201.0	196.3	192.0	190.8
62.5°	211.4	195.8	185.7	178.7	174.1	172.2	171.5
65°	170.3	160.1	152.7	148.4	144.6	144.0	143.7
67.5°	135.4	129.4	125.5	121.0	119.7	117.5	117.1
70°	115.9	111.8	107.1	105.6	104.0	101.9	102.2
72.5°	98.2	94.2	91.1	89.0	88.5	87.6	88.3
75°	71.8	70.6	69.4	67.8	67.2	67.2	66.9
77.5°	51.3	50.2	48.8	47.9	47.8	46.5	47.0
80°	37.2	35.6	35.0	35.3	34.4	34.1	34.1
82.5°	27.5	26.9	26.3	26.4	26.2	25.9	26.2
85°	15.2	14.8	14.8	14.6	14.6	14.3	14.3
87.5°	8.6	9.0	8.7	8.6	8.7	9.0	9.4
90°	16.0	16.9	17.6	18.2	18.8	19.2	19.8
92.5°	35.4	36.6	37.3	37.7	38.2	38.6	39.0
95°	67.4	68.7	69.5	70.0	70.3	70.7	71.0
97.5°	104.9	106.2	106.8	107.0	107.3	107.5	107.7
100°	131.3	133.0	134.0	134.4	134.8	135.1	135.5
102.5°	158.2	160.0	161.2	161.7	162.2	162.7	163.2
105°	200.7	201.9	202.7	203.3	203.7	204.3	204.9
107.5°	246.9	247.4	247.7	247.6	247.6	247.5	247.5
110°	279.2	279.8	280.0	279.8	279.6	279.4	279.2



TEST NUMBER: P333669-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	311.4	311.6	311.6	311.3	311.0	310.6	310.3
115°	360.4	360.3	360.1	359.9	359.7	359.5	359.4
117.5°	410.3	410.5	410.2	409.4	408.7	408.0	407.2
120°	443.6	443.6	443.3	442.5	441.8	441.1	440.3
122.5°	476.2	476.1	475.7	475.2	474.5	473.9	473.4
125°	524.3	523.9	523.7	523.5	523.3	523.1	522.9
127.5°	572.4	572.3	572.0	571.6	571.3	570.9	570.5
130°	604.1	604.0	603.7	603.3	603.0	602.6	602.3
132.5°	634.5	634.4	634.1	633.5	633.0	632.5	631.9
135°	681.5	681.5	681.2	680.4	679.7	679.0	678.2
137.5°	727.3	727.5	727.2	726.3	725.4	724.4	723.5
140°	756.2	756.5	756.3	755.4	754.4	753.5	752.6
142.5°	784.2	784.4	784.0	783.1	782.2	781.3	780.3
145°	824.4	824.4	824.2	823.6	823.0	822.6	822.0
147.5°	862.4	862.9	862.5	861.3	860.0	858.8	857.5
150°	885.6	885.6	885.4	885.0	884.7	884.3	883.9
152.5°	908.1	908.5	908.4	907.8	907.1	906.4	905.7
155°	939.9	940.6	940.4	939.6	938.7	937.8	936.8
157.5°	967.1	967.8	967.6	966.4	965.2	963.9	962.8
160°	983.7	984.4	984.2	983.3	982.4	981.5	980.6
162.5°	999.2	1000.1	1000.0	999.0	997.9	996.9	995.8
165°	1019.9	1020.7	1020.5	1019.5	1018.3	1017.2	1016.1
167.5°	1035.8	1036.9	1036.9	1035.8	1034.6	1033.5	1032.3
170°	1045.1	1046.1	1046.0	1044.7	1043.5	1042.2	1040.9
172.5°	1051.7	1052.7	1052.7	1051.6	1050.4	1049.3	1048.1
175°	1059.1	1060.2	1060.1	1058.8	1057.5	1056.2	1054.9
177.5°	1062.3	1063.1	1063.0	1062.0	1060.9	1060.0	1058.9
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5

(END OF REPORT)