

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333688-930

Luminaire Tested: **S125RDIW-S850D1050U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333688-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1050U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6090.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44																												
1	97	93	89	86	88	85	82	79	71	68	66	57	56	55	45	44	43	38																												
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28																												
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24																												
5	68	57	49	43	62	52	45	40	44	39	35	36	33	29	29	26	24	21																												
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	24	21	18																												
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16																												
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	15																												
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13																												
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6660	6660	6660	6660
5°	7662	6669	5890	6669
10°	8790	6635	5197	6635
15°	9494	6567	4619	6567
20°	10469	6488	4265	6488
25°	12115	6383	3958	6383
30°	13184	6272	3757	6272
35°	11121	6144	3572	6144
40°	7766	5914	3412	5914
45°	5761	5602	3255	5602
50°	4594	5279	3122	5279
55°	3899	4877	3003	4877
60°	3369	4517	2811	4517
65°	3001	4128	2419	4128
70°	2638	3780	2206	3780
75°	2283	3276	2071	3276
80°	1733	2756	1733	2756
85°	1445	2164	1630	2164



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.9	1.6
10°-20°	289.8	4.8
20°-30°	459.5	7.5
30°-40°	554.1	9.1
40°-50°	494.9	8.1
50°-60°	379.5	6.2
60°-70°	246.6	4.0
70°-80°	119.9	2.0
80°-90°	30.9	0.5
90°-100°	40.4	0.7
100°-110°	249.1	4.1
110°-120°	451.8	7.4
120°-130°	579.9	9.5
130°-140°	623.7	10.2
140°-150°	585.4	9.6
150°-160°	473.6	7.8
160°-170°	306.3	5.0
170°-180°	105.6	1.7
0°-30°	848.2	13.9
0°-40°	1402.4	23.0
0°-60°	2276.7	37.4
0°-90°	2674.2	43.9
90°-120°	741.4	12.2
90°-150°	2530.3	41.5
90°-180°	3416.0	56.1
0°-180°	6090.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1031	1031	1031	1031	1031	
5°	1182	1029	908	1029	1182	118
15°	1420	982	691	982	1420	407
25°	1700	896	556	896	1700	781
35°	1410	779	453	779	1410	852
45°	631	613	356	613	631	503
55°	346	433	267	433	346	314
65°	196	270	158	270	196	195
75°	92	131	83	131	92	97
85°	20	29	22	29	20	23
90°	20	1	20	1	20	10
95°	17	47	17	47	17	14
105°	245	242	245	242	245	221
115°	452	455	452	455	452	449
125°	647	647	647	647	647	576
135°	804	807	804	807	804	620
145°	933	936	933	936	933	583
155°	1023	1031	1023	1031	1023	472
165°	1082	1088	1082	1088	1082	305
175°	1107	1112	1107	1112	1107	105
180°	1112	1112	1112	1112	1112	



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1084.8	1084.1	1085.5	1081.7	1082.1	1076.3	1076.3	1071.9	1066.2	1061.8	1059.7
5°	1181.9	1182.8	1181.1	1174.8	1170.5	1164.2	1157.0	1144.3	1133.7	1123.6	1115.5
7.5°	1282.1	1282.6	1277.1	1275.1	1264.4	1256.6	1240.6	1223.4	1208.0	1188.5	1173.7
10°	1340.3	1339.9	1334.0	1329.3	1320.0	1308.1	1292.5	1272.1	1253.1	1231.9	1211.6
12.5°	1374.2	1373.0	1371.2	1365.5	1356.9	1346.4	1333.1	1313.1	1289.6	1266.5	1242.8
15°	1419.9	1416.9	1411.4	1404.2	1392.0	1379.6	1364.9	1347.1	1324.6	1298.4	1276.4
17.5°	1476.4	1476.5	1468.1	1458.1	1441.4	1419.8	1396.9	1368.2	1337.7	1308.8	1285.3
20°	1523.2	1521.9	1513.4	1494.0	1475.0	1447.8	1421.6	1386.4	1349.2	1311.5	1282.3
22.5°	1590.2	1587.0	1578.2	1552.6	1523.1	1488.2	1448.0	1405.1	1360.0	1317.3	1279.0
25°	1700.1	1697.6	1680.3	1650.7	1609.2	1555.3	1502.8	1444.1	1379.2	1323.0	1276.4
27.5°	1775.3	1772.5	1759.7	1735.0	1696.8	1640.2	1569.1	1490.5	1409.7	1332.2	1265.0
30°	1767.9	1774.3	1772.5	1761.1	1732.3	1681.6	1615.9	1527.5	1431.3	1340.3	1260.3
32.5°	1661.5	1667.2	1682.1	1704.5	1706.3	1686.0	1636.9	1555.2	1455.7	1352.2	1256.5
35°	1410.5	1418.2	1447.0	1492.3	1551.5	1601.1	1611.3	1567.2	1477.9	1366.5	1251.0
37.5°	1084.4	1126.1	1150.3	1198.0	1287.5	1378.7	1466.3	1498.5	1460.5	1360.7	1241.9
40°	921.2	931.3	974.5	1028.3	1103.7	1198.5	1323.4	1413.6	1416.5	1347.1	1227.7
42.5°	788.4	801.3	831.0	873.8	938.4	1033.2	1162.1	1281.2	1336.3	1309.9	1209.1
45°	630.8	640.5	662.1	695.1	744.7	823.0	933.9	1071.5	1180.7	1223.4	1159.1
47.5°	518.2	523.4	542.3	567.4	604.1	661.1	747.0	866.4	997.4	1089.2	1080.2
50°	457.2	463.2	477.5	496.6	527.5	575.8	644.3	743.8	878.9	991.1	1013.5
52.5°	409.8	414.7	423.7	441.7	467.2	504.3	559.6	649.6	771.2	890.5	942.3
55°	346.3	349.7	356.9	367.0	387.3	414.0	461.9	524.1	622.3	742.6	818.7
57.5°	294.0	295.6	300.3	309.7	323.7	343.2	377.7	430.5	500.9	609.2	693.2
60°	260.8	262.4	268.4	274.8	285.8	303.5	330.6	367.5	435.2	524.5	609.6
62.5°	234.4	235.4	237.9	244.3	253.9	267.7	288.9	319.0	372.9	451.3	531.7
65°	196.4	196.9	197.7	202.8	208.7	218.9	232.8	254.0	294.6	353.9	425.0
67.5°	160.0	160.6	163.5	165.3	171.5	176.8	185.1	201.3	229.9	269.9	325.1
70°	139.7	139.3	142.3	144.4	146.5	152.8	158.3	171.5	189.2	219.7	265.9
72.5°	120.7	119.6	120.9	121.6	124.5	128.8	134.3	142.4	156.0	177.0	212.4
75°	91.5	91.9	91.9	92.7	94.8	96.5	98.2	102.5	110.1	124.0	143.1
77.5°	64.2	63.5	65.3	65.6	66.8	68.6	70.1	71.8	74.9	80.7	90.5
80°	46.6	46.6	47.0	48.3	47.9	48.7	50.8	52.5	56.3	59.7	63.1
82.5°	35.7	35.4	35.8	36.0	36.0	36.9	37.6	37.9	39.4	41.1	43.5
85°	19.5	19.5	19.9	19.9	20.3	20.3	20.7	20.7	20.7	21.2	21.6
87.5°	11.4	10.9	10.5	10.4	10.6	11.2	10.6	10.1	9.9	9.8	9.9
90°	19.8	19.2	18.7	18.2	17.6	16.9	16.0	15.0	14.1	13.2	11.9
92.5°	18.5	18.2	17.9	17.7	17.4	16.9	16.0	15.0	14.1	13.2	12.1
95°	17.3	17.3	17.3	17.3	17.3	16.9	16.0	15.0	14.1	13.2	20.1
97.5°	17.3	17.3	17.3	17.3	17.3	19.9	25.0	30.2	35.4	40.6	54.4
100°	17.3	18.0	18.8	19.5	20.2	34.2	61.6	88.9	116.2	143.5	142.8
102.5°	103.7	116.2	128.7	141.1	153.6	162.4	167.5	172.7	177.9	183.0	182.6
105°	244.9	245.1	245.2	245.5	245.6	245.7	245.7	245.7	245.7	245.7	245.7
107.5°	308.8	309.2	309.8	310.4	311.0	311.2	311.1	311.1	311.0	311.0	310.6
110°	352.9	352.7	352.5	352.4	352.2	352.4	352.9	353.4	354.0	354.6	354.2



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	392.5	392.7	393.0	393.3	393.5	394.0	394.7	395.4	396.1	396.8	396.6
115°	451.8	453.0	454.0	455.2	456.2	457.1	457.9	458.6	459.3	460.1	459.9
117.5°	515.2	515.7	516.2	516.7	517.1	517.8	518.8	519.8	520.7	521.6	520.9
120°	554.1	555.1	556.0	556.8	557.7	558.4	558.8	559.1	559.5	559.9	559.3
122.5°	591.1	592.2	593.2	594.3	595.3	596.0	596.4	596.7	597.1	597.5	597.2
125°	647.3	647.8	648.4	649.0	649.5	650.1	650.9	651.6	652.3	653.1	653.1
127.5°	694.6	695.9	697.3	698.7	700.0	700.9	701.3	701.7	702.1	702.5	702.6
130°	729.0	729.9	730.8	731.6	732.5	733.3	733.9	734.4	735.0	735.5	735.3
132.5°	760.6	761.5	762.4	763.4	764.3	764.8	764.8	765.0	765.1	765.2	765.6
135°	804.0	805.0	806.2	807.2	808.4	809.1	809.4	809.8	810.2	810.6	810.9
137.5°	847.5	848.5	849.4	850.4	851.3	851.7	851.7	851.6	851.5	851.4	851.7
140°	873.2	874.3	875.4	876.5	877.6	878.0	877.6	877.3	876.9	876.5	876.7
142.5°	897.6	898.7	899.8	900.9	902.0	902.5	902.5	902.4	902.3	902.2	902.0
145°	933.4	934.5	935.6	936.7	937.8	938.2	938.1	937.9	937.8	937.5	937.5
147.5°	963.0	964.3	965.6	966.9	968.2	968.7	968.6	968.3	968.1	967.8	967.7
150°	982.0	983.5	985.0	986.4	987.9	988.5	988.1	987.7	987.4	987.0	986.7
152.5°	999.9	1001.2	1002.5	1003.8	1005.2	1005.6	1005.3	1004.9	1004.5	1004.1	1003.8
155°	1023.3	1024.7	1026.2	1027.7	1029.2	1029.6	1029.1	1028.5	1027.9	1027.4	1027.0
157.5°	1042.9	1044.4	1045.9	1047.3	1048.8	1049.2	1048.6	1048.1	1047.5	1046.8	1046.8
160°	1055.5	1057.0	1058.4	1059.9	1061.3	1061.7	1060.9	1060.2	1059.5	1058.7	1058.6
162.5°	1066.7	1068.3	1069.9	1071.5	1073.1	1073.4	1072.4	1071.4	1070.3	1069.3	1069.1
165°	1081.8	1083.3	1084.8	1086.2	1087.7	1087.9	1086.8	1085.7	1084.6	1083.5	1083.3
167.5°	1092.4	1094.1	1095.7	1097.3	1099.0	1099.2	1097.8	1096.5	1095.2	1093.9	1093.7
170°	1098.3	1100.0	1101.6	1103.3	1104.9	1105.1	1103.6	1102.1	1100.7	1099.2	1098.9
172.5°	1102.3	1103.9	1105.5	1107.3	1108.9	1109.1	1107.7	1106.4	1105.1	1103.8	1103.4
175°	1107.4	1109.1	1110.7	1112.3	1114.0	1114.1	1112.6	1111.2	1109.7	1108.2	1108.1
177.5°	1110.4	1111.6	1112.7	1113.9	1115.1	1115.2	1114.1	1113.0	1112.1	1111.0	1110.8
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1059.7	1057.4	1053.0	1048.9	1043.8	1039.4	1036.3	1032.7	1027.8	1022.1	1017.4
5°	1106.6	1097.3	1085.0	1074.5	1060.9	1050.4	1039.3	1028.7	1018.1	1004.6	992.7
7.5°	1158.6	1139.4	1120.7	1097.1	1075.8	1056.7	1038.4	1019.9	1001.8	982.6	964.0
10°	1190.4	1167.2	1141.3	1111.7	1084.6	1058.7	1035.1	1011.8	987.2	965.6	942.3
12.5°	1220.3	1190.2	1160.7	1123.2	1090.7	1059.2	1029.0	1000.0	973.7	945.7	920.7
15°	1247.2	1217.6	1184.5	1138.8	1093.5	1055.4	1019.9	982.2	949.6	918.3	890.3
17.5°	1257.6	1226.5	1188.1	1144.2	1094.7	1046.8	1000.9	959.6	921.3	884.8	853.4
20°	1253.5	1223.4	1184.1	1142.2	1089.2	1039.3	989.8	944.0	901.3	862.7	829.3
22.5°	1243.7	1212.6	1174.6	1130.3	1080.1	1027.1	974.2	925.4	880.6	840.7	804.3
25°	1229.0	1186.7	1147.7	1104.5	1056.6	1004.2	949.6	895.8	848.0	807.3	767.5
27.5°	1213.7	1160.8	1111.3	1068.4	1017.8	970.9	918.4	863.2	812.9	771.5	730.7
30°	1199.8	1140.5	1085.9	1037.2	989.4	944.9	895.0	841.1	789.5	746.8	705.3
32.5°	1182.5	1119.5	1059.5	1003.3	957.2	913.1	867.9	816.4	766.1	722.0	679.9
35°	1160.8	1080.4	1015.2	955.4	904.2	861.5	820.8	779.3	729.0	683.3	642.2
37.5°	1132.4	1041.1	965.6	900.7	846.6	803.6	771.6	733.7	687.7	643.9	605.8
40°	1115.1	1012.6	930.1	865.8	809.0	763.7	733.7	701.5	659.6	618.5	580.4
42.5°	1092.1	986.6	894.2	827.1	770.1	726.4	696.0	668.0	632.8	594.1	553.3
45°	1046.9	936.0	839.1	767.1	709.6	666.8	638.4	613.4	586.8	551.2	515.6
47.5°	988.1	883.3	781.8	703.3	646.9	607.2	579.7	559.9	540.9	510.6	476.1
50°	941.1	839.9	740.9	664.6	604.5	566.9	541.0	525.4	508.0	480.5	451.7
52.5°	885.6	795.2	698.1	620.3	563.5	528.2	503.4	487.8	473.4	451.0	423.6
55°	798.0	718.8	629.9	559.2	507.2	471.6	447.9	433.1	424.6	405.5	384.0
57.5°	697.0	640.3	561.8	493.7	447.7	412.5	395.2	382.5	373.0	359.5	344.3
60°	626.6	586.8	516.5	451.7	409.4	375.9	360.3	349.7	340.8	329.4	317.5
62.5°	555.1	526.1	465.0	409.4	370.4	342.4	327.8	318.2	307.9	300.3	288.7
65°	459.3	433.5	391.2	347.6	311.6	289.1	278.6	270.1	263.7	255.3	247.2
67.5°	357.3	346.8	317.6	287.6	261.7	241.7	232.6	226.7	219.1	213.9	208.5
70°	294.6	289.6	268.8	248.9	224.8	211.2	202.8	200.2	190.9	185.9	182.1
72.5°	239.1	236.8	224.8	211.0	194.0	182.1	174.3	171.5	165.5	161.4	159.0
75°	163.8	164.7	162.6	153.7	147.3	139.7	132.9	131.3	127.0	123.6	121.5
77.5°	103.6	107.9	108.1	107.7	105.2	100.5	97.7	96.4	92.3	91.0	90.5
80°	71.1	75.7	80.0	79.6	78.8	77.5	75.3	74.1	72.0	70.7	69.9
82.5°	47.5	51.8	55.3	57.6	57.4	56.2	54.7	54.1	53.6	52.7	52.6
85°	22.4	23.3	24.5	27.6	29.6	30.1	29.6	29.2	28.0	28.4	28.8
87.5°	9.9	9.6	9.7	9.5	8.8	10.3	10.9	11.0	10.6	10.3	9.9
90°	10.6	9.4	8.1	6.7	5.2	3.8	2.3	0.8	2.3	3.8	5.2
92.5°	10.9	9.8	8.6	8.6	9.6	10.7	11.7	12.7	11.7	10.7	9.6
95°	27.1	34.1	41.0	44.8	45.3	45.9	46.5	47.0	46.5	45.9	45.3
97.5°	68.2	81.9	95.7	102.1	101.1	100.1	99.1	98.2	99.1	100.1	101.1
100°	142.0	141.3	140.6	139.9	139.3	138.8	138.3	137.7	138.3	138.8	139.3
102.5°	182.1	181.7	181.3	180.8	180.0	179.4	178.6	178.0	178.6	179.4	180.0
105°	245.7	245.7	245.7	245.3	244.6	243.9	243.1	242.4	243.1	243.9	244.6
107.5°	310.3	309.9	309.6	309.4	309.4	309.4	309.4	309.4	309.4	309.4	309.4
110°	353.8	353.4	353.1	352.9	352.9	352.9	352.9	352.9	352.9	352.9	352.9



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	396.3	396.2	395.9	395.6	395.1	394.7	394.3	393.8	394.3	394.7	395.1
115°	459.7	459.6	459.3	458.9	457.9	457.0	456.1	455.2	456.1	457.0	457.9
117.5°	520.2	519.5	518.9	518.5	518.5	518.6	518.6	518.7	518.6	518.6	518.5
120°	558.8	558.2	557.7	557.5	557.7	557.8	558.1	558.2	558.1	557.8	557.7
122.5°	597.0	596.7	596.5	596.0	595.3	594.6	593.9	593.2	593.9	594.6	595.3
125°	653.1	653.1	653.1	652.4	651.1	649.9	648.6	647.3	648.6	649.9	651.1
127.5°	702.8	702.9	703.0	702.5	701.6	700.7	699.9	698.9	699.9	700.7	701.6
130°	735.2	735.0	734.7	734.3	733.3	732.4	731.5	730.6	731.5	732.4	733.3
132.5°	766.0	766.4	766.8	766.5	765.4	764.3	763.3	762.2	763.3	764.3	765.4
135°	811.3	811.6	812.0	811.6	810.6	809.4	808.4	807.2	808.4	809.4	810.6
137.5°	852.2	852.5	852.8	852.5	851.5	850.5	849.6	848.6	849.6	850.5	851.5
140°	876.9	877.1	877.3	877.2	876.8	876.4	876.0	875.7	876.0	876.4	876.8
142.5°	901.7	901.5	901.2	901.0	900.7	900.6	900.3	900.1	900.3	900.6	900.7
145°	937.5	937.5	937.5	937.3	937.0	936.6	936.3	935.9	936.3	936.6	937.0
147.5°	967.4	967.2	967.0	966.9	967.0	967.1	967.2	967.2	967.2	967.1	967.0
150°	986.3	985.9	985.5	985.5	985.9	986.3	986.7	987.0	986.7	986.3	985.9
152.5°	1003.5	1003.1	1002.7	1002.9	1003.7	1004.5	1005.3	1006.2	1005.3	1004.5	1003.7
155°	1026.7	1026.3	1026.0	1026.3	1027.4	1028.5	1029.6	1030.7	1029.6	1028.5	1027.4
157.5°	1046.8	1046.8	1046.8	1047.0	1047.7	1048.4	1049.0	1049.7	1049.0	1048.4	1047.7
160°	1058.4	1058.2	1058.0	1058.5	1059.6	1060.7	1061.8	1062.9	1061.8	1060.7	1059.6
162.5°	1068.9	1068.8	1068.5	1069.0	1070.2	1071.2	1072.4	1073.4	1072.4	1071.2	1070.2
165°	1083.1	1083.0	1082.7	1083.2	1084.3	1085.4	1086.5	1087.6	1086.5	1085.4	1084.3
167.5°	1093.5	1093.3	1093.2	1093.6	1094.8	1095.9	1097.1	1098.1	1097.1	1095.9	1094.8
170°	1098.8	1098.6	1098.5	1098.9	1100.2	1101.6	1102.9	1104.1	1102.9	1101.6	1100.2
172.5°	1103.1	1102.8	1102.4	1102.9	1104.2	1105.5	1106.8	1108.1	1106.8	1105.5	1104.2
175°	1107.8	1107.7	1107.5	1107.9	1109.1	1110.1	1111.3	1112.3	1111.3	1110.1	1109.1
177.5°	1110.8	1110.6	1110.4	1110.8	1111.7	1112.6	1113.5	1114.4	1113.5	1112.6	1111.7
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1014.0	1009.3	1005.8	999.1	994.3	992.3	988.6	987.6	991.3	988.6	988.2
5°	983.8	971.6	961.8	952.1	941.5	934.7	924.5	922.9	920.3	916.6	915.7
7.5°	947.7	931.7	919.2	903.1	889.1	877.8	865.1	859.2	855.8	850.9	844.3
10°	923.3	904.2	887.3	871.2	853.9	839.9	827.2	817.5	811.1	805.2	802.7
12.5°	899.3	879.9	858.2	838.7	819.4	803.6	789.6	783.3	776.2	769.3	763.4
15°	861.9	836.1	812.4	789.9	773.5	756.5	743.0	733.7	723.1	720.1	708.7
17.5°	822.3	797.0	769.2	745.6	726.4	707.8	692.9	682.3	674.4	663.5	658.2
20°	797.6	767.5	740.5	718.8	697.7	675.6	660.4	651.5	643.9	635.0	630.8
22.5°	771.2	741.8	714.0	688.7	667.2	645.6	634.7	625.4	616.8	608.6	603.0
25°	732.4	702.8	673.5	647.3	624.8	609.2	596.5	585.9	581.2	573.2	567.3
27.5°	694.1	662.5	632.2	606.1	588.5	573.0	562.6	554.2	545.8	538.7	533.6
30°	669.3	637.2	604.1	583.3	564.8	549.9	538.5	530.4	524.1	517.7	514.0
32.5°	644.6	611.4	582.1	559.6	542.0	529.3	517.5	509.8	503.1	496.1	491.6
35°	605.0	571.1	547.4	525.4	508.0	496.2	488.1	477.1	471.6	466.5	461.9
37.5°	568.1	536.6	510.9	491.7	476.6	464.8	454.4	448.5	441.7	437.2	433.3
40°	541.0	512.3	488.9	468.6	457.6	444.5	434.8	427.1	422.1	416.1	411.9
42.5°	516.7	489.9	467.2	449.0	435.3	424.2	414.8	407.2	400.7	396.5	393.0
45°	482.2	455.5	433.5	416.5	403.9	393.3	383.5	379.8	371.3	366.2	364.5
47.5°	446.5	422.7	401.5	385.8	372.8	362.8	353.7	345.8	341.2	336.2	333.5
50°	422.5	399.7	379.8	364.5	351.8	340.8	332.3	327.3	320.9	316.3	312.8
52.5°	398.4	377.3	357.4	342.8	331.8	320.8	311.4	306.2	300.3	297.3	294.9
55°	364.1	341.6	324.7	310.3	298.9	288.7	279.8	274.8	270.9	268.0	267.1
57.5°	325.1	307.4	291.6	278.7	266.8	257.2	249.4	244.6	241.2	240.8	238.2
60°	299.7	283.6	269.2	255.3	245.1	236.2	229.4	224.0	220.5	220.1	219.3
62.5°	274.3	258.9	245.6	233.3	224.1	215.6	209.1	202.9	200.9	198.8	197.0
65°	236.7	222.7	211.7	201.9	192.2	185.0	178.6	174.8	170.2	167.6	163.0
67.5°	199.7	188.8	178.2	170.0	162.4	155.6	150.3	144.6	141.5	139.4	136.1
70°	175.3	166.8	156.2	147.3	141.4	135.9	131.7	125.3	123.2	121.5	119.8
72.5°	152.2	144.8	135.9	128.7	122.8	117.6	112.7	109.7	107.6	105.9	104.9
75°	119.8	112.6	105.0	99.9	95.7	91.5	88.9	86.7	85.9	85.5	83.8
77.5°	88.0	84.1	78.0	74.0	71.2	69.5	67.3	66.1	66.0	64.2	63.6
80°	67.3	65.2	60.1	58.5	56.3	54.6	53.3	51.2	49.1	48.3	47.0
82.5°	50.1	47.9	45.9	43.2	41.4	40.4	39.1	38.3	38.6	37.4	36.9
85°	26.7	24.5	23.7	23.3	22.4	23.3	22.8	22.4	22.0	21.6	22.0
87.5°	9.8	10.1	10.0	10.9	10.2	10.8	10.9	10.8	11.0	11.2	11.0
90°	6.7	8.1	9.4	10.6	11.9	13.2	14.1	15.0	16.0	16.9	17.6
92.5°	8.6	8.6	9.8	10.9	12.1	13.2	14.1	15.0	16.0	16.9	17.4
95°	44.8	41.0	34.1	27.1	20.1	13.2	14.1	15.0	16.0	16.9	17.3
97.5°	102.1	95.7	81.9	68.2	54.4	40.6	35.4	30.2	25.0	19.9	17.3
100°	139.9	140.6	141.3	142.0	142.8	143.5	116.2	88.9	61.6	34.2	20.2
102.5°	180.8	181.3	181.7	182.1	182.6	183.0	177.9	172.7	167.5	162.4	153.6
105°	245.3	245.7	245.7	245.7	245.7	245.7	245.7	245.7	245.7	245.7	245.6
107.5°	309.4	309.6	309.9	310.3	310.6	311.0	311.0	311.1	311.1	311.2	311.0
110°	352.9	353.1	353.4	353.8	354.2	354.6	354.0	353.4	352.9	352.4	352.2



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	395.6	395.9	396.2	396.3	396.6	396.8	396.1	395.4	394.7	394.0	393.5
115°	458.9	459.3	459.6	459.7	459.9	460.1	459.3	458.6	457.9	457.1	456.2
117.5°	518.5	518.9	519.5	520.2	520.9	521.6	520.7	519.8	518.8	517.8	517.1
120°	557.5	557.7	558.2	558.8	559.3	559.9	559.5	559.1	558.8	558.4	557.7
122.5°	596.0	596.5	596.7	597.0	597.2	597.5	597.1	596.7	596.4	596.0	595.3
125°	652.4	653.1	653.1	653.1	653.1	653.1	652.3	651.6	650.9	650.1	649.5
127.5°	702.5	703.0	702.9	702.8	702.6	702.5	702.1	701.7	701.3	700.9	700.0
130°	734.3	734.7	735.0	735.2	735.3	735.5	735.0	734.4	733.9	733.3	732.5
132.5°	766.5	766.8	766.4	766.0	765.6	765.2	765.1	765.0	764.8	764.8	764.3
135°	811.6	812.0	811.6	811.3	810.9	810.6	810.2	809.8	809.4	809.1	808.4
137.5°	852.5	852.8	852.5	852.2	851.7	851.4	851.5	851.6	851.7	851.7	851.3
140°	877.2	877.3	877.1	876.9	876.7	876.5	876.9	877.3	877.6	878.0	877.6
142.5°	901.0	901.2	901.5	901.7	902.0	902.2	902.3	902.4	902.5	902.5	902.0
145°	937.3	937.5	937.5	937.5	937.5	937.5	937.8	937.9	938.1	938.2	937.8
147.5°	966.9	967.0	967.2	967.4	967.7	967.8	968.1	968.3	968.6	968.7	968.2
150°	985.5	985.5	985.9	986.3	986.7	987.0	987.4	987.7	988.1	988.5	987.9
152.5°	1002.9	1002.7	1003.1	1003.5	1003.8	1004.1	1004.5	1004.9	1005.3	1005.6	1005.2
155°	1026.3	1026.0	1026.3	1026.7	1027.0	1027.4	1027.9	1028.5	1029.1	1029.6	1029.2
157.5°	1047.0	1046.8	1046.8	1046.8	1046.8	1046.8	1047.5	1048.1	1048.6	1049.2	1048.8
160°	1058.5	1058.0	1058.2	1058.4	1058.6	1058.7	1059.5	1060.2	1060.9	1061.7	1061.3
162.5°	1069.0	1068.5	1068.8	1068.9	1069.1	1069.3	1070.3	1071.4	1072.4	1073.4	1073.1
165°	1083.2	1082.7	1083.0	1083.1	1083.3	1083.5	1084.6	1085.7	1086.8	1087.9	1087.7
167.5°	1093.6	1093.2	1093.3	1093.5	1093.7	1093.9	1095.2	1096.5	1097.8	1099.2	1099.0
170°	1098.9	1098.5	1098.6	1098.8	1098.9	1099.2	1100.7	1102.1	1103.6	1105.1	1104.9
172.5°	1102.9	1102.4	1102.8	1103.1	1103.4	1103.8	1105.1	1106.4	1107.7	1109.1	1108.9
175°	1107.9	1107.5	1107.7	1107.8	1108.1	1108.2	1109.7	1111.2	1112.6	1114.1	1114.0
177.5°	1110.8	1110.4	1110.6	1110.8	1110.8	1111.0	1112.1	1113.0	1114.1	1115.2	1115.1
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	987.9	984.2	983.2	984.6	983.2	984.2	987.9	988.2	988.6	991.3	987.6
5°	911.4	907.3	909.3	908.5	909.3	907.3	911.4	915.7	916.6	920.3	922.9
7.5°	844.2	838.9	833.4	835.2	833.4	838.9	844.2	844.3	850.9	855.8	859.2
10°	797.1	793.0	790.4	792.5	790.4	793.0	797.1	802.7	805.2	811.1	817.5
12.5°	757.5	755.0	752.8	751.9	752.8	755.0	757.5	763.4	769.3	776.2	783.3
15°	703.6	698.5	696.4	690.9	696.4	698.5	703.6	708.7	720.1	723.1	733.7
17.5°	653.9	652.2	646.7	644.3	646.7	652.2	653.9	658.2	663.5	674.4	682.3
20°	624.4	622.7	617.3	620.6	617.3	622.7	624.4	630.8	635.0	643.9	651.5
22.5°	600.1	596.3	594.5	593.5	594.5	596.3	600.1	603.0	608.6	616.8	625.4
25°	565.6	560.1	558.0	555.5	558.0	560.1	565.6	567.3	573.2	581.2	585.9
27.5°	531.2	528.2	525.5	524.8	525.5	528.2	531.2	533.6	538.7	545.8	554.2
30°	508.8	505.9	503.8	503.8	503.8	505.9	508.8	514.0	517.7	524.1	530.4
32.5°	488.9	486.6	484.5	484.1	484.5	486.6	488.9	491.6	496.1	503.1	509.8
35°	459.7	456.4	455.5	453.0	455.5	456.4	459.7	461.9	466.5	471.6	477.1
37.5°	429.5	426.7	426.6	426.4	426.6	426.7	429.5	433.3	437.2	441.7	448.5
40°	410.3	408.1	407.6	404.7	407.6	408.1	410.3	411.9	416.1	422.1	427.1
42.5°	389.6	388.5	387.0	385.7	387.0	388.5	389.6	393.0	396.5	400.7	407.2
45°	361.5	358.6	358.6	356.4	358.6	358.6	361.5	364.5	366.2	371.3	379.8
47.5°	332.6	330.3	330.5	328.3	330.5	330.3	332.6	333.5	336.2	341.2	345.8
50°	313.2	312.0	311.6	310.7	311.6	312.0	313.2	312.8	316.3	320.9	327.3
52.5°	294.0	293.3	295.0	293.1	295.0	293.3	294.0	294.9	297.3	300.3	306.2
55°	268.0	266.7	269.2	266.7	269.2	266.7	268.0	267.1	268.0	270.9	274.8
57.5°	238.1	236.9	239.2	237.9	239.2	236.9	238.1	238.2	240.8	241.2	244.6
60°	218.4	215.9	217.2	217.6	217.2	215.9	218.4	219.3	220.1	220.5	224.0
62.5°	195.1	193.6	194.4	192.6	194.4	193.6	195.1	197.0	198.8	200.9	202.9
65°	162.2	160.9	159.1	158.3	159.1	160.9	162.2	163.0	167.6	170.2	174.8
67.5°	136.2	133.2	133.1	133.8	133.1	133.2	136.2	136.1	139.4	141.5	144.6
70°	117.2	117.2	116.8	116.8	116.8	117.2	117.2	119.8	121.5	123.2	125.3
72.5°	104.0	103.7	103.0	102.6	103.0	103.7	104.0	104.9	105.9	107.6	109.7
75°	83.8	84.2	83.4	83.0	83.4	84.2	83.8	83.8	85.5	85.9	86.7
77.5°	61.9	60.1	61.1	60.1	61.1	60.1	61.9	63.6	64.2	66.0	66.1
80°	47.0	46.6	47.9	46.6	47.9	46.6	47.0	47.0	48.3	49.1	51.2
82.5°	37.2	36.8	37.3	36.4	37.3	36.8	37.2	36.9	37.4	38.6	38.3
85°	22.4	22.0	21.6	22.0	21.6	22.0	22.4	22.0	21.6	22.0	22.4
87.5°	11.4	11.2	11.3	11.4	11.3	11.2	11.4	11.0	11.2	11.0	10.8
90°	18.2	18.7	19.2	19.8	19.2	18.7	18.2	17.6	16.9	16.0	15.0
92.5°	17.7	17.9	18.2	18.5	18.2	17.9	17.7	17.4	16.9	16.0	15.0
95°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	16.9	16.0	15.0
97.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	19.9	25.0	30.2
100°	19.5	18.8	18.0	17.3	18.0	18.8	19.5	20.2	34.2	61.6	88.9
102.5°	141.1	128.7	116.2	103.7	116.2	128.7	141.1	153.6	162.4	167.5	172.7
105°	245.5	245.2	245.1	244.9	245.1	245.2	245.5	245.6	245.7	245.7	245.7
107.5°	310.4	309.8	309.2	308.8	309.2	309.8	310.4	311.0	311.2	311.1	311.1
110°	352.4	352.5	352.7	352.9	352.7	352.5	352.4	352.2	352.4	352.9	353.4



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	393.3	393.0	392.7	392.5	392.7	393.0	393.3	393.5	394.0	394.7	395.4
115°	455.2	454.0	453.0	451.8	453.0	454.0	455.2	456.2	457.1	457.9	458.6
117.5°	516.7	516.2	515.7	515.2	515.7	516.2	516.7	517.1	517.8	518.8	519.8
120°	556.8	556.0	555.1	554.1	555.1	556.0	556.8	557.7	558.4	558.8	559.1
122.5°	594.3	593.2	592.2	591.1	592.2	593.2	594.3	595.3	596.0	596.4	596.7
125°	649.0	648.4	647.8	647.3	647.8	648.4	649.0	649.5	650.1	650.9	651.6
127.5°	698.7	697.3	695.9	694.6	695.9	697.3	698.7	700.0	700.9	701.3	701.7
130°	731.6	730.8	729.9	729.0	729.9	730.8	731.6	732.5	733.3	733.9	734.4
132.5°	763.4	762.4	761.5	760.6	761.5	762.4	763.4	764.3	764.8	764.8	765.0
135°	807.2	806.2	805.0	804.0	805.0	806.2	807.2	808.4	809.1	809.4	809.8
137.5°	850.4	849.4	848.5	847.5	848.5	849.4	850.4	851.3	851.7	851.7	851.6
140°	876.5	875.4	874.3	873.2	874.3	875.4	876.5	877.6	878.0	877.6	877.3
142.5°	900.9	899.8	898.7	897.6	898.7	899.8	900.9	902.0	902.5	902.5	902.4
145°	936.7	935.6	934.5	933.4	934.5	935.6	936.7	937.8	938.2	938.1	937.9
147.5°	966.9	965.6	964.3	963.0	964.3	965.6	966.9	968.2	968.7	968.6	968.3
150°	986.4	985.0	983.5	982.0	983.5	985.0	986.4	987.9	988.5	988.1	987.7
152.5°	1003.8	1002.5	1001.2	999.9	1001.2	1002.5	1003.8	1005.2	1005.6	1005.3	1004.9
155°	1027.7	1026.2	1024.7	1023.3	1024.7	1026.2	1027.7	1029.2	1029.6	1029.1	1028.5
157.5°	1047.3	1045.9	1044.4	1042.9	1044.4	1045.9	1047.3	1048.8	1049.2	1048.6	1048.1
160°	1059.9	1058.4	1057.0	1055.5	1057.0	1058.4	1059.9	1061.3	1061.7	1060.9	1060.2
162.5°	1071.5	1069.9	1068.3	1066.7	1068.3	1069.9	1071.5	1073.1	1073.4	1072.4	1071.4
165°	1086.2	1084.8	1083.3	1081.8	1083.3	1084.8	1086.2	1087.7	1087.9	1086.8	1085.7
167.5°	1097.3	1095.7	1094.1	1092.4	1094.1	1095.7	1097.3	1099.0	1099.2	1097.8	1096.5
170°	1103.3	1101.6	1100.0	1098.3	1100.0	1101.6	1103.3	1104.9	1105.1	1103.6	1102.1
172.5°	1107.3	1105.5	1103.9	1102.3	1103.9	1105.5	1107.3	1108.9	1109.1	1107.7	1106.4
175°	1112.3	1110.7	1109.1	1107.4	1109.1	1110.7	1112.3	1114.0	1114.1	1112.6	1111.2
177.5°	1113.9	1112.7	1111.6	1110.4	1111.6	1112.7	1113.9	1115.1	1115.2	1114.1	1113.0
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	988.6	992.3	994.3	999.1	1005.8	1009.3	1014.0	1017.4	1022.1	1027.8	1032.7
5°	924.5	934.7	941.5	952.1	961.8	971.6	983.8	992.7	1004.6	1018.1	1028.7
7.5°	865.1	877.8	889.1	903.1	919.2	931.7	947.7	964.0	982.6	1001.8	1019.9
10°	827.2	839.9	853.9	871.2	887.3	904.2	923.3	942.3	965.6	987.2	1011.8
12.5°	789.6	803.6	819.4	838.7	858.2	879.9	899.3	920.7	945.7	973.7	1000.0
15°	743.0	756.5	773.5	789.9	812.4	836.1	861.9	890.3	918.3	949.6	982.2
17.5°	692.9	707.8	726.4	745.6	769.2	797.0	822.3	853.4	884.8	921.3	959.6
20°	660.4	675.6	697.7	718.8	740.5	767.5	797.6	829.3	862.7	901.3	944.0
22.5°	634.7	645.6	667.2	688.7	714.0	741.8	771.2	804.3	840.7	880.6	925.4
25°	596.5	609.2	624.8	647.3	673.5	702.8	732.4	767.5	807.3	848.0	895.8
27.5°	562.6	573.0	588.5	606.1	632.2	662.5	694.1	730.7	771.5	812.9	863.2
30°	538.5	549.9	564.8	583.3	604.1	637.2	669.3	705.3	746.8	789.5	841.1
32.5°	517.5	529.3	542.0	559.6	582.1	611.4	644.6	679.9	722.0	766.1	816.4
35°	488.1	496.2	508.0	525.4	547.4	571.1	605.0	642.2	683.3	729.0	779.3
37.5°	454.4	464.8	476.6	491.7	510.9	536.6	568.1	605.8	643.9	687.7	733.7
40°	434.8	444.5	457.6	468.6	488.9	512.3	541.0	580.4	618.5	659.6	701.5
42.5°	414.8	424.2	435.3	449.0	467.2	489.9	516.7	553.3	594.1	632.8	668.0
45°	383.5	393.3	403.9	416.5	433.5	455.5	482.2	515.6	551.2	586.8	613.4
47.5°	353.7	362.8	372.8	385.8	401.5	422.7	446.5	476.1	510.6	540.9	559.9
50°	332.3	340.8	351.8	364.5	379.8	399.7	422.5	451.7	480.5	508.0	525.4
52.5°	311.4	320.8	331.8	342.8	357.4	377.3	398.4	423.6	451.0	473.4	487.8
55°	279.8	288.7	298.9	310.3	324.7	341.6	364.1	384.0	405.5	424.6	433.1
57.5°	249.4	257.2	266.8	278.7	291.6	307.4	325.1	344.3	359.5	373.0	382.5
60°	229.4	236.2	245.1	255.3	269.2	283.6	299.7	317.5	329.4	340.8	349.7
62.5°	209.1	215.6	224.1	233.3	245.6	258.9	274.3	288.7	300.3	307.9	318.2
65°	178.6	185.0	192.2	201.9	211.7	222.7	236.7	247.2	255.3	263.7	270.1
67.5°	150.3	155.6	162.4	170.0	178.2	188.8	199.7	208.5	213.9	219.1	226.7
70°	131.7	135.9	141.4	147.3	156.2	166.8	175.3	182.1	185.9	190.9	200.2
72.5°	112.7	117.6	122.8	128.7	135.9	144.8	152.2	159.0	161.4	165.5	171.5
75°	88.9	91.5	95.7	99.9	105.0	112.6	119.8	121.5	123.6	127.0	131.3
77.5°	67.3	69.5	71.2	74.0	78.0	84.1	88.0	90.5	91.0	92.3	96.4
80°	53.3	54.6	56.3	58.5	60.1	65.2	67.3	69.9	70.7	72.0	74.1
82.5°	39.1	40.4	41.4	43.2	45.9	47.9	50.1	52.6	52.7	53.6	54.1
85°	22.8	23.3	22.4	23.3	23.7	24.5	26.7	28.8	28.4	28.0	29.2
87.5°	10.9	10.8	10.2	10.9	10.0	10.1	9.8	9.9	10.3	10.6	11.0
90°	14.1	13.2	11.9	10.6	9.4	8.1	6.7	5.2	3.8	2.3	0.8
92.5°	14.1	13.2	12.1	10.9	9.8	8.6	8.6	9.6	10.7	11.7	12.7
95°	14.1	13.2	20.1	27.1	34.1	41.0	44.8	45.3	45.9	46.5	47.0
97.5°	35.4	40.6	54.4	68.2	81.9	95.7	102.1	101.1	100.1	99.1	98.2
100°	116.2	143.5	142.8	142.0	141.3	140.6	139.9	139.3	138.8	138.3	137.7
102.5°	177.9	183.0	182.6	182.1	181.7	181.3	180.8	180.0	179.4	178.6	178.0
105°	245.7	245.7	245.7	245.7	245.7	245.7	245.3	244.6	243.9	243.1	242.4
107.5°	311.0	311.0	310.6	310.3	309.9	309.6	309.4	309.4	309.4	309.4	309.4
110°	354.0	354.6	354.2	353.8	353.4	353.1	352.9	352.9	352.9	352.9	352.9



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	396.1	396.8	396.6	396.3	396.2	395.9	395.6	395.1	394.7	394.3	393.8
115°	459.3	460.1	459.9	459.7	459.6	459.3	458.9	457.9	457.0	456.1	455.2
117.5°	520.7	521.6	520.9	520.2	519.5	518.9	518.5	518.5	518.6	518.6	518.7
120°	559.5	559.9	559.3	558.8	558.2	557.7	557.5	557.7	557.8	558.1	558.2
122.5°	597.1	597.5	597.2	597.0	596.7	596.5	596.0	595.3	594.6	593.9	593.2
125°	652.3	653.1	653.1	653.1	653.1	653.1	652.4	651.1	649.9	648.6	647.3
127.5°	702.1	702.5	702.6	702.8	702.9	703.0	702.5	701.6	700.7	699.9	698.9
130°	735.0	735.5	735.3	735.2	735.0	734.7	734.3	733.3	732.4	731.5	730.6
132.5°	765.1	765.2	765.6	766.0	766.4	766.8	766.5	765.4	764.3	763.3	762.2
135°	810.2	810.6	810.9	811.3	811.6	812.0	811.6	810.6	809.4	808.4	807.2
137.5°	851.5	851.4	851.7	852.2	852.5	852.8	852.5	851.5	850.5	849.6	848.6
140°	876.9	876.5	876.7	876.9	877.1	877.3	877.2	876.8	876.4	876.0	875.7
142.5°	902.3	902.2	902.0	901.7	901.5	901.2	901.0	900.7	900.6	900.3	900.1
145°	937.8	937.5	937.5	937.5	937.5	937.5	937.3	937.0	936.6	936.3	935.9
147.5°	968.1	967.8	967.7	967.4	967.2	967.0	966.9	967.0	967.1	967.2	967.2
150°	987.4	987.0	986.7	986.3	985.9	985.5	985.5	985.9	986.3	986.7	987.0
152.5°	1004.5	1004.1	1003.8	1003.5	1003.1	1002.7	1002.9	1003.7	1004.5	1005.3	1006.2
155°	1027.9	1027.4	1027.0	1026.7	1026.3	1026.0	1026.3	1027.4	1028.5	1029.6	1030.7
157.5°	1047.5	1046.8	1046.8	1046.8	1046.8	1046.8	1047.0	1047.7	1048.4	1049.0	1049.7
160°	1059.5	1058.7	1058.6	1058.4	1058.2	1058.0	1058.5	1059.6	1060.7	1061.8	1062.9
162.5°	1070.3	1069.3	1069.1	1068.9	1068.8	1068.5	1069.0	1070.2	1071.2	1072.4	1073.4
165°	1084.6	1083.5	1083.3	1083.1	1083.0	1082.7	1083.2	1084.3	1085.4	1086.5	1087.6
167.5°	1095.2	1093.9	1093.7	1093.5	1093.3	1093.2	1093.6	1094.8	1095.9	1097.1	1098.1
170°	1100.7	1099.2	1098.9	1098.8	1098.6	1098.5	1098.9	1100.2	1101.6	1102.9	1104.1
172.5°	1105.1	1103.8	1103.4	1103.1	1102.8	1102.4	1102.9	1104.2	1105.5	1106.8	1108.1
175°	1109.7	1108.2	1108.1	1107.8	1107.7	1107.5	1107.9	1109.1	1110.1	1111.3	1112.3
177.5°	1112.1	1111.0	1110.8	1110.8	1110.6	1110.4	1110.8	1111.7	1112.6	1113.5	1114.4
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1036.3	1039.4	1043.8	1048.9	1053.0	1057.4	1059.7	1059.7	1061.8	1066.2	1071.9
5°	1039.3	1050.4	1060.9	1074.5	1085.0	1097.3	1106.6	1115.5	1123.6	1133.7	1144.3
7.5°	1038.4	1056.7	1075.8	1097.1	1120.7	1139.4	1158.6	1173.7	1188.5	1208.0	1223.4
10°	1035.1	1058.7	1084.6	1111.7	1141.3	1167.2	1190.4	1211.6	1231.9	1253.1	1272.1
12.5°	1029.0	1059.2	1090.7	1123.2	1160.7	1190.2	1220.3	1242.8	1266.5	1289.6	1313.1
15°	1019.9	1055.4	1093.5	1138.8	1184.5	1217.6	1247.2	1276.4	1298.4	1324.6	1347.1
17.5°	1000.9	1046.8	1094.7	1144.2	1188.1	1226.5	1257.6	1285.3	1308.8	1337.7	1368.2
20°	989.8	1039.3	1089.2	1142.2	1184.1	1223.4	1253.5	1282.3	1311.5	1349.2	1386.4
22.5°	974.2	1027.1	1080.1	1130.3	1174.6	1212.6	1243.7	1279.0	1317.3	1360.0	1405.1
25°	949.6	1004.2	1056.6	1104.5	1147.7	1186.7	1229.0	1276.4	1323.0	1379.2	1444.1
27.5°	918.4	970.9	1017.8	1068.4	1111.3	1160.8	1213.7	1265.0	1332.2	1409.7	1490.5
30°	895.0	944.9	989.4	1037.2	1085.9	1140.5	1199.8	1260.3	1340.3	1431.3	1527.5
32.5°	867.9	913.1	957.2	1003.3	1059.5	1119.5	1182.5	1256.5	1352.2	1455.7	1555.2
35°	820.8	861.5	904.2	955.4	1015.2	1080.4	1160.8	1251.0	1366.5	1477.9	1567.2
37.5°	771.6	803.6	846.6	900.7	965.6	1041.1	1132.4	1241.9	1360.7	1460.5	1498.5
40°	733.7	763.7	809.0	865.8	930.1	1012.6	1115.1	1227.7	1347.1	1416.5	1413.6
42.5°	696.0	726.4	770.1	827.1	894.2	986.6	1092.1	1209.1	1309.9	1336.3	1281.2
45°	638.4	666.8	709.6	767.1	839.1	936.0	1046.9	1159.1	1223.4	1180.7	1071.5
47.5°	579.7	607.2	646.9	703.3	781.8	883.3	988.1	1080.2	1089.2	997.4	866.4
50°	541.0	566.9	604.5	664.6	740.9	839.9	941.1	1013.5	991.1	878.9	743.8
52.5°	503.4	528.2	563.5	620.3	698.1	795.2	885.6	942.3	890.5	771.2	649.6
55°	447.9	471.6	507.2	559.2	629.9	718.8	798.0	818.7	742.6	622.3	524.1
57.5°	395.2	412.5	447.7	493.7	561.8	640.3	697.0	693.2	609.2	500.9	430.5
60°	360.3	375.9	409.4	451.7	516.5	586.8	626.6	609.6	524.5	435.2	367.5
62.5°	327.8	342.4	370.4	409.4	465.0	526.1	555.1	531.7	451.3	372.9	319.0
65°	278.6	289.1	311.6	347.6	391.2	433.5	459.3	425.0	353.9	294.6	254.0
67.5°	232.6	241.7	261.7	287.6	317.6	346.8	357.3	325.1	269.9	229.9	201.3
70°	202.8	211.2	224.8	248.9	268.8	289.6	294.6	265.9	219.7	189.2	171.5
72.5°	174.3	182.1	194.0	211.0	224.8	236.8	239.1	212.4	177.0	156.0	142.4
75°	132.9	139.7	147.3	153.7	162.6	164.7	163.8	143.1	124.0	110.1	102.5
77.5°	97.7	100.5	105.2	107.7	108.1	107.9	103.6	90.5	80.7	74.9	71.8
80°	75.3	77.5	78.8	79.6	80.0	75.7	71.1	63.1	59.7	56.3	52.5
82.5°	54.7	56.2	57.4	57.6	55.3	51.8	47.5	43.5	41.1	39.4	37.9
85°	29.6	30.1	29.6	27.6	24.5	23.3	22.4	21.6	21.2	20.7	20.7
87.5°	10.9	10.3	8.8	9.5	9.7	9.6	9.9	9.9	9.8	9.9	10.1
90°	2.3	3.8	5.2	6.7	8.1	9.4	10.6	11.9	13.2	14.1	15.0
92.5°	11.7	10.7	9.6	8.6	8.6	9.8	10.9	12.1	13.2	14.1	15.0
95°	46.5	45.9	45.3	44.8	41.0	34.1	27.1	20.1	13.2	14.1	15.0
97.5°	99.1	100.1	101.1	102.1	95.7	81.9	68.2	54.4	40.6	35.4	30.2
100°	138.3	138.8	139.3	139.9	140.6	141.3	142.0	142.8	143.5	116.2	88.9
102.5°	178.6	179.4	180.0	180.8	181.3	181.7	182.1	182.6	183.0	177.9	172.7
105°	243.1	243.9	244.6	245.3	245.7	245.7	245.7	245.7	245.7	245.7	245.7
107.5°	309.4	309.4	309.4	309.4	309.6	309.9	310.3	310.6	311.0	311.0	311.1
110°	352.9	352.9	352.9	352.9	353.1	353.4	353.8	354.2	354.6	354.0	353.4



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	394.3	394.7	395.1	395.6	395.9	396.2	396.3	396.6	396.8	396.1	395.4
115°	456.1	457.0	457.9	458.9	459.3	459.6	459.7	459.9	460.1	459.3	458.6
117.5°	518.6	518.6	518.5	518.5	518.9	519.5	520.2	520.9	521.6	520.7	519.8
120°	558.1	557.8	557.7	557.5	557.7	558.2	558.8	559.3	559.9	559.5	559.1
122.5°	593.9	594.6	595.3	596.0	596.5	596.7	597.0	597.2	597.5	597.1	596.7
125°	648.6	649.9	651.1	652.4	653.1	653.1	653.1	653.1	653.1	652.3	651.6
127.5°	699.9	700.7	701.6	702.5	703.0	702.9	702.8	702.6	702.5	702.1	701.7
130°	731.5	732.4	733.3	734.3	734.7	735.0	735.2	735.3	735.5	735.0	734.4
132.5°	763.3	764.3	765.4	766.5	766.8	766.4	766.0	765.6	765.2	765.1	765.0
135°	808.4	809.4	810.6	811.6	812.0	811.6	811.3	810.9	810.6	810.2	809.8
137.5°	849.6	850.5	851.5	852.5	852.8	852.5	852.2	851.7	851.4	851.5	851.6
140°	876.0	876.4	876.8	877.2	877.3	877.1	876.9	876.7	876.5	876.9	877.3
142.5°	900.3	900.6	900.7	901.0	901.2	901.5	901.7	902.0	902.2	902.3	902.4
145°	936.3	936.6	937.0	937.3	937.5	937.5	937.5	937.5	937.5	937.8	937.9
147.5°	967.2	967.1	967.0	966.9	967.0	967.2	967.4	967.7	967.8	968.1	968.3
150°	986.7	986.3	985.9	985.5	985.5	985.9	986.3	986.7	987.0	987.4	987.7
152.5°	1005.3	1004.5	1003.7	1002.9	1002.7	1003.1	1003.5	1003.8	1004.1	1004.5	1004.9
155°	1029.6	1028.5	1027.4	1026.3	1026.0	1026.3	1026.7	1027.0	1027.4	1027.9	1028.5
157.5°	1049.0	1048.4	1047.7	1047.0	1046.8	1046.8	1046.8	1046.8	1046.8	1047.5	1048.1
160°	1061.8	1060.7	1059.6	1058.5	1058.0	1058.2	1058.4	1058.6	1058.7	1059.5	1060.2
162.5°	1072.4	1071.2	1070.2	1069.0	1068.5	1068.8	1068.9	1069.1	1069.3	1070.3	1071.4
165°	1086.5	1085.4	1084.3	1083.2	1082.7	1083.0	1083.1	1083.3	1083.5	1084.6	1085.7
167.5°	1097.1	1095.9	1094.8	1093.6	1093.2	1093.3	1093.5	1093.7	1093.9	1095.2	1096.5
170°	1102.9	1101.6	1100.2	1098.9	1098.5	1098.6	1098.8	1098.9	1099.2	1100.7	1102.1
172.5°	1106.8	1105.5	1104.2	1102.9	1102.4	1102.8	1103.1	1103.4	1103.8	1105.1	1106.4
175°	1111.3	1110.1	1109.1	1107.9	1107.5	1107.7	1107.8	1108.1	1108.2	1109.7	1111.2
177.5°	1113.5	1112.6	1111.7	1110.8	1110.4	1110.6	1110.8	1110.8	1111.0	1112.1	1113.0
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1076.3	1076.3	1082.1	1081.7	1085.5	1084.1	1084.8
5°	1157.0	1164.2	1170.5	1174.8	1181.1	1182.8	1181.9
7.5°	1240.6	1256.6	1264.4	1275.1	1277.1	1282.6	1282.1
10°	1292.5	1308.1	1320.0	1329.3	1334.0	1339.9	1340.3
12.5°	1333.1	1346.4	1356.9	1365.5	1371.2	1373.0	1374.2
15°	1364.9	1379.6	1392.0	1404.2	1411.4	1416.9	1419.9
17.5°	1396.9	1419.8	1441.4	1458.1	1468.1	1476.5	1476.4
20°	1421.6	1447.8	1475.0	1494.0	1513.4	1521.9	1523.2
22.5°	1448.0	1488.2	1523.1	1552.6	1578.2	1587.0	1590.2
25°	1502.8	1555.3	1609.2	1650.7	1680.3	1697.6	1700.1
27.5°	1569.1	1640.2	1696.8	1735.0	1759.7	1772.5	1775.3
30°	1615.9	1681.6	1732.3	1761.1	1772.5	1774.3	1767.9
32.5°	1636.9	1686.0	1706.3	1704.5	1682.1	1667.2	1661.5
35°	1611.3	1601.1	1551.5	1492.3	1447.0	1418.2	1410.5
37.5°	1466.3	1378.7	1287.5	1198.0	1150.3	1126.1	1084.4
40°	1323.4	1198.5	1103.7	1028.3	974.5	931.3	921.2
42.5°	1162.1	1033.2	938.4	873.8	831.0	801.3	788.4
45°	933.9	823.0	744.7	695.1	662.1	640.5	630.8
47.5°	747.0	661.1	604.1	567.4	542.3	523.4	518.2
50°	644.3	575.8	527.5	496.6	477.5	463.2	457.2
52.5°	559.6	504.3	467.2	441.7	423.7	414.7	409.8
55°	461.9	414.0	387.3	367.0	356.9	349.7	346.3
57.5°	377.7	343.2	323.7	309.7	300.3	295.6	294.0
60°	330.6	303.5	285.8	274.8	268.4	262.4	260.8
62.5°	288.9	267.7	253.9	244.3	237.9	235.4	234.4
65°	232.8	218.9	208.7	202.8	197.7	196.9	196.4
67.5°	185.1	176.8	171.5	165.3	163.5	160.6	160.0
70°	158.3	152.8	146.5	144.4	142.3	139.3	139.7
72.5°	134.3	128.8	124.5	121.6	120.9	119.6	120.7
75°	98.2	96.5	94.8	92.7	91.9	91.9	91.5
77.5°	70.1	68.6	66.8	65.6	65.3	63.5	64.2
80°	50.8	48.7	47.9	48.3	47.0	46.6	46.6
82.5°	37.6	36.9	36.0	36.0	35.8	35.4	35.7
85°	20.7	20.3	20.3	19.9	19.9	19.5	19.5
87.5°	10.6	11.2	10.6	10.4	10.5	10.9	11.4
90°	16.0	16.9	17.6	18.2	18.7	19.2	19.8
92.5°	16.0	16.9	17.4	17.7	17.9	18.2	18.5
95°	16.0	16.9	17.3	17.3	17.3	17.3	17.3
97.5°	25.0	19.9	17.3	17.3	17.3	17.3	17.3
100°	61.6	34.2	20.2	19.5	18.8	18.0	17.3
102.5°	167.5	162.4	153.6	141.1	128.7	116.2	103.7
105°	245.7	245.7	245.6	245.5	245.2	245.1	244.9
107.5°	311.1	311.2	311.0	310.4	309.8	309.2	308.8
110°	352.9	352.4	352.2	352.4	352.5	352.7	352.9



TEST NUMBER: P333688-930

CATALOG NUMBER: S125RDIW-S850D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	394.7	394.0	393.5	393.3	393.0	392.7	392.5
115°	457.9	457.1	456.2	455.2	454.0	453.0	451.8
117.5°	518.8	517.8	517.1	516.7	516.2	515.7	515.2
120°	558.8	558.4	557.7	556.8	556.0	555.1	554.1
122.5°	596.4	596.0	595.3	594.3	593.2	592.2	591.1
125°	650.9	650.1	649.5	649.0	648.4	647.8	647.3
127.5°	701.3	700.9	700.0	698.7	697.3	695.9	694.6
130°	733.9	733.3	732.5	731.6	730.8	729.9	729.0
132.5°	764.8	764.8	764.3	763.4	762.4	761.5	760.6
135°	809.4	809.1	808.4	807.2	806.2	805.0	804.0
137.5°	851.7	851.7	851.3	850.4	849.4	848.5	847.5
140°	877.6	878.0	877.6	876.5	875.4	874.3	873.2
142.5°	902.5	902.5	902.0	900.9	899.8	898.7	897.6
145°	938.1	938.2	937.8	936.7	935.6	934.5	933.4
147.5°	968.6	968.7	968.2	966.9	965.6	964.3	963.0
150°	988.1	988.5	987.9	986.4	985.0	983.5	982.0
152.5°	1005.3	1005.6	1005.2	1003.8	1002.5	1001.2	999.9
155°	1029.1	1029.6	1029.2	1027.7	1026.2	1024.7	1023.3
157.5°	1048.6	1049.2	1048.8	1047.3	1045.9	1044.4	1042.9
160°	1060.9	1061.7	1061.3	1059.9	1058.4	1057.0	1055.5
162.5°	1072.4	1073.4	1073.1	1071.5	1069.9	1068.3	1066.7
165°	1086.8	1087.9	1087.7	1086.2	1084.8	1083.3	1081.8
167.5°	1097.8	1099.2	1099.0	1097.3	1095.7	1094.1	1092.4
170°	1103.6	1105.1	1104.9	1103.3	1101.6	1100.0	1098.3
172.5°	1107.7	1109.1	1108.9	1107.3	1105.5	1103.9	1102.3
175°	1112.6	1114.1	1114.0	1112.3	1110.7	1109.1	1107.4
177.5°	1114.1	1115.2	1115.1	1113.9	1112.7	1111.6	1110.4
180°	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3	1112.3

(END OF REPORT)