

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333697-930

Luminaire Tested: **S125RDIW-S850D1560U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333697-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U930-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7084.3 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333697-930
CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	39	32				
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24				
4	73	62	55	49	66	57	51	45	47	42	38	37	34	31	29	26	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	21	18				
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16				
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17	14				
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13				
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11				
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6660	6660	6660	6660
5°	7662	6669	5890	6669
10°	8790	6635	5197	6635
15°	9494	6567	4619	6567
20°	10469	6488	4265	6488
25°	12115	6383	3958	6383
30°	13184	6272	3757	6272
35°	11121	6144	3572	6144
40°	7766	5914	3412	5914
45°	5761	5602	3255	5602
50°	4594	5279	3122	5279
55°	3899	4877	3003	4877
60°	3369	4517	2811	4517
65°	3001	4128	2419	4128
70°	2638	3780	2206	3780
75°	2283	3276	2071	3276
80°	1733	2756	1733	2756
85°	1445	2164	1630	2164



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.9	1.4
10°-20°	289.8	4.1
20°-30°	459.5	6.5
30°-40°	554.1	7.8
40°-50°	494.9	7.0
50°-60°	379.5	5.4
60°-70°	246.6	3.5
70°-80°	119.9	1.7
80°-90°	32.1	0.5
90°-100°	105.8	1.5
100°-110°	312.5	4.4
110°-120°	529.3	7.5
120°-130°	696.6	9.8
130°-140°	780.6	11.0
140°-150°	765.0	10.8
150°-160°	642.6	9.1
160°-170°	427.1	6.0
170°-180°	149.5	2.1
0°-30°	848.2	12.0
0°-40°	1402.4	19.8
0°-60°	2276.7	32.1
0°-90°	2675.3	37.8
90°-120°	947.6	13.4
90°-150°	3189.8	45.0
90°-180°	4409.0	62.2
0°-180°	7084.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1031	1031	1031	1031	1031	
5°	1182	1029	908	1029	1182	118
15°	1420	982	691	982	1420	407
25°	1700	896	556	896	1700	781
35°	1410	779	453	779	1410	852
45°	631	613	356	613	631	503
55°	346	433	267	433	346	314
65°	196	270	158	270	196	195
75°	92	131	83	131	92	97
85°	20	29	22	29	20	23
90°	30	1	30	1	30	18
95°	106	80	106	80	106	108
105°	305	280	305	280	305	323
115°	535	530	535	530	535	529
125°	778	773	778	773	778	695
135°	1010	1006	1010	1006	1010	779
145°	1223	1218	1223	1218	1223	764
155°	1394	1394	1394	1394	1394	642
165°	1512	1516	1512	1516	1512	426
175°	1570	1576	1570	1576	1570	149
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1084.8	1084.1	1085.5	1081.7	1082.1	1076.3	1076.3	1071.9	1066.2	1061.8	1059.7
5°	1181.9	1182.8	1181.1	1174.8	1170.5	1164.2	1157.0	1144.3	1133.7	1123.6	1115.5
7.5°	1282.1	1282.6	1277.1	1275.1	1264.4	1256.6	1240.6	1223.4	1208.0	1188.5	1173.7
10°	1340.3	1339.9	1334.0	1329.3	1320.0	1308.1	1292.5	1272.1	1253.1	1231.9	1211.6
12.5°	1374.2	1373.0	1371.2	1365.5	1356.9	1346.4	1333.1	1313.1	1289.6	1266.5	1242.8
15°	1419.9	1416.9	1411.4	1404.2	1392.0	1379.6	1364.9	1347.1	1324.6	1298.4	1276.4
17.5°	1476.4	1476.5	1468.1	1458.1	1441.4	1419.8	1396.9	1368.2	1337.7	1308.8	1285.3
20°	1523.2	1521.9	1513.4	1494.0	1475.0	1447.8	1421.6	1386.4	1349.2	1311.5	1282.3
22.5°	1590.2	1587.0	1578.2	1552.6	1523.1	1488.2	1448.0	1405.1	1360.0	1317.3	1279.0
25°	1700.1	1697.6	1680.3	1650.7	1609.2	1555.3	1502.8	1444.1	1379.2	1323.0	1276.4
27.5°	1775.3	1772.5	1759.7	1735.0	1696.8	1640.2	1569.1	1490.5	1409.7	1332.2	1265.0
30°	1767.9	1774.3	1772.5	1761.1	1732.3	1681.6	1615.9	1527.5	1431.3	1340.3	1260.3
32.5°	1661.5	1667.2	1682.1	1704.5	1706.3	1686.0	1636.9	1555.2	1455.7	1352.2	1256.5
35°	1410.5	1418.2	1447.0	1492.3	1551.5	1601.1	1611.3	1567.2	1477.9	1366.5	1251.0
37.5°	1084.4	1126.1	1150.3	1198.0	1287.5	1378.7	1466.3	1498.5	1460.5	1360.7	1241.9
40°	921.2	931.3	974.5	1028.3	1103.7	1198.5	1323.4	1413.6	1416.5	1347.1	1227.7
42.5°	788.4	801.3	831.0	873.8	938.4	1033.2	1162.1	1281.2	1336.3	1309.9	1209.1
45°	630.8	640.5	662.1	695.1	744.7	823.0	933.9	1071.5	1180.7	1223.4	1159.1
47.5°	518.2	523.4	542.3	567.4	604.1	661.1	747.0	866.4	997.4	1089.2	1080.2
50°	457.2	463.2	477.5	496.6	527.5	575.8	644.3	743.8	878.9	991.1	1013.5
52.5°	409.8	414.7	423.7	441.7	467.2	504.3	559.6	649.6	771.2	890.5	942.3
55°	346.3	349.7	356.9	367.0	387.3	414.0	461.9	524.1	622.3	742.6	818.7
57.5°	294.0	295.6	300.3	309.7	323.7	343.2	377.7	430.5	500.9	609.2	693.2
60°	260.8	262.4	268.4	274.8	285.8	303.5	330.6	367.5	435.2	524.5	609.6
62.5°	234.4	235.4	237.9	244.3	253.9	267.7	288.9	319.0	372.9	451.3	531.7
65°	196.4	196.9	197.7	202.8	208.7	218.9	232.8	254.0	294.6	353.9	425.0
67.5°	160.0	160.6	163.5	165.3	171.5	176.8	185.1	201.3	229.9	269.9	325.1
70°	139.7	139.3	142.3	144.4	146.5	152.8	158.3	171.5	189.2	219.7	265.9
72.5°	120.7	119.6	120.9	121.6	124.5	128.8	134.3	142.4	156.0	177.0	212.4
75°	91.5	91.9	91.9	92.7	94.8	96.5	98.2	102.5	110.1	124.0	143.1
77.5°	64.2	63.5	65.3	65.6	66.8	68.6	70.1	71.8	74.9	80.7	90.5
80°	46.6	46.6	47.0	48.3	47.9	48.7	50.8	52.5	56.3	59.7	63.1
82.5°	35.7	35.4	35.8	36.0	36.0	36.9	37.6	37.9	39.4	41.1	43.5
85°	19.5	19.5	19.9	19.9	20.3	20.3	20.7	20.7	20.7	21.2	21.6
87.5°	13.4	12.9	12.3	12.1	12.4	12.8	12.2	11.6	11.3	11.0	11.0
90°	29.5	28.7	27.9	27.1	26.3	25.1	23.8	22.4	21.0	19.6	17.8
92.5°	58.0	57.4	56.8	56.3	55.6	54.5	52.6	50.8	49.0	47.2	44.8
95°	105.7	105.2	104.7	104.1	103.5	102.3	100.4	98.5	96.6	94.7	92.0
97.5°	160.4	160.0	159.7	159.4	159.1	157.9	156.1	154.3	152.5	150.7	147.0
100°	201.6	201.1	200.6	200.0	199.5	198.0	195.5	193.1	190.6	188.1	184.6
102.5°	243.0	242.2	241.4	240.7	239.9	238.1	235.5	232.8	230.2	227.5	225.7
105°	304.9	304.1	303.3	302.5	301.7	300.4	298.8	297.2	295.5	293.9	292.2
107.5°	368.4	368.4	368.5	368.5	368.6	368.2	367.4	366.6	365.7	364.9	363.7
110°	415.6	415.9	416.1	416.5	416.7	416.5	415.6	414.8	413.9	413.1	412.3



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.9	462.4	462.8	463.3	463.8	463.8	463.5	463.1	462.7	462.4	461.3
115°	534.9	535.2	535.4	535.7	536.0	536.2	536.5	536.8	537.0	537.4	536.8
117.5°	606.2	607.3	608.4	609.4	610.6	611.0	610.8	610.6	610.3	610.2	609.6
120°	655.4	656.5	657.5	658.7	659.7	660.3	660.3	660.3	660.3	660.3	660.0
122.5°	704.6	705.4	706.3	707.2	708.1	708.6	708.8	709.1	709.2	709.5	708.7
125°	778.4	778.6	778.9	779.2	779.4	779.8	780.4	781.0	781.5	782.0	781.8
127.5°	849.1	849.7	850.3	850.8	851.3	851.7	852.1	852.3	852.6	852.9	852.6
130°	896.4	896.9	897.5	898.1	898.5	898.9	899.3	899.5	899.8	900.1	899.5
132.5°	940.6	941.4	942.2	943.0	943.7	944.2	944.5	944.8	945.0	945.3	945.4
135°	1009.5	1010.6	1011.7	1012.8	1013.9	1014.4	1014.4	1014.4	1014.4	1014.4	1014.2
137.5°	1076.8	1078.2	1079.6	1081.0	1082.4	1082.9	1082.6	1082.2	1081.9	1081.6	1080.9
140°	1120.1	1121.5	1122.9	1124.3	1125.6	1126.0	1125.5	1124.9	1124.4	1123.9	1123.1
142.5°	1161.5	1162.9	1164.2	1165.6	1166.9	1167.5	1167.1	1166.8	1166.4	1166.1	1165.1
145°	1223.4	1224.3	1225.1	1225.9	1226.7	1227.1	1227.1	1227.1	1227.1	1227.1	1226.3
147.5°	1276.4	1278.2	1280.0	1281.9	1283.8	1284.3	1283.7	1283.0	1282.4	1281.7	1281.1
150°	1315.6	1316.2	1316.8	1317.3	1317.8	1318.2	1318.2	1318.2	1318.2	1318.2	1317.0
152.5°	1348.2	1349.2	1350.1	1351.1	1352.1	1352.3	1351.6	1351.0	1350.3	1349.6	1349.2
155°	1394.4	1395.7	1397.1	1398.5	1399.9	1400.0	1398.9	1397.7	1396.7	1395.6	1395.3
157.5°	1433.0	1434.8	1436.6	1438.4	1440.2	1440.6	1439.5	1438.4	1437.3	1436.1	1435.9
160°	1459.5	1460.9	1462.2	1463.6	1465.0	1465.2	1464.0	1463.0	1461.8	1460.8	1460.5
162.5°	1482.1	1483.8	1485.3	1486.9	1488.5	1488.7	1487.4	1486.0	1484.7	1483.4	1483.4
165°	1512.4	1514.1	1515.7	1517.4	1519.0	1519.2	1518.2	1517.0	1516.0	1514.9	1514.6
167.5°	1536.5	1538.2	1539.9	1541.6	1543.3	1543.3	1541.6	1540.0	1538.4	1536.8	1536.8
170°	1549.3	1551.2	1553.1	1555.0	1557.0	1557.1	1555.4	1553.8	1552.2	1550.5	1550.5
172.5°	1560.2	1561.8	1563.5	1565.2	1566.9	1566.9	1565.3	1563.7	1562.0	1560.4	1560.4
175°	1570.2	1572.1	1574.0	1576.0	1577.8	1578.0	1576.4	1574.8	1573.0	1571.4	1571.4
177.5°	1576.1	1577.6	1579.2	1580.7	1582.3	1582.3	1581.0	1579.7	1578.4	1577.1	1577.3
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1059.7	1057.4	1053.0	1048.9	1043.8	1039.4	1036.3	1032.7	1027.8	1022.1	1017.4
5°	1106.6	1097.3	1085.0	1074.5	1060.9	1050.4	1039.3	1028.7	1018.1	1004.6	992.7
7.5°	1158.6	1139.4	1120.7	1097.1	1075.8	1056.7	1038.4	1019.9	1001.8	982.6	964.0
10°	1190.4	1167.2	1141.3	1111.7	1084.6	1058.7	1035.1	1011.8	987.2	965.6	942.3
12.5°	1220.3	1190.2	1160.7	1123.2	1090.7	1059.2	1029.0	1000.0	973.7	945.7	920.7
15°	1247.2	1217.6	1184.5	1138.8	1093.5	1055.4	1019.9	982.2	949.6	918.3	890.3
17.5°	1257.6	1226.5	1188.1	1144.2	1094.7	1046.8	1000.9	959.6	921.3	884.8	853.4
20°	1253.5	1223.4	1184.1	1142.2	1089.2	1039.3	989.8	944.0	901.3	862.7	829.3
22.5°	1243.7	1212.6	1174.6	1130.3	1080.1	1027.1	974.2	925.4	880.6	840.7	804.3
25°	1229.0	1186.7	1147.7	1104.5	1056.6	1004.2	949.6	895.8	848.0	807.3	767.5
27.5°	1213.7	1160.8	1111.3	1068.4	1017.8	970.9	918.4	863.2	812.9	771.5	730.7
30°	1199.8	1140.5	1085.9	1037.2	989.4	944.9	895.0	841.1	789.5	746.8	705.3
32.5°	1182.5	1119.5	1059.5	1003.3	957.2	913.1	867.9	816.4	766.1	722.0	679.9
35°	1160.8	1080.4	1015.2	955.4	904.2	861.5	820.8	779.3	729.0	683.3	642.2
37.5°	1132.4	1041.1	965.6	900.7	846.6	803.6	771.6	733.7	687.7	643.9	605.8
40°	1115.1	1012.6	930.1	865.8	809.0	763.7	733.7	701.5	659.6	618.5	580.4
42.5°	1092.1	986.6	894.2	827.1	770.1	726.4	696.0	668.0	632.8	594.1	553.3
45°	1046.9	936.0	839.1	767.1	709.6	666.8	638.4	613.4	586.8	551.2	515.6
47.5°	988.1	883.3	781.8	703.3	646.9	607.2	579.7	559.9	540.9	510.6	476.1
50°	941.1	839.9	740.9	664.6	604.5	566.9	541.0	525.4	508.0	480.5	451.7
52.5°	885.6	795.2	698.1	620.3	563.5	528.2	503.4	487.8	473.4	451.0	423.6
55°	798.0	718.8	629.9	559.2	507.2	471.6	447.9	433.1	424.6	405.5	384.0
57.5°	697.0	640.3	561.8	493.7	447.7	412.5	395.2	382.5	373.0	359.5	344.3
60°	626.6	586.8	516.5	451.7	409.4	375.9	360.3	349.7	340.8	329.4	317.5
62.5°	555.1	526.1	465.0	409.4	370.4	342.4	327.8	318.2	307.9	300.3	288.7
65°	459.3	433.5	391.2	347.6	311.6	289.1	278.6	270.1	263.7	255.3	247.2
67.5°	357.3	346.8	317.6	287.6	261.7	241.7	232.6	226.7	219.1	213.9	208.5
70°	294.6	289.6	268.8	248.9	224.8	211.2	202.8	200.2	190.9	185.9	182.1
72.5°	239.1	236.8	224.8	211.0	194.0	182.1	174.3	171.5	165.5	161.4	159.0
75°	163.8	164.7	162.6	153.7	147.3	139.7	132.9	131.3	127.0	123.6	121.5
77.5°	103.6	107.9	108.1	107.7	105.2	100.5	97.7	96.4	92.3	91.0	90.5
80°	71.1	75.7	80.0	79.6	78.8	77.5	75.3	74.1	72.0	70.7	69.9
82.5°	47.5	51.8	55.3	57.6	57.4	56.2	54.7	54.1	53.6	52.7	52.6
85°	22.4	23.3	24.5	27.6	29.6	30.1	29.6	29.2	28.0	28.4	28.8
87.5°	10.9	10.6	10.5	10.1	9.4	10.6	11.2	11.1	10.8	10.6	10.4
90°	15.8	13.9	12.0	9.9	7.8	5.6	3.4	1.2	3.4	5.6	7.8
92.5°	42.5	40.2	37.8	35.9	34.3	32.9	31.3	29.8	31.3	32.9	34.3
95°	89.2	86.5	83.7	82.1	81.5	81.0	80.5	79.9	80.5	81.0	81.5
97.5°	143.2	139.4	135.7	133.7	133.5	133.2	133.0	132.8	133.0	133.2	133.5
100°	181.0	177.5	173.9	172.1	172.1	172.1	172.1	172.1	172.1	172.1	172.1
102.5°	223.9	222.1	220.3	218.8	217.7	216.6	215.6	214.4	215.6	216.6	217.7
105°	290.6	288.9	287.3	285.8	284.5	283.1	281.7	280.4	281.7	283.1	284.5
107.5°	362.4	361.2	360.0	358.6	357.3	355.9	354.5	353.1	354.5	355.9	357.3
110°	411.5	410.7	409.9	408.8	407.4	406.0	404.7	403.3	404.7	406.0	407.4



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	460.2	459.2	458.2	457.3	456.6	455.9	455.2	454.4	455.2	455.9	456.6
115°	536.2	535.7	535.2	534.3	533.2	532.1	531.1	529.9	531.1	532.1	533.2
117.5°	609.1	608.6	608.1	607.6	607.2	606.7	606.2	605.7	606.2	606.7	607.2
120°	659.7	659.5	659.2	658.4	657.0	655.7	654.3	652.9	654.3	655.7	657.0
122.5°	708.1	707.4	706.6	706.0	705.6	705.1	704.6	704.1	704.6	705.1	705.6
125°	781.5	781.2	781.0	780.0	778.4	776.7	775.0	773.4	775.0	776.7	778.4
127.5°	852.2	851.9	851.6	850.9	849.9	849.1	848.2	847.2	848.2	849.1	849.9
130°	898.9	898.5	897.9	896.9	895.5	894.2	892.8	891.4	892.8	894.2	895.5
132.5°	945.5	945.7	945.7	944.7	942.5	940.2	938.0	935.7	938.0	940.2	942.5
135°	1013.9	1013.6	1013.3	1012.4	1010.7	1009.1	1007.5	1005.8	1007.5	1009.1	1010.7
137.5°	1080.4	1079.8	1079.1	1078.1	1076.4	1074.9	1073.3	1071.7	1073.3	1074.9	1076.4
140°	1122.3	1121.4	1120.5	1119.5	1118.1	1116.7	1115.4	1114.0	1115.4	1116.7	1118.1
142.5°	1164.1	1163.0	1162.0	1160.9	1159.8	1158.6	1157.5	1156.3	1157.5	1158.6	1159.8
145°	1225.5	1224.7	1223.8	1222.9	1221.8	1220.7	1219.6	1218.5	1219.6	1220.7	1221.8
147.5°	1280.4	1279.8	1279.1	1278.5	1277.9	1277.2	1276.7	1276.1	1276.7	1277.2	1277.9
150°	1316.0	1314.8	1313.8	1313.4	1313.6	1313.9	1314.2	1314.4	1314.2	1313.9	1313.6
152.5°	1348.7	1348.3	1347.9	1347.4	1347.0	1346.7	1346.3	1345.9	1346.3	1346.7	1347.0
155°	1395.1	1394.8	1394.5	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4
157.5°	1435.7	1435.3	1435.1	1435.3	1435.8	1436.5	1437.0	1437.6	1437.0	1436.5	1435.8
160°	1460.2	1460.0	1459.7	1460.0	1460.8	1461.6	1462.4	1463.2	1462.4	1461.6	1460.8
162.5°	1483.3	1483.2	1483.2	1483.4	1484.1	1484.7	1485.2	1485.9	1485.2	1484.7	1484.1
165°	1514.3	1514.1	1513.8	1513.9	1514.5	1515.0	1515.6	1516.1	1515.6	1515.0	1514.5
167.5°	1536.8	1536.8	1536.8	1537.3	1538.4	1539.5	1540.6	1541.6	1540.6	1539.5	1538.4
170°	1550.5	1550.5	1550.5	1551.1	1552.2	1553.2	1554.4	1555.4	1554.4	1553.2	1552.2
172.5°	1560.4	1560.4	1560.4	1560.9	1562.0	1563.1	1564.2	1565.3	1564.2	1563.1	1562.0
175°	1571.4	1571.4	1571.4	1572.0	1573.0	1574.2	1575.2	1576.4	1575.2	1574.2	1573.0
177.5°	1577.5	1577.8	1577.9	1578.5	1579.4	1580.3	1581.1	1582.0	1581.1	1580.3	1579.4
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1014.0	1009.3	1005.8	999.1	994.3	992.3	988.6	987.6	991.3	988.6	988.2
5°	983.8	971.6	961.8	952.1	941.5	934.7	924.5	922.9	920.3	916.6	915.7
7.5°	947.7	931.7	919.2	903.1	889.1	877.8	865.1	859.2	855.8	850.9	844.3
10°	923.3	904.2	887.3	871.2	853.9	839.9	827.2	817.5	811.1	805.2	802.7
12.5°	899.3	879.9	858.2	838.7	819.4	803.6	789.6	783.3	776.2	769.3	763.4
15°	861.9	836.1	812.4	789.9	773.5	756.5	743.0	733.7	723.1	720.1	708.7
17.5°	822.3	797.0	769.2	745.6	726.4	707.8	692.9	682.3	674.4	663.5	658.2
20°	797.6	767.5	740.5	718.8	697.7	675.6	660.4	651.5	643.9	635.0	630.8
22.5°	771.2	741.8	714.0	688.7	667.2	645.6	634.7	625.4	616.8	608.6	603.0
25°	732.4	702.8	673.5	647.3	624.8	609.2	596.5	585.9	581.2	573.2	567.3
27.5°	694.1	662.5	632.2	606.1	588.5	573.0	562.6	554.2	545.8	538.7	533.6
30°	669.3	637.2	604.1	583.3	564.8	549.9	538.5	530.4	524.1	517.7	514.0
32.5°	644.6	611.4	582.1	559.6	542.0	529.3	517.5	509.8	503.1	496.1	491.6
35°	605.0	571.1	547.4	525.4	508.0	496.2	488.1	477.1	471.6	466.5	461.9
37.5°	568.1	536.6	510.9	491.7	476.6	464.8	454.4	448.5	441.7	437.2	433.3
40°	541.0	512.3	488.9	468.6	457.6	444.5	434.8	427.1	422.1	416.1	411.9
42.5°	516.7	489.9	467.2	449.0	435.3	424.2	414.8	407.2	400.7	396.5	393.0
45°	482.2	455.5	433.5	416.5	403.9	393.3	383.5	379.8	371.3	366.2	364.5
47.5°	446.5	422.7	401.5	385.8	372.8	362.8	353.7	345.8	341.2	336.2	333.5
50°	422.5	399.7	379.8	364.5	351.8	340.8	332.3	327.3	320.9	316.3	312.8
52.5°	398.4	377.3	357.4	342.8	331.8	320.8	311.4	306.2	300.3	297.3	294.9
55°	364.1	341.6	324.7	310.3	298.9	288.7	279.8	274.8	270.9	268.0	267.1
57.5°	325.1	307.4	291.6	278.7	266.8	257.2	249.4	244.6	241.2	240.8	238.2
60°	299.7	283.6	269.2	255.3	245.1	236.2	229.4	224.0	220.5	220.1	219.3
62.5°	274.3	258.9	245.6	233.3	224.1	215.6	209.1	202.9	200.9	198.8	197.0
65°	236.7	222.7	211.7	201.9	192.2	185.0	178.6	174.8	170.2	167.6	163.0
67.5°	199.7	188.8	178.2	170.0	162.4	155.6	150.3	144.6	141.5	139.4	136.1
70°	175.3	166.8	156.2	147.3	141.4	135.9	131.7	125.3	123.2	121.5	119.8
72.5°	152.2	144.8	135.9	128.7	122.8	117.6	112.7	109.7	107.6	105.9	104.9
75°	119.8	112.6	105.0	99.9	95.7	91.5	88.9	86.7	85.9	85.5	83.8
77.5°	88.0	84.1	78.0	74.0	71.2	69.5	67.3	66.1	66.0	64.2	63.6
80°	67.3	65.2	60.1	58.5	56.3	54.6	53.3	51.2	49.1	48.3	47.0
82.5°	50.1	47.9	45.9	43.2	41.4	40.4	39.1	38.3	38.6	37.4	36.9
85°	26.7	24.5	23.7	23.3	22.4	23.3	22.8	22.4	22.0	21.6	22.0
87.5°	10.4	10.8	10.9	12.0	11.3	12.1	12.3	12.3	12.6	12.8	12.7
90°	9.9	12.0	13.9	15.8	17.8	19.6	21.0	22.4	23.8	25.1	26.3
92.5°	35.9	37.8	40.2	42.5	44.8	47.2	49.0	50.8	52.6	54.5	55.6
95°	82.1	83.7	86.5	89.2	92.0	94.7	96.6	98.5	100.4	102.3	103.5
97.5°	133.7	135.7	139.4	143.2	147.0	150.7	152.5	154.3	156.1	157.9	159.1
100°	172.1	173.9	177.5	181.0	184.6	188.1	190.6	193.1	195.5	198.0	199.5
102.5°	218.8	220.3	222.1	223.9	225.7	227.5	230.2	232.8	235.5	238.1	239.9
105°	285.8	287.3	288.9	290.6	292.2	293.9	295.5	297.2	298.8	300.4	301.7
107.5°	358.6	360.0	361.2	362.4	363.7	364.9	365.7	366.6	367.4	368.2	368.6
110°	408.8	409.9	410.7	411.5	412.3	413.1	413.9	414.8	415.6	416.5	416.7



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	457.3	458.2	459.2	460.2	461.3	462.4	462.7	463.1	463.5	463.8	463.8
115°	534.3	535.2	535.7	536.2	536.8	537.4	537.0	536.8	536.5	536.2	536.0
117.5°	607.6	608.1	608.6	609.1	609.6	610.2	610.3	610.6	610.8	611.0	610.6
120°	658.4	659.2	659.5	659.7	660.0	660.3	660.3	660.3	660.3	660.3	659.7
122.5°	706.0	706.6	707.4	708.1	708.7	709.5	709.2	709.1	708.8	708.6	708.1
125°	780.0	781.0	781.2	781.5	781.8	782.0	781.5	781.0	780.4	779.8	779.4
127.5°	850.9	851.6	851.9	852.2	852.6	852.9	852.6	852.3	852.1	851.7	851.3
130°	896.9	897.9	898.5	898.9	899.5	900.1	899.8	899.5	899.3	898.9	898.5
132.5°	944.7	945.7	945.7	945.5	945.4	945.3	945.0	944.8	944.5	944.2	943.7
135°	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4	1014.4	1014.4	1014.4	1013.9
137.5°	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9	1082.2	1082.6	1082.9	1082.4
140°	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4	1124.9	1125.5	1126.0	1125.6
142.5°	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4	1166.8	1167.1	1167.5	1166.9
145°	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1	1227.1	1227.1	1227.1	1226.7
147.5°	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4	1283.0	1283.7	1284.3	1283.8
150°	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2	1318.2	1318.2	1318.2	1317.8
152.5°	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3	1351.0	1351.6	1352.3	1352.1
155°	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7	1397.7	1398.9	1400.0	1399.9
157.5°	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3	1438.4	1439.5	1440.6	1440.2
160°	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8	1463.0	1464.0	1465.2	1465.0
162.5°	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7	1486.0	1487.4	1488.7	1488.5
165°	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0	1517.0	1518.2	1519.2	1519.0
167.5°	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4	1540.0	1541.6	1543.3	1543.3
170°	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2	1553.8	1555.4	1557.1	1557.0
172.5°	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0	1563.7	1565.3	1566.9	1566.9
175°	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0	1574.8	1576.4	1578.0	1577.8
177.5°	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4	1579.7	1581.0	1582.3	1582.3
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	987.9	984.2	983.2	984.6	983.2	984.2	987.9	988.2	988.6	991.3	987.6
5°	911.4	907.3	909.3	908.5	909.3	907.3	911.4	915.7	916.6	920.3	922.9
7.5°	844.2	838.9	833.4	835.2	833.4	838.9	844.2	844.3	850.9	855.8	859.2
10°	797.1	793.0	790.4	792.5	790.4	793.0	797.1	802.7	805.2	811.1	817.5
12.5°	757.5	755.0	752.8	751.9	752.8	755.0	757.5	763.4	769.3	776.2	783.3
15°	703.6	698.5	696.4	690.9	696.4	698.5	703.6	708.7	720.1	723.1	733.7
17.5°	653.9	652.2	646.7	644.3	646.7	652.2	653.9	658.2	663.5	674.4	682.3
20°	624.4	622.7	617.3	620.6	617.3	622.7	624.4	630.8	635.0	643.9	651.5
22.5°	600.1	596.3	594.5	593.5	594.5	596.3	600.1	603.0	608.6	616.8	625.4
25°	565.6	560.1	558.0	555.5	558.0	560.1	565.6	567.3	573.2	581.2	585.9
27.5°	531.2	528.2	525.5	524.8	525.5	528.2	531.2	533.6	538.7	545.8	554.2
30°	508.8	505.9	503.8	503.8	503.8	505.9	508.8	514.0	517.7	524.1	530.4
32.5°	488.9	486.6	484.5	484.1	484.5	486.6	488.9	491.6	496.1	503.1	509.8
35°	459.7	456.4	455.5	453.0	455.5	456.4	459.7	461.9	466.5	471.6	477.1
37.5°	429.5	426.7	426.6	426.4	426.6	426.7	429.5	433.3	437.2	441.7	448.5
40°	410.3	408.1	407.6	404.7	407.6	408.1	410.3	411.9	416.1	422.1	427.1
42.5°	389.6	388.5	387.0	385.7	387.0	388.5	389.6	393.0	396.5	400.7	407.2
45°	361.5	358.6	358.6	356.4	358.6	358.6	361.5	364.5	366.2	371.3	379.8
47.5°	332.6	330.3	330.5	328.3	330.5	330.3	332.6	333.5	336.2	341.2	345.8
50°	313.2	312.0	311.6	310.7	311.6	312.0	313.2	312.8	316.3	320.9	327.3
52.5°	294.0	293.3	295.0	293.1	295.0	293.3	294.0	294.9	297.3	300.3	306.2
55°	268.0	266.7	269.2	266.7	269.2	266.7	268.0	267.1	268.0	270.9	274.8
57.5°	238.1	236.9	239.2	237.9	239.2	236.9	238.1	238.2	240.8	241.2	244.6
60°	218.4	215.9	217.2	217.6	217.2	215.9	218.4	219.3	220.1	220.5	224.0
62.5°	195.1	193.6	194.4	192.6	194.4	193.6	195.1	197.0	198.8	200.9	202.9
65°	162.2	160.9	159.1	158.3	159.1	160.9	162.2	163.0	167.6	170.2	174.8
67.5°	136.2	133.2	133.1	133.8	133.1	133.2	136.2	136.1	139.4	141.5	144.6
70°	117.2	117.2	116.8	116.8	116.8	117.2	117.2	119.8	121.5	123.2	125.3
72.5°	104.0	103.7	103.0	102.6	103.0	103.7	104.0	104.9	105.9	107.6	109.7
75°	83.8	84.2	83.4	83.0	83.4	84.2	83.8	83.8	85.5	85.9	86.7
77.5°	61.9	60.1	61.1	60.1	61.1	60.1	61.9	63.6	64.2	66.0	66.1
80°	47.0	46.6	47.9	46.6	47.9	46.6	47.0	47.0	48.3	49.1	51.2
82.5°	37.2	36.8	37.3	36.4	37.3	36.8	37.2	36.9	37.4	38.6	38.3
85°	22.4	22.0	21.6	22.0	21.6	22.0	22.4	22.0	21.6	22.0	22.4
87.5°	13.2	13.0	13.2	13.4	13.2	13.0	13.2	12.7	12.8	12.6	12.3
90°	27.1	27.9	28.7	29.5	28.7	27.9	27.1	26.3	25.1	23.8	22.4
92.5°	56.3	56.8	57.4	58.0	57.4	56.8	56.3	55.6	54.5	52.6	50.8
95°	104.1	104.7	105.2	105.7	105.2	104.7	104.1	103.5	102.3	100.4	98.5
97.5°	159.4	159.7	160.0	160.4	160.0	159.7	159.4	159.1	157.9	156.1	154.3
100°	200.0	200.6	201.1	201.6	201.1	200.6	200.0	199.5	198.0	195.5	193.1
102.5°	240.7	241.4	242.2	243.0	242.2	241.4	240.7	239.9	238.1	235.5	232.8
105°	302.5	303.3	304.1	304.9	304.1	303.3	302.5	301.7	300.4	298.8	297.2
107.5°	368.5	368.5	368.4	368.4	368.4	368.5	368.5	368.6	368.2	367.4	366.6
110°	416.5	416.1	415.9	415.6	415.9	416.1	416.5	416.7	416.5	415.6	414.8



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	463.3	462.8	462.4	461.9	462.4	462.8	463.3	463.8	463.8	463.5	463.1
115°	535.7	535.4	535.2	534.9	535.2	535.4	535.7	536.0	536.2	536.5	536.8
117.5°	609.4	608.4	607.3	606.2	607.3	608.4	609.4	610.6	611.0	610.8	610.6
120°	658.7	657.5	656.5	655.4	656.5	657.5	658.7	659.7	660.3	660.3	660.3
122.5°	707.2	706.3	705.4	704.6	705.4	706.3	707.2	708.1	708.6	708.8	709.1
125°	779.2	778.9	778.6	778.4	778.6	778.9	779.2	779.4	779.8	780.4	781.0
127.5°	850.8	850.3	849.7	849.1	849.7	850.3	850.8	851.3	851.7	852.1	852.3
130°	898.1	897.5	896.9	896.4	896.9	897.5	898.1	898.5	898.9	899.3	899.5
132.5°	943.0	942.2	941.4	940.6	941.4	942.2	943.0	943.7	944.2	944.5	944.8
135°	1012.8	1011.7	1010.6	1009.5	1010.6	1011.7	1012.8	1013.9	1014.4	1014.4	1014.4
137.5°	1081.0	1079.6	1078.2	1076.8	1078.2	1079.6	1081.0	1082.4	1082.9	1082.6	1082.2
140°	1124.3	1122.9	1121.5	1120.1	1121.5	1122.9	1124.3	1125.6	1126.0	1125.5	1124.9
142.5°	1165.6	1164.2	1162.9	1161.5	1162.9	1164.2	1165.6	1166.9	1167.5	1167.1	1166.8
145°	1225.9	1225.1	1224.3	1223.4	1224.3	1225.1	1225.9	1226.7	1227.1	1227.1	1227.1
147.5°	1281.9	1280.0	1278.2	1276.4	1278.2	1280.0	1281.9	1283.8	1284.3	1283.7	1283.0
150°	1317.3	1316.8	1316.2	1315.6	1316.2	1316.8	1317.3	1317.8	1318.2	1318.2	1318.2
152.5°	1351.1	1350.1	1349.2	1348.2	1349.2	1350.1	1351.1	1352.1	1352.3	1351.6	1351.0
155°	1398.5	1397.1	1395.7	1394.4	1395.7	1397.1	1398.5	1399.9	1400.0	1398.9	1397.7
157.5°	1438.4	1436.6	1434.8	1433.0	1434.8	1436.6	1438.4	1440.2	1440.6	1439.5	1438.4
160°	1463.6	1462.2	1460.9	1459.5	1460.9	1462.2	1463.6	1465.0	1465.2	1464.0	1463.0
162.5°	1486.9	1485.3	1483.8	1482.1	1483.8	1485.3	1486.9	1488.5	1488.7	1487.4	1486.0
165°	1517.4	1515.7	1514.1	1512.4	1514.1	1515.7	1517.4	1519.0	1519.2	1518.2	1517.0
167.5°	1541.6	1539.9	1538.2	1536.5	1538.2	1539.9	1541.6	1543.3	1543.3	1541.6	1540.0
170°	1555.0	1553.1	1551.2	1549.3	1551.2	1553.1	1555.0	1557.0	1557.1	1555.4	1553.8
172.5°	1565.2	1563.5	1561.8	1560.2	1561.8	1563.5	1565.2	1566.9	1566.9	1565.3	1563.7
175°	1576.0	1574.0	1572.1	1570.2	1572.1	1574.0	1576.0	1577.8	1578.0	1576.4	1574.8
177.5°	1580.7	1579.2	1577.6	1576.1	1577.6	1579.2	1580.7	1582.3	1582.3	1581.0	1579.7
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	988.6	992.3	994.3	999.1	1005.8	1009.3	1014.0	1017.4	1022.1	1027.8	1032.7
5°	924.5	934.7	941.5	952.1	961.8	971.6	983.8	992.7	1004.6	1018.1	1028.7
7.5°	865.1	877.8	889.1	903.1	919.2	931.7	947.7	964.0	982.6	1001.8	1019.9
10°	827.2	839.9	853.9	871.2	887.3	904.2	923.3	942.3	965.6	987.2	1011.8
12.5°	789.6	803.6	819.4	838.7	858.2	879.9	899.3	920.7	945.7	973.7	1000.0
15°	743.0	756.5	773.5	789.9	812.4	836.1	861.9	890.3	918.3	949.6	982.2
17.5°	692.9	707.8	726.4	745.6	769.2	797.0	822.3	853.4	884.8	921.3	959.6
20°	660.4	675.6	697.7	718.8	740.5	767.5	797.6	829.3	862.7	901.3	944.0
22.5°	634.7	645.6	667.2	688.7	714.0	741.8	771.2	804.3	840.7	880.6	925.4
25°	596.5	609.2	624.8	647.3	673.5	702.8	732.4	767.5	807.3	848.0	895.8
27.5°	562.6	573.0	588.5	606.1	632.2	662.5	694.1	730.7	771.5	812.9	863.2
30°	538.5	549.9	564.8	583.3	604.1	637.2	669.3	705.3	746.8	789.5	841.1
32.5°	517.5	529.3	542.0	559.6	582.1	611.4	644.6	679.9	722.0	766.1	816.4
35°	488.1	496.2	508.0	525.4	547.4	571.1	605.0	642.2	683.3	729.0	779.3
37.5°	454.4	464.8	476.6	491.7	510.9	536.6	568.1	605.8	643.9	687.7	733.7
40°	434.8	444.5	457.6	468.6	488.9	512.3	541.0	580.4	618.5	659.6	701.5
42.5°	414.8	424.2	435.3	449.0	467.2	489.9	516.7	553.3	594.1	632.8	668.0
45°	383.5	393.3	403.9	416.5	433.5	455.5	482.2	515.6	551.2	586.8	613.4
47.5°	353.7	362.8	372.8	385.8	401.5	422.7	446.5	476.1	510.6	540.9	559.9
50°	332.3	340.8	351.8	364.5	379.8	399.7	422.5	451.7	480.5	508.0	525.4
52.5°	311.4	320.8	331.8	342.8	357.4	377.3	398.4	423.6	451.0	473.4	487.8
55°	279.8	288.7	298.9	310.3	324.7	341.6	364.1	384.0	405.5	424.6	433.1
57.5°	249.4	257.2	266.8	278.7	291.6	307.4	325.1	344.3	359.5	373.0	382.5
60°	229.4	236.2	245.1	255.3	269.2	283.6	299.7	317.5	329.4	340.8	349.7
62.5°	209.1	215.6	224.1	233.3	245.6	258.9	274.3	288.7	300.3	307.9	318.2
65°	178.6	185.0	192.2	201.9	211.7	222.7	236.7	247.2	255.3	263.7	270.1
67.5°	150.3	155.6	162.4	170.0	178.2	188.8	199.7	208.5	213.9	219.1	226.7
70°	131.7	135.9	141.4	147.3	156.2	166.8	175.3	182.1	185.9	190.9	200.2
72.5°	112.7	117.6	122.8	128.7	135.9	144.8	152.2	159.0	161.4	165.5	171.5
75°	88.9	91.5	95.7	99.9	105.0	112.6	119.8	121.5	123.6	127.0	131.3
77.5°	67.3	69.5	71.2	74.0	78.0	84.1	88.0	90.5	91.0	92.3	96.4
80°	53.3	54.6	56.3	58.5	60.1	65.2	67.3	69.9	70.7	72.0	74.1
82.5°	39.1	40.4	41.4	43.2	45.9	47.9	50.1	52.6	52.7	53.6	54.1
85°	22.8	23.3	22.4	23.3	23.7	24.5	26.7	28.8	28.4	28.0	29.2
87.5°	12.3	12.1	11.3	12.0	10.9	10.8	10.4	10.4	10.6	10.8	11.1
90°	21.0	19.6	17.8	15.8	13.9	12.0	9.9	7.8	5.6	3.4	1.2
92.5°	49.0	47.2	44.8	42.5	40.2	37.8	35.9	34.3	32.9	31.3	29.8
95°	96.6	94.7	92.0	89.2	86.5	83.7	82.1	81.5	81.0	80.5	79.9
97.5°	152.5	150.7	147.0	143.2	139.4	135.7	133.7	133.5	133.2	133.0	132.8
100°	190.6	188.1	184.6	181.0	177.5	173.9	172.1	172.1	172.1	172.1	172.1
102.5°	230.2	227.5	225.7	223.9	222.1	220.3	218.8	217.7	216.6	215.6	214.4
105°	295.5	293.9	292.2	290.6	288.9	287.3	285.8	284.5	283.1	281.7	280.4
107.5°	365.7	364.9	363.7	362.4	361.2	360.0	358.6	357.3	355.9	354.5	353.1
110°	413.9	413.1	412.3	411.5	410.7	409.9	408.8	407.4	406.0	404.7	403.3



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	462.7	462.4	461.3	460.2	459.2	458.2	457.3	456.6	455.9	455.2	454.4
115°	537.0	537.4	536.8	536.2	535.7	535.2	534.3	533.2	532.1	531.1	529.9
117.5°	610.3	610.2	609.6	609.1	608.6	608.1	607.6	607.2	606.7	606.2	605.7
120°	660.3	660.3	660.0	659.7	659.5	659.2	658.4	657.0	655.7	654.3	652.9
122.5°	709.2	709.5	708.7	708.1	707.4	706.6	706.0	705.6	705.1	704.6	704.1
125°	781.5	782.0	781.8	781.5	781.2	781.0	780.0	778.4	776.7	775.0	773.4
127.5°	852.6	852.9	852.6	852.2	851.9	851.6	850.9	849.9	849.1	848.2	847.2
130°	899.8	900.1	899.5	898.9	898.5	897.9	896.9	895.5	894.2	892.8	891.4
132.5°	945.0	945.3	945.4	945.5	945.7	945.7	944.7	942.5	940.2	938.0	935.7
135°	1014.4	1014.4	1014.2	1013.9	1013.6	1013.3	1012.4	1010.7	1009.1	1007.5	1005.8
137.5°	1081.9	1081.6	1080.9	1080.4	1079.8	1079.1	1078.1	1076.4	1074.9	1073.3	1071.7
140°	1124.4	1123.9	1123.1	1122.3	1121.4	1120.5	1119.5	1118.1	1116.7	1115.4	1114.0
142.5°	1166.4	1166.1	1165.1	1164.1	1163.0	1162.0	1160.9	1159.8	1158.6	1157.5	1156.3
145°	1227.1	1227.1	1226.3	1225.5	1224.7	1223.8	1222.9	1221.8	1220.7	1219.6	1218.5
147.5°	1282.4	1281.7	1281.1	1280.4	1279.8	1279.1	1278.5	1277.9	1277.2	1276.7	1276.1
150°	1318.2	1318.2	1317.0	1316.0	1314.8	1313.8	1313.4	1313.6	1313.9	1314.2	1314.4
152.5°	1350.3	1349.6	1349.2	1348.7	1348.3	1347.9	1347.4	1347.0	1346.7	1346.3	1345.9
155°	1396.7	1395.6	1395.3	1395.1	1394.8	1394.5	1394.4	1394.4	1394.4	1394.4	1394.4
157.5°	1437.3	1436.1	1435.9	1435.7	1435.3	1435.1	1435.3	1435.8	1436.5	1437.0	1437.6
160°	1461.8	1460.8	1460.5	1460.2	1460.0	1459.7	1460.0	1460.8	1461.6	1462.4	1463.2
162.5°	1484.7	1483.4	1483.4	1483.3	1483.2	1483.2	1483.4	1484.1	1484.7	1485.2	1485.9
165°	1516.0	1514.9	1514.6	1514.3	1514.1	1513.8	1513.9	1514.5	1515.0	1515.6	1516.1
167.5°	1538.4	1536.8	1536.8	1536.8	1536.8	1536.8	1537.3	1538.4	1539.5	1540.6	1541.6
170°	1552.2	1550.5	1550.5	1550.5	1550.5	1550.5	1551.1	1552.2	1553.2	1554.4	1555.4
172.5°	1562.0	1560.4	1560.4	1560.4	1560.4	1560.4	1560.9	1562.0	1563.1	1564.2	1565.3
175°	1573.0	1571.4	1571.4	1571.4	1571.4	1571.4	1572.0	1573.0	1574.2	1575.2	1576.4
177.5°	1578.4	1577.1	1577.3	1577.5	1577.8	1577.9	1578.5	1579.4	1580.3	1581.1	1582.0
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1036.3	1039.4	1043.8	1048.9	1053.0	1057.4	1059.7	1059.7	1061.8	1066.2	1071.9
5°	1039.3	1050.4	1060.9	1074.5	1085.0	1097.3	1106.6	1115.5	1123.6	1133.7	1144.3
7.5°	1038.4	1056.7	1075.8	1097.1	1120.7	1139.4	1158.6	1173.7	1188.5	1208.0	1223.4
10°	1035.1	1058.7	1084.6	1111.7	1141.3	1167.2	1190.4	1211.6	1231.9	1253.1	1272.1
12.5°	1029.0	1059.2	1090.7	1123.2	1160.7	1190.2	1220.3	1242.8	1266.5	1289.6	1313.1
15°	1019.9	1055.4	1093.5	1138.8	1184.5	1217.6	1247.2	1276.4	1298.4	1324.6	1347.1
17.5°	1000.9	1046.8	1094.7	1144.2	1188.1	1226.5	1257.6	1285.3	1308.8	1337.7	1368.2
20°	989.8	1039.3	1089.2	1142.2	1184.1	1223.4	1253.5	1282.3	1311.5	1349.2	1386.4
22.5°	974.2	1027.1	1080.1	1130.3	1174.6	1212.6	1243.7	1279.0	1317.3	1360.0	1405.1
25°	949.6	1004.2	1056.6	1104.5	1147.7	1186.7	1229.0	1276.4	1323.0	1379.2	1444.1
27.5°	918.4	970.9	1017.8	1068.4	1111.3	1160.8	1213.7	1265.0	1332.2	1409.7	1490.5
30°	895.0	944.9	989.4	1037.2	1085.9	1140.5	1199.8	1260.3	1340.3	1431.3	1527.5
32.5°	867.9	913.1	957.2	1003.3	1059.5	1119.5	1182.5	1256.5	1352.2	1455.7	1555.2
35°	820.8	861.5	904.2	955.4	1015.2	1080.4	1160.8	1251.0	1366.5	1477.9	1567.2
37.5°	771.6	803.6	846.6	900.7	965.6	1041.1	1132.4	1241.9	1360.7	1460.5	1498.5
40°	733.7	763.7	809.0	865.8	930.1	1012.6	1115.1	1227.7	1347.1	1416.5	1413.6
42.5°	696.0	726.4	770.1	827.1	894.2	986.6	1092.1	1209.1	1309.9	1336.3	1281.2
45°	638.4	666.8	709.6	767.1	839.1	936.0	1046.9	1159.1	1223.4	1180.7	1071.5
47.5°	579.7	607.2	646.9	703.3	781.8	883.3	988.1	1080.2	1089.2	997.4	866.4
50°	541.0	566.9	604.5	664.6	740.9	839.9	941.1	1013.5	991.1	878.9	743.8
52.5°	503.4	528.2	563.5	620.3	698.1	795.2	885.6	942.3	890.5	771.2	649.6
55°	447.9	471.6	507.2	559.2	629.9	718.8	798.0	818.7	742.6	622.3	524.1
57.5°	395.2	412.5	447.7	493.7	561.8	640.3	697.0	693.2	609.2	500.9	430.5
60°	360.3	375.9	409.4	451.7	516.5	586.8	626.6	609.6	524.5	435.2	367.5
62.5°	327.8	342.4	370.4	409.4	465.0	526.1	555.1	531.7	451.3	372.9	319.0
65°	278.6	289.1	311.6	347.6	391.2	433.5	459.3	425.0	353.9	294.6	254.0
67.5°	232.6	241.7	261.7	287.6	317.6	346.8	357.3	325.1	269.9	229.9	201.3
70°	202.8	211.2	224.8	248.9	268.8	289.6	294.6	265.9	219.7	189.2	171.5
72.5°	174.3	182.1	194.0	211.0	224.8	236.8	239.1	212.4	177.0	156.0	142.4
75°	132.9	139.7	147.3	153.7	162.6	164.7	163.8	143.1	124.0	110.1	102.5
77.5°	97.7	100.5	105.2	107.7	108.1	107.9	103.6	90.5	80.7	74.9	71.8
80°	75.3	77.5	78.8	79.6	80.0	75.7	71.1	63.1	59.7	56.3	52.5
82.5°	54.7	56.2	57.4	57.6	55.3	51.8	47.5	43.5	41.1	39.4	37.9
85°	29.6	30.1	29.6	27.6	24.5	23.3	22.4	21.6	21.2	20.7	20.7
87.5°	11.2	10.6	9.4	10.1	10.5	10.6	10.9	11.0	11.0	11.3	11.6
90°	3.4	5.6	7.8	9.9	12.0	13.9	15.8	17.8	19.6	21.0	22.4
92.5°	31.3	32.9	34.3	35.9	37.8	40.2	42.5	44.8	47.2	49.0	50.8
95°	80.5	81.0	81.5	82.1	83.7	86.5	89.2	92.0	94.7	96.6	98.5
97.5°	133.0	133.2	133.5	133.7	135.7	139.4	143.2	147.0	150.7	152.5	154.3
100°	172.1	172.1	172.1	172.1	173.9	177.5	181.0	184.6	188.1	190.6	193.1
102.5°	215.6	216.6	217.7	218.8	220.3	222.1	223.9	225.7	227.5	230.2	232.8
105°	281.7	283.1	284.5	285.8	287.3	288.9	290.6	292.2	293.9	295.5	297.2
107.5°	354.5	355.9	357.3	358.6	360.0	361.2	362.4	363.7	364.9	365.7	366.6
110°	404.7	406.0	407.4	408.8	409.9	410.7	411.5	412.3	413.1	413.9	414.8



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.2	455.9	456.6	457.3	458.2	459.2	460.2	461.3	462.4	462.7	463.1
115°	531.1	532.1	533.2	534.3	535.2	535.7	536.2	536.8	537.4	537.0	536.8
117.5°	606.2	606.7	607.2	607.6	608.1	608.6	609.1	609.6	610.2	610.3	610.6
120°	654.3	655.7	657.0	658.4	659.2	659.5	659.7	660.0	660.3	660.3	660.3
122.5°	704.6	705.1	705.6	706.0	706.6	707.4	708.1	708.7	709.5	709.2	709.1
125°	775.0	776.7	778.4	780.0	781.0	781.2	781.5	781.8	782.0	781.5	781.0
127.5°	848.2	849.1	849.9	850.9	851.6	851.9	852.2	852.6	852.9	852.6	852.3
130°	892.8	894.2	895.5	896.9	897.9	898.5	898.9	899.5	900.1	899.8	899.5
132.5°	938.0	940.2	942.5	944.7	945.7	945.7	945.5	945.4	945.3	945.0	944.8
135°	1007.5	1009.1	1010.7	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4	1014.4
137.5°	1073.3	1074.9	1076.4	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9	1082.2
140°	1115.4	1116.7	1118.1	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4	1124.9
142.5°	1157.5	1158.6	1159.8	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4	1166.8
145°	1219.6	1220.7	1221.8	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1	1227.1
147.5°	1276.7	1277.2	1277.9	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4	1283.0
150°	1314.2	1313.9	1313.6	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2	1318.2
152.5°	1346.3	1346.7	1347.0	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3	1351.0
155°	1394.4	1394.4	1394.4	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7	1397.7
157.5°	1437.0	1436.5	1435.8	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3	1438.4
160°	1462.4	1461.6	1460.8	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8	1463.0
162.5°	1485.2	1484.7	1484.1	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7	1486.0
165°	1515.6	1515.0	1514.5	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0	1517.0
167.5°	1540.6	1539.5	1538.4	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4	1540.0
170°	1554.4	1553.2	1552.2	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2	1553.8
172.5°	1564.2	1563.1	1562.0	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0	1563.7
175°	1575.2	1574.2	1573.0	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0	1574.8
177.5°	1581.1	1580.3	1579.4	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4	1579.7
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3	1031.3
2.5°	1076.3	1076.3	1082.1	1081.7	1085.5	1084.1	1084.8
5°	1157.0	1164.2	1170.5	1174.8	1181.1	1182.8	1181.9
7.5°	1240.6	1256.6	1264.4	1275.1	1277.1	1282.6	1282.1
10°	1292.5	1308.1	1320.0	1329.3	1334.0	1339.9	1340.3
12.5°	1333.1	1346.4	1356.9	1365.5	1371.2	1373.0	1374.2
15°	1364.9	1379.6	1392.0	1404.2	1411.4	1416.9	1419.9
17.5°	1396.9	1419.8	1441.4	1458.1	1468.1	1476.5	1476.4
20°	1421.6	1447.8	1475.0	1494.0	1513.4	1521.9	1523.2
22.5°	1448.0	1488.2	1523.1	1552.6	1578.2	1587.0	1590.2
25°	1502.8	1555.3	1609.2	1650.7	1680.3	1697.6	1700.1
27.5°	1569.1	1640.2	1696.8	1735.0	1759.7	1772.5	1775.3
30°	1615.9	1681.6	1732.3	1761.1	1772.5	1774.3	1767.9
32.5°	1636.9	1686.0	1706.3	1704.5	1682.1	1667.2	1661.5
35°	1611.3	1601.1	1551.5	1492.3	1447.0	1418.2	1410.5
37.5°	1466.3	1378.7	1287.5	1198.0	1150.3	1126.1	1084.4
40°	1323.4	1198.5	1103.7	1028.3	974.5	931.3	921.2
42.5°	1162.1	1033.2	938.4	873.8	831.0	801.3	788.4
45°	933.9	823.0	744.7	695.1	662.1	640.5	630.8
47.5°	747.0	661.1	604.1	567.4	542.3	523.4	518.2
50°	644.3	575.8	527.5	496.6	477.5	463.2	457.2
52.5°	559.6	504.3	467.2	441.7	423.7	414.7	409.8
55°	461.9	414.0	387.3	367.0	356.9	349.7	346.3
57.5°	377.7	343.2	323.7	309.7	300.3	295.6	294.0
60°	330.6	303.5	285.8	274.8	268.4	262.4	260.8
62.5°	288.9	267.7	253.9	244.3	237.9	235.4	234.4
65°	232.8	218.9	208.7	202.8	197.7	196.9	196.4
67.5°	185.1	176.8	171.5	165.3	163.5	160.6	160.0
70°	158.3	152.8	146.5	144.4	142.3	139.3	139.7
72.5°	134.3	128.8	124.5	121.6	120.9	119.6	120.7
75°	98.2	96.5	94.8	92.7	91.9	91.9	91.5
77.5°	70.1	68.6	66.8	65.6	65.3	63.5	64.2
80°	50.8	48.7	47.9	48.3	47.0	46.6	46.6
82.5°	37.6	36.9	36.0	36.0	35.8	35.4	35.7
85°	20.7	20.3	20.3	19.9	19.9	19.5	19.5
87.5°	12.2	12.8	12.4	12.1	12.3	12.9	13.4
90°	23.8	25.1	26.3	27.1	27.9	28.7	29.5
92.5°	52.6	54.5	55.6	56.3	56.8	57.4	58.0
95°	100.4	102.3	103.5	104.1	104.7	105.2	105.7
97.5°	156.1	157.9	159.1	159.4	159.7	160.0	160.4
100°	195.5	198.0	199.5	200.0	200.6	201.1	201.6
102.5°	235.5	238.1	239.9	240.7	241.4	242.2	243.0
105°	298.8	300.4	301.7	302.5	303.3	304.1	304.9
107.5°	367.4	368.2	368.6	368.5	368.5	368.4	368.4
110°	415.6	416.5	416.7	416.5	416.1	415.9	415.6



TEST NUMBER: P333697-930

CATALOG NUMBER: S125RDIW-S850D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	463.5	463.8	463.8	463.3	462.8	462.4	461.9
115°	536.5	536.2	536.0	535.7	535.4	535.2	534.9
117.5°	610.8	611.0	610.6	609.4	608.4	607.3	606.2
120°	660.3	660.3	659.7	658.7	657.5	656.5	655.4
122.5°	708.8	708.6	708.1	707.2	706.3	705.4	704.6
125°	780.4	779.8	779.4	779.2	778.9	778.6	778.4
127.5°	852.1	851.7	851.3	850.8	850.3	849.7	849.1
130°	899.3	898.9	898.5	898.1	897.5	896.9	896.4
132.5°	944.5	944.2	943.7	943.0	942.2	941.4	940.6
135°	1014.4	1014.4	1013.9	1012.8	1011.7	1010.6	1009.5
137.5°	1082.6	1082.9	1082.4	1081.0	1079.6	1078.2	1076.8
140°	1125.5	1126.0	1125.6	1124.3	1122.9	1121.5	1120.1
142.5°	1167.1	1167.5	1166.9	1165.6	1164.2	1162.9	1161.5
145°	1227.1	1227.1	1226.7	1225.9	1225.1	1224.3	1223.4
147.5°	1283.7	1284.3	1283.8	1281.9	1280.0	1278.2	1276.4
150°	1318.2	1318.2	1317.8	1317.3	1316.8	1316.2	1315.6
152.5°	1351.6	1352.3	1352.1	1351.1	1350.1	1349.2	1348.2
155°	1398.9	1400.0	1399.9	1398.5	1397.1	1395.7	1394.4
157.5°	1439.5	1440.6	1440.2	1438.4	1436.6	1434.8	1433.0
160°	1464.0	1465.2	1465.0	1463.6	1462.2	1460.9	1459.5
162.5°	1487.4	1488.7	1488.5	1486.9	1485.3	1483.8	1482.1
165°	1518.2	1519.2	1519.0	1517.4	1515.7	1514.1	1512.4
167.5°	1541.6	1543.3	1543.3	1541.6	1539.9	1538.2	1536.5
170°	1555.4	1557.1	1557.0	1555.0	1553.1	1551.2	1549.3
172.5°	1565.3	1566.9	1566.9	1565.2	1563.5	1561.8	1560.2
175°	1576.4	1578.0	1577.8	1576.0	1574.0	1572.1	1570.2
177.5°	1581.0	1582.3	1582.3	1580.7	1579.2	1577.6	1576.1
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1

(END OF REPORT)