

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333435

Luminaire Tested: **S125DIW-S1090D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333435  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D470U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6066.7 lumens  
Efficiency: N/A  
Efficacy: 131.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333435

CATALOG NUMBER: S125DIW-S1090D470U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333435

CATALOG NUMBER: S125DIW-S1090D470U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	62	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333435

CATALOG NUMBER: S125DIW-S1090D470U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.9	2.7
10°-20°	454.5	7.5
20°-30°	671.0	11.1
30°-40°	783.0	12.9
40°-50°	786.4	13.0
50°-60°	690.3	11.4
60°-70°	514.4	8.5
70°-80°	294.1	4.8
80°-90°	86.8	1.4
90°-100°	39.0	0.6
100°-110°	115.2	1.9
110°-120°	195.1	3.2
120°-130°	256.8	4.2
130°-140°	287.7	4.7
140°-150°	282.0	4.6
150°-160°	236.9	3.9
160°-170°	157.4	2.6
170°-180°	55.1	0.9
0°-30°	1286.4	21.2
0°-40°	2069.4	34.1
0°-60°	3546.2	58.5
0°-90°	4441.5	73.2
90°-120°	349.3	5.8
90°-150°	1175.8	19.4
90°-180°	1625.0	26.8
0°-180°	6066.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	0	4	7	10	11	6
95°	30	31	35	38	39	31
105°	103	106	108	111	112	110
115°	195	197	198	198	197	193
125°	285	288	288	287	287	255
135°	371	373	374	374	372	286
145°	449	451	452	452	451	281
155°	514	514	514	516	514	237
165°	559	558	558	560	558	158
175°	581	579	579	582	579	55
180°	582	582	582	582	582	



TEST NUMBER: P333435

CATALOG NUMBER: S125DIW-S1090D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.2	29.4	29.6	29.7	29.9	29.9	29.8	29.7	29.6	29.5	29.6
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.3	7.8
92.5°	11.0	11.5	12.1	12.7	13.2	13.9	14.8	15.7	16.5	17.4	18.1
95°	29.5	29.7	29.9	30.1	30.3	30.9	31.9	32.9	33.9	34.9	35.6
97.5°	48.9	49.0	49.1	49.2	49.3	50.0	51.4	52.8	54.2	55.6	56.2
100°	63.5	63.5	63.5	63.5	63.5	64.1	65.4	66.7	68.0	69.3	70.3
102.5°	79.0	79.4	79.9	80.3	80.7	81.2	81.9	82.5	83.2	83.8	84.8
105°	103.3	103.8	104.3	104.8	105.4	105.9	106.5	107.1	107.7	108.3	108.9
107.5°	130.2	130.7	131.2	131.7	132.2	132.7	133.1	133.6	134.1	134.5	134.8
110°	148.7	149.2	149.7	150.2	150.7	151.1	151.4	151.7	152.0	152.3	152.6



TEST NUMBER: P333435

CATALOG NUMBER: S125DIW-S1090D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.5	167.8	168.0	168.3	168.6	168.9	169.3	169.7	170.0	170.4	170.6
115°	195.3	195.7	196.2	196.6	197.0	197.3	197.5	197.7	197.9	198.1	198.0
117.5°	223.3	223.4	223.6	223.8	224.0	224.2	224.4	224.5	224.7	224.9	225.0
120°	240.7	241.2	241.7	242.2	242.7	243.0	243.1	243.2	243.3	243.4	243.4
122.5°	259.5	259.7	259.9	260.1	260.2	260.5	260.7	261.0	261.3	261.5	261.4
125°	285.1	285.7	286.3	286.9	287.5	287.9	288.0	288.1	288.2	288.3	288.1
127.5°	312.3	312.6	313.0	313.3	313.7	313.9	314.0	314.1	314.2	314.4	314.3
130°	328.6	329.1	329.6	330.1	330.6	331.0	331.2	331.4	331.6	331.8	331.7
132.5°	344.9	345.7	346.6	347.4	348.2	348.6	348.6	348.5	348.5	348.4	348.3
135°	370.7	371.4	372.0	372.6	373.2	373.5	373.6	373.7	373.8	373.9	373.9
137.5°	395.0	395.6	396.2	396.8	397.4	397.8	398.0	398.2	398.4	398.7	398.8
140°	410.6	411.1	411.6	412.1	412.6	413.1	413.4	413.7	414.0	414.3	414.5
142.5°	426.2	426.6	427.1	427.5	427.9	428.3	428.7	429.1	429.5	429.9	430.0
145°	449.2	449.6	450.0	450.4	450.8	451.1	451.4	451.7	452.0	452.3	452.3
147.5°	470.4	470.6	470.8	471.0	471.3	471.5	471.7	472.0	472.2	472.5	472.7
150°	484.5	484.4	484.3	484.2	484.1	484.3	484.7	485.1	485.5	485.9	485.9
152.5°	496.1	496.3	496.4	496.5	496.7	496.8	497.0	497.2	497.3	497.5	497.7
155°	514.0	514.0	514.0	514.0	514.0	514.0	514.1	514.2	514.3	514.4	514.8
157.5°	529.9	529.7	529.5	529.3	529.0	529.0	529.1	529.2	529.3	529.4	529.8
160°	539.4	539.1	538.7	538.4	538.1	538.0	538.1	538.2	538.3	538.4	538.9
162.5°	547.7	547.5	547.3	547.0	546.8	546.7	546.7	546.7	546.8	546.8	547.3
165°	558.8	558.6	558.4	558.2	558.0	558.0	558.1	558.2	558.3	558.4	558.8
167.5°	568.3	567.9	567.5	567.1	566.7	566.5	566.5	566.5	566.5	566.5	567.1
170°	573.3	572.9	572.5	572.1	571.7	571.5	571.5	571.5	571.5	571.5	572.1
172.5°	577.0	576.6	576.2	575.8	575.4	575.2	575.2	575.2	575.2	575.2	575.8
175°	581.1	580.6	580.2	579.8	579.4	579.2	579.2	579.2	579.2	579.2	579.8
177.5°	583.1	582.8	582.5	582.2	581.8	581.6	581.6	581.5	581.4	581.3	581.8
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333435

CATALOG NUMBER: S125DIW-S1090D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	29.7	29.8	29.9	29.8	29.4	28.9	28.5	28.1
90°	8.3	8.8	9.3	9.7	10.0	10.3	10.6	10.9
92.5°	18.7	19.4	20.1	20.5	20.7	20.9	21.2	21.4
95°	36.3	37.0	37.7	38.2	38.4	38.6	38.8	39.0
97.5°	56.9	57.6	58.2	58.6	58.7	58.9	59.0	59.1
100°	71.2	72.1	73.0	73.5	73.7	73.9	74.1	74.3
102.5°	85.8	86.8	87.8	88.4	88.7	89.0	89.3	89.6
105°	109.5	110.1	110.7	111.2	111.5	111.8	112.1	112.4
107.5°	135.1	135.4	135.7	135.9	135.9	135.8	135.8	135.8
110°	152.9	153.2	153.5	153.6	153.5	153.4	153.3	153.2





TEST NUMBER: P333435

CATALOG NUMBER: S125DIW-S1090D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.8	171.0	171.0	170.8	170.6	170.4	170.2
115°	197.9	197.8	197.7	197.6	197.5	197.4	197.3	197.2
117.5°	225.1	225.1	225.2	225.1	224.7	224.3	223.8	223.4
120°	243.4	243.4	243.4	243.2	242.8	242.4	242.0	241.6
122.5°	261.4	261.3	261.2	261.0	260.7	260.4	260.0	259.7
125°	287.9	287.7	287.5	287.3	287.2	287.1	287.0	286.9
127.5°	314.2	314.1	314.0	313.8	313.6	313.4	313.2	313.0
130°	331.6	331.5	331.4	331.2	331.0	330.8	330.6	330.4
132.5°	348.2	348.1	348.0	347.9	347.6	347.3	347.0	346.7
135°	373.9	373.9	373.9	373.7	373.3	372.9	372.5	372.1
137.5°	398.9	399.0	399.2	399.0	398.5	398.0	397.4	396.9
140°	414.7	414.9	415.1	414.9	414.4	413.9	413.4	412.9
142.5°	430.1	430.2	430.3	430.1	429.6	429.1	428.6	428.1
145°	452.3	452.3	452.3	452.2	451.9	451.6	451.3	451.0
147.5°	472.9	473.2	473.4	473.2	472.5	471.8	471.1	470.5
150°	485.9	485.9	485.9	485.8	485.6	485.4	485.2	485.0
152.5°	498.0	498.2	498.4	498.4	498.0	497.7	497.3	496.9
155°	515.2	515.6	516.0	516.0	515.5	515.0	514.5	514.0
157.5°	530.2	530.6	531.0	530.9	530.2	529.5	528.9	528.2
160°	539.3	539.7	540.1	540.0	539.5	539.0	538.5	538.0
162.5°	547.8	548.2	548.7	548.7	548.1	547.5	546.9	546.3
165°	559.2	559.6	560.0	559.9	559.3	558.7	558.1	557.5
167.5°	567.7	568.3	568.9	568.9	568.2	567.6	567.0	566.4
170°	572.7	573.3	574.0	573.9	573.2	572.5	571.8	571.1
172.5°	576.4	577.0	577.6	577.6	576.9	576.3	575.7	575.1
175°	580.4	581.1	581.7	581.6	580.9	580.2	579.5	578.8
177.5°	582.3	582.8	583.3	583.2	582.7	582.1	581.5	581.0
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4

(END OF REPORT)