

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333345

Luminaire Tested: **S125DIW-S375D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333345  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D470U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3146.6 lumens  
Efficiency: N/A  
Efficacy: 136.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333345

CATALOG NUMBER: S125DIW-S375D470U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333345

CATALOG NUMBER: S125DIW-S375D470U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48					48			
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46					41				
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39					34				
3	81	71	64	58	74	66	59	54	56	51	47	46	43	40	37	35	33					29				
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28					25				
5	68	56	48	42	62	52	45	39	44	39	34	37	33	29	30	27	25					21				
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22					19				
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19					17				
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17					15				
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16					13				
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14					12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3773	3773	3773
5°	3781	3745	3769
10°	3758	3719	3740
15°	3718	3674	3689
20°	3659	3612	3618
25°	3596	3537	3534
30°	3519	3457	3439
35°	3436	3370	3323
40°	3351	3277	3230
45°	3259	3191	3128
50°	3158	3088	2995
55°	3059	2971	2888
60°	2942	2853	2753
65°	2804	2713	2621
70°	2670	2549	2460
75°	2433	2353	2271
80°	2165	2131	2079
85°	1882	1919	1815



TEST NUMBER: P333345

CATALOG NUMBER: S125DIW-S375D470U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	1.8
10°-20°	155.6	4.9
20°-30°	229.7	7.3
30°-40°	268.1	8.5
40°-50°	269.2	8.6
50°-60°	236.3	7.5
60°-70°	176.1	5.6
70°-80°	100.7	3.2
80°-90°	30.6	1.0
90°-100°	39.0	1.2
100°-110°	115.2	3.7
110°-120°	195.1	6.2
120°-130°	256.8	8.2
130°-140°	287.7	9.1
140°-150°	282.0	9.0
150°-160°	236.9	7.5
160°-170°	157.4	5.0
170°-180°	55.1	1.8
0°-30°	440.4	14.0
0°-40°	708.5	22.5
0°-60°	1214.0	38.6
0°-90°	1521.4	48.4
90°-120°	349.3	11.1
90°-150°	1175.8	37.4
90°-180°	1625.0	51.6
0°-180°	3146.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	584	584	584	584	584	
5°	583	582	578	582	581	55
15°	556	554	550	552	552	157
25°	505	502	496	497	496	232
35°	436	434	428	425	422	272
45°	357	355	349	344	342	275
55°	272	270	264	260	256	243
65°	184	182	178	173	172	182
75°	98	96	94	93	91	104
85°	25	26	26	25	24	28
90°	0	4	7	10	11	3
95°	30	31	35	38	39	31
105°	103	106	108	111	112	110
115°	195	197	198	198	197	193
125°	285	288	288	287	287	255
135°	371	373	374	374	372	286
145°	449	451	452	452	451	281
155°	514	514	514	516	514	237
165°	559	558	558	560	558	158
175°	581	579	579	582	579	55
180°	582	582	582	582	582	



TEST NUMBER: P333345

CATALOG NUMBER: S125DIW-S375D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	585.6	585.4	585.2	584.9	584.7	584.1	583.3	582.5	581.7	580.8	581.7
5°	583.2	583.0	582.8	582.6	582.4	581.8	580.8	579.8	578.7	577.7	578.6
7.5°	577.9	577.7	577.5	577.3	577.1	576.4	575.3	574.1	573.0	571.9	572.8
10°	573.1	572.9	572.7	572.5	572.3	571.6	570.5	569.3	568.2	567.1	567.9
12.5°	567.2	566.8	566.4	566.1	565.7	565.0	563.9	562.9	561.8	560.8	561.4
15°	556.0	555.7	555.4	555.1	554.7	554.0	552.9	551.8	550.6	549.5	550.0
17.5°	543.1	542.7	542.2	541.8	541.3	540.5	539.3	538.2	537.0	535.8	536.5
20°	532.4	532.2	532.0	531.8	531.6	530.8	529.5	528.1	526.8	525.5	526.2
22.5°	521.7	521.3	520.9	520.6	520.2	519.4	518.1	516.9	515.6	514.4	514.9
25°	504.7	504.2	503.6	503.1	502.6	501.7	500.4	499.0	497.7	496.4	496.6
27.5°	484.8	484.5	484.2	483.9	483.6	482.7	481.4	480.0	478.6	477.2	477.3
30°	471.9	471.6	471.2	470.9	470.6	469.7	468.2	466.6	465.1	463.5	463.3
32.5°	457.8	457.3	456.9	456.4	455.9	455.0	453.6	452.2	450.9	449.5	449.1
35°	435.8	435.4	435.0	434.6	434.2	433.2	431.8	430.4	428.9	427.5	427.0
37.5°	413.0	412.5	412.0	411.4	410.9	410.0	408.6	407.3	405.9	404.6	403.8
40°	397.5	396.9	396.4	395.9	395.4	394.4	393.0	391.6	390.1	388.7	387.8
42.5°	380.8	380.4	380.0	379.5	379.1	378.2	376.7	375.3	373.8	372.4	371.6
45°	356.8	356.4	356.0	355.6	355.1	354.3	353.1	351.9	350.6	349.4	348.2
47.5°	330.9	330.9	330.9	331.0	331.0	330.3	328.8	327.3	325.8	324.3	323.1
50°	314.3	314.0	313.7	313.3	313.0	312.3	311.0	309.8	308.6	307.3	306.0
52.5°	297.3	297.0	296.8	296.6	296.4	295.6	294.3	293.0	291.6	290.3	289.2
55°	271.7	271.4	271.1	270.8	270.5	269.6	268.2	266.8	265.3	263.9	263.0
57.5°	244.9	244.7	244.5	244.4	244.2	243.5	242.3	241.1	239.9	238.7	237.5
60°	227.8	227.4	227.0	226.6	226.2	225.4	224.3	223.2	222.0	220.9	219.9
62.5°	210.1	209.8	209.4	209.1	208.8	208.1	207.2	206.2	205.2	204.3	203.2
65°	183.5	183.3	183.1	182.9	182.7	182.0	180.9	179.7	178.6	177.5	176.5
67.5°	157.7	157.3	156.8	156.4	156.0	155.3	154.5	153.6	152.8	152.0	151.2
70°	141.4	140.9	140.4	139.9	139.4	138.6	137.7	136.8	135.9	135.0	134.3
72.5°	123.7	123.3	123.0	122.6	122.3	121.8	121.2	120.6	120.0	119.4	118.7
75°	97.5	97.3	97.1	96.9	96.7	96.3	95.8	95.3	94.8	94.3	94.0
77.5°	73.4	73.3	73.2	73.1	73.1	72.9	72.6	72.3	72.0	71.7	71.5
80°	58.2	58.2	58.2	58.2	58.2	58.1	57.9	57.7	57.5	57.3	57.2
82.5°	44.9	44.8	44.6	44.4	44.3	44.2	44.1	44.1	44.0	44.0	43.8
85°	25.4	25.5	25.6	25.7	25.8	25.9	25.9	25.9	25.9	25.9	25.8
87.5°	10.1	10.2	10.4	10.6	10.7	10.8	10.9	10.9	11.0	11.1	11.2
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.3	7.8
92.5°	11.0	11.5	12.1	12.7	13.2	13.9	14.8	15.7	16.5	17.4	18.1
95°	29.5	29.7	29.9	30.1	30.3	30.9	31.9	32.9	33.9	34.9	35.6
97.5°	48.9	49.0	49.1	49.2	49.3	50.0	51.4	52.8	54.2	55.6	56.2
100°	63.5	63.5	63.5	63.5	63.5	64.1	65.4	66.7	68.0	69.3	70.3
102.5°	79.0	79.4	79.9	80.3	80.7	81.2	81.9	82.5	83.2	83.8	84.8
105°	103.3	103.8	104.3	104.8	105.4	105.9	106.5	107.1	107.7	108.3	108.9
107.5°	130.2	130.7	131.2	131.7	132.2	132.7	133.1	133.6	134.1	134.5	134.8
110°	148.7	149.2	149.7	150.2	150.7	151.1	151.4	151.7	152.0	152.3	152.6



TEST NUMBER: P333345

CATALOG NUMBER: S125DIW-S375D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.5	167.8	168.0	168.3	168.6	168.9	169.3	169.7	170.0	170.4	170.6
115°	195.3	195.7	196.2	196.6	197.0	197.3	197.5	197.7	197.9	198.1	198.0
117.5°	223.3	223.4	223.6	223.8	224.0	224.2	224.4	224.5	224.7	224.9	225.0
120°	240.7	241.2	241.7	242.2	242.7	243.0	243.1	243.2	243.3	243.4	243.4
122.5°	259.5	259.7	259.9	260.1	260.2	260.5	260.7	261.0	261.3	261.5	261.4
125°	285.1	285.7	286.3	286.9	287.5	287.9	288.0	288.1	288.2	288.3	288.1
127.5°	312.3	312.6	313.0	313.3	313.7	313.9	314.0	314.1	314.2	314.4	314.3
130°	328.6	329.1	329.6	330.1	330.6	331.0	331.2	331.4	331.6	331.8	331.7
132.5°	344.9	345.7	346.6	347.4	348.2	348.6	348.6	348.5	348.5	348.4	348.3
135°	370.7	371.4	372.0	372.6	373.2	373.5	373.6	373.7	373.8	373.9	373.9
137.5°	395.0	395.6	396.2	396.8	397.4	397.8	398.0	398.2	398.4	398.7	398.8
140°	410.6	411.1	411.6	412.1	412.6	413.1	413.4	413.7	414.0	414.3	414.5
142.5°	426.2	426.6	427.1	427.5	427.9	428.3	428.7	429.1	429.5	429.9	430.0
145°	449.2	449.6	450.0	450.4	450.8	451.1	451.4	451.7	452.0	452.3	452.3
147.5°	470.4	470.6	470.8	471.0	471.3	471.5	471.7	472.0	472.2	472.5	472.7
150°	484.5	484.4	484.3	484.2	484.1	484.3	484.7	485.1	485.5	485.9	485.9
152.5°	496.1	496.3	496.4	496.5	496.7	496.8	497.0	497.2	497.3	497.5	497.7
155°	514.0	514.0	514.0	514.0	514.0	514.0	514.1	514.2	514.3	514.4	514.8
157.5°	529.9	529.7	529.5	529.3	529.0	529.0	529.1	529.2	529.3	529.4	529.8
160°	539.4	539.1	538.7	538.4	538.1	538.0	538.1	538.2	538.3	538.4	538.9
162.5°	547.7	547.5	547.3	547.0	546.8	546.7	546.7	546.7	546.8	546.8	547.3
165°	558.8	558.6	558.4	558.2	558.0	558.0	558.1	558.2	558.3	558.4	558.8
167.5°	568.3	567.9	567.5	567.1	566.7	566.5	566.5	566.5	566.5	566.5	567.1
170°	573.3	572.9	572.5	572.1	571.7	571.5	571.5	571.5	571.5	571.5	572.1
172.5°	577.0	576.6	576.2	575.8	575.4	575.2	575.2	575.2	575.2	575.2	575.8
175°	581.1	580.6	580.2	579.8	579.4	579.2	579.2	579.2	579.2	579.2	579.8
177.5°	583.1	582.8	582.5	582.2	581.8	581.6	581.6	581.5	581.4	581.3	581.8
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333345

CATALOG NUMBER: S125DIW-S375D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	582.5	583.3	584.1	584.5	584.4	584.3	584.3	584.2
5°	579.5	580.5	581.4	581.8	581.7	581.6	581.5	581.4
7.5°	573.7	574.6	575.5	575.9	575.8	575.7	575.6	575.5
10°	568.7	569.5	570.4	570.7	570.6	570.5	570.4	570.3
12.5°	562.1	562.8	563.4	563.7	563.7	563.7	563.7	563.6
15°	550.5	551.0	551.6	551.8	551.8	551.8	551.8	551.8
17.5°	537.1	537.7	538.4	538.4	537.9	537.4	536.9	536.4
20°	526.9	527.6	528.3	528.5	527.9	527.4	526.9	526.4
22.5°	515.3	515.8	516.3	516.3	516.0	515.6	515.3	514.9
25°	496.8	497.0	497.2	497.1	496.8	496.5	496.2	495.9
27.5°	477.3	477.3	477.4	477.3	476.9	476.6	476.3	476.0
30°	463.1	462.9	462.7	462.5	462.2	461.9	461.5	461.2
32.5°	448.8	448.4	448.0	447.6	447.0	446.4	445.9	445.3
35°	426.5	426.0	425.4	424.8	424.0	423.1	422.3	421.5
37.5°	403.1	402.3	401.5	400.9	400.4	400.0	399.5	399.0
40°	386.8	385.9	385.0	384.4	384.1	383.7	383.4	383.1
42.5°	370.7	369.9	369.0	368.4	367.9	367.4	367.0	366.5
45°	346.9	345.7	344.5	343.7	343.4	343.1	342.8	342.5
47.5°	321.8	320.6	319.3	318.3	317.6	316.9	316.2	315.5
50°	304.7	303.3	302.0	301.0	300.2	299.5	298.8	298.1
52.5°	288.0	286.8	285.6	284.7	283.9	283.1	282.3	281.5
55°	262.0	261.1	260.2	259.4	258.7	257.9	257.2	256.5
57.5°	236.3	235.1	233.9	233.1	232.7	232.3	231.9	231.5
60°	218.9	217.8	216.8	215.9	215.2	214.5	213.8	213.1
62.5°	202.1	200.9	199.8	199.0	198.5	197.9	197.3	196.8
65°	175.6	174.7	173.8	173.1	172.7	172.3	171.9	171.5
67.5°	150.4	149.6	148.8	148.3	148.1	147.8	147.6	147.3
70°	133.7	133.1	132.5	132.0	131.6	131.2	130.7	130.3
72.5°	118.0	117.3	116.6	116.1	115.7	115.3	114.8	114.4
75°	93.7	93.4	93.0	92.7	92.3	91.9	91.5	91.0
77.5°	71.4	71.2	71.0	70.8	70.5	70.2	69.9	69.6
80°	57.1	57.0	56.9	56.7	56.5	56.3	56.1	55.9
82.5°	43.6	43.4	43.3	43.1	43.1	43.1	43.0	43.0
85°	25.7	25.6	25.5	25.3	25.1	24.9	24.7	24.5
87.5°	11.3	11.4	11.5	11.5	11.4	11.3	11.2	11.0
90°	8.3	8.8	9.3	9.7	10.0	10.3	10.6	10.9
92.5°	18.7	19.4	20.1	20.5	20.7	20.9	21.2	21.4
95°	36.3	37.0	37.7	38.2	38.4	38.6	38.8	39.0
97.5°	56.9	57.6	58.2	58.6	58.7	58.9	59.0	59.1
100°	71.2	72.1	73.0	73.5	73.7	73.9	74.1	74.3
102.5°	85.8	86.8	87.8	88.4	88.7	89.0	89.3	89.6
105°	109.5	110.1	110.7	111.2	111.5	111.8	112.1	112.4
107.5°	135.1	135.4	135.7	135.9	135.9	135.8	135.8	135.8
110°	152.9	153.2	153.5	153.6	153.5	153.4	153.3	153.2





TEST NUMBER: P333345

CATALOG NUMBER: S125DIW-S375D470U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.8	171.0	171.0	170.8	170.6	170.4	170.2
115°	197.9	197.8	197.7	197.6	197.5	197.4	197.3	197.2
117.5°	225.1	225.1	225.2	225.1	224.7	224.3	223.8	223.4
120°	243.4	243.4	243.4	243.2	242.8	242.4	242.0	241.6
122.5°	261.4	261.3	261.2	261.0	260.7	260.4	260.0	259.7
125°	287.9	287.7	287.5	287.3	287.2	287.1	287.0	286.9
127.5°	314.2	314.1	314.0	313.8	313.6	313.4	313.2	313.0
130°	331.6	331.5	331.4	331.2	331.0	330.8	330.6	330.4
132.5°	348.2	348.1	348.0	347.9	347.6	347.3	347.0	346.7
135°	373.9	373.9	373.9	373.7	373.3	372.9	372.5	372.1
137.5°	398.9	399.0	399.2	399.0	398.5	398.0	397.4	396.9
140°	414.7	414.9	415.1	414.9	414.4	413.9	413.4	412.9
142.5°	430.1	430.2	430.3	430.1	429.6	429.1	428.6	428.1
145°	452.3	452.3	452.3	452.2	451.9	451.6	451.3	451.0
147.5°	472.9	473.2	473.4	473.2	472.5	471.8	471.1	470.5
150°	485.9	485.9	485.9	485.8	485.6	485.4	485.2	485.0
152.5°	498.0	498.2	498.4	498.4	498.0	497.7	497.3	496.9
155°	515.2	515.6	516.0	516.0	515.5	515.0	514.5	514.0
157.5°	530.2	530.6	531.0	530.9	530.2	529.5	528.9	528.2
160°	539.3	539.7	540.1	540.0	539.5	539.0	538.5	538.0
162.5°	547.8	548.2	548.7	548.7	548.1	547.5	546.9	546.3
165°	559.2	559.6	560.0	559.9	559.3	558.7	558.1	557.5
167.5°	567.7	568.3	568.9	568.9	568.2	567.6	567.0	566.4
170°	572.7	573.3	574.0	573.9	573.2	572.5	571.8	571.1
172.5°	576.4	577.0	577.6	577.6	576.9	576.3	575.7	575.1
175°	580.4	581.1	581.7	581.6	580.9	580.2	579.5	578.8
177.5°	582.3	582.8	583.3	583.2	582.7	582.1	581.5	581.0
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4

(END OF REPORT)