

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333703

Luminaire Tested: **S125RDIW-S1090D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333703
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D470U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5849.0 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333703

CATALOG NUMBER: S125RDIW-S1090D470U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333703

CATALOG NUMBER: S125RDIW-S1090D470U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	91	98	94	90	87	85	82	79	76	74	72	68	67	65	62
2	94	87	80	75	89	82	77	72	74	70	66	67	64	61	60	58	55	52
3	86	76	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48	44
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	44	41	38
5	73	61	52	46	69	58	51	45	53	47	42	48	43	39	44	39	36	33
6	67	55	46	41	64	52	45	39	48	42	37	44	38	34	40	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	45	37	32	55	43	36	31	40	34	29	37	31	27	33	29	26	24
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333703

CATALOG NUMBER: S125RDIW-S1090D470U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	2.9
10°-20°	469.7	8.0
20°-30°	681.1	11.6
30°-40°	776.2	13.3
40°-50°	756.6	12.9
50°-60°	636.9	10.9
60°-70°	446.5	7.6
70°-80°	229.5	3.9
80°-90°	59.2	1.0
90°-100°	39.0	0.7
100°-110°	115.2	2.0
110°-120°	195.1	3.3
120°-130°	256.8	4.4
130°-140°	287.7	4.9
140°-150°	282.0	4.8
150°-160°	236.9	4.0
160°-170°	157.4	2.7
170°-180°	55.1	0.9
0°-30°	1318.9	22.5
0°-40°	2095.1	35.8
0°-60°	3488.6	59.6
0°-90°	4223.8	72.2
90°-120°	349.3	6.0
90°-150°	1175.8	20.1
90°-180°	1625.0	27.8
0°-180°	5849.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	0	4	7	10	11	5
95°	30	31	35	38	39	31
105°	103	106	108	111	112	110
115°	195	197	198	198	197	193
125°	285	288	288	287	287	255
135°	371	373	374	374	372	286
145°	449	451	452	452	451	281
155°	514	514	514	516	514	237
165°	559	558	558	560	558	158
175°	581	579	579	582	579	55
180°	582	582	582	582	582	



TEST NUMBER: P333703

CATALOG NUMBER: S125RDIW-S1090D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	24.9	23.4	21.9	20.4	18.9	18.0	17.9	17.8	17.7	17.6	17.8
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.3	7.8
92.5°	11.0	11.5	12.1	12.7	13.2	13.9	14.8	15.7	16.5	17.4	18.1
95°	29.5	29.7	29.9	30.1	30.3	30.9	31.9	32.9	33.9	34.9	35.6
97.5°	48.9	49.0	49.1	49.2	49.3	50.0	51.4	52.8	54.2	55.6	56.2
100°	63.5	63.5	63.5	63.5	63.5	64.1	65.4	66.7	68.0	69.3	70.3
102.5°	79.0	79.4	79.9	80.3	80.7	81.2	81.9	82.5	83.2	83.8	84.8
105°	103.3	103.8	104.3	104.8	105.4	105.9	106.5	107.1	107.7	108.3	108.9
107.5°	130.2	130.7	131.2	131.7	132.2	132.7	133.1	133.6	134.1	134.5	134.8
110°	148.7	149.2	149.7	150.2	150.7	151.1	151.4	151.7	152.0	152.3	152.6



TEST NUMBER: P333703

CATALOG NUMBER: S125RDIW-S1090D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.5	167.8	168.0	168.3	168.6	168.9	169.3	169.7	170.0	170.4	170.6
115°	195.3	195.7	196.2	196.6	197.0	197.3	197.5	197.7	197.9	198.1	198.0
117.5°	223.3	223.4	223.6	223.8	224.0	224.2	224.4	224.5	224.7	224.9	225.0
120°	240.7	241.2	241.7	242.2	242.7	243.0	243.1	243.2	243.3	243.4	243.4
122.5°	259.5	259.7	259.9	260.1	260.2	260.5	260.7	261.0	261.3	261.5	261.4
125°	285.1	285.7	286.3	286.9	287.5	287.9	288.0	288.1	288.2	288.3	288.1
127.5°	312.3	312.6	313.0	313.3	313.7	313.9	314.0	314.1	314.2	314.4	314.3
130°	328.6	329.1	329.6	330.1	330.6	331.0	331.2	331.4	331.6	331.8	331.7
132.5°	344.9	345.7	346.6	347.4	348.2	348.6	348.6	348.5	348.5	348.4	348.3
135°	370.7	371.4	372.0	372.6	373.2	373.5	373.6	373.7	373.8	373.9	373.9
137.5°	395.0	395.6	396.2	396.8	397.4	397.8	398.0	398.2	398.4	398.7	398.8
140°	410.6	411.1	411.6	412.1	412.6	413.1	413.4	413.7	414.0	414.3	414.5
142.5°	426.2	426.6	427.1	427.5	427.9	428.3	428.7	429.1	429.5	429.9	430.0
145°	449.2	449.6	450.0	450.4	450.8	451.1	451.4	451.7	452.0	452.3	452.3
147.5°	470.4	470.6	470.8	471.0	471.3	471.5	471.7	472.0	472.2	472.5	472.7
150°	484.5	484.4	484.3	484.2	484.1	484.3	484.7	485.1	485.5	485.9	485.9
152.5°	496.1	496.3	496.4	496.5	496.7	496.8	497.0	497.2	497.3	497.5	497.7
155°	514.0	514.0	514.0	514.0	514.0	514.0	514.1	514.2	514.3	514.4	514.8
157.5°	529.9	529.7	529.5	529.3	529.0	529.0	529.1	529.2	529.3	529.4	529.8
160°	539.4	539.1	538.7	538.4	538.1	538.0	538.1	538.2	538.3	538.4	538.9
162.5°	547.7	547.5	547.3	547.0	546.8	546.7	546.7	546.7	546.8	546.8	547.3
165°	558.8	558.6	558.4	558.2	558.0	558.0	558.1	558.2	558.3	558.4	558.8
167.5°	568.3	567.9	567.5	567.1	566.7	566.5	566.5	566.5	566.5	566.5	567.1
170°	573.3	572.9	572.5	572.1	571.7	571.5	571.5	571.5	571.5	571.5	572.1
172.5°	577.0	576.6	576.2	575.8	575.4	575.2	575.2	575.2	575.2	575.2	575.8
175°	581.1	580.6	580.2	579.8	579.4	579.2	579.2	579.2	579.2	579.2	579.8
177.5°	583.1	582.8	582.5	582.2	581.8	581.6	581.6	581.5	581.4	581.3	581.8
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333703

CATALOG NUMBER: S125RDIW-S1090D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	17.9	18.0	18.1	18.0	17.8	17.7	17.5	17.3
90°	8.3	8.8	9.3	9.7	10.0	10.3	10.6	10.9
92.5°	18.7	19.4	20.1	20.5	20.7	20.9	21.2	21.4
95°	36.3	37.0	37.7	38.2	38.4	38.6	38.8	39.0
97.5°	56.9	57.6	58.2	58.6	58.7	58.9	59.0	59.1
100°	71.2	72.1	73.0	73.5	73.7	73.9	74.1	74.3
102.5°	85.8	86.8	87.8	88.4	88.7	89.0	89.3	89.6
105°	109.5	110.1	110.7	111.2	111.5	111.8	112.1	112.4
107.5°	135.1	135.4	135.7	135.9	135.9	135.8	135.8	135.8
110°	152.9	153.2	153.5	153.6	153.5	153.4	153.3	153.2



TEST NUMBER: P333703

CATALOG NUMBER: S125RDIW-S1090D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.8	171.0	171.0	170.8	170.6	170.4	170.2
115°	197.9	197.8	197.7	197.6	197.5	197.4	197.3	197.2
117.5°	225.1	225.1	225.2	225.1	224.7	224.3	223.8	223.4
120°	243.4	243.4	243.4	243.2	242.8	242.4	242.0	241.6
122.5°	261.4	261.3	261.2	261.0	260.7	260.4	260.0	259.7
125°	287.9	287.7	287.5	287.3	287.2	287.1	287.0	286.9
127.5°	314.2	314.1	314.0	313.8	313.6	313.4	313.2	313.0
130°	331.6	331.5	331.4	331.2	331.0	330.8	330.6	330.4
132.5°	348.2	348.1	348.0	347.9	347.6	347.3	347.0	346.7
135°	373.9	373.9	373.9	373.7	373.3	372.9	372.5	372.1
137.5°	398.9	399.0	399.2	399.0	398.5	398.0	397.4	396.9
140°	414.7	414.9	415.1	414.9	414.4	413.9	413.4	412.9
142.5°	430.1	430.2	430.3	430.1	429.6	429.1	428.6	428.1
145°	452.3	452.3	452.3	452.2	451.9	451.6	451.3	451.0
147.5°	472.9	473.2	473.4	473.2	472.5	471.8	471.1	470.5
150°	485.9	485.9	485.9	485.8	485.6	485.4	485.2	485.0
152.5°	498.0	498.2	498.4	498.4	498.0	497.7	497.3	496.9
155°	515.2	515.6	516.0	516.0	515.5	515.0	514.5	514.0
157.5°	530.2	530.6	531.0	530.9	530.2	529.5	528.9	528.2
160°	539.3	539.7	540.1	540.0	539.5	539.0	538.5	538.0
162.5°	547.8	548.2	548.7	548.7	548.1	547.5	546.9	546.3
165°	559.2	559.6	560.0	559.9	559.3	558.7	558.1	557.5
167.5°	567.7	568.3	568.9	568.9	568.2	567.6	567.0	566.4
170°	572.7	573.3	574.0	573.9	573.2	572.5	571.8	571.1
172.5°	576.4	577.0	577.6	577.6	576.9	576.3	575.7	575.1
175°	580.4	581.1	581.7	581.6	580.9	580.2	579.5	578.8
177.5°	582.3	582.8	583.3	583.2	582.7	582.1	581.5	581.0
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4

(END OF REPORT)