

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333641

Luminaire Tested: **S125RDIW-S375D470U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333641
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D470U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3084.8 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47																				
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41																				
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35																				
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30																				
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	32	29	26																				
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23																				
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20																				
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18																				
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18	16																				
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	16	14																				
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3635	3635	3635	3635
5°	4182	3640	3215	3640
10°	4798	3621	2837	3621
15°	5182	3584	2521	3584
20°	5714	3542	2328	3542
25°	6613	3484	2161	3484
30°	7196	3424	2051	3424
35°	6070	3354	1949	3354
40°	4239	3228	1862	3228
45°	3145	3058	1777	3058
50°	2508	2882	1704	2882
55°	2128	2662	1639	2662
60°	1838	2466	1535	2466
65°	1638	2253	1320	2253
70°	1441	2064	1205	2064
75°	1245	1787	1130	1787
80°	945	1503	945	1503
85°	785	1178	889	1178



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.7
10°-20°	158.2	5.1
20°-30°	250.8	8.1
30°-40°	302.5	9.8
40°-50°	270.1	8.8
50°-60°	207.1	6.7
60°-70°	134.6	4.4
70°-80°	65.4	2.1
80°-90°	16.9	0.5
90°-100°	39.0	1.3
100°-110°	115.2	3.7
110°-120°	195.1	6.3
120°-130°	256.8	8.3
130°-140°	287.7	9.3
140°-150°	282.0	9.1
150°-160°	236.9	7.7
160°-170°	157.4	5.1
170°-180°	55.1	1.8
0°-30°	463.0	15.0
0°-40°	765.4	24.8
0°-60°	1242.7	40.3
0°-90°	1459.6	47.3
90°-120°	349.3	11.3
90°-150°	1175.8	38.1
90°-180°	1625.0	52.7
0°-180°	3084.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	645	562	496	562	645	64
15°	775	536	377	536	775	222
25°	928	489	303	489	928	426
35°	770	425	247	425	770	465
45°	344	335	195	335	344	275
55°	189	236	146	236	189	172
65°	107	147	86	147	107	107
75°	50	72	45	72	50	53
85°	11	16	12	16	11	12
90°	11	0	11	0	11	7
95°	39	30	39	30	39	40
105°	112	103	112	103	112	119
115°	197	195	197	195	197	195
125°	287	285	287	285	287	256
135°	372	371	372	371	372	287
145°	451	449	451	449	451	282
155°	514	514	514	514	514	237
165°	558	559	558	559	558	157
175°	579	581	579	581	579	55
180°	582	582	582	582	582	



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	592.1	591.7	592.5	590.4	590.6	587.5	587.5	585.1	581.9	579.5	578.4
5°	645.1	645.6	644.7	641.2	638.9	635.4	631.5	624.6	618.8	613.2	608.9
7.5°	699.8	700.1	697.0	696.0	690.1	685.9	677.2	667.7	659.4	648.7	640.6
10°	731.6	731.3	728.1	725.5	720.5	714.0	705.4	694.4	684.0	672.4	661.3
12.5°	750.0	749.4	748.4	745.3	740.6	734.9	727.6	716.7	703.9	691.3	678.3
15°	775.0	773.4	770.4	766.4	759.7	753.0	745.0	735.3	723.0	708.7	696.7
17.5°	805.9	805.9	801.3	795.8	786.7	774.9	762.4	746.8	730.1	714.4	701.6
20°	831.4	830.7	826.1	815.4	805.0	790.2	775.9	756.7	736.4	715.8	699.9
22.5°	868.0	866.2	861.4	847.4	831.3	812.2	790.3	766.9	742.3	719.0	698.0
25°	928.0	926.6	917.1	900.9	878.3	848.9	820.3	788.2	752.8	722.1	696.7
27.5°	969.0	967.5	960.4	947.0	926.1	895.2	856.5	813.5	769.4	727.1	690.5
30°	964.9	968.4	967.5	961.2	945.5	917.8	882.0	833.7	781.2	731.6	687.9
32.5°	906.9	910.0	918.1	930.4	931.3	920.2	893.4	848.8	794.5	738.0	685.8
35°	769.9	774.1	789.8	814.5	846.9	873.9	879.4	855.4	806.6	745.9	682.8
37.5°	591.9	614.6	627.9	653.9	702.8	752.5	800.3	817.9	797.2	742.6	677.9
40°	502.8	508.3	531.9	561.3	602.4	654.1	722.3	771.5	773.1	735.3	670.1
42.5°	430.3	437.4	453.5	477.0	512.2	563.9	634.3	699.3	729.3	714.9	659.9
45°	344.3	349.6	361.4	379.4	406.4	449.2	509.7	584.8	644.4	667.8	632.7
47.5°	282.8	285.7	295.9	309.7	329.7	360.8	407.7	472.9	544.4	594.5	589.6
50°	249.6	252.8	260.6	271.0	287.9	314.2	351.7	406.0	479.7	540.9	553.2
52.5°	223.7	226.4	231.3	241.1	255.0	275.2	305.5	354.6	420.9	486.0	514.4
55°	189.0	190.9	194.8	200.3	211.4	226.0	252.1	286.1	339.7	405.3	446.9
57.5°	160.5	161.4	163.9	169.0	176.7	187.3	206.2	234.9	273.4	332.5	378.4
60°	142.3	143.3	146.5	150.0	156.0	165.7	180.5	200.6	237.5	286.3	332.7
62.5°	127.9	128.5	129.9	133.3	138.6	146.1	157.7	174.1	203.5	246.4	290.2
65°	107.2	107.4	107.9	110.7	113.9	119.5	127.1	138.6	160.8	193.2	232.0
67.5°	87.3	87.7	89.3	90.3	93.6	96.5	101.0	109.8	125.5	147.3	177.5
70°	76.3	76.0	77.6	78.8	79.9	83.4	86.4	93.6	103.3	119.9	145.1
72.5°	65.9	65.3	66.0	66.4	67.9	70.3	73.3	77.7	85.2	96.6	115.9
75°	49.9	50.1	50.1	50.6	51.8	52.7	53.6	55.9	60.1	67.7	78.1
77.5°	35.0	34.7	35.6	35.8	36.5	37.5	38.3	39.2	40.9	44.0	49.4
80°	25.4	25.4	25.6	26.3	26.1	26.6	27.7	28.7	30.7	32.6	34.4
82.5°	19.5	19.3	19.5	19.7	19.6	20.1	20.5	20.7	21.5	22.4	23.7
85°	10.6	10.6	10.9	10.9	11.1	11.1	11.3	11.3	11.3	11.6	11.8
87.5°	6.2	6.0	5.8	5.7	5.8	6.1	5.8	5.5	5.4	5.3	5.4
90°	10.9	10.6	10.3	10.0	9.7	9.3	8.8	8.3	7.8	7.3	6.5
92.5°	21.4	21.2	20.9	20.7	20.5	20.1	19.4	18.7	18.1	17.4	16.5
95°	39.0	38.8	38.6	38.4	38.2	37.7	37.0	36.3	35.6	34.9	33.9
97.5°	59.1	59.0	58.9	58.7	58.6	58.2	57.6	56.9	56.2	55.6	54.2
100°	74.3	74.1	73.9	73.7	73.5	73.0	72.1	71.2	70.3	69.3	68.0
102.5°	89.6	89.3	89.0	88.7	88.4	87.8	86.8	85.8	84.8	83.8	83.2
105°	112.4	112.1	111.8	111.5	111.2	110.7	110.1	109.5	108.9	108.3	107.7
107.5°	135.8	135.8	135.8	135.9	135.9	135.7	135.4	135.1	134.8	134.5	134.1
110°	153.2	153.3	153.4	153.5	153.6	153.5	153.2	152.9	152.6	152.3	152.0



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.2	170.4	170.6	170.8	171.0	171.0	170.8	170.7	170.6	170.4	170.0
115°	197.2	197.3	197.4	197.5	197.6	197.7	197.8	197.9	198.0	198.1	197.9
117.5°	223.4	223.8	224.3	224.7	225.1	225.2	225.1	225.1	225.0	224.9	224.7
120°	241.6	242.0	242.4	242.8	243.2	243.4	243.4	243.4	243.4	243.4	243.3
122.5°	259.7	260.0	260.4	260.7	261.0	261.2	261.3	261.4	261.4	261.5	261.3
125°	286.9	287.0	287.1	287.2	287.3	287.5	287.7	287.9	288.1	288.3	288.2
127.5°	313.0	313.2	313.4	313.6	313.8	314.0	314.1	314.2	314.3	314.4	314.2
130°	330.4	330.6	330.8	331.0	331.2	331.4	331.5	331.6	331.7	331.8	331.6
132.5°	346.7	347.0	347.3	347.6	347.9	348.0	348.1	348.2	348.3	348.4	348.5
135°	372.1	372.5	372.9	373.3	373.7	373.9	373.9	373.9	373.9	373.9	373.8
137.5°	396.9	397.4	398.0	398.5	399.0	399.2	399.0	398.9	398.8	398.7	398.4
140°	412.9	413.4	413.9	414.4	414.9	415.1	414.9	414.7	414.5	414.3	414.0
142.5°	428.1	428.6	429.1	429.6	430.1	430.3	430.2	430.1	430.0	429.9	429.5
145°	451.0	451.3	451.6	451.9	452.2	452.3	452.3	452.3	452.3	452.3	452.0
147.5°	470.5	471.1	471.8	472.5	473.2	473.4	473.2	472.9	472.7	472.5	472.2
150°	485.0	485.2	485.4	485.6	485.8	485.9	485.9	485.9	485.9	485.9	485.5
152.5°	496.9	497.3	497.7	498.0	498.4	498.4	498.2	498.0	497.7	497.5	497.3
155°	514.0	514.5	515.0	515.5	516.0	516.0	515.6	515.2	514.8	514.4	514.3
157.5°	528.2	528.9	529.5	530.2	530.9	531.0	530.6	530.2	529.8	529.4	529.3
160°	538.0	538.5	539.0	539.5	540.0	540.1	539.7	539.3	538.9	538.4	538.3
162.5°	546.3	546.9	547.5	548.1	548.7	548.7	548.2	547.8	547.3	546.8	546.8
165°	557.5	558.1	558.7	559.3	559.9	560.0	559.6	559.2	558.8	558.4	558.3
167.5°	566.4	567.0	567.6	568.2	568.9	568.9	568.3	567.7	567.1	566.5	566.5
170°	571.1	571.8	572.5	573.2	573.9	574.0	573.3	572.7	572.1	571.5	571.5
172.5°	575.1	575.7	576.3	576.9	577.6	577.6	577.0	576.4	575.8	575.2	575.2
175°	578.8	579.5	580.2	580.9	581.6	581.7	581.1	580.4	579.8	579.2	579.2
177.5°	581.0	581.5	582.1	582.7	583.2	583.3	582.8	582.3	581.8	581.3	581.4
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	578.4	577.1	574.7	572.5	569.7	567.3	565.6	563.6	561.0	557.9	555.3
5°	604.0	598.9	592.2	586.4	579.0	573.3	567.3	561.5	555.7	548.3	541.8
7.5°	632.4	621.9	611.7	598.8	587.2	576.8	566.8	556.7	546.8	536.3	526.2
10°	649.8	637.0	623.0	606.8	592.0	577.9	565.0	552.2	538.8	527.1	514.4
12.5°	666.0	649.6	633.5	613.1	595.3	578.1	561.6	545.8	531.5	516.2	502.5
15°	680.7	664.5	646.5	621.6	596.8	576.0	556.6	536.1	518.3	501.2	485.9
17.5°	686.4	669.4	648.5	624.5	597.5	571.3	546.3	523.8	502.8	482.9	465.8
20°	684.2	667.8	646.3	623.4	594.5	567.3	540.2	515.3	491.9	470.9	452.7
22.5°	678.8	661.9	641.1	616.9	589.5	560.6	531.7	505.1	480.7	458.9	439.0
25°	670.8	647.7	626.4	602.8	576.7	548.1	518.3	488.9	462.8	440.6	418.9
27.5°	662.4	633.6	606.5	583.1	555.5	530.0	501.2	471.1	443.7	421.1	398.8
30°	654.8	622.5	592.7	566.1	540.0	515.7	488.5	459.1	430.9	407.6	385.0
32.5°	645.4	611.0	578.3	547.6	522.4	498.4	473.7	445.6	418.2	394.1	371.1
35°	633.6	589.7	554.1	521.5	493.6	470.2	448.0	425.4	397.9	372.9	350.5
37.5°	618.1	568.2	527.1	491.6	462.1	438.7	421.1	400.4	375.3	351.5	330.7
40°	608.6	552.7	507.7	472.5	441.6	416.8	400.4	382.9	360.0	337.6	316.8
42.5°	596.1	538.5	488.1	451.5	420.3	396.5	379.9	364.6	345.4	324.3	302.0
45°	571.4	510.9	458.0	418.7	387.3	363.9	348.4	334.8	320.3	300.8	281.4
47.5°	539.4	482.1	426.7	383.8	353.1	331.4	316.4	305.6	295.2	278.7	259.9
50°	513.7	458.4	404.4	362.8	330.0	309.4	295.3	286.8	277.3	262.3	246.5
52.5°	483.3	434.0	381.1	338.6	307.6	288.3	274.8	266.2	258.4	246.2	231.2
55°	435.6	392.3	343.8	305.2	276.8	257.4	244.5	236.4	231.8	221.4	209.6
57.5°	380.4	349.5	306.7	269.5	244.3	225.2	215.7	208.8	203.6	196.2	187.9
60°	342.0	320.3	281.9	246.5	223.4	205.2	196.6	190.9	186.0	179.8	173.3
62.5°	303.0	287.2	253.8	223.4	202.2	186.9	178.9	173.7	168.1	163.9	157.6
65°	250.7	236.6	213.5	189.7	170.1	157.8	152.0	147.4	144.0	139.3	134.9
67.5°	195.0	189.3	173.3	156.9	142.8	131.9	126.9	123.7	119.6	116.8	113.8
70°	160.8	158.0	146.7	135.9	122.7	115.3	110.7	109.3	104.2	101.4	99.4
72.5°	130.5	129.2	122.7	115.2	105.9	99.4	95.2	93.6	90.3	88.1	86.8
75°	89.4	89.9	88.7	83.9	80.4	76.3	72.6	71.6	69.3	67.5	66.3
77.5°	56.6	58.9	59.0	58.8	57.4	54.9	53.3	52.6	50.4	49.7	49.4
80°	38.8	41.4	43.7	43.4	43.0	42.3	41.1	40.4	39.3	38.6	38.1
82.5°	25.9	28.2	30.2	31.4	31.3	30.6	29.9	29.5	29.3	28.8	28.7
85°	12.2	12.7	13.4	15.0	16.2	16.4	16.2	15.9	15.3	15.5	15.7
87.5°	5.4	5.3	5.3	5.2	4.8	5.6	6.0	6.0	5.8	5.6	5.4
90°	5.8	5.1	4.4	3.7	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	15.7	14.8	13.9	13.2	12.7	12.1	11.5	11.0	11.5	12.1	12.7
95°	32.9	31.9	30.9	30.3	30.1	29.9	29.7	29.5	29.7	29.9	30.1
97.5°	52.8	51.4	50.0	49.3	49.2	49.1	49.0	48.9	49.0	49.1	49.2
100°	66.7	65.4	64.1	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5
102.5°	82.5	81.9	81.2	80.7	80.3	79.9	79.4	79.0	79.4	79.9	80.3
105°	107.1	106.5	105.9	105.4	104.8	104.3	103.8	103.3	103.8	104.3	104.8
107.5°	133.6	133.1	132.7	132.2	131.7	131.2	130.7	130.2	130.7	131.2	131.7
110°	151.7	151.4	151.1	150.7	150.2	149.7	149.2	148.7	149.2	149.7	150.2



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	169.7	169.3	168.9	168.6	168.3	168.0	167.8	167.5	167.8	168.0	168.3
115°	197.7	197.5	197.3	197.0	196.6	196.2	195.7	195.3	195.7	196.2	196.6
117.5°	224.5	224.4	224.2	224.0	223.8	223.6	223.4	223.3	223.4	223.6	223.8
120°	243.2	243.1	243.0	242.7	242.2	241.7	241.2	240.7	241.2	241.7	242.2
122.5°	261.0	260.7	260.5	260.2	260.1	259.9	259.7	259.5	259.7	259.9	260.1
125°	288.1	288.0	287.9	287.5	286.9	286.3	285.7	285.1	285.7	286.3	286.9
127.5°	314.1	314.0	313.9	313.7	313.3	313.0	312.6	312.3	312.6	313.0	313.3
130°	331.4	331.2	331.0	330.6	330.1	329.6	329.1	328.6	329.1	329.6	330.1
132.5°	348.5	348.6	348.6	348.2	347.4	346.6	345.7	344.9	345.7	346.6	347.4
135°	373.7	373.6	373.5	373.2	372.6	372.0	371.4	370.7	371.4	372.0	372.6
137.5°	398.2	398.0	397.8	397.4	396.8	396.2	395.6	395.0	395.6	396.2	396.8
140°	413.7	413.4	413.1	412.6	412.1	411.6	411.1	410.6	411.1	411.6	412.1
142.5°	429.1	428.7	428.3	427.9	427.5	427.1	426.6	426.2	426.6	427.1	427.5
145°	451.7	451.4	451.1	450.8	450.4	450.0	449.6	449.2	449.6	450.0	450.4
147.5°	472.0	471.7	471.5	471.3	471.0	470.8	470.6	470.4	470.6	470.8	471.0
150°	485.1	484.7	484.3	484.1	484.2	484.3	484.4	484.5	484.4	484.3	484.2
152.5°	497.2	497.0	496.8	496.7	496.5	496.4	496.3	496.1	496.3	496.4	496.5
155°	514.2	514.1	514.0	514.0	514.0	514.0	514.0	514.0	514.0	514.0	514.0
157.5°	529.2	529.1	529.0	529.0	529.3	529.5	529.7	529.9	529.7	529.5	529.3
160°	538.2	538.1	538.0	538.1	538.4	538.7	539.1	539.4	539.1	538.7	538.4
162.5°	546.7	546.7	546.7	546.8	547.0	547.3	547.5	547.7	547.5	547.3	547.0
165°	558.2	558.1	558.0	558.0	558.2	558.4	558.6	558.8	558.6	558.4	558.2
167.5°	566.5	566.5	566.5	566.7	567.1	567.5	567.9	568.3	567.9	567.5	567.1
170°	571.5	571.5	571.5	571.7	572.1	572.5	572.9	573.3	572.9	572.5	572.1
172.5°	575.2	575.2	575.2	575.4	575.8	576.2	576.6	577.0	576.6	576.2	575.8
175°	579.2	579.2	579.2	579.4	579.8	580.2	580.6	581.1	580.6	580.2	579.8
177.5°	581.5	581.6	581.6	581.8	582.2	582.5	582.8	583.1	582.8	582.5	582.2
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	553.4	550.9	549.0	545.3	542.7	541.6	539.6	539.0	541.1	539.6	539.4
5°	537.0	530.3	525.0	519.7	513.9	510.2	504.6	503.7	502.3	500.3	499.8
7.5°	517.3	508.5	501.7	492.9	485.3	479.1	472.2	468.9	467.1	464.4	460.8
10°	504.0	493.6	484.3	475.5	466.1	458.4	451.5	446.2	442.7	439.5	438.1
12.5°	490.8	480.2	468.4	457.8	447.2	438.7	431.0	427.5	423.7	419.9	416.7
15°	470.4	456.4	443.4	431.2	422.2	412.9	405.5	400.4	394.7	393.0	386.8
17.5°	448.8	435.0	419.8	407.0	396.5	386.3	378.2	372.4	368.1	362.1	359.3
20°	435.3	418.9	404.1	392.3	380.8	368.8	360.5	355.6	351.5	346.6	344.3
22.5°	420.9	404.9	389.7	375.9	364.2	352.3	346.4	341.4	336.7	332.2	329.1
25°	399.7	383.6	367.6	353.3	341.1	332.5	325.6	319.8	317.3	312.9	309.6
27.5°	378.8	361.6	345.1	330.8	321.2	312.7	307.0	302.5	297.9	294.1	291.2
30°	365.3	347.8	329.7	318.4	308.2	300.2	293.9	289.5	286.1	282.6	280.5
32.5°	351.8	333.7	317.7	305.5	295.9	288.9	282.5	278.2	274.6	270.8	268.3
35°	330.2	311.7	298.8	286.8	277.3	270.8	266.4	260.4	257.4	254.6	252.1
37.5°	310.1	292.9	278.9	268.4	260.1	253.7	248.0	244.8	241.1	238.6	236.5
40°	295.3	279.6	266.9	255.8	249.8	242.6	237.3	233.1	230.4	227.1	224.8
42.5°	282.0	267.4	255.0	245.1	237.6	231.5	226.4	222.2	218.7	216.4	214.5
45°	263.2	248.6	236.6	227.4	220.4	214.7	209.3	207.3	202.6	199.9	198.9
47.5°	243.7	230.7	219.1	210.6	203.5	198.0	193.0	188.8	186.2	183.5	182.0
50°	230.6	218.1	207.3	198.9	192.0	186.0	181.4	178.6	175.1	172.6	170.8
52.5°	217.5	205.9	195.1	187.1	181.1	175.1	169.9	167.2	163.9	162.3	161.0
55°	198.7	186.5	177.2	169.4	163.1	157.6	152.7	150.0	147.9	146.3	145.8
57.5°	177.5	167.8	159.2	152.1	145.6	140.4	136.1	133.5	131.7	131.4	130.0
60°	163.6	154.8	147.0	139.3	133.8	128.9	125.2	122.2	120.4	120.2	119.7
62.5°	149.7	141.3	134.0	127.3	122.3	117.7	114.1	110.8	109.7	108.5	107.5
65°	129.2	121.5	115.5	110.2	104.9	101.0	97.5	95.4	92.9	91.5	89.0
67.5°	109.0	103.1	97.3	92.8	88.6	84.9	82.0	78.9	77.2	76.1	74.3
70°	95.7	91.0	85.3	80.4	77.2	74.2	71.9	68.4	67.2	66.3	65.4
72.5°	83.1	79.0	74.2	70.2	67.0	64.2	61.5	59.9	58.7	57.8	57.3
75°	65.4	61.5	57.3	54.5	52.2	49.9	48.5	47.4	46.9	46.7	45.8
77.5°	48.0	45.9	42.6	40.4	38.9	37.9	36.7	36.1	36.0	35.0	34.7
80°	36.7	35.6	32.8	31.9	30.7	29.8	29.1	28.0	26.8	26.3	25.6
82.5°	27.3	26.2	25.0	23.6	22.6	22.0	21.4	20.9	21.1	20.4	20.1
85°	14.6	13.4	12.9	12.7	12.2	12.7	12.5	12.2	12.0	11.8	12.0
87.5°	5.4	5.5	5.5	6.0	5.6	5.9	6.0	5.9	6.0	6.1	6.0
90°	3.7	4.4	5.1	5.8	6.5	7.3	7.8	8.3	8.8	9.3	9.7
92.5°	13.2	13.9	14.8	15.7	16.5	17.4	18.1	18.7	19.4	20.1	20.5
95°	30.3	30.9	31.9	32.9	33.9	34.9	35.6	36.3	37.0	37.7	38.2
97.5°	49.3	50.0	51.4	52.8	54.2	55.6	56.2	56.9	57.6	58.2	58.6
100°	63.5	64.1	65.4	66.7	68.0	69.3	70.3	71.2	72.1	73.0	73.5
102.5°	80.7	81.2	81.9	82.5	83.2	83.8	84.8	85.8	86.8	87.8	88.4
105°	105.4	105.9	106.5	107.1	107.7	108.3	108.9	109.5	110.1	110.7	111.2
107.5°	132.2	132.7	133.1	133.6	134.1	134.5	134.8	135.1	135.4	135.7	135.9
110°	150.7	151.1	151.4	151.7	152.0	152.3	152.6	152.9	153.2	153.5	153.6



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.6	168.9	169.3	169.7	170.0	170.4	170.6	170.7	170.8	171.0	171.0
115°	197.0	197.3	197.5	197.7	197.9	198.1	198.0	197.9	197.8	197.7	197.6
117.5°	224.0	224.2	224.4	224.5	224.7	224.9	225.0	225.1	225.1	225.2	225.1
120°	242.7	243.0	243.1	243.2	243.3	243.4	243.4	243.4	243.4	243.4	243.2
122.5°	260.2	260.5	260.7	261.0	261.3	261.5	261.4	261.4	261.3	261.2	261.0
125°	287.5	287.9	288.0	288.1	288.2	288.3	288.1	287.9	287.7	287.5	287.3
127.5°	313.7	313.9	314.0	314.1	314.2	314.4	314.3	314.2	314.1	314.0	313.8
130°	330.6	331.0	331.2	331.4	331.6	331.8	331.7	331.6	331.5	331.4	331.2
132.5°	348.2	348.6	348.6	348.5	348.5	348.4	348.3	348.2	348.1	348.0	347.9
135°	373.2	373.5	373.6	373.7	373.8	373.9	373.9	373.9	373.9	373.9	373.7
137.5°	397.4	397.8	398.0	398.2	398.4	398.7	398.8	398.9	399.0	399.2	399.0
140°	412.6	413.1	413.4	413.7	414.0	414.3	414.5	414.7	414.9	415.1	414.9
142.5°	427.9	428.3	428.7	429.1	429.5	429.9	430.0	430.1	430.2	430.3	430.1
145°	450.8	451.1	451.4	451.7	452.0	452.3	452.3	452.3	452.3	452.3	452.2
147.5°	471.3	471.5	471.7	472.0	472.2	472.5	472.7	472.9	473.2	473.4	473.2
150°	484.1	484.3	484.7	485.1	485.5	485.9	485.9	485.9	485.9	485.9	485.8
152.5°	496.7	496.8	497.0	497.2	497.3	497.5	497.7	498.0	498.2	498.4	498.4
155°	514.0	514.0	514.1	514.2	514.3	514.4	514.8	515.2	515.6	516.0	516.0
157.5°	529.0	529.0	529.1	529.2	529.3	529.4	529.8	530.2	530.6	531.0	530.9
160°	538.1	538.0	538.1	538.2	538.3	538.4	538.9	539.3	539.7	540.1	540.0
162.5°	546.8	546.7	546.7	546.7	546.8	546.8	547.3	547.8	548.2	548.7	548.7
165°	558.0	558.0	558.1	558.2	558.3	558.4	558.8	559.2	559.6	560.0	559.9
167.5°	566.7	566.5	566.5	566.5	566.5	566.5	567.1	567.7	568.3	568.9	568.9
170°	571.7	571.5	571.5	571.5	571.5	571.5	572.1	572.7	573.3	574.0	573.9
172.5°	575.4	575.2	575.2	575.2	575.2	575.2	575.8	576.4	577.0	577.6	577.6
175°	579.4	579.2	579.2	579.2	579.2	579.2	579.8	580.4	581.1	581.7	581.6
177.5°	581.8	581.6	581.6	581.5	581.4	581.3	581.8	582.3	582.8	583.3	583.2
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.2	537.2	536.6	537.4	536.6	537.2	539.2	539.4	539.6	541.1	539.0
5°	497.5	495.2	496.3	495.9	496.3	495.2	497.5	499.8	500.3	502.3	503.7
7.5°	460.8	457.9	454.9	455.8	454.9	457.9	460.8	460.8	464.4	467.1	468.9
10°	435.1	432.8	431.4	432.6	431.4	432.8	435.1	438.1	439.5	442.7	446.2
12.5°	413.5	412.1	410.9	410.4	410.9	412.1	413.5	416.7	419.9	423.7	427.5
15°	384.0	381.3	380.1	377.1	380.1	381.3	384.0	386.8	393.0	394.7	400.4
17.5°	356.9	356.0	353.0	351.7	353.0	356.0	356.9	359.3	362.1	368.1	372.4
20°	340.8	339.9	336.9	338.7	336.9	339.9	340.8	344.3	346.6	351.5	355.6
22.5°	327.5	325.5	324.5	324.0	324.5	325.5	327.5	329.1	332.2	336.7	341.4
25°	308.7	305.7	304.5	303.2	304.5	305.7	308.7	309.6	312.9	317.3	319.8
27.5°	289.9	288.3	286.8	286.4	286.8	288.3	289.9	291.2	294.1	297.9	302.5
30°	277.7	276.1	275.0	275.0	275.0	276.1	277.7	280.5	282.6	286.1	289.5
32.5°	266.8	265.6	264.4	264.2	264.4	265.6	266.8	268.3	270.8	274.6	278.2
35°	250.9	249.1	248.6	247.2	248.6	249.1	250.9	252.1	254.6	257.4	260.4
37.5°	234.4	232.9	232.9	232.7	232.9	232.9	234.4	236.5	238.6	241.1	244.8
40°	223.9	222.7	222.5	220.9	222.5	222.7	223.9	224.8	227.1	230.4	233.1
42.5°	212.6	212.0	211.2	210.5	211.2	212.0	212.6	214.5	216.4	218.7	222.2
45°	197.3	195.7	195.7	194.6	195.7	195.7	197.3	198.9	199.9	202.6	207.3
47.5°	181.5	180.3	180.4	179.2	180.4	180.3	181.5	182.0	183.5	186.2	188.8
50°	171.0	170.3	170.1	169.6	170.1	170.3	171.0	170.8	172.6	175.1	178.6
52.5°	160.5	160.1	161.0	160.0	161.0	160.1	160.5	161.0	162.3	163.9	167.2
55°	146.3	145.6	147.0	145.6	147.0	145.6	146.3	145.8	146.3	147.9	150.0
57.5°	130.0	129.3	130.6	129.9	130.6	129.3	130.0	130.0	131.4	131.7	133.5
60°	119.2	117.8	118.5	118.8	118.5	117.8	119.2	119.7	120.2	120.4	122.2
62.5°	106.5	105.6	106.2	105.1	106.2	105.6	106.5	107.5	108.5	109.7	110.8
65°	88.5	87.8	86.9	86.4	86.9	87.8	88.5	89.0	91.5	92.9	95.4
67.5°	74.4	72.7	72.6	73.0	72.6	72.7	74.4	74.3	76.1	77.2	78.9
70°	64.0	64.0	63.8	63.8	63.8	64.0	64.0	65.4	66.3	67.2	68.4
72.5°	56.8	56.6	56.2	56.0	56.2	56.6	56.8	57.3	57.8	58.7	59.9
75°	45.8	46.0	45.5	45.3	45.5	46.0	45.8	45.8	46.7	46.9	47.4
77.5°	33.8	32.8	33.3	32.8	33.3	32.8	33.8	34.7	35.0	36.0	36.1
80°	25.6	25.4	26.1	25.4	26.1	25.4	25.6	25.6	26.3	26.8	28.0
82.5°	20.3	20.1	20.4	19.9	20.4	20.1	20.3	20.1	20.4	21.1	20.9
85°	12.2	12.0	11.8	12.0	11.8	12.0	12.2	12.0	11.8	12.0	12.2
87.5°	6.2	6.1	6.2	6.2	6.2	6.1	6.2	6.0	6.1	6.0	5.9
90°	10.0	10.3	10.6	10.9	10.6	10.3	10.0	9.7	9.3	8.8	8.3
92.5°	20.7	20.9	21.2	21.4	21.2	20.9	20.7	20.5	20.1	19.4	18.7
95°	38.4	38.6	38.8	39.0	38.8	38.6	38.4	38.2	37.7	37.0	36.3
97.5°	58.7	58.9	59.0	59.1	59.0	58.9	58.7	58.6	58.2	57.6	56.9
100°	73.7	73.9	74.1	74.3	74.1	73.9	73.7	73.5	73.0	72.1	71.2
102.5°	88.7	89.0	89.3	89.6	89.3	89.0	88.7	88.4	87.8	86.8	85.8
105°	111.5	111.8	112.1	112.4	112.1	111.8	111.5	111.2	110.7	110.1	109.5
107.5°	135.9	135.8	135.8	135.8	135.8	135.8	135.9	135.9	135.7	135.4	135.1
110°	153.5	153.4	153.3	153.2	153.3	153.4	153.5	153.6	153.5	153.2	152.9



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	170.8	170.6	170.4	170.2	170.4	170.6	170.8	171.0	171.0	170.8	170.7
115°	197.5	197.4	197.3	197.2	197.3	197.4	197.5	197.6	197.7	197.8	197.9
117.5°	224.7	224.3	223.8	223.4	223.8	224.3	224.7	225.1	225.2	225.1	225.1
120°	242.8	242.4	242.0	241.6	242.0	242.4	242.8	243.2	243.4	243.4	243.4
122.5°	260.7	260.4	260.0	259.7	260.0	260.4	260.7	261.0	261.2	261.3	261.4
125°	287.2	287.1	287.0	286.9	287.0	287.1	287.2	287.3	287.5	287.7	287.9
127.5°	313.6	313.4	313.2	313.0	313.2	313.4	313.6	313.8	314.0	314.1	314.2
130°	331.0	330.8	330.6	330.4	330.6	330.8	331.0	331.2	331.4	331.5	331.6
132.5°	347.6	347.3	347.0	346.7	347.0	347.3	347.6	347.9	348.0	348.1	348.2
135°	373.3	372.9	372.5	372.1	372.5	372.9	373.3	373.7	373.9	373.9	373.9
137.5°	398.5	398.0	397.4	396.9	397.4	398.0	398.5	399.0	399.2	399.0	398.9
140°	414.4	413.9	413.4	412.9	413.4	413.9	414.4	414.9	415.1	414.9	414.7
142.5°	429.6	429.1	428.6	428.1	428.6	429.1	429.6	430.1	430.3	430.2	430.1
145°	451.9	451.6	451.3	451.0	451.3	451.6	451.9	452.2	452.3	452.3	452.3
147.5°	472.5	471.8	471.1	470.5	471.1	471.8	472.5	473.2	473.4	473.2	472.9
150°	485.6	485.4	485.2	485.0	485.2	485.4	485.6	485.8	485.9	485.9	485.9
152.5°	498.0	497.7	497.3	496.9	497.3	497.7	498.0	498.4	498.4	498.2	498.0
155°	515.5	515.0	514.5	514.0	514.5	515.0	515.5	516.0	516.0	515.6	515.2
157.5°	530.2	529.5	528.9	528.2	528.9	529.5	530.2	530.9	531.0	530.6	530.2
160°	539.5	539.0	538.5	538.0	538.5	539.0	539.5	540.0	540.1	539.7	539.3
162.5°	548.1	547.5	546.9	546.3	546.9	547.5	548.1	548.7	548.7	548.2	547.8
165°	559.3	558.7	558.1	557.5	558.1	558.7	559.3	559.9	560.0	559.6	559.2
167.5°	568.2	567.6	567.0	566.4	567.0	567.6	568.2	568.9	568.9	568.3	567.7
170°	573.2	572.5	571.8	571.1	571.8	572.5	573.2	573.9	574.0	573.3	572.7
172.5°	576.9	576.3	575.7	575.1	575.7	576.3	576.9	577.6	577.6	577.0	576.4
175°	580.9	580.2	579.5	578.8	579.5	580.2	580.9	581.6	581.7	581.1	580.4
177.5°	582.7	582.1	581.5	581.0	581.5	582.1	582.7	583.2	583.3	582.8	582.3
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.6	541.6	542.7	545.3	549.0	550.9	553.4	555.3	557.9	561.0	563.6
5°	504.6	510.2	513.9	519.7	525.0	530.3	537.0	541.8	548.3	555.7	561.5
7.5°	472.2	479.1	485.3	492.9	501.7	508.5	517.3	526.2	536.3	546.8	556.7
10°	451.5	458.4	466.1	475.5	484.3	493.6	504.0	514.4	527.1	538.8	552.2
12.5°	431.0	438.7	447.2	457.8	468.4	480.2	490.8	502.5	516.2	531.5	545.8
15°	405.5	412.9	422.2	431.2	443.4	456.4	470.4	485.9	501.2	518.3	536.1
17.5°	378.2	386.3	396.5	407.0	419.8	435.0	448.8	465.8	482.9	502.8	523.8
20°	360.5	368.8	380.8	392.3	404.1	418.9	435.3	452.7	470.9	491.9	515.3
22.5°	346.4	352.3	364.2	375.9	389.7	404.9	420.9	439.0	458.9	480.7	505.1
25°	325.6	332.5	341.1	353.3	367.6	383.6	399.7	418.9	440.6	462.8	488.9
27.5°	307.0	312.7	321.2	330.8	345.1	361.6	378.8	398.8	421.1	443.7	471.1
30°	293.9	300.2	308.2	318.4	329.7	347.8	365.3	385.0	407.6	430.9	459.1
32.5°	282.5	288.9	295.9	305.5	317.7	333.7	351.8	371.1	394.1	418.2	445.6
35°	266.4	270.8	277.3	286.8	298.8	311.7	330.2	350.5	372.9	397.9	425.4
37.5°	248.0	253.7	260.1	268.4	278.9	292.9	310.1	330.7	351.5	375.3	400.4
40°	237.3	242.6	249.8	255.8	266.9	279.6	295.3	316.8	337.6	360.0	382.9
42.5°	226.4	231.5	237.6	245.1	255.0	267.4	282.0	302.0	324.3	345.4	364.6
45°	209.3	214.7	220.4	227.4	236.6	248.6	263.2	281.4	300.8	320.3	334.8
47.5°	193.0	198.0	203.5	210.6	219.1	230.7	243.7	259.9	278.7	295.2	305.6
50°	181.4	186.0	192.0	198.9	207.3	218.1	230.6	246.5	262.3	277.3	286.8
52.5°	169.9	175.1	181.1	187.1	195.1	205.9	217.5	231.2	246.2	258.4	266.2
55°	152.7	157.6	163.1	169.4	177.2	186.5	198.7	209.6	221.4	231.8	236.4
57.5°	136.1	140.4	145.6	152.1	159.2	167.8	177.5	187.9	196.2	203.6	208.8
60°	125.2	128.9	133.8	139.3	147.0	154.8	163.6	173.3	179.8	186.0	190.9
62.5°	114.1	117.7	122.3	127.3	134.0	141.3	149.7	157.6	163.9	168.1	173.7
65°	97.5	101.0	104.9	110.2	115.5	121.5	129.2	134.9	139.3	144.0	147.4
67.5°	82.0	84.9	88.6	92.8	97.3	103.1	109.0	113.8	116.8	119.6	123.7
70°	71.9	74.2	77.2	80.4	85.3	91.0	95.7	99.4	101.4	104.2	109.3
72.5°	61.5	64.2	67.0	70.2	74.2	79.0	83.1	86.8	88.1	90.3	93.6
75°	48.5	49.9	52.2	54.5	57.3	61.5	65.4	66.3	67.5	69.3	71.6
77.5°	36.7	37.9	38.9	40.4	42.6	45.9	48.0	49.4	49.7	50.4	52.6
80°	29.1	29.8	30.7	31.9	32.8	35.6	36.7	38.1	38.6	39.3	40.4
82.5°	21.4	22.0	22.6	23.6	25.0	26.2	27.3	28.7	28.8	29.3	29.5
85°	12.5	12.7	12.2	12.7	12.9	13.4	14.6	15.7	15.5	15.3	15.9
87.5°	6.0	5.9	5.6	6.0	5.5	5.5	5.4	5.4	5.6	5.8	6.0
90°	7.8	7.3	6.5	5.8	5.1	4.4	3.7	2.9	2.1	1.3	0.5
92.5°	18.1	17.4	16.5	15.7	14.8	13.9	13.2	12.7	12.1	11.5	11.0
95°	35.6	34.9	33.9	32.9	31.9	30.9	30.3	30.1	29.9	29.7	29.5
97.5°	56.2	55.6	54.2	52.8	51.4	50.0	49.3	49.2	49.1	49.0	48.9
100°	70.3	69.3	68.0	66.7	65.4	64.1	63.5	63.5	63.5	63.5	63.5
102.5°	84.8	83.8	83.2	82.5	81.9	81.2	80.7	80.3	79.9	79.4	79.0
105°	108.9	108.3	107.7	107.1	106.5	105.9	105.4	104.8	104.3	103.8	103.3
107.5°	134.8	134.5	134.1	133.6	133.1	132.7	132.2	131.7	131.2	130.7	130.2
110°	152.6	152.3	152.0	151.7	151.4	151.1	150.7	150.2	149.7	149.2	148.7



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	170.6	170.4	170.0	169.7	169.3	168.9	168.6	168.3	168.0	167.8	167.5
115°	198.0	198.1	197.9	197.7	197.5	197.3	197.0	196.6	196.2	195.7	195.3
117.5°	225.0	224.9	224.7	224.5	224.4	224.2	224.0	223.8	223.6	223.4	223.3
120°	243.4	243.4	243.3	243.2	243.1	243.0	242.7	242.2	241.7	241.2	240.7
122.5°	261.4	261.5	261.3	261.0	260.7	260.5	260.2	260.1	259.9	259.7	259.5
125°	288.1	288.3	288.2	288.1	288.0	287.9	287.5	286.9	286.3	285.7	285.1
127.5°	314.3	314.4	314.2	314.1	314.0	313.9	313.7	313.3	313.0	312.6	312.3
130°	331.7	331.8	331.6	331.4	331.2	331.0	330.6	330.1	329.6	329.1	328.6
132.5°	348.3	348.4	348.5	348.5	348.6	348.6	348.2	347.4	346.6	345.7	344.9
135°	373.9	373.9	373.8	373.7	373.6	373.5	373.2	372.6	372.0	371.4	370.7
137.5°	398.8	398.7	398.4	398.2	398.0	397.8	397.4	396.8	396.2	395.6	395.0
140°	414.5	414.3	414.0	413.7	413.4	413.1	412.6	412.1	411.6	411.1	410.6
142.5°	430.0	429.9	429.5	429.1	428.7	428.3	427.9	427.5	427.1	426.6	426.2
145°	452.3	452.3	452.0	451.7	451.4	451.1	450.8	450.4	450.0	449.6	449.2
147.5°	472.7	472.5	472.2	472.0	471.7	471.5	471.3	471.0	470.8	470.6	470.4
150°	485.9	485.9	485.5	485.1	484.7	484.3	484.1	484.2	484.3	484.4	484.5
152.5°	497.7	497.5	497.3	497.2	497.0	496.8	496.7	496.5	496.4	496.3	496.1
155°	514.8	514.4	514.3	514.2	514.1	514.0	514.0	514.0	514.0	514.0	514.0
157.5°	529.8	529.4	529.3	529.2	529.1	529.0	529.0	529.3	529.5	529.7	529.9
160°	538.9	538.4	538.3	538.2	538.1	538.0	538.1	538.4	538.7	539.1	539.4
162.5°	547.3	546.8	546.8	546.7	546.7	546.7	546.8	547.0	547.3	547.5	547.7
165°	558.8	558.4	558.3	558.2	558.1	558.0	558.0	558.2	558.4	558.6	558.8
167.5°	567.1	566.5	566.5	566.5	566.5	566.5	566.7	567.1	567.5	567.9	568.3
170°	572.1	571.5	571.5	571.5	571.5	571.5	571.7	572.1	572.5	572.9	573.3
172.5°	575.8	575.2	575.2	575.2	575.2	575.2	575.4	575.8	576.2	576.6	577.0
175°	579.8	579.2	579.2	579.2	579.2	579.2	579.4	579.8	580.2	580.6	581.1
177.5°	581.8	581.3	581.4	581.5	581.6	581.6	581.8	582.2	582.5	582.8	583.1
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	565.6	567.3	569.7	572.5	574.7	577.1	578.4	578.4	579.5	581.9	585.1
5°	567.3	573.3	579.0	586.4	592.2	598.9	604.0	608.9	613.2	618.8	624.6
7.5°	566.8	576.8	587.2	598.8	611.7	621.9	632.4	640.6	648.7	659.4	667.7
10°	565.0	577.9	592.0	606.8	623.0	637.0	649.8	661.3	672.4	684.0	694.4
12.5°	561.6	578.1	595.3	613.1	633.5	649.6	666.0	678.3	691.3	703.9	716.7
15°	556.6	576.0	596.8	621.6	646.5	664.5	680.7	696.7	708.7	723.0	735.3
17.5°	546.3	571.3	597.5	624.5	648.5	669.4	686.4	701.6	714.4	730.1	746.8
20°	540.2	567.3	594.5	623.4	646.3	667.8	684.2	699.9	715.8	736.4	756.7
22.5°	531.7	560.6	589.5	616.9	641.1	661.9	678.8	698.0	719.0	742.3	766.9
25°	518.3	548.1	576.7	602.8	626.4	647.7	670.8	696.7	722.1	752.8	788.2
27.5°	501.2	530.0	555.5	583.1	606.5	633.6	662.4	690.5	727.1	769.4	813.5
30°	488.5	515.7	540.0	566.1	592.7	622.5	654.8	687.9	731.6	781.2	833.7
32.5°	473.7	498.4	522.4	547.6	578.3	611.0	645.4	685.8	738.0	794.5	848.8
35°	448.0	470.2	493.6	521.5	554.1	589.7	633.6	682.8	745.9	806.6	855.4
37.5°	421.1	438.7	462.1	491.6	527.1	568.2	618.1	677.9	742.6	797.2	817.9
40°	400.4	416.8	441.6	472.5	507.7	552.7	608.6	670.1	735.3	773.1	771.5
42.5°	379.9	396.5	420.3	451.5	488.1	538.5	596.1	659.9	714.9	729.3	699.3
45°	348.4	363.9	387.3	418.7	458.0	510.9	571.4	632.7	667.8	644.4	584.8
47.5°	316.4	331.4	353.1	383.8	426.7	482.1	539.4	589.6	594.5	544.4	472.9
50°	295.3	309.4	330.0	362.8	404.4	458.4	513.7	553.2	540.9	479.7	406.0
52.5°	274.8	288.3	307.6	338.6	381.1	434.0	483.3	514.4	486.0	420.9	354.6
55°	244.5	257.4	276.8	305.2	343.8	392.3	435.6	446.9	405.3	339.7	286.1
57.5°	215.7	225.2	244.3	269.5	306.7	349.5	380.4	378.4	332.5	273.4	234.9
60°	196.6	205.2	223.4	246.5	281.9	320.3	342.0	332.7	286.3	237.5	200.6
62.5°	178.9	186.9	202.2	223.4	253.8	287.2	303.0	290.2	246.4	203.5	174.1
65°	152.0	157.8	170.1	189.7	213.5	236.6	250.7	232.0	193.2	160.8	138.6
67.5°	126.9	131.9	142.8	156.9	173.3	189.3	195.0	177.5	147.3	125.5	109.8
70°	110.7	115.3	122.7	135.9	146.7	158.0	160.8	145.1	119.9	103.3	93.6
72.5°	95.2	99.4	105.9	115.2	122.7	129.2	130.5	115.9	96.6	85.2	77.7
75°	72.6	76.3	80.4	83.9	88.7	89.9	89.4	78.1	67.7	60.1	55.9
77.5°	53.3	54.9	57.4	58.8	59.0	58.9	56.6	49.4	44.0	40.9	39.2
80°	41.1	42.3	43.0	43.4	43.7	41.4	38.8	34.4	32.6	30.7	28.7
82.5°	29.9	30.6	31.3	31.4	30.2	28.2	25.9	23.7	22.4	21.5	20.7
85°	16.2	16.4	16.2	15.0	13.4	12.7	12.2	11.8	11.6	11.3	11.3
87.5°	6.0	5.6	4.8	5.2	5.3	5.3	5.4	5.4	5.3	5.4	5.5
90°	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.3	7.8	8.3
92.5°	11.5	12.1	12.7	13.2	13.9	14.8	15.7	16.5	17.4	18.1	18.7
95°	29.7	29.9	30.1	30.3	30.9	31.9	32.9	33.9	34.9	35.6	36.3
97.5°	49.0	49.1	49.2	49.3	50.0	51.4	52.8	54.2	55.6	56.2	56.9
100°	63.5	63.5	63.5	63.5	64.1	65.4	66.7	68.0	69.3	70.3	71.2
102.5°	79.4	79.9	80.3	80.7	81.2	81.9	82.5	83.2	83.8	84.8	85.8
105°	103.8	104.3	104.8	105.4	105.9	106.5	107.1	107.7	108.3	108.9	109.5
107.5°	130.7	131.2	131.7	132.2	132.7	133.1	133.6	134.1	134.5	134.8	135.1
110°	149.2	149.7	150.2	150.7	151.1	151.4	151.7	152.0	152.3	152.6	152.9



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	167.8	168.0	168.3	168.6	168.9	169.3	169.7	170.0	170.4	170.6	170.7
115°	195.7	196.2	196.6	197.0	197.3	197.5	197.7	197.9	198.1	198.0	197.9
117.5°	223.4	223.6	223.8	224.0	224.2	224.4	224.5	224.7	224.9	225.0	225.1
120°	241.2	241.7	242.2	242.7	243.0	243.1	243.2	243.3	243.4	243.4	243.4
122.5°	259.7	259.9	260.1	260.2	260.5	260.7	261.0	261.3	261.5	261.4	261.4
125°	285.7	286.3	286.9	287.5	287.9	288.0	288.1	288.2	288.3	288.1	287.9
127.5°	312.6	313.0	313.3	313.7	313.9	314.0	314.1	314.2	314.4	314.3	314.2
130°	329.1	329.6	330.1	330.6	331.0	331.2	331.4	331.6	331.8	331.7	331.6
132.5°	345.7	346.6	347.4	348.2	348.6	348.6	348.5	348.5	348.4	348.3	348.2
135°	371.4	372.0	372.6	373.2	373.5	373.6	373.7	373.8	373.9	373.9	373.9
137.5°	395.6	396.2	396.8	397.4	397.8	398.0	398.2	398.4	398.7	398.8	398.9
140°	411.1	411.6	412.1	412.6	413.1	413.4	413.7	414.0	414.3	414.5	414.7
142.5°	426.6	427.1	427.5	427.9	428.3	428.7	429.1	429.5	429.9	430.0	430.1
145°	449.6	450.0	450.4	450.8	451.1	451.4	451.7	452.0	452.3	452.3	452.3
147.5°	470.6	470.8	471.0	471.3	471.5	471.7	472.0	472.2	472.5	472.7	472.9
150°	484.4	484.3	484.2	484.1	484.3	484.7	485.1	485.5	485.9	485.9	485.9
152.5°	496.3	496.4	496.5	496.7	496.8	497.0	497.2	497.3	497.5	497.7	498.0
155°	514.0	514.0	514.0	514.0	514.0	514.1	514.2	514.3	514.4	514.8	515.2
157.5°	529.7	529.5	529.3	529.0	529.0	529.1	529.2	529.3	529.4	529.8	530.2
160°	539.1	538.7	538.4	538.1	538.0	538.1	538.2	538.3	538.4	538.9	539.3
162.5°	547.5	547.3	547.0	546.8	546.7	546.7	546.7	546.8	546.8	547.3	547.8
165°	558.6	558.4	558.2	558.0	558.0	558.1	558.2	558.3	558.4	558.8	559.2
167.5°	567.9	567.5	567.1	566.7	566.5	566.5	566.5	566.5	566.5	567.1	567.7
170°	572.9	572.5	572.1	571.7	571.5	571.5	571.5	571.5	571.5	572.1	572.7
172.5°	576.6	576.2	575.8	575.4	575.2	575.2	575.2	575.2	575.2	575.8	576.4
175°	580.6	580.2	579.8	579.4	579.2	579.2	579.2	579.2	579.2	579.8	580.4
177.5°	582.8	582.5	582.2	581.8	581.6	581.6	581.5	581.4	581.3	581.8	582.3
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	587.5	587.5	590.6	590.4	592.5	591.7	592.1
5°	631.5	635.4	638.9	641.2	644.7	645.6	645.1
7.5°	677.2	685.9	690.1	696.0	697.0	700.1	699.8
10°	705.4	714.0	720.5	725.5	728.1	731.3	731.6
12.5°	727.6	734.9	740.6	745.3	748.4	749.4	750.0
15°	745.0	753.0	759.7	766.4	770.4	773.4	775.0
17.5°	762.4	774.9	786.7	795.8	801.3	805.9	805.9
20°	775.9	790.2	805.0	815.4	826.1	830.7	831.4
22.5°	790.3	812.2	831.3	847.4	861.4	866.2	868.0
25°	820.3	848.9	878.3	900.9	917.1	926.6	928.0
27.5°	856.5	895.2	926.1	947.0	960.4	967.5	969.0
30°	882.0	917.8	945.5	961.2	967.5	968.4	964.9
32.5°	893.4	920.2	931.3	930.4	918.1	910.0	906.9
35°	879.4	873.9	846.9	814.5	789.8	774.1	769.9
37.5°	800.3	752.5	702.8	653.9	627.9	614.6	591.9
40°	722.3	654.1	602.4	561.3	531.9	508.3	502.8
42.5°	634.3	563.9	512.2	477.0	453.5	437.4	430.3
45°	509.7	449.2	406.4	379.4	361.4	349.6	344.3
47.5°	407.7	360.8	329.7	309.7	295.9	285.7	282.8
50°	351.7	314.2	287.9	271.0	260.6	252.8	249.6
52.5°	305.5	275.2	255.0	241.1	231.3	226.4	223.7
55°	252.1	226.0	211.4	200.3	194.8	190.9	189.0
57.5°	206.2	187.3	176.7	169.0	163.9	161.4	160.5
60°	180.5	165.7	156.0	150.0	146.5	143.3	142.3
62.5°	157.7	146.1	138.6	133.3	129.9	128.5	127.9
65°	127.1	119.5	113.9	110.7	107.9	107.4	107.2
67.5°	101.0	96.5	93.6	90.3	89.3	87.7	87.3
70°	86.4	83.4	79.9	78.8	77.6	76.0	76.3
72.5°	73.3	70.3	67.9	66.4	66.0	65.3	65.9
75°	53.6	52.7	51.8	50.6	50.1	50.1	49.9
77.5°	38.3	37.5	36.5	35.8	35.6	34.7	35.0
80°	27.7	26.6	26.1	26.3	25.6	25.4	25.4
82.5°	20.5	20.1	19.6	19.7	19.5	19.3	19.5
85°	11.3	11.1	11.1	10.9	10.9	10.6	10.6
87.5°	5.8	6.1	5.8	5.7	5.8	6.0	6.2
90°	8.8	9.3	9.7	10.0	10.3	10.6	10.9
92.5°	19.4	20.1	20.5	20.7	20.9	21.2	21.4
95°	37.0	37.7	38.2	38.4	38.6	38.8	39.0
97.5°	57.6	58.2	58.6	58.7	58.9	59.0	59.1
100°	72.1	73.0	73.5	73.7	73.9	74.1	74.3
102.5°	86.8	87.8	88.4	88.7	89.0	89.3	89.6
105°	110.1	110.7	111.2	111.5	111.8	112.1	112.4
107.5°	135.4	135.7	135.9	135.9	135.8	135.8	135.8
110°	153.2	153.5	153.6	153.5	153.4	153.3	153.2



TEST NUMBER: P333641

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	170.8	171.0	171.0	170.8	170.6	170.4	170.2
115°	197.8	197.7	197.6	197.5	197.4	197.3	197.2
117.5°	225.1	225.2	225.1	224.7	224.3	223.8	223.4
120°	243.4	243.4	243.2	242.8	242.4	242.0	241.6
122.5°	261.3	261.2	261.0	260.7	260.4	260.0	259.7
125°	287.7	287.5	287.3	287.2	287.1	287.0	286.9
127.5°	314.1	314.0	313.8	313.6	313.4	313.2	313.0
130°	331.5	331.4	331.2	331.0	330.8	330.6	330.4
132.5°	348.1	348.0	347.9	347.6	347.3	347.0	346.7
135°	373.9	373.9	373.7	373.3	372.9	372.5	372.1
137.5°	399.0	399.2	399.0	398.5	398.0	397.4	396.9
140°	414.9	415.1	414.9	414.4	413.9	413.4	412.9
142.5°	430.2	430.3	430.1	429.6	429.1	428.6	428.1
145°	452.3	452.3	452.2	451.9	451.6	451.3	451.0
147.5°	473.2	473.4	473.2	472.5	471.8	471.1	470.5
150°	485.9	485.9	485.8	485.6	485.4	485.2	485.0
152.5°	498.2	498.4	498.4	498.0	497.7	497.3	496.9
155°	515.6	516.0	516.0	515.5	515.0	514.5	514.0
157.5°	530.6	531.0	530.9	530.2	529.5	528.9	528.2
160°	539.7	540.1	540.0	539.5	539.0	538.5	538.0
162.5°	548.2	548.7	548.7	548.1	547.5	546.9	546.3
165°	559.6	560.0	559.9	559.3	558.7	558.1	557.5
167.5°	568.3	568.9	568.9	568.2	567.6	567.0	566.4
170°	573.3	574.0	573.9	573.2	572.5	571.8	571.1
172.5°	577.0	577.6	577.6	576.9	576.3	575.7	575.1
175°	581.1	581.7	581.6	580.9	580.2	579.5	578.8
177.5°	582.8	583.3	583.2	582.7	582.1	581.5	581.0
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4

(END OF REPORT)