

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333661

Luminaire Tested: **S125RDIW-S610D470U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333661
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D470U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4024.0 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	96	93	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38
4	77	66	59	53	72	63	56	50	55	50	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28
6	65	53	45	40	61	50	43	38	45	39	34	39	35	31	34	31	28	25
7	61	48	40	35	57	46	39	33	41	35	30	36	31	28	31	28	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5977	5977	5977	5977
5°	6876	5984	5285	5984
10°	7887	5954	4663	5954
15°	8519	5893	4145	5893
20°	9394	5822	3827	5822
25°	10871	5728	3552	5728
30°	11830	5629	3371	5629
35°	9979	5513	3205	5513
40°	6969	5306	3062	5306
45°	5170	5027	2922	5027
50°	4122	4736	2801	4736
55°	3498	4376	2694	4376
60°	3023	4053	2523	4053
65°	2694	3704	2172	3704
70°	2368	3393	1979	3393
75°	2049	2939	1859	2939
80°	1555	2473	1555	2473
85°	1297	1941	1467	1941



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	2.2
10°-20°	260.1	6.5
20°-30°	412.3	10.2
30°-40°	497.2	12.4
40°-50°	444.0	11.0
50°-60°	340.5	8.5
60°-70°	221.3	5.5
70°-80°	107.6	2.7
80°-90°	27.0	0.7
90°-100°	39.0	1.0
100°-110°	115.2	2.9
110°-120°	195.1	4.8
120°-130°	256.8	6.4
130°-140°	287.7	7.2
140°-150°	282.0	7.0
150°-160°	236.9	5.9
160°-170°	157.4	3.9
170°-180°	55.1	1.4
0°-30°	761.1	18.9
0°-40°	1258.3	31.3
0°-60°	2042.9	50.8
0°-90°	2398.7	59.6
90°-120°	349.3	8.7
90°-150°	1175.8	29.2
90°-180°	1625.0	40.4
0°-180°	4024.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1061	923	815	923	1061	106
15°	1274	881	620	881	1274	365
25°	1526	804	498	804	1526	700
35°	1266	699	406	699	1266	765
45°	566	550	320	550	566	452
55°	311	389	239	389	311	282
65°	176	242	142	242	176	175
75°	82	118	74	118	82	87
85°	18	26	20	26	18	20
90°	11	0	11	0	11	7
95°	39	30	39	30	39	40
105°	112	103	112	103	112	119
115°	197	195	197	195	197	195
125°	287	285	287	285	287	256
135°	372	371	372	371	372	287
145°	451	449	451	449	451	282
155°	514	514	514	514	514	237
165°	558	559	558	559	558	157
175°	579	581	579	581	579	55
180°	582	582	582	582	582	



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	973.4	972.8	974.0	970.6	971.0	965.8	965.8	961.8	956.7	952.7	950.9
5°	1060.6	1061.4	1059.8	1054.1	1050.3	1044.6	1038.2	1026.8	1017.3	1008.2	1001.0
7.5°	1150.4	1150.9	1145.9	1144.2	1134.6	1127.6	1113.3	1097.8	1084.0	1066.5	1053.2
10°	1202.7	1202.3	1197.0	1192.8	1184.4	1173.8	1159.7	1141.5	1124.4	1105.4	1087.2
12.5°	1233.1	1232.1	1230.4	1225.3	1217.6	1208.1	1196.2	1178.3	1157.2	1136.4	1115.2
15°	1274.1	1271.4	1266.5	1260.0	1249.0	1238.0	1224.7	1208.8	1188.6	1165.1	1145.3
17.5°	1324.8	1324.9	1317.3	1308.4	1293.4	1273.9	1253.4	1227.7	1200.3	1174.4	1153.4
20°	1366.8	1365.6	1358.0	1340.6	1323.5	1299.2	1275.6	1244.1	1210.7	1176.8	1150.6
22.5°	1426.9	1424.0	1416.1	1393.1	1366.6	1335.3	1299.3	1260.8	1220.4	1182.0	1147.6
25°	1525.6	1523.3	1507.7	1481.1	1443.9	1395.6	1348.5	1295.7	1237.6	1187.1	1145.3
27.5°	1593.0	1590.5	1579.0	1556.9	1522.5	1471.8	1408.0	1337.5	1264.9	1195.4	1135.1
30°	1586.3	1592.0	1590.5	1580.3	1554.4	1508.8	1450.0	1370.6	1284.3	1202.7	1130.9
32.5°	1490.9	1496.0	1509.4	1529.5	1531.0	1512.8	1468.8	1395.5	1306.2	1213.3	1127.5
35°	1265.7	1272.6	1298.4	1339.0	1392.2	1436.7	1445.8	1406.3	1326.1	1226.2	1122.5
37.5°	973.1	1010.5	1032.2	1075.0	1155.3	1237.1	1315.7	1344.7	1310.6	1220.9	1114.4
40°	826.6	835.7	874.5	922.7	990.3	1075.4	1187.5	1268.4	1271.0	1208.8	1101.6
42.5°	707.5	719.0	745.6	784.1	842.0	927.1	1042.8	1149.6	1199.0	1175.3	1084.9
45°	566.0	574.7	594.1	623.7	668.2	738.5	838.0	961.5	1059.5	1097.8	1040.1
47.5°	465.0	469.7	486.5	509.1	542.0	593.2	670.2	777.4	895.0	977.4	969.3
50°	410.3	415.6	428.5	445.6	473.3	516.6	578.2	667.4	788.6	889.3	909.4
52.5°	367.7	372.1	380.2	396.4	419.2	452.5	502.2	583.0	692.0	799.0	845.6
55°	310.7	313.8	320.2	329.3	347.6	371.5	414.4	470.3	558.4	666.3	734.7
57.5°	263.8	265.3	269.4	277.8	290.4	307.9	338.9	386.3	449.5	546.6	622.1
60°	234.0	235.5	240.8	246.5	256.4	272.4	296.7	329.7	390.5	470.7	547.0
62.5°	210.3	211.2	213.5	219.2	227.8	240.2	259.3	286.3	334.6	405.0	477.1
65°	176.3	176.6	177.4	182.0	187.3	196.4	208.9	227.9	264.4	317.6	381.4
67.5°	143.6	144.1	146.8	148.4	153.9	158.7	166.1	180.6	206.3	242.1	291.7
70°	125.4	125.0	127.6	129.5	131.4	137.1	142.1	153.8	169.8	197.2	238.6
72.5°	108.3	107.4	108.5	109.2	111.7	115.6	120.5	127.7	140.0	158.9	190.5
75°	82.1	82.4	82.4	83.2	85.1	86.6	88.1	91.9	98.8	111.3	128.4
77.5°	57.6	57.0	58.6	58.8	59.9	61.6	62.9	64.4	67.2	72.4	81.2
80°	41.8	41.8	42.2	43.3	42.9	43.7	45.6	47.1	50.5	53.6	56.6
82.5°	32.1	31.8	32.1	32.4	32.3	33.0	33.7	34.0	35.3	36.8	39.0
85°	17.5	17.5	17.9	17.9	18.2	18.2	18.6	18.6	18.6	19.0	19.4
87.5°	8.9	8.5	8.1	8.1	8.3	8.8	8.4	8.0	7.9	7.8	8.0
90°	10.9	10.6	10.3	10.0	9.7	9.3	8.8	8.3	7.8	7.3	6.5
92.5°	21.4	21.2	20.9	20.7	20.5	20.1	19.4	18.7	18.1	17.4	16.5
95°	39.0	38.8	38.6	38.4	38.2	37.7	37.0	36.3	35.6	34.9	33.9
97.5°	59.1	59.0	58.9	58.7	58.6	58.2	57.6	56.9	56.2	55.6	54.2
100°	74.3	74.1	73.9	73.7	73.5	73.0	72.1	71.2	70.3	69.3	68.0
102.5°	89.6	89.3	89.0	88.7	88.4	87.8	86.8	85.8	84.8	83.8	83.2
105°	112.4	112.1	111.8	111.5	111.2	110.7	110.1	109.5	108.9	108.3	107.7
107.5°	135.8	135.8	135.8	135.9	135.9	135.7	135.4	135.1	134.8	134.5	134.1
110°	153.2	153.3	153.4	153.5	153.6	153.5	153.2	152.9	152.6	152.3	152.0



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.2	170.4	170.6	170.8	171.0	171.0	170.8	170.7	170.6	170.4	170.0
115°	197.2	197.3	197.4	197.5	197.6	197.7	197.8	197.9	198.0	198.1	197.9
117.5°	223.4	223.8	224.3	224.7	225.1	225.2	225.1	225.1	225.0	224.9	224.7
120°	241.6	242.0	242.4	242.8	243.2	243.4	243.4	243.4	243.4	243.4	243.3
122.5°	259.7	260.0	260.4	260.7	261.0	261.2	261.3	261.4	261.4	261.5	261.3
125°	286.9	287.0	287.1	287.2	287.3	287.5	287.7	287.9	288.1	288.3	288.2
127.5°	313.0	313.2	313.4	313.6	313.8	314.0	314.1	314.2	314.3	314.4	314.2
130°	330.4	330.6	330.8	331.0	331.2	331.4	331.5	331.6	331.7	331.8	331.6
132.5°	346.7	347.0	347.3	347.6	347.9	348.0	348.1	348.2	348.3	348.4	348.5
135°	372.1	372.5	372.9	373.3	373.7	373.9	373.9	373.9	373.9	373.9	373.8
137.5°	396.9	397.4	398.0	398.5	399.0	399.2	399.0	398.9	398.8	398.7	398.4
140°	412.9	413.4	413.9	414.4	414.9	415.1	414.9	414.7	414.5	414.3	414.0
142.5°	428.1	428.6	429.1	429.6	430.1	430.3	430.2	430.1	430.0	429.9	429.5
145°	451.0	451.3	451.6	451.9	452.2	452.3	452.3	452.3	452.3	452.3	452.0
147.5°	470.5	471.1	471.8	472.5	473.2	473.4	473.2	472.9	472.7	472.5	472.2
150°	485.0	485.2	485.4	485.6	485.8	485.9	485.9	485.9	485.9	485.9	485.5
152.5°	496.9	497.3	497.7	498.0	498.4	498.4	498.2	498.0	497.7	497.5	497.3
155°	514.0	514.5	515.0	515.5	516.0	516.0	515.6	515.2	514.8	514.4	514.3
157.5°	528.2	528.9	529.5	530.2	530.9	531.0	530.6	530.2	529.8	529.4	529.3
160°	538.0	538.5	539.0	539.5	540.0	540.1	539.7	539.3	538.9	538.4	538.3
162.5°	546.3	546.9	547.5	548.1	548.7	548.7	548.2	547.8	547.3	546.8	546.8
165°	557.5	558.1	558.7	559.3	559.9	560.0	559.6	559.2	558.8	558.4	558.3
167.5°	566.4	567.0	567.6	568.2	568.9	568.9	568.3	567.7	567.1	566.5	566.5
170°	571.1	571.8	572.5	573.2	573.9	574.0	573.3	572.7	572.1	571.5	571.5
172.5°	575.1	575.7	576.3	576.9	577.6	577.6	577.0	576.4	575.8	575.2	575.2
175°	578.8	579.5	580.2	580.9	581.6	581.7	581.1	580.4	579.8	579.2	579.2
177.5°	581.0	581.5	582.1	582.7	583.2	583.3	582.8	582.3	581.8	581.3	581.4
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	950.9	948.8	944.8	941.2	936.6	932.7	929.9	926.6	922.3	917.2	912.9
5°	993.0	984.6	973.6	964.1	952.0	942.5	932.6	923.1	913.6	901.4	890.8
7.5°	1039.6	1022.4	1005.6	984.5	965.3	948.2	931.8	915.2	898.9	881.7	865.0
10°	1068.2	1047.3	1024.1	997.5	973.2	950.1	928.8	907.9	885.9	866.5	845.6
12.5°	1094.9	1068.0	1041.5	1007.9	978.7	950.4	923.3	897.3	873.7	848.6	826.1
15°	1119.1	1092.5	1062.9	1021.9	981.2	947.0	915.1	881.3	852.1	823.9	798.9
17.5°	1128.4	1100.6	1066.1	1026.7	982.3	939.3	898.2	861.1	826.7	793.9	765.7
20°	1124.8	1097.8	1062.5	1024.9	977.4	932.6	888.1	847.1	808.7	774.2	744.2
22.5°	1116.0	1088.1	1054.0	1014.3	969.2	921.6	874.2	830.4	790.2	754.4	721.7
25°	1102.8	1064.8	1029.8	991.1	948.2	901.1	852.1	803.8	760.9	724.4	688.7
27.5°	1089.0	1041.6	997.2	958.6	913.3	871.3	824.0	774.6	729.4	692.3	655.7
30°	1076.6	1023.4	974.4	930.7	887.8	847.9	803.0	754.8	708.5	670.1	632.9
32.5°	1061.1	1004.5	950.7	900.3	858.9	819.3	778.7	732.6	687.5	647.9	610.1
35°	1041.6	969.4	910.9	857.4	811.4	773.0	736.6	699.3	654.1	613.1	576.3
37.5°	1016.1	934.2	866.5	808.1	759.7	721.1	692.4	658.3	617.1	577.8	543.6
40°	1000.6	908.7	834.6	776.8	725.9	685.3	658.3	629.4	591.8	555.0	520.8
42.5°	979.9	885.3	802.4	742.2	691.0	651.9	624.6	599.4	567.8	533.1	496.5
45°	939.4	839.9	752.9	688.3	636.7	598.3	572.8	550.4	526.5	494.6	462.7
47.5°	886.7	792.6	701.5	631.0	580.4	544.8	520.1	502.4	485.3	458.2	427.2
50°	844.5	753.7	664.8	596.4	542.5	508.6	485.5	471.4	455.8	431.2	405.3
52.5°	794.6	713.6	626.5	556.6	505.7	474.0	451.7	437.7	424.8	404.7	380.1
55°	716.1	645.0	565.2	501.8	455.1	423.2	401.9	388.6	381.0	363.9	344.5
57.5°	625.4	574.5	504.2	443.0	401.7	370.1	354.6	343.3	334.7	322.6	308.9
60°	562.2	526.5	463.4	405.3	367.3	337.3	323.3	313.8	305.8	295.5	284.9
62.5°	498.1	472.1	417.3	367.3	332.4	307.2	294.1	285.5	276.3	269.4	259.1
65°	412.2	389.0	351.0	311.9	279.6	259.5	250.0	242.4	236.7	229.1	221.8
67.5°	320.6	311.2	285.0	258.0	234.8	216.9	208.7	203.4	196.5	192.0	187.0
70°	264.4	259.8	241.2	223.4	201.7	189.6	182.0	179.7	171.3	166.8	163.3
72.5°	214.6	212.4	201.7	189.3	174.1	163.4	156.4	153.8	148.5	144.9	142.7
75°	147.0	147.8	145.9	137.9	132.2	125.4	119.3	117.8	114.0	110.9	109.0
77.5°	93.0	96.9	97.0	96.6	94.4	90.2	87.7	86.5	82.8	81.7	81.2
80°	63.8	68.0	71.8	71.4	70.7	69.5	67.6	66.5	64.6	63.4	62.7
82.5°	42.5	46.4	49.6	51.7	51.5	50.4	49.1	48.5	48.2	47.3	47.2
85°	20.1	20.9	22.0	24.7	26.6	27.0	26.6	26.2	25.1	25.5	25.8
87.5°	8.2	8.0	8.2	8.0	7.6	8.9	9.7	9.8	9.4	8.9	8.5
90°	5.8	5.1	4.4	3.7	2.9	2.1	1.3	0.5	1.3	2.1	2.9
92.5°	15.7	14.8	13.9	13.2	12.7	12.1	11.5	11.0	11.5	12.1	12.7
95°	32.9	31.9	30.9	30.3	30.1	29.9	29.7	29.5	29.7	29.9	30.1
97.5°	52.8	51.4	50.0	49.3	49.2	49.1	49.0	48.9	49.0	49.1	49.2
100°	66.7	65.4	64.1	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5
102.5°	82.5	81.9	81.2	80.7	80.3	79.9	79.4	79.0	79.4	79.9	80.3
105°	107.1	106.5	105.9	105.4	104.8	104.3	103.8	103.3	103.8	104.3	104.8
107.5°	133.6	133.1	132.7	132.2	131.7	131.2	130.7	130.2	130.7	131.2	131.7
110°	151.7	151.4	151.1	150.7	150.2	149.7	149.2	148.7	149.2	149.7	150.2



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	169.7	169.3	168.9	168.6	168.3	168.0	167.8	167.5	167.8	168.0	168.3
115°	197.7	197.5	197.3	197.0	196.6	196.2	195.7	195.3	195.7	196.2	196.6
117.5°	224.5	224.4	224.2	224.0	223.8	223.6	223.4	223.3	223.4	223.6	223.8
120°	243.2	243.1	243.0	242.7	242.2	241.7	241.2	240.7	241.2	241.7	242.2
122.5°	261.0	260.7	260.5	260.2	260.1	259.9	259.7	259.5	259.7	259.9	260.1
125°	288.1	288.0	287.9	287.5	286.9	286.3	285.7	285.1	285.7	286.3	286.9
127.5°	314.1	314.0	313.9	313.7	313.3	313.0	312.6	312.3	312.6	313.0	313.3
130°	331.4	331.2	331.0	330.6	330.1	329.6	329.1	328.6	329.1	329.6	330.1
132.5°	348.5	348.6	348.6	348.2	347.4	346.6	345.7	344.9	345.7	346.6	347.4
135°	373.7	373.6	373.5	373.2	372.6	372.0	371.4	370.7	371.4	372.0	372.6
137.5°	398.2	398.0	397.8	397.4	396.8	396.2	395.6	395.0	395.6	396.2	396.8
140°	413.7	413.4	413.1	412.6	412.1	411.6	411.1	410.6	411.1	411.6	412.1
142.5°	429.1	428.7	428.3	427.9	427.5	427.1	426.6	426.2	426.6	427.1	427.5
145°	451.7	451.4	451.1	450.8	450.4	450.0	449.6	449.2	449.6	450.0	450.4
147.5°	472.0	471.7	471.5	471.3	471.0	470.8	470.6	470.4	470.6	470.8	471.0
150°	485.1	484.7	484.3	484.1	484.2	484.3	484.4	484.5	484.4	484.3	484.2
152.5°	497.2	497.0	496.8	496.7	496.5	496.4	496.3	496.1	496.3	496.4	496.5
155°	514.2	514.1	514.0	514.0	514.0	514.0	514.0	514.0	514.0	514.0	514.0
157.5°	529.2	529.1	529.0	529.0	529.3	529.5	529.7	529.9	529.7	529.5	529.3
160°	538.2	538.1	538.0	538.1	538.4	538.7	539.1	539.4	539.1	538.7	538.4
162.5°	546.7	546.7	546.7	546.8	547.0	547.3	547.5	547.7	547.5	547.3	547.0
165°	558.2	558.1	558.0	558.0	558.2	558.4	558.6	558.8	558.6	558.4	558.2
167.5°	566.5	566.5	566.5	566.7	567.1	567.5	567.9	568.3	567.9	567.5	567.1
170°	571.5	571.5	571.5	571.7	572.1	572.5	572.9	573.3	572.9	572.5	572.1
172.5°	575.2	575.2	575.2	575.4	575.8	576.2	576.6	577.0	576.6	576.2	575.8
175°	579.2	579.2	579.2	579.4	579.8	580.2	580.6	581.1	580.6	580.2	579.8
177.5°	581.5	581.6	581.6	581.8	582.2	582.5	582.8	583.1	582.8	582.5	582.2
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	909.9	905.6	902.6	896.5	892.2	890.4	887.1	886.2	889.5	887.1	886.8
5°	882.8	871.8	863.1	854.3	844.8	838.8	829.6	828.1	825.8	822.4	821.7
7.5°	850.4	836.0	824.8	810.3	797.8	787.7	776.3	770.9	767.9	763.5	757.6
10°	828.5	811.4	796.2	781.8	766.2	753.7	742.3	733.5	727.8	722.5	720.2
12.5°	806.9	789.5	770.1	752.6	735.2	721.1	708.5	702.8	696.5	690.3	685.0
15°	773.4	750.2	729.0	708.8	694.0	678.8	666.7	658.3	648.8	646.2	635.9
17.5°	737.9	715.1	690.2	669.0	651.9	635.1	621.8	612.3	605.1	595.3	590.6
20°	715.7	688.7	664.4	645.0	626.0	606.3	592.6	584.6	577.8	569.8	566.0
22.5°	692.0	665.6	640.7	618.0	598.7	579.2	569.5	561.2	553.5	546.1	541.1
25°	657.2	630.6	604.4	580.8	560.7	546.6	535.2	525.7	521.6	514.3	509.0
27.5°	622.8	594.5	567.3	543.8	528.0	514.1	504.8	497.3	489.7	483.4	478.8
30°	600.6	571.7	542.1	523.5	506.7	493.5	483.2	476.0	470.3	464.6	461.2
32.5°	578.4	548.6	522.3	502.2	486.4	474.9	464.4	457.4	451.4	445.1	441.1
35°	542.8	512.4	491.2	471.4	455.8	445.2	438.0	428.1	423.2	418.6	414.4
37.5°	509.8	481.5	458.5	441.2	427.7	417.1	407.8	402.4	396.4	392.3	388.8
40°	485.5	459.6	438.8	420.5	410.6	398.9	390.1	383.3	378.7	373.4	369.6
42.5°	463.6	439.6	419.3	402.9	390.6	380.6	372.2	365.4	359.6	355.8	352.6
45°	432.7	408.7	389.0	373.8	362.4	352.9	344.2	340.7	333.1	328.6	327.1
47.5°	400.7	379.3	360.2	346.2	334.5	325.5	317.3	310.4	306.2	301.7	299.3
50°	379.1	358.6	340.7	327.1	315.7	305.8	298.2	293.6	287.9	283.8	280.7
52.5°	357.5	338.5	320.7	307.6	297.7	287.9	279.4	274.8	269.4	266.7	264.6
55°	326.7	306.6	291.4	278.4	268.2	259.1	251.1	246.5	243.1	240.5	239.7
57.5°	291.7	275.8	261.7	250.0	239.4	230.8	223.8	219.5	216.5	216.1	213.8
60°	268.9	254.5	241.6	229.1	219.9	212.0	205.9	201.0	197.9	197.5	196.8
62.5°	246.2	232.3	220.3	209.3	201.1	193.4	187.7	182.1	180.3	178.4	176.7
65°	212.3	199.8	189.9	181.2	172.5	166.0	160.3	156.9	152.7	150.4	146.3
67.5°	179.1	169.4	159.9	152.6	145.7	139.6	134.9	129.8	127.0	125.1	122.1
70°	157.3	149.7	140.2	132.2	126.9	121.9	118.1	112.4	110.5	109.0	107.5
72.5°	136.6	129.9	121.9	115.5	110.2	105.5	101.1	98.5	96.6	95.0	94.1
75°	107.5	101.0	94.2	89.6	85.9	82.1	79.8	77.9	77.1	76.7	75.2
77.5°	78.9	75.5	70.0	66.4	63.9	62.4	60.3	59.3	59.3	57.6	57.1
80°	60.4	58.5	53.9	52.4	50.5	49.0	47.9	46.0	44.1	43.3	42.2
82.5°	44.9	43.0	41.2	38.7	37.2	36.2	35.1	34.4	34.6	33.6	33.0
85°	23.9	22.0	21.3	20.9	20.1	20.9	20.5	20.1	19.8	19.4	19.8
87.5°	8.3	8.5	8.3	9.1	8.3	8.7	8.8	8.6	8.7	8.8	8.6
90°	3.7	4.4	5.1	5.8	6.5	7.3	7.8	8.3	8.8	9.3	9.7
92.5°	13.2	13.9	14.8	15.7	16.5	17.4	18.1	18.7	19.4	20.1	20.5
95°	30.3	30.9	31.9	32.9	33.9	34.9	35.6	36.3	37.0	37.7	38.2
97.5°	49.3	50.0	51.4	52.8	54.2	55.6	56.2	56.9	57.6	58.2	58.6
100°	63.5	64.1	65.4	66.7	68.0	69.3	70.3	71.2	72.1	73.0	73.5
102.5°	80.7	81.2	81.9	82.5	83.2	83.8	84.8	85.8	86.8	87.8	88.4
105°	105.4	105.9	106.5	107.1	107.7	108.3	108.9	109.5	110.1	110.7	111.2
107.5°	132.2	132.7	133.1	133.6	134.1	134.5	134.8	135.1	135.4	135.7	135.9
110°	150.7	151.1	151.4	151.7	152.0	152.3	152.6	152.9	153.2	153.5	153.6



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.6	168.9	169.3	169.7	170.0	170.4	170.6	170.7	170.8	171.0	171.0
115°	197.0	197.3	197.5	197.7	197.9	198.1	198.0	197.9	197.8	197.7	197.6
117.5°	224.0	224.2	224.4	224.5	224.7	224.9	225.0	225.1	225.1	225.2	225.1
120°	242.7	243.0	243.1	243.2	243.3	243.4	243.4	243.4	243.4	243.4	243.2
122.5°	260.2	260.5	260.7	261.0	261.3	261.5	261.4	261.4	261.3	261.2	261.0
125°	287.5	287.9	288.0	288.1	288.2	288.3	288.1	287.9	287.7	287.5	287.3
127.5°	313.7	313.9	314.0	314.1	314.2	314.4	314.3	314.2	314.1	314.0	313.8
130°	330.6	331.0	331.2	331.4	331.6	331.8	331.7	331.6	331.5	331.4	331.2
132.5°	348.2	348.6	348.6	348.5	348.5	348.4	348.3	348.2	348.1	348.0	347.9
135°	373.2	373.5	373.6	373.7	373.8	373.9	373.9	373.9	373.9	373.9	373.7
137.5°	397.4	397.8	398.0	398.2	398.4	398.7	398.8	398.9	399.0	399.2	399.0
140°	412.6	413.1	413.4	413.7	414.0	414.3	414.5	414.7	414.9	415.1	414.9
142.5°	427.9	428.3	428.7	429.1	429.5	429.9	430.0	430.1	430.2	430.3	430.1
145°	450.8	451.1	451.4	451.7	452.0	452.3	452.3	452.3	452.3	452.3	452.2
147.5°	471.3	471.5	471.7	472.0	472.2	472.5	472.7	472.9	473.2	473.4	473.2
150°	484.1	484.3	484.7	485.1	485.5	485.9	485.9	485.9	485.9	485.9	485.8
152.5°	496.7	496.8	497.0	497.2	497.3	497.5	497.7	498.0	498.2	498.4	498.4
155°	514.0	514.0	514.1	514.2	514.3	514.4	514.8	515.2	515.6	516.0	516.0
157.5°	529.0	529.0	529.1	529.2	529.3	529.4	529.8	530.2	530.6	531.0	530.9
160°	538.1	538.0	538.1	538.2	538.3	538.4	538.9	539.3	539.7	540.1	540.0
162.5°	546.8	546.7	546.7	546.7	546.8	546.8	547.3	547.8	548.2	548.7	548.7
165°	558.0	558.0	558.1	558.2	558.3	558.4	558.8	559.2	559.6	560.0	559.9
167.5°	566.7	566.5	566.5	566.5	566.5	566.5	567.1	567.7	568.3	568.9	568.9
170°	571.7	571.5	571.5	571.5	571.5	571.5	572.1	572.7	573.3	574.0	573.9
172.5°	575.4	575.2	575.2	575.2	575.2	575.2	575.8	576.4	577.0	577.6	577.6
175°	579.4	579.2	579.2	579.2	579.2	579.2	579.8	580.4	581.1	581.7	581.6
177.5°	581.8	581.6	581.6	581.5	581.4	581.3	581.8	582.3	582.8	583.3	583.2
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	886.5	883.1	882.2	883.4	882.2	883.1	886.5	886.8	887.1	889.5	886.2
5°	817.9	814.1	816.0	815.2	816.0	814.1	817.9	821.7	822.4	825.8	828.1
7.5°	757.5	752.8	747.8	749.4	747.8	752.8	757.5	757.6	763.5	767.9	770.9
10°	715.3	711.5	709.2	711.1	709.2	711.5	715.3	720.2	722.5	727.8	733.5
12.5°	679.7	677.5	675.5	674.7	675.5	677.5	679.7	685.0	690.3	696.5	702.8
15°	631.3	626.8	624.9	620.0	624.9	626.8	631.3	635.9	646.2	648.8	658.3
17.5°	586.7	585.2	580.3	578.2	580.3	585.2	586.7	590.6	595.3	605.1	612.3
20°	560.3	558.8	553.9	556.9	553.9	558.8	560.3	566.0	569.8	577.8	584.6
22.5°	538.4	535.1	533.5	532.6	533.5	535.1	538.4	541.1	546.1	553.5	561.2
25°	507.5	502.6	500.7	498.4	500.7	502.6	507.5	509.0	514.3	521.6	525.7
27.5°	476.7	474.0	471.5	470.9	471.5	474.0	476.7	478.8	483.4	489.7	497.3
30°	456.6	453.9	452.0	452.0	452.0	453.9	456.6	461.2	464.6	470.3	476.0
32.5°	438.7	436.6	434.7	434.4	434.7	436.6	438.7	441.1	445.1	451.4	457.4
35°	412.5	409.5	408.7	406.5	408.7	409.5	412.5	414.4	418.6	423.2	428.1
37.5°	385.4	382.9	382.8	382.6	382.8	382.9	385.4	388.8	392.3	396.4	402.4
40°	368.1	366.2	365.8	363.2	365.8	366.2	368.1	369.6	373.4	378.7	383.3
42.5°	349.6	348.6	347.3	346.1	347.3	348.6	349.6	352.6	355.8	359.6	365.4
45°	324.4	321.8	321.8	319.9	321.8	321.8	324.4	327.1	328.6	333.1	340.7
47.5°	298.4	296.4	296.6	294.6	296.6	296.4	298.4	299.3	301.7	306.2	310.4
50°	281.1	280.0	279.6	278.8	279.6	280.0	281.1	280.7	283.8	287.9	293.6
52.5°	263.8	263.3	264.7	263.0	264.7	263.3	263.8	264.6	266.7	269.4	274.8
55°	240.5	239.3	241.6	239.3	241.6	239.3	240.5	239.7	240.5	243.1	246.5
57.5°	213.6	212.6	214.6	213.5	214.6	212.6	213.6	213.8	216.1	216.5	219.5
60°	196.0	193.7	194.9	195.3	194.9	193.7	196.0	196.8	197.5	197.9	201.0
62.5°	175.0	173.7	174.5	172.8	174.5	173.7	175.0	176.7	178.4	180.3	182.1
65°	145.5	144.4	142.8	142.1	142.8	144.4	145.5	146.3	150.4	152.7	156.9
67.5°	122.2	119.5	119.4	120.0	119.4	119.5	122.2	122.1	125.1	127.0	129.8
70°	105.2	105.2	104.8	104.8	104.8	105.2	105.2	107.5	109.0	110.5	112.4
72.5°	93.4	93.1	92.4	92.1	92.4	93.1	93.4	94.1	95.0	96.6	98.5
75°	75.2	75.6	74.8	74.5	74.8	75.6	75.2	75.2	76.7	77.1	77.9
77.5°	55.5	53.9	54.8	53.9	54.8	53.9	55.5	57.1	57.6	59.3	59.3
80°	42.2	41.8	42.9	41.8	42.9	41.8	42.2	42.2	43.3	44.1	46.0
82.5°	33.4	33.0	33.5	32.7	33.5	33.0	33.4	33.0	33.6	34.6	34.4
85°	20.1	19.8	19.4	19.8	19.4	19.8	20.1	19.8	19.4	19.8	20.1
87.5°	9.0	8.7	8.8	8.9	8.8	8.7	9.0	8.6	8.8	8.7	8.6
90°	10.0	10.3	10.6	10.9	10.6	10.3	10.0	9.7	9.3	8.8	8.3
92.5°	20.7	20.9	21.2	21.4	21.2	20.9	20.7	20.5	20.1	19.4	18.7
95°	38.4	38.6	38.8	39.0	38.8	38.6	38.4	38.2	37.7	37.0	36.3
97.5°	58.7	58.9	59.0	59.1	59.0	58.9	58.7	58.6	58.2	57.6	56.9
100°	73.7	73.9	74.1	74.3	74.1	73.9	73.7	73.5	73.0	72.1	71.2
102.5°	88.7	89.0	89.3	89.6	89.3	89.0	88.7	88.4	87.8	86.8	85.8
105°	111.5	111.8	112.1	112.4	112.1	111.8	111.5	111.2	110.7	110.1	109.5
107.5°	135.9	135.8	135.8	135.8	135.8	135.8	135.9	135.9	135.7	135.4	135.1
110°	153.5	153.4	153.3	153.2	153.3	153.4	153.5	153.6	153.5	153.2	152.9



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	170.8	170.6	170.4	170.2	170.4	170.6	170.8	171.0	171.0	170.8	170.7
115°	197.5	197.4	197.3	197.2	197.3	197.4	197.5	197.6	197.7	197.8	197.9
117.5°	224.7	224.3	223.8	223.4	223.8	224.3	224.7	225.1	225.2	225.1	225.1
120°	242.8	242.4	242.0	241.6	242.0	242.4	242.8	243.2	243.4	243.4	243.4
122.5°	260.7	260.4	260.0	259.7	260.0	260.4	260.7	261.0	261.2	261.3	261.4
125°	287.2	287.1	287.0	286.9	287.0	287.1	287.2	287.3	287.5	287.7	287.9
127.5°	313.6	313.4	313.2	313.0	313.2	313.4	313.6	313.8	314.0	314.1	314.2
130°	331.0	330.8	330.6	330.4	330.6	330.8	331.0	331.2	331.4	331.5	331.6
132.5°	347.6	347.3	347.0	346.7	347.0	347.3	347.6	347.9	348.0	348.1	348.2
135°	373.3	372.9	372.5	372.1	372.5	372.9	373.3	373.7	373.9	373.9	373.9
137.5°	398.5	398.0	397.4	396.9	397.4	398.0	398.5	399.0	399.2	399.0	398.9
140°	414.4	413.9	413.4	412.9	413.4	413.9	414.4	414.9	415.1	414.9	414.7
142.5°	429.6	429.1	428.6	428.1	428.6	429.1	429.6	430.1	430.3	430.2	430.1
145°	451.9	451.6	451.3	451.0	451.3	451.6	451.9	452.2	452.3	452.3	452.3
147.5°	472.5	471.8	471.1	470.5	471.1	471.8	472.5	473.2	473.4	473.2	472.9
150°	485.6	485.4	485.2	485.0	485.2	485.4	485.6	485.8	485.9	485.9	485.9
152.5°	498.0	497.7	497.3	496.9	497.3	497.7	498.0	498.4	498.4	498.2	498.0
155°	515.5	515.0	514.5	514.0	514.5	515.0	515.5	516.0	516.0	515.6	515.2
157.5°	530.2	529.5	528.9	528.2	528.9	529.5	530.2	530.9	531.0	530.6	530.2
160°	539.5	539.0	538.5	538.0	538.5	539.0	539.5	540.0	540.1	539.7	539.3
162.5°	548.1	547.5	546.9	546.3	546.9	547.5	548.1	548.7	548.7	548.2	547.8
165°	559.3	558.7	558.1	557.5	558.1	558.7	559.3	559.9	560.0	559.6	559.2
167.5°	568.2	567.6	567.0	566.4	567.0	567.6	568.2	568.9	568.9	568.3	567.7
170°	573.2	572.5	571.8	571.1	571.8	572.5	573.2	573.9	574.0	573.3	572.7
172.5°	576.9	576.3	575.7	575.1	575.7	576.3	576.9	577.6	577.6	577.0	576.4
175°	580.9	580.2	579.5	578.8	579.5	580.2	580.9	581.6	581.7	581.1	580.4
177.5°	582.7	582.1	581.5	581.0	581.5	582.1	582.7	583.2	583.3	582.8	582.3
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	887.1	890.4	892.2	896.5	902.6	905.6	909.9	912.9	917.2	922.3	926.6
5°	829.6	838.8	844.8	854.3	863.1	871.8	882.8	890.8	901.4	913.6	923.1
7.5°	776.3	787.7	797.8	810.3	824.8	836.0	850.4	865.0	881.7	898.9	915.2
10°	742.3	753.7	766.2	781.8	796.2	811.4	828.5	845.6	866.5	885.9	907.9
12.5°	708.5	721.1	735.2	752.6	770.1	789.5	806.9	826.1	848.6	873.7	897.3
15°	666.7	678.8	694.0	708.8	729.0	750.2	773.4	798.9	823.9	852.1	881.3
17.5°	621.8	635.1	651.9	669.0	690.2	715.1	737.9	765.7	793.9	826.7	861.1
20°	592.6	606.3	626.0	645.0	664.4	688.7	715.7	744.2	774.2	808.7	847.1
22.5°	569.5	579.2	598.7	618.0	640.7	665.6	692.0	721.7	754.4	790.2	830.4
25°	535.2	546.6	560.7	580.8	604.4	630.6	657.2	688.7	724.4	760.9	803.8
27.5°	504.8	514.1	528.0	543.8	567.3	594.5	622.8	655.7	692.3	729.4	774.6
30°	483.2	493.5	506.7	523.5	542.1	571.7	600.6	632.9	670.1	708.5	754.8
32.5°	464.4	474.9	486.4	502.2	522.3	548.6	578.4	610.1	647.9	687.5	732.6
35°	438.0	445.2	455.8	471.4	491.2	512.4	542.8	576.3	613.1	654.1	699.3
37.5°	407.8	417.1	427.7	441.2	458.5	481.5	509.8	543.6	577.8	617.1	658.3
40°	390.1	398.9	410.6	420.5	438.8	459.6	485.5	520.8	555.0	591.8	629.4
42.5°	372.2	380.6	390.6	402.9	419.3	439.6	463.6	496.5	533.1	567.8	599.4
45°	344.2	352.9	362.4	373.8	389.0	408.7	432.7	462.7	494.6	526.5	550.4
47.5°	317.3	325.5	334.5	346.2	360.2	379.3	400.7	427.2	458.2	485.3	502.4
50°	298.2	305.8	315.7	327.1	340.7	358.6	379.1	405.3	431.2	455.8	471.4
52.5°	279.4	287.9	297.7	307.6	320.7	338.5	357.5	380.1	404.7	424.8	437.7
55°	251.1	259.1	268.2	278.4	291.4	306.6	326.7	344.5	363.9	381.0	388.6
57.5°	223.8	230.8	239.4	250.0	261.7	275.8	291.7	308.9	322.6	334.7	343.3
60°	205.9	212.0	219.9	229.1	241.6	254.5	268.9	284.9	295.5	305.8	313.8
62.5°	187.7	193.4	201.1	209.3	220.3	232.3	246.2	259.1	269.4	276.3	285.5
65°	160.3	166.0	172.5	181.2	189.9	199.8	212.3	221.8	229.1	236.7	242.4
67.5°	134.9	139.6	145.7	152.6	159.9	169.4	179.1	187.0	192.0	196.5	203.4
70°	118.1	121.9	126.9	132.2	140.2	149.7	157.3	163.3	166.8	171.3	179.7
72.5°	101.1	105.5	110.2	115.5	121.9	129.9	136.6	142.7	144.9	148.5	153.8
75°	79.8	82.1	85.9	89.6	94.2	101.0	107.5	109.0	110.9	114.0	117.8
77.5°	60.3	62.4	63.9	66.4	70.0	75.5	78.9	81.2	81.7	82.8	86.5
80°	47.9	49.0	50.5	52.4	53.9	58.5	60.4	62.7	63.4	64.6	66.5
82.5°	35.1	36.2	37.2	38.7	41.2	43.0	44.9	47.2	47.3	48.2	48.5
85°	20.5	20.9	20.1	20.9	21.3	22.0	23.9	25.8	25.5	25.1	26.2
87.5°	8.8	8.7	8.3	9.1	8.3	8.5	8.3	8.5	8.9	9.4	9.8
90°	7.8	7.3	6.5	5.8	5.1	4.4	3.7	2.9	2.1	1.3	0.5
92.5°	18.1	17.4	16.5	15.7	14.8	13.9	13.2	12.7	12.1	11.5	11.0
95°	35.6	34.9	33.9	32.9	31.9	30.9	30.3	30.1	29.9	29.7	29.5
97.5°	56.2	55.6	54.2	52.8	51.4	50.0	49.3	49.2	49.1	49.0	48.9
100°	70.3	69.3	68.0	66.7	65.4	64.1	63.5	63.5	63.5	63.5	63.5
102.5°	84.8	83.8	83.2	82.5	81.9	81.2	80.7	80.3	79.9	79.4	79.0
105°	108.9	108.3	107.7	107.1	106.5	105.9	105.4	104.8	104.3	103.8	103.3
107.5°	134.8	134.5	134.1	133.6	133.1	132.7	132.2	131.7	131.2	130.7	130.2
110°	152.6	152.3	152.0	151.7	151.4	151.1	150.7	150.2	149.7	149.2	148.7



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	170.6	170.4	170.0	169.7	169.3	168.9	168.6	168.3	168.0	167.8	167.5
115°	198.0	198.1	197.9	197.7	197.5	197.3	197.0	196.6	196.2	195.7	195.3
117.5°	225.0	224.9	224.7	224.5	224.4	224.2	224.0	223.8	223.6	223.4	223.3
120°	243.4	243.4	243.3	243.2	243.1	243.0	242.7	242.2	241.7	241.2	240.7
122.5°	261.4	261.5	261.3	261.0	260.7	260.5	260.2	260.1	259.9	259.7	259.5
125°	288.1	288.3	288.2	288.1	288.0	287.9	287.5	286.9	286.3	285.7	285.1
127.5°	314.3	314.4	314.2	314.1	314.0	313.9	313.7	313.3	313.0	312.6	312.3
130°	331.7	331.8	331.6	331.4	331.2	331.0	330.6	330.1	329.6	329.1	328.6
132.5°	348.3	348.4	348.5	348.5	348.6	348.6	348.2	347.4	346.6	345.7	344.9
135°	373.9	373.9	373.8	373.7	373.6	373.5	373.2	372.6	372.0	371.4	370.7
137.5°	398.8	398.7	398.4	398.2	398.0	397.8	397.4	396.8	396.2	395.6	395.0
140°	414.5	414.3	414.0	413.7	413.4	413.1	412.6	412.1	411.6	411.1	410.6
142.5°	430.0	429.9	429.5	429.1	428.7	428.3	427.9	427.5	427.1	426.6	426.2
145°	452.3	452.3	452.0	451.7	451.4	451.1	450.8	450.4	450.0	449.6	449.2
147.5°	472.7	472.5	472.2	472.0	471.7	471.5	471.3	471.0	470.8	470.6	470.4
150°	485.9	485.9	485.5	485.1	484.7	484.3	484.1	484.2	484.3	484.4	484.5
152.5°	497.7	497.5	497.3	497.2	497.0	496.8	496.7	496.5	496.4	496.3	496.1
155°	514.8	514.4	514.3	514.2	514.1	514.0	514.0	514.0	514.0	514.0	514.0
157.5°	529.8	529.4	529.3	529.2	529.1	529.0	529.0	529.3	529.5	529.7	529.9
160°	538.9	538.4	538.3	538.2	538.1	538.0	538.1	538.4	538.7	539.1	539.4
162.5°	547.3	546.8	546.8	546.7	546.7	546.7	546.8	547.0	547.3	547.5	547.7
165°	558.8	558.4	558.3	558.2	558.1	558.0	558.0	558.2	558.4	558.6	558.8
167.5°	567.1	566.5	566.5	566.5	566.5	566.5	566.7	567.1	567.5	567.9	568.3
170°	572.1	571.5	571.5	571.5	571.5	571.5	571.7	572.1	572.5	572.9	573.3
172.5°	575.8	575.2	575.2	575.2	575.2	575.2	575.4	575.8	576.2	576.6	577.0
175°	579.8	579.2	579.2	579.2	579.2	579.2	579.4	579.8	580.2	580.6	581.1
177.5°	581.8	581.3	581.4	581.5	581.6	581.6	581.8	582.2	582.5	582.8	583.1
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	929.9	932.7	936.6	941.2	944.8	948.8	950.9	950.9	952.7	956.7	961.8
5°	932.6	942.5	952.0	964.1	973.6	984.6	993.0	1001.0	1008.2	1017.3	1026.8
7.5°	931.8	948.2	965.3	984.5	1005.6	1022.4	1039.6	1053.2	1066.5	1084.0	1097.8
10°	928.8	950.1	973.2	997.5	1024.1	1047.3	1068.2	1087.2	1105.4	1124.4	1141.5
12.5°	923.3	950.4	978.7	1007.9	1041.5	1068.0	1094.9	1115.2	1136.4	1157.2	1178.3
15°	915.1	947.0	981.2	1021.9	1062.9	1092.5	1119.1	1145.3	1165.1	1188.6	1208.8
17.5°	898.2	939.3	982.3	1026.7	1066.1	1100.6	1128.4	1153.4	1174.4	1200.3	1227.7
20°	888.1	932.6	977.4	1024.9	1062.5	1097.8	1124.8	1150.6	1176.8	1210.7	1244.1
22.5°	874.2	921.6	969.2	1014.3	1054.0	1088.1	1116.0	1147.6	1182.0	1220.4	1260.8
25°	852.1	901.1	948.2	991.1	1029.8	1064.8	1102.8	1145.3	1187.1	1237.6	1295.7
27.5°	824.0	871.3	913.3	958.6	997.2	1041.6	1089.0	1135.1	1195.4	1264.9	1337.5
30°	803.0	847.9	887.8	930.7	974.4	1023.4	1076.6	1130.9	1202.7	1284.3	1370.6
32.5°	778.7	819.3	858.9	900.3	950.7	1004.5	1061.1	1127.5	1213.3	1306.2	1395.5
35°	736.6	773.0	811.4	857.4	910.9	969.4	1041.6	1122.5	1226.2	1326.1	1406.3
37.5°	692.4	721.1	759.7	808.1	866.5	934.2	1016.1	1114.4	1220.9	1310.6	1344.7
40°	658.3	685.3	725.9	776.8	834.6	908.7	1000.6	1101.6	1208.8	1271.0	1268.4
42.5°	624.6	651.9	691.0	742.2	802.4	885.3	979.9	1084.9	1175.3	1199.0	1149.6
45°	572.8	598.3	636.7	688.3	752.9	839.9	939.4	1040.1	1097.8	1059.5	961.5
47.5°	520.1	544.8	580.4	631.0	701.5	792.6	886.7	969.3	977.4	895.0	777.4
50°	485.5	508.6	542.5	596.4	664.8	753.7	844.5	909.4	889.3	788.6	667.4
52.5°	451.7	474.0	505.7	556.6	626.5	713.6	794.6	845.6	799.0	692.0	583.0
55°	401.9	423.2	455.1	501.8	565.2	645.0	716.1	734.7	666.3	558.4	470.3
57.5°	354.6	370.1	401.7	443.0	504.2	574.5	625.4	622.1	546.6	449.5	386.3
60°	323.3	337.3	367.3	405.3	463.4	526.5	562.2	547.0	470.7	390.5	329.7
62.5°	294.1	307.2	332.4	367.3	417.3	472.1	498.1	477.1	405.0	334.6	286.3
65°	250.0	259.5	279.6	311.9	351.0	389.0	412.2	381.4	317.6	264.4	227.9
67.5°	208.7	216.9	234.8	258.0	285.0	311.2	320.6	291.7	242.1	206.3	180.6
70°	182.0	189.6	201.7	223.4	241.2	259.8	264.4	238.6	197.2	169.8	153.8
72.5°	156.4	163.4	174.1	189.3	201.7	212.4	214.6	190.5	158.9	140.0	127.7
75°	119.3	125.4	132.2	137.9	145.9	147.8	147.0	128.4	111.3	98.8	91.9
77.5°	87.7	90.2	94.4	96.6	97.0	96.9	93.0	81.2	72.4	67.2	64.4
80°	67.6	69.5	70.7	71.4	71.8	68.0	63.8	56.6	53.6	50.5	47.1
82.5°	49.1	50.4	51.5	51.7	49.6	46.4	42.5	39.0	36.8	35.3	34.0
85°	26.6	27.0	26.6	24.7	22.0	20.9	20.1	19.4	19.0	18.6	18.6
87.5°	9.7	8.9	7.6	8.0	8.2	8.0	8.2	8.0	7.8	7.9	8.0
90°	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.3	7.8	8.3
92.5°	11.5	12.1	12.7	13.2	13.9	14.8	15.7	16.5	17.4	18.1	18.7
95°	29.7	29.9	30.1	30.3	30.9	31.9	32.9	33.9	34.9	35.6	36.3
97.5°	49.0	49.1	49.2	49.3	50.0	51.4	52.8	54.2	55.6	56.2	56.9
100°	63.5	63.5	63.5	63.5	64.1	65.4	66.7	68.0	69.3	70.3	71.2
102.5°	79.4	79.9	80.3	80.7	81.2	81.9	82.5	83.2	83.8	84.8	85.8
105°	103.8	104.3	104.8	105.4	105.9	106.5	107.1	107.7	108.3	108.9	109.5
107.5°	130.7	131.2	131.7	132.2	132.7	133.1	133.6	134.1	134.5	134.8	135.1
110°	149.2	149.7	150.2	150.7	151.1	151.4	151.7	152.0	152.3	152.6	152.9



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	167.8	168.0	168.3	168.6	168.9	169.3	169.7	170.0	170.4	170.6	170.7
115°	195.7	196.2	196.6	197.0	197.3	197.5	197.7	197.9	198.1	198.0	197.9
117.5°	223.4	223.6	223.8	224.0	224.2	224.4	224.5	224.7	224.9	225.0	225.1
120°	241.2	241.7	242.2	242.7	243.0	243.1	243.2	243.3	243.4	243.4	243.4
122.5°	259.7	259.9	260.1	260.2	260.5	260.7	261.0	261.3	261.5	261.4	261.4
125°	285.7	286.3	286.9	287.5	287.9	288.0	288.1	288.2	288.3	288.1	287.9
127.5°	312.6	313.0	313.3	313.7	313.9	314.0	314.1	314.2	314.4	314.3	314.2
130°	329.1	329.6	330.1	330.6	331.0	331.2	331.4	331.6	331.8	331.7	331.6
132.5°	345.7	346.6	347.4	348.2	348.6	348.6	348.5	348.5	348.4	348.3	348.2
135°	371.4	372.0	372.6	373.2	373.5	373.6	373.7	373.8	373.9	373.9	373.9
137.5°	395.6	396.2	396.8	397.4	397.8	398.0	398.2	398.4	398.7	398.8	398.9
140°	411.1	411.6	412.1	412.6	413.1	413.4	413.7	414.0	414.3	414.5	414.7
142.5°	426.6	427.1	427.5	427.9	428.3	428.7	429.1	429.5	429.9	430.0	430.1
145°	449.6	450.0	450.4	450.8	451.1	451.4	451.7	452.0	452.3	452.3	452.3
147.5°	470.6	470.8	471.0	471.3	471.5	471.7	472.0	472.2	472.5	472.7	472.9
150°	484.4	484.3	484.2	484.1	484.3	484.7	485.1	485.5	485.9	485.9	485.9
152.5°	496.3	496.4	496.5	496.7	496.8	497.0	497.2	497.3	497.5	497.7	498.0
155°	514.0	514.0	514.0	514.0	514.0	514.1	514.2	514.3	514.4	514.8	515.2
157.5°	529.7	529.5	529.3	529.0	529.0	529.1	529.2	529.3	529.4	529.8	530.2
160°	539.1	538.7	538.4	538.1	538.0	538.1	538.2	538.3	538.4	538.9	539.3
162.5°	547.5	547.3	547.0	546.8	546.7	546.7	546.7	546.8	546.8	547.3	547.8
165°	558.6	558.4	558.2	558.0	558.0	558.1	558.2	558.3	558.4	558.8	559.2
167.5°	567.9	567.5	567.1	566.7	566.5	566.5	566.5	566.5	566.5	567.1	567.7
170°	572.9	572.5	572.1	571.7	571.5	571.5	571.5	571.5	571.5	572.1	572.7
172.5°	576.6	576.2	575.8	575.4	575.2	575.2	575.2	575.2	575.2	575.8	576.4
175°	580.6	580.2	579.8	579.4	579.2	579.2	579.2	579.2	579.2	579.8	580.4
177.5°	582.8	582.5	582.2	581.8	581.6	581.6	581.5	581.4	581.3	581.8	582.3
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	965.8	965.8	971.0	970.6	974.0	972.8	973.4
5°	1038.2	1044.6	1050.3	1054.1	1059.8	1061.4	1060.6
7.5°	1113.3	1127.6	1134.6	1144.2	1145.9	1150.9	1150.4
10°	1159.7	1173.8	1184.4	1192.8	1197.0	1202.3	1202.7
12.5°	1196.2	1208.1	1217.6	1225.3	1230.4	1232.1	1233.1
15°	1224.7	1238.0	1249.0	1260.0	1266.5	1271.4	1274.1
17.5°	1253.4	1273.9	1293.4	1308.4	1317.3	1324.9	1324.8
20°	1275.6	1299.2	1323.5	1340.6	1358.0	1365.6	1366.8
22.5°	1299.3	1335.3	1366.6	1393.1	1416.1	1424.0	1426.9
25°	1348.5	1395.6	1443.9	1481.1	1507.7	1523.3	1525.6
27.5°	1408.0	1471.8	1522.5	1556.9	1579.0	1590.5	1593.0
30°	1450.0	1508.8	1554.4	1580.3	1590.5	1592.0	1586.3
32.5°	1468.8	1512.8	1531.0	1529.5	1509.4	1496.0	1490.9
35°	1445.8	1436.7	1392.2	1339.0	1298.4	1272.6	1265.7
37.5°	1315.7	1237.1	1155.3	1075.0	1032.2	1010.5	973.1
40°	1187.5	1075.4	990.3	922.7	874.5	835.7	826.6
42.5°	1042.8	927.1	842.0	784.1	745.6	719.0	707.5
45°	838.0	738.5	668.2	623.7	594.1	574.7	566.0
47.5°	670.2	593.2	542.0	509.1	486.5	469.7	465.0
50°	578.2	516.6	473.3	445.6	428.5	415.6	410.3
52.5°	502.2	452.5	419.2	396.4	380.2	372.1	367.7
55°	414.4	371.5	347.6	329.3	320.2	313.8	310.7
57.5°	338.9	307.9	290.4	277.8	269.4	265.3	263.8
60°	296.7	272.4	256.4	246.5	240.8	235.5	234.0
62.5°	259.3	240.2	227.8	219.2	213.5	211.2	210.3
65°	208.9	196.4	187.3	182.0	177.4	176.6	176.3
67.5°	166.1	158.7	153.9	148.4	146.8	144.1	143.6
70°	142.1	137.1	131.4	129.5	127.6	125.0	125.4
72.5°	120.5	115.6	111.7	109.2	108.5	107.4	108.3
75°	88.1	86.6	85.1	83.2	82.4	82.4	82.1
77.5°	62.9	61.6	59.9	58.8	58.6	57.0	57.6
80°	45.6	43.7	42.9	43.3	42.2	41.8	41.8
82.5°	33.7	33.0	32.3	32.4	32.1	31.8	32.1
85°	18.6	18.2	18.2	17.9	17.9	17.5	17.5
87.5°	8.4	8.8	8.3	8.1	8.1	8.5	8.9
90°	8.8	9.3	9.7	10.0	10.3	10.6	10.9
92.5°	19.4	20.1	20.5	20.7	20.9	21.2	21.4
95°	37.0	37.7	38.2	38.4	38.6	38.8	39.0
97.5°	57.6	58.2	58.6	58.7	58.9	59.0	59.1
100°	72.1	73.0	73.5	73.7	73.9	74.1	74.3
102.5°	86.8	87.8	88.4	88.7	89.0	89.3	89.6
105°	110.1	110.7	111.2	111.5	111.8	112.1	112.4
107.5°	135.4	135.7	135.9	135.9	135.8	135.8	135.8
110°	153.2	153.5	153.6	153.5	153.4	153.3	153.2



TEST NUMBER: P333661

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	170.8	171.0	171.0	170.8	170.6	170.4	170.2
115°	197.8	197.7	197.6	197.5	197.4	197.3	197.2
117.5°	225.1	225.2	225.1	224.7	224.3	223.8	223.4
120°	243.4	243.4	243.2	242.8	242.4	242.0	241.6
122.5°	261.3	261.2	261.0	260.7	260.4	260.0	259.7
125°	287.7	287.5	287.3	287.2	287.1	287.0	286.9
127.5°	314.1	314.0	313.8	313.6	313.4	313.2	313.0
130°	331.5	331.4	331.2	331.0	330.8	330.6	330.4
132.5°	348.1	348.0	347.9	347.6	347.3	347.0	346.7
135°	373.9	373.9	373.7	373.3	372.9	372.5	372.1
137.5°	399.0	399.2	399.0	398.5	398.0	397.4	396.9
140°	414.9	415.1	414.9	414.4	413.9	413.4	412.9
142.5°	430.2	430.3	430.1	429.6	429.1	428.6	428.1
145°	452.3	452.3	452.2	451.9	451.6	451.3	451.0
147.5°	473.2	473.4	473.2	472.5	471.8	471.1	470.5
150°	485.9	485.9	485.8	485.6	485.4	485.2	485.0
152.5°	498.2	498.4	498.4	498.0	497.7	497.3	496.9
155°	515.6	516.0	516.0	515.5	515.0	514.5	514.0
157.5°	530.6	531.0	530.9	530.2	529.5	528.9	528.2
160°	539.7	540.1	540.0	539.5	539.0	538.5	538.0
162.5°	548.2	548.7	548.7	548.1	547.5	546.9	546.3
165°	559.6	560.0	559.9	559.3	558.7	558.1	557.5
167.5°	568.3	568.9	568.9	568.2	567.6	567.0	566.4
170°	573.3	574.0	573.9	573.2	572.5	571.8	571.1
172.5°	577.0	577.6	577.6	576.9	576.3	575.7	575.1
175°	581.1	581.7	581.6	580.9	580.2	579.5	578.8
177.5°	582.8	583.3	583.2	582.7	582.1	581.5	581.0
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4

(END OF REPORT)