

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333441-935

Luminaire Tested: **S125DIW-S1090D770U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333441-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D770U935-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6116.7 lumens  
Efficiency: N/A  
Efficacy: 114.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333441-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333441-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	24	21	19
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9489	9489	9489
5°	9510	9419	9479
10°	9452	9353	9406
15°	9349	9240	9279
20°	9203	9082	9099
25°	9045	8896	8888
30°	8850	8694	8651
35°	8642	8476	8358
40°	8427	8241	8123
45°	8195	8026	7867
50°	7941	7766	7533
55°	7696	7473	7264
60°	7401	7177	6921
65°	7051	6820	6589
70°	6717	6409	6190
75°	6119	5916	5712
80°	5449	5359	5229
85°	4735	4824	4565



TEST NUMBER: P333441-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.5	2.3
10°-20°	391.3	6.4
20°-30°	577.8	9.4
30°-40°	674.2	11.0
40°-50°	677.1	11.1
50°-60°	594.4	9.7
60°-70°	442.9	7.2
70°-80°	253.2	4.1
80°-90°	75.5	1.2
90°-100°	55.0	0.9
100°-110°	162.4	2.7
110°-120°	275.1	4.5
120°-130°	362.1	5.9
130°-140°	405.7	6.6
140°-150°	397.7	6.5
150°-160°	334.0	5.5
160°-170°	222.0	3.6
170°-180°	77.7	1.3
0°-30°	1107.6	18.1
0°-40°	1781.8	29.1
0°-60°	3053.3	49.9
0°-90°	3824.8	62.5
90°-120°	492.6	8.1
90°-150°	1658.1	27.1
90°-180°	2292.0	37.5
0°-180°	6116.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1469	1469	1469	1469	1469	
5°	1467	1464	1453	1463	1462	139
15°	1398	1394	1382	1388	1388	394
25°	1269	1263	1248	1250	1247	584
35°	1096	1091	1075	1069	1060	685
45°	897	892	879	865	861	691
55°	684	679	664	653	645	610
65°	461	458	446	436	431	458
75°	245	243	237	234	229	261
85°	64	65	65	64	62	71
90°	1	6	10	13	15	6
95°	42	43	49	54	55	44
105°	146	149	153	156	158	156
115°	276	278	279	279	278	272
125°	402	406	406	405	405	360
135°	523	526	527	527	525	403
145°	633	636	638	638	636	396
155°	725	725	726	728	725	334
165°	788	787	788	790	786	222
175°	819	817	817	820	816	78
180°	821	821	821	821	821	



TEST NUMBER: P333441-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1472.9	1472.3	1471.6	1471.0	1470.4	1469.0	1467.0	1464.9	1462.8	1460.8	1462.8
5°	1466.9	1466.4	1465.9	1465.3	1464.8	1463.3	1460.7	1458.1	1455.5	1452.9	1455.3
7.5°	1453.4	1452.9	1452.3	1451.8	1451.3	1449.6	1446.7	1443.9	1441.1	1438.2	1440.5
10°	1441.3	1440.8	1440.3	1439.8	1439.2	1437.5	1434.7	1431.8	1429.0	1426.2	1428.2
12.5°	1426.4	1425.5	1424.5	1423.6	1422.7	1420.9	1418.2	1415.7	1413.0	1410.3	1412.0
15°	1398.3	1397.5	1396.7	1395.9	1395.2	1393.4	1390.5	1387.7	1384.8	1382.0	1383.3
17.5°	1366.0	1364.9	1363.7	1362.5	1361.4	1359.3	1356.4	1353.5	1350.6	1347.6	1349.2
20°	1339.0	1338.5	1338.0	1337.5	1337.0	1335.0	1331.6	1328.3	1324.9	1321.5	1323.4
22.5°	1312.0	1311.1	1310.2	1309.2	1308.3	1306.2	1303.1	1299.9	1296.8	1293.7	1294.9
25°	1269.3	1268.0	1266.7	1265.4	1264.1	1261.8	1258.4	1255.1	1251.7	1248.4	1248.9
27.5°	1219.3	1218.5	1217.7	1216.9	1216.2	1214.1	1210.6	1207.1	1203.7	1200.2	1200.3
30°	1186.7	1185.9	1185.2	1184.4	1183.6	1181.3	1177.4	1173.5	1169.7	1165.8	1165.3
32.5°	1151.4	1150.2	1149.0	1147.8	1146.7	1144.4	1140.8	1137.4	1133.9	1130.5	1129.5
35°	1096.1	1095.0	1094.0	1093.0	1091.9	1089.6	1086.0	1082.4	1078.7	1075.1	1073.8
37.5°	1038.6	1037.3	1036.0	1034.7	1033.5	1031.1	1027.7	1024.3	1020.9	1017.5	1015.5
40°	999.6	998.3	997.0	995.7	994.5	992.0	988.3	984.7	981.1	977.5	975.2
42.5°	957.8	956.7	955.6	954.5	953.4	951.1	947.4	943.8	940.2	936.6	934.4
45°	897.3	896.3	895.3	894.2	893.2	891.1	888.0	884.9	881.8	878.7	875.6
47.5°	832.2	832.2	832.3	832.4	832.4	830.6	826.9	823.1	819.4	815.7	812.5
50°	790.4	789.6	788.8	788.1	787.3	785.3	782.2	779.1	776.0	772.9	769.6
52.5°	747.6	747.0	746.5	745.9	745.4	743.4	740.1	736.8	733.5	730.1	727.2
55°	683.5	682.7	681.9	681.1	680.4	678.1	674.5	670.9	667.3	663.7	661.3
57.5°	615.8	615.4	615.0	614.6	614.2	612.4	609.3	606.3	603.3	600.2	597.2
60°	573.0	572.0	570.9	569.9	568.9	567.0	564.1	561.3	558.4	555.6	553.0
62.5°	528.4	527.5	526.8	525.9	525.1	523.5	521.0	518.6	516.2	513.8	510.9
65°	461.4	460.9	460.4	459.9	459.3	457.7	454.9	452.0	449.2	446.3	444.0
67.5°	396.6	395.5	394.4	393.3	392.3	390.6	388.5	386.4	384.3	382.2	380.2
70°	355.7	354.4	353.1	351.8	350.5	348.7	346.4	344.1	341.7	339.4	337.9
72.5°	311.1	310.1	309.3	308.4	307.5	306.3	304.9	303.3	301.9	300.3	298.6
75°	245.2	244.7	244.2	243.7	243.1	242.3	241.0	239.7	238.4	237.1	236.3
77.5°	184.6	184.3	184.2	184.0	183.7	183.3	182.5	181.8	181.2	180.4	179.9
80°	146.5	146.5	146.5	146.5	146.5	146.2	145.7	145.2	144.6	144.1	143.9
82.5°	113.0	112.5	112.2	111.8	111.3	111.1	111.0	110.9	110.7	110.6	110.2
85°	63.9	64.1	64.4	64.7	64.9	65.1	65.1	65.1	65.1	65.1	64.8
87.5°	25.2	25.5	25.7	25.9	26.2	26.3	26.3	26.3	26.3	26.3	26.3
90°	0.6	1.8	2.9	4.0	5.2	6.3	7.2	8.3	9.2	10.2	10.9
92.5°	15.5	16.3	17.0	17.8	18.7	19.6	20.9	22.1	23.3	24.5	25.5
95°	41.6	41.8	42.1	42.4	42.7	43.6	44.9	46.4	47.8	49.2	50.2
97.5°	69.1	69.1	69.2	69.4	69.5	70.5	72.5	74.5	76.4	78.4	79.3
100°	89.5	89.5	89.5	89.5	89.5	90.4	92.2	94.1	95.9	97.8	99.1
102.5°	111.5	112.0	112.6	113.1	113.7	114.5	115.5	116.4	117.3	118.2	119.7
105°	145.8	146.5	147.1	147.8	148.6	149.4	150.2	151.0	151.9	152.7	153.6
107.5°	183.6	184.3	185.0	185.7	186.4	187.1	187.8	188.4	189.1	189.7	190.1
110°	209.7	210.3	211.0	211.8	212.5	213.0	213.4	213.9	214.3	214.7	215.2



TEST NUMBER: P333441-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	236.3	236.6	236.9	237.4	237.7	238.2	238.7	239.3	239.8	240.3	240.6
115°	275.5	276.0	276.6	277.2	277.8	278.2	278.4	278.7	279.1	279.3	279.1
117.5°	314.9	315.1	315.4	315.6	315.9	316.2	316.4	316.7	316.9	317.2	317.3
120°	339.4	340.1	340.8	341.6	342.2	342.7	342.8	342.9	343.1	343.2	343.2
122.5°	366.0	366.3	366.5	366.8	367.0	367.3	367.6	368.1	368.4	368.8	368.7
125°	402.0	402.9	403.7	404.6	405.4	406.0	406.0	406.2	406.4	406.5	406.2
127.5°	440.4	440.8	441.3	441.9	442.3	442.6	442.8	443.0	443.2	443.3	443.2
130°	463.4	464.1	464.9	465.5	466.2	466.7	467.0	467.3	467.6	467.9	467.7
132.5°	486.4	487.6	488.7	489.9	491.0	491.6	491.5	491.5	491.5	491.4	491.3
135°	522.8	523.7	524.5	525.4	526.2	526.8	526.8	527.0	527.2	527.3	527.3
137.5°	557.1	557.9	558.7	559.6	560.4	560.9	561.3	561.5	561.9	562.2	562.4
140°	579.1	579.8	580.5	581.2	581.9	582.5	582.9	583.3	583.8	584.2	584.4
142.5°	601.1	601.7	602.3	602.9	603.5	604.0	604.6	605.1	605.6	606.1	606.3
145°	633.4	634.0	634.6	635.1	635.7	636.2	636.6	637.1	637.5	637.9	637.9
147.5°	663.3	663.7	663.9	664.3	664.6	664.9	665.2	665.6	665.9	666.2	666.6
150°	683.3	683.1	682.9	682.9	682.7	682.9	683.5	684.1	684.6	685.2	685.2
152.5°	699.6	699.8	700.0	700.3	700.4	700.6	700.9	701.1	701.3	701.5	701.9
155°	724.8	724.8	724.8	724.8	724.8	724.9	725.0	725.1	725.3	725.5	726.0
157.5°	747.3	747.0	746.7	746.4	746.1	746.0	746.1	746.2	746.4	746.6	747.1
160°	760.6	760.2	759.7	759.3	758.9	758.7	758.9	759.1	759.1	759.3	759.9
162.5°	772.4	772.1	771.7	771.5	771.1	770.9	771.0	771.0	771.0	771.1	771.8
165°	788.1	787.8	787.6	787.2	787.0	786.9	787.0	787.1	787.3	787.5	788.0
167.5°	801.4	800.8	800.2	799.7	799.1	798.8	798.8	798.8	798.8	798.8	799.7
170°	808.6	808.0	807.4	806.8	806.2	806.0	806.0	806.0	806.0	806.0	806.8
172.5°	813.6	813.0	812.5	811.9	811.4	811.1	811.1	811.1	811.1	811.1	811.9
175°	819.4	818.8	818.3	817.7	817.1	816.8	816.8	816.8	816.8	816.8	817.7
177.5°	822.3	821.9	821.4	821.0	820.5	820.3	820.1	820.0	819.9	819.8	820.4
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333441-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2	1469.2
2.5°	1464.9	1467.0	1469.0	1470.0	1469.8	1469.6	1469.4	1469.2
5°	1457.6	1459.9	1462.2	1463.3	1463.0	1462.8	1462.5	1462.2
7.5°	1442.8	1445.1	1447.3	1448.4	1448.1	1447.9	1447.6	1447.3
10°	1430.3	1432.4	1434.4	1435.4	1435.1	1434.9	1434.6	1434.3
12.5°	1413.7	1415.3	1416.9	1417.8	1417.7	1417.6	1417.6	1417.6
15°	1384.6	1385.9	1387.2	1387.8	1387.8	1387.8	1387.8	1387.8
17.5°	1350.8	1352.4	1354.0	1354.2	1352.9	1351.6	1350.3	1349.0
20°	1325.2	1327.0	1328.8	1329.0	1327.7	1326.5	1325.2	1323.9
22.5°	1296.1	1297.3	1298.4	1298.6	1297.7	1296.8	1296.0	1295.0
25°	1249.4	1249.9	1250.4	1250.3	1249.5	1248.7	1247.9	1247.2
27.5°	1200.4	1200.5	1200.7	1200.3	1199.5	1198.8	1198.0	1197.2
30°	1164.8	1164.2	1163.7	1163.1	1162.4	1161.6	1160.8	1160.0
32.5°	1128.6	1127.7	1126.8	1125.6	1124.2	1122.8	1121.4	1120.0
35°	1072.5	1071.3	1070.0	1068.3	1066.3	1064.2	1062.1	1060.1
37.5°	1013.7	1011.8	1009.9	1008.3	1007.1	1005.9	1004.7	1003.6
40°	972.8	970.5	968.2	966.6	965.9	965.1	964.3	963.5
42.5°	932.4	930.2	928.2	926.4	925.3	924.1	922.9	921.7
45°	872.5	869.4	866.3	864.4	863.6	862.8	862.0	861.3
47.5°	809.4	806.2	803.1	800.6	798.8	797.0	795.2	793.4
50°	766.2	762.8	759.5	756.9	755.1	753.3	751.5	749.7
52.5°	724.3	721.3	718.4	715.9	713.9	711.9	709.9	707.8
55°	659.0	656.7	654.4	652.3	650.5	648.7	646.9	645.1
57.5°	594.3	591.2	588.2	586.3	585.3	584.3	583.3	582.3
60°	550.4	547.9	545.3	543.0	541.2	539.4	537.6	535.8
62.5°	508.2	505.4	502.6	500.5	499.1	497.7	496.3	494.9
65°	441.7	439.4	437.0	435.3	434.3	433.3	432.2	431.2
67.5°	378.2	376.3	374.3	373.0	372.4	371.8	371.2	370.6
70°	336.3	334.8	333.2	331.9	330.9	329.8	328.8	327.8
72.5°	296.9	295.1	293.3	292.0	290.9	289.9	288.9	287.8
75°	235.6	234.8	234.0	233.1	232.0	231.0	230.0	228.9
77.5°	179.4	179.0	178.6	178.0	177.2	176.5	175.7	175.0
80°	143.6	143.4	143.1	142.7	142.2	141.6	141.1	140.6
82.5°	109.7	109.3	108.8	108.5	108.4	108.3	108.2	108.1
85°	64.6	64.3	64.1	63.6	63.1	62.6	62.1	61.6
87.5°	26.5	26.6	26.8	26.7	26.3	26.0	25.7	25.4
90°	11.6	12.4	13.1	13.6	14.0	14.5	14.9	15.3
92.5°	26.4	27.4	28.3	28.9	29.3	29.5	29.9	30.1
95°	51.2	52.2	53.2	53.8	54.2	54.4	54.7	54.9
97.5°	80.2	81.2	82.1	82.7	82.8	83.0	83.2	83.3
100°	100.3	101.6	102.9	103.7	104.0	104.3	104.5	104.8
102.5°	121.1	122.4	123.8	124.7	125.1	125.5	125.9	126.3
105°	154.5	155.3	156.2	156.8	157.2	157.6	158.1	158.5
107.5°	190.5	191.0	191.4	191.6	191.6	191.6	191.5	191.5
110°	215.6	216.0	216.5	216.6	216.5	216.3	216.2	216.0





TEST NUMBER: P333441-935

CATALOG NUMBER: S125DIW-S1090D770U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	240.7	240.9	241.1	241.1	240.8	240.6	240.3	240.0
115°	279.1	278.9	278.7	278.6	278.4	278.4	278.2	278.0
117.5°	317.4	317.5	317.6	317.4	316.8	316.2	315.6	315.1
120°	343.2	343.2	343.2	342.9	342.4	341.8	341.2	340.7
122.5°	368.6	368.4	368.3	368.1	367.6	367.1	366.7	366.3
125°	406.0	405.6	405.4	405.2	405.0	404.8	404.8	404.6
127.5°	443.1	442.9	442.7	442.6	442.3	442.0	441.7	441.4
130°	467.6	467.4	467.3	467.1	466.8	466.5	466.2	466.0
132.5°	491.1	490.9	490.9	490.5	490.2	489.7	489.4	489.0
135°	527.3	527.3	527.3	527.0	526.4	525.9	525.3	524.8
137.5°	562.6	562.7	562.9	562.6	561.9	561.2	560.5	559.7
140°	584.8	585.0	585.3	585.1	584.4	583.7	583.0	582.3
142.5°	606.5	606.7	606.8	606.6	605.9	605.2	604.4	603.7
145°	637.9	637.9	637.9	637.7	637.2	636.8	636.4	635.9
147.5°	666.9	667.3	667.6	667.3	666.3	665.4	664.4	663.5
150°	685.2	685.2	685.2	685.0	684.8	684.5	684.2	683.9
152.5°	702.2	702.6	702.9	702.8	702.3	701.8	701.3	700.8
155°	726.6	727.1	727.7	727.6	726.9	726.3	725.5	724.8
157.5°	747.7	748.2	748.8	748.6	747.7	746.7	745.8	744.9
160°	760.4	761.0	761.6	761.6	760.8	760.1	759.4	758.7
162.5°	772.5	773.1	773.8	773.8	772.9	772.1	771.3	770.4
165°	788.6	789.2	789.7	789.5	788.8	787.9	787.0	786.2
167.5°	800.6	801.4	802.2	802.2	801.3	800.5	799.6	798.7
170°	807.7	808.6	809.4	809.3	808.3	807.4	806.3	805.4
172.5°	812.8	813.6	814.5	814.5	813.6	812.7	811.8	811.0
175°	818.6	819.4	820.3	820.2	819.2	818.2	817.2	816.2
177.5°	821.1	821.8	822.5	822.4	821.7	820.9	820.1	819.2
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3

(END OF REPORT)