

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333464-935

Luminaire Tested: **S125DIW-S1270D470U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333464-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D470U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 470 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6030.0 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333464-935

CATALOG NUMBER: S125DIW-S1270D470U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333464-935

CATALOG NUMBER: S125DIW-S1270D470U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	62	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10959	10959	10959
5°	10983	10878	10949
10°	10916	10802	10864
15°	10797	10672	10717
20°	10628	10490	10509
25°	10446	10274	10264
30°	10221	10041	9991
35°	9980	9790	9653
40°	9732	9517	9382
45°	9465	9270	9085
50°	9171	8969	8699
55°	8888	8631	8389
60°	8548	8289	7994
65°	8145	7878	7610
70°	7757	7402	7149
75°	7069	6835	6598
80°	6289	6189	6044
85°	5476	5572	5269



TEST NUMBER: P333464-935

CATALOG NUMBER: S125DIW-S1270D470U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.0	2.7
10°-20°	451.9	7.5
20°-30°	667.3	11.1
30°-40°	778.6	12.9
40°-50°	782.0	13.0
50°-60°	686.5	11.4
60°-70°	511.5	8.5
70°-80°	292.5	4.9
80°-90°	86.2	1.4
90°-100°	19.1	0.3
100°-110°	117.7	2.0
110°-120°	213.4	3.5
120°-130°	273.9	4.5
130°-140°	294.6	4.9
140°-150°	276.5	4.6
150°-160°	223.7	3.7
160°-170°	144.7	2.4
170°-180°	49.9	0.8
0°-30°	1279.2	21.2
0°-40°	2057.8	34.1
0°-60°	3526.3	58.5
0°-90°	4416.4	73.2
90°-120°	350.2	5.8
90°-150°	1195.3	19.8
90°-180°	1614.0	26.8
0°-180°	6030.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1694	1691	1678	1689	1689	161
15°	1615	1610	1596	1602	1603	455
25°	1466	1459	1442	1444	1440	674
35°	1266	1260	1242	1235	1224	791
45°	1036	1030	1015	999	995	798
55°	789	784	766	755	745	704
65°	533	530	516	504	498	529
75°	283	280	274	270	264	302
85°	74	75	75	74	71	82
90°	0	4	6	8	9	5
95°	22	20	6	8	8	28
105°	114	116	116	116	116	121
115°	215	217	217	216	213	213
125°	306	308	308	307	306	273
135°	381	384	383	382	380	294
145°	442	443	443	443	441	276
155°	487	485	485	486	483	224
165°	514	512	512	514	511	145
175°	526	523	524	526	523	50
180°	526	526	526	526	526	



TEST NUMBER: P333464-935

CATALOG NUMBER: S125DIW-S1270D470U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1701.1	1700.4	1699.7	1698.9	1698.2	1696.7	1694.3	1691.9	1689.5	1687.1	1689.5
5°	1694.1	1693.5	1692.9	1692.3	1691.7	1690.0	1687.0	1683.9	1681.0	1678.0	1680.7
7.5°	1678.5	1677.9	1677.3	1676.7	1676.1	1674.2	1670.9	1667.7	1664.4	1661.1	1663.7
10°	1664.6	1664.0	1663.4	1662.8	1662.2	1660.3	1657.0	1653.7	1650.4	1647.1	1649.5
12.5°	1647.4	1646.3	1645.3	1644.2	1643.1	1641.1	1638.0	1635.0	1631.9	1628.8	1630.8
15°	1614.9	1614.0	1613.1	1612.2	1611.4	1609.2	1605.9	1602.7	1599.4	1596.1	1597.6
17.5°	1577.6	1576.3	1574.9	1573.6	1572.4	1569.9	1566.6	1563.1	1559.8	1556.3	1558.2
20°	1546.4	1545.8	1545.2	1544.6	1544.0	1541.8	1537.9	1534.0	1530.2	1526.3	1528.4
22.5°	1515.3	1514.2	1513.1	1512.1	1511.0	1508.6	1505.0	1501.4	1497.7	1494.1	1495.5
25°	1465.9	1464.4	1462.9	1461.5	1459.9	1457.2	1453.4	1449.5	1445.6	1441.7	1442.3
27.5°	1408.2	1407.3	1406.4	1405.5	1404.6	1402.1	1398.2	1394.1	1390.2	1386.1	1386.3
30°	1370.6	1369.7	1368.8	1367.9	1367.0	1364.3	1359.9	1355.4	1350.9	1346.4	1345.8
32.5°	1329.8	1328.4	1327.1	1325.7	1324.3	1321.6	1317.6	1313.6	1309.6	1305.6	1304.6
35°	1265.8	1264.7	1263.5	1262.3	1261.1	1258.4	1254.2	1250.1	1245.9	1241.7	1240.3
37.5°	1199.5	1198.1	1196.6	1195.1	1193.6	1190.8	1187.0	1183.0	1179.1	1175.2	1172.9
40°	1154.4	1153.0	1151.5	1150.0	1148.5	1145.6	1141.5	1137.3	1133.2	1128.9	1126.3
42.5°	1106.1	1104.9	1103.6	1102.3	1101.1	1098.4	1094.2	1090.0	1085.9	1081.7	1079.3
45°	1036.3	1035.2	1034.0	1032.8	1031.6	1029.2	1025.6	1022.0	1018.5	1014.9	1011.2
47.5°	961.1	961.2	961.3	961.3	961.4	959.2	955.0	950.7	946.4	942.1	938.5
50°	912.8	912.0	911.0	910.2	909.2	907.0	903.4	899.8	896.3	892.7	888.8
52.5°	863.4	862.8	862.1	861.4	860.8	858.6	854.7	850.9	847.1	843.3	839.9
55°	789.4	788.4	787.6	786.6	785.7	783.3	779.0	774.9	770.7	766.5	763.8
57.5°	711.2	710.8	710.2	709.8	709.3	707.3	703.8	700.3	696.7	693.2	689.7
60°	661.8	660.6	659.4	658.2	657.0	654.8	651.5	648.2	645.0	641.7	638.7
62.5°	610.3	609.3	608.4	607.3	606.4	604.6	601.8	598.9	596.2	593.3	590.1
65°	533.0	532.4	531.8	531.2	530.5	528.6	525.3	522.0	518.8	515.5	512.8
67.5°	458.1	456.8	455.6	454.3	453.1	451.2	448.8	446.3	443.8	441.3	439.1
70°	410.8	409.3	407.8	406.3	404.8	402.7	400.0	397.4	394.7	392.0	390.2
72.5°	359.2	358.2	357.2	356.2	355.2	353.8	352.1	350.3	348.6	346.9	344.8
75°	283.3	282.7	282.1	281.5	280.9	279.8	278.4	276.8	275.3	273.9	272.9
77.5°	213.2	212.9	212.7	212.5	212.2	211.7	210.9	210.0	209.1	208.4	207.8
80°	169.1	169.1	169.1	169.1	169.1	168.8	168.2	167.6	167.0	166.4	166.2
82.5°	130.4	130.0	129.5	129.1	128.5	128.3	128.1	128.0	127.9	127.8	127.3
85°	73.9	74.1	74.4	74.7	75.0	75.2	75.2	75.2	75.2	75.2	74.9
87.5°	29.1	29.2	29.4	29.4	29.6	29.6	29.5	29.4	29.3	29.2	29.3
90°	0.4	1.1	1.8	2.5	3.2	3.8	4.4	5.0	5.6	6.2	6.6
92.5°	6.0	5.5	5.0	4.6	4.0	4.0	4.6	5.2	5.7	6.2	6.6
95°	22.2	22.0	21.7	21.4	21.2	19.4	16.1	12.8	9.6	6.2	6.6
97.5°	46.3	46.8	47.3	47.8	48.2	45.2	38.7	32.2	25.7	19.2	16.7
100°	65.0	65.3	65.6	65.9	66.1	66.4	66.7	67.1	67.4	67.8	54.8
102.5°	84.0	84.4	84.7	85.1	85.4	85.7	85.8	86.0	86.3	86.4	84.0
105°	114.5	114.9	115.2	115.5	115.9	116.1	116.1	116.1	116.1	116.1	116.1
107.5°	146.1	146.1	146.1	146.1	146.1	146.2	146.4	146.5	146.7	146.9	147.0
110°	166.7	166.7	166.7	166.7	166.7	166.8	166.9	167.1	167.3	167.5	167.2



TEST NUMBER: P333464-935

CATALOG NUMBER: S125DIW-S1270D470U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	186.1	186.2	186.4	186.7	186.8	187.0	187.1	187.3	187.4	187.4	187.1
115°	215.0	215.4	215.9	216.3	216.7	217.0	217.1	217.1	217.2	217.3	217.0
117.5°	245.0	245.0	245.0	245.0	245.0	245.1	245.4	245.7	246.1	246.4	246.0
120°	263.7	263.6	263.6	263.5	263.4	263.5	263.7	264.0	264.2	264.5	264.3
122.5°	280.3	280.5	280.9	281.2	281.5	281.7	281.9	282.0	282.1	282.2	282.1
125°	305.7	306.3	306.9	307.5	308.2	308.5	308.5	308.5	308.5	308.5	308.2
127.5°	330.1	330.6	331.1	331.5	331.9	332.1	332.0	332.0	331.9	331.8	331.7
130°	345.1	345.5	345.9	346.4	346.8	347.1	347.2	347.2	347.3	347.4	347.2
132.5°	360.1	360.6	361.1	361.5	362.1	362.2	362.1	361.9	361.6	361.4	361.4
135°	381.3	381.9	382.4	382.9	383.4	383.6	383.4	383.2	383.1	382.9	382.7
137.5°	400.9	401.3	401.7	402.3	402.7	402.9	402.7	402.5	402.3	402.2	402.3
140°	413.6	413.8	414.0	414.1	414.3	414.4	414.3	414.2	414.1	414.1	414.2
142.5°	425.2	425.3	425.4	425.5	425.6	425.7	425.9	425.9	426.1	426.2	426.2
145°	442.1	442.3	442.5	442.6	442.8	442.9	442.9	442.9	442.9	442.9	443.0
147.5°	456.9	456.8	456.8	456.8	456.8	456.8	456.9	457.0	457.1	457.2	457.3
150°	466.2	466.1	465.9	465.7	465.5	465.5	465.7	465.9	466.1	466.2	466.4
152.5°	475.3	474.9	474.5	474.2	473.7	473.6	473.8	474.0	474.2	474.3	474.5
155°	486.9	486.4	485.9	485.3	484.8	484.7	484.8	485.0	485.2	485.3	485.6
157.5°	495.8	495.5	495.2	494.9	494.6	494.5	494.5	494.5	494.5	494.6	494.8
160°	502.0	501.5	501.0	500.5	500.0	499.8	499.9	500.0	500.1	500.2	500.5
162.5°	507.0	506.5	506.0	505.5	505.0	504.8	504.9	505.0	505.1	505.1	505.6
165°	513.8	513.2	512.7	512.2	511.7	511.4	511.5	511.6	511.7	511.8	512.3
167.5°	518.8	518.2	517.7	517.1	516.6	516.3	516.4	516.5	516.6	516.7	517.4
170°	521.6	521.0	520.3	519.7	519.1	518.8	518.9	519.0	519.1	519.2	519.9
172.5°	523.4	522.8	522.2	521.6	521.0	520.8	520.9	521.1	521.2	521.4	522.0
175°	525.5	525.0	524.4	523.9	523.4	523.1	523.2	523.3	523.4	523.5	524.2
177.5°	526.4	526.0	525.6	525.1	524.7	524.5	524.6	524.7	524.8	524.9	525.3
180°	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5



TEST NUMBER: P333464-935

CATALOG NUMBER: S125DIW-S1270D470U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1691.9	1694.3	1696.7	1697.7	1697.5	1697.3	1697.0	1696.8
5°	1683.3	1686.1	1688.8	1690.0	1689.6	1689.4	1689.0	1688.8
7.5°	1666.3	1669.0	1671.5	1672.8	1672.5	1672.1	1671.9	1671.5
10°	1651.9	1654.3	1656.7	1657.7	1657.4	1657.1	1656.8	1656.6
12.5°	1632.7	1634.6	1636.5	1637.4	1637.4	1637.3	1637.3	1637.2
15°	1599.1	1600.6	1602.1	1602.8	1602.8	1602.8	1602.8	1602.8
17.5°	1560.0	1561.9	1563.7	1563.9	1562.5	1561.0	1559.4	1558.0
20°	1530.5	1532.6	1534.6	1535.0	1533.4	1532.0	1530.5	1529.0
22.5°	1496.8	1498.2	1499.6	1499.8	1498.7	1497.7	1496.7	1495.7
25°	1442.9	1443.6	1444.2	1444.0	1443.1	1442.2	1441.3	1440.4
27.5°	1386.4	1386.6	1386.6	1386.2	1385.3	1384.5	1383.5	1382.7
30°	1345.2	1344.6	1344.0	1343.3	1342.4	1341.5	1340.6	1339.7
32.5°	1303.5	1302.4	1301.3	1299.9	1298.4	1296.8	1295.1	1293.6
35°	1238.7	1237.3	1235.8	1233.8	1231.4	1229.1	1226.7	1224.3
37.5°	1170.7	1168.5	1166.3	1164.5	1163.1	1161.7	1160.4	1159.0
40°	1123.6	1120.9	1118.2	1116.5	1115.5	1114.7	1113.7	1112.8
42.5°	1076.9	1074.4	1071.9	1070.1	1068.7	1067.3	1065.9	1064.5
45°	1007.7	1004.1	1000.6	998.3	997.4	996.5	995.6	994.7
47.5°	934.8	931.2	927.6	924.7	922.6	920.5	918.4	916.4
50°	884.9	881.1	877.2	874.2	872.1	870.0	868.0	865.8
52.5°	836.5	833.1	829.7	826.8	824.5	822.2	819.8	817.5
55°	761.1	758.5	755.8	753.4	751.3	749.2	747.1	745.0
57.5°	686.3	682.9	679.4	677.1	676.0	674.9	673.6	672.5
60°	635.7	632.7	629.7	627.2	625.1	623.0	621.0	618.9
62.5°	586.9	583.7	580.5	578.1	576.4	574.8	573.2	571.6
65°	510.1	507.4	504.7	502.8	501.6	500.4	499.2	498.0
67.5°	436.9	434.5	432.3	430.8	430.1	429.4	428.7	427.9
70°	388.4	386.6	384.8	383.3	382.1	380.9	379.8	378.6
72.5°	342.9	340.8	338.8	337.2	336.0	334.8	333.6	332.3
75°	272.1	271.1	270.3	269.2	268.0	266.8	265.6	264.4
77.5°	207.2	206.7	206.2	205.5	204.7	203.8	203.0	202.2
80°	165.8	165.6	165.2	164.8	164.2	163.6	163.0	162.5
82.5°	126.7	126.2	125.6	125.4	125.2	125.1	124.9	124.8
85°	74.6	74.3	74.0	73.5	72.9	72.3	71.7	71.1
87.5°	29.4	29.4	29.5	29.4	28.9	28.5	28.1	27.6
90°	7.1	7.5	7.9	8.4	8.6	8.9	9.1	9.4
92.5°	7.1	7.5	7.9	8.3	8.4	8.5	8.6	8.7
95°	7.1	7.5	7.9	8.2	8.2	8.2	8.2	8.2
97.5°	14.3	11.9	9.4	8.2	8.2	8.2	8.2	8.2
100°	42.0	29.1	16.2	9.6	9.2	8.9	8.5	8.2
102.5°	81.6	79.1	76.7	72.6	66.6	60.8	54.8	49.0
105°	116.1	116.1	116.1	116.1	116.0	115.9	115.8	115.7
107.5°	147.0	147.0	147.0	146.9	146.6	146.4	146.1	145.9
110°	166.9	166.7	166.4	166.3	166.4	166.5	166.6	166.7





TEST NUMBER: P333464-935

CATALOG NUMBER: S125DIW-S1270D470U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	186.8	186.4	186.1	185.9	185.8	185.6	185.5	185.4
115°	216.6	216.3	215.9	215.5	215.0	214.5	214.0	213.4
117.5°	245.5	245.0	244.6	244.3	244.0	243.8	243.6	243.4
120°	264.2	264.0	263.8	263.5	263.0	262.6	262.2	261.7
122.5°	281.9	281.7	281.5	281.2	280.7	280.2	279.7	279.2
125°	307.8	307.5	307.1	306.8	306.5	306.3	306.0	305.7
127.5°	331.5	331.3	331.1	330.7	330.0	329.4	328.7	328.1
130°	346.9	346.6	346.4	346.0	345.6	345.2	344.7	344.3
132.5°	361.4	361.3	361.3	361.0	360.6	360.2	359.7	359.3
135°	382.5	382.4	382.2	381.9	381.3	380.8	380.3	379.8
137.5°	402.3	402.3	402.3	402.2	401.7	401.2	400.8	400.4
140°	414.4	414.6	414.7	414.6	414.1	413.5	413.0	412.5
142.5°	426.3	426.3	426.4	426.1	425.6	425.1	424.6	424.0
145°	443.1	443.2	443.2	443.0	442.5	442.0	441.4	440.9
147.5°	457.4	457.5	457.6	457.4	456.8	456.2	455.5	454.9
150°	466.6	466.7	466.9	466.7	466.0	465.3	464.6	463.9
152.5°	474.7	474.8	475.0	474.8	474.2	473.6	472.9	472.3
155°	485.9	486.1	486.4	486.1	485.4	484.7	484.1	483.4
157.5°	495.1	495.3	495.6	495.4	494.7	494.0	493.4	492.7
160°	500.8	501.2	501.5	501.4	500.7	500.0	499.3	498.6
162.5°	506.1	506.6	507.0	507.0	506.2	505.4	504.6	503.9
165°	512.9	513.4	513.9	513.8	513.2	512.4	511.7	511.0
167.5°	518.0	518.6	519.2	519.2	518.3	517.5	516.8	516.0
170°	520.6	521.3	522.0	521.9	521.2	520.4	519.6	518.8
172.5°	522.6	523.2	523.9	523.8	523.1	522.3	521.5	520.7
175°	524.9	525.6	526.2	526.2	525.5	524.7	523.9	523.1
177.5°	525.8	526.2	526.8	526.8	526.2	525.6	525.0	524.5
180°	525.5	525.5	525.5	525.5	525.5	525.5	525.5	525.5

(END OF REPORT)