

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333353-935

Luminaire Tested: **S125DIW-S375D1050U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333353-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D1050U935-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4453.3 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ···· 90°-270°    - · - · 135°-315°



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	33	32	25
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	25	23	18
4	71	61	53	47	63	55	48	43	44	39	35	33	30	27	23	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	40	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3027	3027	3027	3027
5°	3505	3038	2660	3038
10°	4078	3022	2330	3022
15°	4515	3000	2150	3000
20°	5054	2965	2004	2965
25°	5920	2925	1934	2925
30°	6395	2885	1873	2885
35°	5257	2812	1832	2812
40°	3737	2710	1788	2710
45°	2872	2573	1763	2573
50°	2451	2402	1758	2402
55°	2182	2235	1775	2235
60°	1969	2052	1820	2052
65°	1819	1869	1867	1869
70°	1654	1679	1894	1679
75°	1460	1480	1876	1480
80°	1231	1209	1715	1209
85°	978	867	1386	867



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.1	1.0
10°-20°	134.4	3.0
20°-30°	218.2	4.9
30°-40°	266.1	6.0
40°-50°	242.1	5.4
50°-60°	192.8	4.3
60°-70°	134.3	3.0
70°-80°	71.6	1.6
80°-90°	20.5	0.5
90°-100°	75.1	1.7
100°-110°	221.7	5.0
110°-120°	375.6	8.4
120°-130°	494.3	11.1
130°-140°	553.8	12.4
140°-150°	542.8	12.2
150°-160°	455.9	10.2
160°-170°	303.0	6.8
170°-180°	106.1	2.4
0°-30°	397.6	8.9
0°-40°	663.7	14.9
0°-60°	1098.7	24.7
0°-90°	1325.1	29.8
90°-120°	672.4	15.1
90°-150°	2263.2	50.8
90°-180°	3128.0	70.2
0°-180°	4453.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	541	469	410	469	541	54
15°	675	449	322	449	675	193
25°	831	410	271	410	831	379
35°	667	357	232	357	667	408
45°	314	282	193	282	314	252
55°	194	198	158	198	194	174
65°	119	122	122	122	119	118
75°	58	59	75	59	58	63
85°	13	12	19	12	13	16
90°	21	1	21	1	21	12
95°	75	57	75	57	75	76
105°	216	199	216	199	216	229
115°	380	376	380	376	380	375
125°	552	549	552	549	552	493
135°	716	714	716	714	716	553
145°	868	864	868	864	868	542
155°	989	989	989	989	989	455
165°	1073	1076	1073	1076	1073	302
175°	1114	1118	1114	1118	1114	106
180°	1121	1121	1121	1121	1121	



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	495.8	495.2	494.5	493.3	494.2	491.5	490.3	488.0	485.3	484.3	483.2
5°	540.7	541.7	542.8	538.6	539.0	536.1	529.8	524.6	520.5	515.1	511.3
7.5°	594.9	592.5	592.3	589.6	585.0	581.2	574.5	566.0	557.8	548.4	540.6
10°	621.9	622.2	620.4	617.2	612.2	608.6	599.9	591.5	581.3	569.4	560.9
12.5°	642.3	643.2	640.8	636.5	634.1	626.1	619.2	609.3	597.3	587.7	574.7
15°	675.2	673.0	671.5	666.1	661.9	653.6	642.7	632.2	619.1	607.0	594.9
17.5°	707.0	708.8	705.8	700.9	687.9	678.1	663.5	649.3	632.9	616.6	602.2
20°	735.3	736.9	732.4	723.8	708.3	698.5	679.2	660.9	642.0	621.1	605.2
22.5°	770.7	769.4	763.2	750.2	736.8	718.8	697.8	675.5	651.9	628.3	607.1
25°	830.8	822.4	818.6	802.5	784.9	758.4	729.8	697.2	667.7	636.5	609.4
27.5°	864.2	861.5	857.3	846.1	827.5	799.2	765.4	725.7	684.2	644.7	609.2
30°	857.5	857.9	858.2	854.7	842.7	821.5	787.8	745.1	695.7	651.3	610.4
32.5°	798.2	805.5	812.4	820.6	824.0	819.8	798.8	760.2	709.4	659.0	609.8
35°	666.8	669.1	691.6	713.9	744.1	767.6	783.3	766.1	723.4	665.5	609.0
37.5°	520.0	530.7	546.3	571.4	615.1	654.2	704.5	727.5	713.8	667.6	607.6
40°	443.2	453.2	463.4	489.0	525.8	573.2	630.3	679.0	690.3	660.9	602.8
42.5°	384.1	391.9	403.2	422.5	453.2	495.2	549.7	613.5	652.6	641.5	592.8
45°	314.4	319.3	328.0	343.4	365.7	398.5	446.6	516.3	577.0	597.0	569.0
47.5°	269.1	269.1	275.9	286.4	302.5	330.4	366.0	420.5	485.3	533.3	531.1
50°	243.9	242.9	248.3	257.4	270.2	288.7	322.7	366.3	428.5	482.8	498.0
52.5°	222.2	222.4	225.7	232.5	243.1	258.9	284.3	323.6	376.8	432.6	461.1
55°	193.8	193.0	196.7	201.3	209.1	219.5	237.7	267.8	311.0	365.8	402.9
57.5°	167.6	169.9	171.3	174.5	181.0	188.0	203.4	225.4	259.7	306.8	345.9
60°	152.4	154.5	155.8	158.9	164.1	170.1	182.0	199.9	228.8	269.4	308.2
62.5°	138.7	140.4	140.9	143.7	147.9	153.7	163.1	178.1	201.0	236.4	274.4
65°	119.0	119.0	119.8	122.8	124.8	129.9	137.1	148.0	166.3	194.0	226.4
67.5°	100.0	100.9	100.7	102.0	103.8	107.9	113.0	122.0	135.6	155.8	181.8
70°	87.6	88.3	88.2	89.1	91.1	93.7	97.9	106.4	116.1	133.5	155.8
72.5°	76.4	76.7	76.2	77.5	78.7	80.9	85.7	90.2	99.3	113.9	132.2
75°	58.5	58.9	59.3	60.1	61.3	62.5	64.8	69.4	75.4	86.4	98.1
77.5°	43.8	43.0	44.1	43.9	44.6	45.5	47.6	50.0	54.9	61.9	70.9
80°	33.1	33.2	33.2	33.4	34.4	35.0	36.8	38.6	42.4	47.5	53.9
82.5°	24.1	24.6	24.3	24.7	25.5	25.9	26.9	28.4	30.6	34.7	39.3
85°	13.2	12.1	12.6	12.9	12.9	13.2	13.9	14.6	15.8	17.3	19.1
87.5°	8.0	8.2	8.3	8.1	8.2	8.0	8.4	8.3	8.5	8.9	9.2
90°	20.9	20.3	19.8	19.2	18.6	17.8	16.9	15.9	14.9	13.9	12.6
92.5°	41.2	40.7	40.3	39.9	39.4	38.7	37.4	36.1	34.8	33.5	31.9
95°	75.0	74.6	74.2	73.9	73.4	72.6	71.2	69.9	68.5	67.2	65.3
97.5°	113.7	113.6	113.3	113.0	112.8	112.1	110.8	109.5	108.2	106.9	104.3
100°	143.1	142.7	142.3	141.9	141.5	140.4	138.7	137.0	135.3	133.5	131.0
102.5°	172.4	171.9	171.3	170.7	170.2	169.0	167.1	165.2	163.3	161.4	160.1
105°	216.4	215.8	215.2	214.6	214.0	213.2	212.0	210.9	209.7	208.5	207.3
107.5°	261.4	261.4	261.5	261.5	261.6	261.2	260.7	260.1	259.5	258.9	258.0
110°	294.9	295.1	295.2	295.5	295.7	295.5	294.9	294.3	293.7	293.2	292.6



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.7	328.0	328.4	328.7	329.1	329.1	328.8	328.6	328.3	328.0	327.3
115°	379.5	379.7	379.9	380.0	380.3	380.5	380.6	380.8	381.1	381.3	380.8
117.5°	430.1	430.8	431.6	432.4	433.2	433.5	433.3	433.2	433.1	432.9	432.6
120°	465.0	465.8	466.6	467.4	468.1	468.5	468.5	468.5	468.5	468.5	468.3
122.5°	499.9	500.5	501.1	501.8	502.4	502.7	502.9	503.1	503.3	503.4	502.9
125°	552.2	552.4	552.6	552.8	553.0	553.3	553.7	554.1	554.5	554.8	554.7
127.5°	602.5	602.9	603.3	603.6	604.1	604.3	604.5	604.7	604.9	605.1	604.9
130°	636.0	636.4	636.8	637.1	637.6	637.8	638.0	638.3	638.4	638.6	638.3
132.5°	667.4	668.0	668.5	669.0	669.6	669.9	670.1	670.3	670.5	670.7	670.8
135°	716.3	717.0	717.8	718.6	719.4	719.7	719.7	719.7	719.7	719.7	719.5
137.5°	764.1	765.0	766.0	767.0	767.9	768.3	768.1	767.8	767.6	767.4	767.0
140°	794.8	795.7	796.7	797.7	798.7	798.9	798.6	798.1	797.8	797.4	796.8
142.5°	824.1	825.1	826.0	827.0	827.9	828.4	828.1	827.9	827.6	827.4	826.6
145°	868.1	868.7	869.2	869.8	870.4	870.6	870.6	870.6	870.6	870.6	870.1
147.5°	905.6	906.9	908.2	909.6	910.9	911.3	910.8	910.3	909.9	909.4	909.0
150°	933.5	933.8	934.3	934.6	935.0	935.2	935.2	935.2	935.2	935.2	934.4
152.5°	956.5	957.2	957.9	958.6	959.3	959.4	959.0	958.5	958.0	957.6	957.3
155°	989.3	990.3	991.3	992.2	993.2	993.3	992.6	991.8	991.0	990.2	990.0
157.5°	1016.8	1018.0	1019.3	1020.5	1021.8	1022.1	1021.3	1020.5	1019.8	1019.0	1018.8
160°	1035.5	1036.6	1037.5	1038.5	1039.4	1039.6	1038.8	1038.0	1037.2	1036.5	1036.2
162.5°	1051.6	1052.7	1053.9	1055.0	1056.1	1056.2	1055.2	1054.4	1053.4	1052.5	1052.5
165°	1073.1	1074.3	1075.4	1076.6	1077.7	1077.9	1077.1	1076.3	1075.6	1074.8	1074.6
167.5°	1090.2	1091.4	1092.6	1093.8	1095.0	1095.0	1093.8	1092.7	1091.5	1090.4	1090.4
170°	1099.2	1100.6	1102.0	1103.3	1104.7	1104.7	1103.6	1102.4	1101.3	1100.1	1100.1
172.5°	1106.9	1108.1	1109.3	1110.5	1111.7	1111.7	1110.6	1109.4	1108.3	1107.1	1107.1
175°	1114.0	1115.4	1116.8	1118.2	1119.5	1119.6	1118.4	1117.2	1116.1	1114.9	1114.9
177.5°	1118.3	1119.4	1120.4	1121.5	1122.6	1122.7	1121.8	1120.8	1119.9	1119.0	1119.1
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	482.2	481.1	479.8	477.6	474.9	473.5	471.3	469.8	467.0	464.6	462.0
5°	506.7	501.5	496.8	490.6	483.9	479.5	474.3	468.6	462.5	456.4	449.6
7.5°	532.1	522.9	513.0	502.3	491.8	482.2	472.9	464.0	455.6	445.3	436.7
10°	549.1	537.5	525.2	510.7	496.5	484.2	471.7	460.8	449.6	437.7	427.1
12.5°	566.1	550.8	533.3	517.4	500.4	485.5	470.8	456.8	442.8	429.6	417.2
15°	578.2	564.6	548.5	525.8	506.7	486.2	466.7	448.7	431.7	417.0	401.5
17.5°	586.1	568.6	551.3	529.6	504.5	481.6	459.5	438.8	419.7	401.1	386.2
20°	587.5	569.6	551.5	530.2	504.5	478.3	456.2	431.4	410.9	391.5	373.2
22.5°	587.0	566.7	547.0	525.1	500.1	475.9	449.2	423.9	401.6	382.6	363.5
25°	582.6	560.9	536.1	514.1	489.4	463.7	436.7	410.4	387.8	366.1	347.2
27.5°	578.8	550.7	522.7	497.0	473.1	449.6	423.7	396.8	371.7	349.7	331.9
30°	574.2	543.3	511.9	485.0	460.5	437.7	413.2	386.9	360.7	339.2	320.1
32.5°	570.1	534.1	500.9	471.7	445.7	423.5	401.0	376.0	350.2	328.4	309.3
35°	562.1	520.5	482.4	449.4	421.8	398.9	380.0	356.7	333.0	311.9	293.7
37.5°	551.9	502.6	461.8	427.1	396.8	372.7	355.2	337.3	314.5	294.2	277.7
40°	543.9	489.8	446.6	411.2	379.8	354.7	338.4	321.5	302.6	283.7	266.2
42.5°	533.9	478.4	431.4	393.2	362.1	337.7	320.6	306.3	289.6	271.9	255.7
45°	515.5	457.6	406.7	365.7	334.2	310.1	292.5	281.7	269.1	252.4	238.8
47.5°	488.4	432.7	380.0	337.7	305.2	282.9	266.3	256.0	247.2	234.8	222.3
50°	464.3	414.1	360.7	318.7	286.3	263.8	248.5	239.1	231.6	222.1	211.5
52.5°	437.5	390.6	341.7	300.2	268.1	246.0	231.0	222.7	216.5	209.7	199.2
55°	394.7	354.9	309.5	270.2	240.6	218.9	205.7	198.5	193.4	188.2	181.8
57.5°	347.7	316.5	276.4	240.3	213.0	193.3	181.1	174.1	170.0	167.4	163.7
60°	314.5	287.9	253.3	220.4	193.8	176.2	164.4	158.9	155.6	153.4	150.6
62.5°	283.8	261.9	229.9	199.9	176.6	160.1	149.4	144.1	140.9	139.8	137.6
65°	238.6	221.6	195.2	170.3	150.4	136.3	127.3	122.3	120.4	119.2	119.3
67.5°	193.9	183.7	162.4	141.2	125.3	113.5	106.2	102.5	101.4	99.9	99.9
70°	166.7	158.9	141.0	122.5	108.4	99.3	92.9	88.9	87.9	87.1	87.0
72.5°	142.7	135.9	120.4	105.6	92.8	84.8	79.6	77.1	75.5	75.1	75.0
75°	107.2	103.5	91.1	79.4	70.6	65.1	61.5	59.3	58.1	57.9	58.1
77.5°	76.2	72.9	65.1	56.7	51.2	47.0	44.0	43.2	41.9	41.9	41.8
80°	57.3	55.1	50.1	43.6	39.0	35.4	33.8	32.5	32.0	31.4	32.0
82.5°	41.5	39.2	35.8	31.6	27.8	25.7	24.1	23.7	23.4	23.2	23.2
85°	20.5	20.7	18.7	15.5	13.9	12.7	11.7	11.7	11.5	11.4	11.5
87.5°	9.2	8.7	7.7	7.0	5.9	5.1	4.6	4.5	4.3	4.5	4.9
90°	11.3	9.9	8.5	7.1	5.5	4.0	2.4	0.9	2.4	4.0	5.5
92.5°	30.1	28.5	26.9	25.5	24.4	23.2	22.2	21.1	22.2	23.2	24.4
95°	63.3	61.4	59.4	58.3	57.9	57.5	57.1	56.7	57.1	57.5	57.9
97.5°	101.6	98.9	96.3	94.9	94.7	94.5	94.4	94.2	94.4	94.5	94.7
100°	128.5	125.9	123.4	122.2	122.2	122.2	122.2	122.2	122.2	122.2	122.2
102.5°	158.9	157.6	156.3	155.2	154.5	153.7	152.9	152.1	152.9	153.7	154.5
105°	206.2	205.0	203.9	202.8	201.8	200.9	199.8	198.9	199.8	200.9	201.8
107.5°	257.2	256.2	255.4	254.4	253.5	252.5	251.5	250.6	251.5	252.5	253.5
110°	292.0	291.4	290.8	290.1	289.0	288.1	287.1	286.1	287.1	288.1	289.0





TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.6	325.8	325.1	324.4	324.0	323.5	323.0	322.4	323.0	323.5	324.0
115°	380.5	380.0	379.7	379.1	378.3	377.5	376.8	376.0	376.8	377.5	378.3
117.5°	432.2	431.9	431.5	431.2	430.8	430.4	430.1	429.7	430.1	430.4	430.8
120°	468.1	467.9	467.7	467.1	466.1	465.2	464.3	463.2	464.3	465.2	466.1
122.5°	502.4	501.9	501.4	500.9	500.6	500.2	499.9	499.6	499.9	500.2	500.6
125°	554.5	554.3	554.1	553.4	552.2	551.0	549.9	548.7	549.9	551.0	552.2
127.5°	604.7	604.4	604.2	603.7	603.0	602.4	601.8	601.1	601.8	602.4	603.0
130°	637.8	637.5	637.1	636.4	635.4	634.5	633.4	632.5	633.4	634.5	635.4
132.5°	670.9	671.0	671.1	670.3	668.7	667.1	665.5	663.9	665.5	667.1	668.7
135°	719.4	719.2	718.9	718.3	717.1	715.9	714.8	713.6	714.8	715.9	717.1
137.5°	766.5	766.1	765.7	764.9	763.8	762.7	761.6	760.4	761.6	762.7	763.8
140°	796.3	795.7	795.0	794.3	793.3	792.4	791.3	790.4	791.3	792.4	793.3
142.5°	826.0	825.2	824.5	823.7	822.9	822.1	821.2	820.4	821.2	822.1	822.9
145°	869.5	868.9	868.3	867.6	866.9	866.1	865.3	864.5	865.3	866.1	866.9
147.5°	908.4	908.0	907.6	907.1	906.6	906.3	905.9	905.4	905.9	906.3	906.6
150°	933.7	932.9	932.1	931.9	932.0	932.2	932.5	932.6	932.5	932.2	932.0
152.5°	956.9	956.7	956.3	956.1	955.8	955.5	955.2	954.9	955.2	955.5	955.8
155°	989.8	989.6	989.4	989.3	989.3	989.3	989.3	989.3	989.3	989.3	989.3
157.5°	1018.6	1018.4	1018.2	1018.3	1018.7	1019.2	1019.6	1020.0	1019.6	1019.2	1018.7
160°	1036.0	1035.9	1035.7	1035.9	1036.5	1037.0	1037.6	1038.2	1037.6	1037.0	1036.5
162.5°	1052.4	1052.4	1052.3	1052.5	1052.9	1053.3	1053.8	1054.2	1053.8	1053.3	1052.9
165°	1074.4	1074.3	1074.0	1074.1	1074.5	1074.9	1075.3	1075.7	1075.3	1074.9	1074.5
167.5°	1090.4	1090.4	1090.4	1090.7	1091.5	1092.3	1093.0	1093.8	1093.0	1092.3	1091.5
170°	1100.1	1100.1	1100.1	1100.5	1101.3	1102.1	1102.9	1103.6	1102.9	1102.1	1101.3
172.5°	1107.1	1107.1	1107.1	1107.5	1108.3	1109.1	1109.8	1110.6	1109.8	1109.1	1108.3
175°	1114.9	1114.9	1114.9	1115.3	1116.1	1116.9	1117.7	1118.4	1117.7	1116.9	1116.1
177.5°	1119.3	1119.4	1119.6	1120.0	1120.6	1121.2	1121.8	1122.5	1121.8	1121.2	1120.6
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	460.6	458.8	457.4	454.3	452.5	450.1	448.2	450.3	448.1	449.0	447.5
5°	446.3	440.7	436.7	430.9	425.9	421.4	418.0	417.4	415.8	415.0	412.6
7.5°	429.0	422.0	415.2	407.6	401.2	394.8	390.6	387.2	385.0	381.9	379.9
10°	418.8	409.4	401.5	392.4	384.4	377.4	371.9	369.0	366.4	362.7	361.3
12.5°	406.2	396.6	386.8	377.0	369.4	361.6	356.9	352.7	350.9	346.6	346.2
15°	391.2	376.6	367.0	357.1	346.6	340.2	336.2	331.7	329.7	326.7	324.5
17.5°	373.2	360.2	348.3	337.9	328.9	323.6	318.6	315.5	312.0	310.0	306.5
20°	360.1	347.8	335.8	324.9	317.9	311.8	307.8	304.8	301.2	300.2	296.6
22.5°	349.1	335.5	324.1	314.9	307.3	300.3	296.0	293.9	291.5	288.4	287.7
25°	331.2	317.1	307.4	298.3	291.4	285.1	282.1	279.6	277.2	274.9	274.1
27.5°	315.8	303.2	291.6	283.4	277.4	271.6	269.1	265.9	264.2	262.3	260.2
30°	305.0	292.1	281.9	274.0	267.6	262.4	259.6	257.4	255.9	254.3	253.0
32.5°	293.9	281.9	272.1	264.2	257.9	254.0	251.5	249.9	248.2	246.3	244.8
35°	279.1	266.0	256.4	249.7	244.7	241.7	238.9	237.5	235.6	235.6	233.9
37.5°	262.5	251.2	242.7	236.6	232.1	229.5	226.4	225.5	224.2	223.3	222.8
40°	252.7	242.1	234.2	228.0	223.3	221.0	218.6	217.1	216.3	215.2	214.9
42.5°	242.5	232.4	224.8	219.1	214.9	213.1	210.9	209.7	208.1	206.8	206.6
45°	227.0	217.2	210.3	205.7	202.2	199.9	198.5	196.1	195.4	193.8	193.6
47.5°	212.3	202.9	196.1	192.3	189.2	187.4	185.3	182.9	181.9	181.2	181.1
50°	201.3	192.8	186.4	182.9	179.9	177.3	175.0	173.5	172.9	172.9	173.3
52.5°	190.2	182.9	177.5	173.1	170.3	167.6	165.5	164.5	163.7	164.6	165.3
55°	173.9	166.5	162.6	158.3	155.6	152.4	151.4	151.0	150.4	152.0	152.8
57.5°	156.6	151.4	146.8	142.7	140.2	138.3	137.0	136.7	137.8	138.6	141.2
60°	145.6	139.7	135.5	132.3	129.3	128.1	127.7	127.3	128.1	130.3	133.7
62.5°	133.5	128.7	124.2	121.8	119.6	117.6	117.5	117.8	119.3	121.9	125.3
65°	115.8	111.6	108.7	105.8	104.0	102.9	103.2	104.0	105.8	109.3	113.0
67.5°	97.7	94.9	92.2	90.0	88.3	88.3	88.7	89.9	92.0	95.8	99.3
70°	86.2	83.0	80.8	79.8	78.4	77.6	78.8	80.8	82.6	86.2	89.1
72.5°	74.6	71.8	70.1	69.4	68.8	68.2	68.6	70.8	73.2	76.7	80.2
75°	57.3	56.3	55.1	54.3	53.7	54.2	54.5	56.5	58.5	62.3	66.2
77.5°	41.8	40.8	40.0	39.9	39.5	39.8	40.9	42.4	44.3	47.0	50.0
80°	31.6	31.3	30.8	30.7	30.7	30.8	32.5	33.4	35.2	37.8	40.2
82.5°	23.1	22.8	22.7	22.6	22.8	22.9	23.8	25.1	26.6	28.6	30.7
85°	12.1	11.7	12.3	12.6	12.1	12.7	13.2	13.9	14.6	15.5	16.5
87.5°	5.4	6.0	6.1	6.5	6.8	7.4	7.4	8.3	8.8	9.3	9.3
90°	7.1	8.5	9.9	11.3	12.6	13.9	14.9	15.9	16.9	17.8	18.6
92.5°	25.5	26.9	28.5	30.1	31.9	33.5	34.8	36.1	37.4	38.7	39.4
95°	58.3	59.4	61.4	63.3	65.3	67.2	68.5	69.9	71.2	72.6	73.4
97.5°	94.9	96.3	98.9	101.6	104.3	106.9	108.2	109.5	110.8	112.1	112.8
100°	122.2	123.4	125.9	128.5	131.0	133.5	135.3	137.0	138.7	140.4	141.5
102.5°	155.2	156.3	157.6	158.9	160.1	161.4	163.3	165.2	167.1	169.0	170.2
105°	202.8	203.9	205.0	206.2	207.3	208.5	209.7	210.9	212.0	213.2	214.0
107.5°	254.4	255.4	256.2	257.2	258.0	258.9	259.5	260.1	260.7	261.2	261.6
110°	290.1	290.8	291.4	292.0	292.6	293.2	293.7	294.3	294.9	295.5	295.7



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	324.4	325.1	325.8	326.6	327.3	328.0	328.3	328.6	328.8	329.1	329.1
115°	379.1	379.7	380.0	380.5	380.8	381.3	381.1	380.8	380.6	380.5	380.3
117.5°	431.2	431.5	431.9	432.2	432.6	432.9	433.1	433.2	433.3	433.5	433.2
120°	467.1	467.7	467.9	468.1	468.3	468.5	468.5	468.5	468.5	468.5	468.1
122.5°	500.9	501.4	501.9	502.4	502.9	503.4	503.3	503.1	502.9	502.7	502.4
125°	553.4	554.1	554.3	554.5	554.7	554.8	554.5	554.1	553.7	553.3	553.0
127.5°	603.7	604.2	604.4	604.7	604.9	605.1	604.9	604.7	604.5	604.3	604.1
130°	636.4	637.1	637.5	637.8	638.3	638.6	638.4	638.3	638.0	637.8	637.6
132.5°	670.3	671.1	671.0	670.9	670.8	670.7	670.5	670.3	670.1	669.9	669.6
135°	718.3	718.9	719.2	719.4	719.5	719.7	719.7	719.7	719.7	719.7	719.4
137.5°	764.9	765.7	766.1	766.5	767.0	767.4	767.6	767.8	768.1	768.3	767.9
140°	794.3	795.0	795.7	796.3	796.8	797.4	797.8	798.1	798.6	798.9	798.7
142.5°	823.7	824.5	825.2	826.0	826.6	827.4	827.6	827.9	828.1	828.4	827.9
145°	867.6	868.3	868.9	869.5	870.1	870.6	870.6	870.6	870.6	870.6	870.4
147.5°	907.1	907.6	908.0	908.4	909.0	909.4	909.9	910.3	910.8	911.3	910.9
150°	931.9	932.1	932.9	933.7	934.4	935.2	935.2	935.2	935.2	935.2	935.0
152.5°	956.1	956.3	956.7	956.9	957.3	957.6	958.0	958.5	959.0	959.4	959.3
155°	989.3	989.4	989.6	989.8	990.0	990.2	991.0	991.8	992.6	993.3	993.2
157.5°	1018.3	1018.2	1018.4	1018.6	1018.8	1019.0	1019.8	1020.5	1021.3	1022.1	1021.8
160°	1035.9	1035.7	1035.9	1036.0	1036.2	1036.5	1037.2	1038.0	1038.8	1039.6	1039.4
162.5°	1052.5	1052.3	1052.4	1052.4	1052.5	1052.5	1053.4	1054.4	1055.2	1056.2	1056.1
165°	1074.1	1074.0	1074.3	1074.4	1074.6	1074.8	1075.6	1076.3	1077.1	1077.9	1077.7
167.5°	1090.7	1090.4	1090.4	1090.4	1090.4	1090.4	1091.5	1092.7	1093.8	1095.0	1095.0
170°	1100.5	1100.1	1100.1	1100.1	1100.1	1100.1	1101.3	1102.4	1103.6	1104.7	1104.7
172.5°	1107.5	1107.1	1107.1	1107.1	1107.1	1107.1	1108.3	1109.4	1110.6	1111.7	1111.7
175°	1115.3	1114.9	1114.9	1114.9	1114.9	1114.9	1116.1	1117.2	1118.4	1119.6	1119.5
177.5°	1120.0	1119.6	1119.4	1119.3	1119.1	1119.0	1119.9	1120.8	1121.8	1122.7	1122.6
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	446.6	447.7	446.8	448.1	446.8	447.7	446.6	447.5	449.0	448.1	450.3
5°	411.6	409.8	411.0	410.3	411.0	409.8	411.6	412.6	415.0	415.8	417.4
7.5°	379.4	377.6	375.7	374.7	375.7	377.6	379.4	379.9	381.9	385.0	387.2
10°	359.1	356.9	356.7	355.3	356.7	356.9	359.1	361.3	362.7	366.4	369.0
12.5°	344.3	342.2	340.0	339.4	340.0	342.2	344.3	346.2	346.6	350.9	352.7
15°	323.3	321.7	320.3	321.5	320.3	321.7	323.3	324.5	326.7	329.7	331.7
17.5°	305.8	304.5	304.3	302.8	304.3	304.5	305.8	306.5	310.0	312.0	315.5
20°	294.8	293.9	294.3	291.6	294.3	293.9	294.8	296.6	300.2	301.2	304.8
22.5°	286.1	284.1	283.9	283.4	283.9	284.1	286.1	287.7	288.4	291.5	293.9
25°	272.3	271.4	270.4	271.4	270.4	271.4	272.3	274.1	274.9	277.2	279.6
27.5°	260.4	259.2	258.9	259.1	258.9	259.2	260.4	260.2	262.3	264.2	265.9
30°	253.0	251.1	251.2	251.1	251.2	251.1	253.0	253.0	254.3	255.9	257.4
32.5°	245.1	243.7	243.5	243.1	243.5	243.7	245.1	244.8	246.3	248.2	249.9
35°	233.3	233.3	232.4	232.4	232.4	233.3	233.3	233.9	235.6	235.6	237.5
37.5°	222.3	222.1	221.5	221.6	221.5	222.1	222.3	222.8	223.3	224.2	225.5
40°	214.0	213.9	213.3	212.1	213.3	213.9	214.0	214.9	215.2	216.3	217.1
42.5°	206.1	205.4	205.2	204.7	205.2	205.4	206.1	206.6	206.8	208.1	209.7
45°	193.6	193.6	193.2	193.0	193.2	193.6	193.6	193.6	193.8	195.4	196.1
47.5°	181.4	181.8	182.5	182.4	182.5	181.8	181.4	181.1	181.2	181.9	182.9
50°	174.1	174.3	174.9	175.0	174.9	174.3	174.1	173.3	172.9	172.9	173.5
52.5°	166.0	167.1	167.9	167.7	167.9	167.1	166.0	165.3	164.6	163.7	164.5
55°	154.5	156.0	157.4	157.6	157.4	156.0	154.5	152.8	152.0	150.4	151.0
57.5°	143.4	145.3	146.7	147.2	146.7	145.3	143.4	141.2	138.6	137.8	136.7
60°	135.7	138.3	140.1	140.9	140.1	138.3	135.7	133.7	130.3	128.1	127.3
62.5°	128.4	131.3	133.0	133.2	133.0	131.3	128.4	125.3	121.9	119.3	117.8
65°	116.4	119.3	121.0	122.2	121.0	119.3	116.4	113.0	109.3	105.8	104.0
67.5°	103.5	106.5	108.2	109.2	108.2	106.5	103.5	99.3	95.8	92.0	89.9
70°	94.1	97.1	99.4	100.3	99.4	97.1	94.1	89.1	86.2	82.6	80.8
72.5°	84.9	87.6	89.5	90.4	89.5	87.6	84.9	80.2	76.7	73.2	70.8
75°	68.8	72.4	74.2	75.2	74.2	72.4	68.8	66.2	62.3	58.5	56.5
77.5°	53.0	56.3	57.4	57.9	57.4	56.3	53.0	50.0	47.0	44.3	42.4
80°	42.5	44.6	46.0	46.1	46.0	44.6	42.5	40.2	37.8	35.2	33.4
82.5°	32.7	34.4	34.8	35.3	34.8	34.4	32.7	30.7	28.6	26.6	25.1
85°	17.9	18.7	18.9	18.7	18.9	18.7	17.9	16.5	15.5	14.6	13.9
87.5°	9.7	9.6	9.8	10.2	9.8	9.6	9.7	9.3	9.3	8.8	8.3
90°	19.2	19.8	20.3	20.9	20.3	19.8	19.2	18.6	17.8	16.9	15.9
92.5°	39.9	40.3	40.7	41.2	40.7	40.3	39.9	39.4	38.7	37.4	36.1
95°	73.9	74.2	74.6	75.0	74.6	74.2	73.9	73.4	72.6	71.2	69.9
97.5°	113.0	113.3	113.6	113.7	113.6	113.3	113.0	112.8	112.1	110.8	109.5
100°	141.9	142.3	142.7	143.1	142.7	142.3	141.9	141.5	140.4	138.7	137.0
102.5°	170.7	171.3	171.9	172.4	171.9	171.3	170.7	170.2	169.0	167.1	165.2
105°	214.6	215.2	215.8	216.4	215.8	215.2	214.6	214.0	213.2	212.0	210.9
107.5°	261.5	261.5	261.4	261.4	261.4	261.5	261.5	261.6	261.2	260.7	260.1
110°	295.5	295.2	295.1	294.9	295.1	295.2	295.5	295.7	295.5	294.9	294.3



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	328.7	328.4	328.0	327.7	328.0	328.4	328.7	329.1	329.1	328.8	328.6
115°	380.0	379.9	379.7	379.5	379.7	379.9	380.0	380.3	380.5	380.6	380.8
117.5°	432.4	431.6	430.8	430.1	430.8	431.6	432.4	433.2	433.5	433.3	433.2
120°	467.4	466.6	465.8	465.0	465.8	466.6	467.4	468.1	468.5	468.5	468.5
122.5°	501.8	501.1	500.5	499.9	500.5	501.1	501.8	502.4	502.7	502.9	503.1
125°	552.8	552.6	552.4	552.2	552.4	552.6	552.8	553.0	553.3	553.7	554.1
127.5°	603.6	603.3	602.9	602.5	602.9	603.3	603.6	604.1	604.3	604.5	604.7
130°	637.1	636.8	636.4	636.0	636.4	636.8	637.1	637.6	637.8	638.0	638.3
132.5°	669.0	668.5	668.0	667.4	668.0	668.5	669.0	669.6	669.9	670.1	670.3
135°	718.6	717.8	717.0	716.3	717.0	717.8	718.6	719.4	719.7	719.7	719.7
137.5°	767.0	766.0	765.0	764.1	765.0	766.0	767.0	767.9	768.3	768.1	767.8
140°	797.7	796.7	795.7	794.8	795.7	796.7	797.7	798.7	798.9	798.6	798.1
142.5°	827.0	826.0	825.1	824.1	825.1	826.0	827.0	827.9	828.4	828.1	827.9
145°	869.8	869.2	868.7	868.1	868.7	869.2	869.8	870.4	870.6	870.6	870.6
147.5°	909.6	908.2	906.9	905.6	906.9	908.2	909.6	910.9	911.3	910.8	910.3
150°	934.6	934.3	933.8	933.5	933.8	934.3	934.6	935.0	935.2	935.2	935.2
152.5°	958.6	957.9	957.2	956.5	957.2	957.9	958.6	959.3	959.4	959.0	958.5
155°	992.2	991.3	990.3	989.3	990.3	991.3	992.2	993.2	993.3	992.6	991.8
157.5°	1020.5	1019.3	1018.0	1016.8	1018.0	1019.3	1020.5	1021.8	1022.1	1021.3	1020.5
160°	1038.5	1037.5	1036.6	1035.5	1036.6	1037.5	1038.5	1039.4	1039.6	1038.8	1038.0
162.5°	1055.0	1053.9	1052.7	1051.6	1052.7	1053.9	1055.0	1056.1	1056.2	1055.2	1054.4
165°	1076.6	1075.4	1074.3	1073.1	1074.3	1075.4	1076.6	1077.7	1077.9	1077.1	1076.3
167.5°	1093.8	1092.6	1091.4	1090.2	1091.4	1092.6	1093.8	1095.0	1095.0	1093.8	1092.7
170°	1103.3	1102.0	1100.6	1099.2	1100.6	1102.0	1103.3	1104.7	1104.7	1103.6	1102.4
172.5°	1110.5	1109.3	1108.1	1106.9	1108.1	1109.3	1110.5	1111.7	1111.7	1110.6	1109.4
175°	1118.2	1116.8	1115.4	1114.0	1115.4	1116.8	1118.2	1119.5	1119.6	1118.4	1117.2
177.5°	1121.5	1120.4	1119.4	1118.3	1119.4	1120.4	1121.5	1122.6	1122.7	1121.8	1120.8
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	448.2	450.1	452.5	454.3	457.4	458.8	460.6	462.0	464.6	467.0	469.8
5°	418.0	421.4	425.9	430.9	436.7	440.7	446.3	449.6	456.4	462.5	468.6
7.5°	390.6	394.8	401.2	407.6	415.2	422.0	429.0	436.7	445.3	455.6	464.0
10°	371.9	377.4	384.4	392.4	401.5	409.4	418.8	427.1	437.7	449.6	460.8
12.5°	356.9	361.6	369.4	377.0	386.8	396.6	406.2	417.2	429.6	442.8	456.8
15°	336.2	340.2	346.6	357.1	367.0	376.6	391.2	401.5	417.0	431.7	448.7
17.5°	318.6	323.6	328.9	337.9	348.3	360.2	373.2	386.2	401.1	419.7	438.8
20°	307.8	311.8	317.9	324.9	335.8	347.8	360.1	373.2	391.5	410.9	431.4
22.5°	296.0	300.3	307.3	314.9	324.1	335.5	349.1	363.5	382.6	401.6	423.9
25°	282.1	285.1	291.4	298.3	307.4	317.1	331.2	347.2	366.1	387.8	410.4
27.5°	269.1	271.6	277.4	283.4	291.6	303.2	315.8	331.9	349.7	371.7	396.8
30°	259.6	262.4	267.6	274.0	281.9	292.1	305.0	320.1	339.2	360.7	386.9
32.5°	251.5	254.0	257.9	264.2	272.1	281.9	293.9	309.3	328.4	350.2	376.0
35°	238.9	241.7	244.7	249.7	256.4	266.0	279.1	293.7	311.9	333.0	356.7
37.5°	226.4	229.5	232.1	236.6	242.7	251.2	262.5	277.7	294.2	314.5	337.3
40°	218.6	221.0	223.3	228.0	234.2	242.1	252.7	266.2	283.7	302.6	321.5
42.5°	210.9	213.1	214.9	219.1	224.8	232.4	242.5	255.7	271.9	289.6	306.3
45°	198.5	199.9	202.2	205.7	210.3	217.2	227.0	238.8	252.4	269.1	281.7
47.5°	185.3	187.4	189.2	192.3	196.1	202.9	212.3	222.3	234.8	247.2	256.0
50°	175.0	177.3	179.9	182.9	186.4	192.8	201.3	211.5	222.1	231.6	239.1
52.5°	165.5	167.6	170.3	173.1	177.5	182.9	190.2	199.2	209.7	216.5	222.7
55°	151.4	152.4	155.6	158.3	162.6	166.5	173.9	181.8	188.2	193.4	198.5
57.5°	137.0	138.3	140.2	142.7	146.8	151.4	156.6	163.7	167.4	170.0	174.1
60°	127.7	128.1	129.3	132.3	135.5	139.7	145.6	150.6	153.4	155.6	158.9
62.5°	117.5	117.6	119.6	121.8	124.2	128.7	133.5	137.6	139.8	140.9	144.1
65°	103.2	102.9	104.0	105.8	108.7	111.6	115.8	119.3	119.2	120.4	122.3
67.5°	88.7	88.3	88.3	90.0	92.2	94.9	97.7	99.9	99.9	101.4	102.5
70°	78.8	77.6	78.4	79.8	80.8	83.0	86.2	87.0	87.1	87.9	88.9
72.5°	68.6	68.2	68.8	69.4	70.1	71.8	74.6	75.0	75.1	75.5	77.1
75°	54.5	54.2	53.7	54.3	55.1	56.3	57.3	58.1	57.9	58.1	59.3
77.5°	40.9	39.8	39.5	39.9	40.0	40.8	41.8	41.8	41.9	41.9	43.2
80°	32.5	30.8	30.7	30.7	30.8	31.3	31.6	32.0	31.4	32.0	32.5
82.5°	23.8	22.9	22.8	22.6	22.7	22.8	23.1	23.2	23.2	23.4	23.7
85°	13.2	12.7	12.1	12.6	12.3	11.7	12.1	11.5	11.4	11.5	11.7
87.5°	7.4	7.4	6.8	6.5	6.1	6.0	5.4	4.9	4.5	4.3	4.5
90°	14.9	13.9	12.6	11.3	9.9	8.5	7.1	5.5	4.0	2.4	0.9
92.5°	34.8	33.5	31.9	30.1	28.5	26.9	25.5	24.4	23.2	22.2	21.1
95°	68.5	67.2	65.3	63.3	61.4	59.4	58.3	57.9	57.5	57.1	56.7
97.5°	108.2	106.9	104.3	101.6	98.9	96.3	94.9	94.7	94.5	94.4	94.2
100°	135.3	133.5	131.0	128.5	125.9	123.4	122.2	122.2	122.2	122.2	122.2
102.5°	163.3	161.4	160.1	158.9	157.6	156.3	155.2	154.5	153.7	152.9	152.1
105°	209.7	208.5	207.3	206.2	205.0	203.9	202.8	201.8	200.9	199.8	198.9
107.5°	259.5	258.9	258.0	257.2	256.2	255.4	254.4	253.5	252.5	251.5	250.6
110°	293.7	293.2	292.6	292.0	291.4	290.8	290.1	289.0	288.1	287.1	286.1



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	328.3	328.0	327.3	326.6	325.8	325.1	324.4	324.0	323.5	323.0	322.4
115°	381.1	381.3	380.8	380.5	380.0	379.7	379.1	378.3	377.5	376.8	376.0
117.5°	433.1	432.9	432.6	432.2	431.9	431.5	431.2	430.8	430.4	430.1	429.7
120°	468.5	468.5	468.3	468.1	467.9	467.7	467.1	466.1	465.2	464.3	463.2
122.5°	503.3	503.4	502.9	502.4	501.9	501.4	500.9	500.6	500.2	499.9	499.6
125°	554.5	554.8	554.7	554.5	554.3	554.1	553.4	552.2	551.0	549.9	548.7
127.5°	604.9	605.1	604.9	604.7	604.4	604.2	603.7	603.0	602.4	601.8	601.1
130°	638.4	638.6	638.3	637.8	637.5	637.1	636.4	635.4	634.5	633.4	632.5
132.5°	670.5	670.7	670.8	670.9	671.0	671.1	670.3	668.7	667.1	665.5	663.9
135°	719.7	719.7	719.5	719.4	719.2	718.9	718.3	717.1	715.9	714.8	713.6
137.5°	767.6	767.4	767.0	766.5	766.1	765.7	764.9	763.8	762.7	761.6	760.4
140°	797.8	797.4	796.8	796.3	795.7	795.0	794.3	793.3	792.4	791.3	790.4
142.5°	827.6	827.4	826.6	826.0	825.2	824.5	823.7	822.9	822.1	821.2	820.4
145°	870.6	870.6	870.1	869.5	868.9	868.3	867.6	866.9	866.1	865.3	864.5
147.5°	909.9	909.4	909.0	908.4	908.0	907.6	907.1	906.6	906.3	905.9	905.4
150°	935.2	935.2	934.4	933.7	932.9	932.1	931.9	932.0	932.2	932.5	932.6
152.5°	958.0	957.6	957.3	956.9	956.7	956.3	956.1	955.8	955.5	955.2	954.9
155°	991.0	990.2	990.0	989.8	989.6	989.4	989.3	989.3	989.3	989.3	989.3
157.5°	1019.8	1019.0	1018.8	1018.6	1018.4	1018.2	1018.3	1018.7	1019.2	1019.6	1020.0
160°	1037.2	1036.5	1036.2	1036.0	1035.9	1035.7	1035.9	1036.5	1037.0	1037.6	1038.2
162.5°	1053.4	1052.5	1052.5	1052.4	1052.4	1052.3	1052.5	1052.9	1053.3	1053.8	1054.2
165°	1075.6	1074.8	1074.6	1074.4	1074.3	1074.0	1074.1	1074.5	1074.9	1075.3	1075.7
167.5°	1091.5	1090.4	1090.4	1090.4	1090.4	1090.4	1090.7	1091.5	1092.3	1093.0	1093.8
170°	1101.3	1100.1	1100.1	1100.1	1100.1	1100.1	1100.5	1101.3	1102.1	1102.9	1103.6
172.5°	1108.3	1107.1	1107.1	1107.1	1107.1	1107.1	1107.5	1108.3	1109.1	1109.8	1110.6
175°	1116.1	1114.9	1114.9	1114.9	1114.9	1114.9	1115.3	1116.1	1116.9	1117.7	1118.4
177.5°	1119.9	1119.0	1119.1	1119.3	1119.4	1119.6	1120.0	1120.6	1121.2	1121.8	1122.5
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	471.3	473.5	474.9	477.6	479.8	481.1	482.2	483.2	484.3	485.3	488.0
5°	474.3	479.5	483.9	490.6	496.8	501.5	506.7	511.3	515.1	520.5	524.6
7.5°	472.9	482.2	491.8	502.3	513.0	522.9	532.1	540.6	548.4	557.8	566.0
10°	471.7	484.2	496.5	510.7	525.2	537.5	549.1	560.9	569.4	581.3	591.5
12.5°	470.8	485.5	500.4	517.4	533.3	550.8	566.1	574.7	587.7	597.3	609.3
15°	466.7	486.2	506.7	525.8	548.5	564.6	578.2	594.9	607.0	619.1	632.2
17.5°	459.5	481.6	504.5	529.6	551.3	568.6	586.1	602.2	616.6	632.9	649.3
20°	456.2	478.3	504.5	530.2	551.5	569.6	587.5	605.2	621.1	642.0	660.9
22.5°	449.2	475.9	500.1	525.1	547.0	566.7	587.0	607.1	628.3	651.9	675.5
25°	436.7	463.7	489.4	514.1	536.1	560.9	582.6	609.4	636.5	667.7	697.2
27.5°	423.7	449.6	473.1	497.0	522.7	550.7	578.8	609.2	644.7	684.2	725.7
30°	413.2	437.7	460.5	485.0	511.9	543.3	574.2	610.4	651.3	695.7	745.1
32.5°	401.0	423.5	445.7	471.7	500.9	534.1	570.1	609.8	659.0	709.4	760.2
35°	380.0	398.9	421.8	449.4	482.4	520.5	562.1	609.0	665.5	723.4	766.1
37.5°	355.2	372.7	396.8	427.1	461.8	502.6	551.9	607.6	667.6	713.8	727.5
40°	338.4	354.7	379.8	411.2	446.6	489.8	543.9	602.8	660.9	690.3	679.0
42.5°	320.6	337.7	362.1	393.2	431.4	478.4	533.9	592.8	641.5	652.6	613.5
45°	292.5	310.1	334.2	365.7	406.7	457.6	515.5	569.0	597.0	577.0	516.3
47.5°	266.3	282.9	305.2	337.7	380.0	432.7	488.4	531.1	533.3	485.3	420.5
50°	248.5	263.8	286.3	318.7	360.7	414.1	464.3	498.0	482.8	428.5	366.3
52.5°	231.0	246.0	268.1	300.2	341.7	390.6	437.5	461.1	432.6	376.8	323.6
55°	205.7	218.9	240.6	270.2	309.5	354.9	394.7	402.9	365.8	311.0	267.8
57.5°	181.1	193.3	213.0	240.3	276.4	316.5	347.7	345.9	306.8	259.7	225.4
60°	164.4	176.2	193.8	220.4	253.3	287.9	314.5	308.2	269.4	228.8	199.9
62.5°	149.4	160.1	176.6	199.9	229.9	261.9	283.8	274.4	236.4	201.0	178.1
65°	127.3	136.3	150.4	170.3	195.2	221.6	238.6	226.4	194.0	166.3	148.0
67.5°	106.2	113.5	125.3	141.2	162.4	183.7	193.9	181.8	155.8	135.6	122.0
70°	92.9	99.3	108.4	122.5	141.0	158.9	166.7	155.8	133.5	116.1	106.4
72.5°	79.6	84.8	92.8	105.6	120.4	135.9	142.7	132.2	113.9	99.3	90.2
75°	61.5	65.1	70.6	79.4	91.1	103.5	107.2	98.1	86.4	75.4	69.4
77.5°	44.0	47.0	51.2	56.7	65.1	72.9	76.2	70.9	61.9	54.9	50.0
80°	33.8	35.4	39.0	43.6	50.1	55.1	57.3	53.9	47.5	42.4	38.6
82.5°	24.1	25.7	27.8	31.6	35.8	39.2	41.5	39.3	34.7	30.6	28.4
85°	11.7	12.7	13.9	15.5	18.7	20.7	20.5	19.1	17.3	15.8	14.6
87.5°	4.6	5.1	5.9	7.0	7.7	8.7	9.2	9.2	8.9	8.5	8.3
90°	2.4	4.0	5.5	7.1	8.5	9.9	11.3	12.6	13.9	14.9	15.9
92.5°	22.2	23.2	24.4	25.5	26.9	28.5	30.1	31.9	33.5	34.8	36.1
95°	57.1	57.5	57.9	58.3	59.4	61.4	63.3	65.3	67.2	68.5	69.9
97.5°	94.4	94.5	94.7	94.9	96.3	98.9	101.6	104.3	106.9	108.2	109.5
100°	122.2	122.2	122.2	122.2	123.4	125.9	128.5	131.0	133.5	135.3	137.0
102.5°	152.9	153.7	154.5	155.2	156.3	157.6	158.9	160.1	161.4	163.3	165.2
105°	199.8	200.9	201.8	202.8	203.9	205.0	206.2	207.3	208.5	209.7	210.9
107.5°	251.5	252.5	253.5	254.4	255.4	256.2	257.2	258.0	258.9	259.5	260.1
110°	287.1	288.1	289.0	290.1	290.8	291.4	292.0	292.6	293.2	293.7	294.3





TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	323.0	323.5	324.0	324.4	325.1	325.8	326.6	327.3	328.0	328.3	328.6
115°	376.8	377.5	378.3	379.1	379.7	380.0	380.5	380.8	381.3	381.1	380.8
117.5°	430.1	430.4	430.8	431.2	431.5	431.9	432.2	432.6	432.9	433.1	433.2
120°	464.3	465.2	466.1	467.1	467.7	467.9	468.1	468.3	468.5	468.5	468.5
122.5°	499.9	500.2	500.6	500.9	501.4	501.9	502.4	502.9	503.4	503.3	503.1
125°	549.9	551.0	552.2	553.4	554.1	554.3	554.5	554.7	554.8	554.5	554.1
127.5°	601.8	602.4	603.0	603.7	604.2	604.4	604.7	604.9	605.1	604.9	604.7
130°	633.4	634.5	635.4	636.4	637.1	637.5	637.8	638.3	638.6	638.4	638.3
132.5°	665.5	667.1	668.7	670.3	671.1	671.0	670.9	670.8	670.7	670.5	670.3
135°	714.8	715.9	717.1	718.3	718.9	719.2	719.4	719.5	719.7	719.7	719.7
137.5°	761.6	762.7	763.8	764.9	765.7	766.1	766.5	767.0	767.4	767.6	767.8
140°	791.3	792.4	793.3	794.3	795.0	795.7	796.3	796.8	797.4	797.8	798.1
142.5°	821.2	822.1	822.9	823.7	824.5	825.2	826.0	826.6	827.4	827.6	827.9
145°	865.3	866.1	866.9	867.6	868.3	868.9	869.5	870.1	870.6	870.6	870.6
147.5°	905.9	906.3	906.6	907.1	907.6	908.0	908.4	909.0	909.4	909.9	910.3
150°	932.5	932.2	932.0	931.9	932.1	932.9	933.7	934.4	935.2	935.2	935.2
152.5°	955.2	955.5	955.8	956.1	956.3	956.7	956.9	957.3	957.6	958.0	958.5
155°	989.3	989.3	989.3	989.3	989.4	989.6	989.8	990.0	990.2	991.0	991.8
157.5°	1019.6	1019.2	1018.7	1018.3	1018.2	1018.4	1018.6	1018.8	1019.0	1019.8	1020.5
160°	1037.6	1037.0	1036.5	1035.9	1035.7	1035.9	1036.0	1036.2	1036.5	1037.2	1038.0
162.5°	1053.8	1053.3	1052.9	1052.5	1052.3	1052.4	1052.4	1052.5	1052.5	1053.4	1054.4
165°	1075.3	1074.9	1074.5	1074.1	1074.0	1074.3	1074.4	1074.6	1074.8	1075.6	1076.3
167.5°	1093.0	1092.3	1091.5	1090.7	1090.4	1090.4	1090.4	1090.4	1090.4	1091.5	1092.7
170°	1102.9	1102.1	1101.3	1100.5	1100.1	1100.1	1100.1	1100.1	1100.1	1101.3	1102.4
172.5°	1109.8	1109.1	1108.3	1107.5	1107.1	1107.1	1107.1	1107.1	1107.1	1108.3	1109.4
175°	1117.7	1116.9	1116.1	1115.3	1114.9	1114.9	1114.9	1114.9	1114.9	1116.1	1117.2
177.5°	1121.8	1121.2	1120.6	1120.0	1119.6	1119.4	1119.3	1119.1	1119.0	1119.9	1120.8
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	490.3	491.5	494.2	493.3	494.5	495.2	495.8
5°	529.8	536.1	539.0	538.6	542.8	541.7	540.7
7.5°	574.5	581.2	585.0	589.6	592.3	592.5	594.9
10°	599.9	608.6	612.2	617.2	620.4	622.2	621.9
12.5°	619.2	626.1	634.1	636.5	640.8	643.2	642.3
15°	642.7	653.6	661.9	666.1	671.5	673.0	675.2
17.5°	663.5	678.1	687.9	700.9	705.8	708.8	707.0
20°	679.2	698.5	708.3	723.8	732.4	736.9	735.3
22.5°	697.8	718.8	736.8	750.2	763.2	769.4	770.7
25°	729.8	758.4	784.9	802.5	818.6	822.4	830.8
27.5°	765.4	799.2	827.5	846.1	857.3	861.5	864.2
30°	787.8	821.5	842.7	854.7	858.2	857.9	857.5
32.5°	798.8	819.8	824.0	820.6	812.4	805.5	798.2
35°	783.3	767.6	744.1	713.9	691.6	669.1	666.8
37.5°	704.5	654.2	615.1	571.4	546.3	530.7	520.0
40°	630.3	573.2	525.8	489.0	463.4	453.2	443.2
42.5°	549.7	495.2	453.2	422.5	403.2	391.9	384.1
45°	446.6	398.5	365.7	343.4	328.0	319.3	314.4
47.5°	366.0	330.4	302.5	286.4	275.9	269.1	269.1
50°	322.7	288.7	270.2	257.4	248.3	242.9	243.9
52.5°	284.3	258.9	243.1	232.5	225.7	222.4	222.2
55°	237.7	219.5	209.1	201.3	196.7	193.0	193.8
57.5°	203.4	188.0	181.0	174.5	171.3	169.9	167.6
60°	182.0	170.1	164.1	158.9	155.8	154.5	152.4
62.5°	163.1	153.7	147.9	143.7	140.9	140.4	138.7
65°	137.1	129.9	124.8	122.8	119.8	119.0	119.0
67.5°	113.0	107.9	103.8	102.0	100.7	100.9	100.0
70°	97.9	93.7	91.1	89.1	88.2	88.3	87.6
72.5°	85.7	80.9	78.7	77.5	76.2	76.7	76.4
75°	64.8	62.5	61.3	60.1	59.3	58.9	58.5
77.5°	47.6	45.5	44.6	43.9	44.1	43.0	43.8
80°	36.8	35.0	34.4	33.4	33.2	33.2	33.1
82.5°	26.9	25.9	25.5	24.7	24.3	24.6	24.1
85°	13.9	13.2	12.9	12.9	12.6	12.1	13.2
87.5°	8.4	8.0	8.2	8.1	8.3	8.2	8.0
90°	16.9	17.8	18.6	19.2	19.8	20.3	20.9
92.5°	37.4	38.7	39.4	39.9	40.3	40.7	41.2
95°	71.2	72.6	73.4	73.9	74.2	74.6	75.0
97.5°	110.8	112.1	112.8	113.0	113.3	113.6	113.7
100°	138.7	140.4	141.5	141.9	142.3	142.7	143.1
102.5°	167.1	169.0	170.2	170.7	171.3	171.9	172.4
105°	212.0	213.2	214.0	214.6	215.2	215.8	216.4
107.5°	260.7	261.2	261.6	261.5	261.5	261.4	261.4
110°	294.9	295.5	295.7	295.5	295.2	295.1	294.9



TEST NUMBER: P333353-935

CATALOG NUMBER: S125DIW-S375D1050U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	328.8	329.1	329.1	328.7	328.4	328.0	327.7
115°	380.6	380.5	380.3	380.0	379.9	379.7	379.5
117.5°	433.3	433.5	433.2	432.4	431.6	430.8	430.1
120°	468.5	468.5	468.1	467.4	466.6	465.8	465.0
122.5°	502.9	502.7	502.4	501.8	501.1	500.5	499.9
125°	553.7	553.3	553.0	552.8	552.6	552.4	552.2
127.5°	604.5	604.3	604.1	603.6	603.3	602.9	602.5
130°	638.0	637.8	637.6	637.1	636.8	636.4	636.0
132.5°	670.1	669.9	669.6	669.0	668.5	668.0	667.4
135°	719.7	719.7	719.4	718.6	717.8	717.0	716.3
137.5°	768.1	768.3	767.9	767.0	766.0	765.0	764.1
140°	798.6	798.9	798.7	797.7	796.7	795.7	794.8
142.5°	828.1	828.4	827.9	827.0	826.0	825.1	824.1
145°	870.6	870.6	870.4	869.8	869.2	868.7	868.1
147.5°	910.8	911.3	910.9	909.6	908.2	906.9	905.6
150°	935.2	935.2	935.0	934.6	934.3	933.8	933.5
152.5°	959.0	959.4	959.3	958.6	957.9	957.2	956.5
155°	992.6	993.3	993.2	992.2	991.3	990.3	989.3
157.5°	1021.3	1022.1	1021.8	1020.5	1019.3	1018.0	1016.8
160°	1038.8	1039.6	1039.4	1038.5	1037.5	1036.6	1035.5
162.5°	1055.2	1056.2	1056.1	1055.0	1053.9	1052.7	1051.6
165°	1077.1	1077.9	1077.7	1076.6	1075.4	1074.3	1073.1
167.5°	1093.8	1095.0	1095.0	1093.8	1092.6	1091.4	1090.2
170°	1103.6	1104.7	1104.7	1103.3	1102.0	1100.6	1099.2
172.5°	1110.6	1111.7	1111.7	1110.5	1109.3	1108.1	1106.9
175°	1118.4	1119.6	1119.5	1118.2	1116.8	1115.4	1114.0
177.5°	1121.8	1122.7	1122.6	1121.5	1120.4	1119.4	1118.3
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0

(END OF REPORT)