

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333341-935

Luminaire Tested: **S125DIW-S375D470U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333341-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D470U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2723.1 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	38	36	34	30
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	17
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3027	3027	3027	3027
5°	3505	3038	2660	3038
10°	4078	3022	2330	3022
15°	4515	3000	2150	3000
20°	5054	2965	2004	2965
25°	5920	2925	1934	2925
30°	6395	2885	1873	2885
35°	5257	2812	1832	2812
40°	3737	2710	1788	2710
45°	2872	2573	1763	2573
50°	2451	2402	1758	2402
55°	2182	2235	1775	2235
60°	1969	2052	1820	2052
65°	1819	1869	1867	1869
70°	1654	1679	1894	1679
75°	1460	1480	1876	1480
80°	1231	1209	1715	1209
85°	978	867	1386	867



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	1.7
10°-20°	134.4	4.9
20°-30°	218.2	8.0
30°-40°	266.1	9.8
40°-50°	242.1	8.9
50°-60°	192.8	7.1
60°-70°	134.3	4.9
70°-80°	71.6	2.6
80°-90°	19.2	0.7
90°-100°	33.6	1.2
100°-110°	99.2	3.6
110°-120°	168.0	6.2
120°-130°	221.1	8.1
130°-140°	247.7	9.1
140°-150°	242.8	8.9
150°-160°	203.9	7.5
160°-170°	135.6	5.0
170°-180°	47.4	1.7
0°-30°	397.6	14.6
0°-40°	663.7	24.4
0°-60°	1098.7	40.3
0°-90°	1323.7	48.6
90°-120°	300.8	11.0
90°-150°	1012.4	37.2
90°-180°	1399.0	51.4
0°-180°	2723.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	541	469	410	469	541	54
15°	675	449	322	449	675	193
25°	831	410	271	410	831	379
35°	667	357	232	357	667	408
45°	314	282	193	282	314	252
55°	194	198	158	198	194	174
65°	119	122	122	122	119	118
75°	58	59	75	59	58	63
85°	13	12	19	12	13	15
90°	9	0	9	0	9	6
95°	34	25	34	25	34	34
105°	97	89	97	89	97	103
115°	170	168	170	168	170	168
125°	247	246	247	246	247	221
135°	320	319	320	319	320	247
145°	388	387	388	387	388	242
155°	443	443	443	443	443	204
165°	480	481	480	481	480	135
175°	498	500	498	500	498	47
180°	501	501	501	501	501	



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	495.8	495.2	494.5	493.3	494.2	491.5	490.3	488.0	485.3	484.3	483.2
5°	540.7	541.7	542.8	538.6	539.0	536.1	529.8	524.6	520.5	515.1	511.3
7.5°	594.9	592.5	592.3	589.6	585.0	581.2	574.5	566.0	557.8	548.4	540.6
10°	621.9	622.2	620.4	617.2	612.2	608.6	599.9	591.5	581.3	569.4	560.9
12.5°	642.3	643.2	640.8	636.5	634.1	626.1	619.2	609.3	597.3	587.7	574.7
15°	675.2	673.0	671.5	666.1	661.9	653.6	642.7	632.2	619.1	607.0	594.9
17.5°	707.0	708.8	705.8	700.9	687.9	678.1	663.5	649.3	632.9	616.6	602.2
20°	735.3	736.9	732.4	723.8	708.3	698.5	679.2	660.9	642.0	621.1	605.2
22.5°	770.7	769.4	763.2	750.2	736.8	718.8	697.8	675.5	651.9	628.3	607.1
25°	830.8	822.4	818.6	802.5	784.9	758.4	729.8	697.2	667.7	636.5	609.4
27.5°	864.2	861.5	857.3	846.1	827.5	799.2	765.4	725.7	684.2	644.7	609.2
30°	857.5	857.9	858.2	854.7	842.7	821.5	787.8	745.1	695.7	651.3	610.4
32.5°	798.2	805.5	812.4	820.6	824.0	819.8	798.8	760.2	709.4	659.0	609.8
35°	666.8	669.1	691.6	713.9	744.1	767.6	783.3	766.1	723.4	665.5	609.0
37.5°	520.0	530.7	546.3	571.4	615.1	654.2	704.5	727.5	713.8	667.6	607.6
40°	443.2	453.2	463.4	489.0	525.8	573.2	630.3	679.0	690.3	660.9	602.8
42.5°	384.1	391.9	403.2	422.5	453.2	495.2	549.7	613.5	652.6	641.5	592.8
45°	314.4	319.3	328.0	343.4	365.7	398.5	446.6	516.3	577.0	597.0	569.0
47.5°	269.1	269.1	275.9	286.4	302.5	330.4	366.0	420.5	485.3	533.3	531.1
50°	243.9	242.9	248.3	257.4	270.2	288.7	322.7	366.3	428.5	482.8	498.0
52.5°	222.2	222.4	225.7	232.5	243.1	258.9	284.3	323.6	376.8	432.6	461.1
55°	193.8	193.0	196.7	201.3	209.1	219.5	237.7	267.8	311.0	365.8	402.9
57.5°	167.6	169.9	171.3	174.5	181.0	188.0	203.4	225.4	259.7	306.8	345.9
60°	152.4	154.5	155.8	158.9	164.1	170.1	182.0	199.9	228.8	269.4	308.2
62.5°	138.7	140.4	140.9	143.7	147.9	153.7	163.1	178.1	201.0	236.4	274.4
65°	119.0	119.0	119.8	122.8	124.8	129.9	137.1	148.0	166.3	194.0	226.4
67.5°	100.0	100.9	100.7	102.0	103.8	107.9	113.0	122.0	135.6	155.8	181.8
70°	87.6	88.3	88.2	89.1	91.1	93.7	97.9	106.4	116.1	133.5	155.8
72.5°	76.4	76.7	76.2	77.5	78.7	80.9	85.7	90.2	99.3	113.9	132.2
75°	58.5	58.9	59.3	60.1	61.3	62.5	64.8	69.4	75.4	86.4	98.1
77.5°	43.8	43.0	44.1	43.9	44.6	45.5	47.6	50.0	54.9	61.9	70.9
80°	33.1	33.2	33.2	33.4	34.4	35.0	36.8	38.6	42.4	47.5	53.9
82.5°	24.1	24.6	24.3	24.7	25.5	25.9	26.9	28.4	30.6	34.7	39.3
85°	13.2	12.1	12.6	12.9	12.9	13.2	13.9	14.6	15.8	17.3	19.1
87.5°	5.7	5.9	6.0	6.0	6.1	6.0	6.6	6.5	6.9	7.3	7.8
90°	9.4	9.1	8.9	8.6	8.4	8.0	7.6	7.1	6.7	6.3	5.6
92.5°	18.4	18.3	18.0	17.8	17.7	17.3	16.7	16.1	15.6	15.0	14.2
95°	33.6	33.4	33.2	33.1	32.9	32.5	31.9	31.3	30.7	30.0	29.2
97.5°	50.9	50.8	50.7	50.5	50.5	50.1	49.6	49.0	48.4	47.9	46.7
100°	64.0	63.8	63.6	63.5	63.3	62.9	62.1	61.3	60.5	59.7	58.5
102.5°	77.1	76.9	76.6	76.4	76.1	75.6	74.7	73.9	73.0	72.2	71.6
105°	96.8	96.5	96.3	96.0	95.7	95.3	94.8	94.3	93.8	93.2	92.7
107.5°	116.9	116.9	116.9	117.0	117.0	116.8	116.6	116.3	116.1	115.8	115.5
110°	131.9	132.0	132.1	132.2	132.2	132.2	131.9	131.6	131.4	131.1	130.9



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.5	146.7	146.9	147.1	147.2	147.2	147.1	147.0	146.9	146.7	146.4
115°	169.8	169.9	170.0	170.0	170.1	170.2	170.3	170.4	170.5	170.6	170.4
117.5°	192.3	192.7	193.1	193.5	193.8	193.9	193.8	193.8	193.7	193.6	193.5
120°	208.0	208.4	208.7	209.1	209.4	209.6	209.6	209.6	209.6	209.6	209.5
122.5°	223.6	223.9	224.2	224.5	224.7	224.9	225.0	225.1	225.1	225.2	225.0
125°	247.0	247.1	247.2	247.3	247.4	247.5	247.7	247.9	248.1	248.2	248.1
127.5°	269.5	269.7	269.8	270.0	270.2	270.4	270.4	270.5	270.6	270.7	270.5
130°	284.5	284.6	284.8	285.0	285.2	285.3	285.4	285.5	285.6	285.7	285.5
132.5°	298.5	298.8	299.0	299.3	299.5	299.6	299.7	299.8	299.9	300.0	300.1
135°	320.4	320.7	321.1	321.4	321.8	321.9	321.9	321.9	321.9	321.9	321.8
137.5°	341.7	342.2	342.7	343.1	343.5	343.7	343.5	343.5	343.4	343.3	343.0
140°	355.5	355.9	356.4	356.8	357.2	357.4	357.2	357.1	356.9	356.7	356.5
142.5°	368.6	369.0	369.5	369.9	370.3	370.5	370.4	370.3	370.2	370.1	369.8
145°	388.3	388.6	388.8	389.1	389.3	389.4	389.4	389.4	389.4	389.4	389.2
147.5°	405.1	405.6	406.2	406.8	407.4	407.6	407.4	407.2	407.0	406.8	406.6
150°	417.6	417.8	417.9	418.1	418.3	418.4	418.4	418.4	418.4	418.4	418.0
152.5°	427.8	428.2	428.5	428.8	429.1	429.1	429.0	428.8	428.5	428.3	428.2
155°	442.6	443.0	443.4	443.8	444.3	444.3	443.9	443.6	443.2	442.9	442.8
157.5°	454.8	455.4	455.9	456.5	457.1	457.2	456.8	456.5	456.2	455.8	455.7
160°	463.2	463.6	464.1	464.5	464.9	465.0	464.7	464.3	464.0	463.6	463.5
162.5°	470.4	470.9	471.4	471.9	472.4	472.4	472.0	471.7	471.2	470.8	470.8
165°	480.0	480.5	481.0	481.6	482.1	482.2	481.8	481.5	481.1	480.8	480.7
167.5°	487.7	488.2	488.7	489.2	489.8	489.8	489.3	488.8	488.3	487.8	487.8
170°	491.7	492.3	492.9	493.5	494.1	494.2	493.6	493.1	492.6	492.1	492.1
172.5°	495.2	495.7	496.2	496.7	497.3	497.3	496.8	496.3	495.8	495.2	495.2
175°	498.3	498.9	499.6	500.2	500.8	500.8	500.3	499.7	499.2	498.7	498.7
177.5°	500.2	500.7	501.2	501.7	502.1	502.2	501.8	501.4	500.9	500.5	500.6
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	482.2	481.1	479.8	477.6	474.9	473.5	471.3	469.8	467.0	464.6	462.0
5°	506.7	501.5	496.8	490.6	483.9	479.5	474.3	468.6	462.5	456.4	449.6
7.5°	532.1	522.9	513.0	502.3	491.8	482.2	472.9	464.0	455.6	445.3	436.7
10°	549.1	537.5	525.2	510.7	496.5	484.2	471.7	460.8	449.6	437.7	427.1
12.5°	566.1	550.8	533.3	517.4	500.4	485.5	470.8	456.8	442.8	429.6	417.2
15°	578.2	564.6	548.5	525.8	506.7	486.2	466.7	448.7	431.7	417.0	401.5
17.5°	586.1	568.6	551.3	529.6	504.5	481.6	459.5	438.8	419.7	401.1	386.2
20°	587.5	569.6	551.5	530.2	504.5	478.3	456.2	431.4	410.9	391.5	373.2
22.5°	587.0	566.7	547.0	525.1	500.1	475.9	449.2	423.9	401.6	382.6	363.5
25°	582.6	560.9	536.1	514.1	489.4	463.7	436.7	410.4	387.8	366.1	347.2
27.5°	578.8	550.7	522.7	497.0	473.1	449.6	423.7	396.8	371.7	349.7	331.9
30°	574.2	543.3	511.9	485.0	460.5	437.7	413.2	386.9	360.7	339.2	320.1
32.5°	570.1	534.1	500.9	471.7	445.7	423.5	401.0	376.0	350.2	328.4	309.3
35°	562.1	520.5	482.4	449.4	421.8	398.9	380.0	356.7	333.0	311.9	293.7
37.5°	551.9	502.6	461.8	427.1	396.8	372.7	355.2	337.3	314.5	294.2	277.7
40°	543.9	489.8	446.6	411.2	379.8	354.7	338.4	321.5	302.6	283.7	266.2
42.5°	533.9	478.4	431.4	393.2	362.1	337.7	320.6	306.3	289.6	271.9	255.7
45°	515.5	457.6	406.7	365.7	334.2	310.1	292.5	281.7	269.1	252.4	238.8
47.5°	488.4	432.7	380.0	337.7	305.2	282.9	266.3	256.0	247.2	234.8	222.3
50°	464.3	414.1	360.7	318.7	286.3	263.8	248.5	239.1	231.6	222.1	211.5
52.5°	437.5	390.6	341.7	300.2	268.1	246.0	231.0	222.7	216.5	209.7	199.2
55°	394.7	354.9	309.5	270.2	240.6	218.9	205.7	198.5	193.4	188.2	181.8
57.5°	347.7	316.5	276.4	240.3	213.0	193.3	181.1	174.1	170.0	167.4	163.7
60°	314.5	287.9	253.3	220.4	193.8	176.2	164.4	158.9	155.6	153.4	150.6
62.5°	283.8	261.9	229.9	199.9	176.6	160.1	149.4	144.1	140.9	139.8	137.6
65°	238.6	221.6	195.2	170.3	150.4	136.3	127.3	122.3	120.4	119.2	119.3
67.5°	193.9	183.7	162.4	141.2	125.3	113.5	106.2	102.5	101.4	99.9	99.9
70°	166.7	158.9	141.0	122.5	108.4	99.3	92.9	88.9	87.9	87.1	87.0
72.5°	142.7	135.9	120.4	105.6	92.8	84.8	79.6	77.1	75.5	75.1	75.0
75°	107.2	103.5	91.1	79.4	70.6	65.1	61.5	59.3	58.1	57.9	58.1
77.5°	76.2	72.9	65.1	56.7	51.2	47.0	44.0	43.2	41.9	41.9	41.8
80°	57.3	55.1	50.1	43.6	39.0	35.4	33.8	32.5	32.0	31.4	32.0
82.5°	41.5	39.2	35.8	31.6	27.8	25.7	24.1	23.7	23.4	23.2	23.2
85°	20.5	20.7	18.7	15.5	13.9	12.7	11.7	11.7	11.5	11.4	11.5
87.5°	8.0	7.6	6.8	6.2	5.3	4.6	4.4	4.4	4.0	4.0	4.3
90°	5.0	4.4	3.8	3.2	2.5	1.8	1.1	0.4	1.1	1.8	2.5
92.5°	13.5	12.7	12.0	11.4	10.9	10.4	9.9	9.5	9.9	10.4	10.9
95°	28.3	27.5	26.6	26.1	25.9	25.7	25.6	25.4	25.6	25.7	25.9
97.5°	45.5	44.3	43.0	42.4	42.4	42.3	42.2	42.1	42.2	42.3	42.4
100°	57.4	56.3	55.2	54.7	54.7	54.7	54.7	54.7	54.7	54.7	54.7
102.5°	71.0	70.5	69.9	69.5	69.1	68.8	68.4	68.0	68.4	68.8	69.1
105°	92.2	91.7	91.2	90.7	90.2	89.8	89.4	88.9	89.4	89.8	90.2
107.5°	115.0	114.6	114.3	113.8	113.4	113.0	112.5	112.1	112.5	113.0	113.4
110°	130.6	130.4	130.1	129.8	129.3	128.9	128.5	128.0	128.5	128.9	129.3



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	146.1	145.8	145.4	145.2	144.9	144.6	144.5	144.2	144.5	144.6	144.9
115°	170.2	170.0	169.9	169.6	169.3	168.9	168.5	168.2	168.5	168.9	169.3
117.5°	193.3	193.2	193.0	192.9	192.7	192.5	192.3	192.3	192.3	192.5	192.7
120°	209.4	209.3	209.2	209.0	208.5	208.1	207.7	207.2	207.7	208.1	208.5
122.5°	224.7	224.5	224.3	224.0	223.9	223.8	223.6	223.4	223.6	223.8	223.9
125°	248.1	248.0	247.9	247.5	247.0	246.5	246.0	245.5	246.0	246.5	247.0
127.5°	270.4	270.4	270.3	270.1	269.8	269.5	269.1	268.9	269.1	269.5	269.8
130°	285.3	285.2	285.0	284.6	284.2	283.8	283.4	282.9	283.4	283.8	284.2
132.5°	300.1	300.1	300.1	299.8	299.1	298.4	297.6	297.0	297.6	298.4	299.1
135°	321.8	321.7	321.6	321.3	320.8	320.3	319.8	319.2	319.8	320.3	320.8
137.5°	342.9	342.7	342.5	342.2	341.6	341.1	340.6	340.1	340.6	341.1	341.6
140°	356.2	355.9	355.7	355.2	354.8	354.4	354.0	353.5	354.0	354.4	354.8
142.5°	369.5	369.1	368.8	368.4	368.1	367.7	367.3	367.0	367.3	367.7	368.1
145°	388.9	388.7	388.4	388.1	387.8	387.4	387.1	386.8	387.1	387.4	387.8
147.5°	406.4	406.1	406.0	405.8	405.5	405.4	405.2	405.0	405.2	405.4	405.5
150°	417.7	417.3	417.0	416.8	416.9	417.0	417.1	417.2	417.1	417.0	416.9
152.5°	428.1	427.9	427.7	427.7	427.5	427.4	427.3	427.1	427.3	427.4	427.5
155°	442.7	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6
157.5°	455.6	455.6	455.5	455.5	455.7	455.9	456.1	456.2	456.1	455.9	455.7
160°	463.4	463.3	463.2	463.3	463.6	463.8	464.2	464.4	464.2	463.8	463.6
162.5°	470.7	470.7	470.7	470.8	471.0	471.2	471.4	471.6	471.4	471.2	471.0
165°	480.6	480.5	480.4	480.4	480.6	480.8	481.0	481.1	481.0	480.8	480.6
167.5°	487.8	487.8	487.8	487.9	488.3	488.6	489.0	489.3	489.0	488.6	488.3
170°	492.1	492.1	492.1	492.2	492.6	492.9	493.3	493.6	493.3	492.9	492.6
172.5°	495.2	495.2	495.2	495.4	495.8	496.1	496.5	496.8	496.5	496.1	495.8
175°	498.7	498.7	498.7	498.9	499.2	499.6	499.9	500.3	499.9	499.6	499.2
177.5°	500.7	500.8	500.8	500.9	501.3	501.5	501.8	502.0	501.8	501.5	501.3
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	460.6	458.8	457.4	454.3	452.5	450.1	448.2	450.3	448.1	449.0	447.5
5°	446.3	440.7	436.7	430.9	425.9	421.4	418.0	417.4	415.8	415.0	412.6
7.5°	429.0	422.0	415.2	407.6	401.2	394.8	390.6	387.2	385.0	381.9	379.9
10°	418.8	409.4	401.5	392.4	384.4	377.4	371.9	369.0	366.4	362.7	361.3
12.5°	406.2	396.6	386.8	377.0	369.4	361.6	356.9	352.7	350.9	346.6	346.2
15°	391.2	376.6	367.0	357.1	346.6	340.2	336.2	331.7	329.7	326.7	324.5
17.5°	373.2	360.2	348.3	337.9	328.9	323.6	318.6	315.5	312.0	310.0	306.5
20°	360.1	347.8	335.8	324.9	317.9	311.8	307.8	304.8	301.2	300.2	296.6
22.5°	349.1	335.5	324.1	314.9	307.3	300.3	296.0	293.9	291.5	288.4	287.7
25°	331.2	317.1	307.4	298.3	291.4	285.1	282.1	279.6	277.2	274.9	274.1
27.5°	315.8	303.2	291.6	283.4	277.4	271.6	269.1	265.9	264.2	262.3	260.2
30°	305.0	292.1	281.9	274.0	267.6	262.4	259.6	257.4	255.9	254.3	253.0
32.5°	293.9	281.9	272.1	264.2	257.9	254.0	251.5	249.9	248.2	246.3	244.8
35°	279.1	266.0	256.4	249.7	244.7	241.7	238.9	237.5	235.6	235.6	233.9
37.5°	262.5	251.2	242.7	236.6	232.1	229.5	226.4	225.5	224.2	223.3	222.8
40°	252.7	242.1	234.2	228.0	223.3	221.0	218.6	217.1	216.3	215.2	214.9
42.5°	242.5	232.4	224.8	219.1	214.9	213.1	210.9	209.7	208.1	206.8	206.6
45°	227.0	217.2	210.3	205.7	202.2	199.9	198.5	196.1	195.4	193.8	193.6
47.5°	212.3	202.9	196.1	192.3	189.2	187.4	185.3	182.9	181.9	181.2	181.1
50°	201.3	192.8	186.4	182.9	179.9	177.3	175.0	173.5	172.9	172.9	173.3
52.5°	190.2	182.9	177.5	173.1	170.3	167.6	165.5	164.5	163.7	164.6	165.3
55°	173.9	166.5	162.6	158.3	155.6	152.4	151.4	151.0	150.4	152.0	152.8
57.5°	156.6	151.4	146.8	142.7	140.2	138.3	137.0	136.7	137.8	138.6	141.2
60°	145.6	139.7	135.5	132.3	129.3	128.1	127.7	127.3	128.1	130.3	133.7
62.5°	133.5	128.7	124.2	121.8	119.6	117.6	117.5	117.8	119.3	121.9	125.3
65°	115.8	111.6	108.7	105.8	104.0	102.9	103.2	104.0	105.8	109.3	113.0
67.5°	97.7	94.9	92.2	90.0	88.3	88.3	88.7	89.9	92.0	95.8	99.3
70°	86.2	83.0	80.8	79.8	78.4	77.6	78.8	80.8	82.6	86.2	89.1
72.5°	74.6	71.8	70.1	69.4	68.8	68.2	68.6	70.8	73.2	76.7	80.2
75°	57.3	56.3	55.1	54.3	53.7	54.2	54.5	56.5	58.5	62.3	66.2
77.5°	41.8	40.8	40.0	39.9	39.5	39.8	40.9	42.4	44.3	47.0	50.0
80°	31.6	31.3	30.8	30.7	30.7	30.8	32.5	33.4	35.2	37.8	40.2
82.5°	23.1	22.8	22.7	22.6	22.8	22.9	23.8	25.1	26.6	28.6	30.7
85°	12.1	11.7	12.3	12.6	12.1	12.7	13.2	13.9	14.6	15.5	16.5
87.5°	4.6	5.1	5.0	5.3	5.4	5.9	5.8	6.5	6.9	7.3	7.2
90°	3.2	3.8	4.4	5.0	5.6	6.3	6.7	7.1	7.6	8.0	8.4
92.5°	11.4	12.0	12.7	13.5	14.2	15.0	15.6	16.1	16.7	17.3	17.7
95°	26.1	26.6	27.5	28.3	29.2	30.0	30.7	31.3	31.9	32.5	32.9
97.5°	42.4	43.0	44.3	45.5	46.7	47.9	48.4	49.0	49.6	50.1	50.5
100°	54.7	55.2	56.3	57.4	58.5	59.7	60.5	61.3	62.1	62.9	63.3
102.5°	69.5	69.9	70.5	71.0	71.6	72.2	73.0	73.9	74.7	75.6	76.1
105°	90.7	91.2	91.7	92.2	92.7	93.2	93.8	94.3	94.8	95.3	95.7
107.5°	113.8	114.3	114.6	115.0	115.5	115.8	116.1	116.3	116.6	116.8	117.0
110°	129.8	130.1	130.4	130.6	130.9	131.1	131.4	131.6	131.9	132.2	132.2



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	145.2	145.4	145.8	146.1	146.4	146.7	146.9	147.0	147.1	147.2	147.2
115°	169.6	169.9	170.0	170.2	170.4	170.6	170.5	170.4	170.3	170.2	170.1
117.5°	192.9	193.0	193.2	193.3	193.5	193.6	193.7	193.8	193.8	193.9	193.8
120°	209.0	209.2	209.3	209.4	209.5	209.6	209.6	209.6	209.6	209.6	209.4
122.5°	224.0	224.3	224.5	224.7	225.0	225.2	225.1	225.1	225.0	224.9	224.7
125°	247.5	247.9	248.0	248.1	248.1	248.2	248.1	247.9	247.7	247.5	247.4
127.5°	270.1	270.3	270.4	270.4	270.5	270.7	270.6	270.5	270.4	270.4	270.2
130°	284.6	285.0	285.2	285.3	285.5	285.7	285.6	285.5	285.4	285.3	285.2
132.5°	299.8	300.1	300.1	300.1	300.1	300.0	299.9	299.8	299.7	299.6	299.5
135°	321.3	321.6	321.7	321.8	321.8	321.9	321.9	321.9	321.9	321.9	321.8
137.5°	342.2	342.5	342.7	342.9	343.0	343.3	343.4	343.5	343.5	343.7	343.5
140°	355.2	355.7	355.9	356.2	356.5	356.7	356.9	357.1	357.2	357.4	357.2
142.5°	368.4	368.8	369.1	369.5	369.8	370.1	370.2	370.3	370.4	370.5	370.3
145°	388.1	388.4	388.7	388.9	389.2	389.4	389.4	389.4	389.4	389.4	389.3
147.5°	405.8	406.0	406.1	406.4	406.6	406.8	407.0	407.2	407.4	407.6	407.4
150°	416.8	417.0	417.3	417.7	418.0	418.4	418.4	418.4	418.4	418.4	418.3
152.5°	427.7	427.7	427.9	428.1	428.2	428.3	428.5	428.8	429.0	429.1	429.1
155°	442.6	442.6	442.6	442.7	442.8	442.9	443.2	443.6	443.9	444.3	444.3
157.5°	455.5	455.5	455.6	455.6	455.7	455.8	456.2	456.5	456.8	457.2	457.1
160°	463.3	463.2	463.3	463.4	463.5	463.6	464.0	464.3	464.7	465.0	464.9
162.5°	470.8	470.7	470.7	470.7	470.8	470.8	471.2	471.7	472.0	472.4	472.4
165°	480.4	480.4	480.5	480.6	480.7	480.8	481.1	481.5	481.8	482.2	482.1
167.5°	487.9	487.8	487.8	487.8	487.8	487.8	488.3	488.8	489.3	489.8	489.8
170°	492.2	492.1	492.1	492.1	492.1	492.1	492.6	493.1	493.6	494.2	494.1
172.5°	495.4	495.2	495.2	495.2	495.2	495.2	495.8	496.3	496.8	497.3	497.3
175°	498.9	498.7	498.7	498.7	498.7	498.7	499.2	499.7	500.3	500.8	500.8
177.5°	500.9	500.8	500.8	500.7	500.6	500.5	500.9	501.4	501.8	502.2	502.1
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	446.6	447.7	446.8	448.1	446.8	447.7	446.6	447.5	449.0	448.1	450.3
5°	411.6	409.8	411.0	410.3	411.0	409.8	411.6	412.6	415.0	415.8	417.4
7.5°	379.4	377.6	375.7	374.7	375.7	377.6	379.4	379.9	381.9	385.0	387.2
10°	359.1	356.9	356.7	355.3	356.7	356.9	359.1	361.3	362.7	366.4	369.0
12.5°	344.3	342.2	340.0	339.4	340.0	342.2	344.3	346.2	346.6	350.9	352.7
15°	323.3	321.7	320.3	321.5	320.3	321.7	323.3	324.5	326.7	329.7	331.7
17.5°	305.8	304.5	304.3	302.8	304.3	304.5	305.8	306.5	310.0	312.0	315.5
20°	294.8	293.9	294.3	291.6	294.3	293.9	294.8	296.6	300.2	301.2	304.8
22.5°	286.1	284.1	283.9	283.4	283.9	284.1	286.1	287.7	288.4	291.5	293.9
25°	272.3	271.4	270.4	271.4	270.4	271.4	272.3	274.1	274.9	277.2	279.6
27.5°	260.4	259.2	258.9	259.1	258.9	259.2	260.4	260.2	262.3	264.2	265.9
30°	253.0	251.1	251.2	251.1	251.2	251.1	253.0	253.0	254.3	255.9	257.4
32.5°	245.1	243.7	243.5	243.1	243.5	243.7	245.1	244.8	246.3	248.2	249.9
35°	233.3	233.3	232.4	232.4	232.4	233.3	233.3	233.9	235.6	235.6	237.5
37.5°	222.3	222.1	221.5	221.6	221.5	222.1	222.3	222.8	223.3	224.2	225.5
40°	214.0	213.9	213.3	212.1	213.3	213.9	214.0	214.9	215.2	216.3	217.1
42.5°	206.1	205.4	205.2	204.7	205.2	205.4	206.1	206.6	206.8	208.1	209.7
45°	193.6	193.6	193.2	193.0	193.2	193.6	193.6	193.6	193.8	195.4	196.1
47.5°	181.4	181.8	182.5	182.4	182.5	181.8	181.4	181.1	181.2	181.9	182.9
50°	174.1	174.3	174.9	175.0	174.9	174.3	174.1	173.3	172.9	172.9	173.5
52.5°	166.0	167.1	167.9	167.7	167.9	167.1	166.0	165.3	164.6	163.7	164.5
55°	154.5	156.0	157.4	157.6	157.4	156.0	154.5	152.8	152.0	150.4	151.0
57.5°	143.4	145.3	146.7	147.2	146.7	145.3	143.4	141.2	138.6	137.8	136.7
60°	135.7	138.3	140.1	140.9	140.1	138.3	135.7	133.7	130.3	128.1	127.3
62.5°	128.4	131.3	133.0	133.2	133.0	131.3	128.4	125.3	121.9	119.3	117.8
65°	116.4	119.3	121.0	122.2	121.0	119.3	116.4	113.0	109.3	105.8	104.0
67.5°	103.5	106.5	108.2	109.2	108.2	106.5	103.5	99.3	95.8	92.0	89.9
70°	94.1	97.1	99.4	100.3	99.4	97.1	94.1	89.1	86.2	82.6	80.8
72.5°	84.9	87.6	89.5	90.4	89.5	87.6	84.9	80.2	76.7	73.2	70.8
75°	68.8	72.4	74.2	75.2	74.2	72.4	68.8	66.2	62.3	58.5	56.5
77.5°	53.0	56.3	57.4	57.9	57.4	56.3	53.0	50.0	47.0	44.3	42.4
80°	42.5	44.6	46.0	46.1	46.0	44.6	42.5	40.2	37.8	35.2	33.4
82.5°	32.7	34.4	34.8	35.3	34.8	34.4	32.7	30.7	28.6	26.6	25.1
85°	17.9	18.7	18.9	18.7	18.9	18.7	17.9	16.5	15.5	14.6	13.9
87.5°	7.6	7.5	7.6	7.9	7.6	7.5	7.6	7.2	7.3	6.9	6.5
90°	8.6	8.9	9.1	9.4	9.1	8.9	8.6	8.4	8.0	7.6	7.1
92.5°	17.8	18.0	18.3	18.4	18.3	18.0	17.8	17.7	17.3	16.7	16.1
95°	33.1	33.2	33.4	33.6	33.4	33.2	33.1	32.9	32.5	31.9	31.3
97.5°	50.5	50.7	50.8	50.9	50.8	50.7	50.5	50.5	50.1	49.6	49.0
100°	63.5	63.6	63.8	64.0	63.8	63.6	63.5	63.3	62.9	62.1	61.3
102.5°	76.4	76.6	76.9	77.1	76.9	76.6	76.4	76.1	75.6	74.7	73.9
105°	96.0	96.3	96.5	96.8	96.5	96.3	96.0	95.7	95.3	94.8	94.3
107.5°	117.0	116.9	116.9	116.9	116.9	116.9	117.0	117.0	116.8	116.6	116.3
110°	132.2	132.1	132.0	131.9	132.0	132.1	132.2	132.2	132.2	131.9	131.6



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	147.1	146.9	146.7	146.5	146.7	146.9	147.1	147.2	147.2	147.1	147.0
115°	170.0	170.0	169.9	169.8	169.9	170.0	170.0	170.1	170.2	170.3	170.4
117.5°	193.5	193.1	192.7	192.3	192.7	193.1	193.5	193.8	193.9	193.8	193.8
120°	209.1	208.7	208.4	208.0	208.4	208.7	209.1	209.4	209.6	209.6	209.6
122.5°	224.5	224.2	223.9	223.6	223.9	224.2	224.5	224.7	224.9	225.0	225.1
125°	247.3	247.2	247.1	247.0	247.1	247.2	247.3	247.4	247.5	247.7	247.9
127.5°	270.0	269.8	269.7	269.5	269.7	269.8	270.0	270.2	270.4	270.4	270.5
130°	285.0	284.8	284.6	284.5	284.6	284.8	285.0	285.2	285.3	285.4	285.5
132.5°	299.3	299.0	298.8	298.5	298.8	299.0	299.3	299.5	299.6	299.7	299.8
135°	321.4	321.1	320.7	320.4	320.7	321.1	321.4	321.8	321.9	321.9	321.9
137.5°	343.1	342.7	342.2	341.7	342.2	342.7	343.1	343.5	343.7	343.5	343.5
140°	356.8	356.4	355.9	355.5	355.9	356.4	356.8	357.2	357.4	357.2	357.1
142.5°	369.9	369.5	369.0	368.6	369.0	369.5	369.9	370.3	370.5	370.4	370.3
145°	389.1	388.8	388.6	388.3	388.6	388.8	389.1	389.3	389.4	389.4	389.4
147.5°	406.8	406.2	405.6	405.1	405.6	406.2	406.8	407.4	407.6	407.4	407.2
150°	418.1	417.9	417.8	417.6	417.8	417.9	418.1	418.3	418.4	418.4	418.4
152.5°	428.8	428.5	428.2	427.8	428.2	428.5	428.8	429.1	429.1	429.0	428.8
155°	443.8	443.4	443.0	442.6	443.0	443.4	443.8	444.3	444.3	443.9	443.6
157.5°	456.5	455.9	455.4	454.8	455.4	455.9	456.5	457.1	457.2	456.8	456.5
160°	464.5	464.1	463.6	463.2	463.6	464.1	464.5	464.9	465.0	464.7	464.3
162.5°	471.9	471.4	470.9	470.4	470.9	471.4	471.9	472.4	472.4	472.0	471.7
165°	481.6	481.0	480.5	480.0	480.5	481.0	481.6	482.1	482.2	481.8	481.5
167.5°	489.2	488.7	488.2	487.7	488.2	488.7	489.2	489.8	489.8	489.3	488.8
170°	493.5	492.9	492.3	491.7	492.3	492.9	493.5	494.1	494.2	493.6	493.1
172.5°	496.7	496.2	495.7	495.2	495.7	496.2	496.7	497.3	497.3	496.8	496.3
175°	500.2	499.6	498.9	498.3	498.9	499.6	500.2	500.8	500.8	500.3	499.7
177.5°	501.7	501.2	500.7	500.2	500.7	501.2	501.7	502.1	502.2	501.8	501.4
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	448.2	450.1	452.5	454.3	457.4	458.8	460.6	462.0	464.6	467.0	469.8
5°	418.0	421.4	425.9	430.9	436.7	440.7	446.3	449.6	456.4	462.5	468.6
7.5°	390.6	394.8	401.2	407.6	415.2	422.0	429.0	436.7	445.3	455.6	464.0
10°	371.9	377.4	384.4	392.4	401.5	409.4	418.8	427.1	437.7	449.6	460.8
12.5°	356.9	361.6	369.4	377.0	386.8	396.6	406.2	417.2	429.6	442.8	456.8
15°	336.2	340.2	346.6	357.1	367.0	376.6	391.2	401.5	417.0	431.7	448.7
17.5°	318.6	323.6	328.9	337.9	348.3	360.2	373.2	386.2	401.1	419.7	438.8
20°	307.8	311.8	317.9	324.9	335.8	347.8	360.1	373.2	391.5	410.9	431.4
22.5°	296.0	300.3	307.3	314.9	324.1	335.5	349.1	363.5	382.6	401.6	423.9
25°	282.1	285.1	291.4	298.3	307.4	317.1	331.2	347.2	366.1	387.8	410.4
27.5°	269.1	271.6	277.4	283.4	291.6	303.2	315.8	331.9	349.7	371.7	396.8
30°	259.6	262.4	267.6	274.0	281.9	292.1	305.0	320.1	339.2	360.7	386.9
32.5°	251.5	254.0	257.9	264.2	272.1	281.9	293.9	309.3	328.4	350.2	376.0
35°	238.9	241.7	244.7	249.7	256.4	266.0	279.1	293.7	311.9	333.0	356.7
37.5°	226.4	229.5	232.1	236.6	242.7	251.2	262.5	277.7	294.2	314.5	337.3
40°	218.6	221.0	223.3	228.0	234.2	242.1	252.7	266.2	283.7	302.6	321.5
42.5°	210.9	213.1	214.9	219.1	224.8	232.4	242.5	255.7	271.9	289.6	306.3
45°	198.5	199.9	202.2	205.7	210.3	217.2	227.0	238.8	252.4	269.1	281.7
47.5°	185.3	187.4	189.2	192.3	196.1	202.9	212.3	222.3	234.8	247.2	256.0
50°	175.0	177.3	179.9	182.9	186.4	192.8	201.3	211.5	222.1	231.6	239.1
52.5°	165.5	167.6	170.3	173.1	177.5	182.9	190.2	199.2	209.7	216.5	222.7
55°	151.4	152.4	155.6	158.3	162.6	166.5	173.9	181.8	188.2	193.4	198.5
57.5°	137.0	138.3	140.2	142.7	146.8	151.4	156.6	163.7	167.4	170.0	174.1
60°	127.7	128.1	129.3	132.3	135.5	139.7	145.6	150.6	153.4	155.6	158.9
62.5°	117.5	117.6	119.6	121.8	124.2	128.7	133.5	137.6	139.8	140.9	144.1
65°	103.2	102.9	104.0	105.8	108.7	111.6	115.8	119.3	119.2	120.4	122.3
67.5°	88.7	88.3	88.3	90.0	92.2	94.9	97.7	99.9	99.9	101.4	102.5
70°	78.8	77.6	78.4	79.8	80.8	83.0	86.2	87.0	87.1	87.9	88.9
72.5°	68.6	68.2	68.8	69.4	70.1	71.8	74.6	75.0	75.1	75.5	77.1
75°	54.5	54.2	53.7	54.3	55.1	56.3	57.3	58.1	57.9	58.1	59.3
77.5°	40.9	39.8	39.5	39.9	40.0	40.8	41.8	41.8	41.9	41.9	43.2
80°	32.5	30.8	30.7	30.7	30.8	31.3	31.6	32.0	31.4	32.0	32.5
82.5°	23.8	22.9	22.8	22.6	22.7	22.8	23.1	23.2	23.2	23.4	23.7
85°	13.2	12.7	12.1	12.6	12.3	11.7	12.1	11.5	11.4	11.5	11.7
87.5°	5.8	5.9	5.4	5.3	5.0	5.1	4.6	4.3	4.0	4.0	4.4
90°	6.7	6.3	5.6	5.0	4.4	3.8	3.2	2.5	1.8	1.1	0.4
92.5°	15.6	15.0	14.2	13.5	12.7	12.0	11.4	10.9	10.4	9.9	9.5
95°	30.7	30.0	29.2	28.3	27.5	26.6	26.1	25.9	25.7	25.6	25.4
97.5°	48.4	47.9	46.7	45.5	44.3	43.0	42.4	42.4	42.3	42.2	42.1
100°	60.5	59.7	58.5	57.4	56.3	55.2	54.7	54.7	54.7	54.7	54.7
102.5°	73.0	72.2	71.6	71.0	70.5	69.9	69.5	69.1	68.8	68.4	68.0
105°	93.8	93.2	92.7	92.2	91.7	91.2	90.7	90.2	89.8	89.4	88.9
107.5°	116.1	115.8	115.5	115.0	114.6	114.3	113.8	113.4	113.0	112.5	112.1
110°	131.4	131.1	130.9	130.6	130.4	130.1	129.8	129.3	128.9	128.5	128.0



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	146.9	146.7	146.4	146.1	145.8	145.4	145.2	144.9	144.6	144.5	144.2
115°	170.5	170.6	170.4	170.2	170.0	169.9	169.6	169.3	168.9	168.5	168.2
117.5°	193.7	193.6	193.5	193.3	193.2	193.0	192.9	192.7	192.5	192.3	192.3
120°	209.6	209.6	209.5	209.4	209.3	209.2	209.0	208.5	208.1	207.7	207.2
122.5°	225.1	225.2	225.0	224.7	224.5	224.3	224.0	223.9	223.8	223.6	223.4
125°	248.1	248.2	248.1	248.1	248.0	247.9	247.5	247.0	246.5	246.0	245.5
127.5°	270.6	270.7	270.5	270.4	270.4	270.3	270.1	269.8	269.5	269.1	268.9
130°	285.6	285.7	285.5	285.3	285.2	285.0	284.6	284.2	283.8	283.4	282.9
132.5°	299.9	300.0	300.1	300.1	300.1	300.1	299.8	299.1	298.4	297.6	297.0
135°	321.9	321.9	321.8	321.8	321.7	321.6	321.3	320.8	320.3	319.8	319.2
137.5°	343.4	343.3	343.0	342.9	342.7	342.5	342.2	341.6	341.1	340.6	340.1
140°	356.9	356.7	356.5	356.2	355.9	355.7	355.2	354.8	354.4	354.0	353.5
142.5°	370.2	370.1	369.8	369.5	369.1	368.8	368.4	368.1	367.7	367.3	367.0
145°	389.4	389.4	389.2	388.9	388.7	388.4	388.1	387.8	387.4	387.1	386.8
147.5°	407.0	406.8	406.6	406.4	406.1	406.0	405.8	405.5	405.4	405.2	405.0
150°	418.4	418.4	418.0	417.7	417.3	417.0	416.8	416.9	417.0	417.1	417.2
152.5°	428.5	428.3	428.2	428.1	427.9	427.7	427.7	427.5	427.4	427.3	427.1
155°	443.2	442.9	442.8	442.7	442.6	442.6	442.6	442.6	442.6	442.6	442.6
157.5°	456.2	455.8	455.7	455.6	455.6	455.5	455.5	455.7	455.9	456.1	456.2
160°	464.0	463.6	463.5	463.4	463.3	463.2	463.3	463.6	463.8	464.2	464.4
162.5°	471.2	470.8	470.8	470.7	470.7	470.7	470.8	471.0	471.2	471.4	471.6
165°	481.1	480.8	480.7	480.6	480.5	480.4	480.4	480.6	480.8	481.0	481.1
167.5°	488.3	487.8	487.8	487.8	487.8	487.8	487.9	488.3	488.6	489.0	489.3
170°	492.6	492.1	492.1	492.1	492.1	492.1	492.2	492.6	492.9	493.3	493.6
172.5°	495.8	495.2	495.2	495.2	495.2	495.2	495.4	495.8	496.1	496.5	496.8
175°	499.2	498.7	498.7	498.7	498.7	498.7	498.9	499.2	499.6	499.9	500.3
177.5°	500.9	500.5	500.6	500.7	500.8	500.8	500.9	501.3	501.5	501.8	502.0
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	471.3	473.5	474.9	477.6	479.8	481.1	482.2	483.2	484.3	485.3	488.0
5°	474.3	479.5	483.9	490.6	496.8	501.5	506.7	511.3	515.1	520.5	524.6
7.5°	472.9	482.2	491.8	502.3	513.0	522.9	532.1	540.6	548.4	557.8	566.0
10°	471.7	484.2	496.5	510.7	525.2	537.5	549.1	560.9	569.4	581.3	591.5
12.5°	470.8	485.5	500.4	517.4	533.3	550.8	566.1	574.7	587.7	597.3	609.3
15°	466.7	486.2	506.7	525.8	548.5	564.6	578.2	594.9	607.0	619.1	632.2
17.5°	459.5	481.6	504.5	529.6	551.3	568.6	586.1	602.2	616.6	632.9	649.3
20°	456.2	478.3	504.5	530.2	551.5	569.6	587.5	605.2	621.1	642.0	660.9
22.5°	449.2	475.9	500.1	525.1	547.0	566.7	587.0	607.1	628.3	651.9	675.5
25°	436.7	463.7	489.4	514.1	536.1	560.9	582.6	609.4	636.5	667.7	697.2
27.5°	423.7	449.6	473.1	497.0	522.7	550.7	578.8	609.2	644.7	684.2	725.7
30°	413.2	437.7	460.5	485.0	511.9	543.3	574.2	610.4	651.3	695.7	745.1
32.5°	401.0	423.5	445.7	471.7	500.9	534.1	570.1	609.8	659.0	709.4	760.2
35°	380.0	398.9	421.8	449.4	482.4	520.5	562.1	609.0	665.5	723.4	766.1
37.5°	355.2	372.7	396.8	427.1	461.8	502.6	551.9	607.6	667.6	713.8	727.5
40°	338.4	354.7	379.8	411.2	446.6	489.8	543.9	602.8	660.9	690.3	679.0
42.5°	320.6	337.7	362.1	393.2	431.4	478.4	533.9	592.8	641.5	652.6	613.5
45°	292.5	310.1	334.2	365.7	406.7	457.6	515.5	569.0	597.0	577.0	516.3
47.5°	266.3	282.9	305.2	337.7	380.0	432.7	488.4	531.1	533.3	485.3	420.5
50°	248.5	263.8	286.3	318.7	360.7	414.1	464.3	498.0	482.8	428.5	366.3
52.5°	231.0	246.0	268.1	300.2	341.7	390.6	437.5	461.1	432.6	376.8	323.6
55°	205.7	218.9	240.6	270.2	309.5	354.9	394.7	402.9	365.8	311.0	267.8
57.5°	181.1	193.3	213.0	240.3	276.4	316.5	347.7	345.9	306.8	259.7	225.4
60°	164.4	176.2	193.8	220.4	253.3	287.9	314.5	308.2	269.4	228.8	199.9
62.5°	149.4	160.1	176.6	199.9	229.9	261.9	283.8	274.4	236.4	201.0	178.1
65°	127.3	136.3	150.4	170.3	195.2	221.6	238.6	226.4	194.0	166.3	148.0
67.5°	106.2	113.5	125.3	141.2	162.4	183.7	193.9	181.8	155.8	135.6	122.0
70°	92.9	99.3	108.4	122.5	141.0	158.9	166.7	155.8	133.5	116.1	106.4
72.5°	79.6	84.8	92.8	105.6	120.4	135.9	142.7	132.2	113.9	99.3	90.2
75°	61.5	65.1	70.6	79.4	91.1	103.5	107.2	98.1	86.4	75.4	69.4
77.5°	44.0	47.0	51.2	56.7	65.1	72.9	76.2	70.9	61.9	54.9	50.0
80°	33.8	35.4	39.0	43.6	50.1	55.1	57.3	53.9	47.5	42.4	38.6
82.5°	24.1	25.7	27.8	31.6	35.8	39.2	41.5	39.3	34.7	30.6	28.4
85°	11.7	12.7	13.9	15.5	18.7	20.7	20.5	19.1	17.3	15.8	14.6
87.5°	4.4	4.6	5.3	6.2	6.8	7.6	8.0	7.8	7.3	6.9	6.5
90°	1.1	1.8	2.5	3.2	3.8	4.4	5.0	5.6	6.3	6.7	7.1
92.5°	9.9	10.4	10.9	11.4	12.0	12.7	13.5	14.2	15.0	15.6	16.1
95°	25.6	25.7	25.9	26.1	26.6	27.5	28.3	29.2	30.0	30.7	31.3
97.5°	42.2	42.3	42.4	42.4	43.0	44.3	45.5	46.7	47.9	48.4	49.0
100°	54.7	54.7	54.7	54.7	55.2	56.3	57.4	58.5	59.7	60.5	61.3
102.5°	68.4	68.8	69.1	69.5	69.9	70.5	71.0	71.6	72.2	73.0	73.9
105°	89.4	89.8	90.2	90.7	91.2	91.7	92.2	92.7	93.2	93.8	94.3
107.5°	112.5	113.0	113.4	113.8	114.3	114.6	115.0	115.5	115.8	116.1	116.3
110°	128.5	128.9	129.3	129.8	130.1	130.4	130.6	130.9	131.1	131.4	131.6



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.5	144.6	144.9	145.2	145.4	145.8	146.1	146.4	146.7	146.9	147.0
115°	168.5	168.9	169.3	169.6	169.9	170.0	170.2	170.4	170.6	170.5	170.4
117.5°	192.3	192.5	192.7	192.9	193.0	193.2	193.3	193.5	193.6	193.7	193.8
120°	207.7	208.1	208.5	209.0	209.2	209.3	209.4	209.5	209.6	209.6	209.6
122.5°	223.6	223.8	223.9	224.0	224.3	224.5	224.7	225.0	225.2	225.1	225.1
125°	246.0	246.5	247.0	247.5	247.9	248.0	248.1	248.1	248.2	248.1	247.9
127.5°	269.1	269.5	269.8	270.1	270.3	270.4	270.4	270.5	270.7	270.6	270.5
130°	283.4	283.8	284.2	284.6	285.0	285.2	285.3	285.5	285.7	285.6	285.5
132.5°	297.6	298.4	299.1	299.8	300.1	300.1	300.1	300.1	300.0	299.9	299.8
135°	319.8	320.3	320.8	321.3	321.6	321.7	321.8	321.8	321.9	321.9	321.9
137.5°	340.6	341.1	341.6	342.2	342.5	342.7	342.9	343.0	343.3	343.4	343.5
140°	354.0	354.4	354.8	355.2	355.7	355.9	356.2	356.5	356.7	356.9	357.1
142.5°	367.3	367.7	368.1	368.4	368.8	369.1	369.5	369.8	370.1	370.2	370.3
145°	387.1	387.4	387.8	388.1	388.4	388.7	388.9	389.2	389.4	389.4	389.4
147.5°	405.2	405.4	405.5	405.8	406.0	406.1	406.4	406.6	406.8	407.0	407.2
150°	417.1	417.0	416.9	416.8	417.0	417.3	417.7	418.0	418.4	418.4	418.4
152.5°	427.3	427.4	427.5	427.7	427.7	427.9	428.1	428.2	428.3	428.5	428.8
155°	442.6	442.6	442.6	442.6	442.6	442.6	442.7	442.8	442.9	443.2	443.6
157.5°	456.1	455.9	455.7	455.5	455.5	455.6	455.6	455.7	455.8	456.2	456.5
160°	464.2	463.8	463.6	463.3	463.2	463.3	463.4	463.5	463.6	464.0	464.3
162.5°	471.4	471.2	471.0	470.8	470.7	470.7	470.7	470.8	470.8	471.2	471.7
165°	481.0	480.8	480.6	480.4	480.4	480.5	480.6	480.7	480.8	481.1	481.5
167.5°	489.0	488.6	488.3	487.9	487.8	487.8	487.8	487.8	487.8	488.3	488.8
170°	493.3	492.9	492.6	492.2	492.1	492.1	492.1	492.1	492.1	492.6	493.1
172.5°	496.5	496.1	495.8	495.4	495.2	495.2	495.2	495.2	495.2	495.8	496.3
175°	499.9	499.6	499.2	498.9	498.7	498.7	498.7	498.7	498.7	499.2	499.7
177.5°	501.8	501.5	501.3	500.9	500.8	500.8	500.7	500.6	500.5	500.9	501.4
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.7	468.7	468.7	468.7	468.7	468.7	468.7
2.5°	490.3	491.5	494.2	493.3	494.5	495.2	495.8
5°	529.8	536.1	539.0	538.6	542.8	541.7	540.7
7.5°	574.5	581.2	585.0	589.6	592.3	592.5	594.9
10°	599.9	608.6	612.2	617.2	620.4	622.2	621.9
12.5°	619.2	626.1	634.1	636.5	640.8	643.2	642.3
15°	642.7	653.6	661.9	666.1	671.5	673.0	675.2
17.5°	663.5	678.1	687.9	700.9	705.8	708.8	707.0
20°	679.2	698.5	708.3	723.8	732.4	736.9	735.3
22.5°	697.8	718.8	736.8	750.2	763.2	769.4	770.7
25°	729.8	758.4	784.9	802.5	818.6	822.4	830.8
27.5°	765.4	799.2	827.5	846.1	857.3	861.5	864.2
30°	787.8	821.5	842.7	854.7	858.2	857.9	857.5
32.5°	798.8	819.8	824.0	820.6	812.4	805.5	798.2
35°	783.3	767.6	744.1	713.9	691.6	669.1	666.8
37.5°	704.5	654.2	615.1	571.4	546.3	530.7	520.0
40°	630.3	573.2	525.8	489.0	463.4	453.2	443.2
42.5°	549.7	495.2	453.2	422.5	403.2	391.9	384.1
45°	446.6	398.5	365.7	343.4	328.0	319.3	314.4
47.5°	366.0	330.4	302.5	286.4	275.9	269.1	269.1
50°	322.7	288.7	270.2	257.4	248.3	242.9	243.9
52.5°	284.3	258.9	243.1	232.5	225.7	222.4	222.2
55°	237.7	219.5	209.1	201.3	196.7	193.0	193.8
57.5°	203.4	188.0	181.0	174.5	171.3	169.9	167.6
60°	182.0	170.1	164.1	158.9	155.8	154.5	152.4
62.5°	163.1	153.7	147.9	143.7	140.9	140.4	138.7
65°	137.1	129.9	124.8	122.8	119.8	119.0	119.0
67.5°	113.0	107.9	103.8	102.0	100.7	100.9	100.0
70°	97.9	93.7	91.1	89.1	88.2	88.3	87.6
72.5°	85.7	80.9	78.7	77.5	76.2	76.7	76.4
75°	64.8	62.5	61.3	60.1	59.3	58.9	58.5
77.5°	47.6	45.5	44.6	43.9	44.1	43.0	43.8
80°	36.8	35.0	34.4	33.4	33.2	33.2	33.1
82.5°	26.9	25.9	25.5	24.7	24.3	24.6	24.1
85°	13.9	13.2	12.9	12.9	12.6	12.1	13.2
87.5°	6.6	6.0	6.1	6.0	6.0	5.9	5.7
90°	7.6	8.0	8.4	8.6	8.9	9.1	9.4
92.5°	16.7	17.3	17.7	17.8	18.0	18.3	18.4
95°	31.9	32.5	32.9	33.1	33.2	33.4	33.6
97.5°	49.6	50.1	50.5	50.5	50.7	50.8	50.9
100°	62.1	62.9	63.3	63.5	63.6	63.8	64.0
102.5°	74.7	75.6	76.1	76.4	76.6	76.9	77.1
105°	94.8	95.3	95.7	96.0	96.3	96.5	96.8
107.5°	116.6	116.8	117.0	117.0	116.9	116.9	116.9
110°	131.9	132.2	132.2	132.2	132.1	132.0	131.9



TEST NUMBER: P333341-935

CATALOG NUMBER: S125DIW-S375D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	147.1	147.2	147.2	147.1	146.9	146.7	146.5
115°	170.3	170.2	170.1	170.0	170.0	169.9	169.8
117.5°	193.8	193.9	193.8	193.5	193.1	192.7	192.3
120°	209.6	209.6	209.4	209.1	208.7	208.4	208.0
122.5°	225.0	224.9	224.7	224.5	224.2	223.9	223.6
125°	247.7	247.5	247.4	247.3	247.2	247.1	247.0
127.5°	270.4	270.4	270.2	270.0	269.8	269.7	269.5
130°	285.4	285.3	285.2	285.0	284.8	284.6	284.5
132.5°	299.7	299.6	299.5	299.3	299.0	298.8	298.5
135°	321.9	321.9	321.8	321.4	321.1	320.7	320.4
137.5°	343.5	343.7	343.5	343.1	342.7	342.2	341.7
140°	357.2	357.4	357.2	356.8	356.4	355.9	355.5
142.5°	370.4	370.5	370.3	369.9	369.5	369.0	368.6
145°	389.4	389.4	389.3	389.1	388.8	388.6	388.3
147.5°	407.4	407.6	407.4	406.8	406.2	405.6	405.1
150°	418.4	418.4	418.3	418.1	417.9	417.8	417.6
152.5°	429.0	429.1	429.1	428.8	428.5	428.2	427.8
155°	443.9	444.3	444.3	443.8	443.4	443.0	442.6
157.5°	456.8	457.2	457.1	456.5	455.9	455.4	454.8
160°	464.7	465.0	464.9	464.5	464.1	463.6	463.2
162.5°	472.0	472.4	472.4	471.9	471.4	470.9	470.4
165°	481.8	482.2	482.1	481.6	481.0	480.5	480.0
167.5°	489.3	489.8	489.8	489.2	488.7	488.2	487.7
170°	493.6	494.2	494.1	493.5	492.9	492.3	491.7
172.5°	496.8	497.3	497.3	496.7	496.2	495.7	495.2
175°	500.3	500.8	500.8	500.2	499.6	498.9	498.3
177.5°	501.8	502.2	502.1	501.7	501.2	500.7	500.2
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4

(END OF REPORT)