

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333416-935

Luminaire Tested: **S125DIW-S850D1050U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333416-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1050U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6550.9 lumens  
Efficiency: N/A  
Efficacy: 124.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333416-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333416-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333416-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	1.6
10°-20°	301.0	4.6
20°-30°	444.5	6.8
30°-40°	518.7	7.9
40°-50°	520.9	8.0
50°-60°	457.3	7.0
60°-70°	340.7	5.2
70°-80°	194.8	3.0
80°-90°	59.1	0.9
90°-100°	42.7	0.7
100°-110°	263.1	4.0
110°-120°	477.1	7.3
120°-130°	612.4	9.3
130°-140°	658.7	10.1
140°-150°	618.2	9.4
150°-160°	500.1	7.6
160°-170°	323.4	4.9
170°-180°	111.6	1.7
0°-30°	852.1	13.0
0°-40°	1370.8	20.9
0°-60°	2348.9	35.9
0°-90°	2943.6	44.9
90°-120°	782.9	12.0
90°-150°	2672.2	40.8
90°-180°	3607.0	55.1
0°-180°	6550.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	1	8	14	18	21	5
95°	50	45	14	18	18	63
105°	256	259	260	259	259	271
115°	481	485	486	482	477	476
125°	684	689	690	686	684	610
135°	852	857	856	854	849	657
145°	988	990	990	991	986	618
155°	1088	1084	1085	1087	1081	501
165°	1149	1144	1144	1149	1142	324
175°	1175	1170	1170	1177	1170	112
180°	1175	1175	1175	1175	1175	



TEST NUMBER: P333416-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.5	19.8	20.1	20.4	20.8	20.9	21.0	21.2	21.3	21.4	21.6
90°	0.9	2.4	4.0	5.5	7.1	8.5	9.9	11.2	12.6	13.9	14.9
92.5°	13.4	12.3	11.3	10.2	9.0	9.1	10.3	11.5	12.7	13.9	14.9
95°	49.6	49.1	48.5	47.9	47.4	43.3	36.0	28.7	21.3	13.9	14.9
97.5°	103.7	104.7	105.7	106.8	107.8	101.1	86.5	72.0	57.4	42.9	37.4
100°	145.4	146.0	146.5	147.1	147.7	148.4	149.2	150.0	150.8	151.5	122.7
102.5°	188.0	188.6	189.4	190.1	190.9	191.5	191.9	192.3	192.9	193.3	187.9
105°	256.0	256.8	257.5	258.3	259.1	259.5	259.5	259.5	259.5	259.5	259.5
107.5°	326.7	326.7	326.7	326.7	326.7	326.9	327.3	327.7	328.0	328.5	328.5
110°	372.7	372.7	372.7	372.7	372.7	372.9	373.2	373.7	374.0	374.4	373.8



TEST NUMBER: P333416-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.9	416.4	416.8	417.2	417.8	418.1	418.4	418.5	418.8	419.0	418.3
115°	480.7	481.6	482.6	483.5	484.6	485.1	485.3	485.5	485.7	485.9	485.1
117.5°	547.8	547.7	547.7	547.6	547.6	547.9	548.6	549.4	550.1	550.9	549.8
120°	589.5	589.4	589.1	588.9	588.8	588.9	589.5	590.1	590.6	591.2	590.9
122.5°	626.5	627.2	627.9	628.6	629.4	629.9	630.2	630.4	630.7	630.9	630.6
125°	683.5	684.9	686.3	687.6	689.0	689.7	689.7	689.7	689.7	689.7	688.9
127.5°	738.0	739.1	740.0	741.0	741.9	742.4	742.3	742.2	742.0	741.9	741.5
130°	771.5	772.5	773.4	774.4	775.4	775.9	776.2	776.4	776.5	776.7	776.2
132.5°	804.9	806.1	807.2	808.3	809.4	809.8	809.3	808.9	808.5	808.1	808.0
135°	852.5	853.7	854.8	856.0	857.1	857.6	857.1	856.8	856.4	856.0	855.6
137.5°	896.2	897.2	898.2	899.2	900.3	900.6	900.3	899.9	899.5	899.1	899.2
140°	924.8	925.1	925.6	925.9	926.3	926.4	926.3	926.0	925.8	925.7	926.0
142.5°	950.5	950.8	951.1	951.2	951.5	951.7	952.0	952.3	952.5	952.8	952.9
145°	988.3	988.8	989.1	989.5	989.9	990.1	990.1	990.1	990.1	990.1	990.3
147.5°	1021.4	1021.4	1021.3	1021.2	1021.1	1021.2	1021.4	1021.7	1021.9	1022.1	1022.4
150°	1042.3	1042.0	1041.6	1041.2	1040.8	1040.8	1041.2	1041.6	1042.0	1042.3	1042.8
152.5°	1062.6	1061.7	1060.8	1060.0	1059.1	1058.9	1059.3	1059.7	1060.1	1060.4	1060.8
155°	1088.5	1087.4	1086.2	1085.0	1083.8	1083.5	1083.8	1084.3	1084.6	1085.0	1085.5
157.5°	1108.5	1107.8	1107.2	1106.5	1105.7	1105.4	1105.4	1105.4	1105.5	1105.5	1106.2
160°	1122.5	1121.3	1120.2	1119.0	1117.8	1117.3	1117.5	1117.8	1117.9	1118.1	1118.9
162.5°	1133.6	1132.5	1131.3	1130.1	1128.9	1128.4	1128.7	1128.9	1129.0	1129.2	1130.3
165°	1148.6	1147.5	1146.2	1145.1	1143.9	1143.4	1143.7	1143.8	1144.0	1144.2	1145.4
167.5°	1159.7	1158.6	1157.4	1156.2	1154.9	1154.4	1154.6	1154.8	1155.0	1155.2	1156.6
170°	1166.0	1164.7	1163.3	1161.9	1160.5	1160.0	1160.2	1160.4	1160.5	1160.8	1162.4
172.5°	1170.2	1168.8	1167.4	1166.1	1164.8	1164.2	1164.6	1164.9	1165.3	1165.6	1167.0
175°	1174.7	1173.5	1172.3	1171.2	1170.0	1169.6	1169.8	1169.9	1170.2	1170.4	1171.9
177.5°	1176.8	1175.9	1174.9	1174.0	1173.1	1172.7	1172.9	1173.0	1173.1	1173.3	1174.4
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7



TEST NUMBER: P333416-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	21.8	22.0	22.1	22.1	22.0	21.8	21.5	21.4
90°	15.8	16.9	17.8	18.6	19.2	19.7	20.3	20.9
92.5°	15.8	16.9	17.8	18.4	18.7	18.9	19.2	19.5
95°	15.8	16.9	17.8	18.3	18.3	18.3	18.3	18.3
97.5°	31.9	26.4	21.0	18.3	18.3	18.3	18.3	18.3
100°	93.8	65.0	36.2	21.4	20.6	19.8	19.0	18.3
102.5°	182.4	176.9	171.5	162.2	149.0	135.9	122.7	109.5
105°	259.5	259.5	259.5	259.4	259.2	259.0	258.8	258.6
107.5°	328.6	328.6	328.6	328.4	327.8	327.2	326.6	326.1
110°	373.2	372.7	372.1	372.0	372.1	372.3	372.5	372.7





TEST NUMBER: P333416-935

CATALOG NUMBER: S125DIW-S850D1050U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	417.6	416.8	416.1	415.6	415.3	415.0	414.7	414.5
115°	484.3	483.5	482.8	481.8	480.7	479.5	478.4	477.2
117.5°	548.9	547.9	546.8	546.0	545.6	545.1	544.6	544.1
120°	590.5	590.1	589.7	589.0	588.1	587.1	586.2	585.1
122.5°	630.2	629.8	629.4	628.7	627.6	626.5	625.3	624.2
125°	688.1	687.3	686.6	685.9	685.4	684.8	684.2	683.5
127.5°	741.1	740.6	740.2	739.3	737.9	736.4	734.9	733.6
130°	775.6	775.0	774.4	773.6	772.7	771.7	770.8	769.8
132.5°	807.9	807.7	807.6	807.1	806.2	805.1	804.2	803.2
135°	855.2	854.8	854.5	853.7	852.5	851.4	850.2	849.0
137.5°	899.3	899.4	899.5	899.1	898.0	897.0	896.0	895.0
140°	926.4	926.8	927.2	926.8	925.7	924.5	923.3	922.1
142.5°	953.0	953.0	953.1	952.6	951.4	950.3	949.1	948.0
145°	990.5	990.7	990.8	990.4	989.2	988.1	986.9	985.8
147.5°	1022.6	1022.9	1023.0	1022.5	1021.1	1019.7	1018.3	1016.9
150°	1043.1	1043.5	1043.9	1043.3	1041.7	1040.2	1038.6	1037.1
152.5°	1061.2	1061.6	1062.0	1061.5	1060.1	1058.7	1057.3	1055.9
155°	1086.2	1086.8	1087.4	1086.8	1085.3	1083.7	1082.2	1080.6
157.5°	1106.8	1107.4	1108.0	1107.6	1106.0	1104.5	1102.9	1101.4
160°	1119.6	1120.4	1121.2	1120.8	1119.3	1117.8	1116.2	1114.7
162.5°	1131.4	1132.5	1133.6	1133.2	1131.5	1129.9	1128.2	1126.4
165°	1146.5	1147.7	1148.8	1148.7	1147.1	1145.6	1144.0	1142.5
167.5°	1158.0	1159.3	1160.8	1160.6	1158.8	1157.1	1155.4	1153.7
170°	1163.9	1165.4	1167.0	1166.8	1165.1	1163.4	1161.7	1159.9
172.5°	1168.5	1169.8	1171.2	1171.0	1169.3	1167.5	1165.8	1164.1
175°	1173.5	1175.0	1176.6	1176.5	1174.7	1172.9	1171.2	1169.5
177.5°	1175.4	1176.6	1177.7	1177.6	1176.3	1175.1	1173.9	1172.6
180°	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7	1174.7

(END OF REPORT)