

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333401-935

Luminaire Tested: **S125DIW-S850D470U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333401-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4372.7 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68
1	102	98	94	90	96	92	89	86	82	80	77	73	71	70	65	63	62	58
2	93	86	80	74	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	59	53	73	64	57	51	57	51	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	28
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	24
8	57	44	37	31	54	42	35	30	39	32	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6803	6803	6803	6803
5°	7878	6825	5977	6825
10°	9165	6790	5237	6790
15°	10146	6740	4831	6740
20°	11357	6661	4504	6661
25°	13304	6572	4345	6572
30°	14370	6485	4207	6485
35°	11815	6320	4117	6320
40°	8398	6091	4018	6091
45°	6452	5782	3961	5782
50°	5507	5399	3953	5399
55°	4904	5024	3987	5024
60°	4423	4614	4088	4614
65°	4085	4201	4195	4201
70°	3714	3773	4254	3773
75°	3281	3324	4217	3324
80°	2760	2708	3861	2708
85°	2186	1949	3112	1949



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.4	2.3
10°-20°	301.9	6.9
20°-30°	490.2	11.2
30°-40°	598.0	13.7
40°-50°	544.0	12.4
50°-60°	433.3	9.9
60°-70°	301.8	6.9
70°-80°	160.9	3.7
80°-90°	41.7	1.0
90°-100°	33.6	0.8
100°-110°	99.2	2.3
110°-120°	168.0	3.8
120°-130°	221.1	5.1
130°-140°	247.7	5.7
140°-150°	242.8	5.6
150°-160°	203.9	4.7
160°-170°	135.6	3.1
170°-180°	47.4	1.1
0°-30°	893.6	20.4
0°-40°	1491.6	34.1
0°-60°	2468.9	56.5
0°-90°	2973.4	68.0
90°-120°	300.8	6.9
90°-150°	1012.4	23.2
90°-180°	1399.0	32.0
0°-180°	4372.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1215	1053	922	1053	1215	122
15°	1517	1008	722	1008	1517	434
25°	1867	922	610	922	1867	853
35°	1499	802	522	802	1499	917
45°	706	633	434	633	706	565
55°	436	446	354	446	436	392
65°	267	275	274	275	267	265
75°	132	133	169	133	132	142
85°	30	26	42	26	30	34
90°	9	0	9	0	9	7
95°	34	25	34	25	34	34
105°	97	89	97	89	97	103
115°	170	168	170	168	170	168
125°	247	246	247	246	247	221
135°	320	319	320	319	320	247
145°	388	387	388	387	388	242
155°	443	443	443	443	443	204
165°	480	481	480	481	480	135
175°	498	500	498	500	498	47
180°	501	501	501	501	501	



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1114.1	1112.7	1111.3	1108.4	1110.5	1104.5	1101.6	1096.6	1090.5	1088.4	1085.9
5°	1215.1	1217.4	1219.6	1210.2	1211.2	1204.9	1190.6	1179.0	1169.6	1157.5	1149.0
7.5°	1336.8	1331.5	1331.0	1325.0	1314.5	1306.1	1291.1	1272.0	1253.4	1232.3	1214.9
10°	1397.6	1398.0	1394.0	1386.8	1375.7	1367.6	1348.0	1329.1	1306.4	1279.5	1260.3
12.5°	1443.4	1445.2	1440.1	1430.5	1425.0	1407.0	1391.5	1369.2	1342.1	1320.7	1291.4
15°	1517.4	1512.4	1508.9	1496.8	1487.5	1468.7	1444.1	1420.8	1391.3	1364.0	1336.8
17.5°	1588.7	1592.7	1586.0	1574.9	1545.8	1523.9	1490.9	1459.1	1422.4	1385.8	1353.2
20°	1652.4	1656.0	1645.7	1626.5	1591.6	1569.7	1526.3	1485.2	1442.7	1395.8	1360.0
22.5°	1731.8	1729.0	1715.1	1685.8	1655.6	1615.1	1568.1	1518.1	1464.9	1411.9	1364.3
25°	1867.0	1848.2	1839.7	1803.5	1763.8	1704.3	1639.9	1566.6	1500.4	1430.2	1369.4
27.5°	1941.9	1936.0	1926.6	1901.3	1859.5	1796.0	1720.0	1630.6	1537.3	1448.7	1369.2
30°	1926.9	1927.8	1928.7	1920.6	1893.9	1846.0	1770.5	1674.3	1563.4	1463.7	1371.7
32.5°	1793.9	1810.2	1825.7	1844.1	1851.6	1842.5	1795.1	1708.3	1594.2	1480.9	1370.2
35°	1498.6	1503.6	1554.0	1604.1	1672.1	1724.8	1760.1	1721.7	1625.6	1495.5	1368.5
37.5°	1168.5	1192.7	1227.6	1284.2	1382.2	1470.1	1583.0	1635.0	1604.0	1500.2	1365.4
40°	996.1	1018.5	1041.2	1098.9	1181.6	1288.1	1416.3	1525.9	1551.3	1485.2	1354.6
42.5°	863.1	880.7	906.0	949.4	1018.6	1112.8	1235.4	1378.5	1466.6	1441.6	1332.1
45°	706.4	717.6	737.3	771.6	821.7	895.5	1003.7	1160.2	1296.5	1341.7	1278.7
47.5°	604.6	604.5	619.8	643.6	679.8	742.4	822.4	945.0	1090.7	1198.4	1193.4
50°	548.1	545.9	557.9	578.5	607.1	648.7	725.1	823.0	963.0	1085.0	1119.0
52.5°	499.5	499.7	507.1	522.4	546.3	581.9	638.9	727.2	846.8	972.1	1036.0
55°	435.5	433.7	442.1	452.5	469.8	493.1	534.3	601.8	698.8	822.2	905.3
57.5°	376.8	381.7	385.1	392.3	406.7	422.3	457.0	506.5	583.5	689.4	777.3
60°	342.4	347.4	350.1	357.2	368.9	382.3	409.1	449.4	514.1	605.4	692.5
62.5°	311.7	315.6	316.4	322.9	332.3	345.4	366.5	400.3	451.5	531.3	616.7
65°	267.3	267.3	269.1	275.9	280.3	292.0	308.1	332.6	373.8	435.9	508.8
67.5°	224.6	226.8	226.3	229.3	233.4	242.4	253.9	274.2	304.7	350.1	408.4
70°	196.7	198.5	198.0	200.3	204.7	210.6	220.0	239.2	261.1	300.0	350.1
72.5°	171.7	172.4	171.3	174.2	176.8	181.9	192.4	202.7	223.2	256.0	297.1
75°	131.5	132.3	133.2	135.0	137.7	140.3	145.8	156.0	169.4	194.1	220.4
77.5°	98.5	96.9	99.0	98.8	100.2	102.3	107.0	112.4	123.5	139.1	159.5
80°	74.2	74.6	74.6	75.1	77.3	78.7	82.7	86.7	95.2	106.9	121.1
82.5°	54.2	55.4	54.7	55.4	57.3	58.3	60.5	63.8	68.8	77.9	88.3
85°	29.5	27.3	28.2	29.1	29.1	29.5	31.3	32.6	35.3	38.9	42.9
87.5°	10.4	11.1	11.5	11.4	11.7	11.6	12.9	12.8	13.9	14.8	16.2
90°	9.4	9.1	8.9	8.6	8.4	8.0	7.6	7.1	6.7	6.3	5.6
92.5°	18.4	18.3	18.0	17.8	17.7	17.3	16.7	16.1	15.6	15.0	14.2
95°	33.6	33.4	33.2	33.1	32.9	32.5	31.9	31.3	30.7	30.0	29.2
97.5°	50.9	50.8	50.7	50.5	50.5	50.1	49.6	49.0	48.4	47.9	46.7
100°	64.0	63.8	63.6	63.5	63.3	62.9	62.1	61.3	60.5	59.7	58.5
102.5°	77.1	76.9	76.6	76.4	76.1	75.6	74.7	73.9	73.0	72.2	71.6
105°	96.8	96.5	96.3	96.0	95.7	95.3	94.8	94.3	93.8	93.2	92.7
107.5°	116.9	116.9	116.9	117.0	117.0	116.8	116.6	116.3	116.1	115.8	115.5
110°	131.9	132.0	132.1	132.2	132.2	132.2	131.9	131.6	131.4	131.1	130.9



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.5	146.7	146.9	147.1	147.2	147.2	147.1	147.0	146.9	146.7	146.4
115°	169.8	169.9	170.0	170.0	170.1	170.2	170.3	170.4	170.5	170.6	170.4
117.5°	192.3	192.7	193.1	193.5	193.8	193.9	193.8	193.8	193.7	193.6	193.5
120°	208.0	208.4	208.7	209.1	209.4	209.6	209.6	209.6	209.6	209.6	209.5
122.5°	223.6	223.9	224.2	224.5	224.7	224.9	225.0	225.1	225.1	225.2	225.0
125°	247.0	247.1	247.2	247.3	247.4	247.5	247.7	247.9	248.1	248.2	248.1
127.5°	269.5	269.7	269.8	270.0	270.2	270.4	270.4	270.5	270.6	270.7	270.5
130°	284.5	284.6	284.8	285.0	285.2	285.3	285.4	285.5	285.6	285.7	285.5
132.5°	298.5	298.8	299.0	299.3	299.5	299.6	299.7	299.8	299.9	300.0	300.1
135°	320.4	320.7	321.1	321.4	321.8	321.9	321.9	321.9	321.9	321.9	321.8
137.5°	341.7	342.2	342.7	343.1	343.5	343.7	343.5	343.5	343.4	343.3	343.0
140°	355.5	355.9	356.4	356.8	357.2	357.4	357.2	357.1	356.9	356.7	356.5
142.5°	368.6	369.0	369.5	369.9	370.3	370.5	370.4	370.3	370.2	370.1	369.8
145°	388.3	388.6	388.8	389.1	389.3	389.4	389.4	389.4	389.4	389.4	389.2
147.5°	405.1	405.6	406.2	406.8	407.4	407.6	407.4	407.2	407.0	406.8	406.6
150°	417.6	417.8	417.9	418.1	418.3	418.4	418.4	418.4	418.4	418.4	418.0
152.5°	427.8	428.2	428.5	428.8	429.1	429.1	429.0	428.8	428.5	428.3	428.2
155°	442.6	443.0	443.4	443.8	444.3	444.3	443.9	443.6	443.2	442.9	442.8
157.5°	454.8	455.4	455.9	456.5	457.1	457.2	456.8	456.5	456.2	455.8	455.7
160°	463.2	463.6	464.1	464.5	464.9	465.0	464.7	464.3	464.0	463.6	463.5
162.5°	470.4	470.9	471.4	471.9	472.4	472.4	472.0	471.7	471.2	470.8	470.8
165°	480.0	480.5	481.0	481.6	482.1	482.2	481.8	481.5	481.1	480.8	480.7
167.5°	487.7	488.2	488.7	489.2	489.8	489.8	489.3	488.8	488.3	487.8	487.8
170°	491.7	492.3	492.9	493.5	494.1	494.2	493.6	493.1	492.6	492.1	492.1
172.5°	495.2	495.7	496.2	496.7	497.3	497.3	496.8	496.3	495.8	495.2	495.2
175°	498.3	498.9	499.6	500.2	500.8	500.8	500.3	499.7	499.2	498.7	498.7
177.5°	500.2	500.7	501.2	501.7	502.1	502.2	501.8	501.4	500.9	500.5	500.6
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1083.7	1081.2	1078.3	1073.3	1067.3	1064.0	1059.0	1055.8	1049.4	1044.0	1038.3
5°	1138.7	1127.0	1116.4	1102.5	1087.3	1077.5	1065.8	1052.8	1039.5	1025.6	1010.4
7.5°	1195.7	1175.1	1152.7	1128.7	1105.2	1083.6	1062.9	1042.6	1023.6	1000.7	981.4
10°	1233.9	1208.0	1180.3	1147.6	1115.9	1088.2	1060.1	1035.4	1010.4	983.6	959.8
12.5°	1272.2	1237.7	1198.5	1162.7	1124.5	1091.1	1057.9	1026.5	995.1	965.4	937.7
15°	1299.2	1268.8	1232.6	1181.6	1138.7	1092.7	1048.9	1008.1	970.2	937.1	902.2
17.5°	1317.0	1277.8	1239.0	1190.1	1133.8	1082.3	1032.7	986.1	943.2	901.3	867.7
20°	1320.3	1280.0	1239.3	1191.5	1133.8	1074.8	1025.2	969.2	923.3	879.9	838.7
22.5°	1319.1	1273.6	1229.2	1180.0	1123.8	1069.4	1009.4	952.4	902.5	859.8	816.9
25°	1309.1	1260.3	1204.9	1155.3	1099.8	1042.2	981.4	922.3	871.3	822.6	780.2
27.5°	1300.6	1237.4	1174.7	1116.8	1063.2	1010.4	952.2	891.7	835.3	785.8	745.8
30°	1290.3	1221.0	1150.3	1089.9	1035.0	983.6	928.6	869.6	810.5	762.2	719.4
32.5°	1281.0	1200.2	1125.7	1060.0	1001.7	951.7	901.0	844.9	787.0	738.0	695.0
35°	1263.0	1169.6	1084.2	1010.0	947.8	896.4	853.9	801.6	748.4	701.0	659.9
37.5°	1240.2	1129.3	1037.7	959.8	891.7	837.6	798.1	757.9	706.8	661.2	624.0
40°	1222.3	1100.7	1003.7	924.1	853.5	797.1	760.5	722.5	680.0	637.6	598.2
42.5°	1199.8	1075.0	969.4	883.7	813.7	758.9	720.4	688.1	650.7	611.1	574.5
45°	1158.4	1028.3	913.9	821.7	751.1	697.0	657.2	633.1	604.9	567.3	536.5
47.5°	1097.5	972.2	853.9	758.8	685.9	635.8	598.5	575.3	555.4	527.5	499.6
50°	1043.4	930.4	810.5	716.2	643.3	592.8	558.4	537.4	520.4	498.9	475.3
52.5°	983.0	877.8	768.0	674.8	602.6	552.8	519.1	500.6	486.5	471.1	447.7
55°	887.0	797.6	695.7	607.1	540.5	491.8	462.3	446.2	434.5	422.9	408.6
57.5°	781.2	711.3	621.0	540.1	478.7	434.4	406.8	391.2	382.2	376.2	367.7
60°	706.8	647.0	569.1	495.3	435.5	396.1	369.3	357.2	349.7	344.7	338.5
62.5°	637.8	588.7	516.5	449.2	396.8	359.6	335.7	324.0	316.7	314.3	309.1
65°	536.1	498.1	438.6	382.7	338.0	306.3	286.1	274.9	270.4	267.8	268.3
67.5°	435.8	412.7	364.9	317.3	281.5	254.9	238.8	230.2	228.0	224.5	224.4
70°	374.6	357.2	317.0	275.4	243.7	223.1	208.8	199.8	197.6	195.8	195.4
72.5°	320.6	305.4	270.4	237.1	208.6	190.5	178.7	173.4	169.7	168.7	168.6
75°	241.0	232.5	204.7	178.4	158.7	146.2	138.2	133.2	130.5	130.1	130.5
77.5°	171.3	163.9	146.3	127.6	115.2	105.7	98.9	97.2	94.2	94.3	93.8
80°	128.7	123.8	112.7	97.9	87.6	79.6	76.0	72.8	72.0	70.6	72.0
82.5°	93.3	88.1	80.5	71.1	62.6	57.8	54.2	53.2	52.7	52.0	52.3
85°	46.1	46.5	42.0	34.9	31.3	28.6	26.3	26.3	25.9	25.5	25.9
87.5°	16.7	15.9	14.4	13.2	11.2	10.0	9.6	9.7	8.8	8.6	9.0
90°	5.0	4.4	3.8	3.2	2.5	1.8	1.1	0.4	1.1	1.8	2.5
92.5°	13.5	12.7	12.0	11.4	10.9	10.4	9.9	9.5	9.9	10.4	10.9
95°	28.3	27.5	26.6	26.1	25.9	25.7	25.6	25.4	25.6	25.7	25.9
97.5°	45.5	44.3	43.0	42.4	42.4	42.3	42.2	42.1	42.2	42.3	42.4
100°	57.4	56.3	55.2	54.7	54.7	54.7	54.7	54.7	54.7	54.7	54.7
102.5°	71.0	70.5	69.9	69.5	69.1	68.8	68.4	68.0	68.4	68.8	69.1
105°	92.2	91.7	91.2	90.7	90.2	89.8	89.4	88.9	89.4	89.8	90.2
107.5°	115.0	114.6	114.3	113.8	113.4	113.0	112.5	112.1	112.5	113.0	113.4
110°	130.6	130.4	130.1	129.8	129.3	128.9	128.5	128.0	128.5	128.9	129.3



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	146.1	145.8	145.4	145.2	144.9	144.6	144.5	144.2	144.5	144.6	144.9
115°	170.2	170.0	169.9	169.6	169.3	168.9	168.5	168.2	168.5	168.9	169.3
117.5°	193.3	193.2	193.0	192.9	192.7	192.5	192.3	192.3	192.3	192.5	192.7
120°	209.4	209.3	209.2	209.0	208.5	208.1	207.7	207.2	207.7	208.1	208.5
122.5°	224.7	224.5	224.3	224.0	223.9	223.8	223.6	223.4	223.6	223.8	223.9
125°	248.1	248.0	247.9	247.5	247.0	246.5	246.0	245.5	246.0	246.5	247.0
127.5°	270.4	270.4	270.3	270.1	269.8	269.5	269.1	268.9	269.1	269.5	269.8
130°	285.3	285.2	285.0	284.6	284.2	283.8	283.4	282.9	283.4	283.8	284.2
132.5°	300.1	300.1	300.1	299.8	299.1	298.4	297.6	297.0	297.6	298.4	299.1
135°	321.8	321.7	321.6	321.3	320.8	320.3	319.8	319.2	319.8	320.3	320.8
137.5°	342.9	342.7	342.5	342.2	341.6	341.1	340.6	340.1	340.6	341.1	341.6
140°	356.2	355.9	355.7	355.2	354.8	354.4	354.0	353.5	354.0	354.4	354.8
142.5°	369.5	369.1	368.8	368.4	368.1	367.7	367.3	367.0	367.3	367.7	368.1
145°	388.9	388.7	388.4	388.1	387.8	387.4	387.1	386.8	387.1	387.4	387.8
147.5°	406.4	406.1	406.0	405.8	405.5	405.4	405.2	405.0	405.2	405.4	405.5
150°	417.7	417.3	417.0	416.8	416.9	417.0	417.1	417.2	417.1	417.0	416.9
152.5°	428.1	427.9	427.7	427.7	427.5	427.4	427.3	427.1	427.3	427.4	427.5
155°	442.7	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.6
157.5°	455.6	455.6	455.5	455.5	455.7	455.9	456.1	456.2	456.1	455.9	455.7
160°	463.4	463.3	463.2	463.3	463.6	463.8	464.2	464.4	464.2	463.8	463.6
162.5°	470.7	470.7	470.7	470.8	471.0	471.2	471.4	471.6	471.4	471.2	471.0
165°	480.6	480.5	480.4	480.4	480.6	480.8	481.0	481.1	481.0	480.8	480.6
167.5°	487.8	487.8	487.8	487.9	488.3	488.6	489.0	489.3	489.0	488.6	488.3
170°	492.1	492.1	492.1	492.2	492.6	492.9	493.3	493.6	493.3	492.9	492.6
172.5°	495.2	495.2	495.2	495.4	495.8	496.1	496.5	496.8	496.5	496.1	495.8
175°	498.7	498.7	498.7	498.9	499.2	499.6	499.9	500.3	499.9	499.6	499.2
177.5°	500.7	500.8	500.8	500.9	501.3	501.5	501.8	502.0	501.8	501.5	501.3
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1035.1	1031.1	1027.9	1020.8	1016.8	1011.5	1007.2	1011.8	1006.9	1009.0	1005.7
5°	1002.8	990.3	981.4	968.4	957.2	946.9	939.4	938.0	934.4	932.6	927.2
7.5°	964.0	948.3	933.0	916.0	901.6	887.1	877.8	870.1	865.0	858.3	853.8
10°	941.1	920.1	902.2	881.7	863.8	848.1	835.6	829.3	823.5	815.0	811.9
12.5°	912.8	891.1	869.3	847.3	830.2	812.7	801.9	792.5	788.5	778.9	777.9
15°	879.0	846.4	824.8	802.5	778.8	764.5	755.5	745.3	740.8	734.1	729.2
17.5°	838.5	809.4	782.6	759.4	739.1	727.0	715.9	708.9	701.2	696.8	688.8
20°	809.3	781.5	754.7	730.0	714.5	700.6	691.6	684.9	676.9	674.7	666.6
22.5°	784.5	754.0	728.2	707.6	690.4	674.9	665.1	660.6	655.0	648.2	646.5
25°	744.4	712.6	690.8	670.2	655.0	640.7	634.0	628.2	622.8	617.9	616.0
27.5°	709.7	681.3	655.3	636.7	623.5	610.4	604.5	597.4	593.6	589.6	584.8
30°	685.4	656.3	633.5	615.6	601.3	589.7	583.4	578.5	575.0	571.4	568.7
32.5°	660.3	633.4	611.3	593.8	579.5	570.8	565.2	561.7	557.8	553.5	550.1
35°	627.2	597.7	576.3	561.1	549.9	543.2	536.9	533.8	529.3	529.3	525.7
37.5°	590.0	564.5	545.5	531.7	521.7	515.7	508.9	506.7	503.9	502.0	500.8
40°	567.8	544.1	526.2	512.4	501.6	496.7	491.4	487.8	485.9	483.7	482.8
42.5°	544.9	522.3	505.1	492.3	483.0	478.8	473.8	471.3	467.7	464.8	464.3
45°	510.1	488.2	472.6	462.3	454.3	449.4	446.2	440.8	439.0	435.5	435.0
47.5°	477.1	456.1	440.7	432.3	425.2	421.2	416.3	411.0	408.9	407.1	406.9
50°	452.5	433.3	418.9	410.9	404.2	398.4	393.4	389.9	388.5	388.5	389.4
52.5°	427.4	411.0	398.9	389.1	382.7	376.5	372.0	369.8	367.7	369.9	371.5
55°	390.7	374.2	365.2	355.9	349.7	342.4	340.3	339.3	338.0	341.6	343.4
57.5°	352.0	340.4	329.8	320.6	315.0	310.8	307.8	307.2	309.7	311.4	317.3
60°	327.3	313.8	304.4	297.3	290.6	287.9	287.1	286.1	287.9	292.8	300.4
62.5°	300.1	289.2	279.1	273.7	268.8	264.3	264.2	264.7	268.3	273.9	281.5
65°	260.2	250.8	244.1	237.8	233.8	231.2	232.0	233.8	237.8	245.5	253.9
67.5°	219.7	213.3	207.2	202.2	198.3	198.3	199.2	201.9	206.6	215.4	223.2
70°	193.6	186.4	181.5	179.3	176.2	174.4	177.0	181.5	185.5	193.6	200.3
72.5°	167.5	161.4	157.6	156.0	154.7	153.3	154.1	158.9	164.5	172.5	180.3
75°	128.7	126.5	123.8	122.1	120.7	121.6	122.5	127.0	131.5	139.9	148.9
77.5°	93.9	91.6	90.1	89.6	88.9	89.3	91.9	95.1	99.5	105.7	112.4
80°	71.1	70.2	69.3	68.9	68.9	69.3	72.8	75.1	79.1	85.0	90.3
82.5°	51.7	51.2	51.1	51.0	51.3	51.4	53.6	56.5	59.8	64.2	68.9
85°	27.3	26.3	27.7	28.2	27.3	28.6	29.5	31.3	32.6	34.9	37.1
87.5°	9.6	10.4	10.2	10.7	10.8	11.6	11.4	12.8	13.7	14.5	14.2
90°	3.2	3.8	4.4	5.0	5.6	6.3	6.7	7.1	7.6	8.0	8.4
92.5°	11.4	12.0	12.7	13.5	14.2	15.0	15.6	16.1	16.7	17.3	17.7
95°	26.1	26.6	27.5	28.3	29.2	30.0	30.7	31.3	31.9	32.5	32.9
97.5°	42.4	43.0	44.3	45.5	46.7	47.9	48.4	49.0	49.6	50.1	50.5
100°	54.7	55.2	56.3	57.4	58.5	59.7	60.5	61.3	62.1	62.9	63.3
102.5°	69.5	69.9	70.5	71.0	71.6	72.2	73.0	73.9	74.7	75.6	76.1
105°	90.7	91.2	91.7	92.2	92.7	93.2	93.8	94.3	94.8	95.3	95.7
107.5°	113.8	114.3	114.6	115.0	115.5	115.8	116.1	116.3	116.6	116.8	117.0
110°	129.8	130.1	130.4	130.6	130.9	131.1	131.4	131.6	131.9	132.2	132.2



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	145.2	145.4	145.8	146.1	146.4	146.7	146.9	147.0	147.1	147.2	147.2
115°	169.6	169.9	170.0	170.2	170.4	170.6	170.5	170.4	170.3	170.2	170.1
117.5°	192.9	193.0	193.2	193.3	193.5	193.6	193.7	193.8	193.8	193.9	193.8
120°	209.0	209.2	209.3	209.4	209.5	209.6	209.6	209.6	209.6	209.6	209.4
122.5°	224.0	224.3	224.5	224.7	225.0	225.2	225.1	225.1	225.0	224.9	224.7
125°	247.5	247.9	248.0	248.1	248.1	248.2	248.1	247.9	247.7	247.5	247.4
127.5°	270.1	270.3	270.4	270.4	270.5	270.7	270.6	270.5	270.4	270.4	270.2
130°	284.6	285.0	285.2	285.3	285.5	285.7	285.6	285.5	285.4	285.3	285.2
132.5°	299.8	300.1	300.1	300.1	300.1	300.0	299.9	299.8	299.7	299.6	299.5
135°	321.3	321.6	321.7	321.8	321.8	321.9	321.9	321.9	321.9	321.9	321.8
137.5°	342.2	342.5	342.7	342.9	343.0	343.3	343.4	343.5	343.5	343.7	343.5
140°	355.2	355.7	355.9	356.2	356.5	356.7	356.9	357.1	357.2	357.4	357.2
142.5°	368.4	368.8	369.1	369.5	369.8	370.1	370.2	370.3	370.4	370.5	370.3
145°	388.1	388.4	388.7	388.9	389.2	389.4	389.4	389.4	389.4	389.4	389.3
147.5°	405.8	406.0	406.1	406.4	406.6	406.8	407.0	407.2	407.4	407.6	407.4
150°	416.8	417.0	417.3	417.7	418.0	418.4	418.4	418.4	418.4	418.4	418.3
152.5°	427.7	427.7	427.9	428.1	428.2	428.3	428.5	428.8	429.0	429.1	429.1
155°	442.6	442.6	442.6	442.7	442.8	442.9	443.2	443.6	443.9	444.3	444.3
157.5°	455.5	455.5	455.6	455.6	455.7	455.8	456.2	456.5	456.8	457.2	457.1
160°	463.3	463.2	463.3	463.4	463.5	463.6	464.0	464.3	464.7	465.0	464.9
162.5°	470.8	470.7	470.7	470.7	470.8	470.8	471.2	471.7	472.0	472.4	472.4
165°	480.4	480.4	480.5	480.6	480.7	480.8	481.1	481.5	481.8	482.2	482.1
167.5°	487.9	487.8	487.8	487.8	487.8	487.8	488.3	488.8	489.3	489.8	489.8
170°	492.2	492.1	492.1	492.1	492.1	492.1	492.6	493.1	493.6	494.2	494.1
172.5°	495.4	495.2	495.2	495.2	495.2	495.2	495.8	496.3	496.8	497.3	497.3
175°	498.9	498.7	498.7	498.7	498.7	498.7	499.2	499.7	500.3	500.8	500.8
177.5°	500.9	500.8	500.8	500.7	500.6	500.5	500.9	501.4	501.8	502.2	502.1
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1003.6	1006.1	1003.9	1006.9	1003.9	1006.1	1003.6	1005.7	1009.0	1006.9	1011.8
5°	925.0	921.0	923.7	921.9	923.7	921.0	925.0	927.2	932.6	934.4	938.0
7.5°	852.4	848.5	844.2	842.1	844.2	848.5	852.4	853.8	858.3	865.0	870.1
10°	807.0	802.0	801.6	798.5	801.6	802.0	807.0	811.9	815.0	823.5	829.3
12.5°	773.7	769.1	764.1	762.8	764.1	769.1	773.7	777.9	778.9	788.5	792.5
15°	726.5	722.9	719.8	722.5	719.8	722.9	726.5	729.2	734.1	740.8	745.3
17.5°	687.3	684.3	683.7	680.4	683.7	684.3	687.3	688.8	696.8	701.2	708.9
20°	662.5	660.3	661.2	655.4	661.2	660.3	662.5	666.6	674.7	676.9	684.9
22.5°	642.9	638.5	638.0	636.8	638.0	638.5	642.9	646.5	648.2	655.0	660.6
25°	612.1	609.8	607.6	609.8	607.6	609.8	612.1	616.0	617.9	622.8	628.2
27.5°	585.1	582.5	581.9	582.1	581.9	582.5	585.1	584.8	589.6	593.6	597.4
30°	568.7	564.2	564.6	564.2	564.6	564.2	568.7	568.7	571.4	575.0	578.5
32.5°	550.8	547.8	547.2	546.3	547.2	547.8	550.8	550.1	553.5	557.8	561.7
35°	524.4	524.4	522.2	522.2	522.2	524.4	524.4	525.7	529.3	529.3	533.8
37.5°	499.6	499.2	497.8	498.1	497.8	499.2	499.6	500.8	502.0	503.9	506.7
40°	481.0	480.6	479.2	476.6	479.2	480.6	481.0	482.8	483.7	485.9	487.8
42.5°	463.1	461.7	461.1	460.1	461.1	461.7	463.1	464.3	464.8	467.7	471.3
45°	435.0	435.0	434.1	433.7	434.1	435.0	435.0	435.0	435.5	439.0	440.8
47.5°	407.7	408.5	410.2	409.9	410.2	408.5	407.7	406.9	407.1	408.9	411.0
50°	391.2	391.7	393.0	393.4	393.0	391.7	391.2	389.4	388.5	388.5	389.9
52.5°	373.0	375.6	377.2	376.9	377.2	375.6	373.0	371.5	369.9	367.7	369.8
55°	347.4	350.5	353.6	354.1	353.6	350.5	347.4	343.4	341.6	338.0	339.3
57.5°	322.1	326.5	329.8	330.8	329.8	326.5	322.1	317.3	311.4	309.7	307.2
60°	304.9	310.7	314.8	316.5	314.8	310.7	304.9	300.4	292.8	287.9	286.1
62.5°	288.4	295.0	299.0	299.4	299.0	295.0	288.4	281.5	273.9	268.3	264.7
65°	261.6	268.3	271.8	274.5	271.8	268.3	261.6	253.9	245.5	237.8	233.8
67.5°	232.6	239.3	243.2	245.4	243.2	239.3	232.6	223.2	215.4	206.6	201.9
70°	211.5	218.2	223.5	225.3	223.5	218.2	211.5	200.3	193.6	185.5	181.5
72.5°	190.7	196.7	201.0	203.1	201.0	196.7	190.7	180.3	172.5	164.5	158.9
75°	154.7	162.7	166.8	169.0	166.8	162.7	154.7	148.9	139.9	131.5	127.0
77.5°	119.2	126.7	129.1	130.2	129.1	126.7	119.2	112.4	105.7	99.5	95.1
80°	95.7	100.1	103.2	103.8	103.2	100.1	95.7	90.3	85.0	79.1	75.1
82.5°	73.5	77.2	78.3	79.4	78.3	77.2	73.5	68.9	64.2	59.8	56.5
85°	40.2	42.0	42.4	42.0	42.4	42.0	40.2	37.1	34.9	32.6	31.3
87.5°	15.0	14.6	14.7	15.5	14.7	14.6	15.0	14.2	14.5	13.7	12.8
90°	8.6	8.9	9.1	9.4	9.1	8.9	8.6	8.4	8.0	7.6	7.1
92.5°	17.8	18.0	18.3	18.4	18.3	18.0	17.8	17.7	17.3	16.7	16.1
95°	33.1	33.2	33.4	33.6	33.4	33.2	33.1	32.9	32.5	31.9	31.3
97.5°	50.5	50.7	50.8	50.9	50.8	50.7	50.5	50.5	50.1	49.6	49.0
100°	63.5	63.6	63.8	64.0	63.8	63.6	63.5	63.3	62.9	62.1	61.3
102.5°	76.4	76.6	76.9	77.1	76.9	76.6	76.4	76.1	75.6	74.7	73.9
105°	96.0	96.3	96.5	96.8	96.5	96.3	96.0	95.7	95.3	94.8	94.3
107.5°	117.0	116.9	116.9	116.9	116.9	116.9	117.0	117.0	116.8	116.6	116.3
110°	132.2	132.1	132.0	131.9	132.0	132.1	132.2	132.2	132.2	131.9	131.6



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	147.1	146.9	146.7	146.5	146.7	146.9	147.1	147.2	147.2	147.1	147.0
115°	170.0	170.0	169.9	169.8	169.9	170.0	170.0	170.1	170.2	170.3	170.4
117.5°	193.5	193.1	192.7	192.3	192.7	193.1	193.5	193.8	193.9	193.8	193.8
120°	209.1	208.7	208.4	208.0	208.4	208.7	209.1	209.4	209.6	209.6	209.6
122.5°	224.5	224.2	223.9	223.6	223.9	224.2	224.5	224.7	224.9	225.0	225.1
125°	247.3	247.2	247.1	247.0	247.1	247.2	247.3	247.4	247.5	247.7	247.9
127.5°	270.0	269.8	269.7	269.5	269.7	269.8	270.0	270.2	270.4	270.4	270.5
130°	285.0	284.8	284.6	284.5	284.6	284.8	285.0	285.2	285.3	285.4	285.5
132.5°	299.3	299.0	298.8	298.5	298.8	299.0	299.3	299.5	299.6	299.7	299.8
135°	321.4	321.1	320.7	320.4	320.7	321.1	321.4	321.8	321.9	321.9	321.9
137.5°	343.1	342.7	342.2	341.7	342.2	342.7	343.1	343.5	343.7	343.5	343.5
140°	356.8	356.4	355.9	355.5	355.9	356.4	356.8	357.2	357.4	357.2	357.1
142.5°	369.9	369.5	369.0	368.6	369.0	369.5	369.9	370.3	370.5	370.4	370.3
145°	389.1	388.8	388.6	388.3	388.6	388.8	389.1	389.3	389.4	389.4	389.4
147.5°	406.8	406.2	405.6	405.1	405.6	406.2	406.8	407.4	407.6	407.4	407.2
150°	418.1	417.9	417.8	417.6	417.8	417.9	418.1	418.3	418.4	418.4	418.4
152.5°	428.8	428.5	428.2	427.8	428.2	428.5	428.8	429.1	429.1	429.0	428.8
155°	443.8	443.4	443.0	442.6	443.0	443.4	443.8	444.3	444.3	443.9	443.6
157.5°	456.5	455.9	455.4	454.8	455.4	455.9	456.5	457.1	457.2	456.8	456.5
160°	464.5	464.1	463.6	463.2	463.6	464.1	464.5	464.9	465.0	464.7	464.3
162.5°	471.9	471.4	470.9	470.4	470.9	471.4	471.9	472.4	472.4	472.0	471.7
165°	481.6	481.0	480.5	480.0	480.5	481.0	481.6	482.1	482.2	481.8	481.5
167.5°	489.2	488.7	488.2	487.7	488.2	488.7	489.2	489.8	489.8	489.3	488.8
170°	493.5	492.9	492.3	491.7	492.3	492.9	493.5	494.1	494.2	493.6	493.1
172.5°	496.7	496.2	495.7	495.2	495.7	496.2	496.7	497.3	497.3	496.8	496.3
175°	500.2	499.6	498.9	498.3	498.9	499.6	500.2	500.8	500.8	500.3	499.7
177.5°	501.7	501.2	500.7	500.2	500.7	501.2	501.7	502.1	502.2	501.8	501.4
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1007.2	1011.5	1016.8	1020.8	1027.9	1031.1	1035.1	1038.3	1044.0	1049.4	1055.8
5°	939.4	946.9	957.2	968.4	981.4	990.3	1002.8	1010.4	1025.6	1039.5	1052.8
7.5°	877.8	887.1	901.6	916.0	933.0	948.3	964.0	981.4	1000.7	1023.6	1042.6
10°	835.6	848.1	863.8	881.7	902.2	920.1	941.1	959.8	983.6	1010.4	1035.4
12.5°	801.9	812.7	830.2	847.3	869.3	891.1	912.8	937.7	965.4	995.1	1026.5
15°	755.5	764.5	778.8	802.5	824.8	846.4	879.0	902.2	937.1	970.2	1008.1
17.5°	715.9	727.0	739.1	759.4	782.6	809.4	838.5	867.7	901.3	943.2	986.1
20°	691.6	700.6	714.5	730.0	754.7	781.5	809.3	838.7	879.9	923.3	969.2
22.5°	665.1	674.9	690.4	707.6	728.2	754.0	784.5	816.9	859.8	902.5	952.4
25°	634.0	640.7	655.0	670.2	690.8	712.6	744.4	780.2	822.6	871.3	922.3
27.5°	604.5	610.4	623.5	636.7	655.3	681.3	709.7	745.8	785.8	835.3	891.7
30°	583.4	589.7	601.3	615.6	633.5	656.3	685.4	719.4	762.2	810.5	869.6
32.5°	565.2	570.8	579.5	593.8	611.3	633.4	660.3	695.0	738.0	787.0	844.9
35°	536.9	543.2	549.9	561.1	576.3	597.7	627.2	659.9	701.0	748.4	801.6
37.5°	508.9	515.7	521.7	531.7	545.5	564.5	590.0	624.0	661.2	706.8	757.9
40°	491.4	496.7	501.6	512.4	526.2	544.1	567.8	598.2	637.6	680.0	722.5
42.5°	473.8	478.8	483.0	492.3	505.1	522.3	544.9	574.5	611.1	650.7	688.1
45°	446.2	449.4	454.3	462.3	472.6	488.2	510.1	536.5	567.3	604.9	633.1
47.5°	416.3	421.2	425.2	432.3	440.7	456.1	477.1	499.6	527.5	555.4	575.3
50°	393.4	398.4	404.2	410.9	418.9	433.3	452.5	475.3	498.9	520.4	537.4
52.5°	372.0	376.5	382.7	389.1	398.9	411.0	427.4	447.7	471.1	486.5	500.6
55°	340.3	342.4	349.7	355.9	365.2	374.2	390.7	408.6	422.9	434.5	446.2
57.5°	307.8	310.8	315.0	320.6	329.8	340.4	352.0	367.7	376.2	382.2	391.2
60°	287.1	287.9	290.6	297.3	304.4	313.8	327.3	338.5	344.7	349.7	357.2
62.5°	264.2	264.3	268.8	273.7	279.1	289.2	300.1	309.1	314.3	316.7	324.0
65°	232.0	231.2	233.8	237.8	244.1	250.8	260.2	268.3	267.8	270.4	274.9
67.5°	199.2	198.3	198.3	202.2	207.2	213.3	219.7	224.4	224.5	228.0	230.2
70°	177.0	174.4	176.2	179.3	181.5	186.4	193.6	195.4	195.8	197.6	199.8
72.5°	154.1	153.3	154.7	156.0	157.6	161.4	167.5	168.6	168.7	169.7	173.4
75°	122.5	121.6	120.7	122.1	123.8	126.5	128.7	130.5	130.1	130.5	133.2
77.5°	91.9	89.3	88.9	89.6	90.1	91.6	93.9	93.8	94.3	94.2	97.2
80°	72.8	69.3	68.9	68.9	69.3	70.2	71.1	72.0	70.6	72.0	72.8
82.5°	53.6	51.4	51.3	51.0	51.1	51.2	51.7	52.3	52.0	52.7	53.2
85°	29.5	28.6	27.3	28.2	27.7	26.3	27.3	25.9	25.5	25.9	26.3
87.5°	11.4	11.6	10.8	10.7	10.2	10.4	9.6	9.0	8.6	8.8	9.7
90°	6.7	6.3	5.6	5.0	4.4	3.8	3.2	2.5	1.8	1.1	0.4
92.5°	15.6	15.0	14.2	13.5	12.7	12.0	11.4	10.9	10.4	9.9	9.5
95°	30.7	30.0	29.2	28.3	27.5	26.6	26.1	25.9	25.7	25.6	25.4
97.5°	48.4	47.9	46.7	45.5	44.3	43.0	42.4	42.4	42.3	42.2	42.1
100°	60.5	59.7	58.5	57.4	56.3	55.2	54.7	54.7	54.7	54.7	54.7
102.5°	73.0	72.2	71.6	71.0	70.5	69.9	69.5	69.1	68.8	68.4	68.0
105°	93.8	93.2	92.7	92.2	91.7	91.2	90.7	90.2	89.8	89.4	88.9
107.5°	116.1	115.8	115.5	115.0	114.6	114.3	113.8	113.4	113.0	112.5	112.1
110°	131.4	131.1	130.9	130.6	130.4	130.1	129.8	129.3	128.9	128.5	128.0



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	146.9	146.7	146.4	146.1	145.8	145.4	145.2	144.9	144.6	144.5	144.2
115°	170.5	170.6	170.4	170.2	170.0	169.9	169.6	169.3	168.9	168.5	168.2
117.5°	193.7	193.6	193.5	193.3	193.2	193.0	192.9	192.7	192.5	192.3	192.3
120°	209.6	209.6	209.5	209.4	209.3	209.2	209.0	208.5	208.1	207.7	207.2
122.5°	225.1	225.2	225.0	224.7	224.5	224.3	224.0	223.9	223.8	223.6	223.4
125°	248.1	248.2	248.1	248.1	248.0	247.9	247.5	247.0	246.5	246.0	245.5
127.5°	270.6	270.7	270.5	270.4	270.4	270.3	270.1	269.8	269.5	269.1	268.9
130°	285.6	285.7	285.5	285.3	285.2	285.0	284.6	284.2	283.8	283.4	282.9
132.5°	299.9	300.0	300.1	300.1	300.1	300.1	299.8	299.1	298.4	297.6	297.0
135°	321.9	321.9	321.8	321.8	321.7	321.6	321.3	320.8	320.3	319.8	319.2
137.5°	343.4	343.3	343.0	342.9	342.7	342.5	342.2	341.6	341.1	340.6	340.1
140°	356.9	356.7	356.5	356.2	355.9	355.7	355.2	354.8	354.4	354.0	353.5
142.5°	370.2	370.1	369.8	369.5	369.1	368.8	368.4	368.1	367.7	367.3	367.0
145°	389.4	389.4	389.2	388.9	388.7	388.4	388.1	387.8	387.4	387.1	386.8
147.5°	407.0	406.8	406.6	406.4	406.1	406.0	405.8	405.5	405.4	405.2	405.0
150°	418.4	418.4	418.0	417.7	417.3	417.0	416.8	416.9	417.0	417.1	417.2
152.5°	428.5	428.3	428.2	428.1	427.9	427.7	427.7	427.5	427.4	427.3	427.1
155°	443.2	442.9	442.8	442.7	442.6	442.6	442.6	442.6	442.6	442.6	442.6
157.5°	456.2	455.8	455.7	455.6	455.6	455.5	455.5	455.7	455.9	456.1	456.2
160°	464.0	463.6	463.5	463.4	463.3	463.2	463.3	463.6	463.8	464.2	464.4
162.5°	471.2	470.8	470.8	470.7	470.7	470.7	470.8	471.0	471.2	471.4	471.6
165°	481.1	480.8	480.7	480.6	480.5	480.4	480.4	480.6	480.8	481.0	481.1
167.5°	488.3	487.8	487.8	487.8	487.8	487.8	487.9	488.3	488.6	489.0	489.3
170°	492.6	492.1	492.1	492.1	492.1	492.1	492.2	492.6	492.9	493.3	493.6
172.5°	495.8	495.2	495.2	495.2	495.2	495.2	495.4	495.8	496.1	496.5	496.8
175°	499.2	498.7	498.7	498.7	498.7	498.7	498.9	499.2	499.6	499.9	500.3
177.5°	500.9	500.5	500.6	500.7	500.8	500.8	500.9	501.3	501.5	501.8	502.0
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1059.0	1064.0	1067.3	1073.3	1078.3	1081.2	1083.7	1085.9	1088.4	1090.5	1096.6
5°	1065.8	1077.5	1087.3	1102.5	1116.4	1127.0	1138.7	1149.0	1157.5	1169.6	1179.0
7.5°	1062.9	1083.6	1105.2	1128.7	1152.7	1175.1	1195.7	1214.9	1232.3	1253.4	1272.0
10°	1060.1	1088.2	1115.9	1147.6	1180.3	1208.0	1233.9	1260.3	1279.5	1306.4	1329.1
12.5°	1057.9	1091.1	1124.5	1162.7	1198.5	1237.7	1272.2	1291.4	1320.7	1342.1	1369.2
15°	1048.9	1092.7	1138.7	1181.6	1232.6	1268.8	1299.2	1336.8	1364.0	1391.3	1420.8
17.5°	1032.7	1082.3	1133.8	1190.1	1239.0	1277.8	1317.0	1353.2	1385.8	1422.4	1459.1
20°	1025.2	1074.8	1133.8	1191.5	1239.3	1280.0	1320.3	1360.0	1395.8	1442.7	1485.2
22.5°	1009.4	1069.4	1123.8	1180.0	1229.2	1273.6	1319.1	1364.3	1411.9	1464.9	1518.1
25°	981.4	1042.2	1099.8	1155.3	1204.9	1260.3	1309.1	1369.4	1430.2	1500.4	1566.6
27.5°	952.2	1010.4	1063.2	1116.8	1174.7	1237.4	1300.6	1369.2	1448.7	1537.3	1630.6
30°	928.6	983.6	1035.0	1089.9	1150.3	1221.0	1290.3	1371.7	1463.7	1563.4	1674.3
32.5°	901.0	951.7	1001.7	1060.0	1125.7	1200.2	1281.0	1370.2	1480.9	1594.2	1708.3
35°	853.9	896.4	947.8	1010.0	1084.2	1169.6	1263.0	1368.5	1495.5	1625.6	1721.7
37.5°	798.1	837.6	891.7	959.8	1037.7	1129.3	1240.2	1365.4	1500.2	1604.0	1635.0
40°	760.5	797.1	853.5	924.1	1003.7	1100.7	1222.3	1354.6	1485.2	1551.3	1525.9
42.5°	720.4	758.9	813.7	883.7	969.4	1075.0	1199.8	1332.1	1441.6	1466.6	1378.5
45°	657.2	697.0	751.1	821.7	913.9	1028.3	1158.4	1278.7	1341.7	1296.5	1160.2
47.5°	598.5	635.8	685.9	758.8	853.9	972.2	1097.5	1193.4	1198.4	1090.7	945.0
50°	558.4	592.8	643.3	716.2	810.5	930.4	1043.4	1119.0	1085.0	963.0	823.0
52.5°	519.1	552.8	602.6	674.8	768.0	877.8	983.0	1036.0	972.1	846.8	727.2
55°	462.3	491.8	540.5	607.1	695.7	797.6	887.0	905.3	822.2	698.8	601.8
57.5°	406.8	434.4	478.7	540.1	621.0	711.3	781.2	777.3	689.4	583.5	506.5
60°	369.3	396.1	435.5	495.3	569.1	647.0	706.8	692.5	605.4	514.1	449.4
62.5°	335.7	359.6	396.8	449.2	516.5	588.7	637.8	616.7	531.3	451.5	400.3
65°	286.1	306.3	338.0	382.7	438.6	498.1	536.1	508.8	435.9	373.8	332.6
67.5°	238.8	254.9	281.5	317.3	364.9	412.7	435.8	408.4	350.1	304.7	274.2
70°	208.8	223.1	243.7	275.4	317.0	357.2	374.6	350.1	300.0	261.1	239.2
72.5°	178.7	190.5	208.6	237.1	270.4	305.4	320.6	297.1	256.0	223.2	202.7
75°	138.2	146.2	158.7	178.4	204.7	232.5	241.0	220.4	194.1	169.4	156.0
77.5°	98.9	105.7	115.2	127.6	146.3	163.9	171.3	159.5	139.1	123.5	112.4
80°	76.0	79.6	87.6	97.9	112.7	123.8	128.7	121.1	106.9	95.2	86.7
82.5°	54.2	57.8	62.6	71.1	80.5	88.1	93.3	88.3	77.9	68.8	63.8
85°	26.3	28.6	31.3	34.9	42.0	46.5	46.1	42.9	38.9	35.3	32.6
87.5°	9.6	10.0	11.2	13.2	14.4	15.9	16.7	16.2	14.8	13.9	12.8
90°	1.1	1.8	2.5	3.2	3.8	4.4	5.0	5.6	6.3	6.7	7.1
92.5°	9.9	10.4	10.9	11.4	12.0	12.7	13.5	14.2	15.0	15.6	16.1
95°	25.6	25.7	25.9	26.1	26.6	27.5	28.3	29.2	30.0	30.7	31.3
97.5°	42.2	42.3	42.4	42.4	43.0	44.3	45.5	46.7	47.9	48.4	49.0
100°	54.7	54.7	54.7	54.7	55.2	56.3	57.4	58.5	59.7	60.5	61.3
102.5°	68.4	68.8	69.1	69.5	69.9	70.5	71.0	71.6	72.2	73.0	73.9
105°	89.4	89.8	90.2	90.7	91.2	91.7	92.2	92.7	93.2	93.8	94.3
107.5°	112.5	113.0	113.4	113.8	114.3	114.6	115.0	115.5	115.8	116.1	116.3
110°	128.5	128.9	129.3	129.8	130.1	130.4	130.6	130.9	131.1	131.4	131.6



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.5	144.6	144.9	145.2	145.4	145.8	146.1	146.4	146.7	146.9	147.0
115°	168.5	168.9	169.3	169.6	169.9	170.0	170.2	170.4	170.6	170.5	170.4
117.5°	192.3	192.5	192.7	192.9	193.0	193.2	193.3	193.5	193.6	193.7	193.8
120°	207.7	208.1	208.5	209.0	209.2	209.3	209.4	209.5	209.6	209.6	209.6
122.5°	223.6	223.8	223.9	224.0	224.3	224.5	224.7	225.0	225.2	225.1	225.1
125°	246.0	246.5	247.0	247.5	247.9	248.0	248.1	248.1	248.2	248.1	247.9
127.5°	269.1	269.5	269.8	270.1	270.3	270.4	270.4	270.5	270.7	270.6	270.5
130°	283.4	283.8	284.2	284.6	285.0	285.2	285.3	285.5	285.7	285.6	285.5
132.5°	297.6	298.4	299.1	299.8	300.1	300.1	300.1	300.1	300.0	299.9	299.8
135°	319.8	320.3	320.8	321.3	321.6	321.7	321.8	321.8	321.9	321.9	321.9
137.5°	340.6	341.1	341.6	342.2	342.5	342.7	342.9	343.0	343.3	343.4	343.5
140°	354.0	354.4	354.8	355.2	355.7	355.9	356.2	356.5	356.7	356.9	357.1
142.5°	367.3	367.7	368.1	368.4	368.8	369.1	369.5	369.8	370.1	370.2	370.3
145°	387.1	387.4	387.8	388.1	388.4	388.7	388.9	389.2	389.4	389.4	389.4
147.5°	405.2	405.4	405.5	405.8	406.0	406.1	406.4	406.6	406.8	407.0	407.2
150°	417.1	417.0	416.9	416.8	417.0	417.3	417.7	418.0	418.4	418.4	418.4
152.5°	427.3	427.4	427.5	427.7	427.7	427.9	428.1	428.2	428.3	428.5	428.8
155°	442.6	442.6	442.6	442.6	442.6	442.6	442.7	442.8	442.9	443.2	443.6
157.5°	456.1	455.9	455.7	455.5	455.5	455.6	455.6	455.7	455.8	456.2	456.5
160°	464.2	463.8	463.6	463.3	463.2	463.3	463.4	463.5	463.6	464.0	464.3
162.5°	471.4	471.2	471.0	470.8	470.7	470.7	470.7	470.8	470.8	471.2	471.7
165°	481.0	480.8	480.6	480.4	480.4	480.5	480.6	480.7	480.8	481.1	481.5
167.5°	489.0	488.6	488.3	487.9	487.8	487.8	487.8	487.8	487.8	488.3	488.8
170°	493.3	492.9	492.6	492.2	492.1	492.1	492.1	492.1	492.1	492.6	493.1
172.5°	496.5	496.1	495.8	495.4	495.2	495.2	495.2	495.2	495.2	495.8	496.3
175°	499.9	499.6	499.2	498.9	498.7	498.7	498.7	498.7	498.7	499.2	499.7
177.5°	501.8	501.5	501.3	500.9	500.8	500.8	500.7	500.6	500.5	500.9	501.4
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1101.6	1104.5	1110.5	1108.4	1111.3	1112.7	1114.1
5°	1190.6	1204.9	1211.2	1210.2	1219.6	1217.4	1215.1
7.5°	1291.1	1306.1	1314.5	1325.0	1331.0	1331.5	1336.8
10°	1348.0	1367.6	1375.7	1386.8	1394.0	1398.0	1397.6
12.5°	1391.5	1407.0	1425.0	1430.5	1440.1	1445.2	1443.4
15°	1444.1	1468.7	1487.5	1496.8	1508.9	1512.4	1517.4
17.5°	1490.9	1523.9	1545.8	1574.9	1586.0	1592.7	1588.7
20°	1526.3	1569.7	1591.6	1626.5	1645.7	1656.0	1652.4
22.5°	1568.1	1615.1	1655.6	1685.8	1715.1	1729.0	1731.8
25°	1639.9	1704.3	1763.8	1803.5	1839.7	1848.2	1867.0
27.5°	1720.0	1796.0	1859.5	1901.3	1926.6	1936.0	1941.9
30°	1770.5	1846.0	1893.9	1920.6	1928.7	1927.8	1926.9
32.5°	1795.1	1842.5	1851.6	1844.1	1825.7	1810.2	1793.9
35°	1760.1	1724.8	1672.1	1604.1	1554.0	1503.6	1498.6
37.5°	1583.0	1470.1	1382.2	1284.2	1227.6	1192.7	1168.5
40°	1416.3	1288.1	1181.6	1098.9	1041.2	1018.5	996.1
42.5°	1235.4	1112.8	1018.6	949.4	906.0	880.7	863.1
45°	1003.7	895.5	821.7	771.6	737.3	717.6	706.4
47.5°	822.4	742.4	679.8	643.6	619.8	604.5	604.6
50°	725.1	648.7	607.1	578.5	557.9	545.9	548.1
52.5°	638.9	581.9	546.3	522.4	507.1	499.7	499.5
55°	534.3	493.1	469.8	452.5	442.1	433.7	435.5
57.5°	457.0	422.3	406.7	392.3	385.1	381.7	376.8
60°	409.1	382.3	368.9	357.2	350.1	347.4	342.4
62.5°	366.5	345.4	332.3	322.9	316.4	315.6	311.7
65°	308.1	292.0	280.3	275.9	269.1	267.3	267.3
67.5°	253.9	242.4	233.4	229.3	226.3	226.8	224.6
70°	220.0	210.6	204.7	200.3	198.0	198.5	196.7
72.5°	192.4	181.9	176.8	174.2	171.3	172.4	171.7
75°	145.8	140.3	137.7	135.0	133.2	132.3	131.5
77.5°	107.0	102.3	100.2	98.8	99.0	96.9	98.5
80°	82.7	78.7	77.3	75.1	74.6	74.6	74.2
82.5°	60.5	58.3	57.3	55.4	54.7	55.4	54.2
85°	31.3	29.5	29.1	29.1	28.2	27.3	29.5
87.5°	12.9	11.6	11.7	11.4	11.5	11.1	10.4
90°	7.6	8.0	8.4	8.6	8.9	9.1	9.4
92.5°	16.7	17.3	17.7	17.8	18.0	18.3	18.4
95°	31.9	32.5	32.9	33.1	33.2	33.4	33.6
97.5°	49.6	50.1	50.5	50.5	50.7	50.8	50.9
100°	62.1	62.9	63.3	63.5	63.6	63.8	64.0
102.5°	74.7	75.6	76.1	76.4	76.6	76.9	77.1
105°	94.8	95.3	95.7	96.0	96.3	96.5	96.8
107.5°	116.6	116.8	117.0	117.0	116.9	116.9	116.9
110°	131.9	132.2	132.2	132.2	132.1	132.0	131.9



TEST NUMBER: P333401-935

CATALOG NUMBER: S125DIW-S850D470U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	147.1	147.2	147.2	147.1	146.9	146.7	146.5
115°	170.3	170.2	170.1	170.0	170.0	169.9	169.8
117.5°	193.8	193.9	193.8	193.5	193.1	192.7	192.3
120°	209.6	209.6	209.4	209.1	208.7	208.4	208.0
122.5°	225.0	224.9	224.7	224.5	224.2	223.9	223.6
125°	247.7	247.5	247.4	247.3	247.2	247.1	247.0
127.5°	270.4	270.4	270.2	270.0	269.8	269.7	269.5
130°	285.4	285.3	285.2	285.0	284.8	284.6	284.5
132.5°	299.7	299.6	299.5	299.3	299.0	298.8	298.5
135°	321.9	321.9	321.8	321.4	321.1	320.7	320.4
137.5°	343.5	343.7	343.5	343.1	342.7	342.2	341.7
140°	357.2	357.4	357.2	356.8	356.4	355.9	355.5
142.5°	370.4	370.5	370.3	369.9	369.5	369.0	368.6
145°	389.4	389.4	389.3	389.1	388.8	388.6	388.3
147.5°	407.4	407.6	407.4	406.8	406.2	405.6	405.1
150°	418.4	418.4	418.3	418.1	417.9	417.8	417.6
152.5°	429.0	429.1	429.1	428.8	428.5	428.2	427.8
155°	443.9	444.3	444.3	443.8	443.4	443.0	442.6
157.5°	456.8	457.2	457.1	456.5	455.9	455.4	454.8
160°	464.7	465.0	464.9	464.5	464.1	463.6	463.2
162.5°	472.0	472.4	472.4	471.9	471.4	470.9	470.4
165°	481.8	482.2	482.1	481.6	481.0	480.5	480.0
167.5°	489.3	489.8	489.8	489.2	488.7	488.2	487.7
170°	493.6	494.2	494.1	493.5	492.9	492.3	491.7
172.5°	496.8	497.3	497.3	496.7	496.2	495.7	495.2
175°	500.3	500.8	500.8	500.2	499.6	498.9	498.3
177.5°	501.8	502.2	502.1	501.7	501.2	500.7	500.2
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4

(END OF REPORT)