

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333729-935

Luminaire Tested: **S125RDIW-S1270D1050U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333729-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7366.6 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	57	55	54	49
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	40	37	35	31
5	71	59	51	45	66	55	48	43	49	43	39	42	38	35	37	33	30	27
6	65	53	45	39	61	50	43	38	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	25	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10559	10559	10559	10559
5°	12149	10573	9337	10573
10°	13935	10519	8239	10519
15°	15051	10411	7324	10411
20°	16597	10287	6763	10287
25°	19207	10120	6274	10120
30°	20901	9945	5956	9945
35°	17631	9742	5662	9742
40°	12312	9377	5409	9377
45°	9134	8882	5161	8882
50°	7283	8368	4950	8368
55°	6182	7731	4761	7731
60°	5341	7161	4456	7161
65°	4759	6544	3836	6544
70°	4181	5995	3497	5995
75°	3618	5190	3284	5190
80°	2745	4366	2745	4366
85°	2290	3431	2586	3431



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	2.1
10°-20°	459.5	6.2
20°-30°	728.5	9.9
30°-40°	878.5	11.9
40°-50°	784.5	10.6
50°-60°	601.6	8.2
60°-70°	391.0	5.3
70°-80°	190.1	2.6
80°-90°	47.8	0.6
90°-100°	75.1	1.0
100°-110°	221.7	3.0
110°-120°	375.6	5.1
120°-130°	494.3	6.7
130°-140°	553.8	7.5
140°-150°	542.8	7.4
150°-160°	455.9	6.2
160°-170°	303.0	4.1
170°-180°	106.1	1.4
0°-30°	1344.7	18.3
0°-40°	2223.3	30.2
0°-60°	3609.4	49.0
0°-90°	4238.3	57.5
90°-120°	672.4	9.1
90°-150°	2263.2	30.7
90°-180°	3128.0	42.5
0°-180°	7366.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1635	1635	1635	1635	1635	
5°	1874	1631	1440	1631	1874	187
15°	2251	1557	1095	1557	2251	645
25°	2695	1420	880	1420	2695	1238
35°	2236	1236	718	1236	2236	1351
45°	1000	972	565	972	1000	798
55°	549	687	423	687	549	498
65°	311	428	251	428	311	310
75°	145	208	132	208	145	154
85°	31	46	35	46	31	36
90°	21	1	21	1	21	14
95°	75	57	75	57	75	76
105°	216	199	216	199	216	229
115°	380	376	380	376	380	375
125°	552	549	552	549	552	493
135°	716	714	716	714	716	553
145°	868	864	868	864	868	542
155°	989	989	989	989	989	455
165°	1073	1076	1073	1076	1073	302
175°	1114	1118	1114	1118	1114	106
180°	1121	1121	1121	1121	1121	



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1719.8	1718.7	1720.9	1714.9	1715.5	1706.3	1706.3	1699.4	1690.2	1683.3	1680.1
5°	1873.9	1875.3	1872.5	1862.4	1855.8	1845.7	1834.3	1814.1	1797.3	1781.2	1768.5
7.5°	2032.6	2033.5	2024.6	2021.5	2004.6	1992.3	1966.9	1939.5	1915.2	1884.4	1860.7
10°	2124.9	2124.3	2114.8	2107.5	2092.7	2073.9	2049.1	2016.8	1986.7	1953.1	1920.9
12.5°	2178.6	2176.9	2173.9	2164.9	2151.2	2134.6	2113.5	2081.8	2044.6	2007.9	1970.2
15°	2251.1	2246.3	2237.7	2226.2	2206.7	2187.3	2163.8	2135.6	2100.1	2058.5	2023.5
17.5°	2340.7	2340.9	2327.5	2311.6	2285.2	2250.8	2214.6	2169.0	2120.7	2074.9	2037.8
20°	2414.8	2412.8	2399.4	2368.5	2338.3	2295.3	2253.8	2198.0	2139.0	2079.2	2032.9
22.5°	2521.2	2515.9	2502.0	2461.4	2414.6	2359.2	2295.6	2227.6	2156.2	2088.4	2027.6
25°	2695.4	2691.3	2663.8	2616.8	2551.1	2465.8	2382.6	2289.3	2186.7	2097.4	2023.5
27.5°	2814.6	2810.1	2789.7	2750.7	2690.0	2600.3	2487.7	2363.0	2234.8	2112.0	2005.5
30°	2802.7	2812.8	2810.1	2792.1	2746.4	2665.8	2561.8	2421.6	2269.2	2124.9	1998.0
32.5°	2634.1	2643.2	2666.8	2702.3	2705.0	2672.8	2595.1	2465.6	2307.8	2143.7	1992.1
35°	2236.3	2248.4	2294.0	2365.9	2459.8	2538.3	2554.4	2484.7	2343.0	2166.5	1983.3
37.5°	1719.2	1785.3	1823.7	1899.3	2041.3	2185.7	2324.6	2375.8	2315.5	2157.1	1968.9
40°	1460.4	1476.5	1545.0	1630.2	1749.7	1900.1	2098.1	2241.0	2245.7	2135.6	1946.4
42.5°	1250.0	1270.4	1317.3	1385.4	1487.7	1638.1	1842.5	2031.1	2118.5	2076.6	1916.8
45°	1000.1	1015.5	1049.7	1102.1	1180.6	1304.8	1480.6	1698.7	1871.9	1939.7	1837.6
47.5°	821.5	829.8	859.6	899.5	957.6	1048.1	1184.2	1373.6	1581.2	1726.9	1712.5
50°	724.9	734.3	757.1	787.3	836.3	912.7	1021.5	1179.2	1393.4	1571.2	1606.8
52.5°	649.7	657.5	671.7	700.3	740.7	799.5	887.3	1029.9	1222.6	1411.7	1494.0
55°	549.0	554.4	565.8	581.9	614.2	656.4	732.2	830.9	986.6	1177.2	1298.0
57.5°	466.1	468.7	476.0	490.9	513.2	544.1	598.8	682.4	794.1	965.8	1099.1
60°	413.5	416.1	425.5	435.6	453.1	481.2	524.2	582.6	689.9	831.6	966.5
62.5°	371.5	373.2	377.2	387.3	402.6	424.3	458.1	505.8	591.2	715.6	843.0
65°	311.4	312.1	313.4	321.5	330.9	347.0	369.1	402.7	467.1	561.1	673.8
67.5°	253.7	254.6	259.3	262.2	272.0	280.4	293.4	319.1	364.5	427.8	515.5
70°	221.4	220.8	225.5	228.9	232.2	242.3	251.0	271.8	300.0	348.4	421.5
72.5°	191.4	189.7	191.7	192.9	197.3	204.1	212.9	225.7	247.4	280.7	336.7
75°	145.0	145.7	145.7	147.0	150.3	153.0	155.7	162.4	174.5	196.7	226.9
77.5°	101.8	100.7	103.5	103.9	105.9	108.8	111.2	113.8	118.8	127.9	143.5
80°	73.8	73.8	74.5	76.5	75.9	77.1	80.5	83.3	89.3	94.6	100.0
82.5°	56.7	56.1	56.7	57.2	57.1	58.4	59.6	60.1	62.4	65.1	68.9
85°	30.9	30.9	31.5	31.5	32.2	32.2	32.9	32.9	32.9	33.6	34.3
87.5°	16.0	15.3	14.7	14.6	15.0	15.9	15.2	14.5	14.3	14.0	14.3
90°	20.9	20.3	19.8	19.2	18.6	17.8	16.9	15.9	14.9	13.9	12.6
92.5°	41.2	40.7	40.3	39.9	39.4	38.7	37.4	36.1	34.8	33.5	31.9
95°	75.0	74.6	74.2	73.9	73.4	72.6	71.2	69.9	68.5	67.2	65.3
97.5°	113.7	113.6	113.3	113.0	112.8	112.1	110.8	109.5	108.2	106.9	104.3
100°	143.1	142.7	142.3	141.9	141.5	140.4	138.7	137.0	135.3	133.5	131.0
102.5°	172.4	171.9	171.3	170.7	170.2	169.0	167.1	165.2	163.3	161.4	160.1
105°	216.4	215.8	215.2	214.6	214.0	213.2	212.0	210.9	209.7	208.5	207.3
107.5°	261.4	261.4	261.5	261.5	261.6	261.2	260.7	260.1	259.5	258.9	258.0
110°	294.9	295.1	295.2	295.5	295.7	295.5	294.9	294.3	293.7	293.2	292.6



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.7	328.0	328.4	328.7	329.1	329.1	328.8	328.6	328.3	328.0	327.3
115°	379.5	379.7	379.9	380.0	380.3	380.5	380.6	380.8	381.1	381.3	380.8
117.5°	430.1	430.8	431.6	432.4	433.2	433.5	433.3	433.2	433.1	432.9	432.6
120°	465.0	465.8	466.6	467.4	468.1	468.5	468.5	468.5	468.5	468.5	468.3
122.5°	499.9	500.5	501.1	501.8	502.4	502.7	502.9	503.1	503.3	503.4	502.9
125°	552.2	552.4	552.6	552.8	553.0	553.3	553.7	554.1	554.5	554.8	554.7
127.5°	602.5	602.9	603.3	603.6	604.1	604.3	604.5	604.7	604.9	605.1	604.9
130°	636.0	636.4	636.8	637.1	637.6	637.8	638.0	638.3	638.4	638.6	638.3
132.5°	667.4	668.0	668.5	669.0	669.6	669.9	670.1	670.3	670.5	670.7	670.8
135°	716.3	717.0	717.8	718.6	719.4	719.7	719.7	719.7	719.7	719.7	719.5
137.5°	764.1	765.0	766.0	767.0	767.9	768.3	768.1	767.8	767.6	767.4	767.0
140°	794.8	795.7	796.7	797.7	798.7	798.9	798.6	798.1	797.8	797.4	796.8
142.5°	824.1	825.1	826.0	827.0	827.9	828.4	828.1	827.9	827.6	827.4	826.6
145°	868.1	868.7	869.2	869.8	870.4	870.6	870.6	870.6	870.6	870.6	870.1
147.5°	905.6	906.9	908.2	909.6	910.9	911.3	910.8	910.3	909.9	909.4	909.0
150°	933.5	933.8	934.3	934.6	935.0	935.2	935.2	935.2	935.2	935.2	934.4
152.5°	956.5	957.2	957.9	958.6	959.3	959.4	959.0	958.5	958.0	957.6	957.3
155°	989.3	990.3	991.3	992.2	993.2	993.3	992.6	991.8	991.0	990.2	990.0
157.5°	1016.8	1018.0	1019.3	1020.5	1021.8	1022.1	1021.3	1020.5	1019.8	1019.0	1018.8
160°	1035.5	1036.6	1037.5	1038.5	1039.4	1039.6	1038.8	1038.0	1037.2	1036.5	1036.2
162.5°	1051.6	1052.7	1053.9	1055.0	1056.1	1056.2	1055.2	1054.4	1053.4	1052.5	1052.5
165°	1073.1	1074.3	1075.4	1076.6	1077.7	1077.9	1077.1	1076.3	1075.6	1074.8	1074.6
167.5°	1090.2	1091.4	1092.6	1093.8	1095.0	1095.0	1093.8	1092.7	1091.5	1090.4	1090.4
170°	1099.2	1100.6	1102.0	1103.3	1104.7	1104.7	1103.6	1102.4	1101.3	1100.1	1100.1
172.5°	1106.9	1108.1	1109.3	1110.5	1111.7	1111.7	1110.6	1109.4	1108.3	1107.1	1107.1
175°	1114.0	1115.4	1116.8	1118.2	1119.5	1119.6	1118.4	1117.2	1116.1	1114.9	1114.9
177.5°	1118.3	1119.4	1120.4	1121.5	1122.6	1122.7	1121.8	1120.8	1119.9	1119.0	1119.1
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1680.1	1676.3	1669.3	1662.8	1654.8	1647.9	1643.0	1637.1	1629.6	1620.5	1612.9
5°	1754.4	1739.7	1720.2	1703.4	1682.0	1665.2	1647.7	1630.9	1614.1	1592.7	1573.9
7.5°	1836.9	1806.4	1776.7	1739.4	1705.6	1675.3	1646.3	1617.0	1588.2	1557.7	1528.4
10°	1887.3	1850.4	1809.5	1762.5	1719.5	1678.6	1641.0	1604.0	1565.1	1530.9	1494.0
12.5°	1934.6	1886.9	1840.0	1780.7	1729.1	1679.1	1631.3	1585.3	1543.7	1499.3	1459.7
15°	1977.2	1930.3	1877.9	1805.4	1733.6	1673.2	1616.8	1557.1	1505.4	1455.8	1411.4
17.5°	1993.7	1944.5	1883.7	1814.0	1735.5	1659.5	1586.9	1521.4	1460.6	1402.7	1352.9
20°	1987.3	1939.7	1877.2	1810.8	1726.9	1647.7	1569.2	1496.7	1428.9	1367.8	1314.8
22.5°	1971.8	1922.4	1862.2	1792.0	1712.4	1628.4	1544.5	1467.1	1396.1	1332.9	1275.1
25°	1948.4	1881.3	1819.6	1751.0	1675.2	1592.0	1505.4	1420.1	1344.4	1279.9	1216.9
27.5°	1924.1	1840.3	1761.8	1693.8	1613.6	1539.4	1455.9	1368.5	1288.7	1223.1	1158.4
30°	1902.0	1808.1	1721.5	1644.3	1568.5	1498.1	1418.8	1333.6	1251.7	1184.0	1118.2
32.5°	1874.7	1774.8	1679.6	1590.6	1517.5	1447.6	1375.9	1294.4	1214.7	1144.7	1077.9
35°	1840.3	1712.8	1609.5	1514.8	1433.6	1365.8	1301.4	1235.6	1155.7	1083.2	1018.1
37.5°	1795.2	1650.5	1530.9	1427.8	1342.2	1274.1	1223.2	1163.1	1090.2	1020.8	960.4
40°	1767.8	1605.4	1474.5	1372.5	1282.5	1210.7	1163.1	1112.2	1045.7	980.6	920.2
42.5°	1731.3	1564.1	1417.6	1311.3	1220.8	1151.7	1103.5	1058.9	1003.2	941.9	877.2
45°	1659.7	1483.9	1330.2	1216.2	1124.9	1057.0	1012.1	972.5	930.2	873.8	817.4
47.5°	1566.6	1400.3	1239.5	1114.9	1025.5	962.6	918.9	887.7	857.5	809.5	754.8
50°	1492.0	1331.6	1174.5	1053.7	958.4	898.7	857.7	832.9	805.4	761.7	716.1
52.5°	1403.9	1260.7	1106.9	983.3	893.5	837.5	798.1	773.4	750.6	715.1	671.6
55°	1265.2	1139.6	998.7	886.6	804.1	747.7	710.1	686.6	673.2	643.0	608.7
57.5°	1105.0	1015.0	890.8	782.7	709.7	654.0	626.5	606.5	591.3	570.0	545.8
60°	993.3	930.2	818.8	716.1	649.0	596.0	571.2	554.4	540.3	522.2	503.3
62.5°	880.0	834.1	737.2	649.0	587.3	542.9	519.6	504.5	488.2	476.0	457.7
65°	728.2	687.3	620.2	551.0	494.0	458.4	441.6	428.2	418.1	404.7	391.9
67.5°	566.5	549.8	503.5	455.8	414.9	383.2	368.8	359.4	347.2	339.2	330.5
70°	467.1	459.1	426.2	394.7	356.4	334.9	321.5	317.5	302.7	294.6	288.6
72.5°	379.1	375.3	356.4	334.5	307.5	288.7	276.4	271.8	262.4	256.0	252.1
75°	259.8	261.1	257.7	243.7	233.6	221.4	210.8	208.0	201.4	196.0	192.6
77.5°	164.3	171.2	171.4	170.7	166.7	159.4	154.9	152.9	146.3	144.3	143.5
80°	112.8	120.1	126.8	126.1	124.8	122.9	119.5	117.4	114.1	112.1	110.7
82.5°	75.2	82.1	87.6	91.3	91.0	89.0	86.7	85.8	85.1	83.6	83.3
85°	35.6	36.9	38.9	43.7	47.0	47.6	47.0	46.3	44.3	44.9	45.6
87.5°	14.6	14.3	14.6	14.3	13.4	15.8	17.1	17.4	16.6	15.8	15.1
90°	11.3	9.9	8.5	7.1	5.5	4.0	2.4	0.9	2.4	4.0	5.5
92.5°	30.1	28.5	26.9	25.5	24.4	23.2	22.2	21.1	22.2	23.2	24.4
95°	63.3	61.4	59.4	58.3	57.9	57.5	57.1	56.7	57.1	57.5	57.9
97.5°	101.6	98.9	96.3	94.9	94.7	94.5	94.4	94.2	94.4	94.5	94.7
100°	128.5	125.9	123.4	122.2	122.2	122.2	122.2	122.2	122.2	122.2	122.2
102.5°	158.9	157.6	156.3	155.2	154.5	153.7	152.9	152.1	152.9	153.7	154.5
105°	206.2	205.0	203.9	202.8	201.8	200.9	199.8	198.9	199.8	200.9	201.8
107.5°	257.2	256.2	255.4	254.4	253.5	252.5	251.5	250.6	251.5	252.5	253.5
110°	292.0	291.4	290.8	290.1	289.0	288.1	287.1	286.1	287.1	288.1	289.0



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.6	325.8	325.1	324.4	324.0	323.5	323.0	322.4	323.0	323.5	324.0
115°	380.5	380.0	379.7	379.1	378.3	377.5	376.8	376.0	376.8	377.5	378.3
117.5°	432.2	431.9	431.5	431.2	430.8	430.4	430.1	429.7	430.1	430.4	430.8
120°	468.1	467.9	467.7	467.1	466.1	465.2	464.3	463.2	464.3	465.2	466.1
122.5°	502.4	501.9	501.4	500.9	500.6	500.2	499.9	499.6	499.9	500.2	500.6
125°	554.5	554.3	554.1	553.4	552.2	551.0	549.9	548.7	549.9	551.0	552.2
127.5°	604.7	604.4	604.2	603.7	603.0	602.4	601.8	601.1	601.8	602.4	603.0
130°	637.8	637.5	637.1	636.4	635.4	634.5	633.4	632.5	633.4	634.5	635.4
132.5°	670.9	671.0	671.1	670.3	668.7	667.1	665.5	663.9	665.5	667.1	668.7
135°	719.4	719.2	718.9	718.3	717.1	715.9	714.8	713.6	714.8	715.9	717.1
137.5°	766.5	766.1	765.7	764.9	763.8	762.7	761.6	760.4	761.6	762.7	763.8
140°	796.3	795.7	795.0	794.3	793.3	792.4	791.3	790.4	791.3	792.4	793.3
142.5°	826.0	825.2	824.5	823.7	822.9	822.1	821.2	820.4	821.2	822.1	822.9
145°	869.5	868.9	868.3	867.6	866.9	866.1	865.3	864.5	865.3	866.1	866.9
147.5°	908.4	908.0	907.6	907.1	906.6	906.3	905.9	905.4	905.9	906.3	906.6
150°	933.7	932.9	932.1	931.9	932.0	932.2	932.5	932.6	932.5	932.2	932.0
152.5°	956.9	956.7	956.3	956.1	955.8	955.5	955.2	954.9	955.2	955.5	955.8
155°	989.8	989.6	989.4	989.3	989.3	989.3	989.3	989.3	989.3	989.3	989.3
157.5°	1018.6	1018.4	1018.2	1018.3	1018.7	1019.2	1019.6	1020.0	1019.6	1019.2	1018.7
160°	1036.0	1035.9	1035.7	1035.9	1036.5	1037.0	1037.6	1038.2	1037.6	1037.0	1036.5
162.5°	1052.4	1052.4	1052.3	1052.5	1052.9	1053.3	1053.8	1054.2	1053.8	1053.3	1052.9
165°	1074.4	1074.3	1074.0	1074.1	1074.5	1074.9	1075.3	1075.7	1075.3	1074.9	1074.5
167.5°	1090.4	1090.4	1090.4	1090.7	1091.5	1092.3	1093.0	1093.8	1093.0	1092.3	1091.5
170°	1100.1	1100.1	1100.1	1100.5	1101.3	1102.1	1102.9	1103.6	1102.9	1102.1	1101.3
172.5°	1107.1	1107.1	1107.1	1107.5	1108.3	1109.1	1109.8	1110.6	1109.8	1109.1	1108.3
175°	1114.9	1114.9	1114.9	1115.3	1116.1	1116.9	1117.7	1118.4	1117.7	1116.9	1116.1
177.5°	1119.3	1119.4	1119.6	1120.0	1120.6	1121.2	1121.8	1122.5	1121.8	1121.2	1120.6
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1607.6	1600.1	1594.7	1583.9	1576.4	1573.2	1567.3	1565.6	1571.6	1567.3	1566.8
5°	1559.8	1540.3	1524.9	1509.4	1492.6	1482.0	1465.9	1463.1	1459.1	1453.0	1451.7
7.5°	1502.4	1477.1	1457.2	1431.8	1409.5	1391.7	1371.6	1362.0	1356.8	1349.0	1338.6
10°	1463.8	1433.6	1406.8	1381.2	1353.8	1331.6	1311.5	1296.0	1285.9	1276.5	1272.6
12.5°	1425.6	1394.9	1360.6	1329.7	1299.0	1274.1	1251.8	1241.8	1230.6	1219.6	1210.2
15°	1366.5	1325.5	1288.0	1252.4	1226.2	1199.4	1177.8	1163.1	1146.3	1141.7	1123.5
17.5°	1303.6	1263.5	1219.5	1182.1	1151.7	1122.1	1098.5	1081.8	1069.2	1051.9	1043.5
20°	1264.5	1216.9	1173.9	1139.6	1106.0	1071.2	1047.0	1032.9	1020.8	1006.8	1000.1
22.5°	1222.6	1176.0	1132.0	1091.8	1057.7	1023.4	1006.2	991.6	977.8	964.8	956.0
25°	1161.1	1114.1	1067.8	1026.2	990.7	965.8	945.6	928.8	921.5	908.8	899.3
27.5°	1100.3	1050.3	1002.3	960.8	932.9	908.4	891.8	878.6	865.2	854.1	845.9
30°	1061.1	1010.1	957.8	924.9	895.4	871.8	853.7	840.9	830.9	820.8	814.8
32.5°	1021.9	969.3	922.8	887.3	859.4	839.0	820.4	808.2	797.6	786.4	779.4
35°	959.1	905.4	867.8	832.9	805.4	786.6	773.9	756.4	747.7	739.6	732.2
37.5°	900.7	850.8	810.1	779.5	755.6	736.9	720.4	711.0	700.3	693.0	686.9
40°	857.7	812.1	775.2	743.0	725.6	704.7	689.3	677.2	669.2	659.8	653.1
42.5°	819.1	776.7	740.8	711.9	690.1	672.5	657.6	645.5	635.3	628.6	622.9
45°	764.5	722.2	687.3	660.4	640.3	623.5	608.0	602.0	588.6	580.6	577.9
47.5°	707.9	670.1	636.4	611.7	591.0	575.1	560.7	548.4	541.0	533.0	528.7
50°	669.9	633.6	602.0	577.9	557.8	540.3	526.8	518.8	508.8	501.4	496.0
52.5°	631.7	598.1	566.6	543.5	526.1	508.6	493.6	485.5	476.0	471.3	467.5
55°	577.2	541.7	514.8	492.0	473.8	457.7	443.7	435.6	429.6	424.8	423.5
57.5°	515.5	487.2	462.3	441.8	422.9	407.8	395.5	387.8	382.5	381.8	377.7
60°	475.2	449.7	426.9	404.7	388.6	374.5	363.8	355.1	349.7	349.0	347.7
62.5°	434.9	410.4	389.3	369.8	355.3	341.7	331.6	321.8	318.6	315.2	312.2
65°	375.1	353.0	335.6	320.1	304.7	293.3	283.3	277.2	269.8	265.8	258.4
67.5°	316.5	299.4	282.6	269.6	257.4	246.6	238.2	229.3	224.3	221.1	215.7
70°	277.8	264.4	247.6	233.6	224.2	215.4	208.7	198.6	195.3	192.6	189.9
72.5°	241.3	229.5	215.4	204.1	194.7	186.4	178.7	173.9	170.7	167.9	166.3
75°	189.9	178.6	166.4	158.4	151.7	145.0	140.9	137.6	136.2	135.6	132.9
77.5°	139.5	133.5	123.7	117.4	112.9	110.2	106.6	104.9	104.7	101.8	100.8
80°	106.7	103.3	95.3	92.6	89.3	86.6	84.6	81.2	77.8	76.5	74.5
82.5°	79.3	75.9	72.8	68.4	65.6	64.1	62.0	60.8	61.2	59.3	58.4
85°	42.3	38.9	37.6	36.9	35.6	36.9	36.2	35.6	34.9	34.3	34.9
87.5°	14.8	15.2	14.9	16.2	14.9	15.7	15.8	15.5	15.8	15.9	15.5
90°	7.1	8.5	9.9	11.3	12.6	13.9	14.9	15.9	16.9	17.8	18.6
92.5°	25.5	26.9	28.5	30.1	31.9	33.5	34.8	36.1	37.4	38.7	39.4
95°	58.3	59.4	61.4	63.3	65.3	67.2	68.5	69.9	71.2	72.6	73.4
97.5°	94.9	96.3	98.9	101.6	104.3	106.9	108.2	109.5	110.8	112.1	112.8
100°	122.2	123.4	125.9	128.5	131.0	133.5	135.3	137.0	138.7	140.4	141.5
102.5°	155.2	156.3	157.6	158.9	160.1	161.4	163.3	165.2	167.1	169.0	170.2
105°	202.8	203.9	205.0	206.2	207.3	208.5	209.7	210.9	212.0	213.2	214.0
107.5°	254.4	255.4	256.2	257.2	258.0	258.9	259.5	260.1	260.7	261.2	261.6
110°	290.1	290.8	291.4	292.0	292.6	293.2	293.7	294.3	294.9	295.5	295.7



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	324.4	325.1	325.8	326.6	327.3	328.0	328.3	328.6	328.8	329.1	329.1
115°	379.1	379.7	380.0	380.5	380.8	381.3	381.1	380.8	380.6	380.5	380.3
117.5°	431.2	431.5	431.9	432.2	432.6	432.9	433.1	433.2	433.3	433.5	433.2
120°	467.1	467.7	467.9	468.1	468.3	468.5	468.5	468.5	468.5	468.5	468.1
122.5°	500.9	501.4	501.9	502.4	502.9	503.4	503.3	503.1	502.9	502.7	502.4
125°	553.4	554.1	554.3	554.5	554.7	554.8	554.5	554.1	553.7	553.3	553.0
127.5°	603.7	604.2	604.4	604.7	604.9	605.1	604.9	604.7	604.5	604.3	604.1
130°	636.4	637.1	637.5	637.8	638.3	638.6	638.4	638.3	638.0	637.8	637.6
132.5°	670.3	671.1	671.0	670.9	670.8	670.7	670.5	670.3	670.1	669.9	669.6
135°	718.3	718.9	719.2	719.4	719.5	719.7	719.7	719.7	719.7	719.7	719.4
137.5°	764.9	765.7	766.1	766.5	767.0	767.4	767.6	767.8	768.1	768.3	767.9
140°	794.3	795.0	795.7	796.3	796.8	797.4	797.8	798.1	798.6	798.9	798.7
142.5°	823.7	824.5	825.2	826.0	826.6	827.4	827.6	827.9	828.1	828.4	827.9
145°	867.6	868.3	868.9	869.5	870.1	870.6	870.6	870.6	870.6	870.6	870.4
147.5°	907.1	907.6	908.0	908.4	909.0	909.4	909.9	910.3	910.8	911.3	910.9
150°	931.9	932.1	932.9	933.7	934.4	935.2	935.2	935.2	935.2	935.2	935.0
152.5°	956.1	956.3	956.7	956.9	957.3	957.6	958.0	958.5	959.0	959.4	959.3
155°	989.3	989.4	989.6	989.8	990.0	990.2	991.0	991.8	992.6	993.3	993.2
157.5°	1018.3	1018.2	1018.4	1018.6	1018.8	1019.0	1019.8	1020.5	1021.3	1022.1	1021.8
160°	1035.9	1035.7	1035.9	1036.0	1036.2	1036.5	1037.2	1038.0	1038.8	1039.6	1039.4
162.5°	1052.5	1052.3	1052.4	1052.4	1052.5	1052.5	1053.4	1054.4	1055.2	1056.2	1056.1
165°	1074.1	1074.0	1074.3	1074.4	1074.6	1074.8	1075.6	1076.3	1077.1	1077.9	1077.7
167.5°	1090.7	1090.4	1090.4	1090.4	1090.4	1090.4	1091.5	1092.7	1093.8	1095.0	1095.0
170°	1100.5	1100.1	1100.1	1100.1	1100.1	1100.1	1101.3	1102.4	1103.6	1104.7	1104.7
172.5°	1107.5	1107.1	1107.1	1107.1	1107.1	1107.1	1108.3	1109.4	1110.6	1111.7	1111.7
175°	1115.3	1114.9	1114.9	1114.9	1114.9	1114.9	1116.1	1117.2	1118.4	1119.6	1119.5
177.5°	1120.0	1119.6	1119.4	1119.3	1119.1	1119.0	1119.9	1120.8	1121.8	1122.7	1122.6
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1566.2	1560.3	1558.7	1560.8	1558.7	1560.3	1566.2	1566.8	1567.3	1571.6	1565.6
5°	1445.0	1438.3	1441.7	1440.3	1441.7	1438.3	1445.0	1451.7	1453.0	1459.1	1463.1
7.5°	1338.4	1330.1	1321.2	1324.0	1321.2	1330.1	1338.4	1338.6	1349.0	1356.8	1362.0
10°	1263.8	1257.1	1253.0	1256.4	1253.0	1257.1	1263.8	1272.6	1276.5	1285.9	1296.0
12.5°	1201.0	1197.0	1193.4	1192.0	1193.4	1197.0	1201.0	1210.2	1219.6	1230.6	1241.8
15°	1115.4	1107.4	1104.1	1095.4	1104.1	1107.4	1115.4	1123.5	1141.7	1146.3	1163.1
17.5°	1036.6	1034.0	1025.3	1021.5	1025.3	1034.0	1036.6	1043.5	1051.9	1069.2	1081.8
20°	990.0	987.3	978.5	984.0	978.5	987.3	990.0	1000.1	1006.8	1020.8	1032.9
22.5°	951.3	945.4	942.5	941.0	942.5	945.4	951.3	956.0	964.8	977.8	991.6
25°	896.6	887.9	884.6	880.5	884.6	887.9	896.6	899.3	908.8	921.5	928.8
27.5°	842.1	837.5	833.0	832.0	833.0	837.5	842.1	845.9	854.1	865.2	878.6
30°	806.8	802.0	798.7	798.7	798.7	802.0	806.8	814.8	820.8	830.9	840.9
32.5°	775.1	771.5	768.1	767.6	768.1	771.5	775.1	779.4	786.4	797.6	808.2
35°	728.9	723.5	722.2	718.2	722.2	723.5	728.9	732.2	739.6	747.7	756.4
37.5°	681.0	676.5	676.4	676.0	676.4	676.5	681.0	686.9	693.0	700.3	711.0
40°	650.3	647.0	646.4	641.6	646.4	647.0	650.3	653.1	659.8	669.2	677.2
42.5°	617.6	615.9	613.5	611.6	613.5	615.9	617.6	622.9	628.6	635.3	645.5
45°	573.2	568.4	568.4	565.1	568.4	568.4	573.2	577.9	580.6	588.6	602.0
47.5°	527.3	523.7	524.0	520.6	524.0	523.7	527.3	528.7	533.0	541.0	548.4
50°	496.6	494.6	494.0	492.7	494.0	494.6	496.6	496.0	501.4	508.8	518.8
52.5°	466.1	465.1	467.7	464.7	467.7	465.1	466.1	467.5	471.3	476.0	485.5
55°	424.8	422.8	426.9	422.8	426.9	422.8	424.8	423.5	424.8	429.6	435.6
57.5°	377.5	375.6	379.2	377.2	379.2	375.6	377.5	377.7	381.8	382.5	387.8
60°	346.3	342.3	344.3	345.0	344.3	342.3	346.3	347.7	349.0	349.7	355.1
62.5°	309.3	306.9	308.3	305.2	308.3	306.9	309.3	312.2	315.2	318.6	321.8
65°	257.1	255.0	252.4	251.0	252.4	255.0	257.1	258.4	265.8	269.8	277.2
67.5°	215.9	211.1	211.0	212.1	211.0	211.1	215.9	215.7	221.1	224.3	229.3
70°	185.9	185.9	185.2	185.2	185.2	185.9	185.9	189.9	192.6	195.3	198.6
72.5°	165.0	164.5	163.2	162.7	163.2	164.5	165.0	166.3	167.9	170.7	173.9
75°	132.9	133.5	132.2	131.6	132.2	133.5	132.9	132.9	135.6	136.2	137.6
77.5°	98.2	95.3	96.8	95.3	96.8	95.3	98.2	100.8	101.8	104.7	104.9
80°	74.5	73.8	75.9	73.8	75.9	73.8	74.5	74.5	76.5	77.8	81.2
82.5°	58.9	58.3	59.2	57.7	59.2	58.3	58.9	58.4	59.3	61.2	60.8
85°	35.6	34.9	34.3	34.9	34.3	34.9	35.6	34.9	34.3	34.9	35.6
87.5°	16.2	15.8	15.8	16.0	15.8	15.8	16.2	15.5	15.9	15.8	15.5
90°	19.2	19.8	20.3	20.9	20.3	19.8	19.2	18.6	17.8	16.9	15.9
92.5°	39.9	40.3	40.7	41.2	40.7	40.3	39.9	39.4	38.7	37.4	36.1
95°	73.9	74.2	74.6	75.0	74.6	74.2	73.9	73.4	72.6	71.2	69.9
97.5°	113.0	113.3	113.6	113.7	113.6	113.3	113.0	112.8	112.1	110.8	109.5
100°	141.9	142.3	142.7	143.1	142.7	142.3	141.9	141.5	140.4	138.7	137.0
102.5°	170.7	171.3	171.9	172.4	171.9	171.3	170.7	170.2	169.0	167.1	165.2
105°	214.6	215.2	215.8	216.4	215.8	215.2	214.6	214.0	213.2	212.0	210.9
107.5°	261.5	261.5	261.4	261.4	261.4	261.5	261.5	261.6	261.2	260.7	260.1
110°	295.5	295.2	295.1	294.9	295.1	295.2	295.5	295.7	295.5	294.9	294.3



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	328.7	328.4	328.0	327.7	328.0	328.4	328.7	329.1	329.1	328.8	328.6
115°	380.0	379.9	379.7	379.5	379.7	379.9	380.0	380.3	380.5	380.6	380.8
117.5°	432.4	431.6	430.8	430.1	430.8	431.6	432.4	433.2	433.5	433.3	433.2
120°	467.4	466.6	465.8	465.0	465.8	466.6	467.4	468.1	468.5	468.5	468.5
122.5°	501.8	501.1	500.5	499.9	500.5	501.1	501.8	502.4	502.7	502.9	503.1
125°	552.8	552.6	552.4	552.2	552.4	552.6	552.8	553.0	553.3	553.7	554.1
127.5°	603.6	603.3	602.9	602.5	602.9	603.3	603.6	604.1	604.3	604.5	604.7
130°	637.1	636.8	636.4	636.0	636.4	636.8	637.1	637.6	637.8	638.0	638.3
132.5°	669.0	668.5	668.0	667.4	668.0	668.5	669.0	669.6	669.9	670.1	670.3
135°	718.6	717.8	717.0	716.3	717.0	717.8	718.6	719.4	719.7	719.7	719.7
137.5°	767.0	766.0	765.0	764.1	765.0	766.0	767.0	767.9	768.3	768.1	767.8
140°	797.7	796.7	795.7	794.8	795.7	796.7	797.7	798.7	798.9	798.6	798.1
142.5°	827.0	826.0	825.1	824.1	825.1	826.0	827.0	827.9	828.4	828.1	827.9
145°	869.8	869.2	868.7	868.1	868.7	869.2	869.8	870.4	870.6	870.6	870.6
147.5°	909.6	908.2	906.9	905.6	906.9	908.2	909.6	910.9	911.3	910.8	910.3
150°	934.6	934.3	933.8	933.5	933.8	934.3	934.6	935.0	935.2	935.2	935.2
152.5°	958.6	957.9	957.2	956.5	957.2	957.9	958.6	959.3	959.4	959.0	958.5
155°	992.2	991.3	990.3	989.3	990.3	991.3	992.2	993.2	993.3	992.6	991.8
157.5°	1020.5	1019.3	1018.0	1016.8	1018.0	1019.3	1020.5	1021.8	1022.1	1021.3	1020.5
160°	1038.5	1037.5	1036.6	1035.5	1036.6	1037.5	1038.5	1039.4	1039.6	1038.8	1038.0
162.5°	1055.0	1053.9	1052.7	1051.6	1052.7	1053.9	1055.0	1056.1	1056.2	1055.2	1054.4
165°	1076.6	1075.4	1074.3	1073.1	1074.3	1075.4	1076.6	1077.7	1077.9	1077.1	1076.3
167.5°	1093.8	1092.6	1091.4	1090.2	1091.4	1092.6	1093.8	1095.0	1095.0	1093.8	1092.7
170°	1103.3	1102.0	1100.6	1099.2	1100.6	1102.0	1103.3	1104.7	1104.7	1103.6	1102.4
172.5°	1110.5	1109.3	1108.1	1106.9	1108.1	1109.3	1110.5	1111.7	1111.7	1110.6	1109.4
175°	1118.2	1116.8	1115.4	1114.0	1115.4	1116.8	1118.2	1119.5	1119.6	1118.4	1117.2
177.5°	1121.5	1120.4	1119.4	1118.3	1119.4	1120.4	1121.5	1122.6	1122.7	1121.8	1120.8
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1567.3	1573.2	1576.4	1583.9	1594.7	1600.1	1607.6	1612.9	1620.5	1629.6	1637.1
5°	1465.9	1482.0	1492.6	1509.4	1524.9	1540.3	1559.8	1573.9	1592.7	1614.1	1630.9
7.5°	1371.6	1391.7	1409.5	1431.8	1457.2	1477.1	1502.4	1528.4	1557.7	1588.2	1617.0
10°	1311.5	1331.6	1353.8	1381.2	1406.8	1433.6	1463.8	1494.0	1530.9	1565.1	1604.0
12.5°	1251.8	1274.1	1299.0	1329.7	1360.6	1394.9	1425.6	1459.7	1499.3	1543.7	1585.3
15°	1177.8	1199.4	1226.2	1252.4	1288.0	1325.5	1366.5	1411.4	1455.8	1505.4	1557.1
17.5°	1098.5	1122.1	1151.7	1182.1	1219.5	1263.5	1303.6	1352.9	1402.7	1460.6	1521.4
20°	1047.0	1071.2	1106.0	1139.6	1173.9	1216.9	1264.5	1314.8	1367.8	1428.9	1496.7
22.5°	1006.2	1023.4	1057.7	1091.8	1132.0	1176.0	1222.6	1275.1	1332.9	1396.1	1467.1
25°	945.6	965.8	990.7	1026.2	1067.8	1114.1	1161.1	1216.9	1279.9	1344.4	1420.1
27.5°	891.8	908.4	932.9	960.8	1002.3	1050.3	1100.3	1158.4	1223.1	1288.7	1368.5
30°	853.7	871.8	895.4	924.9	957.8	1010.1	1061.1	1118.2	1184.0	1251.7	1333.6
32.5°	820.4	839.0	859.4	887.3	922.8	969.3	1021.9	1077.9	1144.7	1214.7	1294.4
35°	773.9	786.6	805.4	832.9	867.8	905.4	959.1	1018.1	1083.2	1155.7	1235.6
37.5°	720.4	736.9	755.6	779.5	810.1	850.8	900.7	960.4	1020.8	1090.2	1163.1
40°	689.3	704.7	725.6	743.0	775.2	812.1	857.7	920.2	980.6	1045.7	1112.2
42.5°	657.6	672.5	690.1	711.9	740.8	776.7	819.1	877.2	941.9	1003.2	1058.9
45°	608.0	623.5	640.3	660.4	687.3	722.2	764.5	817.4	873.8	930.2	972.5
47.5°	560.7	575.1	591.0	611.7	636.4	670.1	707.9	754.8	809.5	857.5	887.7
50°	526.8	540.3	557.8	577.9	602.0	633.6	669.9	716.1	761.7	805.4	832.9
52.5°	493.6	508.6	526.1	543.5	566.6	598.1	631.7	671.6	715.1	750.6	773.4
55°	443.7	457.7	473.8	492.0	514.8	541.7	577.2	608.7	643.0	673.2	686.6
57.5°	395.5	407.8	422.9	441.8	462.3	487.2	515.5	545.8	570.0	591.3	606.5
60°	363.8	374.5	388.6	404.7	426.9	449.7	475.2	503.3	522.2	540.3	554.4
62.5°	331.6	341.7	355.3	369.8	389.3	410.4	434.9	457.7	476.0	488.2	504.5
65°	283.3	293.3	304.7	320.1	335.6	353.0	375.1	391.9	404.7	418.1	428.2
67.5°	238.2	246.6	257.4	269.6	282.6	299.4	316.5	330.5	339.2	347.2	359.4
70°	208.7	215.4	224.2	233.6	247.6	264.4	277.8	288.6	294.6	302.7	317.5
72.5°	178.7	186.4	194.7	204.1	215.4	229.5	241.3	252.1	256.0	262.4	271.8
75°	140.9	145.0	151.7	158.4	166.4	178.6	189.9	192.6	196.0	201.4	208.0
77.5°	106.6	110.2	112.9	117.4	123.7	133.5	139.5	143.5	144.3	146.3	152.9
80°	84.6	86.6	89.3	92.6	95.3	103.3	106.7	110.7	112.1	114.1	117.4
82.5°	62.0	64.1	65.6	68.4	72.8	75.9	79.3	83.3	83.6	85.1	85.8
85°	36.2	36.9	35.6	36.9	37.6	38.9	42.3	45.6	44.9	44.3	46.3
87.5°	15.8	15.7	14.9	16.2	14.9	15.2	14.8	15.1	15.8	16.6	17.4
90°	14.9	13.9	12.6	11.3	9.9	8.5	7.1	5.5	4.0	2.4	0.9
92.5°	34.8	33.5	31.9	30.1	28.5	26.9	25.5	24.4	23.2	22.2	21.1
95°	68.5	67.2	65.3	63.3	61.4	59.4	58.3	57.9	57.5	57.1	56.7
97.5°	108.2	106.9	104.3	101.6	98.9	96.3	94.9	94.7	94.5	94.4	94.2
100°	135.3	133.5	131.0	128.5	125.9	123.4	122.2	122.2	122.2	122.2	122.2
102.5°	163.3	161.4	160.1	158.9	157.6	156.3	155.2	154.5	153.7	152.9	152.1
105°	209.7	208.5	207.3	206.2	205.0	203.9	202.8	201.8	200.9	199.8	198.9
107.5°	259.5	258.9	258.0	257.2	256.2	255.4	254.4	253.5	252.5	251.5	250.6
110°	293.7	293.2	292.6	292.0	291.4	290.8	290.1	289.0	288.1	287.1	286.1



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	328.3	328.0	327.3	326.6	325.8	325.1	324.4	324.0	323.5	323.0	322.4
115°	381.1	381.3	380.8	380.5	380.0	379.7	379.1	378.3	377.5	376.8	376.0
117.5°	433.1	432.9	432.6	432.2	431.9	431.5	431.2	430.8	430.4	430.1	429.7
120°	468.5	468.5	468.3	468.1	467.9	467.7	467.1	466.1	465.2	464.3	463.2
122.5°	503.3	503.4	502.9	502.4	501.9	501.4	500.9	500.6	500.2	499.9	499.6
125°	554.5	554.8	554.7	554.5	554.3	554.1	553.4	552.2	551.0	549.9	548.7
127.5°	604.9	605.1	604.9	604.7	604.4	604.2	603.7	603.0	602.4	601.8	601.1
130°	638.4	638.6	638.3	637.8	637.5	637.1	636.4	635.4	634.5	633.4	632.5
132.5°	670.5	670.7	670.8	670.9	671.0	671.1	670.3	668.7	667.1	665.5	663.9
135°	719.7	719.7	719.5	719.4	719.2	718.9	718.3	717.1	715.9	714.8	713.6
137.5°	767.6	767.4	767.0	766.5	766.1	765.7	764.9	763.8	762.7	761.6	760.4
140°	797.8	797.4	796.8	796.3	795.7	795.0	794.3	793.3	792.4	791.3	790.4
142.5°	827.6	827.4	826.6	826.0	825.2	824.5	823.7	822.9	822.1	821.2	820.4
145°	870.6	870.6	870.1	869.5	868.9	868.3	867.6	866.9	866.1	865.3	864.5
147.5°	909.9	909.4	909.0	908.4	908.0	907.6	907.1	906.6	906.3	905.9	905.4
150°	935.2	935.2	934.4	933.7	932.9	932.1	931.9	932.0	932.2	932.5	932.6
152.5°	958.0	957.6	957.3	956.9	956.7	956.3	956.1	955.8	955.5	955.2	954.9
155°	991.0	990.2	990.0	989.8	989.6	989.4	989.3	989.3	989.3	989.3	989.3
157.5°	1019.8	1019.0	1018.8	1018.6	1018.4	1018.2	1018.3	1018.7	1019.2	1019.6	1020.0
160°	1037.2	1036.5	1036.2	1036.0	1035.9	1035.7	1035.9	1036.5	1037.0	1037.6	1038.2
162.5°	1053.4	1052.5	1052.5	1052.4	1052.4	1052.3	1052.5	1052.9	1053.3	1053.8	1054.2
165°	1075.6	1074.8	1074.6	1074.4	1074.3	1074.0	1074.1	1074.5	1074.9	1075.3	1075.7
167.5°	1091.5	1090.4	1090.4	1090.4	1090.4	1090.4	1090.7	1091.5	1092.3	1093.0	1093.8
170°	1101.3	1100.1	1100.1	1100.1	1100.1	1100.1	1100.5	1101.3	1102.1	1102.9	1103.6
172.5°	1108.3	1107.1	1107.1	1107.1	1107.1	1107.1	1107.5	1108.3	1109.1	1109.8	1110.6
175°	1116.1	1114.9	1114.9	1114.9	1114.9	1114.9	1115.3	1116.1	1116.9	1117.7	1118.4
177.5°	1119.9	1119.0	1119.1	1119.3	1119.4	1119.6	1120.0	1120.6	1121.2	1121.8	1122.5
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1643.0	1647.9	1654.8	1662.8	1669.3	1676.3	1680.1	1680.1	1683.3	1690.2	1699.4
5°	1647.7	1665.2	1682.0	1703.4	1720.2	1739.7	1754.4	1768.5	1781.2	1797.3	1814.1
7.5°	1646.3	1675.3	1705.6	1739.4	1776.7	1806.4	1836.9	1860.7	1884.4	1915.2	1939.5
10°	1641.0	1678.6	1719.5	1762.5	1809.5	1850.4	1887.3	1920.9	1953.1	1986.7	2016.8
12.5°	1631.3	1679.1	1729.1	1780.7	1840.0	1886.9	1934.6	1970.2	2007.9	2044.6	2081.8
15°	1616.8	1673.2	1733.6	1805.4	1877.9	1930.3	1977.2	2023.5	2058.5	2100.1	2135.6
17.5°	1586.9	1659.5	1735.5	1814.0	1883.7	1944.5	1993.7	2037.8	2074.9	2120.7	2169.0
20°	1569.2	1647.7	1726.9	1810.8	1877.2	1939.7	1987.3	2032.9	2079.2	2139.0	2198.0
22.5°	1544.5	1628.4	1712.4	1792.0	1862.2	1922.4	1971.8	2027.6	2088.4	2156.2	2227.6
25°	1505.4	1592.0	1675.2	1751.0	1819.6	1881.3	1948.4	2023.5	2097.4	2186.7	2289.3
27.5°	1455.9	1539.4	1613.6	1693.8	1761.8	1840.3	1924.1	2005.5	2112.0	2234.8	2363.0
30°	1418.8	1498.1	1568.5	1644.3	1721.5	1808.1	1902.0	1998.0	2124.9	2269.2	2421.6
32.5°	1375.9	1447.6	1517.5	1590.6	1679.6	1774.8	1874.7	1992.1	2143.7	2307.8	2465.6
35°	1301.4	1365.8	1433.6	1514.8	1609.5	1712.8	1840.3	1983.3	2166.5	2343.0	2484.7
37.5°	1223.2	1274.1	1342.2	1427.8	1530.9	1650.5	1795.2	1968.9	2157.1	2315.5	2375.8
40°	1163.1	1210.7	1282.5	1372.5	1474.5	1605.4	1767.8	1946.4	2135.6	2245.7	2241.0
42.5°	1103.5	1151.7	1220.8	1311.3	1417.6	1564.1	1731.3	1916.8	2076.6	2118.5	2031.1
45°	1012.1	1057.0	1124.9	1216.2	1330.2	1483.9	1659.7	1837.6	1939.7	1871.9	1698.7
47.5°	918.9	962.6	1025.5	1114.9	1239.5	1400.3	1566.6	1712.5	1726.9	1581.2	1373.6
50°	857.7	898.7	958.4	1053.7	1174.5	1331.6	1492.0	1606.8	1571.2	1393.4	1179.2
52.5°	798.1	837.5	893.5	983.3	1106.9	1260.7	1403.9	1494.0	1411.7	1222.6	1029.9
55°	710.1	747.7	804.1	886.6	998.7	1139.6	1265.2	1298.0	1177.2	986.6	830.9
57.5°	626.5	654.0	709.7	782.7	890.8	1015.0	1105.0	1099.1	965.8	794.1	682.4
60°	571.2	596.0	649.0	716.1	818.8	930.2	993.3	966.5	831.6	689.9	582.6
62.5°	519.6	542.9	587.3	649.0	737.2	834.1	880.0	843.0	715.6	591.2	505.8
65°	441.6	458.4	494.0	551.0	620.2	687.3	728.2	673.8	561.1	467.1	402.7
67.5°	368.8	383.2	414.9	455.8	503.5	549.8	566.5	515.5	427.8	364.5	319.1
70°	321.5	334.9	356.4	394.7	426.2	459.1	467.1	421.5	348.4	300.0	271.8
72.5°	276.4	288.7	307.5	334.5	356.4	375.3	379.1	336.7	280.7	247.4	225.7
75°	210.8	221.4	233.6	243.7	257.7	261.1	259.8	226.9	196.7	174.5	162.4
77.5°	154.9	159.4	166.7	170.7	171.4	171.2	164.3	143.5	127.9	118.8	113.8
80°	119.5	122.9	124.8	126.1	126.8	120.1	112.8	100.0	94.6	89.3	83.3
82.5°	86.7	89.0	91.0	91.3	87.6	82.1	75.2	68.9	65.1	62.4	60.1
85°	47.0	47.6	47.0	43.7	38.9	36.9	35.6	34.3	33.6	32.9	32.9
87.5°	17.1	15.8	13.4	14.3	14.6	14.3	14.6	14.3	14.0	14.3	14.5
90°	2.4	4.0	5.5	7.1	8.5	9.9	11.3	12.6	13.9	14.9	15.9
92.5°	22.2	23.2	24.4	25.5	26.9	28.5	30.1	31.9	33.5	34.8	36.1
95°	57.1	57.5	57.9	58.3	59.4	61.4	63.3	65.3	67.2	68.5	69.9
97.5°	94.4	94.5	94.7	94.9	96.3	98.9	101.6	104.3	106.9	108.2	109.5
100°	122.2	122.2	122.2	122.2	123.4	125.9	128.5	131.0	133.5	135.3	137.0
102.5°	152.9	153.7	154.5	155.2	156.3	157.6	158.9	160.1	161.4	163.3	165.2
105°	199.8	200.9	201.8	202.8	203.9	205.0	206.2	207.3	208.5	209.7	210.9
107.5°	251.5	252.5	253.5	254.4	255.4	256.2	257.2	258.0	258.9	259.5	260.1
110°	287.1	288.1	289.0	290.1	290.8	291.4	292.0	292.6	293.2	293.7	294.3



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	323.0	323.5	324.0	324.4	325.1	325.8	326.6	327.3	328.0	328.3	328.6
115°	376.8	377.5	378.3	379.1	379.7	380.0	380.5	380.8	381.3	381.1	380.8
117.5°	430.1	430.4	430.8	431.2	431.5	431.9	432.2	432.6	432.9	433.1	433.2
120°	464.3	465.2	466.1	467.1	467.7	467.9	468.1	468.3	468.5	468.5	468.5
122.5°	499.9	500.2	500.6	500.9	501.4	501.9	502.4	502.9	503.4	503.3	503.1
125°	549.9	551.0	552.2	553.4	554.1	554.3	554.5	554.7	554.8	554.5	554.1
127.5°	601.8	602.4	603.0	603.7	604.2	604.4	604.7	604.9	605.1	604.9	604.7
130°	633.4	634.5	635.4	636.4	637.1	637.5	637.8	638.3	638.6	638.4	638.3
132.5°	665.5	667.1	668.7	670.3	671.1	671.0	670.9	670.8	670.7	670.5	670.3
135°	714.8	715.9	717.1	718.3	718.9	719.2	719.4	719.5	719.7	719.7	719.7
137.5°	761.6	762.7	763.8	764.9	765.7	766.1	766.5	767.0	767.4	767.6	767.8
140°	791.3	792.4	793.3	794.3	795.0	795.7	796.3	796.8	797.4	797.8	798.1
142.5°	821.2	822.1	822.9	823.7	824.5	825.2	826.0	826.6	827.4	827.6	827.9
145°	865.3	866.1	866.9	867.6	868.3	868.9	869.5	870.1	870.6	870.6	870.6
147.5°	905.9	906.3	906.6	907.1	907.6	908.0	908.4	909.0	909.4	909.9	910.3
150°	932.5	932.2	932.0	931.9	932.1	932.9	933.7	934.4	935.2	935.2	935.2
152.5°	955.2	955.5	955.8	956.1	956.3	956.7	956.9	957.3	957.6	958.0	958.5
155°	989.3	989.3	989.3	989.3	989.4	989.6	989.8	990.0	990.2	991.0	991.8
157.5°	1019.6	1019.2	1018.7	1018.3	1018.2	1018.4	1018.6	1018.8	1019.0	1019.8	1020.5
160°	1037.6	1037.0	1036.5	1035.9	1035.7	1035.9	1036.0	1036.2	1036.5	1037.2	1038.0
162.5°	1053.8	1053.3	1052.9	1052.5	1052.3	1052.4	1052.4	1052.5	1052.5	1053.4	1054.4
165°	1075.3	1074.9	1074.5	1074.1	1074.0	1074.3	1074.4	1074.6	1074.8	1075.6	1076.3
167.5°	1093.0	1092.3	1091.5	1090.7	1090.4	1090.4	1090.4	1090.4	1090.4	1091.5	1092.7
170°	1102.9	1102.1	1101.3	1100.5	1100.1	1100.1	1100.1	1100.1	1100.1	1101.3	1102.4
172.5°	1109.8	1109.1	1108.3	1107.5	1107.1	1107.1	1107.1	1107.1	1107.1	1108.3	1109.4
175°	1117.7	1116.9	1116.1	1115.3	1114.9	1114.9	1114.9	1114.9	1114.9	1116.1	1117.2
177.5°	1121.8	1121.2	1120.6	1120.0	1119.6	1119.4	1119.3	1119.1	1119.0	1119.9	1120.8
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0	1635.0
2.5°	1706.3	1706.3	1715.5	1714.9	1720.9	1718.7	1719.8
5°	1834.3	1845.7	1855.8	1862.4	1872.5	1875.3	1873.9
7.5°	1966.9	1992.3	2004.6	2021.5	2024.6	2033.5	2032.6
10°	2049.1	2073.9	2092.7	2107.5	2114.8	2124.3	2124.9
12.5°	2113.5	2134.6	2151.2	2164.9	2173.9	2176.9	2178.6
15°	2163.8	2187.3	2206.7	2226.2	2237.7	2246.3	2251.1
17.5°	2214.6	2250.8	2285.2	2311.6	2327.5	2340.9	2340.7
20°	2253.8	2295.3	2338.3	2368.5	2399.4	2412.8	2414.8
22.5°	2295.6	2359.2	2414.6	2461.4	2502.0	2515.9	2521.2
25°	2382.6	2465.8	2551.1	2616.8	2663.8	2691.3	2695.4
27.5°	2487.7	2600.3	2690.0	2750.7	2789.7	2810.1	2814.6
30°	2561.8	2665.8	2746.4	2792.1	2810.1	2812.8	2802.7
32.5°	2595.1	2672.8	2705.0	2702.3	2666.8	2643.2	2634.1
35°	2554.4	2538.3	2459.8	2365.9	2294.0	2248.4	2236.3
37.5°	2324.6	2185.7	2041.3	1899.3	1823.7	1785.3	1719.2
40°	2098.1	1900.1	1749.7	1630.2	1545.0	1476.5	1460.4
42.5°	1842.5	1638.1	1487.7	1385.4	1317.3	1270.4	1250.0
45°	1480.6	1304.8	1180.6	1102.1	1049.7	1015.5	1000.1
47.5°	1184.2	1048.1	957.6	899.5	859.6	829.8	821.5
50°	1021.5	912.7	836.3	787.3	757.1	734.3	724.9
52.5°	887.3	799.5	740.7	700.3	671.7	657.5	649.7
55°	732.2	656.4	614.2	581.9	565.8	554.4	549.0
57.5°	598.8	544.1	513.2	490.9	476.0	468.7	466.1
60°	524.2	481.2	453.1	435.6	425.5	416.1	413.5
62.5°	458.1	424.3	402.6	387.3	377.2	373.2	371.5
65°	369.1	347.0	330.9	321.5	313.4	312.1	311.4
67.5°	293.4	280.4	272.0	262.2	259.3	254.6	253.7
70°	251.0	242.3	232.2	228.9	225.5	220.8	221.4
72.5°	212.9	204.1	197.3	192.9	191.7	189.7	191.4
75°	155.7	153.0	150.3	147.0	145.7	145.7	145.0
77.5°	111.2	108.8	105.9	103.9	103.5	100.7	101.8
80°	80.5	77.1	75.9	76.5	74.5	73.8	73.8
82.5°	59.6	58.4	57.1	57.2	56.7	56.1	56.7
85°	32.9	32.2	32.2	31.5	31.5	30.9	30.9
87.5°	15.2	15.9	15.0	14.6	14.7	15.3	16.0
90°	16.9	17.8	18.6	19.2	19.8	20.3	20.9
92.5°	37.4	38.7	39.4	39.9	40.3	40.7	41.2
95°	71.2	72.6	73.4	73.9	74.2	74.6	75.0
97.5°	110.8	112.1	112.8	113.0	113.3	113.6	113.7
100°	138.7	140.4	141.5	141.9	142.3	142.7	143.1
102.5°	167.1	169.0	170.2	170.7	171.3	171.9	172.4
105°	212.0	213.2	214.0	214.6	215.2	215.8	216.4
107.5°	260.7	261.2	261.6	261.5	261.5	261.4	261.4
110°	294.9	295.5	295.7	295.5	295.2	295.1	294.9



TEST NUMBER: P333729-935

CATALOG NUMBER: S125RDIW-S1270D1050U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	328.8	329.1	329.1	328.7	328.4	328.0	327.7
115°	380.6	380.5	380.3	380.0	379.9	379.7	379.5
117.5°	433.3	433.5	433.2	432.4	431.6	430.8	430.1
120°	468.5	468.5	468.1	467.4	466.6	465.8	465.0
122.5°	502.9	502.7	502.4	501.8	501.1	500.5	499.9
125°	553.7	553.3	553.0	552.8	552.6	552.4	552.2
127.5°	604.5	604.3	604.1	603.6	603.3	602.9	602.5
130°	638.0	637.8	637.6	637.1	636.8	636.4	636.0
132.5°	670.1	669.9	669.6	669.0	668.5	668.0	667.4
135°	719.7	719.7	719.4	718.6	717.8	717.0	716.3
137.5°	768.1	768.3	767.9	767.0	766.0	765.0	764.1
140°	798.6	798.9	798.7	797.7	796.7	795.7	794.8
142.5°	828.1	828.4	827.9	827.0	826.0	825.1	824.1
145°	870.6	870.6	870.4	869.8	869.2	868.7	868.1
147.5°	910.8	911.3	910.9	909.6	908.2	906.9	905.6
150°	935.2	935.2	935.0	934.6	934.3	933.8	933.5
152.5°	959.0	959.4	959.3	958.6	957.9	957.2	956.5
155°	992.6	993.3	993.2	992.2	991.3	990.3	989.3
157.5°	1021.3	1022.1	1021.8	1020.5	1019.3	1018.0	1016.8
160°	1038.8	1039.6	1039.4	1038.5	1037.5	1036.6	1035.5
162.5°	1055.2	1056.2	1056.1	1055.0	1053.9	1052.7	1051.6
165°	1077.1	1077.9	1077.7	1076.6	1075.4	1074.3	1073.1
167.5°	1093.8	1095.0	1095.0	1093.8	1092.6	1091.4	1090.2
170°	1103.6	1104.7	1104.7	1103.3	1102.0	1100.6	1099.2
172.5°	1110.6	1111.7	1111.7	1110.5	1109.3	1108.1	1106.9
175°	1118.4	1119.6	1119.5	1118.2	1116.8	1115.4	1114.0
177.5°	1121.8	1122.7	1122.6	1121.5	1120.4	1119.4	1118.3
180°	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0	1121.0

(END OF REPORT)