

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333645-935

Luminaire Tested: **S125RDIW-S375D770U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333645-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D770U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3549.2 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	79	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	55	49	65	56	50	45	46	41	38	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	39	41	36	32	33	29	26	25	22	20	17
6	61	50	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	29	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3130	3130	3130	3130
5°	3601	3135	2768	3135
10°	4131	3118	2443	3118
15°	4462	3086	2171	3086
20°	4920	3049	2004	3049
25°	5694	2999	1861	2999
30°	6196	2948	1766	2948
35°	5226	2888	1678	2888
40°	3650	2780	1604	2780
45°	2707	2633	1531	2633
50°	2159	2481	1467	2481
55°	1832	2291	1412	2291
60°	1582	2124	1321	2124
65°	1411	1939	1137	1939
70°	1241	1777	1037	1777
75°	1073	1537	973	1537
80°	815	1294	815	1294
85°	674	1015	763	1015



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	1.3
10°-20°	136.2	3.8
20°-30°	215.9	6.1
30°-40°	260.4	7.3
40°-50°	232.6	6.6
50°-60°	178.3	5.0
60°-70°	115.9	3.3
70°-80°	56.3	1.6
80°-90°	15.2	0.4
90°-100°	55.0	1.5
100°-110°	162.4	4.6
110°-120°	275.1	7.8
120°-130°	362.1	10.2
130°-140°	405.7	11.4
140°-150°	397.7	11.2
150°-160°	334.0	9.4
160°-170°	222.0	6.3
170°-180°	77.7	2.2
0°-30°	398.6	11.2
0°-40°	659.0	18.6
0°-60°	1069.9	30.1
0°-90°	1257.4	35.4
90°-120°	492.6	13.9
90°-150°	1658.1	46.7
90°-180°	2292.0	64.6
0°-180°	3549.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	555	484	427	484	555	55
15°	667	462	325	462	667	191
25°	799	421	261	421	799	367
35°	663	366	213	366	663	400
45°	296	288	168	288	296	237
55°	163	204	125	204	163	148
65°	92	127	74	127	92	92
75°	43	62	39	62	43	46
85°	9	14	10	14	9	11
90°	15	1	15	1	15	9
95°	55	42	55	42	55	56
105°	158	146	158	146	158	168
115°	278	276	278	276	278	275
125°	405	402	405	402	405	361
135°	525	523	525	523	525	405
145°	636	633	636	633	636	397
155°	725	725	725	725	725	334
165°	786	788	786	788	786	222
175°	816	819	816	819	816	78
180°	821	821	821	821	821	



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	509.8	509.5	510.1	508.3	508.5	505.8	505.8	503.8	501.0	498.9	498.0
5°	555.4	555.9	555.1	552.1	550.1	547.1	543.7	537.8	532.8	528.0	524.3
7.5°	602.5	602.8	600.1	599.3	594.2	590.6	583.1	574.9	567.7	558.5	551.6
10°	629.9	629.6	626.9	624.7	620.4	614.8	607.3	597.9	588.9	578.9	569.4
12.5°	645.8	645.2	644.4	641.7	637.7	632.7	626.5	617.1	606.1	595.2	584.0
15°	667.3	665.9	663.3	659.9	654.1	648.3	641.4	633.1	622.5	610.2	599.9
17.5°	693.9	693.9	689.9	685.2	677.3	667.2	656.4	643.0	628.6	615.1	604.1
20°	715.8	715.2	711.3	702.1	693.1	680.4	668.0	651.5	634.0	616.3	602.6
22.5°	747.3	745.8	741.7	729.6	715.7	699.3	680.4	660.3	639.1	619.1	601.0
25°	799.0	797.8	789.6	775.7	756.2	730.9	706.3	678.6	648.2	621.7	599.9
27.5°	834.3	833.0	826.9	815.4	797.4	770.8	737.4	700.4	662.5	626.0	594.5
30°	830.8	833.8	833.0	827.6	814.1	790.2	759.4	717.8	672.6	629.9	592.3
32.5°	780.8	783.5	790.5	801.1	801.8	792.3	769.2	730.8	684.1	635.4	590.5
35°	662.9	666.5	680.0	701.3	729.2	752.4	757.2	736.5	694.5	642.2	587.9
37.5°	509.6	529.2	540.6	563.0	605.1	647.9	689.1	704.2	686.4	639.4	583.7
40°	432.9	437.6	458.0	483.3	518.7	563.2	621.9	664.3	665.6	633.1	577.0
42.5°	370.5	376.6	390.5	410.7	441.0	485.5	546.1	602.1	627.9	615.5	568.2
45°	296.4	301.0	311.2	326.7	349.9	386.8	438.9	503.5	554.8	575.0	544.8
47.5°	243.5	246.0	254.8	266.7	283.9	310.6	351.0	407.2	468.7	511.9	507.6
50°	214.9	217.7	224.4	233.3	247.9	270.5	302.8	349.6	413.0	465.7	476.3
52.5°	192.6	194.9	199.1	207.6	219.6	236.9	263.0	305.3	362.4	418.4	442.9
55°	162.7	164.4	167.7	172.5	182.0	194.6	217.1	246.3	292.5	349.0	384.8
57.5°	138.2	139.0	141.1	145.5	152.1	161.3	177.5	202.2	235.4	286.3	325.8
60°	122.5	123.4	126.1	129.2	134.3	142.7	155.4	172.7	204.5	246.5	286.5
62.5°	110.1	110.6	111.8	114.8	119.3	125.8	135.8	149.9	175.2	212.2	249.9
65°	92.3	92.5	92.9	95.3	98.1	102.9	109.4	119.3	138.4	166.3	199.8
67.5°	75.2	75.5	76.9	77.7	80.6	83.1	87.0	94.5	108.1	126.8	152.8
70°	65.7	65.4	66.8	67.8	68.8	71.8	74.4	80.6	88.9	103.2	124.9
72.5°	56.7	56.2	56.8	57.2	58.5	60.5	63.1	66.9	73.4	83.2	99.8
75°	43.0	43.1	43.1	43.6	44.6	45.4	46.1	48.1	51.7	58.3	67.2
77.5°	30.1	29.9	30.7	30.8	31.4	32.3	33.0	33.8	35.2	37.9	42.5
80°	21.9	21.9	22.0	22.6	22.5	22.9	23.8	24.7	26.4	28.1	29.6
82.5°	16.8	16.6	16.8	17.0	16.9	17.3	17.7	17.8	18.5	19.3	20.4
85°	9.1	9.1	9.4	9.4	9.6	9.6	9.7	9.7	9.7	10.0	10.2
87.5°	6.5	6.3	6.1	6.0	6.0	6.3	5.9	5.7	5.5	5.4	5.3
90°	15.3	14.9	14.5	14.0	13.6	13.1	12.4	11.6	10.9	10.2	9.2
92.5°	30.1	29.9	29.5	29.3	28.9	28.3	27.4	26.4	25.5	24.5	23.3
95°	54.9	54.7	54.4	54.2	53.8	53.2	52.2	51.2	50.2	49.2	47.8
97.5°	83.3	83.2	83.0	82.8	82.7	82.1	81.2	80.2	79.3	78.4	76.4
100°	104.8	104.5	104.3	104.0	103.7	102.9	101.6	100.3	99.1	97.8	95.9
102.5°	126.3	125.9	125.5	125.1	124.7	123.8	122.4	121.1	119.7	118.2	117.3
105°	158.5	158.1	157.6	157.2	156.8	156.2	155.3	154.5	153.6	152.7	151.9
107.5°	191.5	191.5	191.6	191.6	191.6	191.4	191.0	190.5	190.1	189.7	189.1
110°	216.0	216.2	216.3	216.5	216.6	216.5	216.0	215.6	215.2	214.7	214.3



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.0	240.3	240.6	240.8	241.1	241.1	240.9	240.7	240.6	240.3	239.8
115°	278.0	278.2	278.4	278.4	278.6	278.7	278.9	279.1	279.1	279.3	279.1
117.5°	315.1	315.6	316.2	316.8	317.4	317.6	317.5	317.4	317.3	317.2	316.9
120°	340.7	341.2	341.8	342.4	342.9	343.2	343.2	343.2	343.2	343.2	343.1
122.5°	366.3	366.7	367.1	367.6	368.1	368.3	368.4	368.6	368.7	368.8	368.4
125°	404.6	404.8	404.8	405.0	405.2	405.4	405.6	406.0	406.2	406.5	406.4
127.5°	441.4	441.7	442.0	442.3	442.6	442.7	442.9	443.1	443.2	443.3	443.2
130°	466.0	466.2	466.5	466.8	467.1	467.3	467.4	467.6	467.7	467.9	467.6
132.5°	489.0	489.4	489.7	490.2	490.5	490.9	490.9	491.1	491.3	491.4	491.5
135°	524.8	525.3	525.9	526.4	527.0	527.3	527.3	527.3	527.3	527.3	527.2
137.5°	559.7	560.5	561.2	561.9	562.6	562.9	562.7	562.6	562.4	562.2	561.9
140°	582.3	583.0	583.7	584.4	585.1	585.3	585.0	584.8	584.4	584.2	583.8
142.5°	603.7	604.4	605.2	605.9	606.6	606.8	606.7	606.5	606.3	606.1	605.6
145°	635.9	636.4	636.8	637.2	637.7	637.9	637.9	637.9	637.9	637.9	637.5
147.5°	663.5	664.4	665.4	666.3	667.3	667.6	667.3	666.9	666.6	666.2	665.9
150°	683.9	684.2	684.5	684.8	685.0	685.2	685.2	685.2	685.2	685.2	684.6
152.5°	700.8	701.3	701.8	702.3	702.8	702.9	702.6	702.2	701.9	701.5	701.3
155°	724.8	725.5	726.3	726.9	727.6	727.7	727.1	726.6	726.0	725.5	725.3
157.5°	744.9	745.8	746.7	747.7	748.6	748.8	748.2	747.7	747.1	746.6	746.4
160°	758.7	759.4	760.1	760.8	761.6	761.6	761.0	760.4	759.9	759.3	759.1
162.5°	770.4	771.3	772.1	772.9	773.8	773.8	773.1	772.5	771.8	771.1	771.0
165°	786.2	787.0	787.9	788.8	789.5	789.7	789.2	788.6	788.0	787.5	787.3
167.5°	798.7	799.6	800.5	801.3	802.2	802.2	801.4	800.6	799.7	798.8	798.8
170°	805.4	806.3	807.4	808.3	809.3	809.4	808.6	807.7	806.8	806.0	806.0
172.5°	811.0	811.8	812.7	813.6	814.5	814.5	813.6	812.8	811.9	811.1	811.1
175°	816.2	817.2	818.2	819.2	820.2	820.3	819.4	818.6	817.7	816.8	816.8
177.5°	819.2	820.1	820.9	821.7	822.4	822.5	821.8	821.1	820.4	819.8	819.9
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	498.0	496.9	494.8	492.9	490.5	488.4	487.0	485.3	483.0	480.4	478.1
5°	520.0	515.7	509.9	504.9	498.5	493.6	488.4	483.5	478.5	472.1	466.5
7.5°	544.5	535.5	526.7	515.6	505.6	496.6	488.0	479.3	470.8	461.8	453.1
10°	559.5	548.5	536.4	522.5	509.7	497.6	486.5	475.4	463.9	453.8	442.9
12.5°	573.4	559.3	545.4	527.9	512.6	497.7	483.5	469.9	457.6	444.4	432.7
15°	586.1	572.1	556.6	535.2	513.8	495.9	479.2	461.6	446.3	431.5	418.4
17.5°	591.0	576.4	558.4	537.7	514.4	491.9	470.4	451.0	432.9	415.8	401.1
20°	589.1	575.0	556.5	536.7	511.9	488.4	465.1	443.7	423.5	405.4	389.8
22.5°	584.4	569.9	552.0	531.2	507.6	482.7	457.8	434.9	413.9	395.1	378.0
25°	577.6	557.7	539.3	519.0	496.5	471.9	446.3	420.9	398.5	379.4	360.7
27.5°	570.3	545.5	522.2	502.0	478.3	456.3	431.5	405.6	382.0	362.6	343.4
30°	563.8	536.0	510.3	487.4	464.9	444.0	420.6	395.3	371.0	350.9	331.5
32.5°	555.7	526.1	497.9	471.5	449.8	429.1	407.9	383.7	360.1	339.3	319.5
35°	545.5	507.7	477.1	449.0	425.0	404.8	385.7	366.3	342.6	321.1	301.8
37.5°	532.2	489.2	453.8	423.3	397.9	377.7	362.6	344.7	323.1	302.6	284.7
40°	524.0	475.9	437.1	406.8	380.2	358.9	344.7	329.7	310.0	290.7	272.8
42.5°	513.2	463.6	420.3	388.7	361.9	341.4	327.1	313.9	297.4	279.2	260.0
45°	492.0	439.9	394.3	360.5	333.5	313.3	300.0	288.3	275.8	259.0	242.3
47.5°	464.4	415.1	367.4	330.5	304.0	285.3	272.4	263.1	254.2	240.0	223.8
50°	442.3	394.7	348.2	312.4	284.1	266.4	254.3	246.9	238.8	225.8	212.2
52.5°	416.1	373.7	328.1	291.5	264.8	248.2	236.6	229.2	222.5	212.0	199.1
55°	375.1	337.8	296.0	262.8	238.3	221.6	210.5	203.5	199.6	190.6	180.5
57.5°	327.5	300.9	264.1	232.0	210.3	193.9	185.7	179.8	175.3	168.9	161.8
60°	294.5	275.8	242.7	212.2	192.3	176.7	169.3	164.4	160.1	154.8	149.2
62.5°	260.9	247.3	218.5	192.3	174.1	160.9	154.0	149.6	144.7	141.1	135.7
65°	215.9	203.7	183.8	163.3	146.5	135.9	130.9	126.9	124.0	119.9	116.1
67.5°	167.9	163.0	149.2	135.1	123.0	113.6	109.3	106.5	103.0	100.6	98.0
70°	138.4	136.0	126.3	117.0	105.6	99.3	95.3	94.1	89.7	87.3	85.6
72.5°	112.4	111.2	105.6	99.2	91.2	85.6	82.0	80.6	77.7	75.9	74.7
75°	77.0	77.4	76.4	72.2	69.2	65.7	62.5	61.6	59.7	58.1	57.1
77.5°	48.7	50.7	50.8	50.6	49.4	47.3	45.9	45.3	43.4	42.8	42.5
80°	33.4	35.6	37.6	37.4	37.0	36.4	35.4	34.8	33.8	33.2	32.8
82.5°	22.3	24.3	26.0	27.0	26.9	26.3	25.7	25.4	25.2	24.8	24.7
85°	10.5	10.9	11.5	12.9	13.9	14.1	13.9	13.7	13.2	13.3	13.5
87.5°	5.3	5.1	5.1	4.8	4.5	5.1	5.3	5.3	5.2	5.1	4.9
90°	8.3	7.2	6.3	5.2	4.0	2.9	1.8	0.6	1.8	2.9	4.0
92.5°	22.1	20.9	19.6	18.7	17.8	17.0	16.3	15.5	16.3	17.0	17.8
95°	46.4	44.9	43.6	42.7	42.4	42.1	41.8	41.6	41.8	42.1	42.4
97.5°	74.5	72.5	70.5	69.5	69.4	69.2	69.1	69.1	69.1	69.2	69.4
100°	94.1	92.2	90.4	89.5	89.5	89.5	89.5	89.5	89.5	89.5	89.5
102.5°	116.4	115.5	114.5	113.7	113.1	112.6	112.0	111.5	112.0	112.6	113.1
105°	151.0	150.2	149.4	148.6	147.8	147.1	146.5	145.8	146.5	147.1	147.8
107.5°	188.4	187.8	187.1	186.4	185.7	185.0	184.3	183.6	184.3	185.0	185.7
110°	213.9	213.4	213.0	212.5	211.8	211.0	210.3	209.7	210.3	211.0	211.8



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	239.3	238.7	238.2	237.7	237.4	236.9	236.6	236.3	236.6	236.9	237.4
115°	278.7	278.4	278.2	277.8	277.2	276.6	276.0	275.5	276.0	276.6	277.2
117.5°	316.7	316.4	316.2	315.9	315.6	315.4	315.1	314.9	315.1	315.4	315.6
120°	342.9	342.8	342.7	342.2	341.6	340.8	340.1	339.4	340.1	340.8	341.6
122.5°	368.1	367.6	367.3	367.0	366.8	366.5	366.3	366.0	366.3	366.5	366.8
125°	406.2	406.0	406.0	405.4	404.6	403.7	402.9	402.0	402.9	403.7	404.6
127.5°	443.0	442.8	442.6	442.3	441.9	441.3	440.8	440.4	440.8	441.3	441.9
130°	467.3	467.0	466.7	466.2	465.5	464.9	464.1	463.4	464.1	464.9	465.5
132.5°	491.5	491.5	491.6	491.0	489.9	488.7	487.6	486.4	487.6	488.7	489.9
135°	527.0	526.8	526.8	526.2	525.4	524.5	523.7	522.8	523.7	524.5	525.4
137.5°	561.5	561.3	560.9	560.4	559.6	558.7	557.9	557.1	557.9	558.7	559.6
140°	583.3	582.9	582.5	581.9	581.2	580.5	579.8	579.1	579.8	580.5	581.2
142.5°	605.1	604.6	604.0	603.5	602.9	602.3	601.7	601.1	601.7	602.3	602.9
145°	637.1	636.6	636.2	635.7	635.1	634.6	634.0	633.4	634.0	634.6	635.1
147.5°	665.6	665.2	664.9	664.6	664.3	663.9	663.7	663.3	663.7	663.9	664.3
150°	684.1	683.5	682.9	682.7	682.9	682.9	683.1	683.3	683.1	682.9	682.9
152.5°	701.1	700.9	700.6	700.4	700.3	700.0	699.8	699.6	699.8	700.0	700.3
155°	725.1	725.0	724.9	724.8	724.8	724.8	724.8	724.8	724.8	724.8	724.8
157.5°	746.2	746.1	746.0	746.1	746.4	746.7	747.0	747.3	747.0	746.7	746.4
160°	759.1	758.9	758.7	758.9	759.3	759.7	760.2	760.6	760.2	759.7	759.3
162.5°	771.0	771.0	770.9	771.1	771.5	771.7	772.1	772.4	772.1	771.7	771.5
165°	787.1	787.0	786.9	787.0	787.2	787.6	787.8	788.1	787.8	787.6	787.2
167.5°	798.8	798.8	798.8	799.1	799.7	800.2	800.8	801.4	800.8	800.2	799.7
170°	806.0	806.0	806.0	806.2	806.8	807.4	808.0	808.6	808.0	807.4	806.8
172.5°	811.1	811.1	811.1	811.4	811.9	812.5	813.0	813.6	813.0	812.5	811.9
175°	816.8	816.8	816.8	817.1	817.7	818.3	818.8	819.4	818.8	818.3	817.7
177.5°	820.0	820.1	820.3	820.5	821.0	821.4	821.9	822.3	821.9	821.4	821.0
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	476.5	474.3	472.7	469.5	467.3	466.3	464.6	464.1	465.9	464.6	464.4
5°	462.4	456.6	452.0	447.5	442.5	439.3	434.5	433.7	432.5	430.8	430.3
7.5°	445.4	437.8	432.0	424.4	417.8	412.5	406.6	403.7	402.2	399.8	396.7
10°	433.9	425.0	417.0	409.4	401.3	394.7	388.7	384.2	381.2	378.4	377.2
12.5°	422.6	413.5	403.3	394.2	385.0	377.7	371.1	368.1	364.8	361.5	358.8
15°	405.0	393.0	381.8	371.3	363.5	355.5	349.1	344.7	339.8	338.4	333.0
17.5°	386.4	374.5	361.4	350.4	341.4	332.6	325.6	320.6	316.9	311.8	309.4
20°	374.8	360.7	347.9	337.8	327.9	317.5	310.4	306.2	302.6	298.4	296.4
22.5°	362.4	348.6	335.5	323.6	313.6	303.3	298.3	293.9	289.9	286.0	283.4
25°	344.1	330.3	316.5	304.2	293.7	286.3	280.3	275.3	273.2	269.4	266.6
27.5°	326.1	311.3	297.1	284.8	276.6	269.2	264.3	260.5	256.5	253.2	250.7
30°	314.5	299.5	283.9	274.1	265.4	258.5	253.0	249.3	246.3	243.3	241.5
32.5°	302.9	287.3	273.5	263.0	254.8	248.7	243.2	239.5	236.4	233.2	231.0
35°	284.3	268.4	257.3	246.9	238.8	233.2	229.4	224.2	221.6	219.2	217.1
37.5°	267.0	252.2	240.1	231.1	223.9	218.4	213.5	210.8	207.6	205.4	203.6
40°	254.3	240.7	229.8	220.2	215.1	208.9	204.3	200.7	198.4	195.5	193.6
42.5°	242.8	230.2	219.6	211.0	204.6	199.3	194.9	191.3	188.3	186.3	184.7
45°	226.6	214.0	203.7	195.8	189.8	184.9	180.2	178.5	174.4	172.1	171.3
47.5°	209.8	198.6	188.6	181.3	175.2	170.5	166.2	162.6	160.3	158.0	156.7
50°	198.5	187.8	178.5	171.3	165.3	160.1	156.2	153.8	150.8	148.6	147.1
52.5°	187.3	177.3	168.0	161.1	155.9	150.8	146.3	144.0	141.1	139.7	138.6
55°	171.1	160.6	152.6	145.9	140.4	135.7	131.5	129.2	127.3	126.0	125.5
57.5°	152.8	144.5	137.1	131.0	125.4	120.9	117.2	114.9	113.4	113.1	111.9
60°	140.9	133.3	126.6	119.9	115.2	111.0	107.8	105.2	103.7	103.5	103.1
62.5°	128.9	121.7	115.4	109.6	105.3	101.3	98.2	95.4	94.5	93.4	92.6
65°	111.2	104.6	99.4	94.9	90.3	87.0	83.9	82.1	80.0	78.8	76.6
67.5°	93.8	88.8	83.8	79.9	76.3	73.1	70.6	67.9	66.5	65.5	64.0
70°	82.4	78.4	73.4	69.2	66.5	63.9	61.9	58.9	57.9	57.1	56.3
72.5°	71.5	68.0	63.9	60.4	57.7	55.3	53.0	51.6	50.5	49.8	49.3
75°	56.3	53.0	49.3	46.9	44.9	43.0	41.8	40.8	40.4	40.2	39.4
77.5°	41.3	39.5	36.7	34.8	33.5	32.6	31.6	31.1	31.0	30.1	29.9
80°	31.6	30.7	28.2	27.5	26.4	25.7	25.1	24.1	23.1	22.6	22.0
82.5°	23.5	22.6	21.5	20.3	19.5	18.9	18.4	18.0	18.2	17.6	17.3
85°	12.6	11.5	11.1	10.9	10.5	10.9	10.8	10.5	10.3	10.2	10.3
87.5°	5.0	5.3	5.3	5.8	5.5	5.9	6.0	6.0	6.1	6.3	6.2
90°	5.2	6.3	7.2	8.3	9.2	10.2	10.9	11.6	12.4	13.1	13.6
92.5°	18.7	19.6	20.9	22.1	23.3	24.5	25.5	26.4	27.4	28.3	28.9
95°	42.7	43.6	44.9	46.4	47.8	49.2	50.2	51.2	52.2	53.2	53.8
97.5°	69.5	70.5	72.5	74.5	76.4	78.4	79.3	80.2	81.2	82.1	82.7
100°	89.5	90.4	92.2	94.1	95.9	97.8	99.1	100.3	101.6	102.9	103.7
102.5°	113.7	114.5	115.5	116.4	117.3	118.2	119.7	121.1	122.4	123.8	124.7
105°	148.6	149.4	150.2	151.0	151.9	152.7	153.6	154.5	155.3	156.2	156.8
107.5°	186.4	187.1	187.8	188.4	189.1	189.7	190.1	190.5	191.0	191.4	191.6
110°	212.5	213.0	213.4	213.9	214.3	214.7	215.2	215.6	216.0	216.5	216.6



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.7	238.2	238.7	239.3	239.8	240.3	240.6	240.7	240.9	241.1	241.1
115°	277.8	278.2	278.4	278.7	279.1	279.3	279.1	279.1	278.9	278.7	278.6
117.5°	315.9	316.2	316.4	316.7	316.9	317.2	317.3	317.4	317.5	317.6	317.4
120°	342.2	342.7	342.8	342.9	343.1	343.2	343.2	343.2	343.2	343.2	342.9
122.5°	367.0	367.3	367.6	368.1	368.4	368.8	368.7	368.6	368.4	368.3	368.1
125°	405.4	406.0	406.0	406.2	406.4	406.5	406.2	406.0	405.6	405.4	405.2
127.5°	442.3	442.6	442.8	443.0	443.2	443.3	443.2	443.1	442.9	442.7	442.6
130°	466.2	466.7	467.0	467.3	467.6	467.9	467.7	467.6	467.4	467.3	467.1
132.5°	491.0	491.6	491.5	491.5	491.5	491.4	491.3	491.1	490.9	490.9	490.5
135°	526.2	526.8	526.8	527.0	527.2	527.3	527.3	527.3	527.3	527.3	527.0
137.5°	560.4	560.9	561.3	561.5	561.9	562.2	562.4	562.6	562.7	562.9	562.6
140°	581.9	582.5	582.9	583.3	583.8	584.2	584.4	584.8	585.0	585.3	585.1
142.5°	603.5	604.0	604.6	605.1	605.6	606.1	606.3	606.5	606.7	606.8	606.6
145°	635.7	636.2	636.6	637.1	637.5	637.9	637.9	637.9	637.9	637.9	637.7
147.5°	664.6	664.9	665.2	665.6	665.9	666.2	666.6	666.9	667.3	667.6	667.3
150°	682.7	682.9	683.5	684.1	684.6	685.2	685.2	685.2	685.2	685.2	685.0
152.5°	700.4	700.6	700.9	701.1	701.3	701.5	701.9	702.2	702.6	702.9	702.8
155°	724.8	724.9	725.0	725.1	725.3	725.5	726.0	726.6	727.1	727.7	727.6
157.5°	746.1	746.0	746.1	746.2	746.4	746.6	747.1	747.7	748.2	748.8	748.6
160°	758.9	758.7	758.9	759.1	759.1	759.3	759.9	760.4	761.0	761.6	761.6
162.5°	771.1	770.9	771.0	771.0	771.0	771.1	771.8	772.5	773.1	773.8	773.8
165°	787.0	786.9	787.0	787.1	787.3	787.5	788.0	788.6	789.2	789.7	789.5
167.5°	799.1	798.8	798.8	798.8	798.8	798.8	799.7	800.6	801.4	802.2	802.2
170°	806.2	806.0	806.0	806.0	806.0	806.0	806.8	807.7	808.6	809.4	809.3
172.5°	811.4	811.1	811.1	811.1	811.1	811.1	811.9	812.8	813.6	814.5	814.5
175°	817.1	816.8	816.8	816.8	816.8	816.8	817.7	818.6	819.4	820.3	820.2
177.5°	820.5	820.3	820.1	820.0	819.9	819.8	820.4	821.1	821.8	822.5	822.4
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	464.3	462.5	462.0	462.7	462.0	462.5	464.3	464.4	464.6	465.9	464.1
5°	428.3	426.4	427.3	427.0	427.3	426.4	428.3	430.3	430.8	432.5	433.7
7.5°	396.7	394.3	391.7	392.4	391.7	394.3	396.7	396.7	399.8	402.2	403.7
10°	374.6	372.6	371.4	372.5	371.4	372.6	374.6	377.2	378.4	381.2	384.2
12.5°	356.0	354.8	353.8	353.4	353.8	354.8	356.0	358.8	361.5	364.8	368.1
15°	330.6	328.3	327.3	324.7	327.3	328.3	330.6	333.0	338.4	339.8	344.7
17.5°	307.3	306.5	303.9	302.8	303.9	306.5	307.3	309.4	311.8	316.9	320.6
20°	293.4	292.7	290.1	291.6	290.1	292.7	293.4	296.4	298.4	302.6	306.2
22.5°	282.0	280.3	279.4	279.0	279.4	280.3	282.0	283.4	286.0	289.9	293.9
25°	265.8	263.2	262.2	261.1	262.2	263.2	265.8	266.6	269.4	273.2	275.3
27.5°	249.6	248.2	246.9	246.6	246.9	248.2	249.6	250.7	253.2	256.5	260.5
30°	239.1	237.7	236.8	236.8	236.8	237.7	239.1	241.5	243.3	246.3	249.3
32.5°	229.7	228.7	227.6	227.5	227.6	228.7	229.7	231.0	233.2	236.4	239.5
35°	216.0	214.5	214.0	212.8	214.0	214.5	216.0	217.1	219.2	221.6	224.2
37.5°	201.8	200.5	200.5	200.4	200.5	200.5	201.8	203.6	205.4	207.6	210.8
40°	192.8	191.7	191.6	190.2	191.6	191.7	192.8	193.6	195.5	198.4	200.7
42.5°	183.0	182.5	181.8	181.2	181.8	182.5	183.0	184.7	186.3	188.3	191.3
45°	169.9	168.5	168.5	167.6	168.5	168.5	169.9	171.3	172.1	174.4	178.5
47.5°	156.3	155.2	155.3	154.3	155.3	155.2	156.3	156.7	158.0	160.3	162.6
50°	147.2	146.6	146.5	146.0	146.5	146.6	147.2	147.1	148.6	150.8	153.8
52.5°	138.2	137.8	138.6	137.8	138.6	137.8	138.2	138.6	139.7	141.1	144.0
55°	126.0	125.4	126.6	125.4	126.6	125.4	126.0	125.5	126.0	127.3	129.2
57.5°	111.9	111.3	112.4	111.8	112.4	111.3	111.9	111.9	113.1	113.4	114.9
60°	102.6	101.4	102.0	102.3	102.0	101.4	102.6	103.1	103.5	103.7	105.2
62.5°	91.7	90.9	91.4	90.5	91.4	90.9	91.7	92.6	93.4	94.5	95.4
65°	76.2	75.6	74.8	74.4	74.8	75.6	76.2	76.6	78.8	80.0	82.1
67.5°	64.1	62.6	62.5	62.9	62.5	62.6	64.1	64.0	65.5	66.5	67.9
70°	55.1	55.1	54.9	54.9	54.9	55.1	55.1	56.3	57.1	57.9	58.9
72.5°	48.9	48.7	48.4	48.2	48.4	48.7	48.9	49.3	49.8	50.5	51.6
75°	39.4	39.6	39.2	39.0	39.2	39.6	39.4	39.4	40.2	40.4	40.8
77.5°	29.1	28.2	28.7	28.2	28.7	28.2	29.1	29.9	30.1	31.0	31.1
80°	22.0	21.9	22.5	21.9	22.5	21.9	22.0	22.0	22.6	23.1	24.1
82.5°	17.5	17.3	17.6	17.1	17.6	17.3	17.5	17.3	17.6	18.2	18.0
85°	10.5	10.3	10.2	10.3	10.2	10.3	10.5	10.3	10.2	10.3	10.5
87.5°	6.5	6.4	6.5	6.5	6.5	6.4	6.5	6.2	6.3	6.1	6.0
90°	14.0	14.5	14.9	15.3	14.9	14.5	14.0	13.6	13.1	12.4	11.6
92.5°	29.3	29.5	29.9	30.1	29.9	29.5	29.3	28.9	28.3	27.4	26.4
95°	54.2	54.4	54.7	54.9	54.7	54.4	54.2	53.8	53.2	52.2	51.2
97.5°	82.8	83.0	83.2	83.3	83.2	83.0	82.8	82.7	82.1	81.2	80.2
100°	104.0	104.3	104.5	104.8	104.5	104.3	104.0	103.7	102.9	101.6	100.3
102.5°	125.1	125.5	125.9	126.3	125.9	125.5	125.1	124.7	123.8	122.4	121.1
105°	157.2	157.6	158.1	158.5	158.1	157.6	157.2	156.8	156.2	155.3	154.5
107.5°	191.6	191.6	191.5	191.5	191.5	191.6	191.6	191.6	191.4	191.0	190.5
110°	216.5	216.3	216.2	216.0	216.2	216.3	216.5	216.6	216.5	216.0	215.6



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	240.8	240.6	240.3	240.0	240.3	240.6	240.8	241.1	241.1	240.9	240.7
115°	278.4	278.4	278.2	278.0	278.2	278.4	278.4	278.6	278.7	278.9	279.1
117.5°	316.8	316.2	315.6	315.1	315.6	316.2	316.8	317.4	317.6	317.5	317.4
120°	342.4	341.8	341.2	340.7	341.2	341.8	342.4	342.9	343.2	343.2	343.2
122.5°	367.6	367.1	366.7	366.3	366.7	367.1	367.6	368.1	368.3	368.4	368.6
125°	405.0	404.8	404.8	404.6	404.8	404.8	405.0	405.2	405.4	405.6	406.0
127.5°	442.3	442.0	441.7	441.4	441.7	442.0	442.3	442.6	442.7	442.9	443.1
130°	466.8	466.5	466.2	466.0	466.2	466.5	466.8	467.1	467.3	467.4	467.6
132.5°	490.2	489.7	489.4	489.0	489.4	489.7	490.2	490.5	490.9	490.9	491.1
135°	526.4	525.9	525.3	524.8	525.3	525.9	526.4	527.0	527.3	527.3	527.3
137.5°	561.9	561.2	560.5	559.7	560.5	561.2	561.9	562.6	562.9	562.7	562.6
140°	584.4	583.7	583.0	582.3	583.0	583.7	584.4	585.1	585.3	585.0	584.8
142.5°	605.9	605.2	604.4	603.7	604.4	605.2	605.9	606.6	606.8	606.7	606.5
145°	637.2	636.8	636.4	635.9	636.4	636.8	637.2	637.7	637.9	637.9	637.9
147.5°	666.3	665.4	664.4	663.5	664.4	665.4	666.3	667.3	667.6	667.3	666.9
150°	684.8	684.5	684.2	683.9	684.2	684.5	684.8	685.0	685.2	685.2	685.2
152.5°	702.3	701.8	701.3	700.8	701.3	701.8	702.3	702.8	702.9	702.6	702.2
155°	726.9	726.3	725.5	724.8	725.5	726.3	726.9	727.6	727.7	727.1	726.6
157.5°	747.7	746.7	745.8	744.9	745.8	746.7	747.7	748.6	748.8	748.2	747.7
160°	760.8	760.1	759.4	758.7	759.4	760.1	760.8	761.6	761.6	761.0	760.4
162.5°	772.9	772.1	771.3	770.4	771.3	772.1	772.9	773.8	773.8	773.1	772.5
165°	788.8	787.9	787.0	786.2	787.0	787.9	788.8	789.5	789.7	789.2	788.6
167.5°	801.3	800.5	799.6	798.7	799.6	800.5	801.3	802.2	802.2	801.4	800.6
170°	808.3	807.4	806.3	805.4	806.3	807.4	808.3	809.3	809.4	808.6	807.7
172.5°	813.6	812.7	811.8	811.0	811.8	812.7	813.6	814.5	814.5	813.6	812.8
175°	819.2	818.2	817.2	816.2	817.2	818.2	819.2	820.2	820.3	819.4	818.6
177.5°	821.7	820.9	820.1	819.2	820.1	820.9	821.7	822.4	822.5	821.8	821.1
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	464.6	466.3	467.3	469.5	472.7	474.3	476.5	478.1	480.4	483.0	485.3
5°	434.5	439.3	442.5	447.5	452.0	456.6	462.4	466.5	472.1	478.5	483.5
7.5°	406.6	412.5	417.8	424.4	432.0	437.8	445.4	453.1	461.8	470.8	479.3
10°	388.7	394.7	401.3	409.4	417.0	425.0	433.9	442.9	453.8	463.9	475.4
12.5°	371.1	377.7	385.0	394.2	403.3	413.5	422.6	432.7	444.4	457.6	469.9
15°	349.1	355.5	363.5	371.3	381.8	393.0	405.0	418.4	431.5	446.3	461.6
17.5°	325.6	332.6	341.4	350.4	361.4	374.5	386.4	401.1	415.8	432.9	451.0
20°	310.4	317.5	327.9	337.8	347.9	360.7	374.8	389.8	405.4	423.5	443.7
22.5°	298.3	303.3	313.6	323.6	335.5	348.6	362.4	378.0	395.1	413.9	434.9
25°	280.3	286.3	293.7	304.2	316.5	330.3	344.1	360.7	379.4	398.5	420.9
27.5°	264.3	269.2	276.6	284.8	297.1	311.3	326.1	343.4	362.6	382.0	405.6
30°	253.0	258.5	265.4	274.1	283.9	299.5	314.5	331.5	350.9	371.0	395.3
32.5°	243.2	248.7	254.8	263.0	273.5	287.3	302.9	319.5	339.3	360.1	383.7
35°	229.4	233.2	238.8	246.9	257.3	268.4	284.3	301.8	321.1	342.6	366.3
37.5°	213.5	218.4	223.9	231.1	240.1	252.2	267.0	284.7	302.6	323.1	344.7
40°	204.3	208.9	215.1	220.2	229.8	240.7	254.3	272.8	290.7	310.0	329.7
42.5°	194.9	199.3	204.6	211.0	219.6	230.2	242.8	260.0	279.2	297.4	313.9
45°	180.2	184.9	189.8	195.8	203.7	214.0	226.6	242.3	259.0	275.8	288.3
47.5°	166.2	170.5	175.2	181.3	188.6	198.6	209.8	223.8	240.0	254.2	263.1
50°	156.2	160.1	165.3	171.3	178.5	187.8	198.5	212.2	225.8	238.8	246.9
52.5°	146.3	150.8	155.9	161.1	168.0	177.3	187.3	199.1	212.0	222.5	229.2
55°	131.5	135.7	140.4	145.9	152.6	160.6	171.1	180.5	190.6	199.6	203.5
57.5°	117.2	120.9	125.4	131.0	137.1	144.5	152.8	161.8	168.9	175.3	179.8
60°	107.8	111.0	115.2	119.9	126.6	133.3	140.9	149.2	154.8	160.1	164.4
62.5°	98.2	101.3	105.3	109.6	115.4	121.7	128.9	135.7	141.1	144.7	149.6
65°	83.9	87.0	90.3	94.9	99.4	104.6	111.2	116.1	119.9	124.0	126.9
67.5°	70.6	73.1	76.3	79.9	83.8	88.8	93.8	98.0	100.6	103.0	106.5
70°	61.9	63.9	66.5	69.2	73.4	78.4	82.4	85.6	87.3	89.7	94.1
72.5°	53.0	55.3	57.7	60.4	63.9	68.0	71.5	74.7	75.9	77.7	80.6
75°	41.8	43.0	44.9	46.9	49.3	53.0	56.3	57.1	58.1	59.7	61.6
77.5°	31.6	32.6	33.5	34.8	36.7	39.5	41.3	42.5	42.8	43.4	45.3
80°	25.1	25.7	26.4	27.5	28.2	30.7	31.6	32.8	33.2	33.8	34.8
82.5°	18.4	18.9	19.5	20.3	21.5	22.6	23.5	24.7	24.8	25.2	25.4
85°	10.8	10.9	10.5	10.9	11.1	11.5	12.6	13.5	13.3	13.2	13.7
87.5°	6.0	5.9	5.5	5.8	5.3	5.3	5.0	4.9	5.1	5.2	5.3
90°	10.9	10.2	9.2	8.3	7.2	6.3	5.2	4.0	2.9	1.8	0.6
92.5°	25.5	24.5	23.3	22.1	20.9	19.6	18.7	17.8	17.0	16.3	15.5
95°	50.2	49.2	47.8	46.4	44.9	43.6	42.7	42.4	42.1	41.8	41.6
97.5°	79.3	78.4	76.4	74.5	72.5	70.5	69.5	69.4	69.2	69.1	69.1
100°	99.1	97.8	95.9	94.1	92.2	90.4	89.5	89.5	89.5	89.5	89.5
102.5°	119.7	118.2	117.3	116.4	115.5	114.5	113.7	113.1	112.6	112.0	111.5
105°	153.6	152.7	151.9	151.0	150.2	149.4	148.6	147.8	147.1	146.5	145.8
107.5°	190.1	189.7	189.1	188.4	187.8	187.1	186.4	185.7	185.0	184.3	183.6
110°	215.2	214.7	214.3	213.9	213.4	213.0	212.5	211.8	211.0	210.3	209.7



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	240.6	240.3	239.8	239.3	238.7	238.2	237.7	237.4	236.9	236.6	236.3
115°	279.1	279.3	279.1	278.7	278.4	278.2	277.8	277.2	276.6	276.0	275.5
117.5°	317.3	317.2	316.9	316.7	316.4	316.2	315.9	315.6	315.4	315.1	314.9
120°	343.2	343.2	343.1	342.9	342.8	342.7	342.2	341.6	340.8	340.1	339.4
122.5°	368.7	368.8	368.4	368.1	367.6	367.3	367.0	366.8	366.5	366.3	366.0
125°	406.2	406.5	406.4	406.2	406.0	406.0	405.4	404.6	403.7	402.9	402.0
127.5°	443.2	443.3	443.2	443.0	442.8	442.6	442.3	441.9	441.3	440.8	440.4
130°	467.7	467.9	467.6	467.3	467.0	466.7	466.2	465.5	464.9	464.1	463.4
132.5°	491.3	491.4	491.5	491.5	491.5	491.6	491.0	489.9	488.7	487.6	486.4
135°	527.3	527.3	527.2	527.0	526.8	526.8	526.2	525.4	524.5	523.7	522.8
137.5°	562.4	562.2	561.9	561.5	561.3	560.9	560.4	559.6	558.7	557.9	557.1
140°	584.4	584.2	583.8	583.3	582.9	582.5	581.9	581.2	580.5	579.8	579.1
142.5°	606.3	606.1	605.6	605.1	604.6	604.0	603.5	602.9	602.3	601.7	601.1
145°	637.9	637.9	637.5	637.1	636.6	636.2	635.7	635.1	634.6	634.0	633.4
147.5°	666.6	666.2	665.9	665.6	665.2	664.9	664.6	664.3	663.9	663.7	663.3
150°	685.2	685.2	684.6	684.1	683.5	682.9	682.7	682.9	682.9	683.1	683.3
152.5°	701.9	701.5	701.3	701.1	700.9	700.6	700.4	700.3	700.0	699.8	699.6
155°	726.0	725.5	725.3	725.1	725.0	724.9	724.8	724.8	724.8	724.8	724.8
157.5°	747.1	746.6	746.4	746.2	746.1	746.0	746.1	746.4	746.7	747.0	747.3
160°	759.9	759.3	759.1	759.1	758.9	758.7	758.9	759.3	759.7	760.2	760.6
162.5°	771.8	771.1	771.0	771.0	771.0	770.9	771.1	771.5	771.7	772.1	772.4
165°	788.0	787.5	787.3	787.1	787.0	786.9	787.0	787.2	787.6	787.8	788.1
167.5°	799.7	798.8	798.8	798.8	798.8	798.8	799.1	799.7	800.2	800.8	801.4
170°	806.8	806.0	806.0	806.0	806.0	806.0	806.2	806.8	807.4	808.0	808.6
172.5°	811.9	811.1	811.1	811.1	811.1	811.1	811.4	811.9	812.5	813.0	813.6
175°	817.7	816.8	816.8	816.8	816.8	816.8	817.1	817.7	818.3	818.8	819.4
177.5°	820.4	819.8	819.9	820.0	820.1	820.3	820.5	821.0	821.4	821.9	822.3
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	487.0	488.4	490.5	492.9	494.8	496.9	498.0	498.0	498.9	501.0	503.8
5°	488.4	493.6	498.5	504.9	509.9	515.7	520.0	524.3	528.0	532.8	537.8
7.5°	488.0	496.6	505.6	515.6	526.7	535.5	544.5	551.6	558.5	567.7	574.9
10°	486.5	497.6	509.7	522.5	536.4	548.5	559.5	569.4	578.9	588.9	597.9
12.5°	483.5	497.7	512.6	527.9	545.4	559.3	573.4	584.0	595.2	606.1	617.1
15°	479.2	495.9	513.8	535.2	556.6	572.1	586.1	599.9	610.2	622.5	633.1
17.5°	470.4	491.9	514.4	537.7	558.4	576.4	591.0	604.1	615.1	628.6	643.0
20°	465.1	488.4	511.9	536.7	556.5	575.0	589.1	602.6	616.3	634.0	651.5
22.5°	457.8	482.7	507.6	531.2	552.0	569.9	584.4	601.0	619.1	639.1	660.3
25°	446.3	471.9	496.5	519.0	539.3	557.7	577.6	599.9	621.7	648.2	678.6
27.5°	431.5	456.3	478.3	502.0	522.2	545.5	570.3	594.5	626.0	662.5	700.4
30°	420.6	444.0	464.9	487.4	510.3	536.0	563.8	592.3	629.9	672.6	717.8
32.5°	407.9	429.1	449.8	471.5	497.9	526.1	555.7	590.5	635.4	684.1	730.8
35°	385.7	404.8	425.0	449.0	477.1	507.7	545.5	587.9	642.2	694.5	736.5
37.5°	362.6	377.7	397.9	423.3	453.8	489.2	532.2	583.7	639.4	686.4	704.2
40°	344.7	358.9	380.2	406.8	437.1	475.9	524.0	577.0	633.1	665.6	664.3
42.5°	327.1	341.4	361.9	388.7	420.3	463.6	513.2	568.2	615.5	627.9	602.1
45°	300.0	313.3	333.5	360.5	394.3	439.9	492.0	544.8	575.0	554.8	503.5
47.5°	272.4	285.3	304.0	330.5	367.4	415.1	464.4	507.6	511.9	468.7	407.2
50°	254.3	266.4	284.1	312.4	348.2	394.7	442.3	476.3	465.7	413.0	349.6
52.5°	236.6	248.2	264.8	291.5	328.1	373.7	416.1	442.9	418.4	362.4	305.3
55°	210.5	221.6	238.3	262.8	296.0	337.8	375.1	384.8	349.0	292.5	246.3
57.5°	185.7	193.9	210.3	232.0	264.1	300.9	327.5	325.8	286.3	235.4	202.2
60°	169.3	176.7	192.3	212.2	242.7	275.8	294.5	286.5	246.5	204.5	172.7
62.5°	154.0	160.9	174.1	192.3	218.5	247.3	260.9	249.9	212.2	175.2	149.9
65°	130.9	135.9	146.5	163.3	183.8	203.7	215.9	199.8	166.3	138.4	119.3
67.5°	109.3	113.6	123.0	135.1	149.2	163.0	167.9	152.8	126.8	108.1	94.5
70°	95.3	99.3	105.6	117.0	126.3	136.0	138.4	124.9	103.2	88.9	80.6
72.5°	82.0	85.6	91.2	99.2	105.6	111.2	112.4	99.8	83.2	73.4	66.9
75°	62.5	65.7	69.2	72.2	76.4	77.4	77.0	67.2	58.3	51.7	48.1
77.5°	45.9	47.3	49.4	50.6	50.8	50.7	48.7	42.5	37.9	35.2	33.8
80°	35.4	36.4	37.0	37.4	37.6	35.6	33.4	29.6	28.1	26.4	24.7
82.5°	25.7	26.3	26.9	27.0	26.0	24.3	22.3	20.4	19.3	18.5	17.8
85°	13.9	14.1	13.9	12.9	11.5	10.9	10.5	10.2	10.0	9.7	9.7
87.5°	5.3	5.1	4.5	4.8	5.1	5.1	5.3	5.3	5.4	5.5	5.7
90°	1.8	2.9	4.0	5.2	6.3	7.2	8.3	9.2	10.2	10.9	11.6
92.5°	16.3	17.0	17.8	18.7	19.6	20.9	22.1	23.3	24.5	25.5	26.4
95°	41.8	42.1	42.4	42.7	43.6	44.9	46.4	47.8	49.2	50.2	51.2
97.5°	69.1	69.2	69.4	69.5	70.5	72.5	74.5	76.4	78.4	79.3	80.2
100°	89.5	89.5	89.5	89.5	90.4	92.2	94.1	95.9	97.8	99.1	100.3
102.5°	112.0	112.6	113.1	113.7	114.5	115.5	116.4	117.3	118.2	119.7	121.1
105°	146.5	147.1	147.8	148.6	149.4	150.2	151.0	151.9	152.7	153.6	154.5
107.5°	184.3	185.0	185.7	186.4	187.1	187.8	188.4	189.1	189.7	190.1	190.5
110°	210.3	211.0	211.8	212.5	213.0	213.4	213.9	214.3	214.7	215.2	215.6



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	236.6	236.9	237.4	237.7	238.2	238.7	239.3	239.8	240.3	240.6	240.7
115°	276.0	276.6	277.2	277.8	278.2	278.4	278.7	279.1	279.3	279.1	279.1
117.5°	315.1	315.4	315.6	315.9	316.2	316.4	316.7	316.9	317.2	317.3	317.4
120°	340.1	340.8	341.6	342.2	342.7	342.8	342.9	343.1	343.2	343.2	343.2
122.5°	366.3	366.5	366.8	367.0	367.3	367.6	368.1	368.4	368.8	368.7	368.6
125°	402.9	403.7	404.6	405.4	406.0	406.0	406.2	406.4	406.5	406.2	406.0
127.5°	440.8	441.3	441.9	442.3	442.6	442.8	443.0	443.2	443.3	443.2	443.1
130°	464.1	464.9	465.5	466.2	466.7	467.0	467.3	467.6	467.9	467.7	467.6
132.5°	487.6	488.7	489.9	491.0	491.6	491.5	491.5	491.5	491.4	491.3	491.1
135°	523.7	524.5	525.4	526.2	526.8	526.8	527.0	527.2	527.3	527.3	527.3
137.5°	557.9	558.7	559.6	560.4	560.9	561.3	561.5	561.9	562.2	562.4	562.6
140°	579.8	580.5	581.2	581.9	582.5	582.9	583.3	583.8	584.2	584.4	584.8
142.5°	601.7	602.3	602.9	603.5	604.0	604.6	605.1	605.6	606.1	606.3	606.5
145°	634.0	634.6	635.1	635.7	636.2	636.6	637.1	637.5	637.9	637.9	637.9
147.5°	663.7	663.9	664.3	664.6	664.9	665.2	665.6	665.9	666.2	666.6	666.9
150°	683.1	682.9	682.9	682.7	682.9	683.5	684.1	684.6	685.2	685.2	685.2
152.5°	699.8	700.0	700.3	700.4	700.6	700.9	701.1	701.3	701.5	701.9	702.2
155°	724.8	724.8	724.8	724.8	724.9	725.0	725.1	725.3	725.5	726.0	726.6
157.5°	747.0	746.7	746.4	746.1	746.0	746.1	746.2	746.4	746.6	747.1	747.7
160°	760.2	759.7	759.3	758.9	758.7	758.9	759.1	759.1	759.3	759.9	760.4
162.5°	772.1	771.7	771.5	771.1	770.9	771.0	771.0	771.0	771.1	771.8	772.5
165°	787.8	787.6	787.2	787.0	786.9	787.0	787.1	787.3	787.5	788.0	788.6
167.5°	800.8	800.2	799.7	799.1	798.8	798.8	798.8	798.8	798.8	799.7	800.6
170°	808.0	807.4	806.8	806.2	806.0	806.0	806.0	806.0	806.0	806.8	807.7
172.5°	813.0	812.5	811.9	811.4	811.1	811.1	811.1	811.1	811.1	811.9	812.8
175°	818.8	818.3	817.7	817.1	816.8	816.8	816.8	816.8	816.8	817.7	818.6
177.5°	821.9	821.4	821.0	820.5	820.3	820.1	820.0	819.9	819.8	820.4	821.1
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3	821.3



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	505.8	505.8	508.5	508.3	510.1	509.5	509.8
5°	543.7	547.1	550.1	552.1	555.1	555.9	555.4
7.5°	583.1	590.6	594.2	599.3	600.1	602.8	602.5
10°	607.3	614.8	620.4	624.7	626.9	629.6	629.9
12.5°	626.5	632.7	637.7	641.7	644.4	645.2	645.8
15°	641.4	648.3	654.1	659.9	663.3	665.9	667.3
17.5°	656.4	667.2	677.3	685.2	689.9	693.9	693.9
20°	668.0	680.4	693.1	702.1	711.3	715.2	715.8
22.5°	680.4	699.3	715.7	729.6	741.7	745.8	747.3
25°	706.3	730.9	756.2	775.7	789.6	797.8	799.0
27.5°	737.4	770.8	797.4	815.4	826.9	833.0	834.3
30°	759.4	790.2	814.1	827.6	833.0	833.8	830.8
32.5°	769.2	792.3	801.8	801.1	790.5	783.5	780.8
35°	757.2	752.4	729.2	701.3	680.0	666.5	662.9
37.5°	689.1	647.9	605.1	563.0	540.6	529.2	509.6
40°	621.9	563.2	518.7	483.3	458.0	437.6	432.9
42.5°	546.1	485.5	441.0	410.7	390.5	376.6	370.5
45°	438.9	386.8	349.9	326.7	311.2	301.0	296.4
47.5°	351.0	310.6	283.9	266.7	254.8	246.0	243.5
50°	302.8	270.5	247.9	233.3	224.4	217.7	214.9
52.5°	263.0	236.9	219.6	207.6	199.1	194.9	192.6
55°	217.1	194.6	182.0	172.5	167.7	164.4	162.7
57.5°	177.5	161.3	152.1	145.5	141.1	139.0	138.2
60°	155.4	142.7	134.3	129.2	126.1	123.4	122.5
62.5°	135.8	125.8	119.3	114.8	111.8	110.6	110.1
65°	109.4	102.9	98.1	95.3	92.9	92.5	92.3
67.5°	87.0	83.1	80.6	77.7	76.9	75.5	75.2
70°	74.4	71.8	68.8	67.8	66.8	65.4	65.7
72.5°	63.1	60.5	58.5	57.2	56.8	56.2	56.7
75°	46.1	45.4	44.6	43.6	43.1	43.1	43.0
77.5°	33.0	32.3	31.4	30.8	30.7	29.9	30.1
80°	23.8	22.9	22.5	22.6	22.0	21.9	21.9
82.5°	17.7	17.3	16.9	17.0	16.8	16.6	16.8
85°	9.7	9.6	9.6	9.4	9.4	9.1	9.1
87.5°	5.9	6.3	6.0	6.0	6.1	6.3	6.5
90°	12.4	13.1	13.6	14.0	14.5	14.9	15.3
92.5°	27.4	28.3	28.9	29.3	29.5	29.9	30.1
95°	52.2	53.2	53.8	54.2	54.4	54.7	54.9
97.5°	81.2	82.1	82.7	82.8	83.0	83.2	83.3
100°	101.6	102.9	103.7	104.0	104.3	104.5	104.8
102.5°	122.4	123.8	124.7	125.1	125.5	125.9	126.3
105°	155.3	156.2	156.8	157.2	157.6	158.1	158.5
107.5°	191.0	191.4	191.6	191.6	191.6	191.5	191.5
110°	216.0	216.5	216.6	216.5	216.3	216.2	216.0



TEST NUMBER: P333645-935

CATALOG NUMBER: S125RDIW-S375D770U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	240.9	241.1	241.1	240.8	240.6	240.3	240.0
115°	278.9	278.7	278.6	278.4	278.4	278.2	278.0
117.5°	317.5	317.6	317.4	316.8	316.2	315.6	315.1
120°	343.2	343.2	342.9	342.4	341.8	341.2	340.7
122.5°	368.4	368.3	368.1	367.6	367.1	366.7	366.3
125°	405.6	405.4	405.2	405.0	404.8	404.8	404.6
127.5°	442.9	442.7	442.6	442.3	442.0	441.7	441.4
130°	467.4	467.3	467.1	466.8	466.5	466.2	466.0
132.5°	490.9	490.9	490.5	490.2	489.7	489.4	489.0
135°	527.3	527.3	527.0	526.4	525.9	525.3	524.8
137.5°	562.7	562.9	562.6	561.9	561.2	560.5	559.7
140°	585.0	585.3	585.1	584.4	583.7	583.0	582.3
142.5°	606.7	606.8	606.6	605.9	605.2	604.4	603.7
145°	637.9	637.9	637.7	637.2	636.8	636.4	635.9
147.5°	667.3	667.6	667.3	666.3	665.4	664.4	663.5
150°	685.2	685.2	685.0	684.8	684.5	684.2	683.9
152.5°	702.6	702.9	702.8	702.3	701.8	701.3	700.8
155°	727.1	727.7	727.6	726.9	726.3	725.5	724.8
157.5°	748.2	748.8	748.6	747.7	746.7	745.8	744.9
160°	761.0	761.6	761.6	760.8	760.1	759.4	758.7
162.5°	773.1	773.8	773.8	772.9	772.1	771.3	770.4
165°	789.2	789.7	789.5	788.8	787.9	787.0	786.2
167.5°	801.4	802.2	802.2	801.3	800.5	799.6	798.7
170°	808.6	809.4	809.3	808.3	807.4	806.3	805.4
172.5°	813.6	814.5	814.5	813.6	812.7	811.8	811.0
175°	819.4	820.3	820.2	819.2	818.2	817.2	816.2
177.5°	821.8	822.5	822.4	821.7	820.9	820.1	819.2
180°	821.3	821.3	821.3	821.3	821.3	821.3	821.3

(END OF REPORT)