

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333347-840

Luminaire Tested: **S125DIW-S375D770U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333347-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D770U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4241.5 lumens  
Efficiency: N/A  
Efficacy: 139.5 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	37	31
2	87	79	73	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	14	16	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3551	3551	3551	3551
5°	4112	3563	3120	3563
10°	4783	3545	2733	3545
15°	5295	3518	2521	3518
20°	5927	3477	2351	3477
25°	6944	3430	2268	3430
30°	7500	3384	2196	3384
35°	6166	3299	2149	3299
40°	4383	3179	2097	3179
45°	3368	3018	2067	3018
50°	2875	2817	2063	2817
55°	2559	2622	2081	2622
60°	2308	2408	2134	2408
65°	2133	2193	2190	2193
70°	1939	1969	2221	1969
75°	1712	1737	2201	1737
80°	1443	1417	2012	1417
85°	1149	1015	1623	1015



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.9	1.2
10°-20°	157.6	3.7
20°-30°	255.9	6.0
30°-40°	312.1	7.4
40°-50°	283.9	6.7
50°-60°	226.2	5.3
60°-70°	157.5	3.7
70°-80°	84.0	2.0
80°-90°	23.3	0.5
90°-100°	64.5	1.5
100°-110°	190.5	4.5
110°-120°	322.7	7.6
120°-130°	424.7	10.0
130°-140°	475.9	11.2
140°-150°	466.4	11.0
150°-160°	391.7	9.2
160°-170°	260.4	6.1
170°-180°	91.1	2.1
0°-30°	466.4	11.0
0°-40°	778.5	18.4
0°-60°	1288.6	30.4
0°-90°	1553.5	36.6
90°-120°	577.8	13.6
90°-150°	1944.8	45.9
90°-180°	2688.0	63.4
0°-180°	4241.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	634	550	481	550	634	64
15°	792	526	377	526	792	227
25°	974	481	318	481	974	445
35°	782	418	273	418	782	479
45°	369	330	226	330	369	295
55°	227	233	185	233	227	205
65°	140	144	143	144	140	138
75°	69	70	88	70	69	74
85°	16	14	22	14	16	18
90°	18	1	18	1	18	11
95°	64	49	64	49	64	66
105°	186	171	186	171	186	197
115°	326	323	326	323	326	323
125°	474	472	474	472	474	424
135°	616	613	616	613	616	475
145°	746	743	746	743	746	466
155°	850	850	850	850	850	391
165°	922	924	922	924	922	260
175°	957	961	957	961	957	91
180°	963	963	963	963	963	



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	581.5	580.8	580.0	578.6	579.7	576.4	575.0	572.4	569.2	568.0	566.7
5°	634.2	635.4	636.6	631.7	632.2	628.8	621.4	615.3	610.5	604.1	599.7
7.5°	697.7	695.0	694.7	691.6	686.1	681.7	673.9	663.9	654.2	643.2	634.1
10°	729.4	729.7	727.6	723.9	718.0	713.8	703.6	693.8	681.9	667.8	657.8
12.5°	753.4	754.4	751.6	746.6	743.8	734.4	726.3	714.7	700.5	689.3	674.1
15°	791.9	789.4	787.6	781.2	776.4	766.6	753.8	741.5	726.2	712.0	697.7
17.5°	829.2	831.3	827.8	822.0	806.8	795.4	778.2	761.5	742.4	723.3	706.3
20°	862.4	864.3	859.0	848.9	830.7	819.3	796.7	775.2	753.1	728.5	709.8
22.5°	903.9	902.4	895.1	879.9	864.1	843.0	818.5	792.3	764.6	736.9	712.1
25°	974.4	964.6	960.2	941.3	920.6	889.5	856.0	817.7	783.2	746.5	714.8
27.5°	1013.6	1010.5	1005.5	992.4	970.6	937.4	897.8	851.1	802.4	756.2	714.6
30°	1005.7	1006.2	1006.6	1002.5	988.5	963.5	924.0	873.9	816.0	764.0	715.9
32.5°	936.2	944.7	952.9	962.5	966.4	961.6	937.0	891.6	832.0	773.0	715.2
35°	782.1	784.8	811.1	837.3	872.7	900.3	918.7	898.6	848.5	780.5	714.3
37.5°	609.9	622.5	640.8	670.2	721.4	767.3	826.3	853.3	837.2	783.0	712.7
40°	519.9	531.6	543.5	573.6	616.7	672.3	739.2	796.4	809.7	775.2	707.0
42.5°	450.5	459.7	472.9	495.5	531.6	580.8	644.8	719.5	765.5	752.5	695.3
45°	368.7	374.6	384.8	402.7	428.9	467.4	523.8	605.5	676.7	700.2	667.4
47.5°	315.6	315.6	323.6	335.9	354.8	387.5	429.3	493.2	569.3	625.5	622.9
50°	286.1	284.9	291.2	301.9	316.9	338.6	378.5	429.6	502.6	566.3	584.1
52.5°	260.6	260.8	264.7	272.7	285.2	303.7	333.5	379.6	441.9	507.4	540.8
55°	227.3	226.3	230.8	236.1	245.3	257.4	278.8	314.1	364.8	429.1	472.5
57.5°	196.6	199.2	201.0	204.7	212.3	220.5	238.5	264.4	304.6	359.8	405.7
60°	178.7	181.3	182.7	186.4	192.5	199.5	213.5	234.5	268.3	316.0	361.4
62.5°	162.7	164.7	165.2	168.5	173.5	180.3	191.3	208.9	235.7	277.3	321.8
65°	139.6	139.6	140.5	144.0	146.3	152.4	160.8	173.6	195.1	227.5	265.6
67.5°	117.2	118.4	118.2	119.7	121.8	126.5	132.5	143.1	159.1	182.7	213.2
70°	102.7	103.6	103.4	104.5	106.8	109.9	114.8	124.8	136.2	156.5	182.7
72.5°	89.6	90.0	89.4	90.9	92.3	94.9	100.5	105.8	116.4	133.6	155.1
75°	68.6	69.1	69.6	70.5	71.9	73.3	76.0	81.4	88.5	101.3	115.0
77.5°	51.4	50.5	51.7	51.5	52.3	53.4	55.8	58.7	64.4	72.6	83.2
80°	38.8	39.0	39.0	39.2	40.4	41.1	43.1	45.2	49.7	55.7	63.2
82.5°	28.3	28.9	28.5	29.0	29.9	30.4	31.6	33.3	35.9	40.7	46.0
85°	15.5	14.2	14.7	15.1	15.1	15.5	16.4	17.1	18.5	20.3	22.4
87.5°	8.1	8.4	8.5	8.4	8.4	8.3	8.9	8.7	9.1	9.5	10.0
90°	18.0	17.5	17.0	16.5	16.0	15.3	14.5	13.6	12.8	12.0	10.8
92.5°	35.3	35.0	34.6	34.3	33.9	33.2	32.1	31.0	29.9	28.8	27.4
95°	64.4	64.1	63.8	63.5	63.1	62.4	61.2	60.1	58.9	57.8	56.0
97.5°	97.8	97.6	97.4	97.1	96.9	96.3	95.2	94.1	93.0	91.9	89.6
100°	122.9	122.6	122.3	122.0	121.6	120.7	119.2	117.6	116.2	114.7	112.5
102.5°	148.1	147.6	147.2	146.7	146.2	145.2	143.6	142.0	140.4	138.7	137.5
105°	185.9	185.4	184.9	184.4	183.9	183.2	182.2	181.2	180.2	179.2	178.1
107.5°	224.6	224.6	224.7	224.7	224.7	224.5	224.0	223.5	223.0	222.5	221.8
110°	253.4	253.6	253.7	253.9	254.1	253.9	253.4	252.9	252.4	251.9	251.4



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	281.6	281.9	282.2	282.5	282.8	282.8	282.6	282.4	282.2	281.9	281.2
115°	326.1	326.3	326.5	326.6	326.8	326.9	327.1	327.3	327.4	327.6	327.3
117.5°	369.6	370.2	370.9	371.6	372.2	372.5	372.3	372.2	372.1	372.0	371.7
120°	399.6	400.2	400.9	401.6	402.2	402.5	402.5	402.5	402.5	402.5	402.4
122.5°	429.6	430.1	430.6	431.1	431.7	432.0	432.1	432.3	432.4	432.5	432.1
125°	474.5	474.7	474.8	475.0	475.2	475.4	475.7	476.2	476.5	476.8	476.7
127.5°	517.8	518.1	518.4	518.8	519.1	519.3	519.5	519.7	519.8	520.0	519.8
130°	546.5	546.8	547.1	547.5	547.9	548.1	548.3	548.5	548.6	548.8	548.5
132.5°	573.5	574.0	574.4	574.9	575.3	575.7	575.8	576.0	576.2	576.3	576.4
135°	615.5	616.1	616.8	617.4	618.1	618.4	618.4	618.4	618.4	618.4	618.3
137.5°	656.5	657.4	658.2	659.0	659.8	660.2	660.0	659.8	659.6	659.4	659.0
140°	683.0	683.8	684.6	685.5	686.3	686.5	686.2	685.9	685.5	685.2	684.7
142.5°	708.1	708.9	709.8	710.6	711.4	711.8	711.6	711.3	711.1	710.9	710.3
145°	745.9	746.4	746.9	747.4	747.9	748.2	748.2	748.2	748.2	748.2	747.7
147.5°	778.2	779.3	780.4	781.5	782.6	783.0	782.6	782.2	781.8	781.4	781.0
150°	802.1	802.4	802.8	803.1	803.4	803.7	803.7	803.7	803.7	803.7	802.9
152.5°	821.9	822.5	823.1	823.7	824.4	824.5	824.0	823.6	823.2	822.8	822.5
155°	850.1	850.9	851.8	852.6	853.4	853.5	852.8	852.2	851.5	850.9	850.7
157.5°	873.6	874.7	875.9	877.0	878.1	878.3	877.6	877.0	876.3	875.7	875.5
160°	889.9	890.7	891.5	892.3	893.2	893.2	892.6	891.9	891.3	890.6	890.4
162.5°	903.6	904.6	905.5	906.6	907.6	907.6	906.8	906.1	905.2	904.4	904.3
165°	922.1	923.1	924.1	925.1	926.0	926.2	925.6	924.9	924.2	923.6	923.4
167.5°	936.8	937.9	938.9	939.9	940.9	940.9	940.0	939.0	938.0	937.0	937.0
170°	944.6	945.7	947.0	948.1	949.3	949.4	948.4	947.4	946.3	945.3	945.3
172.5°	951.2	952.2	953.2	954.3	955.3	955.3	954.3	953.3	952.3	951.3	951.3
175°	957.4	958.5	959.7	960.8	962.0	962.1	961.1	960.1	959.1	958.1	958.1
177.5°	960.9	961.9	962.8	963.7	964.6	964.7	963.9	963.1	962.3	961.5	961.7
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	565.6	564.3	562.8	560.2	557.0	555.3	552.8	551.1	547.8	544.9	541.9
5°	594.3	588.2	582.7	575.4	567.5	562.4	556.3	549.6	542.5	535.3	527.4
7.5°	624.1	613.3	601.7	589.2	576.8	565.5	554.7	544.2	534.3	522.3	512.2
10°	644.0	630.5	616.0	599.1	582.4	567.9	553.3	540.5	527.4	513.4	501.0
12.5°	664.0	646.0	625.5	606.8	586.9	569.5	552.2	535.7	519.4	503.8	489.4
15°	678.1	662.3	643.4	616.7	594.3	570.3	547.4	526.2	506.3	489.1	470.9
17.5°	687.4	666.9	646.6	621.2	591.8	564.9	539.0	514.6	492.3	470.4	452.9
20°	689.0	668.0	646.8	621.9	591.8	561.0	535.0	505.9	481.9	459.2	437.8
22.5°	688.5	664.7	641.6	615.9	586.5	558.2	526.8	497.2	471.0	448.8	426.4
25°	683.3	657.8	628.8	603.0	574.0	543.9	512.2	481.4	454.8	429.4	407.2
27.5°	678.8	645.9	613.1	582.9	554.9	527.4	497.0	465.4	436.0	410.2	389.3
30°	673.5	637.2	600.4	568.9	540.2	513.4	484.6	453.8	423.0	397.9	375.5
32.5°	668.6	626.4	587.5	553.2	522.8	496.8	470.3	441.0	410.7	385.2	362.7
35°	659.2	610.5	565.8	527.1	494.7	467.9	445.7	418.4	390.6	365.9	344.5
37.5°	647.3	589.5	541.6	501.0	465.4	437.2	416.6	395.6	368.9	345.1	325.7
40°	637.9	574.5	523.8	482.3	445.5	416.1	396.9	377.1	355.0	332.8	312.3
42.5°	626.2	561.1	505.9	461.2	424.7	396.1	376.0	359.2	339.6	318.9	299.9
45°	604.6	536.7	477.0	428.9	392.0	363.8	343.1	330.4	315.7	296.1	280.0
47.5°	572.8	507.5	445.7	396.1	358.0	331.8	312.4	300.2	289.9	275.4	260.7
50°	544.6	485.6	423.0	373.9	335.8	309.4	291.4	280.4	271.7	260.4	248.0
52.5°	513.1	458.2	400.8	352.1	314.5	288.5	270.9	261.3	253.9	245.9	233.7
55°	462.9	416.3	363.0	316.9	282.2	256.7	241.3	232.9	226.8	220.8	213.3
57.5°	407.8	371.2	324.2	281.9	249.8	226.7	212.4	204.2	199.4	196.3	192.0
60°	368.9	337.7	297.1	258.5	227.3	206.7	192.8	186.4	182.5	180.0	176.6
62.5°	332.9	307.2	269.6	234.5	207.1	187.7	175.2	169.1	165.3	164.0	161.4
65°	279.8	259.9	228.9	199.8	176.4	159.9	149.4	143.5	141.2	139.8	140.0
67.5°	227.4	215.4	190.5	165.6	146.9	133.1	124.6	120.2	119.0	117.1	117.1
70°	195.5	186.4	165.4	143.7	127.1	116.4	109.0	104.3	103.1	102.2	102.0
72.5°	167.3	159.4	141.2	123.8	108.9	99.5	93.3	90.5	88.6	88.1	88.0
75°	125.7	121.4	106.8	93.1	82.8	76.3	72.1	69.6	68.2	67.9	68.2
77.5°	89.4	85.5	76.3	66.6	60.1	55.1	51.6	50.7	49.2	49.2	49.0
80°	67.2	64.6	58.8	51.1	45.7	41.5	39.7	38.1	37.6	36.9	37.6
82.5°	48.7	45.9	42.0	37.1	32.6	30.2	28.3	27.8	27.5	27.2	27.3
85°	24.0	24.2	21.9	18.2	16.4	14.9	13.7	13.7	13.5	13.3	13.5
87.5°	10.1	9.5	8.6	7.8	6.6	5.8	5.3	5.2	4.8	4.9	5.5
90°	9.7	8.5	7.4	6.1	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	26.0	24.5	23.0	21.9	20.9	20.0	19.1	18.2	19.1	20.0	20.9
95°	54.4	52.7	51.1	50.1	49.7	49.4	49.1	48.8	49.1	49.4	49.7
97.5°	87.4	85.0	82.7	81.5	81.4	81.2	81.1	81.0	81.1	81.2	81.4
100°	110.4	108.2	106.0	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.9
102.5°	136.5	135.4	134.3	133.4	132.7	132.1	131.4	130.8	131.4	132.1	132.7
105°	177.1	176.2	175.2	174.3	173.4	172.6	171.8	171.0	171.8	172.6	173.4
107.5°	221.0	220.3	219.4	218.6	217.8	217.0	216.1	215.3	216.1	217.0	217.8
110°	250.9	250.3	249.8	249.2	248.4	247.5	246.7	245.9	246.7	247.5	248.4





TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.6	279.9	279.3	278.8	278.4	277.9	277.5	277.1	277.5	277.9	278.4
115°	326.9	326.6	326.3	325.8	325.1	324.5	323.8	323.2	323.8	324.5	325.1
117.5°	371.4	371.1	370.8	370.5	370.2	369.9	369.6	369.3	369.6	369.9	370.2
120°	402.2	402.0	401.9	401.4	400.6	399.7	398.9	398.1	398.9	399.7	400.6
122.5°	431.7	431.2	430.8	430.5	430.2	429.9	429.6	429.3	429.6	429.9	430.2
125°	476.5	476.3	476.2	475.5	474.5	473.5	472.5	471.5	472.5	473.5	474.5
127.5°	519.6	519.4	519.2	518.8	518.3	517.7	517.1	516.5	517.1	517.7	518.3
130°	548.1	547.8	547.4	546.8	546.0	545.2	544.3	543.5	544.3	545.2	546.0
132.5°	576.4	576.5	576.6	575.9	574.6	573.2	571.9	570.5	571.9	573.2	574.6
135°	618.1	617.9	617.8	617.2	616.2	615.2	614.2	613.2	614.2	615.2	616.2
137.5°	658.6	658.3	657.9	657.3	656.3	655.3	654.4	653.4	654.4	655.3	656.3
140°	684.2	683.7	683.2	682.6	681.7	680.9	680.0	679.2	680.0	680.9	681.7
142.5°	709.7	709.1	708.4	707.8	707.1	706.4	705.7	705.0	705.7	706.4	707.1
145°	747.2	746.7	746.2	745.6	744.9	744.3	743.6	743.0	743.6	744.3	744.9
147.5°	780.6	780.2	779.8	779.5	779.1	778.7	778.4	778.0	778.4	778.7	779.1
150°	802.3	801.6	801.0	800.7	800.9	801.0	801.2	801.4	801.2	801.0	800.9
152.5°	822.3	822.0	821.7	821.5	821.3	821.0	820.8	820.6	820.8	821.0	821.3
155°	850.5	850.4	850.2	850.1	850.1	850.1	850.1	850.1	850.1	850.1	850.1
157.5°	875.3	875.1	874.9	875.0	875.5	875.8	876.2	876.6	876.2	875.8	875.5
160°	890.3	890.1	889.9	890.1	890.6	891.1	891.6	892.1	891.6	891.1	890.6
162.5°	904.3	904.3	904.2	904.4	904.8	905.1	905.5	905.9	905.5	905.1	904.8
165°	923.2	923.1	922.9	923.0	923.3	923.7	924.0	924.3	924.0	923.7	923.3
167.5°	937.0	937.0	937.0	937.3	938.0	938.6	939.3	940.0	939.3	938.6	938.0
170°	945.3	945.3	945.3	945.6	946.3	947.0	947.7	948.4	947.7	947.0	946.3
172.5°	951.3	951.3	951.3	951.7	952.3	953.0	953.6	954.3	953.6	953.0	952.3
175°	958.1	958.1	958.1	958.4	959.1	959.8	960.4	961.1	960.4	959.8	959.1
177.5°	961.8	961.9	962.1	962.4	962.9	963.4	964.0	964.5	964.0	963.4	962.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	540.3	538.2	536.5	532.8	530.7	528.0	525.7	528.2	525.5	526.6	524.9
5°	523.4	516.8	512.2	505.4	499.6	494.2	490.3	489.6	487.7	486.8	483.9
7.5°	503.1	494.9	487.0	478.1	470.6	463.0	458.2	454.1	451.5	448.0	445.6
10°	491.2	480.2	470.9	460.2	450.8	442.6	436.2	432.8	429.8	425.4	423.7
12.5°	476.5	465.1	453.7	442.2	433.2	424.1	418.6	413.6	411.5	406.6	406.1
15°	458.8	441.7	430.5	418.9	406.5	399.0	394.4	389.0	386.7	383.1	380.6
17.5°	437.7	422.4	408.5	396.4	385.8	379.5	373.7	370.0	366.0	363.7	359.5
20°	422.3	407.9	393.8	381.0	372.8	365.7	361.0	357.5	353.3	352.1	347.9
22.5°	409.5	393.5	380.1	369.3	360.4	352.2	347.2	344.8	341.9	338.3	337.5
25°	388.5	371.9	360.5	349.8	341.8	334.4	330.9	327.9	325.1	322.4	321.5
27.5°	370.4	355.6	342.0	332.3	325.4	318.6	315.6	311.8	309.8	307.7	305.2
30°	357.7	342.5	330.6	321.3	313.9	307.8	304.5	301.9	300.1	298.2	296.8
32.5°	344.7	330.6	319.1	309.9	302.5	297.9	295.0	293.2	291.1	288.9	287.1
35°	327.4	311.9	300.7	292.9	287.0	283.5	280.2	278.6	276.3	276.3	274.4
37.5°	307.9	294.6	284.7	277.5	272.3	269.1	265.6	264.5	263.0	262.0	261.4
40°	296.4	284.0	274.7	267.4	261.9	259.2	256.4	254.6	253.7	252.5	252.1
42.5°	284.4	272.6	263.7	257.0	252.1	249.9	247.3	246.0	244.1	242.6	242.3
45°	266.2	254.8	246.6	241.3	237.1	234.5	232.9	230.0	229.1	227.3	227.0
47.5°	249.0	238.0	230.0	225.6	222.0	219.8	217.3	214.5	213.4	212.5	212.4
50°	236.1	226.1	218.6	214.5	211.0	207.9	205.3	203.5	202.8	202.8	203.3
52.5°	223.1	214.5	208.2	203.1	199.8	196.5	194.1	193.0	192.0	193.1	193.9
55°	204.0	195.3	190.7	185.7	182.5	178.7	177.5	177.1	176.4	178.2	179.3
57.5°	183.7	177.6	172.2	167.3	164.4	162.2	160.7	160.4	161.7	162.6	165.6
60°	170.8	163.8	159.0	155.2	151.7	150.3	149.8	149.4	150.3	152.8	156.8
62.5°	156.6	151.0	145.6	142.9	140.3	137.9	137.8	138.1	140.0	143.0	146.9
65°	135.8	130.9	127.4	124.1	122.0	120.7	121.1	122.0	124.1	128.2	132.5
67.5°	114.6	111.3	108.2	105.5	103.5	103.5	104.0	105.4	107.9	112.4	116.4
70°	101.1	97.4	94.7	93.6	91.9	91.0	92.4	94.7	96.8	101.1	104.5
72.5°	87.5	84.2	82.2	81.4	80.7	80.0	80.5	83.0	85.8	90.0	94.1
75°	67.2	66.0	64.6	63.7	63.0	63.5	63.9	66.2	68.6	73.0	77.7
77.5°	49.1	47.9	47.0	46.8	46.4	46.7	48.0	49.7	51.9	55.1	58.7
80°	37.1	36.7	36.2	36.0	36.0	36.2	38.1	39.2	41.3	44.3	47.2
82.5°	27.1	26.8	26.7	26.6	26.8	26.9	28.0	29.5	31.2	33.5	36.0
85°	14.2	13.7	14.4	14.7	14.2	14.9	15.5	16.4	17.1	18.2	19.4
87.5°	5.9	6.5	6.6	7.0	7.2	7.8	7.8	8.7	9.3	9.8	9.7
90°	6.1	7.4	8.5	9.7	10.8	12.0	12.8	13.6	14.5	15.3	16.0
92.5°	21.9	23.0	24.5	26.0	27.4	28.8	29.9	31.0	32.1	33.2	33.9
95°	50.1	51.1	52.7	54.4	56.0	57.8	58.9	60.1	61.2	62.4	63.1
97.5°	81.5	82.7	85.0	87.4	89.6	91.9	93.0	94.1	95.2	96.3	96.9
100°	104.9	106.0	108.2	110.4	112.5	114.7	116.2	117.6	119.2	120.7	121.6
102.5°	133.4	134.3	135.4	136.5	137.5	138.7	140.4	142.0	143.6	145.2	146.2
105°	174.3	175.2	176.2	177.1	178.1	179.2	180.2	181.2	182.2	183.2	183.9
107.5°	218.6	219.4	220.3	221.0	221.8	222.5	223.0	223.5	224.0	224.5	224.7
110°	249.2	249.8	250.3	250.9	251.4	251.9	252.4	252.9	253.4	253.9	254.1



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	278.8	279.3	279.9	280.6	281.2	281.9	282.2	282.4	282.6	282.8	282.8
115°	325.8	326.3	326.6	326.9	327.3	327.6	327.4	327.3	327.1	326.9	326.8
117.5°	370.5	370.8	371.1	371.4	371.7	372.0	372.1	372.2	372.3	372.5	372.2
120°	401.4	401.9	402.0	402.2	402.4	402.5	402.5	402.5	402.5	402.5	402.2
122.5°	430.5	430.8	431.2	431.7	432.1	432.5	432.4	432.3	432.1	432.0	431.7
125°	475.5	476.2	476.3	476.5	476.7	476.8	476.5	476.2	475.7	475.4	475.2
127.5°	518.8	519.2	519.4	519.6	519.8	520.0	519.8	519.7	519.5	519.3	519.1
130°	546.8	547.4	547.8	548.1	548.5	548.8	548.6	548.5	548.3	548.1	547.9
132.5°	575.9	576.6	576.5	576.4	576.4	576.3	576.2	576.0	575.8	575.7	575.3
135°	617.2	617.8	617.9	618.1	618.3	618.4	618.4	618.4	618.4	618.4	618.1
137.5°	657.3	657.9	658.3	658.6	659.0	659.4	659.6	659.8	660.0	660.2	659.8
140°	682.6	683.2	683.7	684.2	684.7	685.2	685.5	685.9	686.2	686.5	686.3
142.5°	707.8	708.4	709.1	709.7	710.3	710.9	711.1	711.3	711.6	711.8	711.4
145°	745.6	746.2	746.7	747.2	747.7	748.2	748.2	748.2	748.2	748.2	747.9
147.5°	779.5	779.8	780.2	780.6	781.0	781.4	781.8	782.2	782.6	783.0	782.6
150°	800.7	801.0	801.6	802.3	802.9	803.7	803.7	803.7	803.7	803.7	803.4
152.5°	821.5	821.7	822.0	822.3	822.5	822.8	823.2	823.6	824.0	824.5	824.4
155°	850.1	850.2	850.4	850.5	850.7	850.9	851.5	852.2	852.8	853.5	853.4
157.5°	875.0	874.9	875.1	875.3	875.5	875.7	876.3	877.0	877.6	878.3	878.1
160°	890.1	889.9	890.1	890.3	890.4	890.6	891.3	891.9	892.6	893.2	893.2
162.5°	904.4	904.2	904.3	904.3	904.3	904.4	905.2	906.1	906.8	907.6	907.6
165°	923.0	922.9	923.1	923.2	923.4	923.6	924.2	924.9	925.6	926.2	926.0
167.5°	937.3	937.0	937.0	937.0	937.0	937.0	938.0	939.0	940.0	940.9	940.9
170°	945.6	945.3	945.3	945.3	945.3	945.3	946.3	947.4	948.4	949.4	949.3
172.5°	951.7	951.3	951.3	951.3	951.3	951.3	952.3	953.3	954.3	955.3	955.3
175°	958.4	958.1	958.1	958.1	958.1	958.1	959.1	960.1	961.1	962.1	962.0
177.5°	962.4	962.1	961.9	961.8	961.7	961.5	962.3	963.1	963.9	964.7	964.6
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	523.8	525.1	524.0	525.5	524.0	525.1	523.8	524.9	526.6	525.5	528.2
5°	482.8	480.7	482.1	481.2	482.1	480.7	482.8	483.9	486.8	487.7	489.6
7.5°	444.9	442.9	440.6	439.5	440.6	442.9	444.9	445.6	448.0	451.5	454.1
10°	421.2	418.6	418.4	416.8	418.4	418.6	421.2	423.7	425.4	429.8	432.8
12.5°	403.8	401.4	398.8	398.1	398.8	401.4	403.8	406.1	406.6	411.5	413.6
15°	379.2	377.3	375.7	377.1	375.7	377.3	379.2	380.6	383.1	386.7	389.0
17.5°	358.7	357.2	356.9	355.2	356.9	357.2	358.7	359.5	363.7	366.0	370.0
20°	345.8	344.7	345.2	342.0	345.2	344.7	345.8	347.9	352.1	353.3	357.5
22.5°	335.6	333.3	333.0	332.3	333.0	333.3	335.6	337.5	338.3	341.9	344.8
25°	319.4	318.3	317.1	318.3	317.1	318.3	319.4	321.5	322.4	325.1	327.9
27.5°	305.4	304.0	303.7	303.9	303.7	304.0	305.4	305.2	307.7	309.8	311.8
30°	296.8	294.5	294.7	294.5	294.7	294.5	296.8	296.8	298.2	300.1	301.9
32.5°	287.5	285.9	285.6	285.2	285.6	285.9	287.5	287.1	288.9	291.1	293.2
35°	273.7	273.7	272.6	272.6	272.6	273.7	273.7	274.4	276.3	276.3	278.6
37.5°	260.7	260.5	259.8	259.9	259.8	260.5	260.7	261.4	262.0	263.0	264.5
40°	251.1	250.9	250.1	248.7	250.1	250.9	251.1	252.1	252.5	253.7	254.6
42.5°	241.8	241.0	240.7	240.1	240.7	241.0	241.8	242.3	242.6	244.1	246.0
45°	227.0	227.0	226.6	226.3	226.6	227.0	227.0	227.0	227.3	229.1	230.0
47.5°	212.8	213.2	214.1	213.9	214.1	213.2	212.8	212.4	212.5	213.4	214.5
50°	204.2	204.4	205.1	205.3	205.1	204.4	204.2	203.3	202.8	202.8	203.5
52.5°	194.7	196.0	196.9	196.7	196.9	196.0	194.7	193.9	193.1	192.0	193.0
55°	181.3	183.0	184.6	184.8	184.6	183.0	181.3	179.3	178.2	176.4	177.1
57.5°	168.1	170.4	172.1	172.7	172.1	170.4	168.1	165.6	162.6	161.7	160.4
60°	159.2	162.2	164.3	165.2	164.3	162.2	159.2	156.8	152.8	150.3	149.4
62.5°	150.6	154.0	156.0	156.2	156.0	154.0	150.6	146.9	143.0	140.0	138.1
65°	136.5	140.0	141.9	143.3	141.9	140.0	136.5	132.5	128.2	124.1	122.0
67.5°	121.4	124.9	126.9	128.1	126.9	124.9	121.4	116.4	112.4	107.9	105.4
70°	110.4	113.9	116.6	117.6	116.6	113.9	110.4	104.5	101.1	96.8	94.7
72.5°	99.6	102.7	104.9	106.0	104.9	102.7	99.6	94.1	90.0	85.8	83.0
75°	80.7	84.9	87.1	88.2	87.1	84.9	80.7	77.7	73.0	68.6	66.2
77.5°	62.2	66.0	67.4	68.0	67.4	66.0	62.2	58.7	55.1	51.9	49.7
80°	49.9	52.3	53.9	54.1	53.9	52.3	49.9	47.2	44.3	41.3	39.2
82.5°	38.4	40.3	40.8	41.4	40.8	40.3	38.4	36.0	33.5	31.2	29.5
85°	21.0	21.9	22.2	21.9	22.2	21.9	21.0	19.4	18.2	17.1	16.4
87.5°	10.2	10.1	10.2	10.7	10.2	10.1	10.2	9.7	9.8	9.3	8.7
90°	16.5	17.0	17.5	18.0	17.5	17.0	16.5	16.0	15.3	14.5	13.6
92.5°	34.3	34.6	35.0	35.3	35.0	34.6	34.3	33.9	33.2	32.1	31.0
95°	63.5	63.8	64.1	64.4	64.1	63.8	63.5	63.1	62.4	61.2	60.1
97.5°	97.1	97.4	97.6	97.8	97.6	97.4	97.1	96.9	96.3	95.2	94.1
100°	122.0	122.3	122.6	122.9	122.6	122.3	122.0	121.6	120.7	119.2	117.6
102.5°	146.7	147.2	147.6	148.1	147.6	147.2	146.7	146.2	145.2	143.6	142.0
105°	184.4	184.9	185.4	185.9	185.4	184.9	184.4	183.9	183.2	182.2	181.2
107.5°	224.7	224.7	224.6	224.6	224.6	224.7	224.7	224.7	224.5	224.0	223.5
110°	253.9	253.7	253.6	253.4	253.6	253.7	253.9	254.1	253.9	253.4	252.9



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	282.5	282.2	281.9	281.6	281.9	282.2	282.5	282.8	282.8	282.6	282.4
115°	326.6	326.5	326.3	326.1	326.3	326.5	326.6	326.8	326.9	327.1	327.3
117.5°	371.6	370.9	370.2	369.6	370.2	370.9	371.6	372.2	372.5	372.3	372.2
120°	401.6	400.9	400.2	399.6	400.2	400.9	401.6	402.2	402.5	402.5	402.5
122.5°	431.1	430.6	430.1	429.6	430.1	430.6	431.1	431.7	432.0	432.1	432.3
125°	475.0	474.8	474.7	474.5	474.7	474.8	475.0	475.2	475.4	475.7	476.2
127.5°	518.8	518.4	518.1	517.8	518.1	518.4	518.8	519.1	519.3	519.5	519.7
130°	547.5	547.1	546.8	546.5	546.8	547.1	547.5	547.9	548.1	548.3	548.5
132.5°	574.9	574.4	574.0	573.5	574.0	574.4	574.9	575.3	575.7	575.8	576.0
135°	617.4	616.8	616.1	615.5	616.1	616.8	617.4	618.1	618.4	618.4	618.4
137.5°	659.0	658.2	657.4	656.5	657.4	658.2	659.0	659.8	660.2	660.0	659.8
140°	685.5	684.6	683.8	683.0	683.8	684.6	685.5	686.3	686.5	686.2	685.9
142.5°	710.6	709.8	708.9	708.1	708.9	709.8	710.6	711.4	711.8	711.6	711.3
145°	747.4	746.9	746.4	745.9	746.4	746.9	747.4	747.9	748.2	748.2	748.2
147.5°	781.5	780.4	779.3	778.2	779.3	780.4	781.5	782.6	783.0	782.6	782.2
150°	803.1	802.8	802.4	802.1	802.4	802.8	803.1	803.4	803.7	803.7	803.7
152.5°	823.7	823.1	822.5	821.9	822.5	823.1	823.7	824.4	824.5	824.0	823.6
155°	852.6	851.8	850.9	850.1	850.9	851.8	852.6	853.4	853.5	852.8	852.2
157.5°	877.0	875.9	874.7	873.6	874.7	875.9	877.0	878.1	878.3	877.6	877.0
160°	892.3	891.5	890.7	889.9	890.7	891.5	892.3	893.2	893.2	892.6	891.9
162.5°	906.6	905.5	904.6	903.6	904.6	905.5	906.6	907.6	907.6	906.8	906.1
165°	925.1	924.1	923.1	922.1	923.1	924.1	925.1	926.0	926.2	925.6	924.9
167.5°	939.9	938.9	937.9	936.8	937.9	938.9	939.9	940.9	940.9	940.0	939.0
170°	948.1	947.0	945.7	944.6	945.7	947.0	948.1	949.3	949.4	948.4	947.4
172.5°	954.3	953.2	952.2	951.2	952.2	953.2	954.3	955.3	955.3	954.3	953.3
175°	960.8	959.7	958.5	957.4	958.5	959.7	960.8	962.0	962.1	961.1	960.1
177.5°	963.7	962.8	961.9	960.9	961.9	962.8	963.7	964.6	964.7	963.9	963.1
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	525.7	528.0	530.7	532.8	536.5	538.2	540.3	541.9	544.9	547.8	551.1
5°	490.3	494.2	499.6	505.4	512.2	516.8	523.4	527.4	535.3	542.5	549.6
7.5°	458.2	463.0	470.6	478.1	487.0	494.9	503.1	512.2	522.3	534.3	544.2
10°	436.2	442.6	450.8	460.2	470.9	480.2	491.2	501.0	513.4	527.4	540.5
12.5°	418.6	424.1	433.2	442.2	453.7	465.1	476.5	489.4	503.8	519.4	535.7
15°	394.4	399.0	406.5	418.9	430.5	441.7	458.8	470.9	489.1	506.3	526.2
17.5°	373.7	379.5	385.8	396.4	408.5	422.4	437.7	452.9	470.4	492.3	514.6
20°	361.0	365.7	372.8	381.0	393.8	407.9	422.3	437.8	459.2	481.9	505.9
22.5°	347.2	352.2	360.4	369.3	380.1	393.5	409.5	426.4	448.8	471.0	497.2
25°	330.9	334.4	341.8	349.8	360.5	371.9	388.5	407.2	429.4	454.8	481.4
27.5°	315.6	318.6	325.4	332.3	342.0	355.6	370.4	389.3	410.2	436.0	465.4
30°	304.5	307.8	313.9	321.3	330.6	342.5	357.7	375.5	397.9	423.0	453.8
32.5°	295.0	297.9	302.5	309.9	319.1	330.6	344.7	362.7	385.2	410.7	441.0
35°	280.2	283.5	287.0	292.9	300.7	311.9	327.4	344.5	365.9	390.6	418.4
37.5°	265.6	269.1	272.3	277.5	284.7	294.6	307.9	325.7	345.1	368.9	395.6
40°	256.4	259.2	261.9	267.4	274.7	284.0	296.4	312.3	332.8	355.0	377.1
42.5°	247.3	249.9	252.1	257.0	263.7	272.6	284.4	299.9	318.9	339.6	359.2
45°	232.9	234.5	237.1	241.3	246.6	254.8	266.2	280.0	296.1	315.7	330.4
47.5°	217.3	219.8	222.0	225.6	230.0	238.0	249.0	260.7	275.4	289.9	300.2
50°	205.3	207.9	211.0	214.5	218.6	226.1	236.1	248.0	260.4	271.7	280.4
52.5°	194.1	196.5	199.8	203.1	208.2	214.5	223.1	233.7	245.9	253.9	261.3
55°	177.5	178.7	182.5	185.7	190.7	195.3	204.0	213.3	220.8	226.8	232.9
57.5°	160.7	162.2	164.4	167.3	172.2	177.6	183.7	192.0	196.3	199.4	204.2
60°	149.8	150.3	151.7	155.2	159.0	163.8	170.8	176.6	180.0	182.5	186.4
62.5°	137.8	137.9	140.3	142.9	145.6	151.0	156.6	161.4	164.0	165.3	169.1
65°	121.1	120.7	122.0	124.1	127.4	130.9	135.8	140.0	139.8	141.2	143.5
67.5°	104.0	103.5	103.5	105.5	108.2	111.3	114.6	117.1	117.1	119.0	120.2
70°	92.4	91.0	91.9	93.6	94.7	97.4	101.1	102.0	102.2	103.1	104.3
72.5°	80.5	80.0	80.7	81.4	82.2	84.2	87.5	88.0	88.1	88.6	90.5
75°	63.9	63.5	63.0	63.7	64.6	66.0	67.2	68.2	67.9	68.2	69.6
77.5°	48.0	46.7	46.4	46.8	47.0	47.9	49.1	49.0	49.2	49.2	50.7
80°	38.1	36.2	36.0	36.0	36.2	36.7	37.1	37.6	36.9	37.6	38.1
82.5°	28.0	26.9	26.8	26.6	26.7	26.8	27.1	27.3	27.2	27.5	27.8
85°	15.5	14.9	14.2	14.7	14.4	13.7	14.2	13.5	13.3	13.5	13.7
87.5°	7.8	7.8	7.2	7.0	6.6	6.5	5.9	5.5	4.9	4.8	5.2
90°	12.8	12.0	10.8	9.7	8.5	7.4	6.1	4.7	3.4	2.1	0.7
92.5°	29.9	28.8	27.4	26.0	24.5	23.0	21.9	20.9	20.0	19.1	18.2
95°	58.9	57.8	56.0	54.4	52.7	51.1	50.1	49.7	49.4	49.1	48.8
97.5°	93.0	91.9	89.6	87.4	85.0	82.7	81.5	81.4	81.2	81.1	81.0
100°	116.2	114.7	112.5	110.4	108.2	106.0	104.9	104.9	104.9	104.9	104.9
102.5°	140.4	138.7	137.5	136.5	135.4	134.3	133.4	132.7	132.1	131.4	130.8
105°	180.2	179.2	178.1	177.1	176.2	175.2	174.3	173.4	172.6	171.8	171.0
107.5°	223.0	222.5	221.8	221.0	220.3	219.4	218.6	217.8	217.0	216.1	215.3
110°	252.4	251.9	251.4	250.9	250.3	249.8	249.2	248.4	247.5	246.7	245.9



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	282.2	281.9	281.2	280.6	279.9	279.3	278.8	278.4	277.9	277.5	277.1
115°	327.4	327.6	327.3	326.9	326.6	326.3	325.8	325.1	324.5	323.8	323.2
117.5°	372.1	372.0	371.7	371.4	371.1	370.8	370.5	370.2	369.9	369.6	369.3
120°	402.5	402.5	402.4	402.2	402.0	401.9	401.4	400.6	399.7	398.9	398.1
122.5°	432.4	432.5	432.1	431.7	431.2	430.8	430.5	430.2	429.9	429.6	429.3
125°	476.5	476.8	476.7	476.5	476.3	476.2	475.5	474.5	473.5	472.5	471.5
127.5°	519.8	520.0	519.8	519.6	519.4	519.2	518.8	518.3	517.7	517.1	516.5
130°	548.6	548.8	548.5	548.1	547.8	547.4	546.8	546.0	545.2	544.3	543.5
132.5°	576.2	576.3	576.4	576.4	576.5	576.6	575.9	574.6	573.2	571.9	570.5
135°	618.4	618.4	618.3	618.1	617.9	617.8	617.2	616.2	615.2	614.2	613.2
137.5°	659.6	659.4	659.0	658.6	658.3	657.9	657.3	656.3	655.3	654.4	653.4
140°	685.5	685.2	684.7	684.2	683.7	683.2	682.6	681.7	680.9	680.0	679.2
142.5°	711.1	710.9	710.3	709.7	709.1	708.4	707.8	707.1	706.4	705.7	705.0
145°	748.2	748.2	747.7	747.2	746.7	746.2	745.6	744.9	744.3	743.6	743.0
147.5°	781.8	781.4	781.0	780.6	780.2	779.8	779.5	779.1	778.7	778.4	778.0
150°	803.7	803.7	802.9	802.3	801.6	801.0	800.7	800.9	801.0	801.2	801.4
152.5°	823.2	822.8	822.5	822.3	822.0	821.7	821.5	821.3	821.0	820.8	820.6
155°	851.5	850.9	850.7	850.5	850.4	850.2	850.1	850.1	850.1	850.1	850.1
157.5°	876.3	875.7	875.5	875.3	875.1	874.9	875.0	875.5	875.8	876.2	876.6
160°	891.3	890.6	890.4	890.3	890.1	889.9	890.1	890.6	891.1	891.6	892.1
162.5°	905.2	904.4	904.3	904.3	904.3	904.2	904.4	904.8	905.1	905.5	905.9
165°	924.2	923.6	923.4	923.2	923.1	922.9	923.0	923.3	923.7	924.0	924.3
167.5°	938.0	937.0	937.0	937.0	937.0	937.0	937.3	938.0	938.6	939.3	940.0
170°	946.3	945.3	945.3	945.3	945.3	945.3	945.6	946.3	947.0	947.7	948.4
172.5°	952.3	951.3	951.3	951.3	951.3	951.3	951.7	952.3	953.0	953.6	954.3
175°	959.1	958.1	958.1	958.1	958.1	958.1	958.4	959.1	959.8	960.4	961.1
177.5°	962.3	961.5	961.7	961.8	961.9	962.1	962.4	962.9	963.4	964.0	964.5
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	552.8	555.3	557.0	560.2	562.8	564.3	565.6	566.7	568.0	569.2	572.4
5°	556.3	562.4	567.5	575.4	582.7	588.2	594.3	599.7	604.1	610.5	615.3
7.5°	554.7	565.5	576.8	589.2	601.7	613.3	624.1	634.1	643.2	654.2	663.9
10°	553.3	567.9	582.4	599.1	616.0	630.5	644.0	657.8	667.8	681.9	693.8
12.5°	552.2	569.5	586.9	606.8	625.5	646.0	664.0	674.1	689.3	700.5	714.7
15°	547.4	570.3	594.3	616.7	643.4	662.3	678.1	697.7	712.0	726.2	741.5
17.5°	539.0	564.9	591.8	621.2	646.6	666.9	687.4	706.3	723.3	742.4	761.5
20°	535.0	561.0	591.8	621.9	646.8	668.0	689.0	709.8	728.5	753.1	775.2
22.5°	526.8	558.2	586.5	615.9	641.6	664.7	688.5	712.1	736.9	764.6	792.3
25°	512.2	543.9	574.0	603.0	628.8	657.8	683.3	714.8	746.5	783.2	817.7
27.5°	497.0	527.4	554.9	582.9	613.1	645.9	678.8	714.6	756.2	802.4	851.1
30°	484.6	513.4	540.2	568.9	600.4	637.2	673.5	715.9	764.0	816.0	873.9
32.5°	470.3	496.8	522.8	553.2	587.5	626.4	668.6	715.2	773.0	832.0	891.6
35°	445.7	467.9	494.7	527.1	565.8	610.5	659.2	714.3	780.5	848.5	898.6
37.5°	416.6	437.2	465.4	501.0	541.6	589.5	647.3	712.7	783.0	837.2	853.3
40°	396.9	416.1	445.5	482.3	523.8	574.5	637.9	707.0	775.2	809.7	796.4
42.5°	376.0	396.1	424.7	461.2	505.9	561.1	626.2	695.3	752.5	765.5	719.5
45°	343.1	363.8	392.0	428.9	477.0	536.7	604.6	667.4	700.2	676.7	605.5
47.5°	312.4	331.8	358.0	396.1	445.7	507.5	572.8	622.9	625.5	569.3	493.2
50°	291.4	309.4	335.8	373.9	423.0	485.6	544.6	584.1	566.3	502.6	429.6
52.5°	270.9	288.5	314.5	352.1	400.8	458.2	513.1	540.8	507.4	441.9	379.6
55°	241.3	256.7	282.2	316.9	363.0	416.3	462.9	472.5	429.1	364.8	314.1
57.5°	212.4	226.7	249.8	281.9	324.2	371.2	407.8	405.7	359.8	304.6	264.4
60°	192.8	206.7	227.3	258.5	297.1	337.7	368.9	361.4	316.0	268.3	234.5
62.5°	175.2	187.7	207.1	234.5	269.6	307.2	332.9	321.8	277.3	235.7	208.9
65°	149.4	159.9	176.4	199.8	228.9	259.9	279.8	265.6	227.5	195.1	173.6
67.5°	124.6	133.1	146.9	165.6	190.5	215.4	227.4	213.2	182.7	159.1	143.1
70°	109.0	116.4	127.1	143.7	165.4	186.4	195.5	182.7	156.5	136.2	124.8
72.5°	93.3	99.5	108.9	123.8	141.2	159.4	167.3	155.1	133.6	116.4	105.8
75°	72.1	76.3	82.8	93.1	106.8	121.4	125.7	115.0	101.3	88.5	81.4
77.5°	51.6	55.1	60.1	66.6	76.3	85.5	89.4	83.2	72.6	64.4	58.7
80°	39.7	41.5	45.7	51.1	58.8	64.6	67.2	63.2	55.7	49.7	45.2
82.5°	28.3	30.2	32.6	37.1	42.0	45.9	48.7	46.0	40.7	35.9	33.3
85°	13.7	14.9	16.4	18.2	21.9	24.2	24.0	22.4	20.3	18.5	17.1
87.5°	5.3	5.8	6.6	7.8	8.6	9.5	10.1	10.0	9.5	9.1	8.7
90°	2.1	3.4	4.7	6.1	7.4	8.5	9.7	10.8	12.0	12.8	13.6
92.5°	19.1	20.0	20.9	21.9	23.0	24.5	26.0	27.4	28.8	29.9	31.0
95°	49.1	49.4	49.7	50.1	51.1	52.7	54.4	56.0	57.8	58.9	60.1
97.5°	81.1	81.2	81.4	81.5	82.7	85.0	87.4	89.6	91.9	93.0	94.1
100°	104.9	104.9	104.9	104.9	106.0	108.2	110.4	112.5	114.7	116.2	117.6
102.5°	131.4	132.1	132.7	133.4	134.3	135.4	136.5	137.5	138.7	140.4	142.0
105°	171.8	172.6	173.4	174.3	175.2	176.2	177.1	178.1	179.2	180.2	181.2
107.5°	216.1	217.0	217.8	218.6	219.4	220.3	221.0	221.8	222.5	223.0	223.5
110°	246.7	247.5	248.4	249.2	249.8	250.3	250.9	251.4	251.9	252.4	252.9





TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	277.5	277.9	278.4	278.8	279.3	279.9	280.6	281.2	281.9	282.2	282.4
115°	323.8	324.5	325.1	325.8	326.3	326.6	326.9	327.3	327.6	327.4	327.3
117.5°	369.6	369.9	370.2	370.5	370.8	371.1	371.4	371.7	372.0	372.1	372.2
120°	398.9	399.7	400.6	401.4	401.9	402.0	402.2	402.4	402.5	402.5	402.5
122.5°	429.6	429.9	430.2	430.5	430.8	431.2	431.7	432.1	432.5	432.4	432.3
125°	472.5	473.5	474.5	475.5	476.2	476.3	476.5	476.7	476.8	476.5	476.2
127.5°	517.1	517.7	518.3	518.8	519.2	519.4	519.6	519.8	520.0	519.8	519.7
130°	544.3	545.2	546.0	546.8	547.4	547.8	548.1	548.5	548.8	548.6	548.5
132.5°	571.9	573.2	574.6	575.9	576.6	576.5	576.4	576.4	576.3	576.2	576.0
135°	614.2	615.2	616.2	617.2	617.8	617.9	618.1	618.3	618.4	618.4	618.4
137.5°	654.4	655.3	656.3	657.3	657.9	658.3	658.6	659.0	659.4	659.6	659.8
140°	680.0	680.9	681.7	682.6	683.2	683.7	684.2	684.7	685.2	685.5	685.9
142.5°	705.7	706.4	707.1	707.8	708.4	709.1	709.7	710.3	710.9	711.1	711.3
145°	743.6	744.3	744.9	745.6	746.2	746.7	747.2	747.7	748.2	748.2	748.2
147.5°	778.4	778.7	779.1	779.5	779.8	780.2	780.6	781.0	781.4	781.8	782.2
150°	801.2	801.0	800.9	800.7	801.0	801.6	802.3	802.9	803.7	803.7	803.7
152.5°	820.8	821.0	821.3	821.5	821.7	822.0	822.3	822.5	822.8	823.2	823.6
155°	850.1	850.1	850.1	850.1	850.2	850.4	850.5	850.7	850.9	851.5	852.2
157.5°	876.2	875.8	875.5	875.0	874.9	875.1	875.3	875.5	875.7	876.3	877.0
160°	891.6	891.1	890.6	890.1	889.9	890.1	890.3	890.4	890.6	891.3	891.9
162.5°	905.5	905.1	904.8	904.4	904.2	904.3	904.3	904.3	904.4	905.2	906.1
165°	924.0	923.7	923.3	923.0	922.9	923.1	923.2	923.4	923.6	924.2	924.9
167.5°	939.3	938.6	938.0	937.3	937.0	937.0	937.0	937.0	937.0	938.0	939.0
170°	947.7	947.0	946.3	945.6	945.3	945.3	945.3	945.3	945.3	946.3	947.4
172.5°	953.6	953.0	952.3	951.7	951.3	951.3	951.3	951.3	951.3	952.3	953.3
175°	960.4	959.8	959.1	958.4	958.1	958.1	958.1	958.1	958.1	959.1	960.1
177.5°	964.0	963.4	962.9	962.4	962.1	961.9	961.8	961.7	961.5	962.3	963.1
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3	963.3



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	549.8	549.8	549.8	549.8	549.8	549.8	549.8
2.5°	575.0	576.4	579.7	578.6	580.0	580.8	581.5
5°	621.4	628.8	632.2	631.7	636.6	635.4	634.2
7.5°	673.9	681.7	686.1	691.6	694.7	695.0	697.7
10°	703.6	713.8	718.0	723.9	727.6	729.7	729.4
12.5°	726.3	734.4	743.8	746.6	751.6	754.4	753.4
15°	753.8	766.6	776.4	781.2	787.6	789.4	791.9
17.5°	778.2	795.4	806.8	822.0	827.8	831.3	829.2
20°	796.7	819.3	830.7	848.9	859.0	864.3	862.4
22.5°	818.5	843.0	864.1	879.9	895.1	902.4	903.9
25°	856.0	889.5	920.6	941.3	960.2	964.6	974.4
27.5°	897.8	937.4	970.6	992.4	1005.5	1010.5	1013.6
30°	924.0	963.5	988.5	1002.5	1006.6	1006.2	1005.7
32.5°	937.0	961.6	966.4	962.5	952.9	944.7	936.2
35°	918.7	900.3	872.7	837.3	811.1	784.8	782.1
37.5°	826.3	767.3	721.4	670.2	640.8	622.5	609.9
40°	739.2	672.3	616.7	573.6	543.5	531.6	519.9
42.5°	644.8	580.8	531.6	495.5	472.9	459.7	450.5
45°	523.8	467.4	428.9	402.7	384.8	374.6	368.7
47.5°	429.3	387.5	354.8	335.9	323.6	315.6	315.6
50°	378.5	338.6	316.9	301.9	291.2	284.9	286.1
52.5°	333.5	303.7	285.2	272.7	264.7	260.8	260.6
55°	278.8	257.4	245.3	236.1	230.8	226.3	227.3
57.5°	238.5	220.5	212.3	204.7	201.0	199.2	196.6
60°	213.5	199.5	192.5	186.4	182.7	181.3	178.7
62.5°	191.3	180.3	173.5	168.5	165.2	164.7	162.7
65°	160.8	152.4	146.3	144.0	140.5	139.6	139.6
67.5°	132.5	126.5	121.8	119.7	118.2	118.4	117.2
70°	114.8	109.9	106.8	104.5	103.4	103.6	102.7
72.5°	100.5	94.9	92.3	90.9	89.4	90.0	89.6
75°	76.0	73.3	71.9	70.5	69.6	69.1	68.6
77.5°	55.8	53.4	52.3	51.5	51.7	50.5	51.4
80°	43.1	41.1	40.4	39.2	39.0	39.0	38.8
82.5°	31.6	30.4	29.9	29.0	28.5	28.9	28.3
85°	16.4	15.5	15.1	15.1	14.7	14.2	15.5
87.5°	8.9	8.3	8.4	8.4	8.5	8.4	8.1
90°	14.5	15.3	16.0	16.5	17.0	17.5	18.0
92.5°	32.1	33.2	33.9	34.3	34.6	35.0	35.3
95°	61.2	62.4	63.1	63.5	63.8	64.1	64.4
97.5°	95.2	96.3	96.9	97.1	97.4	97.6	97.8
100°	119.2	120.7	121.6	122.0	122.3	122.6	122.9
102.5°	143.6	145.2	146.2	146.7	147.2	147.6	148.1
105°	182.2	183.2	183.9	184.4	184.9	185.4	185.9
107.5°	224.0	224.5	224.7	224.7	224.7	224.6	224.6
110°	253.4	253.9	254.1	253.9	253.7	253.6	253.4



TEST NUMBER: P333347-840

CATALOG NUMBER: S125DIW-S375D770U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	282.6	282.8	282.8	282.5	282.2	281.9	281.6
115°	327.1	326.9	326.8	326.6	326.5	326.3	326.1
117.5°	372.3	372.5	372.2	371.6	370.9	370.2	369.6
120°	402.5	402.5	402.2	401.6	400.9	400.2	399.6
122.5°	432.1	432.0	431.7	431.1	430.6	430.1	429.6
125°	475.7	475.4	475.2	475.0	474.8	474.7	474.5
127.5°	519.5	519.3	519.1	518.8	518.4	518.1	517.8
130°	548.3	548.1	547.9	547.5	547.1	546.8	546.5
132.5°	575.8	575.7	575.3	574.9	574.4	574.0	573.5
135°	618.4	618.4	618.1	617.4	616.8	616.1	615.5
137.5°	660.0	660.2	659.8	659.0	658.2	657.4	656.5
140°	686.2	686.5	686.3	685.5	684.6	683.8	683.0
142.5°	711.6	711.8	711.4	710.6	709.8	708.9	708.1
145°	748.2	748.2	747.9	747.4	746.9	746.4	745.9
147.5°	782.6	783.0	782.6	781.5	780.4	779.3	778.2
150°	803.7	803.7	803.4	803.1	802.8	802.4	802.1
152.5°	824.0	824.5	824.4	823.7	823.1	822.5	821.9
155°	852.8	853.5	853.4	852.6	851.8	850.9	850.1
157.5°	877.6	878.3	878.1	877.0	875.9	874.7	873.6
160°	892.6	893.2	893.2	892.3	891.5	890.7	889.9
162.5°	906.8	907.6	907.6	906.6	905.5	904.6	903.6
165°	925.6	926.2	926.0	925.1	924.1	923.1	922.1
167.5°	940.0	940.9	940.9	939.9	938.9	937.9	936.8
170°	948.4	949.4	949.3	948.1	947.0	945.7	944.6
172.5°	954.3	955.3	955.3	954.3	953.2	952.2	951.2
175°	961.1	962.1	962.0	960.8	959.7	958.5	957.4
177.5°	963.9	964.7	964.6	963.7	962.8	961.9	960.9
180°	963.3	963.3	963.3	963.3	963.3	963.3	963.3

(END OF REPORT)