

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333388-840

Luminaire Tested: **S125DIW-S610D1340U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333388-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1340U840-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7970.5 lumens
Efficiency: N/A
Efficacy: 148.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	78	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	24	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5837	5837	5837	5837
5°	6760	5857	5128	5857
10°	7864	5827	4494	5827
15°	8705	5784	4145	5784
20°	9745	5716	3865	5716
25°	11416	5640	3729	5640
30°	12331	5565	3610	5565
35°	10138	5423	3533	5423
40°	7206	5227	3447	5227
45°	5536	4961	3399	4961
50°	4725	4633	3392	4633
55°	4208	4310	3422	4310
60°	3796	3959	3509	3959
65°	3506	3605	3599	3605
70°	3186	3238	3652	3238
75°	2815	2852	3618	2852
80°	2369	2325	3310	2325
85°	1875	1675	2675	1675



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.1
10°-20°	259.1	3.3
20°-30°	420.7	5.3
30°-40°	513.1	6.4
40°-50°	466.8	5.9
50°-60°	371.8	4.7
60°-70°	259.0	3.2
70°-80°	138.1	1.7
80°-90°	38.5	0.5
90°-100°	64.1	0.8
100°-110°	395.0	5.0
110°-120°	716.5	9.0
120°-130°	919.5	11.5
130°-140°	989.0	12.4
140°-150°	928.3	11.6
150°-160°	750.9	9.4
160°-170°	485.7	6.1
170°-180°	167.5	2.1
0°-30°	766.7	9.6
0°-40°	1279.9	16.1
0°-60°	2118.5	26.6
0°-90°	2554.1	32.0
90°-120°	1175.6	14.7
90°-150°	4012.4	50.3
90°-180°	5416.0	68.0
0°-180°	7970.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	904	904	904	904	904	
5°	1043	903	791	903	1043	105
15°	1302	865	620	865	1302	373
25°	1602	791	523	791	1602	732
35°	1286	688	448	688	1286	787
45°	606	543	372	543	606	485
55°	374	383	304	383	374	337
65°	229	236	236	236	229	228
75°	113	114	145	114	113	121
85°	25	23	36	23	25	30
90°	31	1	31	1	31	14
95°	28	74	28	74	28	23
105°	388	384	388	384	388	351
115°	716	722	716	722	716	711
125°	1026	1026	1026	1026	1026	913
135°	1275	1280	1275	1280	1275	984
145°	1480	1484	1480	1484	1480	925
155°	1623	1634	1623	1634	1623	748
165°	1716	1725	1716	1725	1716	484
175°	1756	1764	1756	1764	1756	167
180°	1764	1764	1764	1764	1764	



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	956.0	954.7	953.5	951.1	952.9	947.7	945.2	941.0	935.7	933.9	931.7
5°	1042.7	1044.6	1046.5	1038.4	1039.3	1033.9	1021.6	1011.6	1003.6	993.2	985.9
7.5°	1147.0	1142.5	1142.2	1136.9	1127.9	1120.7	1107.8	1091.4	1075.5	1057.4	1042.5
10°	1199.2	1199.6	1196.2	1190.0	1180.4	1173.5	1156.6	1140.5	1121.0	1097.9	1081.5
12.5°	1238.5	1240.1	1235.8	1227.5	1222.7	1207.3	1194.1	1174.9	1151.7	1133.3	1108.1
15°	1302.0	1297.8	1294.7	1284.3	1276.3	1260.2	1239.1	1219.1	1193.9	1170.4	1147.0
17.5°	1363.2	1366.7	1360.9	1351.4	1326.5	1307.6	1279.3	1252.0	1220.4	1189.1	1161.1
20°	1417.9	1421.0	1412.1	1395.6	1365.7	1346.9	1309.7	1274.3	1238.0	1197.7	1167.0
22.5°	1486.0	1483.6	1471.7	1446.5	1420.7	1385.8	1345.6	1302.6	1257.0	1211.4	1170.6
25°	1602.0	1585.9	1578.6	1547.5	1513.4	1462.4	1407.1	1344.2	1287.5	1227.2	1175.1
27.5°	1666.3	1661.2	1653.1	1631.4	1595.6	1541.1	1475.9	1399.3	1319.1	1243.1	1174.8
30°	1653.5	1654.2	1655.0	1648.0	1625.1	1584.0	1519.1	1436.6	1341.5	1256.0	1177.0
32.5°	1539.2	1553.2	1566.6	1582.4	1588.8	1580.9	1540.3	1465.8	1368.0	1270.7	1175.7
35°	1285.9	1290.1	1333.5	1376.4	1434.7	1480.1	1510.4	1477.3	1394.8	1283.2	1174.3
37.5°	1002.6	1023.4	1053.4	1102.0	1186.1	1261.4	1358.4	1402.9	1376.2	1287.3	1171.5
40°	854.7	873.9	893.4	942.9	1013.9	1105.2	1215.3	1309.3	1331.2	1274.3	1162.4
42.5°	740.5	755.8	777.5	814.7	873.9	954.8	1060.1	1182.9	1258.4	1237.0	1143.1
45°	606.1	615.7	632.6	662.2	705.1	768.4	861.2	995.5	1112.5	1151.2	1097.1
47.5°	518.8	518.8	531.9	552.3	583.3	637.0	705.7	810.9	935.8	1028.3	1024.0
50°	470.3	468.4	478.8	496.4	521.0	556.6	622.3	706.3	826.4	931.1	960.2
52.5°	428.6	428.8	435.2	448.2	468.8	499.3	548.3	624.0	726.6	834.0	889.0
55°	373.7	372.1	379.4	388.2	403.2	423.1	458.5	516.3	599.6	705.5	776.8
57.5°	323.4	327.5	330.4	336.6	349.0	362.3	392.1	434.6	500.7	591.6	667.0
60°	293.9	298.1	300.3	306.5	316.5	328.0	351.0	385.6	441.2	519.5	594.2
62.5°	267.4	270.7	271.6	277.0	285.2	296.4	314.5	343.5	387.5	455.9	529.2
65°	229.4	229.4	231.0	236.7	240.5	250.5	264.3	285.4	320.7	374.1	436.6
67.5°	192.7	194.6	194.2	196.7	200.3	208.0	217.9	235.3	261.5	300.3	350.4
70°	168.7	170.4	170.0	171.9	175.7	180.7	188.7	205.2	224.0	257.4	300.3
72.5°	147.3	147.9	146.9	149.5	151.8	156.1	165.1	173.9	191.5	219.6	255.0
75°	112.8	113.5	114.3	115.8	118.2	120.5	125.0	133.9	145.4	166.5	189.1
77.5°	84.5	83.1	84.9	84.7	86.0	87.8	91.8	96.5	105.9	119.3	136.8
80°	63.7	64.0	64.0	64.4	66.3	67.6	71.0	74.4	81.7	91.7	103.9
82.5°	46.5	47.5	46.9	47.6	49.2	50.0	51.9	54.7	59.0	66.9	75.7
85°	25.3	23.4	24.1	24.9	24.9	25.3	26.9	28.0	30.3	33.3	36.9
87.5°	13.6	14.0	14.2	14.0	14.1	13.9	14.8	14.5	15.2	15.9	16.7
90°	31.4	30.5	29.6	28.8	27.9	26.8	25.2	23.8	22.4	20.9	18.9
92.5°	29.3	28.9	28.5	28.1	27.7	26.8	25.2	23.8	22.4	20.9	19.1
95°	27.5	27.5	27.5	27.5	27.5	26.8	25.2	23.8	22.4	20.9	31.9
97.5°	27.5	27.5	27.5	27.5	27.5	31.5	39.8	48.0	56.1	64.3	86.1
100°	27.5	28.6	29.8	30.9	32.1	54.3	97.7	140.9	184.2	227.5	226.3
102.5°	164.5	184.2	204.0	223.8	243.5	257.5	265.7	273.9	282.1	290.2	289.5
105°	388.3	388.6	388.9	389.2	389.5	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	489.6	490.4	491.3	492.1	493.0	493.4	493.4	493.3	493.2	493.2	492.6
110°	559.7	559.4	559.1	558.8	558.5	558.8	559.7	560.5	561.4	562.2	561.7



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	622.4	622.8	623.2	623.6	624.0	624.8	625.9	626.9	628.0	629.1	628.8
115°	716.5	718.2	720.0	721.8	723.5	725.0	726.1	727.3	728.4	729.6	729.3
117.5°	817.0	817.7	818.5	819.2	819.9	821.1	822.6	824.2	825.7	827.2	826.1
120°	878.7	880.1	881.5	883.0	884.4	885.4	886.1	886.7	887.3	887.8	887.0
122.5°	937.3	938.9	940.6	942.3	943.9	945.1	945.6	946.2	946.8	947.5	947.1
125°	1026.4	1027.2	1028.1	1029.1	1029.9	1030.9	1032.1	1033.2	1034.4	1035.5	1035.5
127.5°	1101.5	1103.6	1105.8	1107.9	1110.0	1111.5	1112.1	1112.8	1113.4	1114.0	1114.2
130°	1155.9	1157.3	1158.7	1160.2	1161.6	1162.9	1163.7	1164.6	1165.5	1166.3	1166.0
132.5°	1206.1	1207.5	1209.0	1210.4	1211.8	1212.6	1212.8	1213.0	1213.3	1213.4	1214.1
135°	1274.9	1276.6	1278.3	1280.1	1281.8	1282.9	1283.5	1284.1	1284.8	1285.3	1285.9
137.5°	1343.8	1345.3	1346.9	1348.4	1349.9	1350.6	1350.5	1350.4	1350.3	1350.2	1350.7
140°	1384.6	1386.4	1388.2	1389.9	1391.6	1392.2	1391.6	1391.1	1390.5	1389.9	1390.2
142.5°	1423.4	1425.1	1426.8	1428.6	1430.4	1431.2	1431.1	1430.9	1430.8	1430.7	1430.3
145°	1480.2	1481.9	1483.6	1485.3	1487.1	1487.8	1487.5	1487.2	1486.9	1486.6	1486.6
147.5°	1526.9	1529.0	1531.1	1533.2	1535.3	1536.2	1535.8	1535.5	1535.1	1534.8	1534.4
150°	1557.2	1559.5	1561.9	1564.2	1566.5	1567.4	1566.8	1566.3	1565.7	1565.1	1564.5
152.5°	1585.5	1587.6	1589.7	1591.7	1593.9	1594.6	1594.1	1593.5	1592.9	1592.3	1591.7
155°	1622.7	1625.0	1627.3	1629.6	1631.9	1632.6	1631.7	1630.9	1630.0	1629.2	1628.6
157.5°	1653.8	1656.1	1658.4	1660.7	1663.0	1663.8	1662.8	1661.9	1660.9	1660.0	1660.0
160°	1673.6	1676.0	1678.3	1680.6	1682.9	1683.5	1682.3	1681.2	1680.0	1678.9	1678.6
162.5°	1691.4	1693.9	1696.5	1699.1	1701.6	1702.1	1700.5	1698.8	1697.2	1695.6	1695.3
165°	1715.5	1717.8	1720.1	1722.4	1724.7	1725.1	1723.3	1721.5	1719.8	1718.1	1717.8
167.5°	1732.2	1734.8	1737.5	1740.0	1742.6	1742.9	1740.8	1738.8	1736.7	1734.5	1734.2
170°	1741.6	1744.2	1746.9	1749.5	1752.1	1752.2	1749.9	1747.6	1745.2	1742.9	1742.6
172.5°	1747.9	1750.5	1753.1	1755.8	1758.4	1758.6	1756.6	1754.4	1752.3	1750.2	1749.7
175°	1756.0	1758.6	1761.2	1763.8	1766.5	1766.6	1764.2	1761.9	1759.6	1757.3	1757.1
177.5°	1760.7	1762.5	1764.4	1766.3	1768.2	1768.3	1766.7	1765.0	1763.4	1761.7	1761.5
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	929.9	927.8	925.3	921.0	915.7	913.0	908.8	905.9	900.4	895.9	890.9
5°	977.0	967.1	958.0	946.0	933.0	924.5	914.5	903.4	891.9	880.0	867.0
7.5°	1025.9	1008.4	989.2	968.5	948.4	929.8	912.0	894.6	878.4	858.7	842.0
10°	1058.8	1036.5	1012.8	984.7	957.6	933.7	909.6	888.5	867.0	843.9	823.6
12.5°	1091.7	1062.0	1028.4	997.6	964.9	936.2	907.8	880.8	853.8	828.3	804.7
15°	1114.8	1088.7	1057.6	1013.9	977.0	937.6	900.0	865.1	832.4	804.1	774.2
17.5°	1130.0	1096.5	1063.1	1021.2	972.9	928.7	886.1	846.2	809.4	773.4	744.6
20°	1132.9	1098.3	1063.4	1022.4	972.9	922.2	879.7	831.7	792.1	755.0	719.6
22.5°	1132.0	1092.8	1054.8	1012.5	964.3	917.7	866.2	817.3	774.4	737.8	700.9
25°	1123.3	1081.5	1033.9	991.3	943.7	894.2	842.0	791.4	747.7	705.9	669.4
27.5°	1116.0	1061.8	1007.9	958.3	912.3	867.0	817.1	765.2	716.7	674.3	640.0
30°	1107.1	1047.6	987.0	935.2	888.1	843.9	796.8	746.2	695.5	654.1	617.2
32.5°	1099.1	1029.9	965.9	909.5	859.6	816.7	773.2	725.0	675.3	633.2	596.4
35°	1083.8	1003.6	930.3	866.6	813.2	769.2	732.8	687.8	642.2	601.5	566.2
37.5°	1064.2	969.1	890.4	823.6	765.2	718.7	684.8	650.4	606.5	567.3	535.4
40°	1048.8	944.5	861.2	792.9	732.4	684.0	652.6	620.0	583.5	547.0	513.3
42.5°	1029.5	922.4	831.7	758.3	698.3	651.2	618.1	590.5	558.4	524.3	493.0
45°	994.0	882.3	784.2	705.1	644.5	598.0	563.9	543.2	519.1	486.9	460.4
47.5°	941.7	834.2	732.7	651.1	588.5	545.5	513.5	493.6	476.7	452.7	428.7
50°	895.3	798.3	695.5	614.6	552.0	508.7	479.2	461.1	446.6	428.1	407.8
52.5°	843.5	753.2	659.0	579.0	517.1	474.3	445.4	429.5	417.4	404.1	384.2
55°	761.1	684.4	596.9	521.0	463.8	422.0	396.7	382.8	372.8	362.9	350.6
57.5°	670.3	610.4	532.8	463.4	410.8	372.7	349.1	335.7	327.9	322.8	315.6
60°	606.5	555.1	488.4	425.1	373.7	339.9	316.9	306.5	300.0	295.8	290.4
62.5°	547.2	505.0	443.2	385.5	340.5	308.6	288.0	278.0	271.8	269.7	265.2
65°	460.0	427.4	376.4	328.4	290.0	262.8	245.5	235.9	232.1	229.7	230.1
67.5°	374.0	354.1	313.2	272.3	241.6	218.7	204.9	197.5	195.6	192.6	192.5
70°	321.4	306.5	272.0	236.3	209.0	191.5	179.2	171.5	169.6	168.0	167.6
72.5°	275.1	262.1	232.1	203.5	179.0	163.5	153.4	148.8	145.6	144.7	144.6
75°	206.8	199.4	175.7	153.1	136.2	125.4	118.6	114.3	112.0	111.6	112.0
77.5°	147.0	140.7	125.5	109.5	98.9	90.7	84.8	83.4	80.8	80.9	80.5
80°	110.5	106.2	96.6	84.0	75.2	68.3	65.2	62.5	61.8	60.6	61.8
82.5°	80.1	75.5	69.1	61.0	53.7	49.6	46.5	45.6	45.1	44.6	44.8
85°	39.5	39.9	36.1	29.9	26.9	24.5	22.6	22.6	22.2	21.9	22.2
87.5°	16.9	15.9	14.2	12.8	10.9	9.5	8.7	8.6	8.1	8.3	9.0
90°	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3	3.6	6.0	8.3
92.5°	17.3	15.6	13.7	13.6	15.2	16.9	18.5	20.1	18.5	16.9	15.2
95°	43.0	54.0	65.0	71.0	71.9	72.8	73.6	74.5	73.6	72.8	71.9
97.5°	108.1	129.9	151.7	161.9	160.3	158.8	157.1	155.6	157.1	158.8	160.3
100°	225.2	224.0	222.9	221.9	221.0	220.0	219.2	218.3	219.2	220.0	221.0
102.5°	288.9	288.2	287.5	286.6	285.5	284.4	283.3	282.2	283.3	284.4	285.5
105°	389.6	389.6	389.6	389.1	387.9	386.8	385.6	384.5	385.6	386.8	387.9
107.5°	492.0	491.5	490.9	490.6	490.6	490.6	490.6	490.6	490.6	490.6	490.6
110°	561.1	560.5	559.9	559.7	559.7	559.7	559.7	559.7	559.7	559.7	559.7



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	628.4	628.1	627.8	627.2	626.5	625.9	625.2	624.5	625.2	625.9	626.5
115°	729.0	728.7	728.4	727.6	726.1	724.7	723.2	721.8	723.2	724.7	726.1
117.5°	825.0	823.8	822.7	822.2	822.2	822.3	822.3	822.4	822.3	822.3	822.2
120°	886.1	885.1	884.3	884.0	884.3	884.6	884.9	885.1	884.9	884.6	884.3
122.5°	946.6	946.2	945.8	945.0	943.9	942.8	941.7	940.6	941.7	942.8	943.9
125°	1035.5	1035.5	1035.5	1034.5	1032.5	1030.5	1028.4	1026.4	1028.4	1030.5	1032.5
127.5°	1114.4	1114.5	1114.7	1114.1	1112.6	1111.2	1109.7	1108.2	1109.7	1111.2	1112.6
130°	1165.7	1165.5	1165.2	1164.3	1162.9	1161.3	1159.9	1158.4	1159.9	1161.3	1162.9
132.5°	1214.7	1215.3	1216.0	1215.4	1213.8	1212.0	1210.3	1208.7	1210.3	1212.0	1213.8
135°	1286.5	1287.1	1287.6	1287.1	1285.3	1283.5	1281.8	1280.1	1281.8	1283.5	1285.3
137.5°	1351.2	1351.7	1352.2	1351.7	1350.2	1348.7	1347.2	1345.7	1347.2	1348.7	1350.2
140°	1390.5	1390.8	1391.1	1390.9	1390.3	1389.8	1389.2	1388.6	1389.2	1389.8	1390.3
142.5°	1429.9	1429.5	1429.1	1428.7	1428.4	1427.9	1427.6	1427.2	1427.6	1427.9	1428.4
145°	1486.6	1486.6	1486.6	1486.3	1485.8	1485.2	1484.6	1484.0	1484.6	1485.2	1485.8
147.5°	1534.1	1533.7	1533.4	1533.3	1533.4	1533.5	1533.6	1533.7	1533.6	1533.5	1533.4
150°	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1564.5	1564.0	1563.4
152.5°	1591.1	1590.5	1589.9	1590.3	1591.6	1592.9	1594.2	1595.4	1594.2	1592.9	1591.6
155°	1628.0	1627.4	1626.9	1627.4	1629.2	1630.9	1632.6	1634.4	1632.6	1630.9	1629.2
157.5°	1659.9	1659.8	1659.8	1660.3	1661.3	1662.3	1663.4	1664.5	1663.4	1662.3	1661.3
160°	1678.3	1678.0	1677.7	1678.4	1680.1	1681.9	1683.6	1685.4	1683.6	1681.9	1680.1
162.5°	1695.1	1694.8	1694.5	1695.2	1696.9	1698.6	1700.4	1702.1	1700.4	1698.6	1696.9
165°	1717.5	1717.2	1716.9	1717.7	1719.4	1721.1	1722.8	1724.6	1722.8	1721.1	1719.4
167.5°	1733.9	1733.6	1733.4	1734.1	1736.0	1737.8	1739.6	1741.3	1739.6	1737.8	1736.0
170°	1742.3	1742.0	1741.7	1742.6	1744.6	1746.7	1748.8	1750.8	1748.8	1746.7	1744.6
172.5°	1749.2	1748.7	1748.2	1748.9	1750.9	1753.0	1755.0	1757.1	1755.0	1753.0	1750.9
175°	1756.8	1756.5	1756.2	1756.9	1758.6	1760.4	1762.1	1763.8	1762.1	1760.4	1758.6
177.5°	1761.3	1761.1	1760.8	1761.4	1762.8	1764.2	1765.5	1767.0	1765.5	1764.2	1762.8
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	888.2	884.7	882.0	875.9	872.5	867.9	864.2	868.2	863.9	865.8	863.0
5°	860.5	849.7	842.0	830.9	821.3	812.5	806.0	804.9	801.7	800.2	795.7
7.5°	827.2	813.7	800.5	786.0	773.7	761.2	753.2	746.6	742.3	736.5	732.6
10°	807.5	789.5	774.2	756.5	741.1	727.7	717.0	711.7	706.6	699.3	696.7
12.5°	783.3	764.7	745.9	727.0	712.4	697.3	688.1	680.0	676.6	668.3	667.5
15°	754.2	726.2	707.8	688.6	668.2	656.0	648.3	639.5	635.7	630.0	625.7
17.5°	719.5	694.5	671.5	651.7	634.2	623.9	614.3	608.2	601.7	597.9	591.0
20°	694.4	670.6	647.5	626.4	613.0	601.2	593.5	587.7	580.8	578.9	572.0
22.5°	673.2	646.9	624.8	607.1	592.5	579.1	570.8	566.8	562.1	556.1	554.8
25°	638.7	611.5	592.7	575.0	562.0	549.8	544.0	539.0	534.4	530.2	528.7
27.5°	608.9	584.6	562.3	546.3	535.0	523.8	518.8	512.7	509.3	505.9	501.8
30°	588.1	563.2	543.6	528.3	515.9	506.0	500.6	496.4	493.3	490.3	488.0
32.5°	566.6	543.5	524.5	509.6	497.3	489.8	484.9	482.0	478.6	474.9	472.0
35°	538.3	512.9	494.5	481.4	471.8	466.1	460.7	458.1	454.2	454.2	451.1
37.5°	506.2	484.3	468.1	456.2	447.6	442.4	436.7	434.8	432.3	430.7	429.7
40°	487.2	466.9	451.5	439.6	430.4	426.2	421.6	418.5	417.0	415.1	414.3
42.5°	467.6	448.2	433.4	422.4	414.4	410.8	406.6	404.5	401.3	398.8	398.4
45°	437.7	418.9	405.5	396.7	389.8	385.6	382.8	378.3	376.7	373.7	373.2
47.5°	409.4	391.3	378.2	370.9	364.9	361.4	357.2	352.6	350.8	349.3	349.2
50°	388.2	371.7	359.4	352.5	346.8	341.8	337.6	334.6	333.4	333.4	334.2
52.5°	366.8	352.7	342.2	333.9	328.4	323.1	319.2	317.3	315.6	317.4	318.8
55°	335.3	321.1	313.5	305.4	300.0	293.9	292.0	291.1	290.0	293.1	294.6
57.5°	301.9	292.1	283.1	275.1	270.2	266.7	264.1	263.7	265.8	267.2	272.3
60°	280.8	269.3	261.3	255.1	249.3	247.0	246.3	245.5	247.0	251.3	257.8
62.5°	257.5	248.1	239.4	234.9	230.7	226.8	226.6	227.1	230.1	235.0	241.6
65°	223.3	215.2	209.4	204.1	200.7	198.3	199.1	200.7	204.1	210.7	217.9
67.5°	188.5	183.0	177.8	173.5	170.2	170.2	171.0	173.3	177.3	184.8	191.5
70°	166.1	160.0	155.7	153.8	151.2	149.7	151.9	155.7	159.2	166.1	171.9
72.5°	143.7	138.5	135.2	133.9	132.7	131.5	132.3	136.4	141.1	148.0	154.7
75°	110.5	108.6	106.2	104.7	103.6	104.3	105.1	109.0	112.8	120.1	127.7
77.5°	80.7	78.7	77.3	76.9	76.2	76.6	78.8	81.6	85.4	90.7	96.5
80°	61.0	60.2	59.5	59.1	59.1	59.5	62.5	64.4	67.9	72.9	77.5
82.5°	44.4	43.9	43.8	43.7	44.0	44.1	45.9	48.5	51.3	55.1	59.1
85°	23.4	22.6	23.8	24.1	23.4	24.5	25.3	26.9	28.0	29.9	31.8
87.5°	9.8	10.8	10.9	11.6	12.0	13.1	13.0	14.5	15.5	16.4	16.4
90°	10.6	12.8	14.8	16.9	18.9	20.9	22.4	23.8	25.2	26.8	27.9
92.5°	13.6	13.7	15.6	17.3	19.1	20.9	22.4	23.8	25.2	26.8	27.7
95°	71.0	65.0	54.0	43.0	31.9	20.9	22.4	23.8	25.2	26.8	27.5
97.5°	161.9	151.7	129.9	108.1	86.1	64.3	56.1	48.0	39.8	31.5	27.5
100°	221.9	222.9	224.0	225.2	226.3	227.5	184.2	140.9	97.7	54.3	32.1
102.5°	286.6	287.5	288.2	288.9	289.5	290.2	282.1	273.9	265.7	257.5	243.5
105°	389.1	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.5
107.5°	490.6	490.9	491.5	492.0	492.6	493.2	493.2	493.3	493.4	493.4	493.0
110°	559.7	559.9	560.5	561.1	561.7	562.2	561.4	560.5	559.7	558.8	558.5



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	627.2	627.8	628.1	628.4	628.8	629.1	628.0	626.9	625.9	624.8	624.0
115°	727.6	728.4	728.7	729.0	729.3	729.6	728.4	727.3	726.1	725.0	723.5
117.5°	822.2	822.7	823.8	825.0	826.1	827.2	825.7	824.2	822.6	821.1	819.9
120°	884.0	884.3	885.1	886.1	887.0	887.8	887.3	886.7	886.1	885.4	884.4
122.5°	945.0	945.8	946.2	946.6	947.1	947.5	946.8	946.2	945.6	945.1	943.9
125°	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4	1033.2	1032.1	1030.9	1029.9
127.5°	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4	1112.8	1112.1	1111.5	1110.0
130°	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5	1164.6	1163.7	1162.9	1161.6
132.5°	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3	1213.0	1212.8	1212.6	1211.8
135°	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8	1284.1	1283.5	1282.9	1281.8
137.5°	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3	1350.4	1350.5	1350.6	1349.9
140°	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5	1391.1	1391.6	1392.2	1391.6
142.5°	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8	1430.9	1431.1	1431.2	1430.4
145°	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9	1487.2	1487.5	1487.8	1487.1
147.5°	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1	1535.5	1535.8	1536.2	1535.3
150°	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7	1566.3	1566.8	1567.4	1566.5
152.5°	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9	1593.5	1594.1	1594.6	1593.9
155°	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0	1630.9	1631.7	1632.6	1631.9
157.5°	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9	1661.9	1662.8	1663.8	1663.0
160°	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0	1681.2	1682.3	1683.5	1682.9
162.5°	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2	1698.8	1700.5	1702.1	1701.6
165°	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8	1721.5	1723.3	1725.1	1724.7
167.5°	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7	1738.8	1740.8	1742.9	1742.6
170°	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2	1747.6	1749.9	1752.2	1752.1
172.5°	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3	1754.4	1756.6	1758.6	1758.4
175°	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6	1761.9	1764.2	1766.6	1766.5
177.5°	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4	1765.0	1766.7	1768.3	1768.2
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	861.1	863.3	861.5	863.9	861.5	863.3	861.1	863.0	865.8	863.9	868.2
5°	793.8	790.2	792.5	791.0	792.5	790.2	793.8	795.7	800.2	801.7	804.9
7.5°	731.4	728.1	724.4	722.6	724.4	728.1	731.4	732.6	736.5	742.3	746.6
10°	692.5	688.2	687.8	685.2	687.8	688.2	692.5	696.7	699.3	706.6	711.7
12.5°	663.9	659.9	655.6	654.5	655.6	659.9	663.9	667.5	668.3	676.6	680.0
15°	623.4	620.4	617.6	620.0	617.6	620.4	623.4	625.7	630.0	635.7	639.5
17.5°	589.7	587.1	586.7	583.9	586.7	587.1	589.7	591.0	597.9	601.7	608.2
20°	568.6	566.6	567.3	562.4	567.3	566.6	568.6	572.0	578.9	580.8	587.7
22.5°	551.7	547.9	547.4	546.4	547.4	547.9	551.7	554.8	556.1	562.1	566.8
25°	525.2	523.3	521.4	523.3	521.4	523.3	525.2	528.7	530.2	534.4	539.0
27.5°	502.1	499.8	499.3	499.5	499.3	499.8	502.1	501.8	505.9	509.3	512.7
30°	488.0	484.1	484.5	484.1	484.5	484.1	488.0	488.0	490.3	493.3	496.4
32.5°	472.6	470.0	469.5	468.8	469.5	470.0	472.6	472.0	474.9	478.6	482.0
35°	450.0	450.0	448.1	448.1	448.1	450.0	450.0	451.1	454.2	454.2	458.1
37.5°	428.7	428.4	427.2	427.4	427.2	428.4	428.7	429.7	430.7	432.3	434.8
40°	412.7	412.4	411.2	408.9	411.2	412.4	412.7	414.3	415.1	417.0	418.5
42.5°	397.5	396.2	395.6	394.9	395.6	396.2	397.5	398.4	398.8	401.3	404.5
45°	373.2	373.2	372.5	372.1	372.5	373.2	373.2	373.2	373.7	376.7	378.3
47.5°	349.8	350.5	351.9	351.7	351.9	350.5	349.8	349.2	349.3	350.8	352.6
50°	335.7	336.1	337.2	337.6	337.2	336.1	335.7	334.2	333.4	333.4	334.6
52.5°	320.0	322.2	323.7	323.5	323.7	322.2	320.0	318.8	317.4	315.6	317.3
55°	298.1	300.7	303.5	303.9	303.5	300.7	298.1	294.6	293.1	290.0	291.1
57.5°	276.4	280.1	283.0	283.9	283.0	280.1	276.4	272.3	267.2	265.8	263.7
60°	261.7	266.6	270.0	271.7	270.0	266.6	261.7	257.8	251.3	247.0	245.5
62.5°	247.5	253.1	256.6	256.9	256.6	253.1	247.5	241.6	235.0	230.1	227.1
65°	224.4	230.1	233.3	235.5	233.3	230.1	224.4	217.9	210.7	204.1	200.7
67.5°	199.5	205.3	208.7	210.6	208.7	205.3	199.5	191.5	184.8	177.3	173.3
70°	181.5	187.2	191.8	193.4	191.8	187.2	181.5	171.9	166.1	159.2	155.7
72.5°	163.7	168.7	172.5	174.3	172.5	168.7	163.7	154.7	148.0	141.1	136.4
75°	132.7	139.7	143.1	145.0	143.1	139.7	132.7	127.7	120.1	112.8	109.0
77.5°	102.4	108.7	110.7	111.7	110.7	108.7	102.4	96.5	90.7	85.4	81.6
80°	82.1	85.9	88.7	89.0	88.7	85.9	82.1	77.5	72.9	67.9	64.4
82.5°	63.1	66.2	67.2	68.2	67.2	66.2	63.1	59.1	55.1	51.3	48.5
85°	34.5	36.1	36.5	36.1	36.5	36.1	34.5	31.8	29.9	28.0	26.9
87.5°	17.1	17.0	17.2	18.0	17.2	17.0	17.1	16.4	16.4	15.5	14.5
90°	28.8	29.6	30.5	31.4	30.5	29.6	28.8	27.9	26.8	25.2	23.8
92.5°	28.1	28.5	28.9	29.3	28.9	28.5	28.1	27.7	26.8	25.2	23.8
95°	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	26.8	25.2	23.8
97.5°	27.5	27.5	27.5	27.5	27.5	27.5	27.5	27.5	31.5	39.8	48.0
100°	30.9	29.8	28.6	27.5	28.6	29.8	30.9	32.1	54.3	97.7	140.9
102.5°	223.8	204.0	184.2	164.5	184.2	204.0	223.8	243.5	257.5	265.7	273.9
105°	389.2	388.9	388.6	388.3	388.6	388.9	389.2	389.5	389.6	389.6	389.6
107.5°	492.1	491.3	490.4	489.6	490.4	491.3	492.1	493.0	493.4	493.4	493.3
110°	558.8	559.1	559.4	559.7	559.4	559.1	558.8	558.5	558.8	559.7	560.5



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	623.6	623.2	622.8	622.4	622.8	623.2	623.6	624.0	624.8	625.9	626.9
115°	721.8	720.0	718.2	716.5	718.2	720.0	721.8	723.5	725.0	726.1	727.3
117.5°	819.2	818.5	817.7	817.0	817.7	818.5	819.2	819.9	821.1	822.6	824.2
120°	883.0	881.5	880.1	878.7	880.1	881.5	883.0	884.4	885.4	886.1	886.7
122.5°	942.3	940.6	938.9	937.3	938.9	940.6	942.3	943.9	945.1	945.6	946.2
125°	1029.1	1028.1	1027.2	1026.4	1027.2	1028.1	1029.1	1029.9	1030.9	1032.1	1033.2
127.5°	1107.9	1105.8	1103.6	1101.5	1103.6	1105.8	1107.9	1110.0	1111.5	1112.1	1112.8
130°	1160.2	1158.7	1157.3	1155.9	1157.3	1158.7	1160.2	1161.6	1162.9	1163.7	1164.6
132.5°	1210.4	1209.0	1207.5	1206.1	1207.5	1209.0	1210.4	1211.8	1212.6	1212.8	1213.0
135°	1280.1	1278.3	1276.6	1274.9	1276.6	1278.3	1280.1	1281.8	1282.9	1283.5	1284.1
137.5°	1348.4	1346.9	1345.3	1343.8	1345.3	1346.9	1348.4	1349.9	1350.6	1350.5	1350.4
140°	1389.9	1388.2	1386.4	1384.6	1386.4	1388.2	1389.9	1391.6	1392.2	1391.6	1391.1
142.5°	1428.6	1426.8	1425.1	1423.4	1425.1	1426.8	1428.6	1430.4	1431.2	1431.1	1430.9
145°	1485.3	1483.6	1481.9	1480.2	1481.9	1483.6	1485.3	1487.1	1487.8	1487.5	1487.2
147.5°	1533.2	1531.1	1529.0	1526.9	1529.0	1531.1	1533.2	1535.3	1536.2	1535.8	1535.5
150°	1564.2	1561.9	1559.5	1557.2	1559.5	1561.9	1564.2	1566.5	1567.4	1566.8	1566.3
152.5°	1591.7	1589.7	1587.6	1585.5	1587.6	1589.7	1591.7	1593.9	1594.6	1594.1	1593.5
155°	1629.6	1627.3	1625.0	1622.7	1625.0	1627.3	1629.6	1631.9	1632.6	1631.7	1630.9
157.5°	1660.7	1658.4	1656.1	1653.8	1656.1	1658.4	1660.7	1663.0	1663.8	1662.8	1661.9
160°	1680.6	1678.3	1676.0	1673.6	1676.0	1678.3	1680.6	1682.9	1683.5	1682.3	1681.2
162.5°	1699.1	1696.5	1693.9	1691.4	1693.9	1696.5	1699.1	1701.6	1702.1	1700.5	1698.8
165°	1722.4	1720.1	1717.8	1715.5	1717.8	1720.1	1722.4	1724.7	1725.1	1723.3	1721.5
167.5°	1740.0	1737.5	1734.8	1732.2	1734.8	1737.5	1740.0	1742.6	1742.9	1740.8	1738.8
170°	1749.5	1746.9	1744.2	1741.6	1744.2	1746.9	1749.5	1752.1	1752.2	1749.9	1747.6
172.5°	1755.8	1753.1	1750.5	1747.9	1750.5	1753.1	1755.8	1758.4	1758.6	1756.6	1754.4
175°	1763.8	1761.2	1758.6	1756.0	1758.6	1761.2	1763.8	1766.5	1766.6	1764.2	1761.9
177.5°	1766.3	1764.4	1762.5	1760.7	1762.5	1764.4	1766.3	1768.2	1768.3	1766.7	1765.0
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	864.2	867.9	872.5	875.9	882.0	884.7	888.2	890.9	895.9	900.4	905.9
5°	806.0	812.5	821.3	830.9	842.0	849.7	860.5	867.0	880.0	891.9	903.4
7.5°	753.2	761.2	773.7	786.0	800.5	813.7	827.2	842.0	858.7	878.4	894.6
10°	717.0	727.7	741.1	756.5	774.2	789.5	807.5	823.6	843.9	867.0	888.5
12.5°	688.1	697.3	712.4	727.0	745.9	764.7	783.3	804.7	828.3	853.8	880.8
15°	648.3	656.0	668.2	688.6	707.8	726.2	754.2	774.2	804.1	832.4	865.1
17.5°	614.3	623.9	634.2	651.7	671.5	694.5	719.5	744.6	773.4	809.4	846.2
20°	593.5	601.2	613.0	626.4	647.5	670.6	694.4	719.6	755.0	792.1	831.7
22.5°	570.8	579.1	592.5	607.1	624.8	646.9	673.2	700.9	737.8	774.4	817.3
25°	544.0	549.8	562.0	575.0	592.7	611.5	638.7	669.4	705.9	747.7	791.4
27.5°	518.8	523.8	535.0	546.3	562.3	584.6	608.9	640.0	674.3	716.7	765.2
30°	500.6	506.0	515.9	528.3	543.6	563.2	588.1	617.2	654.1	695.5	746.2
32.5°	484.9	489.8	497.3	509.6	524.5	543.5	566.6	596.4	633.2	675.3	725.0
35°	460.7	466.1	471.8	481.4	494.5	512.9	538.3	566.2	601.5	642.2	687.8
37.5°	436.7	442.4	447.6	456.2	468.1	484.3	506.2	535.4	567.3	606.5	650.4
40°	421.6	426.2	430.4	439.6	451.5	466.9	487.2	513.3	547.0	583.5	620.0
42.5°	406.6	410.8	414.4	422.4	433.4	448.2	467.6	493.0	524.3	558.4	590.5
45°	382.8	385.6	389.8	396.7	405.5	418.9	437.7	460.4	486.9	519.1	543.2
47.5°	357.2	361.4	364.9	370.9	378.2	391.3	409.4	428.7	452.7	476.7	493.6
50°	337.6	341.8	346.8	352.5	359.4	371.7	388.2	407.8	428.1	446.6	461.1
52.5°	319.2	323.1	328.4	333.9	342.2	352.7	366.8	384.2	404.1	417.4	429.5
55°	292.0	293.9	300.0	305.4	313.5	321.1	335.3	350.6	362.9	372.8	382.8
57.5°	264.1	266.7	270.2	275.1	283.1	292.1	301.9	315.6	322.8	327.9	335.7
60°	246.3	247.0	249.3	255.1	261.3	269.3	280.8	290.4	295.8	300.0	306.5
62.5°	226.6	226.8	230.7	234.9	239.4	248.1	257.5	265.2	269.7	271.8	278.0
65°	199.1	198.3	200.7	204.1	209.4	215.2	223.3	230.1	229.7	232.1	235.9
67.5°	171.0	170.2	170.2	173.5	177.8	183.0	188.5	192.5	192.6	195.6	197.5
70°	151.9	149.7	151.2	153.8	155.7	160.0	166.1	167.6	168.0	169.6	171.5
72.5°	132.3	131.5	132.7	133.9	135.2	138.5	143.7	144.6	144.7	145.6	148.8
75°	105.1	104.3	103.6	104.7	106.2	108.6	110.5	112.0	111.6	112.0	114.3
77.5°	78.8	76.6	76.2	76.9	77.3	78.7	80.7	80.5	80.9	80.8	83.4
80°	62.5	59.5	59.1	59.1	59.5	60.2	61.0	61.8	60.6	61.8	62.5
82.5°	45.9	44.1	44.0	43.7	43.8	43.9	44.4	44.8	44.6	45.1	45.6
85°	25.3	24.5	23.4	24.1	23.8	22.6	23.4	22.2	21.9	22.2	22.6
87.5°	13.0	13.1	12.0	11.6	10.9	10.8	9.8	9.0	8.3	8.1	8.6
90°	22.4	20.9	18.9	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3
92.5°	22.4	20.9	19.1	17.3	15.6	13.7	13.6	15.2	16.9	18.5	20.1
95°	22.4	20.9	31.9	43.0	54.0	65.0	71.0	71.9	72.8	73.6	74.5
97.5°	56.1	64.3	86.1	108.1	129.9	151.7	161.9	160.3	158.8	157.1	155.6
100°	184.2	227.5	226.3	225.2	224.0	222.9	221.9	221.0	220.0	219.2	218.3
102.5°	282.1	290.2	289.5	288.9	288.2	287.5	286.6	285.5	284.4	283.3	282.2
105°	389.6	389.6	389.6	389.6	389.6	389.6	389.1	387.9	386.8	385.6	384.5
107.5°	493.2	493.2	492.6	492.0	491.5	490.9	490.6	490.6	490.6	490.6	490.6
110°	561.4	562.2	561.7	561.1	560.5	559.9	559.7	559.7	559.7	559.7	559.7



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	628.0	629.1	628.8	628.4	628.1	627.8	627.2	626.5	625.9	625.2	624.5
115°	728.4	729.6	729.3	729.0	728.7	728.4	727.6	726.1	724.7	723.2	721.8
117.5°	825.7	827.2	826.1	825.0	823.8	822.7	822.2	822.2	822.3	822.3	822.4
120°	887.3	887.8	887.0	886.1	885.1	884.3	884.0	884.3	884.6	884.9	885.1
122.5°	946.8	947.5	947.1	946.6	946.2	945.8	945.0	943.9	942.8	941.7	940.6
125°	1034.4	1035.5	1035.5	1035.5	1035.5	1035.5	1034.5	1032.5	1030.5	1028.4	1026.4
127.5°	1113.4	1114.0	1114.2	1114.4	1114.5	1114.7	1114.1	1112.6	1111.2	1109.7	1108.2
130°	1165.5	1166.3	1166.0	1165.7	1165.5	1165.2	1164.3	1162.9	1161.3	1159.9	1158.4
132.5°	1213.3	1213.4	1214.1	1214.7	1215.3	1216.0	1215.4	1213.8	1212.0	1210.3	1208.7
135°	1284.8	1285.3	1285.9	1286.5	1287.1	1287.6	1287.1	1285.3	1283.5	1281.8	1280.1
137.5°	1350.3	1350.2	1350.7	1351.2	1351.7	1352.2	1351.7	1350.2	1348.7	1347.2	1345.7
140°	1390.5	1389.9	1390.2	1390.5	1390.8	1391.1	1390.9	1390.3	1389.8	1389.2	1388.6
142.5°	1430.8	1430.7	1430.3	1429.9	1429.5	1429.1	1428.7	1428.4	1427.9	1427.6	1427.2
145°	1486.9	1486.6	1486.6	1486.6	1486.6	1486.6	1486.3	1485.8	1485.2	1484.6	1484.0
147.5°	1535.1	1534.8	1534.4	1534.1	1533.7	1533.4	1533.3	1533.4	1533.5	1533.6	1533.7
150°	1565.7	1565.1	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1
152.5°	1592.9	1592.3	1591.7	1591.1	1590.5	1589.9	1590.3	1591.6	1592.9	1594.2	1595.4
155°	1630.0	1629.2	1628.6	1628.0	1627.4	1626.9	1627.4	1629.2	1630.9	1632.6	1634.4
157.5°	1660.9	1660.0	1660.0	1659.9	1659.8	1659.8	1660.3	1661.3	1662.3	1663.4	1664.5
160°	1680.0	1678.9	1678.6	1678.3	1678.0	1677.7	1678.4	1680.1	1681.9	1683.6	1685.4
162.5°	1697.2	1695.6	1695.3	1695.1	1694.8	1694.5	1695.2	1696.9	1698.6	1700.4	1702.1
165°	1719.8	1718.1	1717.8	1717.5	1717.2	1716.9	1717.7	1719.4	1721.1	1722.8	1724.6
167.5°	1736.7	1734.5	1734.2	1733.9	1733.6	1733.4	1734.1	1736.0	1737.8	1739.6	1741.3
170°	1745.2	1742.9	1742.6	1742.3	1742.0	1741.7	1742.6	1744.6	1746.7	1748.8	1750.8
172.5°	1752.3	1750.2	1749.7	1749.2	1748.7	1748.2	1748.9	1750.9	1753.0	1755.0	1757.1
175°	1759.6	1757.3	1757.1	1756.8	1756.5	1756.2	1756.9	1758.6	1760.4	1762.1	1763.8
177.5°	1763.4	1761.7	1761.5	1761.3	1761.1	1760.8	1761.4	1762.8	1764.2	1765.5	1767.0
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	908.8	913.0	915.7	921.0	925.3	927.8	929.9	931.7	933.9	935.7	941.0
5°	914.5	924.5	933.0	946.0	958.0	967.1	977.0	985.9	993.2	1003.6	1011.6
7.5°	912.0	929.8	948.4	968.5	989.2	1008.4	1025.9	1042.5	1057.4	1075.5	1091.4
10°	909.6	933.7	957.6	984.7	1012.8	1036.5	1058.8	1081.5	1097.9	1121.0	1140.5
12.5°	907.8	936.2	964.9	997.6	1028.4	1062.0	1091.7	1108.1	1133.3	1151.7	1174.9
15°	900.0	937.6	977.0	1013.9	1057.6	1088.7	1114.8	1147.0	1170.4	1193.9	1219.1
17.5°	886.1	928.7	972.9	1021.2	1063.1	1096.5	1130.0	1161.1	1189.1	1220.4	1252.0
20°	879.7	922.2	972.9	1022.4	1063.4	1098.3	1132.9	1167.0	1197.7	1238.0	1274.3
22.5°	866.2	917.7	964.3	1012.5	1054.8	1092.8	1132.0	1170.6	1211.4	1257.0	1302.6
25°	842.0	894.2	943.7	991.3	1033.9	1081.5	1123.3	1175.1	1227.2	1287.5	1344.2
27.5°	817.1	867.0	912.3	958.3	1007.9	1061.8	1116.0	1174.8	1243.1	1319.1	1399.3
30°	796.8	843.9	888.1	935.2	987.0	1047.6	1107.1	1177.0	1256.0	1341.5	1436.6
32.5°	773.2	816.7	859.6	909.5	965.9	1029.9	1099.1	1175.7	1270.7	1368.0	1465.8
35°	732.8	769.2	813.2	866.6	930.3	1003.6	1083.8	1174.3	1283.2	1394.8	1477.3
37.5°	684.8	718.7	765.2	823.6	890.4	969.1	1064.2	1171.5	1287.3	1376.2	1402.9
40°	652.6	684.0	732.4	792.9	861.2	944.5	1048.8	1162.4	1274.3	1331.2	1309.3
42.5°	618.1	651.2	698.3	758.3	831.7	922.4	1029.5	1143.1	1237.0	1258.4	1182.9
45°	563.9	598.0	644.5	705.1	784.2	882.3	994.0	1097.1	1151.2	1112.5	995.5
47.5°	513.5	545.5	588.5	651.1	732.7	834.2	941.7	1024.0	1028.3	935.8	810.9
50°	479.2	508.7	552.0	614.6	695.5	798.3	895.3	960.2	931.1	826.4	706.3
52.5°	445.4	474.3	517.1	579.0	659.0	753.2	843.5	889.0	834.0	726.6	624.0
55°	396.7	422.0	463.8	521.0	596.9	684.4	761.1	776.8	705.5	599.6	516.3
57.5°	349.1	372.7	410.8	463.4	532.8	610.4	670.3	667.0	591.6	500.7	434.6
60°	316.9	339.9	373.7	425.1	488.4	555.1	606.5	594.2	519.5	441.2	385.6
62.5°	288.0	308.6	340.5	385.5	443.2	505.0	547.2	529.2	455.9	387.5	343.5
65°	245.5	262.8	290.0	328.4	376.4	427.4	460.0	436.6	374.1	320.7	285.4
67.5°	204.9	218.7	241.6	272.3	313.2	354.1	374.0	350.4	300.3	261.5	235.3
70°	179.2	191.5	209.0	236.3	272.0	306.5	321.4	300.3	257.4	224.0	205.2
72.5°	153.4	163.5	179.0	203.5	232.1	262.1	275.1	255.0	219.6	191.5	173.9
75°	118.6	125.4	136.2	153.1	175.7	199.4	206.8	189.1	166.5	145.4	133.9
77.5°	84.8	90.7	98.9	109.5	125.5	140.7	147.0	136.8	119.3	105.9	96.5
80°	65.2	68.3	75.2	84.0	96.6	106.2	110.5	103.9	91.7	81.7	74.4
82.5°	46.5	49.6	53.7	61.0	69.1	75.5	80.1	75.7	66.9	59.0	54.7
85°	22.6	24.5	26.9	29.9	36.1	39.9	39.5	36.9	33.3	30.3	28.0
87.5°	8.7	9.5	10.9	12.8	14.2	15.9	16.9	16.7	15.9	15.2	14.5
90°	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	20.9	22.4	23.8
92.5°	18.5	16.9	15.2	13.6	13.7	15.6	17.3	19.1	20.9	22.4	23.8
95°	73.6	72.8	71.9	71.0	65.0	54.0	43.0	31.9	20.9	22.4	23.8
97.5°	157.1	158.8	160.3	161.9	151.7	129.9	108.1	86.1	64.3	56.1	48.0
100°	219.2	220.0	221.0	221.9	222.9	224.0	225.2	226.3	227.5	184.2	140.9
102.5°	283.3	284.4	285.5	286.6	287.5	288.2	288.9	289.5	290.2	282.1	273.9
105°	385.6	386.8	387.9	389.1	389.6	389.6	389.6	389.6	389.6	389.6	389.6
107.5°	490.6	490.6	490.6	490.6	490.9	491.5	492.0	492.6	493.2	493.2	493.3
110°	559.7	559.7	559.7	559.7	559.9	560.5	561.1	561.7	562.2	561.4	560.5



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	625.2	625.9	626.5	627.2	627.8	628.1	628.4	628.8	629.1	628.0	626.9
115°	723.2	724.7	726.1	727.6	728.4	728.7	729.0	729.3	729.6	728.4	727.3
117.5°	822.3	822.3	822.2	822.2	822.7	823.8	825.0	826.1	827.2	825.7	824.2
120°	884.9	884.6	884.3	884.0	884.3	885.1	886.1	887.0	887.8	887.3	886.7
122.5°	941.7	942.8	943.9	945.0	945.8	946.2	946.6	947.1	947.5	946.8	946.2
125°	1028.4	1030.5	1032.5	1034.5	1035.5	1035.5	1035.5	1035.5	1035.5	1034.4	1033.2
127.5°	1109.7	1111.2	1112.6	1114.1	1114.7	1114.5	1114.4	1114.2	1114.0	1113.4	1112.8
130°	1159.9	1161.3	1162.9	1164.3	1165.2	1165.5	1165.7	1166.0	1166.3	1165.5	1164.6
132.5°	1210.3	1212.0	1213.8	1215.4	1216.0	1215.3	1214.7	1214.1	1213.4	1213.3	1213.0
135°	1281.8	1283.5	1285.3	1287.1	1287.6	1287.1	1286.5	1285.9	1285.3	1284.8	1284.1
137.5°	1347.2	1348.7	1350.2	1351.7	1352.2	1351.7	1351.2	1350.7	1350.2	1350.3	1350.4
140°	1389.2	1389.8	1390.3	1390.9	1391.1	1390.8	1390.5	1390.2	1389.9	1390.5	1391.1
142.5°	1427.6	1427.9	1428.4	1428.7	1429.1	1429.5	1429.9	1430.3	1430.7	1430.8	1430.9
145°	1484.6	1485.2	1485.8	1486.3	1486.6	1486.6	1486.6	1486.6	1486.6	1486.9	1487.2
147.5°	1533.6	1533.5	1533.4	1533.3	1533.4	1533.7	1534.1	1534.4	1534.8	1535.1	1535.5
150°	1564.5	1564.0	1563.4	1562.8	1562.8	1563.4	1564.0	1564.5	1565.1	1565.7	1566.3
152.5°	1594.2	1592.9	1591.6	1590.3	1589.9	1590.5	1591.1	1591.7	1592.3	1592.9	1593.5
155°	1632.6	1630.9	1629.2	1627.4	1626.9	1627.4	1628.0	1628.6	1629.2	1630.0	1630.9
157.5°	1663.4	1662.3	1661.3	1660.3	1659.8	1659.8	1659.9	1660.0	1660.0	1660.9	1661.9
160°	1683.6	1681.9	1680.1	1678.4	1677.7	1678.0	1678.3	1678.6	1678.9	1680.0	1681.2
162.5°	1700.4	1698.6	1696.9	1695.2	1694.5	1694.8	1695.1	1695.3	1695.6	1697.2	1698.8
165°	1722.8	1721.1	1719.4	1717.7	1716.9	1717.2	1717.5	1717.8	1718.1	1719.8	1721.5
167.5°	1739.6	1737.8	1736.0	1734.1	1733.4	1733.6	1733.9	1734.2	1734.5	1736.7	1738.8
170°	1748.8	1746.7	1744.6	1742.6	1741.7	1742.0	1742.3	1742.6	1742.9	1745.2	1747.6
172.5°	1755.0	1753.0	1750.9	1748.9	1748.2	1748.7	1749.2	1749.7	1750.2	1752.3	1754.4
175°	1762.1	1760.4	1758.6	1756.9	1756.2	1756.5	1756.8	1757.1	1757.3	1759.6	1761.9
177.5°	1765.5	1764.2	1762.8	1761.4	1760.8	1761.1	1761.3	1761.5	1761.7	1763.4	1765.0
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	903.8	903.8	903.8	903.8	903.8	903.8	903.8
2.5°	945.2	947.7	952.9	951.1	953.5	954.7	956.0
5°	1021.6	1033.9	1039.3	1038.4	1046.5	1044.6	1042.7
7.5°	1107.8	1120.7	1127.9	1136.9	1142.2	1142.5	1147.0
10°	1156.6	1173.5	1180.4	1190.0	1196.2	1199.6	1199.2
12.5°	1194.1	1207.3	1222.7	1227.5	1235.8	1240.1	1238.5
15°	1239.1	1260.2	1276.3	1284.3	1294.7	1297.8	1302.0
17.5°	1279.3	1307.6	1326.5	1351.4	1360.9	1366.7	1363.2
20°	1309.7	1346.9	1365.7	1395.6	1412.1	1421.0	1417.9
22.5°	1345.6	1385.8	1420.7	1446.5	1471.7	1483.6	1486.0
25°	1407.1	1462.4	1513.4	1547.5	1578.6	1585.9	1602.0
27.5°	1475.9	1541.1	1595.6	1631.4	1653.1	1661.2	1666.3
30°	1519.1	1584.0	1625.1	1648.0	1655.0	1654.2	1653.5
32.5°	1540.3	1580.9	1588.8	1582.4	1566.6	1553.2	1539.2
35°	1510.4	1480.1	1434.7	1376.4	1333.5	1290.1	1285.9
37.5°	1358.4	1261.4	1186.1	1102.0	1053.4	1023.4	1002.6
40°	1215.3	1105.2	1013.9	942.9	893.4	873.9	854.7
42.5°	1060.1	954.8	873.9	814.7	777.5	755.8	740.5
45°	861.2	768.4	705.1	662.2	632.6	615.7	606.1
47.5°	705.7	637.0	583.3	552.3	531.9	518.8	518.8
50°	622.3	556.6	521.0	496.4	478.8	468.4	470.3
52.5°	548.3	499.3	468.8	448.2	435.2	428.8	428.6
55°	458.5	423.1	403.2	388.2	379.4	372.1	373.7
57.5°	392.1	362.3	349.0	336.6	330.4	327.5	323.4
60°	351.0	328.0	316.5	306.5	300.3	298.1	293.9
62.5°	314.5	296.4	285.2	277.0	271.6	270.7	267.4
65°	264.3	250.5	240.5	236.7	231.0	229.4	229.4
67.5°	217.9	208.0	200.3	196.7	194.2	194.6	192.7
70°	188.7	180.7	175.7	171.9	170.0	170.4	168.7
72.5°	165.1	156.1	151.8	149.5	146.9	147.9	147.3
75°	125.0	120.5	118.2	115.8	114.3	113.5	112.8
77.5°	91.8	87.8	86.0	84.7	84.9	83.1	84.5
80°	71.0	67.6	66.3	64.4	64.0	64.0	63.7
82.5°	51.9	50.0	49.2	47.6	46.9	47.5	46.5
85°	26.9	25.3	24.9	24.9	24.1	23.4	25.3
87.5°	14.8	13.9	14.1	14.0	14.2	14.0	13.6
90°	25.2	26.8	27.9	28.8	29.6	30.5	31.4
92.5°	25.2	26.8	27.7	28.1	28.5	28.9	29.3
95°	25.2	26.8	27.5	27.5	27.5	27.5	27.5
97.5°	39.8	31.5	27.5	27.5	27.5	27.5	27.5
100°	97.7	54.3	32.1	30.9	29.8	28.6	27.5
102.5°	265.7	257.5	243.5	223.8	204.0	184.2	164.5
105°	389.6	389.6	389.5	389.2	388.9	388.6	388.3
107.5°	493.4	493.4	493.0	492.1	491.3	490.4	489.6
110°	559.7	558.8	558.5	558.8	559.1	559.4	559.7



TEST NUMBER: P333388-840

CATALOG NUMBER: S125DIW-S610D1340U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	625.9	624.8	624.0	623.6	623.2	622.8	622.4
115°	726.1	725.0	723.5	721.8	720.0	718.2	716.5
117.5°	822.6	821.1	819.9	819.2	818.5	817.7	817.0
120°	886.1	885.4	884.4	883.0	881.5	880.1	878.7
122.5°	945.6	945.1	943.9	942.3	940.6	938.9	937.3
125°	1032.1	1030.9	1029.9	1029.1	1028.1	1027.2	1026.4
127.5°	1112.1	1111.5	1110.0	1107.9	1105.8	1103.6	1101.5
130°	1163.7	1162.9	1161.6	1160.2	1158.7	1157.3	1155.9
132.5°	1212.8	1212.6	1211.8	1210.4	1209.0	1207.5	1206.1
135°	1283.5	1282.9	1281.8	1280.1	1278.3	1276.6	1274.9
137.5°	1350.5	1350.6	1349.9	1348.4	1346.9	1345.3	1343.8
140°	1391.6	1392.2	1391.6	1389.9	1388.2	1386.4	1384.6
142.5°	1431.1	1431.2	1430.4	1428.6	1426.8	1425.1	1423.4
145°	1487.5	1487.8	1487.1	1485.3	1483.6	1481.9	1480.2
147.5°	1535.8	1536.2	1535.3	1533.2	1531.1	1529.0	1526.9
150°	1566.8	1567.4	1566.5	1564.2	1561.9	1559.5	1557.2
152.5°	1594.1	1594.6	1593.9	1591.7	1589.7	1587.6	1585.5
155°	1631.7	1632.6	1631.9	1629.6	1627.3	1625.0	1622.7
157.5°	1662.8	1663.8	1663.0	1660.7	1658.4	1656.1	1653.8
160°	1682.3	1683.5	1682.9	1680.6	1678.3	1676.0	1673.6
162.5°	1700.5	1702.1	1701.6	1699.1	1696.5	1693.9	1691.4
165°	1723.3	1725.1	1724.7	1722.4	1720.1	1717.8	1715.5
167.5°	1740.8	1742.9	1742.6	1740.0	1737.5	1734.8	1732.2
170°	1749.9	1752.2	1752.1	1749.5	1746.9	1744.2	1741.6
172.5°	1756.6	1758.6	1758.4	1755.8	1753.1	1750.5	1747.9
175°	1764.2	1766.6	1766.5	1763.8	1761.2	1758.6	1756.0
177.5°	1766.7	1768.3	1768.2	1766.3	1764.4	1762.5	1760.7
180°	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)