

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333703-840

Luminaire Tested: **S125RDIW-S1090D470U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333703-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D470U840-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5906.7 lumens  
Efficiency: N/A  
Efficacy: 127.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333703-840

CATALOG NUMBER: S125RDIW-S1090D470U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333703-840

CATALOG NUMBER: S125RDIW-S1090D470U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	91	98	94	90	87	85	82	79	76	74	72	68	67	65	62
2	94	87	80	75	89	82	77	72	74	70	66	67	64	61	60	58	55	52
3	86	76	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48	44
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	44	41	38
5	73	61	52	46	69	58	51	45	53	47	42	48	43	39	44	39	36	33
6	67	55	46	41	64	52	45	39	48	42	37	44	38	34	40	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	45	37	32	55	43	36	31	40	34	29	37	31	27	33	29	26	24
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11657	11657	11657
5°	11684	11551	11622
10°	11596	11444	11444
15°	11457	11212	11120
20°	11281	10888	10757
25°	11075	10570	10337
30°	10818	10197	9871
35°	10555	9813	9351
40°	10309	9413	8838
45°	10011	8965	8280
50°	9711	8478	7698
55°	9364	8014	7076
60°	9016	7448	6409
65°	8604	6791	5645
70°	8135	5973	4864
75°	7483	5036	4047
80°	6590	3954	3396
85°	5550	3231	3031



TEST NUMBER: P333703-840

CATALOG NUMBER: S125RDIW-S1090D470U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.7	2.9
10°-20°	474.3	8.0
20°-30°	687.8	11.6
30°-40°	783.9	13.3
40°-50°	764.1	12.9
50°-60°	643.2	10.9
60°-70°	450.9	7.6
70°-80°	231.8	3.9
80°-90°	59.8	1.0
90°-100°	39.4	0.7
100°-110°	116.3	2.0
110°-120°	197.1	3.3
120°-130°	259.3	4.4
130°-140°	290.6	4.9
140°-150°	284.8	4.8
150°-160°	239.2	4.0
160°-170°	159.0	2.7
170°-180°	55.6	0.9
0°-30°	1331.9	22.5
0°-40°	2115.8	35.8
0°-60°	3523.1	59.6
0°-90°	4265.5	72.2
90°-120°	352.8	6.0
90°-150°	1187.4	20.1
90°-180°	1641.0	27.8
0°-180°	5906.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1805	1805	1805	1805	1805	
5°	1802	1796	1782	1794	1793	171
15°	1714	1704	1677	1675	1663	483
25°	1554	1532	1483	1466	1451	715
35°	1339	1304	1245	1206	1186	838
45°	1096	1055	982	929	907	845
55°	832	786	712	652	628	744
65°	563	515	444	392	369	558
75°	300	258	202	173	162	317
85°	75	51	44	42	41	84
90°	0	4	7	10	11	5
95°	30	31	35	38	39	32
105°	104	107	109	112	114	111
115°	197	199	200	200	199	195
125°	288	290	291	290	290	258
135°	374	377	378	378	376	288
145°	454	455	457	457	455	283
155°	519	519	520	521	519	239
165°	564	564	564	565	563	159
175°	587	585	585	587	584	56
180°	588	588	588	588	588	



TEST NUMBER: P333703-840

CATALOG NUMBER: S125RDIW-S1090D470U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1808.3	1807.6	1806.9	1806.0	1805.3	1803.8	1801.4	1799.0	1796.5	1794.1	1796.5
5°	1802.3	1801.1	1799.9	1798.7	1797.5	1795.1	1791.8	1788.5	1785.1	1781.8	1784.8
7.5°	1784.5	1783.4	1782.2	1781.1	1779.9	1777.4	1773.3	1769.4	1765.3	1761.4	1763.5
10°	1768.2	1767.3	1766.4	1765.4	1764.5	1762.0	1757.8	1753.5	1749.3	1745.0	1746.0
12.5°	1749.6	1748.5	1747.4	1746.2	1745.0	1741.6	1736.0	1730.2	1724.5	1718.8	1719.5
15°	1713.6	1711.8	1710.0	1708.2	1706.4	1702.3	1696.0	1689.6	1683.2	1676.9	1676.6
17.5°	1673.0	1670.2	1667.5	1664.7	1661.8	1656.5	1648.5	1640.5	1632.4	1624.5	1623.0
20°	1641.4	1638.4	1635.4	1632.3	1629.3	1623.0	1613.3	1603.6	1593.9	1584.2	1582.7
22.5°	1606.5	1603.5	1600.4	1597.4	1594.4	1587.8	1577.6	1567.4	1557.2	1547.0	1544.1
25°	1554.2	1549.6	1545.1	1540.5	1536.0	1528.1	1516.9	1505.7	1494.5	1483.3	1479.4
27.5°	1494.2	1488.6	1483.1	1477.6	1472.1	1463.4	1451.4	1439.4	1427.3	1415.3	1409.9
30°	1450.6	1444.8	1439.1	1433.3	1427.5	1418.3	1405.5	1392.8	1380.1	1367.4	1360.4
32.5°	1408.0	1401.3	1394.5	1387.9	1381.1	1371.3	1358.3	1345.3	1332.3	1319.4	1311.7
35°	1338.8	1331.5	1324.2	1317.0	1309.7	1299.2	1285.6	1271.9	1258.3	1244.7	1235.9
37.5°	1270.8	1262.0	1253.1	1244.4	1235.5	1224.1	1209.9	1195.9	1181.8	1167.8	1157.2
40°	1222.8	1213.8	1204.7	1195.6	1186.5	1174.7	1160.1	1145.6	1131.0	1116.5	1105.0
42.5°	1172.7	1163.4	1154.1	1144.7	1135.4	1123.2	1108.1	1093.2	1078.1	1063.1	1052.1
45°	1096.1	1087.3	1078.5	1069.8	1061.0	1048.2	1031.6	1014.9	998.3	981.6	969.5
47.5°	1016.7	1007.4	998.2	989.0	979.7	966.6	949.9	933.0	916.3	899.5	887.0
50°	966.5	956.5	946.5	936.5	926.6	912.9	895.6	878.4	861.1	843.8	831.1
52.5°	912.0	901.8	891.5	881.3	871.1	857.8	841.5	825.2	808.9	792.6	778.9
55°	831.6	821.9	812.2	802.5	792.8	779.5	762.5	745.6	728.6	711.7	698.0
57.5°	750.3	740.0	729.6	719.2	708.9	695.6	679.2	662.9	646.5	630.2	616.8
60°	698.0	687.4	676.8	666.2	655.6	642.1	625.7	609.4	593.0	576.6	563.3
62.5°	642.4	632.3	622.2	612.0	601.9	588.5	572.0	555.3	538.8	522.1	509.8
65°	563.0	552.7	542.4	532.1	521.8	508.7	492.6	476.6	460.5	444.4	432.3
67.5°	484.2	473.9	463.6	453.3	443.0	430.2	414.8	399.4	384.1	368.6	357.6
70°	430.8	420.5	410.2	399.9	389.6	376.9	361.7	346.6	331.4	316.3	306.9
72.5°	378.5	368.4	358.3	348.3	338.2	326.1	311.9	297.7	283.6	269.4	260.7
75°	299.9	290.8	281.8	272.7	263.6	252.7	239.9	227.2	214.5	201.8	195.1
77.5°	222.0	214.7	207.4	200.2	192.9	184.1	174.0	163.8	153.6	143.4	138.8
80°	177.2	170.0	162.7	155.4	148.1	140.3	131.8	123.3	114.8	106.3	103.6
82.5°	133.6	127.0	120.5	114.0	107.4	101.3	95.4	89.6	83.8	78.0	76.7
85°	74.9	69.5	64.0	58.6	53.1	49.7	48.2	46.7	45.1	43.6	43.3
87.5°	25.1	23.6	22.1	20.6	19.1	18.2	18.1	18.0	17.9	17.8	18.0
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.2	5.9	6.6	7.4	7.9
92.5°	11.1	11.6	12.2	12.8	13.3	14.0	14.9	15.9	16.7	17.6	18.3
95°	29.8	30.0	30.2	30.4	30.6	31.2	32.2	33.2	34.2	35.2	36.0
97.5°	49.4	49.5	49.6	49.7	49.8	50.5	51.9	53.3	54.7	56.1	56.8
100°	64.1	64.1	64.1	64.1	64.1	64.7	66.0	67.4	68.7	70.0	71.0
102.5°	79.8	80.2	80.7	81.1	81.5	82.0	82.7	83.3	84.0	84.6	85.6
105°	104.3	104.8	105.3	105.8	106.4	106.9	107.6	108.2	108.8	109.4	110.0
107.5°	131.5	132.0	132.5	133.0	133.5	134.0	134.4	134.9	135.4	135.8	136.1
110°	150.2	150.7	151.2	151.7	152.2	152.6	152.9	153.2	153.5	153.8	154.1



TEST NUMBER: P333703-840

CATALOG NUMBER: S125RDIW-S1090D470U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.2	169.5	169.7	170.0	170.3	170.6	171.0	171.4	171.7	172.1	172.3
115°	197.2	197.6	198.1	198.5	198.9	199.2	199.4	199.7	199.9	200.1	200.0
117.5°	225.5	225.6	225.8	226.0	226.2	226.4	226.6	226.7	226.9	227.1	227.2
120°	243.1	243.6	244.1	244.6	245.1	245.4	245.5	245.6	245.7	245.8	245.8
122.5°	262.1	262.3	262.5	262.7	262.8	263.1	263.3	263.6	263.9	264.1	264.0
125°	287.9	288.5	289.1	289.7	290.3	290.7	290.8	290.9	291.0	291.1	290.9
127.5°	315.4	315.7	316.1	316.4	316.8	317.0	317.1	317.2	317.3	317.5	317.4
130°	331.8	332.3	332.9	333.4	333.9	334.3	334.5	334.7	334.9	335.1	335.0
132.5°	348.3	349.1	350.0	350.8	351.6	352.0	352.0	351.9	351.9	351.8	351.7
135°	374.4	375.1	375.7	376.3	376.9	377.2	377.3	377.4	377.5	377.6	377.6
137.5°	398.9	399.5	400.1	400.7	401.3	401.7	401.9	402.1	402.3	402.6	402.7
140°	414.7	415.2	415.7	416.2	416.7	417.2	417.5	417.8	418.1	418.4	418.6
142.5°	430.4	430.8	431.3	431.7	432.1	432.5	432.9	433.3	433.7	434.1	434.2
145°	453.6	454.0	454.4	454.8	455.2	455.6	455.9	456.2	456.5	456.8	456.8
147.5°	475.0	475.2	475.4	475.6	475.9	476.2	476.4	476.7	476.9	477.2	477.4
150°	489.3	489.2	489.1	489.0	488.9	489.1	489.5	489.9	490.3	490.7	490.7
152.5°	501.0	501.2	501.3	501.4	501.6	501.7	501.9	502.1	502.2	502.4	502.6
155°	519.1	519.1	519.1	519.1	519.1	519.1	519.2	519.3	519.4	519.5	519.9
157.5°	535.1	534.9	534.7	534.5	534.2	534.2	534.3	534.4	534.5	534.6	535.0
160°	544.7	544.4	544.0	543.7	543.4	543.3	543.4	543.5	543.6	543.7	544.2
162.5°	553.1	552.9	552.7	552.4	552.2	552.1	552.1	552.1	552.2	552.2	552.7
165°	564.3	564.1	563.9	563.7	563.5	563.5	563.6	563.7	563.8	563.9	564.3
167.5°	573.9	573.5	573.1	572.7	572.3	572.1	572.1	572.1	572.1	572.1	572.7
170°	579.0	578.6	578.1	577.7	577.3	577.1	577.1	577.1	577.1	577.1	577.7
172.5°	582.7	582.3	581.9	581.5	581.1	580.9	580.9	580.9	580.9	580.9	581.5
175°	586.8	586.3	585.9	585.5	585.1	584.9	584.9	584.9	584.9	584.9	585.5
177.5°	588.9	588.5	588.2	587.9	587.5	587.3	587.3	587.2	587.1	587.0	587.5
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1



TEST NUMBER: P333703-840

CATALOG NUMBER: S125RDIW-S1090D470U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0	1805.0
2.5°	1799.0	1801.4	1803.8	1804.8	1804.6	1804.4	1804.1	1803.9
5°	1787.9	1790.9	1793.9	1795.1	1794.5	1793.9	1793.3	1792.7
7.5°	1765.6	1767.8	1769.9	1770.6	1769.9	1769.3	1768.6	1767.9
10°	1746.9	1747.8	1748.7	1748.7	1747.8	1746.9	1746.0	1745.0
12.5°	1720.2	1720.8	1721.5	1721.1	1719.7	1718.4	1717.0	1715.6
15°	1676.3	1676.0	1675.7	1674.2	1671.4	1668.7	1666.0	1663.2
17.5°	1621.4	1619.9	1618.4	1616.6	1614.3	1612.0	1609.8	1607.6
20°	1581.1	1579.6	1578.1	1576.0	1573.3	1570.5	1567.8	1565.1
22.5°	1541.2	1538.1	1535.2	1532.6	1530.3	1528.1	1525.8	1523.6
25°	1475.4	1471.5	1467.5	1463.9	1460.6	1457.2	1453.9	1450.6
27.5°	1404.3	1398.9	1393.3	1389.0	1385.7	1382.5	1379.3	1376.1
30°	1353.4	1346.5	1339.5	1334.6	1331.9	1329.2	1326.5	1323.7
32.5°	1304.0	1296.3	1288.6	1283.0	1279.6	1276.2	1272.6	1269.2
35°	1227.1	1218.3	1209.5	1203.1	1198.8	1194.6	1190.3	1186.1
37.5°	1146.7	1136.2	1125.6	1118.3	1114.2	1110.0	1105.9	1101.8
40°	1093.5	1082.0	1070.5	1062.9	1059.2	1055.6	1052.0	1048.3
42.5°	1041.1	1030.0	1019.0	1010.8	1005.4	1000.2	994.8	989.5
45°	957.4	945.2	933.1	924.7	920.2	915.6	911.1	906.6
47.5°	874.5	862.0	849.6	840.8	835.8	830.7	825.8	820.7
50°	818.4	805.7	792.9	784.4	779.8	775.3	770.7	766.2
52.5°	765.3	751.5	737.8	728.7	724.2	719.6	715.1	710.5
55°	684.4	670.8	657.1	647.8	643.0	638.1	633.3	628.4
57.5°	603.5	590.2	576.8	567.9	563.7	559.4	555.0	550.8
60°	550.0	536.6	523.3	514.4	509.9	505.3	500.8	496.2
62.5°	497.5	485.0	472.7	464.2	459.7	455.1	450.6	446.1
65°	420.2	408.1	396.0	387.6	383.0	378.5	374.0	369.4
67.5°	346.5	335.4	324.3	316.9	313.3	309.6	306.0	302.4
70°	297.5	288.1	278.7	272.2	268.5	264.9	261.3	257.6
72.5°	252.1	243.4	234.7	229.1	226.7	224.3	221.9	219.4
75°	188.4	181.8	175.1	170.7	168.5	166.4	164.3	162.2
77.5°	134.1	129.5	124.7	121.6	120.1	118.5	116.9	115.3
80°	100.9	98.2	95.4	93.7	93.1	92.5	91.9	91.3
82.5°	75.4	74.1	72.9	72.1	71.7	71.3	71.0	70.6
85°	43.0	42.7	42.4	42.1	41.8	41.5	41.2	40.9
87.5°	18.1	18.2	18.3	18.2	18.0	17.9	17.7	17.5
90°	8.4	8.9	9.4	9.8	10.1	10.4	10.7	11.0
92.5°	18.9	19.6	20.3	20.7	20.9	21.1	21.4	21.6
95°	36.7	37.4	38.1	38.6	38.8	39.0	39.2	39.4
97.5°	57.5	58.2	58.8	59.2	59.3	59.5	59.6	59.7
100°	71.9	72.8	73.7	74.2	74.4	74.6	74.8	75.0
102.5°	86.6	87.7	88.7	89.3	89.6	89.9	90.2	90.5
105°	110.6	111.2	111.8	112.3	112.6	112.9	113.2	113.5
107.5°	136.4	136.7	137.0	137.2	137.2	137.1	137.1	137.1
110°	154.4	154.7	155.0	155.1	155.0	154.9	154.8	154.7





TEST NUMBER: P333703-840

CATALOG NUMBER: S125RDIW-S1090D470U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	172.4	172.5	172.7	172.7	172.5	172.3	172.1	171.9
115°	199.9	199.8	199.7	199.5	199.4	199.3	199.2	199.1
117.5°	227.3	227.3	227.4	227.3	226.9	226.5	226.0	225.6
120°	245.8	245.8	245.8	245.6	245.2	244.8	244.4	244.0
122.5°	264.0	263.9	263.8	263.6	263.3	263.0	262.6	262.3
125°	290.7	290.5	290.3	290.1	290.0	289.9	289.8	289.7
127.5°	317.3	317.2	317.1	316.9	316.7	316.5	316.3	316.1
130°	334.9	334.8	334.7	334.5	334.3	334.1	333.9	333.7
132.5°	351.6	351.5	351.4	351.3	351.0	350.7	350.4	350.1
135°	377.6	377.6	377.6	377.4	377.0	376.6	376.2	375.8
137.5°	402.8	402.9	403.1	402.9	402.4	401.9	401.3	400.8
140°	418.8	419.0	419.2	419.0	418.5	418.0	417.5	417.0
142.5°	434.3	434.4	434.5	434.3	433.8	433.3	432.8	432.3
145°	456.8	456.8	456.8	456.7	456.4	456.1	455.8	455.4
147.5°	477.6	477.9	478.1	477.9	477.2	476.5	475.7	475.1
150°	490.7	490.7	490.7	490.6	490.4	490.2	490.0	489.8
152.5°	502.9	503.1	503.3	503.3	502.9	502.6	502.2	501.8
155°	520.3	520.7	521.1	521.1	520.6	520.1	519.6	519.1
157.5°	535.4	535.8	536.2	536.1	535.4	534.7	534.1	533.4
160°	544.6	545.0	545.4	545.3	544.8	544.3	543.8	543.3
162.5°	553.2	553.6	554.1	554.1	553.5	552.9	552.3	551.7
165°	564.7	565.1	565.5	565.4	564.8	564.2	563.6	563.0
167.5°	573.3	573.9	574.5	574.5	573.8	573.2	572.6	572.0
170°	578.3	579.0	579.7	579.6	578.9	578.1	577.4	576.7
172.5°	582.1	582.7	583.3	583.3	582.6	582.0	581.4	580.8
175°	586.1	586.8	587.4	587.3	586.6	585.9	585.2	584.5
177.5°	588.0	588.5	589.1	589.0	588.4	587.8	587.2	586.7
180°	588.1	588.1	588.1	588.1	588.1	588.1	588.1	588.1

(END OF REPORT)