

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333653-840

Luminaire Tested: **S125RDIW-S375D1340U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333653-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1340U840-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6173.5 lumens  
Efficiency: N/A  
Efficacy: 132.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - 90°-270°    - · - 135°-315°



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	53	47	62	54	47	42	42	37	34	31	28	26	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	20	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3672	3672	3672	3672
5°	4224	3676	3247	3676
10°	4845	3657	2865	3657
15°	5233	3620	2546	3620
20°	5770	3577	2351	3577
25°	6678	3518	2182	3518
30°	7267	3457	2071	3457
35°	6130	3387	1968	3387
40°	4281	3260	1881	3260
45°	3176	3088	1795	3088
50°	2533	2910	1721	2910
55°	2149	2688	1655	2688
60°	1856	2490	1550	2490
65°	1655	2275	1334	2275
70°	1456	2085	1216	2085
75°	1258	1804	1140	1804
80°	956	1517	956	1517
85°	793	1193	897	1193



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	0.9
10°-20°	159.7	2.6
20°-30°	253.3	4.1
30°-40°	305.4	4.9
40°-50°	272.8	4.4
50°-60°	209.2	3.4
60°-70°	135.9	2.2
70°-80°	66.1	1.1
80°-90°	19.5	0.3
90°-100°	112.7	1.8
100°-110°	332.9	5.4
110°-120°	563.9	9.1
120°-130°	742.1	12.0
130°-140°	831.6	13.5
140°-150°	815.0	13.2
150°-160°	684.5	11.1
160°-170°	455.0	7.4
170°-180°	159.2	2.6
0°-30°	467.5	7.6
0°-40°	773.0	12.5
0°-60°	1254.9	20.3
0°-90°	1476.4	23.9
90°-120°	1009.6	16.4
90°-150°	3398.3	55.0
90°-180°	4697.0	76.1
0°-180°	6173.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	652	567	501	567	652	65
15°	783	541	381	541	783	224
25°	937	494	306	494	937	430
35°	778	430	250	430	778	470
45°	348	338	196	338	348	277
55°	191	239	147	239	191	173
65°	108	149	87	149	108	108
75°	50	72	46	72	50	54
85°	11	16	12	16	11	13
90°	31	1	31	1	31	18
95°	113	85	113	85	113	115
105°	325	299	325	299	325	344
115°	570	565	570	565	570	564
125°	829	824	829	824	829	740
135°	1076	1072	1076	1072	1076	830
145°	1303	1298	1303	1298	1303	814
155°	1486	1486	1486	1486	1486	684
165°	1611	1615	1611	1615	1611	454
175°	1673	1679	1673	1679	1673	159
180°	1683	1683	1683	1683	1683	



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	597.9	597.5	598.3	596.2	596.4	593.3	593.3	590.9	587.6	585.2	584.1
5°	651.5	652.0	651.1	647.5	645.2	641.7	637.7	630.8	624.9	619.2	614.9
7.5°	706.7	707.0	703.9	702.9	696.9	692.7	683.9	674.3	665.9	655.1	646.9
10°	738.8	738.5	735.3	732.7	727.6	721.0	712.4	701.3	690.7	679.0	667.8
12.5°	757.4	756.8	755.8	752.7	747.9	742.1	734.8	723.8	710.8	698.1	685.0
15°	782.6	781.0	778.0	774.0	767.2	760.4	752.3	742.6	730.1	715.7	703.6
17.5°	813.9	813.9	809.2	803.7	794.5	782.5	769.9	754.2	737.3	721.4	708.5
20°	839.6	838.9	834.2	823.4	812.9	798.0	783.6	764.2	743.7	722.9	706.8
22.5°	876.6	874.7	869.9	855.8	839.5	820.2	798.1	774.5	749.6	726.1	704.9
25°	937.2	935.7	926.1	909.8	887.0	857.3	828.4	796.0	760.2	729.2	703.6
27.5°	978.6	977.0	969.9	956.3	935.2	904.0	864.9	821.5	777.0	734.3	697.3
30°	974.4	978.0	977.0	970.7	954.8	926.9	890.7	841.9	788.9	738.8	694.7
32.5°	915.8	919.0	927.2	939.6	940.5	929.3	902.2	857.2	802.3	745.3	692.6
35°	777.5	781.7	797.6	822.5	855.3	882.5	888.1	863.8	814.6	753.3	689.5
37.5°	597.7	620.7	634.1	660.4	709.7	759.9	808.2	826.0	805.1	749.9	684.6
40°	507.8	513.3	537.1	566.8	608.3	660.6	729.4	779.1	780.7	742.6	676.7
42.5°	434.5	441.7	458.0	481.7	517.3	569.5	640.6	706.2	736.5	722.0	666.4
45°	347.7	353.0	365.0	383.1	410.4	453.6	514.7	590.6	650.8	674.4	638.9
47.5°	285.6	288.5	298.8	312.8	333.0	364.4	411.7	477.6	549.8	600.4	595.4
50°	252.1	255.3	263.2	273.7	290.7	317.3	355.2	410.0	484.4	546.2	558.7
52.5°	225.9	228.6	233.6	243.5	257.5	277.9	308.5	358.1	425.1	490.8	519.5
55°	190.9	192.8	196.7	202.3	213.5	228.2	254.6	288.9	343.1	409.3	451.3
57.5°	162.1	163.0	165.5	170.7	178.4	189.1	208.2	237.2	276.1	335.8	382.1
60°	143.7	144.7	147.9	151.5	157.5	167.3	182.3	202.6	239.8	289.1	336.0
62.5°	129.2	129.8	131.2	134.6	140.0	147.5	159.3	175.8	205.5	248.8	293.1
65°	108.3	108.5	109.0	111.8	115.0	120.7	128.4	140.0	162.4	195.1	234.3
67.5°	88.2	88.6	90.2	91.2	94.5	97.5	102.0	110.9	126.7	148.8	179.3
70°	77.1	76.7	78.4	79.6	80.7	84.2	87.3	94.5	104.3	121.1	146.5
72.5°	66.6	65.9	66.7	67.1	68.6	71.0	74.0	78.5	86.0	97.6	117.0
75°	50.4	50.6	50.6	51.1	52.3	53.2	54.1	56.5	60.7	68.4	78.9
77.5°	35.3	35.0	36.0	36.2	36.9	37.9	38.7	39.6	41.3	44.4	49.9
80°	25.7	25.7	25.9	26.6	26.4	26.9	28.0	29.0	31.0	32.9	34.7
82.5°	19.7	19.5	19.7	19.9	19.8	20.3	20.7	20.9	21.7	22.6	23.9
85°	10.7	10.7	11.0	11.0	11.2	11.2	11.4	11.4	11.4	11.7	11.9
87.5°	10.4	10.0	9.7	9.5	9.5	9.7	9.2	8.7	8.4	8.1	7.9
90°	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8	22.4	21.0	18.9
92.5°	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1	52.2	50.3	47.8
95°	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9	102.9	100.9	98.0
97.5°	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4	162.5	160.6	156.6
100°	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7	203.1	200.5	196.6
102.5°	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0	245.2	242.4	240.4
105°	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6	314.9	313.1	311.3
107.5°	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5	389.7	388.8	387.5
110°	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9	441.0	440.1	439.3



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3	492.9	492.5	491.4
115°	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9	572.2	572.5	571.9
117.5°	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5	650.3	650.1	649.4
120°	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5	703.5	703.5	703.2
122.5°	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4	755.6	755.9	755.1
125°	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9	832.5	833.1	832.8
127.5°	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0	908.3	908.6	908.3
130°	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3	958.6	958.9	958.3
132.5°	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5	1006.8	1007.1	1007.2
135°	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8	1080.8	1080.8	1080.5
137.5°	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0	1152.6	1152.3	1151.7
140°	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5	1197.9	1197.3	1196.4
142.5°	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0	1242.7	1242.3	1241.2
145°	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4	1307.4	1307.4	1306.5
147.5°	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9	1366.2	1365.5	1364.8
150°	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3	1404.3	1404.3	1403.1
152.5°	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2	1438.6	1437.8	1437.3
155°	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1	1487.9	1486.8	1486.5
157.5°	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4	1531.2	1530.0	1529.7
160°	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5	1557.4	1556.2	1555.9
162.5°	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2	1581.8	1580.3	1580.2
165°	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2	1615.1	1613.9	1613.6
167.5°	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7	1638.9	1637.2	1637.2
170°	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4	1653.7	1651.8	1651.8
172.5°	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9	1664.1	1662.3	1662.3
175°	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6	1675.9	1674.2	1674.2
177.5°	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9	1681.5	1680.1	1680.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	584.1	582.8	580.4	578.1	575.3	572.9	571.2	569.2	566.5	563.4	560.8
5°	610.0	604.8	598.0	592.2	584.7	579.0	572.9	567.0	561.2	553.7	547.1
7.5°	638.6	628.0	617.7	604.7	593.0	582.5	572.4	562.2	552.2	541.6	531.4
10°	656.2	643.3	629.1	612.8	597.8	583.6	570.6	557.6	544.1	532.3	519.5
12.5°	672.6	656.0	639.7	619.1	601.2	583.8	567.1	551.2	536.7	521.3	507.5
15°	687.4	671.1	652.9	627.7	602.7	581.7	562.1	541.4	523.4	506.1	490.7
17.5°	693.2	676.0	654.9	630.7	603.4	576.9	551.7	529.0	507.8	487.7	470.4
20°	690.9	674.4	652.7	629.5	600.4	572.9	545.5	520.4	496.8	475.5	457.2
22.5°	685.5	668.4	647.4	623.0	595.3	566.1	536.9	510.1	485.4	463.4	443.3
25°	677.4	654.1	632.6	608.7	582.4	553.5	523.4	493.7	467.4	444.9	423.0
27.5°	668.9	639.9	612.5	588.9	561.0	535.2	506.1	475.7	448.1	425.3	402.7
30°	661.3	628.6	598.5	571.7	545.3	520.8	493.3	463.6	435.2	411.6	388.8
32.5°	651.8	617.0	584.0	553.0	527.6	503.3	478.4	450.0	422.3	398.0	374.8
35°	639.9	595.5	559.6	526.6	498.5	474.8	452.4	429.6	401.8	376.6	354.0
37.5°	624.2	573.8	532.3	496.4	466.7	443.0	425.3	404.3	379.0	355.0	334.0
40°	614.6	558.2	512.7	477.2	446.0	420.9	404.3	386.7	363.6	340.9	319.9
42.5°	602.0	543.8	492.9	456.0	424.4	400.4	383.6	368.2	348.8	327.5	305.0
45°	577.0	515.9	462.5	422.8	391.1	367.5	351.8	338.1	323.5	303.8	284.2
47.5°	544.7	486.9	430.9	387.6	356.6	334.7	319.5	308.6	298.1	281.4	262.5
50°	518.8	462.9	408.4	366.4	333.3	312.5	298.2	289.6	280.0	264.9	248.9
52.5°	488.1	438.3	384.9	341.9	310.6	291.1	277.5	268.8	260.9	248.6	233.5
55°	439.9	396.2	347.2	308.2	279.5	259.9	246.9	238.7	234.1	223.6	211.7
57.5°	384.2	352.9	309.7	272.2	246.7	227.4	217.8	210.9	205.6	198.1	189.8
60°	345.4	323.5	284.7	248.9	225.6	207.2	198.5	192.8	187.8	181.6	175.0
62.5°	306.0	290.0	256.3	225.6	204.2	188.7	180.7	175.4	169.8	165.5	159.2
65°	253.2	238.9	215.6	191.6	171.8	159.4	153.5	148.9	145.4	140.7	136.2
67.5°	196.9	191.2	175.0	158.4	144.2	133.2	128.2	124.9	120.8	118.0	114.9
70°	162.4	159.6	148.1	137.2	123.9	116.4	111.8	110.4	105.2	102.4	100.4
72.5°	131.8	130.5	123.9	116.3	106.9	100.4	96.1	94.5	91.2	89.0	87.7
75°	90.3	90.8	89.6	84.7	81.2	77.1	73.3	72.3	70.0	68.2	67.0
77.5°	57.2	59.5	59.6	59.4	58.0	55.4	53.8	53.1	50.9	50.2	49.9
80°	39.2	41.8	44.1	43.8	43.4	42.7	41.5	40.8	39.7	39.0	38.5
82.5°	26.2	28.5	30.5	31.7	31.6	30.9	30.2	29.8	29.6	29.1	29.0
85°	12.3	12.8	13.5	15.1	16.4	16.6	16.4	16.1	15.5	15.7	15.9
87.5°	7.7	7.3	7.1	6.6	6.0	6.5	6.6	6.3	6.4	6.5	6.5
90°	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3	3.6	6.0	8.3
92.5°	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7	33.3	34.9	36.6
95°	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1	85.7	86.3	86.8
97.5°	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5	141.7	142.0	142.2
100°	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.4
102.5°	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4	229.6	230.8	232.0
105°	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7	300.1	301.5	303.1
107.5°	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2	377.7	379.1	380.6
110°	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7	431.1	432.6	434.0





TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1	484.9	485.6	486.5
115°	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6	565.7	566.9	568.0
117.5°	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3	645.8	646.3	646.8
120°	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6	697.0	698.5	699.9
122.5°	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1	750.6	751.1	751.6
125°	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9	825.7	827.5	829.2
127.5°	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5	903.5	904.5	905.5
130°	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7	951.2	952.6	954.1
132.5°	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8	999.3	1001.7	1004.0
135°	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6	1073.3	1075.0	1076.8
137.5°	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8	1143.5	1145.2	1146.8
140°	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8	1188.3	1189.7	1191.2
142.5°	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9	1233.1	1234.4	1235.6
145°	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2	1299.3	1300.5	1301.6
147.5°	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5	1360.1	1360.8	1361.4
150°	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4	1400.1	1399.8	1399.5
152.5°	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9	1434.3	1434.7	1435.1
155°	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6	1531.0	1530.3	1529.6
160°	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8	1558.0	1557.1	1556.2
162.5°	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0	1582.4	1581.7	1581.0
165°	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2	1614.6	1614.0	1613.5
167.5°	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4	1641.2	1640.1	1638.9
170°	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1	1656.0	1654.8	1653.7
172.5°	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6	1666.4	1665.3	1664.1
175°	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4	1678.2	1677.1	1675.9
177.5°	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4	1684.5	1683.5	1682.6
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	558.9	556.3	554.4	550.7	548.1	546.9	544.9	544.3	546.4	544.9	544.7
5°	542.3	535.5	530.2	524.8	519.0	515.2	509.6	508.7	507.3	505.2	504.7
7.5°	522.4	513.5	506.6	497.8	490.1	483.8	476.9	473.5	471.7	469.0	465.3
10°	509.0	498.5	489.1	480.2	470.7	462.9	456.0	450.6	447.1	443.8	442.4
12.5°	495.6	484.9	473.0	462.3	451.6	443.0	435.3	431.7	427.9	424.0	420.8
15°	475.0	460.9	447.8	435.5	426.4	417.0	409.5	404.3	398.6	396.9	390.6
17.5°	453.2	439.3	423.9	411.0	400.4	390.1	381.9	376.1	371.7	365.7	362.8
20°	439.6	423.0	408.1	396.2	384.6	372.4	364.1	359.1	355.0	350.0	347.7
22.5°	425.1	408.9	393.5	379.6	367.8	355.8	349.8	344.8	340.0	335.5	332.3
25°	403.6	387.4	371.2	356.8	344.5	335.8	328.8	323.0	320.4	316.0	312.7
27.5°	382.5	365.2	348.5	334.1	324.4	315.8	310.0	305.5	300.8	297.0	294.1
30°	368.9	351.2	333.0	321.5	311.2	303.2	296.8	292.4	288.9	285.4	283.3
32.5°	355.3	337.0	320.8	308.5	298.8	291.8	285.3	280.9	277.3	273.5	270.9
35°	333.5	314.8	301.7	289.6	280.0	273.5	269.0	263.0	259.9	257.1	254.6
37.5°	313.2	295.8	281.7	271.0	262.7	256.2	250.4	247.2	243.5	241.0	238.8
40°	298.2	282.4	269.5	258.3	252.3	245.0	239.6	235.4	232.7	229.3	227.0
42.5°	284.8	270.0	257.5	247.5	239.9	233.8	228.6	224.4	220.9	218.5	216.6
45°	265.8	251.1	238.9	229.6	222.6	216.8	211.4	209.3	204.6	201.9	200.9
47.5°	246.1	233.0	221.3	212.7	205.5	200.0	194.9	190.7	188.0	185.3	183.8
50°	232.9	220.3	209.3	200.9	193.9	187.8	183.2	180.4	176.8	174.3	172.5
52.5°	219.6	207.9	197.0	188.9	182.9	176.8	171.6	168.8	165.5	163.9	162.6
55°	200.7	188.3	178.9	171.1	164.7	159.2	154.2	151.5	149.4	147.7	147.2
57.5°	179.3	169.5	160.8	153.6	147.0	141.8	137.4	134.8	133.0	132.7	131.3
60°	165.2	156.3	148.5	140.7	135.1	130.2	126.4	123.4	121.6	121.4	120.9
62.5°	151.2	142.7	135.3	128.6	123.5	118.9	115.2	111.9	110.8	109.6	108.6
65°	130.5	122.7	116.6	111.3	105.9	102.0	98.5	96.3	93.8	92.4	89.9
67.5°	110.1	104.1	98.3	93.7	89.5	85.7	82.8	79.7	78.0	76.9	75.0
70°	96.6	91.9	86.1	81.2	78.0	74.9	72.6	69.1	67.9	67.0	66.0
72.5°	83.9	79.8	74.9	70.9	67.7	64.8	62.1	60.5	59.3	58.4	57.9
75°	66.0	62.1	57.9	55.0	52.7	50.4	49.0	47.9	47.4	47.2	46.3
77.5°	48.5	46.4	43.0	40.8	39.3	38.3	37.1	36.5	36.4	35.3	35.0
80°	37.1	36.0	33.1	32.2	31.0	30.1	29.4	28.3	27.1	26.6	25.9
82.5°	27.6	26.5	25.2	23.8	22.8	22.2	21.6	21.1	21.3	20.6	20.3
85°	14.7	13.5	13.0	12.8	12.3	12.8	12.6	12.3	12.1	11.9	12.1
87.5°	6.8	7.3	7.5	8.2	8.1	8.7	9.0	9.1	9.4	9.7	9.7
90°	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8	25.3	26.8	28.0
92.5°	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1	56.0	58.0	59.3
95°	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9	106.9	109.1	110.3
97.5°	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4	166.3	168.2	169.5
100°	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7	208.2	210.9	212.5
102.5°	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0	250.9	253.8	255.6
105°	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6	318.3	320.0	321.3
107.5°	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5	391.4	392.3	392.7
110°	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9	442.7	443.6	443.9



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3	493.7	494.1	494.1
115°	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9	571.6	571.3	571.0
117.5°	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5	650.7	651.0	650.5
120°	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5	703.5	703.5	702.9
122.5°	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4	755.2	754.9	754.4
125°	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9	831.4	830.8	830.4
127.5°	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0	907.7	907.5	907.0
130°	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3	958.1	957.8	957.3
132.5°	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5	1006.2	1005.9	1005.4
135°	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8	1080.8	1080.8	1080.2
137.5°	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0	1153.3	1153.7	1153.1
140°	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5	1199.0	1199.6	1199.2
142.5°	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0	1243.4	1243.7	1243.2
145°	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4	1307.4	1307.4	1306.9
147.5°	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9	1367.6	1368.3	1367.7
150°	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3	1404.3	1404.3	1404.0
152.5°	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2	1439.9	1440.6	1440.5
155°	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1	1490.3	1491.5	1491.3
157.5°	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4	1533.5	1534.7	1534.3
160°	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5	1559.7	1560.8	1560.7
162.5°	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2	1584.5	1585.9	1585.8
165°	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2	1617.4	1618.5	1618.2
167.5°	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7	1642.4	1644.2	1644.2
170°	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4	1657.1	1658.8	1658.7
172.5°	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9	1667.6	1669.3	1669.3
175°	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6	1679.4	1681.1	1680.9
177.5°	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9	1684.4	1685.8	1685.7
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.5	542.5	541.9	542.7	541.9	542.5	544.5	544.7	544.9	546.4	544.3
5°	502.4	500.1	501.2	500.8	501.2	500.1	502.4	504.7	505.2	507.3	508.7
7.5°	465.3	462.4	459.4	460.3	459.4	462.4	465.3	465.3	469.0	471.7	473.5
10°	439.4	437.1	435.7	436.9	435.7	437.1	439.4	442.4	443.8	447.1	450.6
12.5°	417.6	416.2	415.0	414.4	415.0	416.2	417.6	420.8	424.0	427.9	431.7
15°	387.8	385.1	383.8	380.8	383.8	385.1	387.8	390.6	396.9	398.6	404.3
17.5°	360.4	359.5	356.5	355.2	356.5	359.5	360.4	362.8	365.7	371.7	376.1
20°	344.2	343.3	340.2	342.0	340.2	343.3	344.2	347.7	350.0	355.0	359.1
22.5°	330.7	328.7	327.7	327.2	327.7	328.7	330.7	332.3	335.5	340.0	344.8
25°	311.7	308.7	307.5	306.2	307.5	308.7	311.7	312.7	316.0	320.4	323.0
27.5°	292.8	291.1	289.6	289.2	289.6	291.1	292.8	294.1	297.0	300.8	305.5
30°	280.4	278.8	277.7	277.7	277.7	278.8	280.4	283.3	285.4	288.9	292.4
32.5°	269.4	268.2	267.0	266.8	267.0	268.2	269.4	270.9	273.5	277.3	280.9
35°	253.4	251.6	251.1	249.6	251.1	251.6	253.4	254.6	257.1	259.9	263.0
37.5°	236.7	235.2	235.2	235.0	235.2	235.2	236.7	238.8	241.0	243.5	247.2
40°	226.1	224.9	224.7	223.1	224.7	224.9	226.1	227.0	229.3	232.7	235.4
42.5°	214.7	214.1	213.3	212.6	213.3	214.1	214.7	216.6	218.5	220.9	224.4
45°	199.2	197.6	197.6	196.5	197.6	197.6	199.2	200.9	201.9	204.6	209.3
47.5°	183.3	182.1	182.2	181.0	182.2	182.1	183.3	183.8	185.3	188.0	190.7
50°	172.7	172.0	171.8	171.3	171.8	172.0	172.7	172.5	174.3	176.8	180.4
52.5°	162.1	161.7	162.6	161.6	162.6	161.7	162.1	162.6	163.9	165.5	168.8
55°	147.7	147.0	148.5	147.0	148.5	147.0	147.7	147.2	147.7	149.4	151.5
57.5°	131.3	130.6	131.9	131.2	131.9	130.6	131.3	131.3	132.7	133.0	134.8
60°	120.4	119.0	119.7	120.0	119.7	119.0	120.4	120.9	121.4	121.6	123.4
62.5°	107.6	106.6	107.2	106.1	107.2	106.6	107.6	108.6	109.6	110.8	111.9
65°	89.4	88.7	87.8	87.3	87.8	88.7	89.4	89.9	92.4	93.8	96.3
67.5°	75.1	73.4	73.3	73.7	73.3	73.4	75.1	75.0	76.9	78.0	79.7
70°	64.6	64.6	64.4	64.4	64.4	64.6	64.6	66.0	67.0	67.9	69.1
72.5°	57.4	57.2	56.8	56.6	56.8	57.2	57.4	57.9	58.4	59.3	60.5
75°	46.3	46.5	45.9	45.7	45.9	46.5	46.3	46.3	47.2	47.4	47.9
77.5°	34.1	33.1	33.6	33.1	33.6	33.1	34.1	35.0	35.3	36.4	36.5
80°	25.9	25.7	26.4	25.7	26.4	25.7	25.9	25.9	26.6	27.1	28.3
82.5°	20.5	20.3	20.6	20.1	20.6	20.3	20.5	20.3	20.6	21.3	21.1
85°	12.3	12.1	11.9	12.1	11.9	12.1	12.3	12.1	11.9	12.1	12.3
87.5°	10.1	10.0	10.2	10.4	10.2	10.0	10.1	9.7	9.7	9.4	9.1
90°	28.8	29.7	30.6	31.4	30.6	29.7	28.8	28.0	26.8	25.3	23.8
92.5°	59.9	60.6	61.2	61.8	61.2	60.6	59.9	59.3	58.0	56.0	54.1
95°	110.9	111.5	112.1	112.7	112.1	111.5	110.9	110.3	109.1	106.9	104.9
97.5°	169.8	170.2	170.5	170.9	170.5	170.2	169.8	169.5	168.2	166.3	164.4
100°	213.1	213.7	214.3	214.8	214.3	213.7	213.1	212.5	210.9	208.2	205.7
102.5°	256.4	257.2	258.0	258.8	258.0	257.2	256.4	255.6	253.8	250.9	248.0
105°	322.2	323.2	324.0	324.9	324.0	323.2	322.2	321.3	320.0	318.3	316.6
107.5°	392.6	392.5	392.5	392.4	392.5	392.5	392.6	392.7	392.3	391.4	390.5
110°	443.6	443.3	443.0	442.7	443.0	443.3	443.6	443.9	443.6	442.7	441.9



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	493.6	493.1	492.5	492.0	492.5	493.1	493.6	494.1	494.1	493.7	493.3
115°	570.7	570.4	570.2	569.9	570.2	570.4	570.7	571.0	571.3	571.6	571.9
117.5°	649.3	648.1	647.0	645.8	647.0	648.1	649.3	650.5	651.0	650.7	650.5
120°	701.7	700.5	699.3	698.2	699.3	700.5	701.7	702.9	703.5	703.5	703.5
122.5°	753.4	752.5	751.5	750.6	751.5	752.5	753.4	754.4	754.9	755.2	755.4
125°	830.1	829.8	829.5	829.2	829.5	829.8	830.1	830.4	830.8	831.4	831.9
127.5°	906.5	905.8	905.2	904.6	905.2	905.8	906.5	907.0	907.5	907.7	908.0
130°	956.7	956.1	955.5	954.9	955.5	956.1	956.7	957.3	957.8	958.1	958.3
132.5°	1004.6	1003.7	1002.9	1002.1	1002.9	1003.7	1004.6	1005.4	1005.9	1006.2	1006.5
135°	1078.9	1077.8	1076.6	1075.5	1076.6	1077.8	1078.9	1080.2	1080.8	1080.8	1080.8
137.5°	1151.7	1150.1	1148.7	1147.3	1148.7	1150.1	1151.7	1153.1	1153.7	1153.3	1153.0
140°	1197.7	1196.3	1194.9	1193.4	1194.9	1196.3	1197.7	1199.2	1199.6	1199.0	1198.5
142.5°	1241.7	1240.3	1238.8	1237.4	1238.8	1240.3	1241.7	1243.2	1243.7	1243.4	1243.0
145°	1306.1	1305.1	1304.2	1303.4	1304.2	1305.1	1306.1	1306.9	1307.4	1307.4	1307.4
147.5°	1365.6	1363.7	1361.7	1359.8	1361.7	1363.7	1365.6	1367.7	1368.3	1367.6	1366.9
150°	1403.4	1402.8	1402.2	1401.7	1402.2	1402.8	1403.4	1404.0	1404.3	1404.3	1404.3
152.5°	1439.4	1438.4	1437.2	1436.2	1437.2	1438.4	1439.4	1440.5	1440.6	1439.9	1439.2
155°	1489.9	1488.4	1486.9	1485.5	1486.9	1488.4	1489.9	1491.3	1491.5	1490.3	1489.1
157.5°	1532.4	1530.5	1528.5	1526.6	1528.5	1530.5	1532.4	1534.3	1534.7	1533.5	1532.4
160°	1559.3	1557.8	1556.4	1554.9	1556.4	1557.8	1559.3	1560.7	1560.8	1559.7	1558.5
162.5°	1584.1	1582.4	1580.7	1579.0	1580.7	1582.4	1584.1	1585.8	1585.9	1584.5	1583.2
165°	1616.5	1614.8	1613.0	1611.2	1613.0	1614.8	1616.5	1618.2	1618.5	1617.4	1616.2
167.5°	1642.3	1640.5	1638.7	1636.9	1638.7	1640.5	1642.3	1644.2	1644.2	1642.4	1640.7
170°	1656.7	1654.7	1652.5	1650.5	1652.5	1654.7	1656.7	1658.7	1658.8	1657.1	1655.4
172.5°	1667.5	1665.7	1663.9	1662.0	1663.9	1665.7	1667.5	1669.3	1669.3	1667.6	1665.9
175°	1678.9	1676.9	1674.9	1672.8	1674.9	1676.9	1678.9	1680.9	1681.1	1679.4	1677.6
177.5°	1683.9	1682.3	1680.7	1679.1	1680.7	1682.3	1683.9	1685.7	1685.8	1684.4	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	544.9	546.9	548.1	550.7	554.4	556.3	558.9	560.8	563.4	566.5	569.2
5°	509.6	515.2	519.0	524.8	530.2	535.5	542.3	547.1	553.7	561.2	567.0
7.5°	476.9	483.8	490.1	497.8	506.6	513.5	522.4	531.4	541.6	552.2	562.2
10°	456.0	462.9	470.7	480.2	489.1	498.5	509.0	519.5	532.3	544.1	557.6
12.5°	435.3	443.0	451.6	462.3	473.0	484.9	495.6	507.5	521.3	536.7	551.2
15°	409.5	417.0	426.4	435.5	447.8	460.9	475.0	490.7	506.1	523.4	541.4
17.5°	381.9	390.1	400.4	411.0	423.9	439.3	453.2	470.4	487.7	507.8	529.0
20°	364.1	372.4	384.6	396.2	408.1	423.0	439.6	457.2	475.5	496.8	520.4
22.5°	349.8	355.8	367.8	379.6	393.5	408.9	425.1	443.3	463.4	485.4	510.1
25°	328.8	335.8	344.5	356.8	371.2	387.4	403.6	423.0	444.9	467.4	493.7
27.5°	310.0	315.8	324.4	334.1	348.5	365.2	382.5	402.7	425.3	448.1	475.7
30°	296.8	303.2	311.2	321.5	333.0	351.2	368.9	388.8	411.6	435.2	463.6
32.5°	285.3	291.8	298.8	308.5	320.8	337.0	355.3	374.8	398.0	422.3	450.0
35°	269.0	273.5	280.0	289.6	301.7	314.8	333.5	354.0	376.6	401.8	429.6
37.5°	250.4	256.2	262.7	271.0	281.7	295.8	313.2	334.0	355.0	379.0	404.3
40°	239.6	245.0	252.3	258.3	269.5	282.4	298.2	319.9	340.9	363.6	386.7
42.5°	228.6	233.8	239.9	247.5	257.5	270.0	284.8	305.0	327.5	348.8	368.2
45°	211.4	216.8	222.6	229.6	238.9	251.1	265.8	284.2	303.8	323.5	338.1
47.5°	194.9	200.0	205.5	212.7	221.3	233.0	246.1	262.5	281.4	298.1	308.6
50°	183.2	187.8	193.9	200.9	209.3	220.3	232.9	248.9	264.9	280.0	289.6
52.5°	171.6	176.8	182.9	188.9	197.0	207.9	219.6	233.5	248.6	260.9	268.8
55°	154.2	159.2	164.7	171.1	178.9	188.3	200.7	211.7	223.6	234.1	238.7
57.5°	137.4	141.8	147.0	153.6	160.8	169.5	179.3	189.8	198.1	205.6	210.9
60°	126.4	130.2	135.1	140.7	148.5	156.3	165.2	175.0	181.6	187.8	192.8
62.5°	115.2	118.9	123.5	128.6	135.3	142.7	151.2	159.2	165.5	169.8	175.4
65°	98.5	102.0	105.9	111.3	116.6	122.7	130.5	136.2	140.7	145.4	148.9
67.5°	82.8	85.7	89.5	93.7	98.3	104.1	110.1	114.9	118.0	120.8	124.9
70°	72.6	74.9	78.0	81.2	86.1	91.9	96.6	100.4	102.4	105.2	110.4
72.5°	62.1	64.8	67.7	70.9	74.9	79.8	83.9	87.7	89.0	91.2	94.5
75°	49.0	50.4	52.7	55.0	57.9	62.1	66.0	67.0	68.2	70.0	72.3
77.5°	37.1	38.3	39.3	40.8	43.0	46.4	48.5	49.9	50.2	50.9	53.1
80°	29.4	30.1	31.0	32.2	33.1	36.0	37.1	38.5	39.0	39.7	40.8
82.5°	21.6	22.2	22.8	23.8	25.2	26.5	27.6	29.0	29.1	29.6	29.8
85°	12.6	12.8	12.3	12.8	13.0	13.5	14.7	15.9	15.7	15.5	16.1
87.5°	9.0	8.7	8.1	8.2	7.5	7.3	6.8	6.5	6.5	6.4	6.3
90°	22.4	21.0	18.9	16.9	14.8	12.8	10.6	8.3	6.0	3.6	1.3
92.5°	52.2	50.3	47.8	45.3	42.8	40.3	38.2	36.6	34.9	33.3	31.7
95°	102.9	100.9	98.0	95.0	92.1	89.3	87.5	86.8	86.3	85.7	85.1
97.5°	162.5	160.6	156.6	152.6	148.6	144.5	142.4	142.2	142.0	141.7	141.5
100°	203.1	200.5	196.6	192.9	189.0	185.3	183.4	183.4	183.4	183.4	183.4
102.5°	245.2	242.4	240.4	238.5	236.6	234.7	233.1	232.0	230.8	229.6	228.4
105°	314.9	313.1	311.3	309.6	307.8	306.1	304.5	303.1	301.5	300.1	298.7
107.5°	389.7	388.8	387.5	386.1	384.8	383.4	382.0	380.6	379.1	377.7	376.2
110°	441.0	440.1	439.3	438.4	437.6	436.7	435.5	434.0	432.6	431.1	429.7



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	492.9	492.5	491.4	490.3	489.2	488.2	487.2	486.5	485.6	484.9	484.1
115°	572.2	572.5	571.9	571.3	570.7	570.2	569.3	568.0	566.9	565.7	564.6
117.5°	650.3	650.1	649.4	648.9	648.4	647.9	647.4	646.8	646.3	645.8	645.3
120°	703.5	703.5	703.2	702.9	702.6	702.3	701.5	699.9	698.5	697.0	695.6
122.5°	755.6	755.9	755.1	754.4	753.6	752.9	752.1	751.6	751.1	750.6	750.1
125°	832.5	833.1	832.8	832.5	832.2	831.9	830.9	829.2	827.5	825.7	823.9
127.5°	908.3	908.6	908.3	907.9	907.6	907.2	906.6	905.5	904.5	903.5	902.5
130°	958.6	958.9	958.3	957.8	957.2	956.5	955.5	954.1	952.6	951.2	949.7
132.5°	1006.8	1007.1	1007.2	1007.3	1007.4	1007.5	1006.4	1004.0	1001.7	999.3	996.8
135°	1080.8	1080.8	1080.5	1080.2	1079.8	1079.5	1078.5	1076.8	1075.0	1073.3	1071.6
137.5°	1152.6	1152.3	1151.7	1150.9	1150.3	1149.6	1148.5	1146.8	1145.2	1143.5	1141.8
140°	1197.9	1197.3	1196.4	1195.6	1194.7	1193.8	1192.7	1191.2	1189.7	1188.3	1186.8
142.5°	1242.7	1242.3	1241.2	1240.1	1239.0	1237.9	1236.8	1235.6	1234.4	1233.1	1231.9
145°	1307.4	1307.4	1306.5	1305.6	1304.7	1303.8	1302.8	1301.6	1300.5	1299.3	1298.2
147.5°	1366.2	1365.5	1364.8	1364.1	1363.4	1362.7	1362.0	1361.4	1360.8	1360.1	1359.5
150°	1404.3	1404.3	1403.1	1402.0	1400.8	1399.6	1399.2	1399.5	1399.8	1400.1	1400.4
152.5°	1438.6	1437.8	1437.3	1436.8	1436.4	1435.9	1435.5	1435.1	1434.7	1434.3	1433.9
155°	1487.9	1486.8	1486.5	1486.2	1485.9	1485.6	1485.5	1485.5	1485.5	1485.5	1485.5
157.5°	1531.2	1530.0	1529.7	1529.4	1529.1	1528.8	1529.0	1529.6	1530.3	1531.0	1531.6
160°	1557.4	1556.2	1555.9	1555.7	1555.4	1555.1	1555.4	1556.2	1557.1	1558.0	1558.8
162.5°	1581.8	1580.3	1580.2	1580.2	1580.1	1580.1	1580.4	1581.0	1581.7	1582.4	1583.0
165°	1615.1	1613.9	1613.6	1613.3	1613.0	1612.8	1612.9	1613.5	1614.0	1614.6	1615.2
167.5°	1638.9	1637.2	1637.2	1637.2	1637.2	1637.2	1637.8	1638.9	1640.1	1641.2	1642.4
170°	1653.7	1651.8	1651.8	1651.8	1651.8	1651.8	1652.4	1653.7	1654.8	1656.0	1657.1
172.5°	1664.1	1662.3	1662.3	1662.3	1662.3	1662.3	1662.9	1664.1	1665.3	1666.4	1667.6
175°	1675.9	1674.2	1674.2	1674.2	1674.2	1674.2	1674.8	1675.9	1677.1	1678.2	1679.4
177.5°	1681.5	1680.1	1680.4	1680.6	1680.8	1681.1	1681.6	1682.6	1683.5	1684.5	1685.4
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	571.2	572.9	575.3	578.1	580.4	582.8	584.1	584.1	585.2	587.6	590.9
5°	572.9	579.0	584.7	592.2	598.0	604.8	610.0	614.9	619.2	624.9	630.8
7.5°	572.4	582.5	593.0	604.7	617.7	628.0	638.6	646.9	655.1	665.9	674.3
10°	570.6	583.6	597.8	612.8	629.1	643.3	656.2	667.8	679.0	690.7	701.3
12.5°	567.1	583.8	601.2	619.1	639.7	656.0	672.6	685.0	698.1	710.8	723.8
15°	562.1	581.7	602.7	627.7	652.9	671.1	687.4	703.6	715.7	730.1	742.6
17.5°	551.7	576.9	603.4	630.7	654.9	676.0	693.2	708.5	721.4	737.3	754.2
20°	545.5	572.9	600.4	629.5	652.7	674.4	690.9	706.8	722.9	743.7	764.2
22.5°	536.9	566.1	595.3	623.0	647.4	668.4	685.5	704.9	726.1	749.6	774.5
25°	523.4	553.5	582.4	608.7	632.6	654.1	677.4	703.6	729.2	760.2	796.0
27.5°	506.1	535.2	561.0	588.9	612.5	639.9	668.9	697.3	734.3	777.0	821.5
30°	493.3	520.8	545.3	571.7	598.5	628.6	661.3	694.7	738.8	788.9	841.9
32.5°	478.4	503.3	527.6	553.0	584.0	617.0	651.8	692.6	745.3	802.3	857.2
35°	452.4	474.8	498.5	526.6	559.6	595.5	639.9	689.5	753.3	814.6	863.8
37.5°	425.3	443.0	466.7	496.4	532.3	573.8	624.2	684.6	749.9	805.1	826.0
40°	404.3	420.9	446.0	477.2	512.7	558.2	614.6	676.7	742.6	780.7	779.1
42.5°	383.6	400.4	424.4	456.0	492.9	543.8	602.0	666.4	722.0	736.5	706.2
45°	351.8	367.5	391.1	422.8	462.5	515.9	577.0	638.9	674.4	650.8	590.6
47.5°	319.5	334.7	356.6	387.6	430.9	486.9	544.7	595.4	600.4	549.8	477.6
50°	298.2	312.5	333.3	366.4	408.4	462.9	518.8	558.7	546.2	484.4	410.0
52.5°	277.5	291.1	310.6	341.9	384.9	438.3	488.1	519.5	490.8	425.1	358.1
55°	246.9	259.9	279.5	308.2	347.2	396.2	439.9	451.3	409.3	343.1	288.9
57.5°	217.8	227.4	246.7	272.2	309.7	352.9	384.2	382.1	335.8	276.1	237.2
60°	198.5	207.2	225.6	248.9	284.7	323.5	345.4	336.0	289.1	239.8	202.6
62.5°	180.7	188.7	204.2	225.6	256.3	290.0	306.0	293.1	248.8	205.5	175.8
65°	153.5	159.4	171.8	191.6	215.6	238.9	253.2	234.3	195.1	162.4	140.0
67.5°	128.2	133.2	144.2	158.4	175.0	191.2	196.9	179.3	148.8	126.7	110.9
70°	111.8	116.4	123.9	137.2	148.1	159.6	162.4	146.5	121.1	104.3	94.5
72.5°	96.1	100.4	106.9	116.3	123.9	130.5	131.8	117.0	97.6	86.0	78.5
75°	73.3	77.1	81.2	84.7	89.6	90.8	90.3	78.9	68.4	60.7	56.5
77.5°	53.8	55.4	58.0	59.4	59.6	59.5	57.2	49.9	44.4	41.3	39.6
80°	41.5	42.7	43.4	43.8	44.1	41.8	39.2	34.7	32.9	31.0	29.0
82.5°	30.2	30.9	31.6	31.7	30.5	28.5	26.2	23.9	22.6	21.7	20.9
85°	16.4	16.6	16.4	15.1	13.5	12.8	12.3	11.9	11.7	11.4	11.4
87.5°	6.6	6.5	6.0	6.6	7.1	7.3	7.7	7.9	8.1	8.4	8.7
90°	3.6	6.0	8.3	10.6	12.8	14.8	16.9	18.9	21.0	22.4	23.8
92.5°	33.3	34.9	36.6	38.2	40.3	42.8	45.3	47.8	50.3	52.2	54.1
95°	85.7	86.3	86.8	87.5	89.3	92.1	95.0	98.0	100.9	102.9	104.9
97.5°	141.7	142.0	142.2	142.4	144.5	148.6	152.6	156.6	160.6	162.5	164.4
100°	183.4	183.4	183.4	183.4	185.3	189.0	192.9	196.6	200.5	203.1	205.7
102.5°	229.6	230.8	232.0	233.1	234.7	236.6	238.5	240.4	242.4	245.2	248.0
105°	300.1	301.5	303.1	304.5	306.1	307.8	309.6	311.3	313.1	314.9	316.6
107.5°	377.7	379.1	380.6	382.0	383.4	384.8	386.1	387.5	388.8	389.7	390.5
110°	431.1	432.6	434.0	435.5	436.7	437.6	438.4	439.3	440.1	441.0	441.9





TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	485.6	486.5	487.2	488.2	489.2	490.3	491.4	492.5	492.9	493.3
115°	565.7	566.9	568.0	569.3	570.2	570.7	571.3	571.9	572.5	572.2	571.9
117.5°	645.8	646.3	646.8	647.4	647.9	648.4	648.9	649.4	650.1	650.3	650.5
120°	697.0	698.5	699.9	701.5	702.3	702.6	702.9	703.2	703.5	703.5	703.5
122.5°	750.6	751.1	751.6	752.1	752.9	753.6	754.4	755.1	755.9	755.6	755.4
125°	825.7	827.5	829.2	830.9	831.9	832.2	832.5	832.8	833.1	832.5	831.9
127.5°	903.5	904.5	905.5	906.6	907.2	907.6	907.9	908.3	908.6	908.3	908.0
130°	951.2	952.6	954.1	955.5	956.5	957.2	957.8	958.3	958.9	958.6	958.3
132.5°	999.3	1001.7	1004.0	1006.4	1007.5	1007.4	1007.3	1007.2	1007.1	1006.8	1006.5
135°	1073.3	1075.0	1076.8	1078.5	1079.5	1079.8	1080.2	1080.5	1080.8	1080.8	1080.8
137.5°	1143.5	1145.2	1146.8	1148.5	1149.6	1150.3	1150.9	1151.7	1152.3	1152.6	1153.0
140°	1188.3	1189.7	1191.2	1192.7	1193.8	1194.7	1195.6	1196.4	1197.3	1197.9	1198.5
142.5°	1233.1	1234.4	1235.6	1236.8	1237.9	1239.0	1240.1	1241.2	1242.3	1242.7	1243.0
145°	1299.3	1300.5	1301.6	1302.8	1303.8	1304.7	1305.6	1306.5	1307.4	1307.4	1307.4
147.5°	1360.1	1360.8	1361.4	1362.0	1362.7	1363.4	1364.1	1364.8	1365.5	1366.2	1366.9
150°	1400.1	1399.8	1399.5	1399.2	1399.6	1400.8	1402.0	1403.1	1404.3	1404.3	1404.3
152.5°	1434.3	1434.7	1435.1	1435.5	1435.9	1436.4	1436.8	1437.3	1437.8	1438.6	1439.2
155°	1485.5	1485.5	1485.5	1485.5	1485.6	1485.9	1486.2	1486.5	1486.8	1487.9	1489.1
157.5°	1531.0	1530.3	1529.6	1529.0	1528.8	1529.1	1529.4	1529.7	1530.0	1531.2	1532.4
160°	1558.0	1557.1	1556.2	1555.4	1555.1	1555.4	1555.7	1555.9	1556.2	1557.4	1558.5
162.5°	1582.4	1581.7	1581.0	1580.4	1580.1	1580.1	1580.2	1580.2	1580.3	1581.8	1583.2
165°	1614.6	1614.0	1613.5	1612.9	1612.8	1613.0	1613.3	1613.6	1613.9	1615.1	1616.2
167.5°	1641.2	1640.1	1638.9	1637.8	1637.2	1637.2	1637.2	1637.2	1637.2	1638.9	1640.7
170°	1656.0	1654.8	1653.7	1652.4	1651.8	1651.8	1651.8	1651.8	1651.8	1653.7	1655.4
172.5°	1666.4	1665.3	1664.1	1662.9	1662.3	1662.3	1662.3	1662.3	1662.3	1664.1	1665.9
175°	1678.2	1677.1	1675.9	1674.8	1674.2	1674.2	1674.2	1674.2	1674.2	1675.9	1677.6
177.5°	1684.5	1683.5	1682.6	1681.6	1681.1	1680.8	1680.6	1680.4	1680.1	1681.5	1682.9
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	593.3	593.3	596.4	596.2	598.3	597.5	597.9
5°	637.7	641.7	645.2	647.5	651.1	652.0	651.5
7.5°	683.9	692.7	696.9	702.9	703.9	707.0	706.7
10°	712.4	721.0	727.6	732.7	735.3	738.5	738.8
12.5°	734.8	742.1	747.9	752.7	755.8	756.8	757.4
15°	752.3	760.4	767.2	774.0	778.0	781.0	782.6
17.5°	769.9	782.5	794.5	803.7	809.2	813.9	813.9
20°	783.6	798.0	812.9	823.4	834.2	838.9	839.6
22.5°	798.1	820.2	839.5	855.8	869.9	874.7	876.6
25°	828.4	857.3	887.0	909.8	926.1	935.7	937.2
27.5°	864.9	904.0	935.2	956.3	969.9	977.0	978.6
30°	890.7	926.9	954.8	970.7	977.0	978.0	974.4
32.5°	902.2	929.3	940.5	939.6	927.2	919.0	915.8
35°	888.1	882.5	855.3	822.5	797.6	781.7	777.5
37.5°	808.2	759.9	709.7	660.4	634.1	620.7	597.7
40°	729.4	660.6	608.3	566.8	537.1	513.3	507.8
42.5°	640.6	569.5	517.3	481.7	458.0	441.7	434.5
45°	514.7	453.6	410.4	383.1	365.0	353.0	347.7
47.5°	411.7	364.4	333.0	312.8	298.8	288.5	285.6
50°	355.2	317.3	290.7	273.7	263.2	255.3	252.1
52.5°	308.5	277.9	257.5	243.5	233.6	228.6	225.9
55°	254.6	228.2	213.5	202.3	196.7	192.8	190.9
57.5°	208.2	189.1	178.4	170.7	165.5	163.0	162.1
60°	182.3	167.3	157.5	151.5	147.9	144.7	143.7
62.5°	159.3	147.5	140.0	134.6	131.2	129.8	129.2
65°	128.4	120.7	115.0	111.8	109.0	108.5	108.3
67.5°	102.0	97.5	94.5	91.2	90.2	88.6	88.2
70°	87.3	84.2	80.7	79.6	78.4	76.7	77.1
72.5°	74.0	71.0	68.6	67.1	66.7	65.9	66.6
75°	54.1	53.2	52.3	51.1	50.6	50.6	50.4
77.5°	38.7	37.9	36.9	36.2	36.0	35.0	35.3
80°	28.0	26.9	26.4	26.6	25.9	25.7	25.7
82.5°	20.7	20.3	19.8	19.9	19.7	19.5	19.7
85°	11.4	11.2	11.2	11.0	11.0	10.7	10.7
87.5°	9.2	9.7	9.5	9.5	9.7	10.0	10.4
90°	25.3	26.8	28.0	28.8	29.7	30.6	31.4
92.5°	56.0	58.0	59.3	59.9	60.6	61.2	61.8
95°	106.9	109.1	110.3	110.9	111.5	112.1	112.7
97.5°	166.3	168.2	169.5	169.8	170.2	170.5	170.9
100°	208.2	210.9	212.5	213.1	213.7	214.3	214.8
102.5°	250.9	253.8	255.6	256.4	257.2	258.0	258.8
105°	318.3	320.0	321.3	322.2	323.2	324.0	324.9
107.5°	391.4	392.3	392.7	392.6	392.5	392.5	392.4
110°	442.7	443.6	443.9	443.6	443.3	443.0	442.7



TEST NUMBER: P333653-840

CATALOG NUMBER: S125RDIW-S375D1340U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.7	494.1	494.1	493.6	493.1	492.5	492.0
115°	571.6	571.3	571.0	570.7	570.4	570.2	569.9
117.5°	650.7	651.0	650.5	649.3	648.1	647.0	645.8
120°	703.5	703.5	702.9	701.7	700.5	699.3	698.2
122.5°	755.2	754.9	754.4	753.4	752.5	751.5	750.6
125°	831.4	830.8	830.4	830.1	829.8	829.5	829.2
127.5°	907.7	907.5	907.0	906.5	905.8	905.2	904.6
130°	958.1	957.8	957.3	956.7	956.1	955.5	954.9
132.5°	1006.2	1005.9	1005.4	1004.6	1003.7	1002.9	1002.1
135°	1080.8	1080.8	1080.2	1078.9	1077.8	1076.6	1075.5
137.5°	1153.3	1153.7	1153.1	1151.7	1150.1	1148.7	1147.3
140°	1199.0	1199.6	1199.2	1197.7	1196.3	1194.9	1193.4
142.5°	1243.4	1243.7	1243.2	1241.7	1240.3	1238.8	1237.4
145°	1307.4	1307.4	1306.9	1306.1	1305.1	1304.2	1303.4
147.5°	1367.6	1368.3	1367.7	1365.6	1363.7	1361.7	1359.8
150°	1404.3	1404.3	1404.0	1403.4	1402.8	1402.2	1401.7
152.5°	1439.9	1440.6	1440.5	1439.4	1438.4	1437.2	1436.2
155°	1490.3	1491.5	1491.3	1489.9	1488.4	1486.9	1485.5
157.5°	1533.5	1534.7	1534.3	1532.4	1530.5	1528.5	1526.6
160°	1559.7	1560.8	1560.7	1559.3	1557.8	1556.4	1554.9
162.5°	1584.5	1585.9	1585.8	1584.1	1582.4	1580.7	1579.0
165°	1617.4	1618.5	1618.2	1616.5	1614.8	1613.0	1611.2
167.5°	1642.4	1644.2	1644.2	1642.3	1640.5	1638.7	1636.9
170°	1657.1	1658.8	1658.7	1656.7	1654.7	1652.5	1650.5
172.5°	1667.6	1669.3	1669.3	1667.5	1665.7	1663.9	1662.0
175°	1679.4	1681.1	1680.9	1678.9	1676.9	1674.9	1672.8
177.5°	1684.4	1685.8	1685.7	1683.9	1682.3	1680.7	1679.1
180°	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3	1683.3

(END OF REPORT)